

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333547-840

Luminaire Tested: **S125RDIP-S610D1205U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333547-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S610D1205U840-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1205 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7265.1 lumens
Efficiency: N/A
Efficacy: 147.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333547-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333547-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33
1	94	90	86	83	85	81	78	75	65	63	61	50	49	47	36	35	35	28
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	30	29	24
3	78	69	62	57	70	63	57	52	50	46	43	39	36	34	28	27	25	20
4	72	61	54	48	64	56	49	44	45	40	36	35	31	29	25	23	22	18
5	66	55	47	41	59	49	43	38	40	35	31	31	28	25	23	21	19	15
6	60	49	41	35	54	44	38	33	36	31	27	28	25	22	21	18	17	13
7	56	44	36	31	50	40	33	29	33	28	24	26	22	19	19	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	23	20	17	17	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	21	18	15	16	14	12	10
10	45	33	26	22	40	30	24	20	25	20	17	20	16	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6561	6561	6561
5°	6576	6501	6541
10°	6526	6441	6441
15°	6449	6310	6258
20°	6349	6128	6054
25°	6233	5949	5818
30°	6088	5739	5557
35°	5941	5523	5263
40°	5802	5298	4975
45°	5634	5045	4661
50°	5466	4772	4332
55°	5271	4510	3984
60°	5074	4193	3608
65°	4843	3822	3177
70°	4579	3361	2738
75°	4212	2832	2278
80°	3712	2228	1912
85°	3127	1815	1704



TEST NUMBER: P333547-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.5	1.3
10°-20°	267.0	3.7
20°-30°	387.1	5.3
30°-40°	441.2	6.1
40°-50°	430.0	5.9
50°-60°	362.0	5.0
60°-70°	253.8	3.5
70°-80°	130.4	1.8
80°-90°	36.2	0.5
90°-100°	57.5	0.8
100°-110°	354.6	4.9
110°-120°	643.1	8.9
120°-130°	825.3	11.4
130°-140°	887.7	12.2
140°-150°	833.2	11.5
150°-160°	674.0	9.3
160°-170°	435.9	6.0
170°-180°	150.4	2.1
0°-30°	749.6	10.3
0°-40°	1190.8	16.4
0°-60°	1982.8	27.3
0°-90°	2403.2	33.1
90°-120°	1055.2	14.5
90°-150°	3601.6	49.6
90°-180°	4862.0	66.9
0°-180°	7265.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1016	1016	1016	1016	1016	
5°	1014	1011	1003	1010	1009	96
15°	964	959	944	943	936	272
25°	875	862	835	825	816	402
35°	754	734	700	679	668	472
45°	617	594	552	523	510	476
55°	468	442	400	367	354	418
65°	317	290	250	220	208	314
75°	169	145	114	97	91	179
85°	42	29	24	24	23	47
90°	1	10	19	24	28	5
95°	67	61	19	24	25	85
105°	345	349	350	350	349	366
115°	648	654	655	650	643	642
125°	921	929	930	925	921	823
135°	1149	1156	1154	1151	1144	885
145°	1332	1334	1334	1335	1329	833
155°	1467	1461	1462	1465	1456	676
165°	1548	1542	1542	1548	1540	437
175°	1583	1577	1577	1586	1576	151
180°	1583	1583	1583	1583	1583	



TEST NUMBER: P333547-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9
2.5°	1017.7	1017.3	1016.9	1016.5	1016.1	1015.2	1013.8	1012.5	1011.1	1009.8	1011.1
5°	1014.3	1013.7	1013.0	1012.3	1011.6	1010.4	1008.5	1006.6	1004.7	1002.8	1004.5
7.5°	1004.4	1003.7	1003.1	1002.4	1001.8	1000.4	998.0	995.8	993.6	991.3	992.5
10°	995.1	994.6	994.1	993.6	993.1	991.7	989.3	986.9	984.5	982.1	982.6
12.5°	984.7	984.1	983.4	982.8	982.1	980.2	977.0	973.8	970.6	967.3	967.8
15°	964.5	963.4	962.4	961.4	960.4	958.1	954.5	950.9	947.4	943.7	943.6
17.5°	941.6	940.1	938.5	937.0	935.3	932.3	927.8	923.3	918.8	914.3	913.4
20°	923.8	922.1	920.4	918.7	917.0	913.4	908.0	902.5	897.1	891.6	890.7
22.5°	904.1	902.4	900.8	899.1	897.4	893.6	887.9	882.2	876.5	870.7	869.1
25°	874.7	872.1	869.6	867.1	864.4	860.0	853.7	847.4	841.1	834.8	832.6
27.5°	840.9	837.9	834.8	831.6	828.5	823.6	816.9	810.1	803.3	796.6	793.5
30°	816.4	813.1	809.9	806.7	803.4	798.2	791.0	784.0	776.8	769.6	765.7
32.5°	792.4	788.7	784.9	781.1	777.3	771.7	764.5	757.2	749.8	742.6	738.2
35°	753.5	749.4	745.3	741.2	737.1	731.2	723.6	715.9	708.2	700.5	695.6
37.5°	715.3	710.2	705.3	700.3	695.4	688.9	681.0	673.1	665.2	657.2	651.4
40°	688.2	683.2	678.0	672.9	667.8	661.2	653.0	644.8	636.6	628.4	622.0
42.5°	660.0	654.8	649.5	644.3	639.0	632.2	623.7	615.2	606.8	598.3	592.1
45°	616.9	612.0	607.0	602.1	597.1	590.0	580.6	571.2	561.8	552.4	545.6
47.5°	572.3	567.0	561.8	556.6	551.4	544.0	534.6	525.1	515.7	506.2	499.3
50°	544.0	538.4	532.7	527.1	521.5	513.8	504.1	494.4	484.6	474.9	467.8
52.5°	513.3	507.6	501.8	496.0	490.3	482.8	473.6	464.4	455.2	446.1	438.4
55°	468.1	462.6	457.2	451.7	446.3	438.7	429.2	419.6	410.1	400.5	392.8
57.5°	422.3	416.5	410.6	404.9	399.0	391.4	382.2	373.0	363.9	354.7	347.1
60°	392.8	386.9	380.9	375.0	369.0	361.4	352.1	343.0	333.8	324.6	317.1
62.5°	361.5	355.9	350.1	344.5	338.8	331.2	321.9	312.6	303.3	293.9	286.9
65°	316.9	311.1	305.3	299.5	293.7	286.3	277.2	268.2	259.1	250.1	243.3
67.5°	272.6	266.7	260.9	255.2	249.3	242.2	233.5	224.8	216.1	207.4	201.3
70°	242.5	236.7	230.9	225.1	219.2	212.1	203.6	195.1	186.5	178.0	172.7
72.5°	213.0	207.3	201.7	196.0	190.4	183.5	175.5	167.5	159.6	151.6	146.7
75°	168.8	163.7	158.5	153.5	148.3	142.2	135.0	127.8	120.7	113.5	109.8
77.5°	124.9	120.8	116.7	112.6	108.6	103.6	97.9	92.2	86.4	80.7	78.1
80°	99.8	95.6	91.6	87.5	83.4	79.0	74.1	69.4	64.6	59.9	58.3
82.5°	75.2	71.5	67.9	64.1	60.5	57.0	53.7	50.4	47.2	43.9	43.2
85°	42.2	39.1	36.1	33.0	29.9	28.0	27.1	26.3	25.4	24.5	24.3
87.5°	14.3	13.8	13.2	12.7	12.2	12.0	12.3	12.5	12.7	12.9	13.2
90°	1.2	3.2	5.4	7.5	9.5	11.5	13.3	15.1	17.0	18.8	20.1
92.5°	18.1	16.7	15.1	13.7	12.2	12.3	13.9	15.6	17.2	18.8	20.1
95°	66.9	66.1	65.3	64.5	63.7	58.5	48.5	38.6	28.7	18.8	20.1
97.5°	139.7	141.1	142.5	143.9	145.3	136.2	116.5	96.9	77.4	57.8	50.4
100°	196.0	196.8	197.5	198.3	199.1	200.1	201.1	202.2	203.2	204.2	165.3
102.5°	253.3	254.3	255.3	256.2	257.2	258.0	258.6	259.3	259.9	260.5	253.2
105°	345.1	346.1	347.1	348.2	349.2	349.7	349.7	349.7	349.7	349.7	349.7
107.5°	440.4	440.4	440.4	440.4	440.4	440.6	441.1	441.6	442.2	442.7	442.7
110°	502.3	502.3	502.3	502.3	502.3	502.6	503.1	503.6	504.1	504.6	503.9



TEST NUMBER: P333547-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	560.6	561.2	561.8	562.4	563.0	563.5	563.8	564.1	564.4	564.7	563.8
115°	647.8	649.1	650.5	651.8	653.1	653.9	654.1	654.4	654.6	654.9	653.9
117.5°	738.2	738.2	738.1	738.1	738.0	738.5	739.5	740.4	741.4	742.5	741.1
120°	794.6	794.3	794.1	793.8	793.6	793.8	794.6	795.4	796.1	796.9	796.4
122.5°	844.3	845.4	846.3	847.3	848.3	849.0	849.3	849.7	850.1	850.4	849.9
125°	921.3	923.1	924.9	926.8	928.6	929.5	929.5	929.5	929.5	929.5	928.5
127.5°	994.8	996.1	997.3	998.7	1000.0	1000.6	1000.4	1000.3	1000.1	1000.0	999.4
130°	1039.9	1041.2	1042.5	1043.8	1045.1	1045.8	1046.1	1046.4	1046.6	1046.9	1046.1
132.5°	1084.9	1086.4	1087.9	1089.4	1091.0	1091.5	1090.9	1090.3	1089.7	1089.1	1089.0
135°	1149.0	1150.5	1152.2	1153.7	1155.3	1155.8	1155.3	1154.8	1154.2	1153.7	1153.2
137.5°	1207.9	1209.3	1210.6	1211.9	1213.4	1213.8	1213.4	1212.8	1212.3	1211.9	1212.0
140°	1246.4	1247.0	1247.5	1248.0	1248.5	1248.6	1248.4	1248.1	1247.9	1247.6	1248.1
142.5°	1281.1	1281.4	1281.8	1282.1	1282.4	1282.7	1283.1	1283.4	1283.8	1284.2	1284.3
145°	1332.1	1332.6	1333.1	1333.6	1334.1	1334.4	1334.4	1334.4	1334.4	1334.4	1334.7
147.5°	1376.6	1376.5	1376.4	1376.3	1376.2	1376.3	1376.6	1377.0	1377.4	1377.7	1378.0
150°	1404.8	1404.3	1403.8	1403.3	1402.8	1402.8	1403.3	1403.8	1404.3	1404.8	1405.3
152.5°	1432.1	1431.0	1429.8	1428.7	1427.4	1427.1	1427.7	1428.3	1428.8	1429.3	1429.8
155°	1467.0	1465.5	1463.9	1462.4	1460.8	1460.3	1460.8	1461.3	1461.9	1462.4	1463.2
157.5°	1494.1	1493.1	1492.2	1491.3	1490.3	1489.9	1490.0	1490.0	1490.1	1490.1	1490.9
160°	1512.9	1511.3	1509.7	1508.1	1506.6	1505.9	1506.2	1506.4	1506.7	1506.9	1508.0
162.5°	1527.8	1526.3	1524.7	1523.2	1521.6	1521.0	1521.2	1521.5	1521.8	1522.0	1523.5
165°	1548.0	1546.5	1544.9	1543.4	1541.8	1541.2	1541.4	1541.7	1541.9	1542.2	1543.8
167.5°	1563.1	1561.5	1559.8	1558.2	1556.6	1555.9	1556.2	1556.4	1556.7	1557.0	1558.8
170°	1571.6	1569.7	1567.8	1566.0	1564.2	1563.5	1563.7	1564.0	1564.2	1564.5	1566.6
172.5°	1577.1	1575.3	1573.5	1571.7	1569.8	1569.1	1569.6	1570.1	1570.5	1571.0	1573.0
175°	1583.3	1581.7	1580.1	1578.5	1577.0	1576.3	1576.6	1576.9	1577.1	1577.4	1579.4
177.5°	1586.1	1584.8	1583.6	1582.4	1581.0	1580.5	1580.7	1580.9	1581.1	1581.3	1582.9
180°	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3



TEST NUMBER: P333547-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9
2.5°	1012.5	1013.8	1015.2	1015.8	1015.7	1015.5	1015.4	1015.3
5°	1006.2	1007.9	1009.7	1010.4	1010.0	1009.7	1009.4	1009.0
7.5°	993.7	994.9	996.1	996.5	996.1	995.7	995.4	995.0
10°	983.1	983.6	984.2	984.2	983.6	983.1	982.6	982.1
12.5°	968.2	968.6	968.9	968.7	967.9	967.1	966.3	965.5
15°	943.4	943.2	943.1	942.2	940.7	939.2	937.7	936.0
17.5°	912.6	911.7	910.9	909.8	908.6	907.3	906.1	904.7
20°	889.9	889.0	888.2	887.0	885.4	883.9	882.4	880.8
22.5°	867.4	865.7	864.0	862.5	861.3	860.0	858.8	857.5
25°	830.4	828.2	826.0	823.8	822.0	820.1	818.3	816.4
27.5°	790.4	787.3	784.2	781.7	779.9	778.1	776.3	774.5
30°	761.7	757.8	753.9	751.1	749.6	748.1	746.6	745.1
32.5°	733.9	729.6	725.3	722.2	720.1	718.2	716.3	714.4
35°	690.6	685.7	680.8	677.1	674.7	672.3	669.9	667.5
37.5°	645.4	639.4	633.5	629.3	627.0	624.8	622.5	620.2
40°	615.4	608.9	602.5	598.2	596.2	594.1	592.1	590.1
42.5°	585.9	579.7	573.5	568.9	565.9	562.9	559.9	556.9
45°	538.8	532.0	525.1	520.5	518.0	515.3	512.8	510.3
47.5°	492.2	485.1	478.2	473.2	470.4	467.6	464.7	461.9
50°	460.6	453.4	446.3	441.4	438.9	436.4	433.7	431.2
52.5°	430.7	422.9	415.3	410.1	407.6	405.1	402.4	399.9
55°	385.2	377.5	369.8	364.7	361.9	359.2	356.5	353.8
57.5°	339.6	332.1	324.7	319.6	317.2	314.8	312.5	310.0
60°	309.5	302.1	294.6	289.5	287.0	284.4	281.9	279.3
62.5°	279.9	273.0	266.0	261.3	258.7	256.2	253.6	251.1
65°	236.5	229.6	222.9	218.1	215.6	213.1	210.5	207.9
67.5°	195.0	188.7	182.5	178.3	176.3	174.3	172.2	170.2
70°	167.4	162.2	156.8	153.2	151.2	149.2	147.0	145.0
72.5°	141.9	136.9	132.1	129.0	127.6	126.2	124.9	123.5
75°	106.0	102.3	98.6	96.0	94.9	93.7	92.5	91.3
77.5°	75.4	72.8	70.2	68.5	67.6	66.7	65.8	64.9
80°	56.8	55.2	53.7	52.8	52.4	52.1	51.7	51.4
82.5°	42.4	41.7	41.0	40.6	40.4	40.2	40.0	39.8
85°	24.2	24.0	23.8	23.7	23.5	23.3	23.2	23.0
87.5°	13.5	13.7	14.0	14.1	14.1	14.1	14.2	14.2
90°	21.4	22.7	24.0	25.0	25.9	26.6	27.4	28.2
92.5°	21.4	22.7	24.0	24.8	25.1	25.5	26.0	26.3
95°	21.4	22.7	24.0	24.6	24.6	24.6	24.6	24.6
97.5°	43.0	35.6	28.3	24.6	24.6	24.6	24.6	24.6
100°	126.5	87.7	48.8	28.8	27.8	26.8	25.7	24.6
102.5°	245.8	238.5	231.2	218.6	200.9	183.1	165.4	147.6
105°	349.7	349.7	349.7	349.6	349.3	349.1	348.8	348.6
107.5°	442.8	442.8	442.9	442.5	441.7	441.0	440.2	439.4
110°	503.1	502.3	501.5	501.3	501.5	501.8	502.1	502.3



TEST NUMBER: P333547-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	562.8	561.8	560.8	560.1	559.8	559.4	559.1	558.7
115°	652.8	651.8	650.8	649.4	647.8	646.3	644.7	643.2
117.5°	739.7	738.4	737.0	736.0	735.3	734.7	734.0	733.3
120°	795.9	795.4	794.9	794.0	792.6	791.3	790.0	788.7
122.5°	849.4	848.9	848.4	847.3	845.8	844.2	842.8	841.3
125°	927.5	926.3	925.3	924.4	923.6	922.9	922.1	921.3
127.5°	998.8	998.3	997.6	996.4	994.5	992.5	990.6	988.7
130°	1045.3	1044.5	1043.8	1042.7	1041.4	1040.2	1038.8	1037.5
132.5°	1088.8	1088.6	1088.5	1087.8	1086.5	1085.2	1083.9	1082.6
135°	1152.7	1152.2	1151.7	1150.5	1149.0	1147.4	1145.9	1144.3
137.5°	1212.1	1212.2	1212.3	1211.7	1210.3	1209.0	1207.6	1206.3
140°	1248.6	1249.1	1249.7	1249.1	1247.6	1246.1	1244.5	1242.9
142.5°	1284.4	1284.5	1284.6	1283.9	1282.3	1280.8	1279.2	1277.7
145°	1334.9	1335.2	1335.4	1334.8	1333.2	1331.7	1330.1	1328.6
147.5°	1378.3	1378.6	1378.9	1378.1	1376.2	1374.3	1372.5	1370.6
150°	1405.9	1406.4	1406.9	1406.1	1404.1	1402.0	1399.9	1397.9
152.5°	1430.3	1430.9	1431.4	1430.7	1428.8	1426.9	1425.0	1423.2
155°	1463.9	1464.7	1465.5	1464.8	1462.8	1460.7	1458.5	1456.5
157.5°	1491.8	1492.6	1493.4	1492.8	1490.7	1488.6	1486.5	1484.4
160°	1509.0	1510.1	1511.2	1510.7	1508.5	1506.4	1504.4	1502.3
162.5°	1524.9	1526.4	1527.8	1527.4	1525.1	1522.8	1520.6	1518.2
165°	1545.3	1546.9	1548.4	1548.1	1546.1	1544.0	1541.9	1539.8
167.5°	1560.7	1562.6	1564.5	1564.3	1561.9	1559.5	1557.2	1554.9
170°	1568.6	1570.7	1572.9	1572.7	1570.3	1568.0	1565.7	1563.3
172.5°	1574.8	1576.7	1578.5	1578.3	1576.0	1573.7	1571.2	1568.9
175°	1581.5	1583.7	1585.7	1585.6	1583.3	1580.9	1578.5	1576.2
177.5°	1584.3	1585.8	1587.2	1587.1	1585.5	1583.8	1582.1	1580.4
180°	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3	1583.3

(END OF REPORT)