

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333548-840

Luminaire Tested: **S125RDIP-S610D1205U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333548-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S610D1205U840-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6611.1 lumens
Efficiency: N/A
Efficacy: 133.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333548-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333548-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36
1	95	91	87	84	86	82	79	76	67	64	62	52	51	49	39	38	37	31
2	86	79	73	68	78	72	67	63	58	55	52	46	44	41	34	33	31	26
3	79	70	63	57	71	64	57	53	52	47	44	41	38	35	30	29	27	22
4	72	62	54	48	65	56	50	45	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20	17
6	61	49	41	36	55	45	38	33	37	32	28	29	26	23	22	20	18	15
7	56	44	37	31	51	41	34	29	33	28	25	27	23	20	20	18	16	13
8	52	40	33	28	47	37	30	26	31	25	22	24	21	18	19	16	14	12
9	49	37	29	25	44	34	27	23	28	23	20	22	19	16	17	15	13	11
10	45	34	27	22	41	31	25	20	26	21	18	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6561	6561	6561
5°	6576	6501	6541
10°	6526	6441	6441
15°	6449	6310	6258
20°	6349	6128	6054
25°	6233	5949	5818
30°	6088	5739	5557
35°	5941	5523	5263
40°	5802	5298	4975
45°	5634	5045	4661
50°	5466	4772	4332
55°	5271	4510	3984
60°	5074	4193	3608
65°	4843	3822	3177
70°	4579	3361	2738
75°	4212	2832	2278
80°	3712	2228	1912
85°	3127	1815	1704



TEST NUMBER: P333548-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.5	1.4
10°-20°	267.0	4.0
20°-30°	387.1	5.9
30°-40°	441.2	6.7
40°-50°	430.0	6.5
50°-60°	362.0	5.5
60°-70°	253.8	3.8
70°-80°	130.4	2.0
80°-90°	36.2	0.5
90°-100°	101.0	1.5
100°-110°	298.2	4.5
110°-120°	505.2	7.6
120°-130°	664.8	10.1
130°-140°	745.0	11.3
140°-150°	730.1	11.0
150°-160°	613.2	9.3
160°-170°	407.6	6.2
170°-180°	142.7	2.2
0°-30°	749.6	11.3
0°-40°	1190.8	18.0
0°-60°	1982.8	30.0
0°-90°	2403.2	36.4
90°-120°	904.4	13.7
90°-150°	3044.3	46.0
90°-180°	4208.0	63.7
0°-180°	6611.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1016	1016	1016	1016	1016	
5°	1014	1011	1003	1010	1009	96
15°	964	959	944	943	936	272
25°	875	862	835	825	816	402
35°	754	734	700	679	668	472
45°	617	594	552	523	510	476
55°	468	442	400	367	354	418
65°	317	290	250	220	208	314
75°	169	145	114	97	91	179
85°	42	29	24	24	23	47
90°	1	10	19	24	28	6
95°	76	79	90	98	101	81
105°	268	274	280	287	291	286
115°	506	510	513	512	510	500
125°	738	745	746	744	743	661
135°	960	967	968	968	963	740
145°	1163	1168	1171	1171	1168	727
155°	1331	1331	1332	1336	1331	613
165°	1447	1445	1446	1450	1443	408
175°	1504	1500	1500	1506	1498	143
180°	1508	1508	1508	1508	1508	



TEST NUMBER: P333548-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9
2.5°	1017.7	1017.3	1016.9	1016.5	1016.1	1015.2	1013.8	1012.5	1011.1	1009.8	1011.1
5°	1014.3	1013.7	1013.0	1012.3	1011.6	1010.4	1008.5	1006.6	1004.7	1002.8	1004.5
7.5°	1004.4	1003.7	1003.1	1002.4	1001.8	1000.4	998.0	995.8	993.6	991.3	992.5
10°	995.1	994.6	994.1	993.6	993.1	991.7	989.3	986.9	984.5	982.1	982.6
12.5°	984.7	984.1	983.4	982.8	982.1	980.2	977.0	973.8	970.6	967.3	967.8
15°	964.5	963.4	962.4	961.4	960.4	958.1	954.5	950.9	947.4	943.7	943.6
17.5°	941.6	940.1	938.5	937.0	935.3	932.3	927.8	923.3	918.8	914.3	913.4
20°	923.8	922.1	920.4	918.7	917.0	913.4	908.0	902.5	897.1	891.6	890.7
22.5°	904.1	902.4	900.8	899.1	897.4	893.6	887.9	882.2	876.5	870.7	869.1
25°	874.7	872.1	869.6	867.1	864.4	860.0	853.7	847.4	841.1	834.8	832.6
27.5°	840.9	837.9	834.8	831.6	828.5	823.6	816.9	810.1	803.3	796.6	793.5
30°	816.4	813.1	809.9	806.7	803.4	798.2	791.0	784.0	776.8	769.6	765.7
32.5°	792.4	788.7	784.9	781.1	777.3	771.7	764.5	757.2	749.8	742.6	738.2
35°	753.5	749.4	745.3	741.2	737.1	731.2	723.6	715.9	708.2	700.5	695.6
37.5°	715.3	710.2	705.3	700.3	695.4	688.9	681.0	673.1	665.2	657.2	651.4
40°	688.2	683.2	678.0	672.9	667.8	661.2	653.0	644.8	636.6	628.4	622.0
42.5°	660.0	654.8	649.5	644.3	639.0	632.2	623.7	615.2	606.8	598.3	592.1
45°	616.9	612.0	607.0	602.1	597.1	590.0	580.6	571.2	561.8	552.4	545.6
47.5°	572.3	567.0	561.8	556.6	551.4	544.0	534.6	525.1	515.7	506.2	499.3
50°	544.0	538.4	532.7	527.1	521.5	513.8	504.1	494.4	484.6	474.9	467.8
52.5°	513.3	507.6	501.8	496.0	490.3	482.8	473.6	464.4	455.2	446.1	438.4
55°	468.1	462.6	457.2	451.7	446.3	438.7	429.2	419.6	410.1	400.5	392.8
57.5°	422.3	416.5	410.6	404.9	399.0	391.4	382.2	373.0	363.9	354.7	347.1
60°	392.8	386.9	380.9	375.0	369.0	361.4	352.1	343.0	333.8	324.6	317.1
62.5°	361.5	355.9	350.1	344.5	338.8	331.2	321.9	312.6	303.3	293.9	286.9
65°	316.9	311.1	305.3	299.5	293.7	286.3	277.2	268.2	259.1	250.1	243.3
67.5°	272.6	266.7	260.9	255.2	249.3	242.2	233.5	224.8	216.1	207.4	201.3
70°	242.5	236.7	230.9	225.1	219.2	212.1	203.6	195.1	186.5	178.0	172.7
72.5°	213.0	207.3	201.7	196.0	190.4	183.5	175.5	167.5	159.6	151.6	146.7
75°	168.8	163.7	158.5	153.5	148.3	142.2	135.0	127.8	120.7	113.5	109.8
77.5°	124.9	120.8	116.7	112.6	108.6	103.6	97.9	92.2	86.4	80.7	78.1
80°	99.8	95.6	91.6	87.5	83.4	79.0	74.1	69.4	64.6	59.9	58.3
82.5°	75.2	71.5	67.9	64.1	60.5	57.0	53.7	50.4	47.2	43.9	43.2
85°	42.2	39.1	36.1	33.0	29.9	28.0	27.1	26.3	25.4	24.5	24.3
87.5°	14.3	13.8	13.2	12.7	12.2	12.0	12.3	12.5	12.7	12.9	13.2
90°	1.2	3.2	5.4	7.5	9.5	11.5	13.3	15.1	17.0	18.8	20.1
92.5°	28.4	29.9	31.3	32.8	34.2	36.1	38.4	40.6	42.8	45.0	46.8
95°	76.2	76.7	77.4	77.9	78.4	79.9	82.5	85.1	87.8	90.4	92.2
97.5°	126.7	126.9	127.1	127.3	127.5	129.5	133.1	136.6	140.3	143.9	145.6
100°	164.3	164.3	164.3	164.3	164.3	166.0	169.4	172.8	176.1	179.6	181.9
102.5°	204.7	205.7	206.7	207.8	208.8	210.3	212.0	213.7	215.4	217.1	219.6
105°	267.5	268.8	270.1	271.5	272.8	274.2	275.8	277.3	278.9	280.4	282.1
107.5°	337.0	338.3	339.6	340.9	342.2	343.5	344.7	345.9	347.1	348.3	349.1
110°	385.0	386.2	387.5	388.8	390.1	391.1	391.9	392.7	393.5	394.3	395.1



TEST NUMBER: P333548-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	433.7	434.4	435.0	435.8	436.5	437.3	438.3	439.3	440.2	441.2	441.6
115°	505.7	506.9	507.9	508.9	510.0	510.7	511.3	511.8	512.3	512.8	512.6
117.5°	578.0	578.6	579.1	579.5	580.0	580.4	580.9	581.4	581.8	582.3	582.5
120°	623.1	624.4	625.7	627.0	628.3	629.1	629.3	629.7	630.0	630.2	630.2
122.5°	672.0	672.5	672.9	673.4	673.8	674.4	675.1	675.8	676.4	677.1	676.9
125°	738.1	739.7	741.2	742.9	744.4	745.3	745.6	745.8	746.1	746.4	745.8
127.5°	808.6	809.4	810.3	811.2	812.1	812.7	813.0	813.3	813.6	814.0	813.6
130°	850.8	852.1	853.4	854.7	856.0	857.0	857.5	858.0	858.5	859.0	858.8
132.5°	893.0	895.1	897.4	899.5	901.6	902.6	902.5	902.4	902.3	902.2	901.9
135°	960.0	961.5	963.1	964.6	966.2	967.1	967.3	967.7	967.9	968.2	968.2
137.5°	1022.8	1024.3	1025.8	1027.3	1028.9	1030.0	1030.5	1031.1	1031.7	1032.2	1032.5
140°	1063.2	1064.5	1065.8	1067.1	1068.4	1069.4	1070.3	1071.1	1071.8	1072.6	1073.1
142.5°	1103.6	1104.7	1105.8	1106.8	1107.9	1109.0	1109.9	1111.0	1112.0	1113.0	1113.3
145°	1163.0	1164.0	1165.1	1166.1	1167.1	1168.0	1168.8	1169.6	1170.3	1171.1	1171.1
147.5°	1217.9	1218.4	1219.0	1219.6	1220.1	1220.7	1221.4	1222.0	1222.6	1223.2	1223.9
150°	1254.5	1254.3	1253.9	1253.7	1253.4	1253.8	1254.9	1255.9	1257.0	1258.0	1258.0
152.5°	1284.5	1284.9	1285.3	1285.7	1286.0	1286.4	1286.8	1287.2	1287.7	1288.1	1288.7
155°	1330.8	1330.8	1330.8	1330.8	1330.8	1330.9	1331.2	1331.4	1331.7	1331.9	1333.0
157.5°	1372.1	1371.5	1370.9	1370.4	1369.8	1369.6	1369.9	1370.2	1370.4	1370.7	1371.7
160°	1396.4	1395.7	1394.9	1394.1	1393.3	1393.1	1393.3	1393.6	1393.9	1394.1	1395.1
162.5°	1418.1	1417.5	1416.9	1416.3	1415.7	1415.5	1415.5	1415.6	1415.6	1415.7	1416.9
165°	1446.9	1446.4	1445.9	1445.4	1444.8	1444.7	1445.0	1445.2	1445.5	1445.7	1446.8
167.5°	1471.4	1470.3	1469.3	1468.2	1467.1	1466.6	1466.6	1466.6	1466.6	1466.6	1468.2
170°	1484.5	1483.5	1482.4	1481.4	1480.4	1479.8	1479.8	1479.8	1479.8	1479.8	1481.4
172.5°	1493.9	1492.9	1491.8	1490.8	1489.8	1489.1	1489.1	1489.1	1489.1	1489.1	1490.8
175°	1504.4	1503.4	1502.4	1501.3	1500.3	1499.8	1499.8	1499.8	1499.8	1499.8	1501.3
177.5°	1509.8	1509.0	1508.1	1507.3	1506.5	1506.0	1505.8	1505.6	1505.3	1505.1	1506.4
180°	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9



TEST NUMBER: P333548-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9
2.5°	1012.5	1013.8	1015.2	1015.8	1015.7	1015.5	1015.4	1015.3
5°	1006.2	1007.9	1009.7	1010.4	1010.0	1009.7	1009.4	1009.0
7.5°	993.7	994.9	996.1	996.5	996.1	995.7	995.4	995.0
10°	983.1	983.6	984.2	984.2	983.6	983.1	982.6	982.1
12.5°	968.2	968.6	968.9	968.7	967.9	967.1	966.3	965.5
15°	943.4	943.2	943.1	942.2	940.7	939.2	937.7	936.0
17.5°	912.6	911.7	910.9	909.8	908.6	907.3	906.1	904.7
20°	889.9	889.0	888.2	887.0	885.4	883.9	882.4	880.8
22.5°	867.4	865.7	864.0	862.5	861.3	860.0	858.8	857.5
25°	830.4	828.2	826.0	823.8	822.0	820.1	818.3	816.4
27.5°	790.4	787.3	784.2	781.7	779.9	778.1	776.3	774.5
30°	761.7	757.8	753.9	751.1	749.6	748.1	746.6	745.1
32.5°	733.9	729.6	725.3	722.2	720.1	718.2	716.3	714.4
35°	690.6	685.7	680.8	677.1	674.7	672.3	669.9	667.5
37.5°	645.4	639.4	633.5	629.3	627.0	624.8	622.5	620.2
40°	615.4	608.9	602.5	598.2	596.2	594.1	592.1	590.1
42.5°	585.9	579.7	573.5	568.9	565.9	562.9	559.9	556.9
45°	538.8	532.0	525.1	520.5	518.0	515.3	512.8	510.3
47.5°	492.2	485.1	478.2	473.2	470.4	467.6	464.7	461.9
50°	460.6	453.4	446.3	441.4	438.9	436.4	433.7	431.2
52.5°	430.7	422.9	415.3	410.1	407.6	405.1	402.4	399.9
55°	385.2	377.5	369.8	364.7	361.9	359.2	356.5	353.8
57.5°	339.6	332.1	324.7	319.6	317.2	314.8	312.5	310.0
60°	309.5	302.1	294.6	289.5	287.0	284.4	281.9	279.3
62.5°	279.9	273.0	266.0	261.3	258.7	256.2	253.6	251.1
65°	236.5	229.6	222.9	218.1	215.6	213.1	210.5	207.9
67.5°	195.0	188.7	182.5	178.3	176.3	174.3	172.2	170.2
70°	167.4	162.2	156.8	153.2	151.2	149.2	147.0	145.0
72.5°	141.9	136.9	132.1	129.0	127.6	126.2	124.9	123.5
75°	106.0	102.3	98.6	96.0	94.9	93.7	92.5	91.3
77.5°	75.4	72.8	70.2	68.5	67.6	66.7	65.8	64.9
80°	56.8	55.2	53.7	52.8	52.4	52.1	51.7	51.4
82.5°	42.4	41.7	41.0	40.6	40.4	40.2	40.0	39.8
85°	24.2	24.0	23.8	23.7	23.5	23.3	23.2	23.0
87.5°	13.5	13.7	14.0	14.1	14.1	14.1	14.2	14.2
90°	21.4	22.7	24.0	25.0	25.9	26.6	27.4	28.2
92.5°	48.5	50.2	51.9	53.1	53.6	54.2	54.8	55.3
95°	94.0	95.8	97.7	98.9	99.4	99.9	100.4	100.9
97.5°	147.3	149.1	150.8	151.8	152.1	152.4	152.7	153.0
100°	184.2	186.6	188.9	190.4	190.9	191.4	192.0	192.5
102.5°	222.2	224.8	227.3	228.9	229.7	230.5	231.2	231.9
105°	283.6	285.2	286.7	287.9	288.7	289.4	290.2	291.0
107.5°	349.8	350.6	351.4	351.8	351.7	351.7	351.6	351.5
110°	395.9	396.7	397.4	397.7	397.4	397.2	396.9	396.7



TEST NUMBER: P333548-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	442.0	442.3	442.7	442.6	442.2	441.7	441.2	440.8
115°	512.3	512.0	511.8	511.5	511.3	511.0	510.7	510.5
117.5°	582.7	582.9	583.1	582.7	581.7	580.7	579.6	578.6
120°	630.2	630.2	630.2	629.7	628.6	627.5	626.5	625.5
122.5°	676.7	676.5	676.3	675.8	674.9	674.1	673.3	672.5
125°	745.3	744.8	744.3	743.9	743.7	743.4	743.1	742.9
127.5°	813.4	813.1	812.9	812.5	812.0	811.4	810.9	810.4
130°	858.5	858.2	858.0	857.6	857.1	856.6	856.0	855.5
132.5°	901.7	901.4	901.1	900.7	899.9	899.2	898.5	897.8
135°	968.2	968.2	968.2	967.7	966.5	965.5	964.5	963.4
137.5°	1032.9	1033.2	1033.5	1033.0	1031.7	1030.4	1029.1	1027.7
140°	1073.6	1074.2	1074.7	1074.3	1073.0	1071.7	1070.4	1069.0
142.5°	1113.6	1113.9	1114.2	1113.7	1112.4	1111.2	1109.8	1108.5
145°	1171.1	1171.1	1171.1	1170.7	1170.0	1169.2	1168.4	1167.6
147.5°	1224.6	1225.2	1225.8	1225.2	1223.5	1221.6	1219.9	1218.1
150°	1258.0	1258.0	1258.0	1257.8	1257.2	1256.7	1256.2	1255.7
152.5°	1289.3	1289.9	1290.5	1290.4	1289.5	1288.5	1287.6	1286.7
155°	1334.0	1335.0	1336.2	1336.0	1334.6	1333.3	1332.1	1330.8
157.5°	1372.7	1373.8	1374.8	1374.5	1372.8	1371.1	1369.4	1367.7
160°	1396.2	1397.2	1398.3	1398.2	1396.8	1395.5	1394.2	1393.0
162.5°	1418.3	1419.5	1420.8	1420.6	1419.1	1417.5	1416.0	1414.5
165°	1447.8	1448.9	1450.0	1449.7	1448.1	1446.5	1445.0	1443.4
167.5°	1469.8	1471.4	1472.9	1472.9	1471.3	1469.7	1468.0	1466.4
170°	1482.9	1484.5	1486.0	1485.9	1484.1	1482.3	1480.5	1478.6
172.5°	1492.3	1493.9	1495.4	1495.4	1493.8	1492.2	1490.6	1488.9
175°	1502.9	1504.4	1506.0	1505.9	1504.1	1502.3	1500.4	1498.5
177.5°	1507.6	1508.9	1510.2	1510.1	1508.6	1507.1	1505.7	1504.2
180°	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9	1507.9

(END OF REPORT)