

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333549-840

Luminaire Tested: **S125RDIP-S610D1205U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333549-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S610D1205U840-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6767.8 lumens
Efficiency: N/A
Efficacy: 137.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333549-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333549-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	36
1	95	91	87	83	86	82	79	76	66	64	62	52	50	49	38	37	36	30
2	86	79	73	68	78	72	67	63	58	55	52	45	43	41	34	32	31	26
3	79	70	63	57	71	63	57	52	51	47	43	40	37	35	30	28	26	22
4	72	62	54	48	65	56	50	44	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	24	22	20	16
6	61	49	41	36	55	45	38	33	37	32	28	29	25	23	22	20	18	14
7	56	44	37	31	51	41	34	29	33	28	24	26	23	20	20	18	16	13
8	52	40	33	28	47	37	30	26	30	25	22	24	21	18	18	16	14	12
9	48	37	29	24	44	34	27	23	28	23	19	22	19	16	17	15	13	10
10	45	34	27	22	41	31	25	20	25	21	17	21	17	14	16	13	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6561	6561	6561
5°	6576	6501	6541
10°	6526	6441	6441
15°	6449	6310	6258
20°	6349	6128	6054
25°	6233	5949	5818
30°	6088	5739	5557
35°	5941	5523	5263
40°	5802	5298	4975
45°	5634	5045	4661
50°	5466	4772	4332
55°	5271	4510	3984
60°	5074	4193	3608
65°	4843	3822	3177
70°	4579	3361	2738
75°	4212	2832	2278
80°	3712	2228	1912
85°	3127	1815	1704



TEST NUMBER: P333549-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.5	1.4
10°-20°	267.0	3.9
20°-30°	387.1	5.7
30°-40°	441.2	6.5
40°-50°	430.0	6.4
50°-60°	362.0	5.3
60°-70°	253.8	3.7
70°-80°	130.4	1.9
80°-90°	36.2	0.5
90°-100°	421.9	6.2
100°-110°	906.9	13.4
110°-120°	851.1	12.6
120°-130°	689.8	10.2
130°-140°	553.5	8.2
140°-150°	417.7	6.2
150°-160°	294.0	4.3
160°-170°	173.3	2.6
170°-180°	56.4	0.8
0°-30°	749.6	11.1
0°-40°	1190.8	17.6
0°-60°	1982.8	29.3
0°-90°	2403.2	35.5
90°-120°	2179.9	32.2
90°-150°	3840.9	56.8
90°-180°	4365.0	64.5
0°-180°	6767.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1016	1016	1016	1016	1016	
5°	1014	1011	1003	1010	1009	96
15°	964	959	944	943	936	272
25°	875	862	835	825	816	402
35°	754	734	700	679	668	472
45°	617	594	552	523	510	476
55°	468	442	400	367	354	418
65°	317	290	250	220	208	314
75°	169	145	114	97	91	179
85°	42	29	24	24	23	47
90°	1	11	19	25	27	4
95°	39	114	1040	472	276	41
105°	133	185	851	1675	1555	140
115°	237	286	683	1472	1732	233
125°	328	385	655	1171	1365	291
135°	385	463	650	982	1134	299
145°	448	513	652	813	894	281
155°	512	550	636	719	750	236
165°	559	574	610	647	657	157
175°	581	581	586	593	590	55
180°	582	582	582	582	582	



TEST NUMBER: P333549-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9
2.5°	1017.7	1017.3	1016.9	1016.5	1016.1	1015.2	1013.8	1012.5	1011.1	1009.8	1011.1
5°	1014.3	1013.7	1013.0	1012.3	1011.6	1010.4	1008.5	1006.6	1004.7	1002.8	1004.5
7.5°	1004.4	1003.7	1003.1	1002.4	1001.8	1000.4	998.0	995.8	993.6	991.3	992.5
10°	995.1	994.6	994.1	993.6	993.1	991.7	989.3	986.9	984.5	982.1	982.6
12.5°	984.7	984.1	983.4	982.8	982.1	980.2	977.0	973.8	970.6	967.3	967.8
15°	964.5	963.4	962.4	961.4	960.4	958.1	954.5	950.9	947.4	943.7	943.6
17.5°	941.6	940.1	938.5	937.0	935.3	932.3	927.8	923.3	918.8	914.3	913.4
20°	923.8	922.1	920.4	918.7	917.0	913.4	908.0	902.5	897.1	891.6	890.7
22.5°	904.1	902.4	900.8	899.1	897.4	893.6	887.9	882.2	876.5	870.7	869.1
25°	874.7	872.1	869.6	867.1	864.4	860.0	853.7	847.4	841.1	834.8	832.6
27.5°	840.9	837.9	834.8	831.6	828.5	823.6	816.9	810.1	803.3	796.6	793.5
30°	816.4	813.1	809.9	806.7	803.4	798.2	791.0	784.0	776.8	769.6	765.7
32.5°	792.4	788.7	784.9	781.1	777.3	771.7	764.5	757.2	749.8	742.6	738.2
35°	753.5	749.4	745.3	741.2	737.1	731.2	723.6	715.9	708.2	700.5	695.6
37.5°	715.3	710.2	705.3	700.3	695.4	688.9	681.0	673.1	665.2	657.2	651.4
40°	688.2	683.2	678.0	672.9	667.8	661.2	653.0	644.8	636.6	628.4	622.0
42.5°	660.0	654.8	649.5	644.3	639.0	632.2	623.7	615.2	606.8	598.3	592.1
45°	616.9	612.0	607.0	602.1	597.1	590.0	580.6	571.2	561.8	552.4	545.6
47.5°	572.3	567.0	561.8	556.6	551.4	544.0	534.6	525.1	515.7	506.2	499.3
50°	544.0	538.4	532.7	527.1	521.5	513.8	504.1	494.4	484.6	474.9	467.8
52.5°	513.3	507.6	501.8	496.0	490.3	482.8	473.6	464.4	455.2	446.1	438.4
55°	468.1	462.6	457.2	451.7	446.3	438.7	429.2	419.6	410.1	400.5	392.8
57.5°	422.3	416.5	410.6	404.9	399.0	391.4	382.2	373.0	363.9	354.7	347.1
60°	392.8	386.9	380.9	375.0	369.0	361.4	352.1	343.0	333.8	324.6	317.1
62.5°	361.5	355.9	350.1	344.5	338.8	331.2	321.9	312.6	303.3	293.9	286.9
65°	316.9	311.1	305.3	299.5	293.7	286.3	277.2	268.2	259.1	250.1	243.3
67.5°	272.6	266.7	260.9	255.2	249.3	242.2	233.5	224.8	216.1	207.4	201.3
70°	242.5	236.7	230.9	225.1	219.2	212.1	203.6	195.1	186.5	178.0	172.7
72.5°	213.0	207.3	201.7	196.0	190.4	183.5	175.5	167.5	159.6	151.6	146.7
75°	168.8	163.7	158.5	153.5	148.3	142.2	135.0	127.8	120.7	113.5	109.8
77.5°	124.9	120.8	116.7	112.6	108.6	103.6	97.9	92.2	86.4	80.7	78.1
80°	99.8	95.6	91.6	87.5	83.4	79.0	74.1	69.4	64.6	59.9	58.3
82.5°	75.2	71.5	67.9	64.1	60.5	57.0	53.7	50.4	47.2	43.9	43.2
85°	42.2	39.1	36.1	33.0	29.9	28.0	27.1	26.3	25.4	24.5	24.3
87.5°	14.3	13.6	13.1	12.6	12.2	12.1	12.2	12.5	12.6	12.9	13.2
90°	1.2	2.3	4.6	7.1	9.4	11.7	12.9	15.2	16.5	18.8	20.0
92.5°	14.3	17.4	27.3	41.8	62.0	96.2	160.3	267.8	384.5	378.3	306.3
95°	38.7	39.9	49.3	62.2	88.0	140.8	266.4	524.5	848.4	1039.7	1017.3
97.5°	64.3	65.7	72.3	85.2	108.5	146.4	229.5	418.7	757.6	1110.2	1287.3
100°	82.1	84.5	89.2	102.1	124.4	159.6	227.6	380.2	675.9	1059.6	1352.9
102.5°	101.9	103.3	107.0	120.9	141.3	175.5	236.1	364.3	613.9	970.4	1313.5
105°	132.6	132.6	138.5	150.2	169.0	201.9	253.5	357.9	553.8	850.7	1187.5
107.5°	162.6	165.0	170.6	180.3	199.8	229.2	279.2	368.7	528.5	768.3	1058.9
110°	184.2	186.6	191.3	201.9	219.4	249.9	298.0	379.0	521.0	729.8	985.6



TEST NUMBER: P333549-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	205.8	208.1	211.9	222.5	240.0	269.6	315.9	392.1	521.0	707.3	931.2
115°	237.0	239.3	242.9	253.5	271.0	300.4	343.9	411.8	524.5	683.0	871.8
117.5°	265.2	268.7	272.5	283.1	303.0	331.3	372.4	434.4	532.3	671.0	836.4
120°	284.0	287.5	292.2	302.8	322.7	352.0	393.1	449.4	539.8	665.3	816.7
122.5°	303.7	306.3	310.0	320.5	342.4	371.7	412.8	466.4	546.3	660.7	799.8
125°	328.5	330.9	336.8	347.3	369.6	400.1	438.9	489.3	557.3	654.8	776.8
127.5°	348.0	351.5	359.1	372.4	396.2	426.7	463.9	510.5	569.8	652.0	755.7
130°	360.2	363.8	373.1	388.4	413.0	443.5	479.9	524.5	577.3	650.1	741.6
132.5°	369.6	374.1	385.4	402.5	428.1	458.6	494.9	536.7	585.7	650.1	730.3
135°	384.9	389.6	403.6	422.4	447.1	478.8	515.1	553.8	597.2	650.1	717.0
137.5°	404.1	407.7	420.8	439.6	463.7	496.3	529.5	566.5	607.8	651.5	705.0
140°	415.4	418.9	433.0	451.8	474.0	505.7	539.8	575.0	612.5	652.4	699.3
142.5°	428.5	431.1	444.2	463.0	484.4	514.2	546.3	579.7	615.3	653.4	694.7
145°	448.3	450.6	462.3	478.8	499.9	526.8	557.3	586.7	618.4	652.4	687.6
147.5°	468.9	470.3	480.4	495.6	513.9	537.7	564.4	591.0	619.6	649.3	680.3
150°	481.1	483.4	491.7	507.0	523.3	543.3	569.1	593.8	619.6	646.5	674.7
152.5°	494.2	495.6	502.9	516.3	531.8	549.9	573.8	595.6	618.6	642.8	668.1
155°	511.6	511.6	518.7	530.4	542.1	558.6	578.5	597.2	616.0	636.0	657.1
157.5°	527.1	526.8	532.5	542.6	552.9	565.3	582.5	598.4	613.0	628.9	646.8
160°	537.5	536.2	541.0	549.2	558.6	569.1	584.4	598.4	610.2	624.3	638.3
162.5°	545.8	544.7	549.4	556.6	564.2	572.9	586.2	597.5	607.3	618.6	630.9
165°	558.6	556.2	559.8	565.6	570.3	577.3	586.7	596.1	603.1	610.2	619.6
167.5°	567.0	565.8	567.9	571.2	574.5	579.0	586.7	593.3	596.5	602.0	608.5
170°	572.6	571.5	572.6	575.0	577.3	580.9	586.7	591.4	593.8	597.2	602.0
172.5°	576.4	574.3	575.4	577.7	579.2	580.9	585.7	589.6	590.0	591.7	595.4
175°	580.9	578.5	579.7	580.9	580.9	580.9	584.4	586.7	585.5	585.5	586.7
177.5°	583.0	581.1	581.1	582.0	581.1	581.1	583.0	583.9	582.0	582.0	583.0
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0



TEST NUMBER: P333549-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9
2.5°	1012.5	1013.8	1015.2	1015.8	1015.7	1015.5	1015.4	1015.3
5°	1006.2	1007.9	1009.7	1010.4	1010.0	1009.7	1009.4	1009.0
7.5°	993.7	994.9	996.1	996.5	996.1	995.7	995.4	995.0
10°	983.1	983.6	984.2	984.2	983.6	983.1	982.6	982.1
12.5°	968.2	968.6	968.9	968.7	967.9	967.1	966.3	965.5
15°	943.4	943.2	943.1	942.2	940.7	939.2	937.7	936.0
17.5°	912.6	911.7	910.9	909.8	908.6	907.3	906.1	904.7
20°	889.9	889.0	888.2	887.0	885.4	883.9	882.4	880.8
22.5°	867.4	865.7	864.0	862.5	861.3	860.0	858.8	857.5
25°	830.4	828.2	826.0	823.8	822.0	820.1	818.3	816.4
27.5°	790.4	787.3	784.2	781.7	779.9	778.1	776.3	774.5
30°	761.7	757.8	753.9	751.1	749.6	748.1	746.6	745.1
32.5°	733.9	729.6	725.3	722.2	720.1	718.2	716.3	714.4
35°	690.6	685.7	680.8	677.1	674.7	672.3	669.9	667.5
37.5°	645.4	639.4	633.5	629.3	627.0	624.8	622.5	620.2
40°	615.4	608.9	602.5	598.2	596.2	594.1	592.1	590.1
42.5°	585.9	579.7	573.5	568.9	565.9	562.9	559.9	556.9
45°	538.8	532.0	525.1	520.5	518.0	515.3	512.8	510.3
47.5°	492.2	485.1	478.2	473.2	470.4	467.6	464.7	461.9
50°	460.6	453.4	446.3	441.4	438.9	436.4	433.7	431.2
52.5°	430.7	422.9	415.3	410.1	407.6	405.1	402.4	399.9
55°	385.2	377.5	369.8	364.7	361.9	359.2	356.5	353.8
57.5°	339.6	332.1	324.7	319.6	317.2	314.8	312.5	310.0
60°	309.5	302.1	294.6	289.5	287.0	284.4	281.9	279.3
62.5°	279.9	273.0	266.0	261.3	258.7	256.2	253.6	251.1
65°	236.5	229.6	222.9	218.1	215.6	213.1	210.5	207.9
67.5°	195.0	188.7	182.5	178.3	176.3	174.3	172.2	170.2
70°	167.4	162.2	156.8	153.2	151.2	149.2	147.0	145.0
72.5°	141.9	136.9	132.1	129.0	127.6	126.2	124.9	123.5
75°	106.0	102.3	98.6	96.0	94.9	93.7	92.5	91.3
77.5°	75.4	72.8	70.2	68.5	67.6	66.7	65.8	64.9
80°	56.8	55.2	53.7	52.8	52.4	52.1	51.7	51.4
82.5°	42.4	41.7	41.0	40.6	40.4	40.2	40.0	39.8
85°	24.2	24.0	23.8	23.7	23.5	23.3	23.2	23.0
87.5°	13.4	13.6	13.9	14.3	14.1	14.0	14.1	14.0
90°	21.1	22.3	23.4	25.9	25.9	25.9	27.0	27.0
92.5°	207.9	150.9	113.6	96.2	81.2	78.4	76.7	74.8
95°	843.6	665.3	521.0	422.4	339.1	303.9	294.6	275.8
97.5°	1256.5	1131.5	990.9	853.7	781.2	715.6	681.6	666.5
100°	1443.3	1385.8	1265.0	1142.9	1062.0	977.4	934.0	915.2
102.5°	1506.2	1541.7	1483.7	1401.1	1314.4	1254.4	1207.2	1193.2
105°	1469.2	1629.9	1681.5	1668.6	1631.0	1592.4	1568.8	1554.8
107.5°	1336.8	1551.3	1683.8	1745.1	1764.1	1763.9	1756.2	1746.8
110°	1239.1	1462.1	1627.5	1727.3	1780.1	1802.4	1810.6	1810.6



TEST NUMBER: P333549-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1162.2	1373.8	1541.2	1658.7	1736.0	1774.2	1794.6	1803.1
115°	1065.5	1247.4	1408.1	1536.0	1627.5	1683.8	1716.7	1731.9
117.5°	1003.0	1159.8	1298.3	1415.6	1507.1	1565.4	1598.0	1607.3
120°	969.3	1110.0	1239.1	1342.4	1429.3	1485.5	1517.2	1526.6
122.5°	943.9	1074.4	1189.4	1286.1	1363.5	1415.1	1446.8	1455.3
125°	907.1	1026.7	1128.8	1213.4	1279.0	1327.2	1352.9	1364.7
127.5°	869.5	981.2	1076.5	1155.6	1215.2	1257.7	1282.1	1287.3
130°	846.1	949.3	1040.9	1117.1	1175.8	1214.5	1238.0	1245.0
132.5°	822.5	919.3	1002.3	1075.8	1134.5	1173.2	1194.8	1202.7
135°	792.0	873.0	948.2	1015.0	1066.6	1105.4	1126.5	1133.6
137.5°	766.3	831.7	894.1	951.0	997.1	1032.4	1051.9	1059.6
140°	752.1	807.3	861.3	910.6	954.0	984.5	1002.1	1007.9
142.5°	739.9	786.7	833.1	875.9	912.7	938.5	955.1	960.1
145°	724.0	760.3	796.8	828.4	856.6	876.6	889.5	894.1
147.5°	709.0	738.5	766.5	790.4	812.7	828.7	836.2	838.3
150°	700.5	726.4	748.6	769.7	787.4	801.4	806.2	807.3
152.5°	691.2	714.2	734.6	751.0	765.8	777.0	781.7	782.9
155°	677.0	695.8	712.3	725.2	736.9	745.1	748.6	749.8
157.5°	663.0	678.4	691.2	701.3	710.3	717.2	720.4	720.2
160°	653.6	665.3	677.0	685.3	693.5	699.3	701.8	700.5
162.5°	643.3	654.1	663.9	671.2	677.5	682.5	683.0	682.7
165°	628.9	637.1	644.2	650.1	654.8	657.1	657.1	657.1
167.5°	615.3	620.8	626.1	630.4	632.7	634.8	633.9	633.7
170°	607.8	611.4	614.9	617.2	619.6	620.8	620.8	619.6
172.5°	599.4	602.9	605.5	606.9	607.3	609.5	607.6	606.4
175°	590.3	590.3	592.6	592.6	592.6	593.8	591.4	590.3
177.5°	583.9	584.8	584.8	584.8	583.9	584.8	582.0	582.0
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0

(END OF REPORT)