

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333525-840

Luminaire Tested: **S125RDIP-S610D365U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333525-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S610D365U840-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3728.5 lumens
Efficiency: N/A
Efficacy: 135.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333525-840

CATALOG NUMBER: S125RDIP-S610D365U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333525-840

CATALOG NUMBER: S125RDIP-S610D365U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	64
1	101	97	93	90	95	91	88	85	81	78	76	71	69	67	62	60	59	55
2	92	85	79	74	87	80	75	70	71	67	63	63	59	57	55	52	50	46
3	85	75	68	62	79	71	64	59	63	58	53	56	52	48	49	46	43	40
4	78	67	59	53	73	63	56	50	56	50	46	50	45	42	44	40	37	34
5	71	60	51	45	67	56	49	43	50	44	40	45	40	36	39	36	33	30
6	66	54	45	39	62	51	43	38	45	39	35	41	36	32	36	32	29	26
7	61	49	40	35	57	46	39	34	41	35	31	37	32	28	33	29	26	23
8	57	44	36	31	53	42	35	30	38	32	28	34	29	25	30	26	23	21
9	53	40	33	28	50	39	32	27	35	29	25	31	26	23	28	24	21	19
10	50	37	30	25	47	36	29	24	32	26	23	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6561	6561	6561
5°	6576	6501	6541
10°	6526	6441	6441
15°	6449	6310	6258
20°	6349	6128	6054
25°	6233	5949	5818
30°	6088	5739	5557
35°	5941	5523	5263
40°	5802	5298	4975
45°	5634	5045	4661
50°	5466	4772	4332
55°	5271	4510	3984
60°	5074	4193	3608
65°	4843	3822	3177
70°	4579	3361	2738
75°	4212	2832	2278
80°	3712	2228	1912
85°	3127	1815	1704



TEST NUMBER: P333525-840

CATALOG NUMBER: S125RDIP-S610D365U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.5	2.6
10°-20°	267.0	7.2
20°-30°	387.1	10.4
30°-40°	441.2	11.8
40°-50°	430.0	11.5
50°-60°	362.0	9.7
60°-70°	253.8	6.8
70°-80°	130.4	3.5
80°-90°	33.9	0.9
90°-100°	128.3	3.4
100°-110°	275.8	7.4
110°-120°	258.9	6.9
120°-130°	209.8	5.6
130°-140°	168.4	4.5
140°-150°	127.0	3.4
150°-160°	89.4	2.4
160°-170°	52.7	1.4
170°-180°	17.1	0.5
0°-30°	749.6	20.1
0°-40°	1190.8	31.9
0°-60°	1982.8	53.2
0°-90°	2400.9	64.4
90°-120°	663.0	17.8
90°-150°	1168.2	31.3
90°-180°	1328.0	35.6
0°-180°	3728.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1016	1016	1016	1016	1016	
5°	1014	1011	1003	1010	1009	96
15°	964	959	944	943	936	272
25°	875	862	835	825	816	402
35°	754	734	700	679	668	472
45°	617	594	552	523	510	476
55°	468	442	400	367	354	418
65°	317	290	250	220	208	314
75°	169	145	114	97	91	179
85°	42	29	24	24	23	47
90°	0	3	6	8	8	3
95°	12	35	316	143	84	13
105°	40	56	259	510	473	43
115°	72	87	208	448	527	71
125°	100	117	199	356	415	89
135°	117	141	198	299	345	91
145°	136	156	198	247	272	85
155°	156	167	194	219	228	72
165°	170	175	186	197	200	48
175°	177	177	178	180	180	17
180°	177	177	177	177	177	



TEST NUMBER: P333525-840

CATALOG NUMBER: S125RDIP-S610D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9
2.5°	1017.7	1017.3	1016.9	1016.5	1016.1	1015.2	1013.8	1012.5	1011.1	1009.8	1011.1
5°	1014.3	1013.7	1013.0	1012.3	1011.6	1010.4	1008.5	1006.6	1004.7	1002.8	1004.5
7.5°	1004.4	1003.7	1003.1	1002.4	1001.8	1000.4	998.0	995.8	993.6	991.3	992.5
10°	995.1	994.6	994.1	993.6	993.1	991.7	989.3	986.9	984.5	982.1	982.6
12.5°	984.7	984.1	983.4	982.8	982.1	980.2	977.0	973.8	970.6	967.3	967.8
15°	964.5	963.4	962.4	961.4	960.4	958.1	954.5	950.9	947.4	943.7	943.6
17.5°	941.6	940.1	938.5	937.0	935.3	932.3	927.8	923.3	918.8	914.3	913.4
20°	923.8	922.1	920.4	918.7	917.0	913.4	908.0	902.5	897.1	891.6	890.7
22.5°	904.1	902.4	900.8	899.1	897.4	893.6	887.9	882.2	876.5	870.7	869.1
25°	874.7	872.1	869.6	867.1	864.4	860.0	853.7	847.4	841.1	834.8	832.6
27.5°	840.9	837.9	834.8	831.6	828.5	823.6	816.9	810.1	803.3	796.6	793.5
30°	816.4	813.1	809.9	806.7	803.4	798.2	791.0	784.0	776.8	769.6	765.7
32.5°	792.4	788.7	784.9	781.1	777.3	771.7	764.5	757.2	749.8	742.6	738.2
35°	753.5	749.4	745.3	741.2	737.1	731.2	723.6	715.9	708.2	700.5	695.6
37.5°	715.3	710.2	705.3	700.3	695.4	688.9	681.0	673.1	665.2	657.2	651.4
40°	688.2	683.2	678.0	672.9	667.8	661.2	653.0	644.8	636.6	628.4	622.0
42.5°	660.0	654.8	649.5	644.3	639.0	632.2	623.7	615.2	606.8	598.3	592.1
45°	616.9	612.0	607.0	602.1	597.1	590.0	580.6	571.2	561.8	552.4	545.6
47.5°	572.3	567.0	561.8	556.6	551.4	544.0	534.6	525.1	515.7	506.2	499.3
50°	544.0	538.4	532.7	527.1	521.5	513.8	504.1	494.4	484.6	474.9	467.8
52.5°	513.3	507.6	501.8	496.0	490.3	482.8	473.6	464.4	455.2	446.1	438.4
55°	468.1	462.6	457.2	451.7	446.3	438.7	429.2	419.6	410.1	400.5	392.8
57.5°	422.3	416.5	410.6	404.9	399.0	391.4	382.2	373.0	363.9	354.7	347.1
60°	392.8	386.9	380.9	375.0	369.0	361.4	352.1	343.0	333.8	324.6	317.1
62.5°	361.5	355.9	350.1	344.5	338.8	331.2	321.9	312.6	303.3	293.9	286.9
65°	316.9	311.1	305.3	299.5	293.7	286.3	277.2	268.2	259.1	250.1	243.3
67.5°	272.6	266.7	260.9	255.2	249.3	242.2	233.5	224.8	216.1	207.4	201.3
70°	242.5	236.7	230.9	225.1	219.2	212.1	203.6	195.1	186.5	178.0	172.7
72.5°	213.0	207.3	201.7	196.0	190.4	183.5	175.5	167.5	159.6	151.6	146.7
75°	168.8	163.7	158.5	153.5	148.3	142.2	135.0	127.8	120.7	113.5	109.8
77.5°	124.9	120.8	116.7	112.6	108.6	103.6	97.9	92.2	86.4	80.7	78.1
80°	99.8	95.6	91.6	87.5	83.4	79.0	74.1	69.4	64.6	59.9	58.3
82.5°	75.2	71.5	67.9	64.1	60.5	57.0	53.7	50.4	47.2	43.9	43.2
85°	42.2	39.1	36.1	33.0	29.9	28.0	27.1	26.3	25.4	24.5	24.3
87.5°	14.2	13.3	12.5	11.7	10.9	10.5	10.4	10.4	10.3	10.3	10.4
90°	0.4	0.7	1.4	2.1	2.8	3.5	3.9	4.6	4.9	5.8	6.1
92.5°	4.3	5.3	8.3	12.7	18.9	29.3	48.8	81.4	116.9	115.0	93.1
95°	11.8	12.1	14.9	18.9	26.8	42.8	81.0	159.6	258.0	316.2	309.4
97.5°	19.6	20.0	22.0	26.0	33.0	44.5	69.8	127.3	230.5	337.7	391.5
100°	24.9	25.7	27.2	31.0	37.9	48.6	69.3	115.6	205.6	322.2	411.5
102.5°	31.0	31.4	32.5	36.8	43.0	53.4	71.8	110.8	186.7	295.2	399.5
105°	40.3	40.3	42.1	45.6	51.4	61.4	77.1	108.9	168.4	258.7	361.2
107.5°	49.5	50.2	51.9	54.8	60.8	69.8	84.9	112.1	160.8	233.7	322.0
110°	56.0	56.8	58.2	61.4	66.8	76.0	90.7	115.3	158.4	222.0	299.8



TEST NUMBER: P333525-840

CATALOG NUMBER: S125RDIP-S610D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	62.6	63.3	64.4	67.7	73.0	82.0	96.0	119.3	158.4	215.1	283.3
115°	72.1	72.8	73.9	77.1	82.4	91.4	104.6	125.2	159.6	207.7	265.2
117.5°	80.7	81.7	82.9	86.0	92.2	100.8	113.3	132.1	161.9	204.1	254.4
120°	86.3	87.5	88.9	92.1	98.2	107.0	119.6	136.7	164.2	202.4	248.4
122.5°	92.4	93.1	94.3	97.6	104.1	113.1	125.5	141.8	166.1	201.0	243.3
125°	100.0	100.7	102.4	105.6	112.4	121.7	133.5	148.9	169.6	199.1	236.3
127.5°	105.8	106.9	109.2	113.3	120.5	129.8	141.1	155.2	173.3	198.3	229.8
130°	109.6	110.7	113.5	118.2	125.6	134.9	145.9	159.6	175.6	197.7	225.6
132.5°	112.4	113.8	117.2	122.4	130.2	139.5	150.6	163.3	178.1	197.7	222.2
135°	117.0	118.5	122.8	128.5	136.0	145.6	156.6	168.4	181.7	197.7	218.0
137.5°	122.9	124.0	127.9	133.7	141.1	151.0	161.1	172.3	184.9	198.1	214.4
140°	126.3	127.4	131.7	137.4	144.2	153.8	164.2	174.9	186.3	198.4	212.7
142.5°	130.4	131.1	135.1	140.9	147.3	156.4	166.1	176.3	187.1	198.7	211.3
145°	136.3	137.0	140.6	145.6	152.1	160.3	169.6	178.4	188.0	198.4	209.1
147.5°	142.6	143.0	146.1	150.8	156.3	163.5	171.7	179.8	188.4	197.5	206.9
150°	146.3	147.0	149.6	154.2	159.2	165.2	173.1	180.6	188.4	196.6	205.2
152.5°	150.4	150.8	153.0	157.0	161.8	167.2	174.5	181.2	188.1	195.5	203.2
155°	155.6	155.6	157.7	161.3	164.9	169.9	175.9	181.7	187.3	193.5	199.9
157.5°	160.4	160.3	162.0	165.0	168.1	172.0	177.1	182.0	186.4	191.3	196.7
160°	163.5	163.1	164.5	167.0	169.9	173.1	177.7	182.0	185.6	189.9	194.2
162.5°	166.0	165.7	167.1	169.4	171.6	174.2	178.3	181.8	184.7	188.1	191.9
165°	169.9	169.2	170.3	172.0	173.5	175.6	178.4	181.3	183.5	185.6	188.4
167.5°	172.5	172.1	172.8	173.7	174.7	176.1	178.4	180.5	181.5	183.1	185.1
170°	174.2	173.8	174.2	174.9	175.6	176.6	178.4	179.9	180.6	181.7	183.1
172.5°	175.3	174.7	175.0	175.7	176.1	176.6	178.1	179.4	179.5	180.0	181.1
175°	176.6	175.9	176.3	176.6	176.6	176.6	177.7	178.4	178.1	178.1	178.4
177.5°	177.3	176.7	176.7	177.0	176.7	176.7	177.3	177.6	177.0	177.0	177.3
180°	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0



TEST NUMBER: P333525-840

CATALOG NUMBER: S125RDIP-S610D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9
2.5°	1012.5	1013.8	1015.2	1015.8	1015.7	1015.5	1015.4	1015.3
5°	1006.2	1007.9	1009.7	1010.4	1010.0	1009.7	1009.4	1009.0
7.5°	993.7	994.9	996.1	996.5	996.1	995.7	995.4	995.0
10°	983.1	983.6	984.2	984.2	983.6	983.1	982.6	982.1
12.5°	968.2	968.6	968.9	968.7	967.9	967.1	966.3	965.5
15°	943.4	943.2	943.1	942.2	940.7	939.2	937.7	936.0
17.5°	912.6	911.7	910.9	909.8	908.6	907.3	906.1	904.7
20°	889.9	889.0	888.2	887.0	885.4	883.9	882.4	880.8
22.5°	867.4	865.7	864.0	862.5	861.3	860.0	858.8	857.5
25°	830.4	828.2	826.0	823.8	822.0	820.1	818.3	816.4
27.5°	790.4	787.3	784.2	781.7	779.9	778.1	776.3	774.5
30°	761.7	757.8	753.9	751.1	749.6	748.1	746.6	745.1
32.5°	733.9	729.6	725.3	722.2	720.1	718.2	716.3	714.4
35°	690.6	685.7	680.8	677.1	674.7	672.3	669.9	667.5
37.5°	645.4	639.4	633.5	629.3	627.0	624.8	622.5	620.2
40°	615.4	608.9	602.5	598.2	596.2	594.1	592.1	590.1
42.5°	585.9	579.7	573.5	568.9	565.9	562.9	559.9	556.9
45°	538.8	532.0	525.1	520.5	518.0	515.3	512.8	510.3
47.5°	492.2	485.1	478.2	473.2	470.4	467.6	464.7	461.9
50°	460.6	453.4	446.3	441.4	438.9	436.4	433.7	431.2
52.5°	430.7	422.9	415.3	410.1	407.6	405.1	402.4	399.9
55°	385.2	377.5	369.8	364.7	361.9	359.2	356.5	353.8
57.5°	339.6	332.1	324.7	319.6	317.2	314.8	312.5	310.0
60°	309.5	302.1	294.6	289.5	287.0	284.4	281.9	279.3
62.5°	279.9	273.0	266.0	261.3	258.7	256.2	253.6	251.1
65°	236.5	229.6	222.9	218.1	215.6	213.1	210.5	207.9
67.5°	195.0	188.7	182.5	178.3	176.3	174.3	172.2	170.2
70°	167.4	162.2	156.8	153.2	151.2	149.2	147.0	145.0
72.5°	141.9	136.9	132.1	129.0	127.6	126.2	124.9	123.5
75°	106.0	102.3	98.6	96.0	94.9	93.7	92.5	91.3
77.5°	75.4	72.8	70.2	68.5	67.6	66.7	65.8	64.9
80°	56.8	55.2	53.7	52.8	52.4	52.1	51.7	51.4
82.5°	42.4	41.7	41.0	40.6	40.4	40.2	40.0	39.8
85°	24.2	24.0	23.8	23.7	23.5	23.3	23.2	23.0
87.5°	10.5	10.6	10.6	10.7	10.6	10.4	10.4	10.2
90°	6.5	6.8	7.2	7.9	7.9	7.9	8.2	8.2
92.5°	63.2	45.8	34.5	29.3	24.7	23.8	23.3	22.7
95°	256.6	202.4	158.4	128.5	103.1	92.4	89.6	83.9
97.5°	382.1	344.2	301.3	259.6	237.6	217.6	207.3	202.7
100°	439.0	421.5	384.8	347.6	323.0	297.3	284.1	278.4
102.5°	458.1	468.9	451.3	426.2	399.8	381.5	367.2	362.9
105°	446.9	495.7	511.4	507.6	496.0	484.3	477.2	472.9
107.5°	406.6	471.8	512.1	530.8	536.5	536.5	534.1	531.3
110°	376.9	444.7	495.0	525.3	541.4	548.2	550.7	550.7



TEST NUMBER: P333525-840

CATALOG NUMBER: S125RDIP-S610D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	353.5	417.9	468.8	504.5	528.0	539.7	545.8	548.5
115°	324.1	379.4	428.3	467.2	495.0	512.1	522.1	526.7
117.5°	305.1	352.7	394.9	430.6	458.4	476.2	486.0	488.9
120°	294.8	337.6	376.9	408.3	434.7	451.8	461.5	464.3
122.5°	287.1	326.8	361.7	391.1	414.8	430.4	440.1	442.6
125°	275.9	312.3	343.4	369.0	389.0	403.6	411.5	415.1
127.5°	264.5	298.4	327.4	351.4	369.6	382.5	389.9	391.5
130°	257.3	288.7	316.6	339.8	357.6	369.4	376.6	378.7
132.5°	250.1	279.6	304.9	327.2	345.1	356.8	363.3	365.8
135°	241.0	265.5	288.4	308.7	324.5	336.2	342.6	344.8
137.5°	233.1	253.0	272.0	289.2	303.3	314.0	319.9	322.2
140°	228.7	245.5	262.0	276.9	290.1	299.4	304.8	306.6
142.5°	225.1	239.2	253.4	266.4	277.6	285.5	290.5	292.1
145°	220.3	231.3	242.4	252.0	260.5	266.6	270.5	272.0
147.5°	215.6	224.6	233.2	240.4	247.2	252.1	254.3	255.0
150°	213.1	221.0	227.7	234.1	239.4	243.8	245.2	245.5
152.5°	210.3	217.2	223.4	228.4	232.9	236.3	237.7	238.1
155°	205.9	211.7	216.6	220.6	224.1	226.6	227.7	228.0
157.5°	201.7	206.3	210.3	213.3	216.1	218.1	219.1	219.0
160°	198.8	202.4	205.9	208.4	211.0	212.7	213.4	213.1
162.5°	195.6	198.9	202.0	204.2	206.1	207.5	207.7	207.6
165°	191.3	193.8	195.9	197.7	199.1	199.9	199.9	199.9
167.5°	187.1	188.8	190.5	191.8	192.5	193.1	192.8	192.7
170°	184.9	185.9	187.0	187.7	188.4	188.8	188.8	188.4
172.5°	182.3	183.4	184.2	184.6	184.7	185.4	184.8	184.4
175°	179.6	179.6	180.3	180.3	180.3	180.6	179.9	179.6
177.5°	177.6	177.8	177.8	177.8	177.6	177.8	177.0	177.0
180°	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0

(END OF REPORT)