

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333530-840

Luminaire Tested: **S125RDIP-S610D590U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333530-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S610D590U840-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4467.3 lumens
Efficiency: N/A
Efficacy: 136.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333530-840

CATALOG NUMBER: S125RDIP-S610D590U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333530-840

CATALOG NUMBER: S125RDIP-S610D590U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60	54
1	99	95	91	87	92	88	85	82	75	73	71	64	62	60	53	52	51	46
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	39
3	82	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37	33
4	76	65	57	51	70	60	53	48	52	47	43	45	41	37	37	34	32	28
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	34	31	28	25
6	64	52	44	38	59	49	41	36	42	37	32	36	32	28	31	27	25	22
7	59	47	39	34	55	44	37	32	38	33	29	33	29	25	28	25	22	20
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	22	20	18
9	51	39	32	27	48	37	30	25	32	27	23	28	24	20	24	20	18	16
10	48	36	29	24	45	34	27	23	30	24	21	26	22	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6561	6561	6561
5°	6576	6501	6541
10°	6526	6441	6441
15°	6449	6310	6258
20°	6349	6128	6054
25°	6233	5949	5818
30°	6088	5739	5557
35°	5941	5523	5263
40°	5802	5298	4975
45°	5634	5045	4661
50°	5466	4772	4332
55°	5271	4510	3984
60°	5074	4193	3608
65°	4843	3822	3177
70°	4579	3361	2738
75°	4212	2832	2278
80°	3712	2228	1912
85°	3127	1815	1704



TEST NUMBER: P333530-840

CATALOG NUMBER: S125RDIP-S610D590U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.5	2.1
10°-20°	267.0	6.0
20°-30°	387.1	8.7
30°-40°	441.2	9.9
40°-50°	430.0	9.6
50°-60°	362.0	8.1
60°-70°	253.8	5.7
70°-80°	130.4	2.9
80°-90°	34.6	0.8
90°-100°	49.6	1.1
100°-110°	146.4	3.3
110°-120°	248.0	5.6
120°-130°	326.4	7.3
130°-140°	365.7	8.2
140°-150°	358.4	8.0
150°-160°	301.1	6.7
160°-170°	200.1	4.5
170°-180°	70.0	1.6
0°-30°	749.6	16.8
0°-40°	1190.8	26.7
0°-60°	1982.8	44.4
0°-90°	2401.6	53.8
90°-120°	444.0	9.9
90°-150°	1494.5	33.5
90°-180°	2066.0	46.2
0°-180°	4467.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1016	1016	1016	1016	1016	
5°	1014	1011	1003	1010	1009	96
15°	964	959	944	943	936	272
25°	875	862	835	825	816	402
35°	754	734	700	679	668	472
45°	617	594	552	523	510	476
55°	468	442	400	367	354	418
65°	317	290	250	220	208	314
75°	169	145	114	97	91	179
85°	42	29	24	24	23	47
90°	1	5	9	12	14	4
95°	38	39	44	48	50	40
105°	131	134	138	141	143	140
115°	248	250	252	251	251	245
125°	362	366	366	365	365	324
135°	471	474	475	475	473	363
145°	571	573	575	575	573	357
155°	653	653	654	656	653	301
165°	710	709	710	712	709	200
175°	738	736	736	739	736	70
180°	740	740	740	740	740	



TEST NUMBER: P333530-840

CATALOG NUMBER: S125RDIP-S610D590U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9
2.5°	1017.7	1017.3	1016.9	1016.5	1016.1	1015.2	1013.8	1012.5	1011.1	1009.8	1011.1
5°	1014.3	1013.7	1013.0	1012.3	1011.6	1010.4	1008.5	1006.6	1004.7	1002.8	1004.5
7.5°	1004.4	1003.7	1003.1	1002.4	1001.8	1000.4	998.0	995.8	993.6	991.3	992.5
10°	995.1	994.6	994.1	993.6	993.1	991.7	989.3	986.9	984.5	982.1	982.6
12.5°	984.7	984.1	983.4	982.8	982.1	980.2	977.0	973.8	970.6	967.3	967.8
15°	964.5	963.4	962.4	961.4	960.4	958.1	954.5	950.9	947.4	943.7	943.6
17.5°	941.6	940.1	938.5	937.0	935.3	932.3	927.8	923.3	918.8	914.3	913.4
20°	923.8	922.1	920.4	918.7	917.0	913.4	908.0	902.5	897.1	891.6	890.7
22.5°	904.1	902.4	900.8	899.1	897.4	893.6	887.9	882.2	876.5	870.7	869.1
25°	874.7	872.1	869.6	867.1	864.4	860.0	853.7	847.4	841.1	834.8	832.6
27.5°	840.9	837.9	834.8	831.6	828.5	823.6	816.9	810.1	803.3	796.6	793.5
30°	816.4	813.1	809.9	806.7	803.4	798.2	791.0	784.0	776.8	769.6	765.7
32.5°	792.4	788.7	784.9	781.1	777.3	771.7	764.5	757.2	749.8	742.6	738.2
35°	753.5	749.4	745.3	741.2	737.1	731.2	723.6	715.9	708.2	700.5	695.6
37.5°	715.3	710.2	705.3	700.3	695.4	688.9	681.0	673.1	665.2	657.2	651.4
40°	688.2	683.2	678.0	672.9	667.8	661.2	653.0	644.8	636.6	628.4	622.0
42.5°	660.0	654.8	649.5	644.3	639.0	632.2	623.7	615.2	606.8	598.3	592.1
45°	616.9	612.0	607.0	602.1	597.1	590.0	580.6	571.2	561.8	552.4	545.6
47.5°	572.3	567.0	561.8	556.6	551.4	544.0	534.6	525.1	515.7	506.2	499.3
50°	544.0	538.4	532.7	527.1	521.5	513.8	504.1	494.4	484.6	474.9	467.8
52.5°	513.3	507.6	501.8	496.0	490.3	482.8	473.6	464.4	455.2	446.1	438.4
55°	468.1	462.6	457.2	451.7	446.3	438.7	429.2	419.6	410.1	400.5	392.8
57.5°	422.3	416.5	410.6	404.9	399.0	391.4	382.2	373.0	363.9	354.7	347.1
60°	392.8	386.9	380.9	375.0	369.0	361.4	352.1	343.0	333.8	324.6	317.1
62.5°	361.5	355.9	350.1	344.5	338.8	331.2	321.9	312.6	303.3	293.9	286.9
65°	316.9	311.1	305.3	299.5	293.7	286.3	277.2	268.2	259.1	250.1	243.3
67.5°	272.6	266.7	260.9	255.2	249.3	242.2	233.5	224.8	216.1	207.4	201.3
70°	242.5	236.7	230.9	225.1	219.2	212.1	203.6	195.1	186.5	178.0	172.7
72.5°	213.0	207.3	201.7	196.0	190.4	183.5	175.5	167.5	159.6	151.6	146.7
75°	168.8	163.7	158.5	153.5	148.3	142.2	135.0	127.8	120.7	113.5	109.8
77.5°	124.9	120.8	116.7	112.6	108.6	103.6	97.9	92.2	86.4	80.7	78.1
80°	99.8	95.6	91.6	87.5	83.4	79.0	74.1	69.4	64.6	59.9	58.3
82.5°	75.2	71.5	67.9	64.1	60.5	57.0	53.7	50.4	47.2	43.9	43.2
85°	42.2	39.1	36.1	33.0	29.9	28.0	27.1	26.3	25.4	24.5	24.3
87.5°	14.2	13.5	12.7	12.0	11.2	10.9	10.9	11.0	11.0	11.0	11.2
90°	0.6	1.6	2.6	3.6	4.6	5.7	6.6	7.5	8.3	9.2	9.9
92.5°	13.9	14.6	15.3	16.1	16.8	17.7	18.8	19.9	21.0	22.1	22.9
95°	37.5	37.7	38.0	38.2	38.5	39.3	40.5	41.8	43.1	44.3	45.2
97.5°	62.2	62.3	62.4	62.5	62.6	63.5	65.3	67.1	68.9	70.6	71.5
100°	80.7	80.7	80.7	80.7	80.7	81.5	83.1	84.8	86.4	88.2	89.3
102.5°	100.5	101.0	101.5	102.0	102.5	103.2	104.0	104.9	105.7	106.5	107.9
105°	131.4	132.0	132.6	133.3	133.9	134.6	135.4	136.1	136.9	137.6	138.5
107.5°	165.4	166.1	166.7	167.3	168.0	168.6	169.3	169.8	170.4	171.0	171.4
110°	188.9	189.6	190.3	190.9	191.6	192.1	192.4	192.8	193.2	193.6	194.0



TEST NUMBER: P333530-840

CATALOG NUMBER: S125RDIP-S610D590U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	212.9	213.3	213.6	213.9	214.3	214.7	215.2	215.6	216.1	216.6	216.8
115°	248.3	248.8	249.3	249.8	250.3	250.7	251.0	251.3	251.5	251.8	251.7
117.5°	283.8	284.0	284.3	284.5	284.7	285.0	285.2	285.4	285.6	285.9	286.0
120°	305.9	306.6	307.2	307.8	308.5	308.8	309.0	309.1	309.2	309.3	309.3
122.5°	329.9	330.1	330.3	330.5	330.8	331.0	331.4	331.7	332.0	332.4	332.3
125°	362.3	363.1	363.9	364.7	365.5	365.9	366.0	366.2	366.3	366.4	366.2
127.5°	397.0	397.4	397.8	398.2	398.7	399.0	399.1	399.3	399.4	399.6	399.5
130°	417.7	418.3	419.0	419.6	420.2	420.7	420.9	421.2	421.4	421.7	421.6
132.5°	438.4	439.5	440.5	441.5	442.6	443.1	443.0	443.0	442.9	442.9	442.8
135°	471.2	472.0	472.8	473.5	474.3	474.7	474.9	475.0	475.1	475.2	475.2
137.5°	502.1	502.9	503.6	504.3	505.1	505.6	505.9	506.1	506.4	506.8	506.9
140°	521.9	522.6	523.2	523.8	524.5	525.0	525.4	525.8	526.1	526.5	526.8
142.5°	541.8	542.3	542.8	543.4	543.9	544.4	544.9	545.4	545.9	546.3	546.5
145°	570.9	571.4	572.0	572.5	573.0	573.4	573.8	574.2	574.6	574.9	574.9
147.5°	597.8	598.1	598.4	598.7	599.1	599.3	599.6	600.0	600.3	600.6	600.9
150°	615.8	615.7	615.6	615.5	615.3	615.5	616.0	616.5	617.0	617.5	617.5
152.5°	630.6	630.8	631.0	631.2	631.3	631.5	631.7	631.9	632.1	632.4	632.7
155°	653.3	653.3	653.3	653.3	653.3	653.4	653.5	653.6	653.8	653.9	654.4
157.5°	673.6	673.3	673.0	672.8	672.5	672.4	672.5	672.7	672.8	672.9	673.4
160°	685.6	685.2	684.8	684.4	684.0	683.9	684.0	684.2	684.3	684.4	684.9
162.5°	696.2	695.9	695.6	695.3	695.0	694.9	694.9	695.0	695.0	695.0	695.6
165°	710.3	710.0	709.8	709.5	709.3	709.2	709.3	709.5	709.6	709.7	710.2
167.5°	722.4	721.9	721.2	720.7	720.2	720.0	720.0	720.0	720.0	720.0	720.7
170°	728.7	728.2	727.7	727.2	726.7	726.5	726.5	726.5	726.5	726.5	727.2
172.5°	733.4	732.9	732.4	731.8	731.3	731.0	731.0	731.0	731.0	731.0	731.8
175°	738.5	738.0	737.5	737.0	736.5	736.3	736.3	736.3	736.3	736.3	737.0
177.5°	741.2	740.8	740.4	740.0	739.5	739.3	739.2	739.1	739.0	738.9	739.5
180°	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3



TEST NUMBER: P333530-840

CATALOG NUMBER: S125RDIP-S610D590U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9
2.5°	1012.5	1013.8	1015.2	1015.8	1015.7	1015.5	1015.4	1015.3
5°	1006.2	1007.9	1009.7	1010.4	1010.0	1009.7	1009.4	1009.0
7.5°	993.7	994.9	996.1	996.5	996.1	995.7	995.4	995.0
10°	983.1	983.6	984.2	984.2	983.6	983.1	982.6	982.1
12.5°	968.2	968.6	968.9	968.7	967.9	967.1	966.3	965.5
15°	943.4	943.2	943.1	942.2	940.7	939.2	937.7	936.0
17.5°	912.6	911.7	910.9	909.8	908.6	907.3	906.1	904.7
20°	889.9	889.0	888.2	887.0	885.4	883.9	882.4	880.8
22.5°	867.4	865.7	864.0	862.5	861.3	860.0	858.8	857.5
25°	830.4	828.2	826.0	823.8	822.0	820.1	818.3	816.4
27.5°	790.4	787.3	784.2	781.7	779.9	778.1	776.3	774.5
30°	761.7	757.8	753.9	751.1	749.6	748.1	746.6	745.1
32.5°	733.9	729.6	725.3	722.2	720.1	718.2	716.3	714.4
35°	690.6	685.7	680.8	677.1	674.7	672.3	669.9	667.5
37.5°	645.4	639.4	633.5	629.3	627.0	624.8	622.5	620.2
40°	615.4	608.9	602.5	598.2	596.2	594.1	592.1	590.1
42.5°	585.9	579.7	573.5	568.9	565.9	562.9	559.9	556.9
45°	538.8	532.0	525.1	520.5	518.0	515.3	512.8	510.3
47.5°	492.2	485.1	478.2	473.2	470.4	467.6	464.7	461.9
50°	460.6	453.4	446.3	441.4	438.9	436.4	433.7	431.2
52.5°	430.7	422.9	415.3	410.1	407.6	405.1	402.4	399.9
55°	385.2	377.5	369.8	364.7	361.9	359.2	356.5	353.8
57.5°	339.6	332.1	324.7	319.6	317.2	314.8	312.5	310.0
60°	309.5	302.1	294.6	289.5	287.0	284.4	281.9	279.3
62.5°	279.9	273.0	266.0	261.3	258.7	256.2	253.6	251.1
65°	236.5	229.6	222.9	218.1	215.6	213.1	210.5	207.9
67.5°	195.0	188.7	182.5	178.3	176.3	174.3	172.2	170.2
70°	167.4	162.2	156.8	153.2	151.2	149.2	147.0	145.0
72.5°	141.9	136.9	132.1	129.0	127.6	126.2	124.9	123.5
75°	106.0	102.3	98.6	96.0	94.9	93.7	92.5	91.3
77.5°	75.4	72.8	70.2	68.5	67.6	66.7	65.8	64.9
80°	56.8	55.2	53.7	52.8	52.4	52.1	51.7	51.4
82.5°	42.4	41.7	41.0	40.6	40.4	40.2	40.0	39.8
85°	24.2	24.0	23.8	23.7	23.5	23.3	23.2	23.0
87.5°	11.3	11.4	11.6	11.6	11.5	11.5	11.4	11.3
90°	10.5	11.1	11.8	12.3	12.7	13.0	13.4	13.8
92.5°	23.8	24.6	25.5	26.1	26.4	26.7	26.9	27.2
95°	46.2	47.1	48.0	48.5	48.8	49.1	49.3	49.6
97.5°	72.3	73.2	74.0	74.5	74.6	74.8	74.9	75.1
100°	90.5	91.6	92.7	93.4	93.7	94.0	94.2	94.5
102.5°	109.1	110.4	111.6	112.4	112.8	113.1	113.5	113.8
105°	139.3	140.0	140.8	141.4	141.7	142.1	142.5	142.9
107.5°	171.8	172.2	172.5	172.7	172.7	172.7	172.6	172.6
110°	194.3	194.7	195.1	195.2	195.1	195.0	194.8	194.7



TEST NUMBER: P333530-840

CATALOG NUMBER: S125RDIP-S610D590U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	217.0	217.1	217.3	217.3	217.1	216.8	216.6	216.4
115°	251.5	251.4	251.3	251.2	251.0	250.9	250.7	250.6
117.5°	286.1	286.2	286.3	286.1	285.6	285.1	284.6	284.0
120°	309.3	309.3	309.3	309.1	308.6	308.1	307.6	307.1
122.5°	332.2	332.1	332.0	331.7	331.3	330.9	330.5	330.1
125°	365.9	365.7	365.4	365.2	365.1	365.0	364.8	364.7
127.5°	399.3	399.2	399.1	398.9	398.6	398.4	398.1	397.9
130°	421.4	421.3	421.2	421.0	420.7	420.5	420.2	420.0
132.5°	442.6	442.5	442.4	442.1	441.8	441.4	441.1	440.7
135°	475.2	475.2	475.2	475.0	474.5	474.0	473.5	473.0
137.5°	507.1	507.2	507.4	507.2	506.4	505.8	505.2	504.5
140°	527.0	527.4	527.6	527.4	526.7	526.1	525.4	524.8
142.5°	546.6	546.8	546.9	546.7	546.1	545.4	544.8	544.2
145°	574.9	574.9	574.9	574.7	574.4	574.0	573.6	573.2
147.5°	601.2	601.5	601.8	601.5	600.6	599.8	598.8	598.0
150°	617.5	617.5	617.5	617.4	617.2	616.9	616.7	616.4
152.5°	633.0	633.3	633.6	633.5	633.0	632.6	632.1	631.7
155°	654.9	655.4	655.9	655.9	655.2	654.6	653.9	653.3
157.5°	673.9	674.4	674.9	674.8	673.9	673.1	672.3	671.4
160°	685.4	685.9	686.4	686.4	685.8	685.1	684.5	683.9
162.5°	696.2	696.8	697.5	697.4	696.7	695.9	695.2	694.4
165°	710.7	711.2	711.9	711.7	710.9	710.1	709.3	708.6
167.5°	721.5	722.4	723.1	723.1	722.3	721.4	720.6	719.9
170°	728.0	728.7	729.5	729.4	728.6	727.7	726.8	725.9
172.5°	732.7	733.4	734.2	734.2	733.4	732.6	731.7	730.9
175°	737.8	738.5	739.3	739.2	738.4	737.5	736.6	735.7
177.5°	740.1	740.7	741.3	741.3	740.6	739.9	739.1	738.4
180°	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3

(END OF REPORT)