

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331741-830

Luminaire Tested: **SA2XXRDIP-C1005D530U830-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331741-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 530 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5586.3 lumens
Efficiency: N/A
Efficacy: 101.4 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331741-830
CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331741-830
 CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	64				
1	102	98	94	91	96	92	89	86	82	79	77	72	70	69	63	62	60	56				
2	94	87	81	76	88	82	77	73	73	69	66	64	61	59	57	54	53	49				
3	86	77	70	65	81	73	67	62	65	60	56	58	54	51	51	48	46	43				
4	80	69	62	56	75	66	59	54	59	53	49	52	48	45	46	43	41	38				
5	74	62	55	49	69	59	52	47	53	48	43	48	43	40	43	39	36	33				
6	68	57	49	43	64	54	47	42	49	43	39	44	39	36	39	35	33	30				
7	64	52	44	39	60	49	42	37	45	39	35	40	36	32	36	32	30	27				
8	59	47	40	35	56	45	38	34	41	35	31	37	32	29	33	30	27	25				
9	56	44	36	31	52	42	35	30	38	32	28	34	30	27	31	27	25	23				
10	52	40	33	29	49	39	32	28	35	30	26	32	28	24	29	25	23	21				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	33562	33562	33562	33562
5°	37483	33773	29945	33773
10°	41589	33536	25956	33536
15°	43632	33045	20451	33045
20°	37826	32316	17698	32316
25°	24807	31319	15800	31319
30°	16697	30109	14300	30109
35°	13525	28586	12899	28586
40°	12026	26930	11936	26930
45°	10885	24987	10654	24987
50°	9907	23059	9869	23059
55°	9312	20921	9191	20921
60°	7789	18962	7698	18962
65°	6567	17219	7450	17219
70°	6071	15375	7024	15375
75°	5677	13381	6488	13381
80°	5244	11018	5774	11018
85°	4817	8688	5076	8688



TEST NUMBER: P331741-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	197.1	3.5
10°-20°	549.1	9.8
20°-30°	707.5	12.7
30°-40°	672.4	12.0
40°-50°	576.0	10.3
50°-60°	438.6	7.9
60°-70°	277.3	5.0
70°-80°	138.5	2.5
80°-90°	37.7	0.7
90°-100°	22.7	0.4
100°-110°	83.2	1.5
110°-120°	222.3	4.0
120°-130°	366.9	6.6
130°-140°	390.2	7.0
140°-150°	362.7	6.5
150°-160°	291.6	5.2
160°-170°	187.9	3.4
170°-180°	64.7	1.2
0°-30°	1453.7	26.0
0°-40°	2126.0	38.1
0°-60°	3140.7	56.2
0°-90°	3594.2	64.3
90°-120°	328.1	5.9
90°-150°	1447.9	25.9
90°-180°	1992.0	35.7
0°-180°	5586.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2079	2079	2079	2079	2079	
5°	2313	2084	1848	2084	2313	228
15°	2610	1977	1224	1977	2610	704
25°	1392	1758	887	1758	1392	661
35°	686	1450	654	1450	686	439
45°	477	1094	467	1094	477	369
55°	331	743	326	743	331	290
65°	172	451	195	451	172	175
75°	91	214	104	214	91	97
85°	26	47	27	47	26	28
90°	13	0	13	0	13	7
95°	21	32	21	32	21	20
105°	37	150	37	150	37	39
115°	40	283	40	283	40	101
125°	421	400	421	400	421	364
135°	511	495	511	495	511	394
145°	583	574	583	574	583	365
155°	632	632	632	632	632	292
165°	664	666	664	666	664	188
175°	677	681	677	681	677	65
180°	680	680	680	680	680	



TEST NUMBER: P331741-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2163.0	2164.8	2166.5	2162.5	2162.5	2159.0	2151.5	2145.7	2129.6	2127.2	2127.2
5°	2312.7	2311.3	2314.1	2304.8	2291.8	2288.9	2275.2	2257.1	2238.4	2217.4	2213.1
7.5°	2461.5	2459.4	2453.5	2452.0	2442.0	2420.2	2398.1	2374.5	2343.3	2312.9	2297.5
10°	2536.7	2560.5	2546.0	2520.7	2525.8	2491.9	2473.8	2442.8	2416.8	2371.2	2361.2
12.5°	2610.6	2620.0	2615.4	2601.0	2594.5	2571.0	2546.6	2519.6	2471.6	2430.7	2395.2
15°	2610.3	2624.0	2627.6	2623.3	2627.0	2625.5	2612.4	2590.1	2548.2	2503.4	2464.4
17.5°	2417.6	2427.1	2450.8	2466.8	2487.1	2529.9	2550.9	2559.2	2553.0	2527.4	2499.9
20°	2201.5	2185.6	2252.0	2286.0	2314.9	2387.1	2449.2	2473.0	2511.3	2510.7	2503.4
22.5°	1895.3	1899.0	1962.0	2002.3	2086.7	2158.9	2229.7	2319.4	2393.5	2442.4	2471.1
25°	1392.5	1420.0	1482.8	1537.8	1631.6	1765.9	1888.0	2029.6	2163.2	2268.7	2369.1
27.5°	1045.8	1047.9	1097.7	1148.4	1204.2	1314.3	1467.9	1637.0	1827.5	1984.7	2165.5
30°	895.6	891.3	912.2	943.3	991.0	1076.2	1191.8	1357.9	1547.8	1784.7	1995.6
32.5°	789.3	789.6	805.3	828.3	867.9	925.4	1004.6	1139.4	1319.0	1551.9	1799.2
35°	686.2	685.4	697.0	713.6	730.2	767.0	821.2	892.0	1015.5	1232.9	1485.7
37.5°	612.2	615.4	621.0	631.4	649.8	670.2	702.8	750.3	838.3	966.9	1179.3
40°	570.6	572.0	579.9	588.6	599.5	615.4	642.1	680.4	744.7	847.3	1002.5
42.5°	532.4	534.0	539.5	547.6	556.2	572.0	594.2	627.3	679.4	759.4	887.5
45°	476.7	476.7	481.7	485.4	494.7	509.2	527.3	554.7	590.8	650.1	735.3
47.5°	424.4	424.5	427.9	434.1	440.0	451.3	469.0	491.4	517.7	563.5	636.3
50°	394.4	395.1	397.3	402.3	406.0	416.0	429.8	449.2	476.7	512.1	572.8
52.5°	370.1	369.7	372.4	374.6	377.0	384.3	394.5	411.7	436.2	467.0	517.3
55°	330.8	327.9	332.2	335.8	338.0	340.9	346.7	357.5	378.4	404.4	442.1
57.5°	281.7	280.5	283.6	286.9	293.7	301.5	306.4	313.3	324.1	342.8	380.0
60°	241.2	241.2	247.7	249.9	257.9	268.0	278.1	283.9	294.7	307.0	334.4
62.5°	205.4	206.0	209.1	211.2	215.7	228.1	242.2	255.0	265.2	276.9	295.1
65°	171.9	173.3	173.3	174.7	177.7	180.6	186.3	196.4	214.5	231.1	244.9
67.5°	145.9	146.4	146.8	148.2	148.9	152.1	154.4	158.9	163.1	178.8	195.9
70°	128.6	130.7	130.0	131.5	132.1	133.7	136.5	138.6	145.2	148.8	158.9
72.5°	112.4	114.0	113.9	114.7	116.6	116.9	119.1	121.3	125.5	128.6	134.0
75°	91.0	90.3	91.0	92.5	93.2	93.9	93.9	96.8	99.0	101.8	105.5
77.5°	70.2	71.0	70.8	71.0	71.1	72.4	72.2	73.5	75.7	77.1	78.9
80°	56.4	57.0	56.4	57.0	57.8	58.5	57.8	58.5	60.7	62.1	62.1
82.5°	43.6	43.7	44.2	44.4	44.5	44.7	45.6	45.8	47.4	47.1	47.7
85°	26.0	25.3	25.3	25.3	26.0	26.8	26.0	26.0	26.8	26.8	26.8
87.5°	11.9	12.4	12.3	12.3	12.3	12.3	12.2	12.6	11.9	12.3	11.6
90°	13.3	13.1	12.8	12.6	12.4	12.1	11.5	10.9	10.4	9.8	9.0
92.5°	13.3	13.2	13.0	12.9	12.7	12.5	12.3	12.0	11.7	11.4	10.9
95°	21.1	21.3	21.4	21.5	21.6	21.4	20.8	20.3	19.7	19.2	18.4
97.5°	28.3	28.1	28.0	27.8	27.7	27.4	27.0	26.6	26.1	25.6	23.9
100°	33.0	32.7	32.5	32.3	32.0	31.6	30.6	29.8	28.9	28.0	26.2
102.5°	35.3	35.0	34.7	34.4	34.1	33.4	32.2	31.1	30.0	28.8	44.4
105°	37.4	36.9	36.5	36.1	35.6	34.8	33.6	32.4	31.2	30.0	59.9
107.5°	38.5	38.0	37.6	37.1	36.8	37.1	38.4	39.6	40.8	42.0	77.8
110°	38.8	38.5	38.0	37.5	37.1	42.3	53.3	64.2	75.1	86.1	117.6



TEST NUMBER: P331741-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	39.2	38.9	38.5	38.2	37.9	57.6	97.5	137.3	177.2	217.2	224.9
115°	40.3	48.2	56.1	63.9	71.8	101.0	151.7	202.3	252.9	303.5	300.8
117.5°	164.7	190.6	216.4	242.2	268.2	287.2	299.4	311.7	324.0	336.1	334.3
120°	300.0	314.8	329.6	344.3	359.1	365.8	364.5	363.2	361.8	360.5	358.5
122.5°	374.4	377.3	380.1	383.0	385.9	386.9	386.2	385.3	384.6	383.8	381.6
125°	420.6	420.3	419.9	419.6	419.2	418.7	417.9	417.2	416.4	415.7	413.6
127.5°	449.7	449.6	449.6	449.5	449.4	448.8	447.7	446.6	445.4	444.4	442.8
130°	467.8	467.9	468.0	468.1	468.3	467.7	466.5	465.2	464.1	462.9	461.7
132.5°	485.5	485.6	485.7	485.8	485.9	485.5	484.5	483.4	482.4	481.4	480.1
135°	511.0	511.3	511.5	511.7	512.0	511.5	510.4	509.3	508.2	507.1	506.1
137.5°	534.4	534.8	535.1	535.5	535.8	535.6	534.4	533.4	532.3	531.2	530.1
140°	548.9	549.5	550.1	550.5	551.1	550.9	549.9	548.9	548.0	547.0	545.7
142.5°	563.1	563.6	564.2	564.8	565.3	565.1	564.2	563.4	562.4	561.6	560.2
145°	582.9	583.4	584.0	584.6	585.0	584.9	584.2	583.4	582.7	581.9	580.0
147.5°	600.3	600.8	601.2	601.7	602.1	602.1	601.5	601.0	600.4	599.8	597.9
150°	611.0	611.4	612.0	612.6	613.1	613.0	612.4	611.7	611.1	610.4	608.7
152.5°	620.0	620.7	621.4	622.2	622.8	622.9	622.3	621.6	620.9	620.3	618.6
155°	632.5	633.5	634.3	635.2	636.0	636.2	635.6	634.9	634.2	633.6	632.3
157.5°	644.0	644.9	645.7	646.6	647.5	647.5	646.8	646.0	645.3	644.6	643.7
160°	650.7	651.5	652.3	653.1	653.8	653.8	653.2	652.5	652.0	651.3	650.6
162.5°	656.3	657.2	658.2	659.1	660.1	660.2	659.4	658.6	657.9	657.1	656.6
165°	664.5	665.3	666.1	666.8	667.6	667.6	666.8	666.1	665.3	664.5	664.2
167.5°	669.8	670.7	671.8	672.7	673.7	673.8	673.1	672.2	671.5	670.7	670.4
170°	672.9	673.9	674.9	675.8	676.8	676.9	676.2	675.4	674.7	673.9	673.6
172.5°	675.2	676.3	677.2	678.3	679.2	679.3	678.5	677.8	677.0	676.3	676.0
175°	677.3	678.4	679.5	680.6	681.7	681.8	681.1	680.3	679.6	678.8	678.5
177.5°	678.6	679.4	680.1	681.0	681.7	681.8	681.3	680.6	680.0	679.4	679.3
180°	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8



TEST NUMBER: P331741-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2128.4	2123.7	2119.8	2109.3	2104.1	2092.5	2090.8	2090.3	2075.3	2060.8	2056.7
5°	2201.5	2189.9	2172.7	2152.4	2131.5	2109.8	2095.4	2083.8	2054.8	2027.4	2011.6
7.5°	2275.2	2250.3	2220.4	2182.2	2150.2	2114.4	2087.8	2064.0	2023.0	1983.7	1957.2
10°	2330.1	2289.6	2249.8	2197.2	2156.0	2115.5	2078.0	2045.5	1999.2	1947.3	1910.4
12.5°	2364.2	2319.7	2264.9	2213.4	2160.0	2108.7	2058.3	2016.6	1962.3	1908.6	1864.8
15°	2410.3	2362.6	2296.1	2222.4	2153.8	2086.7	2028.9	1976.9	1906.1	1841.8	1788.4
17.5°	2448.0	2382.4	2311.0	2225.8	2146.4	2061.0	1986.6	1920.1	1841.4	1763.8	1700.8
20°	2460.0	2395.1	2312.7	2227.5	2133.6	2033.3	1953.0	1880.8	1796.3	1711.8	1639.6
22.5°	2452.6	2402.0	2310.5	2208.5	2112.2	2007.2	1916.7	1832.9	1739.1	1652.8	1569.1
25°	2401.6	2384.3	2297.5	2186.3	2076.5	1954.5	1849.7	1758.0	1651.1	1558.7	1467.6
27.5°	2282.6	2320.1	2266.3	2147.9	2025.8	1895.0	1777.3	1672.8	1561.9	1457.8	1367.2
30°	2168.3	2254.2	2231.1	2121.3	1984.8	1856.2	1724.1	1615.0	1496.6	1389.7	1300.1
32.5°	2011.7	2153.7	2176.2	2084.3	1943.2	1802.0	1663.4	1554.9	1431.3	1318.6	1231.3
35°	1762.4	1974.7	2072.2	2013.7	1872.2	1719.8	1576.7	1450.3	1326.1	1214.8	1128.2
37.5°	1464.9	1754.2	1916.7	1920.8	1790.8	1632.4	1476.6	1351.1	1224.0	1114.7	1021.1
40°	1272.0	1585.4	1797.1	1844.0	1734.2	1563.0	1405.5	1277.7	1153.5	1046.6	939.0
42.5°	1098.6	1410.9	1671.0	1752.7	1665.5	1495.4	1337.4	1203.7	1083.0	981.8	871.9
45°	888.4	1161.4	1448.1	1594.0	1545.7	1388.2	1221.3	1094.3	980.8	893.4	788.0
47.5°	749.4	941.9	1219.4	1416.6	1415.8	1272.1	1108.0	986.2	881.0	799.1	713.8
50°	670.2	837.8	1072.6	1296.5	1315.2	1194.7	1038.6	918.0	819.8	733.9	665.2
52.5°	599.2	737.3	948.4	1163.0	1216.4	1112.0	960.6	849.2	753.9	674.9	616.1
55°	506.3	613.2	773.5	974.3	1055.3	981.6	847.3	743.2	665.9	599.5	548.9
57.5°	428.3	508.5	637.2	798.8	893.1	846.7	735.8	651.4	585.2	525.1	485.2
60°	379.2	444.9	554.0	689.1	793.1	760.5	665.9	587.2	530.8	478.9	441.3
62.5°	333.0	389.5	483.0	592.6	687.9	674.5	597.2	531.1	481.7	434.4	402.6
65°	268.0	309.2	382.1	468.1	544.6	551.1	495.5	450.7	406.6	369.1	340.9
67.5°	213.4	240.3	291.6	364.0	421.4	441.9	407.9	373.7	338.7	309.7	285.3
70°	179.8	201.5	239.0	297.6	350.3	371.9	352.5	325.7	295.4	271.5	250.6
72.5°	145.7	166.8	194.5	237.5	282.7	306.1	299.4	280.1	255.5	235.7	215.9
75°	109.8	116.3	135.1	164.0	199.3	219.6	224.6	214.5	195.0	179.8	168.2
77.5°	81.2	85.1	94.1	109.2	132.3	150.3	157.8	156.6	143.2	134.3	123.5
80°	65.0	67.2	71.5	78.0	95.4	113.4	118.5	118.5	109.1	105.5	94.6
82.5°	49.4	51.0	53.6	57.2	65.3	81.1	86.7	87.8	81.9	77.1	68.6
85°	28.2	27.4	28.9	31.1	32.5	36.9	45.5	46.9	45.5	39.7	37.5
87.5°	11.4	11.9	11.7	10.8	11.2	11.6	14.2	16.9	14.8	13.3	12.3
90°	8.1	7.3	6.3	5.3	4.1	2.9	1.7	0.5	1.7	2.9	4.1
92.5°	10.6	10.1	9.7	9.5	9.6	9.7	9.8	9.9	9.8	9.7	9.6
95°	17.6	16.9	16.1	17.5	21.1	24.8	28.4	32.0	28.4	24.8	21.1
97.5°	22.1	20.4	18.6	22.8	33.0	43.2	53.3	63.4	53.3	43.2	33.0
100°	24.3	22.4	20.6	27.1	42.1	57.1	72.1	87.1	72.1	57.1	42.1
102.5°	59.9	75.5	91.0	100.4	103.5	106.7	109.9	113.0	109.9	106.7	103.5
105°	89.7	119.5	149.4	162.7	159.4	156.1	152.8	149.5	152.8	156.1	159.4
107.5°	113.6	149.4	185.1	201.7	199.1	196.4	193.8	191.1	193.8	196.4	199.1
110°	149.3	180.9	212.4	227.1	224.8	222.5	220.2	217.9	220.2	222.5	224.8



TEST NUMBER: P331741-830
 CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	232.7	240.5	248.4	251.2	249.2	247.1	245.2	243.1	245.2	247.1	249.2
115°	298.0	295.3	292.6	290.3	288.4	286.5	284.6	282.9	284.6	286.5	288.4
117.5°	332.4	330.5	328.7	326.7	324.6	322.5	320.5	318.4	320.5	322.5	324.6
120°	356.7	354.7	352.7	350.9	349.2	347.6	345.9	344.3	345.9	347.6	349.2
122.5°	379.5	377.3	375.2	373.2	371.6	369.9	368.1	366.4	368.1	369.9	371.6
125°	411.5	409.4	407.4	405.6	404.2	402.7	401.3	399.9	401.3	402.7	404.2
127.5°	441.3	439.7	438.2	436.6	435.0	433.5	431.9	430.3	431.9	433.5	435.0
130°	460.4	459.3	458.1	456.6	454.9	453.1	451.3	449.6	451.3	453.1	454.9
132.5°	479.0	477.8	476.5	475.2	473.7	472.2	470.7	469.3	470.7	472.2	473.7
135°	505.2	504.2	503.2	501.8	500.1	498.3	496.6	494.8	496.6	498.3	500.1
137.5°	529.0	527.9	526.8	525.6	524.3	523.1	521.9	520.8	521.9	523.1	524.3
140°	544.6	543.4	542.2	541.1	540.3	539.4	538.5	537.6	538.5	539.4	540.3
142.5°	558.7	557.4	556.0	555.0	554.1	553.4	552.6	551.8	552.6	553.4	554.1
145°	578.2	576.4	574.5	573.6	573.7	573.8	573.9	574.0	573.9	573.8	573.7
147.5°	596.2	594.3	592.5	591.7	592.2	592.6	593.0	593.4	593.0	592.6	592.2
150°	606.9	605.2	603.4	602.9	603.7	604.5	605.2	606.0	605.2	604.5	603.7
152.5°	617.0	615.3	613.6	613.2	614.1	614.9	615.8	616.6	615.8	614.9	614.1
155°	630.9	629.6	628.3	628.1	629.1	630.1	631.1	632.1	631.1	630.1	629.1
157.5°	642.7	641.8	640.9	640.8	641.7	642.5	643.4	644.1	643.4	642.5	641.7
160°	650.0	649.3	648.7	648.7	649.3	650.0	650.6	651.3	650.6	650.0	649.3
162.5°	656.0	655.4	654.9	655.0	655.5	656.2	656.9	657.5	656.9	656.2	655.5
165°	663.8	663.5	663.3	663.4	664.0	664.7	665.3	666.0	665.3	664.7	664.0
167.5°	670.1	669.8	669.5	669.7	670.3	671.0	671.7	672.3	671.7	671.0	670.3
170°	673.4	673.3	673.0	673.3	673.9	674.6	675.2	675.8	675.2	674.6	673.9
172.5°	675.8	675.6	675.3	675.6	676.3	676.9	677.6	678.3	677.6	676.9	676.3
175°	678.3	678.2	678.0	678.2	679.0	679.8	680.5	681.3	680.5	679.8	679.0
177.5°	679.2	679.1	679.0	679.3	680.0	680.5	681.2	681.7	681.2	680.5	680.0
180°	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8



TEST NUMBER: P331741-830
 CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2049.3	2045.2	2037.7	2026.1	2019.2	2007.1	1998.9	2003.6	2004.8	2003.6	2002.4
5°	1994.2	1979.1	1958.1	1937.9	1919.1	1898.8	1887.3	1882.3	1872.2	1866.3	1863.5
7.5°	1927.6	1901.5	1871.9	1836.6	1806.7	1775.4	1759.3	1751.3	1730.7	1719.5	1709.6
10°	1877.9	1836.7	1807.1	1761.0	1732.8	1691.6	1663.4	1664.2	1636.0	1620.0	1608.5
12.5°	1823.1	1777.8	1728.5	1687.0	1647.8	1614.8	1580.7	1567.1	1537.2	1521.8	1490.6
15°	1732.0	1679.3	1627.3	1570.9	1531.3	1480.0	1430.9	1370.9	1322.5	1280.6	1269.0
17.5°	1632.7	1567.4	1515.2	1449.1	1381.0	1294.8	1237.8	1203.1	1173.8	1151.8	1135.3
20°	1564.4	1498.0	1442.4	1342.7	1250.9	1192.5	1150.6	1123.9	1093.5	1069.7	1056.7
22.5°	1492.8	1423.4	1347.6	1236.4	1164.9	1117.9	1080.6	1049.9	1029.4	1010.8	998.9
25°	1391.1	1315.2	1190.3	1113.7	1055.9	1006.8	980.8	962.1	940.4	915.1	903.6
27.5°	1283.6	1163.0	1073.3	1016.3	961.2	929.3	905.9	877.9	858.5	847.1	835.1
30°	1203.3	1082.7	1012.7	950.6	911.5	876.1	848.7	832.8	814.0	794.5	786.6
32.5°	1113.7	1017.4	950.3	898.5	858.9	828.8	807.1	781.4	767.8	755.8	739.1
35°	1002.5	929.5	868.2	826.3	788.7	764.2	738.9	723.7	699.2	689.1	682.6
37.5°	908.3	845.1	799.3	755.1	725.3	698.1	682.7	658.6	647.9	633.9	620.2
40°	855.2	793.1	749.0	712.8	679.7	659.4	639.9	620.5	604.5	598.0	581.5
42.5°	800.9	750.3	706.2	666.7	644.4	623.0	598.3	584.0	567.6	557.0	546.8
45°	725.9	681.1	643.6	611.1	586.4	564.1	548.2	524.3	515.0	494.1	485.4
47.5°	660.1	618.4	582.6	551.7	527.7	513.1	489.8	471.2	456.2	443.4	432.3
50°	613.2	578.5	543.8	516.4	494.7	473.8	450.0	440.5	417.5	410.9	404.4
52.5°	570.4	537.5	505.8	478.9	457.2	436.9	415.8	403.6	388.0	381.5	376.7
55°	510.7	478.9	448.6	424.7	403.0	382.1	369.1	353.9	346.7	341.7	335.8
57.5°	450.5	422.0	398.7	374.6	352.8	336.1	321.1	312.0	304.5	297.8	291.0
60°	412.5	384.9	364.0	341.7	319.2	305.5	294.0	283.1	274.5	264.4	261.5
62.5°	371.9	348.0	328.8	307.0	287.5	274.9	263.9	253.6	243.3	228.6	224.5
65°	316.3	297.6	277.4	259.3	242.0	229.7	213.8	202.3	197.9	196.4	195.8
67.5°	266.1	248.4	231.0	212.4	196.7	185.3	177.3	175.5	172.5	171.6	169.6
70°	232.6	215.9	198.6	181.3	166.2	164.0	161.1	158.2	154.6	153.2	151.7
72.5°	202.6	185.3	168.0	154.1	147.6	144.9	142.0	139.1	136.7	135.3	134.3
75°	155.3	139.4	127.8	122.8	119.1	117.0	112.6	110.5	109.1	106.9	106.1
77.5°	111.8	102.8	97.6	94.3	90.6	88.2	85.8	83.6	82.1	81.6	80.5
80°	85.2	80.9	77.3	73.0	71.5	68.6	67.9	65.7	66.4	64.3	64.3
82.5°	66.2	60.7	57.7	55.6	54.2	51.8	51.2	50.1	50.2	48.6	48.6
85°	33.9	32.5	31.1	29.6	29.6	27.4	28.2	27.4	27.4	26.0	25.3
87.5°	12.1	11.7	10.7	10.8	11.0	10.7	10.7	10.3	10.4	10.5	10.0
90°	5.3	6.3	7.3	8.1	9.0	9.8	10.4	10.9	11.5	12.1	12.4
92.5°	9.5	9.7	10.1	10.6	10.9	11.4	11.7	12.0	12.3	12.5	12.7
95°	17.5	16.1	16.9	17.6	18.4	19.2	19.7	20.3	20.8	21.4	21.6
97.5°	22.8	18.6	20.4	22.1	23.9	25.6	26.1	26.6	27.0	27.4	27.7
100°	27.1	20.6	22.4	24.3	26.2	28.0	28.9	29.8	30.6	31.6	32.0
102.5°	100.4	91.0	75.5	59.9	44.4	28.8	30.0	31.1	32.2	33.4	34.1
105°	162.7	149.4	119.5	89.7	59.9	30.0	31.2	32.4	33.6	34.8	35.6
107.5°	201.7	185.1	149.4	113.6	77.8	42.0	40.8	39.6	38.4	37.1	36.8
110°	227.1	212.4	180.9	149.3	117.6	86.1	75.1	64.2	53.3	42.3	37.1



TEST NUMBER: P331741-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	251.2	248.4	240.5	232.7	224.9	217.2	177.2	137.3	97.5	57.6	37.9
115°	290.3	292.6	295.3	298.0	300.8	303.5	252.9	202.3	151.7	101.0	71.8
117.5°	326.7	328.7	330.5	332.4	334.3	336.1	324.0	311.7	299.4	287.2	268.2
120°	350.9	352.7	354.7	356.7	358.5	360.5	361.8	363.2	364.5	365.8	359.1
122.5°	373.2	375.2	377.3	379.5	381.6	383.8	384.6	385.3	386.2	386.9	385.9
125°	405.6	407.4	409.4	411.5	413.6	415.7	416.4	417.2	417.9	418.7	419.2
127.5°	436.6	438.2	439.7	441.3	442.8	444.4	445.4	446.6	447.7	448.8	449.4
130°	456.6	458.1	459.3	460.4	461.7	462.9	464.1	465.2	466.5	467.7	468.3
132.5°	475.2	476.5	477.8	479.0	480.1	481.4	482.4	483.4	484.5	485.5	485.9
135°	501.8	503.2	504.2	505.2	506.1	507.1	508.2	509.3	510.4	511.5	512.0
137.5°	525.6	526.8	527.9	529.0	530.1	531.2	532.3	533.4	534.4	535.6	535.8
140°	541.1	542.2	543.4	544.6	545.7	547.0	548.0	548.9	549.9	550.9	551.1
142.5°	555.0	556.0	557.4	558.7	560.2	561.6	562.4	563.4	564.2	565.1	565.3
145°	573.6	574.5	576.4	578.2	580.0	581.9	582.7	583.4	584.2	584.9	585.0
147.5°	591.7	592.5	594.3	596.2	597.9	599.8	600.4	601.0	601.5	602.1	602.1
150°	602.9	603.4	605.2	606.9	608.7	610.4	611.1	611.7	612.4	613.0	613.1
152.5°	613.2	613.6	615.3	617.0	618.6	620.3	620.9	621.6	622.3	622.9	622.8
155°	628.1	628.3	629.6	630.9	632.3	633.6	634.2	634.9	635.6	636.2	636.0
157.5°	640.8	640.9	641.8	642.7	643.7	644.6	645.3	646.0	646.8	647.5	647.5
160°	648.7	648.7	649.3	650.0	650.6	651.3	652.0	652.5	653.2	653.8	653.8
162.5°	655.0	654.9	655.4	656.0	656.6	657.1	657.9	658.6	659.4	660.2	660.1
165°	663.4	663.3	663.5	663.8	664.2	664.5	665.3	666.1	666.8	667.6	667.6
167.5°	669.7	669.5	669.8	670.1	670.4	670.7	671.5	672.2	673.1	673.8	673.7
170°	673.3	673.0	673.3	673.4	673.6	673.9	674.7	675.4	676.2	676.9	676.8
172.5°	675.6	675.3	675.6	675.8	676.0	676.3	677.0	677.8	678.5	679.3	679.2
175°	678.2	678.0	678.2	678.3	678.5	678.8	679.6	680.3	681.1	681.8	681.7
177.5°	679.3	679.0	679.1	679.2	679.3	679.4	680.0	680.6	681.3	681.8	681.7
180°	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8



TEST NUMBER: P331741-830
 CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	1996.1	1997.2	1995.6	1996.7	1995.6	1997.2	1996.1	2002.4	2003.6	2004.8	2003.6
5°	1859.8	1851.2	1849.7	1847.6	1849.7	1851.2	1859.8	1863.5	1866.3	1872.2	1882.3
7.5°	1697.2	1695.9	1692.3	1687.2	1692.3	1695.9	1697.2	1709.6	1719.5	1730.7	1751.3
10°	1592.6	1589.0	1588.3	1583.2	1588.3	1589.0	1592.6	1608.5	1620.0	1636.0	1664.2
12.5°	1470.1	1446.9	1444.4	1431.8	1444.4	1446.9	1470.1	1490.6	1521.8	1537.2	1567.1
15°	1251.7	1247.4	1232.9	1223.5	1232.9	1247.4	1251.7	1269.0	1280.6	1322.5	1370.9
17.5°	1126.9	1112.8	1108.2	1106.3	1108.2	1112.8	1126.9	1135.3	1151.8	1173.8	1203.1
20°	1046.6	1033.6	1031.4	1030.0	1031.4	1033.6	1046.6	1056.7	1069.7	1093.5	1123.9
22.5°	991.1	977.5	971.9	967.5	971.9	977.5	991.1	998.9	1010.8	1029.4	1049.9
25°	896.4	891.3	888.4	886.9	888.4	891.3	896.4	903.6	915.1	940.4	962.1
27.5°	822.3	811.2	809.0	805.2	809.0	811.2	822.3	835.1	847.1	858.5	877.9
30°	780.0	776.5	771.4	767.0	771.4	776.5	780.0	786.6	794.5	814.0	832.8
32.5°	730.4	727.4	722.8	720.9	722.8	727.4	730.4	739.1	755.8	767.8	781.4
35°	675.3	665.2	660.9	654.4	660.9	665.2	675.3	682.6	689.1	699.2	723.7
37.5°	617.1	611.8	605.7	607.8	605.7	611.8	617.1	620.2	633.9	647.9	658.6
40°	572.0	568.4	567.0	566.3	567.0	568.4	572.0	581.5	598.0	604.5	620.5
42.5°	536.2	526.2	522.5	522.4	522.5	526.2	536.2	546.8	557.0	567.6	584.0
45°	481.7	472.4	465.9	466.6	465.9	472.4	481.7	485.4	494.1	515.0	524.3
47.5°	426.0	425.7	421.7	422.9	421.7	425.7	426.0	432.3	443.4	456.2	471.2
50°	399.4	395.1	392.2	392.9	392.2	395.1	399.4	404.4	410.9	417.5	440.5
52.5°	374.0	370.2	368.0	371.0	368.0	370.2	374.0	376.7	381.5	388.0	403.6
55°	332.2	327.9	327.2	326.5	327.2	327.9	332.2	335.8	341.7	346.7	353.9
57.5°	285.6	282.7	278.3	276.4	278.3	282.7	285.6	291.0	297.8	304.5	312.0
60°	252.0	246.3	239.0	238.4	239.0	246.3	252.0	261.5	264.4	274.5	283.1
62.5°	221.4	220.3	218.9	218.7	218.9	220.3	221.4	224.5	228.6	243.3	253.6
65°	194.3	193.6	194.3	195.0	194.3	193.6	194.3	195.8	196.4	197.9	202.3
67.5°	169.3	168.0	166.7	167.3	166.7	168.0	169.3	169.6	171.6	172.5	175.5
70°	150.2	149.5	148.8	148.8	148.8	149.5	150.2	151.7	153.2	154.6	158.2
72.5°	131.8	131.6	130.9	130.3	130.9	131.6	131.8	134.3	135.3	136.7	139.1
75°	105.5	104.0	104.0	104.0	104.0	104.0	105.5	106.1	106.9	109.1	110.5
77.5°	80.3	79.6	78.9	78.3	78.9	79.6	80.3	80.5	81.6	82.1	83.6
80°	63.5	62.9	62.1	62.1	62.1	62.9	63.5	64.3	64.3	66.4	65.7
82.5°	48.5	47.8	47.7	47.1	47.7	47.8	48.5	48.6	48.6	50.2	50.1
85°	26.0	26.8	26.0	27.4	26.0	26.8	26.0	25.3	26.0	27.4	27.4
87.5°	10.0	9.5	10.1	9.6	10.1	9.5	10.0	10.0	10.5	10.4	10.3
90°	12.6	12.8	13.1	13.3	13.1	12.8	12.6	12.4	12.1	11.5	10.9
92.5°	12.9	13.0	13.2	13.3	13.2	13.0	12.9	12.7	12.5	12.3	12.0
95°	21.5	21.4	21.3	21.1	21.3	21.4	21.5	21.6	21.4	20.8	20.3
97.5°	27.8	28.0	28.1	28.3	28.1	28.0	27.8	27.7	27.4	27.0	26.6
100°	32.3	32.5	32.7	33.0	32.7	32.5	32.3	32.0	31.6	30.6	29.8
102.5°	34.4	34.7	35.0	35.3	35.0	34.7	34.4	34.1	33.4	32.2	31.1
105°	36.1	36.5	36.9	37.4	36.9	36.5	36.1	35.6	34.8	33.6	32.4
107.5°	37.1	37.6	38.0	38.5	38.0	37.6	37.1	36.8	37.1	38.4	39.6
110°	37.5	38.0	38.5	38.8	38.5	38.0	37.5	37.1	42.3	53.3	64.2



TEST NUMBER: P331741-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	38.2	38.5	38.9	39.2	38.9	38.5	38.2	37.9	57.6	97.5	137.3
115°	63.9	56.1	48.2	40.3	48.2	56.1	63.9	71.8	101.0	151.7	202.3
117.5°	242.2	216.4	190.6	164.7	190.6	216.4	242.2	268.2	287.2	299.4	311.7
120°	344.3	329.6	314.8	300.0	314.8	329.6	344.3	359.1	365.8	364.5	363.2
122.5°	383.0	380.1	377.3	374.4	377.3	380.1	383.0	385.9	386.9	386.2	385.3
125°	419.6	419.9	420.3	420.6	420.3	419.9	419.6	419.2	418.7	417.9	417.2
127.5°	449.5	449.6	449.6	449.7	449.6	449.6	449.5	449.4	448.8	447.7	446.6
130°	468.1	468.0	467.9	467.8	467.9	468.0	468.1	468.3	467.7	466.5	465.2
132.5°	485.8	485.7	485.6	485.5	485.6	485.7	485.8	485.9	485.5	484.5	483.4
135°	511.7	511.5	511.3	511.0	511.3	511.5	511.7	512.0	511.5	510.4	509.3
137.5°	535.5	535.1	534.8	534.4	534.8	535.1	535.5	535.8	535.6	534.4	533.4
140°	550.5	550.1	549.5	548.9	549.5	550.1	550.5	551.1	550.9	549.9	548.9
142.5°	564.8	564.2	563.6	563.1	563.6	564.2	564.8	565.3	565.1	564.2	563.4
145°	584.6	584.0	583.4	582.9	583.4	584.0	584.6	585.0	584.9	584.2	583.4
147.5°	601.7	601.2	600.8	600.3	600.8	601.2	601.7	602.1	602.1	601.5	601.0
150°	612.6	612.0	611.4	611.0	611.4	612.0	612.6	613.1	613.0	612.4	611.7
152.5°	622.2	621.4	620.7	620.0	620.7	621.4	622.2	622.8	622.9	622.3	621.6
155°	635.2	634.3	633.5	632.5	633.5	634.3	635.2	636.0	636.2	635.6	634.9
157.5°	646.6	645.7	644.9	644.0	644.9	645.7	646.6	647.5	647.5	646.8	646.0
160°	653.1	652.3	651.5	650.7	651.5	652.3	653.1	653.8	653.8	653.2	652.5
162.5°	659.1	658.2	657.2	656.3	657.2	658.2	659.1	660.1	660.2	659.4	658.6
165°	666.8	666.1	665.3	664.5	665.3	666.1	666.8	667.6	667.6	666.8	666.1
167.5°	672.7	671.8	670.7	669.8	670.7	671.8	672.7	673.7	673.8	673.1	672.2
170°	675.8	674.9	673.9	672.9	673.9	674.9	675.8	676.8	676.9	676.2	675.4
172.5°	678.3	677.2	676.3	675.2	676.3	677.2	678.3	679.2	679.3	678.5	677.8
175°	680.6	679.5	678.4	677.3	678.4	679.5	680.6	681.7	681.8	681.1	680.3
177.5°	681.0	680.1	679.4	678.6	679.4	680.1	681.0	681.7	681.8	681.3	680.6
180°	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8



TEST NUMBER: P331741-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	1998.9	2007.1	2019.2	2026.1	2037.7	2045.2	2049.3	2056.7	2060.8	2075.3	2090.3
5°	1887.3	1898.8	1919.1	1937.9	1958.1	1979.1	1994.2	2011.6	2027.4	2054.8	2083.8
7.5°	1759.3	1775.4	1806.7	1836.6	1871.9	1901.5	1927.6	1957.2	1983.7	2023.0	2064.0
10°	1663.4	1691.6	1732.8	1761.0	1807.1	1836.7	1877.9	1910.4	1947.3	1999.2	2045.5
12.5°	1580.7	1614.8	1647.8	1687.0	1728.5	1777.8	1823.1	1864.8	1908.6	1962.3	2016.6
15°	1430.9	1480.0	1531.3	1570.9	1627.3	1679.3	1732.0	1788.4	1841.8	1906.1	1976.9
17.5°	1237.8	1294.8	1381.0	1449.1	1515.2	1567.4	1632.7	1700.8	1763.8	1841.4	1920.1
20°	1150.6	1192.5	1250.9	1342.7	1442.4	1498.0	1564.4	1639.6	1711.8	1796.3	1880.8
22.5°	1080.6	1117.9	1164.9	1236.4	1347.6	1423.4	1492.8	1569.1	1652.8	1739.1	1832.9
25°	980.8	1006.8	1055.9	1113.7	1190.3	1315.2	1391.1	1467.6	1558.7	1651.1	1758.0
27.5°	905.9	929.3	961.2	1016.3	1073.3	1163.0	1283.6	1367.2	1457.8	1561.9	1672.8
30°	848.7	876.1	911.5	950.6	1012.7	1082.7	1203.3	1300.1	1389.7	1496.6	1615.0
32.5°	807.1	828.8	858.9	898.5	950.3	1017.4	1113.7	1231.3	1318.6	1431.3	1554.9
35°	738.9	764.2	788.7	826.3	868.2	929.5	1002.5	1128.2	1214.8	1326.1	1450.3
37.5°	682.7	698.1	725.3	755.1	799.3	845.1	908.3	1021.1	1114.7	1224.0	1351.1
40°	639.9	659.4	679.7	712.8	749.0	793.1	855.2	939.0	1046.6	1153.5	1277.7
42.5°	598.3	623.0	644.4	666.7	706.2	750.3	800.9	871.9	981.8	1083.0	1203.7
45°	548.2	564.1	586.4	611.1	643.6	681.1	725.9	788.0	893.4	980.8	1094.3
47.5°	489.8	513.1	527.7	551.7	582.6	618.4	660.1	713.8	799.1	881.0	986.2
50°	450.0	473.8	494.7	516.4	543.8	578.5	613.2	665.2	733.9	819.8	918.0
52.5°	415.8	436.9	457.2	478.9	505.8	537.5	570.4	616.1	674.9	753.9	849.2
55°	369.1	382.1	403.0	424.7	448.6	478.9	510.7	548.9	599.5	665.9	743.2
57.5°	321.1	336.1	352.8	374.6	398.7	422.0	450.5	485.2	525.1	585.2	651.4
60°	294.0	305.5	319.2	341.7	364.0	384.9	412.5	441.3	478.9	530.8	587.2
62.5°	263.9	274.9	287.5	307.0	328.8	348.0	371.9	402.6	434.4	481.7	531.1
65°	213.8	229.7	242.0	259.3	277.4	297.6	316.3	340.9	369.1	406.6	450.7
67.5°	177.3	185.3	196.7	212.4	231.0	248.4	266.1	285.3	309.7	338.7	373.7
70°	161.1	164.0	166.2	181.3	198.6	215.9	232.6	250.6	271.5	295.4	325.7
72.5°	142.0	144.9	147.6	154.1	168.0	185.3	202.6	215.9	235.7	255.5	280.1
75°	112.6	117.0	119.1	122.8	127.8	139.4	155.3	168.2	179.8	195.0	214.5
77.5°	85.8	88.2	90.6	94.3	97.6	102.8	111.8	123.5	134.3	143.2	156.6
80°	67.9	68.6	71.5	73.0	77.3	80.9	85.2	94.6	105.5	109.1	118.5
82.5°	51.2	51.8	54.2	55.6	57.7	60.7	66.2	68.6	77.1	81.9	87.8
85°	28.2	27.4	29.6	29.6	31.1	32.5	33.9	37.5	39.7	45.5	46.9
87.5°	10.7	10.7	11.0	10.8	10.7	11.7	12.1	12.3	13.3	14.8	16.9
90°	10.4	9.8	9.0	8.1	7.3	6.3	5.3	4.1	2.9	1.7	0.5
92.5°	11.7	11.4	10.9	10.6	10.1	9.7	9.5	9.6	9.7	9.8	9.9
95°	19.7	19.2	18.4	17.6	16.9	16.1	17.5	21.1	24.8	28.4	32.0
97.5°	26.1	25.6	23.9	22.1	20.4	18.6	22.8	33.0	43.2	53.3	63.4
100°	28.9	28.0	26.2	24.3	22.4	20.6	27.1	42.1	57.1	72.1	87.1
102.5°	30.0	28.8	44.4	59.9	75.5	91.0	100.4	103.5	106.7	109.9	113.0
105°	31.2	30.0	59.9	89.7	119.5	149.4	162.7	159.4	156.1	152.8	149.5
107.5°	40.8	42.0	77.8	113.6	149.4	185.1	201.7	199.1	196.4	193.8	191.1
110°	75.1	86.1	117.6	149.3	180.9	212.4	227.1	224.8	222.5	220.2	217.9



TEST NUMBER: P331741-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	177.2	217.2	224.9	232.7	240.5	248.4	251.2	249.2	247.1	245.2	243.1
115°	252.9	303.5	300.8	298.0	295.3	292.6	290.3	288.4	286.5	284.6	282.9
117.5°	324.0	336.1	334.3	332.4	330.5	328.7	326.7	324.6	322.5	320.5	318.4
120°	361.8	360.5	358.5	356.7	354.7	352.7	350.9	349.2	347.6	345.9	344.3
122.5°	384.6	383.8	381.6	379.5	377.3	375.2	373.2	371.6	369.9	368.1	366.4
125°	416.4	415.7	413.6	411.5	409.4	407.4	405.6	404.2	402.7	401.3	399.9
127.5°	445.4	444.4	442.8	441.3	439.7	438.2	436.6	435.0	433.5	431.9	430.3
130°	464.1	462.9	461.7	460.4	459.3	458.1	456.6	454.9	453.1	451.3	449.6
132.5°	482.4	481.4	480.1	479.0	477.8	476.5	475.2	473.7	472.2	470.7	469.3
135°	508.2	507.1	506.1	505.2	504.2	503.2	501.8	500.1	498.3	496.6	494.8
137.5°	532.3	531.2	530.1	529.0	527.9	526.8	525.6	524.3	523.1	521.9	520.8
140°	548.0	547.0	545.7	544.6	543.4	542.2	541.1	540.3	539.4	538.5	537.6
142.5°	562.4	561.6	560.2	558.7	557.4	556.0	555.0	554.1	553.4	552.6	551.8
145°	582.7	581.9	580.0	578.2	576.4	574.5	573.6	573.7	573.8	573.9	574.0
147.5°	600.4	599.8	597.9	596.2	594.3	592.5	591.7	592.2	592.6	593.0	593.4
150°	611.1	610.4	608.7	606.9	605.2	603.4	602.9	603.7	604.5	605.2	606.0
152.5°	620.9	620.3	618.6	617.0	615.3	613.6	613.2	614.1	614.9	615.8	616.6
155°	634.2	633.6	632.3	630.9	629.6	628.3	628.1	629.1	630.1	631.1	632.1
157.5°	645.3	644.6	643.7	642.7	641.8	640.9	640.8	641.7	642.5	643.4	644.1
160°	652.0	651.3	650.6	650.0	649.3	648.7	648.7	649.3	650.0	650.6	651.3
162.5°	657.9	657.1	656.6	656.0	655.4	654.9	655.0	655.5	656.2	656.9	657.5
165°	665.3	664.5	664.2	663.8	663.5	663.3	663.4	664.0	664.7	665.3	666.0
167.5°	671.5	670.7	670.4	670.1	669.8	669.5	669.7	670.3	671.0	671.7	672.3
170°	674.7	673.9	673.6	673.4	673.3	673.0	673.3	673.9	674.6	675.2	675.8
172.5°	677.0	676.3	676.0	675.8	675.6	675.3	675.6	676.3	676.9	677.6	678.3
175°	679.6	678.8	678.5	678.3	678.2	678.0	678.2	679.0	679.8	680.5	681.3
177.5°	680.0	679.4	679.3	679.2	679.1	679.0	679.3	680.0	680.5	681.2	681.7
180°	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8



TEST NUMBER: P331741-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2090.8	2092.5	2104.1	2109.3	2119.8	2123.7	2128.4	2127.2	2127.2	2129.6	2145.7
5°	2095.4	2109.8	2131.5	2152.4	2172.7	2189.9	2201.5	2213.1	2217.4	2238.4	2257.1
7.5°	2087.8	2114.4	2150.2	2182.2	2220.4	2250.3	2275.2	2297.5	2312.9	2343.3	2374.5
10°	2078.0	2115.5	2156.0	2197.2	2249.8	2289.6	2330.1	2361.2	2371.2	2416.8	2442.8
12.5°	2058.3	2108.7	2160.0	2213.4	2264.9	2319.7	2364.2	2395.2	2430.7	2471.6	2519.6
15°	2028.9	2086.7	2153.8	2222.4	2296.1	2362.6	2410.3	2464.4	2503.4	2548.2	2590.1
17.5°	1986.6	2061.0	2146.4	2225.8	2311.0	2382.4	2448.0	2499.9	2527.4	2553.0	2559.2
20°	1953.0	2033.3	2133.6	2227.5	2312.7	2395.1	2460.0	2503.4	2510.7	2511.3	2473.0
22.5°	1916.7	2007.2	2112.2	2208.5	2310.5	2402.0	2452.6	2471.1	2442.4	2393.5	2319.4
25°	1849.7	1954.5	2076.5	2186.3	2297.5	2384.3	2401.6	2369.1	2268.7	2163.2	2029.6
27.5°	1777.3	1895.0	2025.8	2147.9	2266.3	2320.1	2282.6	2165.5	1984.7	1827.5	1637.0
30°	1724.1	1856.2	1984.8	2121.3	2231.1	2254.2	2168.3	1995.6	1784.7	1547.8	1357.9
32.5°	1663.4	1802.0	1943.2	2084.3	2176.2	2153.7	2011.7	1799.2	1551.9	1319.0	1139.4
35°	1576.7	1719.8	1872.2	2013.7	2072.2	1974.7	1762.4	1485.7	1232.9	1015.5	892.0
37.5°	1476.6	1632.4	1790.8	1920.8	1916.7	1754.2	1464.9	1179.3	966.9	838.3	750.3
40°	1405.5	1563.0	1734.2	1844.0	1797.1	1585.4	1272.0	1002.5	847.3	744.7	680.4
42.5°	1337.4	1495.4	1665.5	1752.7	1671.0	1410.9	1098.6	887.5	759.4	679.4	627.3
45°	1221.3	1388.2	1545.7	1594.0	1448.1	1161.4	888.4	735.3	650.1	590.8	554.7
47.5°	1108.0	1272.1	1415.8	1416.6	1219.4	941.9	749.4	636.3	563.5	517.7	491.4
50°	1038.6	1194.7	1315.2	1296.5	1072.6	837.8	670.2	572.8	512.1	476.7	449.2
52.5°	960.6	1112.0	1216.4	1163.0	948.4	737.3	599.2	517.3	467.0	436.2	411.7
55°	847.3	981.6	1055.3	974.3	773.5	613.2	506.3	442.1	404.4	378.4	357.5
57.5°	735.8	846.7	893.1	798.8	637.2	508.5	428.3	380.0	342.8	324.1	313.3
60°	665.9	760.5	793.1	689.1	554.0	444.9	379.2	334.4	307.0	294.7	283.9
62.5°	597.2	674.5	687.9	592.6	483.0	389.5	333.0	295.1	276.9	265.2	255.0
65°	495.5	551.1	544.6	468.1	382.1	309.2	268.0	244.9	231.1	214.5	196.4
67.5°	407.9	441.9	421.4	364.0	291.6	240.3	213.4	195.9	178.8	163.1	158.9
70°	352.5	371.9	350.3	297.6	239.0	201.5	179.8	158.9	148.8	145.2	138.6
72.5°	299.4	306.1	282.7	237.5	194.5	166.8	145.7	134.0	128.6	125.5	121.3
75°	224.6	219.6	199.3	164.0	135.1	116.3	109.8	105.5	101.8	99.0	96.8
77.5°	157.8	150.3	132.3	109.2	94.1	85.1	81.2	78.9	77.1	75.7	73.5
80°	118.5	113.4	95.4	78.0	71.5	67.2	65.0	62.1	62.1	60.7	58.5
82.5°	86.7	81.1	65.3	57.2	53.6	51.0	49.4	47.7	47.1	47.4	45.8
85°	45.5	36.9	32.5	31.1	28.9	27.4	28.2	26.8	26.8	26.8	26.0
87.5°	14.2	11.6	11.2	10.8	11.7	11.9	11.4	11.6	12.3	11.9	12.6
90°	1.7	2.9	4.1	5.3	6.3	7.3	8.1	9.0	9.8	10.4	10.9
92.5°	9.8	9.7	9.6	9.5	9.7	10.1	10.6	10.9	11.4	11.7	12.0
95°	28.4	24.8	21.1	17.5	16.1	16.9	17.6	18.4	19.2	19.7	20.3
97.5°	53.3	43.2	33.0	22.8	18.6	20.4	22.1	23.9	25.6	26.1	26.6
100°	72.1	57.1	42.1	27.1	20.6	22.4	24.3	26.2	28.0	28.9	29.8
102.5°	109.9	106.7	103.5	100.4	91.0	75.5	59.9	44.4	28.8	30.0	31.1
105°	152.8	156.1	159.4	162.7	149.4	119.5	89.7	59.9	30.0	31.2	32.4
107.5°	193.8	196.4	199.1	201.7	185.1	149.4	113.6	77.8	42.0	40.8	39.6
110°	220.2	222.5	224.8	227.1	212.4	180.9	149.3	117.6	86.1	75.1	64.2



TEST NUMBER: P331741-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	245.2	247.1	249.2	251.2	248.4	240.5	232.7	224.9	217.2	177.2	137.3
115°	284.6	286.5	288.4	290.3	292.6	295.3	298.0	300.8	303.5	252.9	202.3
117.5°	320.5	322.5	324.6	326.7	328.7	330.5	332.4	334.3	336.1	324.0	311.7
120°	345.9	347.6	349.2	350.9	352.7	354.7	356.7	358.5	360.5	361.8	363.2
122.5°	368.1	369.9	371.6	373.2	375.2	377.3	379.5	381.6	383.8	384.6	385.3
125°	401.3	402.7	404.2	405.6	407.4	409.4	411.5	413.6	415.7	416.4	417.2
127.5°	431.9	433.5	435.0	436.6	438.2	439.7	441.3	442.8	444.4	445.4	446.6
130°	451.3	453.1	454.9	456.6	458.1	459.3	460.4	461.7	462.9	464.1	465.2
132.5°	470.7	472.2	473.7	475.2	476.5	477.8	479.0	480.1	481.4	482.4	483.4
135°	496.6	498.3	500.1	501.8	503.2	504.2	505.2	506.1	507.1	508.2	509.3
137.5°	521.9	523.1	524.3	525.6	526.8	527.9	529.0	530.1	531.2	532.3	533.4
140°	538.5	539.4	540.3	541.1	542.2	543.4	544.6	545.7	547.0	548.0	548.9
142.5°	552.6	553.4	554.1	555.0	556.0	557.4	558.7	560.2	561.6	562.4	563.4
145°	573.9	573.8	573.7	573.6	574.5	576.4	578.2	580.0	581.9	582.7	583.4
147.5°	593.0	592.6	592.2	591.7	592.5	594.3	596.2	597.9	599.8	600.4	601.0
150°	605.2	604.5	603.7	602.9	603.4	605.2	606.9	608.7	610.4	611.1	611.7
152.5°	615.8	614.9	614.1	613.2	613.6	615.3	617.0	618.6	620.3	620.9	621.6
155°	631.1	630.1	629.1	628.1	628.3	629.6	630.9	632.3	633.6	634.2	634.9
157.5°	643.4	642.5	641.7	640.8	640.9	641.8	642.7	643.7	644.6	645.3	646.0
160°	650.6	650.0	649.3	648.7	648.7	649.3	650.0	650.6	651.3	652.0	652.5
162.5°	656.9	656.2	655.5	655.0	654.9	655.4	656.0	656.6	657.1	657.9	658.6
165°	665.3	664.7	664.0	663.4	663.3	663.5	663.8	664.2	664.5	665.3	666.1
167.5°	671.7	671.0	670.3	669.7	669.5	669.8	670.1	670.4	670.7	671.5	672.2
170°	675.2	674.6	673.9	673.3	673.0	673.3	673.4	673.6	673.9	674.7	675.4
172.5°	677.6	676.9	676.3	675.6	675.3	675.6	675.8	676.0	676.3	677.0	677.8
175°	680.5	679.8	679.0	678.2	678.0	678.2	678.3	678.5	678.8	679.6	680.3
177.5°	681.2	680.5	680.0	679.3	679.0	679.1	679.2	679.3	679.4	680.0	680.6
180°	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8



TEST NUMBER: P331741-830
 CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2151.5	2159.0	2162.5	2162.5	2166.5	2164.8	2163.0
5°	2275.2	2288.9	2291.8	2304.8	2314.1	2311.3	2312.7
7.5°	2398.1	2420.2	2442.0	2452.0	2453.5	2459.4	2461.5
10°	2473.8	2491.9	2525.8	2520.7	2546.0	2560.5	2536.7
12.5°	2546.6	2571.0	2594.5	2601.0	2615.4	2620.0	2610.6
15°	2612.4	2625.5	2627.0	2623.3	2627.6	2624.0	2610.3
17.5°	2550.9	2529.9	2487.1	2466.8	2450.8	2427.1	2417.6
20°	2449.2	2387.1	2314.9	2286.0	2252.0	2185.6	2201.5
22.5°	2229.7	2158.9	2086.7	2002.3	1962.0	1899.0	1895.3
25°	1888.0	1765.9	1631.6	1537.8	1482.8	1420.0	1392.5
27.5°	1467.9	1314.3	1204.2	1148.4	1097.7	1047.9	1045.8
30°	1191.8	1076.2	991.0	943.3	912.2	891.3	895.6
32.5°	1004.6	925.4	867.9	828.3	805.3	789.6	789.3
35°	821.2	767.0	730.2	713.6	697.0	685.4	686.2
37.5°	702.8	670.2	649.8	631.4	621.0	615.4	612.2
40°	642.1	615.4	599.5	588.6	579.9	572.0	570.6
42.5°	594.2	572.0	556.2	547.6	539.5	534.0	532.4
45°	527.3	509.2	494.7	485.4	481.7	476.7	476.7
47.5°	469.0	451.3	440.0	434.1	427.9	424.5	424.4
50°	429.8	416.0	406.0	402.3	397.3	395.1	394.4
52.5°	394.5	384.3	377.0	374.6	372.4	369.7	370.1
55°	346.7	340.9	338.0	335.8	332.2	327.9	330.8
57.5°	306.4	301.5	293.7	286.9	283.6	280.5	281.7
60°	278.1	268.0	257.9	249.9	247.7	241.2	241.2
62.5°	242.2	228.1	215.7	211.2	209.1	206.0	205.4
65°	186.3	180.6	177.7	174.7	173.3	173.3	171.9
67.5°	154.4	152.1	148.9	148.2	146.8	146.4	145.9
70°	136.5	133.7	132.1	131.5	130.0	130.7	128.6
72.5°	119.1	116.9	116.6	114.7	113.9	114.0	112.4
75°	93.9	93.9	93.2	92.5	91.0	90.3	91.0
77.5°	72.2	72.4	71.1	71.0	70.8	71.0	70.2
80°	57.8	58.5	57.8	57.0	56.4	57.0	56.4
82.5°	45.6	44.7	44.5	44.4	44.2	43.7	43.6
85°	26.0	26.8	26.0	25.3	25.3	25.3	26.0
87.5°	12.2	12.3	12.3	12.3	12.3	12.4	11.9
90°	11.5	12.1	12.4	12.6	12.8	13.1	13.3
92.5°	12.3	12.5	12.7	12.9	13.0	13.2	13.3
95°	20.8	21.4	21.6	21.5	21.4	21.3	21.1
97.5°	27.0	27.4	27.7	27.8	28.0	28.1	28.3
100°	30.6	31.6	32.0	32.3	32.5	32.7	33.0
102.5°	32.2	33.4	34.1	34.4	34.7	35.0	35.3
105°	33.6	34.8	35.6	36.1	36.5	36.9	37.4
107.5°	38.4	37.1	36.8	37.1	37.6	38.0	38.5
110°	53.3	42.3	37.1	37.5	38.0	38.5	38.8



TEST NUMBER: P331741-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	97.5	57.6	37.9	38.2	38.5	38.9	39.2
115°	151.7	101.0	71.8	63.9	56.1	48.2	40.3
117.5°	299.4	287.2	268.2	242.2	216.4	190.6	164.7
120°	364.5	365.8	359.1	344.3	329.6	314.8	300.0
122.5°	386.2	386.9	385.9	383.0	380.1	377.3	374.4
125°	417.9	418.7	419.2	419.6	419.9	420.3	420.6
127.5°	447.7	448.8	449.4	449.5	449.6	449.6	449.7
130°	466.5	467.7	468.3	468.1	468.0	467.9	467.8
132.5°	484.5	485.5	485.9	485.8	485.7	485.6	485.5
135°	510.4	511.5	512.0	511.7	511.5	511.3	511.0
137.5°	534.4	535.6	535.8	535.5	535.1	534.8	534.4
140°	549.9	550.9	551.1	550.5	550.1	549.5	548.9
142.5°	564.2	565.1	565.3	564.8	564.2	563.6	563.1
145°	584.2	584.9	585.0	584.6	584.0	583.4	582.9
147.5°	601.5	602.1	602.1	601.7	601.2	600.8	600.3
150°	612.4	613.0	613.1	612.6	612.0	611.4	611.0
152.5°	622.3	622.9	622.8	622.2	621.4	620.7	620.0
155°	635.6	636.2	636.0	635.2	634.3	633.5	632.5
157.5°	646.8	647.5	647.5	646.6	645.7	644.9	644.0
160°	653.2	653.8	653.8	653.1	652.3	651.5	650.7
162.5°	659.4	660.2	660.1	659.1	658.2	657.2	656.3
165°	666.8	667.6	667.6	666.8	666.1	665.3	664.5
167.5°	673.1	673.8	673.7	672.7	671.8	670.7	669.8
170°	676.2	676.9	676.8	675.8	674.9	673.9	672.9
172.5°	678.5	679.3	679.2	678.3	677.2	676.3	675.2
175°	681.1	681.8	681.7	680.6	679.5	678.4	677.3
177.5°	681.3	681.8	681.7	681.0	680.1	679.4	678.6
180°	679.8	679.8	679.8	679.8	679.8	679.8	679.8

(END OF REPORT)