

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333531-840

Luminaire Tested: **S125RDIP-S610D590U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333531-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S610D590U840-4F0-1E-UDD-F4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4544.2 lumens  
Efficiency: N/A  
Efficacy: 138.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 32.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333531-840

CATALOG NUMBER: S125RDIP-S610D590U840-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P333531-840

CATALOG NUMBER: S125RDIP-S610D590U840-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	94	91	87	91	88	84	81	75	72	70	63	61	60	52	51	50	45
2	90	83	77	72	83	77	72	67	66	62	59	56	53	50	46	44	43	38
3	82	73	66	60	76	68	61	56	58	53	49	49	46	43	41	39	36	32
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	32	28
5	69	58	50	44	64	54	47	41	47	41	37	40	35	32	33	30	28	24
6	64	52	44	38	59	48	41	36	42	36	32	36	32	28	30	27	24	22
7	59	47	39	33	55	44	37	32	38	32	28	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	26	22	20	17
9	51	39	31	26	47	37	30	25	32	26	23	28	23	20	24	20	18	16
10	48	36	29	24	44	34	27	23	29	24	20	26	21	18	22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6561	6561	6561
5°	6576	6501	6541
10°	6526	6441	6441
15°	6449	6310	6258
20°	6349	6128	6054
25°	6233	5949	5818
30°	6088	5739	5557
35°	5941	5523	5263
40°	5802	5298	4975
45°	5634	5045	4661
50°	5466	4772	4332
55°	5271	4510	3984
60°	5074	4193	3608
65°	4843	3822	3177
70°	4579	3361	2738
75°	4212	2832	2278
80°	3712	2228	1912
85°	3127	1815	1704



TEST NUMBER: P333531-840

CATALOG NUMBER: S125RDIP-S610D590U840-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	95.5	2.1
10°-20°	267.0	5.9
20°-30°	387.1	8.5
30°-40°	441.2	9.7
40°-50°	430.0	9.5
50°-60°	362.0	8.0
60°-70°	253.8	5.6
70°-80°	130.4	2.9
80°-90°	34.5	0.8
90°-100°	207.1	4.6
100°-110°	445.2	9.8
110°-120°	417.8	9.2
120°-130°	338.6	7.5
130°-140°	271.7	6.0
140°-150°	205.1	4.5
150°-160°	144.3	3.2
160°-170°	85.1	1.9
170°-180°	27.7	0.6
0°-30°	749.6	16.5
0°-40°	1190.8	26.2
0°-60°	1982.8	43.6
0°-90°	2401.5	52.8
90°-120°	1070.2	23.5
90°-150°	1885.6	41.5
90°-180°	2143.0	47.2
0°-180°	4544.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1016	1016	1016	1016	1016	
5°	1014	1011	1003	1010	1009	96
15°	964	959	944	943	936	272
25°	875	862	835	825	816	402
35°	754	734	700	679	668	472
45°	617	594	552	523	510	476
55°	468	442	400	367	354	418
65°	317	290	250	220	208	314
75°	169	145	114	97	91	179
85°	42	29	24	24	23	47
90°	1	5	9	12	13	3
95°	19	56	510	232	135	20
105°	65	91	418	822	763	69
115°	116	140	335	723	850	114
125°	161	189	321	575	670	143
135°	189	227	319	482	556	147
145°	220	252	320	399	439	138
155°	251	270	312	353	368	116
165°	274	282	300	318	323	77
175°	285	285	287	291	290	27
180°	286	286	286	286	286	



TEST NUMBER: P333531-840

CATALOG NUMBER: S125RDIP-S610D590U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9
2.5°	1017.7	1017.3	1016.9	1016.5	1016.1	1015.2	1013.8	1012.5	1011.1	1009.8	1011.1
5°	1014.3	1013.7	1013.0	1012.3	1011.6	1010.4	1008.5	1006.6	1004.7	1002.8	1004.5
7.5°	1004.4	1003.7	1003.1	1002.4	1001.8	1000.4	998.0	995.8	993.6	991.3	992.5
10°	995.1	994.6	994.1	993.6	993.1	991.7	989.3	986.9	984.5	982.1	982.6
12.5°	984.7	984.1	983.4	982.8	982.1	980.2	977.0	973.8	970.6	967.3	967.8
15°	964.5	963.4	962.4	961.4	960.4	958.1	954.5	950.9	947.4	943.7	943.6
17.5°	941.6	940.1	938.5	937.0	935.3	932.3	927.8	923.3	918.8	914.3	913.4
20°	923.8	922.1	920.4	918.7	917.0	913.4	908.0	902.5	897.1	891.6	890.7
22.5°	904.1	902.4	900.8	899.1	897.4	893.6	887.9	882.2	876.5	870.7	869.1
25°	874.7	872.1	869.6	867.1	864.4	860.0	853.7	847.4	841.1	834.8	832.6
27.5°	840.9	837.9	834.8	831.6	828.5	823.6	816.9	810.1	803.3	796.6	793.5
30°	816.4	813.1	809.9	806.7	803.4	798.2	791.0	784.0	776.8	769.6	765.7
32.5°	792.4	788.7	784.9	781.1	777.3	771.7	764.5	757.2	749.8	742.6	738.2
35°	753.5	749.4	745.3	741.2	737.1	731.2	723.6	715.9	708.2	700.5	695.6
37.5°	715.3	710.2	705.3	700.3	695.4	688.9	681.0	673.1	665.2	657.2	651.4
40°	688.2	683.2	678.0	672.9	667.8	661.2	653.0	644.8	636.6	628.4	622.0
42.5°	660.0	654.8	649.5	644.3	639.0	632.2	623.7	615.2	606.8	598.3	592.1
45°	616.9	612.0	607.0	602.1	597.1	590.0	580.6	571.2	561.8	552.4	545.6
47.5°	572.3	567.0	561.8	556.6	551.4	544.0	534.6	525.1	515.7	506.2	499.3
50°	544.0	538.4	532.7	527.1	521.5	513.8	504.1	494.4	484.6	474.9	467.8
52.5°	513.3	507.6	501.8	496.0	490.3	482.8	473.6	464.4	455.2	446.1	438.4
55°	468.1	462.6	457.2	451.7	446.3	438.7	429.2	419.6	410.1	400.5	392.8
57.5°	422.3	416.5	410.6	404.9	399.0	391.4	382.2	373.0	363.9	354.7	347.1
60°	392.8	386.9	380.9	375.0	369.0	361.4	352.1	343.0	333.8	324.6	317.1
62.5°	361.5	355.9	350.1	344.5	338.8	331.2	321.9	312.6	303.3	293.9	286.9
65°	316.9	311.1	305.3	299.5	293.7	286.3	277.2	268.2	259.1	250.1	243.3
67.5°	272.6	266.7	260.9	255.2	249.3	242.2	233.5	224.8	216.1	207.4	201.3
70°	242.5	236.7	230.9	225.1	219.2	212.1	203.6	195.1	186.5	178.0	172.7
72.5°	213.0	207.3	201.7	196.0	190.4	183.5	175.5	167.5	159.6	151.6	146.7
75°	168.8	163.7	158.5	153.5	148.3	142.2	135.0	127.8	120.7	113.5	109.8
77.5°	124.9	120.8	116.7	112.6	108.6	103.6	97.9	92.2	86.4	80.7	78.1
80°	99.8	95.6	91.6	87.5	83.4	79.0	74.1	69.4	64.6	59.9	58.3
82.5°	75.2	71.5	67.9	64.1	60.5	57.0	53.7	50.4	47.2	43.9	43.2
85°	42.2	39.1	36.1	33.0	29.9	28.0	27.1	26.3	25.4	24.5	24.3
87.5°	14.2	13.4	12.6	11.9	11.2	10.9	10.9	11.0	10.9	11.0	11.2
90°	0.6	1.1	2.3	3.4	4.6	5.8	6.4	7.5	8.1	9.2	9.8
92.5°	7.1	8.5	13.3	20.5	30.4	47.3	78.7	131.5	188.7	185.7	150.4
95°	19.0	19.6	24.2	30.5	43.2	69.2	130.8	257.5	416.5	510.4	499.5
97.5°	31.6	32.2	35.4	41.8	53.2	71.9	112.7	205.5	371.9	545.0	632.0
100°	40.3	41.5	43.8	50.1	61.1	78.4	111.8	186.6	331.8	520.2	664.2
102.5°	50.0	50.7	52.5	59.4	69.4	86.1	115.9	178.8	301.3	476.4	644.8
105°	65.1	65.1	68.0	73.7	82.9	99.1	124.4	175.7	271.9	417.7	583.0
107.5°	79.9	81.0	83.7	88.5	98.1	112.6	137.1	181.0	259.4	377.2	519.9
110°	90.5	91.6	93.9	99.1	107.8	122.7	146.3	186.0	255.8	358.3	483.9



TEST NUMBER: P333531-840

CATALOG NUMBER: S125RDIP-S610D590U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	101.1	102.2	104.0	109.3	117.9	132.4	155.1	192.5	255.8	347.3	457.2
115°	116.3	117.5	119.3	124.4	133.1	147.4	168.7	202.2	257.5	335.3	428.0
117.5°	130.2	131.9	133.8	139.0	148.8	162.7	182.9	213.3	261.3	329.4	410.6
120°	139.4	141.2	143.4	148.7	158.4	172.8	193.0	220.7	265.0	326.6	400.9
122.5°	149.1	150.4	152.2	157.3	168.1	182.5	202.7	228.9	268.2	324.4	392.6
125°	161.3	162.5	165.3	170.5	181.5	196.4	215.4	240.2	273.7	321.4	381.3
127.5°	170.9	172.6	176.3	182.9	194.5	209.4	227.7	250.5	279.7	320.0	371.0
130°	176.8	178.5	183.2	190.7	202.8	217.7	235.6	257.5	283.5	319.1	364.1
132.5°	181.5	183.7	189.1	197.6	210.2	225.1	243.0	263.5	287.6	319.1	358.5
135°	188.9	191.3	198.1	207.4	219.4	235.0	252.9	271.9	293.2	319.1	351.9
137.5°	198.4	200.2	206.6	215.8	227.6	243.7	259.9	278.1	298.4	319.8	346.1
140°	203.9	205.6	212.6	221.8	232.8	248.3	265.0	282.3	300.7	320.3	343.4
142.5°	210.4	211.7	218.1	227.3	237.8	252.5	268.2	284.6	302.1	320.7	341.0
145°	220.0	221.2	226.9	235.0	245.4	258.6	273.7	288.0	303.6	320.3	337.6
147.5°	230.1	230.9	235.8	243.3	252.3	264.0	277.1	290.1	304.2	318.8	334.0
150°	236.2	237.3	241.4	248.8	256.9	266.7	279.4	291.4	304.2	317.4	331.2
152.5°	242.7	243.3	246.9	253.5	261.1	269.9	281.7	292.4	303.7	315.6	328.0
155°	251.2	251.2	254.6	260.3	266.1	274.2	284.0	293.2	302.5	312.3	322.6
157.5°	258.7	258.6	261.5	266.4	271.5	277.5	286.0	293.8	300.9	308.7	317.5
160°	263.9	263.3	265.6	269.6	274.2	279.4	286.9	293.8	299.5	306.5	313.4
162.5°	268.0	267.4	269.7	273.3	277.0	281.2	287.8	293.4	298.2	303.7	309.7
165°	274.2	273.1	274.8	277.6	279.9	283.5	288.0	292.7	296.1	299.5	304.2
167.5°	278.3	277.8	278.8	280.4	282.1	284.2	288.0	291.2	292.9	295.5	298.7
170°	281.1	280.5	281.1	282.3	283.5	285.2	288.0	290.3	291.4	293.2	295.5
172.5°	283.0	282.0	282.5	283.7	284.4	285.2	287.6	289.4	289.6	290.4	292.3
175°	285.2	284.0	284.6	285.2	285.2	285.2	286.9	288.0	287.4	287.4	288.0
177.5°	286.2	285.3	285.3	285.7	285.3	285.3	286.2	286.6	285.7	285.7	286.2
180°	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7



TEST NUMBER: P333531-840

CATALOG NUMBER: S125RDIP-S610D590U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9
2.5°	1012.5	1013.8	1015.2	1015.8	1015.7	1015.5	1015.4	1015.3
5°	1006.2	1007.9	1009.7	1010.4	1010.0	1009.7	1009.4	1009.0
7.5°	993.7	994.9	996.1	996.5	996.1	995.7	995.4	995.0
10°	983.1	983.6	984.2	984.2	983.6	983.1	982.6	982.1
12.5°	968.2	968.6	968.9	968.7	967.9	967.1	966.3	965.5
15°	943.4	943.2	943.1	942.2	940.7	939.2	937.7	936.0
17.5°	912.6	911.7	910.9	909.8	908.6	907.3	906.1	904.7
20°	889.9	889.0	888.2	887.0	885.4	883.9	882.4	880.8
22.5°	867.4	865.7	864.0	862.5	861.3	860.0	858.8	857.5
25°	830.4	828.2	826.0	823.8	822.0	820.1	818.3	816.4
27.5°	790.4	787.3	784.2	781.7	779.9	778.1	776.3	774.5
30°	761.7	757.8	753.9	751.1	749.6	748.1	746.6	745.1
32.5°	733.9	729.6	725.3	722.2	720.1	718.2	716.3	714.4
35°	690.6	685.7	680.8	677.1	674.7	672.3	669.9	667.5
37.5°	645.4	639.4	633.5	629.3	627.0	624.8	622.5	620.2
40°	615.4	608.9	602.5	598.2	596.2	594.1	592.1	590.1
42.5°	585.9	579.7	573.5	568.9	565.9	562.9	559.9	556.9
45°	538.8	532.0	525.1	520.5	518.0	515.3	512.8	510.3
47.5°	492.2	485.1	478.2	473.2	470.4	467.6	464.7	461.9
50°	460.6	453.4	446.3	441.4	438.9	436.4	433.7	431.2
52.5°	430.7	422.9	415.3	410.1	407.6	405.1	402.4	399.9
55°	385.2	377.5	369.8	364.7	361.9	359.2	356.5	353.8
57.5°	339.6	332.1	324.7	319.6	317.2	314.8	312.5	310.0
60°	309.5	302.1	294.6	289.5	287.0	284.4	281.9	279.3
62.5°	279.9	273.0	266.0	261.3	258.7	256.2	253.6	251.1
65°	236.5	229.6	222.9	218.1	215.6	213.1	210.5	207.9
67.5°	195.0	188.7	182.5	178.3	176.3	174.3	172.2	170.2
70°	167.4	162.2	156.8	153.2	151.2	149.2	147.0	145.0
72.5°	141.9	136.9	132.1	129.0	127.6	126.2	124.9	123.5
75°	106.0	102.3	98.6	96.0	94.9	93.7	92.5	91.3
77.5°	75.4	72.8	70.2	68.5	67.6	66.7	65.8	64.9
80°	56.8	55.2	53.7	52.8	52.4	52.1	51.7	51.4
82.5°	42.4	41.7	41.0	40.6	40.4	40.2	40.0	39.8
85°	24.2	24.0	23.8	23.7	23.5	23.3	23.2	23.0
87.5°	11.3	11.4	11.5	11.7	11.5	11.4	11.4	11.2
90°	10.4	10.9	11.5	12.6	12.6	12.6	13.2	13.2
92.5°	102.1	74.1	55.7	47.3	39.9	38.5	37.7	36.8
95°	414.1	326.6	255.8	207.4	166.5	149.2	144.6	135.4
97.5°	616.8	555.4	486.5	419.1	383.5	351.2	334.6	327.2
100°	708.5	680.3	621.0	561.1	521.3	479.9	458.6	449.3
102.5°	739.4	756.8	728.3	687.8	645.3	615.8	592.7	585.7
105°	721.2	800.1	825.5	819.1	800.7	781.7	770.2	763.3
107.5°	656.2	761.5	826.7	856.7	866.1	866.0	862.1	857.5
110°	608.3	717.8	799.0	848.0	873.8	884.8	888.9	888.9





TEST NUMBER: P333531-840

CATALOG NUMBER: S125RDIP-S610D590U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	570.6	674.5	756.6	814.4	852.2	871.0	881.0	885.1
115°	523.0	612.4	691.3	754.1	799.0	826.7	842.7	850.3
117.5°	492.4	569.4	637.3	695.0	739.9	768.5	784.5	789.1
120°	475.8	544.9	608.3	659.0	701.7	729.3	744.9	749.4
122.5°	463.4	527.5	583.9	631.4	669.3	694.7	710.2	714.4
125°	445.2	504.0	554.2	595.6	627.9	651.6	664.2	669.9
127.5°	426.9	481.7	528.5	567.3	596.5	617.4	629.3	632.0
130°	415.4	466.1	511.0	548.4	577.2	596.2	607.7	611.2
132.5°	403.8	451.3	492.1	528.2	556.9	575.9	586.5	590.5
135°	388.8	428.6	465.4	498.3	523.6	542.6	553.0	556.4
137.5°	376.2	408.3	439.0	466.9	489.5	506.9	516.3	520.2
140°	369.2	396.4	422.8	447.1	468.4	483.3	491.9	494.8
142.5°	363.2	386.2	409.0	430.0	448.1	460.7	468.9	471.3
145°	355.5	373.2	391.1	406.7	420.5	430.3	436.7	439.0
147.5°	348.1	362.5	376.3	388.0	399.0	406.8	410.5	411.5
150°	343.9	356.6	367.5	377.9	386.6	393.4	395.8	396.4
152.5°	339.3	350.6	360.6	368.7	376.0	381.4	383.7	384.4
155°	332.3	341.6	349.6	356.0	361.7	365.8	367.5	368.1
157.5°	325.5	333.1	339.3	344.3	348.7	352.0	353.7	353.6
160°	320.8	326.6	332.3	336.4	340.4	343.4	344.5	343.9
162.5°	315.8	321.1	325.9	329.5	332.6	335.1	335.3	335.2
165°	308.7	312.8	316.3	319.1	321.4	322.6	322.6	322.6
167.5°	302.1	304.8	307.4	309.4	310.6	311.6	311.1	311.0
170°	298.4	300.1	301.8	303.0	304.2	304.8	304.8	304.2
172.5°	294.3	296.0	297.2	297.9	298.2	299.2	298.3	297.7
175°	289.7	289.7	290.9	290.9	290.9	291.4	290.3	289.7
177.5°	286.6	287.1	287.1	287.1	286.6	287.1	285.7	285.7
180°	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7

(END OF REPORT)