

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331743-830

Luminaire Tested: **SA2XXRDIP-C1005D530U830-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331743-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5540.0 lumens
Efficiency: N/A
Efficacy: 100.5 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331743-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331743-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65
1	102	98	94	91	96	92	89	86	82	80	77	72	70	69	63	62	61	57
2	94	87	81	76	88	82	77	73	73	69	66	65	62	59	57	55	53	49
3	86	77	70	65	81	73	67	62	65	61	57	58	55	51	52	49	46	43
4	80	69	62	56	75	66	59	54	59	54	49	53	49	45	47	44	41	38
5	74	63	55	49	69	59	52	47	54	48	44	48	44	40	43	39	37	34
6	68	57	49	43	64	54	47	42	49	43	39	44	39	36	39	36	33	30
7	64	52	44	39	60	49	42	37	45	39	35	40	36	32	36	33	30	27
8	59	47	40	35	56	45	38	34	41	36	31	37	33	29	34	30	27	25
9	56	44	36	32	52	42	35	31	38	33	29	35	30	27	31	28	25	23
10	52	40	33	29	49	39	32	28	35	30	26	32	28	25	29	26	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	33562	33562	33562	33562
5°	37483	33773	29945	33773
10°	41589	33536	25956	33536
15°	43632	33045	20451	33045
20°	37826	32316	17698	32316
25°	24807	31319	15800	31319
30°	16697	30109	14300	30109
35°	13525	28586	12899	28586
40°	12026	26930	11936	26930
45°	10885	24987	10654	24987
50°	9907	23059	9869	23059
55°	9312	20921	9191	20921
60°	7789	18962	7698	18962
65°	6567	17219	7450	17219
70°	6071	15375	7024	15375
75°	5677	13381	6488	13381
80°	5244	11018	5774	11018
85°	4817	8688	5076	8688



TEST NUMBER: P331743-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	197.1	3.6
10°-20°	549.1	9.9
20°-30°	707.5	12.8
30°-40°	672.4	12.1
40°-50°	576.0	10.4
50°-60°	438.6	7.9
60°-70°	277.3	5.0
70°-80°	138.5	2.5
80°-90°	38.6	0.7
90°-100°	111.8	2.0
100°-110°	379.3	6.8
110°-120°	402.9	7.3
120°-130°	331.7	6.0
130°-140°	266.3	4.8
140°-150°	201.3	3.6
150°-160°	141.4	2.6
160°-170°	83.3	1.5
170°-180°	27.1	0.5
0°-30°	1453.7	26.2
0°-40°	2126.0	38.4
0°-60°	3140.7	56.7
0°-90°	3595.0	64.9
90°-120°	893.9	16.1
90°-150°	1693.2	30.6
90°-180°	1945.0	35.1
0°-180°	5540.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2079	2079	2079	2079	2079	
5°	2313	2084	1848	2084	2313	228
15°	2610	1977	1224	1977	2610	704
25°	1392	1758	887	1758	1392	661
35°	686	1450	654	1450	686	439
45°	477	1094	467	1094	477	369
55°	331	743	326	743	331	290
65°	172	451	195	451	172	175
75°	91	214	104	214	91	97
85°	26	47	27	47	26	28
90°	18	1	18	1	18	11
95°	61	19	61	19	61	80
105°	606	66	606	66	606	586
115°	797	116	797	116	797	781
125°	647	161	647	161	647	584
135°	536	189	536	189	536	416
145°	428	216	428	216	428	272
155°	360	246	360	246	360	168
165°	316	268	316	268	316	90
175°	284	279	284	279	284	28
180°	280	280	280	280	280	



TEST NUMBER: P331743-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2163.0	2164.8	2166.5	2162.5	2162.5	2159.0	2151.5	2145.7	2129.6	2127.2	2127.2
5°	2312.7	2311.3	2314.1	2304.8	2291.8	2288.9	2275.2	2257.1	2238.4	2217.4	2213.1
7.5°	2461.5	2459.4	2453.5	2452.0	2442.0	2420.2	2398.1	2374.5	2343.3	2312.9	2297.5
10°	2536.7	2560.5	2546.0	2520.7	2525.8	2491.9	2473.8	2442.8	2416.8	2371.2	2361.2
12.5°	2610.6	2620.0	2615.4	2601.0	2594.5	2571.0	2546.6	2519.6	2471.6	2430.7	2395.2
15°	2610.3	2624.0	2627.6	2623.3	2627.0	2625.5	2612.4	2590.1	2548.2	2503.4	2464.4
17.5°	2417.6	2427.1	2450.8	2466.8	2487.1	2529.9	2550.9	2559.2	2553.0	2527.4	2499.9
20°	2201.5	2185.6	2252.0	2286.0	2314.9	2387.1	2449.2	2473.0	2511.3	2510.7	2503.4
22.5°	1895.3	1899.0	1962.0	2002.3	2086.7	2158.9	2229.7	2319.4	2393.5	2442.4	2471.1
25°	1392.5	1420.0	1482.8	1537.8	1631.6	1765.9	1888.0	2029.6	2163.2	2268.7	2369.1
27.5°	1045.8	1047.9	1097.7	1148.4	1204.2	1314.3	1467.9	1637.0	1827.5	1984.7	2165.5
30°	895.6	891.3	912.2	943.3	991.0	1076.2	1191.8	1357.9	1547.8	1784.7	1995.6
32.5°	789.3	789.6	805.3	828.3	867.9	925.4	1004.6	1139.4	1319.0	1551.9	1799.2
35°	686.2	685.4	697.0	713.6	730.2	767.0	821.2	892.0	1015.5	1232.9	1485.7
37.5°	612.2	615.4	621.0	631.4	649.8	670.2	702.8	750.3	838.3	966.9	1179.3
40°	570.6	572.0	579.9	588.6	599.5	615.4	642.1	680.4	744.7	847.3	1002.5
42.5°	532.4	534.0	539.5	547.6	556.2	572.0	594.2	627.3	679.4	759.4	887.5
45°	476.7	476.7	481.7	485.4	494.7	509.2	527.3	554.7	590.8	650.1	735.3
47.5°	424.4	424.5	427.9	434.1	440.0	451.3	469.0	491.4	517.7	563.5	636.3
50°	394.4	395.1	397.3	402.3	406.0	416.0	429.8	449.2	476.7	512.1	572.8
52.5°	370.1	369.7	372.4	374.6	377.0	384.3	394.5	411.7	436.2	467.0	517.3
55°	330.8	327.9	332.2	335.8	338.0	340.9	346.7	357.5	378.4	404.4	442.1
57.5°	281.7	280.5	283.6	286.9	293.7	301.5	306.4	313.3	324.1	342.8	380.0
60°	241.2	241.2	247.7	249.9	257.9	268.0	278.1	283.9	294.7	307.0	334.4
62.5°	205.4	206.0	209.1	211.2	215.7	228.1	242.2	255.0	265.2	276.9	295.1
65°	171.9	173.3	173.3	174.7	177.7	180.6	186.3	196.4	214.5	231.1	244.9
67.5°	145.9	146.4	146.8	148.2	148.9	152.1	154.4	158.9	163.1	178.8	195.9
70°	128.6	130.7	130.0	131.5	132.1	133.7	136.5	138.6	145.2	148.8	158.9
72.5°	112.4	114.0	113.9	114.7	116.6	116.9	119.1	121.3	125.5	128.6	134.0
75°	91.0	90.3	91.0	92.5	93.2	93.9	93.9	96.8	99.0	101.8	105.5
77.5°	70.2	71.0	70.8	71.0	71.1	72.4	72.2	73.5	75.7	77.1	78.9
80°	56.4	57.0	56.4	57.0	57.8	58.5	57.8	58.5	60.7	62.1	62.1
82.5°	43.6	43.7	44.2	44.4	44.5	44.7	45.6	45.8	47.4	47.1	47.7
85°	26.0	25.3	25.3	25.3	26.0	26.8	26.0	26.0	26.8	26.8	26.8
87.5°	12.8	13.4	13.4	13.4	13.4	13.3	13.0	13.9	13.4	14.0	13.4
90°	17.7	17.7	17.7	17.7	17.7	17.2	16.1	17.2	17.7	18.3	17.7
92.5°	29.8	30.6	30.3	32.0	32.3	35.7	40.2	46.8	59.0	69.8	68.9
95°	61.3	60.7	62.4	66.6	73.6	85.5	108.0	140.8	184.4	210.8	186.5
97.5°	120.6	125.2	133.0	146.2	171.9	210.8	268.9	328.7	377.3	359.7	270.9
100°	192.5	202.1	217.7	240.8	285.4	350.4	424.1	490.8	502.0	424.6	292.4
102.5°	338.7	351.8	371.2	410.7	459.1	528.1	581.9	597.0	548.5	426.8	284.3
105°	605.8	613.3	636.4	669.8	703.0	720.9	713.8	653.1	541.3	398.3	268.2
107.5°	773.8	783.8	788.4	790.2	786.1	760.1	704.2	612.7	494.1	367.8	260.2
110°	824.5	825.1	820.3	810.0	786.9	742.8	674.0	577.9	464.4	353.2	258.5



TEST NUMBER: P331743-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	823.7	820.8	811.6	794.6	762.4	711.9	638.4	546.0	443.7	343.7	259.0
115°	797.1	792.3	778.4	753.6	715.5	660.1	589.7	506.9	418.2	333.3	261.3
117.5°	749.7	745.6	730.9	704.8	665.9	614.0	550.1	477.4	402.1	328.2	265.1
120°	719.2	713.8	698.2	673.0	635.4	586.4	529.4	462.8	393.5	325.2	267.7
122.5°	687.4	682.9	669.0	644.1	610.4	566.2	512.3	451.2	386.2	323.5	270.7
125°	646.7	642.3	628.9	608.5	577.3	537.0	489.7	434.3	375.7	320.4	275.2
127.5°	611.0	607.5	595.9	576.7	549.6	512.4	467.8	417.6	366.1	318.6	279.8
130°	590.7	586.4	575.7	557.4	531.0	495.6	453.2	406.9	359.6	317.6	283.2
132.5°	569.7	565.8	555.9	537.6	511.7	478.4	439.4	396.6	354.4	317.3	286.7
135°	535.9	533.8	524.1	506.3	483.2	453.2	417.6	382.2	347.2	316.6	290.8
137.5°	502.8	499.5	491.1	475.8	454.8	428.5	400.4	370.7	342.1	316.5	294.5
140°	480.0	476.7	468.7	454.8	437.5	413.9	389.2	363.4	339.2	316.0	296.1
142.5°	457.2	456.6	449.4	436.7	420.4	400.6	379.3	357.3	336.2	316.0	297.5
145°	427.8	426.2	420.8	411.7	398.9	383.2	366.6	348.8	332.2	315.0	298.9
147.5°	403.2	402.3	398.6	391.3	380.7	369.3	356.3	342.3	328.1	313.0	299.3
150°	388.6	388.0	384.8	378.4	370.3	360.7	349.4	337.5	324.7	311.8	298.9
152.5°	376.2	376.1	373.7	368.1	361.7	353.4	343.8	332.8	321.7	309.6	298.0
155°	359.6	360.7	358.5	354.8	348.8	342.9	334.9	326.3	316.0	305.9	296.7
157.5°	345.5	345.5	344.6	341.4	337.2	332.6	325.8	318.7	310.8	302.0	294.3
160°	336.5	336.5	335.9	333.3	329.5	325.7	319.8	313.9	306.9	299.4	292.9
162.5°	327.9	328.3	327.8	325.9	322.2	319.3	314.2	309.2	303.5	297.3	291.6
165°	315.6	316.0	316.0	313.9	311.8	309.6	305.9	302.1	297.7	292.9	289.2
167.5°	304.2	304.8	304.9	303.7	302.7	300.8	298.2	295.3	292.2	289.2	286.7
170°	297.3	298.3	298.9	297.3	296.7	295.7	293.5	291.9	289.2	287.0	285.4
172.5°	291.6	292.3	292.8	292.1	291.5	290.9	289.2	288.0	286.2	284.5	283.7
175°	284.4	285.4	286.0	285.4	285.4	284.9	284.4	283.8	282.2	281.6	281.2
177.5°	279.9	280.8	281.3	281.3	281.3	281.3	280.8	280.8	279.9	279.5	279.9
180°	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5



TEST NUMBER: P331743-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2128.4	2123.7	2119.8	2109.3	2104.1	2092.5	2090.8	2090.3	2075.3	2060.8	2056.7
5°	2201.5	2189.9	2172.7	2152.4	2131.5	2109.8	2095.4	2083.8	2054.8	2027.4	2011.6
7.5°	2275.2	2250.3	2220.4	2182.2	2150.2	2114.4	2087.8	2064.0	2023.0	1983.7	1957.2
10°	2330.1	2289.6	2249.8	2197.2	2156.0	2115.5	2078.0	2045.5	1999.2	1947.3	1910.4
12.5°	2364.2	2319.7	2264.9	2213.4	2160.0	2108.7	2058.3	2016.6	1962.3	1908.6	1864.8
15°	2410.3	2362.6	2296.1	2222.4	2153.8	2086.7	2028.9	1976.9	1906.1	1841.8	1788.4
17.5°	2448.0	2382.4	2311.0	2225.8	2146.4	2061.0	1986.6	1920.1	1841.4	1763.8	1700.8
20°	2460.0	2395.1	2312.7	2227.5	2133.6	2033.3	1953.0	1880.8	1796.3	1711.8	1639.6
22.5°	2452.6	2402.0	2310.5	2208.5	2112.2	2007.2	1916.7	1832.9	1739.1	1652.8	1569.1
25°	2401.6	2384.3	2297.5	2186.3	2076.5	1954.5	1849.7	1758.0	1651.1	1558.7	1467.6
27.5°	2282.6	2320.1	2266.3	2147.9	2025.8	1895.0	1777.3	1672.8	1561.9	1457.8	1367.2
30°	2168.3	2254.2	2231.1	2121.3	1984.8	1856.2	1724.1	1615.0	1496.6	1389.7	1300.1
32.5°	2011.7	2153.7	2176.2	2084.3	1943.2	1802.0	1663.4	1554.9	1431.3	1318.6	1231.3
35°	1762.4	1974.7	2072.2	2013.7	1872.2	1719.8	1576.7	1450.3	1326.1	1214.8	1128.2
37.5°	1464.9	1754.2	1916.7	1920.8	1790.8	1632.4	1476.6	1351.1	1224.0	1114.7	1021.1
40°	1272.0	1585.4	1797.1	1844.0	1734.2	1563.0	1405.5	1277.7	1153.5	1046.6	939.0
42.5°	1098.6	1410.9	1671.0	1752.7	1665.5	1495.4	1337.4	1203.7	1083.0	981.8	871.9
45°	888.4	1161.4	1448.1	1594.0	1545.7	1388.2	1221.3	1094.3	980.8	893.4	788.0
47.5°	749.4	941.9	1219.4	1416.6	1415.8	1272.1	1108.0	986.2	881.0	799.1	713.8
50°	670.2	837.8	1072.6	1296.5	1315.2	1194.7	1038.6	918.0	819.8	733.9	665.2
52.5°	599.2	737.3	948.4	1163.0	1216.4	1112.0	960.6	849.2	753.9	674.9	616.1
55°	506.3	613.2	773.5	974.3	1055.3	981.6	847.3	743.2	665.9	599.5	548.9
57.5°	428.3	508.5	637.2	798.8	893.1	846.7	735.8	651.4	585.2	525.1	485.2
60°	379.2	444.9	554.0	689.1	793.1	760.5	665.9	587.2	530.8	478.9	441.3
62.5°	333.0	389.5	483.0	592.6	687.9	674.5	597.2	531.1	481.7	434.4	402.6
65°	268.0	309.2	382.1	468.1	544.6	551.1	495.5	450.7	406.6	369.1	340.9
67.5°	213.4	240.3	291.6	364.0	421.4	441.9	407.9	373.7	338.7	309.7	285.3
70°	179.8	201.5	239.0	297.6	350.3	371.9	352.5	325.7	295.4	271.5	250.6
72.5°	145.7	166.8	194.5	237.5	282.7	306.1	299.4	280.1	255.5	235.7	215.9
75°	109.8	116.3	135.1	164.0	199.3	219.6	224.6	214.5	195.0	179.8	168.2
77.5°	81.2	85.1	94.1	109.2	132.3	150.3	157.8	156.6	143.2	134.3	123.5
80°	65.0	67.2	71.5	78.0	95.4	113.4	118.5	118.5	109.1	105.5	94.6
82.5°	49.4	51.0	53.6	57.2	65.3	81.1	86.7	87.8	81.9	77.1	68.6
85°	28.2	27.4	28.9	31.1	32.5	36.9	45.5	46.9	45.5	39.7	37.5
87.5°	12.7	12.5	12.0	11.1	11.5	11.9	14.3	16.9	14.9	13.6	12.6
90°	14.5	10.7	8.1	6.4	5.4	4.3	2.2	0.6	2.2	4.3	5.4
92.5°	53.6	36.6	24.4	19.3	15.7	13.3	9.4	6.6	9.4	13.3	15.7
95°	124.1	77.4	52.7	39.8	31.2	26.3	20.9	18.9	20.9	26.3	31.2
97.5°	167.3	102.2	71.1	56.5	46.6	39.2	33.6	30.6	33.6	39.2	46.6
100°	176.3	110.7	82.3	67.2	56.5	47.9	43.0	41.4	43.0	47.9	56.5
102.5°	176.7	118.5	92.1	77.1	65.9	57.3	52.5	51.3	52.5	57.3	65.9
105°	179.6	131.7	106.4	91.3	79.6	71.4	67.8	65.6	67.8	71.4	79.6
107.5°	186.9	145.2	120.7	105.6	93.9	86.4	82.8	81.1	82.8	86.4	93.9
110°	192.9	154.3	130.6	115.0	103.8	96.8	93.5	91.3	93.5	96.8	103.8



TEST NUMBER: P331743-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	199.4	162.9	140.1	124.0	113.2	106.6	103.0	100.9	103.0	106.6	113.2
115°	209.1	176.3	153.2	138.6	127.9	121.5	118.3	115.6	118.3	121.5	127.9
117.5°	219.4	188.7	167.3	152.2	141.9	136.2	133.0	130.8	133.0	136.2	141.9
120°	226.3	197.3	176.3	161.3	150.5	145.6	142.4	140.3	142.4	145.6	150.5
122.5°	232.3	205.5	185.8	170.3	159.6	154.3	151.1	149.3	151.1	154.3	159.6
125°	241.9	217.7	198.3	183.3	172.6	166.1	162.9	161.3	162.9	166.1	172.6
127.5°	250.8	229.1	210.3	194.8	184.5	177.4	172.9	170.7	172.9	177.4	184.5
130°	256.4	236.0	217.2	202.1	191.3	183.8	178.4	176.3	178.4	183.8	191.3
132.5°	262.0	242.0	224.0	209.0	197.8	189.8	184.1	181.4	184.1	189.8	197.8
135°	269.3	250.5	233.3	218.2	205.9	197.8	191.3	189.2	191.3	197.8	205.9
137.5°	274.8	257.4	240.3	226.4	214.1	205.6	199.1	196.5	199.1	205.6	214.1
140°	277.9	261.3	245.2	231.1	219.3	210.8	204.2	202.1	204.2	210.8	219.3
142.5°	280.5	264.3	248.5	235.4	224.0	215.5	209.4	207.7	209.4	215.5	224.0
145°	283.8	268.7	254.2	242.4	231.7	223.6	218.2	216.1	218.2	223.6	231.7
147.5°	285.7	272.4	258.7	248.3	239.3	231.9	226.7	225.1	226.7	231.9	239.3
150°	286.5	274.1	261.7	252.1	244.0	237.0	232.7	231.1	232.7	237.0	244.0
152.5°	286.9	275.9	264.8	256.0	248.4	242.2	237.9	237.1	237.9	242.2	248.4
155°	287.6	278.4	269.3	261.3	255.3	249.4	246.2	245.6	246.2	249.4	255.3
157.5°	287.6	280.2	272.5	265.8	261.0	255.9	253.3	252.7	253.3	255.9	261.0
160°	287.6	281.2	274.7	268.7	264.5	260.1	258.0	257.5	258.0	260.1	264.5
162.5°	287.1	281.5	276.0	271.4	267.5	264.0	261.8	262.2	261.8	264.0	267.5
165°	286.0	282.2	277.4	274.1	271.5	268.2	267.1	267.7	267.1	268.2	271.5
167.5°	285.2	282.1	278.5	276.5	274.6	272.5	271.5	272.2	271.5	272.5	274.6
170°	284.4	281.6	279.0	277.4	276.3	274.7	274.1	275.2	274.1	274.7	276.3
172.5°	283.0	281.3	279.4	278.2	277.6	276.0	276.3	276.9	276.3	276.0	277.6
175°	281.6	280.6	279.5	279.0	279.0	277.9	278.4	279.0	278.4	277.9	279.0
177.5°	280.8	279.9	279.5	279.5	279.5	278.6	279.1	279.9	279.1	278.6	279.5
180°	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5



TEST NUMBER: P331743-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2049.3	2045.2	2037.7	2026.1	2019.2	2007.1	1998.9	2003.6	2004.8	2003.6	2002.4
5°	1994.2	1979.1	1958.1	1937.9	1919.1	1898.8	1887.3	1882.3	1872.2	1866.3	1863.5
7.5°	1927.6	1901.5	1871.9	1836.6	1806.7	1775.4	1759.3	1751.3	1730.7	1719.5	1709.6
10°	1877.9	1836.7	1807.1	1761.0	1732.8	1691.6	1663.4	1664.2	1636.0	1620.0	1608.5
12.5°	1823.1	1777.8	1728.5	1687.0	1647.8	1614.8	1580.7	1567.1	1537.2	1521.8	1490.6
15°	1732.0	1679.3	1627.3	1570.9	1531.3	1480.0	1430.9	1370.9	1322.5	1280.6	1269.0
17.5°	1632.7	1567.4	1515.2	1449.1	1381.0	1294.8	1237.8	1203.1	1173.8	1151.8	1135.3
20°	1564.4	1498.0	1442.4	1342.7	1250.9	1192.5	1150.6	1123.9	1093.5	1069.7	1056.7
22.5°	1492.8	1423.4	1347.6	1236.4	1164.9	1117.9	1080.6	1049.9	1029.4	1010.8	998.9
25°	1391.1	1315.2	1190.3	1113.7	1055.9	1006.8	980.8	962.1	940.4	915.1	903.6
27.5°	1283.6	1163.0	1073.3	1016.3	961.2	929.3	905.9	877.9	858.5	847.1	835.1
30°	1203.3	1082.7	1012.7	950.6	911.5	876.1	848.7	832.8	814.0	794.5	786.6
32.5°	1113.7	1017.4	950.3	898.5	858.9	828.8	807.1	781.4	767.8	755.8	739.1
35°	1002.5	929.5	868.2	826.3	788.7	764.2	738.9	723.7	699.2	689.1	682.6
37.5°	908.3	845.1	799.3	755.1	725.3	698.1	682.7	658.6	647.9	633.9	620.2
40°	855.2	793.1	749.0	712.8	679.7	659.4	639.9	620.5	604.5	598.0	581.5
42.5°	800.9	750.3	706.2	666.7	644.4	623.0	598.3	584.0	567.6	557.0	546.8
45°	725.9	681.1	643.6	611.1	586.4	564.1	548.2	524.3	515.0	494.1	485.4
47.5°	660.1	618.4	582.6	551.7	527.7	513.1	489.8	471.2	456.2	443.4	432.3
50°	613.2	578.5	543.8	516.4	494.7	473.8	450.0	440.5	417.5	410.9	404.4
52.5°	570.4	537.5	505.8	478.9	457.2	436.9	415.8	403.6	388.0	381.5	376.7
55°	510.7	478.9	448.6	424.7	403.0	382.1	369.1	353.9	346.7	341.7	335.8
57.5°	450.5	422.0	398.7	374.6	352.8	336.1	321.1	312.0	304.5	297.8	291.0
60°	412.5	384.9	364.0	341.7	319.2	305.5	294.0	283.1	274.5	264.4	261.5
62.5°	371.9	348.0	328.8	307.0	287.5	274.9	263.9	253.6	243.3	228.6	224.5
65°	316.3	297.6	277.4	259.3	242.0	229.7	213.8	202.3	197.9	196.4	195.8
67.5°	266.1	248.4	231.0	212.4	196.7	185.3	177.3	175.5	172.5	171.6	169.6
70°	232.6	215.9	198.6	181.3	166.2	164.0	161.1	158.2	154.6	153.2	151.7
72.5°	202.6	185.3	168.0	154.1	147.6	144.9	142.0	139.1	136.7	135.3	134.3
75°	155.3	139.4	127.8	122.8	119.1	117.0	112.6	110.5	109.1	106.9	106.1
77.5°	111.8	102.8	97.6	94.3	90.6	88.2	85.8	83.6	82.1	81.6	80.5
80°	85.2	80.9	77.3	73.0	71.5	68.6	67.9	65.7	66.4	64.3	64.3
82.5°	66.2	60.7	57.7	55.6	54.2	51.8	51.2	50.1	50.2	48.6	48.6
85°	33.9	32.5	31.1	29.6	29.6	27.4	28.2	27.4	27.4	26.0	25.3
87.5°	12.3	12.0	11.4	12.2	12.8	12.3	12.3	11.5	11.3	11.5	11.0
90°	6.4	8.1	10.7	14.5	17.7	18.3	17.7	17.2	16.1	17.2	17.7
92.5°	19.3	24.4	36.6	53.6	68.9	69.8	59.0	46.8	40.2	35.7	32.3
95°	39.8	52.7	77.4	124.1	186.5	210.8	184.4	140.8	108.0	85.5	73.6
97.5°	56.5	71.1	102.2	167.3	270.9	359.7	377.3	328.7	268.9	210.8	171.9
100°	67.2	82.3	110.7	176.3	292.4	424.6	502.0	490.8	424.1	350.4	285.4
102.5°	77.1	92.1	118.5	176.7	284.3	426.8	548.5	597.0	581.9	528.1	459.1
105°	91.3	106.4	131.7	179.6	268.2	398.3	541.3	653.1	713.8	720.9	703.0
107.5°	105.6	120.7	145.2	186.9	260.2	367.8	494.1	612.7	704.2	760.1	786.1
110°	115.0	130.6	154.3	192.9	258.5	353.2	464.4	577.9	674.0	742.8	786.9



TEST NUMBER: P331743-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	124.0	140.1	162.9	199.4	259.0	343.7	443.7	546.0	638.4	711.9	762.4
115°	138.6	153.2	176.3	209.1	261.3	333.3	418.2	506.9	589.7	660.1	715.5
117.5°	152.2	167.3	188.7	219.4	265.1	328.2	402.1	477.4	550.1	614.0	665.9
120°	161.3	176.3	197.3	226.3	267.7	325.2	393.5	462.8	529.4	586.4	635.4
122.5°	170.3	185.8	205.5	232.3	270.7	323.5	386.2	451.2	512.3	566.2	610.4
125°	183.3	198.3	217.7	241.9	275.2	320.4	375.7	434.3	489.7	537.0	577.3
127.5°	194.8	210.3	229.1	250.8	279.8	318.6	366.1	417.6	467.8	512.4	549.6
130°	202.1	217.2	236.0	256.4	283.2	317.6	359.6	406.9	453.2	495.6	531.0
132.5°	209.0	224.0	242.0	262.0	286.7	317.3	354.4	396.6	439.4	478.4	511.7
135°	218.2	233.3	250.5	269.3	290.8	316.6	347.2	382.2	417.6	453.2	483.2
137.5°	226.4	240.3	257.4	274.8	294.5	316.5	342.1	370.7	400.4	428.5	454.8
140°	231.1	245.2	261.3	277.9	296.1	316.0	339.2	363.4	389.2	413.9	437.5
142.5°	235.4	248.5	264.3	280.5	297.5	316.0	336.2	357.3	379.3	400.6	420.4
145°	242.4	254.2	268.7	283.8	298.9	315.0	332.2	348.8	366.6	383.2	398.9
147.5°	248.3	258.7	272.4	285.7	299.3	313.0	328.1	342.3	356.3	369.3	380.7
150°	252.1	261.7	274.1	286.5	298.9	311.8	324.7	337.5	349.4	360.7	370.3
152.5°	256.0	264.8	275.9	286.9	298.0	309.6	321.7	332.8	343.8	353.4	361.7
155°	261.3	269.3	278.4	287.6	296.7	305.9	316.0	326.3	334.9	342.9	348.8
157.5°	265.8	272.5	280.2	287.6	294.3	302.0	310.8	318.7	325.8	332.6	337.2
160°	268.7	274.7	281.2	287.6	292.9	299.4	306.9	313.9	319.8	325.7	329.5
162.5°	271.4	276.0	281.5	287.1	291.6	297.3	303.5	309.2	314.2	319.3	322.2
165°	274.1	277.4	282.2	286.0	289.2	292.9	297.7	302.1	305.9	309.6	311.8
167.5°	276.5	278.5	282.1	285.2	286.7	289.2	292.2	295.3	298.2	300.8	302.7
170°	277.4	279.0	281.6	284.4	285.4	287.0	289.2	291.9	293.5	295.7	296.7
172.5°	278.2	279.4	281.3	283.0	283.7	284.5	286.2	288.0	289.2	290.9	291.5
175°	279.0	279.5	280.6	281.6	281.2	281.6	282.2	283.8	284.4	284.9	285.4
177.5°	279.5	279.5	279.9	280.8	279.9	279.5	279.9	280.8	280.8	281.3	281.3
180°	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5



TEST NUMBER: P331743-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	1996.1	1997.2	1995.6	1996.7	1995.6	1997.2	1996.1	2002.4	2003.6	2004.8	2003.6
5°	1859.8	1851.2	1849.7	1847.6	1849.7	1851.2	1859.8	1863.5	1866.3	1872.2	1882.3
7.5°	1697.2	1695.9	1692.3	1687.2	1692.3	1695.9	1697.2	1709.6	1719.5	1730.7	1751.3
10°	1592.6	1589.0	1588.3	1583.2	1588.3	1589.0	1592.6	1608.5	1620.0	1636.0	1664.2
12.5°	1470.1	1446.9	1444.4	1431.8	1444.4	1446.9	1470.1	1490.6	1521.8	1537.2	1567.1
15°	1251.7	1247.4	1232.9	1223.5	1232.9	1247.4	1251.7	1269.0	1280.6	1322.5	1370.9
17.5°	1126.9	1112.8	1108.2	1106.3	1108.2	1112.8	1126.9	1135.3	1151.8	1173.8	1203.1
20°	1046.6	1033.6	1031.4	1030.0	1031.4	1033.6	1046.6	1056.7	1069.7	1093.5	1123.9
22.5°	991.1	977.5	971.9	967.5	971.9	977.5	991.1	998.9	1010.8	1029.4	1049.9
25°	896.4	891.3	888.4	886.9	888.4	891.3	896.4	903.6	915.1	940.4	962.1
27.5°	822.3	811.2	809.0	805.2	809.0	811.2	822.3	835.1	847.1	858.5	877.9
30°	780.0	776.5	771.4	767.0	771.4	776.5	780.0	786.6	794.5	814.0	832.8
32.5°	730.4	727.4	722.8	720.9	722.8	727.4	730.4	739.1	755.8	767.8	781.4
35°	675.3	665.2	660.9	654.4	660.9	665.2	675.3	682.6	689.1	699.2	723.7
37.5°	617.1	611.8	605.7	607.8	605.7	611.8	617.1	620.2	633.9	647.9	658.6
40°	572.0	568.4	567.0	566.3	567.0	568.4	572.0	581.5	598.0	604.5	620.5
42.5°	536.2	526.2	522.5	522.4	522.5	526.2	536.2	546.8	557.0	567.6	584.0
45°	481.7	472.4	465.9	466.6	465.9	472.4	481.7	485.4	494.1	515.0	524.3
47.5°	426.0	425.7	421.7	422.9	421.7	425.7	426.0	432.3	443.4	456.2	471.2
50°	399.4	395.1	392.2	392.9	392.2	395.1	399.4	404.4	410.9	417.5	440.5
52.5°	374.0	370.2	368.0	371.0	368.0	370.2	374.0	376.7	381.5	388.0	403.6
55°	332.2	327.9	327.2	326.5	327.2	327.9	332.2	335.8	341.7	346.7	353.9
57.5°	285.6	282.7	278.3	276.4	278.3	282.7	285.6	291.0	297.8	304.5	312.0
60°	252.0	246.3	239.0	238.4	239.0	246.3	252.0	261.5	264.4	274.5	283.1
62.5°	221.4	220.3	218.9	218.7	218.9	220.3	221.4	224.5	228.6	243.3	253.6
65°	194.3	193.6	194.3	195.0	194.3	193.6	194.3	195.8	196.4	197.9	202.3
67.5°	169.3	168.0	166.7	167.3	166.7	168.0	169.3	169.6	171.6	172.5	175.5
70°	150.2	149.5	148.8	148.8	148.8	149.5	150.2	151.7	153.2	154.6	158.2
72.5°	131.8	131.6	130.9	130.3	130.9	131.6	131.8	134.3	135.3	136.7	139.1
75°	105.5	104.0	104.0	104.0	104.0	104.0	105.5	106.1	106.9	109.1	110.5
77.5°	80.3	79.6	78.9	78.3	78.9	79.6	80.3	80.5	81.6	82.1	83.6
80°	63.5	62.9	62.1	62.1	62.1	62.9	63.5	64.3	64.3	66.4	65.7
82.5°	48.5	47.8	47.7	47.1	47.7	47.8	48.5	48.6	48.6	50.2	50.1
85°	26.0	26.8	26.0	27.4	26.0	26.8	26.0	25.3	26.0	27.4	27.4
87.5°	11.0	10.5	11.0	10.5	11.0	10.5	11.0	11.0	11.5	11.3	11.5
90°	17.7	17.7	17.7	17.7	17.7	17.7	17.7	17.7	17.2	16.1	17.2
92.5°	32.0	30.3	30.6	29.8	30.6	30.3	32.0	32.3	35.7	40.2	46.8
95°	66.6	62.4	60.7	61.3	60.7	62.4	66.6	73.6	85.5	108.0	140.8
97.5°	146.2	133.0	125.2	120.6	125.2	133.0	146.2	171.9	210.8	268.9	328.7
100°	240.8	217.7	202.1	192.5	202.1	217.7	240.8	285.4	350.4	424.1	490.8
102.5°	410.7	371.2	351.8	338.7	351.8	371.2	410.7	459.1	528.1	581.9	597.0
105°	669.8	636.4	613.3	605.8	613.3	636.4	669.8	703.0	720.9	713.8	653.1
107.5°	790.2	788.4	783.8	773.8	783.8	788.4	790.2	786.1	760.1	704.2	612.7
110°	810.0	820.3	825.1	824.5	825.1	820.3	810.0	786.9	742.8	674.0	577.9



TEST NUMBER: P331743-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	794.6	811.6	820.8	823.7	820.8	811.6	794.6	762.4	711.9	638.4	546.0
115°	753.6	778.4	792.3	797.1	792.3	778.4	753.6	715.5	660.1	589.7	506.9
117.5°	704.8	730.9	745.6	749.7	745.6	730.9	704.8	665.9	614.0	550.1	477.4
120°	673.0	698.2	713.8	719.2	713.8	698.2	673.0	635.4	586.4	529.4	462.8
122.5°	644.1	669.0	682.9	687.4	682.9	669.0	644.1	610.4	566.2	512.3	451.2
125°	608.5	628.9	642.3	646.7	642.3	628.9	608.5	577.3	537.0	489.7	434.3
127.5°	576.7	595.9	607.5	611.0	607.5	595.9	576.7	549.6	512.4	467.8	417.6
130°	557.4	575.7	586.4	590.7	586.4	575.7	557.4	531.0	495.6	453.2	406.9
132.5°	537.6	555.9	565.8	569.7	565.8	555.9	537.6	511.7	478.4	439.4	396.6
135°	506.3	524.1	533.8	535.9	533.8	524.1	506.3	483.2	453.2	417.6	382.2
137.5°	475.8	491.1	499.5	502.8	499.5	491.1	475.8	454.8	428.5	400.4	370.7
140°	454.8	468.7	476.7	480.0	476.7	468.7	454.8	437.5	413.9	389.2	363.4
142.5°	436.7	449.4	456.6	457.2	456.6	449.4	436.7	420.4	400.6	379.3	357.3
145°	411.7	420.8	426.2	427.8	426.2	420.8	411.7	398.9	383.2	366.6	348.8
147.5°	391.3	398.6	402.3	403.2	402.3	398.6	391.3	380.7	369.3	356.3	342.3
150°	378.4	384.8	388.0	388.6	388.0	384.8	378.4	370.3	360.7	349.4	337.5
152.5°	368.1	373.7	376.1	376.2	376.1	373.7	368.1	361.7	353.4	343.8	332.8
155°	354.8	358.5	360.7	359.6	360.7	358.5	354.8	348.8	342.9	334.9	326.3
157.5°	341.4	344.6	345.5	345.5	345.5	344.6	341.4	337.2	332.6	325.8	318.7
160°	333.3	335.9	336.5	336.5	336.5	335.9	333.3	329.5	325.7	319.8	313.9
162.5°	325.9	327.8	328.3	327.9	328.3	327.8	325.9	322.2	319.3	314.2	309.2
165°	313.9	316.0	316.0	315.6	316.0	316.0	313.9	311.8	309.6	305.9	302.1
167.5°	303.7	304.9	304.8	304.2	304.8	304.9	303.7	302.7	300.8	298.2	295.3
170°	297.3	298.9	298.3	297.3	298.3	298.9	297.3	296.7	295.7	293.5	291.9
172.5°	292.1	292.8	292.3	291.6	292.3	292.8	292.1	291.5	290.9	289.2	288.0
175°	285.4	286.0	285.4	284.4	285.4	286.0	285.4	285.4	284.9	284.4	283.8
177.5°	281.3	281.3	280.8	279.9	280.8	281.3	281.3	281.3	281.3	280.8	280.8
180°	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5



TEST NUMBER: P331743-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	1998.9	2007.1	2019.2	2026.1	2037.7	2045.2	2049.3	2056.7	2060.8	2075.3	2090.3
5°	1887.3	1898.8	1919.1	1937.9	1958.1	1979.1	1994.2	2011.6	2027.4	2054.8	2083.8
7.5°	1759.3	1775.4	1806.7	1836.6	1871.9	1901.5	1927.6	1957.2	1983.7	2023.0	2064.0
10°	1663.4	1691.6	1732.8	1761.0	1807.1	1836.7	1877.9	1910.4	1947.3	1999.2	2045.5
12.5°	1580.7	1614.8	1647.8	1687.0	1728.5	1777.8	1823.1	1864.8	1908.6	1962.3	2016.6
15°	1430.9	1480.0	1531.3	1570.9	1627.3	1679.3	1732.0	1788.4	1841.8	1906.1	1976.9
17.5°	1237.8	1294.8	1381.0	1449.1	1515.2	1567.4	1632.7	1700.8	1763.8	1841.4	1920.1
20°	1150.6	1192.5	1250.9	1342.7	1442.4	1498.0	1564.4	1639.6	1711.8	1796.3	1880.8
22.5°	1080.6	1117.9	1164.9	1236.4	1347.6	1423.4	1492.8	1569.1	1652.8	1739.1	1832.9
25°	980.8	1006.8	1055.9	1113.7	1190.3	1315.2	1391.1	1467.6	1558.7	1651.1	1758.0
27.5°	905.9	929.3	961.2	1016.3	1073.3	1163.0	1283.6	1367.2	1457.8	1561.9	1672.8
30°	848.7	876.1	911.5	950.6	1012.7	1082.7	1203.3	1300.1	1389.7	1496.6	1615.0
32.5°	807.1	828.8	858.9	898.5	950.3	1017.4	1113.7	1231.3	1318.6	1431.3	1554.9
35°	738.9	764.2	788.7	826.3	868.2	929.5	1002.5	1128.2	1214.8	1326.1	1450.3
37.5°	682.7	698.1	725.3	755.1	799.3	845.1	908.3	1021.1	1114.7	1224.0	1351.1
40°	639.9	659.4	679.7	712.8	749.0	793.1	855.2	939.0	1046.6	1153.5	1277.7
42.5°	598.3	623.0	644.4	666.7	706.2	750.3	800.9	871.9	981.8	1083.0	1203.7
45°	548.2	564.1	586.4	611.1	643.6	681.1	725.9	788.0	893.4	980.8	1094.3
47.5°	489.8	513.1	527.7	551.7	582.6	618.4	660.1	713.8	799.1	881.0	986.2
50°	450.0	473.8	494.7	516.4	543.8	578.5	613.2	665.2	733.9	819.8	918.0
52.5°	415.8	436.9	457.2	478.9	505.8	537.5	570.4	616.1	674.9	753.9	849.2
55°	369.1	382.1	403.0	424.7	448.6	478.9	510.7	548.9	599.5	665.9	743.2
57.5°	321.1	336.1	352.8	374.6	398.7	422.0	450.5	485.2	525.1	585.2	651.4
60°	294.0	305.5	319.2	341.7	364.0	384.9	412.5	441.3	478.9	530.8	587.2
62.5°	263.9	274.9	287.5	307.0	328.8	348.0	371.9	402.6	434.4	481.7	531.1
65°	213.8	229.7	242.0	259.3	277.4	297.6	316.3	340.9	369.1	406.6	450.7
67.5°	177.3	185.3	196.7	212.4	231.0	248.4	266.1	285.3	309.7	338.7	373.7
70°	161.1	164.0	166.2	181.3	198.6	215.9	232.6	250.6	271.5	295.4	325.7
72.5°	142.0	144.9	147.6	154.1	168.0	185.3	202.6	215.9	235.7	255.5	280.1
75°	112.6	117.0	119.1	122.8	127.8	139.4	155.3	168.2	179.8	195.0	214.5
77.5°	85.8	88.2	90.6	94.3	97.6	102.8	111.8	123.5	134.3	143.2	156.6
80°	67.9	68.6	71.5	73.0	77.3	80.9	85.2	94.6	105.5	109.1	118.5
82.5°	51.2	51.8	54.2	55.6	57.7	60.7	66.2	68.6	77.1	81.9	87.8
85°	28.2	27.4	29.6	29.6	31.1	32.5	33.9	37.5	39.7	45.5	46.9
87.5°	12.3	12.3	12.8	12.2	11.4	12.0	12.3	12.6	13.6	14.9	16.9
90°	17.7	18.3	17.7	14.5	10.7	8.1	6.4	5.4	4.3	2.2	0.6
92.5°	59.0	69.8	68.9	53.6	36.6	24.4	19.3	15.7	13.3	9.4	6.6
95°	184.4	210.8	186.5	124.1	77.4	52.7	39.8	31.2	26.3	20.9	18.9
97.5°	377.3	359.7	270.9	167.3	102.2	71.1	56.5	46.6	39.2	33.6	30.6
100°	502.0	424.6	292.4	176.3	110.7	82.3	67.2	56.5	47.9	43.0	41.4
102.5°	548.5	426.8	284.3	176.7	118.5	92.1	77.1	65.9	57.3	52.5	51.3
105°	541.3	398.3	268.2	179.6	131.7	106.4	91.3	79.6	71.4	67.8	65.6
107.5°	494.1	367.8	260.2	186.9	145.2	120.7	105.6	93.9	86.4	82.8	81.1
110°	464.4	353.2	258.5	192.9	154.3	130.6	115.0	103.8	96.8	93.5	91.3



TEST NUMBER: P331743-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	443.7	343.7	259.0	199.4	162.9	140.1	124.0	113.2	106.6	103.0	100.9
115°	418.2	333.3	261.3	209.1	176.3	153.2	138.6	127.9	121.5	118.3	115.6
117.5°	402.1	328.2	265.1	219.4	188.7	167.3	152.2	141.9	136.2	133.0	130.8
120°	393.5	325.2	267.7	226.3	197.3	176.3	161.3	150.5	145.6	142.4	140.3
122.5°	386.2	323.5	270.7	232.3	205.5	185.8	170.3	159.6	154.3	151.1	149.3
125°	375.7	320.4	275.2	241.9	217.7	198.3	183.3	172.6	166.1	162.9	161.3
127.5°	366.1	318.6	279.8	250.8	229.1	210.3	194.8	184.5	177.4	172.9	170.7
130°	359.6	317.6	283.2	256.4	236.0	217.2	202.1	191.3	183.8	178.4	176.3
132.5°	354.4	317.3	286.7	262.0	242.0	224.0	209.0	197.8	189.8	184.1	181.4
135°	347.2	316.6	290.8	269.3	250.5	233.3	218.2	205.9	197.8	191.3	189.2
137.5°	342.1	316.5	294.5	274.8	257.4	240.3	226.4	214.1	205.6	199.1	196.5
140°	339.2	316.0	296.1	277.9	261.3	245.2	231.1	219.3	210.8	204.2	202.1
142.5°	336.2	316.0	297.5	280.5	264.3	248.5	235.4	224.0	215.5	209.4	207.7
145°	332.2	315.0	298.9	283.8	268.7	254.2	242.4	231.7	223.6	218.2	216.1
147.5°	328.1	313.0	299.3	285.7	272.4	258.7	248.3	239.3	231.9	226.7	225.1
150°	324.7	311.8	298.9	286.5	274.1	261.7	252.1	244.0	237.0	232.7	231.1
152.5°	321.7	309.6	298.0	286.9	275.9	264.8	256.0	248.4	242.2	237.9	237.1
155°	316.0	305.9	296.7	287.6	278.4	269.3	261.3	255.3	249.4	246.2	245.6
157.5°	310.8	302.0	294.3	287.6	280.2	272.5	265.8	261.0	255.9	253.3	252.7
160°	306.9	299.4	292.9	287.6	281.2	274.7	268.7	264.5	260.1	258.0	257.5
162.5°	303.5	297.3	291.6	287.1	281.5	276.0	271.4	267.5	264.0	261.8	262.2
165°	297.7	292.9	289.2	286.0	282.2	277.4	274.1	271.5	268.2	267.1	267.7
167.5°	292.2	289.2	286.7	285.2	282.1	278.5	276.5	274.6	272.5	271.5	272.2
170°	289.2	287.0	285.4	284.4	281.6	279.0	277.4	276.3	274.7	274.1	275.2
172.5°	286.2	284.5	283.7	283.0	281.3	279.4	278.2	277.6	276.0	276.3	276.9
175°	282.2	281.6	281.2	281.6	280.6	279.5	279.0	279.0	277.9	278.4	279.0
177.5°	279.9	279.5	279.9	280.8	279.9	279.5	279.5	279.5	278.6	279.1	279.9
180°	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5



TEST NUMBER: P331743-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2090.8	2092.5	2104.1	2109.3	2119.8	2123.7	2128.4	2127.2	2127.2	2129.6	2145.7
5°	2095.4	2109.8	2131.5	2152.4	2172.7	2189.9	2201.5	2213.1	2217.4	2238.4	2257.1
7.5°	2087.8	2114.4	2150.2	2182.2	2220.4	2250.3	2275.2	2297.5	2312.9	2343.3	2374.5
10°	2078.0	2115.5	2156.0	2197.2	2249.8	2289.6	2330.1	2361.2	2371.2	2416.8	2442.8
12.5°	2058.3	2108.7	2160.0	2213.4	2264.9	2319.7	2364.2	2395.2	2430.7	2471.6	2519.6
15°	2028.9	2086.7	2153.8	2222.4	2296.1	2362.6	2410.3	2464.4	2503.4	2548.2	2590.1
17.5°	1986.6	2061.0	2146.4	2225.8	2311.0	2382.4	2448.0	2499.9	2527.4	2553.0	2559.2
20°	1953.0	2033.3	2133.6	2227.5	2312.7	2395.1	2460.0	2503.4	2510.7	2511.3	2473.0
22.5°	1916.7	2007.2	2112.2	2208.5	2310.5	2402.0	2452.6	2471.1	2442.4	2393.5	2319.4
25°	1849.7	1954.5	2076.5	2186.3	2297.5	2384.3	2401.6	2369.1	2268.7	2163.2	2029.6
27.5°	1777.3	1895.0	2025.8	2147.9	2266.3	2320.1	2282.6	2165.5	1984.7	1827.5	1637.0
30°	1724.1	1856.2	1984.8	2121.3	2231.1	2254.2	2168.3	1995.6	1784.7	1547.8	1357.9
32.5°	1663.4	1802.0	1943.2	2084.3	2176.2	2153.7	2011.7	1799.2	1551.9	1319.0	1139.4
35°	1576.7	1719.8	1872.2	2013.7	2072.2	1974.7	1762.4	1485.7	1232.9	1015.5	892.0
37.5°	1476.6	1632.4	1790.8	1920.8	1916.7	1754.2	1464.9	1179.3	966.9	838.3	750.3
40°	1405.5	1563.0	1734.2	1844.0	1797.1	1585.4	1272.0	1002.5	847.3	744.7	680.4
42.5°	1337.4	1495.4	1665.5	1752.7	1671.0	1410.9	1098.6	887.5	759.4	679.4	627.3
45°	1221.3	1388.2	1545.7	1594.0	1448.1	1161.4	888.4	735.3	650.1	590.8	554.7
47.5°	1108.0	1272.1	1415.8	1416.6	1219.4	941.9	749.4	636.3	563.5	517.7	491.4
50°	1038.6	1194.7	1315.2	1296.5	1072.6	837.8	670.2	572.8	512.1	476.7	449.2
52.5°	960.6	1112.0	1216.4	1163.0	948.4	737.3	599.2	517.3	467.0	436.2	411.7
55°	847.3	981.6	1055.3	974.3	773.5	613.2	506.3	442.1	404.4	378.4	357.5
57.5°	735.8	846.7	893.1	798.8	637.2	508.5	428.3	380.0	342.8	324.1	313.3
60°	665.9	760.5	793.1	689.1	554.0	444.9	379.2	334.4	307.0	294.7	283.9
62.5°	597.2	674.5	687.9	592.6	483.0	389.5	333.0	295.1	276.9	265.2	255.0
65°	495.5	551.1	544.6	468.1	382.1	309.2	268.0	244.9	231.1	214.5	196.4
67.5°	407.9	441.9	421.4	364.0	291.6	240.3	213.4	195.9	178.8	163.1	158.9
70°	352.5	371.9	350.3	297.6	239.0	201.5	179.8	158.9	148.8	145.2	138.6
72.5°	299.4	306.1	282.7	237.5	194.5	166.8	145.7	134.0	128.6	125.5	121.3
75°	224.6	219.6	199.3	164.0	135.1	116.3	109.8	105.5	101.8	99.0	96.8
77.5°	157.8	150.3	132.3	109.2	94.1	85.1	81.2	78.9	77.1	75.7	73.5
80°	118.5	113.4	95.4	78.0	71.5	67.2	65.0	62.1	62.1	60.7	58.5
82.5°	86.7	81.1	65.3	57.2	53.6	51.0	49.4	47.7	47.1	47.4	45.8
85°	45.5	36.9	32.5	31.1	28.9	27.4	28.2	26.8	26.8	26.8	26.0
87.5°	14.3	11.9	11.5	11.1	12.0	12.5	12.7	13.4	14.0	13.4	13.9
90°	2.2	4.3	5.4	6.4	8.1	10.7	14.5	17.7	18.3	17.7	17.2
92.5°	9.4	13.3	15.7	19.3	24.4	36.6	53.6	68.9	69.8	59.0	46.8
95°	20.9	26.3	31.2	39.8	52.7	77.4	124.1	186.5	210.8	184.4	140.8
97.5°	33.6	39.2	46.6	56.5	71.1	102.2	167.3	270.9	359.7	377.3	328.7
100°	43.0	47.9	56.5	67.2	82.3	110.7	176.3	292.4	424.6	502.0	490.8
102.5°	52.5	57.3	65.9	77.1	92.1	118.5	176.7	284.3	426.8	548.5	597.0
105°	67.8	71.4	79.6	91.3	106.4	131.7	179.6	268.2	398.3	541.3	653.1
107.5°	82.8	86.4	93.9	105.6	120.7	145.2	186.9	260.2	367.8	494.1	612.7
110°	93.5	96.8	103.8	115.0	130.6	154.3	192.9	258.5	353.2	464.4	577.9



TEST NUMBER: P331743-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	103.0	106.6	113.2	124.0	140.1	162.9	199.4	259.0	343.7	443.7	546.0
115°	118.3	121.5	127.9	138.6	153.2	176.3	209.1	261.3	333.3	418.2	506.9
117.5°	133.0	136.2	141.9	152.2	167.3	188.7	219.4	265.1	328.2	402.1	477.4
120°	142.4	145.6	150.5	161.3	176.3	197.3	226.3	267.7	325.2	393.5	462.8
122.5°	151.1	154.3	159.6	170.3	185.8	205.5	232.3	270.7	323.5	386.2	451.2
125°	162.9	166.1	172.6	183.3	198.3	217.7	241.9	275.2	320.4	375.7	434.3
127.5°	172.9	177.4	184.5	194.8	210.3	229.1	250.8	279.8	318.6	366.1	417.6
130°	178.4	183.8	191.3	202.1	217.2	236.0	256.4	283.2	317.6	359.6	406.9
132.5°	184.1	189.8	197.8	209.0	224.0	242.0	262.0	286.7	317.3	354.4	396.6
135°	191.3	197.8	205.9	218.2	233.3	250.5	269.3	290.8	316.6	347.2	382.2
137.5°	199.1	205.6	214.1	226.4	240.3	257.4	274.8	294.5	316.5	342.1	370.7
140°	204.2	210.8	219.3	231.1	245.2	261.3	277.9	296.1	316.0	339.2	363.4
142.5°	209.4	215.5	224.0	235.4	248.5	264.3	280.5	297.5	316.0	336.2	357.3
145°	218.2	223.6	231.7	242.4	254.2	268.7	283.8	298.9	315.0	332.2	348.8
147.5°	226.7	231.9	239.3	248.3	258.7	272.4	285.7	299.3	313.0	328.1	342.3
150°	232.7	237.0	244.0	252.1	261.7	274.1	286.5	298.9	311.8	324.7	337.5
152.5°	237.9	242.2	248.4	256.0	264.8	275.9	286.9	298.0	309.6	321.7	332.8
155°	246.2	249.4	255.3	261.3	269.3	278.4	287.6	296.7	305.9	316.0	326.3
157.5°	253.3	255.9	261.0	265.8	272.5	280.2	287.6	294.3	302.0	310.8	318.7
160°	258.0	260.1	264.5	268.7	274.7	281.2	287.6	292.9	299.4	306.9	313.9
162.5°	261.8	264.0	267.5	271.4	276.0	281.5	287.1	291.6	297.3	303.5	309.2
165°	267.1	268.2	271.5	274.1	277.4	282.2	286.0	289.2	292.9	297.7	302.1
167.5°	271.5	272.5	274.6	276.5	278.5	282.1	285.2	286.7	289.2	292.2	295.3
170°	274.1	274.7	276.3	277.4	279.0	281.6	284.4	285.4	287.0	289.2	291.9
172.5°	276.3	276.0	277.6	278.2	279.4	281.3	283.0	283.7	284.5	286.2	288.0
175°	278.4	277.9	279.0	279.0	279.5	280.6	281.6	281.2	281.6	282.2	283.8
177.5°	279.1	278.6	279.5	279.5	279.5	279.5	280.8	279.9	279.5	279.9	280.8
180°	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5



TEST NUMBER: P331743-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2151.5	2159.0	2162.5	2162.5	2166.5	2164.8	2163.0
5°	2275.2	2288.9	2291.8	2304.8	2314.1	2311.3	2312.7
7.5°	2398.1	2420.2	2442.0	2452.0	2453.5	2459.4	2461.5
10°	2473.8	2491.9	2525.8	2520.7	2546.0	2560.5	2536.7
12.5°	2546.6	2571.0	2594.5	2601.0	2615.4	2620.0	2610.6
15°	2612.4	2625.5	2627.0	2623.3	2627.6	2624.0	2610.3
17.5°	2550.9	2529.9	2487.1	2466.8	2450.8	2427.1	2417.6
20°	2449.2	2387.1	2314.9	2286.0	2252.0	2185.6	2201.5
22.5°	2229.7	2158.9	2086.7	2002.3	1962.0	1899.0	1895.3
25°	1888.0	1765.9	1631.6	1537.8	1482.8	1420.0	1392.5
27.5°	1467.9	1314.3	1204.2	1148.4	1097.7	1047.9	1045.8
30°	1191.8	1076.2	991.0	943.3	912.2	891.3	895.6
32.5°	1004.6	925.4	867.9	828.3	805.3	789.6	789.3
35°	821.2	767.0	730.2	713.6	697.0	685.4	686.2
37.5°	702.8	670.2	649.8	631.4	621.0	615.4	612.2
40°	642.1	615.4	599.5	588.6	579.9	572.0	570.6
42.5°	594.2	572.0	556.2	547.6	539.5	534.0	532.4
45°	527.3	509.2	494.7	485.4	481.7	476.7	476.7
47.5°	469.0	451.3	440.0	434.1	427.9	424.5	424.4
50°	429.8	416.0	406.0	402.3	397.3	395.1	394.4
52.5°	394.5	384.3	377.0	374.6	372.4	369.7	370.1
55°	346.7	340.9	338.0	335.8	332.2	327.9	330.8
57.5°	306.4	301.5	293.7	286.9	283.6	280.5	281.7
60°	278.1	268.0	257.9	249.9	247.7	241.2	241.2
62.5°	242.2	228.1	215.7	211.2	209.1	206.0	205.4
65°	186.3	180.6	177.7	174.7	173.3	173.3	171.9
67.5°	154.4	152.1	148.9	148.2	146.8	146.4	145.9
70°	136.5	133.7	132.1	131.5	130.0	130.7	128.6
72.5°	119.1	116.9	116.6	114.7	113.9	114.0	112.4
75°	93.9	93.9	93.2	92.5	91.0	90.3	91.0
77.5°	72.2	72.4	71.1	71.0	70.8	71.0	70.2
80°	57.8	58.5	57.8	57.0	56.4	57.0	56.4
82.5°	45.6	44.7	44.5	44.4	44.2	43.7	43.6
85°	26.0	26.8	26.0	25.3	25.3	25.3	26.0
87.5°	13.0	13.3	13.4	13.4	13.4	13.4	12.8
90°	16.1	17.2	17.7	17.7	17.7	17.7	17.7
92.5°	40.2	35.7	32.3	32.0	30.3	30.6	29.8
95°	108.0	85.5	73.6	66.6	62.4	60.7	61.3
97.5°	268.9	210.8	171.9	146.2	133.0	125.2	120.6
100°	424.1	350.4	285.4	240.8	217.7	202.1	192.5
102.5°	581.9	528.1	459.1	410.7	371.2	351.8	338.7
105°	713.8	720.9	703.0	669.8	636.4	613.3	605.8
107.5°	704.2	760.1	786.1	790.2	788.4	783.8	773.8
110°	674.0	742.8	786.9	810.0	820.3	825.1	824.5



TEST NUMBER: P331743-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	638.4	711.9	762.4	794.6	811.6	820.8	823.7
115°	589.7	660.1	715.5	753.6	778.4	792.3	797.1
117.5°	550.1	614.0	665.9	704.8	730.9	745.6	749.7
120°	529.4	586.4	635.4	673.0	698.2	713.8	719.2
122.5°	512.3	566.2	610.4	644.1	669.0	682.9	687.4
125°	489.7	537.0	577.3	608.5	628.9	642.3	646.7
127.5°	467.8	512.4	549.6	576.7	595.9	607.5	611.0
130°	453.2	495.6	531.0	557.4	575.7	586.4	590.7
132.5°	439.4	478.4	511.7	537.6	555.9	565.8	569.7
135°	417.6	453.2	483.2	506.3	524.1	533.8	535.9
137.5°	400.4	428.5	454.8	475.8	491.1	499.5	502.8
140°	389.2	413.9	437.5	454.8	468.7	476.7	480.0
142.5°	379.3	400.6	420.4	436.7	449.4	456.6	457.2
145°	366.6	383.2	398.9	411.7	420.8	426.2	427.8
147.5°	356.3	369.3	380.7	391.3	398.6	402.3	403.2
150°	349.4	360.7	370.3	378.4	384.8	388.0	388.6
152.5°	343.8	353.4	361.7	368.1	373.7	376.1	376.2
155°	334.9	342.9	348.8	354.8	358.5	360.7	359.6
157.5°	325.8	332.6	337.2	341.4	344.6	345.5	345.5
160°	319.8	325.7	329.5	333.3	335.9	336.5	336.5
162.5°	314.2	319.3	322.2	325.9	327.8	328.3	327.9
165°	305.9	309.6	311.8	313.9	316.0	316.0	315.6
167.5°	298.2	300.8	302.7	303.7	304.9	304.8	304.2
170°	293.5	295.7	296.7	297.3	298.9	298.3	297.3
172.5°	289.2	290.9	291.5	292.1	292.8	292.3	291.6
175°	284.4	284.9	285.4	285.4	286.0	285.4	284.4
177.5°	280.8	281.3	281.3	281.3	281.3	280.8	279.9
180°	279.5	279.5	279.5	279.5	279.5	279.5	279.5

(END OF REPORT)