

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331744-830

Luminaire Tested: **SA2XXRDIP-C1005D530U830-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331744-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 530 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5276.7 lumens
Efficiency: N/A
Efficacy: 95.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331744-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331744-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62				
1	101	97	93	90	95	91	88	85	80	78	75	70	68	66	60	59	58	54				
2	93	85	79	74	87	80	75	71	71	67	63	62	59	56	54	52	50	46				
3	85	76	68	63	79	71	65	60	63	58	54	55	52	48	48	46	43	40				
4	78	67	60	54	73	64	57	51	56	51	47	50	46	42	44	40	38	34				
5	72	60	52	47	67	57	50	45	51	45	41	45	40	37	40	36	33	30				
6	66	55	47	41	62	52	44	39	46	40	36	41	36	33	36	32	30	27				
7	62	49	42	36	58	47	40	35	42	36	32	37	33	29	33	29	27	24				
8	57	45	37	32	54	43	36	31	39	33	29	34	30	26	31	27	24	22				
9	54	41	34	29	50	39	33	28	36	30	26	32	27	24	28	25	22	20				
10	50	38	31	26	47	36	30	25	33	27	23	30	25	22	26	23	20	18				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25770	25770	25770
5°	25869	25449	25590
10°	25671	25032	24819
15°	25377	24289	23590
20°	24967	23230	22063
25°	24549	22026	20587
30°	23968	20789	18690
35°	23402	19446	17026
40°	22835	18054	15099
45°	22165	16493	13358
50°	21481	14913	11645
55°	20777	13216	10001
60°	19963	11428	8302
65°	19037	9605	7561
70°	17934	7912	6954
75°	16581	7211	6488
80°	14635	6453	5904
85°	11504	5076	5076



TEST NUMBER: P331744-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.4	2.8
10°-20°	410.2	7.8
20°-30°	576.1	10.9
30°-40°	628.2	11.9
40°-50°	577.6	10.9
50°-60°	453.6	8.6
60°-70°	295.8	5.6
70°-80°	152.5	2.9
80°-90°	41.2	0.8
90°-100°	22.7	0.4
100°-110°	83.2	1.6
110°-120°	222.3	4.2
120°-130°	366.9	7.0
130°-140°	390.2	7.4
140°-150°	362.7	6.9
150°-160°	291.6	5.5
160°-170°	187.9	3.6
170°-180°	64.7	1.2
0°-30°	1135.7	21.5
0°-40°	1763.9	33.4
0°-60°	2795.1	53.0
0°-90°	3284.5	62.2
90°-120°	328.1	6.2
90°-150°	1447.9	27.4
90°-180°	1992.0	37.8
0°-180°	5276.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1596	1596	1596	1596	1596	
5°	1596	1588	1570	1582	1579	151
15°	1518	1500	1453	1426	1411	427
25°	1378	1329	1236	1179	1156	633
35°	1187	1111	987	899	864	743
45°	971	871	722	623	585	749
55°	738	623	470	386	355	659
65°	498	381	251	205	198	494
75°	266	168	116	106	104	281
85°	62	33	27	27	27	73
90°	0	6	10	12	13	4
95°	32	17	19	22	21	39
105°	150	156	30	35	37	160
115°	283	291	304	86	40	278
125°	400	406	416	419	421	356
135°	495	502	507	512	511	382
145°	574	574	582	585	583	359
155°	632	628	634	636	632	291
165°	666	663	664	668	664	188
175°	681	678	679	682	677	65
180°	680	680	680	680	680	



TEST NUMBER: P331744-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1
2.5°	1601.9	1600.6	1599.3	1598.1	1596.8	1594.7	1591.9	1589.1	1586.3	1583.5	1586.0
5°	1596.1	1594.5	1592.9	1591.3	1589.7	1586.9	1582.6	1578.5	1574.3	1570.2	1573.0
7.5°	1579.7	1577.7	1575.7	1573.7	1571.7	1568.3	1563.4	1558.5	1553.7	1548.8	1549.6
10°	1565.8	1563.6	1561.3	1559.1	1556.8	1552.5	1546.1	1539.6	1533.2	1526.8	1525.9
12.5°	1548.5	1545.7	1542.9	1540.2	1537.5	1531.9	1523.7	1515.5	1507.3	1499.1	1497.3
15°	1518.2	1514.6	1511.1	1507.5	1504.0	1496.8	1485.9	1475.0	1464.1	1453.1	1447.1
17.5°	1480.8	1475.5	1470.1	1464.7	1459.3	1449.6	1435.6	1421.6	1407.6	1393.6	1386.4
20°	1453.1	1446.7	1440.3	1433.9	1427.5	1416.3	1400.1	1384.1	1368.1	1352.0	1344.0
22.5°	1423.1	1415.9	1408.7	1401.6	1394.3	1381.7	1363.6	1345.5	1327.4	1309.3	1298.9
25°	1378.0	1367.7	1357.4	1347.2	1336.9	1321.3	1300.0	1278.8	1257.6	1236.4	1223.3
27.5°	1323.7	1312.6	1301.4	1290.2	1279.0	1261.5	1237.7	1213.7	1189.9	1166.0	1150.7
30°	1285.6	1273.4	1261.2	1249.0	1236.8	1217.9	1192.1	1166.5	1140.9	1115.1	1098.7
32.5°	1248.6	1234.4	1220.1	1205.9	1191.6	1171.4	1145.2	1119.0	1092.8	1066.6	1047.9
35°	1187.3	1171.0	1154.6	1138.2	1121.9	1099.6	1071.3	1043.1	1014.8	986.6	966.4
37.5°	1126.1	1108.1	1090.1	1072.1	1054.2	1030.2	1000.0	970.0	939.8	909.7	887.5
40°	1083.4	1064.1	1044.8	1025.6	1006.4	981.1	950.0	918.9	887.7	856.6	833.8
42.5°	1039.4	1019.2	998.9	978.5	958.3	932.1	899.9	867.7	835.6	803.4	779.9
45°	970.7	949.1	927.7	906.2	884.7	857.1	823.3	789.7	755.9	722.3	699.5
47.5°	903.6	880.9	858.1	835.3	812.5	783.7	748.9	714.1	679.3	644.5	621.9
50°	855.2	832.4	809.5	786.7	763.9	734.9	699.6	664.3	629.0	593.7	571.6
52.5°	807.8	783.9	760.2	736.3	712.5	683.3	648.8	614.3	579.7	545.2	523.8
55°	738.1	713.1	688.1	663.0	638.0	608.1	573.4	538.8	504.2	469.5	450.2
57.5°	666.8	641.1	615.4	589.7	564.0	534.5	501.2	467.9	434.6	401.2	383.6
60°	618.2	592.6	566.8	541.2	515.5	486.2	453.1	420.0	386.9	353.9	337.5
62.5°	570.9	545.2	519.5	493.8	468.2	439.5	408.0	376.5	345.0	313.5	297.8
65°	498.3	472.3	446.4	420.4	394.4	366.9	338.0	309.2	280.2	251.4	240.4
67.5°	428.4	402.7	376.8	351.0	325.2	299.3	273.3	247.3	221.3	195.3	190.3
70°	379.9	354.9	329.8	304.8	279.7	256.2	234.0	211.9	189.7	167.6	164.4
72.5°	333.7	309.6	285.7	261.6	237.6	216.7	199.0	181.2	163.3	145.6	142.9
75°	265.8	243.3	220.8	198.4	175.9	159.2	148.3	137.4	126.5	115.6	113.3
77.5°	199.1	179.4	159.7	140.0	120.2	107.7	102.5	97.2	91.9	86.7	85.4
80°	157.4	141.1	124.7	108.3	92.0	82.2	79.0	75.8	72.6	69.4	68.1
82.5°	119.3	106.5	93.8	81.0	68.2	60.7	58.5	56.4	54.2	52.0	51.3
85°	62.1	55.3	48.6	41.8	35.2	31.3	30.3	29.4	28.4	27.4	27.4
87.5°	18.6	16.8	15.0	13.1	11.3	10.6	10.7	10.8	11.0	11.2	11.0
90°	0.5	1.7	2.9	4.1	5.3	6.3	7.3	8.1	9.0	9.8	10.4
92.5°	9.9	9.8	9.7	9.6	9.5	9.7	10.1	10.6	10.9	11.4	11.7
95°	32.0	28.4	24.8	21.1	17.5	16.1	16.9	17.6	18.4	19.2	19.7
97.5°	63.4	53.3	43.2	33.0	22.8	18.6	20.4	22.1	23.9	25.6	26.1
100°	87.1	72.1	57.1	42.1	27.1	20.6	22.4	24.3	26.2	28.0	28.9
102.5°	113.0	109.9	106.7	103.5	100.4	91.0	75.5	59.9	44.4	28.8	30.0
105°	149.5	152.8	156.1	159.4	162.7	149.4	119.5	89.7	59.9	30.0	31.2
107.5°	191.1	193.8	196.4	199.1	201.7	185.1	149.4	113.6	77.8	42.0	40.8
110°	217.9	220.2	222.5	224.8	227.1	212.4	180.9	149.3	117.6	86.1	75.1



TEST NUMBER: P331744-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	243.1	245.2	247.1	249.2	251.2	248.4	240.5	232.7	224.9	217.2	177.2
115°	282.9	284.6	286.5	288.4	290.3	292.6	295.3	298.0	300.8	303.5	252.9
117.5°	318.4	320.5	322.5	324.6	326.7	328.7	330.5	332.4	334.3	336.1	324.0
120°	344.3	345.9	347.6	349.2	350.9	352.7	354.7	356.7	358.5	360.5	361.8
122.5°	366.4	368.1	369.9	371.6	373.2	375.2	377.3	379.5	381.6	383.8	384.6
125°	399.9	401.3	402.7	404.2	405.6	407.4	409.4	411.5	413.6	415.7	416.4
127.5°	430.3	431.9	433.5	435.0	436.6	438.2	439.7	441.3	442.8	444.4	445.4
130°	449.6	451.3	453.1	454.9	456.6	458.1	459.3	460.4	461.7	462.9	464.1
132.5°	469.3	470.7	472.2	473.7	475.2	476.5	477.8	479.0	480.1	481.4	482.4
135°	494.8	496.6	498.3	500.1	501.8	503.2	504.2	505.2	506.1	507.1	508.2
137.5°	520.8	521.9	523.1	524.3	525.6	526.8	527.9	529.0	530.1	531.2	532.3
140°	537.6	538.5	539.4	540.3	541.1	542.2	543.4	544.6	545.7	547.0	548.0
142.5°	551.8	552.6	553.4	554.1	555.0	556.0	557.4	558.7	560.2	561.6	562.4
145°	574.0	573.9	573.8	573.7	573.6	574.5	576.4	578.2	580.0	581.9	582.7
147.5°	593.4	593.0	592.6	592.2	591.7	592.5	594.3	596.2	597.9	599.8	600.4
150°	606.0	605.2	604.5	603.7	602.9	603.4	605.2	606.9	608.7	610.4	611.1
152.5°	616.6	615.8	614.9	614.1	613.2	613.6	615.3	617.0	618.6	620.3	620.9
155°	632.1	631.1	630.1	629.1	628.1	628.3	629.6	630.9	632.3	633.6	634.2
157.5°	644.1	643.4	642.5	641.7	640.8	640.9	641.8	642.7	643.7	644.6	645.3
160°	651.3	650.6	650.0	649.3	648.7	648.7	649.3	650.0	650.6	651.3	652.0
162.5°	657.5	656.9	656.2	655.5	655.0	654.9	655.4	656.0	656.6	657.1	657.9
165°	666.0	665.3	664.7	664.0	663.4	663.3	663.5	663.8	664.2	664.5	665.3
167.5°	672.3	671.7	671.0	670.3	669.7	669.5	669.8	670.1	670.4	670.7	671.5
170°	675.8	675.2	674.6	673.9	673.3	673.0	673.3	673.4	673.6	673.9	674.7
172.5°	678.3	677.6	676.9	676.3	675.6	675.3	675.6	675.8	676.0	676.3	677.0
175°	681.3	680.5	679.8	679.0	678.2	678.0	678.2	678.3	678.5	678.8	679.6
177.5°	681.7	681.2	680.5	680.0	679.3	679.0	679.1	679.2	679.3	679.4	680.0
180°	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8



TEST NUMBER: P331744-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1
2.5°	1588.6	1591.1	1593.7	1594.7	1594.2	1593.7	1593.2	1592.7
5°	1575.9	1578.9	1581.7	1582.6	1581.7	1580.7	1579.8	1578.9
7.5°	1550.4	1551.2	1552.1	1551.7	1550.0	1548.3	1546.7	1545.0
10°	1524.8	1523.9	1523.0	1521.5	1519.6	1517.7	1515.7	1513.8
12.5°	1495.6	1493.8	1492.1	1489.7	1486.5	1483.3	1480.1	1476.9
15°	1441.0	1434.8	1428.7	1424.1	1420.9	1417.7	1414.5	1411.3
17.5°	1379.1	1371.9	1364.6	1358.2	1352.7	1347.2	1341.6	1336.1
20°	1336.0	1327.9	1319.9	1312.4	1305.3	1298.3	1291.2	1284.1
22.5°	1288.6	1278.3	1267.9	1260.1	1254.9	1249.6	1244.3	1239.1
25°	1210.1	1197.0	1183.8	1174.9	1170.0	1165.2	1160.4	1155.6
27.5°	1135.3	1119.9	1104.6	1093.1	1085.4	1077.8	1070.2	1062.5
30°	1082.4	1066.0	1049.6	1037.2	1028.5	1019.8	1011.2	1002.5
32.5°	1029.3	1010.6	991.8	978.5	970.3	962.1	953.9	945.8
35°	946.1	926.0	905.7	892.0	885.0	877.9	870.8	863.8
37.5°	865.2	842.9	820.6	805.4	797.4	789.3	781.2	773.1
40°	811.0	788.2	765.4	749.9	741.5	733.1	724.8	716.4
42.5°	756.3	732.7	709.2	693.3	685.2	677.1	669.1	661.0
45°	676.7	653.8	631.0	615.9	608.1	600.4	592.7	585.0
47.5°	599.2	576.6	553.8	539.0	532.1	525.1	518.0	511.0
50°	549.4	527.3	505.1	490.6	483.9	477.1	470.4	463.6
52.5°	502.4	481.0	459.7	445.8	439.6	433.4	427.2	420.9
55°	430.9	411.7	392.4	379.8	373.6	367.5	361.5	355.3
57.5°	366.0	348.3	330.6	319.2	314.1	309.0	303.9	298.7
60°	321.1	304.8	288.4	277.7	272.5	267.4	262.2	257.1
62.5°	282.3	266.6	251.1	241.7	238.7	235.5	232.4	229.4
65°	229.5	218.6	207.6	201.7	200.8	199.8	198.9	197.9
67.5°	185.3	180.3	175.2	172.2	171.3	170.2	169.2	168.1
70°	161.2	158.0	154.8	152.5	151.2	149.9	148.6	147.3
72.5°	140.3	137.5	134.8	133.1	132.3	131.6	130.7	130.0
75°	111.0	108.9	106.6	105.3	105.0	104.6	104.3	104.0
77.5°	84.1	82.8	81.5	80.6	80.1	79.6	79.1	78.6
80°	66.7	65.5	64.2	63.5	63.5	63.5	63.5	63.5
82.5°	50.4	49.7	48.9	48.5	48.5	48.5	48.5	48.5
85°	27.4	27.4	27.4	27.4	27.4	27.4	27.4	27.4
87.5°	10.9	10.7	10.7	10.6	10.7	10.7	10.7	10.7
90°	10.9	11.5	12.1	12.4	12.6	12.8	13.1	13.3
92.5°	12.0	12.3	12.5	12.7	12.9	13.0	13.2	13.3
95°	20.3	20.8	21.4	21.6	21.5	21.4	21.3	21.1
97.5°	26.6	27.0	27.4	27.7	27.8	28.0	28.1	28.3
100°	29.8	30.6	31.6	32.0	32.3	32.5	32.7	33.0
102.5°	31.1	32.2	33.4	34.1	34.4	34.7	35.0	35.3
105°	32.4	33.6	34.8	35.6	36.1	36.5	36.9	37.4
107.5°	39.6	38.4	37.1	36.8	37.1	37.6	38.0	38.5
110°	64.2	53.3	42.3	37.1	37.5	38.0	38.5	38.8



TEST NUMBER: P331744-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	137.3	97.5	57.6	37.9	38.2	38.5	38.9	39.2
115°	202.3	151.7	101.0	71.8	63.9	56.1	48.2	40.3
117.5°	311.7	299.4	287.2	268.2	242.2	216.4	190.6	164.7
120°	363.2	364.5	365.8	359.1	344.3	329.6	314.8	300.0
122.5°	385.3	386.2	386.9	385.9	383.0	380.1	377.3	374.4
125°	417.2	417.9	418.7	419.2	419.6	419.9	420.3	420.6
127.5°	446.6	447.7	448.8	449.4	449.5	449.6	449.6	449.7
130°	465.2	466.5	467.7	468.3	468.1	468.0	467.9	467.8
132.5°	483.4	484.5	485.5	485.9	485.8	485.7	485.6	485.5
135°	509.3	510.4	511.5	512.0	511.7	511.5	511.3	511.0
137.5°	533.4	534.4	535.6	535.8	535.5	535.1	534.8	534.4
140°	548.9	549.9	550.9	551.1	550.5	550.1	549.5	548.9
142.5°	563.4	564.2	565.1	565.3	564.8	564.2	563.6	563.1
145°	583.4	584.2	584.9	585.0	584.6	584.0	583.4	582.9
147.5°	601.0	601.5	602.1	602.1	601.7	601.2	600.8	600.3
150°	611.7	612.4	613.0	613.1	612.6	612.0	611.4	611.0
152.5°	621.6	622.3	622.9	622.8	622.2	621.4	620.7	620.0
155°	634.9	635.6	636.2	636.0	635.2	634.3	633.5	632.5
157.5°	646.0	646.8	647.5	647.5	646.6	645.7	644.9	644.0
160°	652.5	653.2	653.8	653.8	653.1	652.3	651.5	650.7
162.5°	658.6	659.4	660.2	660.1	659.1	658.2	657.2	656.3
165°	666.1	666.8	667.6	667.6	666.8	666.1	665.3	664.5
167.5°	672.2	673.1	673.8	673.7	672.7	671.8	670.7	669.8
170°	675.4	676.2	676.9	676.8	675.8	674.9	673.9	672.9
172.5°	677.8	678.5	679.3	679.2	678.3	677.2	676.3	675.2
175°	680.3	681.1	681.8	681.7	680.6	679.5	678.4	677.3
177.5°	680.6	681.3	681.8	681.7	681.0	680.1	679.4	678.6
180°	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8

(END OF REPORT)