

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333537-840

Luminaire Tested: **S125RDIP-S610D810U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333537-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S610D810U840-4F0-1E-UDD-F4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5339.2 lumens  
Efficiency: N/A  
Efficacy: 139.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 38.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333537-840

CATALOG NUMBER: S125RDIP-S610D810U840-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P333537-840

CATALOG NUMBER: S125RDIP-S610D810U840-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	52	52	52	45
1	97	93	89	85	89	85	82	79	71	69	67	58	56	55	46	45	44	38
2	88	81	75	70	81	75	69	65	62	59	55	51	48	46	41	39	37	32
3	81	71	64	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28
4	74	63	56	50	67	58	52	46	49	44	40	40	37	34	32	30	28	24
5	68	56	48	43	62	52	45	40	44	39	34	36	32	29	29	26	24	21
6	62	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	21	18
7	58	46	38	32	53	42	35	30	36	31	27	30	26	23	24	21	19	16
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	22	19	17	15
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	21	18	15	13
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6561	6561	6561
5°	6576	6501	6541
10°	6526	6441	6441
15°	6449	6310	6258
20°	6349	6128	6054
25°	6233	5949	5818
30°	6088	5739	5557
35°	5941	5523	5263
40°	5802	5298	4975
45°	5634	5045	4661
50°	5466	4772	4332
55°	5271	4510	3984
60°	5074	4193	3608
65°	4843	3822	3177
70°	4579	3361	2738
75°	4212	2832	2278
80°	3712	2228	1912
85°	3127	1815	1704



TEST NUMBER: P333537-840

CATALOG NUMBER: S125RDIP-S610D810U840-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	95.5	1.8
10°-20°	267.0	5.0
20°-30°	387.1	7.3
30°-40°	441.2	8.3
40°-50°	430.0	8.1
50°-60°	362.0	6.8
60°-70°	253.8	4.8
70°-80°	130.4	2.4
80°-90°	35.1	0.7
90°-100°	283.9	5.3
100°-110°	610.3	11.4
110°-120°	572.7	10.7
120°-130°	464.2	8.7
130°-140°	372.5	7.0
140°-150°	281.1	5.3
150°-160°	197.9	3.7
160°-170°	116.6	2.2
170°-180°	37.9	0.7
0°-30°	749.6	14.0
0°-40°	1190.8	22.3
0°-60°	1982.8	37.1
0°-90°	2402.1	45.0
90°-120°	1466.9	27.5
90°-150°	2584.6	48.4
90°-180°	2937.0	55.0
0°-180°	5339.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1016	1016	1016	1016	1016	
5°	1014	1011	1003	1010	1009	96
15°	964	959	944	943	936	272
25°	875	862	835	825	816	402
35°	754	734	700	679	668	472
45°	617	594	552	523	510	476
55°	468	442	400	367	354	418
65°	317	290	250	220	208	314
75°	169	145	114	97	91	179
85°	42	29	24	24	23	47
90°	1	7	13	17	18	3
95°	26	77	700	317	186	28
105°	89	125	572	1127	1046	94
115°	160	192	460	991	1166	157
125°	221	259	441	788	918	196
135°	259	311	438	660	763	201
145°	302	346	439	547	602	189
155°	344	370	428	484	504	158
165°	376	386	411	436	442	106
175°	391	391	394	399	397	37
180°	392	392	392	392	392	



TEST NUMBER: P333537-840

CATALOG NUMBER: S125RDIP-S610D810U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9
2.5°	1017.7	1017.3	1016.9	1016.5	1016.1	1015.2	1013.8	1012.5	1011.1	1009.8	1011.1
5°	1014.3	1013.7	1013.0	1012.3	1011.6	1010.4	1008.5	1006.6	1004.7	1002.8	1004.5
7.5°	1004.4	1003.7	1003.1	1002.4	1001.8	1000.4	998.0	995.8	993.6	991.3	992.5
10°	995.1	994.6	994.1	993.6	993.1	991.7	989.3	986.9	984.5	982.1	982.6
12.5°	984.7	984.1	983.4	982.8	982.1	980.2	977.0	973.8	970.6	967.3	967.8
15°	964.5	963.4	962.4	961.4	960.4	958.1	954.5	950.9	947.4	943.7	943.6
17.5°	941.6	940.1	938.5	937.0	935.3	932.3	927.8	923.3	918.8	914.3	913.4
20°	923.8	922.1	920.4	918.7	917.0	913.4	908.0	902.5	897.1	891.6	890.7
22.5°	904.1	902.4	900.8	899.1	897.4	893.6	887.9	882.2	876.5	870.7	869.1
25°	874.7	872.1	869.6	867.1	864.4	860.0	853.7	847.4	841.1	834.8	832.6
27.5°	840.9	837.9	834.8	831.6	828.5	823.6	816.9	810.1	803.3	796.6	793.5
30°	816.4	813.1	809.9	806.7	803.4	798.2	791.0	784.0	776.8	769.6	765.7
32.5°	792.4	788.7	784.9	781.1	777.3	771.7	764.5	757.2	749.8	742.6	738.2
35°	753.5	749.4	745.3	741.2	737.1	731.2	723.6	715.9	708.2	700.5	695.6
37.5°	715.3	710.2	705.3	700.3	695.4	688.9	681.0	673.1	665.2	657.2	651.4
40°	688.2	683.2	678.0	672.9	667.8	661.2	653.0	644.8	636.6	628.4	622.0
42.5°	660.0	654.8	649.5	644.3	639.0	632.2	623.7	615.2	606.8	598.3	592.1
45°	616.9	612.0	607.0	602.1	597.1	590.0	580.6	571.2	561.8	552.4	545.6
47.5°	572.3	567.0	561.8	556.6	551.4	544.0	534.6	525.1	515.7	506.2	499.3
50°	544.0	538.4	532.7	527.1	521.5	513.8	504.1	494.4	484.6	474.9	467.8
52.5°	513.3	507.6	501.8	496.0	490.3	482.8	473.6	464.4	455.2	446.1	438.4
55°	468.1	462.6	457.2	451.7	446.3	438.7	429.2	419.6	410.1	400.5	392.8
57.5°	422.3	416.5	410.6	404.9	399.0	391.4	382.2	373.0	363.9	354.7	347.1
60°	392.8	386.9	380.9	375.0	369.0	361.4	352.1	343.0	333.8	324.6	317.1
62.5°	361.5	355.9	350.1	344.5	338.8	331.2	321.9	312.6	303.3	293.9	286.9
65°	316.9	311.1	305.3	299.5	293.7	286.3	277.2	268.2	259.1	250.1	243.3
67.5°	272.6	266.7	260.9	255.2	249.3	242.2	233.5	224.8	216.1	207.4	201.3
70°	242.5	236.7	230.9	225.1	219.2	212.1	203.6	195.1	186.5	178.0	172.7
72.5°	213.0	207.3	201.7	196.0	190.4	183.5	175.5	167.5	159.6	151.6	146.7
75°	168.8	163.7	158.5	153.5	148.3	142.2	135.0	127.8	120.7	113.5	109.8
77.5°	124.9	120.8	116.7	112.6	108.6	103.6	97.9	92.2	86.4	80.7	78.1
80°	99.8	95.6	91.6	87.5	83.4	79.0	74.1	69.4	64.6	59.9	58.3
82.5°	75.2	71.5	67.9	64.1	60.5	57.0	53.7	50.4	47.2	43.9	43.2
85°	42.2	39.1	36.1	33.0	29.9	28.0	27.1	26.3	25.4	24.5	24.3
87.5°	14.2	13.4	12.8	12.2	11.5	11.3	11.3	11.5	11.5	11.7	11.9
90°	0.8	1.6	3.1	4.7	6.4	7.9	8.7	10.3	11.0	12.6	13.4
92.5°	9.6	11.7	18.3	28.1	41.7	64.7	107.9	180.2	258.6	254.6	206.1
95°	26.1	26.9	33.1	41.8	59.2	94.7	179.3	352.9	570.9	699.6	684.6
97.5°	43.2	44.2	48.7	57.4	72.9	98.6	154.4	281.8	509.8	747.1	866.2
100°	55.2	56.9	60.0	68.7	83.7	107.3	153.2	255.8	454.8	713.1	910.4
102.5°	68.6	69.5	72.0	81.3	95.0	118.2	158.9	245.1	413.1	653.0	883.9
105°	89.3	89.3	93.2	101.1	113.7	135.8	170.6	240.9	372.7	572.5	799.1
107.5°	109.5	111.0	114.8	121.3	134.4	154.3	187.9	248.1	355.7	517.1	712.6
110°	124.0	125.5	128.7	135.8	147.6	168.1	200.6	255.1	350.6	491.1	663.3



TEST NUMBER: P333537-840

CATALOG NUMBER: S125RDIP-S610D810U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	138.5	140.1	142.6	149.7	161.6	181.5	212.6	263.9	350.6	475.9	626.6
115°	159.5	161.1	163.5	170.6	182.4	202.2	231.4	277.1	352.9	459.6	586.6
117.5°	178.4	180.9	183.4	190.5	203.9	223.0	250.6	292.4	358.2	451.5	562.8
120°	191.1	193.5	196.6	203.7	217.1	236.9	264.5	302.5	363.2	447.7	549.6
122.5°	204.4	206.1	208.6	215.7	230.5	250.1	277.8	313.8	367.6	444.5	538.2
125°	221.1	222.7	226.6	233.7	248.7	269.2	295.3	329.2	375.1	440.6	522.7
127.5°	234.2	236.6	241.7	250.6	266.6	287.1	312.3	343.5	383.4	438.7	508.5
130°	242.4	244.8	251.1	261.4	277.9	298.5	323.0	352.9	388.5	437.5	499.1
132.5°	248.7	251.8	259.3	270.8	288.0	308.6	333.1	361.1	394.2	437.5	491.5
135°	259.0	262.2	271.7	284.3	300.8	322.1	346.7	372.7	401.9	437.5	482.4
137.5°	272.0	274.3	283.2	295.8	312.0	334.0	356.3	381.2	409.0	438.4	474.4
140°	279.5	281.9	291.3	304.0	319.0	340.3	363.2	386.9	412.1	439.0	470.6
142.5°	288.3	290.1	298.9	311.5	326.0	346.0	367.6	390.1	414.0	439.7	467.5
145°	301.6	303.2	311.1	322.1	336.4	354.6	375.1	394.8	416.2	439.0	462.7
147.5°	315.5	316.5	323.3	333.6	345.9	361.8	379.8	397.7	416.9	437.0	457.8
150°	323.8	325.3	330.8	341.1	352.1	365.6	382.9	399.5	416.9	435.0	454.0
152.5°	332.5	333.6	338.4	347.4	357.9	370.0	386.1	400.8	416.3	432.5	449.6
155°	344.3	344.3	349.0	356.9	364.8	375.9	389.3	401.9	414.5	428.0	442.2
157.5°	354.7	354.6	358.3	365.1	372.0	380.4	391.9	402.7	412.5	423.2	435.3
160°	361.6	360.8	364.1	369.5	375.9	382.9	393.2	402.7	410.6	420.1	429.6
162.5°	367.3	366.6	369.7	374.6	379.6	385.5	394.5	402.0	408.7	416.3	424.4
165°	375.9	374.3	376.7	380.6	383.7	388.5	394.8	401.1	405.9	410.6	416.9
167.5°	381.5	380.7	382.1	384.4	386.6	389.6	394.8	399.2	401.4	405.1	409.5
170°	385.4	384.6	385.4	386.9	388.5	390.8	394.8	398.0	399.5	401.9	405.1
172.5°	387.9	386.5	387.2	388.8	389.7	390.8	394.2	396.7	397.0	398.1	400.6
175°	390.8	389.3	390.1	390.8	390.8	390.8	393.2	394.8	394.0	394.0	394.8
177.5°	392.2	391.0	391.0	391.6	391.0	391.0	392.2	392.9	391.6	391.6	392.2
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6



TEST NUMBER: P333537-840

CATALOG NUMBER: S125RDIP-S610D810U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9	1015.9
2.5°	1012.5	1013.8	1015.2	1015.8	1015.7	1015.5	1015.4	1015.3
5°	1006.2	1007.9	1009.7	1010.4	1010.0	1009.7	1009.4	1009.0
7.5°	993.7	994.9	996.1	996.5	996.1	995.7	995.4	995.0
10°	983.1	983.6	984.2	984.2	983.6	983.1	982.6	982.1
12.5°	968.2	968.6	968.9	968.7	967.9	967.1	966.3	965.5
15°	943.4	943.2	943.1	942.2	940.7	939.2	937.7	936.0
17.5°	912.6	911.7	910.9	909.8	908.6	907.3	906.1	904.7
20°	889.9	889.0	888.2	887.0	885.4	883.9	882.4	880.8
22.5°	867.4	865.7	864.0	862.5	861.3	860.0	858.8	857.5
25°	830.4	828.2	826.0	823.8	822.0	820.1	818.3	816.4
27.5°	790.4	787.3	784.2	781.7	779.9	778.1	776.3	774.5
30°	761.7	757.8	753.9	751.1	749.6	748.1	746.6	745.1
32.5°	733.9	729.6	725.3	722.2	720.1	718.2	716.3	714.4
35°	690.6	685.7	680.8	677.1	674.7	672.3	669.9	667.5
37.5°	645.4	639.4	633.5	629.3	627.0	624.8	622.5	620.2
40°	615.4	608.9	602.5	598.2	596.2	594.1	592.1	590.1
42.5°	585.9	579.7	573.5	568.9	565.9	562.9	559.9	556.9
45°	538.8	532.0	525.1	520.5	518.0	515.3	512.8	510.3
47.5°	492.2	485.1	478.2	473.2	470.4	467.6	464.7	461.9
50°	460.6	453.4	446.3	441.4	438.9	436.4	433.7	431.2
52.5°	430.7	422.9	415.3	410.1	407.6	405.1	402.4	399.9
55°	385.2	377.5	369.8	364.7	361.9	359.2	356.5	353.8
57.5°	339.6	332.1	324.7	319.6	317.2	314.8	312.5	310.0
60°	309.5	302.1	294.6	289.5	287.0	284.4	281.9	279.3
62.5°	279.9	273.0	266.0	261.3	258.7	256.2	253.6	251.1
65°	236.5	229.6	222.9	218.1	215.6	213.1	210.5	207.9
67.5°	195.0	188.7	182.5	178.3	176.3	174.3	172.2	170.2
70°	167.4	162.2	156.8	153.2	151.2	149.2	147.0	145.0
72.5°	141.9	136.9	132.1	129.0	127.6	126.2	124.9	123.5
75°	106.0	102.3	98.6	96.0	94.9	93.7	92.5	91.3
77.5°	75.4	72.8	70.2	68.5	67.6	66.7	65.8	64.9
80°	56.8	55.2	53.7	52.8	52.4	52.1	51.7	51.4
82.5°	42.4	41.7	41.0	40.6	40.4	40.2	40.0	39.8
85°	24.2	24.0	23.8	23.7	23.5	23.3	23.2	23.0
87.5°	12.0	12.2	12.3	12.6	12.5	12.3	12.3	12.2
90°	14.2	15.0	15.8	17.4	17.4	17.4	18.2	18.2
92.5°	140.0	101.6	76.4	64.7	54.6	52.7	51.6	50.4
95°	567.7	447.7	350.6	284.3	228.2	204.5	198.2	185.5
97.5°	845.6	761.3	666.7	574.5	525.7	481.5	458.6	448.5
100°	971.2	932.5	851.2	769.1	714.6	657.7	628.5	615.9
102.5°	1013.5	1037.4	998.4	942.8	884.5	844.0	812.3	802.8
105°	988.6	1096.8	1131.6	1122.9	1097.5	1071.5	1055.7	1046.2
107.5°	899.5	1043.9	1133.1	1174.3	1187.1	1186.9	1181.7	1175.4
110°	833.8	983.8	1095.2	1162.3	1197.8	1212.8	1218.4	1218.4





TEST NUMBER: P333537-840

CATALOG NUMBER: S125RDIP-S610D810U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	782.0	924.4	1037.0	1116.2	1168.1	1193.9	1207.6	1213.4
115°	717.0	839.4	947.6	1033.6	1095.2	1133.1	1155.2	1165.5
117.5°	675.0	780.4	873.6	952.6	1014.2	1053.3	1075.3	1081.6
120°	652.2	747.0	833.8	903.3	961.7	999.7	1021.0	1027.2
122.5°	635.2	723.0	800.3	865.5	917.6	952.3	973.6	979.3
125°	610.4	690.9	759.6	816.5	860.7	893.0	910.4	918.3
127.5°	585.1	660.2	724.4	777.6	817.7	846.3	862.7	866.2
130°	569.3	638.8	700.3	751.7	791.2	817.3	833.0	837.8
132.5°	553.5	618.5	674.5	723.9	763.4	789.4	804.0	809.3
135°	533.0	587.4	638.0	683.0	717.7	743.8	758.0	762.8
137.5°	515.6	559.7	601.7	639.9	671.1	694.7	707.8	713.1
140°	506.1	543.2	579.6	612.7	642.0	662.5	674.3	678.2
142.5°	498.0	529.4	560.6	589.4	614.2	631.6	642.8	646.0
145°	487.2	511.7	536.1	557.4	576.4	589.9	598.5	601.7
147.5°	477.1	497.0	515.7	531.9	546.8	557.6	562.7	564.1
150°	471.4	488.8	503.7	518.0	529.9	539.3	542.5	543.2
152.5°	465.0	480.6	494.3	505.3	515.3	522.9	526.0	526.8
155°	455.7	468.3	479.3	488.0	495.8	501.4	503.7	504.5
157.5°	446.2	456.6	465.0	471.9	478.1	482.6	484.8	484.6
160°	439.8	447.7	455.7	461.1	466.7	470.6	472.2	471.4
162.5°	432.8	440.1	446.8	451.6	456.0	459.2	459.6	459.4
165°	423.2	428.8	433.5	437.5	440.6	442.2	442.2	442.2
167.5°	414.0	417.7	421.3	424.1	425.8	427.2	426.6	426.4
170°	409.0	411.4	413.7	415.4	416.9	417.7	417.7	416.9
172.5°	403.3	405.7	407.5	408.4	408.7	410.1	408.9	408.1
175°	397.2	397.2	398.8	398.8	398.8	399.5	398.0	397.2
177.5°	392.9	393.5	393.5	393.5	392.9	393.5	391.6	391.6
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6

(END OF REPORT)