

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331746-830

Luminaire Tested: **SA2XXRDIP-C1005D530U830-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331746-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5230.4 lumens
Efficiency: N/A
Efficacy: 94.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331746-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331746-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	63				
1	101	97	93	90	95	91	88	85	80	78	76	70	68	67	61	60	59	54				
2	93	85	80	74	87	80	75	71	71	67	64	62	59	57	54	52	50	46				
3	85	76	69	63	79	71	65	60	63	58	54	56	52	49	49	46	43	40				
4	78	67	60	54	73	64	57	51	57	51	47	50	46	42	44	41	38	35				
5	72	61	52	47	67	57	50	45	51	45	41	45	41	37	40	36	33	31				
6	67	55	47	41	62	52	44	39	46	40	36	41	36	33	36	33	30	27				
7	62	50	42	36	58	47	40	35	42	36	32	38	33	29	33	30	27	24				
8	57	45	38	32	54	43	36	31	39	33	29	35	30	26	31	27	24	22				
9	54	42	34	29	50	39	33	28	36	30	26	32	27	24	29	25	22	20				
10	50	38	31	26	47	36	30	25	33	27	24	30	25	22	27	23	20	18				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25770	25770	25770
5°	25869	25449	25590
10°	25671	25032	24819
15°	25377	24289	23590
20°	24967	23230	22063
25°	24549	22026	20587
30°	23968	20789	18690
35°	23402	19446	17026
40°	22835	18054	15099
45°	22165	16493	13358
50°	21481	14913	11645
55°	20777	13216	10001
60°	19963	11428	8302
65°	19037	9605	7561
70°	17934	7912	6954
75°	16581	7211	6488
80°	14635	6453	5904
85°	11504	5076	5076



TEST NUMBER: P331746-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.4	2.9
10°-20°	410.2	7.8
20°-30°	576.1	11.0
30°-40°	628.2	12.0
40°-50°	577.6	11.0
50°-60°	453.6	8.7
60°-70°	295.8	5.7
70°-80°	152.5	2.9
80°-90°	42.1	0.8
90°-100°	111.8	2.1
100°-110°	379.3	7.3
110°-120°	402.9	7.7
120°-130°	331.7	6.3
130°-140°	266.3	5.1
140°-150°	201.3	3.8
150°-160°	141.4	2.7
160°-170°	83.3	1.6
170°-180°	27.1	0.5
0°-30°	1135.7	21.7
0°-40°	1763.9	33.7
0°-60°	2795.1	53.4
0°-90°	3285.4	62.8
90°-120°	893.9	17.1
90°-150°	1693.2	32.4
90°-180°	1945.0	37.2
0°-180°	5230.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1596	1596	1596	1596	1596	
5°	1596	1588	1570	1582	1579	151
15°	1518	1500	1453	1426	1411	427
25°	1378	1329	1236	1179	1156	633
35°	1187	1111	987	899	864	743
45°	971	871	722	623	585	749
55°	738	623	470	386	355	659
65°	498	381	251	205	198	494
75°	266	168	116	106	104	281
85°	62	33	27	27	27	73
90°	1	7	18	17	18	4
95°	19	46	211	80	61	20
105°	66	99	398	712	606	70
115°	116	146	333	688	797	115
125°	161	191	320	557	647	143
135°	189	226	317	468	536	146
145°	216	248	315	391	428	136
155°	246	265	306	346	360	113
165°	268	276	293	311	316	75
175°	279	279	282	285	284	26
180°	280	280	280	280	280	



TEST NUMBER: P331746-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1
2.5°	1601.9	1600.6	1599.3	1598.1	1596.8	1594.7	1591.9	1589.1	1586.3	1583.5	1586.0
5°	1596.1	1594.5	1592.9	1591.3	1589.7	1586.9	1582.6	1578.5	1574.3	1570.2	1573.0
7.5°	1579.7	1577.7	1575.7	1573.7	1571.7	1568.3	1563.4	1558.5	1553.7	1548.8	1549.6
10°	1565.8	1563.6	1561.3	1559.1	1556.8	1552.5	1546.1	1539.6	1533.2	1526.8	1525.9
12.5°	1548.5	1545.7	1542.9	1540.2	1537.5	1531.9	1523.7	1515.5	1507.3	1499.1	1497.3
15°	1518.2	1514.6	1511.1	1507.5	1504.0	1496.8	1485.9	1475.0	1464.1	1453.1	1447.1
17.5°	1480.8	1475.5	1470.1	1464.7	1459.3	1449.6	1435.6	1421.6	1407.6	1393.6	1386.4
20°	1453.1	1446.7	1440.3	1433.9	1427.5	1416.3	1400.1	1384.1	1368.1	1352.0	1344.0
22.5°	1423.1	1415.9	1408.7	1401.6	1394.3	1381.7	1363.6	1345.5	1327.4	1309.3	1298.9
25°	1378.0	1367.7	1357.4	1347.2	1336.9	1321.3	1300.0	1278.8	1257.6	1236.4	1223.3
27.5°	1323.7	1312.6	1301.4	1290.2	1279.0	1261.5	1237.7	1213.7	1189.9	1166.0	1150.7
30°	1285.6	1273.4	1261.2	1249.0	1236.8	1217.9	1192.1	1166.5	1140.9	1115.1	1098.7
32.5°	1248.6	1234.4	1220.1	1205.9	1191.6	1171.4	1145.2	1119.0	1092.8	1066.6	1047.9
35°	1187.3	1171.0	1154.6	1138.2	1121.9	1099.6	1071.3	1043.1	1014.8	986.6	966.4
37.5°	1126.1	1108.1	1090.1	1072.1	1054.2	1030.2	1000.0	970.0	939.8	909.7	887.5
40°	1083.4	1064.1	1044.8	1025.6	1006.4	981.1	950.0	918.9	887.7	856.6	833.8
42.5°	1039.4	1019.2	998.9	978.5	958.3	932.1	899.9	867.7	835.6	803.4	779.9
45°	970.7	949.1	927.7	906.2	884.7	857.1	823.3	789.7	755.9	722.3	699.5
47.5°	903.6	880.9	858.1	835.3	812.5	783.7	748.9	714.1	679.3	644.5	621.9
50°	855.2	832.4	809.5	786.7	763.9	734.9	699.6	664.3	629.0	593.7	571.6
52.5°	807.8	783.9	760.2	736.3	712.5	683.3	648.8	614.3	579.7	545.2	523.8
55°	738.1	713.1	688.1	663.0	638.0	608.1	573.4	538.8	504.2	469.5	450.2
57.5°	666.8	641.1	615.4	589.7	564.0	534.5	501.2	467.9	434.6	401.2	383.6
60°	618.2	592.6	566.8	541.2	515.5	486.2	453.1	420.0	386.9	353.9	337.5
62.5°	570.9	545.2	519.5	493.8	468.2	439.5	408.0	376.5	345.0	313.5	297.8
65°	498.3	472.3	446.4	420.4	394.4	366.9	338.0	309.2	280.2	251.4	240.4
67.5°	428.4	402.7	376.8	351.0	325.2	299.3	273.3	247.3	221.3	195.3	190.3
70°	379.9	354.9	329.8	304.8	279.7	256.2	234.0	211.9	189.7	167.6	164.4
72.5°	333.7	309.6	285.7	261.6	237.6	216.7	199.0	181.2	163.3	145.6	142.9
75°	265.8	243.3	220.8	198.4	175.9	159.2	148.3	137.4	126.5	115.6	113.3
77.5°	199.1	179.4	159.7	140.0	120.2	107.7	102.5	97.2	91.9	86.7	85.4
80°	157.4	141.1	124.7	108.3	92.0	82.2	79.0	75.8	72.6	69.4	68.1
82.5°	119.3	106.5	93.8	81.0	68.2	60.7	58.5	56.4	54.2	52.0	51.3
85°	62.1	55.3	48.6	41.8	35.2	31.3	30.3	29.4	28.4	27.4	27.4
87.5°	18.6	16.9	15.3	13.4	11.6	10.8	11.4	12.2	12.8	12.9	12.5
90°	0.6	2.2	4.3	5.4	6.4	8.1	10.7	14.5	17.7	18.3	17.7
92.5°	6.6	9.4	13.3	15.7	19.3	24.4	36.6	53.6	68.9	69.8	59.0
95°	18.9	20.9	26.3	31.2	39.8	52.7	77.4	124.1	186.5	210.8	184.4
97.5°	30.6	33.6	39.2	46.6	56.5	71.1	102.2	167.3	270.9	359.7	377.3
100°	41.4	43.0	47.9	56.5	67.2	82.3	110.7	176.3	292.4	424.6	502.0
102.5°	51.3	52.5	57.3	65.9	77.1	92.1	118.5	176.7	284.3	426.8	548.5
105°	65.6	67.8	71.4	79.6	91.3	106.4	131.7	179.6	268.2	398.3	541.3
107.5°	81.1	82.8	86.4	93.9	105.6	120.7	145.2	186.9	260.2	367.8	494.1
110°	91.3	93.5	96.8	103.8	115.0	130.6	154.3	192.9	258.5	353.2	464.4



TEST NUMBER: P331746-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	100.9	103.0	106.6	113.2	124.0	140.1	162.9	199.4	259.0	343.7	443.7
115°	115.6	118.3	121.5	127.9	138.6	153.2	176.3	209.1	261.3	333.3	418.2
117.5°	130.8	133.0	136.2	141.9	152.2	167.3	188.7	219.4	265.1	328.2	402.1
120°	140.3	142.4	145.6	150.5	161.3	176.3	197.3	226.3	267.7	325.2	393.5
122.5°	149.3	151.1	154.3	159.6	170.3	185.8	205.5	232.3	270.7	323.5	386.2
125°	161.3	162.9	166.1	172.6	183.3	198.3	217.7	241.9	275.2	320.4	375.7
127.5°	170.7	172.9	177.4	184.5	194.8	210.3	229.1	250.8	279.8	318.6	366.1
130°	176.3	178.4	183.8	191.3	202.1	217.2	236.0	256.4	283.2	317.6	359.6
132.5°	181.4	184.1	189.8	197.8	209.0	224.0	242.0	262.0	286.7	317.3	354.4
135°	189.2	191.3	197.8	205.9	218.2	233.3	250.5	269.3	290.8	316.6	347.2
137.5°	196.5	199.1	205.6	214.1	226.4	240.3	257.4	274.8	294.5	316.5	342.1
140°	202.1	204.2	210.8	219.3	231.1	245.2	261.3	277.9	296.1	316.0	339.2
142.5°	207.7	209.4	215.5	224.0	235.4	248.5	264.3	280.5	297.5	316.0	336.2
145°	216.1	218.2	223.6	231.7	242.4	254.2	268.7	283.8	298.9	315.0	332.2
147.5°	225.1	226.7	231.9	239.3	248.3	258.7	272.4	285.7	299.3	313.0	328.1
150°	231.1	232.7	237.0	244.0	252.1	261.7	274.1	286.5	298.9	311.8	324.7
152.5°	237.1	237.9	242.2	248.4	256.0	264.8	275.9	286.9	298.0	309.6	321.7
155°	245.6	246.2	249.4	255.3	261.3	269.3	278.4	287.6	296.7	305.9	316.0
157.5°	252.7	253.3	255.9	261.0	265.8	272.5	280.2	287.6	294.3	302.0	310.8
160°	257.5	258.0	260.1	264.5	268.7	274.7	281.2	287.6	292.9	299.4	306.9
162.5°	262.2	261.8	264.0	267.5	271.4	276.0	281.5	287.1	291.6	297.3	303.5
165°	267.7	267.1	268.2	271.5	274.1	277.4	282.2	286.0	289.2	292.9	297.7
167.5°	272.2	271.5	272.5	274.6	276.5	278.5	282.1	285.2	286.7	289.2	292.2
170°	275.2	274.1	274.7	276.3	277.4	279.0	281.6	284.4	285.4	287.0	289.2
172.5°	276.9	276.3	276.0	277.6	278.2	279.4	281.3	283.0	283.7	284.5	286.2
175°	279.0	278.4	277.9	279.0	279.0	279.5	280.6	281.6	281.2	281.6	282.2
177.5°	279.9	279.1	278.6	279.5	279.5	279.5	279.9	280.8	279.9	279.5	279.9
180°	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5



TEST NUMBER: P331746-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1	1596.1
2.5°	1588.6	1591.1	1593.7	1594.7	1594.2	1593.7	1593.2	1592.7
5°	1575.9	1578.9	1581.7	1582.6	1581.7	1580.7	1579.8	1578.9
7.5°	1550.4	1551.2	1552.1	1551.7	1550.0	1548.3	1546.7	1545.0
10°	1524.8	1523.9	1523.0	1521.5	1519.6	1517.7	1515.7	1513.8
12.5°	1495.6	1493.8	1492.1	1489.7	1486.5	1483.3	1480.1	1476.9
15°	1441.0	1434.8	1428.7	1424.1	1420.9	1417.7	1414.5	1411.3
17.5°	1379.1	1371.9	1364.6	1358.2	1352.7	1347.2	1341.6	1336.1
20°	1336.0	1327.9	1319.9	1312.4	1305.3	1298.3	1291.2	1284.1
22.5°	1288.6	1278.3	1267.9	1260.1	1254.9	1249.6	1244.3	1239.1
25°	1210.1	1197.0	1183.8	1174.9	1170.0	1165.2	1160.4	1155.6
27.5°	1135.3	1119.9	1104.6	1093.1	1085.4	1077.8	1070.2	1062.5
30°	1082.4	1066.0	1049.6	1037.2	1028.5	1019.8	1011.2	1002.5
32.5°	1029.3	1010.6	991.8	978.5	970.3	962.1	953.9	945.8
35°	946.1	926.0	905.7	892.0	885.0	877.9	870.8	863.8
37.5°	865.2	842.9	820.6	805.4	797.4	789.3	781.2	773.1
40°	811.0	788.2	765.4	749.9	741.5	733.1	724.8	716.4
42.5°	756.3	732.7	709.2	693.3	685.2	677.1	669.1	661.0
45°	676.7	653.8	631.0	615.9	608.1	600.4	592.7	585.0
47.5°	599.2	576.6	553.8	539.0	532.1	525.1	518.0	511.0
50°	549.4	527.3	505.1	490.6	483.9	477.1	470.4	463.6
52.5°	502.4	481.0	459.7	445.8	439.6	433.4	427.2	420.9
55°	430.9	411.7	392.4	379.8	373.6	367.5	361.5	355.3
57.5°	366.0	348.3	330.6	319.2	314.1	309.0	303.9	298.7
60°	321.1	304.8	288.4	277.7	272.5	267.4	262.2	257.1
62.5°	282.3	266.6	251.1	241.7	238.7	235.5	232.4	229.4
65°	229.5	218.6	207.6	201.7	200.8	199.8	198.9	197.9
67.5°	185.3	180.3	175.2	172.2	171.3	170.2	169.2	168.1
70°	161.2	158.0	154.8	152.5	151.2	149.9	148.6	147.3
72.5°	140.3	137.5	134.8	133.1	132.3	131.6	130.7	130.0
75°	111.0	108.9	106.6	105.3	105.0	104.6	104.3	104.0
77.5°	84.1	82.8	81.5	80.6	80.1	79.6	79.1	78.6
80°	66.7	65.5	64.2	63.5	63.5	63.5	63.5	63.5
82.5°	50.4	49.7	48.9	48.5	48.5	48.5	48.5	48.5
85°	27.4	27.4	27.4	27.4	27.4	27.4	27.4	27.4
87.5°	12.2	11.7	11.7	11.6	11.6	11.6	11.6	11.6
90°	17.2	16.1	17.2	17.7	17.7	17.7	17.7	17.7
92.5°	46.8	40.2	35.7	32.3	32.0	30.3	30.6	29.8
95°	140.8	108.0	85.5	73.6	66.6	62.4	60.7	61.3
97.5°	328.7	268.9	210.8	171.9	146.2	133.0	125.2	120.6
100°	490.8	424.1	350.4	285.4	240.8	217.7	202.1	192.5
102.5°	597.0	581.9	528.1	459.1	410.7	371.2	351.8	338.7
105°	653.1	713.8	720.9	703.0	669.8	636.4	613.3	605.8
107.5°	612.7	704.2	760.1	786.1	790.2	788.4	783.8	773.8
110°	577.9	674.0	742.8	786.9	810.0	820.3	825.1	824.5



TEST NUMBER: P331746-830

CATALOG NUMBER: SA2XXRDIP-C1005D530U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	546.0	638.4	711.9	762.4	794.6	811.6	820.8	823.7
115°	506.9	589.7	660.1	715.5	753.6	778.4	792.3	797.1
117.5°	477.4	550.1	614.0	665.9	704.8	730.9	745.6	749.7
120°	462.8	529.4	586.4	635.4	673.0	698.2	713.8	719.2
122.5°	451.2	512.3	566.2	610.4	644.1	669.0	682.9	687.4
125°	434.3	489.7	537.0	577.3	608.5	628.9	642.3	646.7
127.5°	417.6	467.8	512.4	549.6	576.7	595.9	607.5	611.0
130°	406.9	453.2	495.6	531.0	557.4	575.7	586.4	590.7
132.5°	396.6	439.4	478.4	511.7	537.6	555.9	565.8	569.7
135°	382.2	417.6	453.2	483.2	506.3	524.1	533.8	535.9
137.5°	370.7	400.4	428.5	454.8	475.8	491.1	499.5	502.8
140°	363.4	389.2	413.9	437.5	454.8	468.7	476.7	480.0
142.5°	357.3	379.3	400.6	420.4	436.7	449.4	456.6	457.2
145°	348.8	366.6	383.2	398.9	411.7	420.8	426.2	427.8
147.5°	342.3	356.3	369.3	380.7	391.3	398.6	402.3	403.2
150°	337.5	349.4	360.7	370.3	378.4	384.8	388.0	388.6
152.5°	332.8	343.8	353.4	361.7	368.1	373.7	376.1	376.2
155°	326.3	334.9	342.9	348.8	354.8	358.5	360.7	359.6
157.5°	318.7	325.8	332.6	337.2	341.4	344.6	345.5	345.5
160°	313.9	319.8	325.7	329.5	333.3	335.9	336.5	336.5
162.5°	309.2	314.2	319.3	322.2	325.9	327.8	328.3	327.9
165°	302.1	305.9	309.6	311.8	313.9	316.0	316.0	315.6
167.5°	295.3	298.2	300.8	302.7	303.7	304.9	304.8	304.2
170°	291.9	293.5	295.7	296.7	297.3	298.9	298.3	297.3
172.5°	288.0	289.2	290.9	291.5	292.1	292.8	292.3	291.6
175°	283.8	284.4	284.9	285.4	285.4	286.0	285.4	284.4
177.5°	280.8	280.8	281.3	281.3	281.3	281.3	280.8	279.9
180°	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5

(END OF REPORT)