

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333569-840

Luminaire Tested: **S125RDIP-S850D1035U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333569-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S850D1035U840-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6927.4 lumens
Efficiency: N/A
Efficacy: 133.2 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333569-840

CATALOG NUMBER: S125RDIP-S850D1035U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333569-840

CATALOG NUMBER: S125RDIP-S850D1035U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48
1	98	94	90	86	90	86	83	80	73	70	68	60	58	57	48	47	47	41
2	89	82	76	71	82	76	71	66	64	60	57	53	51	48	43	41	40	35
3	82	72	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34	30
4	75	64	57	51	69	60	53	48	51	46	41	42	39	36	35	32	30	26
5	69	57	49	44	63	53	46	41	45	40	36	38	34	31	31	28	26	23
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20
7	59	47	39	33	54	43	36	31	37	32	28	31	27	24	26	23	21	18
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	18	16
9	51	39	31	26	47	36	29	25	31	26	22	26	22	19	22	19	17	14
10	47	35	28	24	44	33	27	22	29	23	20	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8250	8250	8250	8250
5°	9491	8261	7295	8261
10°	10887	8218	6437	8218
15°	11760	8134	5722	8134
20°	12967	8036	5283	8036
25°	15007	7906	4903	7906
30°	16330	7770	4653	7770
35°	13775	7611	4424	7611
40°	9620	7325	4226	7325
45°	7136	6940	4032	6940
50°	5690	6539	3867	6539
55°	4829	6040	3719	6040
60°	4173	5594	3481	5594
65°	3718	5113	2997	5113
70°	3269	4683	2732	4683
75°	2827	4057	2565	4057
80°	2146	3414	2146	3414
85°	1786	2682	2023	2682



TEST NUMBER: P333569-840

CATALOG NUMBER: S125RDIP-S850D1035U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.5	1.8
10°-20°	359.0	5.2
20°-30°	569.2	8.2
30°-40°	686.4	9.9
40°-50°	613.0	8.8
50°-60°	470.0	6.8
60°-70°	305.5	4.4
70°-80°	148.5	2.1
80°-90°	38.3	0.6
90°-100°	86.8	1.3
100°-110°	256.2	3.7
110°-120°	434.0	6.3
120°-130°	571.2	8.2
130°-140°	640.0	9.2
140°-150°	627.3	9.1
150°-160°	526.9	7.6
160°-170°	350.2	5.1
170°-180°	122.6	1.8
0°-30°	1050.6	15.2
0°-40°	1737.0	25.1
0°-60°	2820.0	40.7
0°-90°	3312.3	47.8
90°-120°	777.0	11.2
90°-150°	2615.5	37.8
90°-180°	3615.0	52.2
0°-180°	6927.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1277	1277	1277	1277	1277	
5°	1464	1274	1125	1274	1464	146
15°	1759	1217	856	1217	1759	504
25°	2106	1110	688	1110	2106	967
35°	1747	965	561	965	1747	1055
45°	781	760	442	760	781	623
55°	429	536	330	536	429	389
65°	243	335	196	335	243	242
75°	113	163	103	163	113	121
85°	24	36	27	36	24	28
90°	24	1	24	1	24	15
95°	87	66	87	66	87	88
105°	250	230	250	230	250	265
115°	439	434	439	434	439	434
125°	638	634	638	634	638	570
135°	828	825	828	825	828	638
145°	1003	999	1003	999	1003	626
155°	1143	1143	1143	1143	1143	526
165°	1240	1243	1240	1243	1240	350
175°	1288	1292	1288	1292	1288	122
180°	1296	1296	1296	1296	1296	



TEST NUMBER: P333569-840

CATALOG NUMBER: S125RDIP-S850D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4
2.5°	1343.6	1342.8	1344.5	1339.9	1340.3	1333.1	1333.1	1327.7	1320.6	1315.1	1312.6
5°	1464.0	1465.1	1463.0	1455.1	1449.9	1442.0	1433.1	1417.3	1404.2	1391.7	1381.7
7.5°	1588.0	1588.7	1581.9	1579.4	1566.2	1556.5	1536.7	1515.3	1496.3	1472.2	1453.8
10°	1660.1	1659.6	1652.3	1646.5	1635.0	1620.3	1600.9	1575.7	1552.2	1525.9	1500.8
12.5°	1702.1	1700.7	1698.4	1691.4	1680.7	1667.7	1651.2	1626.5	1597.4	1568.7	1539.3
15°	1758.8	1755.0	1748.3	1739.3	1724.1	1708.9	1690.6	1668.6	1640.7	1608.2	1580.9
17.5°	1828.8	1828.9	1818.5	1806.0	1785.3	1758.6	1730.2	1694.7	1656.9	1621.1	1592.1
20°	1886.7	1885.1	1874.6	1850.5	1826.9	1793.3	1760.8	1717.3	1671.1	1624.5	1588.3
22.5°	1969.7	1965.7	1954.8	1923.1	1886.5	1843.3	1793.5	1740.4	1684.6	1631.6	1584.2
25°	2105.9	2102.7	2081.2	2044.6	1993.2	1926.5	1861.5	1788.7	1708.4	1638.7	1580.9
27.5°	2199.0	2195.5	2179.6	2149.1	2101.7	2031.6	1943.6	1846.2	1746.1	1650.1	1566.9
30°	2189.8	2197.7	2195.5	2181.4	2145.8	2082.8	2001.6	1892.0	1772.9	1660.1	1561.0
32.5°	2058.0	2065.1	2083.6	2111.3	2113.4	2088.3	2027.5	1926.3	1803.1	1674.9	1556.4
35°	1747.2	1756.7	1792.3	1848.5	1921.8	1983.2	1995.8	1941.3	1830.6	1692.6	1549.5
37.5°	1343.2	1394.8	1424.8	1483.9	1594.8	1707.7	1816.2	1856.1	1809.1	1685.4	1538.3
40°	1141.0	1153.6	1207.1	1273.7	1367.1	1484.5	1639.2	1750.9	1754.5	1668.6	1520.7
42.5°	976.5	992.5	1029.3	1082.4	1162.4	1279.8	1439.5	1586.9	1655.2	1622.4	1497.6
45°	781.3	793.3	820.1	861.0	922.4	1019.4	1156.8	1327.2	1462.5	1515.4	1435.7
47.5°	641.9	648.3	671.7	702.8	748.2	818.9	925.2	1073.2	1235.5	1349.2	1338.0
50°	566.3	573.7	591.5	615.1	653.4	713.2	798.1	921.3	1088.6	1227.6	1255.4
52.5°	507.6	513.7	524.8	547.1	578.7	624.6	693.2	804.7	955.2	1103.0	1167.2
55°	428.9	433.1	442.0	454.6	479.8	512.8	572.1	649.1	770.8	919.8	1014.1
57.5°	364.2	366.2	371.9	383.5	400.9	425.1	467.9	533.2	620.5	754.6	858.7
60°	323.1	325.1	332.4	340.3	354.0	376.0	409.5	455.1	539.1	649.6	755.1
62.5°	290.3	291.5	294.7	302.6	314.5	331.5	357.9	395.2	461.9	559.1	658.6
65°	243.3	243.9	244.9	251.2	258.5	271.1	288.4	314.6	365.0	438.4	526.4
67.5°	198.2	198.9	202.6	204.8	212.5	219.0	229.2	249.3	284.8	334.3	402.7
70°	173.1	172.5	176.2	178.8	181.5	189.2	196.1	212.4	234.4	272.2	329.3
72.5°	149.6	148.1	149.8	150.7	154.2	159.6	166.3	176.3	193.3	219.2	263.1
75°	113.3	113.8	113.8	114.8	117.4	119.6	121.7	126.9	136.3	153.6	177.2
77.5°	79.5	78.7	80.9	81.2	82.7	85.0	86.8	89.0	92.8	100.0	112.1
80°	57.7	57.7	58.2	59.8	59.3	60.3	62.9	65.0	69.8	73.9	78.2
82.5°	44.2	43.8	44.3	44.6	44.5	45.6	46.6	47.0	48.8	50.9	53.8
85°	24.1	24.1	24.6	24.6	25.1	25.1	25.7	25.7	25.7	26.3	26.8
87.5°	14.0	13.5	12.9	12.8	13.1	13.7	13.1	12.5	12.2	12.0	12.1
90°	24.2	23.5	22.8	22.2	21.5	20.6	19.5	18.4	17.3	16.2	14.5
92.5°	47.6	47.1	46.6	46.2	45.6	44.6	43.1	41.7	40.2	38.7	36.8
95°	86.7	86.2	85.8	85.3	84.9	83.9	82.3	80.8	79.2	77.7	75.4
97.5°	131.5	131.2	131.0	130.7	130.4	129.6	128.1	126.5	125.1	123.6	120.5
100°	165.3	164.9	164.4	164.0	163.6	162.3	160.3	158.2	156.2	154.2	151.4
102.5°	199.2	198.6	197.9	197.3	196.7	195.3	193.1	190.9	188.7	186.5	185.0
105°	250.0	249.3	248.7	248.0	247.3	246.3	245.0	243.7	242.3	241.0	239.6
107.5°	302.1	302.2	302.2	302.2	302.3	301.9	301.2	300.5	299.9	299.2	298.2
110°	340.7	341.0	341.2	341.4	341.6	341.4	340.7	340.1	339.4	338.7	338.1



TEST NUMBER: P333569-840

CATALOG NUMBER: S125RDIP-S850D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	378.7	379.1	379.5	379.9	380.3	380.3	380.0	379.7	379.4	379.1	378.2
115°	438.6	438.8	439.0	439.2	439.5	439.7	439.9	440.1	440.4	440.6	440.1
117.5°	497.1	498.0	498.9	499.7	500.6	501.0	500.8	500.6	500.5	500.3	499.9
120°	537.3	538.3	539.2	540.1	541.0	541.4	541.4	541.4	541.4	541.4	541.2
122.5°	577.7	578.5	579.2	579.9	580.6	581.0	581.2	581.4	581.6	581.7	581.2
125°	638.2	638.4	638.6	638.8	639.0	639.4	639.9	640.4	640.8	641.3	641.0
127.5°	696.3	696.7	697.1	697.6	698.0	698.4	698.6	698.8	699.0	699.3	699.0
130°	735.0	735.4	735.9	736.3	736.8	737.1	737.3	737.5	737.8	738.0	737.5
132.5°	771.2	771.9	772.5	773.2	773.8	774.2	774.5	774.7	774.9	775.1	775.2
135°	827.7	828.6	829.5	830.4	831.3	831.7	831.7	831.7	831.7	831.7	831.5
137.5°	883.0	884.1	885.2	886.4	887.5	887.9	887.6	887.4	887.1	886.8	886.4
140°	918.5	919.6	920.7	921.8	922.9	923.3	922.8	922.4	921.9	921.5	920.8
142.5°	952.3	953.5	954.6	955.7	956.8	957.3	956.9	956.7	956.4	956.1	955.3
145°	1003.2	1003.8	1004.5	1005.2	1005.8	1006.2	1006.2	1006.2	1006.2	1006.2	1005.5
147.5°	1046.5	1048.0	1049.6	1051.1	1052.6	1053.1	1052.6	1052.0	1051.5	1051.0	1050.4
150°	1078.7	1079.2	1079.6	1080.2	1080.6	1080.8	1080.8	1080.8	1080.8	1080.8	1079.8
152.5°	1105.4	1106.2	1107.0	1107.8	1108.6	1108.7	1108.2	1107.7	1107.1	1106.6	1106.2
155°	1143.3	1144.4	1145.5	1146.7	1147.8	1147.9	1147.0	1146.1	1145.2	1144.3	1144.1
157.5°	1175.0	1176.4	1177.9	1179.4	1180.8	1181.1	1180.2	1179.3	1178.5	1177.6	1177.4
160°	1196.7	1197.9	1199.0	1200.1	1201.2	1201.3	1200.4	1199.5	1198.6	1197.7	1197.5
162.5°	1215.3	1216.6	1217.9	1219.2	1220.5	1220.6	1219.5	1218.4	1217.4	1216.3	1216.3
165°	1240.1	1241.4	1242.7	1244.2	1245.5	1245.7	1244.8	1243.9	1243.0	1242.1	1241.8
167.5°	1259.8	1261.2	1262.6	1264.0	1265.4	1265.5	1264.0	1262.7	1261.4	1260.0	1260.0
170°	1270.3	1271.9	1273.4	1275.1	1276.6	1276.7	1275.4	1274.0	1272.7	1271.3	1271.3
172.5°	1279.2	1280.6	1282.0	1283.3	1284.8	1284.8	1283.4	1282.1	1280.7	1279.4	1279.4
175°	1287.5	1289.0	1290.6	1292.2	1293.7	1293.8	1292.5	1291.2	1289.8	1288.5	1288.5
177.5°	1292.3	1293.5	1294.8	1296.1	1297.4	1297.4	1296.4	1295.3	1294.2	1293.1	1293.3
180°	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6



TEST NUMBER: P333569-840

CATALOG NUMBER: S125RDIP-S850D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4
2.5°	1312.6	1309.7	1304.2	1299.2	1292.9	1287.5	1283.6	1279.1	1273.1	1266.1	1260.2
5°	1370.7	1359.2	1343.9	1330.9	1314.0	1301.0	1287.4	1274.2	1261.1	1244.4	1229.6
7.5°	1435.1	1411.3	1388.2	1359.0	1332.5	1308.9	1286.3	1263.3	1240.9	1217.1	1194.1
10°	1474.5	1445.7	1413.7	1377.0	1343.4	1311.4	1282.1	1253.2	1222.8	1196.1	1167.2
12.5°	1511.5	1474.2	1437.6	1391.3	1351.0	1311.9	1274.6	1238.6	1206.1	1171.3	1140.4
15°	1544.8	1508.1	1467.2	1410.6	1354.4	1307.3	1263.2	1216.6	1176.2	1137.4	1102.8
17.5°	1557.7	1519.2	1471.7	1417.2	1355.9	1296.6	1239.8	1188.6	1141.1	1095.9	1057.0
20°	1552.7	1515.4	1466.6	1414.7	1349.2	1287.4	1226.0	1169.3	1116.4	1068.6	1027.2
22.5°	1540.4	1502.0	1454.9	1400.1	1337.9	1272.2	1206.7	1146.3	1090.8	1041.4	996.2
25°	1522.3	1469.9	1421.6	1368.1	1308.8	1243.9	1176.2	1109.5	1050.4	1000.0	950.7
27.5°	1503.3	1437.8	1376.4	1323.3	1260.7	1202.6	1137.5	1069.1	1006.9	955.6	905.0
30°	1486.1	1412.7	1345.0	1284.8	1225.5	1170.4	1108.5	1041.9	978.0	925.0	873.6
32.5°	1464.7	1386.6	1312.3	1242.7	1185.6	1130.9	1075.0	1011.3	949.0	894.3	842.1
35°	1437.8	1338.2	1257.5	1183.5	1120.0	1067.1	1016.7	965.3	902.9	846.4	795.5
37.5°	1402.6	1289.5	1196.1	1115.6	1048.6	995.4	955.7	908.8	851.8	797.6	750.3
40°	1381.2	1254.3	1152.1	1072.4	1002.1	945.9	908.8	868.9	817.0	766.1	718.9
42.5°	1352.7	1222.0	1107.6	1024.5	953.8	899.8	862.1	827.4	783.9	735.9	685.4
45°	1296.8	1159.4	1039.4	950.2	878.9	825.9	790.7	759.8	726.8	682.8	638.6
47.5°	1224.0	1094.1	968.4	871.1	801.2	752.0	718.0	693.6	669.9	632.5	589.7
50°	1165.7	1040.4	917.7	823.2	748.8	702.2	670.1	650.8	629.2	595.1	559.5
52.5°	1096.9	985.0	864.7	768.3	698.0	654.3	623.6	604.2	586.4	558.7	524.7
55°	988.5	890.4	780.2	692.7	628.2	584.1	554.8	536.4	525.9	502.3	475.6
57.5°	863.3	793.0	695.9	611.5	554.5	511.0	489.5	473.8	462.0	445.2	426.5
60°	776.1	726.8	639.7	559.5	507.1	465.6	446.3	433.1	422.1	408.0	393.2
62.5°	687.5	651.7	575.9	507.1	458.8	424.1	406.0	394.2	381.4	371.9	357.6
65°	569.0	536.9	484.5	430.5	386.0	358.1	345.1	334.6	326.7	316.2	306.2
67.5°	442.5	429.6	393.3	356.2	324.2	299.4	288.1	280.7	271.4	265.0	258.2
70°	365.0	358.7	333.0	308.3	278.4	261.7	251.2	248.0	236.5	230.2	225.5
72.5°	296.2	293.3	278.4	261.4	240.2	225.6	215.9	212.4	205.0	200.0	196.9
75°	202.9	204.0	201.4	190.4	182.5	173.1	164.6	162.6	157.3	153.1	150.5
77.5°	128.4	133.7	133.9	133.4	130.3	124.5	121.0	119.5	114.3	112.7	112.1
80°	88.1	93.8	99.1	98.6	97.6	95.9	93.3	91.8	89.2	87.6	86.5
82.5°	58.8	64.1	68.5	71.3	71.1	69.6	67.8	67.1	66.4	65.3	65.1
85°	27.8	28.9	30.4	34.1	36.7	37.3	36.7	36.2	34.6	35.1	35.6
87.5°	12.2	11.9	12.0	11.7	10.9	12.6	13.5	13.6	13.1	12.6	12.2
90°	13.0	11.4	9.9	8.2	6.4	4.5	2.8	1.0	2.8	4.5	6.4
92.5°	34.8	32.9	31.0	29.4	28.2	26.9	25.7	24.4	25.7	26.9	28.2
95°	73.1	70.9	68.7	67.4	66.9	66.4	65.9	65.5	65.9	66.4	66.9
97.5°	117.4	114.3	111.3	109.6	109.5	109.3	109.1	108.9	109.1	109.3	109.5
100°	148.5	145.5	142.6	141.2	141.2	141.2	141.2	141.2	141.2	141.2	141.2
102.5°	183.6	182.1	180.6	179.5	178.5	177.6	176.7	175.8	176.7	177.6	178.5
105°	238.2	236.9	235.6	234.4	233.3	232.1	231.0	229.8	231.0	232.1	233.3
107.5°	297.2	296.1	295.1	294.1	293.0	291.8	290.6	289.5	290.6	291.8	293.0
110°	337.4	336.7	336.1	335.2	334.1	333.0	331.8	330.7	331.8	333.0	334.1



TEST NUMBER: P333569-840

CATALOG NUMBER: S125RDIP-S850D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	377.4	376.6	375.7	375.0	374.4	373.8	373.2	372.6	373.2	373.8	374.4
115°	439.7	439.2	438.8	438.1	437.3	436.4	435.5	434.5	435.5	436.4	437.3
117.5°	499.5	499.1	498.7	498.3	497.9	497.5	497.1	496.7	497.1	497.5	497.9
120°	541.0	540.7	540.5	539.9	538.8	537.6	536.4	535.3	536.4	537.6	538.8
122.5°	580.6	580.0	579.4	579.0	578.6	578.1	577.7	577.3	577.7	578.1	578.6
125°	640.8	640.6	640.4	639.5	638.2	636.8	635.5	634.2	635.5	636.8	638.2
127.5°	698.7	698.5	698.2	697.7	696.9	696.2	695.4	694.7	695.4	696.2	696.9
130°	737.1	736.7	736.2	735.4	734.3	733.2	732.1	730.9	732.1	733.2	734.3
132.5°	775.3	775.4	775.5	774.6	772.7	770.9	769.1	767.2	769.1	770.9	772.7
135°	831.3	831.1	830.9	830.1	828.7	827.4	826.1	824.8	826.1	827.4	828.7
137.5°	885.9	885.3	884.8	883.9	882.6	881.3	880.0	878.8	880.0	881.3	882.6
140°	920.2	919.5	918.8	917.9	916.8	915.6	914.5	913.4	914.5	915.6	916.8
142.5°	954.5	953.6	952.8	951.9	950.9	950.0	949.1	948.1	949.1	950.0	950.9
145°	1004.8	1004.2	1003.5	1002.7	1001.8	1000.9	1000.1	999.2	1000.1	1000.9	1001.8
147.5°	1049.9	1049.4	1048.8	1048.2	1047.8	1047.3	1046.8	1046.3	1046.8	1047.3	1047.8
150°	1079.0	1078.1	1077.2	1076.9	1077.1	1077.3	1077.5	1077.7	1077.5	1077.3	1077.1
152.5°	1105.9	1105.5	1105.2	1104.8	1104.5	1104.2	1103.9	1103.6	1103.9	1104.2	1104.5
155°	1143.9	1143.7	1143.4	1143.3	1143.3	1143.3	1143.3	1143.3	1143.3	1143.3	1143.3
157.5°	1177.1	1176.9	1176.7	1176.8	1177.3	1177.8	1178.3	1178.8	1178.3	1177.8	1177.3
160°	1197.3	1197.1	1196.9	1197.1	1197.7	1198.4	1199.1	1199.7	1199.1	1198.4	1197.7
162.5°	1216.2	1216.2	1216.1	1216.4	1216.8	1217.3	1217.8	1218.3	1217.8	1217.3	1216.8
165°	1241.6	1241.4	1241.2	1241.3	1241.7	1242.2	1242.6	1243.1	1242.6	1242.2	1241.7
167.5°	1260.0	1260.0	1260.0	1260.5	1261.4	1262.3	1263.1	1264.0	1263.1	1262.3	1261.4
170°	1271.3	1271.3	1271.3	1271.8	1272.7	1273.5	1274.4	1275.4	1274.4	1273.5	1272.7
172.5°	1279.4	1279.4	1279.4	1279.9	1280.7	1281.6	1282.5	1283.4	1282.5	1281.6	1280.7
175°	1288.5	1288.5	1288.5	1288.9	1289.8	1290.7	1291.6	1292.5	1291.6	1290.7	1289.8
177.5°	1293.4	1293.6	1293.8	1294.2	1294.9	1295.8	1296.5	1297.2	1296.5	1295.8	1294.9
180°	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6



TEST NUMBER: P333569-840

CATALOG NUMBER: S125RDIP-S850D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4
2.5°	1256.0	1250.1	1245.9	1237.5	1231.6	1229.1	1224.6	1223.2	1227.9	1224.6	1224.1
5°	1218.6	1203.5	1191.3	1179.3	1166.2	1157.8	1145.2	1143.2	1139.9	1135.3	1134.2
7.5°	1173.9	1154.1	1138.5	1118.6	1101.3	1087.3	1071.6	1064.2	1060.1	1054.0	1045.8
10°	1143.7	1120.0	1099.0	1079.1	1057.6	1040.4	1024.6	1012.6	1004.7	997.3	994.2
12.5°	1113.9	1089.8	1063.0	1038.8	1014.9	995.4	978.1	970.2	961.5	952.9	945.5
15°	1067.6	1035.6	1006.2	978.5	958.1	937.1	920.3	908.8	895.6	891.9	877.8
17.5°	1018.5	987.1	952.8	923.5	899.8	876.8	858.3	845.2	835.4	821.8	815.3
20°	988.0	950.7	917.2	890.4	864.1	836.9	818.0	807.0	797.6	786.6	781.3
22.5°	955.2	918.8	884.4	853.0	826.4	799.6	786.2	774.7	764.0	753.9	746.9
25°	907.2	870.5	834.2	801.7	774.0	754.6	738.8	725.7	719.9	710.0	702.7
27.5°	859.7	820.6	783.0	750.7	728.9	709.7	696.8	686.4	676.0	667.3	661.0
30°	829.0	789.2	748.3	722.6	699.5	681.2	667.0	657.0	649.1	641.3	636.6
32.5°	798.4	757.3	721.0	693.2	671.4	655.6	641.0	631.5	623.2	614.5	608.9
35°	749.3	707.4	678.0	650.8	629.2	614.6	604.6	591.0	584.1	577.8	572.1
37.5°	703.7	664.7	632.9	609.0	590.4	575.7	562.9	555.5	547.1	541.5	536.6
40°	670.1	634.5	605.6	580.5	566.8	550.6	538.6	529.1	522.8	515.4	510.2
42.5°	640.0	606.8	578.8	556.1	539.2	525.4	513.8	504.3	496.3	491.1	486.8
45°	597.2	564.2	536.9	515.9	500.3	487.2	475.0	470.4	459.9	453.6	451.5
47.5°	553.1	523.5	497.3	477.9	461.8	449.4	438.1	428.4	422.6	416.5	413.1
50°	523.3	495.0	470.4	451.5	435.8	422.1	411.6	405.4	397.5	391.7	387.5
52.5°	493.5	467.4	442.7	424.6	411.0	397.4	385.7	379.3	371.9	368.2	365.3
55°	451.0	423.1	402.2	384.4	370.2	357.6	346.6	340.3	335.6	331.9	330.8
57.5°	402.7	380.7	361.2	345.2	330.4	318.6	308.9	303.0	298.8	298.2	295.1
60°	371.2	351.3	333.5	316.2	303.6	292.6	284.2	277.4	273.2	272.7	271.7
62.5°	339.8	320.7	304.2	288.9	277.6	267.0	259.0	251.4	248.8	246.2	244.0
65°	293.2	275.8	262.2	250.1	238.0	229.1	221.3	216.5	210.8	207.6	201.9
67.5°	247.3	233.9	220.8	210.6	201.2	192.7	186.1	179.2	175.2	172.7	168.5
70°	217.1	206.6	193.5	182.5	175.1	168.3	163.1	155.2	152.6	150.5	148.3
72.5°	188.5	179.4	168.3	159.5	152.1	145.6	139.6	135.9	133.3	131.2	130.0
75°	148.3	139.5	130.1	123.7	118.6	113.3	110.1	107.4	106.4	105.9	103.8
77.5°	109.0	104.2	96.6	91.7	88.2	86.1	83.3	81.9	81.8	79.5	78.8
80°	83.4	80.8	74.4	72.4	69.8	67.7	66.0	63.4	60.8	59.8	58.2
82.5°	62.0	59.4	56.9	53.5	51.3	50.0	48.5	47.5	47.9	46.4	45.6
85°	33.0	30.4	29.4	28.9	27.8	28.9	28.3	27.8	27.3	26.8	27.3
87.5°	12.1	12.4	12.3	13.5	12.5	13.3	13.5	13.3	13.5	13.7	13.5
90°	8.2	9.9	11.4	13.0	14.5	16.2	17.3	18.4	19.5	20.6	21.5
92.5°	29.4	31.0	32.9	34.8	36.8	38.7	40.2	41.7	43.1	44.6	45.6
95°	67.4	68.7	70.9	73.1	75.4	77.7	79.2	80.8	82.3	83.9	84.9
97.5°	109.6	111.3	114.3	117.4	120.5	123.6	125.1	126.5	128.1	129.6	130.4
100°	141.2	142.6	145.5	148.5	151.4	154.2	156.2	158.2	160.3	162.3	163.6
102.5°	179.5	180.6	182.1	183.6	185.0	186.5	188.7	190.9	193.1	195.3	196.7
105°	234.4	235.6	236.9	238.2	239.6	241.0	242.3	243.7	245.0	246.3	247.3
107.5°	294.1	295.1	296.1	297.2	298.2	299.2	299.9	300.5	301.2	301.9	302.3
110°	335.2	336.1	336.7	337.4	338.1	338.7	339.4	340.1	340.7	341.4	341.6



TEST NUMBER: P333569-840

CATALOG NUMBER: S125RDIP-S850D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	375.0	375.7	376.6	377.4	378.2	379.1	379.4	379.7	380.0	380.3	380.3
115°	438.1	438.8	439.2	439.7	440.1	440.6	440.4	440.1	439.9	439.7	439.5
117.5°	498.3	498.7	499.1	499.5	499.9	500.3	500.5	500.6	500.8	501.0	500.6
120°	539.9	540.5	540.7	541.0	541.2	541.4	541.4	541.4	541.4	541.4	541.0
122.5°	579.0	579.4	580.0	580.6	581.2	581.7	581.6	581.4	581.2	581.0	580.6
125°	639.5	640.4	640.6	640.8	641.0	641.3	640.8	640.4	639.9	639.4	639.0
127.5°	697.7	698.2	698.5	698.7	699.0	699.3	699.0	698.8	698.6	698.4	698.0
130°	735.4	736.2	736.7	737.1	737.5	738.0	737.8	737.5	737.3	737.1	736.8
132.5°	774.6	775.5	775.4	775.3	775.2	775.1	774.9	774.7	774.5	774.2	773.8
135°	830.1	830.9	831.1	831.3	831.5	831.7	831.7	831.7	831.7	831.7	831.3
137.5°	883.9	884.8	885.3	885.9	886.4	886.8	887.1	887.4	887.6	887.9	887.5
140°	917.9	918.8	919.5	920.2	920.8	921.5	921.9	922.4	922.8	923.3	922.9
142.5°	951.9	952.8	953.6	954.5	955.3	956.1	956.4	956.7	956.9	957.3	956.8
145°	1002.7	1003.5	1004.2	1004.8	1005.5	1006.2	1006.2	1006.2	1006.2	1006.2	1005.8
147.5°	1048.2	1048.8	1049.4	1049.9	1050.4	1051.0	1051.5	1052.0	1052.6	1053.1	1052.6
150°	1076.9	1077.2	1078.1	1079.0	1079.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.6
152.5°	1104.8	1105.2	1105.5	1105.9	1106.2	1106.6	1107.1	1107.7	1108.2	1108.7	1108.6
155°	1143.3	1143.4	1143.7	1143.9	1144.1	1144.3	1145.2	1146.1	1147.0	1147.9	1147.8
157.5°	1176.8	1176.7	1176.9	1177.1	1177.4	1177.6	1178.5	1179.3	1180.2	1181.1	1180.8
160°	1197.1	1196.9	1197.1	1197.3	1197.5	1197.7	1198.6	1199.5	1200.4	1201.3	1201.2
162.5°	1216.4	1216.1	1216.2	1216.2	1216.3	1216.3	1217.4	1218.4	1219.5	1220.6	1220.5
165°	1241.3	1241.2	1241.4	1241.6	1241.8	1242.1	1243.0	1243.9	1244.8	1245.7	1245.5
167.5°	1260.5	1260.0	1260.0	1260.0	1260.0	1260.0	1261.4	1262.7	1264.0	1265.5	1265.4
170°	1271.8	1271.3	1271.3	1271.3	1271.3	1271.3	1272.7	1274.0	1275.4	1276.7	1276.6
172.5°	1279.9	1279.4	1279.4	1279.4	1279.4	1279.4	1280.7	1282.1	1283.4	1284.8	1284.8
175°	1288.9	1288.5	1288.5	1288.5	1288.5	1288.5	1289.8	1291.2	1292.5	1293.8	1293.7
177.5°	1294.2	1293.8	1293.6	1293.4	1293.3	1293.1	1294.2	1295.3	1296.4	1297.4	1297.4
180°	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6



TEST NUMBER: P333569-840

CATALOG NUMBER: S125RDIP-S850D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4
2.5°	1223.7	1219.1	1217.8	1219.5	1217.8	1219.1	1223.7	1224.1	1224.6	1227.9	1223.2
5°	1128.9	1123.8	1126.3	1125.3	1126.3	1123.8	1128.9	1134.2	1135.3	1139.9	1143.2
7.5°	1045.7	1039.2	1032.3	1034.5	1032.3	1039.2	1045.7	1045.8	1054.0	1060.1	1064.2
10°	987.3	982.2	979.0	981.6	979.0	982.2	987.3	994.2	997.3	1004.7	1012.6
12.5°	938.3	935.1	932.4	931.3	932.4	935.1	938.3	945.5	952.9	961.5	970.2
15°	871.5	865.3	862.6	855.8	862.6	865.3	871.5	877.8	891.9	895.6	908.8
17.5°	809.9	807.9	801.0	798.1	801.0	807.9	809.9	815.3	821.8	835.4	845.2
20°	773.5	771.3	764.6	768.7	764.6	771.3	773.5	781.3	786.6	797.6	807.0
22.5°	743.3	738.6	736.4	735.2	736.4	738.6	743.3	746.9	753.9	764.0	774.7
25°	700.5	693.8	691.2	688.0	691.2	693.8	700.5	702.7	710.0	719.9	725.7
27.5°	658.0	654.3	650.9	650.1	650.9	654.3	658.0	661.0	667.3	676.0	686.4
30°	630.3	626.6	624.0	624.0	624.0	626.6	630.3	636.6	641.3	649.1	657.0
32.5°	605.5	602.7	600.1	599.7	600.1	602.7	605.5	608.9	614.5	623.2	631.5
35°	569.5	565.3	564.2	561.1	564.2	565.3	569.5	572.1	577.8	584.1	591.0
37.5°	532.0	528.6	528.5	528.2	528.5	528.6	532.0	536.6	541.5	547.1	555.5
40°	508.2	505.5	504.9	501.3	504.9	505.5	508.2	510.2	515.4	522.8	529.1
42.5°	482.5	481.2	479.4	477.8	479.4	481.2	482.5	486.8	491.1	496.3	504.3
45°	447.8	444.1	444.1	441.5	444.1	444.1	447.8	451.5	453.6	459.9	470.4
47.5°	411.9	409.1	409.4	406.7	409.4	409.1	411.9	413.1	416.5	422.6	428.4
50°	388.0	386.5	386.0	384.9	386.0	386.5	388.0	387.5	391.7	397.5	405.4
52.5°	364.2	363.3	365.4	363.0	365.4	363.3	364.2	365.3	368.2	371.9	379.3
55°	331.9	330.3	333.5	330.3	333.5	330.3	331.9	330.8	331.9	335.6	340.3
57.5°	294.9	293.5	296.3	294.7	296.3	293.5	294.9	295.1	298.2	298.8	303.0
60°	270.5	267.4	269.0	269.5	269.0	267.4	270.5	271.7	272.7	273.2	277.4
62.5°	241.7	239.7	240.9	238.5	240.9	239.7	241.7	244.0	246.2	248.8	251.4
65°	200.9	199.2	197.1	196.1	197.1	199.2	200.9	201.9	207.6	210.8	216.5
67.5°	168.7	165.0	164.9	165.7	164.9	165.0	168.7	168.5	172.7	175.2	179.2
70°	145.2	145.2	144.7	144.7	144.7	145.2	145.2	148.3	150.5	152.6	155.2
72.5°	128.9	128.5	127.5	127.1	127.5	128.5	128.9	130.0	131.2	133.3	135.9
75°	103.8	104.3	103.3	102.8	103.3	104.3	103.8	103.8	105.9	106.4	107.4
77.5°	76.6	74.4	75.6	74.4	75.6	74.4	76.6	78.8	79.5	81.8	81.9
80°	58.2	57.7	59.3	57.7	59.3	57.7	58.2	58.2	59.8	60.8	63.4
82.5°	46.0	45.5	46.3	45.1	46.3	45.5	46.0	45.6	46.4	47.9	47.5
85°	27.8	27.3	26.8	27.3	26.8	27.3	27.8	27.3	26.8	27.3	27.8
87.5°	14.0	13.8	13.9	14.0	13.9	13.8	14.0	13.5	13.7	13.5	13.3
90°	22.2	22.8	23.5	24.2	23.5	22.8	22.2	21.5	20.6	19.5	18.4
92.5°	46.2	46.6	47.1	47.6	47.1	46.6	46.2	45.6	44.6	43.1	41.7
95°	85.3	85.8	86.2	86.7	86.2	85.8	85.3	84.9	83.9	82.3	80.8
97.5°	130.7	131.0	131.2	131.5	131.2	131.0	130.7	130.4	129.6	128.1	126.5
100°	164.0	164.4	164.9	165.3	164.9	164.4	164.0	163.6	162.3	160.3	158.2
102.5°	197.3	197.9	198.6	199.2	198.6	197.9	197.3	196.7	195.3	193.1	190.9
105°	248.0	248.7	249.3	250.0	249.3	248.7	248.0	247.3	246.3	245.0	243.7
107.5°	302.2	302.2	302.2	302.1	302.2	302.2	302.2	302.3	301.9	301.2	300.5
110°	341.4	341.2	341.0	340.7	341.0	341.2	341.4	341.6	341.4	340.7	340.1



TEST NUMBER: P333569-840

CATALOG NUMBER: S125RDIP-S850D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	379.9	379.5	379.1	378.7	379.1	379.5	379.9	380.3	380.3	380.0	379.7
115°	439.2	439.0	438.8	438.6	438.8	439.0	439.2	439.5	439.7	439.9	440.1
117.5°	499.7	498.9	498.0	497.1	498.0	498.9	499.7	500.6	501.0	500.8	500.6
120°	540.1	539.2	538.3	537.3	538.3	539.2	540.1	541.0	541.4	541.4	541.4
122.5°	579.9	579.2	578.5	577.7	578.5	579.2	579.9	580.6	581.0	581.2	581.4
125°	638.8	638.6	638.4	638.2	638.4	638.6	638.8	639.0	639.4	639.9	640.4
127.5°	697.6	697.1	696.7	696.3	696.7	697.1	697.6	698.0	698.4	698.6	698.8
130°	736.3	735.9	735.4	735.0	735.4	735.9	736.3	736.8	737.1	737.3	737.5
132.5°	773.2	772.5	771.9	771.2	771.9	772.5	773.2	773.8	774.2	774.5	774.7
135°	830.4	829.5	828.6	827.7	828.6	829.5	830.4	831.3	831.7	831.7	831.7
137.5°	886.4	885.2	884.1	883.0	884.1	885.2	886.4	887.5	887.9	887.6	887.4
140°	921.8	920.7	919.6	918.5	919.6	920.7	921.8	922.9	923.3	922.8	922.4
142.5°	955.7	954.6	953.5	952.3	953.5	954.6	955.7	956.8	957.3	956.9	956.7
145°	1005.2	1004.5	1003.8	1003.2	1003.8	1004.5	1005.2	1005.8	1006.2	1006.2	1006.2
147.5°	1051.1	1049.6	1048.0	1046.5	1048.0	1049.6	1051.1	1052.6	1053.1	1052.6	1052.0
150°	1080.2	1079.6	1079.2	1078.7	1079.2	1079.6	1080.2	1080.6	1080.8	1080.8	1080.8
152.5°	1107.8	1107.0	1106.2	1105.4	1106.2	1107.0	1107.8	1108.6	1108.7	1108.2	1107.7
155°	1146.7	1145.5	1144.4	1143.3	1144.4	1145.5	1146.7	1147.8	1147.9	1147.0	1146.1
157.5°	1179.4	1177.9	1176.4	1175.0	1176.4	1177.9	1179.4	1180.8	1181.1	1180.2	1179.3
160°	1200.1	1199.0	1197.9	1196.7	1197.9	1199.0	1200.1	1201.2	1201.3	1200.4	1199.5
162.5°	1219.2	1217.9	1216.6	1215.3	1216.6	1217.9	1219.2	1220.5	1220.6	1219.5	1218.4
165°	1244.2	1242.7	1241.4	1240.1	1241.4	1242.7	1244.2	1245.5	1245.7	1244.8	1243.9
167.5°	1264.0	1262.6	1261.2	1259.8	1261.2	1262.6	1264.0	1265.4	1265.5	1264.0	1262.7
170°	1275.1	1273.4	1271.9	1270.3	1271.9	1273.4	1275.1	1276.6	1276.7	1275.4	1274.0
172.5°	1283.3	1282.0	1280.6	1279.2	1280.6	1282.0	1283.3	1284.8	1284.8	1283.4	1282.1
175°	1292.2	1290.6	1289.0	1287.5	1289.0	1290.6	1292.2	1293.7	1293.8	1292.5	1291.2
177.5°	1296.1	1294.8	1293.5	1292.3	1293.5	1294.8	1296.1	1297.4	1297.4	1296.4	1295.3
180°	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6



TEST NUMBER: P333569-840

CATALOG NUMBER: S125RDIP-S850D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4
2.5°	1224.6	1229.1	1231.6	1237.5	1245.9	1250.1	1256.0	1260.2	1266.1	1273.1	1279.1
5°	1145.2	1157.8	1166.2	1179.3	1191.3	1203.5	1218.6	1229.6	1244.4	1261.1	1274.2
7.5°	1071.6	1087.3	1101.3	1118.6	1138.5	1154.1	1173.9	1194.1	1217.1	1240.9	1263.3
10°	1024.6	1040.4	1057.6	1079.1	1099.0	1120.0	1143.7	1167.2	1196.1	1222.8	1253.2
12.5°	978.1	995.4	1014.9	1038.8	1063.0	1089.8	1113.9	1140.4	1171.3	1206.1	1238.6
15°	920.3	937.1	958.1	978.5	1006.2	1035.6	1067.6	1102.8	1137.4	1176.2	1216.6
17.5°	858.3	876.8	899.8	923.5	952.8	987.1	1018.5	1057.0	1095.9	1141.1	1188.6
20°	818.0	836.9	864.1	890.4	917.2	950.7	988.0	1027.2	1068.6	1116.4	1169.3
22.5°	786.2	799.6	826.4	853.0	884.4	918.8	955.2	996.2	1041.4	1090.8	1146.3
25°	738.8	754.6	774.0	801.7	834.2	870.5	907.2	950.7	1000.0	1050.4	1109.5
27.5°	696.8	709.7	728.9	750.7	783.0	820.6	859.7	905.0	955.6	1006.9	1069.1
30°	667.0	681.2	699.5	722.6	748.3	789.2	829.0	873.6	925.0	978.0	1041.9
32.5°	641.0	655.6	671.4	693.2	721.0	757.3	798.4	842.1	894.3	949.0	1011.3
35°	604.6	614.6	629.2	650.8	678.0	707.4	749.3	795.5	846.4	902.9	965.3
37.5°	562.9	575.7	590.4	609.0	632.9	664.7	703.7	750.3	797.6	851.8	908.8
40°	538.6	550.6	566.8	580.5	605.6	634.5	670.1	718.9	766.1	817.0	868.9
42.5°	513.8	525.4	539.2	556.1	578.8	606.8	640.0	685.4	735.9	783.9	827.4
45°	475.0	487.2	500.3	515.9	536.9	564.2	597.2	638.6	682.8	726.8	759.8
47.5°	438.1	449.4	461.8	477.9	497.3	523.5	553.1	589.7	632.5	669.9	693.6
50°	411.6	422.1	435.8	451.5	470.4	495.0	523.3	559.5	595.1	629.2	650.8
52.5°	385.7	397.4	411.0	424.6	442.7	467.4	493.5	524.7	558.7	586.4	604.2
55°	346.6	357.6	370.2	384.4	402.2	423.1	451.0	475.6	502.3	525.9	536.4
57.5°	308.9	318.6	330.4	345.2	361.2	380.7	402.7	426.5	445.2	462.0	473.8
60°	284.2	292.6	303.6	316.2	333.5	351.3	371.2	393.2	408.0	422.1	433.1
62.5°	259.0	267.0	277.6	288.9	304.2	320.7	339.8	357.6	371.9	381.4	394.2
65°	221.3	229.1	238.0	250.1	262.2	275.8	293.2	306.2	316.2	326.7	334.6
67.5°	186.1	192.7	201.2	210.6	220.8	233.9	247.3	258.2	265.0	271.4	280.7
70°	163.1	168.3	175.1	182.5	193.5	206.6	217.1	225.5	230.2	236.5	248.0
72.5°	139.6	145.6	152.1	159.5	168.3	179.4	188.5	196.9	200.0	205.0	212.4
75°	110.1	113.3	118.6	123.7	130.1	139.5	148.3	150.5	153.1	157.3	162.6
77.5°	83.3	86.1	88.2	91.7	96.6	104.2	109.0	112.1	112.7	114.3	119.5
80°	66.0	67.7	69.8	72.4	74.4	80.8	83.4	86.5	87.6	89.2	91.8
82.5°	48.5	50.0	51.3	53.5	56.9	59.4	62.0	65.1	65.3	66.4	67.1
85°	28.3	28.9	27.8	28.9	29.4	30.4	33.0	35.6	35.1	34.6	36.2
87.5°	13.5	13.3	12.5	13.5	12.3	12.4	12.1	12.2	12.6	13.1	13.6
90°	17.3	16.2	14.5	13.0	11.4	9.9	8.2	6.4	4.5	2.8	1.0
92.5°	40.2	38.7	36.8	34.8	32.9	31.0	29.4	28.2	26.9	25.7	24.4
95°	79.2	77.7	75.4	73.1	70.9	68.7	67.4	66.9	66.4	65.9	65.5
97.5°	125.1	123.6	120.5	117.4	114.3	111.3	109.6	109.5	109.3	109.1	108.9
100°	156.2	154.2	151.4	148.5	145.5	142.6	141.2	141.2	141.2	141.2	141.2
102.5°	188.7	186.5	185.0	183.6	182.1	180.6	179.5	178.5	177.6	176.7	175.8
105°	242.3	241.0	239.6	238.2	236.9	235.6	234.4	233.3	232.1	231.0	229.8
107.5°	299.9	299.2	298.2	297.2	296.1	295.1	294.1	293.0	291.8	290.6	289.5
110°	339.4	338.7	338.1	337.4	336.7	336.1	335.2	334.1	333.0	331.8	330.7



TEST NUMBER: P333569-840

CATALOG NUMBER: S125RDIP-S850D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	379.4	379.1	378.2	377.4	376.6	375.7	375.0	374.4	373.8	373.2	372.6
115°	440.4	440.6	440.1	439.7	439.2	438.8	438.1	437.3	436.4	435.5	434.5
117.5°	500.5	500.3	499.9	499.5	499.1	498.7	498.3	497.9	497.5	497.1	496.7
120°	541.4	541.4	541.2	541.0	540.7	540.5	539.9	538.8	537.6	536.4	535.3
122.5°	581.6	581.7	581.2	580.6	580.0	579.4	579.0	578.6	578.1	577.7	577.3
125°	640.8	641.3	641.0	640.8	640.6	640.4	639.5	638.2	636.8	635.5	634.2
127.5°	699.0	699.3	699.0	698.7	698.5	698.2	697.7	696.9	696.2	695.4	694.7
130°	737.8	738.0	737.5	737.1	736.7	736.2	735.4	734.3	733.2	732.1	730.9
132.5°	774.9	775.1	775.2	775.3	775.4	775.5	774.6	772.7	770.9	769.1	767.2
135°	831.7	831.7	831.5	831.3	831.1	830.9	830.1	828.7	827.4	826.1	824.8
137.5°	887.1	886.8	886.4	885.9	885.3	884.8	883.9	882.6	881.3	880.0	878.8
140°	921.9	921.5	920.8	920.2	919.5	918.8	917.9	916.8	915.6	914.5	913.4
142.5°	956.4	956.1	955.3	954.5	953.6	952.8	951.9	950.9	950.0	949.1	948.1
145°	1006.2	1006.2	1005.5	1004.8	1004.2	1003.5	1002.7	1001.8	1000.9	1000.1	999.2
147.5°	1051.5	1051.0	1050.4	1049.9	1049.4	1048.8	1048.2	1047.8	1047.3	1046.8	1046.3
150°	1080.8	1080.8	1079.8	1079.0	1078.1	1077.2	1076.9	1077.1	1077.3	1077.5	1077.7
152.5°	1107.1	1106.6	1106.2	1105.9	1105.5	1105.2	1104.8	1104.5	1104.2	1103.9	1103.6
155°	1145.2	1144.3	1144.1	1143.9	1143.7	1143.4	1143.3	1143.3	1143.3	1143.3	1143.3
157.5°	1178.5	1177.6	1177.4	1177.1	1176.9	1176.7	1176.8	1177.3	1177.8	1178.3	1178.8
160°	1198.6	1197.7	1197.5	1197.3	1197.1	1196.9	1197.1	1197.7	1198.4	1199.1	1199.7
162.5°	1217.4	1216.3	1216.3	1216.2	1216.2	1216.1	1216.4	1216.8	1217.3	1217.8	1218.3
165°	1243.0	1242.1	1241.8	1241.6	1241.4	1241.2	1241.3	1241.7	1242.2	1242.6	1243.1
167.5°	1261.4	1260.0	1260.0	1260.0	1260.0	1260.0	1260.5	1261.4	1262.3	1263.1	1264.0
170°	1272.7	1271.3	1271.3	1271.3	1271.3	1271.3	1271.8	1272.7	1273.5	1274.4	1275.4
172.5°	1280.7	1279.4	1279.4	1279.4	1279.4	1279.4	1279.9	1280.7	1281.6	1282.5	1283.4
175°	1289.8	1288.5	1288.5	1288.5	1288.5	1288.5	1288.9	1289.8	1290.7	1291.6	1292.5
177.5°	1294.2	1293.1	1293.3	1293.4	1293.6	1293.8	1294.2	1294.9	1295.8	1296.5	1297.2
180°	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6



TEST NUMBER: P333569-840

CATALOG NUMBER: S125RDIP-S850D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4
2.5°	1283.6	1287.5	1292.9	1299.2	1304.2	1309.7	1312.6	1312.6	1315.1	1320.6	1327.7
5°	1287.4	1301.0	1314.0	1330.9	1343.9	1359.2	1370.7	1381.7	1391.7	1404.2	1417.3
7.5°	1286.3	1308.9	1332.5	1359.0	1388.2	1411.3	1435.1	1453.8	1472.2	1496.3	1515.3
10°	1282.1	1311.4	1343.4	1377.0	1413.7	1445.7	1474.5	1500.8	1525.9	1552.2	1575.7
12.5°	1274.6	1311.9	1351.0	1391.3	1437.6	1474.2	1511.5	1539.3	1568.7	1597.4	1626.5
15°	1263.2	1307.3	1354.4	1410.6	1467.2	1508.1	1544.8	1580.9	1608.2	1640.7	1668.6
17.5°	1239.8	1296.6	1355.9	1417.2	1471.7	1519.2	1557.7	1592.1	1621.1	1656.9	1694.7
20°	1226.0	1287.4	1349.2	1414.7	1466.6	1515.4	1552.7	1588.3	1624.5	1671.1	1717.3
22.5°	1206.7	1272.2	1337.9	1400.1	1454.9	1502.0	1540.4	1584.2	1631.6	1684.6	1740.4
25°	1176.2	1243.9	1308.8	1368.1	1421.6	1469.9	1522.3	1580.9	1638.7	1708.4	1788.7
27.5°	1137.5	1202.6	1260.7	1323.3	1376.4	1437.8	1503.3	1566.9	1650.1	1746.1	1846.2
30°	1108.5	1170.4	1225.5	1284.8	1345.0	1412.7	1486.1	1561.0	1660.1	1772.9	1892.0
32.5°	1075.0	1130.9	1185.6	1242.7	1312.3	1386.6	1464.7	1556.4	1674.9	1803.1	1926.3
35°	1016.7	1067.1	1120.0	1183.5	1257.5	1338.2	1437.8	1549.5	1692.6	1830.6	1941.3
37.5°	955.7	995.4	1048.6	1115.6	1196.1	1289.5	1402.6	1538.3	1685.4	1809.1	1856.1
40°	908.8	945.9	1002.1	1072.4	1152.1	1254.3	1381.2	1520.7	1668.6	1754.5	1750.9
42.5°	862.1	899.8	953.8	1024.5	1107.6	1222.0	1352.7	1497.6	1622.4	1655.2	1586.9
45°	790.7	825.9	878.9	950.2	1039.4	1159.4	1296.8	1435.7	1515.4	1462.5	1327.2
47.5°	718.0	752.0	801.2	871.1	968.4	1094.1	1224.0	1338.0	1349.2	1235.5	1073.2
50°	670.1	702.2	748.8	823.2	917.7	1040.4	1165.7	1255.4	1227.6	1088.6	921.3
52.5°	623.6	654.3	698.0	768.3	864.7	985.0	1096.9	1167.2	1103.0	955.2	804.7
55°	554.8	584.1	628.2	692.7	780.2	890.4	988.5	1014.1	919.8	770.8	649.1
57.5°	489.5	511.0	554.5	611.5	695.9	793.0	863.3	858.7	754.6	620.5	533.2
60°	446.3	465.6	507.1	559.5	639.7	726.8	776.1	755.1	649.6	539.1	455.1
62.5°	406.0	424.1	458.8	507.1	575.9	651.7	687.5	658.6	559.1	461.9	395.2
65°	345.1	358.1	386.0	430.5	484.5	536.9	569.0	526.4	438.4	365.0	314.6
67.5°	288.1	299.4	324.2	356.2	393.3	429.6	442.5	402.7	334.3	284.8	249.3
70°	251.2	261.7	278.4	308.3	333.0	358.7	365.0	329.3	272.2	234.4	212.4
72.5°	215.9	225.6	240.2	261.4	278.4	293.3	296.2	263.1	219.2	193.3	176.3
75°	164.6	173.1	182.5	190.4	201.4	204.0	202.9	177.2	153.6	136.3	126.9
77.5°	121.0	124.5	130.3	133.4	133.9	133.7	128.4	112.1	100.0	92.8	89.0
80°	93.3	95.9	97.6	98.6	99.1	93.8	88.1	78.2	73.9	69.8	65.0
82.5°	67.8	69.6	71.1	71.3	68.5	64.1	58.8	53.8	50.9	48.8	47.0
85°	36.7	37.3	36.7	34.1	30.4	28.9	27.8	26.8	26.3	25.7	25.7
87.5°	13.5	12.6	10.9	11.7	12.0	11.9	12.2	12.1	12.0	12.2	12.5
90°	2.8	4.5	6.4	8.2	9.9	11.4	13.0	14.5	16.2	17.3	18.4
92.5°	25.7	26.9	28.2	29.4	31.0	32.9	34.8	36.8	38.7	40.2	41.7
95°	65.9	66.4	66.9	67.4	68.7	70.9	73.1	75.4	77.7	79.2	80.8
97.5°	109.1	109.3	109.5	109.6	111.3	114.3	117.4	120.5	123.6	125.1	126.5
100°	141.2	141.2	141.2	141.2	142.6	145.5	148.5	151.4	154.2	156.2	158.2
102.5°	176.7	177.6	178.5	179.5	180.6	182.1	183.6	185.0	186.5	188.7	190.9
105°	231.0	232.1	233.3	234.4	235.6	236.9	238.2	239.6	241.0	242.3	243.7
107.5°	290.6	291.8	293.0	294.1	295.1	296.1	297.2	298.2	299.2	299.9	300.5
110°	331.8	333.0	334.1	335.2	336.1	336.7	337.4	338.1	338.7	339.4	340.1



TEST NUMBER: P333569-840

CATALOG NUMBER: S125RDIP-S850D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	373.2	373.8	374.4	375.0	375.7	376.6	377.4	378.2	379.1	379.4	379.7
115°	435.5	436.4	437.3	438.1	438.8	439.2	439.7	440.1	440.6	440.4	440.1
117.5°	497.1	497.5	497.9	498.3	498.7	499.1	499.5	499.9	500.3	500.5	500.6
120°	536.4	537.6	538.8	539.9	540.5	540.7	541.0	541.2	541.4	541.4	541.4
122.5°	577.7	578.1	578.6	579.0	579.4	580.0	580.6	581.2	581.7	581.6	581.4
125°	635.5	636.8	638.2	639.5	640.4	640.6	640.8	641.0	641.3	640.8	640.4
127.5°	695.4	696.2	696.9	697.7	698.2	698.5	698.7	699.0	699.3	699.0	698.8
130°	732.1	733.2	734.3	735.4	736.2	736.7	737.1	737.5	738.0	737.8	737.5
132.5°	769.1	770.9	772.7	774.6	775.5	775.4	775.3	775.2	775.1	774.9	774.7
135°	826.1	827.4	828.7	830.1	830.9	831.1	831.3	831.5	831.7	831.7	831.7
137.5°	880.0	881.3	882.6	883.9	884.8	885.3	885.9	886.4	886.8	887.1	887.4
140°	914.5	915.6	916.8	917.9	918.8	919.5	920.2	920.8	921.5	921.9	922.4
142.5°	949.1	950.0	950.9	951.9	952.8	953.6	954.5	955.3	956.1	956.4	956.7
145°	1000.1	1000.9	1001.8	1002.7	1003.5	1004.2	1004.8	1005.5	1006.2	1006.2	1006.2
147.5°	1046.8	1047.3	1047.8	1048.2	1048.8	1049.4	1049.9	1050.4	1051.0	1051.5	1052.0
150°	1077.5	1077.3	1077.1	1076.9	1077.2	1078.1	1079.0	1079.8	1080.8	1080.8	1080.8
152.5°	1103.9	1104.2	1104.5	1104.8	1105.2	1105.5	1105.9	1106.2	1106.6	1107.1	1107.7
155°	1143.3	1143.3	1143.3	1143.3	1143.4	1143.7	1143.9	1144.1	1144.3	1145.2	1146.1
157.5°	1178.3	1177.8	1177.3	1176.8	1176.7	1176.9	1177.1	1177.4	1177.6	1178.5	1179.3
160°	1199.1	1198.4	1197.7	1197.1	1196.9	1197.1	1197.3	1197.5	1197.7	1198.6	1199.5
162.5°	1217.8	1217.3	1216.8	1216.4	1216.1	1216.2	1216.2	1216.3	1216.3	1217.4	1218.4
165°	1242.6	1242.2	1241.7	1241.3	1241.2	1241.4	1241.6	1241.8	1242.1	1243.0	1243.9
167.5°	1263.1	1262.3	1261.4	1260.5	1260.0	1260.0	1260.0	1260.0	1260.0	1261.4	1262.7
170°	1274.4	1273.5	1272.7	1271.8	1271.3	1271.3	1271.3	1271.3	1271.3	1272.7	1274.0
172.5°	1282.5	1281.6	1280.7	1279.9	1279.4	1279.4	1279.4	1279.4	1279.4	1280.7	1282.1
175°	1291.6	1290.7	1289.8	1288.9	1288.5	1288.5	1288.5	1288.5	1288.5	1289.8	1291.2
177.5°	1296.5	1295.8	1294.9	1294.2	1293.8	1293.6	1293.4	1293.3	1293.1	1294.2	1295.3
180°	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6



TEST NUMBER: P333569-840

CATALOG NUMBER: S125RDIP-S850D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4
2.5°	1333.1	1333.1	1340.3	1339.9	1344.5	1342.8	1343.6
5°	1433.1	1442.0	1449.9	1455.1	1463.0	1465.1	1464.0
7.5°	1536.7	1556.5	1566.2	1579.4	1581.9	1588.7	1588.0
10°	1600.9	1620.3	1635.0	1646.5	1652.3	1659.6	1660.1
12.5°	1651.2	1667.7	1680.7	1691.4	1698.4	1700.7	1702.1
15°	1690.6	1708.9	1724.1	1739.3	1748.3	1755.0	1758.8
17.5°	1730.2	1758.6	1785.3	1806.0	1818.5	1828.9	1828.8
20°	1760.8	1793.3	1826.9	1850.5	1874.6	1885.1	1886.7
22.5°	1793.5	1843.3	1886.5	1923.1	1954.8	1965.7	1969.7
25°	1861.5	1926.5	1993.2	2044.6	2081.2	2102.7	2105.9
27.5°	1943.6	2031.6	2101.7	2149.1	2179.6	2195.5	2199.0
30°	2001.6	2082.8	2145.8	2181.4	2195.5	2197.7	2189.8
32.5°	2027.5	2088.3	2113.4	2111.3	2083.6	2065.1	2058.0
35°	1995.8	1983.2	1921.8	1848.5	1792.3	1756.7	1747.2
37.5°	1816.2	1707.7	1594.8	1483.9	1424.8	1394.8	1343.2
40°	1639.2	1484.5	1367.1	1273.7	1207.1	1153.6	1141.0
42.5°	1439.5	1279.8	1162.4	1082.4	1029.3	992.5	976.5
45°	1156.8	1019.4	922.4	861.0	820.1	793.3	781.3
47.5°	925.2	818.9	748.2	702.8	671.7	648.3	641.9
50°	798.1	713.2	653.4	615.1	591.5	573.7	566.3
52.5°	693.2	624.6	578.7	547.1	524.8	513.7	507.6
55°	572.1	512.8	479.8	454.6	442.0	433.1	428.9
57.5°	467.9	425.1	400.9	383.5	371.9	366.2	364.2
60°	409.5	376.0	354.0	340.3	332.4	325.1	323.1
62.5°	357.9	331.5	314.5	302.6	294.7	291.5	290.3
65°	288.4	271.1	258.5	251.2	244.9	243.9	243.3
67.5°	229.2	219.0	212.5	204.8	202.6	198.9	198.2
70°	196.1	189.2	181.5	178.8	176.2	172.5	173.1
72.5°	166.3	159.6	154.2	150.7	149.8	148.1	149.6
75°	121.7	119.6	117.4	114.8	113.8	113.8	113.3
77.5°	86.8	85.0	82.7	81.2	80.9	78.7	79.5
80°	62.9	60.3	59.3	59.8	58.2	57.7	57.7
82.5°	46.6	45.6	44.5	44.6	44.3	43.8	44.2
85°	25.7	25.1	25.1	24.6	24.6	24.1	24.1
87.5°	13.1	13.7	13.1	12.8	12.9	13.5	14.0
90°	19.5	20.6	21.5	22.2	22.8	23.5	24.2
92.5°	43.1	44.6	45.6	46.2	46.6	47.1	47.6
95°	82.3	83.9	84.9	85.3	85.8	86.2	86.7
97.5°	128.1	129.6	130.4	130.7	131.0	131.2	131.5
100°	160.3	162.3	163.6	164.0	164.4	164.9	165.3
102.5°	193.1	195.3	196.7	197.3	197.9	198.6	199.2
105°	245.0	246.3	247.3	248.0	248.7	249.3	250.0
107.5°	301.2	301.9	302.3	302.2	302.2	302.2	302.1
110°	340.7	341.4	341.6	341.4	341.2	341.0	340.7



TEST NUMBER: P333569-840

CATALOG NUMBER: S125RDIP-S850D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	380.0	380.3	380.3	379.9	379.5	379.1	378.7
115°	439.9	439.7	439.5	439.2	439.0	438.8	438.6
117.5°	500.8	501.0	500.6	499.7	498.9	498.0	497.1
120°	541.4	541.4	541.0	540.1	539.2	538.3	537.3
122.5°	581.2	581.0	580.6	579.9	579.2	578.5	577.7
125°	639.9	639.4	639.0	638.8	638.6	638.4	638.2
127.5°	698.6	698.4	698.0	697.6	697.1	696.7	696.3
130°	737.3	737.1	736.8	736.3	735.9	735.4	735.0
132.5°	774.5	774.2	773.8	773.2	772.5	771.9	771.2
135°	831.7	831.7	831.3	830.4	829.5	828.6	827.7
137.5°	887.6	887.9	887.5	886.4	885.2	884.1	883.0
140°	922.8	923.3	922.9	921.8	920.7	919.6	918.5
142.5°	956.9	957.3	956.8	955.7	954.6	953.5	952.3
145°	1006.2	1006.2	1005.8	1005.2	1004.5	1003.8	1003.2
147.5°	1052.6	1053.1	1052.6	1051.1	1049.6	1048.0	1046.5
150°	1080.8	1080.8	1080.6	1080.2	1079.6	1079.2	1078.7
152.5°	1108.2	1108.7	1108.6	1107.8	1107.0	1106.2	1105.4
155°	1147.0	1147.9	1147.8	1146.7	1145.5	1144.4	1143.3
157.5°	1180.2	1181.1	1180.8	1179.4	1177.9	1176.4	1175.0
160°	1200.4	1201.3	1201.2	1200.1	1199.0	1197.9	1196.7
162.5°	1219.5	1220.6	1220.5	1219.2	1217.9	1216.6	1215.3
165°	1244.8	1245.7	1245.5	1244.2	1242.7	1241.4	1240.1
167.5°	1264.0	1265.5	1265.4	1264.0	1262.6	1261.2	1259.8
170°	1275.4	1276.7	1276.6	1275.1	1273.4	1271.9	1270.3
172.5°	1283.4	1284.8	1284.8	1283.3	1282.0	1280.6	1279.2
175°	1292.5	1293.8	1293.7	1292.2	1290.6	1289.0	1287.5
177.5°	1296.4	1297.4	1297.4	1296.1	1294.8	1293.5	1292.3
180°	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6

(END OF REPORT)