

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333571-840

Luminaire Tested: **S125RDIP-S850D1035U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333571-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S850D1035U840-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7460.4 lumens
Efficiency: N/A
Efficacy: 143.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333571-840

CATALOG NUMBER: S125RDIP-S850D1035U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333571-840

CATALOG NUMBER: S125RDIP-S850D1035U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	97	92	89	85	88	85	82	79	70	68	66	57	56	54	45	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	46	40	38	37	32
3	80	71	64	58	73	66	59	54	55	50	46	45	41	39	35	33	31	27
4	74	63	55	49	67	58	51	46	49	44	40	40	36	33	32	29	27	23
5	68	56	48	42	62	52	45	40	44	38	34	36	32	29	29	26	24	20
6	62	50	43	37	57	47	40	34	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	30	26	22	24	21	19	16
8	53	41	34	29	49	38	32	27	33	27	23	27	23	20	22	19	17	14
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	20	17	15	13
10	46	35	28	23	43	32	26	21	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8969	8969	8969
5°	8989	8887	8941
10°	8921	8804	8804
15°	8815	8625	8555
20°	8678	8376	8276
25°	8521	8131	7952
30°	8322	7845	7594
35°	8121	7550	7194
40°	7932	7242	6800
45°	7701	6898	6370
50°	7471	6523	5923
55°	7203	6164	5444
60°	6935	5730	4930
65°	6619	5225	4343
70°	6258	4594	3743
75°	5759	3873	3114
80°	5069	3042	2615
85°	4276	2482	2334



TEST NUMBER: P333571-840

CATALOG NUMBER: S125RDIP-S850D1035U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.6	1.8
10°-20°	364.9	4.9
20°-30°	529.2	7.1
30°-40°	603.1	8.1
40°-50°	587.8	7.9
50°-60°	494.8	6.6
60°-70°	346.9	4.6
70°-80°	178.3	2.4
80°-90°	47.9	0.6
90°-100°	49.4	0.7
100°-110°	304.6	4.1
110°-120°	552.5	7.4
120°-130°	709.1	9.5
130°-140°	762.7	10.2
140°-150°	715.9	9.6
150°-160°	579.1	7.8
160°-170°	374.5	5.0
170°-180°	129.2	1.7
0°-30°	1024.6	13.7
0°-40°	1627.7	21.8
0°-60°	2710.4	36.3
0°-90°	3283.4	44.0
90°-120°	906.6	12.2
90°-150°	3094.2	41.5
90°-180°	4177.0	56.0
0°-180°	7460.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1389	1389	1389	1389	1389	
5°	1386	1382	1371	1381	1379	131
15°	1318	1311	1290	1289	1280	371
25°	1196	1179	1141	1128	1116	550
35°	1030	1004	958	928	912	645
45°	843	811	755	715	697	650
55°	640	605	547	502	484	572
65°	433	396	342	301	284	429
75°	231	199	155	133	125	244
85°	58	40	34	32	32	65
90°	1	9	16	21	24	5
95°	58	52	16	21	21	73
105°	296	300	300	300	299	314
115°	557	561	563	559	553	552
125°	792	798	799	795	792	707
135°	987	993	991	989	983	761
145°	1144	1146	1146	1147	1142	715
155°	1260	1255	1256	1259	1251	580
165°	1330	1324	1325	1330	1323	376
175°	1360	1355	1355	1362	1354	129
180°	1360	1360	1360	1360	1360	



TEST NUMBER: P333571-840

CATALOG NUMBER: S125RDIP-S850D1035U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7
2.5°	1391.1	1390.6	1390.0	1389.5	1388.9	1387.7	1385.8	1383.9	1382.1	1380.2	1382.1
5°	1386.5	1385.6	1384.6	1383.7	1382.8	1381.1	1378.5	1375.9	1373.3	1370.8	1373.1
7.5°	1372.9	1372.0	1371.1	1370.2	1369.4	1367.4	1364.3	1361.2	1358.2	1355.0	1356.7
10°	1360.3	1359.6	1358.9	1358.2	1357.5	1355.5	1352.3	1349.0	1345.7	1342.5	1343.1
12.5°	1346.0	1345.1	1344.2	1343.4	1342.5	1339.9	1335.4	1331.1	1326.8	1322.3	1322.8
15°	1318.4	1317.0	1315.6	1314.1	1312.7	1309.6	1304.7	1299.8	1294.9	1290.0	1289.8
17.5°	1287.1	1285.0	1282.8	1280.7	1278.5	1274.3	1268.2	1262.0	1255.9	1249.7	1248.6
20°	1262.7	1260.4	1258.1	1255.8	1253.4	1248.5	1241.1	1233.7	1226.2	1218.7	1217.6
22.5°	1235.9	1233.6	1231.2	1228.9	1226.6	1221.5	1213.7	1205.9	1198.0	1190.2	1187.9
25°	1195.7	1192.1	1188.6	1185.2	1181.6	1175.6	1167.0	1158.3	1149.7	1141.1	1138.1
27.5°	1149.5	1145.3	1141.0	1136.8	1132.6	1125.8	1116.6	1107.3	1098.1	1088.8	1084.6
30°	1115.9	1111.5	1107.1	1102.7	1098.2	1091.1	1081.4	1071.6	1061.8	1052.0	1046.6
32.5°	1083.2	1078.0	1072.9	1067.7	1062.5	1054.9	1045.0	1035.0	1025.0	1015.0	1009.2
35°	1030.0	1024.3	1018.8	1013.1	1007.5	999.5	989.1	978.6	968.1	957.6	950.8
37.5°	977.7	970.9	964.1	957.3	950.5	941.7	930.9	920.0	909.2	898.4	890.3
40°	940.8	933.8	926.8	919.8	912.8	903.7	892.5	881.3	870.2	859.0	850.1
42.5°	902.2	895.0	887.9	880.6	873.4	864.1	852.5	841.0	829.4	817.9	809.4
45°	843.2	836.5	829.7	822.9	816.2	806.4	793.6	780.8	768.0	755.2	745.8
47.5°	782.2	775.1	767.9	760.8	753.7	743.7	730.7	717.8	704.9	692.0	682.4
50°	743.6	735.9	728.2	720.5	712.9	702.4	689.0	675.8	662.5	649.2	639.4
52.5°	701.7	693.8	685.9	678.0	670.1	659.9	647.4	634.9	622.3	609.8	599.3
55°	639.7	632.3	624.9	617.4	610.0	599.7	586.6	573.6	560.6	547.4	536.9
57.5°	577.2	569.3	561.3	553.3	545.4	535.1	522.5	509.9	497.4	484.7	474.5
60°	536.9	528.9	520.7	512.5	504.3	494.0	481.4	468.8	456.3	443.6	433.4
62.5°	494.2	486.5	478.7	470.8	463.0	452.8	440.0	427.3	414.4	401.7	392.2
65°	433.1	425.3	417.3	409.4	401.4	391.3	379.0	366.6	354.3	341.9	332.5
67.5°	372.5	364.6	356.7	348.8	340.8	330.9	319.1	307.3	295.5	283.6	275.1
70°	331.4	323.5	315.6	307.6	299.7	289.9	278.3	266.6	255.0	243.3	236.1
72.5°	291.1	283.4	275.7	267.9	260.2	250.9	239.9	229.0	218.1	207.2	200.6
75°	230.8	223.8	216.7	209.7	202.8	194.4	184.6	174.8	165.0	155.2	150.1
77.5°	170.8	165.1	159.6	154.0	148.3	141.7	133.8	126.0	118.2	110.4	106.7
80°	136.3	130.8	125.1	119.6	114.0	108.0	101.4	94.8	88.4	81.8	79.7
82.5°	102.8	97.8	92.7	87.7	82.6	77.9	73.4	69.0	64.4	60.0	59.0
85°	57.7	53.5	49.3	45.1	40.9	38.2	37.1	35.9	34.7	33.5	33.3
87.5°	19.5	18.6	17.6	16.7	15.8	15.3	15.5	15.6	15.7	15.9	16.1
90°	1.0	2.8	4.5	6.4	8.2	9.9	11.4	13.0	14.5	16.2	17.3
92.5°	15.6	14.2	13.0	11.7	10.5	10.6	11.9	13.3	14.7	16.2	17.3
95°	57.5	56.8	56.1	55.4	54.8	50.2	41.7	33.1	24.6	16.2	17.3
97.5°	120.0	121.2	122.4	123.6	124.8	117.0	100.2	83.3	66.4	49.6	43.3
100°	168.3	169.1	169.8	170.4	171.1	171.9	172.8	173.7	174.5	175.4	142.1
102.5°	217.6	218.4	219.3	220.2	221.0	221.7	222.3	222.8	223.3	223.9	217.5
105°	296.4	297.3	298.2	299.1	300.0	300.4	300.4	300.4	300.4	300.4	300.4
107.5°	378.3	378.3	378.3	378.3	378.3	378.5	379.0	379.4	379.9	380.3	380.4
110°	431.5	431.5	431.5	431.5	431.5	431.8	432.2	432.7	433.1	433.5	432.9



TEST NUMBER: P333571-840

CATALOG NUMBER: S125RDIP-S850D1035U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	481.6	482.1	482.6	483.2	483.7	484.1	484.4	484.6	484.9	485.2	484.3
115°	556.6	557.7	558.9	560.0	561.1	561.8	562.0	562.2	562.4	562.6	561.8
117.5°	634.2	634.2	634.1	634.1	634.1	634.5	635.3	636.1	637.0	637.8	636.7
120°	682.7	682.4	682.2	682.0	681.8	682.0	682.7	683.3	684.0	684.7	684.2
122.5°	725.4	726.2	727.1	727.9	728.8	729.3	729.7	730.0	730.3	730.6	730.1
125°	791.5	793.0	794.7	796.3	797.8	798.6	798.6	798.6	798.6	798.6	797.7
127.5°	854.6	855.8	856.9	858.0	859.1	859.6	859.5	859.4	859.2	859.1	858.6
130°	893.3	894.5	895.6	896.8	897.9	898.5	898.8	899.0	899.2	899.4	898.8
132.5°	932.1	933.4	934.7	935.9	937.3	937.7	937.2	936.8	936.2	935.7	935.5
135°	987.1	988.5	989.9	991.2	992.5	993.0	992.5	992.1	991.6	991.2	990.7
137.5°	1037.7	1038.9	1040.1	1041.3	1042.4	1042.8	1042.4	1042.0	1041.6	1041.2	1041.3
140°	1070.9	1071.3	1071.8	1072.2	1072.6	1072.8	1072.5	1072.3	1072.1	1071.9	1072.3
142.5°	1100.7	1101.0	1101.3	1101.5	1101.8	1102.1	1102.4	1102.7	1103.0	1103.3	1103.4
145°	1144.5	1144.9	1145.3	1145.8	1146.2	1146.5	1146.5	1146.5	1146.5	1146.5	1146.7
147.5°	1182.8	1182.7	1182.6	1182.5	1182.3	1182.5	1182.8	1183.1	1183.3	1183.6	1183.9
150°	1207.0	1206.5	1206.1	1205.6	1205.2	1205.2	1205.6	1206.1	1206.5	1207.0	1207.4
152.5°	1230.3	1229.4	1228.4	1227.4	1226.4	1226.2	1226.6	1227.0	1227.5	1227.9	1228.4
155°	1260.4	1259.1	1257.7	1256.4	1255.1	1254.6	1255.1	1255.5	1255.9	1256.4	1257.1
157.5°	1283.5	1282.7	1282.0	1281.2	1280.4	1280.0	1280.0	1280.1	1280.1	1280.2	1280.9
160°	1299.7	1298.4	1297.1	1295.7	1294.3	1293.7	1294.0	1294.2	1294.4	1294.6	1295.6
162.5°	1312.6	1311.3	1309.9	1308.6	1307.3	1306.7	1306.9	1307.2	1307.4	1307.6	1308.9
165°	1330.0	1328.6	1327.3	1326.0	1324.6	1324.0	1324.2	1324.4	1324.7	1324.9	1326.3
167.5°	1342.9	1341.5	1340.1	1338.7	1337.4	1336.8	1337.0	1337.2	1337.4	1337.7	1339.3
170°	1350.1	1348.6	1347.0	1345.4	1343.8	1343.2	1343.4	1343.6	1343.8	1344.1	1345.8
172.5°	1354.9	1353.4	1351.8	1350.3	1348.7	1348.2	1348.5	1348.9	1349.3	1349.7	1351.3
175°	1360.2	1358.9	1357.6	1356.1	1354.8	1354.3	1354.5	1354.7	1354.9	1355.1	1357.0
177.5°	1362.6	1361.6	1360.5	1359.4	1358.4	1357.9	1358.1	1358.3	1358.5	1358.6	1359.9
180°	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2



TEST NUMBER: P333571-840

CATALOG NUMBER: S125RDIP-S850D1035U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7
2.5°	1383.9	1385.8	1387.7	1388.6	1388.4	1388.2	1388.0	1387.8
5°	1375.4	1377.8	1380.1	1381.1	1380.6	1380.1	1379.7	1379.2
7.5°	1358.4	1360.0	1361.6	1362.1	1361.6	1361.1	1360.6	1360.1
10°	1343.8	1344.5	1345.2	1345.2	1344.5	1343.8	1343.1	1342.5
12.5°	1323.3	1323.8	1324.3	1324.1	1323.0	1321.9	1320.9	1319.8
15°	1289.6	1289.3	1289.1	1288.0	1285.9	1283.7	1281.6	1279.5
17.5°	1247.4	1246.3	1245.1	1243.6	1241.9	1240.2	1238.5	1236.8
20°	1216.4	1215.2	1214.1	1212.4	1210.3	1208.2	1206.1	1204.1
22.5°	1185.6	1183.4	1181.0	1179.0	1177.3	1175.6	1173.9	1172.2
25°	1135.1	1132.1	1129.0	1126.2	1123.6	1121.1	1118.5	1115.9
27.5°	1080.4	1076.1	1071.9	1068.5	1066.1	1063.6	1061.2	1058.6
30°	1041.3	1035.9	1030.5	1026.8	1024.7	1022.6	1020.5	1018.3
32.5°	1003.2	997.2	991.4	987.0	984.4	981.8	979.1	976.4
35°	944.0	937.3	930.5	925.5	922.2	919.0	915.7	912.4
37.5°	882.2	874.0	866.0	860.3	857.2	853.9	850.8	847.7
40°	841.2	832.4	823.5	817.7	815.0	812.1	809.3	806.6
42.5°	800.9	792.4	784.0	777.6	773.6	769.4	765.3	761.2
45°	736.5	727.2	717.8	711.4	707.9	704.5	700.9	697.4
47.5°	672.8	663.2	653.6	646.8	643.0	639.1	635.2	631.4
50°	629.7	619.9	610.1	603.4	600.0	596.4	592.9	589.5
52.5°	588.8	578.1	567.6	560.6	557.1	553.6	550.2	546.6
55°	526.5	516.0	505.5	498.4	494.7	491.0	487.3	483.5
57.5°	464.2	454.0	443.7	437.0	433.6	430.3	427.1	423.7
60°	423.1	412.8	402.6	395.8	392.2	388.8	385.3	381.7
62.5°	382.6	373.1	363.7	357.2	353.7	350.1	346.7	343.2
65°	323.3	314.0	304.6	298.2	294.7	291.2	287.7	284.2
67.5°	266.5	258.0	249.4	243.8	241.1	238.2	235.4	232.7
70°	228.8	221.7	214.4	209.4	206.6	203.8	201.1	198.2
72.5°	193.9	187.2	180.6	176.3	174.4	172.6	170.8	168.8
75°	145.0	139.9	134.7	131.4	129.7	128.1	126.4	124.8
77.5°	103.1	99.6	95.9	93.6	92.4	91.2	90.0	88.8
80°	77.7	75.5	73.4	72.1	71.7	71.2	70.7	70.3
82.5°	58.1	57.1	56.0	55.4	55.1	54.9	54.6	54.3
85°	33.1	32.8	32.6	32.4	32.1	31.9	31.7	31.5
87.5°	16.3	16.5	16.7	16.8	16.8	16.7	16.7	16.6
90°	18.4	19.5	20.6	21.5	22.2	22.8	23.5	24.2
92.5°	18.4	19.5	20.6	21.3	21.6	21.9	22.3	22.6
95°	18.4	19.5	20.6	21.2	21.2	21.2	21.2	21.2
97.5°	37.0	30.7	24.3	21.2	21.2	21.2	21.2	21.2
100°	108.7	75.3	41.9	24.7	23.8	22.9	22.1	21.2
102.5°	211.2	204.9	198.5	187.8	172.6	157.3	142.1	126.8
105°	300.4	300.4	300.4	300.3	300.1	299.9	299.7	299.4
107.5°	380.4	380.5	380.5	380.2	379.5	378.9	378.2	377.5
110°	432.2	431.5	430.9	430.7	430.9	431.1	431.3	431.5



TEST NUMBER: P333571-840

CATALOG NUMBER: S125RDIP-S850D1035U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	483.5	482.6	481.8	481.2	480.9	480.6	480.3	480.0
115°	560.9	560.0	559.1	558.0	556.6	555.2	553.9	552.6
117.5°	635.5	634.4	633.2	632.3	631.8	631.2	630.6	630.0
120°	683.8	683.3	682.9	682.1	681.0	679.8	678.7	677.6
122.5°	729.7	729.3	728.8	727.9	726.7	725.4	724.1	722.8
125°	796.8	795.9	795.0	794.3	793.6	792.8	792.2	791.5
127.5°	858.1	857.6	857.1	856.1	854.3	852.7	851.1	849.4
130°	898.1	897.4	896.8	895.9	894.7	893.6	892.5	891.3
132.5°	935.4	935.3	935.1	934.5	933.4	932.3	931.2	930.1
135°	990.3	989.9	989.4	988.5	987.1	985.8	984.4	983.1
137.5°	1041.4	1041.5	1041.6	1041.0	1039.9	1038.6	1037.5	1036.3
140°	1072.8	1073.2	1073.6	1073.2	1071.9	1070.5	1069.1	1067.8
142.5°	1103.5	1103.6	1103.7	1103.1	1101.7	1100.3	1099.0	1097.6
145°	1146.9	1147.1	1147.3	1146.8	1145.5	1144.1	1142.8	1141.5
147.5°	1184.1	1184.4	1184.7	1184.0	1182.3	1180.7	1179.1	1177.5
150°	1207.9	1208.3	1208.7	1208.1	1206.3	1204.5	1202.6	1200.9
152.5°	1228.8	1229.3	1229.7	1229.1	1227.5	1225.9	1224.3	1222.6
155°	1257.7	1258.4	1259.1	1258.5	1256.7	1254.9	1253.1	1251.3
157.5°	1281.6	1282.3	1283.0	1282.5	1280.7	1278.9	1277.1	1275.4
160°	1296.5	1297.4	1298.3	1297.8	1296.1	1294.2	1292.4	1290.6
162.5°	1310.1	1311.3	1312.6	1312.2	1310.3	1308.3	1306.4	1304.3
165°	1327.6	1329.0	1330.3	1330.1	1328.3	1326.5	1324.7	1322.9
167.5°	1340.9	1342.5	1344.1	1343.9	1341.9	1339.9	1337.9	1335.8
170°	1347.7	1349.5	1351.3	1351.1	1349.1	1347.2	1345.1	1343.1
172.5°	1352.9	1354.5	1356.1	1355.9	1353.9	1351.9	1349.9	1348.0
175°	1358.8	1360.6	1362.3	1362.2	1360.2	1358.2	1356.1	1354.1
177.5°	1361.1	1362.4	1363.6	1363.5	1362.1	1360.7	1359.3	1357.8
180°	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2	1360.2

(END OF REPORT)