

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331615-830

Luminaire Tested: **SA2XXRDIP-C290D330U830-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331615-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C290D330U830-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 330 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2300.2 lumens
Efficiency: N/A
Efficacy: 113.3 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331615-830
CATALOG NUMBER: SA2XXRDIP-C290D330U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331615-830

CATALOG NUMBER: SA2XXRDIP-C290D330U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53	46
1	98	94	90	87	90	86	83	80	72	70	68	59	58	57	48	47	46	40
2	90	83	77	72	82	76	71	67	64	61	58	53	51	49	43	41	40	35
3	82	73	66	61	75	68	62	57	57	53	49	48	45	42	39	37	35	31
4	76	65	58	52	69	61	54	49	52	47	43	43	40	37	35	33	31	27
5	70	59	51	45	64	55	48	43	47	41	37	39	35	32	32	29	27	24
6	64	53	45	40	59	49	43	38	42	37	33	36	32	29	29	27	25	22
7	60	48	41	35	55	45	38	33	39	33	30	33	29	26	27	24	22	20
8	56	44	37	32	51	41	34	30	35	30	27	30	26	23	25	22	20	18
9	52	40	33	28	48	38	31	27	33	28	24	28	24	21	23	21	18	16
10	49	37	30	26	45	35	29	24	30	25	22	26	22	19	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9947	9947	9947	9947
5°	11110	10010	8877	10010
10°	12329	9940	7694	9940
15°	12933	9795	6063	9795
20°	11213	9579	5246	9579
25°	7352	9283	4684	9283
30°	4950	8925	4238	8925
35°	4009	8474	3824	8474
40°	3564	7982	3539	7982
45°	3226	7405	3158	7405
50°	2936	6835	2926	6835
55°	2759	6201	2725	6201
60°	2309	5622	2283	5622
65°	1948	5104	2208	5104
70°	1799	4556	2082	4556
75°	1684	3968	1921	3968
80°	1553	3273	1711	3273
85°	1426	2575	1501	2575



TEST NUMBER: P331615-830

CATALOG NUMBER: SA2XXRDIP-C290D330U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.4	2.5
10°-20°	162.8	7.1
20°-30°	209.7	9.1
30°-40°	199.3	8.7
40°-50°	170.7	7.4
50°-60°	130.0	5.7
60°-70°	82.2	3.6
70°-80°	41.0	1.8
80°-90°	11.7	0.5
90°-100°	14.0	0.6
100°-110°	51.5	2.2
110°-120°	137.7	6.0
120°-130°	227.3	9.9
130°-140°	241.8	10.5
140°-150°	224.7	9.8
150°-160°	180.7	7.9
160°-170°	116.4	5.1
170°-180°	40.1	1.7
0°-30°	430.9	18.7
0°-40°	630.2	27.4
0°-60°	931.0	40.5
0°-90°	1065.9	46.3
90°-120°	203.3	8.8
90°-150°	897.1	39.0
90°-180°	1234.0	53.6
0°-180°	2300.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	616	616	616	616	616	
5°	686	618	548	618	686	68
15°	774	586	363	586	774	209
25°	413	521	263	521	413	196
35°	203	430	194	430	203	130
45°	141	324	138	324	141	109
55°	98	220	97	220	98	86
65°	51	134	58	134	51	52
75°	27	64	31	64	27	29
85°	8	14	8	14	8	8
90°	8	0	8	0	8	4
95°	13	20	13	20	13	12
105°	23	93	23	93	23	24
115°	25	175	25	175	25	63
125°	260	248	260	248	260	225
135°	317	307	317	307	317	244
145°	361	356	361	356	361	226
155°	392	392	392	392	392	181
165°	412	413	412	413	412	116
175°	420	422	420	422	420	40
180°	421	421	421	421	421	



TEST NUMBER: P331615-830

CATALOG NUMBER: SA2XXRDIP-C290D330U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1
2.5°	641.2	641.7	642.2	641.0	641.0	640.0	637.7	636.0	631.2	630.6	630.6
5°	685.5	685.1	686.0	683.2	679.4	678.4	674.4	669.0	663.5	657.3	656.0
7.5°	729.6	729.0	727.3	726.8	723.9	717.4	710.9	703.9	694.7	685.6	681.1
10°	752.0	759.0	754.7	747.2	748.7	738.7	733.3	724.1	716.3	702.9	699.9
12.5°	773.8	776.7	775.2	771.0	769.1	762.1	754.9	746.9	732.6	720.6	710.0
15°	773.7	777.8	778.9	777.6	778.6	778.3	774.4	767.8	755.4	742.1	730.5
17.5°	716.6	719.4	726.5	731.2	737.3	749.9	756.2	758.6	756.8	749.1	741.0
20°	652.6	647.9	667.6	677.6	686.2	707.6	726.0	733.1	744.4	744.2	742.1
22.5°	561.8	562.9	581.5	593.5	618.5	640.0	660.9	687.5	709.5	724.0	732.4
25°	412.7	420.9	439.5	455.8	483.6	523.5	559.7	601.6	641.2	672.5	702.3
27.5°	310.0	310.7	325.4	340.4	356.9	389.6	435.2	485.2	541.7	588.3	641.9
30°	265.5	264.2	270.4	279.7	293.8	319.1	353.3	402.5	458.8	529.0	591.5
32.5°	233.9	234.0	238.7	245.5	257.2	274.3	297.7	337.8	391.0	460.1	533.3
35°	203.4	203.2	206.6	211.5	216.4	227.3	243.5	264.4	301.0	365.4	440.4
37.5°	181.4	182.4	184.1	187.2	192.6	198.7	208.3	222.4	248.5	286.6	349.6
40°	169.1	169.6	171.9	174.5	177.7	182.4	190.3	201.7	220.7	251.1	297.2
42.5°	157.9	158.3	159.9	162.3	164.9	169.6	176.2	186.0	201.4	225.1	263.1
45°	141.3	141.3	142.8	143.8	146.7	150.9	156.3	164.5	175.1	192.7	217.9
47.5°	125.8	125.8	126.9	128.7	130.4	133.7	139.0	145.7	153.4	167.0	188.6
50°	116.9	117.2	117.7	119.2	120.4	123.3	127.4	133.2	141.3	151.8	169.8
52.5°	109.7	109.6	110.4	111.0	111.8	113.9	117.0	122.1	129.3	138.5	153.4
55°	98.0	97.2	98.5	99.5	100.2	101.0	102.7	105.9	112.2	119.9	131.0
57.5°	83.5	83.1	84.1	85.0	87.1	89.4	90.9	92.8	96.0	101.6	112.6
60°	71.5	71.5	73.4	74.1	76.4	79.5	82.5	84.2	87.4	91.0	99.2
62.5°	60.9	61.1	61.9	62.6	63.9	67.6	71.8	75.6	78.6	82.1	87.5
65°	51.0	51.4	51.4	51.8	52.7	53.5	55.2	58.2	63.6	68.5	72.6
67.5°	43.3	43.4	43.5	43.9	44.1	45.1	45.8	47.1	48.4	53.0	58.1
70°	38.1	38.7	38.5	38.9	39.2	39.6	40.4	41.1	43.1	44.1	47.1
72.5°	33.3	33.7	33.7	34.0	34.6	34.7	35.3	36.0	37.2	38.1	39.8
75°	27.0	26.8	27.0	27.4	27.6	27.8	27.8	28.7	29.3	30.2	31.3
77.5°	20.8	21.0	21.0	21.0	21.1	21.5	21.4	21.8	22.4	22.9	23.4
80°	16.7	16.9	16.7	16.9	17.2	17.3	17.2	17.3	18.0	18.4	18.4
82.5°	12.9	13.0	13.1	13.1	13.2	13.2	13.6	13.6	14.0	13.9	14.1
85°	7.7	7.5	7.5	7.5	7.7	7.9	7.7	7.7	7.9	7.9	7.9
87.5°	4.4	4.5	4.5	4.4	4.4	4.4	4.3	4.4	4.2	4.3	4.1
90°	8.2	8.1	7.9	7.8	7.7	7.4	7.1	6.8	6.4	6.1	5.6
92.5°	8.2	8.1	8.1	8.0	7.9	7.7	7.6	7.4	7.3	7.1	6.8
95°	13.1	13.2	13.2	13.3	13.4	13.2	12.9	12.5	12.3	11.9	11.4
97.5°	17.5	17.4	17.3	17.2	17.2	17.0	16.7	16.5	16.2	15.9	14.8
100°	20.5	20.3	20.2	20.0	19.9	19.5	19.0	18.5	17.9	17.3	16.2
102.5°	21.9	21.7	21.5	21.3	21.1	20.6	20.0	19.2	18.6	17.8	27.5
105°	23.2	22.9	22.6	22.3	22.1	21.6	20.8	20.1	19.3	18.6	37.0
107.5°	23.8	23.6	23.3	23.0	22.7	23.0	23.8	24.5	25.3	26.0	48.2
110°	24.0	23.8	23.6	23.3	23.0	26.2	33.0	39.8	46.6	53.3	72.9



TEST NUMBER: P331615-830

CATALOG NUMBER: SA2XXRDIP-C290D330U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	24.3	24.1	23.8	23.7	23.5	35.7	60.4	85.1	109.8	134.5	139.3
115°	25.0	29.9	34.8	39.6	44.5	62.6	94.0	125.4	156.7	188.0	186.3
117.5°	102.1	118.1	134.1	150.1	166.2	178.0	185.5	193.1	200.7	208.3	207.1
120°	185.9	195.0	204.2	213.3	222.4	226.6	225.8	225.0	224.2	223.4	222.2
122.5°	232.0	233.8	235.5	237.3	239.0	239.7	239.2	238.7	238.3	237.8	236.5
125°	260.5	260.3	260.1	260.0	259.8	259.4	258.9	258.4	258.0	257.5	256.2
127.5°	278.6	278.5	278.5	278.5	278.4	278.1	277.4	276.7	276.0	275.3	274.4
130°	289.8	289.9	289.9	290.0	290.1	289.7	289.0	288.2	287.5	286.8	286.1
132.5°	300.8	300.9	301.0	301.0	301.0	300.8	300.1	299.5	298.9	298.2	297.5
135°	316.6	316.8	316.9	317.1	317.2	316.9	316.2	315.6	314.9	314.2	313.6
137.5°	331.1	331.3	331.6	331.8	332.0	331.8	331.1	330.5	329.8	329.1	328.5
140°	340.1	340.4	340.8	341.1	341.5	341.3	340.7	340.1	339.5	338.8	338.2
142.5°	348.8	349.2	349.6	349.9	350.2	350.2	349.6	349.0	348.5	347.9	347.0
145°	361.1	361.5	361.8	362.1	362.5	362.4	361.9	361.5	361.0	360.5	359.4
147.5°	371.9	372.2	372.5	372.8	373.1	373.1	372.7	372.3	371.9	371.6	370.5
150°	378.5	378.8	379.2	379.6	379.8	379.8	379.4	379.0	378.6	378.2	377.1
152.5°	384.1	384.6	385.0	385.4	385.9	385.9	385.5	385.1	384.7	384.3	383.2
155°	391.9	392.5	393.0	393.5	394.1	394.2	393.7	393.3	392.9	392.5	391.7
157.5°	399.1	399.5	400.1	400.6	401.1	401.1	400.8	400.3	399.8	399.4	398.8
160°	403.2	403.7	404.2	404.6	405.1	405.1	404.7	404.4	403.9	403.5	403.1
162.5°	406.6	407.2	407.7	408.3	409.0	409.0	408.5	408.0	407.6	407.2	406.8
165°	411.7	412.2	412.6	413.1	413.6	413.6	413.1	412.6	412.2	411.7	411.5
167.5°	414.9	415.6	416.1	416.8	417.4	417.5	417.0	416.5	416.0	415.6	415.4
170°	416.9	417.5	418.1	418.8	419.3	419.4	419.0	418.5	418.0	417.5	417.4
172.5°	418.4	419.0	419.6	420.2	420.8	420.8	420.4	419.9	419.4	419.0	418.9
175°	419.6	420.3	421.0	421.7	422.4	422.4	422.0	421.5	421.0	420.6	420.5
177.5°	420.5	420.9	421.4	421.9	422.4	422.4	422.1	421.7	421.3	420.9	420.8
180°	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1



TEST NUMBER: P331615-830

CATALOG NUMBER: SA2XXRDIP-C290D330U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1
2.5°	630.9	629.5	628.3	625.3	623.7	620.3	619.8	619.6	615.2	610.9	609.6
5°	652.6	649.1	644.0	638.0	631.8	625.4	621.1	617.6	609.1	601.0	596.3
7.5°	674.4	667.0	658.2	646.9	637.3	626.8	618.9	611.8	599.6	588.0	580.1
10°	690.7	678.7	666.9	651.3	639.0	627.1	616.0	606.3	592.7	577.2	566.3
12.5°	700.8	687.6	671.4	656.1	640.3	625.0	610.1	597.8	581.6	565.7	552.8
15°	714.4	700.3	680.6	658.7	638.5	618.5	601.4	586.0	565.1	545.9	530.1
17.5°	725.7	706.2	685.0	659.8	636.2	611.0	588.9	569.2	545.8	522.8	504.2
20°	729.2	709.9	685.5	660.3	632.4	602.7	578.9	557.5	532.4	507.4	486.0
22.5°	727.0	712.0	684.9	654.6	626.1	595.0	568.2	543.3	515.5	489.9	465.1
25°	711.9	706.7	681.1	648.1	615.6	579.4	548.3	521.1	489.5	462.0	435.1
27.5°	676.7	687.8	671.8	636.7	600.5	561.8	526.8	495.9	463.0	432.2	405.3
30°	642.7	668.2	661.4	628.8	588.3	550.3	511.0	478.7	443.7	411.9	385.4
32.5°	596.3	638.4	645.1	617.8	576.0	534.1	493.0	460.9	424.2	390.9	365.0
35°	522.4	585.3	614.3	596.9	555.0	509.7	467.4	429.9	393.0	360.1	334.4
37.5°	434.2	520.0	568.2	569.4	530.8	483.9	437.7	400.5	362.8	330.5	302.7
40°	377.0	470.0	532.7	546.6	514.1	463.4	416.6	378.7	342.0	310.2	278.3
42.5°	325.6	418.2	495.3	519.5	493.7	443.3	396.4	356.8	321.0	291.1	258.4
45°	263.3	344.3	429.2	472.5	458.2	411.5	362.0	324.3	290.8	264.9	233.6
47.5°	222.2	279.2	361.5	419.9	419.7	377.1	328.4	292.4	261.2	236.9	211.6
50°	198.7	248.4	317.9	384.3	389.8	354.1	307.8	272.1	243.0	217.5	197.2
52.5°	177.6	218.6	281.1	344.8	360.6	329.6	284.7	251.8	223.5	200.0	182.7
55°	150.1	181.8	229.3	288.8	312.8	291.0	251.1	220.3	197.4	177.7	162.7
57.5°	127.0	150.7	188.9	236.8	264.7	251.0	218.1	193.0	173.4	155.6	143.8
60°	112.4	131.9	164.2	204.2	235.1	225.5	197.4	174.1	157.4	141.9	130.8
62.5°	98.7	115.5	143.2	175.7	203.9	199.9	177.0	157.4	142.8	128.8	119.3
65°	79.5	91.6	113.3	138.7	161.5	163.3	146.8	133.6	120.6	109.4	101.0
67.5°	63.2	71.3	86.4	107.9	124.9	131.0	120.9	110.7	100.4	91.8	84.5
70°	53.3	59.8	70.9	88.2	103.9	110.3	104.4	96.5	87.6	80.5	74.3
72.5°	43.2	49.5	57.7	70.4	83.8	90.8	88.7	83.0	75.8	69.8	64.0
75°	32.5	34.5	40.1	48.6	59.1	65.1	66.5	63.6	57.8	53.3	49.9
77.5°	24.0	25.3	27.9	32.3	39.2	44.6	46.8	46.4	42.4	39.9	36.6
80°	19.2	19.9	21.2	23.1	28.3	33.6	35.2	35.2	32.3	31.3	28.1
82.5°	14.6	15.1	15.9	17.0	19.3	24.0	25.7	26.0	24.3	22.9	20.4
85°	8.4	8.1	8.6	9.2	9.6	10.9	13.5	13.9	13.5	11.8	11.1
87.5°	4.0	4.0	3.9	3.6	3.6	3.6	4.3	5.0	4.5	4.1	4.0
90°	5.0	4.4	4.0	3.3	2.5	1.8	1.0	0.3	1.0	1.8	2.5
92.5°	6.5	6.2	6.0	5.8	5.9	6.0	6.1	6.1	6.1	6.0	5.9
95°	10.9	10.5	10.0	10.8	13.1	15.4	17.5	19.8	17.5	15.4	13.1
97.5°	13.7	12.6	11.5	14.1	20.5	26.7	33.0	39.3	33.0	26.7	20.5
100°	15.1	13.9	12.7	16.9	26.1	35.3	44.7	53.9	44.7	35.3	26.1
102.5°	37.1	46.8	56.4	62.2	64.2	66.1	68.1	70.0	68.1	66.1	64.2
105°	55.6	74.1	92.6	100.8	98.8	96.7	94.6	92.7	94.6	96.7	98.8
107.5°	70.4	92.6	114.7	125.0	123.4	121.7	120.1	118.4	120.1	121.7	123.4
110°	92.5	112.1	131.6	140.7	139.3	137.9	136.4	135.0	136.4	137.9	139.3



TEST NUMBER: P331615-830

CATALOG NUMBER: SA2XXRDIP-C290D330U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	144.2	149.0	153.8	155.6	154.4	153.2	151.8	150.6	151.8	153.2	154.4
115°	184.6	182.9	181.3	179.8	178.7	177.6	176.3	175.2	176.3	177.6	178.7
117.5°	205.9	204.8	203.6	202.4	201.1	199.8	198.5	197.3	198.5	199.8	201.1
120°	220.9	219.7	218.5	217.4	216.4	215.4	214.3	213.3	214.3	215.4	216.4
122.5°	235.1	233.8	232.4	231.3	230.2	229.1	228.1	227.0	228.1	229.1	230.2
125°	255.0	253.6	252.4	251.3	250.4	249.5	248.6	247.8	248.6	249.5	250.4
127.5°	273.4	272.4	271.5	270.5	269.6	268.5	267.6	266.6	267.6	268.5	269.6
130°	285.3	284.6	283.8	282.9	281.8	280.7	279.7	278.5	279.7	280.7	281.8
132.5°	296.7	296.0	295.2	294.5	293.5	292.6	291.6	290.8	291.6	292.6	293.5
135°	313.0	312.4	311.8	310.9	309.8	308.8	307.6	306.6	307.6	308.8	309.8
137.5°	327.7	327.1	326.4	325.6	324.9	324.1	323.4	322.6	323.4	324.1	324.9
140°	337.4	336.7	335.9	335.3	334.7	334.1	333.7	333.1	333.7	334.1	334.7
142.5°	346.2	345.3	344.5	343.8	343.4	342.8	342.3	341.9	342.3	342.8	343.4
145°	358.3	357.0	355.9	355.3	355.4	355.5	355.6	355.6	355.6	355.5	355.4
147.5°	369.4	368.2	367.0	366.6	366.8	367.1	367.4	367.7	367.4	367.1	366.8
150°	376.1	374.9	373.9	373.5	374.0	374.5	374.9	375.4	374.9	374.5	374.0
152.5°	382.2	381.2	380.1	379.9	380.4	381.0	381.5	382.0	381.5	381.0	380.4
155°	390.9	390.1	389.3	389.2	389.7	390.4	391.0	391.6	391.0	390.4	389.7
157.5°	398.2	397.7	397.1	397.0	397.6	398.0	398.6	399.1	398.6	398.0	397.6
160°	402.7	402.3	401.9	401.9	402.3	402.7	403.1	403.5	403.1	402.7	402.3
162.5°	406.4	406.0	405.8	405.8	406.1	406.6	407.0	407.4	407.0	406.6	406.1
165°	411.3	411.1	410.9	411.0	411.4	411.8	412.3	412.6	412.3	411.8	411.4
167.5°	415.2	415.0	414.8	414.9	415.3	415.8	416.1	416.5	416.1	415.8	415.3
170°	417.3	417.1	417.0	417.1	417.5	417.9	418.3	418.8	418.3	417.9	417.5
172.5°	418.7	418.6	418.4	418.6	419.0	419.3	419.8	420.2	419.8	419.3	419.0
175°	420.3	420.2	420.0	420.2	420.7	421.1	421.6	422.1	421.6	421.1	420.7
177.5°	420.8	420.8	420.8	420.8	421.2	421.6	422.0	422.4	422.0	421.6	421.2
180°	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1



TEST NUMBER: P331615-830

CATALOG NUMBER: SA2XXRDIP-C290D330U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1
2.5°	607.5	606.2	604.0	600.6	598.5	594.9	592.6	593.9	594.3	593.9	593.6
5°	591.2	586.6	580.4	574.4	568.8	562.9	559.4	558.0	555.0	553.3	552.3
7.5°	571.4	563.6	554.9	544.4	535.6	526.2	521.5	519.2	513.0	509.7	506.8
10°	556.7	544.4	535.6	522.0	513.6	501.4	493.0	493.3	484.9	480.2	476.8
12.5°	540.4	527.0	512.4	500.0	488.4	478.6	468.5	464.5	455.6	451.1	441.9
15°	513.4	497.8	482.4	465.7	453.9	438.7	424.1	406.3	392.0	379.6	376.2
17.5°	484.0	464.6	449.1	429.5	409.3	383.8	366.9	356.6	348.0	341.4	336.5
20°	463.7	444.0	427.5	398.0	370.8	353.5	341.1	333.1	324.1	317.1	313.2
22.5°	442.5	422.0	399.4	366.5	345.3	331.4	320.4	311.2	305.1	299.6	296.1
25°	412.4	389.8	352.8	330.2	313.0	298.4	290.8	285.2	278.8	271.3	267.9
27.5°	380.5	344.8	318.1	301.2	284.9	275.5	268.5	260.2	254.5	251.1	247.5
30°	356.7	320.9	300.2	281.7	270.2	259.7	251.6	246.9	241.3	235.5	233.2
32.5°	330.2	301.6	281.6	266.4	254.6	245.6	239.2	231.6	227.6	224.0	219.1
35°	297.2	275.5	257.3	245.0	233.8	226.5	219.0	214.5	207.3	204.2	202.4
37.5°	269.3	250.5	237.0	223.9	215.0	207.0	202.4	195.2	192.1	187.8	183.8
40°	253.4	235.1	222.1	211.3	201.4	195.5	189.7	183.9	179.2	177.3	172.4
42.5°	237.4	222.4	209.3	197.7	191.1	184.6	177.4	173.1	168.2	165.1	162.1
45°	215.2	201.9	190.8	181.2	173.8	167.2	162.5	155.4	152.7	146.5	143.8
47.5°	195.7	183.3	172.7	163.5	156.5	152.1	145.2	139.7	135.3	131.4	128.1
50°	181.8	171.4	161.2	153.1	146.7	140.4	133.4	130.6	123.8	121.8	119.9
52.5°	169.1	159.3	150.0	141.9	135.5	129.5	123.3	119.6	115.0	113.1	111.7
55°	151.4	141.9	133.0	125.9	119.5	113.3	109.4	104.9	102.7	101.2	99.5
57.5°	133.6	125.1	118.2	111.0	104.5	99.6	95.2	92.5	90.3	88.3	86.2
60°	122.2	114.1	107.9	101.2	94.6	90.6	87.2	83.9	81.3	78.3	77.5
62.5°	110.3	103.1	97.5	91.0	85.2	81.5	78.2	75.2	72.1	67.8	66.5
65°	93.8	88.2	82.2	76.8	71.7	68.1	63.3	59.9	58.6	58.2	58.1
67.5°	78.9	73.6	68.4	63.0	58.3	55.0	52.5	52.0	51.1	50.9	50.2
70°	68.9	64.0	58.9	53.7	49.2	48.6	47.8	46.8	45.8	45.4	45.0
72.5°	60.0	55.0	49.8	45.7	43.7	43.0	42.1	41.2	40.5	40.1	39.9
75°	46.0	41.3	37.9	36.4	35.3	34.7	33.4	32.8	32.3	31.7	31.5
77.5°	33.2	30.4	28.9	28.0	26.9	26.2	25.4	24.8	24.3	24.2	23.8
80°	25.3	23.9	22.9	21.6	21.2	20.4	20.2	19.5	19.7	19.0	19.0
82.5°	19.6	18.0	17.1	16.5	16.0	15.4	15.2	14.9	14.9	14.4	14.4
85°	10.1	9.6	9.2	8.8	8.8	8.1	8.4	8.1	8.1	7.7	7.5
87.5°	3.9	3.9	3.7	3.8	3.9	3.8	3.9	3.8	3.9	3.9	3.8
90°	3.3	4.0	4.4	5.0	5.6	6.1	6.4	6.8	7.1	7.4	7.7
92.5°	5.8	6.0	6.2	6.5	6.8	7.1	7.3	7.4	7.6	7.7	7.9
95°	10.8	10.0	10.5	10.9	11.4	11.9	12.3	12.5	12.9	13.2	13.4
97.5°	14.1	11.5	12.6	13.7	14.8	15.9	16.2	16.5	16.7	17.0	17.2
100°	16.9	12.7	13.9	15.1	16.2	17.3	17.9	18.5	19.0	19.5	19.9
102.5°	62.2	56.4	46.8	37.1	27.5	17.8	18.6	19.2	20.0	20.6	21.1
105°	100.8	92.6	74.1	55.6	37.0	18.6	19.3	20.1	20.8	21.6	22.1
107.5°	125.0	114.7	92.6	70.4	48.2	26.0	25.3	24.5	23.8	23.0	22.7
110°	140.7	131.6	112.1	92.5	72.9	53.3	46.6	39.8	33.0	26.2	23.0



TEST NUMBER: P331615-830

CATALOG NUMBER: SA2XXRDIP-C290D330U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	155.6	153.8	149.0	144.2	139.3	134.5	109.8	85.1	60.4	35.7	23.5
115°	179.8	181.3	182.9	184.6	186.3	188.0	156.7	125.4	94.0	62.6	44.5
117.5°	202.4	203.6	204.8	205.9	207.1	208.3	200.7	193.1	185.5	178.0	166.2
120°	217.4	218.5	219.7	220.9	222.2	223.4	224.2	225.0	225.8	226.6	222.4
122.5°	231.3	232.4	233.8	235.1	236.5	237.8	238.3	238.7	239.2	239.7	239.0
125°	251.3	252.4	253.6	255.0	256.2	257.5	258.0	258.4	258.9	259.4	259.8
127.5°	270.5	271.5	272.4	273.4	274.4	275.3	276.0	276.7	277.4	278.1	278.4
130°	282.9	283.8	284.6	285.3	286.1	286.8	287.5	288.2	289.0	289.7	290.1
132.5°	294.5	295.2	296.0	296.7	297.5	298.2	298.9	299.5	300.1	300.8	301.0
135°	310.9	311.8	312.4	313.0	313.6	314.2	314.9	315.6	316.2	316.9	317.2
137.5°	325.6	326.4	327.1	327.7	328.5	329.1	329.8	330.5	331.1	331.8	332.0
140°	335.3	335.9	336.7	337.4	338.2	338.8	339.5	340.1	340.7	341.3	341.5
142.5°	343.8	344.5	345.3	346.2	347.0	347.9	348.5	349.0	349.6	350.2	350.2
145°	355.3	355.9	357.0	358.3	359.4	360.5	361.0	361.5	361.9	362.4	362.5
147.5°	366.6	367.0	368.2	369.4	370.5	371.6	371.9	372.3	372.7	373.1	373.1
150°	373.5	373.9	374.9	376.1	377.1	378.2	378.6	379.0	379.4	379.8	379.8
152.5°	379.9	380.1	381.2	382.2	383.2	384.3	384.7	385.1	385.5	385.9	385.9
155°	389.2	389.3	390.1	390.9	391.7	392.5	392.9	393.3	393.7	394.2	394.1
157.5°	397.0	397.1	397.7	398.2	398.8	399.4	399.8	400.3	400.8	401.1	401.1
160°	401.9	401.9	402.3	402.7	403.1	403.5	403.9	404.4	404.7	405.1	405.1
162.5°	405.8	405.8	406.0	406.4	406.8	407.2	407.6	408.0	408.5	409.0	409.0
165°	411.0	410.9	411.1	411.3	411.5	411.7	412.2	412.6	413.1	413.6	413.6
167.5°	414.9	414.8	415.0	415.2	415.4	415.6	416.0	416.5	417.0	417.5	417.4
170°	417.1	417.0	417.1	417.3	417.4	417.5	418.0	418.5	419.0	419.4	419.3
172.5°	418.6	418.4	418.6	418.7	418.9	419.0	419.4	419.9	420.4	420.8	420.8
175°	420.2	420.0	420.2	420.3	420.5	420.6	421.0	421.5	422.0	422.4	422.4
177.5°	420.8	420.8	420.8	420.8	420.8	420.9	421.3	421.7	422.1	422.4	422.4
180°	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1



TEST NUMBER: P331615-830

CATALOG NUMBER: SA2XXRDIP-C290D330U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1
2.5°	591.7	592.0	591.5	591.8	591.5	592.0	591.7	593.6	593.9	594.3	593.9
5°	551.3	548.7	548.3	547.7	548.3	548.7	551.3	552.3	553.3	555.0	558.0
7.5°	503.1	502.8	501.6	500.1	501.6	502.8	503.1	506.8	509.7	513.0	519.2
10°	472.1	471.0	470.8	469.3	470.8	471.0	472.1	476.8	480.2	484.9	493.3
12.5°	435.7	428.9	428.2	424.4	428.2	428.9	435.7	441.9	451.1	455.6	464.5
15°	371.1	369.8	365.4	362.7	365.4	369.8	371.1	376.2	379.6	392.0	406.3
17.5°	334.0	329.8	328.5	327.9	328.5	329.8	334.0	336.5	341.4	348.0	356.6
20°	310.2	306.4	305.8	305.3	305.8	306.4	310.2	313.2	317.1	324.1	333.1
22.5°	293.8	289.7	288.1	286.8	288.1	289.7	293.8	296.1	299.6	305.1	311.2
25°	265.7	264.2	263.3	262.9	263.3	264.2	265.7	267.9	271.3	278.8	285.2
27.5°	243.7	240.4	239.8	238.7	239.8	240.4	243.7	247.5	251.1	254.5	260.2
30°	231.2	230.2	228.7	227.3	228.7	230.2	231.2	233.2	235.5	241.3	246.9
32.5°	216.5	215.6	214.2	213.7	214.2	215.6	216.5	219.1	224.0	227.6	231.6
35°	200.2	197.2	195.9	194.0	195.9	197.2	200.2	202.4	204.2	207.3	214.5
37.5°	182.9	181.3	179.6	180.2	179.6	181.3	182.9	183.8	187.8	192.1	195.2
40°	169.6	168.5	168.1	167.9	168.1	168.5	169.6	172.4	177.3	179.2	183.9
42.5°	158.9	156.0	154.9	154.9	154.9	156.0	158.9	162.1	165.1	168.2	173.1
45°	142.8	140.1	138.1	138.3	138.1	140.1	142.8	143.8	146.5	152.7	155.4
47.5°	126.3	126.2	125.0	125.4	125.0	126.2	126.3	128.1	131.4	135.3	139.7
50°	118.4	117.2	116.2	116.5	116.2	117.2	118.4	119.9	121.8	123.8	130.6
52.5°	110.8	109.7	109.1	110.0	109.1	109.7	110.8	111.7	113.1	115.0	119.6
55°	98.5	97.2	97.0	96.8	97.0	97.2	98.5	99.5	101.2	102.7	104.9
57.5°	84.6	83.8	82.5	82.0	82.5	83.8	84.6	86.2	88.3	90.3	92.5
60°	74.7	73.0	70.9	70.7	70.9	73.0	74.7	77.5	78.3	81.3	83.9
62.5°	65.6	65.3	64.8	64.8	64.8	65.3	65.6	66.5	67.8	72.1	75.2
65°	57.6	57.4	57.6	57.8	57.6	57.4	57.6	58.1	58.2	58.6	59.9
67.5°	50.1	49.8	49.4	49.6	49.4	49.8	50.1	50.2	50.9	51.1	52.0
70°	44.5	44.3	44.1	44.1	44.1	44.3	44.5	45.0	45.4	45.8	46.8
72.5°	39.0	39.0	38.8	38.6	38.8	39.0	39.0	39.9	40.1	40.5	41.2
75°	31.3	30.8	30.8	30.8	30.8	30.8	31.3	31.5	31.7	32.3	32.8
77.5°	23.8	23.6	23.4	23.2	23.4	23.6	23.8	23.8	24.2	24.3	24.8
80°	18.9	18.7	18.4	18.4	18.4	18.7	18.9	19.0	19.0	19.7	19.5
82.5°	14.4	14.1	14.1	13.9	14.1	14.1	14.4	14.4	14.4	14.9	14.9
85°	7.7	7.9	7.7	8.1	7.7	7.9	7.7	7.5	7.7	8.1	8.1
87.5°	3.8	3.7	3.9	3.7	3.9	3.7	3.8	3.8	3.9	3.9	3.8
90°	7.8	7.9	8.1	8.2	8.1	7.9	7.8	7.7	7.4	7.1	6.8
92.5°	8.0	8.1	8.1	8.2	8.1	8.1	8.0	7.9	7.7	7.6	7.4
95°	13.3	13.2	13.2	13.1	13.2	13.2	13.3	13.4	13.2	12.9	12.5
97.5°	17.2	17.3	17.4	17.5	17.4	17.3	17.2	17.2	17.0	16.7	16.5
100°	20.0	20.2	20.3	20.5	20.3	20.2	20.0	19.9	19.5	19.0	18.5
102.5°	21.3	21.5	21.7	21.9	21.7	21.5	21.3	21.1	20.6	20.0	19.2
105°	22.3	22.6	22.9	23.2	22.9	22.6	22.3	22.1	21.6	20.8	20.1
107.5°	23.0	23.3	23.6	23.8	23.6	23.3	23.0	22.7	23.0	23.8	24.5
110°	23.3	23.6	23.8	24.0	23.8	23.6	23.3	23.0	26.2	33.0	39.8



TEST NUMBER: P331615-830

CATALOG NUMBER: SA2XXRDIP-C290D330U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	23.7	23.8	24.1	24.3	24.1	23.8	23.7	23.5	35.7	60.4	85.1
115°	39.6	34.8	29.9	25.0	29.9	34.8	39.6	44.5	62.6	94.0	125.4
117.5°	150.1	134.1	118.1	102.1	118.1	134.1	150.1	166.2	178.0	185.5	193.1
120°	213.3	204.2	195.0	185.9	195.0	204.2	213.3	222.4	226.6	225.8	225.0
122.5°	237.3	235.5	233.8	232.0	233.8	235.5	237.3	239.0	239.7	239.2	238.7
125°	260.0	260.1	260.3	260.5	260.3	260.1	260.0	259.8	259.4	258.9	258.4
127.5°	278.5	278.5	278.5	278.6	278.5	278.5	278.5	278.4	278.1	277.4	276.7
130°	290.0	289.9	289.9	289.8	289.9	289.9	290.0	290.1	289.7	289.0	288.2
132.5°	301.0	301.0	300.9	300.8	300.9	301.0	301.0	301.0	300.8	300.1	299.5
135°	317.1	316.9	316.8	316.6	316.8	316.9	317.1	317.2	316.9	316.2	315.6
137.5°	331.8	331.6	331.3	331.1	331.3	331.6	331.8	332.0	331.8	331.1	330.5
140°	341.1	340.8	340.4	340.1	340.4	340.8	341.1	341.5	341.3	340.7	340.1
142.5°	349.9	349.6	349.2	348.8	349.2	349.6	349.9	350.2	350.2	349.6	349.0
145°	362.1	361.8	361.5	361.1	361.5	361.8	362.1	362.5	362.4	361.9	361.5
147.5°	372.8	372.5	372.2	371.9	372.2	372.5	372.8	373.1	373.1	372.7	372.3
150°	379.6	379.2	378.8	378.5	378.8	379.2	379.6	379.8	379.8	379.4	379.0
152.5°	385.4	385.0	384.6	384.1	384.6	385.0	385.4	385.9	385.9	385.5	385.1
155°	393.5	393.0	392.5	391.9	392.5	393.0	393.5	394.1	394.2	393.7	393.3
157.5°	400.6	400.1	399.5	399.1	399.5	400.1	400.6	401.1	401.1	400.8	400.3
160°	404.6	404.2	403.7	403.2	403.7	404.2	404.6	405.1	405.1	404.7	404.4
162.5°	408.3	407.7	407.2	406.6	407.2	407.7	408.3	409.0	409.0	408.5	408.0
165°	413.1	412.6	412.2	411.7	412.2	412.6	413.1	413.6	413.6	413.1	412.6
167.5°	416.8	416.1	415.6	414.9	415.6	416.1	416.8	417.4	417.5	417.0	416.5
170°	418.8	418.1	417.5	416.9	417.5	418.1	418.8	419.3	419.4	419.0	418.5
172.5°	420.2	419.6	419.0	418.4	419.0	419.6	420.2	420.8	420.8	420.4	419.9
175°	421.7	421.0	420.3	419.6	420.3	421.0	421.7	422.4	422.4	422.0	421.5
177.5°	421.9	421.4	420.9	420.5	420.9	421.4	421.9	422.4	422.4	422.1	421.7
180°	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1



TEST NUMBER: P331615-830
 CATALOG NUMBER: SA2XXRDIP-C290D330U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1
2.5°	592.6	594.9	598.5	600.6	604.0	606.2	607.5	609.6	610.9	615.2	619.6
5°	559.4	562.9	568.8	574.4	580.4	586.6	591.2	596.3	601.0	609.1	617.6
7.5°	521.5	526.2	535.6	544.4	554.9	563.6	571.4	580.1	588.0	599.6	611.8
10°	493.0	501.4	513.6	522.0	535.6	544.4	556.7	566.3	577.2	592.7	606.3
12.5°	468.5	478.6	488.4	500.0	512.4	527.0	540.4	552.8	565.7	581.6	597.8
15°	424.1	438.7	453.9	465.7	482.4	497.8	513.4	530.1	545.9	565.1	586.0
17.5°	366.9	383.8	409.3	429.5	449.1	464.6	484.0	504.2	522.8	545.8	569.2
20°	341.1	353.5	370.8	398.0	427.5	444.0	463.7	486.0	507.4	532.4	557.5
22.5°	320.4	331.4	345.3	366.5	399.4	422.0	442.5	465.1	489.9	515.5	543.3
25°	290.8	298.4	313.0	330.2	352.8	389.8	412.4	435.1	462.0	489.5	521.1
27.5°	268.5	275.5	284.9	301.2	318.1	344.8	380.5	405.3	432.2	463.0	495.9
30°	251.6	259.7	270.2	281.7	300.2	320.9	356.7	385.4	411.9	443.7	478.7
32.5°	239.2	245.6	254.6	266.4	281.6	301.6	330.2	365.0	390.9	424.2	460.9
35°	219.0	226.5	233.8	245.0	257.3	275.5	297.2	334.4	360.1	393.0	429.9
37.5°	202.4	207.0	215.0	223.9	237.0	250.5	269.3	302.7	330.5	362.8	400.5
40°	189.7	195.5	201.4	211.3	222.1	235.1	253.4	278.3	310.2	342.0	378.7
42.5°	177.4	184.6	191.1	197.7	209.3	222.4	237.4	258.4	291.1	321.0	356.8
45°	162.5	167.2	173.8	181.2	190.8	201.9	215.2	233.6	264.9	290.8	324.3
47.5°	145.2	152.1	156.5	163.5	172.7	183.3	195.7	211.6	236.9	261.2	292.4
50°	133.4	140.4	146.7	153.1	161.2	171.4	181.8	197.2	217.5	243.0	272.1
52.5°	123.3	129.5	135.5	141.9	150.0	159.3	169.1	182.7	200.0	223.5	251.8
55°	109.4	113.3	119.5	125.9	133.0	141.9	151.4	162.7	177.7	197.4	220.3
57.5°	95.2	99.6	104.5	111.0	118.2	125.1	133.6	143.8	155.6	173.4	193.0
60°	87.2	90.6	94.6	101.2	107.9	114.1	122.2	130.8	141.9	157.4	174.1
62.5°	78.2	81.5	85.2	91.0	97.5	103.1	110.3	119.3	128.8	142.8	157.4
65°	63.3	68.1	71.7	76.8	82.2	88.2	93.8	101.0	109.4	120.6	133.6
67.5°	52.5	55.0	58.3	63.0	68.4	73.6	78.9	84.5	91.8	100.4	110.7
70°	47.8	48.6	49.2	53.7	58.9	64.0	68.9	74.3	80.5	87.6	96.5
72.5°	42.1	43.0	43.7	45.7	49.8	55.0	60.0	64.0	69.8	75.8	83.0
75°	33.4	34.7	35.3	36.4	37.9	41.3	46.0	49.9	53.3	57.8	63.6
77.5°	25.4	26.2	26.9	28.0	28.9	30.4	33.2	36.6	39.9	42.4	46.4
80°	20.2	20.4	21.2	21.6	22.9	23.9	25.3	28.1	31.3	32.3	35.2
82.5°	15.2	15.4	16.0	16.5	17.1	18.0	19.6	20.4	22.9	24.3	26.0
85°	8.4	8.1	8.8	8.8	9.2	9.6	10.1	11.1	11.8	13.5	13.9
87.5°	3.9	3.8	3.9	3.8	3.7	3.9	3.9	4.0	4.1	4.5	5.0
90°	6.4	6.1	5.6	5.0	4.4	4.0	3.3	2.5	1.8	1.0	0.3
92.5°	7.3	7.1	6.8	6.5	6.2	6.0	5.8	5.9	6.0	6.1	6.1
95°	12.3	11.9	11.4	10.9	10.5	10.0	10.8	13.1	15.4	17.5	19.8
97.5°	16.2	15.9	14.8	13.7	12.6	11.5	14.1	20.5	26.7	33.0	39.3
100°	17.9	17.3	16.2	15.1	13.9	12.7	16.9	26.1	35.3	44.7	53.9
102.5°	18.6	17.8	27.5	37.1	46.8	56.4	62.2	64.2	66.1	68.1	70.0
105°	19.3	18.6	37.0	55.6	74.1	92.6	100.8	98.8	96.7	94.6	92.7
107.5°	25.3	26.0	48.2	70.4	92.6	114.7	125.0	123.4	121.7	120.1	118.4
110°	46.6	53.3	72.9	92.5	112.1	131.6	140.7	139.3	137.9	136.4	135.0



TEST NUMBER: P331615-830

CATALOG NUMBER: SA2XXRDIP-C290D330U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	109.8	134.5	139.3	144.2	149.0	153.8	155.6	154.4	153.2	151.8	150.6
115°	156.7	188.0	186.3	184.6	182.9	181.3	179.8	178.7	177.6	176.3	175.2
117.5°	200.7	208.3	207.1	205.9	204.8	203.6	202.4	201.1	199.8	198.5	197.3
120°	224.2	223.4	222.2	220.9	219.7	218.5	217.4	216.4	215.4	214.3	213.3
122.5°	238.3	237.8	236.5	235.1	233.8	232.4	231.3	230.2	229.1	228.1	227.0
125°	258.0	257.5	256.2	255.0	253.6	252.4	251.3	250.4	249.5	248.6	247.8
127.5°	276.0	275.3	274.4	273.4	272.4	271.5	270.5	269.6	268.5	267.6	266.6
130°	287.5	286.8	286.1	285.3	284.6	283.8	282.9	281.8	280.7	279.7	278.5
132.5°	298.9	298.2	297.5	296.7	296.0	295.2	294.5	293.5	292.6	291.6	290.8
135°	314.9	314.2	313.6	313.0	312.4	311.8	310.9	309.8	308.8	307.6	306.6
137.5°	329.8	329.1	328.5	327.7	327.1	326.4	325.6	324.9	324.1	323.4	322.6
140°	339.5	338.8	338.2	337.4	336.7	335.9	335.3	334.7	334.1	333.7	333.1
142.5°	348.5	347.9	347.0	346.2	345.3	344.5	343.8	343.4	342.8	342.3	341.9
145°	361.0	360.5	359.4	358.3	357.0	355.9	355.3	355.4	355.5	355.6	355.6
147.5°	371.9	371.6	370.5	369.4	368.2	367.0	366.6	366.8	367.1	367.4	367.7
150°	378.6	378.2	377.1	376.1	374.9	373.9	373.5	374.0	374.5	374.9	375.4
152.5°	384.7	384.3	383.2	382.2	381.2	380.1	379.9	380.4	381.0	381.5	382.0
155°	392.9	392.5	391.7	390.9	390.1	389.3	389.2	389.7	390.4	391.0	391.6
157.5°	399.8	399.4	398.8	398.2	397.7	397.1	397.0	397.6	398.0	398.6	399.1
160°	403.9	403.5	403.1	402.7	402.3	401.9	401.9	402.3	402.7	403.1	403.5
162.5°	407.6	407.2	406.8	406.4	406.0	405.8	405.8	406.1	406.6	407.0	407.4
165°	412.2	411.7	411.5	411.3	411.1	410.9	411.0	411.4	411.8	412.3	412.6
167.5°	416.0	415.6	415.4	415.2	415.0	414.8	414.9	415.3	415.8	416.1	416.5
170°	418.0	417.5	417.4	417.3	417.1	417.0	417.1	417.5	417.9	418.3	418.8
172.5°	419.4	419.0	418.9	418.7	418.6	418.4	418.6	419.0	419.3	419.8	420.2
175°	421.0	420.6	420.5	420.3	420.2	420.0	420.2	420.7	421.1	421.6	422.1
177.5°	421.3	420.9	420.8	420.8	420.8	420.8	420.8	421.2	421.6	422.0	422.4
180°	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1



TEST NUMBER: P331615-830

CATALOG NUMBER: SA2XXRDIP-C290D330U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1
2.5°	619.8	620.3	623.7	625.3	628.3	629.5	630.9	630.6	630.6	631.2	636.0
5°	621.1	625.4	631.8	638.0	644.0	649.1	652.6	656.0	657.3	663.5	669.0
7.5°	618.9	626.8	637.3	646.9	658.2	667.0	674.4	681.1	685.6	694.7	703.9
10°	616.0	627.1	639.0	651.3	666.9	678.7	690.7	699.9	702.9	716.3	724.1
12.5°	610.1	625.0	640.3	656.1	671.4	687.6	700.8	710.0	720.6	732.6	746.9
15°	601.4	618.5	638.5	658.7	680.6	700.3	714.4	730.5	742.1	755.4	767.8
17.5°	588.9	611.0	636.2	659.8	685.0	706.2	725.7	741.0	749.1	756.8	758.6
20°	578.9	602.7	632.4	660.3	685.5	709.9	729.2	742.1	744.2	744.4	733.1
22.5°	568.2	595.0	626.1	654.6	684.9	712.0	727.0	732.4	724.0	709.5	687.5
25°	548.3	579.4	615.6	648.1	681.1	706.7	711.9	702.3	672.5	641.2	601.6
27.5°	526.8	561.8	600.5	636.7	671.8	687.8	676.7	641.9	588.3	541.7	485.2
30°	511.0	550.3	588.3	628.8	661.4	668.2	642.7	591.5	529.0	458.8	402.5
32.5°	493.0	534.1	576.0	617.8	645.1	638.4	596.3	533.3	460.1	391.0	337.8
35°	467.4	509.7	555.0	596.9	614.3	585.3	522.4	440.4	365.4	301.0	264.4
37.5°	437.7	483.9	530.8	569.4	568.2	520.0	434.2	349.6	286.6	248.5	222.4
40°	416.6	463.4	514.1	546.6	532.7	470.0	377.0	297.2	251.1	220.7	201.7
42.5°	396.4	443.3	493.7	519.5	495.3	418.2	325.6	263.1	225.1	201.4	186.0
45°	362.0	411.5	458.2	472.5	429.2	344.3	263.3	217.9	192.7	175.1	164.5
47.5°	328.4	377.1	419.7	419.9	361.5	279.2	222.2	188.6	167.0	153.4	145.7
50°	307.8	354.1	389.8	384.3	317.9	248.4	198.7	169.8	151.8	141.3	133.2
52.5°	284.7	329.6	360.6	344.8	281.1	218.6	177.6	153.4	138.5	129.3	122.1
55°	251.1	291.0	312.8	288.8	229.3	181.8	150.1	131.0	119.9	112.2	105.9
57.5°	218.1	251.0	264.7	236.8	188.9	150.7	127.0	112.6	101.6	96.0	92.8
60°	197.4	225.5	235.1	204.2	164.2	131.9	112.4	99.2	91.0	87.4	84.2
62.5°	177.0	199.9	203.9	175.7	143.2	115.5	98.7	87.5	82.1	78.6	75.6
65°	146.8	163.3	161.5	138.7	113.3	91.6	79.5	72.6	68.5	63.6	58.2
67.5°	120.9	131.0	124.9	107.9	86.4	71.3	63.2	58.1	53.0	48.4	47.1
70°	104.4	110.3	103.9	88.2	70.9	59.8	53.3	47.1	44.1	43.1	41.1
72.5°	88.7	90.8	83.8	70.4	57.7	49.5	43.2	39.8	38.1	37.2	36.0
75°	66.5	65.1	59.1	48.6	40.1	34.5	32.5	31.3	30.2	29.3	28.7
77.5°	46.8	44.6	39.2	32.3	27.9	25.3	24.0	23.4	22.9	22.4	21.8
80°	35.2	33.6	28.3	23.1	21.2	19.9	19.2	18.4	18.4	18.0	17.3
82.5°	25.7	24.0	19.3	17.0	15.9	15.1	14.6	14.1	13.9	14.0	13.6
85°	13.5	10.9	9.6	9.2	8.6	8.1	8.4	7.9	7.9	7.9	7.7
87.5°	4.3	3.6	3.6	3.6	3.9	4.0	4.0	4.1	4.3	4.2	4.4
90°	1.0	1.8	2.5	3.3	4.0	4.4	5.0	5.6	6.1	6.4	6.8
92.5°	6.1	6.0	5.9	5.8	6.0	6.2	6.5	6.8	7.1	7.3	7.4
95°	17.5	15.4	13.1	10.8	10.0	10.5	10.9	11.4	11.9	12.3	12.5
97.5°	33.0	26.7	20.5	14.1	11.5	12.6	13.7	14.8	15.9	16.2	16.5
100°	44.7	35.3	26.1	16.9	12.7	13.9	15.1	16.2	17.3	17.9	18.5
102.5°	68.1	66.1	64.2	62.2	56.4	46.8	37.1	27.5	17.8	18.6	19.2
105°	94.6	96.7	98.8	100.8	92.6	74.1	55.6	37.0	18.6	19.3	20.1
107.5°	120.1	121.7	123.4	125.0	114.7	92.6	70.4	48.2	26.0	25.3	24.5
110°	136.4	137.9	139.3	140.7	131.6	112.1	92.5	72.9	53.3	46.6	39.8



TEST NUMBER: P331615-830

CATALOG NUMBER: SA2XXRDIP-C290D330U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	151.8	153.2	154.4	155.6	153.8	149.0	144.2	139.3	134.5	109.8	85.1
115°	176.3	177.6	178.7	179.8	181.3	182.9	184.6	186.3	188.0	156.7	125.4
117.5°	198.5	199.8	201.1	202.4	203.6	204.8	205.9	207.1	208.3	200.7	193.1
120°	214.3	215.4	216.4	217.4	218.5	219.7	220.9	222.2	223.4	224.2	225.0
122.5°	228.1	229.1	230.2	231.3	232.4	233.8	235.1	236.5	237.8	238.3	238.7
125°	248.6	249.5	250.4	251.3	252.4	253.6	255.0	256.2	257.5	258.0	258.4
127.5°	267.6	268.5	269.6	270.5	271.5	272.4	273.4	274.4	275.3	276.0	276.7
130°	279.7	280.7	281.8	282.9	283.8	284.6	285.3	286.1	286.8	287.5	288.2
132.5°	291.6	292.6	293.5	294.5	295.2	296.0	296.7	297.5	298.2	298.9	299.5
135°	307.6	308.8	309.8	310.9	311.8	312.4	313.0	313.6	314.2	314.9	315.6
137.5°	323.4	324.1	324.9	325.6	326.4	327.1	327.7	328.5	329.1	329.8	330.5
140°	333.7	334.1	334.7	335.3	335.9	336.7	337.4	338.2	338.8	339.5	340.1
142.5°	342.3	342.8	343.4	343.8	344.5	345.3	346.2	347.0	347.9	348.5	349.0
145°	355.6	355.5	355.4	355.3	355.9	357.0	358.3	359.4	360.5	361.0	361.5
147.5°	367.4	367.1	366.8	366.6	367.0	368.2	369.4	370.5	371.6	371.9	372.3
150°	374.9	374.5	374.0	373.5	373.9	374.9	376.1	377.1	378.2	378.6	379.0
152.5°	381.5	381.0	380.4	379.9	380.1	381.2	382.2	383.2	384.3	384.7	385.1
155°	391.0	390.4	389.7	389.2	389.3	390.1	390.9	391.7	392.5	392.9	393.3
157.5°	398.6	398.0	397.6	397.0	397.1	397.7	398.2	398.8	399.4	399.8	400.3
160°	403.1	402.7	402.3	401.9	401.9	402.3	402.7	403.1	403.5	403.9	404.4
162.5°	407.0	406.6	406.1	405.8	405.8	406.0	406.4	406.8	407.2	407.6	408.0
165°	412.3	411.8	411.4	411.0	410.9	411.1	411.3	411.5	411.7	412.2	412.6
167.5°	416.1	415.8	415.3	414.9	414.8	415.0	415.2	415.4	415.6	416.0	416.5
170°	418.3	417.9	417.5	417.1	417.0	417.1	417.3	417.4	417.5	418.0	418.5
172.5°	419.8	419.3	419.0	418.6	418.4	418.6	418.7	418.9	419.0	419.4	419.9
175°	421.6	421.1	420.7	420.2	420.0	420.2	420.3	420.5	420.6	421.0	421.5
177.5°	422.0	421.6	421.2	420.8	420.8	420.8	420.8	420.8	420.9	421.3	421.7
180°	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1



TEST NUMBER: P331615-830
 CATALOG NUMBER: SA2XXRDIP-C290D330U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	616.1	616.1	616.1	616.1	616.1	616.1	616.1
2.5°	637.7	640.0	641.0	641.0	642.2	641.7	641.2
5°	674.4	678.4	679.4	683.2	686.0	685.1	685.5
7.5°	710.9	717.4	723.9	726.8	727.3	729.0	729.6
10°	733.3	738.7	748.7	747.2	754.7	759.0	752.0
12.5°	754.9	762.1	769.1	771.0	775.2	776.7	773.8
15°	774.4	778.3	778.6	777.6	778.9	777.8	773.7
17.5°	756.2	749.9	737.3	731.2	726.5	719.4	716.6
20°	726.0	707.6	686.2	677.6	667.6	647.9	652.6
22.5°	660.9	640.0	618.5	593.5	581.5	562.9	561.8
25°	559.7	523.5	483.6	455.8	439.5	420.9	412.7
27.5°	435.2	389.6	356.9	340.4	325.4	310.7	310.0
30°	353.3	319.1	293.8	279.7	270.4	264.2	265.5
32.5°	297.7	274.3	257.2	245.5	238.7	234.0	233.9
35°	243.5	227.3	216.4	211.5	206.6	203.2	203.4
37.5°	208.3	198.7	192.6	187.2	184.1	182.4	181.4
40°	190.3	182.4	177.7	174.5	171.9	169.6	169.1
42.5°	176.2	169.6	164.9	162.3	159.9	158.3	157.9
45°	156.3	150.9	146.7	143.8	142.8	141.3	141.3
47.5°	139.0	133.7	130.4	128.7	126.9	125.8	125.8
50°	127.4	123.3	120.4	119.2	117.7	117.2	116.9
52.5°	117.0	113.9	111.8	111.0	110.4	109.6	109.7
55°	102.7	101.0	100.2	99.5	98.5	97.2	98.0
57.5°	90.9	89.4	87.1	85.0	84.1	83.1	83.5
60°	82.5	79.5	76.4	74.1	73.4	71.5	71.5
62.5°	71.8	67.6	63.9	62.6	61.9	61.1	60.9
65°	55.2	53.5	52.7	51.8	51.4	51.4	51.0
67.5°	45.8	45.1	44.1	43.9	43.5	43.4	43.3
70°	40.4	39.6	39.2	38.9	38.5	38.7	38.1
72.5°	35.3	34.7	34.6	34.0	33.7	33.7	33.3
75°	27.8	27.8	27.6	27.4	27.0	26.8	27.0
77.5°	21.4	21.5	21.1	21.0	21.0	21.0	20.8
80°	17.2	17.3	17.2	16.9	16.7	16.9	16.7
82.5°	13.6	13.2	13.2	13.1	13.1	13.0	12.9
85°	7.7	7.9	7.7	7.5	7.5	7.5	7.7
87.5°	4.3	4.4	4.4	4.4	4.5	4.5	4.4
90°	7.1	7.4	7.7	7.8	7.9	8.1	8.2
92.5°	7.6	7.7	7.9	8.0	8.1	8.1	8.2
95°	12.9	13.2	13.4	13.3	13.2	13.2	13.1
97.5°	16.7	17.0	17.2	17.2	17.3	17.4	17.5
100°	19.0	19.5	19.9	20.0	20.2	20.3	20.5
102.5°	20.0	20.6	21.1	21.3	21.5	21.7	21.9
105°	20.8	21.6	22.1	22.3	22.6	22.9	23.2
107.5°	23.8	23.0	22.7	23.0	23.3	23.6	23.8
110°	33.0	26.2	23.0	23.3	23.6	23.8	24.0



TEST NUMBER: P331615-830

CATALOG NUMBER: SA2XXRDIP-C290D330U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	60.4	35.7	23.5	23.7	23.8	24.1	24.3
115°	94.0	62.6	44.5	39.6	34.8	29.9	25.0
117.5°	185.5	178.0	166.2	150.1	134.1	118.1	102.1
120°	225.8	226.6	222.4	213.3	204.2	195.0	185.9
122.5°	239.2	239.7	239.0	237.3	235.5	233.8	232.0
125°	258.9	259.4	259.8	260.0	260.1	260.3	260.5
127.5°	277.4	278.1	278.4	278.5	278.5	278.5	278.6
130°	289.0	289.7	290.1	290.0	289.9	289.9	289.8
132.5°	300.1	300.8	301.0	301.0	301.0	300.9	300.8
135°	316.2	316.9	317.2	317.1	316.9	316.8	316.6
137.5°	331.1	331.8	332.0	331.8	331.6	331.3	331.1
140°	340.7	341.3	341.5	341.1	340.8	340.4	340.1
142.5°	349.6	350.2	350.2	349.9	349.6	349.2	348.8
145°	361.9	362.4	362.5	362.1	361.8	361.5	361.1
147.5°	372.7	373.1	373.1	372.8	372.5	372.2	371.9
150°	379.4	379.8	379.8	379.6	379.2	378.8	378.5
152.5°	385.5	385.9	385.9	385.4	385.0	384.6	384.1
155°	393.7	394.2	394.1	393.5	393.0	392.5	391.9
157.5°	400.8	401.1	401.1	400.6	400.1	399.5	399.1
160°	404.7	405.1	405.1	404.6	404.2	403.7	403.2
162.5°	408.5	409.0	409.0	408.3	407.7	407.2	406.6
165°	413.1	413.6	413.6	413.1	412.6	412.2	411.7
167.5°	417.0	417.5	417.4	416.8	416.1	415.6	414.9
170°	419.0	419.4	419.3	418.8	418.1	417.5	416.9
172.5°	420.4	420.8	420.8	420.2	419.6	419.0	418.4
175°	422.0	422.4	422.4	421.7	421.0	420.3	419.6
177.5°	422.1	422.4	422.4	421.9	421.4	420.9	420.5
180°	421.1	421.1	421.1	421.1	421.1	421.1	421.1

(END OF REPORT)