

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333572-840

Luminaire Tested: **S125RDIP-S850D1035U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333572-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S850D1035U840-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6898.5 lumens
Efficiency: N/A
Efficacy: 132.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333572-840

CATALOG NUMBER: S125RDIP-S850D1035U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333572-840

CATALOG NUMBER: S125RDIP-S850D1035U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	48	47	46
2	89	82	76	71	82	75	70	66	63	60	56	53	50	47	42	41	39
3	81	72	65	59	74	66	60	55	56	51	48	47	43	40	38	35	33
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	31	28	25
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	22
7	58	46	38	33	53	43	36	31	37	31	27	31	27	24	25	22	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	18	16
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8969	8969	8969
5°	8989	8887	8941
10°	8921	8804	8804
15°	8815	8625	8555
20°	8678	8376	8276
25°	8521	8131	7952
30°	8322	7845	7594
35°	8121	7550	7194
40°	7932	7242	6800
45°	7701	6898	6370
50°	7471	6523	5923
55°	7203	6164	5444
60°	6935	5730	4930
65°	6619	5225	4343
70°	6258	4594	3743
75°	5759	3873	3114
80°	5069	3042	2615
85°	4276	2482	2334



TEST NUMBER: P333572-840

CATALOG NUMBER: S125RDIP-S850D1035U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.6	1.9
10°-20°	364.9	5.3
20°-30°	529.2	7.7
30°-40°	603.1	8.7
40°-50°	587.8	8.5
50°-60°	494.8	7.2
60°-70°	346.9	5.0
70°-80°	178.3	2.6
80°-90°	47.9	0.7
90°-100°	86.8	1.3
100°-110°	256.2	3.7
110°-120°	434.0	6.3
120°-130°	571.2	8.3
130°-140°	640.0	9.3
140°-150°	627.3	9.1
150°-160°	526.9	7.6
160°-170°	350.2	5.1
170°-180°	122.6	1.8
0°-30°	1024.6	14.9
0°-40°	1627.7	23.6
0°-60°	2710.4	39.3
0°-90°	3283.4	47.6
90°-120°	777.0	11.3
90°-150°	2615.5	37.9
90°-180°	3615.0	52.4
0°-180°	6898.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1389	1389	1389	1389	1389	
5°	1386	1382	1371	1381	1379	131
15°	1318	1311	1290	1289	1280	371
25°	1196	1179	1141	1128	1116	550
35°	1030	1004	958	928	912	645
45°	843	811	755	715	697	650
55°	640	605	547	502	484	572
65°	433	396	342	301	284	429
75°	231	199	155	133	125	244
85°	58	40	34	32	32	65
90°	1	9	16	21	24	6
95°	66	68	78	84	87	70
105°	230	235	241	247	250	245
115°	434	438	441	440	439	430
125°	634	640	641	639	638	568
135°	825	830	832	832	828	635
145°	999	1003	1006	1006	1003	624
155°	1143	1143	1144	1148	1143	526
165°	1243	1241	1242	1246	1240	351
175°	1292	1289	1288	1294	1288	123
180°	1296	1296	1296	1296	1296	



TEST NUMBER: P333572-840

CATALOG NUMBER: S125RDIP-S850D1035U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7
2.5°	1391.1	1390.6	1390.0	1389.5	1388.9	1387.7	1385.8	1383.9	1382.1	1380.2	1382.1
5°	1386.5	1385.6	1384.6	1383.7	1382.8	1381.1	1378.5	1375.9	1373.3	1370.8	1373.1
7.5°	1372.9	1372.0	1371.1	1370.2	1369.4	1367.4	1364.3	1361.2	1358.2	1355.0	1356.7
10°	1360.3	1359.6	1358.9	1358.2	1357.5	1355.5	1352.3	1349.0	1345.7	1342.5	1343.1
12.5°	1346.0	1345.1	1344.2	1343.4	1342.5	1339.9	1335.4	1331.1	1326.8	1322.3	1322.8
15°	1318.4	1317.0	1315.6	1314.1	1312.7	1309.6	1304.7	1299.8	1294.9	1290.0	1289.8
17.5°	1287.1	1285.0	1282.8	1280.7	1278.5	1274.3	1268.2	1262.0	1255.9	1249.7	1248.6
20°	1262.7	1260.4	1258.1	1255.8	1253.4	1248.5	1241.1	1233.7	1226.2	1218.7	1217.6
22.5°	1235.9	1233.6	1231.2	1228.9	1226.6	1221.5	1213.7	1205.9	1198.0	1190.2	1187.9
25°	1195.7	1192.1	1188.6	1185.2	1181.6	1175.6	1167.0	1158.3	1149.7	1141.1	1138.1
27.5°	1149.5	1145.3	1141.0	1136.8	1132.6	1125.8	1116.6	1107.3	1098.1	1088.8	1084.6
30°	1115.9	1111.5	1107.1	1102.7	1098.2	1091.1	1081.4	1071.6	1061.8	1052.0	1046.6
32.5°	1083.2	1078.0	1072.9	1067.7	1062.5	1054.9	1045.0	1035.0	1025.0	1015.0	1009.2
35°	1030.0	1024.3	1018.8	1013.1	1007.5	999.5	989.1	978.6	968.1	957.6	950.8
37.5°	977.7	970.9	964.1	957.3	950.5	941.7	930.9	920.0	909.2	898.4	890.3
40°	940.8	933.8	926.8	919.8	912.8	903.7	892.5	881.3	870.2	859.0	850.1
42.5°	902.2	895.0	887.9	880.6	873.4	864.1	852.5	841.0	829.4	817.9	809.4
45°	843.2	836.5	829.7	822.9	816.2	806.4	793.6	780.8	768.0	755.2	745.8
47.5°	782.2	775.1	767.9	760.8	753.7	743.7	730.7	717.8	704.9	692.0	682.4
50°	743.6	735.9	728.2	720.5	712.9	702.4	689.0	675.8	662.5	649.2	639.4
52.5°	701.7	693.8	685.9	678.0	670.1	659.9	647.4	634.9	622.3	609.8	599.3
55°	639.7	632.3	624.9	617.4	610.0	599.7	586.6	573.6	560.6	547.4	536.9
57.5°	577.2	569.3	561.3	553.3	545.4	535.1	522.5	509.9	497.4	484.7	474.5
60°	536.9	528.9	520.7	512.5	504.3	494.0	481.4	468.8	456.3	443.6	433.4
62.5°	494.2	486.5	478.7	470.8	463.0	452.8	440.0	427.3	414.4	401.7	392.2
65°	433.1	425.3	417.3	409.4	401.4	391.3	379.0	366.6	354.3	341.9	332.5
67.5°	372.5	364.6	356.7	348.8	340.8	330.9	319.1	307.3	295.5	283.6	275.1
70°	331.4	323.5	315.6	307.6	299.7	289.9	278.3	266.6	255.0	243.3	236.1
72.5°	291.1	283.4	275.7	267.9	260.2	250.9	239.9	229.0	218.1	207.2	200.6
75°	230.8	223.8	216.7	209.7	202.8	194.4	184.6	174.8	165.0	155.2	150.1
77.5°	170.8	165.1	159.6	154.0	148.3	141.7	133.8	126.0	118.2	110.4	106.7
80°	136.3	130.8	125.1	119.6	114.0	108.0	101.4	94.8	88.4	81.8	79.7
82.5°	102.8	97.8	92.7	87.7	82.6	77.9	73.4	69.0	64.4	60.0	59.0
85°	57.7	53.5	49.3	45.1	40.9	38.2	37.1	35.9	34.7	33.5	33.3
87.5°	19.5	18.6	17.6	16.7	15.8	15.3	15.5	15.6	15.7	15.9	16.1
90°	1.0	2.8	4.5	6.4	8.2	9.9	11.4	13.0	14.5	16.2	17.3
92.5°	24.4	25.7	26.9	28.2	29.4	31.0	32.9	34.8	36.8	38.7	40.2
95°	65.5	65.9	66.4	66.9	67.4	68.7	70.9	73.1	75.4	77.7	79.2
97.5°	108.9	109.1	109.3	109.5	109.6	111.3	114.3	117.4	120.5	123.6	125.1
100°	141.2	141.2	141.2	141.2	141.2	142.6	145.5	148.5	151.4	154.2	156.2
102.5°	175.8	176.7	177.6	178.5	179.5	180.6	182.1	183.6	185.0	186.5	188.7
105°	229.8	231.0	232.1	233.3	234.4	235.6	236.9	238.2	239.6	241.0	242.3
107.5°	289.5	290.6	291.8	293.0	294.1	295.1	296.1	297.2	298.2	299.2	299.9
110°	330.7	331.8	333.0	334.1	335.2	336.1	336.7	337.4	338.1	338.7	339.4



TEST NUMBER: P333572-840

CATALOG NUMBER: S125RDIP-S850D1035U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	372.6	373.2	373.8	374.4	375.0	375.7	376.6	377.4	378.2	379.1	379.4
115°	434.5	435.5	436.4	437.3	438.1	438.8	439.2	439.7	440.1	440.6	440.4
117.5°	496.7	497.1	497.5	497.9	498.3	498.7	499.1	499.5	499.9	500.3	500.5
120°	535.3	536.4	537.6	538.8	539.9	540.5	540.7	541.0	541.2	541.4	541.4
122.5°	577.3	577.7	578.1	578.6	579.0	579.4	580.0	580.6	581.2	581.7	581.6
125°	634.2	635.5	636.8	638.2	639.5	640.4	640.6	640.8	641.0	641.3	640.8
127.5°	694.7	695.4	696.2	696.9	697.7	698.2	698.5	698.7	699.0	699.3	699.0
130°	730.9	732.1	733.2	734.3	735.4	736.2	736.7	737.1	737.5	738.0	737.8
132.5°	767.2	769.1	770.9	772.7	774.6	775.5	775.4	775.3	775.2	775.1	774.9
135°	824.8	826.1	827.4	828.7	830.1	830.9	831.1	831.3	831.5	831.7	831.7
137.5°	878.8	880.0	881.3	882.6	883.9	884.8	885.3	885.9	886.4	886.8	887.1
140°	913.4	914.5	915.6	916.8	917.9	918.8	919.5	920.2	920.8	921.5	921.9
142.5°	948.1	949.1	950.0	950.9	951.9	952.8	953.6	954.5	955.3	956.1	956.4
145°	999.2	1000.1	1000.9	1001.8	1002.7	1003.5	1004.2	1004.8	1005.5	1006.2	1006.2
147.5°	1046.3	1046.8	1047.3	1047.8	1048.2	1048.8	1049.4	1049.9	1050.4	1051.0	1051.5
150°	1077.7	1077.5	1077.3	1077.1	1076.9	1077.2	1078.1	1079.0	1079.8	1080.8	1080.8
152.5°	1103.6	1103.9	1104.2	1104.5	1104.8	1105.2	1105.5	1105.9	1106.2	1106.6	1107.1
155°	1143.3	1143.3	1143.3	1143.3	1143.3	1143.4	1143.7	1143.9	1144.1	1144.3	1145.2
157.5°	1178.8	1178.3	1177.8	1177.3	1176.8	1176.7	1176.9	1177.1	1177.4	1177.6	1178.5
160°	1199.7	1199.1	1198.4	1197.7	1197.1	1196.9	1197.1	1197.3	1197.5	1197.7	1198.6
162.5°	1218.3	1217.8	1217.3	1216.8	1216.4	1216.1	1216.2	1216.2	1216.3	1216.3	1217.4
165°	1243.1	1242.6	1242.2	1241.7	1241.3	1241.2	1241.4	1241.6	1241.8	1242.1	1243.0
167.5°	1264.0	1263.1	1262.3	1261.4	1260.5	1260.0	1260.0	1260.0	1260.0	1260.0	1261.4
170°	1275.4	1274.4	1273.5	1272.7	1271.8	1271.3	1271.3	1271.3	1271.3	1271.3	1272.7
172.5°	1283.4	1282.5	1281.6	1280.7	1279.9	1279.4	1279.4	1279.4	1279.4	1279.4	1280.7
175°	1292.5	1291.6	1290.7	1289.8	1288.9	1288.5	1288.5	1288.5	1288.5	1288.5	1289.8
177.5°	1297.2	1296.5	1295.8	1294.9	1294.2	1293.8	1293.6	1293.4	1293.3	1293.1	1294.2
180°	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6



TEST NUMBER: P333572-840

CATALOG NUMBER: S125RDIP-S850D1035U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7	1388.7
2.5°	1383.9	1385.8	1387.7	1388.6	1388.4	1388.2	1388.0	1387.8
5°	1375.4	1377.8	1380.1	1381.1	1380.6	1380.1	1379.7	1379.2
7.5°	1358.4	1360.0	1361.6	1362.1	1361.6	1361.1	1360.6	1360.1
10°	1343.8	1344.5	1345.2	1345.2	1344.5	1343.8	1343.1	1342.5
12.5°	1323.3	1323.8	1324.3	1324.1	1323.0	1321.9	1320.9	1319.8
15°	1289.6	1289.3	1289.1	1288.0	1285.9	1283.7	1281.6	1279.5
17.5°	1247.4	1246.3	1245.1	1243.6	1241.9	1240.2	1238.5	1236.8
20°	1216.4	1215.2	1214.1	1212.4	1210.3	1208.2	1206.1	1204.1
22.5°	1185.6	1183.4	1181.0	1179.0	1177.3	1175.6	1173.9	1172.2
25°	1135.1	1132.1	1129.0	1126.2	1123.6	1121.1	1118.5	1115.9
27.5°	1080.4	1076.1	1071.9	1068.5	1066.1	1063.6	1061.2	1058.6
30°	1041.3	1035.9	1030.5	1026.8	1024.7	1022.6	1020.5	1018.3
32.5°	1003.2	997.2	991.4	987.0	984.4	981.8	979.1	976.4
35°	944.0	937.3	930.5	925.5	922.2	919.0	915.7	912.4
37.5°	882.2	874.0	866.0	860.3	857.2	853.9	850.8	847.7
40°	841.2	832.4	823.5	817.7	815.0	812.1	809.3	806.6
42.5°	800.9	792.4	784.0	777.6	773.6	769.4	765.3	761.2
45°	736.5	727.2	717.8	711.4	707.9	704.5	700.9	697.4
47.5°	672.8	663.2	653.6	646.8	643.0	639.1	635.2	631.4
50°	629.7	619.9	610.1	603.4	600.0	596.4	592.9	589.5
52.5°	588.8	578.1	567.6	560.6	557.1	553.6	550.2	546.6
55°	526.5	516.0	505.5	498.4	494.7	491.0	487.3	483.5
57.5°	464.2	454.0	443.7	437.0	433.6	430.3	427.1	423.7
60°	423.1	412.8	402.6	395.8	392.2	388.8	385.3	381.7
62.5°	382.6	373.1	363.7	357.2	353.7	350.1	346.7	343.2
65°	323.3	314.0	304.6	298.2	294.7	291.2	287.7	284.2
67.5°	266.5	258.0	249.4	243.8	241.1	238.2	235.4	232.7
70°	228.8	221.7	214.4	209.4	206.6	203.8	201.1	198.2
72.5°	193.9	187.2	180.6	176.3	174.4	172.6	170.8	168.8
75°	145.0	139.9	134.7	131.4	129.7	128.1	126.4	124.8
77.5°	103.1	99.6	95.9	93.6	92.4	91.2	90.0	88.8
80°	77.7	75.5	73.4	72.1	71.7	71.2	70.7	70.3
82.5°	58.1	57.1	56.0	55.4	55.1	54.9	54.6	54.3
85°	33.1	32.8	32.6	32.4	32.1	31.9	31.7	31.5
87.5°	16.3	16.5	16.7	16.8	16.8	16.7	16.7	16.6
90°	18.4	19.5	20.6	21.5	22.2	22.8	23.5	24.2
92.5°	41.7	43.1	44.6	45.6	46.2	46.6	47.1	47.6
95°	80.8	82.3	83.9	84.9	85.3	85.8	86.2	86.7
97.5°	126.5	128.1	129.6	130.4	130.7	131.0	131.2	131.5
100°	158.2	160.3	162.3	163.6	164.0	164.4	164.9	165.3
102.5°	190.9	193.1	195.3	196.7	197.3	197.9	198.6	199.2
105°	243.7	245.0	246.3	247.3	248.0	248.7	249.3	250.0
107.5°	300.5	301.2	301.9	302.3	302.2	302.2	302.2	302.1
110°	340.1	340.7	341.4	341.6	341.4	341.2	341.0	340.7



TEST NUMBER: P333572-840

CATALOG NUMBER: S125RDIP-S850D1035U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	379.7	380.0	380.3	380.3	379.9	379.5	379.1	378.7
115°	440.1	439.9	439.7	439.5	439.2	439.0	438.8	438.6
117.5°	500.6	500.8	501.0	500.6	499.7	498.9	498.0	497.1
120°	541.4	541.4	541.4	541.0	540.1	539.2	538.3	537.3
122.5°	581.4	581.2	581.0	580.6	579.9	579.2	578.5	577.7
125°	640.4	639.9	639.4	639.0	638.8	638.6	638.4	638.2
127.5°	698.8	698.6	698.4	698.0	697.6	697.1	696.7	696.3
130°	737.5	737.3	737.1	736.8	736.3	735.9	735.4	735.0
132.5°	774.7	774.5	774.2	773.8	773.2	772.5	771.9	771.2
135°	831.7	831.7	831.7	831.3	830.4	829.5	828.6	827.7
137.5°	887.4	887.6	887.9	887.5	886.4	885.2	884.1	883.0
140°	922.4	922.8	923.3	922.9	921.8	920.7	919.6	918.5
142.5°	956.7	956.9	957.3	956.8	955.7	954.6	953.5	952.3
145°	1006.2	1006.2	1006.2	1005.8	1005.2	1004.5	1003.8	1003.2
147.5°	1052.0	1052.6	1053.1	1052.6	1051.1	1049.6	1048.0	1046.5
150°	1080.8	1080.8	1080.8	1080.6	1080.2	1079.6	1079.2	1078.7
152.5°	1107.7	1108.2	1108.7	1108.6	1107.8	1107.0	1106.2	1105.4
155°	1146.1	1147.0	1147.9	1147.8	1146.7	1145.5	1144.4	1143.3
157.5°	1179.3	1180.2	1181.1	1180.8	1179.4	1177.9	1176.4	1175.0
160°	1199.5	1200.4	1201.3	1201.2	1200.1	1199.0	1197.9	1196.7
162.5°	1218.4	1219.5	1220.6	1220.5	1219.2	1217.9	1216.6	1215.3
165°	1243.9	1244.8	1245.7	1245.5	1244.2	1242.7	1241.4	1240.1
167.5°	1262.7	1264.0	1265.5	1265.4	1264.0	1262.6	1261.2	1259.8
170°	1274.0	1275.4	1276.7	1276.6	1275.1	1273.4	1271.9	1270.3
172.5°	1282.1	1283.4	1284.8	1284.8	1283.3	1282.0	1280.6	1279.2
175°	1291.2	1292.5	1293.8	1293.7	1292.2	1290.6	1289.0	1287.5
177.5°	1295.3	1296.4	1297.4	1297.4	1296.1	1294.8	1293.5	1292.3
180°	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6

(END OF REPORT)