

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333558-840

Luminaire Tested: **S125RDIP-S850D590U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333558-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S850D590U840-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5453.7 lumens
Efficiency: N/A
Efficacy: 135.3 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333558-840

CATALOG NUMBER: S125RDIP-S850D590U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333558-840

CATALOG NUMBER: S125RDIP-S850D590U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	101	97	93	89	94	90	87	84	79	77	75	69	67	65	59	58	57	52
2	92	85	79	74	86	80	74	70	70	66	62	61	58	55	53	50	49	45
3	84	75	68	62	79	71	64	59	62	57	53	54	51	47	47	44	42	38
4	77	67	59	53	72	63	56	50	55	50	46	49	44	41	42	39	36	33
5	71	60	52	46	66	56	49	44	50	44	40	44	39	36	38	35	32	29
6	66	54	46	40	61	51	43	38	45	39	35	40	35	31	35	31	28	26
7	61	49	41	35	57	46	39	34	41	35	31	36	31	28	32	28	25	23
8	57	44	36	31	53	42	35	30	37	32	27	33	28	25	29	25	23	20
9	53	40	33	28	49	38	31	27	34	29	25	31	26	23	27	23	20	18
10	49	37	30	25	46	35	29	24	32	26	22	28	24	20	25	21	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8250	8250	8250	8250
5°	9491	8261	7295	8261
10°	10887	8218	6437	8218
15°	11760	8134	5722	8134
20°	12967	8036	5283	8036
25°	15007	7906	4903	7906
30°	16330	7770	4653	7770
35°	13775	7611	4424	7611
40°	9620	7325	4226	7325
45°	7136	6940	4032	6940
50°	5690	6539	3867	6539
55°	4829	6040	3719	6040
60°	4173	5594	3481	5594
65°	3718	5113	2997	5113
70°	3269	4683	2732	4683
75°	2827	4057	2565	4057
80°	2146	3414	2146	3414
85°	1786	2682	2023	2682



TEST NUMBER: P333558-840

CATALOG NUMBER: S125RDIP-S850D590U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.5	2.2
10°-20°	359.0	6.6
20°-30°	569.2	10.4
30°-40°	686.4	12.6
40°-50°	613.0	11.2
50°-60°	470.0	8.6
60°-70°	305.5	5.6
70°-80°	148.5	2.7
80°-90°	37.0	0.7
90°-100°	207.1	3.8
100°-110°	445.2	8.2
110°-120°	417.8	7.7
120°-130°	338.6	6.2
130°-140°	271.7	5.0
140°-150°	205.1	3.8
150°-160°	144.3	2.6
160°-170°	85.1	1.6
170°-180°	27.7	0.5
0°-30°	1050.6	19.3
0°-40°	1737.0	31.9
0°-60°	2820.0	51.7
0°-90°	3311.0	60.7
90°-120°	1070.2	19.6
90°-150°	1885.6	34.6
90°-180°	2143.0	39.3
0°-180°	5453.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1277	1277	1277	1277	1277	
5°	1464	1274	1125	1274	1464	146
15°	1759	1217	856	1217	1759	504
25°	2106	1110	688	1110	2106	967
35°	1747	965	561	965	1747	1055
45°	781	760	442	760	781	623
55°	429	536	330	536	429	389
65°	243	335	196	335	243	242
75°	113	163	103	163	113	121
85°	24	36	27	36	24	28
90°	13	1	13	1	13	10
95°	135	19	135	19	135	192
105°	763	65	763	65	763	759
115°	850	116	850	116	850	831
125°	670	161	670	161	670	606
135°	556	189	556	189	556	431
145°	439	220	439	220	439	279
155°	368	251	368	251	368	172
165°	323	274	323	274	323	92
175°	290	285	290	285	290	28
180°	286	286	286	286	286	



TEST NUMBER: P333558-840

CATALOG NUMBER: S125RDIP-S850D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4
2.5°	1343.6	1342.8	1344.5	1339.9	1340.3	1333.1	1333.1	1327.7	1320.6	1315.1	1312.6
5°	1464.0	1465.1	1463.0	1455.1	1449.9	1442.0	1433.1	1417.3	1404.2	1391.7	1381.7
7.5°	1588.0	1588.7	1581.9	1579.4	1566.2	1556.5	1536.7	1515.3	1496.3	1472.2	1453.8
10°	1660.1	1659.6	1652.3	1646.5	1635.0	1620.3	1600.9	1575.7	1552.2	1525.9	1500.8
12.5°	1702.1	1700.7	1698.4	1691.4	1680.7	1667.7	1651.2	1626.5	1597.4	1568.7	1539.3
15°	1758.8	1755.0	1748.3	1739.3	1724.1	1708.9	1690.6	1668.6	1640.7	1608.2	1580.9
17.5°	1828.8	1828.9	1818.5	1806.0	1785.3	1758.6	1730.2	1694.7	1656.9	1621.1	1592.1
20°	1886.7	1885.1	1874.6	1850.5	1826.9	1793.3	1760.8	1717.3	1671.1	1624.5	1588.3
22.5°	1969.7	1965.7	1954.8	1923.1	1886.5	1843.3	1793.5	1740.4	1684.6	1631.6	1584.2
25°	2105.9	2102.7	2081.2	2044.6	1993.2	1926.5	1861.5	1788.7	1708.4	1638.7	1580.9
27.5°	2199.0	2195.5	2179.6	2149.1	2101.7	2031.6	1943.6	1846.2	1746.1	1650.1	1566.9
30°	2189.8	2197.7	2195.5	2181.4	2145.8	2082.8	2001.6	1892.0	1772.9	1660.1	1561.0
32.5°	2058.0	2065.1	2083.6	2111.3	2113.4	2088.3	2027.5	1926.3	1803.1	1674.9	1556.4
35°	1747.2	1756.7	1792.3	1848.5	1921.8	1983.2	1995.8	1941.3	1830.6	1692.6	1549.5
37.5°	1343.2	1394.8	1424.8	1483.9	1594.8	1707.7	1816.2	1856.1	1809.1	1685.4	1538.3
40°	1141.0	1153.6	1207.1	1273.7	1367.1	1484.5	1639.2	1750.9	1754.5	1668.6	1520.7
42.5°	976.5	992.5	1029.3	1082.4	1162.4	1279.8	1439.5	1586.9	1655.2	1622.4	1497.6
45°	781.3	793.3	820.1	861.0	922.4	1019.4	1156.8	1327.2	1462.5	1515.4	1435.7
47.5°	641.9	648.3	671.7	702.8	748.2	818.9	925.2	1073.2	1235.5	1349.2	1338.0
50°	566.3	573.7	591.5	615.1	653.4	713.2	798.1	921.3	1088.6	1227.6	1255.4
52.5°	507.6	513.7	524.8	547.1	578.7	624.6	693.2	804.7	955.2	1103.0	1167.2
55°	428.9	433.1	442.0	454.6	479.8	512.8	572.1	649.1	770.8	919.8	1014.1
57.5°	364.2	366.2	371.9	383.5	400.9	425.1	467.9	533.2	620.5	754.6	858.7
60°	323.1	325.1	332.4	340.3	354.0	376.0	409.5	455.1	539.1	649.6	755.1
62.5°	290.3	291.5	294.7	302.6	314.5	331.5	357.9	395.2	461.9	559.1	658.6
65°	243.3	243.9	244.9	251.2	258.5	271.1	288.4	314.6	365.0	438.4	526.4
67.5°	198.2	198.9	202.6	204.8	212.5	219.0	229.2	249.3	284.8	334.3	402.7
70°	173.1	172.5	176.2	178.8	181.5	189.2	196.1	212.4	234.4	272.2	329.3
72.5°	149.6	148.1	149.8	150.7	154.2	159.6	166.3	176.3	193.3	219.2	263.1
75°	113.3	113.8	113.8	114.8	117.4	119.6	121.7	126.9	136.3	153.6	177.2
77.5°	79.5	78.7	80.9	81.2	82.7	85.0	86.8	89.0	92.8	100.0	112.1
80°	57.7	57.7	58.2	59.8	59.3	60.3	62.9	65.0	69.8	73.9	78.2
82.5°	44.2	43.8	44.3	44.6	44.5	45.6	46.6	47.0	48.8	50.9	53.8
85°	24.1	24.1	24.6	24.6	25.1	25.1	25.7	25.7	25.7	26.3	26.8
87.5°	11.9	11.4	10.9	10.9	11.3	11.9	11.4	10.9	10.8	10.6	10.8
90°	13.2	13.2	12.6	12.6	12.6	11.5	10.9	10.4	9.8	9.2	8.1
92.5°	36.8	37.7	38.5	39.9	47.3	55.7	74.1	102.1	150.4	185.7	188.7
95°	135.4	144.6	149.2	166.5	207.4	255.8	326.6	414.1	499.5	510.4	416.5
97.5°	327.2	334.6	351.2	383.5	419.1	486.5	555.4	616.8	632.0	545.0	371.9
100°	449.3	458.6	479.9	521.3	561.1	621.0	680.3	708.5	664.2	520.2	331.8
102.5°	585.7	592.7	615.8	645.3	687.8	728.3	756.8	739.4	644.8	476.4	301.3
105°	763.3	770.2	781.7	800.7	819.1	825.5	800.1	721.2	583.0	417.7	271.9
107.5°	857.5	862.1	866.0	866.1	856.7	826.7	761.5	656.2	519.9	377.2	259.4
110°	888.9	888.9	884.8	873.8	848.0	799.0	717.8	608.3	483.9	358.3	255.8



TEST NUMBER: P333558-840

CATALOG NUMBER: S125RDIP-S850D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	885.1	881.0	871.0	852.2	814.4	756.6	674.5	570.6	457.2	347.3	255.8
115°	850.3	842.7	826.7	799.0	754.1	691.3	612.4	523.0	428.0	335.3	257.5
117.5°	789.1	784.5	768.5	739.9	695.0	637.3	569.4	492.4	410.6	329.4	261.3
120°	749.4	744.9	729.3	701.7	659.0	608.3	544.9	475.8	400.9	326.6	265.0
122.5°	714.4	710.2	694.7	669.3	631.4	583.9	527.5	463.4	392.6	324.4	268.2
125°	669.9	664.2	651.6	627.9	595.6	554.2	504.0	445.2	381.3	321.4	273.7
127.5°	632.0	629.3	617.4	596.5	567.3	528.5	481.7	426.9	371.0	320.0	279.7
130°	611.2	607.7	596.2	577.2	548.4	511.0	466.1	415.4	364.1	319.1	283.5
132.5°	590.5	586.5	575.9	556.9	528.2	492.1	451.3	403.8	358.5	319.1	287.6
135°	556.4	553.0	542.6	523.6	498.3	465.4	428.6	388.8	351.9	319.1	293.2
137.5°	520.2	516.3	506.9	489.5	466.9	439.0	408.3	376.2	346.1	319.8	298.4
140°	494.8	491.9	483.3	468.4	447.1	422.8	396.4	369.2	343.4	320.3	300.7
142.5°	471.3	468.9	460.7	448.1	430.0	409.0	386.2	363.2	341.0	320.7	302.1
145°	439.0	436.7	430.3	420.5	406.7	391.1	373.2	355.5	337.6	320.3	303.6
147.5°	411.5	410.5	406.8	399.0	388.0	376.3	362.5	348.1	334.0	318.8	304.2
150°	396.4	395.8	393.4	386.6	377.9	367.5	356.6	343.9	331.2	317.4	304.2
152.5°	384.4	383.7	381.4	376.0	368.7	360.6	350.6	339.3	328.0	315.6	303.7
155°	368.1	367.5	365.8	361.7	356.0	349.6	341.6	332.3	322.6	312.3	302.5
157.5°	353.6	353.7	352.0	348.7	344.3	339.3	333.1	325.5	317.5	308.7	300.9
160°	343.9	344.5	343.4	340.4	336.4	332.3	326.6	320.8	313.4	306.5	299.5
162.5°	335.2	335.3	335.1	332.6	329.5	325.9	321.1	315.8	309.7	303.7	298.2
165°	322.6	322.6	322.6	321.4	319.1	316.3	312.8	308.7	304.2	299.5	296.1
167.5°	311.0	311.1	311.6	310.6	309.4	307.4	304.8	302.1	298.7	295.5	292.9
170°	304.2	304.8	304.8	304.2	303.0	301.8	300.1	298.4	295.5	293.2	291.4
172.5°	297.7	298.3	299.2	298.2	297.9	297.2	296.0	294.3	292.3	290.4	289.6
175°	289.7	290.3	291.4	290.9	290.9	290.9	289.7	289.7	288.0	287.4	287.4
177.5°	285.7	285.7	287.1	286.6	287.1	287.1	287.1	286.6	286.2	285.7	285.7
180°	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7



TEST NUMBER: P333558-840

CATALOG NUMBER: S125RDIP-S850D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4
2.5°	1312.6	1309.7	1304.2	1299.2	1292.9	1287.5	1283.6	1279.1	1273.1	1266.1	1260.2
5°	1370.7	1359.2	1343.9	1330.9	1314.0	1301.0	1287.4	1274.2	1261.1	1244.4	1229.6
7.5°	1435.1	1411.3	1388.2	1359.0	1332.5	1308.9	1286.3	1263.3	1240.9	1217.1	1194.1
10°	1474.5	1445.7	1413.7	1377.0	1343.4	1311.4	1282.1	1253.2	1222.8	1196.1	1167.2
12.5°	1511.5	1474.2	1437.6	1391.3	1351.0	1311.9	1274.6	1238.6	1206.1	1171.3	1140.4
15°	1544.8	1508.1	1467.2	1410.6	1354.4	1307.3	1263.2	1216.6	1176.2	1137.4	1102.8
17.5°	1557.7	1519.2	1471.7	1417.2	1355.9	1296.6	1239.8	1188.6	1141.1	1095.9	1057.0
20°	1552.7	1515.4	1466.6	1414.7	1349.2	1287.4	1226.0	1169.3	1116.4	1068.6	1027.2
22.5°	1540.4	1502.0	1454.9	1400.1	1337.9	1272.2	1206.7	1146.3	1090.8	1041.4	996.2
25°	1522.3	1469.9	1421.6	1368.1	1308.8	1243.9	1176.2	1109.5	1050.4	1000.0	950.7
27.5°	1503.3	1437.8	1376.4	1323.3	1260.7	1202.6	1137.5	1069.1	1006.9	955.6	905.0
30°	1486.1	1412.7	1345.0	1284.8	1225.5	1170.4	1108.5	1041.9	978.0	925.0	873.6
32.5°	1464.7	1386.6	1312.3	1242.7	1185.6	1130.9	1075.0	1011.3	949.0	894.3	842.1
35°	1437.8	1338.2	1257.5	1183.5	1120.0	1067.1	1016.7	965.3	902.9	846.4	795.5
37.5°	1402.6	1289.5	1196.1	1115.6	1048.6	995.4	955.7	908.8	851.8	797.6	750.3
40°	1381.2	1254.3	1152.1	1072.4	1002.1	945.9	908.8	868.9	817.0	766.1	718.9
42.5°	1352.7	1222.0	1107.6	1024.5	953.8	899.8	862.1	827.4	783.9	735.9	685.4
45°	1296.8	1159.4	1039.4	950.2	878.9	825.9	790.7	759.8	726.8	682.8	638.6
47.5°	1224.0	1094.1	968.4	871.1	801.2	752.0	718.0	693.6	669.9	632.5	589.7
50°	1165.7	1040.4	917.7	823.2	748.8	702.2	670.1	650.8	629.2	595.1	559.5
52.5°	1096.9	985.0	864.7	768.3	698.0	654.3	623.6	604.2	586.4	558.7	524.7
55°	988.5	890.4	780.2	692.7	628.2	584.1	554.8	536.4	525.9	502.3	475.6
57.5°	863.3	793.0	695.9	611.5	554.5	511.0	489.5	473.8	462.0	445.2	426.5
60°	776.1	726.8	639.7	559.5	507.1	465.6	446.3	433.1	422.1	408.0	393.2
62.5°	687.5	651.7	575.9	507.1	458.8	424.1	406.0	394.2	381.4	371.9	357.6
65°	569.0	536.9	484.5	430.5	386.0	358.1	345.1	334.6	326.7	316.2	306.2
67.5°	442.5	429.6	393.3	356.2	324.2	299.4	288.1	280.7	271.4	265.0	258.2
70°	365.0	358.7	333.0	308.3	278.4	261.7	251.2	248.0	236.5	230.2	225.5
72.5°	296.2	293.3	278.4	261.4	240.2	225.6	215.9	212.4	205.0	200.0	196.9
75°	202.9	204.0	201.4	190.4	182.5	173.1	164.6	162.6	157.3	153.1	150.5
77.5°	128.4	133.7	133.9	133.4	130.3	124.5	121.0	119.5	114.3	112.7	112.1
80°	88.1	93.8	99.1	98.6	97.6	95.9	93.3	91.8	89.2	87.6	86.5
82.5°	58.8	64.1	68.5	71.3	71.1	69.6	67.8	67.1	66.4	65.3	65.1
85°	27.8	28.9	30.4	34.1	36.7	37.3	36.7	36.2	34.6	35.1	35.6
87.5°	11.1	10.9	11.2	11.0	10.3	12.2	13.2	13.5	12.8	12.2	11.6
90°	7.5	6.4	5.8	4.6	3.4	2.3	1.1	0.6	1.1	2.3	3.4
92.5°	131.5	78.7	47.3	30.4	20.5	13.3	8.5	7.1	8.5	13.3	20.5
95°	257.5	130.8	69.2	43.2	30.5	24.2	19.6	19.0	19.6	24.2	30.5
97.5°	205.5	112.7	71.9	53.2	41.8	35.4	32.2	31.6	32.2	35.4	41.8
100°	186.6	111.8	78.4	61.1	50.1	43.8	41.5	40.3	41.5	43.8	50.1
102.5°	178.8	115.9	86.1	69.4	59.4	52.5	50.7	50.0	50.7	52.5	59.4
105°	175.7	124.4	99.1	82.9	73.7	68.0	65.1	65.1	65.1	68.0	73.7
107.5°	181.0	137.1	112.6	98.1	88.5	83.7	81.0	79.9	81.0	83.7	88.5
110°	186.0	146.3	122.7	107.8	99.1	93.9	91.6	90.5	91.6	93.9	99.1



TEST NUMBER: P333558-840

CATALOG NUMBER: S125RDIP-S850D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	192.5	155.1	132.4	117.9	109.3	104.0	102.2	101.1	102.2	104.0	109.3
115°	202.2	168.7	147.4	133.1	124.4	119.3	117.5	116.3	117.5	119.3	124.4
117.5°	213.3	182.9	162.7	148.8	139.0	133.8	131.9	130.2	131.9	133.8	139.0
120°	220.7	193.0	172.8	158.4	148.7	143.4	141.2	139.4	141.2	143.4	148.7
122.5°	228.9	202.7	182.5	168.1	157.3	152.2	150.4	149.1	150.4	152.2	157.3
125°	240.2	215.4	196.4	181.5	170.5	165.3	162.5	161.3	162.5	165.3	170.5
127.5°	250.5	227.7	209.4	194.5	182.9	176.3	172.6	170.9	172.6	176.3	182.9
130°	257.5	235.6	217.7	202.8	190.7	183.2	178.5	176.8	178.5	183.2	190.7
132.5°	263.5	243.0	225.1	210.2	197.6	189.1	183.7	181.5	183.7	189.1	197.6
135°	271.9	252.9	235.0	219.4	207.4	198.1	191.3	188.9	191.3	198.1	207.4
137.5°	278.1	259.9	243.7	227.6	215.8	206.6	200.2	198.4	200.2	206.6	215.8
140°	282.3	265.0	248.3	232.8	221.8	212.6	205.6	203.9	205.6	212.6	221.8
142.5°	284.6	268.2	252.5	237.8	227.3	218.1	211.7	210.4	211.7	218.1	227.3
145°	288.0	273.7	258.6	245.4	235.0	226.9	221.2	220.0	221.2	226.9	235.0
147.5°	290.1	277.1	264.0	252.3	243.3	235.8	230.9	230.1	230.9	235.8	243.3
150°	291.4	279.4	266.7	256.9	248.8	241.4	237.3	236.2	237.3	241.4	248.8
152.5°	292.4	281.7	269.9	261.1	253.5	246.9	243.3	242.7	243.3	246.9	253.5
155°	293.2	284.0	274.2	266.1	260.3	254.6	251.2	251.2	251.2	254.6	260.3
157.5°	293.8	286.0	277.5	271.5	266.4	261.5	258.6	258.7	258.6	261.5	266.4
160°	293.8	286.9	279.4	274.2	269.6	265.6	263.3	263.9	263.3	265.6	269.6
162.5°	293.4	287.8	281.2	277.0	273.3	269.7	267.4	268.0	267.4	269.7	273.3
165°	292.7	288.0	283.5	279.9	277.6	274.8	273.1	274.2	273.1	274.8	277.6
167.5°	291.2	288.0	284.2	282.1	280.4	278.8	277.8	278.3	277.8	278.8	280.4
170°	290.3	288.0	285.2	283.5	282.3	281.1	280.5	281.1	280.5	281.1	282.3
172.5°	289.4	287.6	285.2	284.4	283.7	282.5	282.0	283.0	282.0	282.5	283.7
175°	288.0	286.9	285.2	285.2	285.2	284.6	284.0	285.2	284.0	284.6	285.2
177.5°	286.6	286.2	285.3	285.3	285.7	285.3	285.3	286.2	285.3	285.3	285.7
180°	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7



TEST NUMBER: P333558-840

CATALOG NUMBER: S125RDIP-S850D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4
2.5°	1256.0	1250.1	1245.9	1237.5	1231.6	1229.1	1224.6	1223.2	1227.9	1224.6	1224.1
5°	1218.6	1203.5	1191.3	1179.3	1166.2	1157.8	1145.2	1143.2	1139.9	1135.3	1134.2
7.5°	1173.9	1154.1	1138.5	1118.6	1101.3	1087.3	1071.6	1064.2	1060.1	1054.0	1045.8
10°	1143.7	1120.0	1099.0	1079.1	1057.6	1040.4	1024.6	1012.6	1004.7	997.3	994.2
12.5°	1113.9	1089.8	1063.0	1038.8	1014.9	995.4	978.1	970.2	961.5	952.9	945.5
15°	1067.6	1035.6	1006.2	978.5	958.1	937.1	920.3	908.8	895.6	891.9	877.8
17.5°	1018.5	987.1	952.8	923.5	899.8	876.8	858.3	845.2	835.4	821.8	815.3
20°	988.0	950.7	917.2	890.4	864.1	836.9	818.0	807.0	797.6	786.6	781.3
22.5°	955.2	918.8	884.4	853.0	826.4	799.6	786.2	774.7	764.0	753.9	746.9
25°	907.2	870.5	834.2	801.7	774.0	754.6	738.8	725.7	719.9	710.0	702.7
27.5°	859.7	820.6	783.0	750.7	728.9	709.7	696.8	686.4	676.0	667.3	661.0
30°	829.0	789.2	748.3	722.6	699.5	681.2	667.0	657.0	649.1	641.3	636.6
32.5°	798.4	757.3	721.0	693.2	671.4	655.6	641.0	631.5	623.2	614.5	608.9
35°	749.3	707.4	678.0	650.8	629.2	614.6	604.6	591.0	584.1	577.8	572.1
37.5°	703.7	664.7	632.9	609.0	590.4	575.7	562.9	555.5	547.1	541.5	536.6
40°	670.1	634.5	605.6	580.5	566.8	550.6	538.6	529.1	522.8	515.4	510.2
42.5°	640.0	606.8	578.8	556.1	539.2	525.4	513.8	504.3	496.3	491.1	486.8
45°	597.2	564.2	536.9	515.9	500.3	487.2	475.0	470.4	459.9	453.6	451.5
47.5°	553.1	523.5	497.3	477.9	461.8	449.4	438.1	428.4	422.6	416.5	413.1
50°	523.3	495.0	470.4	451.5	435.8	422.1	411.6	405.4	397.5	391.7	387.5
52.5°	493.5	467.4	442.7	424.6	411.0	397.4	385.7	379.3	371.9	368.2	365.3
55°	451.0	423.1	402.2	384.4	370.2	357.6	346.6	340.3	335.6	331.9	330.8
57.5°	402.7	380.7	361.2	345.2	330.4	318.6	308.9	303.0	298.8	298.2	295.1
60°	371.2	351.3	333.5	316.2	303.6	292.6	284.2	277.4	273.2	272.7	271.7
62.5°	339.8	320.7	304.2	288.9	277.6	267.0	259.0	251.4	248.8	246.2	244.0
65°	293.2	275.8	262.2	250.1	238.0	229.1	221.3	216.5	210.8	207.6	201.9
67.5°	247.3	233.9	220.8	210.6	201.2	192.7	186.1	179.2	175.2	172.7	168.5
70°	217.1	206.6	193.5	182.5	175.1	168.3	163.1	155.2	152.6	150.5	148.3
72.5°	188.5	179.4	168.3	159.5	152.1	145.6	139.6	135.9	133.3	131.2	130.0
75°	148.3	139.5	130.1	123.7	118.6	113.3	110.1	107.4	106.4	105.9	103.8
77.5°	109.0	104.2	96.6	91.7	88.2	86.1	83.3	81.9	81.8	79.5	78.8
80°	83.4	80.8	74.4	72.4	69.8	67.7	66.0	63.4	60.8	59.8	58.2
82.5°	62.0	59.4	56.9	53.5	51.3	50.0	48.5	47.5	47.9	46.4	45.6
85°	33.0	30.4	29.4	28.9	27.8	28.9	28.3	27.8	27.3	26.8	27.3
87.5°	11.4	11.6	11.3	12.4	11.3	11.9	12.0	11.7	11.8	11.9	11.7
90°	4.6	5.8	6.4	7.5	8.1	9.2	9.8	10.4	10.9	11.5	12.6
92.5°	30.4	47.3	78.7	131.5	188.7	185.7	150.4	102.1	74.1	55.7	47.3
95°	43.2	69.2	130.8	257.5	416.5	510.4	499.5	414.1	326.6	255.8	207.4
97.5°	53.2	71.9	112.7	205.5	371.9	545.0	632.0	616.8	555.4	486.5	419.1
100°	61.1	78.4	111.8	186.6	331.8	520.2	664.2	708.5	680.3	621.0	561.1
102.5°	69.4	86.1	115.9	178.8	301.3	476.4	644.8	739.4	756.8	728.3	687.8
105°	82.9	99.1	124.4	175.7	271.9	417.7	583.0	721.2	800.1	825.5	819.1
107.5°	98.1	112.6	137.1	181.0	259.4	377.2	519.9	656.2	761.5	826.7	856.7
110°	107.8	122.7	146.3	186.0	255.8	358.3	483.9	608.3	717.8	799.0	848.0



TEST NUMBER: P333558-840

CATALOG NUMBER: S125RDIP-S850D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	117.9	132.4	155.1	192.5	255.8	347.3	457.2	570.6	674.5	756.6	814.4
115°	133.1	147.4	168.7	202.2	257.5	335.3	428.0	523.0	612.4	691.3	754.1
117.5°	148.8	162.7	182.9	213.3	261.3	329.4	410.6	492.4	569.4	637.3	695.0
120°	158.4	172.8	193.0	220.7	265.0	326.6	400.9	475.8	544.9	608.3	659.0
122.5°	168.1	182.5	202.7	228.9	268.2	324.4	392.6	463.4	527.5	583.9	631.4
125°	181.5	196.4	215.4	240.2	273.7	321.4	381.3	445.2	504.0	554.2	595.6
127.5°	194.5	209.4	227.7	250.5	279.7	320.0	371.0	426.9	481.7	528.5	567.3
130°	202.8	217.7	235.6	257.5	283.5	319.1	364.1	415.4	466.1	511.0	548.4
132.5°	210.2	225.1	243.0	263.5	287.6	319.1	358.5	403.8	451.3	492.1	528.2
135°	219.4	235.0	252.9	271.9	293.2	319.1	351.9	388.8	428.6	465.4	498.3
137.5°	227.6	243.7	259.9	278.1	298.4	319.8	346.1	376.2	408.3	439.0	466.9
140°	232.8	248.3	265.0	282.3	300.7	320.3	343.4	369.2	396.4	422.8	447.1
142.5°	237.8	252.5	268.2	284.6	302.1	320.7	341.0	363.2	386.2	409.0	430.0
145°	245.4	258.6	273.7	288.0	303.6	320.3	337.6	355.5	373.2	391.1	406.7
147.5°	252.3	264.0	277.1	290.1	304.2	318.8	334.0	348.1	362.5	376.3	388.0
150°	256.9	266.7	279.4	291.4	304.2	317.4	331.2	343.9	356.6	367.5	377.9
152.5°	261.1	269.9	281.7	292.4	303.7	315.6	328.0	339.3	350.6	360.6	368.7
155°	266.1	274.2	284.0	293.2	302.5	312.3	322.6	332.3	341.6	349.6	356.0
157.5°	271.5	277.5	286.0	293.8	300.9	308.7	317.5	325.5	333.1	339.3	344.3
160°	274.2	279.4	286.9	293.8	299.5	306.5	313.4	320.8	326.6	332.3	336.4
162.5°	277.0	281.2	287.8	293.4	298.2	303.7	309.7	315.8	321.1	325.9	329.5
165°	279.9	283.5	288.0	292.7	296.1	299.5	304.2	308.7	312.8	316.3	319.1
167.5°	282.1	284.2	288.0	291.2	292.9	295.5	298.7	302.1	304.8	307.4	309.4
170°	283.5	285.2	288.0	290.3	291.4	293.2	295.5	298.4	300.1	301.8	303.0
172.5°	284.4	285.2	287.6	289.4	289.6	290.4	292.3	294.3	296.0	297.2	297.9
175°	285.2	285.2	286.9	288.0	287.4	287.4	288.0	289.7	289.7	290.9	290.9
177.5°	285.3	285.3	286.2	286.6	285.7	285.7	286.2	286.6	287.1	287.1	287.1
180°	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7



TEST NUMBER: P333558-840

CATALOG NUMBER: S125RDIP-S850D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4
2.5°	1223.7	1219.1	1217.8	1219.5	1217.8	1219.1	1223.7	1224.1	1224.6	1227.9	1223.2
5°	1128.9	1123.8	1126.3	1125.3	1126.3	1123.8	1128.9	1134.2	1135.3	1139.9	1143.2
7.5°	1045.7	1039.2	1032.3	1034.5	1032.3	1039.2	1045.7	1045.8	1054.0	1060.1	1064.2
10°	987.3	982.2	979.0	981.6	979.0	982.2	987.3	994.2	997.3	1004.7	1012.6
12.5°	938.3	935.1	932.4	931.3	932.4	935.1	938.3	945.5	952.9	961.5	970.2
15°	871.5	865.3	862.6	855.8	862.6	865.3	871.5	877.8	891.9	895.6	908.8
17.5°	809.9	807.9	801.0	798.1	801.0	807.9	809.9	815.3	821.8	835.4	845.2
20°	773.5	771.3	764.6	768.7	764.6	771.3	773.5	781.3	786.6	797.6	807.0
22.5°	743.3	738.6	736.4	735.2	736.4	738.6	743.3	746.9	753.9	764.0	774.7
25°	700.5	693.8	691.2	688.0	691.2	693.8	700.5	702.7	710.0	719.9	725.7
27.5°	658.0	654.3	650.9	650.1	650.9	654.3	658.0	661.0	667.3	676.0	686.4
30°	630.3	626.6	624.0	624.0	624.0	626.6	630.3	636.6	641.3	649.1	657.0
32.5°	605.5	602.7	600.1	599.7	600.1	602.7	605.5	608.9	614.5	623.2	631.5
35°	569.5	565.3	564.2	561.1	564.2	565.3	569.5	572.1	577.8	584.1	591.0
37.5°	532.0	528.6	528.5	528.2	528.5	528.6	532.0	536.6	541.5	547.1	555.5
40°	508.2	505.5	504.9	501.3	504.9	505.5	508.2	510.2	515.4	522.8	529.1
42.5°	482.5	481.2	479.4	477.8	479.4	481.2	482.5	486.8	491.1	496.3	504.3
45°	447.8	444.1	444.1	441.5	444.1	444.1	447.8	451.5	453.6	459.9	470.4
47.5°	411.9	409.1	409.4	406.7	409.4	409.1	411.9	413.1	416.5	422.6	428.4
50°	388.0	386.5	386.0	384.9	386.0	386.5	388.0	387.5	391.7	397.5	405.4
52.5°	364.2	363.3	365.4	363.0	365.4	363.3	364.2	365.3	368.2	371.9	379.3
55°	331.9	330.3	333.5	330.3	333.5	330.3	331.9	330.8	331.9	335.6	340.3
57.5°	294.9	293.5	296.3	294.7	296.3	293.5	294.9	295.1	298.2	298.8	303.0
60°	270.5	267.4	269.0	269.5	269.0	267.4	270.5	271.7	272.7	273.2	277.4
62.5°	241.7	239.7	240.9	238.5	240.9	239.7	241.7	244.0	246.2	248.8	251.4
65°	200.9	199.2	197.1	196.1	197.1	199.2	200.9	201.9	207.6	210.8	216.5
67.5°	168.7	165.0	164.9	165.7	164.9	165.0	168.7	168.5	172.7	175.2	179.2
70°	145.2	145.2	144.7	144.7	144.7	145.2	145.2	148.3	150.5	152.6	155.2
72.5°	128.9	128.5	127.5	127.1	127.5	128.5	128.9	130.0	131.2	133.3	135.9
75°	103.8	104.3	103.3	102.8	103.3	104.3	103.8	103.8	105.9	106.4	107.4
77.5°	76.6	74.4	75.6	74.4	75.6	74.4	76.6	78.8	79.5	81.8	81.9
80°	58.2	57.7	59.3	57.7	59.3	57.7	58.2	58.2	59.8	60.8	63.4
82.5°	46.0	45.5	46.3	45.1	46.3	45.5	46.0	45.6	46.4	47.9	47.5
85°	27.8	27.3	26.8	27.3	26.8	27.3	27.8	27.3	26.8	27.3	27.8
87.5°	12.2	11.7	11.9	11.9	11.9	11.7	12.2	11.7	11.9	11.8	11.7
90°	12.6	12.6	13.2	13.2	13.2	12.6	12.6	12.6	11.5	10.9	10.4
92.5°	39.9	38.5	37.7	36.8	37.7	38.5	39.9	47.3	55.7	74.1	102.1
95°	166.5	149.2	144.6	135.4	144.6	149.2	166.5	207.4	255.8	326.6	414.1
97.5°	383.5	351.2	334.6	327.2	334.6	351.2	383.5	419.1	486.5	555.4	616.8
100°	521.3	479.9	458.6	449.3	458.6	479.9	521.3	561.1	621.0	680.3	708.5
102.5°	645.3	615.8	592.7	585.7	592.7	615.8	645.3	687.8	728.3	756.8	739.4
105°	800.7	781.7	770.2	763.3	770.2	781.7	800.7	819.1	825.5	800.1	721.2
107.5°	866.1	866.0	862.1	857.5	862.1	866.0	866.1	856.7	826.7	761.5	656.2
110°	873.8	884.8	888.9	888.9	888.9	884.8	873.8	848.0	799.0	717.8	608.3



TEST NUMBER: P333558-840

CATALOG NUMBER: S125RDIP-S850D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	852.2	871.0	881.0	885.1	881.0	871.0	852.2	814.4	756.6	674.5	570.6
115°	799.0	826.7	842.7	850.3	842.7	826.7	799.0	754.1	691.3	612.4	523.0
117.5°	739.9	768.5	784.5	789.1	784.5	768.5	739.9	695.0	637.3	569.4	492.4
120°	701.7	729.3	744.9	749.4	744.9	729.3	701.7	659.0	608.3	544.9	475.8
122.5°	669.3	694.7	710.2	714.4	710.2	694.7	669.3	631.4	583.9	527.5	463.4
125°	627.9	651.6	664.2	669.9	664.2	651.6	627.9	595.6	554.2	504.0	445.2
127.5°	596.5	617.4	629.3	632.0	629.3	617.4	596.5	567.3	528.5	481.7	426.9
130°	577.2	596.2	607.7	611.2	607.7	596.2	577.2	548.4	511.0	466.1	415.4
132.5°	556.9	575.9	586.5	590.5	586.5	575.9	556.9	528.2	492.1	451.3	403.8
135°	523.6	542.6	553.0	556.4	553.0	542.6	523.6	498.3	465.4	428.6	388.8
137.5°	489.5	506.9	516.3	520.2	516.3	506.9	489.5	466.9	439.0	408.3	376.2
140°	468.4	483.3	491.9	494.8	491.9	483.3	468.4	447.1	422.8	396.4	369.2
142.5°	448.1	460.7	468.9	471.3	468.9	460.7	448.1	430.0	409.0	386.2	363.2
145°	420.5	430.3	436.7	439.0	436.7	430.3	420.5	406.7	391.1	373.2	355.5
147.5°	399.0	406.8	410.5	411.5	410.5	406.8	399.0	388.0	376.3	362.5	348.1
150°	386.6	393.4	395.8	396.4	395.8	393.4	386.6	377.9	367.5	356.6	343.9
152.5°	376.0	381.4	383.7	384.4	383.7	381.4	376.0	368.7	360.6	350.6	339.3
155°	361.7	365.8	367.5	368.1	367.5	365.8	361.7	356.0	349.6	341.6	332.3
157.5°	348.7	352.0	353.7	353.6	353.7	352.0	348.7	344.3	339.3	333.1	325.5
160°	340.4	343.4	344.5	343.9	344.5	343.4	340.4	336.4	332.3	326.6	320.8
162.5°	332.6	335.1	335.3	335.2	335.3	335.1	332.6	329.5	325.9	321.1	315.8
165°	321.4	322.6	322.6	322.6	322.6	322.6	321.4	319.1	316.3	312.8	308.7
167.5°	310.6	311.6	311.1	311.0	311.1	311.6	310.6	309.4	307.4	304.8	302.1
170°	304.2	304.8	304.8	304.2	304.8	304.8	304.2	303.0	301.8	300.1	298.4
172.5°	298.2	299.2	298.3	297.7	298.3	299.2	298.2	297.9	297.2	296.0	294.3
175°	290.9	291.4	290.3	289.7	290.3	291.4	290.9	290.9	290.9	289.7	289.7
177.5°	286.6	287.1	285.7	285.7	285.7	287.1	286.6	287.1	287.1	287.1	286.6
180°	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7



TEST NUMBER: P333558-840

CATALOG NUMBER: S125RDIP-S850D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4
2.5°	1224.6	1229.1	1231.6	1237.5	1245.9	1250.1	1256.0	1260.2	1266.1	1273.1	1279.1
5°	1145.2	1157.8	1166.2	1179.3	1191.3	1203.5	1218.6	1229.6	1244.4	1261.1	1274.2
7.5°	1071.6	1087.3	1101.3	1118.6	1138.5	1154.1	1173.9	1194.1	1217.1	1240.9	1263.3
10°	1024.6	1040.4	1057.6	1079.1	1099.0	1120.0	1143.7	1167.2	1196.1	1222.8	1253.2
12.5°	978.1	995.4	1014.9	1038.8	1063.0	1089.8	1113.9	1140.4	1171.3	1206.1	1238.6
15°	920.3	937.1	958.1	978.5	1006.2	1035.6	1067.6	1102.8	1137.4	1176.2	1216.6
17.5°	858.3	876.8	899.8	923.5	952.8	987.1	1018.5	1057.0	1095.9	1141.1	1188.6
20°	818.0	836.9	864.1	890.4	917.2	950.7	988.0	1027.2	1068.6	1116.4	1169.3
22.5°	786.2	799.6	826.4	853.0	884.4	918.8	955.2	996.2	1041.4	1090.8	1146.3
25°	738.8	754.6	774.0	801.7	834.2	870.5	907.2	950.7	1000.0	1050.4	1109.5
27.5°	696.8	709.7	728.9	750.7	783.0	820.6	859.7	905.0	955.6	1006.9	1069.1
30°	667.0	681.2	699.5	722.6	748.3	789.2	829.0	873.6	925.0	978.0	1041.9
32.5°	641.0	655.6	671.4	693.2	721.0	757.3	798.4	842.1	894.3	949.0	1011.3
35°	604.6	614.6	629.2	650.8	678.0	707.4	749.3	795.5	846.4	902.9	965.3
37.5°	562.9	575.7	590.4	609.0	632.9	664.7	703.7	750.3	797.6	851.8	908.8
40°	538.6	550.6	566.8	580.5	605.6	634.5	670.1	718.9	766.1	817.0	868.9
42.5°	513.8	525.4	539.2	556.1	578.8	606.8	640.0	685.4	735.9	783.9	827.4
45°	475.0	487.2	500.3	515.9	536.9	564.2	597.2	638.6	682.8	726.8	759.8
47.5°	438.1	449.4	461.8	477.9	497.3	523.5	553.1	589.7	632.5	669.9	693.6
50°	411.6	422.1	435.8	451.5	470.4	495.0	523.3	559.5	595.1	629.2	650.8
52.5°	385.7	397.4	411.0	424.6	442.7	467.4	493.5	524.7	558.7	586.4	604.2
55°	346.6	357.6	370.2	384.4	402.2	423.1	451.0	475.6	502.3	525.9	536.4
57.5°	308.9	318.6	330.4	345.2	361.2	380.7	402.7	426.5	445.2	462.0	473.8
60°	284.2	292.6	303.6	316.2	333.5	351.3	371.2	393.2	408.0	422.1	433.1
62.5°	259.0	267.0	277.6	288.9	304.2	320.7	339.8	357.6	371.9	381.4	394.2
65°	221.3	229.1	238.0	250.1	262.2	275.8	293.2	306.2	316.2	326.7	334.6
67.5°	186.1	192.7	201.2	210.6	220.8	233.9	247.3	258.2	265.0	271.4	280.7
70°	163.1	168.3	175.1	182.5	193.5	206.6	217.1	225.5	230.2	236.5	248.0
72.5°	139.6	145.6	152.1	159.5	168.3	179.4	188.5	196.9	200.0	205.0	212.4
75°	110.1	113.3	118.6	123.7	130.1	139.5	148.3	150.5	153.1	157.3	162.6
77.5°	83.3	86.1	88.2	91.7	96.6	104.2	109.0	112.1	112.7	114.3	119.5
80°	66.0	67.7	69.8	72.4	74.4	80.8	83.4	86.5	87.6	89.2	91.8
82.5°	48.5	50.0	51.3	53.5	56.9	59.4	62.0	65.1	65.3	66.4	67.1
85°	28.3	28.9	27.8	28.9	29.4	30.4	33.0	35.6	35.1	34.6	36.2
87.5°	12.0	11.9	11.3	12.4	11.3	11.6	11.4	11.6	12.2	12.8	13.5
90°	9.8	9.2	8.1	7.5	6.4	5.8	4.6	3.4	2.3	1.1	0.6
92.5°	150.4	185.7	188.7	131.5	78.7	47.3	30.4	20.5	13.3	8.5	7.1
95°	499.5	510.4	416.5	257.5	130.8	69.2	43.2	30.5	24.2	19.6	19.0
97.5°	632.0	545.0	371.9	205.5	112.7	71.9	53.2	41.8	35.4	32.2	31.6
100°	664.2	520.2	331.8	186.6	111.8	78.4	61.1	50.1	43.8	41.5	40.3
102.5°	644.8	476.4	301.3	178.8	115.9	86.1	69.4	59.4	52.5	50.7	50.0
105°	583.0	417.7	271.9	175.7	124.4	99.1	82.9	73.7	68.0	65.1	65.1
107.5°	519.9	377.2	259.4	181.0	137.1	112.6	98.1	88.5	83.7	81.0	79.9
110°	483.9	358.3	255.8	186.0	146.3	122.7	107.8	99.1	93.9	91.6	90.5



TEST NUMBER: P333558-840

CATALOG NUMBER: S125RDIP-S850D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	457.2	347.3	255.8	192.5	155.1	132.4	117.9	109.3	104.0	102.2	101.1
115°	428.0	335.3	257.5	202.2	168.7	147.4	133.1	124.4	119.3	117.5	116.3
117.5°	410.6	329.4	261.3	213.3	182.9	162.7	148.8	139.0	133.8	131.9	130.2
120°	400.9	326.6	265.0	220.7	193.0	172.8	158.4	148.7	143.4	141.2	139.4
122.5°	392.6	324.4	268.2	228.9	202.7	182.5	168.1	157.3	152.2	150.4	149.1
125°	381.3	321.4	273.7	240.2	215.4	196.4	181.5	170.5	165.3	162.5	161.3
127.5°	371.0	320.0	279.7	250.5	227.7	209.4	194.5	182.9	176.3	172.6	170.9
130°	364.1	319.1	283.5	257.5	235.6	217.7	202.8	190.7	183.2	178.5	176.8
132.5°	358.5	319.1	287.6	263.5	243.0	225.1	210.2	197.6	189.1	183.7	181.5
135°	351.9	319.1	293.2	271.9	252.9	235.0	219.4	207.4	198.1	191.3	188.9
137.5°	346.1	319.8	298.4	278.1	259.9	243.7	227.6	215.8	206.6	200.2	198.4
140°	343.4	320.3	300.7	282.3	265.0	248.3	232.8	221.8	212.6	205.6	203.9
142.5°	341.0	320.7	302.1	284.6	268.2	252.5	237.8	227.3	218.1	211.7	210.4
145°	337.6	320.3	303.6	288.0	273.7	258.6	245.4	235.0	226.9	221.2	220.0
147.5°	334.0	318.8	304.2	290.1	277.1	264.0	252.3	243.3	235.8	230.9	230.1
150°	331.2	317.4	304.2	291.4	279.4	266.7	256.9	248.8	241.4	237.3	236.2
152.5°	328.0	315.6	303.7	292.4	281.7	269.9	261.1	253.5	246.9	243.3	242.7
155°	322.6	312.3	302.5	293.2	284.0	274.2	266.1	260.3	254.6	251.2	251.2
157.5°	317.5	308.7	300.9	293.8	286.0	277.5	271.5	266.4	261.5	258.6	258.7
160°	313.4	306.5	299.5	293.8	286.9	279.4	274.2	269.6	265.6	263.3	263.9
162.5°	309.7	303.7	298.2	293.4	287.8	281.2	277.0	273.3	269.7	267.4	268.0
165°	304.2	299.5	296.1	292.7	288.0	283.5	279.9	277.6	274.8	273.1	274.2
167.5°	298.7	295.5	292.9	291.2	288.0	284.2	282.1	280.4	278.8	277.8	278.3
170°	295.5	293.2	291.4	290.3	288.0	285.2	283.5	282.3	281.1	280.5	281.1
172.5°	292.3	290.4	289.6	289.4	287.6	285.2	284.4	283.7	282.5	282.0	283.0
175°	288.0	287.4	287.4	288.0	286.9	285.2	285.2	285.2	284.6	284.0	285.2
177.5°	286.2	285.7	285.7	286.6	286.2	285.3	285.3	285.7	285.3	285.3	286.2
180°	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7



TEST NUMBER: P333558-840

CATALOG NUMBER: S125RDIP-S850D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4
2.5°	1283.6	1287.5	1292.9	1299.2	1304.2	1309.7	1312.6	1312.6	1315.1	1320.6	1327.7
5°	1287.4	1301.0	1314.0	1330.9	1343.9	1359.2	1370.7	1381.7	1391.7	1404.2	1417.3
7.5°	1286.3	1308.9	1332.5	1359.0	1388.2	1411.3	1435.1	1453.8	1472.2	1496.3	1515.3
10°	1282.1	1311.4	1343.4	1377.0	1413.7	1445.7	1474.5	1500.8	1525.9	1552.2	1575.7
12.5°	1274.6	1311.9	1351.0	1391.3	1437.6	1474.2	1511.5	1539.3	1568.7	1597.4	1626.5
15°	1263.2	1307.3	1354.4	1410.6	1467.2	1508.1	1544.8	1580.9	1608.2	1640.7	1668.6
17.5°	1239.8	1296.6	1355.9	1417.2	1471.7	1519.2	1557.7	1592.1	1621.1	1656.9	1694.7
20°	1226.0	1287.4	1349.2	1414.7	1466.6	1515.4	1552.7	1588.3	1624.5	1671.1	1717.3
22.5°	1206.7	1272.2	1337.9	1400.1	1454.9	1502.0	1540.4	1584.2	1631.6	1684.6	1740.4
25°	1176.2	1243.9	1308.8	1368.1	1421.6	1469.9	1522.3	1580.9	1638.7	1708.4	1788.7
27.5°	1137.5	1202.6	1260.7	1323.3	1376.4	1437.8	1503.3	1566.9	1650.1	1746.1	1846.2
30°	1108.5	1170.4	1225.5	1284.8	1345.0	1412.7	1486.1	1561.0	1660.1	1772.9	1892.0
32.5°	1075.0	1130.9	1185.6	1242.7	1312.3	1386.6	1464.7	1556.4	1674.9	1803.1	1926.3
35°	1016.7	1067.1	1120.0	1183.5	1257.5	1338.2	1437.8	1549.5	1692.6	1830.6	1941.3
37.5°	955.7	995.4	1048.6	1115.6	1196.1	1289.5	1402.6	1538.3	1685.4	1809.1	1856.1
40°	908.8	945.9	1002.1	1072.4	1152.1	1254.3	1381.2	1520.7	1668.6	1754.5	1750.9
42.5°	862.1	899.8	953.8	1024.5	1107.6	1222.0	1352.7	1497.6	1622.4	1655.2	1586.9
45°	790.7	825.9	878.9	950.2	1039.4	1159.4	1296.8	1435.7	1515.4	1462.5	1327.2
47.5°	718.0	752.0	801.2	871.1	968.4	1094.1	1224.0	1338.0	1349.2	1235.5	1073.2
50°	670.1	702.2	748.8	823.2	917.7	1040.4	1165.7	1255.4	1227.6	1088.6	921.3
52.5°	623.6	654.3	698.0	768.3	864.7	985.0	1096.9	1167.2	1103.0	955.2	804.7
55°	554.8	584.1	628.2	692.7	780.2	890.4	988.5	1014.1	919.8	770.8	649.1
57.5°	489.5	511.0	554.5	611.5	695.9	793.0	863.3	858.7	754.6	620.5	533.2
60°	446.3	465.6	507.1	559.5	639.7	726.8	776.1	755.1	649.6	539.1	455.1
62.5°	406.0	424.1	458.8	507.1	575.9	651.7	687.5	658.6	559.1	461.9	395.2
65°	345.1	358.1	386.0	430.5	484.5	536.9	569.0	526.4	438.4	365.0	314.6
67.5°	288.1	299.4	324.2	356.2	393.3	429.6	442.5	402.7	334.3	284.8	249.3
70°	251.2	261.7	278.4	308.3	333.0	358.7	365.0	329.3	272.2	234.4	212.4
72.5°	215.9	225.6	240.2	261.4	278.4	293.3	296.2	263.1	219.2	193.3	176.3
75°	164.6	173.1	182.5	190.4	201.4	204.0	202.9	177.2	153.6	136.3	126.9
77.5°	121.0	124.5	130.3	133.4	133.9	133.7	128.4	112.1	100.0	92.8	89.0
80°	93.3	95.9	97.6	98.6	99.1	93.8	88.1	78.2	73.9	69.8	65.0
82.5°	67.8	69.6	71.1	71.3	68.5	64.1	58.8	53.8	50.9	48.8	47.0
85°	36.7	37.3	36.7	34.1	30.4	28.9	27.8	26.8	26.3	25.7	25.7
87.5°	13.2	12.2	10.3	11.0	11.2	10.9	11.1	10.8	10.6	10.8	10.9
90°	1.1	2.3	3.4	4.6	5.8	6.4	7.5	8.1	9.2	9.8	10.4
92.5°	8.5	13.3	20.5	30.4	47.3	78.7	131.5	188.7	185.7	150.4	102.1
95°	19.6	24.2	30.5	43.2	69.2	130.8	257.5	416.5	510.4	499.5	414.1
97.5°	32.2	35.4	41.8	53.2	71.9	112.7	205.5	371.9	545.0	632.0	616.8
100°	41.5	43.8	50.1	61.1	78.4	111.8	186.6	331.8	520.2	664.2	708.5
102.5°	50.7	52.5	59.4	69.4	86.1	115.9	178.8	301.3	476.4	644.8	739.4
105°	65.1	68.0	73.7	82.9	99.1	124.4	175.7	271.9	417.7	583.0	721.2
107.5°	81.0	83.7	88.5	98.1	112.6	137.1	181.0	259.4	377.2	519.9	656.2
110°	91.6	93.9	99.1	107.8	122.7	146.3	186.0	255.8	358.3	483.9	608.3



TEST NUMBER: P333558-840

CATALOG NUMBER: S125RDIP-S850D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	102.2	104.0	109.3	117.9	132.4	155.1	192.5	255.8	347.3	457.2	570.6
115°	117.5	119.3	124.4	133.1	147.4	168.7	202.2	257.5	335.3	428.0	523.0
117.5°	131.9	133.8	139.0	148.8	162.7	182.9	213.3	261.3	329.4	410.6	492.4
120°	141.2	143.4	148.7	158.4	172.8	193.0	220.7	265.0	326.6	400.9	475.8
122.5°	150.4	152.2	157.3	168.1	182.5	202.7	228.9	268.2	324.4	392.6	463.4
125°	162.5	165.3	170.5	181.5	196.4	215.4	240.2	273.7	321.4	381.3	445.2
127.5°	172.6	176.3	182.9	194.5	209.4	227.7	250.5	279.7	320.0	371.0	426.9
130°	178.5	183.2	190.7	202.8	217.7	235.6	257.5	283.5	319.1	364.1	415.4
132.5°	183.7	189.1	197.6	210.2	225.1	243.0	263.5	287.6	319.1	358.5	403.8
135°	191.3	198.1	207.4	219.4	235.0	252.9	271.9	293.2	319.1	351.9	388.8
137.5°	200.2	206.6	215.8	227.6	243.7	259.9	278.1	298.4	319.8	346.1	376.2
140°	205.6	212.6	221.8	232.8	248.3	265.0	282.3	300.7	320.3	343.4	369.2
142.5°	211.7	218.1	227.3	237.8	252.5	268.2	284.6	302.1	320.7	341.0	363.2
145°	221.2	226.9	235.0	245.4	258.6	273.7	288.0	303.6	320.3	337.6	355.5
147.5°	230.9	235.8	243.3	252.3	264.0	277.1	290.1	304.2	318.8	334.0	348.1
150°	237.3	241.4	248.8	256.9	266.7	279.4	291.4	304.2	317.4	331.2	343.9
152.5°	243.3	246.9	253.5	261.1	269.9	281.7	292.4	303.7	315.6	328.0	339.3
155°	251.2	254.6	260.3	266.1	274.2	284.0	293.2	302.5	312.3	322.6	332.3
157.5°	258.6	261.5	266.4	271.5	277.5	286.0	293.8	300.9	308.7	317.5	325.5
160°	263.3	265.6	269.6	274.2	279.4	286.9	293.8	299.5	306.5	313.4	320.8
162.5°	267.4	269.7	273.3	277.0	281.2	287.8	293.4	298.2	303.7	309.7	315.8
165°	273.1	274.8	277.6	279.9	283.5	288.0	292.7	296.1	299.5	304.2	308.7
167.5°	277.8	278.8	280.4	282.1	284.2	288.0	291.2	292.9	295.5	298.7	302.1
170°	280.5	281.1	282.3	283.5	285.2	288.0	290.3	291.4	293.2	295.5	298.4
172.5°	282.0	282.5	283.7	284.4	285.2	287.6	289.4	289.6	290.4	292.3	294.3
175°	284.0	284.6	285.2	285.2	285.2	286.9	288.0	287.4	287.4	288.0	289.7
177.5°	285.3	285.3	285.7	285.3	285.3	286.2	286.6	285.7	285.7	286.2	286.6
180°	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7



TEST NUMBER: P333558-840

CATALOG NUMBER: S125RDIP-S850D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4
2.5°	1333.1	1333.1	1340.3	1339.9	1344.5	1342.8	1343.6
5°	1433.1	1442.0	1449.9	1455.1	1463.0	1465.1	1464.0
7.5°	1536.7	1556.5	1566.2	1579.4	1581.9	1588.7	1588.0
10°	1600.9	1620.3	1635.0	1646.5	1652.3	1659.6	1660.1
12.5°	1651.2	1667.7	1680.7	1691.4	1698.4	1700.7	1702.1
15°	1690.6	1708.9	1724.1	1739.3	1748.3	1755.0	1758.8
17.5°	1730.2	1758.6	1785.3	1806.0	1818.5	1828.9	1828.8
20°	1760.8	1793.3	1826.9	1850.5	1874.6	1885.1	1886.7
22.5°	1793.5	1843.3	1886.5	1923.1	1954.8	1965.7	1969.7
25°	1861.5	1926.5	1993.2	2044.6	2081.2	2102.7	2105.9
27.5°	1943.6	2031.6	2101.7	2149.1	2179.6	2195.5	2199.0
30°	2001.6	2082.8	2145.8	2181.4	2195.5	2197.7	2189.8
32.5°	2027.5	2088.3	2113.4	2111.3	2083.6	2065.1	2058.0
35°	1995.8	1983.2	1921.8	1848.5	1792.3	1756.7	1747.2
37.5°	1816.2	1707.7	1594.8	1483.9	1424.8	1394.8	1343.2
40°	1639.2	1484.5	1367.1	1273.7	1207.1	1153.6	1141.0
42.5°	1439.5	1279.8	1162.4	1082.4	1029.3	992.5	976.5
45°	1156.8	1019.4	922.4	861.0	820.1	793.3	781.3
47.5°	925.2	818.9	748.2	702.8	671.7	648.3	641.9
50°	798.1	713.2	653.4	615.1	591.5	573.7	566.3
52.5°	693.2	624.6	578.7	547.1	524.8	513.7	507.6
55°	572.1	512.8	479.8	454.6	442.0	433.1	428.9
57.5°	467.9	425.1	400.9	383.5	371.9	366.2	364.2
60°	409.5	376.0	354.0	340.3	332.4	325.1	323.1
62.5°	357.9	331.5	314.5	302.6	294.7	291.5	290.3
65°	288.4	271.1	258.5	251.2	244.9	243.9	243.3
67.5°	229.2	219.0	212.5	204.8	202.6	198.9	198.2
70°	196.1	189.2	181.5	178.8	176.2	172.5	173.1
72.5°	166.3	159.6	154.2	150.7	149.8	148.1	149.6
75°	121.7	119.6	117.4	114.8	113.8	113.8	113.3
77.5°	86.8	85.0	82.7	81.2	80.9	78.7	79.5
80°	62.9	60.3	59.3	59.8	58.2	57.7	57.7
82.5°	46.6	45.6	44.5	44.6	44.3	43.8	44.2
85°	25.7	25.1	25.1	24.6	24.6	24.1	24.1
87.5°	11.4	11.9	11.3	10.9	10.9	11.4	11.9
90°	10.9	11.5	12.6	12.6	12.6	13.2	13.2
92.5°	74.1	55.7	47.3	39.9	38.5	37.7	36.8
95°	326.6	255.8	207.4	166.5	149.2	144.6	135.4
97.5°	555.4	486.5	419.1	383.5	351.2	334.6	327.2
100°	680.3	621.0	561.1	521.3	479.9	458.6	449.3
102.5°	756.8	728.3	687.8	645.3	615.8	592.7	585.7
105°	800.1	825.5	819.1	800.7	781.7	770.2	763.3
107.5°	761.5	826.7	856.7	866.1	866.0	862.1	857.5
110°	717.8	799.0	848.0	873.8	884.8	888.9	888.9



TEST NUMBER: P333558-840

CATALOG NUMBER: S125RDIP-S850D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	674.5	756.6	814.4	852.2	871.0	881.0	885.1
115°	612.4	691.3	754.1	799.0	826.7	842.7	850.3
117.5°	569.4	637.3	695.0	739.9	768.5	784.5	789.1
120°	544.9	608.3	659.0	701.7	729.3	744.9	749.4
122.5°	527.5	583.9	631.4	669.3	694.7	710.2	714.4
125°	504.0	554.2	595.6	627.9	651.6	664.2	669.9
127.5°	481.7	528.5	567.3	596.5	617.4	629.3	632.0
130°	466.1	511.0	548.4	577.2	596.2	607.7	611.2
132.5°	451.3	492.1	528.2	556.9	575.9	586.5	590.5
135°	428.6	465.4	498.3	523.6	542.6	553.0	556.4
137.5°	408.3	439.0	466.9	489.5	506.9	516.3	520.2
140°	396.4	422.8	447.1	468.4	483.3	491.9	494.8
142.5°	386.2	409.0	430.0	448.1	460.7	468.9	471.3
145°	373.2	391.1	406.7	420.5	430.3	436.7	439.0
147.5°	362.5	376.3	388.0	399.0	406.8	410.5	411.5
150°	356.6	367.5	377.9	386.6	393.4	395.8	396.4
152.5°	350.6	360.6	368.7	376.0	381.4	383.7	384.4
155°	341.6	349.6	356.0	361.7	365.8	367.5	368.1
157.5°	333.1	339.3	344.3	348.7	352.0	353.7	353.6
160°	326.6	332.3	336.4	340.4	343.4	344.5	343.9
162.5°	321.1	325.9	329.5	332.6	335.1	335.3	335.2
165°	312.8	316.3	319.1	321.4	322.6	322.6	322.6
167.5°	304.8	307.4	309.4	310.6	311.6	311.1	311.0
170°	300.1	301.8	303.0	304.2	304.8	304.8	304.2
172.5°	296.0	297.2	297.9	298.2	299.2	298.3	297.7
175°	289.7	290.9	290.9	290.9	291.4	290.3	289.7
177.5°	287.1	287.1	287.1	286.6	287.1	285.7	285.7
180°	285.7	285.7	285.7	285.7	285.7	285.7	285.7

(END OF REPORT)