

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331637-830

Luminaire Tested: **SA2XXRDIP-C290D925U830-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331637-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C290D925U830-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4094.3 lumens  
Efficiency: N/A  
Efficacy: 109.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331637-830  
CATALOG NUMBER: SA2XXRDIP-C290D925U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331637-830

CATALOG NUMBER: SA2XXRDIP-C290D925U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24
1	92	88	84	81	82	78	75	73	60	58	57	44	43	42	29	28	27	20
2	84	77	71	67	75	69	64	60	53	50	47	39	37	35	25	24	23	18
3	77	68	61	56	68	61	55	50	47	43	40	34	32	30	23	21	20	15
4	70	60	53	47	62	54	47	43	42	37	34	31	28	26	20	19	18	13
5	64	53	46	40	57	48	41	37	37	33	29	28	25	22	19	17	15	12
6	59	48	40	35	53	43	36	32	34	29	26	25	22	20	17	15	14	10
7	55	43	36	30	49	39	32	28	30	26	22	23	20	17	15	14	12	9
8	51	39	32	27	45	35	29	24	28	23	20	21	18	15	14	12	11	8
9	47	36	28	24	42	32	26	22	25	21	18	19	16	14	13	11	10	8
10	44	32	26	21	39	29	23	19	23	19	16	18	15	12	12	10	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7640	7640	7640
5°	7669	7543	7585
10°	7609	7420	7356
15°	7522	7199	6992
20°	7400	6887	6541
25°	7277	6531	6102
30°	7105	6162	5541
35°	6936	5765	5048
40°	6768	5351	4477
45°	6572	4889	3959
50°	6365	4421	3451
55°	6159	3916	2967
60°	5916	3387	2464
65°	5643	2846	2239
70°	5316	2346	2058
75°	4916	2133	1921
80°	4342	1906	1757
85°	3409	1501	1501



TEST NUMBER: P331637-830

CATALOG NUMBER: SA2XXRDIP-C290D925U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	44.3	1.1
10°-20°	121.6	3.0
20°-30°	170.8	4.2
30°-40°	186.2	4.5
40°-50°	171.2	4.2
50°-60°	134.5	3.3
60°-70°	87.7	2.1
70°-80°	45.2	1.1
80°-90°	16.2	0.4
90°-100°	70.6	1.7
100°-110°	219.4	5.4
110°-120°	375.0	9.2
120°-130°	493.1	12.0
130°-140°	553.4	13.5
140°-150°	542.7	13.3
150°-160°	455.2	11.1
160°-170°	301.9	7.4
170°-180°	105.5	2.6
0°-30°	336.6	8.2
0°-40°	522.8	12.8
0°-60°	828.5	20.2
0°-90°	977.6	23.9
90°-120°	665.0	16.2
90°-150°	2254.1	55.1
90°-180°	3117.0	76.1
0°-180°	4094.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	473	473	473	473	473	
5°	473	471	465	469	468	45
15°	450	445	431	423	418	127
25°	408	394	367	350	342	188
35°	352	329	292	266	256	220
45°	288	258	214	185	173	222
55°	219	185	139	114	105	195
65°	148	113	74	61	59	146
75°	79	50	34	31	31	83
85°	18	10	8	8	8	22
90°	1	13	33	31	32	3
95°	49	58	60	60	58	56
105°	202	205	207	209	209	214
115°	376	381	380	379	376	372
125°	547	555	553	550	549	489
135°	708	718	720	719	717	547
145°	860	866	872	873	869	537
155°	983	986	988	993	990	452
165°	1070	1069	1069	1074	1070	301
175°	1113	1110	1108	1114	1109	106
180°	1115	1115	1115	1115	1115	



TEST NUMBER: P331637-830

CATALOG NUMBER: SA2XXRDIP-C290D925U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	473.2	473.2	473.2	473.2	473.2	473.2	473.2	473.2	473.2	473.2	473.2
2.5°	474.9	474.5	474.1	473.7	473.3	472.7	471.8	471.1	470.2	469.4	470.1
5°	473.2	472.7	472.2	471.7	471.3	470.3	469.1	467.9	466.7	465.4	466.3
7.5°	468.3	467.7	467.0	466.5	465.9	464.9	463.4	461.9	460.5	459.1	459.3
10°	464.1	463.4	462.8	462.1	461.5	460.1	458.3	456.4	454.5	452.6	452.3
12.5°	459.0	458.2	457.3	456.6	455.7	454.1	451.7	449.2	446.8	444.3	443.8
15°	450.0	448.9	447.9	446.9	445.8	443.7	440.5	437.2	433.9	430.7	429.0
17.5°	438.9	437.3	435.7	434.1	432.5	429.7	425.6	421.4	417.3	413.1	410.9
20°	430.7	428.9	427.0	425.0	423.1	419.8	415.0	410.3	405.6	400.8	398.4
22.5°	421.9	419.7	417.5	415.5	413.3	409.5	404.2	398.8	393.5	388.1	385.0
25°	408.5	405.4	402.4	399.4	396.3	391.6	385.3	379.1	372.8	366.6	362.6
27.5°	392.4	389.1	385.8	382.5	379.1	373.9	366.8	359.8	352.7	345.6	341.1
30°	381.1	377.5	373.8	370.2	366.6	361.0	353.4	345.8	338.2	330.5	325.7
32.5°	370.1	365.9	361.7	357.4	353.2	347.2	339.5	331.7	324.0	316.1	310.7
35°	351.9	347.1	342.2	337.4	332.5	325.9	317.5	309.2	300.9	292.5	286.4
37.5°	333.8	328.5	323.1	317.8	312.5	305.4	296.4	287.5	278.6	269.7	263.1
40°	321.1	315.5	309.7	304.0	298.3	290.9	281.6	272.4	263.2	253.9	247.1
42.5°	308.1	302.1	296.1	290.1	284.1	276.3	266.7	257.2	247.7	238.2	231.2
45°	287.8	281.3	274.9	268.6	262.2	254.0	244.0	234.0	224.0	214.1	207.4
47.5°	267.9	261.1	254.4	247.6	240.8	232.3	222.0	211.7	201.3	191.1	184.4
50°	253.4	246.8	240.0	233.2	226.5	217.8	207.4	196.9	186.4	176.0	169.4
52.5°	239.4	232.3	225.4	218.3	211.2	202.6	192.3	182.1	171.8	161.6	155.2
55°	218.8	211.4	204.0	196.5	189.1	180.3	169.9	159.7	149.4	139.1	133.5
57.5°	197.7	190.0	182.4	174.8	167.2	158.4	148.5	138.7	128.8	118.9	113.7
60°	183.2	175.7	168.1	160.4	152.8	144.1	134.3	124.5	114.7	104.9	100.0
62.5°	169.2	161.6	154.0	146.4	138.7	130.3	120.9	111.6	102.3	92.9	88.3
65°	147.7	140.0	132.3	124.6	116.9	108.8	100.2	91.6	83.0	74.5	71.3
67.5°	127.0	119.3	111.7	104.1	96.4	88.7	81.0	73.3	65.6	57.9	56.4
70°	112.6	105.2	97.7	90.4	82.9	76.0	69.4	62.8	56.3	49.7	48.7
72.5°	98.9	91.8	84.6	77.6	70.4	64.3	59.0	53.7	48.4	43.2	42.3
75°	78.8	72.1	65.5	58.8	52.1	47.2	43.9	40.7	37.5	34.2	33.6
77.5°	59.0	53.2	47.3	41.5	35.6	32.0	30.3	28.8	27.2	25.7	25.4
80°	46.7	41.8	36.9	32.1	27.2	24.3	23.4	22.4	21.5	20.5	20.2
82.5°	35.3	31.6	27.8	24.0	20.3	18.0	17.3	16.7	16.0	15.5	15.2
85°	18.4	16.4	14.4	12.4	10.5	9.2	9.0	8.7	8.4	8.1	8.1
87.5°	5.7	5.6	5.5	5.4	5.3	5.7	6.6	7.4	8.4	9.3	9.1
90°	0.9	3.5	5.9	8.5	10.9	14.5	19.1	23.8	28.3	32.9	32.5
92.5°	16.8	18.6	20.5	22.2	24.1	25.5	26.7	27.7	28.8	29.9	30.0
95°	48.9	51.0	53.1	55.1	57.3	58.5	58.9	59.4	59.8	60.2	60.2
97.5°	89.4	91.2	93.0	94.9	96.7	98.0	98.9	99.6	100.4	101.2	101.2
100°	119.4	121.1	122.8	124.5	126.1	127.3	127.9	128.6	129.2	129.8	129.8
102.5°	151.1	152.4	153.7	155.0	156.4	157.5	158.3	159.1	159.9	160.7	160.8
105°	202.3	202.8	203.5	204.2	204.7	205.3	205.7	206.1	206.5	206.9	207.4
107.5°	253.7	254.7	255.6	256.6	257.5	257.9	257.9	257.9	257.9	257.9	258.1
110°	286.9	288.1	289.4	290.7	291.9	292.6	292.6	292.6	292.6	292.6	292.6



TEST NUMBER: P331637-830

CATALOG NUMBER: SA2XXRDIP-C290D925U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	323.0	324.2	325.6	326.8	328.0	328.6	328.4	328.2	328.1	327.9	327.4
115°	376.3	377.5	378.7	380.0	381.3	381.6	381.3	380.9	380.4	380.0	379.8
117.5°	429.3	430.9	432.6	434.3	436.0	436.2	435.1	433.9	432.7	431.6	431.0
120°	464.7	466.4	468.0	469.7	471.4	471.4	469.7	468.0	466.4	464.7	464.7
122.5°	497.0	499.0	501.1	503.0	505.0	505.5	504.3	503.1	502.0	500.8	500.3
125°	547.4	549.3	551.2	553.1	555.0	555.6	555.0	554.3	553.7	553.1	552.4
127.5°	596.5	598.9	601.3	603.7	606.1	606.9	606.1	605.4	604.6	603.9	603.1
130°	627.4	630.1	632.8	635.6	638.3	639.4	638.9	638.6	638.2	637.7	637.3
132.5°	662.0	664.2	666.5	668.6	670.9	672.0	672.1	672.2	672.2	672.3	671.5
135°	708.3	710.6	712.8	715.2	717.5	718.9	719.3	719.6	720.1	720.5	720.3
137.5°	757.1	758.8	760.7	762.6	764.5	765.7	766.3	766.9	767.4	767.9	767.8
140°	786.4	788.2	790.1	792.0	793.9	795.3	796.4	797.4	798.5	799.6	799.6
142.5°	816.4	818.3	820.2	822.1	824.0	825.3	826.0	826.7	827.4	828.1	828.3
145°	859.7	861.2	862.6	864.1	865.5	867.0	868.2	869.4	870.7	871.9	872.1
147.5°	898.2	900.0	901.8	903.5	905.3	906.6	907.5	908.2	909.1	909.9	910.4
150°	924.6	925.9	927.1	928.4	929.6	930.7	931.5	932.4	933.2	934.1	934.6
152.5°	947.9	949.2	950.5	951.7	953.0	954.1	955.1	956.1	957.1	958.1	958.9
155°	983.0	983.5	984.2	984.9	985.4	986.1	986.7	987.3	988.0	988.5	989.7
157.5°	1012.9	1013.2	1013.7	1014.1	1014.6	1014.9	1015.3	1015.7	1016.1	1016.4	1017.9
160°	1031.0	1031.3	1031.7	1032.2	1032.6	1032.9	1033.1	1033.3	1033.5	1033.7	1035.0
162.5°	1047.4	1047.5	1047.6	1047.7	1047.8	1047.9	1048.2	1048.4	1048.6	1048.8	1050.2
165°	1069.5	1069.3	1069.0	1068.8	1068.7	1068.6	1068.6	1068.6	1068.6	1068.6	1070.0
167.5°	1087.9	1087.3	1086.7	1086.0	1085.4	1085.1	1085.1	1085.0	1085.0	1084.9	1086.4
170°	1097.7	1097.0	1096.5	1095.8	1095.1	1094.8	1094.6	1094.4	1094.1	1093.9	1095.4
172.5°	1104.5	1103.8	1103.2	1102.6	1101.9	1101.5	1101.4	1101.1	1100.9	1100.7	1102.2
175°	1112.8	1112.1	1111.4	1110.9	1110.2	1109.7	1109.3	1108.9	1108.4	1108.1	1109.5
177.5°	1116.2	1115.6	1115.1	1114.7	1114.1	1113.7	1113.3	1113.0	1112.7	1112.4	1113.3
180°	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7



TEST NUMBER: P331637-830

CATALOG NUMBER: SA2XXRDIP-C290D925U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	473.2	473.2	473.2	473.2	473.2	473.2	473.2	473.2
2.5°	470.9	471.6	472.4	472.7	472.6	472.4	472.2	472.1
5°	467.1	468.0	468.8	469.1	468.8	468.5	468.3	468.0
7.5°	459.6	459.9	460.1	460.0	459.5	458.9	458.5	458.0
10°	452.0	451.8	451.5	451.0	450.4	449.9	449.3	448.7
12.5°	443.4	442.8	442.3	441.6	440.6	439.7	438.8	437.8
15°	427.2	425.3	423.5	422.2	421.2	420.2	419.2	418.3
17.5°	408.8	406.6	404.5	402.7	401.0	399.4	397.7	396.1
20°	396.1	393.6	391.2	389.0	386.9	384.8	382.8	380.7
22.5°	382.0	378.9	375.9	373.5	371.9	370.4	368.8	367.3
25°	358.7	354.8	350.9	348.3	346.9	345.3	343.9	342.5
27.5°	336.5	332.0	327.4	324.0	321.8	319.5	317.3	315.0
30°	320.8	316.0	311.1	307.5	304.8	302.3	299.7	297.2
32.5°	305.1	299.5	294.0	290.0	287.7	285.2	282.8	280.4
35°	280.5	274.5	268.4	264.4	262.3	260.2	258.2	256.1
37.5°	256.5	249.9	243.3	238.7	236.4	233.9	231.6	229.1
40°	240.4	233.7	226.9	222.3	219.8	217.4	214.8	212.4
42.5°	224.1	217.2	210.2	205.6	203.1	200.8	198.3	196.0
45°	200.6	193.8	187.1	182.6	180.3	178.0	175.7	173.4
47.5°	177.6	170.9	164.2	159.8	157.7	155.6	153.5	151.5
50°	162.9	156.3	149.7	145.4	143.5	141.5	139.4	137.4
52.5°	148.9	142.6	136.3	132.1	130.4	128.5	126.6	124.8
55°	127.7	122.1	116.3	112.5	110.7	109.0	107.2	105.4
57.5°	108.5	103.2	98.0	94.6	93.1	91.6	90.1	88.5
60°	95.2	90.4	85.5	82.3	80.8	79.3	77.8	76.3
62.5°	83.7	79.1	74.5	71.6	70.7	69.8	68.9	68.0
65°	68.1	64.8	61.5	59.8	59.5	59.2	58.9	58.6
67.5°	55.0	53.4	51.9	51.1	50.7	50.4	50.1	49.9
70°	47.8	46.8	45.9	45.2	44.8	44.4	44.0	43.6
72.5°	41.6	40.7	40.0	39.5	39.2	39.0	38.7	38.5
75°	32.9	32.2	31.6	31.2	31.1	31.0	30.9	30.8
77.5°	24.9	24.5	24.1	23.9	23.8	23.6	23.5	23.3
80°	19.8	19.4	19.0	18.9	18.9	18.9	18.9	18.9
82.5°	15.0	14.7	14.5	14.4	14.4	14.4	14.4	14.4
85°	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1
87.5°	9.0	8.9	8.7	8.7	8.7	8.7	8.8	8.8
90°	32.0	31.7	31.3	31.1	31.4	31.6	31.8	32.0
92.5°	30.1	30.2	30.3	30.3	30.3	30.3	30.4	30.4
95°	60.2	60.2	60.2	59.9	59.6	59.2	58.7	58.3
97.5°	101.2	101.2	101.2	101.2	101.1	101.1	101.0	101.0
100°	129.8	129.8	129.8	129.7	129.5	129.3	129.0	128.8
102.5°	161.0	161.2	161.4	161.3	161.1	160.9	160.7	160.5
105°	207.7	208.2	208.6	208.8	208.8	208.8	208.8	208.8
107.5°	258.3	258.4	258.5	258.2	257.2	256.3	255.3	254.3
110°	292.6	292.6	292.6	292.2	291.6	291.0	290.3	289.7





TEST NUMBER: P331637-830

CATALOG NUMBER: SA2XXRDIP-C290D925U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	326.9	326.4	325.9	325.4	325.0	324.5	324.0	323.6
115°	379.6	379.4	379.2	378.7	378.1	377.5	376.8	376.3
117.5°	430.6	430.1	429.5	429.0	428.4	427.7	427.1	426.5
120°	464.7	464.7	464.7	464.4	463.7	463.1	462.5	461.8
122.5°	499.7	499.3	498.8	498.3	497.9	497.4	496.9	496.4
125°	551.9	551.2	550.5	550.2	550.0	549.7	549.5	549.3
127.5°	602.4	601.6	600.9	600.1	599.5	598.8	598.1	597.5
130°	636.9	636.5	636.0	635.5	634.6	633.8	632.9	632.1
132.5°	670.5	669.6	668.6	667.9	667.2	666.6	665.9	665.2
135°	720.1	719.9	719.6	719.3	718.6	718.0	717.4	716.7
137.5°	767.6	767.4	767.2	766.8	765.9	765.1	764.2	763.4
140°	799.6	799.6	799.6	799.1	798.2	797.4	796.6	795.8
142.5°	828.5	828.6	828.8	828.5	827.6	826.8	826.0	825.1
145°	872.3	872.6	872.8	872.5	871.7	870.8	870.0	869.1
147.5°	910.9	911.3	911.8	911.6	910.9	910.0	909.3	908.4
150°	935.3	935.9	936.5	936.5	935.9	935.3	934.6	934.1
152.5°	959.7	960.5	961.3	961.3	960.5	959.7	958.9	958.1
155°	990.7	991.7	992.8	993.0	992.3	991.7	991.1	990.4
157.5°	1019.3	1020.7	1022.1	1022.3	1021.3	1020.3	1019.3	1018.3
160°	1036.2	1037.5	1038.8	1039.0	1038.1	1037.3	1036.4	1035.6
162.5°	1051.6	1053.0	1054.4	1054.7	1053.7	1052.6	1051.7	1050.7
165°	1071.5	1072.9	1074.4	1074.6	1073.6	1072.5	1071.5	1070.4
167.5°	1087.8	1089.3	1090.7	1090.9	1089.9	1088.7	1087.7	1086.6
170°	1096.8	1098.3	1099.8	1099.9	1098.6	1097.4	1096.1	1094.9
172.5°	1103.6	1105.1	1106.5	1106.6	1105.4	1104.2	1102.9	1101.6
175°	1111.0	1112.4	1113.9	1114.0	1112.8	1111.4	1110.2	1109.0
177.5°	1114.4	1115.4	1116.3	1116.3	1115.4	1114.4	1113.3	1112.4
180°	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7

(END OF REPORT)