

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333294-940

Luminaire Tested: **S125DIP-S1090D1205U940-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333294-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1090D1205U940-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7816.2 lumens
Efficiency: N/A
Efficacy: 119.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333294-940

CATALOG NUMBER: S125DIP-S1090D1205U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333294-940

CATALOG NUMBER: S125DIP-S1090D1205U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	50	49	48	43
2	89	82	75	70	82	76	70	66	64	60	57	54	51	48	44	42	40	36
3	81	72	64	58	75	66	60	55	57	52	48	47	44	41	39	36	34	30
4	74	63	56	49	68	59	52	46	50	45	41	42	38	35	35	32	29	26
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26	22
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	28	25	23	20
7	58	46	38	32	53	43	35	30	37	31	27	31	27	23	26	23	20	17
8	54	42	34	28	50	39	32	27	33	28	24	29	24	21	24	20	18	16
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9827	9827	9827
5°	9849	9756	9818
10°	9789	9686	9742
15°	9682	9570	9610
20°	9531	9407	9423
25°	9368	9213	9204
30°	9165	9004	8959
35°	8949	8779	8656
40°	8728	8535	8413
45°	8488	8312	8147
50°	8225	8043	7801
55°	7970	7739	7523
60°	7665	7432	7167
65°	7303	7065	6825
70°	6956	6637	6411
75°	6338	6128	5916
80°	5642	5553	5415
85°	4905	4994	4728



TEST NUMBER: P333294-940

CATALOG NUMBER: S125DIP-S1090D1205U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.5	1.8
10°-20°	405.3	5.2
20°-30°	598.4	7.7
30°-40°	698.2	8.9
40°-50°	701.3	9.0
50°-60°	615.6	7.9
60°-70°	458.7	5.9
70°-80°	262.3	3.4
80°-90°	79.2	1.0
90°-100°	372.5	4.8
100°-110°	800.8	10.2
110°-120°	751.5	9.6
120°-130°	609.1	7.8
130°-140°	488.8	6.3
140°-150°	368.8	4.7
150°-160°	259.6	3.3
160°-170°	153.0	2.0
170°-180°	49.8	0.6
0°-30°	1147.1	14.7
0°-40°	1845.3	23.6
0°-60°	3162.2	40.5
0°-90°	3962.3	50.7
90°-120°	1924.8	24.6
90°-150°	3391.5	43.4
90°-180°	3854.0	49.3
0°-180°	7816.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1522	1522	1522	1522	1522	
5°	1519	1516	1505	1515	1514	144
15°	1448	1444	1431	1437	1437	408
25°	1315	1308	1293	1295	1292	605
35°	1135	1130	1114	1107	1098	710
45°	929	924	910	896	892	716
55°	708	703	687	677	668	632
65°	478	475	462	452	447	474
75°	254	251	246	242	237	271
85°	66	67	67	66	64	74
90°	1	9	17	22	24	6
95°	34	101	918	416	244	36
105°	117	164	751	1479	1373	123
115°	209	252	603	1300	1529	206
125°	290	340	578	1034	1205	257
135°	340	409	574	867	1001	264
145°	396	453	576	718	790	248
155°	452	486	562	635	662	208
165°	493	507	539	571	580	139
175°	513	513	517	523	521	49
180°	514	514	514	514	514	



TEST NUMBER: P333294-940

CATALOG NUMBER: S125DIP-S1090D1205U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6
2.5°	1525.4	1524.8	1524.1	1523.5	1522.9	1521.4	1519.3	1517.2	1515.0	1512.9	1515.0
5°	1519.2	1518.7	1518.1	1517.6	1517.1	1515.5	1512.8	1510.1	1507.4	1504.8	1507.2
7.5°	1505.2	1504.7	1504.1	1503.6	1503.1	1501.3	1498.3	1495.4	1492.5	1489.5	1491.9
10°	1492.7	1492.2	1491.7	1491.1	1490.6	1488.8	1485.9	1482.9	1480.0	1477.0	1479.2
12.5°	1477.3	1476.3	1475.3	1474.4	1473.5	1471.6	1468.8	1466.2	1463.4	1460.6	1462.4
15°	1448.1	1447.3	1446.5	1445.7	1444.9	1443.1	1440.1	1437.2	1434.2	1431.3	1432.6
17.5°	1414.7	1413.5	1412.3	1411.1	1410.0	1407.8	1404.8	1401.8	1398.7	1395.6	1397.3
20°	1386.8	1386.3	1385.7	1385.2	1384.6	1382.6	1379.1	1375.6	1372.2	1368.7	1370.6
22.5°	1358.8	1357.9	1356.9	1355.9	1355.0	1352.8	1349.6	1346.3	1343.1	1339.8	1341.0
25°	1314.6	1313.2	1311.9	1310.5	1309.2	1306.8	1303.3	1299.8	1296.4	1292.9	1293.4
27.5°	1262.8	1261.9	1261.1	1260.3	1259.5	1257.4	1253.7	1250.2	1246.6	1243.0	1243.1
30°	1229.0	1228.2	1227.4	1226.6	1225.8	1223.4	1219.4	1215.4	1211.4	1207.4	1206.8
32.5°	1192.5	1191.2	1190.0	1188.7	1187.6	1185.2	1181.5	1177.9	1174.4	1170.8	1169.8
35°	1135.1	1134.1	1133.0	1131.9	1130.9	1128.5	1124.7	1121.0	1117.2	1113.5	1112.1
37.5°	1075.7	1074.3	1073.0	1071.7	1070.3	1067.9	1064.3	1060.9	1057.3	1053.8	1051.8
40°	1035.3	1033.9	1032.6	1031.3	1029.9	1027.3	1023.6	1019.8	1016.1	1012.4	1010.0
42.5°	991.9	990.8	989.7	988.6	987.4	985.0	981.2	977.5	973.7	970.0	967.8
45°	929.3	928.3	927.2	926.1	925.1	922.9	919.7	916.5	913.3	910.1	906.9
47.5°	861.9	861.9	862.0	862.1	862.1	860.2	856.4	852.5	848.6	844.8	841.5
50°	818.6	817.8	817.0	816.2	815.4	813.3	810.1	806.9	803.7	800.5	797.0
52.5°	774.3	773.6	773.1	772.5	772.0	769.9	766.5	763.0	759.6	756.2	753.1
55°	707.8	707.0	706.2	705.4	704.6	702.3	698.6	694.8	691.1	687.3	684.9
57.5°	637.8	637.3	636.9	636.5	636.1	634.3	631.1	627.9	624.8	621.6	618.5
60°	593.4	592.4	591.3	590.2	589.2	587.2	584.2	581.3	578.4	575.4	572.7
62.5°	547.2	546.4	545.5	544.7	543.9	542.2	539.6	537.1	534.6	532.1	529.1
65°	477.9	477.3	476.8	476.3	475.7	474.0	471.1	468.1	465.2	462.3	459.9
67.5°	410.7	409.6	408.5	407.3	406.3	404.6	402.3	400.2	398.0	395.8	393.8
70°	368.4	367.0	365.7	364.4	363.0	361.1	358.7	356.3	353.9	351.5	349.9
72.5°	322.2	321.2	320.3	319.4	318.5	317.3	315.8	314.1	312.6	311.0	309.2
75°	254.0	253.4	252.9	252.4	251.8	250.9	249.6	248.3	246.9	245.6	244.8
77.5°	191.2	190.9	190.7	190.6	190.3	189.8	189.0	188.3	187.6	186.8	186.4
80°	151.7	151.7	151.7	151.7	151.7	151.4	150.9	150.3	149.8	149.3	149.0
82.5°	117.0	116.5	116.2	115.7	115.3	115.0	114.9	114.9	114.7	114.6	114.1
85°	66.2	66.4	66.7	67.0	67.2	67.4	67.4	67.4	67.4	67.4	67.1
87.5°	26.2	26.4	26.8	27.3	27.6	28.0	28.0	28.2	28.2	28.4	28.5
90°	1.1	2.1	4.1	6.2	8.3	10.3	11.4	13.5	14.5	16.6	17.7
92.5°	12.7	15.3	24.1	36.9	54.8	85.0	141.5	236.5	339.5	334.0	270.5
95°	34.2	35.2	43.5	54.9	77.7	124.3	235.2	463.2	749.1	918.0	898.3
97.5°	56.8	58.1	63.8	75.3	95.8	129.3	202.7	369.7	669.0	980.3	1136.7
100°	72.5	74.6	78.7	90.2	109.9	140.9	201.0	335.7	596.8	935.6	1194.6
102.5°	90.0	91.2	94.5	106.7	124.8	155.0	208.5	321.6	542.1	856.8	1159.8
105°	117.1	117.1	122.3	132.6	149.2	178.3	223.8	316.0	489.0	751.2	1048.6
107.5°	143.6	145.7	150.6	159.2	176.4	202.4	246.6	325.6	466.6	678.4	935.0
110°	162.6	164.8	168.9	178.3	193.8	220.7	263.1	334.7	460.0	644.4	870.3



TEST NUMBER: P333294-940

CATALOG NUMBER: S125DIP-S1090D1205U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	181.7	183.8	187.1	196.4	212.0	238.1	278.9	346.3	460.0	624.6	822.2
115°	209.3	211.3	214.5	223.8	239.3	265.3	303.6	363.6	463.2	603.1	769.8
117.5°	234.2	237.3	240.6	249.9	267.5	292.6	328.9	383.6	470.0	592.5	738.5
120°	250.7	253.9	258.0	267.3	284.9	310.9	347.1	396.8	476.6	587.5	721.1
122.5°	268.1	270.5	273.8	283.0	302.4	328.2	364.5	411.8	482.4	583.4	706.2
125°	290.1	292.2	297.4	306.7	326.4	353.3	387.5	432.0	492.1	578.2	685.9
127.5°	307.3	310.4	317.1	328.9	349.8	376.7	409.7	450.8	503.1	575.7	667.3
130°	318.1	321.2	329.5	343.0	364.7	391.6	423.7	463.2	509.8	574.0	654.9
132.5°	326.4	330.3	340.3	355.4	378.0	404.9	437.0	473.9	517.2	574.0	644.9
135°	339.8	344.0	356.4	373.0	394.8	422.8	454.9	489.0	527.4	574.0	633.1
137.5°	356.9	360.0	371.6	388.2	409.5	438.3	467.5	500.2	536.7	575.2	622.5
140°	366.8	369.9	382.4	399.0	418.6	446.6	476.6	507.7	540.8	576.0	617.5
142.5°	378.4	380.7	392.3	408.8	427.8	454.1	482.4	511.8	543.3	576.9	613.4
145°	395.8	397.9	408.2	422.8	441.4	465.2	492.1	518.1	546.1	576.0	607.2
147.5°	414.0	415.3	424.2	437.7	453.8	474.7	498.4	521.8	547.1	573.4	600.7
150°	424.8	426.9	434.2	447.6	462.1	479.7	502.5	524.3	547.1	570.9	595.8
152.5°	436.4	437.7	444.1	455.9	469.6	485.5	506.7	525.9	546.3	567.6	590.0
155°	451.7	451.7	458.0	468.3	478.7	493.2	510.8	527.4	543.9	561.6	580.2
157.5°	465.5	465.2	470.2	479.1	488.2	499.2	514.3	528.4	541.3	555.4	571.1
160°	474.6	473.5	477.7	484.9	493.2	502.5	516.0	528.4	538.8	551.3	563.7
162.5°	482.0	481.0	485.1	491.5	498.2	505.9	517.6	527.6	536.3	546.3	557.1
165°	493.2	491.2	494.3	499.4	503.5	509.8	518.1	526.4	532.5	538.8	547.1
167.5°	500.7	499.6	501.5	504.4	507.3	511.2	518.1	523.9	526.7	531.5	537.3
170°	505.6	504.6	505.6	507.7	509.8	512.9	518.1	522.2	524.3	527.4	531.5
172.5°	509.0	507.1	508.1	510.1	511.4	512.9	517.2	520.6	520.9	522.5	525.8
175°	512.9	510.8	511.8	512.9	512.9	512.9	516.0	518.1	517.0	517.0	518.1
177.5°	514.8	513.1	513.1	513.9	513.1	513.1	514.8	515.6	513.9	513.9	514.8
180°	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9



TEST NUMBER: P333294-940

CATALOG NUMBER: S125DIP-S1090D1205U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6
2.5°	1517.2	1519.3	1521.4	1522.4	1522.2	1522.0	1521.8	1521.6
5°	1509.6	1512.0	1514.4	1515.5	1515.2	1514.9	1514.7	1514.4
7.5°	1494.2	1496.6	1499.0	1500.0	1499.8	1499.5	1499.2	1499.0
10°	1481.3	1483.5	1485.6	1486.6	1486.3	1486.0	1485.8	1485.5
12.5°	1464.1	1465.8	1467.5	1468.4	1468.3	1468.2	1468.2	1468.1
15°	1434.0	1435.3	1436.6	1437.3	1437.3	1437.3	1437.3	1437.3
17.5°	1399.0	1400.6	1402.3	1402.5	1401.1	1399.8	1398.5	1397.1
20°	1372.4	1374.3	1376.2	1376.4	1375.1	1373.8	1372.4	1371.1
22.5°	1342.3	1343.5	1344.7	1344.9	1344.0	1343.1	1342.2	1341.2
25°	1294.0	1294.5	1295.0	1294.9	1294.1	1293.2	1292.4	1291.6
27.5°	1243.2	1243.3	1243.5	1243.1	1242.3	1241.5	1240.7	1239.9
30°	1206.3	1205.8	1205.2	1204.6	1203.8	1203.0	1202.2	1201.4
32.5°	1168.9	1167.9	1167.0	1165.7	1164.3	1162.9	1161.4	1159.9
35°	1110.8	1109.5	1108.1	1106.4	1104.3	1102.2	1100.0	1097.9
37.5°	1049.8	1047.8	1045.9	1044.3	1043.0	1041.8	1040.5	1039.4
40°	1007.5	1005.1	1002.7	1001.1	1000.3	999.5	998.7	997.9
42.5°	965.6	963.4	961.3	959.5	958.3	957.1	955.8	954.6
45°	903.7	900.4	897.2	895.2	894.4	893.6	892.8	892.0
47.5°	838.3	835.0	831.8	829.2	827.3	825.5	823.6	821.7
50°	793.5	790.1	786.6	783.9	782.0	780.2	778.3	776.4
52.5°	750.1	747.1	744.0	741.5	739.3	737.3	735.2	733.1
55°	682.5	680.1	677.7	675.6	673.7	671.8	669.9	668.1
57.5°	615.5	612.3	609.2	607.2	606.2	605.1	604.1	603.1
60°	570.1	567.4	564.7	562.4	560.5	558.7	556.8	554.9
62.5°	526.3	523.4	520.5	518.4	516.9	515.5	514.0	512.6
65°	457.4	455.0	452.6	450.8	449.8	448.7	447.6	446.6
67.5°	391.7	389.7	387.6	386.3	385.7	385.0	384.4	383.8
70°	348.3	346.7	345.1	343.8	342.7	341.6	340.5	339.5
72.5°	307.5	305.6	303.8	302.4	301.3	300.2	299.2	298.1
75°	244.0	243.2	242.4	241.4	240.3	239.2	238.2	237.1
77.5°	185.8	185.4	184.9	184.3	183.5	182.8	182.0	181.3
80°	148.7	148.5	148.2	147.8	147.2	146.7	146.2	145.6
82.5°	113.6	113.2	112.7	112.4	112.3	112.2	112.1	111.9
85°	66.9	66.6	66.3	65.9	65.4	64.8	64.3	63.8
87.5°	28.8	29.0	29.2	29.4	29.0	28.5	28.3	27.9
90°	18.6	19.7	20.7	22.8	22.8	22.8	23.8	23.8
92.5°	183.6	133.2	100.3	85.0	71.7	69.2	67.8	66.1
95°	744.9	587.5	460.0	373.0	299.4	268.3	260.1	243.5
97.5°	1109.5	999.1	874.9	753.9	689.8	631.9	601.8	588.5
100°	1274.4	1223.7	1117.0	1009.1	937.7	863.1	824.7	808.2
102.5°	1330.0	1361.3	1310.1	1237.2	1160.7	1107.6	1066.0	1053.6
105°	1297.3	1439.2	1484.8	1473.4	1440.2	1406.0	1385.3	1372.9
107.5°	1180.4	1369.8	1486.8	1541.0	1557.7	1557.6	1550.7	1542.4
110°	1094.1	1291.0	1437.1	1525.2	1571.8	1591.5	1598.7	1598.7



TEST NUMBER: P333294-940

CATALOG NUMBER: S125DIP-S1090D1205U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1026.2	1213.1	1360.8	1464.6	1532.9	1566.6	1584.7	1592.1
115°	940.8	1101.4	1243.3	1356.3	1437.1	1486.8	1515.8	1529.3
117.5°	885.6	1024.1	1146.4	1250.0	1330.8	1382.2	1411.0	1419.2
120°	855.9	980.2	1094.1	1185.4	1262.0	1311.7	1339.7	1348.0
122.5°	833.5	948.7	1050.3	1135.6	1204.0	1249.6	1277.6	1285.0
125°	800.9	906.6	996.8	1071.4	1129.4	1171.9	1194.6	1205.1
127.5°	767.8	866.4	950.6	1020.4	1073.0	1110.5	1132.1	1136.7
130°	747.1	838.2	919.1	986.4	1038.2	1072.4	1093.1	1099.3
132.5°	726.3	811.7	885.0	949.9	1001.7	1035.9	1055.0	1062.0
135°	699.4	770.9	837.2	896.3	941.8	976.1	994.7	1000.9
137.5°	676.6	734.4	789.5	839.7	880.5	911.6	928.8	935.6
140°	664.1	712.8	760.5	804.1	842.4	869.3	884.8	890.0
142.5°	653.4	694.6	735.7	773.4	805.9	828.7	843.4	847.7
145°	639.3	671.4	703.6	731.5	756.3	774.0	785.4	789.5
147.5°	626.1	652.1	676.8	697.9	717.6	731.7	738.3	740.2
150°	618.6	641.4	661.0	679.7	695.3	707.7	711.9	712.8
152.5°	610.3	630.6	648.6	663.2	676.2	686.1	690.3	691.3
155°	597.8	614.4	628.9	640.3	650.7	657.9	661.0	662.1
157.5°	585.4	599.1	610.3	619.2	627.2	633.3	636.1	636.0
160°	577.1	587.5	597.8	605.1	612.3	617.5	619.6	618.6
162.5°	568.0	577.6	586.2	592.6	598.2	602.6	603.1	602.8
165°	555.4	562.6	568.8	574.0	578.2	580.2	580.2	580.2
167.5°	543.3	548.1	552.9	556.6	558.7	560.5	559.7	559.5
170°	536.7	539.8	543.0	545.0	547.1	548.1	548.1	547.1
172.5°	529.2	532.4	534.7	535.9	536.3	538.1	536.5	535.5
175°	521.2	521.2	523.3	523.3	523.3	524.3	522.2	521.2
177.5°	515.6	516.4	516.4	516.4	515.6	516.4	513.9	513.9
180°	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9

(END OF REPORT)