

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331638-830

Luminaire Tested: **SA2XXRDIP-C290D925U830-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331638-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C290D925U830-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4381.4 lumens
Efficiency: N/A
Efficacy: 117.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331638-830
CATALOG NUMBER: SA2XXRDIP-C290D925U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331638-830

CATALOG NUMBER: SA2XXRDIP-C290D925U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31	22
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	27	27	26	19
2	84	77	71	66	74	68	64	59	52	49	47	38	36	34	24	23	22	16
3	76	68	61	55	68	60	54	50	46	42	39	34	31	29	22	20	19	14
4	70	60	52	47	62	53	47	42	41	37	34	30	27	25	20	18	17	12
5	64	53	46	40	57	48	41	36	37	32	29	27	24	22	18	16	15	11
6	59	48	40	35	52	43	36	31	33	29	25	24	21	19	16	14	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12	9
8	50	39	31	26	45	35	29	24	27	23	19	20	17	15	13	12	10	8
9	47	35	28	23	42	32	26	21	25	20	17	19	16	13	12	11	9	7
10	44	32	25	21	39	29	23	19	23	19	16	17	14	12	12	10	9	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7640	7640	7640
5°	7669	7543	7585
10°	7609	7420	7356
15°	7522	7199	6992
20°	7400	6887	6541
25°	7277	6531	6102
30°	7105	6162	5541
35°	6936	5765	5048
40°	6768	5351	4477
45°	6572	4889	3959
50°	6365	4421	3451
55°	6159	3916	2967
60°	5916	3387	2464
65°	5643	2846	2239
70°	5316	2346	2058
75°	4916	2133	1921
80°	4342	1906	1757
85°	3409	1501	1501



TEST NUMBER: P331638-830

CATALOG NUMBER: SA2XXRDIP-C290D925U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.3	1.0
10°-20°	121.6	2.8
20°-30°	170.8	3.9
30°-40°	186.2	4.2
40°-50°	171.2	3.9
50°-60°	134.5	3.1
60°-70°	87.7	2.0
70°-80°	45.2	1.0
80°-90°	16.1	0.4
90°-100°	195.6	4.5
100°-110°	663.7	15.1
110°-120°	705.1	16.1
120°-130°	580.4	13.2
130°-140°	466.1	10.6
140°-150°	352.2	8.0
150°-160°	247.5	5.6
160°-170°	145.7	3.3
170°-180°	47.4	1.1
0°-30°	336.6	7.7
0°-40°	522.8	11.9
0°-60°	828.5	18.9
0°-90°	977.5	22.3
90°-120°	1564.4	35.7
90°-150°	2963.2	67.6
90°-180°	3404.0	77.7
0°-180°	4381.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	473	473	473	473	473	
5°	473	471	465	469	468	45
15°	450	445	431	423	418	127
25°	408	394	367	350	342	188
35°	352	329	292	266	256	220
45°	288	258	214	185	173	222
55°	219	185	139	114	105	195
65°	148	113	74	61	59	146
75°	79	50	34	31	31	83
85°	18	10	8	8	8	22
90°	1	13	32	31	31	3
95°	33	81	369	139	107	35
105°	115	173	697	1246	1060	122
115°	202	255	583	1204	1395	200
125°	282	334	561	975	1132	251
135°	331	395	554	819	938	256
145°	378	435	551	684	749	237
155°	430	464	535	605	629	198
165°	468	483	513	544	552	132
175°	488	489	493	499	498	46
180°	489	489	489	489	489	



TEST NUMBER: P331638-830

CATALOG NUMBER: SA2XXRDIP-C290D925U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	473.2	473.2	473.2	473.2	473.2	473.2	473.2	473.2	473.2	473.2	473.2
2.5°	474.9	474.5	474.1	473.7	473.3	472.7	471.8	471.1	470.2	469.4	470.1
5°	473.2	472.7	472.2	471.7	471.3	470.3	469.1	467.9	466.7	465.4	466.3
7.5°	468.3	467.7	467.0	466.5	465.9	464.9	463.4	461.9	460.5	459.1	459.3
10°	464.1	463.4	462.8	462.1	461.5	460.1	458.3	456.4	454.5	452.6	452.3
12.5°	459.0	458.2	457.3	456.6	455.7	454.1	451.7	449.2	446.8	444.3	443.8
15°	450.0	448.9	447.9	446.9	445.8	443.7	440.5	437.2	433.9	430.7	429.0
17.5°	438.9	437.3	435.7	434.1	432.5	429.7	425.6	421.4	417.3	413.1	410.9
20°	430.7	428.9	427.0	425.0	423.1	419.8	415.0	410.3	405.6	400.8	398.4
22.5°	421.9	419.7	417.5	415.5	413.3	409.5	404.2	398.8	393.5	388.1	385.0
25°	408.5	405.4	402.4	399.4	396.3	391.6	385.3	379.1	372.8	366.6	362.6
27.5°	392.4	389.1	385.8	382.5	379.1	373.9	366.8	359.8	352.7	345.6	341.1
30°	381.1	377.5	373.8	370.2	366.6	361.0	353.4	345.8	338.2	330.5	325.7
32.5°	370.1	365.9	361.7	357.4	353.2	347.2	339.5	331.7	324.0	316.1	310.7
35°	351.9	347.1	342.2	337.4	332.5	325.9	317.5	309.2	300.9	292.5	286.4
37.5°	333.8	328.5	323.1	317.8	312.5	305.4	296.4	287.5	278.6	269.7	263.1
40°	321.1	315.5	309.7	304.0	298.3	290.9	281.6	272.4	263.2	253.9	247.1
42.5°	308.1	302.1	296.1	290.1	284.1	276.3	266.7	257.2	247.7	238.2	231.2
45°	287.8	281.3	274.9	268.6	262.2	254.0	244.0	234.0	224.0	214.1	207.4
47.5°	267.9	261.1	254.4	247.6	240.8	232.3	222.0	211.7	201.3	191.1	184.4
50°	253.4	246.8	240.0	233.2	226.5	217.8	207.4	196.9	186.4	176.0	169.4
52.5°	239.4	232.3	225.4	218.3	211.2	202.6	192.3	182.1	171.8	161.6	155.2
55°	218.8	211.4	204.0	196.5	189.1	180.3	169.9	159.7	149.4	139.1	133.5
57.5°	197.7	190.0	182.4	174.8	167.2	158.4	148.5	138.7	128.8	118.9	113.7
60°	183.2	175.7	168.1	160.4	152.8	144.1	134.3	124.5	114.7	104.9	100.0
62.5°	169.2	161.6	154.0	146.4	138.7	130.3	120.9	111.6	102.3	92.9	88.3
65°	147.7	140.0	132.3	124.6	116.9	108.8	100.2	91.6	83.0	74.5	71.3
67.5°	127.0	119.3	111.7	104.1	96.4	88.7	81.0	73.3	65.6	57.9	56.4
70°	112.6	105.2	97.7	90.4	82.9	76.0	69.4	62.8	56.3	49.7	48.7
72.5°	98.9	91.8	84.6	77.6	70.4	64.3	59.0	53.7	48.4	43.2	42.3
75°	78.8	72.1	65.5	58.8	52.1	47.2	43.9	40.7	37.5	34.2	33.6
77.5°	59.0	53.2	47.3	41.5	35.6	32.0	30.3	28.8	27.2	25.7	25.4
80°	46.7	41.8	36.9	32.1	27.2	24.3	23.4	22.4	21.5	20.5	20.2
82.5°	35.3	31.6	27.8	24.0	20.3	18.0	17.3	16.7	16.0	15.5	15.2
85°	18.4	16.4	14.4	12.4	10.5	9.2	9.0	8.7	8.4	8.1	8.1
87.5°	5.7	5.7	5.7	5.6	5.3	5.6	6.5	7.8	9.0	9.1	8.9
90°	0.9	3.8	7.5	9.4	11.3	14.1	18.9	25.4	31.0	32.0	31.0
92.5°	11.5	16.6	23.4	27.4	33.8	42.7	64.0	93.9	120.6	122.2	103.3
95°	32.9	36.7	46.1	54.6	69.7	92.2	135.4	217.3	326.4	368.7	322.6
97.5°	53.6	58.7	68.7	81.4	98.8	124.3	178.7	292.8	474.1	629.5	660.3
100°	72.4	75.2	83.7	98.8	117.6	143.9	193.8	308.6	511.7	743.1	878.6
102.5°	89.7	91.8	100.3	115.4	134.9	161.3	207.4	309.3	497.5	746.9	959.9
105°	114.8	118.6	125.1	139.2	159.9	186.2	230.5	314.1	469.4	697.0	947.3
107.5°	141.9	144.9	151.3	164.3	184.7	211.3	254.2	327.2	455.4	643.7	864.7
110°	159.9	163.7	169.3	181.5	201.3	228.6	269.9	337.7	452.5	618.0	812.8



TEST NUMBER: P331638-830

CATALOG NUMBER: SA2XXRDIP-C290D925U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	176.4	180.2	186.6	198.1	217.1	245.2	285.0	349.0	453.2	601.4	776.7
115°	202.3	207.0	212.6	223.9	242.7	268.1	308.6	365.9	457.1	583.2	731.9
117.5°	228.9	232.7	238.4	248.4	266.4	292.8	330.2	384.0	463.9	574.4	703.6
120°	245.5	249.3	255.0	263.3	282.2	308.6	345.3	396.1	468.4	569.1	688.6
122.5°	261.4	264.3	269.9	279.2	298.0	325.1	359.5	406.5	473.7	566.1	675.8
125°	282.2	285.0	290.7	302.0	320.7	347.1	381.0	423.3	481.6	560.6	657.5
127.5°	298.8	302.6	310.4	322.8	340.9	368.0	401.0	438.9	489.7	557.4	640.6
130°	308.6	312.3	321.7	334.9	353.7	380.0	412.9	448.7	495.8	555.9	629.3
132.5°	317.5	322.1	332.2	346.2	365.7	392.1	423.5	458.5	501.7	555.2	620.3
135°	331.1	334.9	346.2	360.2	381.9	408.2	438.4	471.3	508.9	554.0	607.7
137.5°	343.9	348.5	359.7	374.8	396.2	420.7	450.4	481.1	515.3	553.8	598.8
140°	353.7	357.5	368.7	383.8	404.5	429.0	457.1	486.4	518.3	553.1	593.6
142.5°	363.4	366.5	377.0	392.1	412.0	435.0	462.4	490.9	520.6	553.1	588.3
145°	378.1	381.9	391.3	405.5	424.2	445.0	470.3	496.7	523.0	551.2	581.4
147.5°	394.0	396.8	405.8	418.8	434.4	452.9	476.7	499.9	523.8	547.9	574.2
150°	404.5	407.3	414.8	427.1	441.2	458.1	479.8	501.3	523.0	545.6	568.2
152.5°	415.0	416.3	423.9	434.6	448.0	463.4	482.8	502.1	521.5	541.9	562.9
155°	429.9	430.8	436.5	446.9	457.1	471.3	487.3	503.2	519.2	535.3	553.1
157.5°	442.3	443.3	447.8	456.8	465.1	476.9	490.5	503.2	514.9	528.5	543.9
160°	450.6	451.6	455.2	462.8	470.3	480.7	492.0	503.2	512.6	524.0	537.2
162.5°	458.8	458.3	462.0	468.1	474.9	483.0	492.8	502.5	510.4	520.2	531.1
165°	468.4	467.5	469.4	475.0	479.8	485.4	493.9	500.5	506.1	512.6	521.1
167.5°	476.4	475.2	476.9	480.5	483.9	487.5	493.7	499.2	501.7	506.1	511.3
170°	481.6	479.8	480.7	483.5	485.4	488.2	492.9	497.7	499.5	502.3	506.1
172.5°	484.7	483.5	483.0	485.8	486.9	489.0	492.2	495.4	496.5	497.9	500.9
175°	488.2	487.3	486.4	488.2	488.2	489.2	491.1	492.9	492.0	492.9	493.9
177.5°	489.9	488.4	487.7	489.2	489.2	489.2	489.9	491.4	489.9	489.2	489.9
180°	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2



TEST NUMBER: P331638-830

CATALOG NUMBER: SA2XXRDIP-C290D925U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	473.2	473.2	473.2	473.2	473.2	473.2	473.2	473.2
2.5°	470.9	471.6	472.4	472.7	472.6	472.4	472.2	472.1
5°	467.1	468.0	468.8	469.1	468.8	468.5	468.3	468.0
7.5°	459.6	459.9	460.1	460.0	459.5	458.9	458.5	458.0
10°	452.0	451.8	451.5	451.0	450.4	449.9	449.3	448.7
12.5°	443.4	442.8	442.3	441.6	440.6	439.7	438.8	437.8
15°	427.2	425.3	423.5	422.2	421.2	420.2	419.2	418.3
17.5°	408.8	406.6	404.5	402.7	401.0	399.4	397.7	396.1
20°	396.1	393.6	391.2	389.0	386.9	384.8	382.8	380.7
22.5°	382.0	378.9	375.9	373.5	371.9	370.4	368.8	367.3
25°	358.7	354.8	350.9	348.3	346.9	345.3	343.9	342.5
27.5°	336.5	332.0	327.4	324.0	321.8	319.5	317.3	315.0
30°	320.8	316.0	311.1	307.5	304.8	302.3	299.7	297.2
32.5°	305.1	299.5	294.0	290.0	287.7	285.2	282.8	280.4
35°	280.5	274.5	268.4	264.4	262.3	260.2	258.2	256.1
37.5°	256.5	249.9	243.3	238.7	236.4	233.9	231.6	229.1
40°	240.4	233.7	226.9	222.3	219.8	217.4	214.8	212.4
42.5°	224.1	217.2	210.2	205.6	203.1	200.8	198.3	196.0
45°	200.6	193.8	187.1	182.6	180.3	178.0	175.7	173.4
47.5°	177.6	170.9	164.2	159.8	157.7	155.6	153.5	151.5
50°	162.9	156.3	149.7	145.4	143.5	141.5	139.4	137.4
52.5°	148.9	142.6	136.3	132.1	130.4	128.5	126.6	124.8
55°	127.7	122.1	116.3	112.5	110.7	109.0	107.2	105.4
57.5°	108.5	103.2	98.0	94.6	93.1	91.6	90.1	88.5
60°	95.2	90.4	85.5	82.3	80.8	79.3	77.8	76.3
62.5°	83.7	79.1	74.5	71.6	70.7	69.8	68.9	68.0
65°	68.1	64.8	61.5	59.8	59.5	59.2	58.9	58.6
67.5°	55.0	53.4	51.9	51.1	50.7	50.4	50.1	49.9
70°	47.8	46.8	45.9	45.2	44.8	44.4	44.0	43.6
72.5°	41.6	40.7	40.0	39.5	39.2	39.0	38.7	38.5
75°	32.9	32.2	31.6	31.2	31.1	31.0	30.9	30.8
77.5°	24.9	24.5	24.1	23.9	23.8	23.6	23.5	23.3
80°	19.8	19.4	19.0	18.9	18.9	18.9	18.9	18.9
82.5°	15.0	14.7	14.5	14.4	14.4	14.4	14.4	14.4
85°	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1
87.5°	8.6	8.2	8.5	8.6	8.6	8.6	8.6	8.6
90°	30.1	28.2	30.1	31.0	31.0	31.0	31.0	31.0
92.5°	82.0	70.4	62.5	56.6	55.9	52.9	53.6	52.1
95°	246.5	189.1	149.6	128.8	116.7	109.1	106.3	107.3
97.5°	575.1	470.5	368.7	300.9	255.9	232.7	219.0	211.1
100°	858.8	742.2	613.3	499.5	421.4	381.0	353.7	336.8
102.5°	1044.7	1018.4	924.2	803.5	718.7	649.6	615.6	592.7
105°	1142.9	1249.2	1261.5	1230.4	1172.1	1113.8	1073.3	1060.2
107.5°	1072.2	1232.3	1330.1	1375.6	1383.0	1379.8	1371.7	1354.2
110°	1011.3	1179.6	1300.0	1377.1	1417.6	1435.5	1444.0	1443.0



TEST NUMBER: P331638-830

CATALOG NUMBER: SA2XXRDIP-C290D925U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	955.5	1117.2	1245.9	1334.3	1390.5	1420.4	1436.4	1441.5
115°	887.0	1031.9	1155.2	1252.1	1318.8	1362.1	1386.6	1395.1
117.5°	835.5	962.7	1074.4	1165.4	1233.4	1279.1	1305.0	1312.0
120°	809.9	926.6	1026.2	1111.9	1177.7	1221.9	1249.2	1258.7
122.5°	789.6	896.5	990.9	1068.3	1127.3	1170.7	1195.0	1203.0
125°	760.1	857.0	939.7	1010.3	1064.9	1100.6	1124.1	1131.6
127.5°	730.9	818.6	896.6	961.8	1009.4	1042.8	1063.2	1069.2
130°	712.1	793.0	867.3	929.4	975.5	1007.5	1026.2	1033.8
132.5°	694.0	768.9	837.2	895.5	940.8	972.9	990.1	996.9
135°	668.8	730.9	793.0	845.6	886.1	917.2	934.1	937.8
137.5°	648.7	700.6	749.9	795.8	832.7	859.4	874.3	880.0
140°	635.9	681.1	724.3	765.7	795.8	820.3	834.4	840.0
142.5°	625.4	663.7	701.0	735.7	764.2	786.5	799.0	800.1
145°	610.5	641.6	670.7	698.0	720.6	736.6	745.9	748.8
147.5°	599.0	623.5	646.2	666.2	684.9	697.6	704.0	705.7
150°	590.8	611.4	631.2	648.1	662.2	673.5	679.2	680.1
152.5°	582.5	601.6	618.4	633.1	644.1	653.9	658.1	658.3
155°	571.0	586.1	600.1	610.5	620.9	627.5	631.2	629.3
157.5°	557.6	570.2	582.1	590.2	597.5	602.9	604.6	604.6
160°	549.3	559.7	570.0	576.6	583.2	588.0	588.9	588.9
162.5°	541.1	549.9	558.7	563.8	570.4	573.6	574.6	573.8
165°	528.7	535.3	541.9	545.6	549.3	553.1	553.1	552.1
167.5°	516.8	521.9	526.4	529.8	531.5	533.6	533.4	532.3
170°	510.8	513.6	517.4	519.2	520.2	523.0	522.1	520.2
172.5°	504.0	506.1	509.1	510.2	511.1	512.5	511.5	510.4
175°	496.7	497.7	498.6	499.5	499.5	500.5	499.5	497.7
177.5°	491.4	491.4	492.2	492.2	492.2	492.2	491.4	489.9
180°	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2

(END OF REPORT)