

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331659-830

Luminaire Tested: **SA2XXRDIP-C485D725U830-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331659-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C485D725U830-4F0-1E-UDD-A4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4420.2 lumens  
Efficiency: N/A  
Efficacy: 115.1 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 38.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331659-830  
CATALOG NUMBER: SA2XXRDIP-C485D725U830-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P331659-830

CATALOG NUMBER: SA2XXRDIP-C485D725U830-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47	40
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	41	41	35
2	88	81	75	71	80	74	69	65	61	58	55	49	47	45	38	36	35	30
3	81	72	65	60	73	66	60	55	54	50	47	44	41	39	34	32	31	26
4	74	64	57	51	67	59	52	47	49	44	40	40	36	34	31	29	27	23
5	68	57	50	44	62	53	46	41	44	39	35	36	32	30	28	26	24	21
6	63	52	44	39	57	48	41	36	40	35	31	33	29	26	26	23	22	19
7	58	47	39	34	53	43	37	32	36	31	28	30	26	24	24	21	19	17
8	54	43	35	30	50	39	33	28	33	28	25	28	24	21	22	20	18	15
9	51	39	32	27	46	36	30	26	31	26	22	25	22	19	21	18	16	14
10	47	36	29	25	43	33	27	23	28	24	20	24	20	18	19	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	16356	16356	16356	16356
5°	18266	16459	14593	16459
10°	20266	16342	12650	16342
15°	21264	16104	9967	16104
20°	18433	15747	8624	15747
25°	12089	15262	7701	15262
30°	8138	14673	6969	14673
35°	6591	13931	6286	13931
40°	5861	13122	5817	13122
45°	5304	12177	5190	12177
50°	4828	11235	4808	11235
55°	4538	10196	4479	10196
60°	3794	9242	3749	9242
65°	3202	8390	3629	8390
70°	2960	7492	3423	7492
75°	2770	6519	3163	6519
80°	2548	5365	2817	5365
85°	2334	4242	2482	4242



TEST NUMBER: P331659-830

CATALOG NUMBER: SA2XXRDIP-C485D725U830-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	96.0	2.2
10°-20°	267.6	6.1
20°-30°	344.8	7.8
30°-40°	327.7	7.4
40°-50°	280.7	6.4
50°-60°	213.8	4.8
60°-70°	135.1	3.1
70°-80°	67.5	1.5
80°-90°	21.0	0.5
90°-100°	153.2	3.5
100°-110°	519.8	11.8
110°-120°	552.3	12.5
120°-130°	454.6	10.3
130°-140°	365.1	8.3
140°-150°	275.9	6.2
150°-160°	193.9	4.4
160°-170°	114.1	2.6
170°-180°	37.1	0.8
0°-30°	708.4	16.0
0°-40°	1036.1	23.4
0°-60°	1530.5	34.6
0°-90°	1754.1	39.7
90°-120°	1225.3	27.7
90°-150°	2320.9	52.5
90°-180°	2666.0	60.3
0°-180°	4420.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1013	1013	1013	1013	1013	
5°	1127	1016	900	1016	1127	111
15°	1272	963	596	963	1272	343
25°	679	857	432	857	679	322
35°	334	707	319	707	334	214
45°	232	533	227	533	232	180
55°	161	362	159	362	161	141
65°	84	220	95	220	84	85
75°	44	104	51	104	44	47
85°	13	23	13	23	13	14
90°	24	1	24	1	24	14
95°	84	26	84	26	84	109
105°	830	90	830	90	830	803
115°	1093	158	1093	158	1093	1070
125°	886	221	886	221	886	801
135°	735	259	735	259	735	571
145°	586	296	586	296	586	372
155°	493	337	493	337	493	230
165°	432	367	432	367	432	124
175°	390	382	390	382	390	38
180°	383	383	383	383	383	



TEST NUMBER: P331659-830

CATALOG NUMBER: SA2XXRDIP-C485D725U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0
2.5°	1054.1	1055.0	1055.8	1053.9	1053.9	1052.2	1048.5	1045.7	1037.7	1036.6	1036.6
5°	1127.0	1126.3	1127.8	1123.1	1116.8	1115.4	1108.7	1099.9	1090.8	1080.5	1078.5
7.5°	1199.6	1198.5	1195.7	1194.9	1190.1	1179.4	1168.7	1157.2	1142.0	1127.1	1119.6
10°	1236.1	1247.7	1240.8	1228.4	1230.9	1214.4	1205.5	1190.4	1177.7	1155.6	1150.7
12.5°	1272.1	1276.8	1274.5	1267.5	1264.4	1252.9	1241.0	1227.9	1204.5	1184.6	1167.2
15°	1272.1	1278.7	1280.5	1278.4	1280.2	1279.4	1273.1	1262.2	1241.8	1219.9	1201.0
17.5°	1178.2	1182.8	1194.3	1202.1	1212.0	1232.8	1243.1	1247.2	1244.1	1231.6	1218.2
20°	1072.8	1065.1	1097.5	1114.0	1128.1	1163.3	1193.5	1205.1	1223.8	1223.5	1219.9
22.5°	923.6	925.4	956.1	975.7	1016.9	1052.1	1086.6	1130.3	1166.4	1190.2	1204.2
25°	678.6	692.0	722.6	749.3	795.1	860.6	920.1	989.1	1054.1	1105.6	1154.5
27.5°	509.6	510.7	534.9	559.7	586.8	640.5	715.4	797.8	890.6	967.1	1055.3
30°	436.5	434.3	444.6	459.7	483.0	524.4	580.8	661.8	754.3	869.8	972.5
32.5°	384.7	384.7	392.5	403.7	422.9	450.9	489.6	555.3	642.8	756.3	876.8
35°	334.4	334.0	339.7	347.8	355.8	373.8	400.2	434.7	494.9	600.9	724.1
37.5°	298.3	299.9	302.7	307.7	316.6	326.6	342.5	365.6	408.5	471.2	574.7
40°	278.1	278.8	282.7	286.9	292.2	299.9	312.9	331.6	362.9	412.8	488.5
42.5°	259.5	260.1	263.0	266.8	271.0	278.8	289.5	305.7	331.1	370.0	432.5
45°	232.3	232.3	234.8	236.5	241.1	248.2	256.9	270.3	287.9	316.8	358.4
47.5°	206.8	206.9	208.5	211.5	214.4	219.9	228.6	239.5	252.3	274.7	310.1
50°	192.2	192.6	193.6	196.0	197.8	202.7	209.4	219.0	232.3	249.6	279.1
52.5°	180.3	180.1	181.4	182.6	183.7	187.3	192.3	200.7	212.6	227.6	252.1
55°	161.2	159.8	161.9	163.6	164.8	166.2	168.9	174.3	184.5	197.1	215.4
57.5°	137.2	136.7	138.2	139.8	143.1	146.9	149.3	152.7	158.0	167.0	185.2
60°	117.5	117.5	120.7	121.8	125.6	130.5	135.5	138.4	143.6	149.6	163.0
62.5°	100.1	100.4	101.9	102.9	105.1	111.1	118.1	124.2	129.2	135.0	143.8
65°	83.8	84.5	84.5	85.2	86.6	88.0	90.8	95.8	104.5	112.6	119.3
67.5°	71.1	71.4	71.5	72.2	72.6	74.1	75.2	77.5	79.5	87.2	95.5
70°	62.7	63.7	63.3	64.1	64.4	65.1	66.5	67.6	70.8	72.5	77.5
72.5°	54.8	55.5	55.5	55.9	56.8	56.9	58.1	59.1	61.2	62.7	65.3
75°	44.4	44.0	44.4	45.1	45.4	45.7	45.7	47.1	48.3	49.7	51.4
77.5°	34.2	34.6	34.5	34.6	34.6	35.3	35.2	35.8	36.9	37.6	38.5
80°	27.4	27.8	27.4	27.8	28.2	28.5	28.2	28.5	29.6	30.3	30.3
82.5°	21.3	21.3	21.6	21.6	21.7	21.8	22.2	22.3	23.1	22.9	23.2
85°	12.6	12.3	12.3	12.3	12.6	13.0	12.6	12.6	13.0	13.0	13.0
87.5°	9.3	9.6	9.6	9.6	9.6	9.5	9.2	9.8	9.6	10.1	9.6
90°	24.3	24.3	24.3	24.3	24.3	23.6	22.1	23.6	24.3	25.1	24.3
92.5°	40.8	42.0	41.4	43.7	44.4	48.9	55.1	64.3	80.9	95.8	94.4
95°	84.0	83.2	85.5	91.3	100.9	117.2	148.1	193.0	252.7	288.8	255.7
97.5°	165.3	171.5	182.3	200.4	235.6	288.8	368.5	450.4	517.3	493.0	371.4
100°	263.7	277.0	298.4	330.1	391.2	480.4	581.4	672.7	688.2	582.0	400.8
102.5°	464.2	482.1	508.8	562.9	629.3	723.8	797.7	818.3	751.8	585.0	389.6
105°	830.4	840.7	872.3	918.0	963.7	988.1	978.5	895.2	742.0	545.9	367.7
107.5°	1060.6	1074.4	1080.7	1083.3	1077.5	1041.8	965.2	839.8	677.2	504.1	356.8
110°	1130.2	1131.0	1124.4	1110.3	1078.6	1018.2	924.0	792.0	636.6	484.1	354.4



TEST NUMBER: P331659-830

CATALOG NUMBER: SA2XXRDIP-C485D725U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1129.1	1125.1	1112.6	1089.1	1045.1	975.8	875.0	748.5	608.3	471.1	355.0
115°	1092.7	1086.0	1066.9	1032.9	980.6	904.7	808.2	694.7	573.3	456.9	358.1
117.5°	1027.7	1022.1	1001.9	966.1	912.8	841.6	754.0	654.4	551.1	449.9	363.4
120°	985.8	978.5	957.1	922.5	870.9	803.8	725.8	634.3	539.3	445.7	366.9
122.5°	942.2	936.0	917.0	883.0	836.7	776.1	702.2	618.5	529.3	443.4	371.1
125°	886.4	880.4	862.0	834.1	791.3	736.0	671.2	595.3	515.0	439.1	377.2
127.5°	837.4	832.7	816.8	790.6	753.3	702.3	641.1	572.5	501.7	436.6	383.6
130°	809.7	803.8	789.1	764.0	727.9	679.3	621.1	557.7	492.9	435.5	388.3
132.5°	780.8	775.5	762.0	737.0	701.4	655.7	602.3	543.6	485.9	434.9	393.0
135°	734.6	731.6	718.4	694.1	662.3	621.1	572.5	523.9	476.0	433.9	398.6
137.5°	689.2	684.8	673.2	652.2	623.3	587.4	548.7	508.1	469.0	433.9	403.6
140°	658.0	653.6	642.4	623.3	599.7	567.3	533.5	498.0	465.0	433.2	406.0
142.5°	626.7	625.8	616.0	598.6	576.2	549.0	519.9	489.8	460.8	433.2	407.7
145°	586.4	584.3	576.9	564.4	546.7	525.4	502.5	478.2	455.3	431.8	409.6
147.5°	552.7	551.4	546.4	536.4	521.8	506.1	488.3	469.2	449.8	429.1	410.3
150°	532.7	532.0	527.5	518.7	507.7	494.4	478.9	462.7	445.0	427.3	409.6
152.5°	515.6	515.5	512.2	504.5	495.9	484.4	471.3	456.2	440.9	424.4	408.5
155°	492.9	494.4	491.4	486.3	478.2	470.0	459.0	447.2	433.2	419.2	406.7
157.5°	473.6	473.6	472.3	468.0	462.2	455.9	446.7	436.8	426.0	414.0	403.3
160°	461.2	461.2	460.5	456.9	451.7	446.5	438.4	430.3	420.8	410.4	401.5
162.5°	449.4	450.1	449.3	446.8	441.7	437.6	430.7	423.8	415.9	407.5	399.8
165°	432.5	433.2	433.2	430.3	427.3	424.4	419.2	414.1	408.2	401.5	396.4
167.5°	416.9	417.7	417.9	416.3	415.0	412.3	408.8	404.8	400.5	396.4	393.0
170°	407.5	408.9	409.6	407.5	406.7	405.2	402.3	400.1	396.4	393.4	391.2
172.5°	399.8	400.7	401.4	400.4	399.6	398.8	396.4	394.7	392.3	389.9	388.9
175°	389.7	391.2	392.0	391.2	391.2	390.5	389.7	389.0	386.8	386.1	385.3
177.5°	383.7	384.9	385.5	385.5	385.5	385.5	384.9	384.9	383.7	383.1	383.7
180°	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1



TEST NUMBER: P331659-830  
 CATALOG NUMBER: SA2XXRDIP-C485D725U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0
2.5°	1037.2	1035.0	1033.0	1027.9	1025.4	1019.7	1018.9	1018.6	1011.3	1004.3	1002.3
5°	1072.8	1067.2	1058.8	1048.9	1038.7	1028.1	1021.1	1015.5	1001.4	988.0	980.2
7.5°	1108.7	1096.6	1082.0	1063.4	1047.8	1030.4	1017.5	1005.8	985.8	966.7	953.8
10°	1135.5	1115.8	1096.5	1070.7	1050.7	1031.0	1012.7	996.8	974.3	949.0	930.9
12.5°	1152.1	1130.4	1103.7	1078.6	1052.6	1027.6	1003.1	982.7	956.3	930.1	908.7
15°	1174.6	1151.3	1119.0	1083.1	1049.6	1016.9	988.7	963.4	928.9	897.6	871.5
17.5°	1193.0	1160.9	1126.1	1084.7	1045.9	1004.4	968.1	935.7	897.3	859.5	828.9
20°	1198.8	1167.2	1127.0	1085.5	1039.7	990.8	951.8	916.5	875.3	834.2	799.0
22.5°	1195.1	1170.5	1125.9	1076.2	1029.4	978.2	934.1	893.2	847.5	805.5	764.7
25°	1170.4	1161.9	1119.6	1065.5	1011.9	952.4	901.4	856.7	804.6	759.6	715.2
27.5°	1112.4	1130.7	1104.5	1046.7	987.2	923.4	866.1	815.2	761.1	710.4	666.2
30°	1056.7	1098.5	1087.2	1033.8	967.2	904.6	840.2	787.0	729.3	677.2	633.6
32.5°	980.3	1049.5	1060.5	1015.8	947.0	878.1	810.6	757.7	697.5	642.5	600.0
35°	858.8	962.3	1009.8	981.3	912.3	838.1	768.4	706.8	646.2	592.0	549.8
37.5°	713.9	854.8	934.1	936.0	872.7	795.5	719.6	658.5	596.4	543.3	497.6
40°	619.8	772.6	875.7	898.6	845.1	761.7	684.9	622.6	562.1	510.0	457.6
42.5°	535.4	687.6	814.4	854.1	811.6	728.8	651.8	586.6	527.7	478.4	424.9
45°	432.9	566.0	705.7	776.8	753.3	676.5	595.2	533.3	478.0	435.4	384.0
47.5°	365.2	459.0	594.2	690.4	689.9	619.9	540.0	480.6	429.3	389.5	347.8
50°	326.6	408.3	522.7	631.8	640.9	582.2	506.1	447.3	399.5	357.6	324.1
52.5°	292.0	359.3	462.1	566.8	592.8	541.9	468.2	413.9	367.4	328.9	300.2
55°	246.8	298.8	377.0	474.9	514.3	478.3	412.8	362.2	324.5	292.2	267.5
57.5°	208.7	247.8	310.5	389.3	435.2	412.6	358.6	317.4	285.2	255.9	236.5
60°	184.8	216.8	269.9	335.8	386.4	370.6	324.5	286.2	258.7	233.4	215.1
62.5°	162.3	189.8	235.4	288.8	335.3	328.7	291.1	258.8	234.8	211.7	196.2
65°	130.5	150.6	186.2	228.1	265.4	268.5	241.5	219.6	198.1	179.8	166.2
67.5°	104.0	117.1	142.1	177.4	205.4	215.4	198.8	182.1	165.0	150.9	139.0
70°	87.7	98.2	116.5	145.1	170.7	181.3	171.7	158.7	143.9	132.3	122.2
72.5°	71.1	81.3	94.8	115.7	137.8	149.2	145.9	136.5	124.5	114.9	105.3
75°	53.5	56.6	65.8	79.9	97.2	107.0	109.4	104.5	95.0	87.7	82.0
77.5°	39.6	41.5	45.8	53.3	64.5	73.2	76.9	76.3	69.7	65.5	60.2
80°	31.7	32.7	34.9	38.0	46.5	55.2	57.7	57.7	53.2	51.4	46.1
82.5°	24.0	24.9	26.1	27.9	31.9	39.5	42.2	42.8	39.9	37.6	33.5
85°	13.8	13.4	14.0	15.2	15.8	17.9	22.1	22.9	22.1	19.3	18.3
87.5°	8.8	8.0	7.3	6.6	6.5	6.5	7.4	8.3	7.6	7.4	7.1
90°	19.9	14.7	11.0	8.9	7.4	5.9	2.9	0.8	2.9	5.9	7.4
92.5°	73.5	50.1	33.5	26.5	21.5	18.3	13.0	9.0	13.0	18.3	21.5
95°	170.2	106.1	72.2	54.5	42.7	36.1	28.7	25.8	28.7	36.1	42.7
97.5°	229.3	140.0	97.4	77.4	63.8	53.8	46.0	42.0	46.0	53.8	63.8
100°	241.7	151.7	112.7	92.1	77.4	65.6	58.9	56.7	58.9	65.6	77.4
102.5°	242.2	162.4	126.3	105.7	90.3	78.5	71.9	70.3	71.9	78.5	90.3
105°	246.1	180.5	145.9	125.3	109.1	98.0	92.8	89.9	92.8	98.0	109.1
107.5°	256.3	199.1	165.5	144.7	128.7	118.5	113.5	111.1	113.5	118.5	128.7
110°	264.5	211.4	179.1	157.7	142.2	132.6	128.2	125.3	128.2	132.6	142.2





TEST NUMBER: P331659-830

CATALOG NUMBER: SA2XXRDIP-C485D725U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	273.3	223.3	192.0	170.0	155.1	146.2	141.2	138.2	141.2	146.2	155.1
115°	286.6	241.7	210.0	190.1	175.3	166.5	162.1	158.4	162.1	166.5	175.3
117.5°	300.8	258.6	229.3	208.7	194.5	186.7	182.3	179.4	182.3	186.7	194.5
120°	310.2	270.4	241.7	221.0	206.3	199.6	195.3	192.3	195.3	199.6	206.3
122.5°	318.5	281.6	254.7	233.4	218.7	211.4	207.1	204.7	207.1	211.4	218.7
125°	331.6	298.4	271.8	251.3	236.5	227.6	223.3	221.0	223.3	227.6	236.5
127.5°	343.7	314.1	288.2	267.0	252.9	243.2	237.0	234.0	237.0	243.2	252.9
130°	351.5	323.5	297.7	277.0	262.3	251.9	244.6	241.7	244.6	251.9	262.3
132.5°	359.1	331.7	307.1	286.4	271.2	260.2	252.3	248.7	252.3	260.2	271.2
135°	369.1	343.4	319.8	299.2	282.2	271.2	262.3	259.4	262.3	271.2	282.2
137.5°	376.8	352.8	329.5	310.4	293.5	281.7	272.9	269.4	272.9	281.7	293.5
140°	380.9	358.1	336.0	316.8	300.6	288.8	279.9	277.0	279.9	288.8	300.6
142.5°	384.5	362.2	340.7	322.7	307.1	295.3	287.1	284.6	287.1	295.3	307.1
145°	389.0	368.4	348.5	332.2	317.5	306.5	299.2	296.1	299.2	306.5	317.5
147.5°	391.5	373.4	354.7	340.3	328.0	317.8	310.8	308.6	310.8	317.8	328.0
150°	392.7	375.8	358.8	345.5	334.5	324.9	319.1	316.8	319.1	324.9	334.5
152.5°	393.3	378.1	363.0	350.8	340.4	332.0	326.1	325.1	326.1	332.0	340.4
155°	394.2	381.6	369.1	358.1	350.0	341.9	337.4	336.7	337.4	341.9	350.0
157.5°	394.2	384.2	373.5	364.3	357.8	350.7	347.1	346.5	347.1	350.7	357.8
160°	394.2	385.3	376.5	368.4	362.5	356.6	353.6	352.9	353.6	356.6	362.5
162.5°	393.6	386.0	378.2	371.9	366.6	361.9	358.9	359.4	358.9	361.9	366.6
165°	392.0	386.8	380.2	375.8	372.1	367.7	366.2	366.9	366.2	367.7	372.1
167.5°	391.0	386.6	381.8	379.0	376.4	373.5	372.2	373.2	372.2	373.5	376.4
170°	389.7	386.1	382.4	380.2	378.7	376.5	375.8	377.2	375.8	376.5	378.7
172.5°	388.0	385.5	383.0	381.4	380.5	378.2	378.7	379.6	378.7	378.2	380.5
175°	386.1	384.6	383.1	382.4	382.4	380.9	381.6	382.4	381.6	380.9	382.4
177.5°	384.9	383.7	383.1	383.1	383.1	381.9	382.6	383.7	382.6	381.9	383.1
180°	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1



TEST NUMBER: P331659-830

CATALOG NUMBER: SA2XXRDIP-C485D725U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0
2.5°	998.6	996.6	993.0	987.4	984.0	978.1	974.1	976.4	976.9	976.4	975.8
5°	971.9	964.4	954.2	944.3	935.2	925.4	919.7	917.3	912.3	909.6	908.1
7.5°	939.3	926.6	912.2	895.0	880.4	865.2	857.3	853.5	843.4	837.9	833.1
10°	915.1	895.0	880.6	858.1	844.4	824.3	810.6	811.0	797.2	789.5	783.8
12.5°	888.4	866.4	842.4	822.1	803.0	786.9	770.3	763.6	749.0	741.6	726.4
15°	844.0	818.3	793.1	765.5	746.2	721.2	697.3	668.1	644.5	624.1	618.4
17.5°	795.6	763.8	738.4	706.2	673.0	630.9	603.2	586.3	572.0	561.3	553.3
20°	762.4	730.0	702.9	654.3	609.6	581.1	560.7	547.7	532.9	521.3	514.9
22.5°	727.5	693.7	656.8	602.5	567.7	544.8	526.6	511.6	501.6	492.6	486.8
25°	677.9	640.9	580.0	542.7	514.6	490.7	478.0	468.8	458.3	445.9	440.4
27.5°	625.6	566.8	523.0	495.3	468.4	452.9	441.5	427.8	418.4	412.8	407.0
30°	586.4	527.6	493.5	463.2	444.2	427.0	413.6	405.9	396.7	387.2	383.3
32.5°	542.7	495.8	463.1	437.9	418.6	403.9	393.3	380.8	374.2	368.3	360.2
35°	488.5	453.0	423.1	402.7	384.4	372.4	360.1	352.7	340.7	335.8	332.6
37.5°	442.6	411.8	389.5	368.0	353.5	340.3	332.7	320.9	315.8	308.9	302.2
40°	416.7	386.4	365.0	347.4	331.2	321.3	311.9	302.4	294.6	291.4	283.3
42.5°	390.3	365.6	344.1	324.9	314.1	303.6	291.6	284.6	276.5	271.5	266.5
45°	353.7	332.0	313.6	297.7	285.8	274.9	267.1	255.5	251.0	240.7	236.5
47.5°	321.6	301.3	283.9	268.8	257.1	250.1	238.7	229.6	222.3	216.0	210.7
50°	298.8	281.9	265.0	251.7	241.1	230.9	219.3	214.7	203.4	200.3	197.1
52.5°	278.0	261.9	246.5	233.4	222.8	212.9	202.6	196.7	189.1	185.9	183.6
55°	248.8	233.4	218.6	207.0	196.4	186.2	179.8	172.5	168.9	166.5	163.6
57.5°	219.5	205.7	194.3	182.6	171.9	163.8	156.5	152.0	148.4	145.2	141.8
60°	201.0	187.6	177.4	166.5	155.6	148.9	143.3	138.0	133.7	128.8	127.4
62.5°	181.3	169.6	160.2	149.6	140.1	133.9	128.7	123.7	118.6	111.4	109.4
65°	154.2	145.1	135.2	126.4	117.9	112.0	104.2	98.6	96.4	95.8	95.4
67.5°	129.7	121.0	112.5	103.6	95.9	90.3	86.3	85.5	84.1	83.6	82.7
70°	113.3	105.3	96.8	88.3	81.0	79.9	78.5	77.1	75.3	74.6	73.9
72.5°	98.7	90.3	81.9	75.1	71.9	70.6	69.2	67.8	66.6	65.9	65.5
75°	75.7	68.0	62.3	59.9	58.1	57.0	55.0	53.8	53.2	52.1	51.7
77.5°	54.5	50.1	47.5	46.0	44.1	43.0	41.8	40.7	40.0	39.8	39.2
80°	41.6	39.4	37.7	35.5	34.9	33.5	33.1	32.0	32.4	31.3	31.3
82.5°	32.2	29.6	28.1	27.1	26.4	25.3	24.9	24.4	24.5	23.8	23.8
85°	16.6	15.8	15.2	14.4	14.4	13.4	13.8	13.4	13.4	12.6	12.3
87.5°	7.2	7.3	7.4	8.5	9.3	9.2	9.0	8.7	8.4	8.7	8.5
90°	8.9	11.0	14.7	19.9	24.3	25.1	24.3	23.6	22.1	23.6	24.3
92.5°	26.5	33.5	50.1	73.5	94.4	95.8	80.9	64.3	55.1	48.9	44.4
95°	54.5	72.2	106.1	170.2	255.7	288.8	252.7	193.0	148.1	117.2	100.9
97.5°	77.4	97.4	140.0	229.3	371.4	493.0	517.3	450.4	368.5	288.8	235.6
100°	92.1	112.7	151.7	241.7	400.8	582.0	688.2	672.7	581.4	480.4	391.2
102.5°	105.7	126.3	162.4	242.2	389.6	585.0	751.8	818.3	797.7	723.8	629.3
105°	125.3	145.9	180.5	246.1	367.7	545.9	742.0	895.2	978.5	988.1	963.7
107.5°	144.7	165.5	199.1	256.3	356.8	504.1	677.2	839.8	965.2	1041.8	1077.5
110°	157.7	179.1	211.4	264.5	354.4	484.1	636.6	792.0	924.0	1018.2	1078.6



TEST NUMBER: P331659-830  
 CATALOG NUMBER: SA2XXRDIP-C485D725U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	170.0	192.0	223.3	273.3	355.0	471.1	608.3	748.5	875.0	975.8	1045.1
115°	190.1	210.0	241.7	286.6	358.1	456.9	573.3	694.7	808.2	904.7	980.6
117.5°	208.7	229.3	258.6	300.8	363.4	449.9	551.1	654.4	754.0	841.6	912.8
120°	221.0	241.7	270.4	310.2	366.9	445.7	539.3	634.3	725.8	803.8	870.9
122.5°	233.4	254.7	281.6	318.5	371.1	443.4	529.3	618.5	702.2	776.1	836.7
125°	251.3	271.8	298.4	331.6	377.2	439.1	515.0	595.3	671.2	736.0	791.3
127.5°	267.0	288.2	314.1	343.7	383.6	436.6	501.7	572.5	641.1	702.3	753.3
130°	277.0	297.7	323.5	351.5	388.3	435.5	492.9	557.7	621.1	679.3	727.9
132.5°	286.4	307.1	331.7	359.1	393.0	434.9	485.9	543.6	602.3	655.7	701.4
135°	299.2	319.8	343.4	369.1	398.6	433.9	476.0	523.9	572.5	621.1	662.3
137.5°	310.4	329.5	352.8	376.8	403.6	433.9	469.0	508.1	548.7	587.4	623.3
140°	316.8	336.0	358.1	380.9	406.0	433.2	465.0	498.0	533.5	567.3	599.7
142.5°	322.7	340.7	362.2	384.5	407.7	433.2	460.8	489.8	519.9	549.0	576.2
145°	332.2	348.5	368.4	389.0	409.6	431.8	455.3	478.2	502.5	525.4	546.7
147.5°	340.3	354.7	373.4	391.5	410.3	429.1	449.8	469.2	488.3	506.1	521.8
150°	345.5	358.8	375.8	392.7	409.6	427.3	445.0	462.7	478.9	494.4	507.7
152.5°	350.8	363.0	378.1	393.3	408.5	424.4	440.9	456.2	471.3	484.4	495.9
155°	358.1	369.1	381.6	394.2	406.7	419.2	433.2	447.2	459.0	470.0	478.2
157.5°	364.3	373.5	384.2	394.2	403.3	414.0	426.0	436.8	446.7	455.9	462.2
160°	368.4	376.5	385.3	394.2	401.5	410.4	420.8	430.3	438.4	446.5	451.7
162.5°	371.9	378.2	386.0	393.6	399.8	407.5	415.9	423.8	430.7	437.6	441.7
165°	375.8	380.2	386.8	392.0	396.4	401.5	408.2	414.1	419.2	424.4	427.3
167.5°	379.0	381.8	386.6	391.0	393.0	396.4	400.5	404.8	408.8	412.3	415.0
170°	380.2	382.4	386.1	389.7	391.2	393.4	396.4	400.1	402.3	405.2	406.7
172.5°	381.4	383.0	385.5	388.0	388.9	389.9	392.3	394.7	396.4	398.8	399.6
175°	382.4	383.1	384.6	386.1	385.3	386.1	386.8	389.0	389.7	390.5	391.2
177.5°	383.1	383.1	383.7	384.9	383.7	383.1	383.7	384.9	384.9	385.5	385.5
180°	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1



TEST NUMBER: P331659-830  
 CATALOG NUMBER: SA2XXRDIP-C485D725U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0
2.5°	972.7	973.3	972.4	973.0	972.4	973.3	972.7	975.8	976.4	976.9	976.4
5°	906.3	902.1	901.4	900.4	901.4	902.1	906.3	908.1	909.6	912.3	917.3
7.5°	827.1	826.4	824.7	822.2	824.7	826.4	827.1	833.1	837.9	843.4	853.5
10°	776.1	774.4	774.0	771.6	774.0	774.4	776.1	783.8	789.5	797.2	811.0
12.5°	716.4	705.1	703.9	697.8	703.9	705.1	716.4	726.4	741.6	749.0	763.6
15°	610.0	607.8	600.9	596.3	600.9	607.8	610.0	618.4	624.1	644.5	668.1
17.5°	549.1	542.2	540.1	539.1	540.1	542.2	549.1	553.3	561.3	572.0	586.3
20°	510.0	503.7	502.7	501.9	502.7	503.7	510.0	514.9	521.3	532.9	547.7
22.5°	483.0	476.4	473.6	471.6	473.6	476.4	483.0	486.8	492.6	501.6	511.6
25°	436.8	434.3	432.9	432.3	432.9	434.3	436.8	440.4	445.9	458.3	468.8
27.5°	400.7	395.3	394.2	392.4	394.2	395.3	400.7	407.0	412.8	418.4	427.8
30°	380.1	378.3	375.9	373.8	375.9	378.3	380.1	383.3	387.2	396.7	405.9
32.5°	355.9	354.5	352.2	351.3	352.2	354.5	355.9	360.2	368.3	374.2	380.8
35°	329.1	324.1	322.1	318.9	322.1	324.1	329.1	332.6	335.8	340.7	352.7
37.5°	300.8	298.1	295.2	296.2	295.2	298.1	300.8	302.2	308.9	315.8	320.9
40°	278.8	277.0	276.3	276.0	276.3	277.0	278.8	283.3	291.4	294.6	302.4
42.5°	261.3	256.5	254.6	254.6	254.6	256.5	261.3	266.5	271.5	276.5	284.6
45°	234.8	230.2	227.1	227.3	227.1	230.2	234.8	236.5	240.7	251.0	255.5
47.5°	207.6	207.5	205.5	206.1	205.5	207.5	207.6	210.7	216.0	222.3	229.6
50°	194.6	192.6	191.1	191.4	191.1	192.6	194.6	197.1	200.3	203.4	214.7
52.5°	182.3	180.4	179.3	180.8	179.3	180.4	182.3	183.6	185.9	189.1	196.7
55°	161.9	159.8	159.5	159.1	159.5	159.8	161.9	163.6	166.5	168.9	172.5
57.5°	139.2	137.8	135.6	134.8	135.6	137.8	139.2	141.8	145.2	148.4	152.0
60°	122.8	120.0	116.5	116.1	116.5	120.0	122.8	127.4	128.8	133.7	138.0
62.5°	107.9	107.4	106.7	106.6	106.7	107.4	107.9	109.4	111.4	118.6	123.7
65°	94.7	94.3	94.7	95.0	94.7	94.3	94.7	95.4	95.8	96.4	98.6
67.5°	82.5	81.9	81.2	81.5	81.2	81.9	82.5	82.7	83.6	84.1	85.5
70°	73.2	72.9	72.5	72.5	72.5	72.9	73.2	73.9	74.6	75.3	77.1
72.5°	64.2	64.1	63.8	63.5	63.8	64.1	64.2	65.5	65.9	66.6	67.8
75°	51.4	50.7	50.7	50.7	50.7	50.7	51.4	51.7	52.1	53.2	53.8
77.5°	39.1	38.8	38.5	38.2	38.5	38.8	39.1	39.2	39.8	40.0	40.7
80°	31.0	30.6	30.3	30.3	30.3	30.6	31.0	31.3	31.3	32.4	32.0
82.5°	23.7	23.3	23.2	22.9	23.2	23.3	23.7	23.8	23.8	24.5	24.4
85°	12.6	13.0	12.6	13.4	12.6	13.0	12.6	12.3	12.6	13.4	13.4
87.5°	8.5	8.2	8.5	8.2	8.5	8.2	8.5	8.5	8.7	8.4	8.7
90°	24.3	24.3	24.3	24.3	24.3	24.3	24.3	24.3	23.6	22.1	23.6
92.5°	43.7	41.4	42.0	40.8	42.0	41.4	43.7	44.4	48.9	55.1	64.3
95°	91.3	85.5	83.2	84.0	83.2	85.5	91.3	100.9	117.2	148.1	193.0
97.5°	200.4	182.3	171.5	165.3	171.5	182.3	200.4	235.6	288.8	368.5	450.4
100°	330.1	298.4	277.0	263.7	277.0	298.4	330.1	391.2	480.4	581.4	672.7
102.5°	562.9	508.8	482.1	464.2	482.1	508.8	562.9	629.3	723.8	797.7	818.3
105°	918.0	872.3	840.7	830.4	840.7	872.3	918.0	963.7	988.1	978.5	895.2
107.5°	1083.3	1080.7	1074.4	1060.6	1074.4	1080.7	1083.3	1077.5	1041.8	965.2	839.8
110°	1110.3	1124.4	1131.0	1130.2	1131.0	1124.4	1110.3	1078.6	1018.2	924.0	792.0



TEST NUMBER: P331659-830

CATALOG NUMBER: SA2XXRDIP-C485D725U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1089.1	1112.6	1125.1	1129.1	1125.1	1112.6	1089.1	1045.1	975.8	875.0	748.5
115°	1032.9	1066.9	1086.0	1092.7	1086.0	1066.9	1032.9	980.6	904.7	808.2	694.7
117.5°	966.1	1001.9	1022.1	1027.7	1022.1	1001.9	966.1	912.8	841.6	754.0	654.4
120°	922.5	957.1	978.5	985.8	978.5	957.1	922.5	870.9	803.8	725.8	634.3
122.5°	883.0	917.0	936.0	942.2	936.0	917.0	883.0	836.7	776.1	702.2	618.5
125°	834.1	862.0	880.4	886.4	880.4	862.0	834.1	791.3	736.0	671.2	595.3
127.5°	790.6	816.8	832.7	837.4	832.7	816.8	790.6	753.3	702.3	641.1	572.5
130°	764.0	789.1	803.8	809.7	803.8	789.1	764.0	727.9	679.3	621.1	557.7
132.5°	737.0	762.0	775.5	780.8	775.5	762.0	737.0	701.4	655.7	602.3	543.6
135°	694.1	718.4	731.6	734.6	731.6	718.4	694.1	662.3	621.1	572.5	523.9
137.5°	652.2	673.2	684.8	689.2	684.8	673.2	652.2	623.3	587.4	548.7	508.1
140°	623.3	642.4	653.6	658.0	653.6	642.4	623.3	599.7	567.3	533.5	498.0
142.5°	598.6	616.0	625.8	626.7	625.8	616.0	598.6	576.2	549.0	519.9	489.8
145°	564.4	576.9	584.3	586.4	584.3	576.9	564.4	546.7	525.4	502.5	478.2
147.5°	536.4	546.4	551.4	552.7	551.4	546.4	536.4	521.8	506.1	488.3	469.2
150°	518.7	527.5	532.0	532.7	532.0	527.5	518.7	507.7	494.4	478.9	462.7
152.5°	504.5	512.2	515.5	515.6	515.5	512.2	504.5	495.9	484.4	471.3	456.2
155°	486.3	491.4	494.4	492.9	494.4	491.4	486.3	478.2	470.0	459.0	447.2
157.5°	468.0	472.3	473.6	473.6	473.6	472.3	468.0	462.2	455.9	446.7	436.8
160°	456.9	460.5	461.2	461.2	461.2	460.5	456.9	451.7	446.5	438.4	430.3
162.5°	446.8	449.3	450.1	449.4	450.1	449.3	446.8	441.7	437.6	430.7	423.8
165°	430.3	433.2	433.2	432.5	433.2	433.2	430.3	427.3	424.4	419.2	414.1
167.5°	416.3	417.9	417.7	416.9	417.7	417.9	416.3	415.0	412.3	408.8	404.8
170°	407.5	409.6	408.9	407.5	408.9	409.6	407.5	406.7	405.2	402.3	400.1
172.5°	400.4	401.4	400.7	399.8	400.7	401.4	400.4	399.6	398.8	396.4	394.7
175°	391.2	392.0	391.2	389.7	391.2	392.0	391.2	391.2	390.5	389.7	389.0
177.5°	385.5	385.5	384.9	383.7	384.9	385.5	385.5	385.5	385.5	384.9	384.9
180°	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1



TEST NUMBER: P331659-830  
 CATALOG NUMBER: SA2XXRDIP-C485D725U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0
2.5°	974.1	978.1	984.0	987.4	993.0	996.6	998.6	1002.3	1004.3	1011.3	1018.6
5°	919.7	925.4	935.2	944.3	954.2	964.4	971.9	980.2	988.0	1001.4	1015.5
7.5°	857.3	865.2	880.4	895.0	912.2	926.6	939.3	953.8	966.7	985.8	1005.8
10°	810.6	824.3	844.4	858.1	880.6	895.0	915.1	930.9	949.0	974.3	996.8
12.5°	770.3	786.9	803.0	822.1	842.4	866.4	888.4	908.7	930.1	956.3	982.7
15°	697.3	721.2	746.2	765.5	793.1	818.3	844.0	871.5	897.6	928.9	963.4
17.5°	603.2	630.9	673.0	706.2	738.4	763.8	795.6	828.9	859.5	897.3	935.7
20°	560.7	581.1	609.6	654.3	702.9	730.0	762.4	799.0	834.2	875.3	916.5
22.5°	526.6	544.8	567.7	602.5	656.8	693.7	727.5	764.7	805.5	847.5	893.2
25°	478.0	490.7	514.6	542.7	580.0	640.9	677.9	715.2	759.6	804.6	856.7
27.5°	441.5	452.9	468.4	495.3	523.0	566.8	625.6	666.2	710.4	761.1	815.2
30°	413.6	427.0	444.2	463.2	493.5	527.6	586.4	633.6	677.2	729.3	787.0
32.5°	393.3	403.9	418.6	437.9	463.1	495.8	542.7	600.0	642.5	697.5	757.7
35°	360.1	372.4	384.4	402.7	423.1	453.0	488.5	549.8	592.0	646.2	706.8
37.5°	332.7	340.3	353.5	368.0	389.5	411.8	442.6	497.6	543.3	596.4	658.5
40°	311.9	321.3	331.2	347.4	365.0	386.4	416.7	457.6	510.0	562.1	622.6
42.5°	291.6	303.6	314.1	324.9	344.1	365.6	390.3	424.9	478.4	527.7	586.6
45°	267.1	274.9	285.8	297.7	313.6	332.0	353.7	384.0	435.4	478.0	533.3
47.5°	238.7	250.1	257.1	268.8	283.9	301.3	321.6	347.8	389.5	429.3	480.6
50°	219.3	230.9	241.1	251.7	265.0	281.9	298.8	324.1	357.6	399.5	447.3
52.5°	202.6	212.9	222.8	233.4	246.5	261.9	278.0	300.2	328.9	367.4	413.9
55°	179.8	186.2	196.4	207.0	218.6	233.4	248.8	267.5	292.2	324.5	362.2
57.5°	156.5	163.8	171.9	182.6	194.3	205.7	219.5	236.5	255.9	285.2	317.4
60°	143.3	148.9	155.6	166.5	177.4	187.6	201.0	215.1	233.4	258.7	286.2
62.5°	128.7	133.9	140.1	149.6	160.2	169.6	181.3	196.2	211.7	234.8	258.8
65°	104.2	112.0	117.9	126.4	135.2	145.1	154.2	166.2	179.8	198.1	219.6
67.5°	86.3	90.3	95.9	103.6	112.5	121.0	129.7	139.0	150.9	165.0	182.1
70°	78.5	79.9	81.0	88.3	96.8	105.3	113.3	122.2	132.3	143.9	158.7
72.5°	69.2	70.6	71.9	75.1	81.9	90.3	98.7	105.3	114.9	124.5	136.5
75°	55.0	57.0	58.1	59.9	62.3	68.0	75.7	82.0	87.7	95.0	104.5
77.5°	41.8	43.0	44.1	46.0	47.5	50.1	54.5	60.2	65.5	69.7	76.3
80°	33.1	33.5	34.9	35.5	37.7	39.4	41.6	46.1	51.4	53.2	57.7
82.5°	24.9	25.3	26.4	27.1	28.1	29.6	32.2	33.5	37.6	39.9	42.8
85°	13.8	13.4	14.4	14.4	15.2	15.8	16.6	18.3	19.3	22.1	22.9
87.5°	9.0	9.2	9.3	8.5	7.4	7.3	7.2	7.1	7.4	7.6	8.3
90°	24.3	25.1	24.3	19.9	14.7	11.0	8.9	7.4	5.9	2.9	0.8
92.5°	80.9	95.8	94.4	73.5	50.1	33.5	26.5	21.5	18.3	13.0	9.0
95°	252.7	288.8	255.7	170.2	106.1	72.2	54.5	42.7	36.1	28.7	25.8
97.5°	517.3	493.0	371.4	229.3	140.0	97.4	77.4	63.8	53.8	46.0	42.0
100°	688.2	582.0	400.8	241.7	151.7	112.7	92.1	77.4	65.6	58.9	56.7
102.5°	751.8	585.0	389.6	242.2	162.4	126.3	105.7	90.3	78.5	71.9	70.3
105°	742.0	545.9	367.7	246.1	180.5	145.9	125.3	109.1	98.0	92.8	89.9
107.5°	677.2	504.1	356.8	256.3	199.1	165.5	144.7	128.7	118.5	113.5	111.1
110°	636.6	484.1	354.4	264.5	211.4	179.1	157.7	142.2	132.6	128.2	125.3



TEST NUMBER: P331659-830

CATALOG NUMBER: SA2XXRDIP-C485D725U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	608.3	471.1	355.0	273.3	223.3	192.0	170.0	155.1	146.2	141.2	138.2
115°	573.3	456.9	358.1	286.6	241.7	210.0	190.1	175.3	166.5	162.1	158.4
117.5°	551.1	449.9	363.4	300.8	258.6	229.3	208.7	194.5	186.7	182.3	179.4
120°	539.3	445.7	366.9	310.2	270.4	241.7	221.0	206.3	199.6	195.3	192.3
122.5°	529.3	443.4	371.1	318.5	281.6	254.7	233.4	218.7	211.4	207.1	204.7
125°	515.0	439.1	377.2	331.6	298.4	271.8	251.3	236.5	227.6	223.3	221.0
127.5°	501.7	436.6	383.6	343.7	314.1	288.2	267.0	252.9	243.2	237.0	234.0
130°	492.9	435.5	388.3	351.5	323.5	297.7	277.0	262.3	251.9	244.6	241.7
132.5°	485.9	434.9	393.0	359.1	331.7	307.1	286.4	271.2	260.2	252.3	248.7
135°	476.0	433.9	398.6	369.1	343.4	319.8	299.2	282.2	271.2	262.3	259.4
137.5°	469.0	433.9	403.6	376.8	352.8	329.5	310.4	293.5	281.7	272.9	269.4
140°	465.0	433.2	406.0	380.9	358.1	336.0	316.8	300.6	288.8	279.9	277.0
142.5°	460.8	433.2	407.7	384.5	362.2	340.7	322.7	307.1	295.3	287.1	284.6
145°	455.3	431.8	409.6	389.0	368.4	348.5	332.2	317.5	306.5	299.2	296.1
147.5°	449.8	429.1	410.3	391.5	373.4	354.7	340.3	328.0	317.8	310.8	308.6
150°	445.0	427.3	409.6	392.7	375.8	358.8	345.5	334.5	324.9	319.1	316.8
152.5°	440.9	424.4	408.5	393.3	378.1	363.0	350.8	340.4	332.0	326.1	325.1
155°	433.2	419.2	406.7	394.2	381.6	369.1	358.1	350.0	341.9	337.4	336.7
157.5°	426.0	414.0	403.3	394.2	384.2	373.5	364.3	357.8	350.7	347.1	346.5
160°	420.8	410.4	401.5	394.2	385.3	376.5	368.4	362.5	356.6	353.6	352.9
162.5°	415.9	407.5	399.8	393.6	386.0	378.2	371.9	366.6	361.9	358.9	359.4
165°	408.2	401.5	396.4	392.0	386.8	380.2	375.8	372.1	367.7	366.2	366.9
167.5°	400.5	396.4	393.0	391.0	386.6	381.8	379.0	376.4	373.5	372.2	373.2
170°	396.4	393.4	391.2	389.7	386.1	382.4	380.2	378.7	376.5	375.8	377.2
172.5°	392.3	389.9	388.9	388.0	385.5	383.0	381.4	380.5	378.2	378.7	379.6
175°	386.8	386.1	385.3	386.1	384.6	383.1	382.4	382.4	380.9	381.6	382.4
177.5°	383.7	383.1	383.7	384.9	383.7	383.1	383.1	383.1	381.9	382.6	383.7
180°	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1



TEST NUMBER: P331659-830

CATALOG NUMBER: SA2XXRDIP-C485D725U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0
2.5°	1018.9	1019.7	1025.4	1027.9	1033.0	1035.0	1037.2	1036.6	1036.6	1037.7	1045.7
5°	1021.1	1028.1	1038.7	1048.9	1058.8	1067.2	1072.8	1078.5	1080.5	1090.8	1099.9
7.5°	1017.5	1030.4	1047.8	1063.4	1082.0	1096.6	1108.7	1119.6	1127.1	1142.0	1157.2
10°	1012.7	1031.0	1050.7	1070.7	1096.5	1115.8	1135.5	1150.7	1155.6	1177.7	1190.4
12.5°	1003.1	1027.6	1052.6	1078.6	1103.7	1130.4	1152.1	1167.2	1184.6	1204.5	1227.9
15°	988.7	1016.9	1049.6	1083.1	1119.0	1151.3	1174.6	1201.0	1219.9	1241.8	1262.2
17.5°	968.1	1004.4	1045.9	1084.7	1126.1	1160.9	1193.0	1218.2	1231.6	1244.1	1247.2
20°	951.8	990.8	1039.7	1085.5	1127.0	1167.2	1198.8	1219.9	1223.5	1223.8	1205.1
22.5°	934.1	978.2	1029.4	1076.2	1125.9	1170.5	1195.1	1204.2	1190.2	1166.4	1130.3
25°	901.4	952.4	1011.9	1065.5	1119.6	1161.9	1170.4	1154.5	1105.6	1054.1	989.1
27.5°	866.1	923.4	987.2	1046.7	1104.5	1130.7	1112.4	1055.3	967.1	890.6	797.8
30°	840.2	904.6	967.2	1033.8	1087.2	1098.5	1056.7	972.5	869.8	754.3	661.8
32.5°	810.6	878.1	947.0	1015.8	1060.5	1049.5	980.3	876.8	756.3	642.8	555.3
35°	768.4	838.1	912.3	981.3	1009.8	962.3	858.8	724.1	600.9	494.9	434.7
37.5°	719.6	795.5	872.7	936.0	934.1	854.8	713.9	574.7	471.2	408.5	365.6
40°	684.9	761.7	845.1	898.6	875.7	772.6	619.8	488.5	412.8	362.9	331.6
42.5°	651.8	728.8	811.6	854.1	814.4	687.6	535.4	432.5	370.0	331.1	305.7
45°	595.2	676.5	753.3	776.8	705.7	566.0	432.9	358.4	316.8	287.9	270.3
47.5°	540.0	619.9	689.9	690.4	594.2	459.0	365.2	310.1	274.7	252.3	239.5
50°	506.1	582.2	640.9	631.8	522.7	408.3	326.6	279.1	249.6	232.3	219.0
52.5°	468.2	541.9	592.8	566.8	462.1	359.3	292.0	252.1	227.6	212.6	200.7
55°	412.8	478.3	514.3	474.9	377.0	298.8	246.8	215.4	197.1	184.5	174.3
57.5°	358.6	412.6	435.2	389.3	310.5	247.8	208.7	185.2	167.0	158.0	152.7
60°	324.5	370.6	386.4	335.8	269.9	216.8	184.8	163.0	149.6	143.6	138.4
62.5°	291.1	328.7	335.3	288.8	235.4	189.8	162.3	143.8	135.0	129.2	124.2
65°	241.5	268.5	265.4	228.1	186.2	150.6	130.5	119.3	112.6	104.5	95.8
67.5°	198.8	215.4	205.4	177.4	142.1	117.1	104.0	95.5	87.2	79.5	77.5
70°	171.7	181.3	170.7	145.1	116.5	98.2	87.7	77.5	72.5	70.8	67.6
72.5°	145.9	149.2	137.8	115.7	94.8	81.3	71.1	65.3	62.7	61.2	59.1
75°	109.4	107.0	97.2	79.9	65.8	56.6	53.5	51.4	49.7	48.3	47.1
77.5°	76.9	73.2	64.5	53.3	45.8	41.5	39.6	38.5	37.6	36.9	35.8
80°	57.7	55.2	46.5	38.0	34.9	32.7	31.7	30.3	30.3	29.6	28.5
82.5°	42.2	39.5	31.9	27.9	26.1	24.9	24.0	23.2	22.9	23.1	22.3
85°	22.1	17.9	15.8	15.2	14.0	13.4	13.8	13.0	13.0	13.0	12.6
87.5°	7.4	6.5	6.5	6.6	7.3	8.0	8.8	9.6	10.1	9.6	9.8
90°	2.9	5.9	7.4	8.9	11.0	14.7	19.9	24.3	25.1	24.3	23.6
92.5°	13.0	18.3	21.5	26.5	33.5	50.1	73.5	94.4	95.8	80.9	64.3
95°	28.7	36.1	42.7	54.5	72.2	106.1	170.2	255.7	288.8	252.7	193.0
97.5°	46.0	53.8	63.8	77.4	97.4	140.0	229.3	371.4	493.0	517.3	450.4
100°	58.9	65.6	77.4	92.1	112.7	151.7	241.7	400.8	582.0	688.2	672.7
102.5°	71.9	78.5	90.3	105.7	126.3	162.4	242.2	389.6	585.0	751.8	818.3
105°	92.8	98.0	109.1	125.3	145.9	180.5	246.1	367.7	545.9	742.0	895.2
107.5°	113.5	118.5	128.7	144.7	165.5	199.1	256.3	356.8	504.1	677.2	839.8
110°	128.2	132.6	142.2	157.7	179.1	211.4	264.5	354.4	484.1	636.6	792.0





TEST NUMBER: P331659-830

CATALOG NUMBER: SA2XXRDIP-C485D725U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	141.2	146.2	155.1	170.0	192.0	223.3	273.3	355.0	471.1	608.3	748.5
115°	162.1	166.5	175.3	190.1	210.0	241.7	286.6	358.1	456.9	573.3	694.7
117.5°	182.3	186.7	194.5	208.7	229.3	258.6	300.8	363.4	449.9	551.1	654.4
120°	195.3	199.6	206.3	221.0	241.7	270.4	310.2	366.9	445.7	539.3	634.3
122.5°	207.1	211.4	218.7	233.4	254.7	281.6	318.5	371.1	443.4	529.3	618.5
125°	223.3	227.6	236.5	251.3	271.8	298.4	331.6	377.2	439.1	515.0	595.3
127.5°	237.0	243.2	252.9	267.0	288.2	314.1	343.7	383.6	436.6	501.7	572.5
130°	244.6	251.9	262.3	277.0	297.7	323.5	351.5	388.3	435.5	492.9	557.7
132.5°	252.3	260.2	271.2	286.4	307.1	331.7	359.1	393.0	434.9	485.9	543.6
135°	262.3	271.2	282.2	299.2	319.8	343.4	369.1	398.6	433.9	476.0	523.9
137.5°	272.9	281.7	293.5	310.4	329.5	352.8	376.8	403.6	433.9	469.0	508.1
140°	279.9	288.8	300.6	316.8	336.0	358.1	380.9	406.0	433.2	465.0	498.0
142.5°	287.1	295.3	307.1	322.7	340.7	362.2	384.5	407.7	433.2	460.8	489.8
145°	299.2	306.5	317.5	332.2	348.5	368.4	389.0	409.6	431.8	455.3	478.2
147.5°	310.8	317.8	328.0	340.3	354.7	373.4	391.5	410.3	429.1	449.8	469.2
150°	319.1	324.9	334.5	345.5	358.8	375.8	392.7	409.6	427.3	445.0	462.7
152.5°	326.1	332.0	340.4	350.8	363.0	378.1	393.3	408.5	424.4	440.9	456.2
155°	337.4	341.9	350.0	358.1	369.1	381.6	394.2	406.7	419.2	433.2	447.2
157.5°	347.1	350.7	357.8	364.3	373.5	384.2	394.2	403.3	414.0	426.0	436.8
160°	353.6	356.6	362.5	368.4	376.5	385.3	394.2	401.5	410.4	420.8	430.3
162.5°	358.9	361.9	366.6	371.9	378.2	386.0	393.6	399.8	407.5	415.9	423.8
165°	366.2	367.7	372.1	375.8	380.2	386.8	392.0	396.4	401.5	408.2	414.1
167.5°	372.2	373.5	376.4	379.0	381.8	386.6	391.0	393.0	396.4	400.5	404.8
170°	375.8	376.5	378.7	380.2	382.4	386.1	389.7	391.2	393.4	396.4	400.1
172.5°	378.7	378.2	380.5	381.4	383.0	385.5	388.0	388.9	389.9	392.3	394.7
175°	381.6	380.9	382.4	382.4	383.1	384.6	386.1	385.3	386.1	386.8	389.0
177.5°	382.6	381.9	383.1	383.1	383.1	383.7	384.9	383.7	383.1	383.7	384.9
180°	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1



TEST NUMBER: P331659-830  
 CATALOG NUMBER: SA2XXRDIP-C485D725U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0
2.5°	1048.5	1052.2	1053.9	1053.9	1055.8	1055.0	1054.1
5°	1108.7	1115.4	1116.8	1123.1	1127.8	1126.3	1127.0
7.5°	1168.7	1179.4	1190.1	1194.9	1195.7	1198.5	1199.6
10°	1205.5	1214.4	1230.9	1228.4	1240.8	1247.7	1236.1
12.5°	1241.0	1252.9	1264.4	1267.5	1274.5	1276.8	1272.1
15°	1273.1	1279.4	1280.2	1278.4	1280.5	1278.7	1272.1
17.5°	1243.1	1232.8	1212.0	1202.1	1194.3	1182.8	1178.2
20°	1193.5	1163.3	1128.1	1114.0	1097.5	1065.1	1072.8
22.5°	1086.6	1052.1	1016.9	975.7	956.1	925.4	923.6
25°	920.1	860.6	795.1	749.3	722.6	692.0	678.6
27.5°	715.4	640.5	586.8	559.7	534.9	510.7	509.6
30°	580.8	524.4	483.0	459.7	444.6	434.3	436.5
32.5°	489.6	450.9	422.9	403.7	392.5	384.7	384.7
35°	400.2	373.8	355.8	347.8	339.7	334.0	334.4
37.5°	342.5	326.6	316.6	307.7	302.7	299.9	298.3
40°	312.9	299.9	292.2	286.9	282.7	278.8	278.1
42.5°	289.5	278.8	271.0	266.8	263.0	260.1	259.5
45°	256.9	248.2	241.1	236.5	234.8	232.3	232.3
47.5°	228.6	219.9	214.4	211.5	208.5	206.9	206.8
50°	209.4	202.7	197.8	196.0	193.6	192.6	192.2
52.5°	192.3	187.3	183.7	182.6	181.4	180.1	180.3
55°	168.9	166.2	164.8	163.6	161.9	159.8	161.2
57.5°	149.3	146.9	143.1	139.8	138.2	136.7	137.2
60°	135.5	130.5	125.6	121.8	120.7	117.5	117.5
62.5°	118.1	111.1	105.1	102.9	101.9	100.4	100.1
65°	90.8	88.0	86.6	85.2	84.5	84.5	83.8
67.5°	75.2	74.1	72.6	72.2	71.5	71.4	71.1
70°	66.5	65.1	64.4	64.1	63.3	63.7	62.7
72.5°	58.1	56.9	56.8	55.9	55.5	55.5	54.8
75°	45.7	45.7	45.4	45.1	44.4	44.0	44.4
77.5°	35.2	35.3	34.6	34.6	34.5	34.6	34.2
80°	28.2	28.5	28.2	27.8	27.4	27.8	27.4
82.5°	22.2	21.8	21.7	21.6	21.6	21.3	21.3
85°	12.6	13.0	12.6	12.3	12.3	12.3	12.6
87.5°	9.2	9.5	9.6	9.6	9.6	9.6	9.3
90°	22.1	23.6	24.3	24.3	24.3	24.3	24.3
92.5°	55.1	48.9	44.4	43.7	41.4	42.0	40.8
95°	148.1	117.2	100.9	91.3	85.5	83.2	84.0
97.5°	368.5	288.8	235.6	200.4	182.3	171.5	165.3
100°	581.4	480.4	391.2	330.1	298.4	277.0	263.7
102.5°	797.7	723.8	629.3	562.9	508.8	482.1	464.2
105°	978.5	988.1	963.7	918.0	872.3	840.7	830.4
107.5°	965.2	1041.8	1077.5	1083.3	1080.7	1074.4	1060.6
110°	924.0	1018.2	1078.6	1110.3	1124.4	1131.0	1130.2



TEST NUMBER: P331659-830

CATALOG NUMBER: SA2XXRDIP-C485D725U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	875.0	975.8	1045.1	1089.1	1112.6	1125.1	1129.1
115°	808.2	904.7	980.6	1032.9	1066.9	1086.0	1092.7
117.5°	754.0	841.6	912.8	966.1	1001.9	1022.1	1027.7
120°	725.8	803.8	870.9	922.5	957.1	978.5	985.8
122.5°	702.2	776.1	836.7	883.0	917.0	936.0	942.2
125°	671.2	736.0	791.3	834.1	862.0	880.4	886.4
127.5°	641.1	702.3	753.3	790.6	816.8	832.7	837.4
130°	621.1	679.3	727.9	764.0	789.1	803.8	809.7
132.5°	602.3	655.7	701.4	737.0	762.0	775.5	780.8
135°	572.5	621.1	662.3	694.1	718.4	731.6	734.6
137.5°	548.7	587.4	623.3	652.2	673.2	684.8	689.2
140°	533.5	567.3	599.7	623.3	642.4	653.6	658.0
142.5°	519.9	549.0	576.2	598.6	616.0	625.8	626.7
145°	502.5	525.4	546.7	564.4	576.9	584.3	586.4
147.5°	488.3	506.1	521.8	536.4	546.4	551.4	552.7
150°	478.9	494.4	507.7	518.7	527.5	532.0	532.7
152.5°	471.3	484.4	495.9	504.5	512.2	515.5	515.6
155°	459.0	470.0	478.2	486.3	491.4	494.4	492.9
157.5°	446.7	455.9	462.2	468.0	472.3	473.6	473.6
160°	438.4	446.5	451.7	456.9	460.5	461.2	461.2
162.5°	430.7	437.6	441.7	446.8	449.3	450.1	449.4
165°	419.2	424.4	427.3	430.3	433.2	433.2	432.5
167.5°	408.8	412.3	415.0	416.3	417.9	417.7	416.9
170°	402.3	405.2	406.7	407.5	409.6	408.9	407.5
172.5°	396.4	398.8	399.6	400.4	401.4	400.7	399.8
175°	389.7	390.5	391.2	391.2	392.0	391.2	389.7
177.5°	384.9	385.5	385.5	385.5	385.5	384.9	383.7
180°	383.1	383.1	383.1	383.1	383.1	383.1	383.1

(END OF REPORT)