

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333270-940

Luminaire Tested: **S125DIP-S1090D810U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333270-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1090D810U940-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6596.6 lumens
Efficiency: N/A
Efficacy: 121.3 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333270-940

CATALOG NUMBER: S125DIP-S1090D810U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333270-940

CATALOG NUMBER: S125DIP-S1090D810U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	100	96	92	89	94	90	87	84	79	76	74	68	67	65	59	57	56	52
2	92	84	78	73	86	79	74	69	69	65	62	60	57	55	52	50	48	44
3	84	74	67	61	78	70	63	58	61	56	52	54	50	46	46	43	41	37
4	77	66	58	52	72	62	55	49	55	49	45	48	43	40	41	38	35	32
5	71	59	51	45	66	55	48	43	49	43	39	43	38	35	37	34	31	28
6	65	53	45	39	61	50	43	37	44	38	34	39	34	31	34	30	27	25
7	60	48	40	34	56	45	38	33	40	34	30	35	31	27	31	27	24	22
8	56	43	36	30	52	41	34	29	37	31	27	32	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	22	20	18
10	49	36	29	24	46	35	28	23	31	25	22	28	23	20	24	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9158	9158	9158	9158
5°	10605	9189	8045	9189
10°	12338	9141	7050	9141
15°	13658	9074	6503	9074
20°	15289	8968	6064	8968
25°	17910	8848	5850	8848
30°	19345	8730	5665	8730
35°	15906	8508	5542	8508
40°	11306	8200	5409	8200
45°	8685	7784	5332	7784
50°	7414	7268	5322	7268
55°	6600	6764	5368	6764
60°	5955	6212	5504	6212
65°	5500	5656	5647	5656
70°	5000	5080	5729	5080
75°	4414	4474	5677	4474
80°	3715	3649	5192	3649
85°	2942	2631	4187	2631



TEST NUMBER: P333270-940

CATALOG NUMBER: S125DIP-S1090D810U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.5	2.1
10°-20°	406.4	6.2
20°-30°	660.0	10.0
30°-40°	805.0	12.2
40°-50°	732.3	11.1
50°-60°	583.3	8.8
60°-70°	406.3	6.2
70°-80°	216.7	3.3
80°-90°	56.6	0.9
90°-100°	250.7	3.8
100°-110°	538.9	8.2
110°-120°	505.7	7.7
120°-130°	409.8	6.2
130°-140°	328.9	5.0
140°-150°	248.2	3.8
150°-160°	174.7	2.6
160°-170°	103.0	1.6
170°-180°	33.5	0.5
0°-30°	1202.9	18.2
0°-40°	2008.0	30.4
0°-60°	3323.6	50.4
0°-90°	4003.2	60.7
90°-120°	1295.2	19.6
90°-150°	2282.2	34.6
90°-180°	2593.0	39.3
0°-180°	6596.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1418	1418	1418	1418	1418	
5°	1636	1417	1241	1417	1636	165
15°	2043	1357	973	1357	2043	585
25°	2513	1242	821	1242	2513	1148
35°	2017	1079	703	1079	2017	1235
45°	951	852	584	852	951	761
55°	586	601	477	601	586	528
65°	360	370	370	370	360	357
75°	177	179	228	179	177	191
85°	40	36	56	36	40	46
90°	16	1	16	1	16	13
95°	164	23	164	23	164	232
105°	924	79	924	79	924	918
115°	1029	141	1029	141	1029	1005
125°	811	195	811	195	811	734
135°	674	229	674	229	674	522
145°	531	266	531	266	531	338
155°	446	304	446	304	446	208
165°	390	332	390	332	390	112
175°	351	345	351	345	351	34
180°	346	346	346	346	346	



TEST NUMBER: P333270-940

CATALOG NUMBER: S125DIP-S1090D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1499.9	1497.9	1496.0	1492.1	1495.0	1486.8	1483.0	1476.2	1468.0	1465.2	1461.8
5°	1635.8	1638.9	1641.9	1629.2	1630.4	1622.0	1602.8	1587.1	1574.5	1558.2	1546.8
7.5°	1799.6	1792.4	1791.9	1783.7	1769.6	1758.3	1738.0	1712.3	1687.4	1658.9	1635.5
10°	1881.4	1882.0	1876.6	1867.0	1851.9	1841.1	1814.6	1789.3	1758.6	1722.5	1696.7
12.5°	1943.0	1945.5	1938.8	1925.7	1918.3	1894.1	1873.4	1843.3	1806.8	1777.9	1738.6
15°	2042.7	2036.1	2031.3	2015.0	2002.4	1977.1	1944.0	1912.7	1872.9	1836.3	1799.6
17.5°	2138.8	2144.0	2135.0	2120.2	2081.0	2051.5	2007.1	1964.3	1914.8	1865.5	1821.7
20°	2224.5	2229.3	2215.5	2189.6	2142.6	2113.2	2054.8	1999.4	1942.2	1879.0	1830.9
22.5°	2331.4	2327.5	2308.8	2269.5	2228.8	2174.3	2111.1	2043.7	1972.0	1900.7	1836.7
25°	2513.4	2488.1	2476.6	2428.0	2374.4	2294.3	2207.6	2108.9	2019.8	1925.4	1843.5
27.5°	2614.2	2606.3	2593.5	2559.6	2503.3	2417.7	2315.5	2195.2	2069.6	1950.3	1843.2
30°	2594.0	2595.2	2596.4	2585.6	2549.5	2485.1	2383.4	2254.0	2104.7	1970.5	1846.5
32.5°	2414.9	2436.8	2457.7	2482.5	2492.7	2480.3	2416.6	2299.7	2146.1	1993.6	1844.6
35°	2017.4	2024.1	2092.0	2159.5	2250.9	2322.0	2369.5	2317.7	2188.3	2013.2	1842.3
37.5°	1573.1	1605.5	1652.6	1728.8	1860.8	1979.1	2131.1	2201.0	2159.3	2019.6	1838.1
40°	1341.0	1371.0	1401.8	1479.3	1590.7	1733.9	1906.7	2054.1	2088.5	1999.4	1823.6
42.5°	1161.8	1185.7	1219.8	1278.1	1371.2	1498.1	1663.0	1855.7	1974.3	1940.6	1793.3
45°	950.9	966.0	992.5	1038.8	1106.3	1205.5	1351.2	1561.8	1745.4	1806.2	1721.4
47.5°	814.0	813.9	834.5	866.5	915.1	999.4	1107.1	1272.2	1468.3	1613.4	1606.6
50°	737.9	734.9	751.1	778.8	817.3	873.3	976.2	1108.0	1296.4	1460.7	1506.5
52.5°	672.4	672.8	682.8	703.2	735.5	783.3	860.1	979.0	1140.0	1308.6	1394.7
55°	586.2	583.8	595.2	609.1	632.6	663.9	719.3	810.1	940.7	1106.8	1218.8
57.5°	507.2	513.9	518.4	528.1	547.6	568.6	615.2	681.9	785.5	928.1	1046.4
60°	461.0	467.6	471.3	480.9	496.5	514.6	550.7	604.8	692.1	814.9	932.3
62.5°	419.6	424.8	426.0	434.6	447.5	465.0	493.4	539.0	607.9	715.2	830.2
65°	359.9	359.9	362.3	371.3	377.4	393.0	414.6	447.8	503.2	586.8	684.9
67.5°	302.4	305.2	304.7	308.6	314.1	326.4	341.9	369.2	410.2	471.3	549.7
70°	264.8	267.2	266.6	269.7	275.6	283.5	296.1	322.0	351.5	403.9	471.3
72.5°	231.1	232.1	230.5	234.5	238.1	245.0	259.0	272.9	300.4	344.6	400.0
75°	176.9	178.2	179.3	181.7	185.4	189.0	196.2	210.1	228.1	261.2	296.8
77.5°	132.7	130.4	133.2	132.9	134.9	137.7	144.1	151.4	166.2	187.2	214.6
80°	99.9	100.5	100.5	101.1	104.2	105.9	111.4	116.7	128.2	143.8	163.1
82.5°	72.9	74.5	73.6	74.6	77.1	78.5	81.5	86.0	92.6	104.9	118.8
85°	39.7	36.7	37.9	39.1	39.1	39.7	42.1	44.0	47.5	52.3	57.8
87.5°	14.8	15.7	16.1	16.1	16.6	16.2	18.0	17.9	19.3	20.5	22.2
90°	16.1	16.1	15.3	15.3	15.3	13.9	13.3	12.6	11.9	11.1	9.7
92.5°	44.5	45.6	46.5	48.2	57.2	67.5	89.7	123.6	182.0	224.8	228.4
95°	163.8	175.0	180.6	201.5	251.0	309.6	395.3	501.3	604.5	617.8	504.1
97.5°	396.0	404.9	425.2	464.2	507.3	588.7	672.3	746.6	764.8	659.7	450.1
100°	543.9	555.0	580.8	631.0	679.1	751.6	823.4	857.6	803.9	629.6	401.6
102.5°	708.9	717.3	745.3	781.0	832.5	881.5	916.1	894.9	780.5	576.6	364.8
105°	923.8	932.2	946.1	969.1	991.5	999.2	968.5	872.9	705.6	505.5	329.1
107.5°	1037.9	1043.5	1048.0	1048.2	1036.9	1000.5	921.8	794.2	629.2	456.6	314.1
110°	1075.8	1075.8	1070.9	1057.7	1026.3	967.1	868.7	736.3	585.7	433.6	309.6



TEST NUMBER: P333270-940

CATALOG NUMBER: S125DIP-S1090D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1071.4	1066.3	1054.2	1031.4	985.6	915.7	816.3	690.5	553.3	420.3	309.6
115°	1029.1	1020.0	1000.5	967.1	912.7	836.7	741.2	633.1	518.0	405.8	311.7
117.5°	955.0	949.5	930.1	895.5	841.2	771.4	689.1	596.0	497.0	398.7	316.3
120°	907.0	901.5	882.7	849.2	797.6	736.3	659.6	575.9	485.3	395.3	320.7
122.5°	864.7	859.7	840.9	810.2	764.2	706.7	638.4	560.9	475.2	392.5	324.6
125°	810.8	803.9	788.5	760.0	720.9	670.7	610.1	539.0	461.5	389.1	331.2
127.5°	764.8	761.8	747.3	722.0	686.6	639.6	583.0	516.7	449.0	387.4	338.6
130°	739.8	735.6	721.7	698.7	663.8	618.4	564.1	502.7	440.7	386.3	343.0
132.5°	714.6	709.9	697.1	674.0	639.2	595.6	546.2	488.7	434.0	386.3	348.0
135°	673.5	669.3	656.7	633.7	603.1	563.4	518.7	470.6	426.0	386.3	354.9
137.5°	629.6	625.0	613.4	592.5	565.0	531.3	494.2	455.3	418.9	387.1	361.1
140°	598.9	595.4	585.0	566.9	541.0	511.8	479.7	446.9	415.5	387.6	363.9
142.5°	570.4	567.6	557.7	542.3	520.4	495.0	467.4	439.7	412.8	388.3	365.6
145°	531.3	528.5	520.8	509.0	492.2	473.4	451.8	430.2	408.6	387.6	367.5
147.5°	498.1	496.9	492.4	482.9	469.7	455.4	438.8	421.2	404.2	385.8	368.1
150°	479.7	479.0	476.2	467.9	457.4	444.8	431.6	416.3	400.9	384.1	368.1
152.5°	465.2	464.5	461.7	455.0	446.2	436.5	424.4	410.6	397.0	381.9	367.6
155°	445.5	444.8	442.7	437.8	430.9	423.2	413.5	402.3	390.5	377.9	366.0
157.5°	427.9	428.1	426.1	422.1	416.7	410.6	403.1	394.0	384.3	373.7	364.3
160°	416.3	417.0	415.5	412.1	407.2	402.3	395.3	388.3	379.3	371.0	362.6
162.5°	405.6	405.8	405.5	402.6	398.8	394.5	388.6	382.2	374.8	367.6	360.9
165°	390.5	390.5	390.5	389.1	386.3	382.8	378.6	373.7	368.1	362.6	358.4
167.5°	376.5	376.7	377.2	375.9	374.5	372.0	368.8	365.6	361.6	357.7	354.5
170°	368.1	368.8	368.8	368.1	366.8	365.3	363.3	361.1	357.7	354.9	352.8
172.5°	360.3	361.1	362.1	360.9	360.6	359.8	358.2	356.1	353.7	351.5	350.5
175°	350.7	351.4	352.8	352.1	352.1	352.1	350.7	350.7	348.6	347.9	347.9
177.5°	345.8	345.8	347.5	347.0	347.5	347.5	347.5	347.0	346.3	345.8	345.8
180°	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8



TEST NUMBER: P333270-940

CATALOG NUMBER: S125DIP-S1090D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1458.9	1455.5	1451.7	1444.9	1436.7	1432.4	1425.7	1421.4	1412.6	1405.4	1397.8
5°	1532.9	1517.3	1502.9	1484.2	1463.7	1450.5	1434.9	1417.4	1399.4	1380.6	1360.2
7.5°	1609.6	1581.9	1551.8	1519.5	1487.8	1458.7	1430.8	1403.6	1378.0	1347.2	1321.1
10°	1661.2	1626.2	1588.9	1545.0	1502.3	1464.9	1427.0	1393.9	1360.2	1324.1	1292.2
12.5°	1712.6	1666.2	1613.5	1565.2	1513.8	1468.7	1424.2	1381.9	1339.5	1299.6	1262.3
15°	1749.0	1708.1	1659.3	1590.7	1532.9	1471.0	1411.9	1357.2	1306.0	1261.5	1214.6
17.5°	1773.0	1720.2	1667.9	1602.0	1526.3	1457.0	1390.2	1327.5	1269.8	1213.4	1168.1
20°	1777.3	1723.1	1668.4	1603.9	1526.3	1446.9	1380.1	1304.8	1242.9	1184.5	1129.1
22.5°	1775.8	1714.5	1654.8	1588.6	1512.9	1439.7	1358.9	1282.2	1215.0	1157.5	1099.7
25°	1762.3	1696.7	1622.0	1555.2	1480.6	1402.9	1321.1	1241.6	1173.0	1107.4	1050.3
27.5°	1751.0	1665.8	1581.4	1503.4	1431.4	1360.2	1281.8	1200.5	1124.4	1057.9	1004.1
30°	1737.0	1643.7	1548.5	1467.3	1393.3	1324.1	1250.1	1170.6	1091.2	1026.2	968.4
32.5°	1724.5	1615.8	1515.4	1426.9	1348.5	1281.2	1213.0	1137.4	1059.4	993.5	935.7
35°	1700.2	1574.5	1459.6	1359.6	1275.9	1206.8	1149.6	1079.1	1007.5	943.7	888.3
37.5°	1669.6	1520.3	1397.0	1292.2	1200.5	1127.6	1074.3	1020.3	951.5	890.0	840.0
40°	1645.5	1481.8	1351.2	1244.0	1149.0	1073.1	1023.8	972.6	915.4	858.3	805.3
42.5°	1615.2	1447.2	1304.9	1189.6	1095.5	1021.6	969.8	926.4	875.9	822.6	773.5
45°	1559.4	1384.3	1230.2	1106.3	1011.1	938.3	884.8	852.2	814.3	763.8	722.2
47.5°	1477.5	1308.8	1149.4	1021.5	923.4	855.9	805.7	774.5	747.8	710.2	672.5
50°	1404.7	1252.5	1091.2	964.2	866.1	798.1	751.7	723.4	700.5	671.6	639.8
52.5°	1323.4	1181.7	1033.8	908.3	811.2	744.1	698.7	673.9	654.8	634.1	602.7
55°	1194.1	1073.7	936.5	817.3	727.6	662.0	622.3	600.7	585.1	569.4	550.1
57.5°	1051.7	957.5	836.0	727.0	644.4	584.8	547.7	526.6	514.4	506.4	495.1
60°	951.5	870.9	766.2	666.8	586.2	533.2	497.1	480.9	470.6	464.0	455.6
62.5°	858.6	792.4	695.4	604.8	534.2	484.1	451.9	436.1	426.3	423.1	416.2
65°	721.7	670.5	590.4	515.2	455.0	412.2	385.2	370.1	364.1	360.5	361.1
67.5°	586.7	555.5	491.2	427.0	379.1	343.2	321.6	310.0	306.9	302.1	302.0
70°	504.4	480.9	426.7	370.8	328.0	300.3	281.1	269.0	266.0	263.6	263.1
72.5°	431.7	411.1	364.1	319.2	280.8	256.5	240.6	233.4	228.5	227.0	226.9
75°	324.4	313.0	275.6	240.1	213.7	196.8	186.0	179.3	175.8	175.1	175.8
77.5°	230.6	220.6	196.9	171.7	155.1	142.3	133.1	130.8	126.7	126.9	126.3
80°	173.3	166.7	151.7	131.8	118.0	107.1	102.3	98.1	96.9	95.1	96.9
82.5°	125.6	118.6	108.3	95.7	84.3	77.8	72.9	71.6	70.9	70.1	70.4
85°	62.0	62.6	56.5	46.9	42.1	38.5	35.5	35.5	34.9	34.3	34.9
87.5°	23.0	21.8	19.7	17.9	15.2	13.6	12.8	13.1	11.9	11.6	12.4
90°	9.1	7.7	7.0	5.6	4.2	2.8	1.4	0.7	1.4	2.8	4.2
92.5°	159.1	95.2	57.2	36.8	24.8	16.1	10.3	8.5	10.3	16.1	24.8
95°	311.7	158.3	83.6	52.3	36.9	29.2	23.7	23.0	23.7	29.2	36.9
97.5°	248.8	136.3	87.0	64.4	50.6	43.0	39.1	38.2	39.1	43.0	50.6
100°	225.9	135.3	94.8	73.9	60.6	53.0	50.2	48.8	50.2	53.0	60.6
102.5°	216.4	140.3	104.3	83.9	71.8	63.6	61.3	60.5	61.3	63.6	71.8
105°	212.7	150.6	119.9	100.4	89.3	82.3	78.8	78.8	78.8	82.3	89.3
107.5°	219.1	165.9	136.3	118.7	107.1	101.4	98.0	96.7	98.0	101.4	107.1
110°	225.2	177.1	148.5	130.4	119.9	113.6	110.8	109.5	110.8	113.6	119.9



TEST NUMBER: P333270-940

CATALOG NUMBER: S125DIP-S1090D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	233.0	187.7	160.2	142.7	132.2	125.9	123.7	122.3	123.7	125.9	132.2
115°	244.7	204.3	178.5	161.0	150.6	144.4	142.2	140.8	142.2	144.4	150.6
117.5°	258.2	221.3	196.9	180.0	168.2	161.9	159.7	157.6	159.7	161.9	168.2
120°	267.1	233.5	209.2	191.7	179.9	173.6	170.9	168.7	170.9	173.6	179.9
122.5°	277.1	245.3	220.9	203.5	190.5	184.2	182.0	180.5	182.0	184.2	190.5
125°	290.7	260.7	237.7	219.6	206.3	200.1	196.6	195.2	196.6	200.1	206.3
127.5°	303.3	275.7	253.5	235.4	221.3	213.4	208.9	206.8	208.9	213.4	221.3
130°	311.7	285.2	263.6	245.4	230.8	221.7	216.2	214.0	216.2	221.7	230.8
132.5°	318.9	294.1	272.5	254.3	239.2	229.0	222.3	219.6	222.3	229.0	239.2
135°	329.1	306.1	284.5	265.6	251.0	239.9	231.5	228.7	231.5	239.9	251.0
137.5°	336.6	314.6	294.9	275.5	261.2	250.0	242.2	240.1	242.2	250.0	261.2
140°	341.6	320.7	300.5	281.7	268.4	257.3	248.9	246.8	248.9	257.3	268.4
142.5°	344.5	324.6	305.5	287.8	275.1	263.9	256.2	254.6	256.2	263.9	275.1
145°	348.6	331.2	313.1	297.0	284.5	274.7	267.7	266.4	267.7	274.7	284.5
147.5°	351.2	335.4	319.5	305.4	294.5	285.4	279.5	278.6	279.5	285.4	294.5
150°	352.8	338.1	322.8	310.9	301.2	292.1	287.2	285.9	287.2	292.1	301.2
152.5°	353.9	340.9	326.7	316.0	306.7	298.8	294.5	293.6	294.5	298.8	306.7
155°	354.9	343.8	331.9	322.1	315.1	308.2	304.0	304.0	304.0	308.2	315.1
157.5°	355.6	346.1	335.9	328.5	322.4	316.4	313.1	313.2	313.1	316.4	322.4
160°	355.6	347.2	338.1	331.9	326.3	321.5	318.6	319.3	318.6	321.5	326.3
162.5°	355.0	348.3	340.4	335.2	330.7	326.5	323.7	324.3	323.7	326.5	330.7
165°	354.2	348.6	343.0	338.9	336.1	332.6	330.5	331.9	330.5	332.6	336.1
167.5°	352.5	348.6	344.0	341.3	339.4	337.4	336.2	336.9	336.2	337.4	339.4
170°	351.4	348.6	345.1	343.0	341.6	340.3	339.6	340.3	339.6	340.3	341.6
172.5°	350.3	348.0	345.1	344.1	343.3	341.9	341.3	342.5	341.3	341.9	343.3
175°	348.6	347.2	345.1	345.1	345.1	344.5	343.8	345.1	343.8	344.5	345.1
177.5°	347.0	346.3	345.3	345.3	345.8	345.3	345.3	346.3	345.3	345.3	345.8
180°	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8



TEST NUMBER: P333270-940

CATALOG NUMBER: S125DIP-S1090D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1393.4	1388.1	1383.8	1374.1	1368.9	1361.6	1355.8	1362.1	1355.4	1358.3	1354.0
5°	1350.0	1333.1	1321.1	1303.6	1288.6	1274.7	1264.5	1262.7	1257.8	1255.4	1248.2
7.5°	1297.7	1276.7	1256.0	1233.1	1213.8	1194.2	1181.7	1171.4	1164.5	1155.5	1149.3
10°	1266.9	1238.6	1214.6	1186.9	1162.8	1141.7	1124.9	1116.4	1108.7	1097.2	1093.0
12.5°	1228.9	1199.6	1170.3	1140.7	1117.5	1094.0	1079.6	1066.8	1061.4	1048.6	1047.2
15°	1183.3	1139.3	1110.4	1080.3	1048.5	1029.2	1017.2	1003.3	997.3	988.3	981.6
17.5°	1128.8	1089.6	1053.5	1022.3	995.0	978.7	963.9	954.3	944.0	938.1	927.2
20°	1089.4	1052.0	1015.9	982.8	961.8	943.1	931.0	922.0	911.2	908.2	897.4
22.5°	1056.1	1014.9	980.3	952.5	929.5	908.5	895.5	889.3	881.8	872.5	870.4
25°	1002.1	959.4	929.9	902.2	881.7	862.5	853.5	845.6	838.4	831.8	829.4
27.5°	955.4	917.2	882.2	857.2	839.4	821.8	813.9	804.3	799.1	793.7	787.2
30°	922.7	883.5	852.8	828.8	809.5	793.9	785.4	778.8	774.0	769.2	765.5
32.5°	888.9	852.7	823.0	799.4	780.2	768.3	760.9	756.2	750.9	745.1	740.6
35°	844.5	804.7	775.8	755.4	740.3	731.3	722.8	718.6	712.6	712.6	707.8
37.5°	794.2	759.9	734.4	715.8	702.2	694.2	685.0	682.2	678.3	675.7	674.0
40°	764.4	732.5	708.4	689.7	675.3	668.7	661.5	656.7	654.2	651.2	650.0
42.5°	733.5	703.1	680.0	662.8	650.2	644.6	637.8	634.5	629.6	625.7	625.0
45°	686.7	657.2	636.1	622.3	611.4	604.8	600.7	593.4	591.0	586.2	585.6
47.5°	642.3	614.0	593.3	582.0	572.5	567.0	560.4	553.2	550.5	548.0	547.8
50°	609.1	583.2	563.9	553.1	544.1	536.3	529.7	524.9	523.0	523.0	524.2
52.5°	575.4	553.3	537.0	523.7	515.2	506.8	500.8	497.8	495.1	498.0	500.2
55°	526.0	503.7	491.7	479.1	470.6	461.0	458.0	456.8	455.0	459.9	462.3
57.5°	473.8	458.2	444.1	431.5	423.9	418.4	414.3	413.6	417.0	419.3	427.0
60°	440.6	422.5	409.8	400.2	391.2	387.6	386.4	385.2	387.6	394.2	404.5
62.5°	403.9	389.3	375.7	368.5	361.9	355.8	355.6	356.3	361.1	368.7	378.9
65°	350.3	337.6	328.6	320.2	314.8	311.1	312.4	314.8	320.2	330.4	341.9
67.5°	295.8	287.1	279.0	272.2	267.0	267.0	268.2	271.8	278.2	290.0	300.4
70°	260.6	251.0	244.3	241.4	237.1	234.7	238.4	244.3	249.8	260.6	269.7
72.5°	225.4	217.3	212.1	210.1	208.2	206.3	207.5	214.0	221.3	232.2	242.6
75°	173.3	170.3	166.7	164.3	162.5	163.7	164.9	170.9	176.9	188.4	200.5
77.5°	126.5	123.4	121.2	120.6	119.7	120.3	123.6	128.0	133.9	142.3	151.4
80°	95.7	94.5	93.3	92.6	92.6	93.3	98.1	101.1	106.6	114.3	121.5
82.5°	69.7	68.9	68.8	68.6	69.1	69.2	72.1	76.1	80.5	86.4	92.6
85°	36.7	35.5	37.3	37.9	36.7	38.5	39.7	42.1	44.0	46.9	49.9
87.5°	13.2	14.4	14.1	14.8	15.0	16.2	15.9	17.9	19.0	20.2	19.9
90°	5.6	7.0	7.7	9.1	9.7	11.1	11.9	12.6	13.3	13.9	15.3
92.5°	36.8	57.2	95.2	159.1	228.4	224.8	182.0	123.6	89.7	67.5	57.2
95°	52.3	83.6	158.3	311.7	504.1	617.8	604.5	501.3	395.3	309.6	251.0
97.5°	64.4	87.0	136.3	248.8	450.1	659.7	764.8	746.6	672.3	588.7	507.3
100°	73.9	94.8	135.3	225.9	401.6	629.6	803.9	857.6	823.4	751.6	679.1
102.5°	83.9	104.3	140.3	216.4	364.8	576.6	780.5	894.9	916.1	881.5	832.5
105°	100.4	119.9	150.6	212.7	329.1	505.5	705.6	872.9	968.5	999.2	991.5
107.5°	118.7	136.3	165.9	219.1	314.1	456.6	629.2	794.2	921.8	1000.5	1036.9
110°	130.4	148.5	177.1	225.2	309.6	433.6	585.7	736.3	868.7	967.1	1026.3



TEST NUMBER: P333270-940

CATALOG NUMBER: S125DIP-S1090D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	142.7	160.2	187.7	233.0	309.6	420.3	553.3	690.5	816.3	915.7	985.6
115°	161.0	178.5	204.3	244.7	311.7	405.8	518.0	633.1	741.2	836.7	912.7
117.5°	180.0	196.9	221.3	258.2	316.3	398.7	497.0	596.0	689.1	771.4	841.2
120°	191.7	209.2	233.5	267.1	320.7	395.3	485.3	575.9	659.6	736.3	797.6
122.5°	203.5	220.9	245.3	277.1	324.6	392.5	475.2	560.9	638.4	706.7	764.2
125°	219.6	237.7	260.7	290.7	331.2	389.1	461.5	539.0	610.1	670.7	720.9
127.5°	235.4	253.5	275.7	303.3	338.6	387.4	449.0	516.7	583.0	639.6	686.6
130°	245.4	263.6	285.2	311.7	343.0	386.3	440.7	502.7	564.1	618.4	663.8
132.5°	254.3	272.5	294.1	318.9	348.0	386.3	434.0	488.7	546.2	595.6	639.2
135°	265.6	284.5	306.1	329.1	354.9	386.3	426.0	470.6	518.7	563.4	603.1
137.5°	275.5	294.9	314.6	336.6	361.1	387.1	418.9	455.3	494.2	531.3	565.0
140°	281.7	300.5	320.7	341.6	363.9	387.6	415.5	446.9	479.7	511.8	541.0
142.5°	287.8	305.5	324.6	344.5	365.6	388.3	412.8	439.7	467.4	495.0	520.4
145°	297.0	313.1	331.2	348.6	367.5	387.6	408.6	430.2	451.8	473.4	492.2
147.5°	305.4	319.5	335.4	351.2	368.1	385.8	404.2	421.2	438.8	455.4	469.7
150°	310.9	322.8	338.1	352.8	368.1	384.1	400.9	416.3	431.6	444.8	457.4
152.5°	316.0	326.7	340.9	353.9	367.6	381.9	397.0	410.6	424.4	436.5	446.2
155°	322.1	331.9	343.8	354.9	366.0	377.9	390.5	402.3	413.5	423.2	430.9
157.5°	328.5	335.9	346.1	355.6	364.3	373.7	384.3	394.0	403.1	410.6	416.7
160°	331.9	338.1	347.2	355.6	362.6	371.0	379.3	388.3	395.3	402.3	407.2
162.5°	335.2	340.4	348.3	355.0	360.9	367.6	374.8	382.2	388.6	394.5	398.8
165°	338.9	343.0	348.6	354.2	358.4	362.6	368.1	373.7	378.6	382.8	386.3
167.5°	341.3	344.0	348.6	352.5	354.5	357.7	361.6	365.6	368.8	372.0	374.5
170°	343.0	345.1	348.6	351.4	352.8	354.9	357.7	361.1	363.3	365.3	366.8
172.5°	344.1	345.1	348.0	350.3	350.5	351.5	353.7	356.1	358.2	359.8	360.6
175°	345.1	345.1	347.2	348.6	347.9	347.9	348.6	350.7	350.7	352.1	352.1
177.5°	345.3	345.3	346.3	347.0	345.8	345.8	346.3	347.0	347.5	347.5	347.5
180°	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8



TEST NUMBER: P333270-940

CATALOG NUMBER: S125DIP-S1090D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1351.0	1354.4	1351.6	1355.4	1351.6	1354.4	1351.0	1354.0	1358.3	1355.4	1362.1
5°	1245.3	1239.8	1243.4	1241.0	1243.4	1239.8	1245.3	1248.2	1255.4	1257.8	1262.7
7.5°	1147.5	1142.4	1136.4	1133.6	1136.4	1142.4	1147.5	1149.3	1155.5	1164.5	1171.4
10°	1086.4	1079.8	1079.1	1075.0	1079.1	1079.8	1086.4	1093.0	1097.2	1108.7	1116.4
12.5°	1041.6	1035.5	1028.6	1026.8	1028.6	1035.5	1041.6	1047.2	1048.6	1061.4	1066.8
15°	978.0	973.2	969.0	972.6	969.0	973.2	978.0	981.6	988.3	997.3	1003.3
17.5°	925.1	921.2	920.5	916.1	920.5	921.2	925.1	927.2	938.1	944.0	954.3
20°	892.0	888.9	890.2	882.3	890.2	888.9	892.0	897.4	908.2	911.2	922.0
22.5°	865.5	859.6	858.9	857.3	858.9	859.6	865.5	870.4	872.5	881.8	889.3
25°	823.9	820.9	818.0	820.9	818.0	820.9	823.9	829.4	831.8	838.4	845.6
27.5°	787.7	784.1	783.3	783.6	783.3	784.1	787.7	787.2	793.7	799.1	804.3
30°	765.5	759.6	760.2	759.6	760.2	759.6	765.5	765.5	769.2	774.0	778.8
32.5°	741.5	737.4	736.6	735.5	736.6	737.4	741.5	740.6	745.1	750.9	756.2
35°	706.0	706.0	702.9	702.9	702.9	706.0	706.0	707.8	712.6	712.6	718.6
37.5°	672.6	672.0	670.2	670.5	670.2	672.0	672.6	674.0	675.7	678.3	682.2
40°	647.6	647.0	645.2	641.6	645.2	647.0	647.6	650.0	651.2	654.2	656.7
42.5°	623.5	621.5	620.6	619.5	620.6	621.5	623.5	625.0	625.7	629.6	634.5
45°	585.6	585.6	584.4	583.8	584.4	585.6	585.6	585.6	586.2	591.0	593.4
47.5°	548.8	549.8	552.1	551.8	552.1	549.8	548.8	547.8	548.0	550.5	553.2
50°	526.6	527.3	529.1	529.7	529.1	527.3	526.6	524.2	523.0	523.0	524.9
52.5°	502.0	505.6	507.8	507.5	507.8	505.6	502.0	500.2	498.0	495.1	497.8
55°	467.6	471.9	476.1	476.7	476.1	471.9	467.6	462.3	459.9	455.0	456.8
57.5°	433.5	439.4	443.9	445.4	443.9	439.4	433.5	427.0	419.3	417.0	413.6
60°	410.5	418.3	423.7	426.1	423.7	418.3	410.5	404.5	394.2	387.6	385.2
62.5°	388.3	397.1	402.5	403.0	402.5	397.1	388.3	378.9	368.7	361.1	356.3
65°	352.0	361.1	366.0	369.5	366.0	361.1	352.0	341.9	330.4	320.2	314.8
67.5°	313.1	322.1	327.4	330.3	327.4	322.1	313.1	300.4	290.0	278.2	271.8
70°	284.7	293.7	301.0	303.4	301.0	293.7	284.7	269.7	260.6	249.8	244.3
72.5°	256.7	264.8	270.6	273.5	270.6	264.8	256.7	242.6	232.2	221.3	214.0
75°	208.2	219.1	224.5	227.5	224.5	219.1	208.2	200.5	188.4	176.9	170.9
77.5°	160.6	170.4	173.7	175.2	173.7	170.4	160.6	151.4	142.3	133.9	128.0
80°	128.8	134.8	139.0	139.6	139.0	134.8	128.8	121.5	114.3	106.6	101.1
82.5°	99.0	104.0	105.3	106.9	105.3	104.0	99.0	92.6	86.4	80.5	76.1
85°	54.1	56.5	57.2	56.5	57.2	56.5	54.1	49.9	46.9	44.0	42.1
87.5°	20.9	20.4	20.5	21.5	20.5	20.4	20.9	19.9	20.2	19.0	17.9
90°	15.3	15.3	16.1	16.1	16.1	15.3	15.3	15.3	13.9	13.3	12.6
92.5°	48.2	46.5	45.6	44.5	45.6	46.5	48.2	57.2	67.5	89.7	123.6
95°	201.5	180.6	175.0	163.8	175.0	180.6	201.5	251.0	309.6	395.3	501.3
97.5°	464.2	425.2	404.9	396.0	404.9	425.2	464.2	507.3	588.7	672.3	746.6
100°	631.0	580.8	555.0	543.9	555.0	580.8	631.0	679.1	751.6	823.4	857.6
102.5°	781.0	745.3	717.3	708.9	717.3	745.3	781.0	832.5	881.5	916.1	894.9
105°	969.1	946.1	932.2	923.8	932.2	946.1	969.1	991.5	999.2	968.5	872.9
107.5°	1048.2	1048.0	1043.5	1037.9	1043.5	1048.0	1048.2	1036.9	1000.5	921.8	794.2
110°	1057.7	1070.9	1075.8	1075.8	1075.8	1070.9	1057.7	1026.3	967.1	868.7	736.3



TEST NUMBER: P333270-940

CATALOG NUMBER: S125DIP-S1090D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1031.4	1054.2	1066.3	1071.4	1066.3	1054.2	1031.4	985.6	915.7	816.3	690.5
115°	967.1	1000.5	1020.0	1029.1	1020.0	1000.5	967.1	912.7	836.7	741.2	633.1
117.5°	895.5	930.1	949.5	955.0	949.5	930.1	895.5	841.2	771.4	689.1	596.0
120°	849.2	882.7	901.5	907.0	901.5	882.7	849.2	797.6	736.3	659.6	575.9
122.5°	810.2	840.9	859.7	864.7	859.7	840.9	810.2	764.2	706.7	638.4	560.9
125°	760.0	788.5	803.9	810.8	803.9	788.5	760.0	720.9	670.7	610.1	539.0
127.5°	722.0	747.3	761.8	764.8	761.8	747.3	722.0	686.6	639.6	583.0	516.7
130°	698.7	721.7	735.6	739.8	735.6	721.7	698.7	663.8	618.4	564.1	502.7
132.5°	674.0	697.1	709.9	714.6	709.9	697.1	674.0	639.2	595.6	546.2	488.7
135°	633.7	656.7	669.3	673.5	669.3	656.7	633.7	603.1	563.4	518.7	470.6
137.5°	592.5	613.4	625.0	629.6	625.0	613.4	592.5	565.0	531.3	494.2	455.3
140°	566.9	585.0	595.4	598.9	595.4	585.0	566.9	541.0	511.8	479.7	446.9
142.5°	542.3	557.7	567.6	570.4	567.6	557.7	542.3	520.4	495.0	467.4	439.7
145°	509.0	520.8	528.5	531.3	528.5	520.8	509.0	492.2	473.4	451.8	430.2
147.5°	482.9	492.4	496.9	498.1	496.9	492.4	482.9	469.7	455.4	438.8	421.2
150°	467.9	476.2	479.0	479.7	479.0	476.2	467.9	457.4	444.8	431.6	416.3
152.5°	455.0	461.7	464.5	465.2	464.5	461.7	455.0	446.2	436.5	424.4	410.6
155°	437.8	442.7	444.8	445.5	444.8	442.7	437.8	430.9	423.2	413.5	402.3
157.5°	422.1	426.1	428.1	427.9	428.1	426.1	422.1	416.7	410.6	403.1	394.0
160°	412.1	415.5	417.0	416.3	417.0	415.5	412.1	407.2	402.3	395.3	388.3
162.5°	402.6	405.5	405.8	405.6	405.8	405.5	402.6	398.8	394.5	388.6	382.2
165°	389.1	390.5	390.5	390.5	390.5	390.5	389.1	386.3	382.8	378.6	373.7
167.5°	375.9	377.2	376.7	376.5	376.7	377.2	375.9	374.5	372.0	368.8	365.6
170°	368.1	368.8	368.8	368.1	368.8	368.8	368.1	366.8	365.3	363.3	361.1
172.5°	360.9	362.1	361.1	360.3	361.1	362.1	360.9	360.6	359.8	358.2	356.1
175°	352.1	352.8	351.4	350.7	351.4	352.8	352.1	352.1	352.1	350.7	350.7
177.5°	347.0	347.5	345.8	345.8	345.8	347.5	347.0	347.5	347.5	347.5	347.0
180°	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8



TEST NUMBER: P333270-940

CATALOG NUMBER: S125DIP-S1090D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1355.8	1361.6	1368.9	1374.1	1383.8	1388.1	1393.4	1397.8	1405.4	1412.6	1421.4
5°	1264.5	1274.7	1288.6	1303.6	1321.1	1333.1	1350.0	1360.2	1380.6	1399.4	1417.4
7.5°	1181.7	1194.2	1213.8	1233.1	1256.0	1276.7	1297.7	1321.1	1347.2	1378.0	1403.6
10°	1124.9	1141.7	1162.8	1186.9	1214.6	1238.6	1266.9	1292.2	1324.1	1360.2	1393.9
12.5°	1079.6	1094.0	1117.5	1140.7	1170.3	1199.6	1228.9	1262.3	1299.6	1339.5	1381.9
15°	1017.2	1029.2	1048.5	1080.3	1110.4	1139.3	1183.3	1214.6	1261.5	1306.0	1357.2
17.5°	963.9	978.7	995.0	1022.3	1053.5	1089.6	1128.8	1168.1	1213.4	1269.8	1327.5
20°	931.0	943.1	961.8	982.8	1015.9	1052.0	1089.4	1129.1	1184.5	1242.9	1304.8
22.5°	895.5	908.5	929.5	952.5	980.3	1014.9	1056.1	1099.7	1157.5	1215.0	1282.2
25°	853.5	862.5	881.7	902.2	929.9	959.4	1002.1	1050.3	1107.4	1173.0	1241.6
27.5°	813.9	821.8	839.4	857.2	882.2	917.2	955.4	1004.1	1057.9	1124.4	1200.5
30°	785.4	793.9	809.5	828.8	852.8	883.5	922.7	968.4	1026.2	1091.2	1170.6
32.5°	760.9	768.3	780.2	799.4	823.0	852.7	888.9	935.7	993.5	1059.4	1137.4
35°	722.8	731.3	740.3	755.4	775.8	804.7	844.5	888.3	943.7	1007.5	1079.1
37.5°	685.0	694.2	702.2	715.8	734.4	759.9	794.2	840.0	890.0	951.5	1020.3
40°	661.5	668.7	675.3	689.7	708.4	732.5	764.4	805.3	858.3	915.4	972.6
42.5°	637.8	644.6	650.2	662.8	680.0	703.1	733.5	773.5	822.6	875.9	926.4
45°	600.7	604.8	611.4	622.3	636.1	657.2	686.7	722.2	763.8	814.3	852.2
47.5°	560.4	567.0	572.5	582.0	593.3	614.0	642.3	672.5	710.2	747.8	774.5
50°	529.7	536.3	544.1	553.1	563.9	583.2	609.1	639.8	671.6	700.5	723.4
52.5°	500.8	506.8	515.2	523.7	537.0	553.3	575.4	602.7	634.1	654.8	673.9
55°	458.0	461.0	470.6	479.1	491.7	503.7	526.0	550.1	569.4	585.1	600.7
57.5°	414.3	418.4	423.9	431.5	444.1	458.2	473.8	495.1	506.4	514.4	526.6
60°	386.4	387.6	391.2	400.2	409.8	422.5	440.6	455.6	464.0	470.6	480.9
62.5°	355.6	355.8	361.9	368.5	375.7	389.3	403.9	416.2	423.1	426.3	436.1
65°	312.4	311.1	314.8	320.2	328.6	337.6	350.3	361.1	360.5	364.1	370.1
67.5°	268.2	267.0	267.0	272.2	279.0	287.1	295.8	302.0	302.1	306.9	310.0
70°	238.4	234.7	237.1	241.4	244.3	251.0	260.6	263.1	263.6	266.0	269.0
72.5°	207.5	206.3	208.2	210.1	212.1	217.3	225.4	226.9	227.0	228.5	233.4
75°	164.9	163.7	162.5	164.3	166.7	170.3	173.3	175.8	175.1	175.8	179.3
77.5°	123.6	120.3	119.7	120.6	121.2	123.4	126.5	126.3	126.9	126.7	130.8
80°	98.1	93.3	92.6	92.6	93.3	94.5	95.7	96.9	95.1	96.9	98.1
82.5°	72.1	69.2	69.1	68.6	68.8	68.9	69.7	70.4	70.1	70.9	71.6
85°	39.7	38.5	36.7	37.9	37.3	35.5	36.7	34.9	34.3	34.9	35.5
87.5°	15.9	16.2	15.0	14.8	14.1	14.4	13.2	12.4	11.6	11.9	13.1
90°	11.9	11.1	9.7	9.1	7.7	7.0	5.6	4.2	2.8	1.4	0.7
92.5°	182.0	224.8	228.4	159.1	95.2	57.2	36.8	24.8	16.1	10.3	8.5
95°	604.5	617.8	504.1	311.7	158.3	83.6	52.3	36.9	29.2	23.7	23.0
97.5°	764.8	659.7	450.1	248.8	136.3	87.0	64.4	50.6	43.0	39.1	38.2
100°	803.9	629.6	401.6	225.9	135.3	94.8	73.9	60.6	53.0	50.2	48.8
102.5°	780.5	576.6	364.8	216.4	140.3	104.3	83.9	71.8	63.6	61.3	60.5
105°	705.6	505.5	329.1	212.7	150.6	119.9	100.4	89.3	82.3	78.8	78.8
107.5°	629.2	456.6	314.1	219.1	165.9	136.3	118.7	107.1	101.4	98.0	96.7
110°	585.7	433.6	309.6	225.2	177.1	148.5	130.4	119.9	113.6	110.8	109.5



TEST NUMBER: P333270-940

CATALOG NUMBER: S125DIP-S1090D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	553.3	420.3	309.6	233.0	187.7	160.2	142.7	132.2	125.9	123.7	122.3
115°	518.0	405.8	311.7	244.7	204.3	178.5	161.0	150.6	144.4	142.2	140.8
117.5°	497.0	398.7	316.3	258.2	221.3	196.9	180.0	168.2	161.9	159.7	157.6
120°	485.3	395.3	320.7	267.1	233.5	209.2	191.7	179.9	173.6	170.9	168.7
122.5°	475.2	392.5	324.6	277.1	245.3	220.9	203.5	190.5	184.2	182.0	180.5
125°	461.5	389.1	331.2	290.7	260.7	237.7	219.6	206.3	200.1	196.6	195.2
127.5°	449.0	387.4	338.6	303.3	275.7	253.5	235.4	221.3	213.4	208.9	206.8
130°	440.7	386.3	343.0	311.7	285.2	263.6	245.4	230.8	221.7	216.2	214.0
132.5°	434.0	386.3	348.0	318.9	294.1	272.5	254.3	239.2	229.0	222.3	219.6
135°	426.0	386.3	354.9	329.1	306.1	284.5	265.6	251.0	239.9	231.5	228.7
137.5°	418.9	387.1	361.1	336.6	314.6	294.9	275.5	261.2	250.0	242.2	240.1
140°	415.5	387.6	363.9	341.6	320.7	300.5	281.7	268.4	257.3	248.9	246.8
142.5°	412.8	388.3	365.6	344.5	324.6	305.5	287.8	275.1	263.9	256.2	254.6
145°	408.6	387.6	367.5	348.6	331.2	313.1	297.0	284.5	274.7	267.7	266.4
147.5°	404.2	385.8	368.1	351.2	335.4	319.5	305.4	294.5	285.4	279.5	278.6
150°	400.9	384.1	368.1	352.8	338.1	322.8	310.9	301.2	292.1	287.2	285.9
152.5°	397.0	381.9	367.6	353.9	340.9	326.7	316.0	306.7	298.8	294.5	293.6
155°	390.5	377.9	366.0	354.9	343.8	331.9	322.1	315.1	308.2	304.0	304.0
157.5°	384.3	373.7	364.3	355.6	346.1	335.9	328.5	322.4	316.4	313.1	313.2
160°	379.3	371.0	362.6	355.6	347.2	338.1	331.9	326.3	321.5	318.6	319.3
162.5°	374.8	367.6	360.9	355.0	348.3	340.4	335.2	330.7	326.5	323.7	324.3
165°	368.1	362.6	358.4	354.2	348.6	343.0	338.9	336.1	332.6	330.5	331.9
167.5°	361.6	357.7	354.5	352.5	348.6	344.0	341.3	339.4	337.4	336.2	336.9
170°	357.7	354.9	352.8	351.4	348.6	345.1	343.0	341.6	340.3	339.6	340.3
172.5°	353.7	351.5	350.5	350.3	348.0	345.1	344.1	343.3	341.9	341.3	342.5
175°	348.6	347.9	347.9	348.6	347.2	345.1	345.1	345.1	344.5	343.8	345.1
177.5°	346.3	345.8	345.8	347.0	346.3	345.3	345.3	345.8	345.3	345.3	346.3
180°	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8



TEST NUMBER: P333270-940

CATALOG NUMBER: S125DIP-S1090D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1425.7	1432.4	1436.7	1444.9	1451.7	1455.5	1458.9	1461.8	1465.2	1468.0	1476.2
5°	1434.9	1450.5	1463.7	1484.2	1502.9	1517.3	1532.9	1546.8	1558.2	1574.5	1587.1
7.5°	1430.8	1458.7	1487.8	1519.5	1551.8	1581.9	1609.6	1635.5	1658.9	1687.4	1712.3
10°	1427.0	1464.9	1502.3	1545.0	1588.9	1626.2	1661.2	1696.7	1722.5	1758.6	1789.3
12.5°	1424.2	1468.7	1513.8	1565.2	1613.5	1666.2	1712.6	1738.6	1777.9	1806.8	1843.3
15°	1411.9	1471.0	1532.9	1590.7	1659.3	1708.1	1749.0	1799.6	1836.3	1872.9	1912.7
17.5°	1390.2	1457.0	1526.3	1602.0	1667.9	1720.2	1773.0	1821.7	1865.5	1914.8	1964.3
20°	1380.1	1446.9	1526.3	1603.9	1668.4	1723.1	1777.3	1830.9	1879.0	1942.2	1999.4
22.5°	1358.9	1439.7	1512.9	1588.6	1654.8	1714.5	1775.8	1836.7	1900.7	1972.0	2043.7
25°	1321.1	1402.9	1480.6	1555.2	1622.0	1696.7	1762.3	1843.5	1925.4	2019.8	2108.9
27.5°	1281.8	1360.2	1431.4	1503.4	1581.4	1665.8	1751.0	1843.2	1950.3	2069.6	2195.2
30°	1250.1	1324.1	1393.3	1467.3	1548.5	1643.7	1737.0	1846.5	1970.5	2104.7	2254.0
32.5°	1213.0	1281.2	1348.5	1426.9	1515.4	1615.8	1724.5	1844.6	1993.6	2146.1	2299.7
35°	1149.6	1206.8	1275.9	1359.6	1459.6	1574.5	1700.2	1842.3	2013.2	2188.3	2317.7
37.5°	1074.3	1127.6	1200.5	1292.2	1397.0	1520.3	1669.6	1838.1	2019.6	2159.3	2201.0
40°	1023.8	1073.1	1149.0	1244.0	1351.2	1481.8	1645.5	1823.6	1999.4	2088.5	2054.1
42.5°	969.8	1021.6	1095.5	1189.6	1304.9	1447.2	1615.2	1793.3	1940.6	1974.3	1855.7
45°	884.8	938.3	1011.1	1106.3	1230.2	1384.3	1559.4	1721.4	1806.2	1745.4	1561.8
47.5°	805.7	855.9	923.4	1021.5	1149.4	1308.8	1477.5	1606.6	1613.4	1468.3	1272.2
50°	751.7	798.1	866.1	964.2	1091.2	1252.5	1404.7	1506.5	1460.7	1296.4	1108.0
52.5°	698.7	744.1	811.2	908.3	1033.8	1181.7	1323.4	1394.7	1308.6	1140.0	979.0
55°	622.3	662.0	727.6	817.3	936.5	1073.7	1194.1	1218.8	1106.8	940.7	810.1
57.5°	547.7	584.8	644.4	727.0	836.0	957.5	1051.7	1046.4	928.1	785.5	681.9
60°	497.1	533.2	586.2	666.8	766.2	870.9	951.5	932.3	814.9	692.1	604.8
62.5°	451.9	484.1	534.2	604.8	695.4	792.4	858.6	830.2	715.2	607.9	539.0
65°	385.2	412.2	455.0	515.2	590.4	670.5	721.7	684.9	586.8	503.2	447.8
67.5°	321.6	343.2	379.1	427.0	491.2	555.5	586.7	549.7	471.3	410.2	369.2
70°	281.1	300.3	328.0	370.8	426.7	480.9	504.4	471.3	403.9	351.5	322.0
72.5°	240.6	256.5	280.8	319.2	364.1	411.1	431.7	400.0	344.6	300.4	272.9
75°	186.0	196.8	213.7	240.1	275.6	313.0	324.4	296.8	261.2	228.1	210.1
77.5°	133.1	142.3	155.1	171.7	196.9	220.6	230.6	214.6	187.2	166.2	151.4
80°	102.3	107.1	118.0	131.8	151.7	166.7	173.3	163.1	143.8	128.2	116.7
82.5°	72.9	77.8	84.3	95.7	108.3	118.6	125.6	118.8	104.9	92.6	86.0
85°	35.5	38.5	42.1	46.9	56.5	62.6	62.0	57.8	52.3	47.5	44.0
87.5°	12.8	13.6	15.2	17.9	19.7	21.8	23.0	22.2	20.5	19.3	17.9
90°	1.4	2.8	4.2	5.6	7.0	7.7	9.1	9.7	11.1	11.9	12.6
92.5°	10.3	16.1	24.8	36.8	57.2	95.2	159.1	228.4	224.8	182.0	123.6
95°	23.7	29.2	36.9	52.3	83.6	158.3	311.7	504.1	617.8	604.5	501.3
97.5°	39.1	43.0	50.6	64.4	87.0	136.3	248.8	450.1	659.7	764.8	746.6
100°	50.2	53.0	60.6	73.9	94.8	135.3	225.9	401.6	629.6	803.9	857.6
102.5°	61.3	63.6	71.8	83.9	104.3	140.3	216.4	364.8	576.6	780.5	894.9
105°	78.8	82.3	89.3	100.4	119.9	150.6	212.7	329.1	505.5	705.6	872.9
107.5°	98.0	101.4	107.1	118.7	136.3	165.9	219.1	314.1	456.6	629.2	794.2
110°	110.8	113.6	119.9	130.4	148.5	177.1	225.2	309.6	433.6	585.7	736.3



TEST NUMBER: P333270-940

CATALOG NUMBER: S125DIP-S1090D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	123.7	125.9	132.2	142.7	160.2	187.7	233.0	309.6	420.3	553.3	690.5
115°	142.2	144.4	150.6	161.0	178.5	204.3	244.7	311.7	405.8	518.0	633.1
117.5°	159.7	161.9	168.2	180.0	196.9	221.3	258.2	316.3	398.7	497.0	596.0
120°	170.9	173.6	179.9	191.7	209.2	233.5	267.1	320.7	395.3	485.3	575.9
122.5°	182.0	184.2	190.5	203.5	220.9	245.3	277.1	324.6	392.5	475.2	560.9
125°	196.6	200.1	206.3	219.6	237.7	260.7	290.7	331.2	389.1	461.5	539.0
127.5°	208.9	213.4	221.3	235.4	253.5	275.7	303.3	338.6	387.4	449.0	516.7
130°	216.2	221.7	230.8	245.4	263.6	285.2	311.7	343.0	386.3	440.7	502.7
132.5°	222.3	229.0	239.2	254.3	272.5	294.1	318.9	348.0	386.3	434.0	488.7
135°	231.5	239.9	251.0	265.6	284.5	306.1	329.1	354.9	386.3	426.0	470.6
137.5°	242.2	250.0	261.2	275.5	294.9	314.6	336.6	361.1	387.1	418.9	455.3
140°	248.9	257.3	268.4	281.7	300.5	320.7	341.6	363.9	387.6	415.5	446.9
142.5°	256.2	263.9	275.1	287.8	305.5	324.6	344.5	365.6	388.3	412.8	439.7
145°	267.7	274.7	284.5	297.0	313.1	331.2	348.6	367.5	387.6	408.6	430.2
147.5°	279.5	285.4	294.5	305.4	319.5	335.4	351.2	368.1	385.8	404.2	421.2
150°	287.2	292.1	301.2	310.9	322.8	338.1	352.8	368.1	384.1	400.9	416.3
152.5°	294.5	298.8	306.7	316.0	326.7	340.9	353.9	367.6	381.9	397.0	410.6
155°	304.0	308.2	315.1	322.1	331.9	343.8	354.9	366.0	377.9	390.5	402.3
157.5°	313.1	316.4	322.4	328.5	335.9	346.1	355.6	364.3	373.7	384.3	394.0
160°	318.6	321.5	326.3	331.9	338.1	347.2	355.6	362.6	371.0	379.3	388.3
162.5°	323.7	326.5	330.7	335.2	340.4	348.3	355.0	360.9	367.6	374.8	382.2
165°	330.5	332.6	336.1	338.9	343.0	348.6	354.2	358.4	362.6	368.1	373.7
167.5°	336.2	337.4	339.4	341.3	344.0	348.6	352.5	354.5	357.7	361.6	365.6
170°	339.6	340.3	341.6	343.0	345.1	348.6	351.4	352.8	354.9	357.7	361.1
172.5°	341.3	341.9	343.3	344.1	345.1	348.0	350.3	350.5	351.5	353.7	356.1
175°	343.8	344.5	345.1	345.1	345.1	347.2	348.6	347.9	347.9	348.6	350.7
177.5°	345.3	345.3	345.8	345.3	345.3	346.3	347.0	345.8	345.8	346.3	347.0
180°	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8



TEST NUMBER: P333270-940

CATALOG NUMBER: S125DIP-S1090D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0	1418.0
2.5°	1483.0	1486.8	1495.0	1492.1	1496.0	1497.9	1499.9
5°	1602.8	1622.0	1630.4	1629.2	1641.9	1638.9	1635.8
7.5°	1738.0	1758.3	1769.6	1783.7	1791.9	1792.4	1799.6
10°	1814.6	1841.1	1851.9	1867.0	1876.6	1882.0	1881.4
12.5°	1873.4	1894.1	1918.3	1925.7	1938.8	1945.5	1943.0
15°	1944.0	1977.1	2002.4	2015.0	2031.3	2036.1	2042.7
17.5°	2007.1	2051.5	2081.0	2120.2	2135.0	2144.0	2138.8
20°	2054.8	2113.2	2142.6	2189.6	2215.5	2229.3	2224.5
22.5°	2111.1	2174.3	2228.8	2269.5	2308.8	2327.5	2331.4
25°	2207.6	2294.3	2374.4	2428.0	2476.6	2488.1	2513.4
27.5°	2315.5	2417.7	2503.3	2559.6	2593.5	2606.3	2614.2
30°	2383.4	2485.1	2549.5	2585.6	2596.4	2595.2	2594.0
32.5°	2416.6	2480.3	2492.7	2482.5	2457.7	2436.8	2414.9
35°	2369.5	2322.0	2250.9	2159.5	2092.0	2024.1	2017.4
37.5°	2131.1	1979.1	1860.8	1728.8	1652.6	1605.5	1573.1
40°	1906.7	1733.9	1590.7	1479.3	1401.8	1371.0	1341.0
42.5°	1663.0	1498.1	1371.2	1278.1	1219.8	1185.7	1161.8
45°	1351.2	1205.5	1106.3	1038.8	992.5	966.0	950.9
47.5°	1107.1	999.4	915.1	866.5	834.5	813.9	814.0
50°	976.2	873.3	817.3	778.8	751.1	734.9	737.9
52.5°	860.1	783.3	735.5	703.2	682.8	672.8	672.4
55°	719.3	663.9	632.6	609.1	595.2	583.8	586.2
57.5°	615.2	568.6	547.6	528.1	518.4	513.9	507.2
60°	550.7	514.6	496.5	480.9	471.3	467.6	461.0
62.5°	493.4	465.0	447.5	434.6	426.0	424.8	419.6
65°	414.6	393.0	377.4	371.3	362.3	359.9	359.9
67.5°	341.9	326.4	314.1	308.6	304.7	305.2	302.4
70°	296.1	283.5	275.6	269.7	266.6	267.2	264.8
72.5°	259.0	245.0	238.1	234.5	230.5	232.1	231.1
75°	196.2	189.0	185.4	181.7	179.3	178.2	176.9
77.5°	144.1	137.7	134.9	132.9	133.2	130.4	132.7
80°	111.4	105.9	104.2	101.1	100.5	100.5	99.9
82.5°	81.5	78.5	77.1	74.6	73.6	74.5	72.9
85°	42.1	39.7	39.1	39.1	37.9	36.7	39.7
87.5°	18.0	16.2	16.6	16.1	16.1	15.7	14.8
90°	13.3	13.9	15.3	15.3	15.3	16.1	16.1
92.5°	89.7	67.5	57.2	48.2	46.5	45.6	44.5
95°	395.3	309.6	251.0	201.5	180.6	175.0	163.8
97.5°	672.3	588.7	507.3	464.2	425.2	404.9	396.0
100°	823.4	751.6	679.1	631.0	580.8	555.0	543.9
102.5°	916.1	881.5	832.5	781.0	745.3	717.3	708.9
105°	968.5	999.2	991.5	969.1	946.1	932.2	923.8
107.5°	921.8	1000.5	1036.9	1048.2	1048.0	1043.5	1037.9
110°	868.7	967.1	1026.3	1057.7	1070.9	1075.8	1075.8



TEST NUMBER: P333270-940

CATALOG NUMBER: S125DIP-S1090D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	816.3	915.7	985.6	1031.4	1054.2	1066.3	1071.4
115°	741.2	836.7	912.7	967.1	1000.5	1020.0	1029.1
117.5°	689.1	771.4	841.2	895.5	930.1	949.5	955.0
120°	659.6	736.3	797.6	849.2	882.7	901.5	907.0
122.5°	638.4	706.7	764.2	810.2	840.9	859.7	864.7
125°	610.1	670.7	720.9	760.0	788.5	803.9	810.8
127.5°	583.0	639.6	686.6	722.0	747.3	761.8	764.8
130°	564.1	618.4	663.8	698.7	721.7	735.6	739.8
132.5°	546.2	595.6	639.2	674.0	697.1	709.9	714.6
135°	518.7	563.4	603.1	633.7	656.7	669.3	673.5
137.5°	494.2	531.3	565.0	592.5	613.4	625.0	629.6
140°	479.7	511.8	541.0	566.9	585.0	595.4	598.9
142.5°	467.4	495.0	520.4	542.3	557.7	567.6	570.4
145°	451.8	473.4	492.2	509.0	520.8	528.5	531.3
147.5°	438.8	455.4	469.7	482.9	492.4	496.9	498.1
150°	431.6	444.8	457.4	467.9	476.2	479.0	479.7
152.5°	424.4	436.5	446.2	455.0	461.7	464.5	465.2
155°	413.5	423.2	430.9	437.8	442.7	444.8	445.5
157.5°	403.1	410.6	416.7	422.1	426.1	428.1	427.9
160°	395.3	402.3	407.2	412.1	415.5	417.0	416.3
162.5°	388.6	394.5	398.8	402.6	405.5	405.8	405.6
165°	378.6	382.8	386.3	389.1	390.5	390.5	390.5
167.5°	368.8	372.0	374.5	375.9	377.2	376.7	376.5
170°	363.3	365.3	366.8	368.1	368.8	368.8	368.1
172.5°	358.2	359.8	360.6	360.9	362.1	361.1	360.3
175°	350.7	352.1	352.1	352.1	352.8	351.4	350.7
177.5°	347.5	347.5	347.5	347.0	347.5	345.8	345.8
180°	345.8	345.8	345.8	345.8	345.8	345.8	345.8

(END OF REPORT)