

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333333-940

Luminaire Tested: **S125DIP-S1270D1205U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333333-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1270D1205U940-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8478.1 lumens
Efficiency: N/A
Efficacy: 118.2 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333333-940
CATALOG NUMBER: S125DIP-S1270D1205U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333333-940

CATALOG NUMBER: S125DIP-S1270D1205U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	55
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	51	46
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	48	45	44	39
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	40	37	33
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32	29
5	69	58	50	44	64	54	47	42	47	41	37	40	36	33	34	31	28	25
6	64	52	44	38	59	49	41	36	42	37	32	37	32	29	31	28	25	22
7	59	47	39	33	55	44	37	32	38	33	29	33	29	25	28	25	22	20
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	22	20	18
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	24	20	18	16
10	48	36	28	24	44	34	27	23	30	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10577	10577	10577	10577
5°	12248	10613	9292	10613
10°	14250	10558	8141	10558
15°	15774	10480	7511	10480
20°	17657	10357	7003	10357
25°	20685	10219	6757	10219
30°	22342	10082	6542	10082
35°	18370	9826	6401	9826
40°	13057	9470	6247	9470
45°	10030	8990	6158	8990
50°	8562	8395	6146	8395
55°	7624	7812	6199	7812
60°	6877	7174	6356	7174
65°	6353	6533	6522	6533
70°	5776	5867	6617	5867
75°	5100	5168	6558	5168
80°	4292	4214	5995	4214
85°	3394	3038	4846	3038



TEST NUMBER: P333333-940

CATALOG NUMBER: S125DIP-S1270D1205U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.7	1.9
10°-20°	469.4	5.5
20°-30°	762.2	9.0
30°-40°	929.8	11.0
40°-50°	845.8	10.0
50°-60°	673.7	7.9
60°-70°	469.3	5.5
70°-80°	250.2	3.0
80°-90°	66.0	0.8
90°-100°	372.5	4.4
100°-110°	800.8	9.4
110°-120°	751.5	8.9
120°-130°	609.1	7.2
130°-140°	488.8	5.8
140°-150°	368.8	4.4
150°-160°	259.6	3.1
160°-170°	153.0	1.8
170°-180°	49.8	0.6
0°-30°	1389.3	16.4
0°-40°	2319.0	27.4
0°-60°	3838.6	45.3
0°-90°	4624.1	54.5
90°-120°	1924.8	22.7
90°-150°	3391.5	40.0
90°-180°	3854.0	45.5
0°-180°	8478.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1638	1638	1638	1638	1638	
5°	1889	1637	1433	1637	1889	190
15°	2359	1567	1123	1567	2359	675
25°	2903	1434	948	1434	2903	1326
35°	2330	1246	812	1246	2330	1426
45°	1098	984	674	984	1098	879
55°	677	694	550	694	677	610
65°	416	428	427	428	416	413
75°	204	207	263	207	204	220
85°	46	41	65	41	46	54
90°	24	1	24	1	24	18
95°	244	34	244	34	244	345
105°	1373	117	1373	117	1373	1365
115°	1529	209	1529	209	1529	1494
125°	1205	290	1205	290	1205	1090
135°	1001	340	1001	340	1001	776
145°	790	396	790	396	790	502
155°	662	452	662	452	662	309
165°	580	493	580	493	580	166
175°	521	513	521	513	521	51
180°	514	514	514	514	514	



TEST NUMBER: P333333-940

CATALOG NUMBER: S125DIP-S1270D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7
2.5°	1732.2	1730.0	1727.8	1723.3	1726.6	1717.2	1712.7	1705.0	1695.5	1692.2	1688.3
5°	1889.3	1892.7	1896.2	1881.7	1883.0	1873.3	1851.1	1833.0	1818.4	1799.7	1786.5
7.5°	2078.4	2070.2	2069.5	2060.0	2043.8	2030.7	2007.3	1977.5	1948.8	1916.0	1888.9
10°	2172.9	2173.6	2167.4	2156.2	2138.9	2126.4	2095.8	2066.5	2031.1	1989.4	1959.5
12.5°	2244.1	2247.0	2239.1	2224.1	2215.5	2187.5	2163.6	2128.9	2086.7	2053.3	2007.9
15°	2359.2	2351.5	2346.0	2327.2	2312.7	2283.4	2245.2	2209.0	2163.2	2120.8	2078.4
17.5°	2470.1	2476.3	2465.8	2448.7	2403.4	2369.4	2318.1	2268.5	2211.4	2154.6	2104.0
20°	2569.1	2574.7	2558.7	2528.8	2474.6	2440.5	2373.1	2309.2	2243.1	2170.2	2114.5
22.5°	2692.6	2688.2	2666.6	2621.1	2574.1	2511.1	2438.2	2360.3	2277.6	2195.1	2121.2
25°	2902.8	2873.5	2860.3	2804.1	2742.2	2649.7	2549.7	2435.6	2332.8	2223.7	2129.1
27.5°	3019.2	3010.1	2995.3	2956.2	2891.1	2792.2	2674.2	2535.3	2390.2	2252.5	2128.7
30°	2995.9	2997.3	2998.7	2986.2	2944.5	2870.1	2752.6	2603.2	2430.8	2275.8	2132.6
32.5°	2789.1	2814.3	2838.6	2867.2	2878.9	2864.5	2791.0	2656.0	2478.6	2302.5	2130.4
35°	2330.0	2337.6	2416.2	2494.0	2599.7	2681.7	2736.7	2676.8	2527.4	2325.1	2127.7
37.5°	1816.8	1854.3	1908.6	1996.6	2149.1	2285.6	2461.2	2542.0	2493.8	2332.5	2122.9
40°	1548.7	1583.5	1618.9	1708.6	1837.2	2002.6	2202.1	2372.4	2412.0	2309.2	2106.2
42.5°	1341.8	1369.4	1408.7	1476.1	1583.6	1730.1	1920.7	2143.3	2280.2	2241.3	2071.2
45°	1098.2	1115.6	1146.2	1199.8	1277.6	1392.3	1560.5	1803.8	2015.8	2086.0	1988.0
47.5°	940.0	940.0	963.7	1000.7	1056.9	1154.3	1278.7	1469.4	1695.8	1863.3	1855.6
50°	852.2	848.7	867.5	899.5	944.0	1008.6	1127.5	1279.7	1497.3	1687.0	1739.8
52.5°	776.6	776.9	788.5	812.2	849.4	904.6	993.5	1130.7	1316.5	1511.3	1610.9
55°	677.1	674.2	687.4	703.5	730.6	766.7	830.6	935.6	1086.5	1278.3	1407.6
57.5°	585.9	593.5	598.8	609.9	632.4	656.6	710.5	787.6	907.2	1071.8	1208.5
60°	532.4	540.1	544.3	555.4	573.5	594.3	636.1	698.6	799.4	941.2	1076.7
62.5°	484.6	490.6	492.0	502.0	516.7	537.1	569.9	622.4	702.0	826.1	958.9
65°	415.7	415.7	418.5	428.9	435.9	453.9	478.9	517.2	581.1	677.7	791.0
67.5°	349.2	352.6	351.9	356.4	362.8	376.9	394.8	426.4	473.8	544.3	634.9
70°	305.9	308.6	307.9	311.4	318.3	327.4	342.0	371.8	405.9	466.5	544.3
72.5°	266.9	268.0	266.3	270.8	275.0	282.9	299.2	315.1	347.0	398.1	462.0
75°	204.4	205.7	207.1	209.9	214.1	218.3	226.6	242.6	263.4	301.7	342.7
77.5°	153.2	150.5	153.9	153.5	155.9	159.1	166.4	174.9	192.0	216.2	247.9
80°	115.4	116.1	116.1	116.8	120.3	122.3	128.6	134.8	148.0	166.1	188.4
82.5°	84.3	86.1	85.0	86.2	89.1	90.6	94.1	99.2	106.9	121.1	137.2
85°	45.8	42.4	43.8	45.2	45.2	45.8	48.7	50.7	54.9	60.5	66.7
87.5°	18.1	19.3	19.6	19.6	20.2	19.7	21.8	21.5	23.0	24.4	26.2
90°	23.8	23.8	22.8	22.8	22.8	20.7	19.7	18.6	17.7	16.6	14.5
92.5°	66.1	67.8	69.2	71.7	85.0	100.3	133.2	183.6	270.5	334.0	339.5
95°	243.5	260.1	268.3	299.4	373.0	460.0	587.5	744.9	898.3	918.0	749.1
97.5°	588.5	601.8	631.9	689.8	753.9	874.9	999.1	1109.5	1136.7	980.3	669.0
100°	808.2	824.7	863.1	937.7	1009.1	1117.0	1223.7	1274.4	1194.6	935.6	596.8
102.5°	1053.6	1066.0	1107.6	1160.7	1237.2	1310.1	1361.3	1330.0	1159.8	856.8	542.1
105°	1372.9	1385.3	1406.0	1440.2	1473.4	1484.8	1439.2	1297.3	1048.6	751.2	489.0
107.5°	1542.4	1550.7	1557.6	1557.7	1541.0	1486.8	1369.8	1180.4	935.0	678.4	466.6
110°	1598.7	1598.7	1591.5	1571.8	1525.2	1437.1	1291.0	1094.1	870.3	644.4	460.0



TEST NUMBER: P333333-940

CATALOG NUMBER: S125DIP-S1270D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1592.1	1584.7	1566.6	1532.9	1464.6	1360.8	1213.1	1026.2	822.2	624.6	460.0
115°	1529.3	1515.8	1486.8	1437.1	1356.3	1243.3	1101.4	940.8	769.8	603.1	463.2
117.5°	1419.2	1411.0	1382.2	1330.8	1250.0	1146.4	1024.1	885.6	738.5	592.5	470.0
120°	1348.0	1339.7	1311.7	1262.0	1185.4	1094.1	980.2	855.9	721.1	587.5	476.6
122.5°	1285.0	1277.6	1249.6	1204.0	1135.6	1050.3	948.7	833.5	706.2	583.4	482.4
125°	1205.1	1194.6	1171.9	1129.4	1071.4	996.8	906.6	800.9	685.9	578.2	492.1
127.5°	1136.7	1132.1	1110.5	1073.0	1020.4	950.6	866.4	767.8	667.3	575.7	503.1
130°	1099.3	1093.1	1072.4	1038.2	986.4	919.1	838.2	747.1	654.9	574.0	509.8
132.5°	1062.0	1055.0	1035.9	1001.7	949.9	885.0	811.7	726.3	644.9	574.0	517.2
135°	1000.9	994.7	976.1	941.8	896.3	837.2	770.9	699.4	633.1	574.0	527.4
137.5°	935.6	928.8	911.6	880.5	839.7	789.5	734.4	676.6	622.5	575.2	536.7
140°	890.0	884.8	869.3	842.4	804.1	760.5	712.8	664.1	617.5	576.0	540.8
142.5°	847.7	843.4	828.7	805.9	773.4	735.7	694.6	653.4	613.4	576.9	543.3
145°	789.5	785.4	774.0	756.3	731.5	703.6	671.4	639.3	607.2	576.0	546.1
147.5°	740.2	738.3	731.7	717.6	697.9	676.8	652.1	626.1	600.7	573.4	547.1
150°	712.8	711.9	707.7	695.3	679.7	661.0	641.4	618.6	595.8	570.9	547.1
152.5°	691.3	690.3	686.1	676.2	663.2	648.6	630.6	610.3	590.0	567.6	546.3
155°	662.1	661.0	657.9	650.7	640.3	628.9	614.4	597.8	580.2	561.6	543.9
157.5°	636.0	636.1	633.3	627.2	619.2	610.3	599.1	585.4	571.1	555.4	541.3
160°	618.6	619.6	617.5	612.3	605.1	597.8	587.5	577.1	563.7	551.3	538.8
162.5°	602.8	603.1	602.6	598.2	592.6	586.2	577.6	568.0	557.1	546.3	536.3
165°	580.2	580.2	580.2	578.2	574.0	568.8	562.6	555.4	547.1	538.8	532.5
167.5°	559.5	559.7	560.5	558.7	556.6	552.9	548.1	543.3	537.3	531.5	526.7
170°	547.1	548.1	548.1	547.1	545.0	543.0	539.8	536.7	531.5	527.4	524.3
172.5°	535.5	536.5	538.1	536.3	535.9	534.7	532.4	529.2	525.8	522.5	520.9
175°	521.2	522.2	524.3	523.3	523.3	523.3	521.2	521.2	518.1	517.0	517.0
177.5°	513.9	513.9	516.4	515.6	516.4	516.4	516.4	515.6	514.8	513.9	513.9
180°	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9



TEST NUMBER: P333333-940

CATALOG NUMBER: S125DIP-S1270D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7
2.5°	1685.0	1681.1	1676.6	1668.8	1659.4	1654.4	1646.5	1641.6	1631.6	1623.2	1614.4
5°	1770.4	1752.4	1735.7	1714.1	1690.5	1675.2	1657.2	1637.0	1616.1	1594.6	1570.9
7.5°	1859.0	1827.0	1792.2	1754.9	1718.3	1684.6	1652.5	1621.0	1591.5	1555.9	1525.8
10°	1918.5	1878.2	1835.1	1784.3	1735.0	1691.9	1648.1	1609.9	1570.9	1529.2	1492.4
12.5°	1978.0	1924.3	1863.4	1807.7	1748.4	1696.3	1644.8	1596.0	1547.0	1500.8	1457.9
15°	2020.0	1972.7	1916.4	1837.2	1770.4	1698.9	1630.8	1567.4	1508.4	1457.0	1402.8
17.5°	2047.6	1986.7	1926.3	1850.2	1762.8	1682.7	1605.5	1533.1	1466.5	1401.3	1349.1
20°	2052.6	1990.1	1926.8	1852.4	1762.8	1671.1	1593.8	1507.0	1435.4	1368.0	1304.0
22.5°	2051.0	1980.0	1911.3	1834.7	1747.2	1662.7	1569.4	1480.9	1403.1	1336.9	1270.1
25°	2035.2	1959.5	1873.3	1796.2	1709.9	1620.3	1525.8	1434.0	1354.8	1279.0	1213.0
27.5°	2022.2	1924.0	1826.3	1736.3	1653.1	1570.9	1480.4	1386.4	1298.6	1221.8	1159.6
30°	2006.1	1898.4	1788.5	1694.7	1609.2	1529.2	1443.8	1352.0	1260.3	1185.2	1118.5
32.5°	1991.6	1866.1	1750.2	1648.0	1557.5	1479.7	1400.9	1313.6	1223.5	1147.4	1080.6
35°	1963.7	1818.4	1685.6	1570.2	1473.6	1393.7	1327.7	1246.3	1163.6	1089.9	1026.0
37.5°	1928.2	1755.9	1613.4	1492.4	1386.4	1302.3	1240.7	1178.3	1098.9	1028.0	970.1
40°	1900.4	1711.4	1560.5	1436.8	1327.0	1239.4	1182.4	1123.3	1057.3	991.2	930.1
42.5°	1865.4	1671.3	1507.2	1373.9	1265.2	1179.9	1120.1	1069.9	1011.6	950.1	893.3
45°	1801.0	1598.7	1420.8	1277.6	1167.8	1083.7	1021.8	984.3	940.5	882.1	834.1
47.5°	1706.4	1511.5	1327.5	1179.7	1066.4	988.5	930.5	894.5	863.6	820.2	776.7
50°	1622.4	1446.5	1260.3	1113.6	1000.2	921.7	868.2	835.5	809.1	775.7	738.9
52.5°	1528.4	1364.8	1194.1	1049.1	936.8	859.4	807.0	778.3	756.3	732.4	696.1
55°	1379.1	1240.1	1081.6	944.0	840.3	764.6	718.7	693.8	675.6	657.5	635.3
57.5°	1214.6	1105.9	965.5	839.7	744.3	675.4	632.6	608.2	594.1	584.9	571.8
60°	1098.9	1005.8	884.8	770.2	677.1	615.9	574.2	555.4	543.6	535.9	526.2
62.5°	991.7	915.2	803.2	698.5	617.0	559.1	521.9	503.6	492.4	488.7	480.6
65°	833.4	774.4	681.9	595.0	525.5	476.2	444.9	427.5	420.5	416.3	417.1
67.5°	677.6	641.6	567.3	493.2	437.7	396.4	371.3	358.0	354.5	348.9	348.8
70°	582.5	555.4	492.8	428.2	378.8	346.9	324.6	310.7	307.2	304.4	303.8
72.5°	498.6	474.7	420.5	368.7	324.3	296.2	277.9	269.6	263.9	262.2	262.1
75°	374.7	361.5	318.3	277.3	246.7	227.3	214.8	207.1	203.0	202.2	203.0
77.5°	266.4	254.9	227.5	198.4	179.1	164.3	153.7	151.1	146.4	146.5	145.8
80°	200.2	192.5	175.1	152.2	136.3	123.8	118.2	113.3	111.9	109.9	111.9
82.5°	145.2	137.0	125.1	110.5	97.3	89.8	84.3	82.8	81.9	80.9	81.3
85°	71.6	72.3	65.4	54.2	48.7	44.5	41.0	41.0	40.3	39.6	40.3
87.5°	27.2	25.6	23.2	21.1	17.9	15.9	14.9	15.2	13.7	13.6	14.6
90°	13.5	11.4	10.3	8.3	6.2	4.1	2.1	1.1	2.1	4.1	6.2
92.5°	236.5	141.5	85.0	54.8	36.9	24.1	15.3	12.7	15.3	24.1	36.9
95°	463.2	235.2	124.3	77.7	54.9	43.5	35.2	34.2	35.2	43.5	54.9
97.5°	369.7	202.7	129.3	95.8	75.3	63.8	58.1	56.8	58.1	63.8	75.3
100°	335.7	201.0	140.9	109.9	90.2	78.7	74.6	72.5	74.6	78.7	90.2
102.5°	321.6	208.5	155.0	124.8	106.7	94.5	91.2	90.0	91.2	94.5	106.7
105°	316.0	223.8	178.3	149.2	132.6	122.3	117.1	117.1	117.1	122.3	132.6
107.5°	325.6	246.6	202.4	176.4	159.2	150.6	145.7	143.6	145.7	150.6	159.2
110°	334.7	263.1	220.7	193.8	178.3	168.9	164.8	162.6	164.8	168.9	178.3



TEST NUMBER: P333333-940

CATALOG NUMBER: S125DIP-S1270D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	346.3	278.9	238.1	212.0	196.4	187.1	183.8	181.7	183.8	187.1	196.4
115°	363.6	303.6	265.3	239.3	223.8	214.5	211.3	209.3	211.3	214.5	223.8
117.5°	383.6	328.9	292.6	267.5	249.9	240.6	237.3	234.2	237.3	240.6	249.9
120°	396.8	347.1	310.9	284.9	267.3	258.0	253.9	250.7	253.9	258.0	267.3
122.5°	411.8	364.5	328.2	302.4	283.0	273.8	270.5	268.1	270.5	273.8	283.0
125°	432.0	387.5	353.3	326.4	306.7	297.4	292.2	290.1	292.2	297.4	306.7
127.5°	450.8	409.7	376.7	349.8	328.9	317.1	310.4	307.3	310.4	317.1	328.9
130°	463.2	423.7	391.6	364.7	343.0	329.5	321.2	318.1	321.2	329.5	343.0
132.5°	473.9	437.0	404.9	378.0	355.4	340.3	330.3	326.4	330.3	340.3	355.4
135°	489.0	454.9	422.8	394.8	373.0	356.4	344.0	339.8	344.0	356.4	373.0
137.5°	500.2	467.5	438.3	409.5	388.2	371.6	360.0	356.9	360.0	371.6	388.2
140°	507.7	476.6	446.6	418.6	399.0	382.4	369.9	366.8	369.9	382.4	399.0
142.5°	511.8	482.4	454.1	427.8	408.8	392.3	380.7	378.4	380.7	392.3	408.8
145°	518.1	492.1	465.2	441.4	422.8	408.2	397.9	395.8	397.9	408.2	422.8
147.5°	521.8	498.4	474.7	453.8	437.7	424.2	415.3	414.0	415.3	424.2	437.7
150°	524.3	502.5	479.7	462.1	447.6	434.2	426.9	424.8	426.9	434.2	447.6
152.5°	525.9	506.7	485.5	469.6	455.9	444.1	437.7	436.4	437.7	444.1	455.9
155°	527.4	510.8	493.2	478.7	468.3	458.0	451.7	451.7	451.7	458.0	468.3
157.5°	528.4	514.3	499.2	488.2	479.1	470.2	465.2	465.5	465.2	470.2	479.1
160°	528.4	516.0	502.5	493.2	484.9	477.7	473.5	474.6	473.5	477.7	484.9
162.5°	527.6	517.6	505.9	498.2	491.5	485.1	481.0	482.0	481.0	485.1	491.5
165°	526.4	518.1	509.8	503.5	499.4	494.3	491.2	493.2	491.2	494.3	499.4
167.5°	523.9	518.1	511.2	507.3	504.4	501.5	499.6	500.7	499.6	501.5	504.4
170°	522.2	518.1	512.9	509.8	507.7	505.6	504.6	505.6	504.6	505.6	507.7
172.5°	520.6	517.2	512.9	511.4	510.1	508.1	507.1	509.0	507.1	508.1	510.1
175°	518.1	516.0	512.9	512.9	512.9	511.8	510.8	512.9	510.8	511.8	512.9
177.5°	515.6	514.8	513.1	513.1	513.9	513.1	513.1	514.8	513.1	513.1	513.9
180°	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9



TEST NUMBER: P333333-940

CATALOG NUMBER: S125DIP-S1270D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7
2.5°	1609.3	1603.2	1598.2	1587.1	1580.9	1572.6	1565.9	1573.2	1565.4	1568.7	1563.7
5°	1559.2	1539.6	1525.8	1505.6	1488.3	1472.2	1460.4	1458.3	1452.8	1450.0	1441.6
7.5°	1498.8	1474.4	1450.5	1424.2	1401.9	1379.2	1364.8	1352.8	1344.9	1334.4	1327.4
10°	1463.2	1430.6	1402.8	1370.7	1342.9	1318.7	1299.1	1289.4	1280.4	1267.2	1262.3
12.5°	1419.2	1385.5	1351.6	1317.4	1290.7	1263.6	1246.9	1232.2	1225.9	1211.0	1209.5
15°	1366.5	1315.8	1282.5	1247.7	1210.9	1188.7	1174.7	1158.8	1151.8	1141.4	1133.7
17.5°	1303.8	1258.4	1216.7	1180.7	1149.1	1130.4	1113.1	1102.2	1090.2	1083.4	1070.9
20°	1258.1	1215.0	1173.3	1135.1	1110.8	1089.2	1075.3	1064.9	1052.4	1048.9	1036.4
22.5°	1219.8	1172.2	1132.2	1100.1	1073.5	1049.2	1034.2	1027.1	1018.5	1007.8	1005.2
25°	1157.4	1108.0	1074.0	1042.0	1018.3	996.1	985.7	976.6	968.3	960.6	957.9
27.5°	1103.4	1059.4	1018.9	990.0	969.4	949.1	940.0	929.0	922.8	916.7	909.2
30°	1065.6	1020.4	985.0	957.2	935.0	916.9	907.1	899.5	893.9	888.3	884.2
32.5°	1026.7	984.8	950.5	923.3	901.0	887.3	878.8	873.3	867.2	860.5	855.2
35°	975.3	929.3	896.0	872.4	855.0	844.5	834.8	829.9	823.0	823.0	817.4
37.5°	917.3	877.6	848.2	826.6	811.0	801.7	791.2	787.8	783.4	780.4	778.6
40°	882.8	846.0	818.1	796.6	779.9	772.2	763.9	758.4	755.5	752.1	750.7
42.5°	847.2	812.0	785.3	765.4	751.0	744.5	736.6	732.8	727.2	722.6	721.8
45°	793.1	759.0	734.8	718.7	706.2	698.6	693.8	685.4	682.6	677.1	676.4
47.5°	741.8	709.2	685.3	672.2	661.2	655.0	647.3	638.9	635.8	632.9	632.7
50°	703.5	673.6	651.3	638.8	628.4	619.4	611.7	606.1	604.0	604.0	605.5
52.5°	664.5	639.1	620.2	604.8	595.0	585.4	578.4	575.0	571.8	575.2	577.7
55°	607.5	581.8	567.9	553.3	543.6	532.4	529.0	527.6	525.5	531.1	533.9
57.5°	547.2	529.1	512.8	498.4	489.6	483.2	478.5	477.7	481.6	484.2	493.2
60°	508.8	487.9	473.4	462.3	451.8	447.6	446.3	444.9	447.6	455.3	467.1
62.5°	466.5	449.6	433.9	425.5	417.9	411.0	410.6	411.5	417.1	425.8	437.7
65°	404.6	389.9	379.5	369.8	363.6	359.4	360.8	363.6	369.8	381.7	394.8
67.5°	341.6	331.5	322.3	314.3	308.4	308.4	309.8	313.9	321.3	334.9	347.0
70°	301.0	289.9	282.2	278.7	273.8	271.1	275.3	282.2	288.5	301.0	311.4
72.5°	260.4	250.9	245.0	242.6	240.5	238.3	239.7	247.2	255.7	268.1	280.3
75°	200.2	196.7	192.5	189.8	187.7	189.0	190.5	197.4	204.4	217.6	231.5
77.5°	146.2	142.5	140.0	139.3	138.2	138.8	142.8	147.9	154.7	164.3	174.9
80°	110.5	109.1	107.7	107.0	107.0	107.7	113.3	116.8	123.1	132.1	140.4
82.5°	80.5	79.6	79.4	79.3	79.8	79.9	83.3	87.8	93.0	99.8	107.0
85°	42.4	41.0	43.1	43.8	42.4	44.5	45.8	48.7	50.7	54.2	57.7
87.5°	15.5	17.1	16.8	17.7	17.9	19.4	19.1	21.5	22.8	24.2	24.0
90°	8.3	10.3	11.4	13.5	14.5	16.6	17.7	18.6	19.7	20.7	22.8
92.5°	54.8	85.0	141.5	236.5	339.5	334.0	270.5	183.6	133.2	100.3	85.0
95°	77.7	124.3	235.2	463.2	749.1	918.0	898.3	744.9	587.5	460.0	373.0
97.5°	95.8	129.3	202.7	369.7	669.0	980.3	1136.7	1109.5	999.1	874.9	753.9
100°	109.9	140.9	201.0	335.7	596.8	935.6	1194.6	1274.4	1223.7	1117.0	1009.1
102.5°	124.8	155.0	208.5	321.6	542.1	856.8	1159.8	1330.0	1361.3	1310.1	1237.2
105°	149.2	178.3	223.8	316.0	489.0	751.2	1048.6	1297.3	1439.2	1484.8	1473.4
107.5°	176.4	202.4	246.6	325.6	466.6	678.4	935.0	1180.4	1369.8	1486.8	1541.0
110°	193.8	220.7	263.1	334.7	460.0	644.4	870.3	1094.1	1291.0	1437.1	1525.2



TEST NUMBER: P333333-940

CATALOG NUMBER: S125DIP-S1270D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	212.0	238.1	278.9	346.3	460.0	624.6	822.2	1026.2	1213.1	1360.8	1464.6
115°	239.3	265.3	303.6	363.6	463.2	603.1	769.8	940.8	1101.4	1243.3	1356.3
117.5°	267.5	292.6	328.9	383.6	470.0	592.5	738.5	885.6	1024.1	1146.4	1250.0
120°	284.9	310.9	347.1	396.8	476.6	587.5	721.1	855.9	980.2	1094.1	1185.4
122.5°	302.4	328.2	364.5	411.8	482.4	583.4	706.2	833.5	948.7	1050.3	1135.6
125°	326.4	353.3	387.5	432.0	492.1	578.2	685.9	800.9	906.6	996.8	1071.4
127.5°	349.8	376.7	409.7	450.8	503.1	575.7	667.3	767.8	866.4	950.6	1020.4
130°	364.7	391.6	423.7	463.2	509.8	574.0	654.9	747.1	838.2	919.1	986.4
132.5°	378.0	404.9	437.0	473.9	517.2	574.0	644.9	726.3	811.7	885.0	949.9
135°	394.8	422.8	454.9	489.0	527.4	574.0	633.1	699.4	770.9	837.2	896.3
137.5°	409.5	438.3	467.5	500.2	536.7	575.2	622.5	676.6	734.4	789.5	839.7
140°	418.6	446.6	476.6	507.7	540.8	576.0	617.5	664.1	712.8	760.5	804.1
142.5°	427.8	454.1	482.4	511.8	543.3	576.9	613.4	653.4	694.6	735.7	773.4
145°	441.4	465.2	492.1	518.1	546.1	576.0	607.2	639.3	671.4	703.6	731.5
147.5°	453.8	474.7	498.4	521.8	547.1	573.4	600.7	626.1	652.1	676.8	697.9
150°	462.1	479.7	502.5	524.3	547.1	570.9	595.8	618.6	641.4	661.0	679.7
152.5°	469.6	485.5	506.7	525.9	546.3	567.6	590.0	610.3	630.6	648.6	663.2
155°	478.7	493.2	510.8	527.4	543.9	561.6	580.2	597.8	614.4	628.9	640.3
157.5°	488.2	499.2	514.3	528.4	541.3	555.4	571.1	585.4	599.1	610.3	619.2
160°	493.2	502.5	516.0	528.4	538.8	551.3	563.7	577.1	587.5	597.8	605.1
162.5°	498.2	505.9	517.6	527.6	536.3	546.3	557.1	568.0	577.6	586.2	592.6
165°	503.5	509.8	518.1	526.4	532.5	538.8	547.1	555.4	562.6	568.8	574.0
167.5°	507.3	511.2	518.1	523.9	526.7	531.5	537.3	543.3	548.1	552.9	556.6
170°	509.8	512.9	518.1	522.2	524.3	527.4	531.5	536.7	539.8	543.0	545.0
172.5°	511.4	512.9	517.2	520.6	520.9	522.5	525.8	529.2	532.4	534.7	535.9
175°	512.9	512.9	516.0	518.1	517.0	517.0	518.1	521.2	521.2	523.3	523.3
177.5°	513.1	513.1	514.8	515.6	513.9	513.9	514.8	515.6	516.4	516.4	516.4
180°	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9



TEST NUMBER: P333333-940

CATALOG NUMBER: S125DIP-S1270D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7
2.5°	1560.4	1564.2	1560.9	1565.4	1560.9	1564.2	1560.4	1563.7	1568.7	1565.4	1573.2
5°	1438.2	1431.9	1436.1	1433.3	1436.1	1431.9	1438.2	1441.6	1450.0	1452.8	1458.3
7.5°	1325.3	1319.3	1312.5	1309.3	1312.5	1319.3	1325.3	1327.4	1334.4	1344.9	1352.8
10°	1254.6	1247.1	1246.3	1241.4	1246.3	1247.1	1254.6	1262.3	1267.2	1280.4	1289.4
12.5°	1202.9	1195.9	1187.9	1185.9	1187.9	1195.9	1202.9	1209.5	1211.0	1225.9	1232.2
15°	1129.5	1124.0	1119.1	1123.3	1119.1	1124.0	1129.5	1133.7	1141.4	1151.8	1158.8
17.5°	1068.5	1063.9	1063.1	1057.9	1063.1	1063.9	1068.5	1070.9	1083.4	1090.2	1102.2
20°	1030.2	1026.7	1028.1	1019.0	1028.1	1026.7	1030.2	1036.4	1048.9	1052.4	1064.9
22.5°	999.6	992.7	991.9	990.2	991.9	992.7	999.6	1005.2	1007.8	1018.5	1027.1
25°	951.6	948.2	944.7	948.2	944.7	948.2	951.6	957.9	960.6	968.3	976.6
27.5°	909.7	905.6	904.6	905.0	904.6	905.6	909.7	909.2	916.7	922.8	929.0
30°	884.2	877.3	877.9	877.3	877.9	877.3	884.2	884.2	888.3	893.9	899.5
32.5°	856.4	851.7	850.7	849.4	850.7	851.7	856.4	855.2	860.5	867.2	873.3
35°	815.4	815.4	811.9	811.9	811.9	815.4	815.4	817.4	823.0	823.0	829.9
37.5°	776.9	776.1	774.1	774.4	774.1	776.1	776.9	778.6	780.4	783.4	787.8
40°	748.0	747.3	745.1	741.0	745.1	747.3	748.0	750.7	752.1	755.5	758.4
42.5°	720.1	717.7	716.8	715.4	716.8	717.7	720.1	721.8	722.6	727.2	732.8
45°	676.4	676.4	674.9	674.2	674.9	676.4	676.4	676.4	677.1	682.6	685.4
47.5°	633.8	635.1	637.7	637.3	637.7	635.1	633.8	632.7	632.9	635.8	638.9
50°	608.2	608.9	611.0	611.7	611.0	608.9	608.2	605.5	604.0	604.0	606.1
52.5°	579.9	583.9	586.6	586.1	586.6	583.9	579.9	577.7	575.2	571.8	575.0
55°	540.1	544.9	549.8	550.5	549.8	544.9	540.1	533.9	531.1	525.5	527.6
57.5°	500.8	507.6	512.7	514.3	512.7	507.6	500.8	493.2	484.2	481.6	477.7
60°	474.0	483.1	489.4	492.1	489.4	483.1	474.0	467.1	455.3	447.6	444.9
62.5°	448.4	458.6	464.8	465.5	464.8	458.6	448.4	437.7	425.8	417.1	411.5
65°	406.6	417.1	422.6	426.8	422.6	417.1	406.6	394.8	381.7	369.8	363.6
67.5°	361.6	372.0	378.2	381.5	378.2	372.0	361.6	347.0	334.9	321.3	313.9
70°	328.8	339.2	347.6	350.4	347.6	339.2	328.8	311.4	301.0	288.5	282.2
72.5°	296.5	305.9	312.5	315.8	312.5	305.9	296.5	280.3	268.1	255.7	247.2
75°	240.5	253.0	259.3	262.8	259.3	253.0	240.5	231.5	217.6	204.4	197.4
77.5°	185.5	196.9	200.6	202.4	200.6	196.9	185.5	174.9	164.3	154.7	147.9
80°	148.7	155.7	160.6	161.2	160.6	155.7	148.7	140.4	132.1	123.1	116.8
82.5°	114.3	120.1	121.6	123.4	121.6	120.1	114.3	107.0	99.8	93.0	87.8
85°	62.6	65.4	66.1	65.4	66.1	65.4	62.6	57.7	54.2	50.7	48.7
87.5°	25.1	24.6	24.8	25.9	24.8	24.6	25.1	24.0	24.2	22.8	21.5
90°	22.8	22.8	23.8	23.8	23.8	22.8	22.8	22.8	20.7	19.7	18.6
92.5°	71.7	69.2	67.8	66.1	67.8	69.2	71.7	85.0	100.3	133.2	183.6
95°	299.4	268.3	260.1	243.5	260.1	268.3	299.4	373.0	460.0	587.5	744.9
97.5°	689.8	631.9	601.8	588.5	601.8	631.9	689.8	753.9	874.9	999.1	1109.5
100°	937.7	863.1	824.7	808.2	824.7	863.1	937.7	1009.1	1117.0	1223.7	1274.4
102.5°	1160.7	1107.6	1066.0	1053.6	1066.0	1107.6	1160.7	1237.2	1310.1	1361.3	1330.0
105°	1440.2	1406.0	1385.3	1372.9	1385.3	1406.0	1440.2	1473.4	1484.8	1439.2	1297.3
107.5°	1557.7	1557.6	1550.7	1542.4	1550.7	1557.6	1557.7	1541.0	1486.8	1369.8	1180.4
110°	1571.8	1591.5	1598.7	1598.7	1598.7	1591.5	1571.8	1525.2	1437.1	1291.0	1094.1



TEST NUMBER: P333333-940

CATALOG NUMBER: S125DIP-S1270D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1532.9	1566.6	1584.7	1592.1	1584.7	1566.6	1532.9	1464.6	1360.8	1213.1	1026.2
115°	1437.1	1486.8	1515.8	1529.3	1515.8	1486.8	1437.1	1356.3	1243.3	1101.4	940.8
117.5°	1330.8	1382.2	1411.0	1419.2	1411.0	1382.2	1330.8	1250.0	1146.4	1024.1	885.6
120°	1262.0	1311.7	1339.7	1348.0	1339.7	1311.7	1262.0	1185.4	1094.1	980.2	855.9
122.5°	1204.0	1249.6	1277.6	1285.0	1277.6	1249.6	1204.0	1135.6	1050.3	948.7	833.5
125°	1129.4	1171.9	1194.6	1205.1	1194.6	1171.9	1129.4	1071.4	996.8	906.6	800.9
127.5°	1073.0	1110.5	1132.1	1136.7	1132.1	1110.5	1073.0	1020.4	950.6	866.4	767.8
130°	1038.2	1072.4	1093.1	1099.3	1093.1	1072.4	1038.2	986.4	919.1	838.2	747.1
132.5°	1001.7	1035.9	1055.0	1062.0	1055.0	1035.9	1001.7	949.9	885.0	811.7	726.3
135°	941.8	976.1	994.7	1000.9	994.7	976.1	941.8	896.3	837.2	770.9	699.4
137.5°	880.5	911.6	928.8	935.6	928.8	911.6	880.5	839.7	789.5	734.4	676.6
140°	842.4	869.3	884.8	890.0	884.8	869.3	842.4	804.1	760.5	712.8	664.1
142.5°	805.9	828.7	843.4	847.7	843.4	828.7	805.9	773.4	735.7	694.6	653.4
145°	756.3	774.0	785.4	789.5	785.4	774.0	756.3	731.5	703.6	671.4	639.3
147.5°	717.6	731.7	738.3	740.2	738.3	731.7	717.6	697.9	676.8	652.1	626.1
150°	695.3	707.7	711.9	712.8	711.9	707.7	695.3	679.7	661.0	641.4	618.6
152.5°	676.2	686.1	690.3	691.3	690.3	686.1	676.2	663.2	648.6	630.6	610.3
155°	650.7	657.9	661.0	662.1	661.0	657.9	650.7	640.3	628.9	614.4	597.8
157.5°	627.2	633.3	636.1	636.0	636.1	633.3	627.2	619.2	610.3	599.1	585.4
160°	612.3	617.5	619.6	618.6	619.6	617.5	612.3	605.1	597.8	587.5	577.1
162.5°	598.2	602.6	603.1	602.8	603.1	602.6	598.2	592.6	586.2	577.6	568.0
165°	578.2	580.2	580.2	580.2	580.2	580.2	578.2	574.0	568.8	562.6	555.4
167.5°	558.7	560.5	559.7	559.5	559.7	560.5	558.7	556.6	552.9	548.1	543.3
170°	547.1	548.1	548.1	547.1	548.1	548.1	547.1	545.0	543.0	539.8	536.7
172.5°	536.3	538.1	536.5	535.5	536.5	538.1	536.3	535.9	534.7	532.4	529.2
175°	523.3	524.3	522.2	521.2	522.2	524.3	523.3	523.3	523.3	521.2	521.2
177.5°	515.6	516.4	513.9	513.9	513.9	516.4	515.6	516.4	516.4	516.4	515.6
180°	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9



TEST NUMBER: P333333-940

CATALOG NUMBER: S125DIP-S1270D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7
2.5°	1565.9	1572.6	1580.9	1587.1	1598.2	1603.2	1609.3	1614.4	1623.2	1631.6	1641.6
5°	1460.4	1472.2	1488.3	1505.6	1525.8	1539.6	1559.2	1570.9	1594.6	1616.1	1637.0
7.5°	1364.8	1379.2	1401.9	1424.2	1450.5	1474.4	1498.8	1525.8	1555.9	1591.5	1621.0
10°	1299.1	1318.7	1342.9	1370.7	1402.8	1430.6	1463.2	1492.4	1529.2	1570.9	1609.9
12.5°	1246.9	1263.6	1290.7	1317.4	1351.6	1385.5	1419.2	1457.9	1500.8	1547.0	1596.0
15°	1174.7	1188.7	1210.9	1247.7	1282.5	1315.8	1366.5	1402.8	1457.0	1508.4	1567.4
17.5°	1113.1	1130.4	1149.1	1180.7	1216.7	1258.4	1303.8	1349.1	1401.3	1466.5	1533.1
20°	1075.3	1089.2	1110.8	1135.1	1173.3	1215.0	1258.1	1304.0	1368.0	1435.4	1507.0
22.5°	1034.2	1049.2	1073.5	1100.1	1132.2	1172.2	1219.8	1270.1	1336.9	1403.1	1480.9
25°	985.7	996.1	1018.3	1042.0	1074.0	1108.0	1157.4	1213.0	1279.0	1354.8	1434.0
27.5°	940.0	949.1	969.4	990.0	1018.9	1059.4	1103.4	1159.6	1221.8	1298.6	1386.4
30°	907.1	916.9	935.0	957.2	985.0	1020.4	1065.6	1118.5	1185.2	1260.3	1352.0
32.5°	878.8	887.3	901.0	923.3	950.5	984.8	1026.7	1080.6	1147.4	1223.5	1313.6
35°	834.8	844.5	855.0	872.4	896.0	929.3	975.3	1026.0	1089.9	1163.6	1246.3
37.5°	791.2	801.7	811.0	826.6	848.2	877.6	917.3	970.1	1028.0	1098.9	1178.3
40°	763.9	772.2	779.9	796.6	818.1	846.0	882.8	930.1	991.2	1057.3	1123.3
42.5°	736.6	744.5	751.0	765.4	785.3	812.0	847.2	893.3	950.1	1011.6	1069.9
45°	693.8	698.6	706.2	718.7	734.8	759.0	793.1	834.1	882.1	940.5	984.3
47.5°	647.3	655.0	661.2	672.2	685.3	709.2	741.8	776.7	820.2	863.6	894.5
50°	611.7	619.4	628.4	638.8	651.3	673.6	703.5	738.9	775.7	809.1	835.5
52.5°	578.4	585.4	595.0	604.8	620.2	639.1	664.5	696.1	732.4	756.3	778.3
55°	529.0	532.4	543.6	553.3	567.9	581.8	607.5	635.3	657.5	675.6	693.8
57.5°	478.5	483.2	489.6	498.4	512.8	529.1	547.2	571.8	584.9	594.1	608.2
60°	446.3	447.6	451.8	462.3	473.4	487.9	508.8	526.2	535.9	543.6	555.4
62.5°	410.6	411.0	417.9	425.5	433.9	449.6	466.5	480.6	488.7	492.4	503.6
65°	360.8	359.4	363.6	369.8	379.5	389.9	404.6	417.1	416.3	420.5	427.5
67.5°	309.8	308.4	308.4	314.3	322.3	331.5	341.6	348.8	348.9	354.5	358.0
70°	275.3	271.1	273.8	278.7	282.2	289.9	301.0	303.8	304.4	307.2	310.7
72.5°	239.7	238.3	240.5	242.6	245.0	250.9	260.4	262.1	262.2	263.9	269.6
75°	190.5	189.0	187.7	189.8	192.5	196.7	200.2	203.0	202.2	203.0	207.1
77.5°	142.8	138.8	138.2	139.3	140.0	142.5	146.2	145.8	146.5	146.4	151.1
80°	113.3	107.7	107.0	107.0	107.7	109.1	110.5	111.9	109.9	111.9	113.3
82.5°	83.3	79.9	79.8	79.3	79.4	79.6	80.5	81.3	80.9	81.9	82.8
85°	45.8	44.5	42.4	43.8	43.1	41.0	42.4	40.3	39.6	40.3	41.0
87.5°	19.1	19.4	17.9	17.7	16.8	17.1	15.5	14.6	13.6	13.7	15.2
90°	17.7	16.6	14.5	13.5	11.4	10.3	8.3	6.2	4.1	2.1	1.1
92.5°	270.5	334.0	339.5	236.5	141.5	85.0	54.8	36.9	24.1	15.3	12.7
95°	898.3	918.0	749.1	463.2	235.2	124.3	77.7	54.9	43.5	35.2	34.2
97.5°	1136.7	980.3	669.0	369.7	202.7	129.3	95.8	75.3	63.8	58.1	56.8
100°	1194.6	935.6	596.8	335.7	201.0	140.9	109.9	90.2	78.7	74.6	72.5
102.5°	1159.8	856.8	542.1	321.6	208.5	155.0	124.8	106.7	94.5	91.2	90.0
105°	1048.6	751.2	489.0	316.0	223.8	178.3	149.2	132.6	122.3	117.1	117.1
107.5°	935.0	678.4	466.6	325.6	246.6	202.4	176.4	159.2	150.6	145.7	143.6
110°	870.3	644.4	460.0	334.7	263.1	220.7	193.8	178.3	168.9	164.8	162.6



TEST NUMBER: P333333-940

CATALOG NUMBER: S125DIP-S1270D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	822.2	624.6	460.0	346.3	278.9	238.1	212.0	196.4	187.1	183.8	181.7
115°	769.8	603.1	463.2	363.6	303.6	265.3	239.3	223.8	214.5	211.3	209.3
117.5°	738.5	592.5	470.0	383.6	328.9	292.6	267.5	249.9	240.6	237.3	234.2
120°	721.1	587.5	476.6	396.8	347.1	310.9	284.9	267.3	258.0	253.9	250.7
122.5°	706.2	583.4	482.4	411.8	364.5	328.2	302.4	283.0	273.8	270.5	268.1
125°	685.9	578.2	492.1	432.0	387.5	353.3	326.4	306.7	297.4	292.2	290.1
127.5°	667.3	575.7	503.1	450.8	409.7	376.7	349.8	328.9	317.1	310.4	307.3
130°	654.9	574.0	509.8	463.2	423.7	391.6	364.7	343.0	329.5	321.2	318.1
132.5°	644.9	574.0	517.2	473.9	437.0	404.9	378.0	355.4	340.3	330.3	326.4
135°	633.1	574.0	527.4	489.0	454.9	422.8	394.8	373.0	356.4	344.0	339.8
137.5°	622.5	575.2	536.7	500.2	467.5	438.3	409.5	388.2	371.6	360.0	356.9
140°	617.5	576.0	540.8	507.7	476.6	446.6	418.6	399.0	382.4	369.9	366.8
142.5°	613.4	576.9	543.3	511.8	482.4	454.1	427.8	408.8	392.3	380.7	378.4
145°	607.2	576.0	546.1	518.1	492.1	465.2	441.4	422.8	408.2	397.9	395.8
147.5°	600.7	573.4	547.1	521.8	498.4	474.7	453.8	437.7	424.2	415.3	414.0
150°	595.8	570.9	547.1	524.3	502.5	479.7	462.1	447.6	434.2	426.9	424.8
152.5°	590.0	567.6	546.3	525.9	506.7	485.5	469.6	455.9	444.1	437.7	436.4
155°	580.2	561.6	543.9	527.4	510.8	493.2	478.7	468.3	458.0	451.7	451.7
157.5°	571.1	555.4	541.3	528.4	514.3	499.2	488.2	479.1	470.2	465.2	465.5
160°	563.7	551.3	538.8	528.4	516.0	502.5	493.2	484.9	477.7	473.5	474.6
162.5°	557.1	546.3	536.3	527.6	517.6	505.9	498.2	491.5	485.1	481.0	482.0
165°	547.1	538.8	532.5	526.4	518.1	509.8	503.5	499.4	494.3	491.2	493.2
167.5°	537.3	531.5	526.7	523.9	518.1	511.2	507.3	504.4	501.5	499.6	500.7
170°	531.5	527.4	524.3	522.2	518.1	512.9	509.8	507.7	505.6	504.6	505.6
172.5°	525.8	522.5	520.9	520.6	517.2	512.9	511.4	510.1	508.1	507.1	509.0
175°	518.1	517.0	517.0	518.1	516.0	512.9	512.9	512.9	511.8	510.8	512.9
177.5°	514.8	513.9	513.9	515.6	514.8	513.1	513.1	513.9	513.1	513.1	514.8
180°	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9



TEST NUMBER: P333333-940

CATALOG NUMBER: S125DIP-S1270D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7
2.5°	1646.5	1654.4	1659.4	1668.8	1676.6	1681.1	1685.0	1688.3	1692.2	1695.5	1705.0
5°	1657.2	1675.2	1690.5	1714.1	1735.7	1752.4	1770.4	1786.5	1799.7	1818.4	1833.0
7.5°	1652.5	1684.6	1718.3	1754.9	1792.2	1827.0	1859.0	1888.9	1916.0	1948.8	1977.5
10°	1648.1	1691.9	1735.0	1784.3	1835.1	1878.2	1918.5	1959.5	1989.4	2031.1	2066.5
12.5°	1644.8	1696.3	1748.4	1807.7	1863.4	1924.3	1978.0	2007.9	2053.3	2086.7	2128.9
15°	1630.8	1698.9	1770.4	1837.2	1916.4	1972.7	2020.0	2078.4	2120.8	2163.2	2209.0
17.5°	1605.5	1682.7	1762.8	1850.2	1926.3	1986.7	2047.6	2104.0	2154.6	2211.4	2268.5
20°	1593.8	1671.1	1762.8	1852.4	1926.8	1990.1	2052.6	2114.5	2170.2	2243.1	2309.2
22.5°	1569.4	1662.7	1747.2	1834.7	1911.3	1980.0	2051.0	2121.2	2195.1	2277.6	2360.3
25°	1525.8	1620.3	1709.9	1796.2	1873.3	1959.5	2035.2	2129.1	2223.7	2332.8	2435.6
27.5°	1480.4	1570.9	1653.1	1736.3	1826.3	1924.0	2022.2	2128.7	2252.5	2390.2	2535.3
30°	1443.8	1529.2	1609.2	1694.7	1788.5	1898.4	2006.1	2132.6	2275.8	2430.8	2603.2
32.5°	1400.9	1479.7	1557.5	1648.0	1750.2	1866.1	1991.6	2130.4	2302.5	2478.6	2656.0
35°	1327.7	1393.7	1473.6	1570.2	1685.6	1818.4	1963.7	2127.7	2325.1	2527.4	2676.8
37.5°	1240.7	1302.3	1386.4	1492.4	1613.4	1755.9	1928.2	2122.9	2332.5	2493.8	2542.0
40°	1182.4	1239.4	1327.0	1436.8	1560.5	1711.4	1900.4	2106.2	2309.2	2412.0	2372.4
42.5°	1120.1	1179.9	1265.2	1373.9	1507.2	1671.3	1865.4	2071.2	2241.3	2280.2	2143.3
45°	1021.8	1083.7	1167.8	1277.6	1420.8	1598.7	1801.0	1988.0	2086.0	2015.8	1803.8
47.5°	930.5	988.5	1066.4	1179.7	1327.5	1511.5	1706.4	1855.6	1863.3	1695.8	1469.4
50°	868.2	921.7	1000.2	1113.6	1260.3	1446.5	1622.4	1739.8	1687.0	1497.3	1279.7
52.5°	807.0	859.4	936.8	1049.1	1194.1	1364.8	1528.4	1610.9	1511.3	1316.5	1130.7
55°	718.7	764.6	840.3	944.0	1081.6	1240.1	1379.1	1407.6	1278.3	1086.5	935.6
57.5°	632.6	675.4	744.3	839.7	965.5	1105.9	1214.6	1208.5	1071.8	907.2	787.6
60°	574.2	615.9	677.1	770.2	884.8	1005.8	1098.9	1076.7	941.2	799.4	698.6
62.5°	521.9	559.1	617.0	698.5	803.2	915.2	991.7	958.9	826.1	702.0	622.4
65°	444.9	476.2	525.5	595.0	681.9	774.4	833.4	791.0	677.7	581.1	517.2
67.5°	371.3	396.4	437.7	493.2	567.3	641.6	677.6	634.9	544.3	473.8	426.4
70°	324.6	346.9	378.8	428.2	492.8	555.4	582.5	544.3	466.5	405.9	371.8
72.5°	277.9	296.2	324.3	368.7	420.5	474.7	498.6	462.0	398.1	347.0	315.1
75°	214.8	227.3	246.7	277.3	318.3	361.5	374.7	342.7	301.7	263.4	242.6
77.5°	153.7	164.3	179.1	198.4	227.5	254.9	266.4	247.9	216.2	192.0	174.9
80°	118.2	123.8	136.3	152.2	175.1	192.5	200.2	188.4	166.1	148.0	134.8
82.5°	84.3	89.8	97.3	110.5	125.1	137.0	145.2	137.2	121.1	106.9	99.2
85°	41.0	44.5	48.7	54.2	65.4	72.3	71.6	66.7	60.5	54.9	50.7
87.5°	14.9	15.9	17.9	21.1	23.2	25.6	27.2	26.2	24.4	23.0	21.5
90°	2.1	4.1	6.2	8.3	10.3	11.4	13.5	14.5	16.6	17.7	18.6
92.5°	15.3	24.1	36.9	54.8	85.0	141.5	236.5	339.5	334.0	270.5	183.6
95°	35.2	43.5	54.9	77.7	124.3	235.2	463.2	749.1	918.0	898.3	744.9
97.5°	58.1	63.8	75.3	95.8	129.3	202.7	369.7	669.0	980.3	1136.7	1109.5
100°	74.6	78.7	90.2	109.9	140.9	201.0	335.7	596.8	935.6	1194.6	1274.4
102.5°	91.2	94.5	106.7	124.8	155.0	208.5	321.6	542.1	856.8	1159.8	1330.0
105°	117.1	122.3	132.6	149.2	178.3	223.8	316.0	489.0	751.2	1048.6	1297.3
107.5°	145.7	150.6	159.2	176.4	202.4	246.6	325.6	466.6	678.4	935.0	1180.4
110°	164.8	168.9	178.3	193.8	220.7	263.1	334.7	460.0	644.4	870.3	1094.1



TEST NUMBER: P333333-940

CATALOG NUMBER: S125DIP-S1270D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	183.8	187.1	196.4	212.0	238.1	278.9	346.3	460.0	624.6	822.2	1026.2
115°	211.3	214.5	223.8	239.3	265.3	303.6	363.6	463.2	603.1	769.8	940.8
117.5°	237.3	240.6	249.9	267.5	292.6	328.9	383.6	470.0	592.5	738.5	885.6
120°	253.9	258.0	267.3	284.9	310.9	347.1	396.8	476.6	587.5	721.1	855.9
122.5°	270.5	273.8	283.0	302.4	328.2	364.5	411.8	482.4	583.4	706.2	833.5
125°	292.2	297.4	306.7	326.4	353.3	387.5	432.0	492.1	578.2	685.9	800.9
127.5°	310.4	317.1	328.9	349.8	376.7	409.7	450.8	503.1	575.7	667.3	767.8
130°	321.2	329.5	343.0	364.7	391.6	423.7	463.2	509.8	574.0	654.9	747.1
132.5°	330.3	340.3	355.4	378.0	404.9	437.0	473.9	517.2	574.0	644.9	726.3
135°	344.0	356.4	373.0	394.8	422.8	454.9	489.0	527.4	574.0	633.1	699.4
137.5°	360.0	371.6	388.2	409.5	438.3	467.5	500.2	536.7	575.2	622.5	676.6
140°	369.9	382.4	399.0	418.6	446.6	476.6	507.7	540.8	576.0	617.5	664.1
142.5°	380.7	392.3	408.8	427.8	454.1	482.4	511.8	543.3	576.9	613.4	653.4
145°	397.9	408.2	422.8	441.4	465.2	492.1	518.1	546.1	576.0	607.2	639.3
147.5°	415.3	424.2	437.7	453.8	474.7	498.4	521.8	547.1	573.4	600.7	626.1
150°	426.9	434.2	447.6	462.1	479.7	502.5	524.3	547.1	570.9	595.8	618.6
152.5°	437.7	444.1	455.9	469.6	485.5	506.7	525.9	546.3	567.6	590.0	610.3
155°	451.7	458.0	468.3	478.7	493.2	510.8	527.4	543.9	561.6	580.2	597.8
157.5°	465.2	470.2	479.1	488.2	499.2	514.3	528.4	541.3	555.4	571.1	585.4
160°	473.5	477.7	484.9	493.2	502.5	516.0	528.4	538.8	551.3	563.7	577.1
162.5°	481.0	485.1	491.5	498.2	505.9	517.6	527.6	536.3	546.3	557.1	568.0
165°	491.2	494.3	499.4	503.5	509.8	518.1	526.4	532.5	538.8	547.1	555.4
167.5°	499.6	501.5	504.4	507.3	511.2	518.1	523.9	526.7	531.5	537.3	543.3
170°	504.6	505.6	507.7	509.8	512.9	518.1	522.2	524.3	527.4	531.5	536.7
172.5°	507.1	508.1	510.1	511.4	512.9	517.2	520.6	520.9	522.5	525.8	529.2
175°	510.8	511.8	512.9	512.9	512.9	516.0	518.1	517.0	517.0	518.1	521.2
177.5°	513.1	513.1	513.9	513.1	513.1	514.8	515.6	513.9	513.9	514.8	515.6
180°	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9



TEST NUMBER: P333333-940

CATALOG NUMBER: S125DIP-S1270D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7
2.5°	1712.7	1717.2	1726.6	1723.3	1727.8	1730.0	1732.2
5°	1851.1	1873.3	1883.0	1881.7	1896.2	1892.7	1889.3
7.5°	2007.3	2030.7	2043.8	2060.0	2069.5	2070.2	2078.4
10°	2095.8	2126.4	2138.9	2156.2	2167.4	2173.6	2172.9
12.5°	2163.6	2187.5	2215.5	2224.1	2239.1	2247.0	2244.1
15°	2245.2	2283.4	2312.7	2327.2	2346.0	2351.5	2359.2
17.5°	2318.1	2369.4	2403.4	2448.7	2465.8	2476.3	2470.1
20°	2373.1	2440.5	2474.6	2528.8	2558.7	2574.7	2569.1
22.5°	2438.2	2511.1	2574.1	2621.1	2666.6	2688.2	2692.6
25°	2549.7	2649.7	2742.2	2804.1	2860.3	2873.5	2902.8
27.5°	2674.2	2792.2	2891.1	2956.2	2995.3	3010.1	3019.2
30°	2752.6	2870.1	2944.5	2986.2	2998.7	2997.3	2995.9
32.5°	2791.0	2864.5	2878.9	2867.2	2838.6	2814.3	2789.1
35°	2736.7	2681.7	2599.7	2494.0	2416.2	2337.6	2330.0
37.5°	2461.2	2285.6	2149.1	1996.6	1908.6	1854.3	1816.8
40°	2202.1	2002.6	1837.2	1708.6	1618.9	1583.5	1548.7
42.5°	1920.7	1730.1	1583.6	1476.1	1408.7	1369.4	1341.8
45°	1560.5	1392.3	1277.6	1199.8	1146.2	1115.6	1098.2
47.5°	1278.7	1154.3	1056.9	1000.7	963.7	940.0	940.0
50°	1127.5	1008.6	944.0	899.5	867.5	848.7	852.2
52.5°	993.5	904.6	849.4	812.2	788.5	776.9	776.6
55°	830.6	766.7	730.6	703.5	687.4	674.2	677.1
57.5°	710.5	656.6	632.4	609.9	598.8	593.5	585.9
60°	636.1	594.3	573.5	555.4	544.3	540.1	532.4
62.5°	569.9	537.1	516.7	502.0	492.0	490.6	484.6
65°	478.9	453.9	435.9	428.9	418.5	415.7	415.7
67.5°	394.8	376.9	362.8	356.4	351.9	352.6	349.2
70°	342.0	327.4	318.3	311.4	307.9	308.6	305.9
72.5°	299.2	282.9	275.0	270.8	266.3	268.0	266.9
75°	226.6	218.3	214.1	209.9	207.1	205.7	204.4
77.5°	166.4	159.1	155.9	153.5	153.9	150.5	153.2
80°	128.6	122.3	120.3	116.8	116.1	116.1	115.4
82.5°	94.1	90.6	89.1	86.2	85.0	86.1	84.3
85°	48.7	45.8	45.2	45.2	43.8	42.4	45.8
87.5°	21.8	19.7	20.2	19.6	19.6	19.3	18.1
90°	19.7	20.7	22.8	22.8	22.8	23.8	23.8
92.5°	133.2	100.3	85.0	71.7	69.2	67.8	66.1
95°	587.5	460.0	373.0	299.4	268.3	260.1	243.5
97.5°	999.1	874.9	753.9	689.8	631.9	601.8	588.5
100°	1223.7	1117.0	1009.1	937.7	863.1	824.7	808.2
102.5°	1361.3	1310.1	1237.2	1160.7	1107.6	1066.0	1053.6
105°	1439.2	1484.8	1473.4	1440.2	1406.0	1385.3	1372.9
107.5°	1369.8	1486.8	1541.0	1557.7	1557.6	1550.7	1542.4
110°	1291.0	1437.1	1525.2	1571.8	1591.5	1598.7	1598.7



TEST NUMBER: P333333-940

CATALOG NUMBER: S125DIP-S1270D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1213.1	1360.8	1464.6	1532.9	1566.6	1584.7	1592.1
115°	1101.4	1243.3	1356.3	1437.1	1486.8	1515.8	1529.3
117.5°	1024.1	1146.4	1250.0	1330.8	1382.2	1411.0	1419.2
120°	980.2	1094.1	1185.4	1262.0	1311.7	1339.7	1348.0
122.5°	948.7	1050.3	1135.6	1204.0	1249.6	1277.6	1285.0
125°	906.6	996.8	1071.4	1129.4	1171.9	1194.6	1205.1
127.5°	866.4	950.6	1020.4	1073.0	1110.5	1132.1	1136.7
130°	838.2	919.1	986.4	1038.2	1072.4	1093.1	1099.3
132.5°	811.7	885.0	949.9	1001.7	1035.9	1055.0	1062.0
135°	770.9	837.2	896.3	941.8	976.1	994.7	1000.9
137.5°	734.4	789.5	839.7	880.5	911.6	928.8	935.6
140°	712.8	760.5	804.1	842.4	869.3	884.8	890.0
142.5°	694.6	735.7	773.4	805.9	828.7	843.4	847.7
145°	671.4	703.6	731.5	756.3	774.0	785.4	789.5
147.5°	652.1	676.8	697.9	717.6	731.7	738.3	740.2
150°	641.4	661.0	679.7	695.3	707.7	711.9	712.8
152.5°	630.6	648.6	663.2	676.2	686.1	690.3	691.3
155°	614.4	628.9	640.3	650.7	657.9	661.0	662.1
157.5°	599.1	610.3	619.2	627.2	633.3	636.1	636.0
160°	587.5	597.8	605.1	612.3	617.5	619.6	618.6
162.5°	577.6	586.2	592.6	598.2	602.6	603.1	602.8
165°	562.6	568.8	574.0	578.2	580.2	580.2	580.2
167.5°	548.1	552.9	556.6	558.7	560.5	559.7	559.5
170°	539.8	543.0	545.0	547.1	548.1	548.1	547.1
172.5°	532.4	534.7	535.9	536.3	538.1	536.5	535.5
175°	521.2	523.3	523.3	523.3	524.3	522.2	521.2
177.5°	516.4	516.4	516.4	515.6	516.4	513.9	513.9
180°	513.9	513.9	513.9	513.9	513.9	513.9	513.9

(END OF REPORT)