

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333337-940

Luminaire Tested: **S125DIP-S1270D1205U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333337-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1270D1205U940-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8868.8 lumens
Efficiency: N/A
Efficacy: 123.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333337-940

CATALOG NUMBER: S125DIP-S1270D1205U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333337-940

CATALOG NUMBER: S125DIP-S1270D1205U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52
1	98	94	90	86	91	87	83	80	74	71	69	62	60	58	51	50	48	43
2	89	82	76	70	82	76	70	66	65	61	57	54	51	49	45	43	41	36
3	81	72	64	59	75	67	60	55	57	52	48	48	44	41	40	37	35	31
4	74	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30	26
5	68	57	48	42	63	53	45	40	45	40	35	38	34	31	32	29	26	23
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	26	23	20
7	58	46	38	32	54	43	36	31	37	31	27	31	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16
9	50	38	31	25	46	36	29	24	31	25	22	27	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	21	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11349	11349	11349
5°	11374	11267	11339
10°	11305	11187	11252
15°	11183	11053	11099
20°	11008	10864	10883
25°	10819	10641	10630
30°	10586	10399	10347
35°	10336	10139	9996
40°	10080	9857	9716
45°	9803	9600	9409
50°	9499	9289	9010
55°	9205	8939	8688
60°	8853	8584	8280
65°	8436	8159	7882
70°	8033	7666	7404
75°	7321	7079	6832
80°	6512	6412	6259
85°	5669	5765	5461



TEST NUMBER: P333337-940

CATALOG NUMBER: S125DIP-S1270D1205U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.7	1.9
10°-20°	468.1	5.3
20°-30°	691.1	7.8
30°-40°	806.4	9.1
40°-50°	809.9	9.1
50°-60°	710.9	8.0
60°-70°	529.7	6.0
70°-80°	302.9	3.4
80°-90°	91.0	1.0
90°-100°	50.8	0.6
100°-110°	313.1	3.5
110°-120°	567.9	6.4
120°-130°	728.8	8.2
130°-140°	783.9	8.8
140°-150°	735.8	8.3
150°-160°	595.2	6.7
160°-170°	384.9	4.3
170°-180°	132.8	1.5
0°-30°	1324.8	14.9
0°-40°	2131.2	24.0
0°-60°	3652.1	41.2
0°-90°	4575.8	51.6
90°-120°	931.8	10.5
90°-150°	3180.2	35.9
90°-180°	4293.0	48.4
0°-180°	8868.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1757	1757	1757	1757	1757	
5°	1754	1751	1738	1750	1749	166
15°	1672	1668	1653	1660	1660	471
25°	1518	1511	1493	1496	1492	698
35°	1311	1305	1286	1279	1268	820
45°	1073	1067	1051	1035	1030	827
55°	818	812	794	781	772	730
65°	552	548	534	522	516	548
75°	293	290	284	279	274	313
85°	76	78	78	76	74	85
90°	1	9	17	22	25	7
95°	59	54	17	22	22	75
105°	305	309	309	309	308	323
115°	572	577	578	574	568	567
125°	814	820	821	817	814	726
135°	1015	1020	1019	1016	1010	782
145°	1176	1178	1178	1179	1173	735
155°	1295	1290	1291	1294	1286	597
165°	1367	1361	1362	1367	1360	386
175°	1398	1392	1393	1400	1392	133
180°	1398	1398	1398	1398	1398	



TEST NUMBER: P333337-940

CATALOG NUMBER: S125DIP-S1270D1205U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3
2.5°	1761.8	1761.0	1760.3	1759.5	1758.8	1757.2	1754.7	1752.2	1749.8	1747.3	1749.8
5°	1754.5	1753.9	1753.3	1752.7	1752.0	1750.2	1747.1	1744.0	1741.0	1737.9	1740.6
7.5°	1738.4	1737.8	1737.1	1736.5	1735.9	1733.9	1730.5	1727.2	1723.8	1720.4	1723.1
10°	1723.9	1723.3	1722.7	1722.1	1721.4	1719.5	1716.1	1712.7	1709.2	1705.8	1708.3
12.5°	1706.1	1705.0	1704.0	1702.8	1701.7	1699.6	1696.4	1693.3	1690.1	1686.9	1689.0
15°	1672.5	1671.6	1670.6	1669.7	1668.8	1666.6	1663.2	1659.8	1656.4	1653.1	1654.6
17.5°	1633.9	1632.5	1631.1	1629.8	1628.4	1625.9	1622.5	1618.9	1615.4	1611.9	1613.8
20°	1601.6	1601.0	1600.4	1599.7	1599.1	1596.8	1592.8	1588.8	1584.7	1580.7	1582.9
22.5°	1569.3	1568.3	1567.1	1566.0	1564.9	1562.5	1558.7	1555.0	1551.1	1547.4	1548.8
25°	1518.2	1516.6	1515.1	1513.6	1512.0	1509.2	1505.2	1501.2	1497.2	1493.2	1493.8
27.5°	1458.4	1457.5	1456.5	1455.6	1454.7	1452.2	1448.0	1443.9	1439.8	1435.6	1435.7
30°	1419.5	1418.5	1417.6	1416.7	1415.8	1413.0	1408.4	1403.7	1399.1	1394.5	1393.8
32.5°	1377.2	1375.8	1374.4	1373.0	1371.5	1368.8	1364.6	1360.5	1356.3	1352.2	1351.1
35°	1311.0	1309.8	1308.6	1307.3	1306.1	1303.3	1299.0	1294.7	1290.3	1286.0	1284.5
37.5°	1242.3	1240.8	1239.3	1237.7	1236.2	1233.3	1229.3	1225.2	1221.1	1217.1	1214.8
40°	1195.6	1194.1	1192.6	1191.0	1189.5	1186.5	1182.2	1177.9	1173.6	1169.2	1166.4
42.5°	1145.6	1144.3	1143.0	1141.7	1140.4	1137.6	1133.3	1128.9	1124.6	1120.3	1117.8
45°	1073.3	1072.1	1070.9	1069.6	1068.4	1065.9	1062.2	1058.5	1054.8	1051.1	1047.3
47.5°	995.4	995.5	995.6	995.6	995.7	993.5	989.1	984.6	980.2	975.7	972.0
50°	945.4	944.5	943.5	942.6	941.6	939.3	935.7	931.9	928.3	924.5	920.5
52.5°	894.2	893.6	892.9	892.2	891.5	889.2	885.2	881.3	877.4	873.3	869.9
55°	817.5	816.5	815.6	814.7	813.8	811.2	806.8	802.5	798.2	793.9	791.0
57.5°	736.6	736.1	735.6	735.1	734.6	732.5	728.9	725.2	721.6	717.9	714.3
60°	685.4	684.2	683.0	681.7	680.5	678.1	674.8	671.4	668.0	664.6	661.5
62.5°	632.0	631.1	630.1	629.0	628.0	626.2	623.2	620.3	617.4	614.5	611.2
65°	552.0	551.3	550.7	550.1	549.5	547.4	544.0	540.6	537.3	533.9	531.1
67.5°	474.4	473.1	471.8	470.5	469.2	467.3	464.8	462.2	459.7	457.1	454.8
70°	425.4	423.9	422.3	420.8	419.3	417.1	414.3	411.5	408.8	406.0	404.1
72.5°	372.0	371.0	370.0	368.9	367.8	366.4	364.6	362.8	361.1	359.3	357.1
75°	293.4	292.7	292.1	291.5	290.9	289.8	288.3	286.7	285.2	283.7	282.7
77.5°	220.8	220.5	220.3	220.1	219.8	219.3	218.4	217.5	216.6	215.8	215.3
80°	175.1	175.1	175.1	175.1	175.1	174.9	174.2	173.6	173.0	172.4	172.1
82.5°	135.1	134.6	134.1	133.7	133.1	132.9	132.7	132.6	132.5	132.3	131.8
85°	76.5	76.8	77.0	77.4	77.7	77.8	77.8	77.8	77.8	77.8	77.6
87.5°	30.2	30.6	30.9	31.3	31.7	31.9	32.0	32.1	32.2	32.2	32.5
90°	1.1	2.9	4.7	6.6	8.4	10.2	11.8	13.4	15.0	16.6	17.7
92.5°	16.0	14.7	13.4	12.1	10.8	10.9	12.3	13.7	15.2	16.6	17.7
95°	59.0	58.4	57.7	57.0	56.3	51.6	42.8	34.1	25.3	16.6	17.7
97.5°	123.3	124.6	125.8	127.1	128.3	120.3	102.9	85.6	68.3	51.0	44.5
100°	173.1	173.8	174.4	175.1	175.8	176.6	177.5	178.5	179.4	180.3	146.0
102.5°	223.6	224.5	225.4	226.2	227.1	227.8	228.4	229.0	229.5	230.1	223.6
105°	304.7	305.6	306.5	307.5	308.4	308.8	308.8	308.8	308.8	308.8	308.8
107.5°	388.9	388.9	388.9	388.9	388.9	389.1	389.5	389.9	390.5	390.9	390.9
110°	443.5	443.5	443.5	443.5	443.5	443.8	444.3	444.7	445.1	445.6	445.0



TEST NUMBER: P333337-940

CATALOG NUMBER: S125DIP-S1270D1205U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	495.0	495.5	496.1	496.6	497.1	497.6	497.8	498.1	498.4	498.6	497.8
115°	572.0	573.2	574.4	575.5	576.7	577.4	577.6	577.8	578.0	578.3	577.4
117.5°	651.8	651.8	651.8	651.8	651.7	652.1	653.0	653.8	654.7	655.6	654.4
120°	701.6	701.3	701.2	700.9	700.7	700.9	701.6	702.3	702.9	703.6	703.2
122.5°	745.6	746.5	747.3	748.1	749.0	749.7	749.9	750.3	750.6	750.9	750.5
125°	813.5	815.1	816.7	818.3	819.9	820.7	820.7	820.7	820.7	820.7	819.8
127.5°	878.4	879.6	880.7	881.8	883.0	883.5	883.3	883.2	883.1	883.0	882.4
130°	918.2	919.4	920.5	921.7	922.8	923.5	923.7	924.0	924.2	924.4	923.7
132.5°	958.0	959.3	960.6	962.0	963.3	963.8	963.2	962.7	962.2	961.7	961.6
135°	1014.6	1015.9	1017.4	1018.7	1020.1	1020.6	1020.1	1019.7	1019.1	1018.7	1018.2
137.5°	1066.6	1067.8	1069.0	1070.1	1071.4	1071.7	1071.4	1070.9	1070.5	1070.1	1070.2
140°	1100.5	1101.1	1101.5	1102.0	1102.4	1102.5	1102.3	1102.1	1101.9	1101.6	1102.1
142.5°	1131.2	1131.5	1131.8	1132.1	1132.4	1132.7	1133.0	1133.3	1133.6	1134.0	1134.1
145°	1176.3	1176.7	1177.1	1177.6	1178.0	1178.3	1178.3	1178.3	1178.3	1178.3	1178.6
147.5°	1215.6	1215.5	1215.4	1215.3	1215.2	1215.3	1215.6	1215.8	1216.2	1216.5	1216.7
150°	1240.5	1240.0	1239.6	1239.1	1238.7	1238.7	1239.1	1239.6	1240.0	1240.5	1240.9
152.5°	1264.5	1263.6	1262.5	1261.5	1260.4	1260.2	1260.7	1261.1	1261.6	1262.0	1262.5
155°	1295.4	1294.1	1292.6	1291.3	1289.9	1289.4	1289.9	1290.3	1290.8	1291.3	1292.0
157.5°	1319.3	1318.4	1317.6	1316.8	1315.9	1315.5	1315.6	1315.6	1315.7	1315.7	1316.4
160°	1335.9	1334.4	1333.1	1331.7	1330.3	1329.7	1330.0	1330.2	1330.4	1330.6	1331.6
162.5°	1349.1	1347.7	1346.3	1345.0	1343.5	1343.0	1343.2	1343.5	1343.7	1343.9	1345.2
165°	1366.9	1365.6	1364.1	1362.8	1361.4	1360.8	1361.0	1361.3	1361.5	1361.7	1363.2
167.5°	1380.2	1378.8	1377.3	1375.9	1374.5	1373.9	1374.1	1374.3	1374.6	1374.8	1376.4
170°	1387.7	1386.1	1384.4	1382.8	1381.2	1380.5	1380.7	1381.0	1381.2	1381.4	1383.3
172.5°	1392.6	1391.0	1389.4	1387.8	1386.2	1385.5	1386.0	1386.4	1386.8	1387.2	1388.9
175°	1398.0	1396.6	1395.3	1393.8	1392.5	1391.9	1392.1	1392.4	1392.6	1392.9	1394.6
177.5°	1400.5	1399.4	1398.3	1397.2	1396.1	1395.6	1395.8	1396.0	1396.2	1396.3	1397.7
180°	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0



TEST NUMBER: P333337-940

CATALOG NUMBER: S125DIP-S1270D1205U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3
2.5°	1752.2	1754.7	1757.2	1758.3	1758.1	1757.8	1757.6	1757.3
5°	1743.4	1746.2	1749.0	1750.2	1749.9	1749.6	1749.3	1749.0
7.5°	1725.7	1728.5	1731.2	1732.4	1732.1	1731.8	1731.5	1731.2
10°	1710.8	1713.3	1715.7	1716.8	1716.5	1716.2	1715.9	1715.7
12.5°	1691.0	1692.9	1694.9	1695.9	1695.8	1695.7	1695.7	1695.6
15°	1656.2	1657.7	1659.2	1660.0	1660.0	1660.0	1660.0	1660.0
17.5°	1615.7	1617.7	1619.5	1619.7	1618.2	1616.7	1615.1	1613.6
20°	1585.1	1587.2	1589.4	1589.7	1588.1	1586.6	1585.1	1583.5
22.5°	1550.2	1551.7	1553.1	1553.3	1552.2	1551.1	1550.1	1549.1
25°	1494.4	1495.0	1495.7	1495.5	1494.6	1493.6	1492.7	1491.7
27.5°	1435.8	1436.0	1436.1	1435.7	1434.8	1433.9	1432.9	1432.0
30°	1393.2	1392.6	1392.0	1391.2	1390.3	1389.4	1388.4	1387.5
32.5°	1350.0	1348.9	1347.7	1346.3	1344.7	1343.0	1341.3	1339.7
35°	1282.9	1281.4	1279.9	1277.8	1275.3	1272.9	1270.4	1267.9
37.5°	1212.5	1210.2	1207.9	1206.0	1204.6	1203.2	1201.8	1200.3
40°	1163.7	1160.9	1158.1	1156.3	1155.3	1154.4	1153.4	1152.5
42.5°	1115.3	1112.7	1110.2	1108.2	1106.8	1105.4	1103.9	1102.5
45°	1043.7	1039.9	1036.3	1033.9	1033.0	1032.1	1031.1	1030.2
47.5°	968.1	964.4	960.6	957.7	955.5	953.3	951.2	949.0
50°	916.5	912.5	908.5	905.4	903.2	901.1	898.9	896.7
52.5°	866.3	862.8	859.3	856.3	853.9	851.5	849.1	846.7
55°	788.3	785.5	782.7	780.2	778.1	776.0	773.7	771.6
57.5°	710.8	707.2	703.6	701.2	700.1	698.9	697.7	696.5
60°	658.4	655.3	652.2	649.6	647.4	645.2	643.1	641.0
62.5°	607.8	604.5	601.2	598.7	597.0	595.3	593.6	592.0
65°	528.3	525.5	522.7	520.8	519.5	518.3	517.0	515.8
67.5°	452.5	450.0	447.7	446.2	445.4	444.7	444.0	443.2
70°	402.3	400.4	398.5	397.0	395.7	394.5	393.3	392.1
72.5°	355.1	352.9	350.9	349.2	347.9	346.7	345.4	344.2
75°	281.8	280.8	279.9	278.8	277.6	276.3	275.1	273.8
77.5°	214.6	214.1	213.6	212.9	212.0	211.1	210.3	209.4
80°	171.7	171.5	171.1	170.7	170.0	169.4	168.8	168.3
82.5°	131.3	130.7	130.1	129.8	129.7	129.6	129.4	129.3
85°	77.2	77.0	76.6	76.2	75.5	74.9	74.3	73.7
87.5°	32.7	32.9	33.2	33.1	32.7	32.4	32.0	31.7
90°	18.9	20.1	21.2	22.1	22.8	23.5	24.2	24.9
92.5°	18.9	20.1	21.2	21.9	22.2	22.6	22.9	23.2
95°	18.9	20.1	21.2	21.8	21.8	21.8	21.8	21.8
97.5°	38.0	31.5	25.0	21.8	21.8	21.8	21.8	21.8
100°	111.7	77.4	43.1	25.4	24.5	23.6	22.6	21.8
102.5°	217.0	210.6	204.1	193.1	177.4	161.7	146.1	130.4
105°	308.8	308.8	308.8	308.7	308.4	308.3	308.0	307.8
107.5°	391.0	391.0	391.1	390.7	390.0	389.4	388.7	388.0
110°	444.3	443.5	442.8	442.6	442.8	443.1	443.4	443.5



TEST NUMBER: P333337-940

CATALOG NUMBER: S125DIP-S1270D1205U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	497.0	496.1	495.2	494.5	494.3	493.9	493.7	493.3
115°	576.4	575.5	574.6	573.5	572.0	570.7	569.3	567.9
117.5°	653.2	652.0	650.8	649.9	649.3	648.7	648.1	647.5
120°	702.8	702.3	701.9	701.1	699.9	698.7	697.6	696.4
122.5°	750.0	749.6	749.1	748.1	746.8	745.5	744.2	742.9
125°	818.9	818.0	817.1	816.3	815.6	814.9	814.2	813.5
127.5°	881.9	881.5	880.9	879.9	878.2	876.4	874.7	873.0
130°	923.0	922.3	921.7	920.7	919.5	918.5	917.3	916.1
132.5°	961.4	961.3	961.2	960.6	959.4	958.2	957.1	955.9
135°	1017.8	1017.4	1016.9	1015.9	1014.6	1013.2	1011.8	1010.4
137.5°	1070.3	1070.4	1070.5	1070.0	1068.7	1067.6	1066.3	1065.1
140°	1102.5	1103.0	1103.5	1103.0	1101.6	1100.3	1098.9	1097.5
142.5°	1134.2	1134.3	1134.3	1133.7	1132.3	1131.0	1129.5	1128.2
145°	1178.8	1179.0	1179.2	1178.7	1177.2	1175.9	1174.5	1173.1
147.5°	1217.0	1217.3	1217.5	1216.8	1215.2	1213.5	1211.9	1210.2
150°	1241.4	1241.9	1242.3	1241.6	1239.8	1238.0	1236.1	1234.3
152.5°	1262.9	1263.5	1263.9	1263.3	1261.6	1260.0	1258.3	1256.7
155°	1292.6	1293.3	1294.1	1293.4	1291.6	1289.8	1287.9	1286.1
157.5°	1317.2	1317.9	1318.7	1318.1	1316.3	1314.5	1312.6	1310.7
160°	1332.5	1333.4	1334.4	1333.9	1332.0	1330.2	1328.4	1326.5
162.5°	1346.5	1347.8	1349.1	1348.7	1346.7	1344.6	1342.6	1340.6
165°	1364.5	1365.9	1367.3	1367.0	1365.2	1363.3	1361.5	1359.7
167.5°	1378.1	1379.7	1381.4	1381.3	1379.1	1377.1	1375.0	1373.0
170°	1385.1	1387.0	1388.8	1388.7	1386.6	1384.6	1382.5	1380.4
172.5°	1390.5	1392.2	1393.8	1393.7	1391.6	1389.6	1387.4	1385.4
175°	1396.5	1398.4	1400.2	1400.1	1398.0	1396.0	1393.8	1391.8
177.5°	1398.9	1400.3	1401.5	1401.4	1400.0	1398.5	1397.0	1395.5
180°	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0

(END OF REPORT)