

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331682-830

Luminaire Tested: **SA2XXRDIP-C675D530U830-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331682-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C675D530U830-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 530 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4176.5 lumens  
Efficiency: N/A  
Efficacy: 103.6 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 40.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331682-830  
CATALOG NUMBER: SA2XXRDIP-C675D530U830-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331682-830

CATALOG NUMBER: SA2XXRDIP-C675D530U830-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57	57	57	57	
1	100	96	93	89	93	90	87	84	78	76	74	67	65	64	57	56	55	50	50	50	50	
2	92	85	79	75	86	80	75	70	69	66	62	60	57	55	51	49	48	43	43	43	43	
3	85	76	69	63	79	71	65	60	62	58	54	54	50	48	46	44	42	38	38	38	38	
4	78	68	60	55	73	64	57	52	56	51	47	49	45	42	42	39	37	34	34	34	34	
5	72	61	53	48	67	57	51	45	51	45	41	44	40	37	38	35	33	30	30	30	30	
6	67	55	47	42	62	52	45	40	46	41	36	41	36	33	35	32	29	27	27	27	27	
7	62	50	43	37	58	48	41	36	42	37	33	37	33	30	33	29	27	24	24	24	24	
8	58	46	39	33	54	44	37	32	39	33	29	34	30	27	30	27	24	22	22	22	22	
9	54	42	35	30	51	40	34	29	36	31	27	32	28	24	28	25	22	20	20	20	20	
10	51	39	32	27	48	37	31	26	33	28	24	30	25	22	26	23	20	19	19	19	19	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	22357	22357	22357	22357
5°	24969	22498	19947	22498
10°	27702	22338	17290	22338
15°	29065	22011	13623	22011
20°	25197	21526	11789	21526
25°	16527	20861	10525	20861
30°	11123	20057	9527	20057
35°	9008	19042	8592	19042
40°	8011	17939	7950	17939
45°	7250	16643	7099	16643
50°	6599	15360	6574	15360
55°	6204	13937	6120	13937
60°	5189	12633	5125	12633
65°	4374	11469	4963	11469
70°	4046	10244	4683	10244
75°	3780	8914	4323	8914
80°	3487	7336	3849	7336
85°	3205	5798	3390	5798



TEST NUMBER: P331682-830

CATALOG NUMBER: SA2XXRDIP-C675D530U830-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	131.3	3.1
10°-20°	365.7	8.8
20°-30°	471.3	11.3
30°-40°	447.9	10.7
40°-50°	383.7	9.2
50°-60°	292.2	7.0
60°-70°	184.7	4.4
70°-80°	92.2	2.2
80°-90°	26.6	0.6
90°-100°	40.4	1.0
100°-110°	125.3	3.0
110°-120°	214.3	5.1
120°-130°	281.8	6.7
130°-140°	316.2	7.6
140°-150°	310.1	7.4
150°-160°	260.1	6.2
160°-170°	172.5	4.1
170°-180°	60.3	1.4
0°-30°	968.3	23.2
0°-40°	1416.2	33.9
0°-60°	2092.1	50.1
0°-90°	2395.6	57.4
90°-120°	380.0	9.1
90°-150°	1288.0	30.8
90°-180°	1781.0	42.6
0°-180°	4176.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1385	1385	1385	1385	1385	
5°	1541	1388	1231	1388	1541	152
15°	1739	1317	815	1317	1739	469
25°	928	1171	591	1171	928	440
35°	457	966	436	966	457	292
45°	318	729	311	729	318	246
55°	220	495	217	495	220	193
65°	114	300	130	300	114	117
75°	61	143	69	143	61	64
85°	17	31	18	31	17	19
90°	18	1	18	1	18	9
95°	33	28	33	28	33	37
105°	119	116	119	116	119	125
115°	215	215	215	215	215	212
125°	314	313	314	313	314	280
135°	410	405	410	405	410	315
145°	497	491	497	491	497	310
155°	566	562	566	562	566	260
165°	612	611	612	611	612	172
175°	634	636	634	636	634	60
180°	637	637	637	637	637	



TEST NUMBER: P331682-830

CATALOG NUMBER: SA2XXRDIP-C675D530U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1440.9	1442.0	1443.2	1440.5	1440.5	1438.1	1433.1	1429.4	1418.5	1417.0	1417.0
5°	1540.6	1539.5	1541.5	1535.3	1526.6	1524.7	1515.5	1503.5	1491.0	1477.1	1474.1
7.5°	1639.6	1638.2	1634.4	1633.3	1626.6	1612.1	1597.4	1581.8	1560.9	1540.7	1530.5
10°	1689.7	1705.6	1695.9	1679.1	1682.5	1659.9	1647.8	1627.2	1609.9	1579.5	1572.8
12.5°	1739.0	1745.2	1742.2	1732.6	1728.2	1712.6	1696.4	1678.4	1646.4	1619.2	1595.5
15°	1738.8	1747.9	1750.3	1747.5	1749.8	1748.9	1740.2	1725.3	1697.4	1667.5	1641.6
17.5°	1610.4	1616.7	1632.6	1643.2	1656.7	1685.2	1699.2	1704.7	1700.5	1683.6	1665.3
20°	1466.5	1455.9	1500.2	1522.8	1542.0	1590.1	1631.4	1647.4	1672.8	1672.4	1667.5
22.5°	1262.4	1265.0	1306.9	1333.8	1390.0	1438.0	1485.3	1545.0	1594.3	1626.9	1646.1
25°	927.7	945.9	987.8	1024.4	1086.8	1176.4	1257.6	1352.0	1441.0	1511.2	1578.1
27.5°	696.6	698.0	731.2	765.0	802.1	875.4	977.8	1090.4	1217.3	1322.0	1442.5
30°	596.6	593.7	607.7	628.4	660.1	716.9	793.8	904.6	1031.0	1188.8	1329.4
32.5°	525.8	525.9	536.5	551.8	578.2	616.4	669.1	759.0	878.6	1033.8	1198.4
35°	457.0	456.6	464.3	475.3	486.4	511.0	547.1	594.2	676.5	821.2	989.7
37.5°	407.8	409.9	413.7	420.6	432.8	446.5	468.2	499.8	558.4	644.0	785.6
40°	380.1	381.1	386.3	392.1	399.4	409.9	427.7	453.2	496.1	564.4	667.8
42.5°	354.7	355.6	359.4	364.8	370.4	381.1	395.8	417.8	452.5	505.9	591.2
45°	317.5	317.5	320.9	323.3	329.6	339.2	351.2	369.5	393.6	433.0	489.7
47.5°	282.7	282.8	285.0	289.2	293.1	300.6	312.5	327.3	344.9	375.4	423.9
50°	262.7	263.2	264.6	268.0	270.4	277.1	286.3	299.3	317.5	341.1	381.5
52.5°	246.6	246.2	248.1	249.5	251.2	256.0	262.8	274.3	290.6	311.1	344.6
55°	220.4	218.4	221.3	223.8	225.2	227.1	230.9	238.2	252.1	269.5	294.5
57.5°	187.7	186.9	188.9	191.1	195.7	200.9	204.1	208.7	215.9	228.4	253.2
60°	160.7	160.7	165.0	166.5	171.7	178.5	185.2	189.1	196.3	204.4	222.7
62.5°	136.9	137.2	139.2	140.7	143.6	151.9	161.4	169.8	176.6	184.5	196.6
65°	114.5	115.5	115.5	116.4	118.4	120.3	124.1	130.8	142.9	153.9	163.1
67.5°	97.2	97.5	97.7	98.7	99.2	101.3	102.8	105.8	108.7	119.1	130.4
70°	85.7	87.1	86.6	87.6	88.0	89.0	91.0	92.4	96.7	99.2	105.8
72.5°	74.8	75.9	75.8	76.4	77.7	77.9	79.4	80.9	83.6	85.7	89.3
75°	60.6	60.1	60.6	61.5	62.0	62.6	62.6	64.5	65.9	67.9	70.2
77.5°	46.8	47.2	47.1	47.2	47.3	48.2	48.1	49.0	50.4	51.4	52.5
80°	37.5	38.0	37.5	38.0	38.5	38.9	38.5	38.9	40.4	41.4	41.4
82.5°	29.0	29.1	29.4	29.5	29.6	29.7	30.4	30.5	31.6	31.4	31.8
85°	17.3	16.9	16.9	16.9	17.3	17.8	17.3	17.3	17.8	17.8	17.8
87.5°	9.8	10.2	10.2	10.1	10.1	10.1	10.2	10.6	10.3	10.7	9.8
90°	18.3	18.2	18.0	17.9	17.8	17.8	18.1	18.4	18.6	18.9	16.2
92.5°	17.4	17.4	17.3	17.3	17.3	17.2	17.2	17.2	17.2	17.1	16.5
95°	33.4	33.6	33.8	34.0	34.3	34.4	34.4	34.4	34.4	34.4	34.1
97.5°	57.7	57.8	57.8	57.8	57.8	57.9	57.9	57.9	57.9	57.9	57.4
100°	73.6	73.8	73.9	74.0	74.1	74.2	74.2	74.2	74.2	74.2	73.8
102.5°	91.7	91.8	91.9	92.1	92.2	92.2	92.1	92.0	91.9	91.8	91.3
105°	119.3	119.3	119.3	119.3	119.3	119.2	118.9	118.8	118.5	118.3	118.0
107.5°	145.3	145.9	146.5	146.9	147.5	147.8	147.7	147.6	147.5	147.4	147.4
110°	165.5	165.9	166.3	166.6	167.0	167.1	167.1	167.1	167.1	167.1	167.1



TEST NUMBER: P331682-830  
 CATALOG NUMBER: SA2XXRDIP-C675D530U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	184.9	185.1	185.4	185.7	186.0	186.2	186.5	186.8	187.1	187.4	187.5
115°	215.0	215.4	215.7	216.0	216.4	216.7	216.8	216.9	217.1	217.2	217.4
117.5°	243.6	244.0	244.4	244.8	245.2	245.4	245.7	246.0	246.3	246.6	247.2
120°	263.9	264.3	264.7	264.9	265.3	265.5	265.5	265.5	265.5	265.5	266.5
122.5°	283.7	284.0	284.2	284.5	284.7	285.0	285.3	285.6	285.9	286.2	286.8
125°	313.9	314.0	314.1	314.2	314.3	314.6	315.0	315.3	315.7	316.0	316.4
127.5°	341.4	341.8	342.1	342.5	342.9	343.4	343.7	344.2	344.6	345.1	345.5
130°	361.2	361.7	362.1	362.6	363.1	363.4	363.7	363.9	364.2	364.4	364.7
132.5°	380.1	380.5	380.9	381.3	381.6	382.1	382.6	383.1	383.7	384.2	384.2
135°	409.5	409.9	410.3	410.7	410.9	411.2	411.3	411.5	411.6	411.7	411.5
137.5°	436.2	436.7	437.2	437.6	438.1	438.4	438.5	438.6	438.7	438.8	438.5
140°	454.7	455.2	455.6	456.1	456.7	456.9	456.9	456.9	456.9	456.9	456.3
142.5°	471.5	471.9	472.4	472.9	473.3	473.5	473.4	473.3	473.3	473.2	472.8
145°	496.6	497.1	497.6	498.0	498.5	498.7	498.6	498.5	498.3	498.2	497.6
147.5°	519.1	519.5	520.0	520.5	520.9	521.0	520.8	520.5	520.2	520.0	519.4
150°	533.8	534.0	534.4	534.8	535.2	535.2	534.8	534.4	534.0	533.8	533.2
152.5°	547.5	547.9	548.4	548.8	549.3	549.3	548.8	548.4	547.9	547.5	546.9
155°	566.0	566.3	566.7	567.0	567.4	567.3	566.7	566.1	565.5	564.9	564.5
157.5°	581.8	582.5	583.1	583.6	584.2	584.1	583.2	582.4	581.6	580.8	580.6
160°	591.7	592.2	592.8	593.2	593.7	593.5	592.9	592.1	591.4	590.7	590.6
162.5°	600.4	601.0	601.5	602.1	602.7	602.6	601.7	600.9	600.1	599.3	599.2
165°	611.6	612.3	612.8	613.4	614.1	613.9	613.1	612.3	611.4	610.6	610.6
167.5°	620.9	621.5	622.2	622.7	623.4	623.3	622.5	621.6	620.8	619.9	619.9
170°	625.7	626.3	627.1	627.7	628.5	628.4	627.6	626.8	625.9	625.1	625.2
172.5°	629.5	630.2	630.9	631.7	632.4	632.3	631.5	630.7	629.8	629.0	629.1
175°	633.7	634.4	635.1	635.8	636.6	636.5	635.7	634.8	634.0	633.1	633.4
177.5°	635.7	636.2	636.8	637.3	637.9	637.9	637.3	636.8	636.2	635.7	635.8
180°	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9



TEST NUMBER: P331682-830  
 CATALOG NUMBER: SA2XXRDIP-C675D530U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1417.8	1414.7	1412.0	1405.0	1401.7	1393.9	1392.8	1392.4	1382.3	1372.7	1370.1
5°	1466.5	1458.8	1447.2	1433.7	1419.8	1405.3	1395.7	1388.1	1368.8	1350.5	1339.9
7.5°	1515.5	1499.0	1479.0	1453.6	1432.3	1408.4	1390.7	1374.9	1347.6	1321.4	1303.7
10°	1552.1	1525.1	1498.7	1463.6	1436.2	1409.2	1384.2	1362.5	1331.7	1297.1	1272.5
12.5°	1574.8	1545.2	1508.7	1474.3	1438.9	1404.6	1371.1	1343.3	1307.1	1271.3	1242.2
15°	1605.5	1573.8	1529.5	1480.5	1434.7	1390.0	1351.5	1316.8	1269.7	1226.9	1191.3
17.5°	1630.6	1587.0	1539.4	1482.6	1429.7	1372.8	1323.2	1279.0	1226.5	1174.9	1132.9
20°	1638.7	1595.4	1540.6	1483.8	1421.3	1354.3	1301.0	1252.8	1196.6	1140.3	1092.1
22.5°	1633.7	1600.1	1539.0	1471.1	1407.0	1337.0	1276.7	1220.9	1158.5	1101.0	1045.2
25°	1599.8	1588.2	1530.5	1456.3	1383.3	1301.9	1232.2	1171.0	1099.9	1038.3	977.6
27.5°	1520.5	1545.5	1509.7	1430.8	1349.4	1262.3	1183.8	1114.3	1040.4	971.1	910.7
30°	1444.4	1501.6	1486.2	1413.1	1322.1	1236.5	1148.5	1075.8	996.9	925.7	866.0
32.5°	1340.0	1434.6	1449.6	1388.5	1294.4	1200.3	1108.1	1035.8	953.4	878.4	820.2
35°	1173.9	1315.4	1380.4	1341.3	1247.1	1145.6	1050.3	966.1	883.4	809.3	751.5
37.5°	975.8	1168.5	1276.7	1279.5	1192.9	1087.3	983.6	900.0	815.3	742.5	680.1
40°	847.3	1056.0	1197.0	1228.3	1155.2	1041.1	936.2	851.1	768.4	697.1	625.5
42.5°	731.8	939.8	1113.1	1167.5	1109.4	996.1	890.9	801.8	721.4	654.0	580.8
45°	591.8	773.6	964.7	1061.9	1029.6	924.7	813.6	728.9	653.4	595.1	524.9
47.5°	499.2	627.4	812.2	943.7	943.1	847.3	738.0	657.0	586.9	532.3	475.4
50°	446.5	558.1	714.4	863.7	876.1	795.8	691.8	611.5	546.1	488.8	443.1
52.5°	399.2	491.2	631.7	774.7	810.3	740.7	639.9	565.7	502.2	449.6	410.4
55°	337.2	408.5	515.3	649.0	702.9	653.8	564.4	495.1	443.6	399.4	365.6
57.5°	285.3	338.7	424.4	532.2	594.8	564.0	490.1	433.9	389.8	349.8	323.2
60°	252.6	296.3	369.0	459.0	528.3	506.6	443.6	391.2	353.6	319.0	294.0
62.5°	221.8	259.4	321.7	394.7	458.3	449.3	397.8	353.8	320.9	289.4	268.2
65°	178.5	205.9	254.5	311.8	362.8	367.1	330.1	300.2	270.9	245.8	227.1
67.5°	142.1	160.0	194.3	242.5	280.7	294.4	271.7	248.9	225.6	206.3	190.0
70°	119.8	134.2	159.3	198.2	233.4	247.8	234.8	217.0	196.8	180.9	166.9
72.5°	97.1	111.1	129.6	158.2	188.3	203.9	199.3	186.6	170.2	157.0	143.8
75°	73.1	77.5	90.0	109.2	132.8	146.3	149.7	142.9	129.9	119.8	112.1
77.5°	54.1	56.6	62.7	72.8	88.1	100.2	105.1	104.3	95.4	89.4	82.3
80°	43.3	44.8	47.6	51.9	63.5	75.5	78.9	78.9	72.7	70.2	63.1
82.5°	32.9	33.9	35.7	38.1	43.5	54.0	57.8	58.5	54.6	51.4	45.7
85°	18.8	18.3	19.2	20.6	21.7	24.5	30.3	31.3	30.3	26.5	25.0
87.5°	9.2	9.1	8.6	7.8	7.9	8.0	9.6	11.3	10.0	9.1	8.7
90°	13.6	10.9	8.3	6.3	4.8	3.4	2.0	0.6	2.0	3.4	4.8
92.5°	15.8	15.3	14.6	13.8	12.7	11.7	10.7	9.6	10.7	11.7	12.7
95°	33.9	33.6	33.5	32.7	31.6	30.3	29.1	28.0	29.1	30.3	31.6
97.5°	56.9	56.5	56.0	55.2	54.2	53.2	52.1	51.1	52.1	53.2	54.2
100°	73.4	73.1	72.8	72.1	71.2	70.1	69.2	68.2	69.2	70.1	71.2
102.5°	90.9	90.5	90.0	89.4	88.6	87.8	87.1	86.3	87.1	87.8	88.6
105°	117.7	117.5	117.3	117.0	116.6	116.3	115.9	115.6	115.9	116.3	116.6
107.5°	147.4	147.4	147.4	147.1	146.6	146.1	145.5	145.1	145.5	146.1	146.6
110°	167.1	167.1	167.1	166.8	166.1	165.3	164.7	163.9	164.7	165.3	166.1





TEST NUMBER: P331682-830

CATALOG NUMBER: SA2XXRDIP-C675D530U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	187.6	187.7	187.8	187.5	186.7	186.0	185.3	184.5	185.3	186.0	186.7
115°	217.6	217.8	218.1	217.8	217.2	216.4	215.7	215.0	215.7	216.4	217.2
117.5°	247.9	248.6	249.3	249.1	248.2	247.2	246.3	245.3	246.3	247.2	248.2
120°	267.4	268.3	269.4	269.4	268.3	267.4	266.5	265.5	266.5	267.4	268.3
122.5°	287.5	288.1	288.8	288.6	287.5	286.3	285.1	284.0	285.1	286.3	287.5
125°	316.8	317.1	317.4	317.1	316.0	315.0	313.9	312.8	313.9	315.0	316.0
127.5°	345.9	346.4	346.8	346.3	345.0	343.6	342.2	340.8	342.2	343.6	345.0
130°	364.9	365.1	365.3	364.7	363.2	361.6	360.1	358.5	360.1	361.6	363.2
132.5°	384.1	384.1	384.0	383.3	382.1	380.8	379.6	378.2	379.6	380.8	382.1
135°	411.2	410.9	410.8	410.0	408.7	407.4	406.0	404.7	406.0	407.4	408.7
137.5°	438.2	437.9	437.5	436.9	435.8	434.7	433.7	432.5	433.7	434.7	435.8
140°	455.6	455.1	454.5	453.6	452.5	451.5	450.4	449.3	450.4	451.5	452.5
142.5°	472.4	472.0	471.6	470.8	469.8	468.7	467.6	466.6	467.6	468.7	469.8
145°	496.8	496.1	495.4	494.6	493.8	492.9	492.1	491.3	492.1	492.9	493.8
147.5°	519.0	518.5	518.0	517.3	516.3	515.3	514.3	513.3	514.3	515.3	516.3
150°	532.7	532.3	531.8	531.2	530.5	529.8	529.0	528.4	529.0	529.8	530.5
152.5°	546.3	545.7	545.2	544.5	543.8	543.1	542.4	541.7	542.4	543.1	543.8
155°	564.2	563.8	563.5	563.1	562.7	562.4	562.0	561.7	562.0	562.4	562.7
157.5°	580.4	580.1	579.9	579.8	579.5	579.2	579.0	578.7	579.0	579.2	579.5
160°	590.4	590.3	590.2	590.0	589.7	589.6	589.3	589.1	589.3	589.6	589.7
162.5°	599.1	598.9	598.8	598.7	598.7	598.6	598.6	598.5	598.6	598.6	598.7
165°	610.6	610.6	610.6	610.7	610.8	610.9	611.0	611.1	611.0	610.9	610.8
167.5°	620.0	620.0	620.0	620.2	620.6	620.9	621.3	621.6	621.3	620.9	620.6
170°	625.3	625.5	625.6	625.8	626.1	626.5	626.9	627.3	626.9	626.5	626.1
172.5°	629.2	629.3	629.4	629.7	630.0	630.4	630.7	631.1	630.7	630.4	630.0
175°	633.7	633.9	634.1	634.4	634.8	635.1	635.5	635.8	635.5	635.1	634.8
177.5°	636.0	636.2	636.4	636.6	636.9	637.2	637.4	637.8	637.4	637.2	636.9
180°	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9



TEST NUMBER: P331682-830

CATALOG NUMBER: SA2XXRDIP-C675D530U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1365.1	1362.4	1357.4	1349.6	1345.0	1336.9	1331.5	1334.6	1335.4	1334.6	1333.9
5°	1328.4	1318.2	1304.3	1290.8	1278.4	1264.9	1257.2	1253.8	1247.1	1243.2	1241.3
7.5°	1284.0	1266.6	1246.9	1223.4	1203.4	1182.6	1172.0	1166.6	1152.8	1145.4	1138.8
10°	1250.9	1223.5	1203.8	1173.0	1154.2	1126.8	1108.1	1108.5	1089.8	1079.1	1071.5
12.5°	1214.4	1184.2	1151.4	1123.7	1097.6	1075.6	1053.0	1043.9	1023.9	1013.7	993.0
15°	1153.8	1118.6	1084.0	1046.4	1020.0	985.8	953.1	913.1	880.9	853.0	845.4
17.5°	1087.5	1044.1	1009.3	965.3	919.9	862.4	824.5	801.3	781.9	767.2	756.2
20°	1042.1	997.9	960.8	894.4	833.3	794.4	766.5	748.7	728.4	712.6	703.9
22.5°	994.4	948.2	897.7	823.6	776.0	744.7	719.8	699.4	685.7	673.3	665.4
25°	926.6	876.1	792.9	741.9	703.4	670.7	653.4	640.8	626.4	609.5	601.9
27.5°	855.1	774.7	714.9	677.0	640.3	619.0	603.4	584.8	571.8	564.3	556.3
30°	801.5	721.2	674.6	633.2	607.2	583.6	565.3	554.8	542.2	529.2	524.0
32.5°	741.9	677.7	633.0	598.5	572.1	552.0	537.6	520.5	511.4	503.4	492.4
35°	667.8	619.3	578.3	550.4	525.4	509.1	492.2	482.1	465.7	459.0	454.7
37.5°	605.0	562.9	532.4	502.9	483.1	465.1	454.8	438.7	431.6	422.3	413.1
40°	569.7	528.3	498.9	474.9	452.7	439.2	426.3	413.3	402.7	398.4	387.3
42.5°	533.5	499.8	470.4	444.0	429.2	415.0	398.6	389.1	378.1	371.1	364.2
45°	483.5	453.7	428.7	407.0	390.7	375.8	365.1	349.3	343.1	329.0	323.3
47.5°	439.7	411.9	388.0	367.5	351.5	341.8	326.3	313.9	303.9	295.3	287.9
50°	408.5	385.4	362.3	344.0	329.6	315.7	299.7	293.5	278.1	273.7	269.5
52.5°	380.0	358.1	336.9	319.0	304.5	291.0	277.0	268.8	258.4	254.1	251.0
55°	340.2	319.0	298.8	282.9	268.4	254.5	245.8	235.7	230.9	227.5	223.8
57.5°	300.1	281.1	265.6	249.5	235.0	223.9	213.9	207.8	202.8	198.4	193.8
60°	274.8	256.5	242.5	227.5	212.6	203.5	195.9	188.6	182.9	176.1	174.2
62.5°	247.8	231.8	219.0	204.4	191.5	183.1	175.8	169.0	162.0	152.2	149.5
65°	210.8	198.2	184.7	172.8	161.2	153.0	142.4	134.7	131.9	130.8	130.4
67.5°	177.3	165.4	153.8	141.6	131.0	123.5	118.1	116.9	114.9	114.3	113.0
70°	155.0	143.8	132.3	120.7	110.7	109.2	107.3	105.4	102.9	102.0	101.0
72.5°	134.9	123.5	111.9	102.6	98.3	96.5	94.6	92.7	91.0	90.1	89.4
75°	103.4	92.8	85.2	81.8	79.4	77.9	75.0	73.6	72.7	71.2	70.7
77.5°	74.5	68.5	64.9	62.9	60.3	58.8	57.1	55.7	54.7	54.4	53.6
80°	56.7	53.9	51.5	48.6	47.6	45.7	45.2	43.8	44.3	42.8	42.8
82.5°	44.1	40.4	38.4	37.0	36.1	34.6	34.0	33.4	33.5	32.4	32.4
85°	22.6	21.7	20.6	19.7	19.7	18.3	18.8	18.3	18.3	17.3	16.9
87.5°	8.6	8.6	8.4	8.9	9.4	9.5	9.5	9.0	9.0	9.0	8.6
90°	6.3	8.3	10.9	13.6	16.2	18.9	18.6	18.4	18.1	17.8	17.8
92.5°	13.8	14.6	15.3	15.8	16.5	17.1	17.2	17.2	17.2	17.2	17.3
95°	32.7	33.5	33.6	33.9	34.1	34.4	34.4	34.4	34.4	34.4	34.3
97.5°	55.2	56.0	56.5	56.9	57.4	57.9	57.9	57.9	57.9	57.9	57.8
100°	72.1	72.8	73.1	73.4	73.8	74.2	74.2	74.2	74.2	74.2	74.1
102.5°	89.4	90.0	90.5	90.9	91.3	91.8	91.9	92.0	92.1	92.2	92.2
105°	117.0	117.3	117.5	117.7	118.0	118.3	118.5	118.8	118.9	119.2	119.3
107.5°	147.1	147.4	147.4	147.4	147.4	147.4	147.5	147.6	147.7	147.8	147.5
110°	166.8	167.1	167.1	167.1	167.1	167.1	167.1	167.1	167.1	167.1	167.0



TEST NUMBER: P331682-830

CATALOG NUMBER: SA2XXRDIP-C675D530U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	187.5	187.8	187.7	187.6	187.5	187.4	187.1	186.8	186.5	186.2	186.0
115°	217.8	218.1	217.8	217.6	217.4	217.2	217.1	216.9	216.8	216.7	216.4
117.5°	249.1	249.3	248.6	247.9	247.2	246.6	246.3	246.0	245.7	245.4	245.2
120°	269.4	269.4	268.3	267.4	266.5	265.5	265.5	265.5	265.5	265.5	265.3
122.5°	288.6	288.8	288.1	287.5	286.8	286.2	285.9	285.6	285.3	285.0	284.7
125°	317.1	317.4	317.1	316.8	316.4	316.0	315.7	315.3	315.0	314.6	314.3
127.5°	346.3	346.8	346.4	345.9	345.5	345.1	344.6	344.2	343.7	343.4	342.9
130°	364.7	365.3	365.1	364.9	364.7	364.4	364.2	363.9	363.7	363.4	363.1
132.5°	383.3	384.0	384.1	384.1	384.2	384.2	383.7	383.1	382.6	382.1	381.6
135°	410.0	410.8	410.9	411.2	411.5	411.7	411.6	411.5	411.3	411.2	410.9
137.5°	436.9	437.5	437.9	438.2	438.5	438.8	438.7	438.6	438.5	438.4	438.1
140°	453.6	454.5	455.1	455.6	456.3	456.9	456.9	456.9	456.9	456.9	456.7
142.5°	470.8	471.6	472.0	472.4	472.8	473.2	473.3	473.3	473.4	473.5	473.3
145°	494.6	495.4	496.1	496.8	497.6	498.2	498.3	498.5	498.6	498.7	498.5
147.5°	517.3	518.0	518.5	519.0	519.4	520.0	520.2	520.5	520.8	521.0	520.9
150°	531.2	531.8	532.3	532.7	533.2	533.8	534.0	534.4	534.8	535.2	535.2
152.5°	544.5	545.2	545.7	546.3	546.9	547.5	547.9	548.4	548.8	549.3	549.3
155°	563.1	563.5	563.8	564.2	564.5	564.9	565.5	566.1	566.7	567.3	567.4
157.5°	579.8	579.9	580.1	580.4	580.6	580.8	581.6	582.4	583.2	584.1	584.2
160°	590.0	590.2	590.3	590.4	590.6	590.7	591.4	592.1	592.9	593.5	593.7
162.5°	598.7	598.8	598.9	599.1	599.2	599.3	600.1	600.9	601.7	602.6	602.7
165°	610.7	610.6	610.6	610.6	610.6	610.6	611.4	612.3	613.1	613.9	614.1
167.5°	620.2	620.0	620.0	620.0	619.9	619.9	620.8	621.6	622.5	623.3	623.4
170°	625.8	625.6	625.5	625.3	625.2	625.1	625.9	626.8	627.6	628.4	628.5
172.5°	629.7	629.4	629.3	629.2	629.1	629.0	629.8	630.7	631.5	632.3	632.4
175°	634.4	634.1	633.9	633.7	633.4	633.1	634.0	634.8	635.7	636.5	636.6
177.5°	636.6	636.4	636.2	636.0	635.8	635.7	636.2	636.8	637.3	637.9	637.9
180°	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9



TEST NUMBER: P331682-830

CATALOG NUMBER: SA2XXRDIP-C675D530U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1329.6	1330.4	1329.3	1330.0	1329.3	1330.4	1329.6	1333.9	1334.6	1335.4	1334.6
5°	1238.9	1233.1	1232.2	1230.7	1232.2	1233.1	1238.9	1241.3	1243.2	1247.1	1253.8
7.5°	1130.6	1129.6	1127.3	1123.9	1127.3	1129.6	1130.6	1138.8	1145.4	1152.8	1166.6
10°	1060.8	1058.5	1058.0	1054.6	1058.0	1058.5	1060.8	1071.5	1079.1	1089.8	1108.5
12.5°	979.3	963.7	962.1	953.8	962.1	963.7	979.3	993.0	1013.7	1023.9	1043.9
15°	833.8	830.9	821.2	815.0	821.2	830.9	833.8	845.4	853.0	880.9	913.1
17.5°	750.6	741.2	738.2	736.9	738.2	741.2	750.6	756.2	767.2	781.9	801.3
20°	697.1	688.5	687.0	686.1	687.0	688.5	697.1	703.9	712.6	728.4	748.7
22.5°	660.2	651.1	647.4	644.5	647.4	651.1	660.2	665.4	673.3	685.7	699.4
25°	597.1	593.7	591.8	590.8	591.8	593.7	597.1	601.9	609.5	626.4	640.8
27.5°	547.7	540.3	538.9	536.4	538.9	540.3	547.7	556.3	564.3	571.8	584.8
30°	519.6	517.2	513.9	511.0	513.9	517.2	519.6	524.0	529.2	542.2	554.8
32.5°	486.5	484.5	481.5	480.1	481.5	484.5	486.5	492.4	503.4	511.4	520.5
35°	449.9	443.1	440.3	435.9	440.3	443.1	449.9	454.7	459.0	465.7	482.1
37.5°	411.0	407.6	403.5	404.9	403.5	407.6	411.0	413.1	422.3	431.6	438.7
40°	381.1	378.6	377.7	377.2	377.7	378.6	381.1	387.3	398.4	402.7	413.3
42.5°	357.2	350.5	348.1	348.0	348.1	350.5	357.2	364.2	371.1	378.1	389.1
45°	320.9	314.6	310.3	310.9	310.3	314.6	320.9	323.3	329.0	343.1	349.3
47.5°	283.8	283.6	280.9	281.7	280.9	283.6	283.8	287.9	295.3	303.9	313.9
50°	266.1	263.2	261.3	261.7	261.3	263.2	266.1	269.5	273.7	278.1	293.5
52.5°	249.1	246.7	245.1	247.1	245.1	246.7	249.1	251.0	254.1	258.4	268.8
55°	221.3	218.4	217.9	217.4	217.9	218.4	221.3	223.8	227.5	230.9	235.7
57.5°	190.2	188.3	185.4	184.2	185.4	188.3	190.2	193.8	198.4	202.8	207.8
60°	167.9	164.1	159.3	158.7	159.3	164.1	167.9	174.2	176.1	182.9	188.6
62.5°	147.5	146.8	145.8	145.7	145.8	146.8	147.5	149.5	152.2	162.0	169.0
65°	129.4	128.9	129.4	129.9	129.4	128.9	129.4	130.4	130.8	131.9	134.7
67.5°	112.8	111.9	111.0	111.4	111.0	111.9	112.8	113.0	114.3	114.9	116.9
70°	100.1	99.6	99.2	99.2	99.2	99.6	100.1	101.0	102.0	102.9	105.4
72.5°	87.8	87.7	87.2	86.8	87.2	87.7	87.8	89.4	90.1	91.0	92.7
75°	70.2	69.3	69.3	69.3	69.3	69.3	70.2	70.7	71.2	72.7	73.6
77.5°	53.5	53.1	52.5	52.1	52.5	53.1	53.5	53.6	54.4	54.7	55.7
80°	42.3	41.8	41.4	41.4	41.4	41.8	42.3	42.8	42.8	44.3	43.8
82.5°	32.3	31.9	31.8	31.4	31.8	31.9	32.3	32.4	32.4	33.5	33.4
85°	17.3	17.8	17.3	18.3	17.3	17.8	17.3	16.9	17.3	18.3	18.3
87.5°	8.6	8.2	8.7	8.3	8.7	8.2	8.6	8.6	9.0	9.0	9.0
90°	17.9	18.0	18.2	18.3	18.2	18.0	17.9	17.8	17.8	18.1	18.4
92.5°	17.3	17.3	17.4	17.4	17.4	17.3	17.3	17.3	17.2	17.2	17.2
95°	34.0	33.8	33.6	33.4	33.6	33.8	34.0	34.3	34.4	34.4	34.4
97.5°	57.8	57.8	57.8	57.7	57.8	57.8	57.8	57.8	57.9	57.9	57.9
100°	74.0	73.9	73.8	73.6	73.8	73.9	74.0	74.1	74.2	74.2	74.2
102.5°	92.1	91.9	91.8	91.7	91.8	91.9	92.1	92.2	92.2	92.1	92.0
105°	119.3	119.3	119.3	119.3	119.3	119.3	119.3	119.3	119.2	118.9	118.8
107.5°	146.9	146.5	145.9	145.3	145.9	146.5	146.9	147.5	147.8	147.7	147.6
110°	166.6	166.3	165.9	165.5	165.9	166.3	166.6	167.0	167.1	167.1	167.1



TEST NUMBER: P331682-830

CATALOG NUMBER: SA2XXRDIP-C675D530U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	185.7	185.4	185.1	184.9	185.1	185.4	185.7	186.0	186.2	186.5	186.8
115°	216.0	215.7	215.4	215.0	215.4	215.7	216.0	216.4	216.7	216.8	216.9
117.5°	244.8	244.4	244.0	243.6	244.0	244.4	244.8	245.2	245.4	245.7	246.0
120°	264.9	264.7	264.3	263.9	264.3	264.7	264.9	265.3	265.5	265.5	265.5
122.5°	284.5	284.2	284.0	283.7	284.0	284.2	284.5	284.7	285.0	285.3	285.6
125°	314.2	314.1	314.0	313.9	314.0	314.1	314.2	314.3	314.6	315.0	315.3
127.5°	342.5	342.1	341.8	341.4	341.8	342.1	342.5	342.9	343.4	343.7	344.2
130°	362.6	362.1	361.7	361.2	361.7	362.1	362.6	363.1	363.4	363.7	363.9
132.5°	381.3	380.9	380.5	380.1	380.5	380.9	381.3	381.6	382.1	382.6	383.1
135°	410.7	410.3	409.9	409.5	409.9	410.3	410.7	410.9	411.2	411.3	411.5
137.5°	437.6	437.2	436.7	436.2	436.7	437.2	437.6	438.1	438.4	438.5	438.6
140°	456.1	455.6	455.2	454.7	455.2	455.6	456.1	456.7	456.9	456.9	456.9
142.5°	472.9	472.4	471.9	471.5	471.9	472.4	472.9	473.3	473.5	473.4	473.3
145°	498.0	497.6	497.1	496.6	497.1	497.6	498.0	498.5	498.7	498.6	498.5
147.5°	520.5	520.0	519.5	519.1	519.5	520.0	520.5	520.9	521.0	520.8	520.5
150°	534.8	534.4	534.0	533.8	534.0	534.4	534.8	535.2	535.2	534.8	534.4
152.5°	548.8	548.4	547.9	547.5	547.9	548.4	548.8	549.3	549.3	548.8	548.4
155°	567.0	566.7	566.3	566.0	566.3	566.7	567.0	567.4	567.3	566.7	566.1
157.5°	583.6	583.1	582.5	581.8	582.5	583.1	583.6	584.2	584.1	583.2	582.4
160°	593.2	592.8	592.2	591.7	592.2	592.8	593.2	593.7	593.5	592.9	592.1
162.5°	602.1	601.5	601.0	600.4	601.0	601.5	602.1	602.7	602.6	601.7	600.9
165°	613.4	612.8	612.3	611.6	612.3	612.8	613.4	614.1	613.9	613.1	612.3
167.5°	622.7	622.2	621.5	620.9	621.5	622.2	622.7	623.4	623.3	622.5	621.6
170°	627.7	627.1	626.3	625.7	626.3	627.1	627.7	628.5	628.4	627.6	626.8
172.5°	631.7	630.9	630.2	629.5	630.2	630.9	631.7	632.4	632.3	631.5	630.7
175°	635.8	635.1	634.4	633.7	634.4	635.1	635.8	636.6	636.5	635.7	634.8
177.5°	637.3	636.8	636.2	635.7	636.2	636.8	637.3	637.9	637.9	637.3	636.8
180°	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9



TEST NUMBER: P331682-830  
 CATALOG NUMBER: SA2XXRDIP-C675D530U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1331.5	1336.9	1345.0	1349.6	1357.4	1362.4	1365.1	1370.1	1372.7	1382.3	1392.4
5°	1257.2	1264.9	1278.4	1290.8	1304.3	1318.2	1328.4	1339.9	1350.5	1368.8	1388.1
7.5°	1172.0	1182.6	1203.4	1223.4	1246.9	1266.6	1284.0	1303.7	1321.4	1347.6	1374.9
10°	1108.1	1126.8	1154.2	1173.0	1203.8	1223.5	1250.9	1272.5	1297.1	1331.7	1362.5
12.5°	1053.0	1075.6	1097.6	1123.7	1151.4	1184.2	1214.4	1242.2	1271.3	1307.1	1343.3
15°	953.1	985.8	1020.0	1046.4	1084.0	1118.6	1153.8	1191.3	1226.9	1269.7	1316.8
17.5°	824.5	862.4	919.9	965.3	1009.3	1044.1	1087.5	1132.9	1174.9	1226.5	1279.0
20°	766.5	794.4	833.3	894.4	960.8	997.9	1042.1	1092.1	1140.3	1196.6	1252.8
22.5°	719.8	744.7	776.0	823.6	897.7	948.2	994.4	1045.2	1101.0	1158.5	1220.9
25°	653.4	670.7	703.4	741.9	792.9	876.1	926.6	977.6	1038.3	1099.9	1171.0
27.5°	603.4	619.0	640.3	677.0	714.9	774.7	855.1	910.7	971.1	1040.4	1114.3
30°	565.3	583.6	607.2	633.2	674.6	721.2	801.5	866.0	925.7	996.9	1075.8
32.5°	537.6	552.0	572.1	598.5	633.0	677.7	741.9	820.2	878.4	953.4	1035.8
35°	492.2	509.1	525.4	550.4	578.3	619.3	667.8	751.5	809.3	883.4	966.1
37.5°	454.8	465.1	483.1	502.9	532.4	562.9	605.0	680.1	742.5	815.3	900.0
40°	426.3	439.2	452.7	474.9	498.9	528.3	569.7	625.5	697.1	768.4	851.1
42.5°	398.6	415.0	429.2	444.0	470.4	499.8	533.5	580.8	654.0	721.4	801.8
45°	365.1	375.8	390.7	407.0	428.7	453.7	483.5	524.9	595.1	653.4	728.9
47.5°	326.3	341.8	351.5	367.5	388.0	411.9	439.7	475.4	532.3	586.9	657.0
50°	299.7	315.7	329.6	344.0	362.3	385.4	408.5	443.1	488.8	546.1	611.5
52.5°	277.0	291.0	304.5	319.0	336.9	358.1	380.0	410.4	449.6	502.2	565.7
55°	245.8	254.5	268.4	282.9	298.8	319.0	340.2	365.6	399.4	443.6	495.1
57.5°	213.9	223.9	235.0	249.5	265.6	281.1	300.1	323.2	349.8	389.8	433.9
60°	195.9	203.5	212.6	227.5	242.5	256.5	274.8	294.0	319.0	353.6	391.2
62.5°	175.8	183.1	191.5	204.4	219.0	231.8	247.8	268.2	289.4	320.9	353.8
65°	142.4	153.0	161.2	172.8	184.7	198.2	210.8	227.1	245.8	270.9	300.2
67.5°	118.1	123.5	131.0	141.6	153.8	165.4	177.3	190.0	206.3	225.6	248.9
70°	107.3	109.2	110.7	120.7	132.3	143.8	155.0	166.9	180.9	196.8	217.0
72.5°	94.6	96.5	98.3	102.6	111.9	123.5	134.9	143.8	157.0	170.2	186.6
75°	75.0	77.9	79.4	81.8	85.2	92.8	103.4	112.1	119.8	129.9	142.9
77.5°	57.1	58.8	60.3	62.9	64.9	68.5	74.5	82.3	89.4	95.4	104.3
80°	45.2	45.7	47.6	48.6	51.5	53.9	56.7	63.1	70.2	72.7	78.9
82.5°	34.0	34.6	36.1	37.0	38.4	40.4	44.1	45.7	51.4	54.6	58.5
85°	18.8	18.3	19.7	19.7	20.6	21.7	22.6	25.0	26.5	30.3	31.3
87.5°	9.5	9.5	9.4	8.9	8.4	8.6	8.6	8.7	9.1	10.0	11.3
90°	18.6	18.9	16.2	13.6	10.9	8.3	6.3	4.8	3.4	2.0	0.6
92.5°	17.2	17.1	16.5	15.8	15.3	14.6	13.8	12.7	11.7	10.7	9.6
95°	34.4	34.4	34.1	33.9	33.6	33.5	32.7	31.6	30.3	29.1	28.0
97.5°	57.9	57.9	57.4	56.9	56.5	56.0	55.2	54.2	53.2	52.1	51.1
100°	74.2	74.2	73.8	73.4	73.1	72.8	72.1	71.2	70.1	69.2	68.2
102.5°	91.9	91.8	91.3	90.9	90.5	90.0	89.4	88.6	87.8	87.1	86.3
105°	118.5	118.3	118.0	117.7	117.5	117.3	117.0	116.6	116.3	115.9	115.6
107.5°	147.5	147.4	147.4	147.4	147.4	147.4	147.1	146.6	146.1	145.5	145.1
110°	167.1	167.1	167.1	167.1	167.1	167.1	166.8	166.1	165.3	164.7	163.9



TEST NUMBER: P331682-830

CATALOG NUMBER: SA2XXRDIP-C675D530U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	187.1	187.4	187.5	187.6	187.7	187.8	187.5	186.7	186.0	185.3	184.5
115°	217.1	217.2	217.4	217.6	217.8	218.1	217.8	217.2	216.4	215.7	215.0
117.5°	246.3	246.6	247.2	247.9	248.6	249.3	249.1	248.2	247.2	246.3	245.3
120°	265.5	265.5	266.5	267.4	268.3	269.4	269.4	268.3	267.4	266.5	265.5
122.5°	285.9	286.2	286.8	287.5	288.1	288.8	288.6	287.5	286.3	285.1	284.0
125°	315.7	316.0	316.4	316.8	317.1	317.4	317.1	316.0	315.0	313.9	312.8
127.5°	344.6	345.1	345.5	345.9	346.4	346.8	346.3	345.0	343.6	342.2	340.8
130°	364.2	364.4	364.7	364.9	365.1	365.3	364.7	363.2	361.6	360.1	358.5
132.5°	383.7	384.2	384.2	384.1	384.1	384.0	383.3	382.1	380.8	379.6	378.2
135°	411.6	411.7	411.5	411.2	410.9	410.8	410.0	408.7	407.4	406.0	404.7
137.5°	438.7	438.8	438.5	438.2	437.9	437.5	436.9	435.8	434.7	433.7	432.5
140°	456.9	456.9	456.3	455.6	455.1	454.5	453.6	452.5	451.5	450.4	449.3
142.5°	473.3	473.2	472.8	472.4	472.0	471.6	470.8	469.8	468.7	467.6	466.6
145°	498.3	498.2	497.6	496.8	496.1	495.4	494.6	493.8	492.9	492.1	491.3
147.5°	520.2	520.0	519.4	519.0	518.5	518.0	517.3	516.3	515.3	514.3	513.3
150°	534.0	533.8	533.2	532.7	532.3	531.8	531.2	530.5	529.8	529.0	528.4
152.5°	547.9	547.5	546.9	546.3	545.7	545.2	544.5	543.8	543.1	542.4	541.7
155°	565.5	564.9	564.5	564.2	563.8	563.5	563.1	562.7	562.4	562.0	561.7
157.5°	581.6	580.8	580.6	580.4	580.1	579.9	579.8	579.5	579.2	579.0	578.7
160°	591.4	590.7	590.6	590.4	590.3	590.2	590.0	589.7	589.6	589.3	589.1
162.5°	600.1	599.3	599.2	599.1	598.9	598.8	598.7	598.7	598.6	598.6	598.5
165°	611.4	610.6	610.6	610.6	610.6	610.6	610.7	610.8	610.9	611.0	611.1
167.5°	620.8	619.9	619.9	620.0	620.0	620.0	620.2	620.6	620.9	621.3	621.6
170°	625.9	625.1	625.2	625.3	625.5	625.6	625.8	626.1	626.5	626.9	627.3
172.5°	629.8	629.0	629.1	629.2	629.3	629.4	629.7	630.0	630.4	630.7	631.1
175°	634.0	633.1	633.4	633.7	633.9	634.1	634.4	634.8	635.1	635.5	635.8
177.5°	636.2	635.7	635.8	636.0	636.2	636.4	636.6	636.9	637.2	637.4	637.8
180°	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9



TEST NUMBER: P331682-830  
 CATALOG NUMBER: SA2XXRDIP-C675D530U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1392.8	1393.9	1401.7	1405.0	1412.0	1414.7	1417.8	1417.0	1417.0	1418.5	1429.4
5°	1395.7	1405.3	1419.8	1433.7	1447.2	1458.8	1466.5	1474.1	1477.1	1491.0	1503.5
7.5°	1390.7	1408.4	1432.3	1453.6	1479.0	1499.0	1515.5	1530.5	1540.7	1560.9	1581.8
10°	1384.2	1409.2	1436.2	1463.6	1498.7	1525.1	1552.1	1572.8	1579.5	1609.9	1627.2
12.5°	1371.1	1404.6	1438.9	1474.3	1508.7	1545.2	1574.8	1595.5	1619.2	1646.4	1678.4
15°	1351.5	1390.0	1434.7	1480.5	1529.5	1573.8	1605.5	1641.6	1667.5	1697.4	1725.3
17.5°	1323.2	1372.8	1429.7	1482.6	1539.4	1587.0	1630.6	1665.3	1683.6	1700.5	1704.7
20°	1301.0	1354.3	1421.3	1483.8	1540.6	1595.4	1638.7	1667.5	1672.4	1672.8	1647.4
22.5°	1276.7	1337.0	1407.0	1471.1	1539.0	1600.1	1633.7	1646.1	1626.9	1594.3	1545.0
25°	1232.2	1301.9	1383.3	1456.3	1530.5	1588.2	1599.8	1578.1	1511.2	1441.0	1352.0
27.5°	1183.8	1262.3	1349.4	1430.8	1509.7	1545.5	1520.5	1442.5	1322.0	1217.3	1090.4
30°	1148.5	1236.5	1322.1	1413.1	1486.2	1501.6	1444.4	1329.4	1188.8	1031.0	904.6
32.5°	1108.1	1200.3	1294.4	1388.5	1449.6	1434.6	1340.0	1198.4	1033.8	878.6	759.0
35°	1050.3	1145.6	1247.1	1341.3	1380.4	1315.4	1173.9	989.7	821.2	676.5	594.2
37.5°	983.6	1087.3	1192.9	1279.5	1276.7	1168.5	975.8	785.6	644.0	558.4	499.8
40°	936.2	1041.1	1155.2	1228.3	1197.0	1056.0	847.3	667.8	564.4	496.1	453.2
42.5°	890.9	996.1	1109.4	1167.5	1113.1	939.8	731.8	591.2	505.9	452.5	417.8
45°	813.6	924.7	1029.6	1061.9	964.7	773.6	591.8	489.7	433.0	393.6	369.5
47.5°	738.0	847.3	943.1	943.7	812.2	627.4	499.2	423.9	375.4	344.9	327.3
50°	691.8	795.8	876.1	863.7	714.4	558.1	446.5	381.5	341.1	317.5	299.3
52.5°	639.9	740.7	810.3	774.7	631.7	491.2	399.2	344.6	311.1	290.6	274.3
55°	564.4	653.8	702.9	649.0	515.3	408.5	337.2	294.5	269.5	252.1	238.2
57.5°	490.1	564.0	594.8	532.2	424.4	338.7	285.3	253.2	228.4	215.9	208.7
60°	443.6	506.6	528.3	459.0	369.0	296.3	252.6	222.7	204.4	196.3	189.1
62.5°	397.8	449.3	458.3	394.7	321.7	259.4	221.8	196.6	184.5	176.6	169.8
65°	330.1	367.1	362.8	311.8	254.5	205.9	178.5	163.1	153.9	142.9	130.8
67.5°	271.7	294.4	280.7	242.5	194.3	160.0	142.1	130.4	119.1	108.7	105.8
70°	234.8	247.8	233.4	198.2	159.3	134.2	119.8	105.8	99.2	96.7	92.4
72.5°	199.3	203.9	188.3	158.2	129.6	111.1	97.1	89.3	85.7	83.6	80.9
75°	149.7	146.3	132.8	109.2	90.0	77.5	73.1	70.2	67.9	65.9	64.5
77.5°	105.1	100.2	88.1	72.8	62.7	56.6	54.1	52.5	51.4	50.4	49.0
80°	78.9	75.5	63.5	51.9	47.6	44.8	43.3	41.4	41.4	40.4	38.9
82.5°	57.8	54.0	43.5	38.1	35.7	33.9	32.9	31.8	31.4	31.6	30.5
85°	30.3	24.5	21.7	20.6	19.2	18.3	18.8	17.8	17.8	17.8	17.3
87.5°	9.6	8.0	7.9	7.8	8.6	9.1	9.2	9.8	10.7	10.3	10.6
90°	2.0	3.4	4.8	6.3	8.3	10.9	13.6	16.2	18.9	18.6	18.4
92.5°	10.7	11.7	12.7	13.8	14.6	15.3	15.8	16.5	17.1	17.2	17.2
95°	29.1	30.3	31.6	32.7	33.5	33.6	33.9	34.1	34.4	34.4	34.4
97.5°	52.1	53.2	54.2	55.2	56.0	56.5	56.9	57.4	57.9	57.9	57.9
100°	69.2	70.1	71.2	72.1	72.8	73.1	73.4	73.8	74.2	74.2	74.2
102.5°	87.1	87.8	88.6	89.4	90.0	90.5	90.9	91.3	91.8	91.9	92.0
105°	115.9	116.3	116.6	117.0	117.3	117.5	117.7	118.0	118.3	118.5	118.8
107.5°	145.5	146.1	146.6	147.1	147.4	147.4	147.4	147.4	147.4	147.5	147.6
110°	164.7	165.3	166.1	166.8	167.1	167.1	167.1	167.1	167.1	167.1	167.1





TEST NUMBER: P331682-830

CATALOG NUMBER: SA2XXRDIP-C675D530U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	185.3	186.0	186.7	187.5	187.8	187.7	187.6	187.5	187.4	187.1	186.8
115°	215.7	216.4	217.2	217.8	218.1	217.8	217.6	217.4	217.2	217.1	216.9
117.5°	246.3	247.2	248.2	249.1	249.3	248.6	247.9	247.2	246.6	246.3	246.0
120°	266.5	267.4	268.3	269.4	269.4	268.3	267.4	266.5	265.5	265.5	265.5
122.5°	285.1	286.3	287.5	288.6	288.8	288.1	287.5	286.8	286.2	285.9	285.6
125°	313.9	315.0	316.0	317.1	317.4	317.1	316.8	316.4	316.0	315.7	315.3
127.5°	342.2	343.6	345.0	346.3	346.8	346.4	345.9	345.5	345.1	344.6	344.2
130°	360.1	361.6	363.2	364.7	365.3	365.1	364.9	364.7	364.4	364.2	363.9
132.5°	379.6	380.8	382.1	383.3	384.0	384.1	384.1	384.2	384.2	383.7	383.1
135°	406.0	407.4	408.7	410.0	410.8	410.9	411.2	411.5	411.7	411.6	411.5
137.5°	433.7	434.7	435.8	436.9	437.5	437.9	438.2	438.5	438.8	438.7	438.6
140°	450.4	451.5	452.5	453.6	454.5	455.1	455.6	456.3	456.9	456.9	456.9
142.5°	467.6	468.7	469.8	470.8	471.6	472.0	472.4	472.8	473.2	473.3	473.3
145°	492.1	492.9	493.8	494.6	495.4	496.1	496.8	497.6	498.2	498.3	498.5
147.5°	514.3	515.3	516.3	517.3	518.0	518.5	519.0	519.4	520.0	520.2	520.5
150°	529.0	529.8	530.5	531.2	531.8	532.3	532.7	533.2	533.8	534.0	534.4
152.5°	542.4	543.1	543.8	544.5	545.2	545.7	546.3	546.9	547.5	547.9	548.4
155°	562.0	562.4	562.7	563.1	563.5	563.8	564.2	564.5	564.9	565.5	566.1
157.5°	579.0	579.2	579.5	579.8	579.9	580.1	580.4	580.6	580.8	581.6	582.4
160°	589.3	589.6	589.7	590.0	590.2	590.3	590.4	590.6	590.7	591.4	592.1
162.5°	598.6	598.6	598.7	598.7	598.8	598.9	599.1	599.2	599.3	600.1	600.9
165°	611.0	610.9	610.8	610.7	610.6	610.6	610.6	610.6	610.6	611.4	612.3
167.5°	621.3	620.9	620.6	620.2	620.0	620.0	620.0	619.9	619.9	620.8	621.6
170°	626.9	626.5	626.1	625.8	625.6	625.5	625.3	625.2	625.1	625.9	626.8
172.5°	630.7	630.4	630.0	629.7	629.4	629.3	629.2	629.1	629.0	629.8	630.7
175°	635.5	635.1	634.8	634.4	634.1	633.9	633.7	633.4	633.1	634.0	634.8
177.5°	637.4	637.2	636.9	636.6	636.4	636.2	636.0	635.8	635.7	636.2	636.8
180°	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9



TEST NUMBER: P331682-830

CATALOG NUMBER: SA2XXRDIP-C675D530U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1433.1	1438.1	1440.5	1440.5	1443.2	1442.0	1440.9
5°	1515.5	1524.7	1526.6	1535.3	1541.5	1539.5	1540.6
7.5°	1597.4	1612.1	1626.6	1633.3	1634.4	1638.2	1639.6
10°	1647.8	1659.9	1682.5	1679.1	1695.9	1705.6	1689.7
12.5°	1696.4	1712.6	1728.2	1732.6	1742.2	1745.2	1739.0
15°	1740.2	1748.9	1749.8	1747.5	1750.3	1747.9	1738.8
17.5°	1699.2	1685.2	1656.7	1643.2	1632.6	1616.7	1610.4
20°	1631.4	1590.1	1542.0	1522.8	1500.2	1455.9	1466.5
22.5°	1485.3	1438.0	1390.0	1333.8	1306.9	1265.0	1262.4
25°	1257.6	1176.4	1086.8	1024.4	987.8	945.9	927.7
27.5°	977.8	875.4	802.1	765.0	731.2	698.0	696.6
30°	793.8	716.9	660.1	628.4	607.7	593.7	596.6
32.5°	669.1	616.4	578.2	551.8	536.5	525.9	525.8
35°	547.1	511.0	486.4	475.3	464.3	456.6	457.0
37.5°	468.2	446.5	432.8	420.6	413.7	409.9	407.8
40°	427.7	409.9	399.4	392.1	386.3	381.1	380.1
42.5°	395.8	381.1	370.4	364.8	359.4	355.6	354.7
45°	351.2	339.2	329.6	323.3	320.9	317.5	317.5
47.5°	312.5	300.6	293.1	289.2	285.0	282.8	282.7
50°	286.3	277.1	270.4	268.0	264.6	263.2	262.7
52.5°	262.8	256.0	251.2	249.5	248.1	246.2	246.6
55°	230.9	227.1	225.2	223.8	221.3	218.4	220.4
57.5°	204.1	200.9	195.7	191.1	188.9	186.9	187.7
60°	185.2	178.5	171.7	166.5	165.0	160.7	160.7
62.5°	161.4	151.9	143.6	140.7	139.2	137.2	136.9
65°	124.1	120.3	118.4	116.4	115.5	115.5	114.5
67.5°	102.8	101.3	99.2	98.7	97.7	97.5	97.2
70°	91.0	89.0	88.0	87.6	86.6	87.1	85.7
72.5°	79.4	77.9	77.7	76.4	75.8	75.9	74.8
75°	62.6	62.6	62.0	61.5	60.6	60.1	60.6
77.5°	48.1	48.2	47.3	47.2	47.1	47.2	46.8
80°	38.5	38.9	38.5	38.0	37.5	38.0	37.5
82.5°	30.4	29.7	29.6	29.5	29.4	29.1	29.0
85°	17.3	17.8	17.3	16.9	16.9	16.9	17.3
87.5°	10.2	10.1	10.1	10.1	10.2	10.2	9.8
90°	18.1	17.8	17.8	17.9	18.0	18.2	18.3
92.5°	17.2	17.2	17.3	17.3	17.3	17.4	17.4
95°	34.4	34.4	34.3	34.0	33.8	33.6	33.4
97.5°	57.9	57.9	57.8	57.8	57.8	57.8	57.7
100°	74.2	74.2	74.1	74.0	73.9	73.8	73.6
102.5°	92.1	92.2	92.2	92.1	91.9	91.8	91.7
105°	118.9	119.2	119.3	119.3	119.3	119.3	119.3
107.5°	147.7	147.8	147.5	146.9	146.5	145.9	145.3
110°	167.1	167.1	167.0	166.6	166.3	165.9	165.5



TEST NUMBER: P331682-830

CATALOG NUMBER: SA2XXRDIP-C675D530U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	186.5	186.2	186.0	185.7	185.4	185.1	184.9
115°	216.8	216.7	216.4	216.0	215.7	215.4	215.0
117.5°	245.7	245.4	245.2	244.8	244.4	244.0	243.6
120°	265.5	265.5	265.3	264.9	264.7	264.3	263.9
122.5°	285.3	285.0	284.7	284.5	284.2	284.0	283.7
125°	315.0	314.6	314.3	314.2	314.1	314.0	313.9
127.5°	343.7	343.4	342.9	342.5	342.1	341.8	341.4
130°	363.7	363.4	363.1	362.6	362.1	361.7	361.2
132.5°	382.6	382.1	381.6	381.3	380.9	380.5	380.1
135°	411.3	411.2	410.9	410.7	410.3	409.9	409.5
137.5°	438.5	438.4	438.1	437.6	437.2	436.7	436.2
140°	456.9	456.9	456.7	456.1	455.6	455.2	454.7
142.5°	473.4	473.5	473.3	472.9	472.4	471.9	471.5
145°	498.6	498.7	498.5	498.0	497.6	497.1	496.6
147.5°	520.8	521.0	520.9	520.5	520.0	519.5	519.1
150°	534.8	535.2	535.2	534.8	534.4	534.0	533.8
152.5°	548.8	549.3	549.3	548.8	548.4	547.9	547.5
155°	566.7	567.3	567.4	567.0	566.7	566.3	566.0
157.5°	583.2	584.1	584.2	583.6	583.1	582.5	581.8
160°	592.9	593.5	593.7	593.2	592.8	592.2	591.7
162.5°	601.7	602.6	602.7	602.1	601.5	601.0	600.4
165°	613.1	613.9	614.1	613.4	612.8	612.3	611.6
167.5°	622.5	623.3	623.4	622.7	622.2	621.5	620.9
170°	627.6	628.4	628.5	627.7	627.1	626.3	625.7
172.5°	631.5	632.3	632.4	631.7	630.9	630.2	629.5
175°	635.7	636.5	636.6	635.8	635.1	634.4	633.7
177.5°	637.3	637.9	637.9	637.3	636.8	636.2	635.7
180°	636.9	636.9	636.9	636.9	636.9	636.9	636.9

(END OF REPORT)