

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333321-940

Luminaire Tested: **S125DIP-S1270D810U940-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333321-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1270D810U940-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7168.2 lumens
Efficiency: N/A
Efficacy: 118.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333321-940

CATALOG NUMBER: S125DIP-S1270D810U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333321-940

CATALOG NUMBER: S125DIP-S1270D810U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69	64
1	101	96	92	89	94	91	87	84	80	77	75	70	68	66	61	59	58	54
2	92	84	78	72	86	79	74	69	70	66	62	61	58	55	53	51	49	45
3	84	74	66	60	78	70	63	58	62	56	52	54	50	47	47	44	41	38
4	77	65	57	51	72	62	54	49	55	49	44	48	44	40	42	39	36	33
5	70	58	50	44	66	55	48	42	49	43	38	43	39	35	38	34	31	28
6	65	52	44	38	61	50	42	37	44	38	33	39	34	30	35	31	27	25
7	60	47	39	34	56	45	38	32	40	34	30	36	31	27	32	28	24	22
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	20
9	52	39	32	27	49	38	30	26	34	28	24	30	25	22	27	23	20	18
10	49	36	29	24	46	35	28	23	31	25	21	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11349	11349	11349
5°	11374	11267	11339
10°	11305	11187	11252
15°	11183	11053	11099
20°	11008	10864	10883
25°	10819	10641	10630
30°	10586	10399	10347
35°	10336	10139	9996
40°	10080	9857	9716
45°	9803	9600	9409
50°	9499	9289	9010
55°	9205	8939	8688
60°	8853	8584	8280
65°	8436	8159	7882
70°	8033	7666	7404
75°	7321	7079	6832
80°	6512	6412	6259
85°	5669	5765	5461



TEST NUMBER: P333321-940

CATALOG NUMBER: S125DIP-S1270D810U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.7	2.3
10°-20°	468.1	6.5
20°-30°	691.1	9.6
30°-40°	806.4	11.2
40°-50°	809.9	11.3
50°-60°	710.9	9.9
60°-70°	529.7	7.4
70°-80°	302.9	4.2
80°-90°	90.0	1.3
90°-100°	250.7	3.5
100°-110°	538.9	7.5
110°-120°	505.7	7.1
120°-130°	409.8	5.7
130°-140°	328.9	4.6
140°-150°	248.2	3.5
150°-160°	174.7	2.4
160°-170°	103.0	1.4
170°-180°	33.5	0.5
0°-30°	1324.8	18.5
0°-40°	2131.2	29.7
0°-60°	3652.1	50.9
0°-90°	4574.8	63.8
90°-120°	1295.2	18.1
90°-150°	2282.2	31.8
90°-180°	2593.0	36.2
0°-180°	7168.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1757	1757	1757	1757	1757	
5°	1754	1751	1738	1750	1749	166
15°	1672	1668	1653	1660	1660	471
25°	1518	1511	1493	1496	1492	698
35°	1311	1305	1286	1279	1268	820
45°	1073	1067	1051	1035	1030	827
55°	818	812	794	781	772	730
65°	552	548	534	522	516	548
75°	293	290	284	279	274	313
85°	76	78	78	76	74	85
90°	1	6	11	15	16	5
95°	23	68	618	280	164	24
105°	79	110	506	995	924	83
115°	141	170	406	875	1029	139
125°	195	229	389	696	811	173
135°	229	275	386	583	674	178
145°	266	305	388	483	531	167
155°	304	327	378	427	446	140
165°	332	341	363	385	390	93
175°	345	345	348	352	351	33
180°	346	346	346	346	346	



TEST NUMBER: P333321-940

CATALOG NUMBER: S125DIP-S1270D810U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3
2.5°	1761.8	1761.0	1760.3	1759.5	1758.8	1757.2	1754.7	1752.2	1749.8	1747.3	1749.8
5°	1754.5	1753.9	1753.3	1752.7	1752.0	1750.2	1747.1	1744.0	1741.0	1737.9	1740.6
7.5°	1738.4	1737.8	1737.1	1736.5	1735.9	1733.9	1730.5	1727.2	1723.8	1720.4	1723.1
10°	1723.9	1723.3	1722.7	1722.1	1721.4	1719.5	1716.1	1712.7	1709.2	1705.8	1708.3
12.5°	1706.1	1705.0	1704.0	1702.8	1701.7	1699.6	1696.4	1693.3	1690.1	1686.9	1689.0
15°	1672.5	1671.6	1670.6	1669.7	1668.8	1666.6	1663.2	1659.8	1656.4	1653.1	1654.6
17.5°	1633.9	1632.5	1631.1	1629.8	1628.4	1625.9	1622.5	1618.9	1615.4	1611.9	1613.8
20°	1601.6	1601.0	1600.4	1599.7	1599.1	1596.8	1592.8	1588.8	1584.7	1580.7	1582.9
22.5°	1569.3	1568.3	1567.1	1566.0	1564.9	1562.5	1558.7	1555.0	1551.1	1547.4	1548.8
25°	1518.2	1516.6	1515.1	1513.6	1512.0	1509.2	1505.2	1501.2	1497.2	1493.2	1493.8
27.5°	1458.4	1457.5	1456.5	1455.6	1454.7	1452.2	1448.0	1443.9	1439.8	1435.6	1435.7
30°	1419.5	1418.5	1417.6	1416.7	1415.8	1413.0	1408.4	1403.7	1399.1	1394.5	1393.8
32.5°	1377.2	1375.8	1374.4	1373.0	1371.5	1368.8	1364.6	1360.5	1356.3	1352.2	1351.1
35°	1311.0	1309.8	1308.6	1307.3	1306.1	1303.3	1299.0	1294.7	1290.3	1286.0	1284.5
37.5°	1242.3	1240.8	1239.3	1237.7	1236.2	1233.3	1229.3	1225.2	1221.1	1217.1	1214.8
40°	1195.6	1194.1	1192.6	1191.0	1189.5	1186.5	1182.2	1177.9	1173.6	1169.2	1166.4
42.5°	1145.6	1144.3	1143.0	1141.7	1140.4	1137.6	1133.3	1128.9	1124.6	1120.3	1117.8
45°	1073.3	1072.1	1070.9	1069.6	1068.4	1065.9	1062.2	1058.5	1054.8	1051.1	1047.3
47.5°	995.4	995.5	995.6	995.6	995.7	993.5	989.1	984.6	980.2	975.7	972.0
50°	945.4	944.5	943.5	942.6	941.6	939.3	935.7	931.9	928.3	924.5	920.5
52.5°	894.2	893.6	892.9	892.2	891.5	889.2	885.2	881.3	877.4	873.3	869.9
55°	817.5	816.5	815.6	814.7	813.8	811.2	806.8	802.5	798.2	793.9	791.0
57.5°	736.6	736.1	735.6	735.1	734.6	732.5	728.9	725.2	721.6	717.9	714.3
60°	685.4	684.2	683.0	681.7	680.5	678.1	674.8	671.4	668.0	664.6	661.5
62.5°	632.0	631.1	630.1	629.0	628.0	626.2	623.2	620.3	617.4	614.5	611.2
65°	552.0	551.3	550.7	550.1	549.5	547.4	544.0	540.6	537.3	533.9	531.1
67.5°	474.4	473.1	471.8	470.5	469.2	467.3	464.8	462.2	459.7	457.1	454.8
70°	425.4	423.9	422.3	420.8	419.3	417.1	414.3	411.5	408.8	406.0	404.1
72.5°	372.0	371.0	370.0	368.9	367.8	366.4	364.6	362.8	361.1	359.3	357.1
75°	293.4	292.7	292.1	291.5	290.9	289.8	288.3	286.7	285.2	283.7	282.7
77.5°	220.8	220.5	220.3	220.1	219.8	219.3	218.4	217.5	216.6	215.8	215.3
80°	175.1	175.1	175.1	175.1	175.1	174.9	174.2	173.6	173.0	172.4	172.1
82.5°	135.1	134.6	134.1	133.7	133.1	132.9	132.7	132.6	132.5	132.3	131.8
85°	76.5	76.8	77.0	77.4	77.7	77.8	77.8	77.8	77.8	77.8	77.6
87.5°	30.1	30.3	30.6	30.9	31.1	31.3	31.2	31.2	31.1	31.1	31.3
90°	0.7	1.4	2.8	4.2	5.6	7.0	7.7	9.1	9.7	11.1	11.9
92.5°	8.5	10.3	16.1	24.8	36.8	57.2	95.2	159.1	228.4	224.8	182.0
95°	23.0	23.7	29.2	36.9	52.3	83.6	158.3	311.7	504.1	617.8	604.5
97.5°	38.2	39.1	43.0	50.6	64.4	87.0	136.3	248.8	450.1	659.7	764.8
100°	48.8	50.2	53.0	60.6	73.9	94.8	135.3	225.9	401.6	629.6	803.9
102.5°	60.5	61.3	63.6	71.8	83.9	104.3	140.3	216.4	364.8	576.6	780.5
105°	78.8	78.8	82.3	89.3	100.4	119.9	150.6	212.7	329.1	505.5	705.6
107.5°	96.7	98.0	101.4	107.1	118.7	136.3	165.9	219.1	314.1	456.6	629.2
110°	109.5	110.8	113.6	119.9	130.4	148.5	177.1	225.2	309.6	433.6	585.7



TEST NUMBER: P333321-940

CATALOG NUMBER: S125DIP-S1270D810U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	122.3	123.7	125.9	132.2	142.7	160.2	187.7	233.0	309.6	420.3	553.3
115°	140.8	142.2	144.4	150.6	161.0	178.5	204.3	244.7	311.7	405.8	518.0
117.5°	157.6	159.7	161.9	168.2	180.0	196.9	221.3	258.2	316.3	398.7	497.0
120°	168.7	170.9	173.6	179.9	191.7	209.2	233.5	267.1	320.7	395.3	485.3
122.5°	180.5	182.0	184.2	190.5	203.5	220.9	245.3	277.1	324.6	392.5	475.2
125°	195.2	196.6	200.1	206.3	219.6	237.7	260.7	290.7	331.2	389.1	461.5
127.5°	206.8	208.9	213.4	221.3	235.4	253.5	275.7	303.3	338.6	387.4	449.0
130°	214.0	216.2	221.7	230.8	245.4	263.6	285.2	311.7	343.0	386.3	440.7
132.5°	219.6	222.3	229.0	239.2	254.3	272.5	294.1	318.9	348.0	386.3	434.0
135°	228.7	231.5	239.9	251.0	265.6	284.5	306.1	329.1	354.9	386.3	426.0
137.5°	240.1	242.2	250.0	261.2	275.5	294.9	314.6	336.6	361.1	387.1	418.9
140°	246.8	248.9	257.3	268.4	281.7	300.5	320.7	341.6	363.9	387.6	415.5
142.5°	254.6	256.2	263.9	275.1	287.8	305.5	324.6	344.5	365.6	388.3	412.8
145°	266.4	267.7	274.7	284.5	297.0	313.1	331.2	348.6	367.5	387.6	408.6
147.5°	278.6	279.5	285.4	294.5	305.4	319.5	335.4	351.2	368.1	385.8	404.2
150°	285.9	287.2	292.1	301.2	310.9	322.8	338.1	352.8	368.1	384.1	400.9
152.5°	293.6	294.5	298.8	306.7	316.0	326.7	340.9	353.9	367.6	381.9	397.0
155°	304.0	304.0	308.2	315.1	322.1	331.9	343.8	354.9	366.0	377.9	390.5
157.5°	313.2	313.1	316.4	322.4	328.5	335.9	346.1	355.6	364.3	373.7	384.3
160°	319.3	318.6	321.5	326.3	331.9	338.1	347.2	355.6	362.6	371.0	379.3
162.5°	324.3	323.7	326.5	330.7	335.2	340.4	348.3	355.0	360.9	367.6	374.8
165°	331.9	330.5	332.6	336.1	338.9	343.0	348.6	354.2	358.4	362.6	368.1
167.5°	336.9	336.2	337.4	339.4	341.3	344.0	348.6	352.5	354.5	357.7	361.6
170°	340.3	339.6	340.3	341.6	343.0	345.1	348.6	351.4	352.8	354.9	357.7
172.5°	342.5	341.3	341.9	343.3	344.1	345.1	348.0	350.3	350.5	351.5	353.7
175°	345.1	343.8	344.5	345.1	345.1	345.1	347.2	348.6	347.9	347.9	348.6
177.5°	346.3	345.3	345.3	345.8	345.3	345.3	346.3	347.0	345.8	345.8	346.3
180°	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8



TEST NUMBER: P333321-940

CATALOG NUMBER: S125DIP-S1270D810U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3
2.5°	1752.2	1754.7	1757.2	1758.3	1758.1	1757.8	1757.6	1757.3
5°	1743.4	1746.2	1749.0	1750.2	1749.9	1749.6	1749.3	1749.0
7.5°	1725.7	1728.5	1731.2	1732.4	1732.1	1731.8	1731.5	1731.2
10°	1710.8	1713.3	1715.7	1716.8	1716.5	1716.2	1715.9	1715.7
12.5°	1691.0	1692.9	1694.9	1695.9	1695.8	1695.7	1695.7	1695.6
15°	1656.2	1657.7	1659.2	1660.0	1660.0	1660.0	1660.0	1660.0
17.5°	1615.7	1617.7	1619.5	1619.7	1618.2	1616.7	1615.1	1613.6
20°	1585.1	1587.2	1589.4	1589.7	1588.1	1586.6	1585.1	1583.5
22.5°	1550.2	1551.7	1553.1	1553.3	1552.2	1551.1	1550.1	1549.1
25°	1494.4	1495.0	1495.7	1495.5	1494.6	1493.6	1492.7	1491.7
27.5°	1435.8	1436.0	1436.1	1435.7	1434.8	1433.9	1432.9	1432.0
30°	1393.2	1392.6	1392.0	1391.2	1390.3	1389.4	1388.4	1387.5
32.5°	1350.0	1348.9	1347.7	1346.3	1344.7	1343.0	1341.3	1339.7
35°	1282.9	1281.4	1279.9	1277.8	1275.3	1272.9	1270.4	1267.9
37.5°	1212.5	1210.2	1207.9	1206.0	1204.6	1203.2	1201.8	1200.3
40°	1163.7	1160.9	1158.1	1156.3	1155.3	1154.4	1153.4	1152.5
42.5°	1115.3	1112.7	1110.2	1108.2	1106.8	1105.4	1103.9	1102.5
45°	1043.7	1039.9	1036.3	1033.9	1033.0	1032.1	1031.1	1030.2
47.5°	968.1	964.4	960.6	957.7	955.5	953.3	951.2	949.0
50°	916.5	912.5	908.5	905.4	903.2	901.1	898.9	896.7
52.5°	866.3	862.8	859.3	856.3	853.9	851.5	849.1	846.7
55°	788.3	785.5	782.7	780.2	778.1	776.0	773.7	771.6
57.5°	710.8	707.2	703.6	701.2	700.1	698.9	697.7	696.5
60°	658.4	655.3	652.2	649.6	647.4	645.2	643.1	641.0
62.5°	607.8	604.5	601.2	598.7	597.0	595.3	593.6	592.0
65°	528.3	525.5	522.7	520.8	519.5	518.3	517.0	515.8
67.5°	452.5	450.0	447.7	446.2	445.4	444.7	444.0	443.2
70°	402.3	400.4	398.5	397.0	395.7	394.5	393.3	392.1
72.5°	355.1	352.9	350.9	349.2	347.9	346.7	345.4	344.2
75°	281.8	280.8	279.9	278.8	277.6	276.3	275.1	273.8
77.5°	214.6	214.1	213.6	212.9	212.0	211.1	210.3	209.4
80°	171.7	171.5	171.1	170.7	170.0	169.4	168.8	168.3
82.5°	131.3	130.7	130.1	129.8	129.7	129.6	129.4	129.3
85°	77.2	77.0	76.6	76.2	75.5	74.9	74.3	73.7
87.5°	31.4	31.6	31.7	31.7	31.2	30.8	30.4	29.9
90°	12.6	13.3	13.9	15.3	15.3	15.3	16.1	16.1
92.5°	123.6	89.7	67.5	57.2	48.2	46.5	45.6	44.5
95°	501.3	395.3	309.6	251.0	201.5	180.6	175.0	163.8
97.5°	746.6	672.3	588.7	507.3	464.2	425.2	404.9	396.0
100°	857.6	823.4	751.6	679.1	631.0	580.8	555.0	543.9
102.5°	894.9	916.1	881.5	832.5	781.0	745.3	717.3	708.9
105°	872.9	968.5	999.2	991.5	969.1	946.1	932.2	923.8
107.5°	794.2	921.8	1000.5	1036.9	1048.2	1048.0	1043.5	1037.9
110°	736.3	868.7	967.1	1026.3	1057.7	1070.9	1075.8	1075.8



TEST NUMBER: P333321-940

CATALOG NUMBER: S125DIP-S1270D810U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	690.5	816.3	915.7	985.6	1031.4	1054.2	1066.3	1071.4
115°	633.1	741.2	836.7	912.7	967.1	1000.5	1020.0	1029.1
117.5°	596.0	689.1	771.4	841.2	895.5	930.1	949.5	955.0
120°	575.9	659.6	736.3	797.6	849.2	882.7	901.5	907.0
122.5°	560.9	638.4	706.7	764.2	810.2	840.9	859.7	864.7
125°	539.0	610.1	670.7	720.9	760.0	788.5	803.9	810.8
127.5°	516.7	583.0	639.6	686.6	722.0	747.3	761.8	764.8
130°	502.7	564.1	618.4	663.8	698.7	721.7	735.6	739.8
132.5°	488.7	546.2	595.6	639.2	674.0	697.1	709.9	714.6
135°	470.6	518.7	563.4	603.1	633.7	656.7	669.3	673.5
137.5°	455.3	494.2	531.3	565.0	592.5	613.4	625.0	629.6
140°	446.9	479.7	511.8	541.0	566.9	585.0	595.4	598.9
142.5°	439.7	467.4	495.0	520.4	542.3	557.7	567.6	570.4
145°	430.2	451.8	473.4	492.2	509.0	520.8	528.5	531.3
147.5°	421.2	438.8	455.4	469.7	482.9	492.4	496.9	498.1
150°	416.3	431.6	444.8	457.4	467.9	476.2	479.0	479.7
152.5°	410.6	424.4	436.5	446.2	455.0	461.7	464.5	465.2
155°	402.3	413.5	423.2	430.9	437.8	442.7	444.8	445.5
157.5°	394.0	403.1	410.6	416.7	422.1	426.1	428.1	427.9
160°	388.3	395.3	402.3	407.2	412.1	415.5	417.0	416.3
162.5°	382.2	388.6	394.5	398.8	402.6	405.5	405.8	405.6
165°	373.7	378.6	382.8	386.3	389.1	390.5	390.5	390.5
167.5°	365.6	368.8	372.0	374.5	375.9	377.2	376.7	376.5
170°	361.1	363.3	365.3	366.8	368.1	368.8	368.8	368.1
172.5°	356.1	358.2	359.8	360.6	360.9	362.1	361.1	360.3
175°	350.7	350.7	352.1	352.1	352.1	352.8	351.4	350.7
177.5°	347.0	347.5	347.5	347.5	347.0	347.5	345.8	345.8
180°	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8

(END OF REPORT)