

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331690-830

Luminaire Tested: **SA2XXRDIP-C675D725U830-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331690-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C675D725U830-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 725 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4919.7 lumens
Efficiency: N/A
Efficacy: 107.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331690-830
CATALOG NUMBER: SA2XXRDIP-C675D725U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331690-830

CATALOG NUMBER: SA2XXRDIP-C675D725U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44				44
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44				38	
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38				33	
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	37	34	33				28	
4	74	64	56	51	68	59	52	47	50	45	41	41	37	35	33	30	28				25	
5	68	57	49	44	63	53	46	41	45	39	35	37	33	30	30	27	25				22	
6	63	51	44	38	58	48	41	36	40	35	31	34	30	27	27	24	22				19	
7	58	47	39	33	54	43	36	31	37	31	28	31	27	24	25	22	20				17	
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18				16	
9	51	39	31	27	46	36	29	25	31	26	22	26	22	19	21	18	16				14	
10	47	36	29	24	43	33	27	23	28	23	20	24	20	17	20	17	15				13	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17166	17166	17166
5°	17232	16951	17045
10°	17100	16674	16531
15°	16904	16181	15714
20°	16632	15474	14698
25°	16352	14672	13714
30°	15966	13848	12450
35°	15589	12952	11341
40°	15209	12026	10058
45°	14764	10985	8896
50°	14307	9934	7759
55°	13841	8802	6663
60°	13298	7611	5532
65°	12684	6395	5039
70°	11948	5268	4631
75°	11042	4803	4323
80°	9754	4296	3933
85°	7669	3390	3390



TEST NUMBER: P331690-830

CATALOG NUMBER: SA2XXRDIP-C675D725U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.5	2.0
10°-20°	273.3	5.6
20°-30°	383.7	7.8
30°-40°	418.4	8.5
40°-50°	384.7	7.8
50°-60°	302.2	6.1
60°-70°	197.0	4.0
70°-80°	101.6	2.1
80°-90°	28.7	0.6
90°-100°	31.1	0.6
100°-110°	114.0	2.3
110°-120°	304.7	6.2
120°-130°	502.9	10.2
130°-140°	534.9	10.9
140°-150°	497.1	10.1
150°-160°	399.7	8.1
160°-170°	257.6	5.2
170°-180°	88.7	1.8
0°-30°	756.5	15.4
0°-40°	1174.9	23.9
0°-60°	1861.8	37.8
0°-90°	2189.1	44.5
90°-120°	449.7	9.1
90°-150°	1984.7	40.3
90°-180°	2731.0	55.5
0°-180°	4919.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1063	1063	1063	1063	1063	
5°	1063	1058	1046	1054	1052	101
15°	1011	999	968	950	940	285
25°	918	885	824	786	770	422
35°	791	740	657	599	575	495
45°	647	580	481	415	390	499
55°	492	415	313	257	237	439
65°	332	254	167	136	132	329
75°	177	112	77	71	69	187
85°	41	22	18	18	18	49
90°	1	8	14	17	18	4
95°	44	23	26	29	29	54
105°	205	214	41	48	51	219
115°	388	399	416	118	55	382
125°	548	557	570	574	576	489
135°	678	689	695	701	700	524
145°	787	787	798	802	799	492
155°	866	861	868	872	867	399
165°	913	909	911	915	911	258
175°	934	929	930	934	928	89
180°	932	932	932	932	932	



TEST NUMBER: P331690-830

CATALOG NUMBER: SA2XXRDIP-C675D725U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2
2.5°	1067.1	1066.2	1065.4	1064.5	1063.7	1062.2	1060.4	1058.5	1056.7	1054.8	1056.5
5°	1063.2	1062.2	1061.1	1060.0	1058.9	1057.1	1054.2	1051.5	1048.7	1045.9	1047.8
7.5°	1052.3	1050.9	1049.6	1048.3	1047.0	1044.6	1041.4	1038.2	1034.9	1031.7	1032.2
10°	1043.0	1041.5	1040.0	1038.5	1037.0	1034.2	1029.8	1025.6	1021.3	1017.0	1016.4
12.5°	1031.4	1029.6	1027.7	1026.0	1024.1	1020.5	1015.0	1009.6	1004.0	998.5	997.4
15°	1011.3	1008.9	1006.5	1004.2	1001.8	997.0	989.8	982.5	975.2	968.0	963.9
17.5°	986.5	982.9	979.3	975.6	972.0	965.6	956.3	947.0	937.6	928.3	923.5
20°	968.0	963.7	959.4	955.2	950.8	943.4	932.6	922.0	911.3	900.6	895.2
22.5°	947.9	943.2	938.4	933.6	928.8	920.4	908.3	896.3	884.2	872.1	865.3
25°	917.9	911.1	904.3	897.4	890.6	880.1	866.0	851.9	837.7	823.6	814.8
27.5°	881.7	874.3	866.9	859.4	852.0	840.3	824.4	808.5	792.6	776.7	766.5
30°	856.4	848.2	840.1	832.0	823.9	811.2	794.1	777.0	759.9	742.8	731.9
32.5°	831.7	822.2	812.8	803.2	793.7	780.2	762.8	745.4	727.9	710.5	698.0
35°	790.9	780.0	769.1	758.2	747.3	732.4	713.6	694.8	676.0	657.1	643.7
37.5°	750.2	738.1	726.1	714.2	702.2	686.2	666.2	646.1	626.0	606.0	591.2
40°	721.6	708.8	696.0	683.2	670.3	653.6	632.8	612.1	591.4	570.6	555.4
42.5°	692.4	678.9	665.3	651.9	638.4	620.9	599.5	578.1	556.6	535.2	519.4
45°	646.6	632.3	617.9	603.6	589.3	570.9	548.5	526.0	503.5	481.1	465.9
47.5°	601.9	586.7	571.6	556.4	541.2	522.1	498.9	475.7	452.5	429.3	414.2
50°	569.6	554.4	539.2	524.1	508.9	489.6	466.0	442.5	419.0	395.5	380.7
52.5°	538.1	522.2	506.3	490.5	474.6	455.2	432.2	409.2	386.2	363.2	348.9
55°	491.7	475.0	458.4	441.7	425.0	405.1	382.0	358.9	335.8	312.7	299.9
57.5°	444.1	427.1	409.9	392.9	375.7	356.1	333.8	311.7	289.5	267.3	255.5
60°	411.8	394.7	377.6	360.5	343.4	323.9	301.8	279.7	257.8	235.7	224.8
62.5°	380.2	363.2	346.0	328.9	311.8	292.8	271.8	250.8	229.8	208.8	198.4
65°	332.0	314.6	297.3	280.0	262.7	244.4	225.2	205.9	186.6	167.4	160.1
67.5°	285.4	268.2	251.0	233.8	216.6	199.3	182.0	164.8	147.4	130.1	126.8
70°	253.1	236.4	219.7	203.0	186.3	170.6	155.9	141.1	126.4	111.6	109.4
72.5°	222.3	206.2	190.3	174.3	158.3	144.4	132.5	120.6	108.9	97.0	95.2
75°	177.0	162.1	147.1	132.1	117.2	106.0	98.8	91.5	84.3	77.0	75.5
77.5°	132.6	119.4	106.3	93.2	80.1	71.7	68.2	64.8	61.3	57.8	56.8
80°	104.9	94.0	83.0	72.2	61.3	54.8	52.6	50.4	48.4	46.2	45.3
82.5°	79.5	71.0	62.5	53.9	45.4	40.4	39.0	37.5	36.1	34.7	34.1
85°	41.4	36.9	32.4	27.9	23.4	20.8	20.2	19.6	18.9	18.3	18.3
87.5°	12.4	11.4	10.4	9.3	8.3	7.9	8.1	8.4	8.6	8.9	8.9
90°	0.7	2.4	4.0	5.7	7.3	8.7	9.9	11.1	12.3	13.5	14.2
92.5°	13.6	13.5	13.3	13.2	13.0	13.3	13.9	14.4	15.1	15.6	16.0
95°	43.8	38.9	33.9	29.0	24.0	22.1	23.2	24.2	25.3	26.3	27.1
97.5°	87.0	73.0	59.1	45.1	31.2	25.4	27.9	30.3	32.8	35.2	35.8
100°	119.3	98.8	78.3	57.8	37.2	28.3	30.8	33.4	35.9	38.5	39.6
102.5°	155.0	150.6	146.3	141.9	137.5	124.7	103.4	82.1	60.8	39.5	41.1
105°	205.0	209.4	214.0	218.5	222.9	204.7	163.8	122.9	82.0	41.1	42.8
107.5°	262.0	265.6	269.3	272.9	276.5	253.8	204.7	155.7	106.6	57.6	55.9
110°	298.7	301.8	305.0	308.1	311.2	291.2	247.9	204.6	161.3	118.0	103.0



TEST NUMBER: P331690-830

CATALOG NUMBER: SA2XXRDIP-C675D725U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	333.2	336.0	338.7	341.6	344.3	340.4	329.7	319.0	308.3	297.6	243.0
115°	387.7	390.2	392.8	395.3	397.8	401.1	404.7	408.5	412.3	416.0	346.7
117.5°	436.4	439.2	442.1	444.9	447.7	450.4	453.1	455.6	458.2	460.8	444.0
120°	471.9	474.2	476.5	478.7	481.0	483.4	486.2	488.8	491.5	494.2	496.0
122.5°	502.2	504.5	506.9	509.3	511.6	514.3	517.3	520.2	523.1	526.0	527.1
125°	548.2	550.1	552.0	554.0	555.9	558.4	561.2	564.0	566.8	569.8	570.8
127.5°	589.8	592.0	594.2	596.3	598.4	600.6	602.8	604.8	607.0	609.1	610.7
130°	616.2	618.7	621.0	623.4	625.8	627.8	629.5	631.1	632.8	634.4	636.1
132.5°	643.2	645.3	647.3	649.3	651.4	653.2	654.9	656.5	658.2	659.8	661.2
135°	678.3	680.7	683.1	685.5	687.9	689.8	691.1	692.4	693.8	695.1	696.6
137.5°	713.8	715.4	717.1	718.8	720.5	722.1	723.6	725.1	726.6	728.2	729.6
140°	737.0	738.1	739.3	740.6	741.7	743.2	744.8	746.5	748.1	749.8	751.1
142.5°	756.4	757.4	758.6	759.6	760.6	762.1	764.0	765.9	767.8	769.7	770.9
145°	786.8	786.6	786.6	786.4	786.3	787.4	789.9	792.5	795.0	797.6	798.7
147.5°	813.4	812.8	812.3	811.7	811.2	812.1	814.6	817.1	819.6	822.2	822.9
150°	830.7	829.6	828.6	827.6	826.4	827.2	829.5	831.9	834.3	836.7	837.6
152.5°	845.2	844.0	842.9	841.7	840.6	841.1	843.4	845.6	847.9	850.2	851.1
155°	866.4	865.1	863.7	862.3	861.0	861.2	863.0	864.8	866.6	868.4	869.3
157.5°	883.0	881.8	880.7	879.6	878.4	878.4	879.8	881.0	882.2	883.5	884.6
160°	892.7	891.7	890.9	889.9	889.1	889.1	889.9	890.9	891.7	892.7	893.6
162.5°	901.4	900.4	899.6	898.6	897.7	897.7	898.4	899.2	900.0	900.8	901.8
165°	912.9	912.0	911.2	910.2	909.3	909.1	909.6	910.0	910.4	910.9	911.9
167.5°	921.5	920.7	919.7	918.9	917.9	917.7	918.1	918.5	919.0	919.4	920.4
170°	926.4	925.5	924.6	923.7	922.8	922.5	922.8	923.1	923.4	923.7	924.7
172.5°	929.6	928.7	927.8	926.9	926.0	925.8	926.0	926.3	926.6	926.9	928.0
175°	933.8	932.7	931.7	930.7	929.6	929.3	929.5	929.8	930.1	930.5	931.5
177.5°	934.5	933.7	932.8	932.0	931.1	930.8	930.9	931.0	931.1	931.2	932.1
180°	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8



TEST NUMBER: P331690-830

CATALOG NUMBER: SA2XXRDIP-C675D725U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2
2.5°	1058.2	1059.9	1061.6	1062.2	1062.0	1061.6	1061.3	1060.9
5°	1049.7	1051.7	1053.6	1054.2	1053.6	1052.9	1052.3	1051.7
7.5°	1032.7	1033.3	1033.9	1033.6	1032.5	1031.4	1030.3	1029.2
10°	1015.8	1015.1	1014.5	1013.5	1012.2	1011.0	1009.7	1008.3
12.5°	996.3	995.1	993.9	992.3	990.1	988.1	985.9	983.7
15°	959.9	955.7	951.7	948.6	946.5	944.3	942.2	940.1
17.5°	918.7	913.8	909.0	904.7	901.1	897.4	893.7	890.0
20°	889.9	884.6	879.2	874.2	869.5	864.8	860.1	855.4
22.5°	858.4	851.5	844.6	839.4	835.8	832.4	828.9	825.4
25°	806.1	797.3	788.5	782.6	779.4	776.2	773.0	769.8
27.5°	756.2	746.0	735.8	728.1	723.0	717.9	712.8	707.8
30°	721.0	710.1	699.2	690.9	685.0	679.3	673.5	667.8
32.5°	685.6	673.2	660.7	651.8	646.3	640.9	635.5	630.1
35°	630.3	616.8	603.3	594.2	589.5	584.8	580.1	575.4
37.5°	576.3	561.5	546.7	536.5	531.1	525.8	520.4	515.0
40°	540.2	525.0	509.8	499.5	493.9	488.3	482.8	477.2
42.5°	503.8	488.0	472.4	461.8	456.5	451.1	445.7	440.3
45°	450.7	435.5	420.4	410.2	405.1	399.9	394.8	389.6
47.5°	399.2	384.1	368.9	359.1	354.4	349.8	345.1	340.4
50°	366.0	351.2	336.5	326.8	322.3	317.8	313.4	308.9
52.5°	334.7	320.4	306.1	297.0	292.8	288.7	284.6	280.4
55°	287.1	274.2	261.4	253.0	248.9	244.8	240.7	236.7
57.5°	243.7	232.1	220.3	212.6	209.2	205.9	202.4	199.0
60°	214.0	203.0	192.1	184.9	181.5	178.1	174.7	171.3
62.5°	188.0	177.6	167.2	161.0	158.9	156.9	154.9	152.8
65°	152.9	145.6	138.4	134.4	133.7	133.1	132.4	131.9
67.5°	123.4	120.1	116.8	114.7	114.0	113.4	112.7	112.0
70°	107.4	105.2	103.0	101.6	100.7	99.8	99.0	98.1
72.5°	93.4	91.6	89.8	88.7	88.1	87.7	87.1	86.6
75°	74.0	72.5	71.0	70.1	69.9	69.7	69.5	69.3
77.5°	56.0	55.1	54.3	53.7	53.3	53.1	52.7	52.3
80°	44.5	43.6	42.8	42.3	42.3	42.3	42.3	42.3
82.5°	33.6	33.1	32.6	32.3	32.3	32.3	32.3	32.3
85°	18.3	18.3	18.3	18.3	18.3	18.3	18.3	18.3
87.5°	8.8	8.8	8.8	8.8	8.9	9.0	9.0	9.0
90°	15.0	15.7	16.5	17.0	17.3	17.6	17.9	18.2
92.5°	16.4	16.8	17.2	17.5	17.6	17.8	18.0	18.2
95°	27.8	28.6	29.3	29.6	29.4	29.3	29.1	29.0
97.5°	36.4	36.9	37.6	38.0	38.2	38.4	38.5	38.7
100°	40.8	42.0	43.3	44.0	44.3	44.6	44.9	45.1
102.5°	42.6	44.2	45.7	46.8	47.1	47.6	48.0	48.4
105°	44.4	46.1	47.7	48.8	49.5	50.0	50.6	51.3
107.5°	54.2	52.5	50.9	50.3	50.9	51.6	52.1	52.7
110°	88.0	73.0	58.1	50.9	51.5	52.0	52.7	53.3



TEST NUMBER: P331690-830

CATALOG NUMBER: SA2XXRDIP-C675D725U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	188.3	133.7	79.0	51.8	52.4	52.9	53.3	53.8
115°	277.3	207.9	138.6	98.4	87.7	76.8	66.1	55.3
117.5°	427.3	410.4	393.6	367.5	332.1	296.6	261.2	225.7
120°	497.9	499.6	501.4	492.2	471.9	451.8	431.5	411.3
122.5°	528.2	529.2	530.4	529.0	525.0	521.0	517.2	513.2
125°	571.8	572.9	573.9	574.7	575.1	575.6	576.0	576.5
127.5°	612.2	613.7	615.2	616.0	616.1	616.2	616.3	616.4
130°	637.7	639.4	641.0	641.8	641.7	641.5	641.3	641.2
132.5°	662.6	664.0	665.4	666.1	665.9	665.8	665.6	665.4
135°	698.1	699.6	701.2	701.7	701.4	701.2	700.8	700.5
137.5°	731.1	732.5	734.1	734.5	734.1	733.5	733.0	732.4
140°	752.4	753.8	755.2	755.4	754.7	753.9	753.2	752.4
142.5°	772.1	773.4	774.6	774.9	774.1	773.4	772.6	771.8
145°	799.7	800.8	801.8	801.9	801.3	800.5	799.7	799.0
147.5°	823.7	824.5	825.3	825.4	824.7	824.1	823.5	822.8
150°	838.5	839.4	840.3	840.4	839.6	838.9	838.1	837.4
152.5°	852.0	852.9	853.8	853.8	852.8	851.8	850.8	849.8
155°	870.2	871.1	872.0	871.9	870.6	869.5	868.3	867.0
157.5°	885.5	886.6	887.6	887.5	886.4	885.1	884.0	882.9
160°	894.5	895.4	896.3	896.2	895.1	894.1	893.1	892.0
162.5°	902.8	903.8	904.8	904.7	903.4	902.1	900.9	899.6
165°	912.9	914.1	915.1	915.1	914.1	912.9	911.9	910.9
167.5°	921.5	922.6	923.6	923.4	922.1	920.8	919.4	918.0
170°	925.8	926.8	927.9	927.7	926.4	925.0	923.7	922.4
172.5°	929.1	930.1	931.1	930.9	929.6	928.3	926.9	925.6
175°	932.6	933.6	934.6	934.4	932.9	931.4	929.9	928.4
177.5°	932.9	933.8	934.6	934.5	933.4	932.4	931.2	930.2
180°	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8

(END OF REPORT)