

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333151-940

Luminaire Tested: **S125DIP-S375D1205U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333151-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S375D1205U940-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5665.8 lumens
Efficiency: N/A
Efficacy: 134.3 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333151-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333151-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24
1	92	88	84	81	82	78	75	73	60	58	57	44	43	42	29	28	28	21
2	84	77	71	66	74	69	64	60	53	50	47	39	37	35	25	24	23	17
3	77	68	61	55	68	60	55	50	47	43	40	34	32	30	23	21	20	15
4	70	60	52	47	62	53	47	42	42	37	34	30	28	25	20	19	17	13
5	64	53	45	40	57	48	41	36	37	32	29	27	24	22	18	16	15	11
6	59	47	40	34	52	43	36	31	33	29	25	25	21	19	16	15	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12	9
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10	8
9	47	35	28	23	41	32	25	21	25	20	17	19	15	13	13	11	9	7
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3135	3135	3135	3135
5°	3630	3146	2755	3146
10°	4224	3129	2413	3129
15°	4676	3107	2226	3107
20°	5234	3070	2076	3070
25°	6131	3029	2003	3029
30°	6623	2988	1939	2988
35°	5445	2912	1898	2912
40°	3871	2807	1851	2807
45°	2974	2665	1825	2665
50°	2538	2488	1822	2488
55°	2260	2315	1838	2315
60°	2038	2126	1885	2126
65°	1883	1936	1933	1936
70°	1713	1739	1962	1739
75°	1510	1532	1941	1532
80°	1272	1250	1778	1250
85°	1008	897	1438	897



TEST NUMBER: P333151-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.7	0.8
10°-20°	139.1	2.5
20°-30°	225.9	4.0
30°-40°	275.6	4.9
40°-50°	250.7	4.4
50°-60°	199.7	3.5
60°-70°	139.1	2.5
70°-80°	74.2	1.3
80°-90°	21.6	0.4
90°-100°	50.8	0.9
100°-110°	313.1	5.5
110°-120°	567.9	10.0
120°-130°	728.8	12.9
130°-140°	783.9	13.8
140°-150°	735.8	13.0
150°-160°	595.2	10.5
160°-170°	384.9	6.8
170°-180°	132.8	2.3
0°-30°	411.8	7.3
0°-40°	687.4	12.1
0°-60°	1137.8	20.1
0°-90°	1372.7	24.2
90°-120°	931.8	16.4
90°-150°	3180.2	56.1
90°-180°	4293.0	75.8
0°-180°	5665.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	485	485	485	485	485	
5°	560	485	425	485	560	56
15°	699	465	333	465	699	200
25°	860	425	281	425	860	393
35°	691	369	241	369	691	423
45°	326	292	200	292	326	261
55°	201	206	163	206	201	181
65°	123	127	126	127	123	122
75°	60	61	78	61	60	65
85°	14	12	19	12	14	16
90°	25	1	25	1	25	11
95°	22	59	22	59	22	18
105°	308	305	308	305	308	278
115°	568	572	568	572	568	564
125°	814	814	814	814	814	724
135°	1010	1015	1010	1015	1010	780
145°	1173	1176	1173	1176	1173	733
155°	1286	1295	1286	1295	1286	593
165°	1360	1367	1360	1367	1360	384
175°	1392	1398	1392	1398	1392	132
180°	1398	1398	1398	1398	1398	



TEST NUMBER: P333151-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	513.4	512.8	512.1	510.9	511.8	509.0	507.7	505.4	502.6	501.6	500.4
5°	560.0	561.1	562.1	557.8	558.2	555.3	548.7	543.3	539.0	533.4	529.5
7.5°	616.1	613.7	613.4	610.6	605.8	601.9	595.0	586.2	577.7	567.9	559.9
10°	644.1	644.4	642.5	639.2	634.0	630.3	621.3	612.6	602.1	589.7	580.9
12.5°	665.2	666.1	663.7	659.2	656.7	648.5	641.3	631.1	618.6	608.7	595.2
15°	699.3	697.1	695.4	689.8	685.5	676.9	665.6	654.8	641.2	628.7	616.1
17.5°	732.2	734.1	730.9	725.9	712.4	702.3	687.2	672.4	655.5	638.6	623.7
20°	761.5	763.2	758.5	749.6	733.5	723.4	703.5	684.5	664.9	643.3	626.8
22.5°	798.2	796.8	790.4	776.9	763.0	744.4	722.7	699.6	675.1	650.7	628.7
25°	860.4	851.8	847.8	831.2	812.9	785.4	755.8	722.0	691.5	659.2	631.2
27.5°	895.0	892.2	887.9	876.3	857.0	827.7	792.7	751.5	708.6	667.7	631.0
30°	888.1	888.5	888.9	885.2	872.8	850.8	815.9	771.7	720.5	674.6	632.1
32.5°	826.7	834.2	841.4	849.9	853.4	849.1	827.3	787.3	734.7	682.5	631.5
35°	690.6	692.9	716.2	739.3	770.6	795.0	811.2	793.4	749.2	689.2	630.7
37.5°	538.5	549.7	565.8	591.8	637.0	677.5	729.6	753.5	739.2	691.4	629.3
40°	459.1	469.4	479.9	506.5	544.6	593.6	652.7	703.2	715.0	684.5	624.3
42.5°	397.8	405.9	417.6	437.6	469.4	512.8	569.4	635.3	675.9	664.4	613.9
45°	325.6	330.7	339.7	355.6	378.7	412.7	462.5	534.7	597.5	618.3	589.3
47.5°	278.7	278.7	285.7	296.6	313.3	342.1	379.1	435.5	502.7	552.3	550.0
50°	252.6	251.6	257.2	266.6	279.8	299.0	334.2	379.3	443.8	500.1	515.8
52.5°	230.2	230.3	233.7	240.8	251.8	268.1	294.4	335.2	390.2	448.0	477.5
55°	200.7	199.8	203.8	208.5	216.6	227.3	246.2	277.3	322.1	378.9	417.2
57.5°	173.6	175.9	177.5	180.7	187.4	194.7	210.6	233.4	268.9	317.7	358.2
60°	157.8	160.1	161.3	164.6	170.0	176.2	188.5	207.1	236.9	279.0	319.1
62.5°	143.7	145.4	145.9	148.8	153.2	159.2	168.9	184.5	208.1	244.9	284.2
65°	123.2	123.2	124.0	127.2	129.2	134.6	142.0	153.3	172.3	200.9	234.5
67.5°	103.5	104.5	104.3	105.7	107.5	111.7	117.0	126.4	140.4	161.3	188.2
70°	90.7	91.5	91.3	92.3	94.3	97.0	101.4	110.2	120.3	138.2	161.3
72.5°	79.1	79.5	78.9	80.3	81.5	83.8	88.7	93.5	102.8	118.0	137.0
75°	60.5	61.0	61.4	62.2	63.5	64.7	67.1	71.9	78.1	89.4	101.6
77.5°	45.4	44.6	45.7	45.5	46.2	47.2	49.3	51.8	56.9	64.1	73.5
80°	34.2	34.4	34.4	34.6	35.7	36.3	38.1	39.9	43.9	49.2	55.8
82.5°	25.0	25.5	25.1	25.6	26.4	26.8	27.9	29.4	31.7	35.9	40.7
85°	13.6	12.6	13.0	13.4	13.4	13.6	14.4	15.1	16.3	17.9	19.8
87.5°	8.9	9.1	9.2	9.0	9.0	8.8	9.3	9.1	9.3	9.5	9.9
90°	24.9	24.2	23.5	22.8	22.1	21.2	20.1	18.9	17.7	16.6	15.0
92.5°	23.2	22.9	22.6	22.2	21.9	21.2	20.1	18.9	17.7	16.6	15.2
95°	21.8	21.8	21.8	21.8	21.8	21.2	20.1	18.9	17.7	16.6	25.3
97.5°	21.8	21.8	21.8	21.8	21.8	25.0	31.5	38.0	44.5	51.0	68.3
100°	21.8	22.6	23.6	24.5	25.4	43.1	77.4	111.7	146.0	180.3	179.4
102.5°	130.4	146.1	161.7	177.4	193.1	204.1	210.6	217.0	223.6	230.1	229.5
105°	307.8	308.0	308.3	308.4	308.7	308.8	308.8	308.8	308.8	308.8	308.8
107.5°	388.0	388.7	389.4	390.0	390.7	391.1	391.0	391.0	390.9	390.9	390.5
110°	443.5	443.4	443.1	442.8	442.6	442.8	443.5	444.3	445.0	445.6	445.1



TEST NUMBER: P333151-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	493.3	493.7	493.9	494.3	494.5	495.2	496.1	497.0	497.8	498.6	498.4
115°	567.9	569.3	570.7	572.0	573.5	574.6	575.5	576.4	577.4	578.3	578.0
117.5°	647.5	648.1	648.7	649.3	649.9	650.8	652.0	653.2	654.4	655.6	654.7
120°	696.4	697.6	698.7	699.9	701.1	701.9	702.3	702.8	703.2	703.6	702.9
122.5°	742.9	744.2	745.5	746.8	748.1	749.1	749.6	750.0	750.5	750.9	750.6
125°	813.5	814.2	814.9	815.6	816.3	817.1	818.0	818.9	819.8	820.7	820.7
127.5°	873.0	874.7	876.4	878.2	879.9	880.9	881.5	881.9	882.4	883.0	883.1
130°	916.1	917.3	918.5	919.5	920.7	921.7	922.3	923.0	923.7	924.4	924.2
132.5°	955.9	957.1	958.2	959.4	960.6	961.2	961.3	961.4	961.6	961.7	962.2
135°	1010.4	1011.8	1013.2	1014.6	1015.9	1016.9	1017.4	1017.8	1018.2	1018.7	1019.1
137.5°	1065.1	1066.3	1067.6	1068.7	1070.0	1070.5	1070.4	1070.3	1070.2	1070.1	1070.5
140°	1097.5	1098.9	1100.3	1101.6	1103.0	1103.5	1103.0	1102.5	1102.1	1101.6	1101.9
142.5°	1128.2	1129.5	1131.0	1132.3	1133.7	1134.3	1134.3	1134.2	1134.1	1134.0	1133.6
145°	1173.1	1174.5	1175.9	1177.2	1178.7	1179.2	1179.0	1178.8	1178.6	1178.3	1178.3
147.5°	1210.2	1211.9	1213.5	1215.2	1216.8	1217.5	1217.3	1217.0	1216.7	1216.5	1216.2
150°	1234.3	1236.1	1238.0	1239.8	1241.6	1242.3	1241.9	1241.4	1240.9	1240.5	1240.0
152.5°	1256.7	1258.3	1260.0	1261.6	1263.3	1263.9	1263.5	1262.9	1262.5	1262.0	1261.6
155°	1286.1	1287.9	1289.8	1291.6	1293.4	1294.1	1293.3	1292.6	1292.0	1291.3	1290.8
157.5°	1310.7	1312.6	1314.5	1316.3	1318.1	1318.7	1317.9	1317.2	1316.4	1315.7	1315.7
160°	1326.5	1328.4	1330.2	1332.0	1333.9	1334.4	1333.4	1332.5	1331.6	1330.6	1330.4
162.5°	1340.6	1342.6	1344.6	1346.7	1348.7	1349.1	1347.8	1346.5	1345.2	1343.9	1343.7
165°	1359.7	1361.5	1363.3	1365.2	1367.0	1367.3	1365.9	1364.5	1363.2	1361.7	1361.5
167.5°	1373.0	1375.0	1377.1	1379.1	1381.3	1381.4	1379.7	1378.1	1376.4	1374.8	1374.6
170°	1380.4	1382.5	1384.6	1386.6	1388.7	1388.8	1387.0	1385.1	1383.3	1381.4	1381.2
172.5°	1385.4	1387.4	1389.6	1391.6	1393.7	1393.8	1392.2	1390.5	1388.9	1387.2	1386.8
175°	1391.8	1393.8	1396.0	1398.0	1400.1	1400.2	1398.4	1396.5	1394.6	1392.9	1392.6
177.5°	1395.5	1397.0	1398.5	1400.0	1401.4	1401.5	1400.3	1398.9	1397.7	1396.3	1396.2
180°	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0



TEST NUMBER: P333151-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	499.4	498.3	497.0	494.6	491.9	490.4	488.1	486.6	483.7	481.2	478.5
5°	524.8	519.4	514.5	508.1	501.1	496.6	491.2	485.3	479.0	472.7	465.7
7.5°	551.1	541.5	531.3	520.2	509.3	499.4	489.8	480.5	471.8	461.2	452.3
10°	568.6	556.7	543.9	529.0	514.2	501.5	488.6	477.2	465.7	453.3	442.4
12.5°	586.3	570.4	552.3	535.8	518.3	502.8	487.6	473.1	458.6	444.9	432.1
15°	598.8	584.8	568.1	544.6	524.8	503.5	483.4	464.7	447.1	431.9	415.8
17.5°	607.0	588.9	571.0	548.5	522.5	498.8	475.9	454.4	434.7	415.4	399.9
20°	608.4	589.9	571.1	549.1	522.5	495.3	472.4	446.7	425.5	405.5	386.6
22.5°	608.0	586.9	566.5	543.9	517.9	492.8	465.2	439.0	415.9	396.3	376.5
25°	603.3	580.9	555.3	532.4	506.8	480.3	452.3	425.1	401.6	379.2	359.5
27.5°	599.4	570.3	541.4	514.7	490.0	465.7	438.8	411.0	385.0	362.2	343.8
30°	594.7	562.7	530.1	502.3	477.0	453.3	427.9	400.7	373.5	351.3	331.5
32.5°	590.4	553.1	518.8	488.5	461.6	438.6	415.3	389.4	362.7	340.1	320.3
35°	582.1	539.0	499.6	465.5	436.8	413.1	393.5	369.4	344.9	323.1	304.2
37.5°	571.6	520.5	478.2	442.4	411.0	386.0	367.8	349.3	325.7	304.7	287.6
40°	563.3	507.3	462.5	425.9	393.3	367.4	350.4	333.0	313.4	293.8	275.7
42.5°	552.9	495.4	446.7	407.2	375.1	349.7	332.0	317.2	299.9	281.6	264.8
45°	533.9	473.9	421.2	378.7	346.2	321.2	302.9	291.8	278.7	261.4	247.3
47.5°	505.8	448.1	393.5	349.7	316.1	293.0	275.8	265.1	256.0	243.2	230.2
50°	480.9	428.8	373.5	330.1	296.5	273.2	257.3	247.6	239.9	230.0	219.0
52.5°	453.1	404.6	353.9	310.9	277.7	254.8	239.2	230.7	224.2	217.1	206.3
55°	408.8	367.6	320.6	279.8	249.1	226.7	213.0	205.6	200.3	194.9	188.3
57.5°	360.1	327.8	286.2	248.9	220.6	200.2	187.5	180.3	176.1	173.3	169.5
60°	325.7	298.2	262.3	228.3	200.7	182.5	170.2	164.6	161.1	158.9	156.0
62.5°	293.9	271.3	238.1	207.1	182.9	165.8	154.7	149.3	146.0	144.8	142.5
65°	247.1	229.5	202.2	176.4	155.8	141.2	131.9	126.7	124.7	123.4	123.6
67.5°	200.8	190.2	168.2	146.2	129.7	117.5	110.0	106.1	105.0	103.4	103.4
70°	172.6	164.6	146.1	126.9	112.3	102.8	96.2	92.1	91.0	90.2	90.1
72.5°	147.8	140.7	124.7	109.3	96.1	87.8	82.4	79.9	78.2	77.8	77.7
75°	111.0	107.2	94.3	82.2	73.1	67.4	63.7	61.4	60.2	59.9	60.2
77.5°	78.9	75.5	67.4	58.8	53.1	48.7	45.6	44.8	43.4	43.4	43.2
80°	59.3	57.1	51.9	45.1	40.4	36.6	35.0	33.6	33.2	32.5	33.2
82.5°	43.0	40.6	37.1	32.7	28.8	26.7	25.0	24.5	24.3	24.0	24.1
85°	21.2	21.4	19.4	16.1	14.4	13.2	12.1	12.1	11.9	11.8	11.9
87.5°	9.9	9.3	8.3	7.5	6.2	5.4	4.9	4.6	4.5	4.7	5.3
90°	13.4	11.8	10.2	8.4	6.6	4.7	2.9	1.1	2.9	4.7	6.6
92.5°	13.7	12.3	10.9	10.8	12.1	13.4	14.7	16.0	14.7	13.4	12.1
95°	34.1	42.8	51.6	56.3	57.0	57.7	58.4	59.0	58.4	57.7	57.0
97.5°	85.6	102.9	120.3	128.3	127.1	125.8	124.6	123.3	124.6	125.8	127.1
100°	178.5	177.5	176.6	175.8	175.1	174.4	173.8	173.1	173.8	174.4	175.1
102.5°	229.0	228.4	227.8	227.1	226.2	225.4	224.5	223.6	224.5	225.4	226.2
105°	308.8	308.8	308.8	308.4	307.5	306.5	305.6	304.7	305.6	306.5	307.5
107.5°	389.9	389.5	389.1	388.9	388.9	388.9	388.9	388.9	388.9	388.9	388.9
110°	444.7	444.3	443.8	443.5	443.5	443.5	443.5	443.5	443.5	443.5	443.5



TEST NUMBER: P333151-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	498.1	497.8	497.6	497.1	496.6	496.1	495.5	495.0	495.5	496.1	496.6
115°	577.8	577.6	577.4	576.7	575.5	574.4	573.2	572.0	573.2	574.4	575.5
117.5°	653.8	653.0	652.1	651.7	651.8	651.8	651.8	651.8	651.8	651.8	651.8
120°	702.3	701.6	700.9	700.7	700.9	701.2	701.3	701.6	701.3	701.2	700.9
122.5°	750.3	749.9	749.7	749.0	748.1	747.3	746.5	745.6	746.5	747.3	748.1
125°	820.7	820.7	820.7	819.9	818.3	816.7	815.1	813.5	815.1	816.7	818.3
127.5°	883.2	883.3	883.5	883.0	881.8	880.7	879.6	878.4	879.6	880.7	881.8
130°	924.0	923.7	923.5	922.8	921.7	920.5	919.4	918.2	919.4	920.5	921.7
132.5°	962.7	963.2	963.8	963.3	962.0	960.6	959.3	958.0	959.3	960.6	962.0
135°	1019.7	1020.1	1020.6	1020.1	1018.7	1017.4	1015.9	1014.6	1015.9	1017.4	1018.7
137.5°	1070.9	1071.4	1071.7	1071.4	1070.1	1069.0	1067.8	1066.6	1067.8	1069.0	1070.1
140°	1102.1	1102.3	1102.5	1102.4	1102.0	1101.5	1101.1	1100.5	1101.1	1101.5	1102.0
142.5°	1133.3	1133.0	1132.7	1132.4	1132.1	1131.8	1131.5	1131.2	1131.5	1131.8	1132.1
145°	1178.3	1178.3	1178.3	1178.0	1177.6	1177.1	1176.7	1176.3	1176.7	1177.1	1177.6
147.5°	1215.8	1215.6	1215.3	1215.2	1215.3	1215.4	1215.5	1215.6	1215.5	1215.4	1215.3
150°	1239.6	1239.1	1238.7	1238.7	1239.1	1239.6	1240.0	1240.5	1240.0	1239.6	1239.1
152.5°	1261.1	1260.7	1260.2	1260.4	1261.5	1262.5	1263.6	1264.5	1263.6	1262.5	1261.5
155°	1290.3	1289.9	1289.4	1289.9	1291.3	1292.6	1294.1	1295.4	1294.1	1292.6	1291.3
157.5°	1315.6	1315.6	1315.5	1315.9	1316.8	1317.6	1318.4	1319.3	1318.4	1317.6	1316.8
160°	1330.2	1330.0	1329.7	1330.3	1331.7	1333.1	1334.4	1335.9	1334.4	1333.1	1331.7
162.5°	1343.5	1343.2	1343.0	1343.5	1345.0	1346.3	1347.7	1349.1	1347.7	1346.3	1345.0
165°	1361.3	1361.0	1360.8	1361.4	1362.8	1364.1	1365.6	1366.9	1365.6	1364.1	1362.8
167.5°	1374.3	1374.1	1373.9	1374.5	1375.9	1377.3	1378.8	1380.2	1378.8	1377.3	1375.9
170°	1381.0	1380.7	1380.5	1381.2	1382.8	1384.4	1386.1	1387.7	1386.1	1384.4	1382.8
172.5°	1386.4	1386.0	1385.5	1386.2	1387.8	1389.4	1391.0	1392.6	1391.0	1389.4	1387.8
175°	1392.4	1392.1	1391.9	1392.5	1393.8	1395.3	1396.6	1398.0	1396.6	1395.3	1393.8
177.5°	1396.0	1395.8	1395.6	1396.1	1397.2	1398.3	1399.4	1400.5	1399.4	1398.3	1397.2
180°	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0



TEST NUMBER: P333151-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	477.1	475.2	473.8	470.5	468.6	466.2	464.2	466.4	464.0	465.0	463.5
5°	462.2	456.4	452.3	446.3	441.1	436.4	432.9	432.3	430.6	429.8	427.3
7.5°	444.3	437.0	430.0	422.1	415.5	408.8	404.6	401.0	398.7	395.6	393.4
10°	433.7	424.0	415.8	406.4	398.1	390.8	385.1	382.2	379.5	375.6	374.2
12.5°	420.7	410.7	400.6	390.5	382.5	374.5	369.6	365.2	363.4	359.0	358.6
15°	405.1	390.0	380.1	369.9	358.9	352.3	348.2	343.5	341.4	338.3	336.1
17.5°	386.5	373.0	360.7	350.0	340.6	335.1	329.9	326.7	323.2	321.1	317.4
20°	372.9	360.2	347.8	336.4	329.2	322.9	318.8	315.7	311.9	310.9	307.2
22.5°	361.6	347.5	335.6	326.1	318.3	311.0	306.6	304.4	301.9	298.7	298.0
25°	343.0	328.4	318.3	308.9	301.8	295.2	292.2	289.5	287.0	284.7	283.9
27.5°	327.1	314.0	302.0	293.5	287.3	281.3	278.7	275.4	273.6	271.7	269.5
30°	315.8	302.5	291.9	283.7	277.1	271.8	268.9	266.6	265.0	263.3	262.1
32.5°	304.3	291.9	281.8	273.7	267.1	263.1	260.5	258.9	257.1	255.1	253.5
35°	289.1	275.4	265.6	258.6	253.4	250.3	247.4	246.0	244.0	244.0	242.3
37.5°	271.9	260.1	251.4	245.0	240.4	237.6	234.5	233.5	232.2	231.3	230.8
40°	261.7	250.7	242.5	236.1	231.2	228.9	226.4	224.8	224.0	222.9	222.6
42.5°	251.1	240.7	232.8	226.9	222.6	220.7	218.4	217.2	215.5	214.2	213.9
45°	235.1	225.0	217.8	213.0	209.4	207.1	205.6	203.1	202.3	200.7	200.5
47.5°	219.9	210.2	203.1	199.2	196.0	194.1	191.9	189.4	188.4	187.6	187.5
50°	208.5	199.7	193.1	189.4	186.3	183.6	181.3	179.7	179.1	179.1	179.5
52.5°	197.0	189.4	183.9	179.3	176.4	173.5	171.4	170.4	169.5	170.5	171.2
55°	180.1	172.5	168.4	164.0	161.1	157.8	156.8	156.4	155.8	157.4	158.3
57.5°	162.2	156.9	152.0	147.8	145.2	143.2	141.9	141.6	142.8	143.6	146.2
60°	150.8	144.6	140.4	137.1	133.9	132.7	132.2	131.9	132.7	134.9	138.5
62.5°	138.3	133.3	128.6	126.2	123.9	121.8	121.7	122.0	123.6	126.3	129.7
65°	119.9	115.6	112.5	109.6	107.7	106.6	106.9	107.7	109.6	113.2	117.0
67.5°	101.2	98.3	95.5	93.2	91.4	91.4	91.8	93.1	95.2	99.2	102.8
70°	89.3	86.0	83.6	82.7	81.1	80.3	81.6	83.6	85.5	89.3	92.3
72.5°	77.2	74.4	72.6	71.9	71.2	70.6	71.1	73.3	75.8	79.5	83.1
75°	59.3	58.3	57.1	56.3	55.6	56.1	56.4	58.5	60.5	64.5	68.6
77.5°	43.3	42.3	41.5	41.3	40.9	41.2	42.4	43.9	45.8	48.7	51.8
80°	32.7	32.4	31.9	31.7	31.7	31.9	33.6	34.6	36.5	39.1	41.6
82.5°	23.9	23.6	23.5	23.5	23.6	23.7	24.7	26.0	27.6	29.6	31.7
85°	12.6	12.1	12.8	13.0	12.6	13.2	13.6	14.4	15.1	16.1	17.1
87.5°	5.8	6.5	6.6	7.1	7.4	8.1	8.2	9.1	9.6	10.2	10.2
90°	8.4	10.2	11.8	13.4	15.0	16.6	17.7	18.9	20.1	21.2	22.1
92.5°	10.8	10.9	12.3	13.7	15.2	16.6	17.7	18.9	20.1	21.2	21.9
95°	56.3	51.6	42.8	34.1	25.3	16.6	17.7	18.9	20.1	21.2	21.8
97.5°	128.3	120.3	102.9	85.6	68.3	51.0	44.5	38.0	31.5	25.0	21.8
100°	175.8	176.6	177.5	178.5	179.4	180.3	146.0	111.7	77.4	43.1	25.4
102.5°	227.1	227.8	228.4	229.0	229.5	230.1	223.6	217.0	210.6	204.1	193.1
105°	308.4	308.8	308.8	308.8	308.8	308.8	308.8	308.8	308.8	308.8	308.7
107.5°	388.9	389.1	389.5	389.9	390.5	390.9	390.9	391.0	391.0	391.1	390.7
110°	443.5	443.8	444.3	444.7	445.1	445.6	445.0	444.3	443.5	442.8	442.6



TEST NUMBER: P333151-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	497.1	497.6	497.8	498.1	498.4	498.6	497.8	497.0	496.1	495.2	494.5
115°	576.7	577.4	577.6	577.8	578.0	578.3	577.4	576.4	575.5	574.6	573.5
117.5°	651.7	652.1	653.0	653.8	654.7	655.6	654.4	653.2	652.0	650.8	649.9
120°	700.7	700.9	701.6	702.3	702.9	703.6	703.2	702.8	702.3	701.9	701.1
122.5°	749.0	749.7	749.9	750.3	750.6	750.9	750.5	750.0	749.6	749.1	748.1
125°	819.9	820.7	820.7	820.7	820.7	820.7	819.8	818.9	818.0	817.1	816.3
127.5°	883.0	883.5	883.3	883.2	883.1	883.0	882.4	881.9	881.5	880.9	879.9
130°	922.8	923.5	923.7	924.0	924.2	924.4	923.7	923.0	922.3	921.7	920.7
132.5°	963.3	963.8	963.2	962.7	962.2	961.7	961.6	961.4	961.3	961.2	960.6
135°	1020.1	1020.6	1020.1	1019.7	1019.1	1018.7	1018.2	1017.8	1017.4	1016.9	1015.9
137.5°	1071.4	1071.7	1071.4	1070.9	1070.5	1070.1	1070.2	1070.3	1070.4	1070.5	1070.0
140°	1102.4	1102.5	1102.3	1102.1	1101.9	1101.6	1102.1	1102.5	1103.0	1103.5	1103.0
142.5°	1132.4	1132.7	1133.0	1133.3	1133.6	1134.0	1134.1	1134.2	1134.3	1134.3	1133.7
145°	1178.0	1178.3	1178.3	1178.3	1178.3	1178.3	1178.6	1178.8	1179.0	1179.2	1178.7
147.5°	1215.2	1215.3	1215.6	1215.8	1216.2	1216.5	1216.7	1217.0	1217.3	1217.5	1216.8
150°	1238.7	1238.7	1239.1	1239.6	1240.0	1240.5	1240.9	1241.4	1241.9	1242.3	1241.6
152.5°	1260.4	1260.2	1260.7	1261.1	1261.6	1262.0	1262.5	1262.9	1263.5	1263.9	1263.3
155°	1289.9	1289.4	1289.9	1290.3	1290.8	1291.3	1292.0	1292.6	1293.3	1294.1	1293.4
157.5°	1315.9	1315.5	1315.6	1315.6	1315.7	1315.7	1316.4	1317.2	1317.9	1318.7	1318.1
160°	1330.3	1329.7	1330.0	1330.2	1330.4	1330.6	1331.6	1332.5	1333.4	1334.4	1333.9
162.5°	1343.5	1343.0	1343.2	1343.5	1343.7	1343.9	1345.2	1346.5	1347.8	1349.1	1348.7
165°	1361.4	1360.8	1361.0	1361.3	1361.5	1361.7	1363.2	1364.5	1365.9	1367.3	1367.0
167.5°	1374.5	1373.9	1374.1	1374.3	1374.6	1374.8	1376.4	1378.1	1379.7	1381.4	1381.3
170°	1381.2	1380.5	1380.7	1381.0	1381.2	1381.4	1383.3	1385.1	1387.0	1388.8	1388.7
172.5°	1386.2	1385.5	1386.0	1386.4	1386.8	1387.2	1388.9	1390.5	1392.2	1393.8	1393.7
175°	1392.5	1391.9	1392.1	1392.4	1392.6	1392.9	1394.6	1396.5	1398.4	1400.2	1400.1
177.5°	1396.1	1395.6	1395.8	1396.0	1396.2	1396.3	1397.7	1398.9	1400.3	1401.5	1401.4
180°	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0



TEST NUMBER: P333151-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	462.5	463.7	462.7	464.0	462.7	463.7	462.5	463.5	465.0	464.0	466.4
5°	426.3	424.5	425.7	424.9	425.7	424.5	426.3	427.3	429.8	430.6	432.3
7.5°	392.9	391.1	389.1	388.1	389.1	391.1	392.9	393.4	395.6	398.7	401.0
10°	371.9	369.6	369.4	368.0	369.4	369.6	371.9	374.2	375.6	379.5	382.2
12.5°	356.6	354.5	352.1	351.5	352.1	354.5	356.6	358.6	359.0	363.4	365.2
15°	334.8	333.1	331.7	333.0	331.7	333.1	334.8	336.1	338.3	341.4	343.5
17.5°	316.7	315.4	315.1	313.6	315.1	315.4	316.7	317.4	321.1	323.2	326.7
20°	305.3	304.3	304.8	302.0	304.8	304.3	305.3	307.2	310.9	311.9	315.7
22.5°	296.3	294.3	294.0	293.5	294.0	294.3	296.3	298.0	298.7	301.9	304.4
25°	282.0	281.1	280.0	281.1	280.0	281.1	282.0	283.9	284.7	287.0	289.5
27.5°	269.7	268.4	268.1	268.3	268.1	268.4	269.7	269.5	271.7	273.6	275.4
30°	262.1	260.0	260.2	260.0	260.2	260.0	262.1	262.1	263.3	265.0	266.6
32.5°	253.9	252.4	252.2	251.8	252.2	252.4	253.9	253.5	255.1	257.1	258.9
35°	241.7	241.7	240.7	240.7	240.7	241.7	241.7	242.3	244.0	244.0	246.0
37.5°	230.2	230.1	229.4	229.5	229.4	230.1	230.2	230.8	231.3	232.2	233.5
40°	221.7	221.5	220.9	219.6	220.9	221.5	221.7	222.6	222.9	224.0	224.8
42.5°	213.5	212.8	212.5	212.0	212.5	212.8	213.5	213.9	214.2	215.5	217.2
45°	200.5	200.5	200.1	199.8	200.1	200.5	200.5	200.5	200.7	202.3	203.1
47.5°	187.9	188.2	189.0	188.9	189.0	188.2	187.9	187.5	187.6	188.4	189.4
50°	180.3	180.5	181.1	181.3	181.1	180.5	180.3	179.5	179.1	179.1	179.7
52.5°	171.9	173.1	173.9	173.7	173.9	173.1	171.9	171.2	170.5	169.5	170.4
55°	160.1	161.6	163.0	163.2	163.0	161.6	160.1	158.3	157.4	155.8	156.4
57.5°	148.5	150.4	151.9	152.5	151.9	150.4	148.5	146.2	143.6	142.8	141.6
60°	140.5	143.2	145.1	145.9	145.1	143.2	140.5	138.5	134.9	132.7	131.9
62.5°	133.0	136.0	137.8	137.9	137.8	136.0	133.0	129.7	126.3	123.6	122.0
65°	120.6	123.6	125.3	126.5	125.3	123.6	120.6	117.0	113.2	109.6	107.7
67.5°	107.2	110.3	112.1	113.1	112.1	110.3	107.2	102.8	99.2	95.2	93.1
70°	97.5	100.6	103.0	103.9	103.0	100.6	97.5	92.3	89.3	85.5	83.6
72.5°	87.9	90.7	92.6	93.6	92.6	90.7	87.9	83.1	79.5	75.8	73.3
75°	71.2	75.0	76.9	77.8	76.9	75.0	71.2	68.6	64.5	60.5	58.5
77.5°	54.9	58.3	59.5	60.0	59.5	58.3	54.9	51.8	48.7	45.8	43.9
80°	44.1	46.2	47.6	47.8	47.6	46.2	44.1	41.6	39.1	36.5	34.6
82.5°	33.9	35.6	36.0	36.6	36.0	35.6	33.9	31.7	29.6	27.6	26.0
85°	18.5	19.4	19.6	19.4	19.6	19.4	18.5	17.1	16.1	15.1	14.4
87.5°	10.7	10.6	10.8	11.2	10.8	10.6	10.7	10.2	10.2	9.6	9.1
90°	22.8	23.5	24.2	24.9	24.2	23.5	22.8	22.1	21.2	20.1	18.9
92.5°	22.2	22.6	22.9	23.2	22.9	22.6	22.2	21.9	21.2	20.1	18.9
95°	21.8	21.8	21.8	21.8	21.8	21.8	21.8	21.8	21.2	20.1	18.9
97.5°	21.8	21.8	21.8	21.8	21.8	21.8	21.8	21.8	25.0	31.5	38.0
100°	24.5	23.6	22.6	21.8	22.6	23.6	24.5	25.4	43.1	77.4	111.7
102.5°	177.4	161.7	146.1	130.4	146.1	161.7	177.4	193.1	204.1	210.6	217.0
105°	308.4	308.3	308.0	307.8	308.0	308.3	308.4	308.7	308.8	308.8	308.8
107.5°	390.0	389.4	388.7	388.0	388.7	389.4	390.0	390.7	391.1	391.0	391.0
110°	442.8	443.1	443.4	443.5	443.4	443.1	442.8	442.6	442.8	443.5	444.3



TEST NUMBER: P333151-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	494.3	493.9	493.7	493.3	493.7	493.9	494.3	494.5	495.2	496.1	497.0
115°	572.0	570.7	569.3	567.9	569.3	570.7	572.0	573.5	574.6	575.5	576.4
117.5°	649.3	648.7	648.1	647.5	648.1	648.7	649.3	649.9	650.8	652.0	653.2
120°	699.9	698.7	697.6	696.4	697.6	698.7	699.9	701.1	701.9	702.3	702.8
122.5°	746.8	745.5	744.2	742.9	744.2	745.5	746.8	748.1	749.1	749.6	750.0
125°	815.6	814.9	814.2	813.5	814.2	814.9	815.6	816.3	817.1	818.0	818.9
127.5°	878.2	876.4	874.7	873.0	874.7	876.4	878.2	879.9	880.9	881.5	881.9
130°	919.5	918.5	917.3	916.1	917.3	918.5	919.5	920.7	921.7	922.3	923.0
132.5°	959.4	958.2	957.1	955.9	957.1	958.2	959.4	960.6	961.2	961.3	961.4
135°	1014.6	1013.2	1011.8	1010.4	1011.8	1013.2	1014.6	1015.9	1016.9	1017.4	1017.8
137.5°	1068.7	1067.6	1066.3	1065.1	1066.3	1067.6	1068.7	1070.0	1070.5	1070.4	1070.3
140°	1101.6	1100.3	1098.9	1097.5	1098.9	1100.3	1101.6	1103.0	1103.5	1103.0	1102.5
142.5°	1132.3	1131.0	1129.5	1128.2	1129.5	1131.0	1132.3	1133.7	1134.3	1134.3	1134.2
145°	1177.2	1175.9	1174.5	1173.1	1174.5	1175.9	1177.2	1178.7	1179.2	1179.0	1178.8
147.5°	1215.2	1213.5	1211.9	1210.2	1211.9	1213.5	1215.2	1216.8	1217.5	1217.3	1217.0
150°	1239.8	1238.0	1236.1	1234.3	1236.1	1238.0	1239.8	1241.6	1242.3	1241.9	1241.4
152.5°	1261.6	1260.0	1258.3	1256.7	1258.3	1260.0	1261.6	1263.3	1263.9	1263.5	1262.9
155°	1291.6	1289.8	1287.9	1286.1	1287.9	1289.8	1291.6	1293.4	1294.1	1293.3	1292.6
157.5°	1316.3	1314.5	1312.6	1310.7	1312.6	1314.5	1316.3	1318.1	1318.7	1317.9	1317.2
160°	1332.0	1330.2	1328.4	1326.5	1328.4	1330.2	1332.0	1333.9	1334.4	1333.4	1332.5
162.5°	1346.7	1344.6	1342.6	1340.6	1342.6	1344.6	1346.7	1348.7	1349.1	1347.8	1346.5
165°	1365.2	1363.3	1361.5	1359.7	1361.5	1363.3	1365.2	1367.0	1367.3	1365.9	1364.5
167.5°	1379.1	1377.1	1375.0	1373.0	1375.0	1377.1	1379.1	1381.3	1381.4	1379.7	1378.1
170°	1386.6	1384.6	1382.5	1380.4	1382.5	1384.6	1386.6	1388.7	1388.8	1387.0	1385.1
172.5°	1391.6	1389.6	1387.4	1385.4	1387.4	1389.6	1391.6	1393.7	1393.8	1392.2	1390.5
175°	1398.0	1396.0	1393.8	1391.8	1393.8	1396.0	1398.0	1400.1	1400.2	1398.4	1396.5
177.5°	1400.0	1398.5	1397.0	1395.5	1397.0	1398.5	1400.0	1401.4	1401.5	1400.3	1398.9
180°	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0



TEST NUMBER: P333151-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	464.2	466.2	468.6	470.5	473.8	475.2	477.1	478.5	481.2	483.7	486.6
5°	432.9	436.4	441.1	446.3	452.3	456.4	462.2	465.7	472.7	479.0	485.3
7.5°	404.6	408.8	415.5	422.1	430.0	437.0	444.3	452.3	461.2	471.8	480.5
10°	385.1	390.8	398.1	406.4	415.8	424.0	433.7	442.4	453.3	465.7	477.2
12.5°	369.6	374.5	382.5	390.5	400.6	410.7	420.7	432.1	444.9	458.6	473.1
15°	348.2	352.3	358.9	369.9	380.1	390.0	405.1	415.8	431.9	447.1	464.7
17.5°	329.9	335.1	340.6	350.0	360.7	373.0	386.5	399.9	415.4	434.7	454.4
20°	318.8	322.9	329.2	336.4	347.8	360.2	372.9	386.6	405.5	425.5	446.7
22.5°	306.6	311.0	318.3	326.1	335.6	347.5	361.6	376.5	396.3	415.9	439.0
25°	292.2	295.2	301.8	308.9	318.3	328.4	343.0	359.5	379.2	401.6	425.1
27.5°	278.7	281.3	287.3	293.5	302.0	314.0	327.1	343.8	362.2	385.0	411.0
30°	268.9	271.8	277.1	283.7	291.9	302.5	315.8	331.5	351.3	373.5	400.7
32.5°	260.5	263.1	267.1	273.7	281.8	291.9	304.3	320.3	340.1	362.7	389.4
35°	247.4	250.3	253.4	258.6	265.6	275.4	289.1	304.2	323.1	344.9	369.4
37.5°	234.5	237.6	240.4	245.0	251.4	260.1	271.9	287.6	304.7	325.7	349.3
40°	226.4	228.9	231.2	236.1	242.5	250.7	261.7	275.7	293.8	313.4	333.0
42.5°	218.4	220.7	222.6	226.9	232.8	240.7	251.1	264.8	281.6	299.9	317.2
45°	205.6	207.1	209.4	213.0	217.8	225.0	235.1	247.3	261.4	278.7	291.8
47.5°	191.9	194.1	196.0	199.2	203.1	210.2	219.9	230.2	243.2	256.0	265.1
50°	181.3	183.6	186.3	189.4	193.1	199.7	208.5	219.0	230.0	239.9	247.6
52.5°	171.4	173.5	176.4	179.3	183.9	189.4	197.0	206.3	217.1	224.2	230.7
55°	156.8	157.8	161.1	164.0	168.4	172.5	180.1	188.3	194.9	200.3	205.6
57.5°	141.9	143.2	145.2	147.8	152.0	156.9	162.2	169.5	173.3	176.1	180.3
60°	132.2	132.7	133.9	137.1	140.4	144.6	150.8	156.0	158.9	161.1	164.6
62.5°	121.7	121.8	123.9	126.2	128.6	133.3	138.3	142.5	144.8	146.0	149.3
65°	106.9	106.6	107.7	109.6	112.5	115.6	119.9	123.6	123.4	124.7	126.7
67.5°	91.8	91.4	91.4	93.2	95.5	98.3	101.2	103.4	103.4	105.0	106.1
70°	81.6	80.3	81.1	82.7	83.6	86.0	89.3	90.1	90.2	91.0	92.1
72.5°	71.1	70.6	71.2	71.9	72.6	74.4	77.2	77.7	77.8	78.2	79.9
75°	56.4	56.1	55.6	56.3	57.1	58.3	59.3	60.2	59.9	60.2	61.4
77.5°	42.4	41.2	40.9	41.3	41.5	42.3	43.3	43.2	43.4	43.4	44.8
80°	33.6	31.9	31.7	31.7	31.9	32.4	32.7	33.2	32.5	33.2	33.6
82.5°	24.7	23.7	23.6	23.5	23.5	23.6	23.9	24.1	24.0	24.3	24.5
85°	13.6	13.2	12.6	13.0	12.8	12.1	12.6	11.9	11.8	11.9	12.1
87.5°	8.2	8.1	7.4	7.1	6.6	6.5	5.8	5.3	4.7	4.5	4.6
90°	17.7	16.6	15.0	13.4	11.8	10.2	8.4	6.6	4.7	2.9	1.1
92.5°	17.7	16.6	15.2	13.7	12.3	10.9	10.8	12.1	13.4	14.7	16.0
95°	17.7	16.6	25.3	34.1	42.8	51.6	56.3	57.0	57.7	58.4	59.0
97.5°	44.5	51.0	68.3	85.6	102.9	120.3	128.3	127.1	125.8	124.6	123.3
100°	146.0	180.3	179.4	178.5	177.5	176.6	175.8	175.1	174.4	173.8	173.1
102.5°	223.6	230.1	229.5	229.0	228.4	227.8	227.1	226.2	225.4	224.5	223.6
105°	308.8	308.8	308.8	308.8	308.8	308.8	308.4	307.5	306.5	305.6	304.7
107.5°	390.9	390.9	390.5	389.9	389.5	389.1	388.9	388.9	388.9	388.9	388.9
110°	445.0	445.6	445.1	444.7	444.3	443.8	443.5	443.5	443.5	443.5	443.5



TEST NUMBER: P333151-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	497.8	498.6	498.4	498.1	497.8	497.6	497.1	496.6	496.1	495.5	495.0
115°	577.4	578.3	578.0	577.8	577.6	577.4	576.7	575.5	574.4	573.2	572.0
117.5°	654.4	655.6	654.7	653.8	653.0	652.1	651.7	651.8	651.8	651.8	651.8
120°	703.2	703.6	702.9	702.3	701.6	700.9	700.7	700.9	701.2	701.3	701.6
122.5°	750.5	750.9	750.6	750.3	749.9	749.7	749.0	748.1	747.3	746.5	745.6
125°	819.8	820.7	820.7	820.7	820.7	820.7	819.9	818.3	816.7	815.1	813.5
127.5°	882.4	883.0	883.1	883.2	883.3	883.5	883.0	881.8	880.7	879.6	878.4
130°	923.7	924.4	924.2	924.0	923.7	923.5	922.8	921.7	920.5	919.4	918.2
132.5°	961.6	961.7	962.2	962.7	963.2	963.8	963.3	962.0	960.6	959.3	958.0
135°	1018.2	1018.7	1019.1	1019.7	1020.1	1020.6	1020.1	1018.7	1017.4	1015.9	1014.6
137.5°	1070.2	1070.1	1070.5	1070.9	1071.4	1071.7	1071.4	1070.1	1069.0	1067.8	1066.6
140°	1102.1	1101.6	1101.9	1102.1	1102.3	1102.5	1102.4	1102.0	1101.5	1101.1	1100.5
142.5°	1134.1	1134.0	1133.6	1133.3	1133.0	1132.7	1132.4	1132.1	1131.8	1131.5	1131.2
145°	1178.6	1178.3	1178.3	1178.3	1178.3	1178.3	1178.0	1177.6	1177.1	1176.7	1176.3
147.5°	1216.7	1216.5	1216.2	1215.8	1215.6	1215.3	1215.2	1215.3	1215.4	1215.5	1215.6
150°	1240.9	1240.5	1240.0	1239.6	1239.1	1238.7	1238.7	1239.1	1239.6	1240.0	1240.5
152.5°	1262.5	1262.0	1261.6	1261.1	1260.7	1260.2	1260.4	1261.5	1262.5	1263.6	1264.5
155°	1292.0	1291.3	1290.8	1290.3	1289.9	1289.4	1289.9	1291.3	1292.6	1294.1	1295.4
157.5°	1316.4	1315.7	1315.7	1315.6	1315.6	1315.5	1315.9	1316.8	1317.6	1318.4	1319.3
160°	1331.6	1330.6	1330.4	1330.2	1330.0	1329.7	1330.3	1331.7	1333.1	1334.4	1335.9
162.5°	1345.2	1343.9	1343.7	1343.5	1343.2	1343.0	1343.5	1345.0	1346.3	1347.7	1349.1
165°	1363.2	1361.7	1361.5	1361.3	1361.0	1360.8	1361.4	1362.8	1364.1	1365.6	1366.9
167.5°	1376.4	1374.8	1374.6	1374.3	1374.1	1373.9	1374.5	1375.9	1377.3	1378.8	1380.2
170°	1383.3	1381.4	1381.2	1381.0	1380.7	1380.5	1381.2	1382.8	1384.4	1386.1	1387.7
172.5°	1388.9	1387.2	1386.8	1386.4	1386.0	1385.5	1386.2	1387.8	1389.4	1391.0	1392.6
175°	1394.6	1392.9	1392.6	1392.4	1392.1	1391.9	1392.5	1393.8	1395.3	1396.6	1398.0
177.5°	1397.7	1396.3	1396.2	1396.0	1395.8	1395.6	1396.1	1397.2	1398.3	1399.4	1400.5
180°	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0



TEST NUMBER: P333151-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	488.1	490.4	491.9	494.6	497.0	498.3	499.4	500.4	501.6	502.6	505.4
5°	491.2	496.6	501.1	508.1	514.5	519.4	524.8	529.5	533.4	539.0	543.3
7.5°	489.8	499.4	509.3	520.2	531.3	541.5	551.1	559.9	567.9	577.7	586.2
10°	488.6	501.5	514.2	529.0	543.9	556.7	568.6	580.9	589.7	602.1	612.6
12.5°	487.6	502.8	518.3	535.8	552.3	570.4	586.3	595.2	608.7	618.6	631.1
15°	483.4	503.5	524.8	544.6	568.1	584.8	598.8	616.1	628.7	641.2	654.8
17.5°	475.9	498.8	522.5	548.5	571.0	588.9	607.0	623.7	638.6	655.5	672.4
20°	472.4	495.3	522.5	549.1	571.1	589.9	608.4	626.8	643.3	664.9	684.5
22.5°	465.2	492.8	517.9	543.9	566.5	586.9	608.0	628.7	650.7	675.1	699.6
25°	452.3	480.3	506.8	532.4	555.3	580.9	603.3	631.2	659.2	691.5	722.0
27.5°	438.8	465.7	490.0	514.7	541.4	570.3	599.4	631.0	667.7	708.6	751.5
30°	427.9	453.3	477.0	502.3	530.1	562.7	594.7	632.1	674.6	720.5	771.7
32.5°	415.3	438.6	461.6	488.5	518.8	553.1	590.4	631.5	682.5	734.7	787.3
35°	393.5	413.1	436.8	465.5	499.6	539.0	582.1	630.7	689.2	749.2	793.4
37.5°	367.8	386.0	411.0	442.4	478.2	520.5	571.6	629.3	691.4	739.2	753.5
40°	350.4	367.4	393.3	425.9	462.5	507.3	563.3	624.3	684.5	715.0	703.2
42.5°	332.0	349.7	375.1	407.2	446.7	495.4	552.9	613.9	664.4	675.9	635.3
45°	302.9	321.2	346.2	378.7	421.2	473.9	533.9	589.3	618.3	597.5	534.7
47.5°	275.8	293.0	316.1	349.7	393.5	448.1	505.8	550.0	552.3	502.7	435.5
50°	257.3	273.2	296.5	330.1	373.5	428.8	480.9	515.8	500.1	443.8	379.3
52.5°	239.2	254.8	277.7	310.9	353.9	404.6	453.1	477.5	448.0	390.2	335.2
55°	213.0	226.7	249.1	279.8	320.6	367.6	408.8	417.2	378.9	322.1	277.3
57.5°	187.5	200.2	220.6	248.9	286.2	327.8	360.1	358.2	317.7	268.9	233.4
60°	170.2	182.5	200.7	228.3	262.3	298.2	325.7	319.1	279.0	236.9	207.1
62.5°	154.7	165.8	182.9	207.1	238.1	271.3	293.9	284.2	244.9	208.1	184.5
65°	131.9	141.2	155.8	176.4	202.2	229.5	247.1	234.5	200.9	172.3	153.3
67.5°	110.0	117.5	129.7	146.2	168.2	190.2	200.8	188.2	161.3	140.4	126.4
70°	96.2	102.8	112.3	126.9	146.1	164.6	172.6	161.3	138.2	120.3	110.2
72.5°	82.4	87.8	96.1	109.3	124.7	140.7	147.8	137.0	118.0	102.8	93.5
75°	63.7	67.4	73.1	82.2	94.3	107.2	111.0	101.6	89.4	78.1	71.9
77.5°	45.6	48.7	53.1	58.8	67.4	75.5	78.9	73.5	64.1	56.9	51.8
80°	35.0	36.6	40.4	45.1	51.9	57.1	59.3	55.8	49.2	43.9	39.9
82.5°	25.0	26.7	28.8	32.7	37.1	40.6	43.0	40.7	35.9	31.7	29.4
85°	12.1	13.2	14.4	16.1	19.4	21.4	21.2	19.8	17.9	16.3	15.1
87.5°	4.9	5.4	6.2	7.5	8.3	9.3	9.9	9.9	9.5	9.3	9.1
90°	2.9	4.7	6.6	8.4	10.2	11.8	13.4	15.0	16.6	17.7	18.9
92.5°	14.7	13.4	12.1	10.8	10.9	12.3	13.7	15.2	16.6	17.7	18.9
95°	58.4	57.7	57.0	56.3	51.6	42.8	34.1	25.3	16.6	17.7	18.9
97.5°	124.6	125.8	127.1	128.3	120.3	102.9	85.6	68.3	51.0	44.5	38.0
100°	173.8	174.4	175.1	175.8	176.6	177.5	178.5	179.4	180.3	146.0	111.7
102.5°	224.5	225.4	226.2	227.1	227.8	228.4	229.0	229.5	230.1	223.6	217.0
105°	305.6	306.5	307.5	308.4	308.8	308.8	308.8	308.8	308.8	308.8	308.8
107.5°	388.9	388.9	388.9	388.9	389.1	389.5	389.9	390.5	390.9	390.9	391.0
110°	443.5	443.5	443.5	443.5	443.8	444.3	444.7	445.1	445.6	445.0	444.3



TEST NUMBER: P333151-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	495.5	496.1	496.6	497.1	497.6	497.8	498.1	498.4	498.6	497.8	497.0
115°	573.2	574.4	575.5	576.7	577.4	577.6	577.8	578.0	578.3	577.4	576.4
117.5°	651.8	651.8	651.8	651.7	652.1	653.0	653.8	654.7	655.6	654.4	653.2
120°	701.3	701.2	700.9	700.7	700.9	701.6	702.3	702.9	703.6	703.2	702.8
122.5°	746.5	747.3	748.1	749.0	749.7	749.9	750.3	750.6	750.9	750.5	750.0
125°	815.1	816.7	818.3	819.9	820.7	820.7	820.7	820.7	820.7	819.8	818.9
127.5°	879.6	880.7	881.8	883.0	883.5	883.3	883.2	883.1	883.0	882.4	881.9
130°	919.4	920.5	921.7	922.8	923.5	923.7	924.0	924.2	924.4	923.7	923.0
132.5°	959.3	960.6	962.0	963.3	963.8	963.2	962.7	962.2	961.7	961.6	961.4
135°	1015.9	1017.4	1018.7	1020.1	1020.6	1020.1	1019.7	1019.1	1018.7	1018.2	1017.8
137.5°	1067.8	1069.0	1070.1	1071.4	1071.7	1071.4	1070.9	1070.5	1070.1	1070.2	1070.3
140°	1101.1	1101.5	1102.0	1102.4	1102.5	1102.3	1102.1	1101.9	1101.6	1102.1	1102.5
142.5°	1131.5	1131.8	1132.1	1132.4	1132.7	1133.0	1133.3	1133.6	1134.0	1134.1	1134.2
145°	1176.7	1177.1	1177.6	1178.0	1178.3	1178.3	1178.3	1178.3	1178.3	1178.6	1178.8
147.5°	1215.5	1215.4	1215.3	1215.2	1215.3	1215.6	1215.8	1216.2	1216.5	1216.7	1217.0
150°	1240.0	1239.6	1239.1	1238.7	1238.7	1239.1	1239.6	1240.0	1240.5	1240.9	1241.4
152.5°	1263.6	1262.5	1261.5	1260.4	1260.2	1260.7	1261.1	1261.6	1262.0	1262.5	1262.9
155°	1294.1	1292.6	1291.3	1289.9	1289.4	1289.9	1290.3	1290.8	1291.3	1292.0	1292.6
157.5°	1318.4	1317.6	1316.8	1315.9	1315.5	1315.6	1315.6	1315.7	1315.7	1316.4	1317.2
160°	1334.4	1333.1	1331.7	1330.3	1329.7	1330.0	1330.2	1330.4	1330.6	1331.6	1332.5
162.5°	1347.7	1346.3	1345.0	1343.5	1343.0	1343.2	1343.5	1343.7	1343.9	1345.2	1346.5
165°	1365.6	1364.1	1362.8	1361.4	1360.8	1361.0	1361.3	1361.5	1361.7	1363.2	1364.5
167.5°	1378.8	1377.3	1375.9	1374.5	1373.9	1374.1	1374.3	1374.6	1374.8	1376.4	1378.1
170°	1386.1	1384.4	1382.8	1381.2	1380.5	1380.7	1381.0	1381.2	1381.4	1383.3	1385.1
172.5°	1391.0	1389.4	1387.8	1386.2	1385.5	1386.0	1386.4	1386.8	1387.2	1388.9	1390.5
175°	1396.6	1395.3	1393.8	1392.5	1391.9	1392.1	1392.4	1392.6	1392.9	1394.6	1396.5
177.5°	1399.4	1398.3	1397.2	1396.1	1395.6	1395.8	1396.0	1396.2	1396.3	1397.7	1398.9
180°	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0



TEST NUMBER: P333151-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	507.7	509.0	511.8	510.9	512.1	512.8	513.4
5°	548.7	555.3	558.2	557.8	562.1	561.1	560.0
7.5°	595.0	601.9	605.8	610.6	613.4	613.7	616.1
10°	621.3	630.3	634.0	639.2	642.5	644.4	644.1
12.5°	641.3	648.5	656.7	659.2	663.7	666.1	665.2
15°	665.6	676.9	685.5	689.8	695.4	697.1	699.3
17.5°	687.2	702.3	712.4	725.9	730.9	734.1	732.2
20°	703.5	723.4	733.5	749.6	758.5	763.2	761.5
22.5°	722.7	744.4	763.0	776.9	790.4	796.8	798.2
25°	755.8	785.4	812.9	831.2	847.8	851.8	860.4
27.5°	792.7	827.7	857.0	876.3	887.9	892.2	895.0
30°	815.9	850.8	872.8	885.2	888.9	888.5	888.1
32.5°	827.3	849.1	853.4	849.9	841.4	834.2	826.7
35°	811.2	795.0	770.6	739.3	716.2	692.9	690.6
37.5°	729.6	677.5	637.0	591.8	565.8	549.7	538.5
40°	652.7	593.6	544.6	506.5	479.9	469.4	459.1
42.5°	569.4	512.8	469.4	437.6	417.6	405.9	397.8
45°	462.5	412.7	378.7	355.6	339.7	330.7	325.6
47.5°	379.1	342.1	313.3	296.6	285.7	278.7	278.7
50°	334.2	299.0	279.8	266.6	257.2	251.6	252.6
52.5°	294.4	268.1	251.8	240.8	233.7	230.3	230.2
55°	246.2	227.3	216.6	208.5	203.8	199.8	200.7
57.5°	210.6	194.7	187.4	180.7	177.5	175.9	173.6
60°	188.5	176.2	170.0	164.6	161.3	160.1	157.8
62.5°	168.9	159.2	153.2	148.8	145.9	145.4	143.7
65°	142.0	134.6	129.2	127.2	124.0	123.2	123.2
67.5°	117.0	111.7	107.5	105.7	104.3	104.5	103.5
70°	101.4	97.0	94.3	92.3	91.3	91.5	90.7
72.5°	88.7	83.8	81.5	80.3	78.9	79.5	79.1
75°	67.1	64.7	63.5	62.2	61.4	61.0	60.5
77.5°	49.3	47.2	46.2	45.5	45.7	44.6	45.4
80°	38.1	36.3	35.7	34.6	34.4	34.4	34.2
82.5°	27.9	26.8	26.4	25.6	25.1	25.5	25.0
85°	14.4	13.6	13.4	13.4	13.0	12.6	13.6
87.5°	9.3	8.8	9.0	9.0	9.2	9.1	8.9
90°	20.1	21.2	22.1	22.8	23.5	24.2	24.9
92.5°	20.1	21.2	21.9	22.2	22.6	22.9	23.2
95°	20.1	21.2	21.8	21.8	21.8	21.8	21.8
97.5°	31.5	25.0	21.8	21.8	21.8	21.8	21.8
100°	77.4	43.1	25.4	24.5	23.6	22.6	21.8
102.5°	210.6	204.1	193.1	177.4	161.7	146.1	130.4
105°	308.8	308.8	308.7	308.4	308.3	308.0	307.8
107.5°	391.0	391.1	390.7	390.0	389.4	388.7	388.0
110°	443.5	442.8	442.6	442.8	443.1	443.4	443.5



TEST NUMBER: P333151-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	496.1	495.2	494.5	494.3	493.9	493.7	493.3
115°	575.5	574.6	573.5	572.0	570.7	569.3	567.9
117.5°	652.0	650.8	649.9	649.3	648.7	648.1	647.5
120°	702.3	701.9	701.1	699.9	698.7	697.6	696.4
122.5°	749.6	749.1	748.1	746.8	745.5	744.2	742.9
125°	818.0	817.1	816.3	815.6	814.9	814.2	813.5
127.5°	881.5	880.9	879.9	878.2	876.4	874.7	873.0
130°	922.3	921.7	920.7	919.5	918.5	917.3	916.1
132.5°	961.3	961.2	960.6	959.4	958.2	957.1	955.9
135°	1017.4	1016.9	1015.9	1014.6	1013.2	1011.8	1010.4
137.5°	1070.4	1070.5	1070.0	1068.7	1067.6	1066.3	1065.1
140°	1103.0	1103.5	1103.0	1101.6	1100.3	1098.9	1097.5
142.5°	1134.3	1134.3	1133.7	1132.3	1131.0	1129.5	1128.2
145°	1179.0	1179.2	1178.7	1177.2	1175.9	1174.5	1173.1
147.5°	1217.3	1217.5	1216.8	1215.2	1213.5	1211.9	1210.2
150°	1241.9	1242.3	1241.6	1239.8	1238.0	1236.1	1234.3
152.5°	1263.5	1263.9	1263.3	1261.6	1260.0	1258.3	1256.7
155°	1293.3	1294.1	1293.4	1291.6	1289.8	1287.9	1286.1
157.5°	1317.9	1318.7	1318.1	1316.3	1314.5	1312.6	1310.7
160°	1333.4	1334.4	1333.9	1332.0	1330.2	1328.4	1326.5
162.5°	1347.8	1349.1	1348.7	1346.7	1344.6	1342.6	1340.6
165°	1365.9	1367.3	1367.0	1365.2	1363.3	1361.5	1359.7
167.5°	1379.7	1381.4	1381.3	1379.1	1377.1	1375.0	1373.0
170°	1387.0	1388.8	1388.7	1386.6	1384.6	1382.5	1380.4
172.5°	1392.2	1393.8	1393.7	1391.6	1389.6	1387.4	1385.4
175°	1398.4	1400.2	1400.1	1398.0	1396.0	1393.8	1391.8
177.5°	1400.3	1401.5	1401.4	1400.0	1398.5	1397.0	1395.5
180°	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0

(END OF REPORT)