

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331696-830

Luminaire Tested: **SA2XXRDIP-C675D925U830-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331696-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C675D925U830-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 925 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5676.0 lumens
Efficiency: N/A
Efficacy: 109.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331696-830
CATALOG NUMBER: SA2XXRDIP-C675D925U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331696-830

CATALOG NUMBER: SA2XXRDIP-C675D925U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	96	91	88	84	87	83	80	77	68	66	64	54	52	51	41	40	39	33
2	87	80	74	70	79	73	68	64	60	56	53	48	45	43	36	35	34	28
3	80	71	64	58	72	65	59	54	53	49	45	42	40	37	33	31	29	25
4	73	63	55	50	66	58	51	46	47	43	39	38	35	32	29	27	25	21
5	67	56	48	43	61	51	45	40	43	38	34	34	31	28	27	24	22	19
6	62	50	43	37	56	46	39	35	38	33	30	31	27	25	24	22	20	17
7	57	46	38	33	52	42	35	30	35	30	26	28	25	22	22	20	18	15
8	53	41	34	29	48	38	32	27	32	27	23	26	22	20	20	18	16	13
9	50	38	31	26	45	35	28	24	29	24	21	24	20	18	19	16	14	12
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17166	17166	17166
5°	17232	16951	17045
10°	17100	16674	16531
15°	16904	16181	15714
20°	16632	15474	14698
25°	16352	14672	13714
30°	15966	13848	12450
35°	15589	12952	11341
40°	15209	12026	10058
45°	14764	10985	8896
50°	14307	9934	7759
55°	13841	8802	6663
60°	13298	7611	5532
65°	12684	6395	5039
70°	11948	5268	4631
75°	11042	4803	4323
80°	9754	4296	3933
85°	7669	3390	3390



TEST NUMBER: P331696-830

CATALOG NUMBER: SA2XXRDIP-C675D925U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.5	1.8
10°-20°	273.3	4.8
20°-30°	383.7	6.8
30°-40°	418.4	7.4
40°-50°	384.7	6.8
50°-60°	302.2	5.3
60°-70°	197.0	3.5
70°-80°	101.6	1.8
80°-90°	29.3	0.5
90°-100°	39.7	0.7
100°-110°	145.5	2.6
110°-120°	389.0	6.9
120°-130°	642.1	11.3
130°-140°	682.9	12.0
140°-150°	634.7	11.2
150°-160°	510.3	9.0
160°-170°	328.8	5.8
170°-180°	113.2	2.0
0°-30°	756.5	13.3
0°-40°	1174.9	20.7
0°-60°	1861.8	32.8
0°-90°	2189.7	38.6
90°-120°	574.2	10.1
90°-150°	2533.9	44.6
90°-180°	3486.0	61.4
0°-180°	5676.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1063	1063	1063	1063	1063	
5°	1063	1058	1046	1054	1052	101
15°	1011	999	968	950	940	285
25°	918	885	824	786	770	422
35°	791	740	657	599	575	495
45°	647	580	481	415	390	499
55°	492	415	313	257	237	439
65°	332	254	167	136	132	329
75°	177	112	77	71	69	187
85°	41	22	18	18	18	49
90°	1	10	17	21	23	4
95°	56	29	34	38	37	68
105°	262	273	52	62	65	280
115°	495	510	531	151	71	487
125°	700	711	727	733	736	624
135°	866	879	888	896	894	669
145°	1005	1005	1018	1024	1020	628
155°	1106	1099	1109	1113	1107	509
165°	1166	1161	1163	1168	1163	329
175°	1192	1187	1188	1193	1185	113
180°	1190	1190	1190	1190	1190	



TEST NUMBER: P331696-830

CATALOG NUMBER: SA2XXRDIP-C675D925U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2
2.5°	1067.1	1066.2	1065.4	1064.5	1063.7	1062.2	1060.4	1058.5	1056.7	1054.8	1056.5
5°	1063.2	1062.2	1061.1	1060.0	1058.9	1057.1	1054.2	1051.5	1048.7	1045.9	1047.8
7.5°	1052.3	1050.9	1049.6	1048.3	1047.0	1044.6	1041.4	1038.2	1034.9	1031.7	1032.2
10°	1043.0	1041.5	1040.0	1038.5	1037.0	1034.2	1029.8	1025.6	1021.3	1017.0	1016.4
12.5°	1031.4	1029.6	1027.7	1026.0	1024.1	1020.5	1015.0	1009.6	1004.0	998.5	997.4
15°	1011.3	1008.9	1006.5	1004.2	1001.8	997.0	989.8	982.5	975.2	968.0	963.9
17.5°	986.5	982.9	979.3	975.6	972.0	965.6	956.3	947.0	937.6	928.3	923.5
20°	968.0	963.7	959.4	955.2	950.8	943.4	932.6	922.0	911.3	900.6	895.2
22.5°	947.9	943.2	938.4	933.6	928.8	920.4	908.3	896.3	884.2	872.1	865.3
25°	917.9	911.1	904.3	897.4	890.6	880.1	866.0	851.9	837.7	823.6	814.8
27.5°	881.7	874.3	866.9	859.4	852.0	840.3	824.4	808.5	792.6	776.7	766.5
30°	856.4	848.2	840.1	832.0	823.9	811.2	794.1	777.0	759.9	742.8	731.9
32.5°	831.7	822.2	812.8	803.2	793.7	780.2	762.8	745.4	727.9	710.5	698.0
35°	790.9	780.0	769.1	758.2	747.3	732.4	713.6	694.8	676.0	657.1	643.7
37.5°	750.2	738.1	726.1	714.2	702.2	686.2	666.2	646.1	626.0	606.0	591.2
40°	721.6	708.8	696.0	683.2	670.3	653.6	632.8	612.1	591.4	570.6	555.4
42.5°	692.4	678.9	665.3	651.9	638.4	620.9	599.5	578.1	556.6	535.2	519.4
45°	646.6	632.3	617.9	603.6	589.3	570.9	548.5	526.0	503.5	481.1	465.9
47.5°	601.9	586.7	571.6	556.4	541.2	522.1	498.9	475.7	452.5	429.3	414.2
50°	569.6	554.4	539.2	524.1	508.9	489.6	466.0	442.5	419.0	395.5	380.7
52.5°	538.1	522.2	506.3	490.5	474.6	455.2	432.2	409.2	386.2	363.2	348.9
55°	491.7	475.0	458.4	441.7	425.0	405.1	382.0	358.9	335.8	312.7	299.9
57.5°	444.1	427.1	409.9	392.9	375.7	356.1	333.8	311.7	289.5	267.3	255.5
60°	411.8	394.7	377.6	360.5	343.4	323.9	301.8	279.7	257.8	235.7	224.8
62.5°	380.2	363.2	346.0	328.9	311.8	292.8	271.8	250.8	229.8	208.8	198.4
65°	332.0	314.6	297.3	280.0	262.7	244.4	225.2	205.9	186.6	167.4	160.1
67.5°	285.4	268.2	251.0	233.8	216.6	199.3	182.0	164.8	147.4	130.1	126.8
70°	253.1	236.4	219.7	203.0	186.3	170.6	155.9	141.1	126.4	111.6	109.4
72.5°	222.3	206.2	190.3	174.3	158.3	144.4	132.5	120.6	108.9	97.0	95.2
75°	177.0	162.1	147.1	132.1	117.2	106.0	98.8	91.5	84.3	77.0	75.5
77.5°	132.6	119.4	106.3	93.2	80.1	71.7	68.2	64.8	61.3	57.8	56.8
80°	104.9	94.0	83.0	72.2	61.3	54.8	52.6	50.4	48.4	46.2	45.3
82.5°	79.5	71.0	62.5	53.9	45.4	40.4	39.0	37.5	36.1	34.7	34.1
85°	41.4	36.9	32.4	27.9	23.4	20.8	20.2	19.6	18.9	18.3	18.3
87.5°	12.4	11.5	10.6	9.6	8.7	8.4	8.7	9.0	9.3	9.6	9.6
90°	0.8	2.9	5.1	7.2	9.2	11.1	12.6	14.1	15.6	17.2	18.2
92.5°	17.3	17.2	17.0	16.8	16.6	16.9	17.7	18.5	19.2	20.0	20.5
95°	56.0	49.7	43.4	37.0	30.7	28.2	29.6	30.9	32.2	33.6	34.5
97.5°	111.0	93.2	75.5	57.7	39.9	32.5	35.6	38.7	41.8	45.0	45.7
100°	152.4	126.1	99.9	73.7	47.5	36.1	39.3	42.6	45.8	49.1	50.6
102.5°	197.8	192.3	186.7	181.2	175.6	159.3	132.1	104.8	77.7	50.4	52.4
105°	261.6	267.4	273.1	278.9	284.6	261.4	209.2	156.9	104.7	52.5	54.6
107.5°	334.5	339.1	343.7	348.4	353.1	324.0	261.4	198.8	136.1	73.5	71.4
110°	381.4	385.4	389.4	393.4	397.4	371.7	316.5	261.2	205.9	150.6	131.5



TEST NUMBER: P331696-830

CATALOG NUMBER: SA2XXRDIP-C675D925U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	425.4	429.0	432.5	436.1	439.6	434.6	420.9	407.3	393.6	379.9	310.2
115°	494.9	498.2	501.4	504.7	507.9	512.0	516.8	521.6	526.3	531.1	442.5
117.5°	557.1	560.7	564.4	568.1	571.7	575.1	578.4	581.7	585.0	588.2	566.8
120°	602.6	605.4	608.3	611.1	614.1	617.2	620.7	624.1	627.5	630.9	633.3
122.5°	641.1	644.1	647.1	650.2	653.2	656.6	660.3	664.1	667.9	671.7	673.0
125°	699.8	702.3	704.8	707.3	709.8	712.8	716.5	720.1	723.8	727.4	728.8
127.5°	753.0	755.8	758.6	761.3	764.0	766.8	769.5	772.2	775.0	777.7	779.6
130°	786.8	789.9	792.9	796.0	799.0	801.6	803.7	805.8	807.9	810.0	812.1
132.5°	821.2	823.8	826.4	829.1	831.6	834.0	836.1	838.2	840.3	842.4	844.2
135°	866.0	869.0	872.1	875.2	878.3	880.6	882.3	884.1	885.8	887.5	889.4
137.5°	911.3	913.4	915.6	917.7	919.8	921.9	923.8	925.8	927.7	929.7	931.5
140°	940.8	942.4	944.0	945.5	947.0	948.9	950.9	953.0	955.2	957.2	958.9
142.5°	965.6	967.0	968.5	969.8	971.2	973.1	975.4	977.9	980.3	982.7	984.3
145°	1004.6	1004.4	1004.2	1004.0	1003.8	1005.3	1008.6	1011.8	1015.1	1018.3	1019.6
147.5°	1038.5	1037.7	1037.1	1036.3	1035.6	1036.8	1040.0	1043.3	1046.5	1049.7	1050.7
150°	1060.5	1059.2	1057.8	1056.5	1055.2	1056.0	1059.1	1062.2	1065.3	1068.3	1069.4
152.5°	1079.1	1077.6	1076.1	1074.7	1073.2	1073.8	1076.8	1079.7	1082.6	1085.5	1086.7
155°	1106.2	1104.5	1102.7	1101.0	1099.3	1099.6	1101.8	1104.2	1106.5	1108.7	1109.8
157.5°	1127.3	1125.9	1124.5	1122.9	1121.5	1121.6	1123.2	1124.8	1126.4	1128.0	1129.4
160°	1139.7	1138.6	1137.5	1136.2	1135.1	1135.1	1136.2	1137.5	1138.6	1139.7	1140.9
162.5°	1150.8	1149.6	1148.5	1147.3	1146.1	1146.0	1147.1	1148.0	1149.1	1150.1	1151.3
165°	1165.5	1164.4	1163.3	1162.1	1160.9	1160.6	1161.2	1161.8	1162.4	1163.0	1164.3
167.5°	1176.6	1175.4	1174.3	1173.1	1172.0	1171.7	1172.2	1172.7	1173.3	1173.8	1175.2
170°	1182.8	1181.6	1180.4	1179.3	1178.2	1177.8	1178.2	1178.6	1178.9	1179.3	1180.6
172.5°	1186.8	1185.7	1184.6	1183.5	1182.3	1181.9	1182.3	1182.7	1183.1	1183.5	1184.8
175°	1192.2	1190.9	1189.6	1188.2	1186.8	1186.4	1186.8	1187.1	1187.5	1187.9	1189.3
177.5°	1193.1	1192.0	1191.0	1189.9	1188.8	1188.4	1188.5	1188.6	1188.8	1188.9	1190.1
180°	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7



TEST NUMBER: P331696-830

CATALOG NUMBER: SA2XXRDIP-C675D925U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2
2.5°	1058.2	1059.9	1061.6	1062.2	1062.0	1061.6	1061.3	1060.9
5°	1049.7	1051.7	1053.6	1054.2	1053.6	1052.9	1052.3	1051.7
7.5°	1032.7	1033.3	1033.9	1033.6	1032.5	1031.4	1030.3	1029.2
10°	1015.8	1015.1	1014.5	1013.5	1012.2	1011.0	1009.7	1008.3
12.5°	996.3	995.1	993.9	992.3	990.1	988.1	985.9	983.7
15°	959.9	955.7	951.7	948.6	946.5	944.3	942.2	940.1
17.5°	918.7	913.8	909.0	904.7	901.1	897.4	893.7	890.0
20°	889.9	884.6	879.2	874.2	869.5	864.8	860.1	855.4
22.5°	858.4	851.5	844.6	839.4	835.8	832.4	828.9	825.4
25°	806.1	797.3	788.5	782.6	779.4	776.2	773.0	769.8
27.5°	756.2	746.0	735.8	728.1	723.0	717.9	712.8	707.8
30°	721.0	710.1	699.2	690.9	685.0	679.3	673.5	667.8
32.5°	685.6	673.2	660.7	651.8	646.3	640.9	635.5	630.1
35°	630.3	616.8	603.3	594.2	589.5	584.8	580.1	575.4
37.5°	576.3	561.5	546.7	536.5	531.1	525.8	520.4	515.0
40°	540.2	525.0	509.8	499.5	493.9	488.3	482.8	477.2
42.5°	503.8	488.0	472.4	461.8	456.5	451.1	445.7	440.3
45°	450.7	435.5	420.4	410.2	405.1	399.9	394.8	389.6
47.5°	399.2	384.1	368.9	359.1	354.4	349.8	345.1	340.4
50°	366.0	351.2	336.5	326.8	322.3	317.8	313.4	308.9
52.5°	334.7	320.4	306.1	297.0	292.8	288.7	284.6	280.4
55°	287.1	274.2	261.4	253.0	248.9	244.8	240.7	236.7
57.5°	243.7	232.1	220.3	212.6	209.2	205.9	202.4	199.0
60°	214.0	203.0	192.1	184.9	181.5	178.1	174.7	171.3
62.5°	188.0	177.6	167.2	161.0	158.9	156.9	154.9	152.8
65°	152.9	145.6	138.4	134.4	133.7	133.1	132.4	131.9
67.5°	123.4	120.1	116.8	114.7	114.0	113.4	112.7	112.0
70°	107.4	105.2	103.0	101.6	100.7	99.8	99.0	98.1
72.5°	93.4	91.6	89.8	88.7	88.1	87.7	87.1	86.6
75°	74.0	72.5	71.0	70.1	69.9	69.7	69.5	69.3
77.5°	56.0	55.1	54.3	53.7	53.3	53.1	52.7	52.3
80°	44.5	43.6	42.8	42.3	42.3	42.3	42.3	42.3
82.5°	33.6	33.1	32.6	32.3	32.3	32.3	32.3	32.3
85°	18.3	18.3	18.3	18.3	18.3	18.3	18.3	18.3
87.5°	9.6	9.7	9.7	9.7	9.8	9.9	10.0	10.0
90°	19.1	20.1	21.0	21.7	22.1	22.4	22.9	23.3
92.5°	20.9	21.5	22.0	22.3	22.5	22.8	23.0	23.3
95°	35.4	36.5	37.4	37.8	37.6	37.4	37.2	37.0
97.5°	46.5	47.2	48.0	48.4	48.7	48.9	49.2	49.4
100°	52.1	53.6	55.2	56.2	56.6	56.9	57.3	57.7
102.5°	54.4	56.5	58.4	59.7	60.2	60.7	61.3	61.8
105°	56.7	58.8	60.9	62.4	63.2	63.9	64.7	65.4
107.5°	69.2	67.1	64.9	64.3	65.0	65.8	66.5	67.3
110°	112.4	93.2	74.1	64.9	65.7	66.4	67.2	68.1



TEST NUMBER: P331696-830

CATALOG NUMBER: SA2XXRDIP-C675D925U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	240.4	170.6	100.9	66.3	66.8	67.5	68.1	68.7
115°	354.0	265.4	176.8	125.6	111.9	98.1	84.4	70.6
117.5°	545.4	524.1	502.6	469.2	424.0	378.7	333.5	288.2
120°	635.6	637.9	640.2	628.4	602.6	576.7	550.9	525.1
122.5°	674.4	675.7	677.1	675.3	670.3	665.2	660.3	655.3
125°	730.1	731.4	732.7	733.7	734.2	734.8	735.5	736.0
127.5°	781.6	783.5	785.5	786.5	786.6	786.7	786.8	786.9
130°	814.3	816.3	818.4	819.4	819.3	819.0	818.8	818.6
132.5°	846.0	847.8	849.6	850.4	850.2	850.0	849.8	849.6
135°	891.4	893.2	895.1	895.9	895.5	895.1	894.8	894.4
137.5°	933.4	935.3	937.2	937.8	937.2	936.5	935.9	935.2
140°	960.6	962.4	964.1	964.5	963.6	962.6	961.7	960.6
142.5°	985.8	987.4	989.0	989.3	988.4	987.4	986.5	985.4
145°	1021.1	1022.4	1023.7	1023.9	1022.9	1022.0	1021.1	1020.1
147.5°	1051.7	1052.6	1053.7	1053.8	1052.9	1052.2	1051.3	1050.6
150°	1070.5	1071.8	1072.9	1073.0	1072.0	1071.0	1070.1	1069.1
152.5°	1087.8	1088.9	1090.1	1090.1	1088.7	1087.5	1086.3	1085.0
155°	1111.1	1112.2	1113.3	1113.1	1111.6	1110.0	1108.5	1107.0
157.5°	1130.6	1131.9	1133.2	1133.1	1131.6	1130.1	1128.6	1127.2
160°	1142.0	1143.2	1144.3	1144.2	1142.8	1141.5	1140.2	1138.9
162.5°	1152.6	1154.0	1155.3	1155.1	1153.5	1151.8	1150.2	1148.5
165°	1165.6	1167.0	1168.3	1168.3	1167.0	1165.6	1164.3	1163.0
167.5°	1176.5	1177.8	1179.2	1178.9	1177.2	1175.5	1173.8	1172.1
170°	1182.0	1183.4	1184.7	1184.5	1182.8	1181.0	1179.3	1177.6
172.5°	1186.1	1187.5	1188.8	1188.6	1186.8	1185.2	1183.5	1181.8
175°	1190.6	1191.9	1193.3	1193.0	1191.1	1189.2	1187.2	1185.3
177.5°	1191.1	1192.2	1193.3	1193.1	1191.8	1190.3	1188.9	1187.6
180°	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7

(END OF REPORT)