

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333130-940

Luminaire Tested: **S125DIP-S375D590U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333130-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S375D590U940-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3464.5 lumens
Efficiency: N/A
Efficacy: 135.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333130-940

CATALOG NUMBER: S125DIP-S375D590U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333130-940

CATALOG NUMBER: S125DIP-S375D590U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	91	87	84	86	83	80	77	68	65	63	54	52	51	41	40	39	33
2	87	79	73	68	79	72	67	63	59	56	52	47	44	42	36	34	33	27
3	79	70	63	57	72	64	57	52	52	48	44	42	38	36	32	30	28	23
4	72	62	54	48	65	56	50	44	46	41	37	37	33	31	28	26	24	20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21	17
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18	15
7	56	44	36	31	51	41	34	29	34	28	25	27	23	20	21	18	16	13
8	52	40	33	27	47	37	30	25	31	25	22	25	21	18	19	17	15	12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11
10	45	33	26	22	41	31	24	20	26	21	17	21	17	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3364	3364	3364
5°	3371	3339	3361
10°	3351	3316	3335
15°	3315	3276	3290
20°	3263	3221	3226
25°	3207	3154	3151
30°	3138	3082	3067
35°	3064	3005	2964
40°	2989	2922	2880
45°	2906	2846	2789
50°	2816	2753	2671
55°	2728	2649	2575
60°	2623	2545	2454
65°	2500	2419	2337
70°	2381	2274	2194
75°	2168	2099	2024
80°	1930	1901	1852
85°	1675	1712	1615



TEST NUMBER: P333130-940

CATALOG NUMBER: S125DIP-S375D590U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.1	1.4
10°-20°	138.7	4.0
20°-30°	204.9	5.9
30°-40°	239.0	6.9
40°-50°	240.1	6.9
50°-60°	210.7	6.1
60°-70°	157.0	4.5
70°-80°	89.8	2.6
80°-90°	27.5	0.8
90°-100°	24.9	0.7
100°-110°	153.7	4.4
110°-120°	278.8	8.0
120°-130°	357.8	10.3
130°-140°	384.8	11.1
140°-150°	361.2	10.4
150°-160°	292.2	8.4
160°-170°	189.0	5.5
170°-180°	65.2	1.9
0°-30°	392.7	11.3
0°-40°	631.7	18.2
0°-60°	1082.6	31.2
0°-90°	1356.9	39.2
90°-120°	457.4	13.2
90°-150°	1561.2	45.1
90°-180°	2108.0	60.8
0°-180°	3464.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	521	521	521	521	521	
5°	520	519	515	519	518	49
15°	496	494	490	492	492	140
25°	450	448	443	443	442	207
35°	389	387	381	379	376	243
45°	318	316	312	307	305	245
55°	242	241	235	232	229	216
65°	164	163	158	155	153	162
75°	87	86	84	83	81	93
85°	23	23	23	23	22	25
90°	0	5	8	11	12	2
95°	29	26	8	11	11	37
105°	150	152	152	152	151	159
115°	281	283	284	282	279	278
125°	399	403	403	401	399	357
135°	498	501	500	499	496	384
145°	578	578	578	579	576	361
155°	636	633	634	635	631	293
165°	671	668	668	671	667	189
175°	686	683	684	687	683	65
180°	686	686	686	686	686	



TEST NUMBER: P333130-940

CATALOG NUMBER: S125DIP-S375D590U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9
2.5°	522.2	522.0	521.8	521.6	521.4	520.8	520.1	519.4	518.7	517.9	518.7
5°	520.0	519.9	519.7	519.5	519.3	518.8	517.9	517.0	516.0	515.1	515.9
7.5°	515.3	515.1	515.0	514.8	514.6	514.0	513.0	511.9	511.0	510.0	510.8
10°	511.0	510.9	510.7	510.5	510.3	509.7	508.7	507.7	506.7	505.7	506.4
12.5°	505.8	505.4	505.1	504.8	504.4	503.8	502.8	501.9	501.0	500.1	500.6
15°	495.8	495.5	495.3	495.0	494.6	494.0	493.0	492.0	491.0	490.0	490.4
17.5°	484.3	483.9	483.5	483.1	482.7	482.0	480.9	479.9	478.8	477.8	478.4
20°	474.7	474.6	474.4	474.2	474.0	473.3	472.2	470.9	469.8	468.6	469.2
22.5°	465.2	464.8	464.5	464.2	463.9	463.2	462.0	460.9	459.8	458.7	459.1
25°	450.0	449.6	449.1	448.6	448.2	447.4	446.2	445.0	443.8	442.6	442.8
27.5°	432.3	432.0	431.8	431.5	431.2	430.4	429.3	428.0	426.8	425.5	425.6
30°	420.8	420.5	420.2	419.9	419.6	418.8	417.5	416.1	414.7	413.3	413.1
32.5°	408.2	407.8	407.4	407.0	406.5	405.7	404.5	403.2	402.1	400.8	400.5
35°	388.6	388.3	387.9	387.5	387.2	386.3	385.0	383.8	382.5	381.2	380.8
37.5°	368.3	367.8	367.4	366.8	366.4	365.6	364.4	363.2	361.9	360.8	360.1
40°	354.5	353.9	353.5	353.0	352.6	351.7	350.4	349.2	347.9	346.6	345.8
42.5°	339.6	339.2	338.9	338.4	338.0	337.2	335.9	334.7	333.3	332.1	331.4
45°	318.2	317.8	317.4	317.1	316.6	315.9	314.9	313.8	312.6	311.6	310.5
47.5°	295.1	295.1	295.1	295.2	295.2	294.5	293.2	291.9	290.5	289.2	288.1
50°	280.3	280.0	279.7	279.4	279.1	278.5	277.3	276.3	275.2	274.0	272.9
52.5°	265.1	264.8	264.7	264.5	264.3	263.6	262.4	261.3	260.0	258.9	257.9
55°	242.3	242.0	241.7	241.5	241.2	240.4	239.2	237.9	236.6	235.3	234.5
57.5°	218.4	218.2	218.0	217.9	217.8	217.1	216.1	215.0	213.9	212.9	211.8
60°	203.1	202.8	202.4	202.1	201.7	201.0	200.0	199.0	198.0	197.0	196.1
62.5°	187.3	187.1	186.7	186.5	186.2	185.6	184.8	183.9	183.0	182.2	181.2
65°	163.6	163.5	163.3	163.1	162.9	162.3	161.3	160.2	159.3	158.3	157.4
67.5°	140.6	140.3	139.8	139.5	139.1	138.5	137.8	137.0	136.3	135.5	134.8
70°	126.1	125.6	125.2	124.8	124.3	123.6	122.8	122.0	121.2	120.4	119.8
72.5°	110.3	109.9	109.7	109.3	109.1	108.6	108.1	107.5	107.0	106.5	105.8
75°	86.9	86.8	86.6	86.4	86.2	85.9	85.4	85.0	84.5	84.1	83.8
77.5°	65.5	65.4	65.3	65.2	65.2	65.0	64.7	64.5	64.2	63.9	63.8
80°	51.9	51.9	51.9	51.9	51.9	51.8	51.6	51.5	51.3	51.1	51.0
82.5°	40.0	39.9	39.8	39.6	39.5	39.4	39.3	39.3	39.2	39.2	39.1
85°	22.6	22.7	22.8	22.9	23.0	23.1	23.1	23.1	23.1	23.1	23.0
87.5°	9.0	9.2	9.4	9.5	9.7	9.9	10.0	10.0	10.1	10.2	10.3
90°	0.5	1.4	2.3	3.2	4.1	5.0	5.8	6.6	7.3	8.1	8.7
92.5°	7.8	7.2	6.6	6.0	5.3	5.4	6.1	6.8	7.4	8.1	8.7
95°	29.0	28.6	28.4	28.0	27.6	25.3	21.0	16.8	12.4	8.1	8.7
97.5°	60.5	61.2	61.8	62.3	63.0	59.0	50.6	42.0	33.5	25.1	21.8
100°	85.0	85.3	85.6	86.0	86.3	86.7	87.2	87.7	88.1	88.5	71.7
102.5°	109.8	110.2	110.7	111.1	111.5	111.8	112.1	112.4	112.7	113.0	109.8
105°	149.5	150.0	150.5	151.0	151.4	151.6	151.6	151.6	151.6	151.6	151.6
107.5°	190.9	190.9	190.9	190.9	190.9	191.0	191.2	191.5	191.7	191.9	191.9
110°	217.8	217.8	217.8	217.8	217.8	217.8	218.1	218.3	218.6	218.7	218.5



TEST NUMBER: P333130-940

CATALOG NUMBER: S125DIP-S375D590U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	243.0	243.3	243.5	243.8	244.1	244.2	244.4	244.5	244.7	244.8	244.4
115°	280.8	281.4	282.0	282.5	283.1	283.5	283.6	283.7	283.7	283.9	283.5
117.5°	320.0	319.9	319.9	319.9	319.9	320.1	320.6	321.0	321.4	321.8	321.3
120°	344.5	344.3	344.2	344.1	343.9	344.1	344.5	344.7	345.1	345.4	345.2
122.5°	366.0	366.4	366.8	367.3	367.7	368.0	368.2	368.4	368.5	368.6	368.5
125°	399.4	400.2	400.9	401.7	402.5	403.0	403.0	403.0	403.0	403.0	402.5
127.5°	431.2	431.8	432.4	432.9	433.5	433.7	433.6	433.6	433.5	433.5	433.2
130°	450.8	451.3	451.9	452.5	453.0	453.3	453.4	453.6	453.7	453.8	453.4
132.5°	470.3	470.9	471.6	472.3	472.9	473.1	472.9	472.6	472.3	472.2	472.1
135°	498.1	498.7	499.4	500.1	500.8	501.1	500.8	500.5	500.3	500.1	499.9
137.5°	523.6	524.2	524.8	525.4	525.9	526.2	525.9	525.8	525.6	525.3	525.4
140°	540.3	540.6	540.7	541.0	541.2	541.3	541.2	541.0	540.9	540.8	541.0
142.5°	555.4	555.5	555.6	555.8	555.9	556.1	556.2	556.3	556.5	556.7	556.7
145°	577.5	577.7	577.9	578.1	578.4	578.5	578.5	578.5	578.5	578.5	578.5
147.5°	596.7	596.7	596.6	596.6	596.6	596.6	596.7	596.9	597.0	597.2	597.4
150°	608.9	608.8	608.5	608.3	608.1	608.1	608.3	608.5	608.8	608.9	609.2
152.5°	620.8	620.3	619.8	619.3	618.8	618.7	618.8	619.1	619.3	619.6	619.8
155°	636.0	635.3	634.6	633.9	633.2	633.0	633.2	633.5	633.6	633.9	634.3
157.5°	647.6	647.2	646.8	646.4	646.0	645.9	645.9	645.9	645.9	646.0	646.3
160°	655.8	655.1	654.4	653.7	653.1	652.8	652.9	653.0	653.1	653.3	653.7
162.5°	662.3	661.6	660.9	660.2	659.6	659.3	659.4	659.5	659.6	659.8	660.4
165°	671.0	670.4	669.7	669.1	668.3	668.1	668.2	668.2	668.4	668.5	669.1
167.5°	677.5	676.9	676.2	675.5	674.8	674.5	674.6	674.7	674.8	674.9	675.7
170°	681.3	680.5	679.7	678.9	678.1	677.7	677.8	678.0	678.1	678.1	679.0
172.5°	683.7	682.9	682.1	681.3	680.5	680.2	680.4	680.6	680.8	681.0	681.8
175°	686.3	685.6	684.9	684.3	683.6	683.3	683.4	683.6	683.7	683.8	684.7
177.5°	687.5	687.0	686.4	685.9	685.4	685.1	685.2	685.3	685.4	685.5	686.2
180°	686.3	686.3	686.3	686.3	686.3	686.3	686.3	686.3	686.3	686.3	686.3



TEST NUMBER: P333130-940

CATALOG NUMBER: S125DIP-S375D590U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	520.9	520.9	520.9	520.9	520.9	520.9	520.9	520.9
2.5°	519.4	520.1	520.8	521.2	521.1	521.0	521.0	520.9
5°	516.7	517.6	518.4	518.8	518.7	518.6	518.5	518.4
7.5°	511.6	512.4	513.2	513.5	513.4	513.4	513.3	513.2
10°	507.1	507.8	508.6	508.9	508.8	508.7	508.6	508.5
12.5°	501.2	501.9	502.4	502.7	502.7	502.7	502.7	502.6
15°	490.9	491.3	491.9	492.0	492.0	492.0	492.0	492.0
17.5°	478.9	479.5	480.1	480.1	479.7	479.2	478.8	478.3
20°	469.8	470.5	471.1	471.3	470.7	470.3	469.8	469.4
22.5°	459.5	459.9	460.4	460.4	460.1	459.8	459.5	459.1
25°	443.0	443.2	443.4	443.3	443.0	442.7	442.5	442.2
27.5°	425.6	425.6	425.7	425.6	425.3	425.0	424.7	424.5
30°	413.0	412.8	412.6	412.4	412.1	411.9	411.5	411.3
32.5°	400.2	399.8	399.5	399.1	398.6	398.1	397.6	397.1
35°	380.3	379.9	379.3	378.8	378.1	377.3	376.6	375.9
37.5°	359.4	358.7	358.0	357.5	357.0	356.7	356.2	355.8
40°	344.9	344.1	343.3	342.8	342.5	342.1	341.9	341.6
42.5°	330.6	329.8	329.0	328.5	328.1	327.6	327.3	326.8
45°	309.3	308.3	307.2	306.5	306.2	305.9	305.7	305.4
47.5°	287.0	285.9	284.7	283.8	283.2	282.6	282.0	281.3
50°	271.7	270.5	269.3	268.4	267.7	267.1	266.4	265.8
52.5°	256.8	255.7	254.7	253.9	253.2	252.4	251.7	251.0
55°	233.6	232.8	232.0	231.3	230.7	230.0	229.3	228.7
57.5°	210.7	209.6	208.6	207.9	207.5	207.1	206.8	206.4
60°	195.2	194.2	193.3	192.5	191.9	191.3	190.6	190.0
62.5°	180.2	179.1	178.2	177.5	177.0	176.5	175.9	175.5
65°	156.6	155.8	155.0	154.4	154.0	153.6	153.3	152.9
67.5°	134.1	133.4	132.7	132.2	132.1	131.8	131.6	131.3
70°	119.2	118.7	118.2	117.7	117.3	117.0	116.5	116.2
72.5°	105.2	104.6	104.0	103.5	103.2	102.8	102.4	102.0
75°	83.6	83.3	82.9	82.7	82.3	81.9	81.6	81.1
77.5°	63.7	63.5	63.3	63.1	62.9	62.6	62.3	62.1
80°	50.9	50.8	50.7	50.6	50.4	50.2	50.0	49.8
82.5°	38.9	38.7	38.6	38.4	38.4	38.4	38.3	38.3
85°	22.9	22.8	22.7	22.6	22.4	22.2	22.0	21.8
87.5°	10.4	10.5	10.6	10.7	10.6	10.5	10.4	10.3
90°	9.3	9.8	10.4	10.9	11.2	11.5	11.9	12.2
92.5°	9.3	9.8	10.4	10.8	10.9	11.1	11.2	11.4
95°	9.3	9.8	10.4	10.7	10.7	10.7	10.7	10.7
97.5°	18.6	15.4	12.3	10.7	10.7	10.7	10.7	10.7
100°	54.8	38.0	21.1	12.5	12.0	11.6	11.1	10.7
102.5°	106.6	103.3	100.2	94.8	87.0	79.4	71.7	64.0
105°	151.6	151.6	151.6	151.6	151.4	151.3	151.2	151.1
107.5°	192.0	192.0	192.0	191.8	191.5	191.2	190.8	190.5
110°	218.1	217.8	217.4	217.3	217.4	217.5	217.7	217.8



TEST NUMBER: P333130-940

CATALOG NUMBER: S125DIP-S375D590U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	244.0	243.5	243.1	242.8	242.6	242.5	242.4	242.2
115°	282.9	282.5	282.0	281.5	280.8	280.2	279.5	278.8
117.5°	320.7	320.0	319.5	319.1	318.8	318.4	318.2	317.9
120°	345.0	344.7	344.6	344.1	343.6	343.0	342.4	341.9
122.5°	368.2	368.0	367.7	367.3	366.7	366.0	365.3	364.7
125°	402.1	401.5	401.1	400.7	400.4	400.0	399.8	399.4
127.5°	432.9	432.7	432.5	431.9	431.1	430.3	429.4	428.6
130°	453.2	452.8	452.5	452.0	451.5	450.8	450.3	449.8
132.5°	472.0	471.9	471.9	471.5	471.0	470.4	469.8	469.3
135°	499.6	499.4	499.2	498.7	498.1	497.4	496.7	496.1
137.5°	525.4	525.5	525.5	525.2	524.7	524.1	523.5	522.9
140°	541.3	541.4	541.7	541.4	540.8	540.1	539.5	538.8
142.5°	556.8	556.8	556.9	556.5	555.9	555.2	554.5	553.8
145°	578.7	578.8	578.9	578.6	577.9	577.3	576.6	575.9
147.5°	597.4	597.6	597.7	597.4	596.6	595.8	594.9	594.1
150°	609.4	609.7	609.8	609.6	608.7	607.7	606.8	605.9
152.5°	620.0	620.3	620.5	620.2	619.4	618.6	617.7	616.9
155°	634.6	634.9	635.3	635.0	634.1	633.2	632.3	631.3
157.5°	646.7	647.0	647.4	647.1	646.2	645.2	644.4	643.5
160°	654.2	654.6	655.1	654.8	653.9	653.0	652.1	651.2
162.5°	661.0	661.6	662.3	662.1	661.1	660.1	659.2	658.1
165°	669.9	670.6	671.2	671.1	670.2	669.3	668.4	667.4
167.5°	676.5	677.3	678.1	678.1	677.1	676.0	675.0	674.0
170°	680.0	680.9	681.8	681.7	680.7	679.7	678.7	677.7
172.5°	682.6	683.5	684.3	684.2	683.1	682.2	681.1	680.1
175°	685.5	686.4	687.4	687.3	686.3	685.3	684.3	683.2
177.5°	686.8	687.4	688.0	688.0	687.2	686.5	685.8	685.1
180°	686.3	686.3	686.3	686.3	686.3	686.3	686.3	686.3

(END OF REPORT)