

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333189-940

Luminaire Tested: **S125DIP-S610D1035U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333189-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S610D1035U940-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5565.5 lumens  
Efficiency: N/A  
Efficacy: 125.1 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 44.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333189-940

CATALOG NUMBER: S125DIP-S610D1035U940-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333189-940

CATALOG NUMBER: S125DIP-S610D1035U940-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	47	47	47	41
1	96	92	88	84	87	84	80	78	69	66	64	55	53	52	42	41	40	34
2	87	80	74	69	79	73	68	64	60	57	54	48	46	44	37	36	34	29
3	80	71	63	58	72	65	58	54	53	49	45	43	40	37	33	31	29	25
4	73	62	55	49	66	57	51	45	47	42	39	38	35	32	30	27	25	21
5	67	56	48	42	61	51	44	39	42	37	33	34	31	28	27	24	22	19
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	22	19	16
7	57	45	37	32	52	41	34	30	35	29	25	28	24	21	22	19	17	15
8	53	41	33	28	48	38	31	26	31	26	23	26	22	19	20	18	15	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	5154	5154	5154	5154
5°	5969	5172	4528	5172
10°	6944	5145	3968	5145
15°	7687	5107	3660	5107
20°	8605	5047	3413	5047
25°	10080	4980	3293	4980
30°	10888	4914	3188	4914
35°	8952	4788	3120	4788
40°	6363	4615	3044	4615
45°	4888	4381	3001	4381
50°	4173	4091	2995	4091
55°	3715	3806	3021	3806
60°	3352	3495	3099	3495
65°	3096	3183	3177	3183
70°	2814	2859	3225	2859
75°	2485	2518	3194	2518
80°	2094	2053	2923	2053
85°	1660	1482	2356	1482



TEST NUMBER: P333189-940

CATALOG NUMBER: S125DIP-S610D1035U940-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	76.8	1.4
10°-20°	228.8	4.1
20°-30°	371.4	6.7
30°-40°	453.1	8.1
40°-50°	412.2	7.4
50°-60°	328.3	5.9
60°-70°	228.7	4.1
70°-80°	121.9	2.2
80°-90°	33.2	0.6
90°-100°	320.0	5.8
100°-110°	688.0	12.4
110°-120°	645.7	11.6
120°-130°	523.3	9.4
130°-140°	419.9	7.5
140°-150°	316.9	5.7
150°-160°	223.1	4.0
160°-170°	131.5	2.4
170°-180°	42.8	0.8
0°-30°	677.0	12.2
0°-40°	1130.1	20.3
0°-60°	1870.6	33.6
0°-90°	2254.5	40.5
90°-120°	1653.7	29.7
90°-150°	2913.7	52.4
90°-180°	3311.0	59.5
0°-180°	5565.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	798	798	798	798	798	
5°	921	798	698	798	921	93
15°	1150	764	547	764	1150	329
25°	1415	699	462	699	1415	646
35°	1135	607	396	607	1135	695
45°	535	480	329	480	535	428
55°	330	338	268	338	330	297
65°	203	208	208	208	203	201
75°	100	101	128	101	100	107
85°	22	20	32	20	22	26
90°	20	1	20	1	20	15
95°	209	29	209	29	209	296
105°	1180	101	1180	101	1180	1172
115°	1314	180	1314	180	1314	1284
125°	1035	249	1035	249	1035	937
135°	860	292	860	292	860	666
145°	678	340	678	340	678	431
155°	569	388	569	388	569	265
165°	498	424	498	424	498	143
175°	448	441	448	441	448	44
180°	442	442	442	442	442	



TEST NUMBER: P333189-940

CATALOG NUMBER: S125DIP-S610D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1
2.5°	844.2	843.0	842.0	839.8	841.4	836.8	834.6	830.9	826.3	824.7	822.7
5°	920.7	922.4	924.1	916.9	917.7	912.9	902.1	893.2	886.2	877.0	870.6
7.5°	1012.8	1008.8	1008.5	1003.9	996.0	989.6	978.2	963.7	949.7	933.7	920.5
10°	1058.9	1059.3	1056.2	1050.8	1042.3	1036.2	1021.3	1007.1	989.8	969.5	954.9
12.5°	1093.6	1095.0	1091.2	1083.9	1079.7	1066.0	1054.4	1037.4	1016.9	1000.7	978.5
15°	1149.7	1145.9	1143.3	1134.1	1126.9	1112.8	1094.1	1076.5	1054.2	1033.5	1012.8
17.5°	1203.7	1206.8	1201.7	1193.3	1171.3	1154.6	1129.6	1105.5	1077.6	1050.0	1025.3
20°	1252.0	1254.7	1246.9	1232.3	1205.9	1189.3	1156.5	1125.2	1093.1	1057.6	1030.5
22.5°	1312.2	1310.0	1299.5	1277.3	1254.5	1223.7	1188.2	1150.2	1109.9	1069.7	1033.7
25°	1414.6	1400.3	1393.9	1366.5	1336.3	1291.3	1242.5	1187.0	1136.8	1083.6	1037.6
27.5°	1471.3	1466.9	1459.7	1440.6	1408.9	1360.8	1303.2	1235.6	1164.8	1097.7	1037.3
30°	1460.0	1460.6	1461.3	1455.2	1434.9	1398.6	1341.4	1268.5	1184.5	1109.0	1039.3
32.5°	1359.1	1371.5	1383.3	1397.2	1402.9	1396.0	1360.1	1294.3	1207.9	1122.0	1038.1
35°	1135.4	1139.2	1177.5	1215.4	1266.9	1306.9	1333.6	1304.5	1231.6	1133.1	1036.9
37.5°	885.3	903.7	930.1	973.0	1047.3	1113.8	1199.4	1238.8	1215.2	1136.7	1034.5
40°	754.7	771.7	788.9	832.6	895.3	975.9	1073.1	1156.1	1175.5	1125.2	1026.4
42.5°	653.9	667.4	686.5	719.3	771.7	843.1	936.0	1044.5	1111.2	1092.3	1009.3
45°	535.2	543.7	558.6	584.7	622.6	678.5	760.5	879.0	982.3	1016.6	968.8
47.5°	458.1	458.1	469.7	487.7	515.1	562.5	623.1	716.0	826.3	908.0	904.2
50°	415.3	413.6	422.8	438.4	460.0	491.5	549.5	623.7	729.7	822.2	847.8
52.5°	378.4	378.6	384.2	395.7	413.9	440.9	484.1	551.0	641.6	736.5	785.0
55°	329.9	328.6	335.0	342.8	356.1	373.6	404.8	455.9	529.4	622.9	685.9
57.5°	285.5	289.2	291.8	297.2	308.2	319.9	346.3	383.8	442.1	522.4	589.0
60°	259.5	263.2	265.2	270.6	279.5	289.6	310.0	340.5	389.6	458.7	524.7
62.5°	236.1	239.1	239.8	244.6	251.8	261.7	277.7	303.3	342.1	402.5	467.3
65°	202.6	202.6	203.9	209.0	212.4	221.2	233.4	252.0	283.2	330.3	385.5
67.5°	170.1	171.8	171.5	173.7	176.8	183.7	192.4	207.8	230.9	265.2	309.4
70°	149.0	150.4	150.1	151.8	155.2	159.5	166.7	181.2	197.8	227.3	265.2
72.5°	130.1	130.6	129.7	132.0	134.0	137.9	145.8	153.6	169.1	193.9	225.2
75°	99.6	100.2	100.9	102.3	104.3	106.4	110.4	118.2	128.4	147.0	167.0
77.5°	74.6	73.4	75.0	74.8	76.0	77.5	81.1	85.2	93.5	105.3	120.8
80°	56.3	56.5	56.5	56.9	58.6	59.7	62.7	65.7	72.1	81.0	91.8
82.5°	41.0	41.9	41.4	42.0	43.4	44.1	45.8	48.3	52.1	59.0	66.9
85°	22.4	20.7	21.3	22.0	22.0	22.4	23.7	24.7	26.8	29.4	32.5
87.5°	10.6	11.1	11.2	11.2	11.5	11.1	12.0	11.9	12.5	13.1	13.9
90°	20.5	20.5	19.6	19.6	19.6	17.8	16.9	16.1	15.2	14.3	12.5
92.5°	56.8	58.2	59.5	61.6	73.0	86.1	114.5	157.7	232.3	287.0	291.6
95°	209.2	223.5	230.6	257.3	320.5	395.2	504.7	640.1	771.8	788.7	643.6
97.5°	505.6	517.0	542.8	592.7	647.6	751.6	858.3	953.2	976.5	842.3	574.7
100°	694.4	708.6	741.5	805.6	867.0	959.6	1051.3	1094.9	1026.4	803.8	512.7
102.5°	905.1	915.8	951.6	997.2	1062.8	1125.5	1169.5	1142.6	996.5	736.2	465.7
105°	1179.5	1190.2	1208.0	1237.3	1265.8	1275.6	1236.4	1114.5	900.9	645.3	420.2
107.5°	1325.1	1332.2	1338.1	1338.3	1323.8	1277.4	1176.8	1014.1	803.3	582.9	400.9
110°	1373.5	1373.5	1367.3	1350.4	1310.4	1234.7	1109.1	940.0	747.7	553.7	395.2



TEST NUMBER: P333189-940

CATALOG NUMBER: S125DIP-S610D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1367.8	1361.5	1345.9	1316.9	1258.4	1169.1	1042.2	881.6	706.4	536.6	395.2
115°	1313.9	1302.3	1277.4	1234.7	1165.2	1068.2	946.3	808.2	661.4	518.1	397.9
117.5°	1219.3	1212.2	1187.5	1143.4	1073.9	984.9	879.9	760.9	634.5	509.0	403.8
120°	1158.2	1151.0	1126.9	1084.2	1018.3	940.0	842.1	735.3	619.6	504.7	409.5
122.5°	1104.0	1097.6	1073.5	1034.4	975.6	902.2	815.0	716.0	606.7	501.1	414.5
125°	1035.3	1026.4	1006.7	970.3	920.4	856.3	778.9	688.1	589.3	496.7	422.8
127.5°	976.5	972.6	954.0	921.9	876.6	816.6	744.4	659.6	573.3	494.5	432.3
130°	944.5	939.1	921.3	892.0	847.5	789.6	720.1	641.9	562.6	493.1	438.0
132.5°	912.4	906.3	890.0	860.6	816.1	760.4	697.3	624.0	554.0	493.1	444.3
135°	859.9	854.5	838.6	809.1	770.0	719.3	662.3	600.8	543.9	493.1	453.1
137.5°	803.8	798.0	783.2	756.4	721.4	678.3	631.0	581.3	534.8	494.2	461.1
140°	764.6	760.2	746.9	723.7	690.8	653.4	612.4	570.6	530.6	494.9	464.7
142.5°	728.3	724.6	711.9	692.4	664.4	632.0	596.7	561.3	527.0	495.6	466.8
145°	678.3	674.8	664.9	649.8	628.5	604.4	576.8	549.2	521.7	494.9	469.1
147.5°	636.0	634.4	628.7	616.5	599.6	581.5	560.3	537.9	516.1	492.6	470.0
150°	612.4	611.5	608.0	597.3	584.0	567.9	551.0	531.5	511.8	490.4	470.0
152.5°	593.9	593.0	589.5	580.9	569.7	557.2	541.7	524.3	506.8	487.7	469.3
155°	568.8	567.9	565.3	559.0	550.1	540.4	527.9	513.6	498.5	482.5	467.3
157.5°	546.4	546.5	544.0	539.0	532.0	524.3	514.7	502.9	490.6	477.2	465.0
160°	531.5	532.4	530.6	526.1	519.9	513.6	504.7	495.8	484.3	473.6	462.9
162.5°	517.9	518.1	517.7	514.0	509.2	503.6	496.1	488.0	478.6	469.3	460.7
165°	498.5	498.5	498.5	496.7	493.1	488.7	483.4	477.2	470.0	462.9	457.5
167.5°	480.7	480.9	481.6	480.0	478.2	475.0	470.9	466.8	461.6	456.6	452.5
170°	470.0	470.9	470.9	470.0	468.2	466.5	463.8	461.1	456.6	453.1	450.4
172.5°	460.0	460.9	462.4	460.7	460.4	459.3	457.4	454.7	451.7	448.8	447.5
175°	447.7	448.6	450.4	449.5	449.5	449.5	447.7	447.7	445.1	444.2	444.2
177.5°	441.5	441.5	443.6	442.9	443.6	443.6	443.6	442.9	442.2	441.5	441.5
180°	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5



TEST NUMBER: P333189-940

CATALOG NUMBER: S125DIP-S610D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1
2.5°	821.1	819.2	817.1	813.2	808.6	806.2	802.5	800.0	795.0	791.0	786.7
5°	862.7	854.0	845.9	835.4	823.9	816.4	807.5	797.7	787.6	777.0	765.5
7.5°	905.9	890.4	873.4	855.2	837.4	821.0	805.3	790.0	775.6	758.2	743.5
10°	935.0	915.3	894.3	869.5	845.5	824.5	803.2	784.5	765.5	745.2	727.3
12.5°	963.9	937.7	908.1	880.9	852.0	826.7	801.6	777.8	753.9	731.4	710.5
15°	984.4	961.4	933.9	895.3	862.7	827.9	794.7	763.8	735.0	710.0	683.6
17.5°	997.8	968.2	938.7	901.7	859.1	820.0	782.4	747.2	714.7	682.9	657.5
20°	1000.3	969.8	939.0	902.8	859.1	814.3	776.8	734.4	699.5	666.6	635.4
22.5°	999.5	964.9	931.4	894.0	851.5	810.3	764.8	721.7	683.8	651.5	618.9
25°	991.8	954.9	912.9	875.3	833.3	789.6	743.5	698.8	660.2	623.3	591.1
27.5°	985.4	937.5	890.0	846.1	805.6	765.5	721.5	675.6	632.8	595.4	565.1
30°	977.6	925.1	871.6	825.8	784.2	745.2	703.6	658.9	614.1	577.6	545.0
32.5°	970.5	909.4	852.9	803.1	759.0	721.1	682.7	640.2	596.3	559.1	526.6
35°	957.0	886.2	821.4	765.2	718.1	679.2	647.0	607.3	567.0	531.1	500.0
37.5°	939.7	855.7	786.2	727.3	675.6	634.6	604.7	574.3	535.6	501.0	472.8
40°	926.1	834.0	760.5	700.2	646.7	604.0	576.2	547.4	515.2	483.0	453.3
42.5°	909.0	814.5	734.4	669.6	616.6	575.0	545.8	521.4	493.0	463.0	435.3
45°	877.7	779.1	692.4	622.6	569.1	528.1	497.9	479.7	458.3	429.9	406.5
47.5°	831.5	736.6	646.9	574.9	519.7	481.7	453.4	435.9	420.9	399.8	378.5
50°	790.6	704.9	614.1	542.7	487.4	449.2	423.1	407.2	394.3	378.0	360.1
52.5°	744.8	665.0	581.9	511.2	456.6	418.8	393.2	379.2	368.5	356.9	339.2
55°	672.1	604.3	527.1	460.0	409.6	372.6	350.3	338.0	329.2	320.5	309.6
57.5°	591.9	539.0	470.5	409.2	362.7	329.1	308.3	296.4	289.5	285.0	278.7
60°	535.6	490.2	431.2	375.3	329.9	300.1	279.8	270.6	264.9	261.2	256.5
62.5°	483.2	445.9	391.4	340.4	300.7	272.5	254.3	245.5	240.0	238.2	234.2
65°	406.2	377.4	332.3	290.0	256.1	232.0	216.8	208.3	204.9	202.9	203.2
67.5°	330.2	312.6	276.5	240.4	213.3	193.1	180.9	174.4	172.7	170.0	170.0
70°	283.8	270.6	240.1	208.7	184.6	169.1	158.2	151.4	149.7	148.4	148.0
72.5°	242.9	231.4	204.9	179.7	158.1	144.4	135.5	131.3	128.6	127.8	127.7
75°	182.6	176.1	155.2	135.2	120.3	110.8	104.7	100.9	98.9	98.5	98.9
77.5°	129.8	124.2	110.8	96.7	87.3	80.1	74.9	73.7	71.3	71.4	71.1
80°	97.6	93.8	85.3	74.2	66.4	60.3	57.6	55.2	54.6	53.5	54.6
82.5°	70.7	66.7	61.0	53.9	47.4	43.8	41.0	40.3	39.9	39.4	39.6
85°	34.9	35.2	31.8	26.4	23.7	21.7	20.0	20.0	19.6	19.4	19.6
87.5°	14.3	13.4	12.0	10.9	9.2	8.0	7.4	7.5	6.9	7.0	7.6
90°	11.6	9.8	8.9	7.1	5.4	3.6	1.8	0.9	1.8	3.6	5.4
92.5°	203.1	121.6	73.0	47.0	31.7	20.7	13.2	10.9	13.2	20.7	31.7
95°	397.9	202.1	106.8	66.8	47.2	37.4	30.2	29.3	30.2	37.4	47.2
97.5°	317.6	174.2	111.1	82.2	64.6	54.8	49.8	48.8	49.8	54.8	64.6
100°	288.4	172.7	121.1	94.3	77.4	67.7	64.1	62.3	64.1	67.7	77.4
102.5°	276.3	179.1	133.1	107.2	91.7	81.1	78.3	77.3	78.3	81.1	91.7
105°	271.5	192.3	153.1	128.2	114.0	105.0	100.6	100.6	100.6	105.0	114.0
107.5°	279.7	211.9	174.0	151.5	136.7	129.4	125.2	123.4	125.2	129.4	136.7
110°	287.5	226.1	189.6	166.5	153.1	145.1	141.5	139.7	141.5	145.1	153.1





TEST NUMBER: P333189-940

CATALOG NUMBER: S125DIP-S610D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	297.5	239.6	204.6	182.1	168.8	160.8	157.9	156.1	157.9	160.8	168.8
115°	312.5	260.8	227.9	205.6	192.3	184.2	181.6	179.9	181.6	184.2	192.3
117.5°	329.6	282.6	251.4	229.9	214.7	206.7	203.8	201.2	203.8	206.7	214.7
120°	340.9	298.2	267.1	244.8	229.7	221.7	218.1	215.4	218.1	221.7	229.7
122.5°	353.7	313.2	282.0	259.8	243.2	235.1	232.3	230.4	232.3	235.1	243.2
125°	371.2	333.0	303.5	280.4	263.5	255.5	251.0	249.2	251.0	255.5	263.5
127.5°	387.2	352.0	323.7	300.5	282.6	272.4	266.7	264.0	266.7	272.4	282.6
130°	397.9	364.1	336.4	313.3	294.6	283.1	276.0	273.3	276.0	283.1	294.6
132.5°	407.2	375.5	347.9	324.8	305.3	292.3	283.7	280.4	283.7	292.3	305.3
135°	420.2	390.7	363.2	339.1	320.5	306.2	295.5	291.9	295.5	306.2	320.5
137.5°	429.8	401.6	376.6	351.8	333.5	319.2	309.2	306.6	309.2	319.2	333.5
140°	436.2	409.5	383.7	359.6	342.7	328.5	317.8	315.1	317.8	328.5	342.7
142.5°	439.7	414.5	390.0	367.5	351.2	337.0	327.1	325.1	327.1	337.0	351.2
145°	445.1	422.8	399.7	379.2	363.2	350.7	341.8	340.0	341.8	350.7	363.2
147.5°	448.3	428.2	407.9	389.9	376.0	364.4	356.8	355.7	356.8	364.4	376.0
150°	450.4	431.8	412.1	397.0	384.6	373.0	366.8	365.0	366.8	373.0	384.6
152.5°	451.8	435.3	417.1	403.4	391.6	381.6	376.0	375.0	376.0	381.6	391.6
155°	453.1	438.8	423.7	411.3	402.3	393.4	388.1	388.1	388.1	393.4	402.3
157.5°	454.0	441.8	428.9	419.5	411.6	403.9	399.7	399.8	399.7	403.9	411.6
160°	454.0	443.3	431.8	423.7	416.6	410.4	406.8	407.7	406.8	410.4	416.6
162.5°	453.3	444.7	434.6	428.0	422.3	416.8	413.2	414.1	413.2	416.8	422.3
165°	452.2	445.1	438.0	432.7	429.1	424.6	422.0	423.7	422.0	424.6	429.1
167.5°	450.0	445.1	439.2	435.9	433.4	430.9	429.3	430.2	429.3	430.9	433.4
170°	448.6	445.1	440.6	438.0	436.2	434.4	433.5	434.4	433.5	434.4	436.2
172.5°	447.2	444.3	440.6	439.3	438.3	436.6	435.7	437.3	435.7	436.6	438.3
175°	445.1	443.3	440.6	440.6	440.6	439.7	438.8	440.6	438.8	439.7	440.6
177.5°	442.9	442.2	440.8	440.8	441.5	440.8	440.8	442.2	440.8	440.8	441.5
180°	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5



TEST NUMBER: P333189-940

CATALOG NUMBER: S125DIP-S610D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1
2.5°	784.3	781.2	778.8	773.4	770.4	766.3	763.1	766.6	762.9	764.5	762.1
5°	759.8	750.3	743.5	733.7	725.2	717.5	711.7	710.7	707.9	706.6	702.6
7.5°	730.4	718.5	706.9	694.0	683.1	672.2	665.0	659.2	655.4	650.3	646.8
10°	713.0	697.1	683.6	668.0	654.4	642.6	633.1	628.4	623.9	617.5	615.2
12.5°	691.6	675.2	658.6	641.9	629.0	615.7	607.6	600.5	597.4	590.1	589.4
15°	665.9	641.2	625.0	608.1	590.0	579.3	572.5	564.7	561.3	556.2	552.5
17.5°	635.3	613.2	592.9	575.4	560.0	550.9	542.4	537.1	531.3	528.0	521.8
20°	613.1	592.1	571.8	553.1	541.3	530.8	524.1	519.0	512.8	511.1	505.1
22.5°	594.4	571.2	551.7	536.1	523.2	511.3	504.0	500.5	496.3	491.1	489.9
25°	564.0	539.9	523.3	507.7	496.2	485.4	480.4	475.9	471.9	468.1	466.8
27.5°	537.7	516.2	496.5	482.4	472.4	462.5	458.1	452.7	449.7	446.7	443.1
30°	519.3	497.3	480.0	466.5	455.6	446.8	442.0	438.4	435.6	432.9	430.9
32.5°	500.3	479.9	463.2	450.0	439.1	432.5	428.2	425.6	422.6	419.4	416.8
35°	475.3	452.9	436.7	425.1	416.6	411.5	406.8	404.5	401.1	401.1	398.3
37.5°	447.0	427.7	413.3	402.8	395.2	390.7	385.6	384.0	381.7	380.3	379.4
40°	430.2	412.2	398.7	388.2	380.0	376.3	372.3	369.5	368.2	366.5	365.9
42.5°	412.9	395.7	382.7	373.0	366.0	362.7	359.0	357.1	354.4	352.1	351.8
45°	386.5	369.9	358.0	350.3	344.2	340.5	338.0	334.0	332.6	329.9	329.6
47.5°	361.5	345.5	333.9	327.5	322.2	319.1	315.4	311.4	309.8	308.4	308.4
50°	342.8	328.2	317.4	311.3	306.2	301.8	298.1	295.4	294.4	294.4	295.1
52.5°	323.9	311.5	302.2	294.8	290.0	285.3	281.9	280.2	278.7	280.3	281.5
55°	296.0	283.6	276.8	269.7	264.9	259.5	257.8	257.1	256.1	258.8	260.1
57.5°	266.6	257.9	249.9	242.9	238.6	235.5	233.2	232.8	234.7	235.9	240.4
60°	248.0	237.8	230.7	225.2	220.2	218.1	217.5	216.8	218.1	221.9	227.7
62.5°	227.4	219.1	211.4	207.4	203.7	200.3	200.1	200.5	203.2	207.5	213.3
65°	197.2	190.0	184.9	180.2	177.2	175.1	175.8	177.2	180.2	186.0	192.4
67.5°	166.5	161.6	157.0	153.2	150.3	150.3	151.0	153.0	156.6	163.2	169.1
70°	146.7	141.2	137.5	135.8	133.5	132.2	134.1	137.5	140.5	146.7	151.8
72.5°	126.9	122.3	119.4	118.2	117.2	116.1	116.8	120.5	124.6	130.7	136.6
75°	97.6	95.9	93.8	92.5	91.5	92.1	92.8	96.2	99.6	106.0	112.8
77.5°	71.2	69.5	68.2	67.9	67.3	67.7	69.6	72.1	75.4	80.1	85.2
80°	53.9	53.1	52.5	52.2	52.2	52.5	55.2	56.9	59.9	64.4	68.4
82.5°	39.2	38.8	38.7	38.6	38.9	39.0	40.6	42.8	45.3	48.7	52.2
85°	20.7	20.0	21.0	21.3	20.7	21.7	22.4	23.7	24.7	26.4	28.1
87.5°	8.2	9.1	9.0	9.6	9.8	10.7	10.6	11.9	12.6	13.3	13.4
90°	7.1	8.9	9.8	11.6	12.5	14.3	15.2	16.1	16.9	17.8	19.6
92.5°	47.0	73.0	121.6	203.1	291.6	287.0	232.3	157.7	114.5	86.1	73.0
95°	66.8	106.8	202.1	397.9	643.6	788.7	771.8	640.1	504.7	395.2	320.5
97.5°	82.2	111.1	174.2	317.6	574.7	842.3	976.5	953.2	858.3	751.6	647.6
100°	94.3	121.1	172.7	288.4	512.7	803.8	1026.4	1094.9	1051.3	959.6	867.0
102.5°	107.2	133.1	179.1	276.3	465.7	736.2	996.5	1142.6	1169.5	1125.5	1062.8
105°	128.2	153.1	192.3	271.5	420.2	645.3	900.9	1114.5	1236.4	1275.6	1265.8
107.5°	151.5	174.0	211.9	279.7	400.9	582.9	803.3	1014.1	1176.8	1277.4	1323.8
110°	166.5	189.6	226.1	287.5	395.2	553.7	747.7	940.0	1109.1	1234.7	1310.4



TEST NUMBER: P333189-940

CATALOG NUMBER: S125DIP-S610D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	182.1	204.6	239.6	297.5	395.2	536.6	706.4	881.6	1042.2	1169.1	1258.4
115°	205.6	227.9	260.8	312.5	397.9	518.1	661.4	808.2	946.3	1068.2	1165.2
117.5°	229.9	251.4	282.6	329.6	403.8	509.0	634.5	760.9	879.9	984.9	1073.9
120°	244.8	267.1	298.2	340.9	409.5	504.7	619.6	735.3	842.1	940.0	1018.3
122.5°	259.8	282.0	313.2	353.7	414.5	501.1	606.7	716.0	815.0	902.2	975.6
125°	280.4	303.5	333.0	371.2	422.8	496.7	589.3	688.1	778.9	856.3	920.4
127.5°	300.5	323.7	352.0	387.2	432.3	494.5	573.3	659.6	744.4	816.6	876.6
130°	313.3	336.4	364.1	397.9	438.0	493.1	562.6	641.9	720.1	789.6	847.5
132.5°	324.8	347.9	375.5	407.2	444.3	493.1	554.0	624.0	697.3	760.4	816.1
135°	339.1	363.2	390.7	420.2	453.1	493.1	543.9	600.8	662.3	719.3	770.0
137.5°	351.8	376.6	401.6	429.8	461.1	494.2	534.8	581.3	631.0	678.3	721.4
140°	359.6	383.7	409.5	436.2	464.7	494.9	530.6	570.6	612.4	653.4	690.8
142.5°	367.5	390.0	414.5	439.7	466.8	495.6	527.0	561.3	596.7	632.0	664.4
145°	379.2	399.7	422.8	445.1	469.1	494.9	521.7	549.2	576.8	604.4	628.5
147.5°	389.9	407.9	428.2	448.3	470.0	492.6	516.1	537.9	560.3	581.5	599.6
150°	397.0	412.1	431.8	450.4	470.0	490.4	511.8	531.5	551.0	567.9	584.0
152.5°	403.4	417.1	435.3	451.8	469.3	487.7	506.8	524.3	541.7	557.2	569.7
155°	411.3	423.7	438.8	453.1	467.3	482.5	498.5	513.6	527.9	540.4	550.1
157.5°	419.5	428.9	441.8	454.0	465.0	477.2	490.6	502.9	514.7	524.3	532.0
160°	423.7	431.8	443.3	454.0	462.9	473.6	484.3	495.8	504.7	513.6	519.9
162.5°	428.0	434.6	444.7	453.3	460.7	469.3	478.6	488.0	496.1	503.6	509.2
165°	432.7	438.0	445.1	452.2	457.5	462.9	470.0	477.2	483.4	488.7	493.1
167.5°	435.9	439.2	445.1	450.0	452.5	456.6	461.6	466.8	470.9	475.0	478.2
170°	438.0	440.6	445.1	448.6	450.4	453.1	456.6	461.1	463.8	466.5	468.2
172.5°	439.3	440.6	444.3	447.2	447.5	448.8	451.7	454.7	457.4	459.3	460.4
175°	440.6	440.6	443.3	445.1	444.2	444.2	445.1	447.7	447.7	449.5	449.5
177.5°	440.8	440.8	442.2	442.9	441.5	441.5	442.2	442.9	443.6	443.6	443.6
180°	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5



TEST NUMBER: P333189-940

CATALOG NUMBER: S125DIP-S610D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1
2.5°	760.4	762.3	760.7	762.9	760.7	762.3	760.4	762.1	764.5	762.9	766.6
5°	700.9	697.8	699.8	698.5	699.8	697.8	700.9	702.6	706.6	707.9	710.7
7.5°	645.9	642.9	639.6	638.0	639.6	642.9	645.9	646.8	650.3	655.4	659.2
10°	611.4	607.7	607.3	605.0	607.3	607.7	611.4	615.2	617.5	623.9	628.4
12.5°	586.2	582.7	578.9	577.9	578.9	582.7	586.2	589.4	590.1	597.4	600.5
15°	550.5	547.8	545.4	547.4	545.4	547.8	550.5	552.5	556.2	561.3	564.7
17.5°	520.7	518.4	518.1	515.6	518.1	518.4	520.7	521.8	528.0	531.3	537.1
20°	502.0	500.3	501.0	496.6	501.0	500.3	502.0	505.1	511.1	512.8	519.0
22.5°	487.1	483.8	483.4	482.5	483.4	483.8	487.1	489.9	491.1	496.3	500.5
25°	463.8	462.1	460.4	462.1	460.4	462.1	463.8	466.8	468.1	471.9	475.9
27.5°	443.4	441.3	440.9	441.0	440.9	441.3	443.4	443.1	446.7	449.7	452.7
30°	430.9	427.5	427.8	427.5	427.8	427.5	430.9	430.9	432.9	435.6	438.4
32.5°	417.3	415.0	414.6	413.9	414.6	415.0	417.3	416.8	419.4	422.6	425.6
35°	397.3	397.3	395.7	395.7	395.7	397.3	397.3	398.3	401.1	401.1	404.5
37.5°	378.5	378.3	377.2	377.4	377.2	378.3	378.5	379.4	380.3	381.7	384.0
40°	364.4	364.2	363.1	361.1	363.1	364.2	364.4	365.9	366.5	368.2	369.5
42.5°	351.0	349.8	349.3	348.7	349.3	349.8	351.0	351.8	352.1	354.4	357.1
45°	329.6	329.6	329.0	328.6	329.0	329.6	329.6	329.6	329.9	332.6	334.0
47.5°	308.9	309.5	310.8	310.6	310.8	309.5	308.9	308.4	308.4	309.8	311.4
50°	296.4	296.8	297.7	298.1	297.7	296.8	296.4	295.1	294.4	294.4	295.4
52.5°	282.6	284.5	285.8	285.6	285.8	284.5	282.6	281.5	280.3	278.7	280.2
55°	263.2	265.6	268.0	268.3	268.0	265.6	263.2	260.1	258.8	256.1	257.1
57.5°	244.1	247.4	249.9	250.7	249.9	247.4	244.1	240.4	235.9	234.7	232.8
60°	231.0	235.4	238.4	239.9	238.4	235.4	231.0	227.7	221.9	218.1	216.8
62.5°	218.6	223.5	226.6	226.9	226.6	223.5	218.6	213.3	207.5	203.2	200.5
65°	198.1	203.2	206.0	207.9	206.0	203.2	198.1	192.4	186.0	180.2	177.2
67.5°	176.2	181.3	184.3	185.9	184.3	181.3	176.2	169.1	163.2	156.6	153.0
70°	160.2	165.3	169.3	170.8	169.3	165.3	160.2	151.8	146.7	140.5	137.5
72.5°	144.5	149.0	152.3	153.9	152.3	149.0	144.5	136.6	130.7	124.6	120.5
75°	117.2	123.3	126.4	128.0	126.4	123.3	117.2	112.8	106.0	99.6	96.2
77.5°	90.4	95.9	97.7	98.6	97.7	95.9	90.4	85.2	80.1	75.4	72.1
80°	72.5	75.9	78.3	78.6	78.3	75.9	72.5	68.4	64.4	59.9	56.9
82.5°	55.7	58.5	59.3	60.2	59.3	58.5	55.7	52.2	48.7	45.3	42.8
85°	30.5	31.8	32.2	31.8	32.2	31.8	30.5	28.1	26.4	24.7	23.7
87.5°	13.9	13.6	13.8	14.4	13.8	13.6	13.9	13.4	13.3	12.6	11.9
90°	19.6	19.6	20.5	20.5	20.5	19.6	19.6	19.6	17.8	16.9	16.1
92.5°	61.6	59.5	58.2	56.8	58.2	59.5	61.6	73.0	86.1	114.5	157.7
95°	257.3	230.6	223.5	209.2	223.5	230.6	257.3	320.5	395.2	504.7	640.1
97.5°	592.7	542.8	517.0	505.6	517.0	542.8	592.7	647.6	751.6	858.3	953.2
100°	805.6	741.5	708.6	694.4	708.6	741.5	805.6	867.0	959.6	1051.3	1094.9
102.5°	997.2	951.6	915.8	905.1	915.8	951.6	997.2	1062.8	1125.5	1169.5	1142.6
105°	1237.3	1208.0	1190.2	1179.5	1190.2	1208.0	1237.3	1265.8	1275.6	1236.4	1114.5
107.5°	1338.3	1338.1	1332.2	1325.1	1332.2	1338.1	1338.3	1323.8	1277.4	1176.8	1014.1
110°	1350.4	1367.3	1373.5	1373.5	1373.5	1367.3	1350.4	1310.4	1234.7	1109.1	940.0



TEST NUMBER: P333189-940

CATALOG NUMBER: S125DIP-S610D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1316.9	1345.9	1361.5	1367.8	1361.5	1345.9	1316.9	1258.4	1169.1	1042.2	881.6
115°	1234.7	1277.4	1302.3	1313.9	1302.3	1277.4	1234.7	1165.2	1068.2	946.3	808.2
117.5°	1143.4	1187.5	1212.2	1219.3	1212.2	1187.5	1143.4	1073.9	984.9	879.9	760.9
120°	1084.2	1126.9	1151.0	1158.2	1151.0	1126.9	1084.2	1018.3	940.0	842.1	735.3
122.5°	1034.4	1073.5	1097.6	1104.0	1097.6	1073.5	1034.4	975.6	902.2	815.0	716.0
125°	970.3	1006.7	1026.4	1035.3	1026.4	1006.7	970.3	920.4	856.3	778.9	688.1
127.5°	921.9	954.0	972.6	976.5	972.6	954.0	921.9	876.6	816.6	744.4	659.6
130°	892.0	921.3	939.1	944.5	939.1	921.3	892.0	847.5	789.6	720.1	641.9
132.5°	860.6	890.0	906.3	912.4	906.3	890.0	860.6	816.1	760.4	697.3	624.0
135°	809.1	838.6	854.5	859.9	854.5	838.6	809.1	770.0	719.3	662.3	600.8
137.5°	756.4	783.2	798.0	803.8	798.0	783.2	756.4	721.4	678.3	631.0	581.3
140°	723.7	746.9	760.2	764.6	760.2	746.9	723.7	690.8	653.4	612.4	570.6
142.5°	692.4	711.9	724.6	728.3	724.6	711.9	692.4	664.4	632.0	596.7	561.3
145°	649.8	664.9	674.8	678.3	674.8	664.9	649.8	628.5	604.4	576.8	549.2
147.5°	616.5	628.7	634.4	636.0	634.4	628.7	616.5	599.6	581.5	560.3	537.9
150°	597.3	608.0	611.5	612.4	611.5	608.0	597.3	584.0	567.9	551.0	531.5
152.5°	580.9	589.5	593.0	593.9	593.0	589.5	580.9	569.7	557.2	541.7	524.3
155°	559.0	565.3	567.9	568.8	567.9	565.3	559.0	550.1	540.4	527.9	513.6
157.5°	539.0	544.0	546.5	546.4	546.5	544.0	539.0	532.0	524.3	514.7	502.9
160°	526.1	530.6	532.4	531.5	532.4	530.6	526.1	519.9	513.6	504.7	495.8
162.5°	514.0	517.7	518.1	517.9	518.1	517.7	514.0	509.2	503.6	496.1	488.0
165°	496.7	498.5	498.5	498.5	498.5	498.5	496.7	493.1	488.7	483.4	477.2
167.5°	480.0	481.6	480.9	480.7	480.9	481.6	480.0	478.2	475.0	470.9	466.8
170°	470.0	470.9	470.9	470.0	470.9	470.9	470.0	468.2	466.5	463.8	461.1
172.5°	460.7	462.4	460.9	460.0	460.9	462.4	460.7	460.4	459.3	457.4	454.7
175°	449.5	450.4	448.6	447.7	448.6	450.4	449.5	449.5	449.5	447.7	447.7
177.5°	442.9	443.6	441.5	441.5	441.5	443.6	442.9	443.6	443.6	443.6	442.9
180°	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5



TEST NUMBER: P333189-940

CATALOG NUMBER: S125DIP-S610D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1
2.5°	763.1	766.3	770.4	773.4	778.8	781.2	784.3	786.7	791.0	795.0	800.0
5°	711.7	717.5	725.2	733.7	743.5	750.3	759.8	765.5	777.0	787.6	797.7
7.5°	665.0	672.2	683.1	694.0	706.9	718.5	730.4	743.5	758.2	775.6	790.0
10°	633.1	642.6	654.4	668.0	683.6	697.1	713.0	727.3	745.2	765.5	784.5
12.5°	607.6	615.7	629.0	641.9	658.6	675.2	691.6	710.5	731.4	753.9	777.8
15°	572.5	579.3	590.0	608.1	625.0	641.2	665.9	683.6	710.0	735.0	763.8
17.5°	542.4	550.9	560.0	575.4	592.9	613.2	635.3	657.5	682.9	714.7	747.2
20°	524.1	530.8	541.3	553.1	571.8	592.1	613.1	635.4	666.6	699.5	734.4
22.5°	504.0	511.3	523.2	536.1	551.7	571.2	594.4	618.9	651.5	683.8	721.7
25°	480.4	485.4	496.2	507.7	523.3	539.9	564.0	591.1	623.3	660.2	698.8
27.5°	458.1	462.5	472.4	482.4	496.5	516.2	537.7	565.1	595.4	632.8	675.6
30°	442.0	446.8	455.6	466.5	480.0	497.3	519.3	545.0	577.6	614.1	658.9
32.5°	428.2	432.5	439.1	450.0	463.2	479.9	500.3	526.6	559.1	596.3	640.2
35°	406.8	411.5	416.6	425.1	436.7	452.9	475.3	500.0	531.1	567.0	607.3
37.5°	385.6	390.7	395.2	402.8	413.3	427.7	447.0	472.8	501.0	535.6	574.3
40°	372.3	376.3	380.0	388.2	398.7	412.2	430.2	453.3	483.0	515.2	547.4
42.5°	359.0	362.7	366.0	373.0	382.7	395.7	412.9	435.3	463.0	493.0	521.4
45°	338.0	340.5	344.2	350.3	358.0	369.9	386.5	406.5	429.9	458.3	479.7
47.5°	315.4	319.1	322.2	327.5	333.9	345.5	361.5	378.5	399.8	420.9	435.9
50°	298.1	301.8	306.2	311.3	317.4	328.2	342.8	360.1	378.0	394.3	407.2
52.5°	281.9	285.3	290.0	294.8	302.2	311.5	323.9	339.2	356.9	368.5	379.2
55°	257.8	259.5	264.9	269.7	276.8	283.6	296.0	309.6	320.5	329.2	338.0
57.5°	233.2	235.5	238.6	242.9	249.9	257.9	266.6	278.7	285.0	289.5	296.4
60°	217.5	218.1	220.2	225.2	230.7	237.8	248.0	256.5	261.2	264.9	270.6
62.5°	200.1	200.3	203.7	207.4	211.4	219.1	227.4	234.2	238.2	240.0	245.5
65°	175.8	175.1	177.2	180.2	184.9	190.0	197.2	203.2	202.9	204.9	208.3
67.5°	151.0	150.3	150.3	153.2	157.0	161.6	166.5	170.0	170.0	172.7	174.4
70°	134.1	132.2	133.5	135.8	137.5	141.2	146.7	148.0	148.4	149.7	151.4
72.5°	116.8	116.1	117.2	118.2	119.4	122.3	126.9	127.7	127.8	128.6	131.3
75°	92.8	92.1	91.5	92.5	93.8	95.9	97.6	98.9	98.5	98.9	100.9
77.5°	69.6	67.7	67.3	67.9	68.2	69.5	71.2	71.1	71.4	71.3	73.7
80°	55.2	52.5	52.2	52.2	52.5	53.1	53.9	54.6	53.5	54.6	55.2
82.5°	40.6	39.0	38.9	38.6	38.7	38.8	39.2	39.6	39.4	39.9	40.3
85°	22.4	21.7	20.7	21.3	21.0	20.0	20.7	19.6	19.4	19.6	20.0
87.5°	10.6	10.7	9.8	9.6	9.0	9.1	8.2	7.6	7.0	6.9	7.5
90°	15.2	14.3	12.5	11.6	9.8	8.9	7.1	5.4	3.6	1.8	0.9
92.5°	232.3	287.0	291.6	203.1	121.6	73.0	47.0	31.7	20.7	13.2	10.9
95°	771.8	788.7	643.6	397.9	202.1	106.8	66.8	47.2	37.4	30.2	29.3
97.5°	976.5	842.3	574.7	317.6	174.2	111.1	82.2	64.6	54.8	49.8	48.8
100°	1026.4	803.8	512.7	288.4	172.7	121.1	94.3	77.4	67.7	64.1	62.3
102.5°	996.5	736.2	465.7	276.3	179.1	133.1	107.2	91.7	81.1	78.3	77.3
105°	900.9	645.3	420.2	271.5	192.3	153.1	128.2	114.0	105.0	100.6	100.6
107.5°	803.3	582.9	400.9	279.7	211.9	174.0	151.5	136.7	129.4	125.2	123.4
110°	747.7	553.7	395.2	287.5	226.1	189.6	166.5	153.1	145.1	141.5	139.7



TEST NUMBER: P333189-940

CATALOG NUMBER: S125DIP-S610D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	706.4	536.6	395.2	297.5	239.6	204.6	182.1	168.8	160.8	157.9	156.1
115°	661.4	518.1	397.9	312.5	260.8	227.9	205.6	192.3	184.2	181.6	179.9
117.5°	634.5	509.0	403.8	329.6	282.6	251.4	229.9	214.7	206.7	203.8	201.2
120°	619.6	504.7	409.5	340.9	298.2	267.1	244.8	229.7	221.7	218.1	215.4
122.5°	606.7	501.1	414.5	353.7	313.2	282.0	259.8	243.2	235.1	232.3	230.4
125°	589.3	496.7	422.8	371.2	333.0	303.5	280.4	263.5	255.5	251.0	249.2
127.5°	573.3	494.5	432.3	387.2	352.0	323.7	300.5	282.6	272.4	266.7	264.0
130°	562.6	493.1	438.0	397.9	364.1	336.4	313.3	294.6	283.1	276.0	273.3
132.5°	554.0	493.1	444.3	407.2	375.5	347.9	324.8	305.3	292.3	283.7	280.4
135°	543.9	493.1	453.1	420.2	390.7	363.2	339.1	320.5	306.2	295.5	291.9
137.5°	534.8	494.2	461.1	429.8	401.6	376.6	351.8	333.5	319.2	309.2	306.6
140°	530.6	494.9	464.7	436.2	409.5	383.7	359.6	342.7	328.5	317.8	315.1
142.5°	527.0	495.6	466.8	439.7	414.5	390.0	367.5	351.2	337.0	327.1	325.1
145°	521.7	494.9	469.1	445.1	422.8	399.7	379.2	363.2	350.7	341.8	340.0
147.5°	516.1	492.6	470.0	448.3	428.2	407.9	389.9	376.0	364.4	356.8	355.7
150°	511.8	490.4	470.0	450.4	431.8	412.1	397.0	384.6	373.0	366.8	365.0
152.5°	506.8	487.7	469.3	451.8	435.3	417.1	403.4	391.6	381.6	376.0	375.0
155°	498.5	482.5	467.3	453.1	438.8	423.7	411.3	402.3	393.4	388.1	388.1
157.5°	490.6	477.2	465.0	454.0	441.8	428.9	419.5	411.6	403.9	399.7	399.8
160°	484.3	473.6	462.9	454.0	443.3	431.8	423.7	416.6	410.4	406.8	407.7
162.5°	478.6	469.3	460.7	453.3	444.7	434.6	428.0	422.3	416.8	413.2	414.1
165°	470.0	462.9	457.5	452.2	445.1	438.0	432.7	429.1	424.6	422.0	423.7
167.5°	461.6	456.6	452.5	450.0	445.1	439.2	435.9	433.4	430.9	429.3	430.2
170°	456.6	453.1	450.4	448.6	445.1	440.6	438.0	436.2	434.4	433.5	434.4
172.5°	451.7	448.8	447.5	447.2	444.3	440.6	439.3	438.3	436.6	435.7	437.3
175°	445.1	444.2	444.2	445.1	443.3	440.6	440.6	440.6	439.7	438.8	440.6
177.5°	442.2	441.5	441.5	442.9	442.2	440.8	440.8	441.5	440.8	440.8	442.2
180°	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5



TEST NUMBER: P333189-940

CATALOG NUMBER: S125DIP-S610D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1
2.5°	802.5	806.2	808.6	813.2	817.1	819.2	821.1	822.7	824.7	826.3	830.9
5°	807.5	816.4	823.9	835.4	845.9	854.0	862.7	870.6	877.0	886.2	893.2
7.5°	805.3	821.0	837.4	855.2	873.4	890.4	905.9	920.5	933.7	949.7	963.7
10°	803.2	824.5	845.5	869.5	894.3	915.3	935.0	954.9	969.5	989.8	1007.1
12.5°	801.6	826.7	852.0	880.9	908.1	937.7	963.9	978.5	1000.7	1016.9	1037.4
15°	794.7	827.9	862.7	895.3	933.9	961.4	984.4	1012.8	1033.5	1054.2	1076.5
17.5°	782.4	820.0	859.1	901.7	938.7	968.2	997.8	1025.3	1050.0	1077.6	1105.5
20°	776.8	814.3	859.1	902.8	939.0	969.8	1000.3	1030.5	1057.6	1093.1	1125.2
22.5°	764.8	810.3	851.5	894.0	931.4	964.9	999.5	1033.7	1069.7	1109.9	1150.2
25°	743.5	789.6	833.3	875.3	912.9	954.9	991.8	1037.6	1083.6	1136.8	1187.0
27.5°	721.5	765.5	805.6	846.1	890.0	937.5	985.4	1037.3	1097.7	1164.8	1235.6
30°	703.6	745.2	784.2	825.8	871.6	925.1	977.6	1039.3	1109.0	1184.5	1268.5
32.5°	682.7	721.1	759.0	803.1	852.9	909.4	970.5	1038.1	1122.0	1207.9	1294.3
35°	647.0	679.2	718.1	765.2	821.4	886.2	957.0	1036.9	1133.1	1231.6	1304.5
37.5°	604.7	634.6	675.6	727.3	786.2	855.7	939.7	1034.5	1136.7	1215.2	1238.8
40°	576.2	604.0	646.7	700.2	760.5	834.0	926.1	1026.4	1125.2	1175.5	1156.1
42.5°	545.8	575.0	616.6	669.6	734.4	814.5	909.0	1009.3	1092.3	1111.2	1044.5
45°	497.9	528.1	569.1	622.6	692.4	779.1	877.7	968.8	1016.6	982.3	879.0
47.5°	453.4	481.7	519.7	574.9	646.9	736.6	831.5	904.2	908.0	826.3	716.0
50°	423.1	449.2	487.4	542.7	614.1	704.9	790.6	847.8	822.2	729.7	623.7
52.5°	393.2	418.8	456.6	511.2	581.9	665.0	744.8	785.0	736.5	641.6	551.0
55°	350.3	372.6	409.6	460.0	527.1	604.3	672.1	685.9	622.9	529.4	455.9
57.5°	308.3	329.1	362.7	409.2	470.5	539.0	591.9	589.0	522.4	442.1	383.8
60°	279.8	300.1	329.9	375.3	431.2	490.2	535.6	524.7	458.7	389.6	340.5
62.5°	254.3	272.5	300.7	340.4	391.4	445.9	483.2	467.3	402.5	342.1	303.3
65°	216.8	232.0	256.1	290.0	332.3	377.4	406.2	385.5	330.3	283.2	252.0
67.5°	180.9	193.1	213.3	240.4	276.5	312.6	330.2	309.4	265.2	230.9	207.8
70°	158.2	169.1	184.6	208.7	240.1	270.6	283.8	265.2	227.3	197.8	181.2
72.5°	135.5	144.4	158.1	179.7	204.9	231.4	242.9	225.2	193.9	169.1	153.6
75°	104.7	110.8	120.3	135.2	155.2	176.1	182.6	167.0	147.0	128.4	118.2
77.5°	74.9	80.1	87.3	96.7	110.8	124.2	129.8	120.8	105.3	93.5	85.2
80°	57.6	60.3	66.4	74.2	85.3	93.8	97.6	91.8	81.0	72.1	65.7
82.5°	41.0	43.8	47.4	53.9	61.0	66.7	70.7	66.9	59.0	52.1	48.3
85°	20.0	21.7	23.7	26.4	31.8	35.2	34.9	32.5	29.4	26.8	24.7
87.5°	7.4	8.0	9.2	10.9	12.0	13.4	14.3	13.9	13.1	12.5	11.9
90°	1.8	3.6	5.4	7.1	8.9	9.8	11.6	12.5	14.3	15.2	16.1
92.5°	13.2	20.7	31.7	47.0	73.0	121.6	203.1	291.6	287.0	232.3	157.7
95°	30.2	37.4	47.2	66.8	106.8	202.1	397.9	643.6	788.7	771.8	640.1
97.5°	49.8	54.8	64.6	82.2	111.1	174.2	317.6	574.7	842.3	976.5	953.2
100°	64.1	67.7	77.4	94.3	121.1	172.7	288.4	512.7	803.8	1026.4	1094.9
102.5°	78.3	81.1	91.7	107.2	133.1	179.1	276.3	465.7	736.2	996.5	1142.6
105°	100.6	105.0	114.0	128.2	153.1	192.3	271.5	420.2	645.3	900.9	1114.5
107.5°	125.2	129.4	136.7	151.5	174.0	211.9	279.7	400.9	582.9	803.3	1014.1
110°	141.5	145.1	153.1	166.5	189.6	226.1	287.5	395.2	553.7	747.7	940.0





TEST NUMBER: P333189-940

CATALOG NUMBER: S125DIP-S610D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	157.9	160.8	168.8	182.1	204.6	239.6	297.5	395.2	536.6	706.4	881.6
115°	181.6	184.2	192.3	205.6	227.9	260.8	312.5	397.9	518.1	661.4	808.2
117.5°	203.8	206.7	214.7	229.9	251.4	282.6	329.6	403.8	509.0	634.5	760.9
120°	218.1	221.7	229.7	244.8	267.1	298.2	340.9	409.5	504.7	619.6	735.3
122.5°	232.3	235.1	243.2	259.8	282.0	313.2	353.7	414.5	501.1	606.7	716.0
125°	251.0	255.5	263.5	280.4	303.5	333.0	371.2	422.8	496.7	589.3	688.1
127.5°	266.7	272.4	282.6	300.5	323.7	352.0	387.2	432.3	494.5	573.3	659.6
130°	276.0	283.1	294.6	313.3	336.4	364.1	397.9	438.0	493.1	562.6	641.9
132.5°	283.7	292.3	305.3	324.8	347.9	375.5	407.2	444.3	493.1	554.0	624.0
135°	295.5	306.2	320.5	339.1	363.2	390.7	420.2	453.1	493.1	543.9	600.8
137.5°	309.2	319.2	333.5	351.8	376.6	401.6	429.8	461.1	494.2	534.8	581.3
140°	317.8	328.5	342.7	359.6	383.7	409.5	436.2	464.7	494.9	530.6	570.6
142.5°	327.1	337.0	351.2	367.5	390.0	414.5	439.7	466.8	495.6	527.0	561.3
145°	341.8	350.7	363.2	379.2	399.7	422.8	445.1	469.1	494.9	521.7	549.2
147.5°	356.8	364.4	376.0	389.9	407.9	428.2	448.3	470.0	492.6	516.1	537.9
150°	366.8	373.0	384.6	397.0	412.1	431.8	450.4	470.0	490.4	511.8	531.5
152.5°	376.0	381.6	391.6	403.4	417.1	435.3	451.8	469.3	487.7	506.8	524.3
155°	388.1	393.4	402.3	411.3	423.7	438.8	453.1	467.3	482.5	498.5	513.6
157.5°	399.7	403.9	411.6	419.5	428.9	441.8	454.0	465.0	477.2	490.6	502.9
160°	406.8	410.4	416.6	423.7	431.8	443.3	454.0	462.9	473.6	484.3	495.8
162.5°	413.2	416.8	422.3	428.0	434.6	444.7	453.3	460.7	469.3	478.6	488.0
165°	422.0	424.6	429.1	432.7	438.0	445.1	452.2	457.5	462.9	470.0	477.2
167.5°	429.3	430.9	433.4	435.9	439.2	445.1	450.0	452.5	456.6	461.6	466.8
170°	433.5	434.4	436.2	438.0	440.6	445.1	448.6	450.4	453.1	456.6	461.1
172.5°	435.7	436.6	438.3	439.3	440.6	444.3	447.2	447.5	448.8	451.7	454.7
175°	438.8	439.7	440.6	440.6	440.6	443.3	445.1	444.2	444.2	445.1	447.7
177.5°	440.8	440.8	441.5	440.8	440.8	442.2	442.9	441.5	441.5	442.2	442.9
180°	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5



TEST NUMBER: P333189-940

CATALOG NUMBER: S125DIP-S610D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	798.1	798.1	798.1	798.1	798.1	798.1	798.1
2.5°	834.6	836.8	841.4	839.8	842.0	843.0	844.2
5°	902.1	912.9	917.7	916.9	924.1	922.4	920.7
7.5°	978.2	989.6	996.0	1003.9	1008.5	1008.8	1012.8
10°	1021.3	1036.2	1042.3	1050.8	1056.2	1059.3	1058.9
12.5°	1054.4	1066.0	1079.7	1083.9	1091.2	1095.0	1093.6
15°	1094.1	1112.8	1126.9	1134.1	1143.3	1145.9	1149.7
17.5°	1129.6	1154.6	1171.3	1193.3	1201.7	1206.8	1203.7
20°	1156.5	1189.3	1205.9	1232.3	1246.9	1254.7	1252.0
22.5°	1188.2	1223.7	1254.5	1277.3	1299.5	1310.0	1312.2
25°	1242.5	1291.3	1336.3	1366.5	1393.9	1400.3	1414.6
27.5°	1303.2	1360.8	1408.9	1440.6	1459.7	1466.9	1471.3
30°	1341.4	1398.6	1434.9	1455.2	1461.3	1460.6	1460.0
32.5°	1360.1	1396.0	1402.9	1397.2	1383.3	1371.5	1359.1
35°	1333.6	1306.9	1266.9	1215.4	1177.5	1139.2	1135.4
37.5°	1199.4	1113.8	1047.3	973.0	930.1	903.7	885.3
40°	1073.1	975.9	895.3	832.6	788.9	771.7	754.7
42.5°	936.0	843.1	771.7	719.3	686.5	667.4	653.9
45°	760.5	678.5	622.6	584.7	558.6	543.7	535.2
47.5°	623.1	562.5	515.1	487.7	469.7	458.1	458.1
50°	549.5	491.5	460.0	438.4	422.8	413.6	415.3
52.5°	484.1	440.9	413.9	395.7	384.2	378.6	378.4
55°	404.8	373.6	356.1	342.8	335.0	328.6	329.9
57.5°	346.3	319.9	308.2	297.2	291.8	289.2	285.5
60°	310.0	289.6	279.5	270.6	265.2	263.2	259.5
62.5°	277.7	261.7	251.8	244.6	239.8	239.1	236.1
65°	233.4	221.2	212.4	209.0	203.9	202.6	202.6
67.5°	192.4	183.7	176.8	173.7	171.5	171.8	170.1
70°	166.7	159.5	155.2	151.8	150.1	150.4	149.0
72.5°	145.8	137.9	134.0	132.0	129.7	130.6	130.1
75°	110.4	106.4	104.3	102.3	100.9	100.2	99.6
77.5°	81.1	77.5	76.0	74.8	75.0	73.4	74.6
80°	62.7	59.7	58.6	56.9	56.5	56.5	56.3
82.5°	45.8	44.1	43.4	42.0	41.4	41.9	41.0
85°	23.7	22.4	22.0	22.0	21.3	20.7	22.4
87.5°	12.0	11.1	11.5	11.2	11.2	11.1	10.6
90°	16.9	17.8	19.6	19.6	19.6	20.5	20.5
92.5°	114.5	86.1	73.0	61.6	59.5	58.2	56.8
95°	504.7	395.2	320.5	257.3	230.6	223.5	209.2
97.5°	858.3	751.6	647.6	592.7	542.8	517.0	505.6
100°	1051.3	959.6	867.0	805.6	741.5	708.6	694.4
102.5°	1169.5	1125.5	1062.8	997.2	951.6	915.8	905.1
105°	1236.4	1275.6	1265.8	1237.3	1208.0	1190.2	1179.5
107.5°	1176.8	1277.4	1323.8	1338.3	1338.1	1332.2	1325.1
110°	1109.1	1234.7	1310.4	1350.4	1367.3	1373.5	1373.5



TEST NUMBER: P333189-940

CATALOG NUMBER: S125DIP-S610D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	1042.2	1169.1	1258.4	1316.9	1345.9	1361.5	1367.8
115°	946.3	1068.2	1165.2	1234.7	1277.4	1302.3	1313.9
117.5°	879.9	984.9	1073.9	1143.4	1187.5	1212.2	1219.3
120°	842.1	940.0	1018.3	1084.2	1126.9	1151.0	1158.2
122.5°	815.0	902.2	975.6	1034.4	1073.5	1097.6	1104.0
125°	778.9	856.3	920.4	970.3	1006.7	1026.4	1035.3
127.5°	744.4	816.6	876.6	921.9	954.0	972.6	976.5
130°	720.1	789.6	847.5	892.0	921.3	939.1	944.5
132.5°	697.3	760.4	816.1	860.6	890.0	906.3	912.4
135°	662.3	719.3	770.0	809.1	838.6	854.5	859.9
137.5°	631.0	678.3	721.4	756.4	783.2	798.0	803.8
140°	612.4	653.4	690.8	723.7	746.9	760.2	764.6
142.5°	596.7	632.0	664.4	692.4	711.9	724.6	728.3
145°	576.8	604.4	628.5	649.8	664.9	674.8	678.3
147.5°	560.3	581.5	599.6	616.5	628.7	634.4	636.0
150°	551.0	567.9	584.0	597.3	608.0	611.5	612.4
152.5°	541.7	557.2	569.7	580.9	589.5	593.0	593.9
155°	527.9	540.4	550.1	559.0	565.3	567.9	568.8
157.5°	514.7	524.3	532.0	539.0	544.0	546.5	546.4
160°	504.7	513.6	519.9	526.1	530.6	532.4	531.5
162.5°	496.1	503.6	509.2	514.0	517.7	518.1	517.9
165°	483.4	488.7	493.1	496.7	498.5	498.5	498.5
167.5°	470.9	475.0	478.2	480.0	481.6	480.9	480.7
170°	463.8	466.5	468.2	470.0	470.9	470.9	470.0
172.5°	457.4	459.3	460.4	460.7	462.4	460.9	460.0
175°	447.7	449.5	449.5	449.5	450.4	448.6	447.7
177.5°	443.6	443.6	443.6	442.9	443.6	441.5	441.5
180°	441.5	441.5	441.5	441.5	441.5	441.5	441.5

(END OF REPORT)