

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331717-830

Luminaire Tested: **SA2XXRDIP-C865D725U830-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331717-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C865D725U830-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 725 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5843.5 lumens
Efficiency: N/A
Efficacy: 107.4 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331717-830

CATALOG NUMBER: SA2XXRDIP-C865D725U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331717-830

CATALOG NUMBER: SA2XXRDIP-C865D725U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53				
1	99	95	92	88	92	89	85	83	76	74	72	64	63	61	54	52	52	46				
2	91	84	78	74	84	78	73	69	68	64	61	57	55	53	48	46	45	40				
3	84	75	68	62	78	70	64	59	60	56	52	52	48	46	44	41	39	35				
4	77	67	59	54	71	63	56	51	54	49	45	47	43	40	40	37	35	31				
5	71	60	52	47	66	56	50	44	49	44	40	42	38	35	36	33	31	28				
6	66	54	47	41	61	51	44	39	45	39	35	39	35	31	33	30	28	25				
7	61	50	42	37	57	47	40	35	41	35	32	36	31	28	31	27	25	23				
8	57	45	38	33	53	43	36	31	38	32	28	33	29	26	28	25	23	20				
9	53	42	34	30	50	39	33	28	35	29	26	30	26	23	26	23	21	19				
10	50	38	31	27	47	36	30	26	32	27	23	28	24	21	25	21	19	17				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	29061	29061	29061	29061
5°	32456	29242	25929	29242
10°	36008	29037	22474	29037
15°	37778	28612	17708	28612
20°	32752	27981	15323	27981
25°	21480	27118	13682	27118
30°	14458	26071	12381	26071
35°	11710	24750	11168	24750
40°	10414	23317	10334	23317
45°	9423	21633	9225	21633
50°	8578	19964	8545	19964
55°	8062	18117	7958	18117
60°	6746	16417	6665	16417
65°	5685	14907	6449	14907
70°	5254	13312	6080	13312
75°	4916	11591	5614	11591
80°	4537	9530	5002	9530
85°	4168	7521	4409	7521



TEST NUMBER: P331717-830

CATALOG NUMBER: SA2XXRDIP-C865D725U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	170.6	2.9
10°-20°	475.4	8.1
20°-30°	612.6	10.5
30°-40°	582.2	10.0
40°-50°	498.7	8.5
50°-60°	379.8	6.5
60°-70°	240.1	4.1
70°-80°	119.9	2.1
80°-90°	33.5	0.6
90°-100°	31.1	0.5
100°-110°	114.0	2.0
110°-120°	304.7	5.2
120°-130°	502.9	8.6
130°-140°	534.9	9.2
140°-150°	497.1	8.5
150°-160°	399.7	6.8
160°-170°	257.6	4.4
170°-180°	88.7	1.5
0°-30°	1258.6	21.5
0°-40°	1840.8	31.5
0°-60°	2719.4	46.5
0°-90°	3112.9	53.3
90°-120°	449.7	7.7
90°-150°	1984.7	34.0
90°-180°	2731.0	46.7
0°-180°	5843.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1800	1800	1800	1800	1800	
5°	2002	1804	1600	1804	2002	198
15°	2260	1712	1059	1712	2260	610
25°	1206	1522	768	1522	1206	572
35°	594	1256	567	1256	594	380
45°	413	947	404	947	413	319
55°	286	644	283	644	286	251
65°	149	390	169	390	149	152
75°	79	186	90	186	79	84
85°	22	41	24	41	22	25
90°	18	1	18	1	18	9
95°	29	44	29	44	29	27
105°	51	205	51	205	51	53
115°	55	388	55	388	55	138
125°	576	548	576	548	576	499
135°	700	678	700	678	700	540
145°	799	787	799	787	799	500
155°	867	866	867	866	867	400
165°	911	913	911	913	911	257
175°	928	934	928	934	928	88
180°	932	932	932	932	932	



TEST NUMBER: P331717-830
 CATALOG NUMBER: SA2XXRDIP-C865D725U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9
2.5°	1872.9	1874.4	1875.9	1872.4	1872.4	1869.4	1862.9	1857.9	1843.9	1841.9	1841.9
5°	2002.5	2001.2	2003.8	1995.6	1984.3	1981.9	1970.0	1954.4	1938.1	1920.0	1916.2
7.5°	2131.3	2129.4	2124.4	2123.1	2114.4	2095.6	2076.4	2056.1	2029.0	2002.6	1989.3
10°	2196.3	2217.0	2204.5	2182.6	2187.0	2157.6	2141.9	2115.1	2092.5	2053.1	2044.4
12.5°	2260.4	2268.5	2264.6	2252.1	2246.6	2226.1	2205.0	2181.6	2140.0	2104.7	2073.9
15°	2260.1	2272.0	2275.1	2271.4	2274.5	2273.3	2262.0	2242.6	2206.4	2167.6	2133.8
17.5°	2093.3	2101.6	2122.0	2135.9	2153.4	2190.5	2208.8	2215.8	2210.5	2188.3	2164.5
20°	1906.2	1892.4	1949.9	1979.3	2004.3	2066.9	2120.7	2141.4	2174.4	2173.9	2167.6
22.5°	1641.0	1644.3	1698.8	1733.7	1806.8	1869.3	1930.6	2008.3	2072.4	2114.8	2139.6
25°	1205.7	1229.5	1283.9	1331.4	1412.8	1529.1	1634.7	1757.4	1873.0	1964.4	2051.3
27.5°	905.6	907.3	950.5	994.4	1042.6	1137.9	1271.0	1417.4	1582.3	1718.4	1875.0
30°	775.5	771.8	789.9	816.7	858.0	931.8	1031.9	1175.7	1340.2	1545.3	1728.0
32.5°	683.4	683.6	697.3	717.2	751.5	801.3	869.8	986.7	1142.1	1343.7	1557.8
35°	594.1	593.5	603.5	617.8	632.3	664.1	711.1	772.3	879.3	1067.5	1286.4
37.5°	530.1	532.8	537.7	546.7	562.6	580.3	608.5	649.7	725.9	837.2	1021.2
40°	494.1	495.3	502.2	509.7	519.1	532.8	556.0	589.1	644.8	733.6	868.0
42.5°	461.0	462.3	467.1	474.2	481.5	495.3	514.4	543.1	588.2	657.5	768.5
45°	412.7	412.7	417.2	420.3	428.4	440.9	456.6	480.3	511.5	562.9	636.7
47.5°	367.5	367.6	370.5	375.9	381.0	390.8	406.1	425.6	448.3	488.0	551.0
50°	341.5	342.0	343.9	348.4	351.5	360.2	372.1	389.0	412.7	443.4	496.0
52.5°	320.5	320.1	322.4	324.3	326.5	332.7	341.6	356.5	377.8	404.4	447.9
55°	286.4	283.9	287.7	290.8	292.7	295.2	300.2	309.5	327.7	350.2	382.8
57.5°	243.9	242.9	245.5	248.4	254.3	261.0	265.3	271.3	280.7	296.8	329.0
60°	208.9	208.9	214.5	216.4	223.3	232.1	240.8	245.8	255.1	265.8	289.5
62.5°	177.9	178.3	181.0	182.9	186.7	197.5	209.7	220.7	229.6	239.8	255.5
65°	148.8	150.1	150.1	151.4	153.8	156.4	161.4	170.1	185.8	200.1	212.0
67.5°	126.3	126.7	127.1	128.4	128.9	131.7	133.7	137.6	141.2	154.9	169.6
70°	111.3	113.2	112.5	113.9	114.4	115.6	118.2	120.1	125.7	128.8	137.6
72.5°	97.3	98.7	98.6	99.3	100.9	101.2	103.2	105.1	108.7	111.3	116.0
75°	78.8	78.1	78.8	80.0	80.7	81.3	81.3	83.8	85.7	88.2	91.3
77.5°	60.8	61.5	61.3	61.5	61.5	62.7	62.6	63.6	65.5	66.8	68.3
80°	48.8	49.4	48.8	49.4	50.0	50.6	50.0	50.6	52.5	53.8	53.8
82.5°	37.8	37.9	38.3	38.4	38.5	38.6	39.5	39.7	41.0	40.8	41.3
85°	22.5	21.9	21.9	21.9	22.5	23.1	22.5	22.5	23.1	23.1	23.1
87.5°	11.7	12.1	12.1	12.0	11.9	11.8	11.7	12.0	11.3	11.7	10.9
90°	18.2	17.9	17.6	17.3	17.0	16.5	15.7	15.0	14.2	13.5	12.3
92.5°	18.2	18.0	17.8	17.6	17.5	17.2	16.8	16.4	16.0	15.6	15.1
95°	29.0	29.1	29.3	29.4	29.6	29.3	28.6	27.8	27.1	26.3	25.3
97.5°	38.7	38.5	38.4	38.2	38.0	37.6	36.9	36.4	35.8	35.2	32.8
100°	45.1	44.9	44.6	44.3	44.0	43.3	42.0	40.8	39.6	38.5	35.9
102.5°	48.4	48.0	47.6	47.1	46.8	45.7	44.2	42.6	41.1	39.5	60.8
105°	51.3	50.6	50.0	49.5	48.8	47.7	46.1	44.4	42.8	41.1	82.0
107.5°	52.7	52.1	51.6	50.9	50.3	50.9	52.5	54.2	55.9	57.6	106.6
110°	53.3	52.7	52.0	51.5	50.9	58.1	73.0	88.0	103.0	118.0	161.3



TEST NUMBER: P331717-830

CATALOG NUMBER: SA2XXRDIP-C865D725U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	53.8	53.3	52.9	52.4	51.8	79.0	133.7	188.3	243.0	297.6	308.3
115°	55.3	66.1	76.8	87.7	98.4	138.6	207.9	277.3	346.7	416.0	412.3
117.5°	225.7	261.2	296.6	332.1	367.5	393.6	410.4	427.3	444.0	460.8	458.2
120°	411.3	431.5	451.8	471.9	492.2	501.4	499.6	497.9	496.0	494.2	491.5
122.5°	513.2	517.2	521.0	525.0	529.0	530.4	529.2	528.2	527.1	526.0	523.1
125°	576.5	576.0	575.6	575.1	574.7	573.9	572.9	571.8	570.8	569.8	566.8
127.5°	616.4	616.3	616.2	616.1	616.0	615.2	613.7	612.2	610.7	609.1	607.0
130°	641.2	641.3	641.5	641.7	641.8	641.0	639.4	637.7	636.1	634.4	632.8
132.5°	665.4	665.6	665.8	665.9	666.1	665.4	664.0	662.6	661.2	659.8	658.2
135°	700.5	700.8	701.2	701.4	701.7	701.2	699.6	698.1	696.6	695.1	693.8
137.5°	732.4	733.0	733.5	734.1	734.5	734.1	732.5	731.1	729.6	728.2	726.6
140°	752.4	753.2	753.9	754.7	755.4	755.2	753.8	752.4	751.1	749.8	748.1
142.5°	771.8	772.6	773.4	774.1	774.9	774.6	773.4	772.1	770.9	769.7	767.8
145°	799.0	799.7	800.5	801.3	801.9	801.8	800.8	799.7	798.7	797.6	795.0
147.5°	822.8	823.5	824.1	824.7	825.4	825.3	824.5	823.7	822.9	822.2	819.6
150°	837.4	838.1	838.9	839.6	840.4	840.3	839.4	838.5	837.6	836.7	834.3
152.5°	849.8	850.8	851.8	852.8	853.8	853.8	852.9	852.0	851.1	850.2	847.9
155°	867.0	868.3	869.5	870.6	871.9	872.0	871.1	870.2	869.3	868.4	866.6
157.5°	882.9	884.0	885.1	886.4	887.5	887.6	886.6	885.5	884.6	883.5	882.2
160°	892.0	893.1	894.1	895.1	896.2	896.3	895.4	894.5	893.6	892.7	891.7
162.5°	899.6	900.9	902.1	903.4	904.7	904.8	903.8	902.8	901.8	900.8	900.0
165°	910.9	911.9	912.9	914.1	915.1	915.1	914.1	912.9	911.9	910.9	910.4
167.5°	918.0	919.4	920.8	922.1	923.4	923.6	922.6	921.5	920.4	919.4	919.0
170°	922.4	923.7	925.0	926.4	927.7	927.9	926.8	925.8	924.7	923.7	923.4
172.5°	925.6	926.9	928.3	929.6	930.9	931.1	930.1	929.1	928.0	926.9	926.6
175°	928.4	929.9	931.4	932.9	934.4	934.6	933.6	932.6	931.5	930.5	930.1
177.5°	930.2	931.2	932.4	933.4	934.5	934.6	933.8	932.9	932.1	931.2	931.1
180°	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8



TEST NUMBER: P331717-830

CATALOG NUMBER: SA2XXRDIP-C865D725U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9
2.5°	1842.9	1838.9	1835.4	1826.4	1821.8	1811.8	1810.3	1809.9	1796.9	1784.3	1780.8
5°	1906.2	1896.2	1881.1	1863.7	1845.5	1826.7	1814.2	1804.2	1779.2	1755.5	1741.7
7.5°	1970.0	1948.4	1922.6	1889.4	1861.8	1830.8	1807.7	1787.1	1751.6	1717.6	1694.7
10°	2017.5	1982.4	1948.0	1902.4	1866.8	1831.7	1799.2	1771.1	1731.1	1686.0	1654.2
12.5°	2047.0	2008.5	1961.1	1916.5	1870.3	1825.7	1782.3	1746.1	1699.0	1652.6	1614.6
15°	2086.9	2045.6	1988.1	1924.3	1864.9	1806.8	1756.7	1711.7	1650.4	1594.7	1548.4
17.5°	2119.6	2062.8	2001.0	1927.2	1858.4	1784.5	1720.0	1662.6	1594.3	1527.2	1472.6
20°	2130.1	2073.8	2002.5	1928.7	1847.4	1760.5	1691.0	1628.5	1555.3	1482.1	1419.7
22.5°	2123.5	2079.8	2000.5	1912.1	1828.9	1738.0	1659.5	1587.0	1505.8	1431.2	1358.6
25°	2079.4	2064.4	1989.3	1893.0	1798.0	1692.3	1601.6	1522.2	1429.6	1349.6	1270.7
27.5°	1976.5	2008.8	1962.4	1859.7	1754.1	1640.8	1538.8	1448.4	1352.4	1262.3	1183.7
30°	1877.5	1951.8	1931.8	1836.7	1718.5	1607.2	1492.8	1398.4	1295.8	1203.2	1125.7
32.5°	1741.8	1864.7	1884.3	1804.8	1682.5	1560.2	1440.3	1346.3	1239.3	1141.7	1066.1
35°	1526.0	1709.8	1794.2	1743.6	1621.0	1489.0	1365.2	1255.7	1148.2	1051.9	976.9
37.5°	1268.4	1518.8	1659.5	1663.1	1550.6	1413.3	1278.6	1169.9	1059.8	965.3	884.0
40°	1101.3	1372.7	1555.9	1596.6	1501.6	1353.3	1217.0	1106.3	998.7	906.2	813.0
42.5°	951.2	1221.6	1446.9	1517.6	1442.0	1294.8	1158.0	1042.3	937.7	850.2	755.0
45°	769.2	1005.6	1253.9	1380.3	1338.3	1202.0	1057.5	947.4	849.2	773.6	682.3
47.5°	648.9	815.5	1055.7	1226.6	1225.9	1101.5	959.3	853.9	762.8	691.9	618.0
50°	580.3	725.5	928.7	1122.6	1138.8	1034.3	899.3	794.8	709.8	635.4	576.0
52.5°	518.8	638.4	821.1	1007.0	1053.3	962.8	831.8	735.4	652.8	584.4	533.5
55°	438.4	530.9	669.8	843.7	913.7	849.9	733.6	643.6	576.6	519.1	475.3
57.5°	370.9	440.3	551.7	691.6	773.3	733.1	637.2	564.0	506.7	454.7	420.1
60°	328.3	385.2	479.7	596.6	686.6	658.6	576.6	508.4	459.7	414.6	382.1
62.5°	288.3	337.2	418.1	513.0	595.6	584.0	517.1	459.9	417.2	376.1	348.6
65°	232.1	267.7	330.8	405.3	471.6	477.2	429.0	390.2	352.1	319.6	295.2
67.5°	184.7	208.0	252.5	315.2	364.9	382.6	353.2	323.6	293.3	268.2	247.0
70°	155.7	174.5	207.0	257.7	303.3	322.1	305.2	282.0	255.8	235.2	217.0
72.5°	126.2	144.5	168.4	205.7	244.8	265.0	259.2	242.5	221.2	204.2	187.0
75°	95.1	100.7	117.0	141.9	172.6	190.1	194.5	185.8	168.8	155.7	145.7
77.5°	70.3	73.7	81.4	94.5	114.6	130.2	136.6	135.5	123.9	116.3	107.0
80°	56.3	58.2	61.9	67.6	82.6	98.2	102.5	102.5	94.4	91.3	81.9
82.5°	42.8	44.1	46.4	49.5	56.6	70.1	75.0	76.1	70.9	66.8	59.4
85°	24.4	23.8	25.0	26.9	28.2	31.9	39.4	40.6	39.4	34.4	32.5
87.5°	10.7	11.0	10.7	10.0	10.1	10.3	12.4	14.6	13.0	11.8	11.1
90°	11.1	9.9	8.7	7.3	5.7	4.0	2.4	0.7	2.4	4.0	5.7
92.5°	14.4	13.9	13.3	13.0	13.2	13.3	13.5	13.6	13.5	13.3	13.2
95°	24.2	23.2	22.1	24.0	29.0	33.9	38.9	43.8	38.9	33.9	29.0
97.5°	30.3	27.9	25.4	31.2	45.1	59.1	73.0	87.0	73.0	59.1	45.1
100°	33.4	30.8	28.3	37.2	57.8	78.3	98.8	119.3	98.8	78.3	57.8
102.5°	82.1	103.4	124.7	137.5	141.9	146.3	150.6	155.0	150.6	146.3	141.9
105°	122.9	163.8	204.7	222.9	218.5	214.0	209.4	205.0	209.4	214.0	218.5
107.5°	155.7	204.7	253.8	276.5	272.9	269.3	265.6	262.0	265.6	269.3	272.9
110°	204.6	247.9	291.2	311.2	308.1	305.0	301.8	298.7	301.8	305.0	308.1



TEST NUMBER: P331717-830

CATALOG NUMBER: SA2XXRDIP-C865D725U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	319.0	329.7	340.4	344.3	341.6	338.7	336.0	333.2	336.0	338.7	341.6
115°	408.5	404.7	401.1	397.8	395.3	392.8	390.2	387.7	390.2	392.8	395.3
117.5°	455.6	453.1	450.4	447.7	444.9	442.1	439.2	436.4	439.2	442.1	444.9
120°	488.8	486.2	483.4	481.0	478.7	476.5	474.2	471.9	474.2	476.5	478.7
122.5°	520.2	517.3	514.3	511.6	509.3	506.9	504.5	502.2	504.5	506.9	509.3
125°	564.0	561.2	558.4	555.9	554.0	552.0	550.1	548.2	550.1	552.0	554.0
127.5°	604.8	602.8	600.6	598.4	596.3	594.2	592.0	589.8	592.0	594.2	596.3
130°	631.1	629.5	627.8	625.8	623.4	621.0	618.7	616.2	618.7	621.0	623.4
132.5°	656.5	654.9	653.2	651.4	649.3	647.3	645.3	643.2	645.3	647.3	649.3
135°	692.4	691.1	689.8	687.9	685.5	683.1	680.7	678.3	680.7	683.1	685.5
137.5°	725.1	723.6	722.1	720.5	718.8	717.1	715.4	713.8	715.4	717.1	718.8
140°	746.5	744.8	743.2	741.7	740.6	739.3	738.1	737.0	738.1	739.3	740.6
142.5°	765.9	764.0	762.1	760.6	759.6	758.6	757.4	756.4	757.4	758.6	759.6
145°	792.5	789.9	787.4	786.3	786.4	786.6	786.6	786.8	786.6	786.6	786.4
147.5°	817.1	814.6	812.1	811.2	811.7	812.3	812.8	813.4	812.8	812.3	811.7
150°	831.9	829.5	827.2	826.4	827.6	828.6	829.6	830.7	829.6	828.6	827.6
152.5°	845.6	843.4	841.1	840.6	841.7	842.9	844.0	845.2	844.0	842.9	841.7
155°	864.8	863.0	861.2	861.0	862.3	863.7	865.1	866.4	865.1	863.7	862.3
157.5°	881.0	879.8	878.4	878.4	879.6	880.7	881.8	883.0	881.8	880.7	879.6
160°	890.9	889.9	889.1	889.1	889.9	890.9	891.7	892.7	891.7	890.9	889.9
162.5°	899.2	898.4	897.7	897.7	898.6	899.6	900.4	901.4	900.4	899.6	898.6
165°	910.0	909.6	909.1	909.3	910.2	911.2	912.0	912.9	912.0	911.2	910.2
167.5°	918.5	918.1	917.7	917.9	918.9	919.7	920.7	921.5	920.7	919.7	918.9
170°	923.1	922.8	922.5	922.8	923.7	924.6	925.5	926.4	925.5	924.6	923.7
172.5°	926.3	926.0	925.8	926.0	926.9	927.8	928.7	929.6	928.7	927.8	926.9
175°	929.8	929.5	929.3	929.6	930.7	931.7	932.7	933.8	932.7	931.7	930.7
177.5°	931.0	930.9	930.8	931.1	932.0	932.8	933.7	934.5	933.7	932.8	932.0
180°	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8



TEST NUMBER: P331717-830

CATALOG NUMBER: SA2XXRDIP-C865D725U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9
2.5°	1774.3	1770.8	1764.3	1754.4	1748.3	1737.9	1730.8	1734.8	1735.8	1734.8	1733.8
5°	1726.6	1713.5	1695.4	1677.9	1661.6	1644.2	1634.1	1629.8	1621.0	1616.0	1613.5
7.5°	1669.1	1646.4	1620.7	1590.3	1564.3	1537.2	1523.3	1516.5	1498.5	1488.7	1480.3
10°	1626.0	1590.4	1564.7	1524.7	1500.3	1464.6	1440.3	1440.9	1416.5	1402.7	1392.7
12.5°	1578.5	1539.4	1496.7	1460.7	1426.7	1398.1	1368.8	1356.8	1331.0	1317.7	1290.6
15°	1499.7	1454.1	1409.0	1360.2	1325.8	1281.4	1238.9	1186.9	1145.1	1108.8	1098.8
17.5°	1413.6	1357.1	1311.9	1254.6	1195.7	1121.1	1071.8	1041.6	1016.3	997.2	983.0
20°	1354.6	1297.0	1248.9	1162.6	1083.2	1032.6	996.3	973.1	946.9	926.2	914.9
22.5°	1292.5	1232.5	1166.9	1070.5	1008.6	968.0	935.7	909.1	891.3	875.2	864.9
25°	1204.5	1138.8	1030.7	964.3	914.3	871.8	849.2	833.0	814.3	792.4	782.3
27.5°	1111.4	1007.0	929.3	880.1	832.3	804.6	784.4	760.1	743.3	733.5	723.0
30°	1041.9	937.5	876.8	823.0	789.2	758.6	734.8	721.0	704.8	688.0	681.1
32.5°	964.3	880.9	822.7	778.0	743.7	717.6	698.8	676.6	664.8	654.4	640.0
35°	868.0	804.8	751.7	715.5	683.0	661.7	639.8	626.6	605.4	596.6	591.0
37.5°	786.5	731.7	692.0	653.7	628.0	604.5	591.1	570.2	561.0	548.8	537.0
40°	740.5	686.6	648.6	617.3	588.5	571.0	554.1	537.2	523.5	517.8	503.4
42.5°	693.4	649.7	611.5	577.2	558.0	539.4	518.1	505.7	491.4	482.3	473.4
45°	628.5	589.7	557.2	529.0	507.8	488.4	474.7	454.0	445.9	427.7	420.3
47.5°	571.5	535.5	504.4	477.7	456.9	444.3	424.1	408.0	395.0	383.9	374.2
50°	530.9	501.0	470.9	447.1	428.4	410.3	389.6	381.4	361.5	355.8	350.2
52.5°	493.9	465.4	437.9	414.6	395.9	378.2	360.1	349.5	335.9	330.4	326.2
55°	442.1	414.6	388.3	367.7	348.9	330.8	319.6	306.4	300.2	295.8	290.8
57.5°	390.1	365.3	345.3	324.3	305.5	291.1	278.1	270.1	263.6	257.9	251.9
60°	357.1	333.3	315.2	295.8	276.4	264.6	254.5	245.2	237.6	228.8	226.4
62.5°	322.1	301.3	284.6	265.8	248.9	238.0	228.5	219.6	210.7	197.8	194.4
65°	273.9	257.7	240.2	224.5	209.5	198.9	185.1	175.1	171.4	170.1	169.5
67.5°	230.4	215.0	200.0	184.0	170.3	160.5	153.4	151.9	149.3	148.5	146.8
70°	201.3	187.0	172.0	156.9	143.8	141.9	139.5	137.0	133.8	132.6	131.3
72.5°	175.3	160.5	145.4	133.5	127.8	125.5	122.9	120.5	118.3	117.1	116.3
75°	134.5	120.7	110.7	106.3	103.2	101.3	97.6	95.7	94.4	92.6	91.9
77.5°	96.8	89.1	84.5	81.7	78.4	76.4	74.3	72.4	71.1	70.7	69.7
80°	73.8	70.0	66.9	63.2	61.9	59.4	58.8	56.9	57.5	55.7	55.7
82.5°	57.3	52.5	49.9	48.2	46.9	44.9	44.3	43.4	43.5	42.1	42.1
85°	29.4	28.2	26.9	25.6	25.6	23.8	24.4	23.8	23.8	22.5	21.9
87.5°	10.9	10.7	10.0	10.2	10.5	10.2	10.4	10.0	10.2	10.3	9.9
90°	7.3	8.7	9.9	11.1	12.3	13.5	14.2	15.0	15.7	16.5	17.0
92.5°	13.0	13.3	13.9	14.4	15.1	15.6	16.0	16.4	16.8	17.2	17.5
95°	24.0	22.1	23.2	24.2	25.3	26.3	27.1	27.8	28.6	29.3	29.6
97.5°	31.2	25.4	27.9	30.3	32.8	35.2	35.8	36.4	36.9	37.6	38.0
100°	37.2	28.3	30.8	33.4	35.9	38.5	39.6	40.8	42.0	43.3	44.0
102.5°	137.5	124.7	103.4	82.1	60.8	39.5	41.1	42.6	44.2	45.7	46.8
105°	222.9	204.7	163.8	122.9	82.0	41.1	42.8	44.4	46.1	47.7	48.8
107.5°	276.5	253.8	204.7	155.7	106.6	57.6	55.9	54.2	52.5	50.9	50.3
110°	311.2	291.2	247.9	204.6	161.3	118.0	103.0	88.0	73.0	58.1	50.9



TEST NUMBER: P331717-830

CATALOG NUMBER: SA2XXRDIP-C865D725U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	344.3	340.4	329.7	319.0	308.3	297.6	243.0	188.3	133.7	79.0	51.8
115°	397.8	401.1	404.7	408.5	412.3	416.0	346.7	277.3	207.9	138.6	98.4
117.5°	447.7	450.4	453.1	455.6	458.2	460.8	444.0	427.3	410.4	393.6	367.5
120°	481.0	483.4	486.2	488.8	491.5	494.2	496.0	497.9	499.6	501.4	492.2
122.5°	511.6	514.3	517.3	520.2	523.1	526.0	527.1	528.2	529.2	530.4	529.0
125°	555.9	558.4	561.2	564.0	566.8	569.8	570.8	571.8	572.9	573.9	574.7
127.5°	598.4	600.6	602.8	604.8	607.0	609.1	610.7	612.2	613.7	615.2	616.0
130°	625.8	627.8	629.5	631.1	632.8	634.4	636.1	637.7	639.4	641.0	641.8
132.5°	651.4	653.2	654.9	656.5	658.2	659.8	661.2	662.6	664.0	665.4	666.1
135°	687.9	689.8	691.1	692.4	693.8	695.1	696.6	698.1	699.6	701.2	701.7
137.5°	720.5	722.1	723.6	725.1	726.6	728.2	729.6	731.1	732.5	734.1	734.5
140°	741.7	743.2	744.8	746.5	748.1	749.8	751.1	752.4	753.8	755.2	755.4
142.5°	760.6	762.1	764.0	765.9	767.8	769.7	770.9	772.1	773.4	774.6	774.9
145°	786.3	787.4	789.9	792.5	795.0	797.6	798.7	799.7	800.8	801.8	801.9
147.5°	811.2	812.1	814.6	817.1	819.6	822.2	822.9	823.7	824.5	825.3	825.4
150°	826.4	827.2	829.5	831.9	834.3	836.7	837.6	838.5	839.4	840.3	840.4
152.5°	840.6	841.1	843.4	845.6	847.9	850.2	851.1	852.0	852.9	853.8	853.8
155°	861.0	861.2	863.0	864.8	866.6	868.4	869.3	870.2	871.1	872.0	871.9
157.5°	878.4	878.4	879.8	881.0	882.2	883.5	884.6	885.5	886.6	887.6	887.5
160°	889.1	889.1	889.9	890.9	891.7	892.7	893.6	894.5	895.4	896.3	896.2
162.5°	897.7	897.7	898.4	899.2	900.0	900.8	901.8	902.8	903.8	904.8	904.7
165°	909.3	909.1	909.6	910.0	910.4	910.9	911.9	912.9	914.1	915.1	915.1
167.5°	917.9	917.7	918.1	918.5	919.0	919.4	920.4	921.5	922.6	923.6	923.4
170°	922.8	922.5	922.8	923.1	923.4	923.7	924.7	925.8	926.8	927.9	927.7
172.5°	926.0	925.8	926.0	926.3	926.6	926.9	928.0	929.1	930.1	931.1	930.9
175°	929.6	929.3	929.5	929.8	930.1	930.5	931.5	932.6	933.6	934.6	934.4
177.5°	931.1	930.8	930.9	931.0	931.1	931.2	932.1	932.9	933.8	934.6	934.5
180°	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8



TEST NUMBER: P331717-830

CATALOG NUMBER: SA2XXRDIP-C865D725U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9
2.5°	1728.3	1729.3	1727.8	1728.8	1727.8	1729.3	1728.3	1733.8	1734.8	1735.8	1734.8
5°	1610.3	1602.9	1601.6	1599.8	1601.6	1602.9	1610.3	1613.5	1616.0	1621.0	1629.8
7.5°	1469.5	1468.4	1465.3	1460.9	1465.3	1468.4	1469.5	1480.3	1488.7	1498.5	1516.5
10°	1378.9	1375.8	1375.3	1370.8	1375.3	1375.8	1378.9	1392.7	1402.7	1416.5	1440.9
12.5°	1272.9	1252.7	1250.7	1239.7	1250.7	1252.7	1272.9	1290.6	1317.7	1331.0	1356.8
15°	1083.8	1080.1	1067.5	1059.4	1067.5	1080.1	1083.8	1098.8	1108.8	1145.1	1186.9
17.5°	975.7	963.5	959.6	957.8	959.6	963.5	975.7	983.0	997.2	1016.3	1041.6
20°	906.2	894.9	893.1	891.8	893.1	894.9	906.2	914.9	926.2	946.9	973.1
22.5°	858.2	846.4	841.5	837.7	841.5	846.4	858.2	864.9	875.2	891.3	909.1
25°	776.1	771.8	769.2	768.0	769.2	771.8	776.1	782.3	792.4	814.3	833.0
27.5°	711.9	702.3	700.4	697.2	700.4	702.3	711.9	723.0	733.5	743.3	760.1
30°	675.4	672.3	667.9	664.1	667.9	672.3	675.4	681.1	688.0	704.8	721.0
32.5°	632.4	629.8	625.8	624.2	625.8	629.8	632.4	640.0	654.4	664.8	676.6
35°	584.8	576.0	572.2	566.6	572.2	576.0	584.8	591.0	596.6	605.4	626.6
37.5°	534.3	529.7	524.4	526.3	524.4	529.7	534.3	537.0	548.8	561.0	570.2
40°	495.3	492.2	491.0	490.3	491.0	492.2	495.3	503.4	517.8	523.5	537.2
42.5°	464.3	455.6	452.4	452.2	452.4	455.6	464.3	473.4	482.3	491.4	505.7
45°	417.2	409.0	403.4	404.0	403.4	409.0	417.2	420.3	427.7	445.9	454.0
47.5°	368.8	368.6	365.1	366.3	365.1	368.6	368.8	374.2	383.9	395.0	408.0
50°	345.8	342.0	339.6	340.2	339.6	342.0	345.8	350.2	355.8	361.5	381.4
52.5°	323.9	320.6	318.6	321.2	318.6	320.6	323.9	326.2	330.4	335.9	349.5
55°	287.7	283.9	283.3	282.7	283.3	283.9	287.7	290.8	295.8	300.2	306.4
57.5°	247.3	244.8	241.0	239.4	241.0	244.8	247.3	251.9	257.9	263.6	270.1
60°	218.3	213.3	207.0	206.4	207.0	213.3	218.3	226.4	228.8	237.6	245.2
62.5°	191.7	190.8	189.5	189.4	189.5	190.8	191.7	194.4	197.8	210.7	219.6
65°	168.2	167.6	168.2	168.8	168.2	167.6	168.2	169.5	170.1	171.4	175.1
67.5°	146.6	145.4	144.3	144.9	144.3	145.4	146.6	146.8	148.5	149.3	151.9
70°	130.1	129.4	128.8	128.8	128.8	129.4	130.1	131.3	132.6	133.8	137.0
72.5°	114.0	114.0	113.3	112.8	113.3	114.0	114.0	116.3	117.1	118.3	120.5
75°	91.3	90.0	90.0	90.0	90.0	90.0	91.3	91.9	92.6	94.4	95.7
77.5°	69.6	68.9	68.3	67.8	68.3	68.9	69.6	69.7	70.7	71.1	72.4
80°	55.0	54.4	53.8	53.8	53.8	54.4	55.0	55.7	55.7	57.5	56.9
82.5°	42.0	41.4	41.3	40.8	41.3	41.4	42.0	42.1	42.1	43.5	43.4
85°	22.5	23.1	22.5	23.8	22.5	23.1	22.5	21.9	22.5	23.8	23.8
87.5°	10.0	9.5	10.1	9.6	10.1	9.5	10.0	9.9	10.3	10.2	10.0
90°	17.3	17.6	17.9	18.2	17.9	17.6	17.3	17.0	16.5	15.7	15.0
92.5°	17.6	17.8	18.0	18.2	18.0	17.8	17.6	17.5	17.2	16.8	16.4
95°	29.4	29.3	29.1	29.0	29.1	29.3	29.4	29.6	29.3	28.6	27.8
97.5°	38.2	38.4	38.5	38.7	38.5	38.4	38.2	38.0	37.6	36.9	36.4
100°	44.3	44.6	44.9	45.1	44.9	44.6	44.3	44.0	43.3	42.0	40.8
102.5°	47.1	47.6	48.0	48.4	48.0	47.6	47.1	46.8	45.7	44.2	42.6
105°	49.5	50.0	50.6	51.3	50.6	50.0	49.5	48.8	47.7	46.1	44.4
107.5°	50.9	51.6	52.1	52.7	52.1	51.6	50.9	50.3	50.9	52.5	54.2
110°	51.5	52.0	52.7	53.3	52.7	52.0	51.5	50.9	58.1	73.0	88.0



TEST NUMBER: P331717-830

CATALOG NUMBER: SA2XXRDIP-C865D725U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	52.4	52.9	53.3	53.8	53.3	52.9	52.4	51.8	79.0	133.7	188.3
115°	87.7	76.8	66.1	55.3	66.1	76.8	87.7	98.4	138.6	207.9	277.3
117.5°	332.1	296.6	261.2	225.7	261.2	296.6	332.1	367.5	393.6	410.4	427.3
120°	471.9	451.8	431.5	411.3	431.5	451.8	471.9	492.2	501.4	499.6	497.9
122.5°	525.0	521.0	517.2	513.2	517.2	521.0	525.0	529.0	530.4	529.2	528.2
125°	575.1	575.6	576.0	576.5	576.0	575.6	575.1	574.7	573.9	572.9	571.8
127.5°	616.1	616.2	616.3	616.4	616.3	616.2	616.1	616.0	615.2	613.7	612.2
130°	641.7	641.5	641.3	641.2	641.3	641.5	641.7	641.8	641.0	639.4	637.7
132.5°	665.9	665.8	665.6	665.4	665.6	665.8	665.9	666.1	665.4	664.0	662.6
135°	701.4	701.2	700.8	700.5	700.8	701.2	701.4	701.7	701.2	699.6	698.1
137.5°	734.1	733.5	733.0	732.4	733.0	733.5	734.1	734.5	734.1	732.5	731.1
140°	754.7	753.9	753.2	752.4	753.2	753.9	754.7	755.4	755.2	753.8	752.4
142.5°	774.1	773.4	772.6	771.8	772.6	773.4	774.1	774.9	774.6	773.4	772.1
145°	801.3	800.5	799.7	799.0	799.7	800.5	801.3	801.9	801.8	800.8	799.7
147.5°	824.7	824.1	823.5	822.8	823.5	824.1	824.7	825.4	825.3	824.5	823.7
150°	839.6	838.9	838.1	837.4	838.1	838.9	839.6	840.4	840.3	839.4	838.5
152.5°	852.8	851.8	850.8	849.8	850.8	851.8	852.8	853.8	853.8	852.9	852.0
155°	870.6	869.5	868.3	867.0	868.3	869.5	870.6	871.9	872.0	871.1	870.2
157.5°	886.4	885.1	884.0	882.9	884.0	885.1	886.4	887.5	887.6	886.6	885.5
160°	895.1	894.1	893.1	892.0	893.1	894.1	895.1	896.2	896.3	895.4	894.5
162.5°	903.4	902.1	900.9	899.6	900.9	902.1	903.4	904.7	904.8	903.8	902.8
165°	914.1	912.9	911.9	910.9	911.9	912.9	914.1	915.1	915.1	914.1	912.9
167.5°	922.1	920.8	919.4	918.0	919.4	920.8	922.1	923.4	923.6	922.6	921.5
170°	926.4	925.0	923.7	922.4	923.7	925.0	926.4	927.7	927.9	926.8	925.8
172.5°	929.6	928.3	926.9	925.6	926.9	928.3	929.6	930.9	931.1	930.1	929.1
175°	932.9	931.4	929.9	928.4	929.9	931.4	932.9	934.4	934.6	933.6	932.6
177.5°	933.4	932.4	931.2	930.2	931.2	932.4	933.4	934.5	934.6	933.8	932.9
180°	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8



TEST NUMBER: P331717-830

CATALOG NUMBER: SA2XXRDIP-C865D725U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9
2.5°	1730.8	1737.9	1748.3	1754.4	1764.3	1770.8	1774.3	1780.8	1784.3	1796.9	1809.9
5°	1634.1	1644.2	1661.6	1677.9	1695.4	1713.5	1726.6	1741.7	1755.5	1779.2	1804.2
7.5°	1523.3	1537.2	1564.3	1590.3	1620.7	1646.4	1669.1	1694.7	1717.6	1751.6	1787.1
10°	1440.3	1464.6	1500.3	1524.7	1564.7	1590.4	1626.0	1654.2	1686.0	1731.1	1771.1
12.5°	1368.8	1398.1	1426.7	1460.7	1496.7	1539.4	1578.5	1614.6	1652.6	1699.0	1746.1
15°	1238.9	1281.4	1325.8	1360.2	1409.0	1454.1	1499.7	1548.4	1594.7	1650.4	1711.7
17.5°	1071.8	1121.1	1195.7	1254.6	1311.9	1357.1	1413.6	1472.6	1527.2	1594.3	1662.6
20°	996.3	1032.6	1083.2	1162.6	1248.9	1297.0	1354.6	1419.7	1482.1	1555.3	1628.5
22.5°	935.7	968.0	1008.6	1070.5	1166.9	1232.5	1292.5	1358.6	1431.2	1505.8	1587.0
25°	849.2	871.8	914.3	964.3	1030.7	1138.8	1204.5	1270.7	1349.6	1429.6	1522.2
27.5°	784.4	804.6	832.3	880.1	929.3	1007.0	1111.4	1183.7	1262.3	1352.4	1448.4
30°	734.8	758.6	789.2	823.0	876.8	937.5	1041.9	1125.7	1203.2	1295.8	1398.4
32.5°	698.8	717.6	743.7	778.0	822.7	880.9	964.3	1066.1	1141.7	1239.3	1346.3
35°	639.8	661.7	683.0	715.5	751.7	804.8	868.0	976.9	1051.9	1148.2	1255.7
37.5°	591.1	604.5	628.0	653.7	692.0	731.7	786.5	884.0	965.3	1059.8	1169.9
40°	554.1	571.0	588.5	617.3	648.6	686.6	740.5	813.0	906.2	998.7	1106.3
42.5°	518.1	539.4	558.0	577.2	611.5	649.7	693.4	755.0	850.2	937.7	1042.3
45°	474.7	488.4	507.8	529.0	557.2	589.7	628.5	682.3	773.6	849.2	947.4
47.5°	424.1	444.3	456.9	477.7	504.4	535.5	571.5	618.0	691.9	762.8	853.9
50°	389.6	410.3	428.4	447.1	470.9	501.0	530.9	576.0	635.4	709.8	794.8
52.5°	360.1	378.2	395.9	414.6	437.9	465.4	493.9	533.5	584.4	652.8	735.4
55°	319.6	330.8	348.9	367.7	388.3	414.6	442.1	475.3	519.1	576.6	643.6
57.5°	278.1	291.1	305.5	324.3	345.3	365.3	390.1	420.1	454.7	506.7	564.0
60°	254.5	264.6	276.4	295.8	315.2	333.3	357.1	382.1	414.6	459.7	508.4
62.5°	228.5	238.0	248.9	265.8	284.6	301.3	322.1	348.6	376.1	417.2	459.9
65°	185.1	198.9	209.5	224.5	240.2	257.7	273.9	295.2	319.6	352.1	390.2
67.5°	153.4	160.5	170.3	184.0	200.0	215.0	230.4	247.0	268.2	293.3	323.6
70°	139.5	141.9	143.8	156.9	172.0	187.0	201.3	217.0	235.2	255.8	282.0
72.5°	122.9	125.5	127.8	133.5	145.4	160.5	175.3	187.0	204.2	221.2	242.5
75°	97.6	101.3	103.2	106.3	110.7	120.7	134.5	145.7	155.7	168.8	185.8
77.5°	74.3	76.4	78.4	81.7	84.5	89.1	96.8	107.0	116.3	123.9	135.5
80°	58.8	59.4	61.9	63.2	66.9	70.0	73.8	81.9	91.3	94.4	102.5
82.5°	44.3	44.9	46.9	48.2	49.9	52.5	57.3	59.4	66.8	70.9	76.1
85°	24.4	23.8	25.6	25.6	26.9	28.2	29.4	32.5	34.4	39.4	40.6
87.5°	10.4	10.2	10.5	10.2	10.0	10.7	10.9	11.1	11.8	13.0	14.6
90°	14.2	13.5	12.3	11.1	9.9	8.7	7.3	5.7	4.0	2.4	0.7
92.5°	16.0	15.6	15.1	14.4	13.9	13.3	13.0	13.2	13.3	13.5	13.6
95°	27.1	26.3	25.3	24.2	23.2	22.1	24.0	29.0	33.9	38.9	43.8
97.5°	35.8	35.2	32.8	30.3	27.9	25.4	31.2	45.1	59.1	73.0	87.0
100°	39.6	38.5	35.9	33.4	30.8	28.3	37.2	57.8	78.3	98.8	119.3
102.5°	41.1	39.5	60.8	82.1	103.4	124.7	137.5	141.9	146.3	150.6	155.0
105°	42.8	41.1	82.0	122.9	163.8	204.7	222.9	218.5	214.0	209.4	205.0
107.5°	55.9	57.6	106.6	155.7	204.7	253.8	276.5	272.9	269.3	265.6	262.0
110°	103.0	118.0	161.3	204.6	247.9	291.2	311.2	308.1	305.0	301.8	298.7



TEST NUMBER: P331717-830

CATALOG NUMBER: SA2XXRDIP-C865D725U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	243.0	297.6	308.3	319.0	329.7	340.4	344.3	341.6	338.7	336.0	333.2
115°	346.7	416.0	412.3	408.5	404.7	401.1	397.8	395.3	392.8	390.2	387.7
117.5°	444.0	460.8	458.2	455.6	453.1	450.4	447.7	444.9	442.1	439.2	436.4
120°	496.0	494.2	491.5	488.8	486.2	483.4	481.0	478.7	476.5	474.2	471.9
122.5°	527.1	526.0	523.1	520.2	517.3	514.3	511.6	509.3	506.9	504.5	502.2
125°	570.8	569.8	566.8	564.0	561.2	558.4	555.9	554.0	552.0	550.1	548.2
127.5°	610.7	609.1	607.0	604.8	602.8	600.6	598.4	596.3	594.2	592.0	589.8
130°	636.1	634.4	632.8	631.1	629.5	627.8	625.8	623.4	621.0	618.7	616.2
132.5°	661.2	659.8	658.2	656.5	654.9	653.2	651.4	649.3	647.3	645.3	643.2
135°	696.6	695.1	693.8	692.4	691.1	689.8	687.9	685.5	683.1	680.7	678.3
137.5°	729.6	728.2	726.6	725.1	723.6	722.1	720.5	718.8	717.1	715.4	713.8
140°	751.1	749.8	748.1	746.5	744.8	743.2	741.7	740.6	739.3	738.1	737.0
142.5°	770.9	769.7	767.8	765.9	764.0	762.1	760.6	759.6	758.6	757.4	756.4
145°	798.7	797.6	795.0	792.5	789.9	787.4	786.3	786.4	786.6	786.6	786.8
147.5°	822.9	822.2	819.6	817.1	814.6	812.1	811.2	811.7	812.3	812.8	813.4
150°	837.6	836.7	834.3	831.9	829.5	827.2	826.4	827.6	828.6	829.6	830.7
152.5°	851.1	850.2	847.9	845.6	843.4	841.1	840.6	841.7	842.9	844.0	845.2
155°	869.3	868.4	866.6	864.8	863.0	861.2	861.0	862.3	863.7	865.1	866.4
157.5°	884.6	883.5	882.2	881.0	879.8	878.4	878.4	879.6	880.7	881.8	883.0
160°	893.6	892.7	891.7	890.9	889.9	889.1	889.1	889.9	890.9	891.7	892.7
162.5°	901.8	900.8	900.0	899.2	898.4	897.7	897.7	898.6	899.6	900.4	901.4
165°	911.9	910.9	910.4	910.0	909.6	909.1	909.3	910.2	911.2	912.0	912.9
167.5°	920.4	919.4	919.0	918.5	918.1	917.7	917.9	918.9	919.7	920.7	921.5
170°	924.7	923.7	923.4	923.1	922.8	922.5	922.8	923.7	924.6	925.5	926.4
172.5°	928.0	926.9	926.6	926.3	926.0	925.8	926.0	926.9	927.8	928.7	929.6
175°	931.5	930.5	930.1	929.8	929.5	929.3	929.6	930.7	931.7	932.7	933.8
177.5°	932.1	931.2	931.1	931.0	930.9	930.8	931.1	932.0	932.8	933.7	934.5
180°	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8



TEST NUMBER: P331717-830

CATALOG NUMBER: SA2XXRDIP-C865D725U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9
2.5°	1810.3	1811.8	1821.8	1826.4	1835.4	1838.9	1842.9	1841.9	1841.9	1843.9	1857.9
5°	1814.2	1826.7	1845.5	1863.7	1881.1	1896.2	1906.2	1916.2	1920.0	1938.1	1954.4
7.5°	1807.7	1830.8	1861.8	1889.4	1922.6	1948.4	1970.0	1989.3	2002.6	2029.0	2056.1
10°	1799.2	1831.7	1866.8	1902.4	1948.0	1982.4	2017.5	2044.4	2053.1	2092.5	2115.1
12.5°	1782.3	1825.7	1870.3	1916.5	1961.1	2008.5	2047.0	2073.9	2104.7	2140.0	2181.6
15°	1756.7	1806.8	1864.9	1924.3	1988.1	2045.6	2086.9	2133.8	2167.6	2206.4	2242.6
17.5°	1720.0	1784.5	1858.4	1927.2	2001.0	2062.8	2119.6	2164.5	2188.3	2210.5	2215.8
20°	1691.0	1760.5	1847.4	1928.7	2002.5	2073.8	2130.1	2167.6	2173.9	2174.4	2141.4
22.5°	1659.5	1738.0	1828.9	1912.1	2000.5	2079.8	2123.5	2139.6	2114.8	2072.4	2008.3
25°	1601.6	1692.3	1798.0	1893.0	1989.3	2064.4	2079.4	2051.3	1964.4	1873.0	1757.4
27.5°	1538.8	1640.8	1754.1	1859.7	1962.4	2008.8	1976.5	1875.0	1718.4	1582.3	1417.4
30°	1492.8	1607.2	1718.5	1836.7	1931.8	1951.8	1877.5	1728.0	1545.3	1340.2	1175.7
32.5°	1440.3	1560.2	1682.5	1804.8	1884.3	1864.7	1741.8	1557.8	1343.7	1142.1	986.7
35°	1365.2	1489.0	1621.0	1743.6	1794.2	1709.8	1526.0	1286.4	1067.5	879.3	772.3
37.5°	1278.6	1413.3	1550.6	1663.1	1659.5	1518.8	1268.4	1021.2	837.2	725.9	649.7
40°	1217.0	1353.3	1501.6	1596.6	1555.9	1372.7	1101.3	868.0	733.6	644.8	589.1
42.5°	1158.0	1294.8	1442.0	1517.6	1446.9	1221.6	951.2	768.5	657.5	588.2	543.1
45°	1057.5	1202.0	1338.3	1380.3	1253.9	1005.6	769.2	636.7	562.9	511.5	480.3
47.5°	959.3	1101.5	1225.9	1226.6	1055.7	815.5	648.9	551.0	488.0	448.3	425.6
50°	899.3	1034.3	1138.8	1122.6	928.7	725.5	580.3	496.0	443.4	412.7	389.0
52.5°	831.8	962.8	1053.3	1007.0	821.1	638.4	518.8	447.9	404.4	377.8	356.5
55°	733.6	849.9	913.7	843.7	669.8	530.9	438.4	382.8	350.2	327.7	309.5
57.5°	637.2	733.1	773.3	691.6	551.7	440.3	370.9	329.0	296.8	280.7	271.3
60°	576.6	658.6	686.6	596.6	479.7	385.2	328.3	289.5	265.8	255.1	245.8
62.5°	517.1	584.0	595.6	513.0	418.1	337.2	288.3	255.5	239.8	229.6	220.7
65°	429.0	477.2	471.6	405.3	330.8	267.7	232.1	212.0	200.1	185.8	170.1
67.5°	353.2	382.6	364.9	315.2	252.5	208.0	184.7	169.6	154.9	141.2	137.6
70°	305.2	322.1	303.3	257.7	207.0	174.5	155.7	137.6	128.8	125.7	120.1
72.5°	259.2	265.0	244.8	205.7	168.4	144.5	126.2	116.0	111.3	108.7	105.1
75°	194.5	190.1	172.6	141.9	117.0	100.7	95.1	91.3	88.2	85.7	83.8
77.5°	136.6	130.2	114.6	94.5	81.4	73.7	70.3	68.3	66.8	65.5	63.6
80°	102.5	98.2	82.6	67.6	61.9	58.2	56.3	53.8	53.8	52.5	50.6
82.5°	75.0	70.1	56.6	49.5	46.4	44.1	42.8	41.3	40.8	41.0	39.7
85°	39.4	31.9	28.2	26.9	25.0	23.8	24.4	23.1	23.1	23.1	22.5
87.5°	12.4	10.3	10.1	10.0	10.7	11.0	10.7	10.9	11.7	11.3	12.0
90°	2.4	4.0	5.7	7.3	8.7	9.9	11.1	12.3	13.5	14.2	15.0
92.5°	13.5	13.3	13.2	13.0	13.3	13.9	14.4	15.1	15.6	16.0	16.4
95°	38.9	33.9	29.0	24.0	22.1	23.2	24.2	25.3	26.3	27.1	27.8
97.5°	73.0	59.1	45.1	31.2	25.4	27.9	30.3	32.8	35.2	35.8	36.4
100°	98.8	78.3	57.8	37.2	28.3	30.8	33.4	35.9	38.5	39.6	40.8
102.5°	150.6	146.3	141.9	137.5	124.7	103.4	82.1	60.8	39.5	41.1	42.6
105°	209.4	214.0	218.5	222.9	204.7	163.8	122.9	82.0	41.1	42.8	44.4
107.5°	265.6	269.3	272.9	276.5	253.8	204.7	155.7	106.6	57.6	55.9	54.2
110°	301.8	305.0	308.1	311.2	291.2	247.9	204.6	161.3	118.0	103.0	88.0



TEST NUMBER: P331717-830

CATALOG NUMBER: SA2XXRDIP-C865D725U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	336.0	338.7	341.6	344.3	340.4	329.7	319.0	308.3	297.6	243.0	188.3
115°	390.2	392.8	395.3	397.8	401.1	404.7	408.5	412.3	416.0	346.7	277.3
117.5°	439.2	442.1	444.9	447.7	450.4	453.1	455.6	458.2	460.8	444.0	427.3
120°	474.2	476.5	478.7	481.0	483.4	486.2	488.8	491.5	494.2	496.0	497.9
122.5°	504.5	506.9	509.3	511.6	514.3	517.3	520.2	523.1	526.0	527.1	528.2
125°	550.1	552.0	554.0	555.9	558.4	561.2	564.0	566.8	569.8	570.8	571.8
127.5°	592.0	594.2	596.3	598.4	600.6	602.8	604.8	607.0	609.1	610.7	612.2
130°	618.7	621.0	623.4	625.8	627.8	629.5	631.1	632.8	634.4	636.1	637.7
132.5°	645.3	647.3	649.3	651.4	653.2	654.9	656.5	658.2	659.8	661.2	662.6
135°	680.7	683.1	685.5	687.9	689.8	691.1	692.4	693.8	695.1	696.6	698.1
137.5°	715.4	717.1	718.8	720.5	722.1	723.6	725.1	726.6	728.2	729.6	731.1
140°	738.1	739.3	740.6	741.7	743.2	744.8	746.5	748.1	749.8	751.1	752.4
142.5°	757.4	758.6	759.6	760.6	762.1	764.0	765.9	767.8	769.7	770.9	772.1
145°	786.6	786.6	786.4	786.3	787.4	789.9	792.5	795.0	797.6	798.7	799.7
147.5°	812.8	812.3	811.7	811.2	812.1	814.6	817.1	819.6	822.2	822.9	823.7
150°	829.6	828.6	827.6	826.4	827.2	829.5	831.9	834.3	836.7	837.6	838.5
152.5°	844.0	842.9	841.7	840.6	841.1	843.4	845.6	847.9	850.2	851.1	852.0
155°	865.1	863.7	862.3	861.0	861.2	863.0	864.8	866.6	868.4	869.3	870.2
157.5°	881.8	880.7	879.6	878.4	878.4	879.8	881.0	882.2	883.5	884.6	885.5
160°	891.7	890.9	889.9	889.1	889.1	889.9	890.9	891.7	892.7	893.6	894.5
162.5°	900.4	899.6	898.6	897.7	897.7	898.4	899.2	900.0	900.8	901.8	902.8
165°	912.0	911.2	910.2	909.3	909.1	909.6	910.0	910.4	910.9	911.9	912.9
167.5°	920.7	919.7	918.9	917.9	917.7	918.1	918.5	919.0	919.4	920.4	921.5
170°	925.5	924.6	923.7	922.8	922.5	922.8	923.1	923.4	923.7	924.7	925.8
172.5°	928.7	927.8	926.9	926.0	925.8	926.0	926.3	926.6	926.9	928.0	929.1
175°	932.7	931.7	930.7	929.6	929.3	929.5	929.8	930.1	930.5	931.5	932.6
177.5°	933.7	932.8	932.0	931.1	930.8	930.9	931.0	931.1	931.2	932.1	932.9
180°	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8



TEST NUMBER: P331717-830

CATALOG NUMBER: SA2XXRDIP-C865D725U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9
2.5°	1862.9	1869.4	1872.4	1872.4	1875.9	1874.4	1872.9
5°	1970.0	1981.9	1984.3	1995.6	2003.8	2001.2	2002.5
7.5°	2076.4	2095.6	2114.4	2123.1	2124.4	2129.4	2131.3
10°	2141.9	2157.6	2187.0	2182.6	2204.5	2217.0	2196.3
12.5°	2205.0	2226.1	2246.6	2252.1	2264.6	2268.5	2260.4
15°	2262.0	2273.3	2274.5	2271.4	2275.1	2272.0	2260.1
17.5°	2208.8	2190.5	2153.4	2135.9	2122.0	2101.6	2093.3
20°	2120.7	2066.9	2004.3	1979.3	1949.9	1892.4	1906.2
22.5°	1930.6	1869.3	1806.8	1733.7	1698.8	1644.3	1641.0
25°	1634.7	1529.1	1412.8	1331.4	1283.9	1229.5	1205.7
27.5°	1271.0	1137.9	1042.6	994.4	950.5	907.3	905.6
30°	1031.9	931.8	858.0	816.7	789.9	771.8	775.5
32.5°	869.8	801.3	751.5	717.2	697.3	683.6	683.4
35°	711.1	664.1	632.3	617.8	603.5	593.5	594.1
37.5°	608.5	580.3	562.6	546.7	537.7	532.8	530.1
40°	556.0	532.8	519.1	509.7	502.2	495.3	494.1
42.5°	514.4	495.3	481.5	474.2	467.1	462.3	461.0
45°	456.6	440.9	428.4	420.3	417.2	412.7	412.7
47.5°	406.1	390.8	381.0	375.9	370.5	367.6	367.5
50°	372.1	360.2	351.5	348.4	343.9	342.0	341.5
52.5°	341.6	332.7	326.5	324.3	322.4	320.1	320.5
55°	300.2	295.2	292.7	290.8	287.7	283.9	286.4
57.5°	265.3	261.0	254.3	248.4	245.5	242.9	243.9
60°	240.8	232.1	223.3	216.4	214.5	208.9	208.9
62.5°	209.7	197.5	186.7	182.9	181.0	178.3	177.9
65°	161.4	156.4	153.8	151.4	150.1	150.1	148.8
67.5°	133.7	131.7	128.9	128.4	127.1	126.7	126.3
70°	118.2	115.6	114.4	113.9	112.5	113.2	111.3
72.5°	103.2	101.2	100.9	99.3	98.6	98.7	97.3
75°	81.3	81.3	80.7	80.0	78.8	78.1	78.8
77.5°	62.6	62.7	61.5	61.5	61.3	61.5	60.8
80°	50.0	50.6	50.0	49.4	48.8	49.4	48.8
82.5°	39.5	38.6	38.5	38.4	38.3	37.9	37.8
85°	22.5	23.1	22.5	21.9	21.9	21.9	22.5
87.5°	11.7	11.8	11.9	12.0	12.1	12.1	11.7
90°	15.7	16.5	17.0	17.3	17.6	17.9	18.2
92.5°	16.8	17.2	17.5	17.6	17.8	18.0	18.2
95°	28.6	29.3	29.6	29.4	29.3	29.1	29.0
97.5°	36.9	37.6	38.0	38.2	38.4	38.5	38.7
100°	42.0	43.3	44.0	44.3	44.6	44.9	45.1
102.5°	44.2	45.7	46.8	47.1	47.6	48.0	48.4
105°	46.1	47.7	48.8	49.5	50.0	50.6	51.3
107.5°	52.5	50.9	50.3	50.9	51.6	52.1	52.7
110°	73.0	58.1	50.9	51.5	52.0	52.7	53.3



TEST NUMBER: P331717-830

CATALOG NUMBER: SA2XXRDIP-C865D725U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	133.7	79.0	51.8	52.4	52.9	53.3	53.8
115°	207.9	138.6	98.4	87.7	76.8	66.1	55.3
117.5°	410.4	393.6	367.5	332.1	296.6	261.2	225.7
120°	499.6	501.4	492.2	471.9	451.8	431.5	411.3
122.5°	529.2	530.4	529.0	525.0	521.0	517.2	513.2
125°	572.9	573.9	574.7	575.1	575.6	576.0	576.5
127.5°	613.7	615.2	616.0	616.1	616.2	616.3	616.4
130°	639.4	641.0	641.8	641.7	641.5	641.3	641.2
132.5°	664.0	665.4	666.1	665.9	665.8	665.6	665.4
135°	699.6	701.2	701.7	701.4	701.2	700.8	700.5
137.5°	732.5	734.1	734.5	734.1	733.5	733.0	732.4
140°	753.8	755.2	755.4	754.7	753.9	753.2	752.4
142.5°	773.4	774.6	774.9	774.1	773.4	772.6	771.8
145°	800.8	801.8	801.9	801.3	800.5	799.7	799.0
147.5°	824.5	825.3	825.4	824.7	824.1	823.5	822.8
150°	839.4	840.3	840.4	839.6	838.9	838.1	837.4
152.5°	852.9	853.8	853.8	852.8	851.8	850.8	849.8
155°	871.1	872.0	871.9	870.6	869.5	868.3	867.0
157.5°	886.6	887.6	887.5	886.4	885.1	884.0	882.9
160°	895.4	896.3	896.2	895.1	894.1	893.1	892.0
162.5°	903.8	904.8	904.7	903.4	902.1	900.9	899.6
165°	914.1	915.1	915.1	914.1	912.9	911.9	910.9
167.5°	922.6	923.6	923.4	922.1	920.8	919.4	918.0
170°	926.8	927.9	927.7	926.4	925.0	923.7	922.4
172.5°	930.1	931.1	930.9	929.6	928.3	926.9	925.6
175°	933.6	934.6	934.4	932.9	931.4	929.9	928.4
177.5°	933.8	934.6	934.5	933.4	932.4	931.2	930.2
180°	931.8	931.8	931.8	931.8	931.8	931.8	931.8

(END OF REPORT)