

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333166-940

Luminaire Tested: **S125DIP-S610D365U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333166-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S610D365U940-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3535.0 lumens  
Efficiency: N/A  
Efficacy: 128.5 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 27.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333166-940

CATALOG NUMBER: S125DIP-S610D365U940-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333166-940

CATALOG NUMBER: S125DIP-S610D365U940-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68	63
1	101	96	92	89	94	90	87	84	79	77	74	69	67	66	60	59	57	53
2	92	84	78	72	86	79	73	69	70	65	62	61	58	55	53	50	48	44
3	84	74	66	60	78	69	63	57	61	56	52	54	50	46	47	44	41	37
4	76	65	57	51	71	62	54	49	55	49	44	48	43	40	42	38	35	32
5	70	58	50	44	66	55	48	42	49	43	38	43	38	34	38	34	31	28
6	65	52	44	38	61	50	42	36	44	38	33	39	34	30	34	30	27	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	27	31	27	24	22
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	19
9	52	39	32	27	49	37	30	26	34	28	24	30	25	22	27	23	20	17
10	49	36	29	24	46	34	28	23	31	25	21	28	23	20	25	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5531	5531	5531
5°	5544	5490	5525
10°	5509	5452	5483
15°	5449	5386	5409
20°	5364	5294	5304
25°	5273	5185	5181
30°	5158	5068	5043
35°	5037	4941	4872
40°	4912	4804	4736
45°	4778	4678	4585
50°	4629	4527	4391
55°	4486	4355	4234
60°	4314	4184	4035
65°	4109	3976	3842
70°	3914	3737	3609
75°	3566	3449	3331
80°	3172	3124	3046
85°	2764	2808	2660



TEST NUMBER: P333166-940

CATALOG NUMBER: S125DIP-S610D365U940-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	80.7	2.3
10°-20°	228.1	6.5
20°-30°	336.8	9.5
30°-40°	393.0	11.1
40°-50°	394.7	11.2
50°-60°	346.5	9.8
60°-70°	258.2	7.3
70°-80°	147.6	4.2
80°-90°	43.8	1.2
90°-100°	15.5	0.4
100°-110°	95.2	2.7
110°-120°	172.7	4.9
120°-130°	221.7	6.3
130°-140°	238.4	6.7
140°-150°	223.8	6.3
150°-160°	181.0	5.1
160°-170°	117.1	3.3
170°-180°	40.4	1.1
0°-30°	645.6	18.3
0°-40°	1038.6	29.4
0°-60°	1779.7	50.3
0°-90°	2229.3	63.1
90°-120°	283.4	8.0
90°-150°	967.3	27.4
90°-180°	1306.0	36.9
0°-180°	3535.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	856	856	856	856	856	
5°	855	853	847	853	852	81
15°	815	813	806	809	809	230
25°	740	736	728	729	727	340
35°	639	636	627	623	618	399
45°	523	520	512	504	502	403
55°	398	396	387	381	376	356
65°	269	267	260	254	251	267
75°	143	142	138	136	134	152
85°	37	38	38	37	36	42
90°	0	3	5	7	8	3
95°	18	16	5	6	7	23
105°	93	94	94	94	94	98
115°	174	176	176	175	173	172
125°	247	250	250	248	247	221
135°	309	310	310	309	307	238
145°	358	358	358	359	357	224
155°	394	392	393	394	391	181
165°	416	414	414	416	414	117
175°	425	424	424	426	423	40
180°	425	425	425	425	425	



TEST NUMBER: P333166-940

CATALOG NUMBER: S125DIP-S610D365U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4
2.5°	858.5	858.2	857.8	857.5	857.1	856.3	855.2	853.9	852.7	851.5	852.7
5°	855.1	854.7	854.4	854.1	853.8	852.9	851.4	849.9	848.4	846.9	848.3
7.5°	847.1	846.9	846.6	846.2	846.0	845.0	843.3	841.7	840.0	838.4	839.6
10°	840.1	839.8	839.5	839.2	838.9	837.9	836.2	834.6	832.9	831.3	832.5
12.5°	831.4	830.9	830.4	829.8	829.3	828.2	826.7	825.2	823.6	822.1	823.0
15°	815.0	814.6	814.1	813.7	813.2	812.2	810.6	808.9	807.2	805.6	806.3
17.5°	796.2	795.6	794.9	794.2	793.5	792.4	790.7	788.9	787.2	785.5	786.4
20°	780.5	780.2	779.9	779.6	779.3	778.2	776.2	774.3	772.3	770.3	771.4
22.5°	764.7	764.2	763.7	763.1	762.6	761.4	759.6	757.8	755.9	754.0	754.7
25°	739.9	739.0	738.3	737.6	736.8	735.5	733.5	731.6	729.6	727.6	728.0
27.5°	710.7	710.2	709.8	709.4	708.9	707.7	705.6	703.6	701.6	699.6	699.6
30°	691.7	691.3	690.8	690.4	689.9	688.6	686.3	684.0	681.8	679.6	679.2
32.5°	671.1	670.5	669.8	669.1	668.3	667.0	665.0	663.0	660.9	659.0	658.4
35°	638.9	638.3	637.7	637.1	636.5	635.2	633.0	630.9	628.8	626.7	626.0
37.5°	605.4	604.7	604.0	603.2	602.4	601.0	599.1	597.1	595.0	593.1	592.0
40°	582.6	581.9	581.1	580.4	579.6	578.2	576.1	574.0	571.9	569.8	568.5
42.5°	558.3	557.7	557.0	556.3	555.7	554.4	552.2	550.2	548.0	545.9	544.7
45°	523.1	522.5	521.8	521.2	520.7	519.4	517.6	515.9	514.0	512.2	510.4
47.5°	485.1	485.1	485.2	485.2	485.2	484.1	482.0	479.8	477.7	475.5	473.7
50°	460.7	460.2	459.8	459.3	458.9	457.8	455.9	454.1	452.4	450.6	448.6
52.5°	435.8	435.4	435.2	434.8	434.4	433.3	431.4	429.4	427.6	425.6	423.9
55°	398.4	397.9	397.4	397.0	396.5	395.3	393.2	391.1	389.0	386.8	385.5
57.5°	358.9	358.7	358.5	358.2	358.0	357.0	355.2	353.4	351.6	349.9	348.1
60°	334.0	333.4	332.8	332.2	331.6	330.5	328.9	327.2	325.5	323.9	322.4
62.5°	308.0	307.6	307.0	306.6	306.0	305.1	303.7	302.3	300.9	299.4	297.8
65°	268.9	268.7	268.4	268.0	267.8	266.8	265.1	263.5	261.8	260.2	258.8
67.5°	231.1	230.5	229.9	229.3	228.6	227.7	226.5	225.2	224.0	222.7	221.6
70°	207.3	206.6	205.8	205.1	204.3	203.2	201.9	200.5	199.2	197.9	196.9
72.5°	181.3	180.7	180.3	179.8	179.2	178.5	177.7	176.8	175.9	175.0	174.1
75°	142.9	142.7	142.3	142.0	141.8	141.2	140.4	139.7	138.9	138.2	137.8
77.5°	107.6	107.5	107.4	107.2	107.1	106.8	106.4	106.0	105.6	105.1	104.9
80°	85.3	85.3	85.3	85.3	85.3	85.2	84.9	84.6	84.4	84.0	83.8
82.5°	65.9	65.6	65.4	65.1	64.9	64.7	64.6	64.6	64.6	64.5	64.2
85°	37.3	37.5	37.5	37.7	37.9	37.9	37.9	37.9	37.9	37.9	37.8
87.5°	14.7	14.8	14.9	15.1	15.2	15.2	15.2	15.2	15.2	15.1	15.2
90°	0.4	0.9	1.4	2.0	2.6	3.1	3.6	4.1	4.5	5.1	5.4
92.5°	4.8	4.5	4.1	3.7	3.3	3.3	3.7	4.2	4.6	5.1	5.4
95°	17.9	17.7	17.6	17.3	17.1	15.7	13.0	10.3	7.7	5.1	5.4
97.5°	37.5	37.9	38.3	38.6	39.1	36.6	31.3	26.0	20.8	15.5	13.6
100°	52.6	52.9	53.1	53.2	53.5	53.7	54.0	54.3	54.6	54.8	44.4
102.5°	68.0	68.3	68.6	68.8	69.1	69.3	69.5	69.6	69.8	70.0	68.0
105°	92.6	92.9	93.3	93.5	93.8	93.9	93.9	93.9	93.9	93.9	93.9
107.5°	118.2	118.2	118.2	118.2	118.2	118.3	118.5	118.6	118.8	118.9	118.9
110°	134.9	134.9	134.9	134.9	134.9	135.0	135.1	135.3	135.4	135.5	135.4



TEST NUMBER: P333166-940

CATALOG NUMBER: S125DIP-S610D365U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	150.5	150.7	150.9	151.1	151.2	151.3	151.4	151.5	151.6	151.7	151.4
115°	174.0	174.3	174.7	175.0	175.4	175.6	175.7	175.8	175.8	175.8	175.6
117.5°	198.2	198.2	198.2	198.2	198.2	198.3	198.6	198.9	199.1	199.4	199.0
120°	213.4	213.3	213.3	213.2	213.1	213.2	213.4	213.6	213.8	214.0	213.9
122.5°	226.8	227.0	227.3	227.6	227.8	228.0	228.1	228.2	228.3	228.4	228.3
125°	247.4	247.9	248.4	248.9	249.4	249.7	249.7	249.7	249.7	249.7	249.3
127.5°	267.2	267.5	267.9	268.2	268.6	268.8	268.7	268.7	268.6	268.6	268.4
130°	279.3	279.6	280.0	280.4	280.7	280.9	281.0	281.0	281.1	281.2	281.0
132.5°	291.4	291.8	292.2	292.6	293.0	293.1	293.0	292.8	292.7	292.5	292.5
135°	308.6	309.0	309.4	309.9	310.2	310.4	310.2	310.1	310.0	309.9	309.7
137.5°	324.4	324.8	325.1	325.5	325.8	326.0	325.8	325.7	325.6	325.5	325.5
140°	334.7	334.9	335.0	335.2	335.3	335.4	335.3	335.2	335.1	335.1	335.2
142.5°	344.1	344.2	344.3	344.3	344.4	344.5	344.6	344.7	344.8	344.9	344.9
145°	357.8	357.9	358.0	358.2	358.3	358.4	358.4	358.4	358.4	358.4	358.5
147.5°	369.7	369.7	369.7	369.6	369.6	369.6	369.7	369.8	369.9	370.0	370.1
150°	377.3	377.2	377.0	376.8	376.7	376.7	376.8	377.0	377.2	377.3	377.5
152.5°	384.6	384.3	384.0	383.7	383.3	383.3	383.4	383.6	383.7	383.9	384.0
155°	394.0	393.6	393.2	392.7	392.4	392.2	392.4	392.4	392.6	392.7	393.0
157.5°	401.3	401.0	400.7	400.5	400.3	400.1	400.1	400.2	400.2	400.2	400.4
160°	406.3	405.9	405.5	405.0	404.7	404.5	404.5	404.6	404.7	404.7	405.0
162.5°	410.4	409.9	409.5	409.0	408.7	408.5	408.6	408.6	408.7	408.8	409.1
165°	415.7	415.4	414.9	414.5	414.1	413.9	413.9	414.0	414.1	414.2	414.6
167.5°	419.8	419.4	418.9	418.5	418.0	417.9	417.9	418.0	418.1	418.1	418.7
170°	422.0	421.6	421.1	420.6	420.1	419.9	420.0	420.0	420.1	420.2	420.7
172.5°	423.6	423.1	422.6	422.1	421.6	421.4	421.5	421.7	421.8	422.0	422.4
175°	425.2	424.8	424.4	423.9	423.6	423.4	423.4	423.5	423.6	423.7	424.2
177.5°	426.0	425.6	425.3	425.0	424.6	424.5	424.5	424.6	424.6	424.7	425.1
180°	425.2	425.2	425.2	425.2	425.2	425.2	425.2	425.2	425.2	425.2	425.2



TEST NUMBER: P333166-940

CATALOG NUMBER: S125DIP-S610D365U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4
2.5°	853.9	855.2	856.3	856.8	856.8	856.6	856.5	856.4
5°	849.6	851.0	852.3	852.9	852.7	852.7	852.5	852.3
7.5°	841.0	842.3	843.6	844.3	844.1	843.9	843.8	843.6
10°	833.7	834.9	836.2	836.7	836.5	836.3	836.2	836.1
12.5°	824.0	825.0	825.9	826.4	826.3	826.3	826.3	826.3
15°	807.1	807.8	808.6	809.0	809.0	809.0	809.0	809.0
17.5°	787.4	788.3	789.3	789.3	788.5	787.8	787.1	786.3
20°	772.4	773.5	774.5	774.7	773.9	773.2	772.4	771.7
22.5°	755.5	756.2	756.9	757.0	756.4	755.9	755.4	754.9
25°	728.3	728.5	728.9	728.8	728.3	727.9	727.5	727.0
27.5°	699.7	699.8	699.8	699.6	699.2	698.7	698.3	697.9
30°	678.9	678.7	678.3	678.0	677.5	677.1	676.6	676.2
32.5°	657.9	657.3	656.7	656.1	655.3	654.5	653.6	652.8
35°	625.2	624.5	623.7	622.7	621.5	620.3	619.1	617.9
37.5°	590.8	589.8	588.6	587.7	587.0	586.4	585.7	585.0
40°	567.0	565.7	564.4	563.5	563.0	562.6	562.1	561.7
42.5°	543.5	542.2	541.0	540.0	539.3	538.7	538.0	537.3
45°	508.5	506.8	505.0	503.8	503.4	502.9	502.5	502.0
47.5°	471.8	469.9	468.1	466.7	465.7	464.6	463.5	462.4
50°	446.7	444.7	442.7	441.2	440.1	439.1	438.0	437.0
52.5°	422.1	420.4	418.7	417.3	416.2	414.9	413.8	412.6
55°	384.1	382.8	381.5	380.2	379.2	378.1	377.1	376.0
57.5°	346.3	344.6	342.9	341.7	341.2	340.5	340.0	339.5
60°	320.8	319.3	317.8	316.6	315.5	314.4	313.3	312.4
62.5°	296.2	294.6	292.9	291.8	291.0	290.1	289.3	288.5
65°	257.4	256.1	254.8	253.8	253.2	252.5	252.0	251.4
67.5°	220.5	219.4	218.2	217.4	217.0	216.7	216.3	216.0
70°	196.0	195.1	194.2	193.5	192.9	192.3	191.6	191.1
72.5°	173.0	172.0	170.9	170.1	169.5	169.0	168.4	167.7
75°	137.3	136.9	136.4	135.9	135.3	134.6	134.1	133.5
77.5°	104.6	104.3	104.1	103.7	103.3	102.9	102.5	102.0
80°	83.7	83.6	83.4	83.2	82.8	82.6	82.3	81.9
82.5°	63.9	63.7	63.4	63.2	63.2	63.1	63.0	63.0
85°	37.6	37.5	37.4	37.1	36.8	36.5	36.2	35.9
87.5°	15.2	15.3	15.3	15.3	15.2	14.9	14.7	14.5
90°	5.7	6.1	6.4	6.7	7.0	7.1	7.3	7.6
92.5°	5.7	6.1	6.4	6.7	6.8	6.9	7.0	7.0
95°	5.7	6.1	6.4	6.6	6.6	6.6	6.6	6.6
97.5°	11.6	9.5	7.6	6.6	6.6	6.6	6.6	6.6
100°	34.0	23.5	13.1	7.8	7.5	7.2	6.9	6.6
102.5°	66.0	64.0	62.1	58.7	53.9	49.2	44.4	39.7
105°	93.9	93.9	93.9	93.9	93.8	93.7	93.7	93.6
107.5°	119.0	119.0	119.0	118.9	118.7	118.4	118.2	118.0
110°	135.1	134.9	134.7	134.6	134.7	134.7	134.8	134.9





TEST NUMBER: P333166-940

CATALOG NUMBER: S125DIP-S610D365U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	151.1	150.9	150.6	150.4	150.3	150.3	150.2	150.1
115°	175.3	175.0	174.8	174.4	174.0	173.6	173.2	172.7
117.5°	198.7	198.3	198.0	197.7	197.5	197.3	197.2	197.0
120°	213.7	213.6	213.5	213.2	212.9	212.5	212.1	211.8
122.5°	228.1	228.0	227.8	227.6	227.1	226.8	226.3	226.0
125°	249.1	248.8	248.5	248.3	248.1	247.9	247.6	247.4
127.5°	268.2	268.0	268.0	267.6	267.1	266.5	266.1	265.6
130°	280.7	280.5	280.4	280.0	279.7	279.4	279.0	278.7
132.5°	292.4	292.4	292.3	292.1	291.8	291.4	291.1	290.8
135°	309.6	309.4	309.2	309.0	308.6	308.2	307.7	307.3
137.5°	325.6	325.6	325.6	325.4	325.0	324.7	324.3	324.0
140°	335.4	335.5	335.6	335.5	335.1	334.7	334.2	333.8
142.5°	344.9	345.0	345.0	344.8	344.4	343.9	343.6	343.1
145°	358.6	358.6	358.6	358.5	358.1	357.7	357.2	356.8
147.5°	370.1	370.2	370.3	370.1	369.6	369.1	368.6	368.1
150°	377.6	377.7	377.8	377.6	377.1	376.6	375.9	375.4
152.5°	384.1	384.2	384.4	384.2	383.7	383.3	382.7	382.2
155°	393.2	393.3	393.6	393.4	392.9	392.3	391.7	391.2
157.5°	400.6	400.8	401.1	400.9	400.4	399.8	399.2	398.7
160°	405.3	405.6	405.8	405.7	405.1	404.6	404.0	403.5
162.5°	409.6	409.9	410.4	410.2	409.6	408.9	408.4	407.8
165°	415.0	415.4	415.9	415.8	415.3	414.6	414.1	413.6
167.5°	419.2	419.6	420.2	420.1	419.5	418.8	418.2	417.6
170°	421.2	421.9	422.4	422.4	421.8	421.2	420.4	419.8
172.5°	422.9	423.5	423.9	423.9	423.3	422.6	422.0	421.3
175°	424.7	425.3	425.9	425.9	425.2	424.5	423.9	423.3
177.5°	425.5	425.9	426.2	426.2	425.8	425.3	424.9	424.5
180°	425.2	425.2	425.2	425.2	425.2	425.2	425.2	425.2

(END OF REPORT)