

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333175-940

Luminaire Tested: **S125DIP-S610D590U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333175-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S610D590U940-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4337.4 lumens
Efficiency: N/A
Efficacy: 132.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333175-940

CATALOG NUMBER: S125DIP-S610D590U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333175-940

CATALOG NUMBER: S125DIP-S610D590U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	86	90	87	83	80	74	71	69	62	60	58	51	49	48	43
2	89	82	76	70	82	76	70	66	65	60	57	54	51	49	45	42	41	36
3	81	72	64	59	75	67	60	55	57	52	48	48	44	41	39	37	35	31
4	74	64	56	50	68	59	52	47	51	45	41	43	39	35	35	32	30	26
5	68	57	48	42	63	53	45	40	45	40	35	38	34	31	32	29	26	23
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	25	23	20
7	58	46	38	32	54	43	36	30	37	31	27	31	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16
9	50	38	30	25	46	36	29	24	31	25	22	26	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	21	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5531	5531	5531
5°	5544	5490	5525
10°	5509	5452	5483
15°	5449	5386	5409
20°	5364	5294	5304
25°	5273	5185	5181
30°	5158	5068	5043
35°	5037	4941	4872
40°	4912	4804	4736
45°	4778	4678	4585
50°	4629	4527	4391
55°	4486	4355	4234
60°	4314	4184	4035
65°	4109	3976	3842
70°	3914	3737	3609
75°	3566	3449	3331
80°	3172	3124	3046
85°	2764	2808	2660



TEST NUMBER: P333175-940

CATALOG NUMBER: S125DIP-S610D590U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.7	1.9
10°-20°	228.1	5.3
20°-30°	336.8	7.8
30°-40°	393.0	9.1
40°-50°	394.7	9.1
50°-60°	346.5	8.0
60°-70°	258.2	6.0
70°-80°	147.6	3.4
80°-90°	44.4	1.0
90°-100°	24.9	0.6
100°-110°	153.7	3.5
110°-120°	278.8	6.4
120°-130°	357.8	8.2
130°-140°	384.8	8.9
140°-150°	361.2	8.3
150°-160°	292.2	6.7
160°-170°	189.0	4.4
170°-180°	65.2	1.5
0°-30°	645.6	14.9
0°-40°	1038.6	23.9
0°-60°	1779.7	41.0
0°-90°	2229.8	51.4
90°-120°	457.4	10.5
90°-150°	1561.2	36.0
90°-180°	2108.0	48.6
0°-180°	4337.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	856	856	856	856	856	
5°	855	853	847	853	852	81
15°	815	813	806	809	809	230
25°	740	736	728	729	727	340
35°	639	636	627	623	618	399
45°	523	520	512	504	502	403
55°	398	396	387	381	376	356
65°	269	267	260	254	251	267
75°	143	142	138	136	134	152
85°	37	38	38	37	36	42
90°	0	5	8	11	12	3
95°	29	26	8	11	11	37
105°	150	152	152	152	151	159
115°	281	283	284	282	279	278
125°	399	403	403	401	399	357
135°	498	501	500	499	496	384
145°	578	578	578	579	576	361
155°	636	633	634	635	631	293
165°	671	668	668	671	667	189
175°	686	683	684	687	683	65
180°	686	686	686	686	686	



TEST NUMBER: P333175-940

CATALOG NUMBER: S125DIP-S610D590U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4
2.5°	858.5	858.2	857.8	857.5	857.1	856.3	855.2	853.9	852.7	851.5	852.7
5°	855.1	854.7	854.4	854.1	853.8	852.9	851.4	849.9	848.4	846.9	848.3
7.5°	847.1	846.9	846.6	846.2	846.0	845.0	843.3	841.7	840.0	838.4	839.6
10°	840.1	839.8	839.5	839.2	838.9	837.9	836.2	834.6	832.9	831.3	832.5
12.5°	831.4	830.9	830.4	829.8	829.3	828.2	826.7	825.2	823.6	822.1	823.0
15°	815.0	814.6	814.1	813.7	813.2	812.2	810.6	808.9	807.2	805.6	806.3
17.5°	796.2	795.6	794.9	794.2	793.5	792.4	790.7	788.9	787.2	785.5	786.4
20°	780.5	780.2	779.9	779.6	779.3	778.2	776.2	774.3	772.3	770.3	771.4
22.5°	764.7	764.2	763.7	763.1	762.6	761.4	759.6	757.8	755.9	754.0	754.7
25°	739.9	739.0	738.3	737.6	736.8	735.5	733.5	731.6	729.6	727.6	728.0
27.5°	710.7	710.2	709.8	709.4	708.9	707.7	705.6	703.6	701.6	699.6	699.6
30°	691.7	691.3	690.8	690.4	689.9	688.6	686.3	684.0	681.8	679.6	679.2
32.5°	671.1	670.5	669.8	669.1	668.3	667.0	665.0	663.0	660.9	659.0	658.4
35°	638.9	638.3	637.7	637.1	636.5	635.2	633.0	630.9	628.8	626.7	626.0
37.5°	605.4	604.7	604.0	603.2	602.4	601.0	599.1	597.1	595.0	593.1	592.0
40°	582.6	581.9	581.1	580.4	579.6	578.2	576.1	574.0	571.9	569.8	568.5
42.5°	558.3	557.7	557.0	556.3	555.7	554.4	552.2	550.2	548.0	545.9	544.7
45°	523.1	522.5	521.8	521.2	520.7	519.4	517.6	515.9	514.0	512.2	510.4
47.5°	485.1	485.1	485.2	485.2	485.2	484.1	482.0	479.8	477.7	475.5	473.7
50°	460.7	460.2	459.8	459.3	458.9	457.8	455.9	454.1	452.4	450.6	448.6
52.5°	435.8	435.4	435.2	434.8	434.4	433.3	431.4	429.4	427.6	425.6	423.9
55°	398.4	397.9	397.4	397.0	396.5	395.3	393.2	391.1	389.0	386.8	385.5
57.5°	358.9	358.7	358.5	358.2	358.0	357.0	355.2	353.4	351.6	349.9	348.1
60°	334.0	333.4	332.8	332.2	331.6	330.5	328.9	327.2	325.5	323.9	322.4
62.5°	308.0	307.6	307.0	306.6	306.0	305.1	303.7	302.3	300.9	299.4	297.8
65°	268.9	268.7	268.4	268.0	267.8	266.8	265.1	263.5	261.8	260.2	258.8
67.5°	231.1	230.5	229.9	229.3	228.6	227.7	226.5	225.2	224.0	222.7	221.6
70°	207.3	206.6	205.8	205.1	204.3	203.2	201.9	200.5	199.2	197.9	196.9
72.5°	181.3	180.7	180.3	179.8	179.2	178.5	177.7	176.8	175.9	175.0	174.1
75°	142.9	142.7	142.3	142.0	141.8	141.2	140.4	139.7	138.9	138.2	137.8
77.5°	107.6	107.5	107.4	107.2	107.1	106.8	106.4	106.0	105.6	105.1	104.9
80°	85.3	85.3	85.3	85.3	85.3	85.2	84.9	84.6	84.4	84.0	83.8
82.5°	65.9	65.6	65.4	65.1	64.9	64.7	64.6	64.6	64.6	64.5	64.2
85°	37.3	37.5	37.5	37.7	37.9	37.9	37.9	37.9	37.9	37.9	37.8
87.5°	14.7	14.9	15.1	15.2	15.4	15.6	15.6	15.6	15.7	15.7	15.9
90°	0.5	1.4	2.3	3.2	4.1	5.0	5.8	6.6	7.3	8.1	8.7
92.5°	7.8	7.2	6.6	6.0	5.3	5.4	6.1	6.8	7.4	8.1	8.7
95°	29.0	28.6	28.4	28.0	27.6	25.3	21.0	16.8	12.4	8.1	8.7
97.5°	60.5	61.2	61.8	62.3	63.0	59.0	50.6	42.0	33.5	25.1	21.8
100°	85.0	85.3	85.6	86.0	86.3	86.7	87.2	87.7	88.1	88.5	71.7
102.5°	109.8	110.2	110.7	111.1	111.5	111.8	112.1	112.4	112.7	113.0	109.8
105°	149.5	150.0	150.5	151.0	151.4	151.6	151.6	151.6	151.6	151.6	151.6
107.5°	190.9	190.9	190.9	190.9	190.9	191.0	191.2	191.5	191.7	191.9	191.9
110°	217.8	217.8	217.8	217.8	217.8	217.8	218.1	218.3	218.6	218.7	218.5



TEST NUMBER: P333175-940

CATALOG NUMBER: S125DIP-S610D590U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	243.0	243.3	243.5	243.8	244.1	244.2	244.4	244.5	244.7	244.8	244.4
115°	280.8	281.4	282.0	282.5	283.1	283.5	283.6	283.7	283.7	283.9	283.5
117.5°	320.0	319.9	319.9	319.9	319.9	320.1	320.6	321.0	321.4	321.8	321.3
120°	344.5	344.3	344.2	344.1	343.9	344.1	344.5	344.7	345.1	345.4	345.2
122.5°	366.0	366.4	366.8	367.3	367.7	368.0	368.2	368.4	368.5	368.6	368.5
125°	399.4	400.2	400.9	401.7	402.5	403.0	403.0	403.0	403.0	403.0	402.5
127.5°	431.2	431.8	432.4	432.9	433.5	433.7	433.6	433.6	433.5	433.5	433.2
130°	450.8	451.3	451.9	452.5	453.0	453.3	453.4	453.6	453.7	453.8	453.4
132.5°	470.3	470.9	471.6	472.3	472.9	473.1	472.9	472.6	472.3	472.2	472.1
135°	498.1	498.7	499.4	500.1	500.8	501.1	500.8	500.5	500.3	500.1	499.9
137.5°	523.6	524.2	524.8	525.4	525.9	526.2	525.9	525.8	525.6	525.3	525.4
140°	540.3	540.6	540.7	541.0	541.2	541.3	541.2	541.0	540.9	540.8	541.0
142.5°	555.4	555.5	555.6	555.8	555.9	556.1	556.2	556.3	556.5	556.7	556.7
145°	577.5	577.7	577.9	578.1	578.4	578.5	578.5	578.5	578.5	578.5	578.5
147.5°	596.7	596.7	596.6	596.6	596.6	596.6	596.7	596.9	597.0	597.2	597.4
150°	608.9	608.8	608.5	608.3	608.1	608.1	608.3	608.5	608.8	608.9	609.2
152.5°	620.8	620.3	619.8	619.3	618.8	618.7	618.8	619.1	619.3	619.6	619.8
155°	636.0	635.3	634.6	633.9	633.2	633.0	633.2	633.5	633.6	633.9	634.3
157.5°	647.6	647.2	646.8	646.4	646.0	645.9	645.9	645.9	645.9	646.0	646.3
160°	655.8	655.1	654.4	653.7	653.1	652.8	652.9	653.0	653.1	653.3	653.7
162.5°	662.3	661.6	660.9	660.2	659.6	659.3	659.4	659.5	659.6	659.8	660.4
165°	671.0	670.4	669.7	669.1	668.3	668.1	668.2	668.2	668.4	668.5	669.1
167.5°	677.5	676.9	676.2	675.5	674.8	674.5	674.6	674.7	674.8	674.9	675.7
170°	681.3	680.5	679.7	678.9	678.1	677.7	677.8	678.0	678.1	678.1	679.0
172.5°	683.7	682.9	682.1	681.3	680.5	680.2	680.4	680.6	680.8	681.0	681.8
175°	686.3	685.6	684.9	684.3	683.6	683.3	683.4	683.6	683.7	683.8	684.7
177.5°	687.5	687.0	686.4	685.9	685.4	685.1	685.2	685.3	685.4	685.5	686.2
180°	686.3	686.3	686.3	686.3	686.3	686.3	686.3	686.3	686.3	686.3	686.3



TEST NUMBER: P333175-940

CATALOG NUMBER: S125DIP-S610D590U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4
2.5°	853.9	855.2	856.3	856.8	856.8	856.6	856.5	856.4
5°	849.6	851.0	852.3	852.9	852.7	852.7	852.5	852.3
7.5°	841.0	842.3	843.6	844.3	844.1	843.9	843.8	843.6
10°	833.7	834.9	836.2	836.7	836.5	836.3	836.2	836.1
12.5°	824.0	825.0	825.9	826.4	826.3	826.3	826.3	826.3
15°	807.1	807.8	808.6	809.0	809.0	809.0	809.0	809.0
17.5°	787.4	788.3	789.3	789.3	788.5	787.8	787.1	786.3
20°	772.4	773.5	774.5	774.7	773.9	773.2	772.4	771.7
22.5°	755.5	756.2	756.9	757.0	756.4	755.9	755.4	754.9
25°	728.3	728.5	728.9	728.8	728.3	727.9	727.5	727.0
27.5°	699.7	699.8	699.8	699.6	699.2	698.7	698.3	697.9
30°	678.9	678.7	678.3	678.0	677.5	677.1	676.6	676.2
32.5°	657.9	657.3	656.7	656.1	655.3	654.5	653.6	652.8
35°	625.2	624.5	623.7	622.7	621.5	620.3	619.1	617.9
37.5°	590.8	589.8	588.6	587.7	587.0	586.4	585.7	585.0
40°	567.0	565.7	564.4	563.5	563.0	562.6	562.1	561.7
42.5°	543.5	542.2	541.0	540.0	539.3	538.7	538.0	537.3
45°	508.5	506.8	505.0	503.8	503.4	502.9	502.5	502.0
47.5°	471.8	469.9	468.1	466.7	465.7	464.6	463.5	462.4
50°	446.7	444.7	442.7	441.2	440.1	439.1	438.0	437.0
52.5°	422.1	420.4	418.7	417.3	416.2	414.9	413.8	412.6
55°	384.1	382.8	381.5	380.2	379.2	378.1	377.1	376.0
57.5°	346.3	344.6	342.9	341.7	341.2	340.5	340.0	339.5
60°	320.8	319.3	317.8	316.6	315.5	314.4	313.3	312.4
62.5°	296.2	294.6	292.9	291.8	291.0	290.1	289.3	288.5
65°	257.4	256.1	254.8	253.8	253.2	252.5	252.0	251.4
67.5°	220.5	219.4	218.2	217.4	217.0	216.7	216.3	216.0
70°	196.0	195.1	194.2	193.5	192.9	192.3	191.6	191.1
72.5°	173.0	172.0	170.9	170.1	169.5	169.0	168.4	167.7
75°	137.3	136.9	136.4	135.9	135.3	134.6	134.1	133.5
77.5°	104.6	104.3	104.1	103.7	103.3	102.9	102.5	102.0
80°	83.7	83.6	83.4	83.2	82.8	82.6	82.3	81.9
82.5°	63.9	63.7	63.4	63.2	63.2	63.1	63.0	63.0
85°	37.6	37.5	37.4	37.1	36.8	36.5	36.2	35.9
87.5°	16.0	16.1	16.1	16.1	16.0	15.8	15.6	15.4
90°	9.3	9.8	10.4	10.9	11.2	11.5	11.9	12.2
92.5°	9.3	9.8	10.4	10.8	10.9	11.1	11.2	11.4
95°	9.3	9.8	10.4	10.7	10.7	10.7	10.7	10.7
97.5°	18.6	15.4	12.3	10.7	10.7	10.7	10.7	10.7
100°	54.8	38.0	21.1	12.5	12.0	11.6	11.1	10.7
102.5°	106.6	103.3	100.2	94.8	87.0	79.4	71.7	64.0
105°	151.6	151.6	151.6	151.6	151.4	151.3	151.2	151.1
107.5°	192.0	192.0	192.0	191.8	191.5	191.2	190.8	190.5
110°	218.1	217.8	217.4	217.3	217.4	217.5	217.7	217.8



TEST NUMBER: P333175-940

CATALOG NUMBER: S125DIP-S610D590U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	244.0	243.5	243.1	242.8	242.6	242.5	242.4	242.2
115°	282.9	282.5	282.0	281.5	280.8	280.2	279.5	278.8
117.5°	320.7	320.0	319.5	319.1	318.8	318.4	318.2	317.9
120°	345.0	344.7	344.6	344.1	343.6	343.0	342.4	341.9
122.5°	368.2	368.0	367.7	367.3	366.7	366.0	365.3	364.7
125°	402.1	401.5	401.1	400.7	400.4	400.0	399.8	399.4
127.5°	432.9	432.7	432.5	431.9	431.1	430.3	429.4	428.6
130°	453.2	452.8	452.5	452.0	451.5	450.8	450.3	449.8
132.5°	472.0	471.9	471.9	471.5	471.0	470.4	469.8	469.3
135°	499.6	499.4	499.2	498.7	498.1	497.4	496.7	496.1
137.5°	525.4	525.5	525.5	525.2	524.7	524.1	523.5	522.9
140°	541.3	541.4	541.7	541.4	540.8	540.1	539.5	538.8
142.5°	556.8	556.8	556.9	556.5	555.9	555.2	554.5	553.8
145°	578.7	578.8	578.9	578.6	577.9	577.3	576.6	575.9
147.5°	597.4	597.6	597.7	597.4	596.6	595.8	594.9	594.1
150°	609.4	609.7	609.8	609.6	608.7	607.7	606.8	605.9
152.5°	620.0	620.3	620.5	620.2	619.4	618.6	617.7	616.9
155°	634.6	634.9	635.3	635.0	634.1	633.2	632.3	631.3
157.5°	646.7	647.0	647.4	647.1	646.2	645.2	644.4	643.5
160°	654.2	654.6	655.1	654.8	653.9	653.0	652.1	651.2
162.5°	661.0	661.6	662.3	662.1	661.1	660.1	659.2	658.1
165°	669.9	670.6	671.2	671.1	670.2	669.3	668.4	667.4
167.5°	676.5	677.3	678.1	678.1	677.1	676.0	675.0	674.0
170°	680.0	680.9	681.8	681.7	680.7	679.7	678.7	677.7
172.5°	682.6	683.5	684.3	684.2	683.1	682.2	681.1	680.1
175°	685.5	686.4	687.4	687.3	686.3	685.3	684.3	683.2
177.5°	686.8	687.4	688.0	688.0	687.2	686.5	685.8	685.1
180°	686.3	686.3	686.3	686.3	686.3	686.3	686.3	686.3

(END OF REPORT)