

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333177-940

Luminaire Tested: **S125DIP-S610D590U940-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333177-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S610D590U940-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4121.8 lumens
Efficiency: N/A
Efficacy: 125.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333177-940

CATALOG NUMBER: S125DIP-S610D590U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333177-940

CATALOG NUMBER: S125DIP-S610D590U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	94	90	87	91	88	84	81	75	72	70	63	62	60	53	52	50	45
2	90	82	76	71	83	76	71	66	66	62	58	56	53	50	46	44	42	38
3	82	72	65	59	76	67	61	56	58	53	49	49	45	42	41	38	36	32
4	75	64	56	50	69	60	53	47	51	46	42	44	40	36	37	34	31	28
5	69	57	49	43	64	53	46	40	46	40	36	39	35	31	33	30	27	24
6	63	51	43	37	59	48	40	35	41	36	31	36	31	28	30	27	24	21
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21	19
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19	17
9	51	38	31	26	47	36	29	24	31	26	22	27	23	20	23	20	17	15
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5531	5531	5531
5°	5544	5490	5525
10°	5509	5452	5483
15°	5449	5386	5409
20°	5364	5294	5304
25°	5273	5185	5181
30°	5158	5068	5043
35°	5037	4941	4872
40°	4912	4804	4736
45°	4778	4678	4585
50°	4629	4527	4391
55°	4486	4355	4234
60°	4314	4184	4035
65°	4109	3976	3842
70°	3914	3737	3609
75°	3566	3449	3331
80°	3172	3124	3046
85°	2764	2808	2660



TEST NUMBER: P333177-940

CATALOG NUMBER: S125DIP-S610D590U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.7	2.0
10°-20°	228.1	5.5
20°-30°	336.8	8.2
30°-40°	393.0	9.5
40°-50°	394.7	9.6
50°-60°	346.5	8.4
60°-70°	258.2	6.3
70°-80°	147.6	3.6
80°-90°	44.3	1.1
90°-100°	182.9	4.4
100°-110°	393.1	9.5
110°-120°	369.0	9.0
120°-130°	299.0	7.3
130°-140°	240.0	5.8
140°-150°	181.1	4.4
150°-160°	127.5	3.1
160°-170°	75.1	1.8
170°-180°	24.4	0.6
0°-30°	645.6	15.7
0°-40°	1038.6	25.2
0°-60°	1779.7	43.2
0°-90°	2229.8	54.1
90°-120°	945.0	22.9
90°-150°	1665.0	40.4
90°-180°	1892.0	45.9
0°-180°	4121.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	856	856	856	856	856	
5°	855	853	847	853	852	81
15°	815	813	806	809	809	230
25°	740	736	728	729	727	340
35°	639	636	627	623	618	399
45°	523	520	512	504	502	403
55°	398	396	387	381	376	356
65°	269	267	260	254	251	267
75°	143	142	138	136	134	152
85°	37	38	38	37	36	42
90°	0	5	8	11	12	3
95°	17	50	451	205	120	18
105°	58	80	369	726	674	61
115°	103	124	296	638	751	101
125°	142	167	284	508	592	126
135°	167	201	282	426	491	129
145°	194	223	283	352	388	122
155°	222	239	276	312	325	102
165°	242	249	264	281	285	68
175°	252	252	254	257	256	24
180°	252	252	252	252	252	



TEST NUMBER: P333177-940

CATALOG NUMBER: S125DIP-S610D590U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4
2.5°	858.5	858.2	857.8	857.5	857.1	856.3	855.2	853.9	852.7	851.5	852.7
5°	855.1	854.7	854.4	854.1	853.8	852.9	851.4	849.9	848.4	846.9	848.3
7.5°	847.1	846.9	846.6	846.2	846.0	845.0	843.3	841.7	840.0	838.4	839.6
10°	840.1	839.8	839.5	839.2	838.9	837.9	836.2	834.6	832.9	831.3	832.5
12.5°	831.4	830.9	830.4	829.8	829.3	828.2	826.7	825.2	823.6	822.1	823.0
15°	815.0	814.6	814.1	813.7	813.2	812.2	810.6	808.9	807.2	805.6	806.3
17.5°	796.2	795.6	794.9	794.2	793.5	792.4	790.7	788.9	787.2	785.5	786.4
20°	780.5	780.2	779.9	779.6	779.3	778.2	776.2	774.3	772.3	770.3	771.4
22.5°	764.7	764.2	763.7	763.1	762.6	761.4	759.6	757.8	755.9	754.0	754.7
25°	739.9	739.0	738.3	737.6	736.8	735.5	733.5	731.6	729.6	727.6	728.0
27.5°	710.7	710.2	709.8	709.4	708.9	707.7	705.6	703.6	701.6	699.6	699.6
30°	691.7	691.3	690.8	690.4	689.9	688.6	686.3	684.0	681.8	679.6	679.2
32.5°	671.1	670.5	669.8	669.1	668.3	667.0	665.0	663.0	660.9	659.0	658.4
35°	638.9	638.3	637.7	637.1	636.5	635.2	633.0	630.9	628.8	626.7	626.0
37.5°	605.4	604.7	604.0	603.2	602.4	601.0	599.1	597.1	595.0	593.1	592.0
40°	582.6	581.9	581.1	580.4	579.6	578.2	576.1	574.0	571.9	569.8	568.5
42.5°	558.3	557.7	557.0	556.3	555.7	554.4	552.2	550.2	548.0	545.9	544.7
45°	523.1	522.5	521.8	521.2	520.7	519.4	517.6	515.9	514.0	512.2	510.4
47.5°	485.1	485.1	485.2	485.2	485.2	484.1	482.0	479.8	477.7	475.5	473.7
50°	460.7	460.2	459.8	459.3	458.9	457.8	455.9	454.1	452.4	450.6	448.6
52.5°	435.8	435.4	435.2	434.8	434.4	433.3	431.4	429.4	427.6	425.6	423.9
55°	398.4	397.9	397.4	397.0	396.5	395.3	393.2	391.1	389.0	386.8	385.5
57.5°	358.9	358.7	358.5	358.2	358.0	357.0	355.2	353.4	351.6	349.9	348.1
60°	334.0	333.4	332.8	332.2	331.6	330.5	328.9	327.2	325.5	323.9	322.4
62.5°	308.0	307.6	307.0	306.6	306.0	305.1	303.7	302.3	300.9	299.4	297.8
65°	268.9	268.7	268.4	268.0	267.8	266.8	265.1	263.5	261.8	260.2	258.8
67.5°	231.1	230.5	229.9	229.3	228.6	227.7	226.5	225.2	224.0	222.7	221.6
70°	207.3	206.6	205.8	205.1	204.3	203.2	201.9	200.5	199.2	197.9	196.9
72.5°	181.3	180.7	180.3	179.8	179.2	178.5	177.7	176.8	175.9	175.0	174.1
75°	142.9	142.7	142.3	142.0	141.8	141.2	140.4	139.7	138.9	138.2	137.8
77.5°	107.6	107.5	107.4	107.2	107.1	106.8	106.4	106.0	105.6	105.1	104.9
80°	85.3	85.3	85.3	85.3	85.3	85.2	84.9	84.6	84.4	84.0	83.8
82.5°	65.9	65.6	65.4	65.1	64.9	64.7	64.6	64.6	64.6	64.5	64.2
85°	37.3	37.5	37.5	37.7	37.9	37.9	37.9	37.9	37.9	37.9	37.8
87.5°	14.7	14.8	15.1	15.2	15.4	15.6	15.6	15.7	15.6	15.7	15.8
90°	0.5	1.0	2.1	3.0	4.1	5.1	5.6	6.6	7.1	8.1	8.6
92.5°	6.2	7.5	11.8	18.1	26.8	41.7	69.5	116.1	166.7	164.0	132.8
95°	16.8	17.3	21.4	26.9	38.2	61.1	115.5	227.4	367.7	450.7	441.0
97.5°	27.9	28.4	31.3	36.9	47.0	63.5	99.5	181.5	328.4	481.3	558.0
100°	35.6	36.6	38.7	44.2	53.9	69.2	98.7	164.8	293.0	459.3	586.5
102.5°	44.1	44.8	46.4	52.4	61.3	76.1	102.4	157.9	266.1	420.6	569.4
105°	57.5	57.5	60.0	65.1	73.2	87.5	109.9	155.2	240.0	368.8	514.8
107.5°	70.5	71.5	73.9	78.1	86.6	99.4	121.1	159.8	229.1	333.1	459.1
110°	79.9	80.9	82.9	87.5	95.1	108.3	129.2	164.3	225.9	316.4	427.3



TEST NUMBER: P333177-940

CATALOG NUMBER: S125DIP-S610D590U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	89.3	90.2	91.8	96.5	104.1	116.9	137.0	170.0	225.9	306.7	403.7
115°	102.7	103.8	105.3	109.9	117.5	130.2	149.0	178.5	227.4	296.0	377.9
117.5°	114.9	116.5	118.2	122.7	131.3	143.7	161.5	188.3	230.7	290.9	362.6
120°	123.1	124.7	126.6	131.3	139.9	152.6	170.4	194.8	234.0	288.4	354.0
122.5°	131.6	132.8	134.4	138.9	148.5	161.1	179.0	202.2	236.8	286.4	346.7
125°	142.4	143.5	146.0	150.5	160.2	173.4	190.2	212.1	241.7	283.8	336.7
127.5°	150.9	152.4	155.7	161.5	171.7	184.9	201.1	221.2	247.0	282.6	327.6
130°	156.1	157.7	161.8	168.4	179.1	192.3	208.0	227.4	250.3	281.8	321.5
132.5°	160.2	162.2	167.0	174.5	185.6	198.8	214.5	232.6	254.0	281.8	316.6
135°	166.8	168.9	175.0	183.2	193.8	207.5	223.3	240.0	258.9	281.8	310.8
137.5°	175.2	176.7	182.4	190.6	201.0	215.2	229.5	245.6	263.5	282.4	305.6
140°	180.0	181.6	187.7	195.8	205.5	219.3	234.0	249.2	265.6	282.9	303.2
142.5°	185.7	186.9	192.6	200.7	210.0	222.9	236.8	251.3	266.7	283.2	301.1
145°	194.3	195.3	200.4	207.5	216.7	228.4	241.7	254.3	268.0	282.9	298.1
147.5°	203.2	203.8	208.2	214.8	222.7	233.1	244.7	256.2	268.6	281.5	294.9
150°	208.6	209.6	213.1	219.7	226.9	235.5	246.7	257.3	268.6	280.3	292.5
152.5°	214.3	214.8	218.0	223.8	230.5	238.4	248.7	258.2	268.1	278.7	289.6
155°	221.8	221.8	224.8	229.9	235.0	242.1	250.7	258.9	267.1	275.7	284.8
157.5°	228.5	228.4	230.9	235.2	239.7	245.0	252.5	259.4	265.7	272.6	280.4
160°	233.0	232.5	234.5	238.1	242.1	246.7	253.3	259.4	264.5	270.6	276.7
162.5°	236.7	236.1	238.2	241.3	244.6	248.3	254.1	259.0	263.3	268.1	273.5
165°	242.1	241.1	242.6	245.1	247.2	250.3	254.3	258.4	261.4	264.5	268.6
167.5°	245.8	245.3	246.2	247.6	249.1	250.9	254.3	257.2	258.6	260.9	263.8
170°	248.3	247.7	248.3	249.2	250.3	251.8	254.3	256.4	257.3	258.9	260.9
172.5°	249.9	249.0	249.4	250.5	251.1	251.8	254.0	255.6	255.7	256.5	258.1
175°	251.8	250.7	251.3	251.8	251.8	251.8	253.3	254.3	253.8	253.8	254.3
177.5°	252.7	251.9	251.9	252.3	251.9	251.9	252.7	253.1	252.3	252.3	252.7
180°	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3



TEST NUMBER: P333177-940

CATALOG NUMBER: S125DIP-S610D590U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4
2.5°	853.9	855.2	856.3	856.8	856.8	856.6	856.5	856.4
5°	849.6	851.0	852.3	852.9	852.7	852.7	852.5	852.3
7.5°	841.0	842.3	843.6	844.3	844.1	843.9	843.8	843.6
10°	833.7	834.9	836.2	836.7	836.5	836.3	836.2	836.1
12.5°	824.0	825.0	825.9	826.4	826.3	826.3	826.3	826.3
15°	807.1	807.8	808.6	809.0	809.0	809.0	809.0	809.0
17.5°	787.4	788.3	789.3	789.3	788.5	787.8	787.1	786.3
20°	772.4	773.5	774.5	774.7	773.9	773.2	772.4	771.7
22.5°	755.5	756.2	756.9	757.0	756.4	755.9	755.4	754.9
25°	728.3	728.5	728.9	728.8	728.3	727.9	727.5	727.0
27.5°	699.7	699.8	699.8	699.6	699.2	698.7	698.3	697.9
30°	678.9	678.7	678.3	678.0	677.5	677.1	676.6	676.2
32.5°	657.9	657.3	656.7	656.1	655.3	654.5	653.6	652.8
35°	625.2	624.5	623.7	622.7	621.5	620.3	619.1	617.9
37.5°	590.8	589.8	588.6	587.7	587.0	586.4	585.7	585.0
40°	567.0	565.7	564.4	563.5	563.0	562.6	562.1	561.7
42.5°	543.5	542.2	541.0	540.0	539.3	538.7	538.0	537.3
45°	508.5	506.8	505.0	503.8	503.4	502.9	502.5	502.0
47.5°	471.8	469.9	468.1	466.7	465.7	464.6	463.5	462.4
50°	446.7	444.7	442.7	441.2	440.1	439.1	438.0	437.0
52.5°	422.1	420.4	418.7	417.3	416.2	414.9	413.8	412.6
55°	384.1	382.8	381.5	380.2	379.2	378.1	377.1	376.0
57.5°	346.3	344.6	342.9	341.7	341.2	340.5	340.0	339.5
60°	320.8	319.3	317.8	316.6	315.5	314.4	313.3	312.4
62.5°	296.2	294.6	292.9	291.8	291.0	290.1	289.3	288.5
65°	257.4	256.1	254.8	253.8	253.2	252.5	252.0	251.4
67.5°	220.5	219.4	218.2	217.4	217.0	216.7	216.3	216.0
70°	196.0	195.1	194.2	193.5	192.9	192.3	191.6	191.1
72.5°	173.0	172.0	170.9	170.1	169.5	169.0	168.4	167.7
75°	137.3	136.9	136.4	135.9	135.3	134.6	134.1	133.5
77.5°	104.6	104.3	104.1	103.7	103.3	102.9	102.5	102.0
80°	83.7	83.6	83.4	83.2	82.8	82.6	82.3	81.9
82.5°	63.9	63.7	63.4	63.2	63.2	63.1	63.0	63.0
85°	37.6	37.5	37.4	37.1	36.8	36.5	36.2	35.9
87.5°	16.0	16.1	16.1	16.2	16.0	15.7	15.6	15.3
90°	9.2	9.6	10.2	11.1	11.1	11.1	11.7	11.7
92.5°	90.2	65.5	49.2	41.7	35.2	34.0	33.3	32.5
95°	365.7	288.4	225.9	183.2	147.0	131.7	127.7	119.6
97.5°	544.7	490.4	429.5	370.1	338.7	310.1	295.4	288.9
100°	625.6	600.7	548.3	495.4	460.3	423.7	404.9	396.7
102.5°	652.9	668.2	643.1	607.3	569.8	543.8	523.3	517.2
105°	636.9	706.5	728.9	723.3	707.0	690.3	680.1	674.0
107.5°	579.4	672.4	730.0	756.4	764.7	764.6	761.3	757.2
110°	537.2	633.8	705.5	748.8	771.6	781.3	784.9	784.9



TEST NUMBER: P333177-940

CATALOG NUMBER: S125DIP-S610D590U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	503.8	595.6	668.1	719.1	752.5	769.1	777.9	781.6
115°	461.8	540.7	610.4	665.8	705.5	730.0	744.1	750.8
117.5°	434.8	502.7	562.8	613.7	653.4	678.6	692.7	696.8
120°	420.2	481.2	537.2	581.9	619.6	644.0	657.7	661.7
122.5°	409.2	465.7	515.6	557.5	591.0	613.4	627.1	630.8
125°	393.2	445.1	489.4	525.9	554.5	575.3	586.5	591.6
127.5°	376.9	425.3	466.6	501.0	526.7	545.2	555.7	558.0
130°	366.8	411.5	451.2	484.2	509.7	526.5	536.6	539.7
132.5°	356.6	398.5	434.5	466.4	491.8	508.5	517.9	521.4
135°	343.3	378.4	411.0	440.0	462.4	479.1	488.3	491.3
137.5°	332.2	360.5	387.6	412.2	432.2	447.5	455.9	459.3
140°	326.0	350.0	373.4	394.8	413.6	426.8	434.4	436.9
142.5°	320.7	341.0	361.1	379.7	395.7	406.8	414.0	416.2
145°	313.9	329.6	345.4	359.1	371.3	380.0	385.6	387.6
147.5°	307.4	320.1	332.3	342.6	352.3	359.2	362.5	363.4
150°	303.6	314.9	324.5	333.7	341.3	347.4	349.5	350.0
152.5°	299.6	309.6	318.4	325.6	332.0	336.8	338.9	339.4
155°	293.5	301.7	308.7	314.3	319.4	323.0	324.5	325.0
157.5°	287.4	294.1	299.6	304.0	307.9	310.9	312.3	312.2
160°	283.3	288.4	293.5	297.0	300.6	303.2	304.2	303.6
162.5°	278.8	283.6	287.8	291.0	293.7	295.9	296.0	296.0
165°	272.6	276.2	279.3	281.8	283.8	284.8	284.8	284.8
167.5°	266.7	269.1	271.4	273.2	274.3	275.2	274.7	274.6
170°	263.5	265.0	266.5	267.5	268.6	269.1	269.1	268.6
172.5°	259.8	261.4	262.4	263.1	263.3	264.2	263.4	262.9
175°	255.8	255.8	256.9	256.9	256.9	257.3	256.4	255.8
177.5°	253.1	253.5	253.5	253.5	253.1	253.5	252.3	252.3
180°	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3

(END OF REPORT)