

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331422-930

Luminaire Tested: **SA2XXDIP-C1005D330U930-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331422-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C1005D330U930-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4630.4 lumens
Efficiency: N/A
Efficacy: 93.0 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331422-930
CATALOG NUMBER: SA2XXDIP-C1005D330U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331422-930

CATALOG NUMBER: SA2XXDIP-C1005D330U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	108	108	108	108	99	99	99	90	90	90	81	81	81	77
1	105	100	97	93	100	96	93	90	88	85	83	80	78	76	73	72	70	67
2	96	89	83	77	91	85	79	75	78	74	70	71	68	65	65	63	60	57
3	88	79	71	66	84	75	69	64	69	64	60	64	59	56	59	55	52	49
4	81	70	62	56	77	67	60	55	62	56	52	57	53	49	53	49	46	43
5	75	63	55	49	71	61	53	48	56	50	45	52	47	43	48	44	40	38
6	69	57	49	43	66	55	48	42	51	45	40	47	42	38	44	39	36	34
7	64	52	44	38	61	50	43	37	47	40	36	43	38	34	40	36	32	30
8	60	48	40	34	57	46	39	34	43	37	32	40	35	31	37	33	29	27
9	56	44	36	31	54	42	35	30	40	33	29	37	32	28	35	30	27	25
10	53	40	33	28	50	39	32	28	37	31	27	34	29	25	32	28	24	23

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	26248	26248	26248	26248
5°	29428	26420	23412	26420
10°	33721	26202	20261	26202
15°	37305	25723	17901	25723
20°	36737	25206	16318	25206
25°	33127	24522	15316	24522
30°	27374	23426	14585	23426
35°	19951	22277	14063	22277
40°	15934	20925	13774	20925
45°	13924	19358	13381	19358
50°	13089	17844	13122	17844
55°	12065	16304	12769	16304
60°	11057	14667	12226	14667
65°	10074	13200	11694	13200
70°	9144	11769	10914	11769
75°	8110	10175	9669	10175
80°	6974	8424	7782	8424
85°	6262	6262	4631	6262



TEST NUMBER: P331422-930

CATALOG NUMBER: SA2XXDIP-C1005D330U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.8	3.3
10°-20°	450.1	9.7
20°-30°	653.3	14.1
30°-40°	689.3	14.9
40°-50°	610.4	13.2
50°-60°	487.1	10.5
60°-70°	331.1	7.1
70°-80°	169.7	3.7
80°-90°	42.3	0.9
90°-100°	59.9	1.3
100°-110°	203.2	4.4
110°-120°	215.9	4.7
120°-130°	177.7	3.8
130°-140°	142.7	3.1
140°-150°	107.9	2.3
150°-160°	75.8	1.6
160°-170°	44.6	1.0
170°-180°	14.5	0.3
0°-30°	1258.2	27.2
0°-40°	1947.5	42.1
0°-60°	3045.0	65.8
0°-90°	3588.1	77.5
90°-120°	479.1	10.3
90°-150°	907.4	19.6
90°-180°	1042.0	22.5
0°-180°	4630.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1626	1626	1626	1626	1626	
5°	1816	1630	1444	1630	1816	181
15°	2232	1539	1071	1539	2232	616
25°	1860	1376	860	1376	1860	840
35°	1012	1130	714	1130	1012	658
45°	610	848	586	848	610	480
55°	429	579	454	579	429	384
65°	264	346	306	346	264	262
75°	130	163	155	163	130	139
85°	34	34	25	34	34	37
90°	10	0	10	0	10	7
95°	33	10	33	10	33	43
105°	325	35	325	35	325	314
115°	427	62	427	62	427	418
125°	347	86	347	86	347	313
135°	287	101	287	101	287	223
145°	229	116	229	116	229	146
155°	193	132	193	132	193	90
165°	169	144	169	144	169	48
175°	152	150	152	150	152	15
180°	150	150	150	150	150	



TEST NUMBER: P331422-930

CATALOG NUMBER: SA2XXDIP-C1005D330U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1700.7	1701.2	1702.2	1694.2	1693.2	1693.2	1686.2	1680.3	1673.2	1663.7	1664.8
5°	1815.7	1822.5	1825.0	1817.5	1806.3	1805.1	1794.5	1776.9	1760.7	1747.6	1738.2
7.5°	1952.9	1955.7	1949.5	1939.7	1931.3	1916.3	1896.5	1877.1	1850.1	1825.2	1806.7
10°	2056.8	2060.6	2050.0	2035.6	2023.7	2006.3	1977.5	1948.2	1912.5	1878.2	1850.6
12.5°	2135.8	2145.1	2131.4	2129.6	2109.3	2085.2	2051.0	2036.1	1986.0	1938.1	1908.7
15°	2231.8	2231.1	2232.5	2220.5	2205.5	2201.8	2165.6	2126.2	2055.6	2027.5	1978.7
17.5°	2204.1	2213.5	2217.9	2217.8	2217.5	2215.1	2203.4	2178.6	2143.2	2097.6	2041.3
20°	2138.1	2150.6	2152.5	2166.8	2175.0	2185.6	2190.0	2183.0	2161.2	2123.1	2074.4
22.5°	2036.1	2039.6	2045.5	2067.8	2085.5	2112.1	2126.0	2149.0	2140.7	2122.1	2081.4
25°	1859.5	1853.2	1875.0	1886.3	1926.9	1969.4	2000.0	2033.8	2063.8	2081.9	2070.0
27.5°	1647.2	1637.9	1670.6	1700.5	1733.5	1779.5	1827.2	1883.5	1930.4	1989.0	2009.1
30°	1468.3	1473.9	1505.1	1537.0	1587.0	1652.0	1705.7	1767.6	1834.4	1900.1	1945.6
32.5°	1275.4	1297.0	1316.7	1365.5	1409.6	1482.1	1560.7	1638.1	1721.5	1796.1	1866.7
35°	1012.2	1037.1	1064.7	1100.2	1162.1	1234.0	1310.8	1415.2	1528.9	1630.8	1714.5
37.5°	852.0	848.0	863.7	889.5	939.6	997.6	1086.1	1189.1	1323.0	1442.7	1560.7
40°	756.0	753.5	764.8	788.5	826.6	869.1	946.6	1037.1	1161.5	1307.7	1448.3
42.5°	690.1	691.5	697.8	714.5	740.6	775.6	833.6	910.7	1024.6	1162.3	1313.4
45°	609.8	614.2	621.1	629.2	644.2	672.9	705.4	760.4	850.4	965.3	1114.0
47.5°	552.0	552.2	559.2	566.3	575.2	591.4	617.9	652.4	715.9	809.5	937.3
50°	521.1	516.7	521.7	527.3	536.7	548.0	565.4	597.9	640.4	716.0	822.9
52.5°	483.1	483.2	487.7	489.8	498.2	509.5	525.5	548.0	586.4	645.6	733.4
55°	428.6	431.7	434.2	438.0	445.5	453.6	466.1	481.1	511.1	555.5	620.4
57.5°	377.4	378.4	380.9	388.0	392.7	400.2	412.1	425.7	445.2	478.1	526.9
60°	342.4	342.4	347.4	350.5	356.8	364.3	373.7	386.8	404.2	431.1	470.5
62.5°	310.4	309.9	311.9	317.0	321.8	328.8	338.1	349.3	365.7	389.6	422.0
65°	263.7	262.4	266.2	267.4	272.4	279.3	286.8	298.6	311.8	329.3	358.0
67.5°	218.7	220.2	222.2	224.5	227.3	234.6	239.5	247.9	259.0	273.5	293.0
70°	193.7	193.7	193.7	195.6	199.3	203.1	208.1	214.9	225.6	238.1	255.5
72.5°	165.7	167.7	169.7	168.6	173.3	175.5	181.6	185.5	195.6	203.6	219.1
75°	130.0	130.0	130.0	133.1	134.9	136.8	140.6	144.3	149.4	159.3	167.5
77.5°	96.9	96.7	97.3	98.1	100.1	102.3	103.5	106.8	111.5	116.1	122.9
80°	75.0	76.2	76.9	78.1	78.1	79.3	80.0	84.4	87.5	90.6	95.0
82.5°	58.0	58.2	58.4	58.6	59.1	59.8	61.5	62.9	64.0	66.6	70.0
85°	33.8	33.1	33.1	34.3	33.8	33.8	35.0	36.2	36.2	36.9	38.7
87.5°	14.9	14.9	15.4	14.9	14.9	15.3	15.2	14.8	15.4	16.0	16.4
90°	9.5	9.5	9.5	9.5	9.5	9.2	8.6	9.2	9.5	9.8	9.5
92.5°	16.0	16.4	16.2	17.1	17.4	19.2	21.5	25.1	31.6	37.4	36.9
95°	32.9	32.5	33.4	35.7	39.5	45.8	57.9	75.5	98.8	112.9	100.0
97.5°	64.7	67.1	71.3	78.4	92.1	112.9	144.1	176.1	202.2	192.7	145.2
100°	103.1	108.4	116.7	129.1	153.0	187.8	227.3	263.0	269.0	227.6	156.7
102.5°	181.5	188.5	198.9	220.0	246.1	283.0	311.9	319.9	293.9	228.7	152.3
105°	324.7	328.6	341.0	358.9	376.8	386.3	382.5	350.0	290.1	213.4	143.7
107.5°	414.7	420.0	422.6	423.5	421.3	407.3	377.4	328.3	264.8	197.1	139.5
110°	441.9	442.2	439.6	434.1	421.8	398.1	361.3	309.7	248.9	189.2	138.6



TEST NUMBER: P331422-930

CATALOG NUMBER: SA2XXDIP-C1005D330U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	441.4	439.9	435.0	425.8	408.6	381.5	342.1	292.6	237.8	184.2	138.8
115°	427.2	424.6	417.1	403.9	383.4	353.8	316.0	271.7	224.1	178.6	140.0
117.5°	401.8	399.6	391.8	377.7	356.9	329.1	294.8	255.8	215.5	175.9	142.1
120°	385.5	382.5	374.2	360.7	340.5	314.3	283.7	248.0	210.8	174.3	143.5
122.5°	368.4	366.0	358.6	345.2	327.1	303.5	274.5	241.8	206.9	173.3	145.0
125°	346.6	344.2	337.0	326.1	309.4	287.8	262.4	232.8	201.4	171.7	147.5
127.5°	327.4	325.5	319.4	309.1	294.5	274.6	250.7	223.8	196.2	170.7	149.9
130°	316.6	314.3	308.5	298.7	284.6	265.6	242.9	218.1	192.7	170.2	151.8
132.5°	305.3	303.2	297.9	288.1	274.3	256.4	235.5	212.5	190.0	170.0	153.7
135°	287.2	286.1	280.9	271.3	258.9	242.9	223.8	204.8	186.1	169.7	155.9
137.5°	269.5	267.7	263.2	255.0	243.7	229.7	214.6	198.7	183.4	169.6	157.8
140°	257.2	255.5	251.2	243.7	234.5	221.8	208.6	194.7	181.7	169.4	158.7
142.5°	245.0	244.7	240.8	234.0	225.3	214.7	203.3	191.5	180.2	169.4	159.4
145°	229.3	228.4	225.6	220.6	213.8	205.4	196.5	186.9	178.1	168.8	160.1
147.5°	216.1	215.6	213.6	209.7	204.0	197.9	190.9	183.4	175.9	167.8	160.4
150°	208.3	208.0	206.3	202.8	198.4	193.3	187.3	180.9	174.0	167.1	160.1
152.5°	201.6	201.5	200.2	197.3	193.9	189.4	184.3	178.4	172.4	165.9	159.7
155°	192.7	193.3	192.2	190.1	186.9	183.8	179.4	174.9	169.4	163.9	159.0
157.5°	185.2	185.2	184.7	183.0	180.8	178.2	174.6	170.8	166.6	161.8	157.7
160°	180.3	180.3	180.0	178.6	176.6	174.6	171.4	168.2	164.4	160.5	157.0
162.5°	175.7	175.9	175.7	174.7	172.7	171.1	168.4	165.7	162.7	159.3	156.3
165°	169.1	169.4	169.4	168.2	167.1	165.9	163.9	161.9	159.6	157.0	155.0
167.5°	163.0	163.3	163.4	162.7	162.2	161.2	159.8	158.2	156.6	155.0	153.7
170°	159.3	159.9	160.1	159.3	159.0	158.4	157.3	156.5	155.0	153.8	153.0
172.5°	156.3	156.6	156.9	156.5	156.2	155.9	155.0	154.3	153.4	152.5	152.1
175°	152.4	153.0	153.3	153.0	153.0	152.7	152.4	152.1	151.2	150.9	150.7
177.5°	150.0	150.5	150.7	150.7	150.7	150.7	150.5	150.5	150.0	149.8	150.0
180°	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8



TEST NUMBER: P331422-930
 CATALOG NUMBER: SA2XXDIP-C1005D330U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1668.3	1664.3	1661.7	1652.8	1644.7	1636.7	1634.3	1635.2	1624.2	1613.7	1609.2
5°	1733.2	1720.7	1708.9	1692.0	1672.0	1650.1	1638.8	1630.1	1608.3	1584.5	1570.8
7.5°	1791.5	1773.6	1750.7	1719.0	1689.9	1655.5	1633.6	1614.2	1582.3	1548.7	1528.3
10°	1826.9	1802.5	1773.2	1734.5	1698.8	1657.0	1627.6	1598.2	1560.7	1520.8	1495.7
12.5°	1857.4	1824.6	1795.7	1746.0	1703.8	1651.5	1616.7	1575.2	1535.8	1488.2	1463.8
15°	1930.1	1869.4	1814.4	1758.2	1706.3	1633.2	1594.5	1538.9	1487.0	1428.3	1400.2
17.5°	1986.2	1918.0	1831.4	1760.0	1699.5	1618.5	1561.6	1495.0	1433.7	1366.6	1328.4
20°	2018.1	1940.0	1846.9	1761.9	1689.5	1597.0	1535.1	1467.0	1395.2	1319.6	1278.4
22.5°	2037.1	1955.0	1863.0	1754.4	1669.5	1579.5	1501.6	1427.0	1354.2	1272.6	1229.4
25°	2043.1	1968.1	1870.7	1748.2	1644.5	1542.6	1448.9	1376.5	1288.3	1212.1	1149.0
27.5°	2013.4	1959.7	1865.9	1736.4	1615.6	1496.6	1392.0	1309.9	1217.0	1134.2	1070.8
30°	1976.9	1945.6	1854.4	1724.4	1592.6	1464.5	1349.6	1256.5	1164.0	1080.3	1015.3
32.5°	1920.4	1913.7	1833.4	1707.5	1568.1	1424.1	1305.1	1211.0	1108.6	1026.3	964.3
35°	1809.5	1839.4	1788.8	1669.5	1522.0	1366.4	1237.7	1130.2	1024.1	945.3	887.2
37.5°	1660.8	1735.2	1722.0	1613.9	1459.8	1303.7	1161.6	1049.3	948.1	868.6	811.6
40°	1558.3	1653.3	1667.0	1571.4	1415.8	1255.2	1104.6	992.8	894.1	821.7	764.1
42.5°	1448.3	1559.3	1597.0	1520.4	1367.8	1204.3	1053.7	937.8	840.1	769.6	718.7
45°	1264.0	1410.8	1479.0	1435.2	1287.8	1120.3	965.3	847.8	759.1	692.9	653.5
47.5°	1091.7	1252.1	1343.7	1328.2	1198.7	1032.8	879.6	766.9	680.5	627.7	592.5
50°	969.7	1134.7	1245.2	1250.3	1134.7	970.3	816.6	710.4	631.0	581.7	552.9
52.5°	863.7	1021.2	1141.7	1168.2	1063.2	905.3	760.1	654.4	584.6	539.2	513.5
55°	725.4	858.5	992.2	1040.9	956.6	806.7	672.3	579.2	513.6	482.3	459.8
57.5°	603.1	714.0	837.5	891.4	839.4	711.0	585.1	504.2	451.0	423.6	406.3
60°	538.6	626.1	736.1	800.4	755.4	641.1	531.1	454.2	410.5	386.1	369.9
62.5°	478.6	556.1	649.1	707.9	683.4	575.6	477.1	409.3	371.5	348.6	336.9
65°	394.8	456.1	528.0	582.3	566.1	484.2	403.7	345.5	315.5	297.4	288.0
67.5°	325.1	369.4	419.2	466.8	453.7	395.7	331.0	285.8	263.4	247.8	242.1
70°	281.2	314.9	359.3	397.4	386.8	339.2	288.0	249.3	229.9	216.8	211.2
72.5°	239.2	266.9	300.8	331.9	324.7	285.3	242.6	213.3	198.4	186.3	181.7
75°	180.6	201.8	222.4	243.0	241.2	210.6	185.6	163.1	151.2	141.9	140.0
77.5°	133.3	145.2	159.2	171.5	168.0	150.6	130.9	118.1	109.3	103.1	102.1
80°	101.8	108.7	118.7	127.4	123.1	115.6	100.0	90.6	84.4	78.1	75.6
82.5°	73.9	80.7	86.7	91.5	88.1	81.1	71.5	65.1	61.4	57.1	56.1
85°	38.7	42.5	45.0	46.2	45.0	40.6	36.2	33.8	30.7	28.8	28.1
87.5°	16.6	16.1	15.9	16.7	15.1	14.9	12.7	11.1	10.8	10.4	9.5
90°	7.7	5.8	4.3	3.4	2.9	2.3	1.1	0.3	1.1	2.3	2.9
92.5°	28.8	19.6	13.0	10.4	8.4	7.2	5.1	3.5	5.1	7.2	8.4
95°	66.5	41.5	28.2	21.3	16.7	14.1	11.3	10.1	11.3	14.1	16.7
97.5°	89.7	54.7	38.1	30.2	24.9	21.0	17.9	16.4	17.9	21.0	24.9
100°	94.5	59.4	44.1	36.0	30.2	25.6	23.1	22.2	23.1	25.6	30.2
102.5°	94.7	63.5	49.4	41.3	35.3	30.7	28.1	27.5	28.1	30.7	35.3
105°	96.2	70.6	57.1	49.0	42.6	38.3	36.3	35.1	36.3	38.3	42.6
107.5°	100.2	77.9	64.7	56.6	50.3	46.3	44.4	43.5	44.4	46.3	50.3
110°	103.4	82.7	70.0	61.6	55.6	51.9	50.1	49.0	50.1	51.9	55.6



TEST NUMBER: P331422-930

CATALOG NUMBER: SA2XXDIP-C1005D330U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	106.9	87.3	75.1	66.4	60.7	57.2	55.2	54.1	55.2	57.2	60.7
115°	112.0	94.5	82.1	74.4	68.6	65.1	63.3	62.0	63.3	65.1	68.6
117.5°	117.6	101.1	89.7	81.6	76.1	73.0	71.3	70.1	71.3	73.0	76.1
120°	121.3	105.7	94.5	86.4	80.6	78.1	76.3	75.2	76.3	78.1	80.6
122.5°	124.5	110.1	99.5	91.2	85.5	82.7	81.0	80.1	81.0	82.7	85.5
125°	129.6	116.7	106.3	98.2	92.5	89.0	87.3	86.4	87.3	89.0	92.5
127.5°	134.4	122.8	112.7	104.4	98.9	95.1	92.6	91.5	92.6	95.1	98.9
130°	137.4	126.5	116.3	108.4	102.6	98.5	95.6	94.5	95.6	98.5	102.6
132.5°	140.4	129.7	120.1	112.0	106.0	101.7	98.7	97.3	98.7	101.7	106.0
135°	144.3	134.3	125.0	117.0	110.3	106.0	102.6	101.4	102.6	106.0	110.3
137.5°	147.3	137.9	128.8	121.3	114.8	110.1	106.7	105.3	106.7	110.1	114.8
140°	149.0	140.0	131.3	123.8	117.6	112.9	109.5	108.4	109.5	112.9	117.6
142.5°	150.3	141.6	133.2	126.2	120.1	115.4	112.3	111.3	112.3	115.4	120.1
145°	152.1	144.1	136.2	130.0	124.2	119.8	117.0	115.8	117.0	119.8	124.2
147.5°	153.1	146.0	138.7	133.1	128.2	124.3	121.5	120.7	121.5	124.3	128.2
150°	153.5	146.9	140.3	135.1	130.8	127.0	124.7	123.8	124.7	127.0	130.8
152.5°	153.8	147.8	141.9	137.2	133.1	129.8	127.5	127.1	127.5	129.8	133.1
155°	154.1	149.2	144.3	140.0	136.8	133.6	131.9	131.7	131.9	133.6	136.8
157.5°	154.1	150.2	146.0	142.4	139.9	137.1	135.7	135.4	135.7	137.1	139.9
160°	154.1	150.7	147.2	144.1	141.7	139.4	138.3	137.9	138.3	139.4	141.7
162.5°	153.8	150.9	147.9	145.4	143.3	141.5	140.3	140.6	140.3	141.5	143.3
165°	153.3	151.2	148.6	146.9	145.4	143.7	143.2	143.5	143.2	143.7	145.4
167.5°	152.9	151.2	149.3	148.2	147.2	146.0	145.5	145.9	145.5	146.0	147.2
170°	152.4	150.9	149.5	148.6	148.1	147.2	146.9	147.5	146.9	147.2	148.1
172.5°	151.7	150.7	149.8	149.1	148.8	147.9	148.1	148.4	148.1	147.9	148.8
175°	150.9	150.3	149.8	149.5	149.5	149.0	149.2	149.5	149.2	149.0	149.5
177.5°	150.5	150.0	149.8	149.8	149.8	149.4	149.5	150.0	149.5	149.4	149.8
180°	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8



TEST NUMBER: P331422-930

CATALOG NUMBER: SA2XXDIP-C1005D330U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1604.3	1601.2	1590.7	1585.3	1576.3	1567.7	1562.3	1564.8	1566.8	1565.8	1564.2
5°	1558.3	1546.4	1528.3	1512.6	1501.4	1480.8	1472.0	1467.7	1464.0	1459.5	1455.1
7.5°	1503.5	1484.8	1458.8	1436.6	1415.5	1389.9	1375.3	1366.6	1357.6	1347.7	1339.0
10°	1464.5	1438.3	1410.8	1379.6	1354.6	1331.5	1310.8	1297.1	1284.6	1272.8	1264.0
12.5°	1423.6	1393.3	1359.3	1316.6	1289.1	1256.0	1252.9	1228.7	1209.1	1201.8	1191.5
15°	1358.3	1315.8	1272.8	1222.1	1200.3	1170.3	1151.5	1132.8	1115.9	1104.0	1100.9
17.5°	1284.3	1229.2	1186.3	1150.0	1114.2	1083.5	1066.2	1051.2	1037.3	1021.4	1019.3
20°	1227.8	1180.2	1133.4	1101.6	1064.7	1033.4	1012.2	997.2	985.3	975.9	967.8
22.5°	1174.3	1122.3	1079.4	1044.6	1008.2	982.9	966.2	951.7	941.8	931.5	923.8
25°	1088.4	1047.8	1000.9	961.6	931.6	915.3	901.6	889.1	882.9	876.0	867.2
27.5°	1013.3	968.2	924.3	893.8	867.5	853.1	843.3	834.9	829.0	825.0	820.0
30°	960.3	914.7	880.4	850.4	828.5	814.2	807.9	802.9	796.0	793.5	791.0
32.5°	909.3	868.2	838.9	812.9	792.0	782.6	776.9	772.4	767.0	764.5	759.5
35°	837.2	802.9	774.1	759.8	742.9	734.7	730.4	724.1	719.2	716.6	716.0
37.5°	769.4	739.6	720.6	702.1	695.0	690.1	684.0	679.8	678.3	677.9	677.3
40°	725.4	701.0	684.2	669.2	666.0	658.5	653.5	649.8	649.8	650.4	649.8
42.5°	685.4	663.6	648.7	635.7	632.0	627.5	622.6	622.3	623.3	625.4	623.3
45°	624.8	609.2	598.6	592.3	585.5	581.1	580.4	582.3	582.9	583.6	585.5
47.5°	569.1	558.7	549.1	542.2	539.2	538.4	537.7	541.0	544.0	545.1	548.0
50°	536.1	524.2	516.1	511.7	509.2	507.9	509.2	513.0	515.4	518.6	520.5
52.5°	499.1	490.7	485.1	481.8	480.7	481.5	481.8	486.0	490.0	491.1	492.0
55°	448.0	441.7	440.5	434.9	437.3	436.8	439.9	442.4	446.1	449.9	450.5
57.5°	397.0	392.0	388.7	389.1	389.9	392.6	395.3	399.7	403.7	407.6	408.0
60°	363.1	360.5	358.7	358.7	359.9	363.6	366.7	371.1	373.7	376.1	378.0
62.5°	332.0	329.5	327.7	328.6	331.9	334.1	337.8	340.1	342.7	345.1	346.0
65°	283.1	281.8	283.6	284.9	285.5	288.7	293.0	294.9	297.4	298.6	303.0
67.5°	237.9	238.1	237.9	239.7	243.3	244.0	248.2	252.6	253.1	255.4	258.3
70°	207.4	208.7	209.9	211.2	214.3	215.6	218.7	220.5	223.1	224.9	226.8
72.5°	179.4	179.7	180.9	180.7	183.3	186.1	188.7	190.5	193.1	195.4	197.3
75°	138.1	138.1	139.3	140.0	143.1	146.2	145.6	146.8	149.4	151.8	153.1
77.5°	100.9	99.5	100.9	101.5	102.5	105.1	105.6	107.4	110.2	109.3	110.7
80°	76.9	75.0	76.9	77.5	77.5	80.6	80.6	81.9	83.7	81.9	83.7
82.5°	54.9	54.0	55.4	55.5	56.5	56.6	57.6	57.9	59.8	58.9	59.8
85°	27.5	26.9	27.5	26.9	27.5	28.1	28.1	27.5	27.5	28.8	26.9
87.5°	9.2	8.9	8.6	9.0	8.9	8.5	7.9	7.8	7.7	6.8	6.9
90°	3.4	4.3	5.8	7.7	9.5	9.8	9.5	9.2	8.6	9.2	9.5
92.5°	10.4	13.0	19.6	28.8	36.9	37.4	31.6	25.1	21.5	19.2	17.4
95°	21.3	28.2	41.5	66.5	100.0	112.9	98.8	75.5	57.9	45.8	39.5
97.5°	30.2	38.1	54.7	89.7	145.2	192.7	202.2	176.1	144.1	112.9	92.1
100°	36.0	44.1	59.4	94.5	156.7	227.6	269.0	263.0	227.3	187.8	153.0
102.5°	41.3	49.4	63.5	94.7	152.3	228.7	293.9	319.9	311.9	283.0	246.1
105°	49.0	57.1	70.6	96.2	143.7	213.4	290.1	350.0	382.5	386.3	376.8
107.5°	56.6	64.7	77.9	100.2	139.5	197.1	264.8	328.3	377.4	407.3	421.3
110°	61.6	70.0	82.7	103.4	138.6	189.2	248.9	309.7	361.3	398.1	421.8



TEST NUMBER: P331422-930

CATALOG NUMBER: SA2XXDIP-C1005D330U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	66.4	75.1	87.3	106.9	138.8	184.2	237.8	292.6	342.1	381.5	408.6
115°	74.4	82.1	94.5	112.0	140.0	178.6	224.1	271.7	316.0	353.8	383.4
117.5°	81.6	89.7	101.1	117.6	142.1	175.9	215.5	255.8	294.8	329.1	356.9
120°	86.4	94.5	105.7	121.3	143.5	174.3	210.8	248.0	283.7	314.3	340.5
122.5°	91.2	99.5	110.1	124.5	145.0	173.3	206.9	241.8	274.5	303.5	327.1
125°	98.2	106.3	116.7	129.6	147.5	171.7	201.4	232.8	262.4	287.8	309.4
127.5°	104.4	112.7	122.8	134.4	149.9	170.7	196.2	223.8	250.7	274.6	294.5
130°	108.4	116.3	126.5	137.4	151.8	170.2	192.7	218.1	242.9	265.6	284.6
132.5°	112.0	120.1	129.7	140.4	153.7	170.0	190.0	212.5	235.5	256.4	274.3
135°	117.0	125.0	134.3	144.3	155.9	169.7	186.1	204.8	223.8	242.9	258.9
137.5°	121.3	128.8	137.9	147.3	157.8	169.6	183.4	198.7	214.6	229.7	243.7
140°	123.8	131.3	140.0	149.0	158.7	169.4	181.7	194.7	208.6	221.8	234.5
142.5°	126.2	133.2	141.6	150.3	159.4	169.4	180.2	191.5	203.3	214.7	225.3
145°	130.0	136.2	144.1	152.1	160.1	168.8	178.1	186.9	196.5	205.4	213.8
147.5°	133.1	138.7	146.0	153.1	160.4	167.8	175.9	183.4	190.9	197.9	204.0
150°	135.1	140.3	146.9	153.5	160.1	167.1	174.0	180.9	187.3	193.3	198.4
152.5°	137.2	141.9	147.8	153.8	159.7	165.9	172.4	178.4	184.3	189.4	193.9
155°	140.0	144.3	149.2	154.1	159.0	163.9	169.4	174.9	179.4	183.8	186.9
157.5°	142.4	146.0	150.2	154.1	157.7	161.8	166.6	170.8	174.6	178.2	180.8
160°	144.1	147.2	150.7	154.1	157.0	160.5	164.4	168.2	171.4	174.6	176.6
162.5°	145.4	147.9	150.9	153.8	156.3	159.3	162.7	165.7	168.4	171.1	172.7
165°	146.9	148.6	151.2	153.3	155.0	157.0	159.6	161.9	163.9	165.9	167.1
167.5°	148.2	149.3	151.2	152.9	153.7	155.0	156.6	158.2	159.8	161.2	162.2
170°	148.6	149.5	150.9	152.4	153.0	153.8	155.0	156.5	157.3	158.4	159.0
172.5°	149.1	149.8	150.7	151.7	152.1	152.5	153.4	154.3	155.0	155.9	156.2
175°	149.5	149.8	150.3	150.9	150.7	150.9	151.2	152.1	152.4	152.7	153.0
177.5°	149.8	149.8	150.0	150.5	150.0	149.8	150.0	150.5	150.5	150.7	150.7
180°	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8



TEST NUMBER: P331422-930

CATALOG NUMBER: SA2XXDIP-C1005D330U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1559.3	1558.3	1558.3	1553.8	1558.3	1558.3	1559.3	1564.2	1565.8	1566.8	1564.8
5°	1446.4	1444.5	1441.4	1444.5	1441.4	1444.5	1446.4	1455.1	1459.5	1464.0	1467.7
7.5°	1334.8	1327.3	1326.2	1318.8	1326.2	1327.3	1334.8	1339.0	1347.7	1357.6	1366.6
10°	1253.4	1248.4	1247.7	1235.8	1247.7	1248.4	1253.4	1264.0	1272.8	1284.6	1297.1
12.5°	1191.4	1179.4	1181.8	1174.8	1181.8	1179.4	1191.4	1191.5	1201.8	1209.1	1228.7
15°	1084.0	1084.0	1081.6	1070.9	1081.6	1084.0	1084.0	1100.9	1104.0	1115.9	1132.8
17.5°	1007.0	1005.7	999.7	1002.7	999.7	1005.7	1007.0	1019.3	1021.4	1037.3	1051.2
20°	960.9	957.2	949.7	949.7	949.7	957.2	960.9	967.8	975.9	985.3	997.2
22.5°	917.5	917.2	909.2	911.7	909.2	917.2	917.5	923.8	931.5	941.8	951.7
25°	866.6	861.6	857.9	859.7	857.9	861.6	866.6	867.2	876.0	882.9	889.1
27.5°	818.4	815.6	815.4	810.2	815.4	815.6	818.4	820.0	825.0	829.0	834.9
30°	790.4	784.2	785.4	782.3	785.4	784.2	790.4	791.0	793.5	796.0	802.9
32.5°	758.4	756.1	754.9	752.3	754.9	756.1	758.4	759.5	764.5	767.0	772.4
35°	714.8	715.4	712.2	713.5	712.2	715.4	714.8	716.0	716.6	719.2	724.1
37.5°	676.7	678.7	677.2	677.5	677.2	678.7	676.7	677.3	677.9	678.3	679.8
40°	651.7	651.7	651.7	653.5	651.7	651.7	651.7	649.8	650.4	649.8	649.8
42.5°	627.7	626.7	625.7	625.6	625.7	626.7	627.7	623.3	625.4	623.3	622.3
45°	586.7	588.6	589.2	586.0	589.2	588.6	586.7	585.5	583.6	582.9	582.3
47.5°	549.6	549.8	549.6	552.4	549.6	549.8	549.6	548.0	545.1	544.0	541.0
50°	523.6	522.4	523.6	522.4	523.6	522.4	523.6	520.5	518.6	515.4	513.0
52.5°	496.1	496.4	495.6	495.4	495.6	496.4	496.1	492.0	491.1	490.0	486.0
55°	453.0	454.2	453.6	453.6	453.6	454.2	453.0	450.5	449.9	446.1	442.4
57.5°	408.4	409.5	410.3	407.6	410.3	409.5	408.4	408.0	407.6	403.7	399.7
60°	377.4	380.5	379.8	378.6	379.8	380.5	377.4	378.0	376.1	373.7	371.1
62.5°	348.9	350.0	349.9	349.7	349.9	350.0	348.9	346.0	345.1	342.7	340.1
65°	304.9	306.1	304.3	306.1	304.3	306.1	304.9	303.0	298.6	297.4	294.9
67.5°	257.6	258.0	259.3	260.2	259.3	258.0	257.6	258.3	255.4	253.1	252.6
70°	228.0	227.5	229.3	231.2	229.3	227.5	228.0	226.8	224.9	223.1	220.5
72.5°	197.1	198.4	197.8	199.2	197.8	198.4	197.1	197.3	195.4	193.1	190.5
75°	151.8	153.7	153.1	155.0	153.1	153.7	151.8	153.1	151.8	149.4	146.8
77.5°	109.7	110.0	109.7	110.7	109.7	110.0	109.7	110.7	109.3	110.2	107.4
80°	83.7	82.5	81.2	83.7	81.2	82.5	83.7	83.7	81.9	83.7	81.9
82.5°	58.2	58.9	57.7	57.7	57.7	58.9	58.2	59.8	58.9	59.8	57.9
85°	26.9	26.3	25.0	25.0	25.0	26.3	26.9	26.9	28.8	27.5	27.5
87.5°	6.9	6.4	6.4	5.9	6.4	6.4	6.9	6.9	6.8	7.7	7.8
90°	9.5	9.5	9.5	9.5	9.5	9.5	9.5	9.5	9.2	8.6	9.2
92.5°	17.1	16.2	16.4	16.0	16.4	16.2	17.1	17.4	19.2	21.5	25.1
95°	35.7	33.4	32.5	32.9	32.5	33.4	35.7	39.5	45.8	57.9	75.5
97.5°	78.4	71.3	67.1	64.7	67.1	71.3	78.4	92.1	112.9	144.1	176.1
100°	129.1	116.7	108.4	103.1	108.4	116.7	129.1	153.0	187.8	227.3	263.0
102.5°	220.0	198.9	188.5	181.5	188.5	198.9	220.0	246.1	283.0	311.9	319.9
105°	358.9	341.0	328.6	324.7	328.6	341.0	358.9	376.8	386.3	382.5	350.0
107.5°	423.5	422.6	420.0	414.7	420.0	422.6	423.5	421.3	407.3	377.4	328.3
110°	434.1	439.6	442.2	441.9	442.2	439.6	434.1	421.8	398.1	361.3	309.7



TEST NUMBER: P331422-930

CATALOG NUMBER: SA2XXDIP-C1005D330U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	425.8	435.0	439.9	441.4	439.9	435.0	425.8	408.6	381.5	342.1	292.6
115°	403.9	417.1	424.6	427.2	424.6	417.1	403.9	383.4	353.8	316.0	271.7
117.5°	377.7	391.8	399.6	401.8	399.6	391.8	377.7	356.9	329.1	294.8	255.8
120°	360.7	374.2	382.5	385.5	382.5	374.2	360.7	340.5	314.3	283.7	248.0
122.5°	345.2	358.6	366.0	368.4	366.0	358.6	345.2	327.1	303.5	274.5	241.8
125°	326.1	337.0	344.2	346.6	344.2	337.0	326.1	309.4	287.8	262.4	232.8
127.5°	309.1	319.4	325.5	327.4	325.5	319.4	309.1	294.5	274.6	250.7	223.8
130°	298.7	308.5	314.3	316.6	314.3	308.5	298.7	284.6	265.6	242.9	218.1
132.5°	288.1	297.9	303.2	305.3	303.2	297.9	288.1	274.3	256.4	235.5	212.5
135°	271.3	280.9	286.1	287.2	286.1	280.9	271.3	258.9	242.9	223.8	204.8
137.5°	255.0	263.2	267.7	269.5	267.7	263.2	255.0	243.7	229.7	214.6	198.7
140°	243.7	251.2	255.5	257.2	255.5	251.2	243.7	234.5	221.8	208.6	194.7
142.5°	234.0	240.8	244.7	245.0	244.7	240.8	234.0	225.3	214.7	203.3	191.5
145°	220.6	225.6	228.4	229.3	228.4	225.6	220.6	213.8	205.4	196.5	186.9
147.5°	209.7	213.6	215.6	216.1	215.6	213.6	209.7	204.0	197.9	190.9	183.4
150°	202.8	206.3	208.0	208.3	208.0	206.3	202.8	198.4	193.3	187.3	180.9
152.5°	197.3	200.2	201.5	201.6	201.5	200.2	197.3	193.9	189.4	184.3	178.4
155°	190.1	192.2	193.3	192.7	193.3	192.2	190.1	186.9	183.8	179.4	174.9
157.5°	183.0	184.7	185.2	185.2	185.2	184.7	183.0	180.8	178.2	174.6	170.8
160°	178.6	180.0	180.3	180.3	180.3	180.0	178.6	176.6	174.6	171.4	168.2
162.5°	174.7	175.7	175.9	175.7	175.9	175.7	174.7	172.7	171.1	168.4	165.7
165°	168.2	169.4	169.4	169.1	169.4	169.4	168.2	167.1	165.9	163.9	161.9
167.5°	162.7	163.4	163.3	163.0	163.3	163.4	162.7	162.2	161.2	159.8	158.2
170°	159.3	160.1	159.9	159.3	159.9	160.1	159.3	159.0	158.4	157.3	156.5
172.5°	156.5	156.9	156.6	156.3	156.6	156.9	156.5	156.2	155.9	155.0	154.3
175°	153.0	153.3	153.0	152.4	153.0	153.3	153.0	153.0	152.7	152.4	152.1
177.5°	150.7	150.7	150.5	150.0	150.5	150.7	150.7	150.7	150.7	150.5	150.5
180°	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8



TEST NUMBER: P331422-930
 CATALOG NUMBER: SA2XXDIP-C1005D330U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1562.3	1567.7	1576.3	1585.3	1590.7	1601.2	1604.3	1609.2	1613.7	1624.2	1635.2
5°	1472.0	1480.8	1501.4	1512.6	1528.3	1546.4	1558.3	1570.8	1584.5	1608.3	1630.1
7.5°	1375.3	1389.9	1415.5	1436.6	1458.8	1484.8	1503.5	1528.3	1548.7	1582.3	1614.2
10°	1310.8	1331.5	1354.6	1379.6	1410.8	1438.3	1464.5	1495.7	1520.8	1560.7	1598.2
12.5°	1252.9	1256.0	1289.1	1316.6	1359.3	1393.3	1423.6	1463.8	1488.2	1535.8	1575.2
15°	1151.5	1170.3	1200.3	1222.1	1272.8	1315.8	1358.3	1400.2	1428.3	1487.0	1538.9
17.5°	1066.2	1083.5	1114.2	1150.0	1186.3	1229.2	1284.3	1328.4	1366.6	1433.7	1495.0
20°	1012.2	1033.4	1064.7	1101.6	1133.4	1180.2	1227.8	1278.4	1319.6	1395.2	1467.0
22.5°	966.2	982.9	1008.2	1044.6	1079.4	1122.3	1174.3	1229.4	1272.6	1354.2	1427.0
25°	901.6	915.3	931.6	961.6	1000.9	1047.8	1088.4	1149.0	1212.1	1288.3	1376.5
27.5°	843.3	853.1	867.5	893.8	924.3	968.2	1013.3	1070.8	1134.2	1217.0	1309.9
30°	807.9	814.2	828.5	850.4	880.4	914.7	960.3	1015.3	1080.3	1164.0	1256.5
32.5°	776.9	782.6	792.0	812.9	838.9	868.2	909.3	964.3	1026.3	1108.6	1211.0
35°	730.4	734.7	742.9	759.8	774.1	802.9	837.2	887.2	945.3	1024.1	1130.2
37.5°	684.0	690.1	695.0	702.1	720.6	739.6	769.4	811.6	868.6	948.1	1049.3
40°	653.5	658.5	666.0	669.2	684.2	701.0	725.4	764.1	821.7	894.1	992.8
42.5°	622.6	627.5	632.0	635.7	648.7	663.6	685.4	718.7	769.6	840.1	937.8
45°	580.4	581.1	585.5	592.3	598.6	609.2	624.8	653.5	692.9	759.1	847.8
47.5°	537.7	538.4	539.2	542.2	549.1	558.7	569.1	592.5	627.7	680.5	766.9
50°	509.2	507.9	509.2	511.7	516.1	524.2	536.1	552.9	581.7	631.0	710.4
52.5°	481.8	481.5	480.7	481.8	485.1	490.7	499.1	513.5	539.2	584.6	654.4
55°	439.9	436.8	437.3	434.9	440.5	441.7	448.0	459.8	482.3	513.6	579.2
57.5°	395.3	392.6	389.9	389.1	388.7	392.0	397.0	406.3	423.6	451.0	504.2
60°	366.7	363.6	359.9	358.7	358.7	360.5	363.1	369.9	386.1	410.5	454.2
62.5°	337.8	334.1	331.9	328.6	327.7	329.5	332.0	336.9	348.6	371.5	409.3
65°	293.0	288.7	285.5	284.9	283.6	281.8	283.1	288.0	297.4	315.5	345.5
67.5°	248.2	244.0	243.3	239.7	237.9	238.1	237.9	242.1	247.8	263.4	285.8
70°	218.7	215.6	214.3	211.2	209.9	208.7	207.4	211.2	216.8	229.9	249.3
72.5°	188.7	186.1	183.3	180.7	180.9	179.7	179.4	181.7	186.3	198.4	213.3
75°	145.6	146.2	143.1	140.0	139.3	138.1	138.1	140.0	141.9	151.2	163.1
77.5°	105.6	105.1	102.5	101.5	100.9	99.5	100.9	102.1	103.1	109.3	118.1
80°	80.6	80.6	77.5	77.5	76.9	75.0	76.9	75.6	78.1	84.4	90.6
82.5°	57.6	56.6	56.5	55.5	55.4	54.0	54.9	56.1	57.1	61.4	65.1
85°	28.1	28.1	27.5	26.9	27.5	26.9	27.5	28.1	28.8	30.7	33.8
87.5°	7.9	8.5	8.9	9.0	8.6	8.9	9.2	9.5	10.4	10.8	11.1
90°	9.5	9.8	9.5	7.7	5.8	4.3	3.4	2.9	2.3	1.1	0.3
92.5°	31.6	37.4	36.9	28.8	19.6	13.0	10.4	8.4	7.2	5.1	3.5
95°	98.8	112.9	100.0	66.5	41.5	28.2	21.3	16.7	14.1	11.3	10.1
97.5°	202.2	192.7	145.2	89.7	54.7	38.1	30.2	24.9	21.0	17.9	16.4
100°	269.0	227.6	156.7	94.5	59.4	44.1	36.0	30.2	25.6	23.1	22.2
102.5°	293.9	228.7	152.3	94.7	63.5	49.4	41.3	35.3	30.7	28.1	27.5
105°	290.1	213.4	143.7	96.2	70.6	57.1	49.0	42.6	38.3	36.3	35.1
107.5°	264.8	197.1	139.5	100.2	77.9	64.7	56.6	50.3	46.3	44.4	43.5
110°	248.9	189.2	138.6	103.4	82.7	70.0	61.6	55.6	51.9	50.1	49.0



TEST NUMBER: P331422-930

CATALOG NUMBER: SA2XXDIP-C1005D330U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	237.8	184.2	138.8	106.9	87.3	75.1	66.4	60.7	57.2	55.2	54.1
115°	224.1	178.6	140.0	112.0	94.5	82.1	74.4	68.6	65.1	63.3	62.0
117.5°	215.5	175.9	142.1	117.6	101.1	89.7	81.6	76.1	73.0	71.3	70.1
120°	210.8	174.3	143.5	121.3	105.7	94.5	86.4	80.6	78.1	76.3	75.2
122.5°	206.9	173.3	145.0	124.5	110.1	99.5	91.2	85.5	82.7	81.0	80.1
125°	201.4	171.7	147.5	129.6	116.7	106.3	98.2	92.5	89.0	87.3	86.4
127.5°	196.2	170.7	149.9	134.4	122.8	112.7	104.4	98.9	95.1	92.6	91.5
130°	192.7	170.2	151.8	137.4	126.5	116.3	108.4	102.6	98.5	95.6	94.5
132.5°	190.0	170.0	153.7	140.4	129.7	120.1	112.0	106.0	101.7	98.7	97.3
135°	186.1	169.7	155.9	144.3	134.3	125.0	117.0	110.3	106.0	102.6	101.4
137.5°	183.4	169.6	157.8	147.3	137.9	128.8	121.3	114.8	110.1	106.7	105.3
140°	181.7	169.4	158.7	149.0	140.0	131.3	123.8	117.6	112.9	109.5	108.4
142.5°	180.2	169.4	159.4	150.3	141.6	133.2	126.2	120.1	115.4	112.3	111.3
145°	178.1	168.8	160.1	152.1	144.1	136.2	130.0	124.2	119.8	117.0	115.8
147.5°	175.9	167.8	160.4	153.1	146.0	138.7	133.1	128.2	124.3	121.5	120.7
150°	174.0	167.1	160.1	153.5	146.9	140.3	135.1	130.8	127.0	124.7	123.8
152.5°	172.4	165.9	159.7	153.8	147.8	141.9	137.2	133.1	129.8	127.5	127.1
155°	169.4	163.9	159.0	154.1	149.2	144.3	140.0	136.8	133.6	131.9	131.7
157.5°	166.6	161.8	157.7	154.1	150.2	146.0	142.4	139.9	137.1	135.7	135.4
160°	164.4	160.5	157.0	154.1	150.7	147.2	144.1	141.7	139.4	138.3	137.9
162.5°	162.7	159.3	156.3	153.8	150.9	147.9	145.4	143.3	141.5	140.3	140.6
165°	159.6	157.0	155.0	153.3	151.2	148.6	146.9	145.4	143.7	143.2	143.5
167.5°	156.6	155.0	153.7	152.9	151.2	149.3	148.2	147.2	146.0	145.5	145.9
170°	155.0	153.8	153.0	152.4	150.9	149.5	148.6	148.1	147.2	146.9	147.5
172.5°	153.4	152.5	152.1	151.7	150.7	149.8	149.1	148.8	147.9	148.1	148.4
175°	151.2	150.9	150.7	150.9	150.3	149.8	149.5	149.5	149.0	149.2	149.5
177.5°	150.0	149.8	150.0	150.5	150.0	149.8	149.8	149.8	149.8	149.5	150.0
180°	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8



TEST NUMBER: P331422-930

CATALOG NUMBER: SA2XXDIP-C1005D330U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1634.3	1636.7	1644.7	1652.8	1661.7	1664.3	1668.3	1664.8	1663.7	1673.2	1680.3
5°	1638.8	1650.1	1672.0	1692.0	1708.9	1720.7	1733.2	1738.2	1747.6	1760.7	1776.9
7.5°	1633.6	1655.5	1689.9	1719.0	1750.7	1773.6	1791.5	1806.7	1825.2	1850.1	1877.1
10°	1627.6	1657.0	1698.8	1734.5	1773.2	1802.5	1826.9	1850.6	1878.2	1912.5	1948.2
12.5°	1616.7	1651.5	1703.8	1746.0	1795.7	1824.6	1857.4	1908.7	1938.1	1986.0	2036.1
15°	1594.5	1633.2	1706.3	1758.2	1814.4	1869.4	1930.1	1978.7	2027.5	2055.6	2126.2
17.5°	1561.6	1618.5	1699.5	1760.0	1831.4	1918.0	1986.2	2041.3	2097.6	2143.2	2178.6
20°	1535.1	1597.0	1689.5	1761.9	1846.9	1940.0	2018.1	2074.4	2123.1	2161.2	2183.0
22.5°	1501.6	1579.5	1669.5	1754.4	1863.0	1955.0	2037.1	2081.4	2122.1	2140.7	2149.0
25°	1448.9	1542.6	1644.5	1748.2	1870.7	1968.1	2043.1	2070.0	2081.9	2063.8	2033.8
27.5°	1392.0	1496.6	1615.6	1736.4	1865.9	1959.7	2013.4	2009.1	1989.0	1930.4	1883.5
30°	1349.6	1464.5	1592.6	1724.4	1854.4	1945.6	1976.9	1945.6	1900.1	1834.4	1767.6
32.5°	1305.1	1424.1	1568.1	1707.5	1833.4	1913.7	1920.4	1866.7	1796.1	1721.5	1638.1
35°	1237.7	1366.4	1522.0	1669.5	1788.8	1839.4	1809.5	1714.5	1630.8	1528.9	1415.2
37.5°	1161.6	1303.7	1459.8	1613.9	1722.0	1735.2	1660.8	1560.7	1442.7	1323.0	1189.1
40°	1104.6	1255.2	1415.8	1571.4	1667.0	1653.3	1558.3	1448.3	1307.7	1161.5	1037.1
42.5°	1053.7	1204.3	1367.8	1520.4	1597.0	1559.3	1448.3	1313.4	1162.3	1024.6	910.7
45°	965.3	1120.3	1287.8	1435.2	1479.0	1410.8	1264.0	1114.0	965.3	850.4	760.4
47.5°	879.6	1032.8	1198.7	1328.2	1343.7	1252.1	1091.7	937.3	809.5	715.9	652.4
50°	816.6	970.3	1134.7	1250.3	1245.2	1134.7	969.7	822.9	716.0	640.4	597.9
52.5°	760.1	905.3	1063.2	1168.2	1141.7	1021.2	863.7	733.4	645.6	586.4	548.0
55°	672.3	806.7	956.6	1040.9	992.2	858.5	725.4	620.4	555.5	511.1	481.1
57.5°	585.1	711.0	839.4	891.4	837.5	714.0	603.1	526.9	478.1	445.2	425.7
60°	531.1	641.1	755.4	800.4	736.1	626.1	538.6	470.5	431.1	404.2	386.8
62.5°	477.1	575.6	683.4	707.9	649.1	556.1	478.6	422.0	389.6	365.7	349.3
65°	403.7	484.2	566.1	582.3	528.0	456.1	394.8	358.0	329.3	311.8	298.6
67.5°	331.0	395.7	453.7	466.8	419.2	369.4	325.1	293.0	273.5	259.0	247.9
70°	288.0	339.2	386.8	397.4	359.3	314.9	281.2	255.5	238.1	225.6	214.9
72.5°	242.6	285.3	324.7	331.9	300.8	266.9	239.2	219.1	203.6	195.6	185.5
75°	185.6	210.6	241.2	243.0	222.4	201.8	180.6	167.5	159.3	149.4	144.3
77.5°	130.9	150.6	168.0	171.5	159.2	145.2	133.3	122.9	116.1	111.5	106.8
80°	100.0	115.6	123.1	127.4	118.7	108.7	101.8	95.0	90.6	87.5	84.4
82.5°	71.5	81.1	88.1	91.5	86.7	80.7	73.9	70.0	66.6	64.0	62.9
85°	36.2	40.6	45.0	46.2	45.0	42.5	38.7	38.7	36.9	36.2	36.2
87.5°	12.7	14.9	15.1	16.7	15.9	16.1	16.6	16.4	16.0	15.4	14.8
90°	1.1	2.3	2.9	3.4	4.3	5.8	7.7	9.5	9.8	9.5	9.2
92.5°	5.1	7.2	8.4	10.4	13.0	19.6	28.8	36.9	37.4	31.6	25.1
95°	11.3	14.1	16.7	21.3	28.2	41.5	66.5	100.0	112.9	98.8	75.5
97.5°	17.9	21.0	24.9	30.2	38.1	54.7	89.7	145.2	192.7	202.2	176.1
100°	23.1	25.6	30.2	36.0	44.1	59.4	94.5	156.7	227.6	269.0	263.0
102.5°	28.1	30.7	35.3	41.3	49.4	63.5	94.7	152.3	228.7	293.9	319.9
105°	36.3	38.3	42.6	49.0	57.1	70.6	96.2	143.7	213.4	290.1	350.0
107.5°	44.4	46.3	50.3	56.6	64.7	77.9	100.2	139.5	197.1	264.8	328.3
110°	50.1	51.9	55.6	61.6	70.0	82.7	103.4	138.6	189.2	248.9	309.7



TEST NUMBER: P331422-930

CATALOG NUMBER: SA2XXDIP-C1005D330U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	55.2	57.2	60.7	66.4	75.1	87.3	106.9	138.8	184.2	237.8	292.6
115°	63.3	65.1	68.6	74.4	82.1	94.5	112.0	140.0	178.6	224.1	271.7
117.5°	71.3	73.0	76.1	81.6	89.7	101.1	117.6	142.1	175.9	215.5	255.8
120°	76.3	78.1	80.6	86.4	94.5	105.7	121.3	143.5	174.3	210.8	248.0
122.5°	81.0	82.7	85.5	91.2	99.5	110.1	124.5	145.0	173.3	206.9	241.8
125°	87.3	89.0	92.5	98.2	106.3	116.7	129.6	147.5	171.7	201.4	232.8
127.5°	92.6	95.1	98.9	104.4	112.7	122.8	134.4	149.9	170.7	196.2	223.8
130°	95.6	98.5	102.6	108.4	116.3	126.5	137.4	151.8	170.2	192.7	218.1
132.5°	98.7	101.7	106.0	112.0	120.1	129.7	140.4	153.7	170.0	190.0	212.5
135°	102.6	106.0	110.3	117.0	125.0	134.3	144.3	155.9	169.7	186.1	204.8
137.5°	106.7	110.1	114.8	121.3	128.8	137.9	147.3	157.8	169.6	183.4	198.7
140°	109.5	112.9	117.6	123.8	131.3	140.0	149.0	158.7	169.4	181.7	194.7
142.5°	112.3	115.4	120.1	126.2	133.2	141.6	150.3	159.4	169.4	180.2	191.5
145°	117.0	119.8	124.2	130.0	136.2	144.1	152.1	160.1	168.8	178.1	186.9
147.5°	121.5	124.3	128.2	133.1	138.7	146.0	153.1	160.4	167.8	175.9	183.4
150°	124.7	127.0	130.8	135.1	140.3	146.9	153.5	160.1	167.1	174.0	180.9
152.5°	127.5	129.8	133.1	137.2	141.9	147.8	153.8	159.7	165.9	172.4	178.4
155°	131.9	133.6	136.8	140.0	144.3	149.2	154.1	159.0	163.9	169.4	174.9
157.5°	135.7	137.1	139.9	142.4	146.0	150.2	154.1	157.7	161.8	166.6	170.8
160°	138.3	139.4	141.7	144.1	147.2	150.7	154.1	157.0	160.5	164.4	168.2
162.5°	140.3	141.5	143.3	145.4	147.9	150.9	153.8	156.3	159.3	162.7	165.7
165°	143.2	143.7	145.4	146.9	148.6	151.2	153.3	155.0	157.0	159.6	161.9
167.5°	145.5	146.0	147.2	148.2	149.3	151.2	152.9	153.7	155.0	156.6	158.2
170°	146.9	147.2	148.1	148.6	149.5	150.9	152.4	153.0	153.8	155.0	156.5
172.5°	148.1	147.9	148.8	149.1	149.8	150.7	151.7	152.1	152.5	153.4	154.3
175°	149.2	149.0	149.5	149.5	149.8	150.3	150.9	150.7	150.9	151.2	152.1
177.5°	149.5	149.4	149.8	149.8	149.8	150.0	150.5	150.0	149.8	150.0	150.5
180°	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8



TEST NUMBER: P331422-930
 CATALOG NUMBER: SA2XXDIP-C1005D330U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1686.2	1693.2	1693.2	1694.2	1702.2	1701.2	1700.7
5°	1794.5	1805.1	1806.3	1817.5	1825.0	1822.5	1815.7
7.5°	1896.5	1916.3	1931.3	1939.7	1949.5	1955.7	1952.9
10°	1977.5	2006.3	2023.7	2035.6	2050.0	2060.6	2056.8
12.5°	2051.0	2085.2	2109.3	2129.6	2131.4	2145.1	2135.8
15°	2165.6	2201.8	2205.5	2220.5	2232.5	2231.1	2231.8
17.5°	2203.4	2215.1	2217.5	2217.8	2217.9	2213.5	2204.1
20°	2190.0	2185.6	2175.0	2166.8	2152.5	2150.6	2138.1
22.5°	2126.0	2112.1	2085.5	2067.8	2045.5	2039.6	2036.1
25°	2000.0	1969.4	1926.9	1886.3	1875.0	1853.2	1859.5
27.5°	1827.2	1779.5	1733.5	1700.5	1670.6	1637.9	1647.2
30°	1705.7	1652.0	1587.0	1537.0	1505.1	1473.9	1468.3
32.5°	1560.7	1482.1	1409.6	1365.5	1316.7	1297.0	1275.4
35°	1310.8	1234.0	1162.1	1100.2	1064.7	1037.1	1012.2
37.5°	1086.1	997.6	939.6	889.5	863.7	848.0	852.0
40°	946.6	869.1	826.6	788.5	764.8	753.5	756.0
42.5°	833.6	775.6	740.6	714.5	697.8	691.5	690.1
45°	705.4	672.9	644.2	629.2	621.1	614.2	609.8
47.5°	617.9	591.4	575.2	566.3	559.2	552.2	552.0
50°	565.4	548.0	536.7	527.3	521.7	516.7	521.1
52.5°	525.5	509.5	498.2	489.8	487.7	483.2	483.1
55°	466.1	453.6	445.5	438.0	434.2	431.7	428.6
57.5°	412.1	400.2	392.7	388.0	380.9	378.4	377.4
60°	373.7	364.3	356.8	350.5	347.4	342.4	342.4
62.5°	338.1	328.8	321.8	317.0	311.9	309.9	310.4
65°	286.8	279.3	272.4	267.4	266.2	262.4	263.7
67.5°	239.5	234.6	227.3	224.5	222.2	220.2	218.7
70°	208.1	203.1	199.3	195.6	193.7	193.7	193.7
72.5°	181.6	175.5	173.3	168.6	169.7	167.7	165.7
75°	140.6	136.8	134.9	133.1	130.0	130.0	130.0
77.5°	103.5	102.3	100.1	98.1	97.3	96.7	96.9
80°	80.0	79.3	78.1	78.1	76.9	76.2	75.0
82.5°	61.5	59.8	59.1	58.6	58.4	58.2	58.0
85°	35.0	33.8	33.8	34.3	33.1	33.1	33.8
87.5°	15.2	15.3	14.9	14.9	15.4	14.9	14.9
90°	8.6	9.2	9.5	9.5	9.5	9.5	9.5
92.5°	21.5	19.2	17.4	17.1	16.2	16.4	16.0
95°	57.9	45.8	39.5	35.7	33.4	32.5	32.9
97.5°	144.1	112.9	92.1	78.4	71.3	67.1	64.7
100°	227.3	187.8	153.0	129.1	116.7	108.4	103.1
102.5°	311.9	283.0	246.1	220.0	198.9	188.5	181.5
105°	382.5	386.3	376.8	358.9	341.0	328.6	324.7
107.5°	377.4	407.3	421.3	423.5	422.6	420.0	414.7
110°	361.3	398.1	421.8	434.1	439.6	442.2	441.9



TEST NUMBER: P331422-930

CATALOG NUMBER: SA2XXDIP-C1005D330U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	342.1	381.5	408.6	425.8	435.0	439.9	441.4
115°	316.0	353.8	383.4	403.9	417.1	424.6	427.2
117.5°	294.8	329.1	356.9	377.7	391.8	399.6	401.8
120°	283.7	314.3	340.5	360.7	374.2	382.5	385.5
122.5°	274.5	303.5	327.1	345.2	358.6	366.0	368.4
125°	262.4	287.8	309.4	326.1	337.0	344.2	346.6
127.5°	250.7	274.6	294.5	309.1	319.4	325.5	327.4
130°	242.9	265.6	284.6	298.7	308.5	314.3	316.6
132.5°	235.5	256.4	274.3	288.1	297.9	303.2	305.3
135°	223.8	242.9	258.9	271.3	280.9	286.1	287.2
137.5°	214.6	229.7	243.7	255.0	263.2	267.7	269.5
140°	208.6	221.8	234.5	243.7	251.2	255.5	257.2
142.5°	203.3	214.7	225.3	234.0	240.8	244.7	245.0
145°	196.5	205.4	213.8	220.6	225.6	228.4	229.3
147.5°	190.9	197.9	204.0	209.7	213.6	215.6	216.1
150°	187.3	193.3	198.4	202.8	206.3	208.0	208.3
152.5°	184.3	189.4	193.9	197.3	200.2	201.5	201.6
155°	179.4	183.8	186.9	190.1	192.2	193.3	192.7
157.5°	174.6	178.2	180.8	183.0	184.7	185.2	185.2
160°	171.4	174.6	176.6	178.6	180.0	180.3	180.3
162.5°	168.4	171.1	172.7	174.7	175.7	175.9	175.7
165°	163.9	165.9	167.1	168.2	169.4	169.4	169.1
167.5°	159.8	161.2	162.2	162.7	163.4	163.3	163.0
170°	157.3	158.4	159.0	159.3	160.1	159.9	159.3
172.5°	155.0	155.9	156.2	156.5	156.9	156.6	156.3
175°	152.4	152.7	153.0	153.0	153.3	153.0	152.4
177.5°	150.5	150.7	150.7	150.7	150.7	150.5	150.0
180°	149.8	149.8	149.8	149.8	149.8	149.8	149.8

(END OF REPORT)