

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333185-940

Luminaire Tested: **S125DIP-S610D810U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333185-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S610D810U940-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4730.6 lumens
Efficiency: N/A
Efficacy: 123.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333185-940

CATALOG NUMBER: S125DIP-S610D810U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333185-940

CATALOG NUMBER: S125DIP-S610D810U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	54	54	54	47						47														
1	97	93	89	85	89	85	82	79	72	69	67	59	57	56	47	46	45	40						40														
2	88	81	75	70	81	75	69	65	63	59	55	52	49	46	41	40	38	33						33														
3	81	71	64	58	74	66	59	54	55	50	47	46	42	39	37	34	32	28						28														
4	74	63	55	49	67	58	51	46	49	44	40	41	37	34	33	30	28	24						24														
5	68	56	48	42	62	52	45	39	44	38	34	36	32	29	30	27	24	21						21														
6	62	50	42	36	57	47	39	34	39	34	30	33	29	25	27	24	21	18						18														
7	58	45	37	32	53	42	35	30	36	30	26	30	26	22	24	21	19	16						16														
8	53	41	33	28	49	38	31	26	33	27	23	27	23	20	22	19	17	15						15														
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15	13						13														
10	46	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14	12						12														

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5531	5531	5531
5°	5544	5490	5525
10°	5509	5452	5483
15°	5449	5386	5409
20°	5364	5294	5304
25°	5273	5185	5181
30°	5158	5068	5043
35°	5037	4941	4872
40°	4912	4804	4736
45°	4778	4678	4585
50°	4629	4527	4391
55°	4486	4355	4234
60°	4314	4184	4035
65°	4109	3976	3842
70°	3914	3737	3609
75°	3566	3449	3331
80°	3172	3124	3046
85°	2764	2808	2660



TEST NUMBER: P333185-940

CATALOG NUMBER: S125DIP-S610D810U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.7	1.7
10°-20°	228.1	4.8
20°-30°	336.8	7.1
30°-40°	393.0	8.3
40°-50°	394.7	8.3
50°-60°	346.5	7.3
60°-70°	258.2	5.5
70°-80°	147.6	3.1
80°-90°	44.9	0.9
90°-100°	60.0	1.3
100°-110°	177.2	3.7
110°-120°	300.2	6.3
120°-130°	395.0	8.4
130°-140°	442.6	9.4
140°-150°	433.8	9.2
150°-160°	364.4	7.7
160°-170°	242.2	5.1
170°-180°	84.8	1.8
0°-30°	645.6	13.6
0°-40°	1038.6	22.0
0°-60°	1779.7	37.6
0°-90°	2230.4	47.1
90°-120°	537.4	11.4
90°-150°	1808.9	38.2
90°-180°	2500.0	52.8
0°-180°	4730.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	856	856	856	856	856	
5°	855	853	847	853	852	81
15°	815	813	806	809	809	230
25°	740	736	728	729	727	340
35°	639	636	627	623	618	399
45°	523	520	512	504	502	403
55°	398	396	387	381	376	356
65°	269	267	260	254	251	267
75°	143	142	138	136	134	152
85°	37	38	38	37	36	42
90°	1	6	11	15	17	5
95°	45	47	54	58	60	48
105°	159	162	167	171	173	170
115°	300	303	305	304	303	297
125°	438	443	443	442	441	393
135°	570	574	575	575	572	439
145°	691	694	696	696	694	432
155°	791	791	791	794	791	364
165°	860	858	859	861	858	242
175°	894	891	891	895	890	85
180°	896	896	896	896	896	



TEST NUMBER: P333185-940

CATALOG NUMBER: S125DIP-S610D810U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4
2.5°	858.5	858.2	857.8	857.5	857.1	856.3	855.2	853.9	852.7	851.5	852.7
5°	855.1	854.7	854.4	854.1	853.8	852.9	851.4	849.9	848.4	846.9	848.3
7.5°	847.1	846.9	846.6	846.2	846.0	845.0	843.3	841.7	840.0	838.4	839.6
10°	840.1	839.8	839.5	839.2	838.9	837.9	836.2	834.6	832.9	831.3	832.5
12.5°	831.4	830.9	830.4	829.8	829.3	828.2	826.7	825.2	823.6	822.1	823.0
15°	815.0	814.6	814.1	813.7	813.2	812.2	810.6	808.9	807.2	805.6	806.3
17.5°	796.2	795.6	794.9	794.2	793.5	792.4	790.7	788.9	787.2	785.5	786.4
20°	780.5	780.2	779.9	779.6	779.3	778.2	776.2	774.3	772.3	770.3	771.4
22.5°	764.7	764.2	763.7	763.1	762.6	761.4	759.6	757.8	755.9	754.0	754.7
25°	739.9	739.0	738.3	737.6	736.8	735.5	733.5	731.6	729.6	727.6	728.0
27.5°	710.7	710.2	709.8	709.4	708.9	707.7	705.6	703.6	701.6	699.6	699.6
30°	691.7	691.3	690.8	690.4	689.9	688.6	686.3	684.0	681.8	679.6	679.2
32.5°	671.1	670.5	669.8	669.1	668.3	667.0	665.0	663.0	660.9	659.0	658.4
35°	638.9	638.3	637.7	637.1	636.5	635.2	633.0	630.9	628.8	626.7	626.0
37.5°	605.4	604.7	604.0	603.2	602.4	601.0	599.1	597.1	595.0	593.1	592.0
40°	582.6	581.9	581.1	580.4	579.6	578.2	576.1	574.0	571.9	569.8	568.5
42.5°	558.3	557.7	557.0	556.3	555.7	554.4	552.2	550.2	548.0	545.9	544.7
45°	523.1	522.5	521.8	521.2	520.7	519.4	517.6	515.9	514.0	512.2	510.4
47.5°	485.1	485.1	485.2	485.2	485.2	484.1	482.0	479.8	477.7	475.5	473.7
50°	460.7	460.2	459.8	459.3	458.9	457.8	455.9	454.1	452.4	450.6	448.6
52.5°	435.8	435.4	435.2	434.8	434.4	433.3	431.4	429.4	427.6	425.6	423.9
55°	398.4	397.9	397.4	397.0	396.5	395.3	393.2	391.1	389.0	386.8	385.5
57.5°	358.9	358.7	358.5	358.2	358.0	357.0	355.2	353.4	351.6	349.9	348.1
60°	334.0	333.4	332.8	332.2	331.6	330.5	328.9	327.2	325.5	323.9	322.4
62.5°	308.0	307.6	307.0	306.6	306.0	305.1	303.7	302.3	300.9	299.4	297.8
65°	268.9	268.7	268.4	268.0	267.8	266.8	265.1	263.5	261.8	260.2	258.8
67.5°	231.1	230.5	229.9	229.3	228.6	227.7	226.5	225.2	224.0	222.7	221.6
70°	207.3	206.6	205.8	205.1	204.3	203.2	201.9	200.5	199.2	197.9	196.9
72.5°	181.3	180.7	180.3	179.8	179.2	178.5	177.7	176.8	175.9	175.0	174.1
75°	142.9	142.7	142.3	142.0	141.8	141.2	140.4	139.7	138.9	138.2	137.8
77.5°	107.6	107.5	107.4	107.2	107.1	106.8	106.4	106.0	105.6	105.1	104.9
80°	85.3	85.3	85.3	85.3	85.3	85.2	84.9	84.6	84.4	84.0	83.8
82.5°	65.9	65.6	65.4	65.1	64.9	64.7	64.6	64.6	64.6	64.5	64.2
85°	37.3	37.5	37.5	37.7	37.9	37.9	37.9	37.9	37.9	37.9	37.8
87.5°	14.8	15.0	15.2	15.5	15.8	16.0	16.1	16.1	16.2	16.3	16.5
90°	0.7	2.0	3.2	4.5	5.6	6.8	7.9	9.0	10.1	11.1	11.9
92.5°	16.9	17.7	18.6	19.4	20.3	21.4	22.7	24.1	25.4	26.8	27.8
95°	45.3	45.7	45.9	46.3	46.5	47.5	49.0	50.6	52.2	53.7	54.8
97.5°	75.3	75.4	75.5	75.7	75.8	77.0	79.1	81.2	83.4	85.5	86.5
100°	97.6	97.6	97.6	97.6	97.6	98.6	100.7	102.6	104.7	106.6	108.1
102.5°	121.6	122.3	122.9	123.5	124.1	124.9	125.9	127.0	128.0	129.0	130.5
105°	159.0	159.8	160.5	161.3	162.1	162.9	163.9	164.8	165.7	166.7	167.6
107.5°	200.3	201.0	201.8	202.6	203.4	204.1	204.8	205.5	206.3	207.0	207.4
110°	228.7	229.5	230.2	231.0	231.8	232.5	232.9	233.4	233.8	234.3	234.8



TEST NUMBER: P333185-940

CATALOG NUMBER: S125DIP-S610D810U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	257.7	258.2	258.5	259.0	259.3	259.8	260.4	261.0	261.6	262.2	262.4
115°	300.5	301.1	301.8	302.4	303.0	303.4	303.8	304.1	304.4	304.7	304.5
117.5°	343.5	343.8	344.0	344.3	344.6	344.9	345.2	345.4	345.7	346.0	346.1
120°	370.2	371.0	371.8	372.6	373.4	373.8	374.0	374.2	374.3	374.4	374.4
122.5°	399.2	399.6	399.8	400.1	400.4	400.7	401.1	401.5	401.9	402.3	402.2
125°	438.5	439.5	440.4	441.4	442.3	442.8	443.0	443.2	443.3	443.4	443.2
127.5°	480.5	481.0	481.4	482.0	482.5	482.9	483.0	483.2	483.5	483.7	483.5
130°	505.5	506.3	507.1	507.8	508.6	509.2	509.4	509.8	510.1	510.4	510.2
132.5°	530.7	531.9	533.2	534.4	535.7	536.3	536.3	536.2	536.1	536.1	535.9
135°	570.3	571.3	572.2	573.2	574.1	574.6	574.8	575.0	575.1	575.2	575.2
137.5°	607.8	608.7	609.6	610.5	611.4	612.0	612.3	612.6	613.0	613.3	613.5
140°	631.8	632.5	633.3	634.1	634.8	635.4	635.9	636.4	636.9	637.3	637.7
142.5°	655.8	656.4	657.0	657.6	658.4	659.0	659.5	660.1	660.7	661.3	661.5
145°	691.0	691.6	692.2	692.9	693.5	694.0	694.5	694.9	695.4	695.9	695.9
147.5°	723.6	724.0	724.3	724.7	725.0	725.3	725.8	726.1	726.5	726.8	727.2
150°	745.4	745.2	745.1	744.9	744.8	745.0	745.6	746.3	746.9	747.5	747.5
152.5°	763.2	763.5	763.7	763.9	764.1	764.4	764.6	764.8	765.1	765.4	765.7
155°	790.7	790.7	790.7	790.7	790.7	790.8	790.9	791.1	791.2	791.4	792.0
157.5°	815.3	814.9	814.6	814.2	813.9	813.8	814.0	814.1	814.2	814.4	815.0
160°	829.7	829.3	828.8	828.4	827.9	827.8	827.9	828.0	828.2	828.4	829.0
162.5°	842.6	842.2	841.9	841.6	841.2	841.1	841.1	841.2	841.2	841.2	842.0
165°	859.8	859.4	859.2	858.8	858.5	858.4	858.5	858.7	858.9	859.1	859.7
167.5°	874.2	873.6	873.0	872.4	871.7	871.5	871.5	871.5	871.5	871.5	872.4
170°	882.1	881.5	880.8	880.2	879.6	879.2	879.2	879.2	879.2	879.2	880.2
172.5°	887.6	887.0	886.4	885.7	885.1	884.8	884.8	884.8	884.8	884.8	885.7
175°	893.9	893.3	892.7	892.1	891.4	891.1	891.1	891.1	891.1	891.1	892.1
177.5°	897.2	896.6	896.2	895.6	895.1	894.8	894.7	894.6	894.5	894.3	895.1
180°	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0



TEST NUMBER: P333185-940

CATALOG NUMBER: S125DIP-S610D810U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	856.4	856.4	856.4	856.4	856.4	856.4	856.4	856.4
2.5°	853.9	855.2	856.3	856.8	856.8	856.6	856.5	856.4
5°	849.6	851.0	852.3	852.9	852.7	852.7	852.5	852.3
7.5°	841.0	842.3	843.6	844.3	844.1	843.9	843.8	843.6
10°	833.7	834.9	836.2	836.7	836.5	836.3	836.2	836.1
12.5°	824.0	825.0	825.9	826.4	826.3	826.3	826.3	826.3
15°	807.1	807.8	808.6	809.0	809.0	809.0	809.0	809.0
17.5°	787.4	788.3	789.3	789.3	788.5	787.8	787.1	786.3
20°	772.4	773.5	774.5	774.7	773.9	773.2	772.4	771.7
22.5°	755.5	756.2	756.9	757.0	756.4	755.9	755.4	754.9
25°	728.3	728.5	728.9	728.8	728.3	727.9	727.5	727.0
27.5°	699.7	699.8	699.8	699.6	699.2	698.7	698.3	697.9
30°	678.9	678.7	678.3	678.0	677.5	677.1	676.6	676.2
32.5°	657.9	657.3	656.7	656.1	655.3	654.5	653.6	652.8
35°	625.2	624.5	623.7	622.7	621.5	620.3	619.1	617.9
37.5°	590.8	589.8	588.6	587.7	587.0	586.4	585.7	585.0
40°	567.0	565.7	564.4	563.5	563.0	562.6	562.1	561.7
42.5°	543.5	542.2	541.0	540.0	539.3	538.7	538.0	537.3
45°	508.5	506.8	505.0	503.8	503.4	502.9	502.5	502.0
47.5°	471.8	469.9	468.1	466.7	465.7	464.6	463.5	462.4
50°	446.7	444.7	442.7	441.2	440.1	439.1	438.0	437.0
52.5°	422.1	420.4	418.7	417.3	416.2	414.9	413.8	412.6
55°	384.1	382.8	381.5	380.2	379.2	378.1	377.1	376.0
57.5°	346.3	344.6	342.9	341.7	341.2	340.5	340.0	339.5
60°	320.8	319.3	317.8	316.6	315.5	314.4	313.3	312.4
62.5°	296.2	294.6	292.9	291.8	291.0	290.1	289.3	288.5
65°	257.4	256.1	254.8	253.8	253.2	252.5	252.0	251.4
67.5°	220.5	219.4	218.2	217.4	217.0	216.7	216.3	216.0
70°	196.0	195.1	194.2	193.5	192.9	192.3	191.6	191.1
72.5°	173.0	172.0	170.9	170.1	169.5	169.0	168.4	167.7
75°	137.3	136.9	136.4	135.9	135.3	134.6	134.1	133.5
77.5°	104.6	104.3	104.1	103.7	103.3	102.9	102.5	102.0
80°	83.7	83.6	83.4	83.2	82.8	82.6	82.3	81.9
82.5°	63.9	63.7	63.4	63.2	63.2	63.1	63.0	63.0
85°	37.6	37.5	37.4	37.1	36.8	36.5	36.2	35.9
87.5°	16.7	16.8	16.9	16.9	16.8	16.7	16.5	16.3
90°	12.7	13.5	14.3	14.9	15.3	15.8	16.2	16.8
92.5°	28.8	29.9	30.9	31.6	31.9	32.2	32.5	32.9
95°	55.8	57.0	58.1	58.8	59.0	59.4	59.7	59.9
97.5°	87.6	88.5	89.6	90.2	90.3	90.5	90.8	91.0
100°	109.5	110.8	112.3	113.2	113.4	113.7	114.0	114.3
102.5°	132.1	133.6	135.1	136.1	136.5	136.9	137.3	137.8
105°	168.5	169.4	170.4	171.0	171.6	172.0	172.5	172.9
107.5°	207.9	208.3	208.8	209.0	209.0	208.9	208.9	208.9
110°	235.2	235.7	236.1	236.3	236.1	235.9	235.9	235.7



TEST NUMBER: P333185-940

CATALOG NUMBER: S125DIP-S610D810U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	262.6	262.8	263.1	263.1	262.7	262.4	262.2	261.9
115°	304.4	304.3	304.1	303.9	303.8	303.6	303.4	303.4
117.5°	346.3	346.3	346.5	346.3	345.6	345.0	344.4	343.8
120°	374.4	374.4	374.4	374.2	373.5	372.9	372.3	371.7
122.5°	402.1	402.0	401.8	401.5	401.0	400.6	400.0	399.6
125°	442.8	442.6	442.2	442.0	441.8	441.7	441.6	441.4
127.5°	483.3	483.1	483.0	482.8	482.5	482.1	481.9	481.5
130°	510.1	510.0	509.8	509.5	509.3	508.9	508.6	508.3
132.5°	535.7	535.6	535.5	535.1	534.8	534.3	533.9	533.4
135°	575.2	575.2	575.2	575.0	574.4	573.7	573.1	572.5
137.5°	613.7	613.9	614.0	613.8	613.0	612.2	611.4	610.6
140°	637.9	638.2	638.6	638.3	637.6	636.8	636.0	635.3
142.5°	661.6	661.8	662.0	661.7	660.9	660.2	659.4	658.6
145°	695.9	695.9	695.9	695.6	695.2	694.7	694.3	693.8
147.5°	727.5	728.0	728.3	728.0	726.9	725.9	724.9	723.8
150°	747.5	747.5	747.5	747.3	747.0	746.7	746.4	746.1
152.5°	766.1	766.4	766.8	766.7	766.2	765.6	765.1	764.5
155°	792.6	793.3	793.9	793.8	793.0	792.3	791.5	790.7
157.5°	815.6	816.3	816.9	816.7	815.6	814.7	813.6	812.6
160°	829.6	830.2	830.8	830.8	830.0	829.2	828.4	827.7
162.5°	842.7	843.5	844.2	844.1	843.2	842.3	841.4	840.5
165°	860.3	860.9	861.5	861.4	860.4	859.5	858.5	857.6
167.5°	873.3	874.2	875.2	875.1	874.2	873.3	872.3	871.3
170°	881.1	882.1	883.0	882.9	881.8	880.7	879.7	878.6
172.5°	886.7	887.6	888.6	888.6	887.6	886.6	885.6	884.7
175°	893.0	893.9	894.8	894.7	893.7	892.6	891.5	890.5
177.5°	895.8	896.5	897.3	897.2	896.3	895.5	894.7	893.8
180°	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0

(END OF REPORT)