

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333243-940

Luminaire Tested: **S125DIP-S850D1205U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333243-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S850D1205U940-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6935.1 lumens
Efficiency: N/A
Efficacy: 121.9 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333243-940

CATALOG NUMBER: S125DIP-S850D1205U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333243-940

CATALOG NUMBER: S125DIP-S850D1205U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	97	93	89	85	88	85	82	79	71	68	66	57	56	55	45	44	43	38
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	40	38	37	32
3	81	71	64	58	74	66	59	54	55	50	47	45	42	39	36	33	32	27
4	74	63	55	50	67	58	51	46	49	44	40	40	36	33	32	29	27	24
5	68	56	48	42	62	52	45	40	44	38	34	36	32	29	29	26	24	20
6	62	50	42	37	57	47	40	34	39	34	30	33	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	30	25	22	24	21	19	16
8	53	41	34	28	49	38	31	27	32	27	23	27	23	20	22	19	17	14
9	50	38	30	25	46	35	28	24	30	24	21	25	21	18	20	17	15	13
10	46	34	27	23	43	32	26	21	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7045	7045	7045	7045
5°	8159	7069	6190	7069
10°	9492	7033	5423	7033
15°	10508	6981	5003	6981
20°	11762	6899	4665	6899
25°	13779	6807	4501	6807
30°	14882	6716	4357	6716
35°	12236	6545	4264	6545
40°	8697	6308	4161	6308
45°	6682	5989	4103	5989
50°	5704	5591	4093	5591
55°	5078	5203	4130	5203
60°	4580	4779	4234	4779
65°	4232	4351	4345	4351
70°	3848	3909	4407	3909
75°	3399	3441	4367	3441
80°	2860	2804	3998	2804
85°	2267	2023	3223	2023



TEST NUMBER: P333243-940

CATALOG NUMBER: S125DIP-S850D1205U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.0	1.5
10°-20°	312.7	4.5
20°-30°	507.7	7.3
30°-40°	619.3	8.9
40°-50°	563.4	8.1
50°-60°	448.8	6.5
60°-70°	312.6	4.5
70°-80°	166.7	2.4
80°-90°	44.9	0.6
90°-100°	372.5	5.4
100°-110°	800.8	11.5
110°-120°	751.5	10.8
120°-130°	609.1	8.8
130°-140°	488.8	7.0
140°-150°	368.8	5.3
150°-160°	259.6	3.7
160°-170°	153.0	2.2
170°-180°	49.8	0.7
0°-30°	925.4	13.3
0°-40°	1544.8	22.3
0°-60°	2556.9	36.9
0°-90°	3081.2	44.4
90°-120°	1924.8	27.8
90°-150°	3391.5	48.9
90°-180°	3854.0	55.6
0°-180°	6935.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1091	1091	1091	1091	1091	
5°	1258	1090	955	1090	1258	127
15°	1572	1044	748	1044	1572	450
25°	1934	955	632	955	1934	883
35°	1552	830	541	830	1552	950
45°	732	656	449	656	732	586
55°	451	462	367	462	451	406
65°	277	285	284	285	277	275
75°	136	138	175	138	136	147
85°	31	27	44	27	31	36
90°	24	1	24	1	24	17
95°	244	34	244	34	244	345
105°	1373	117	1373	117	1373	1365
115°	1529	209	1529	209	1529	1494
125°	1205	290	1205	290	1205	1090
135°	1001	340	1001	340	1001	776
145°	790	396	790	396	790	502
155°	662	452	662	452	662	309
165°	580	493	580	493	580	166
175°	521	513	521	513	521	51
180°	514	514	514	514	514	



TEST NUMBER: P333243-940

CATALOG NUMBER: S125DIP-S850D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	1153.9	1152.4	1150.9	1147.9	1150.1	1143.9	1140.9	1135.7	1129.4	1127.2	1124.6
5°	1258.5	1260.8	1263.1	1253.4	1254.4	1247.9	1233.1	1221.0	1211.3	1198.8	1190.0
7.5°	1384.5	1378.9	1378.5	1372.3	1361.4	1352.7	1337.1	1317.3	1298.2	1276.3	1258.2
10°	1447.4	1447.9	1443.7	1436.3	1424.8	1416.4	1396.1	1376.5	1353.0	1325.2	1305.3
12.5°	1494.9	1496.7	1491.5	1481.5	1475.9	1457.1	1441.2	1418.1	1390.0	1367.8	1337.5
15°	1571.6	1566.4	1562.7	1550.2	1540.5	1521.1	1495.6	1471.5	1440.9	1412.6	1384.5
17.5°	1645.4	1649.5	1642.5	1631.1	1601.0	1578.2	1544.1	1511.1	1473.1	1435.2	1401.5
20°	1711.4	1715.0	1704.4	1684.5	1648.4	1625.7	1580.7	1538.2	1494.2	1445.6	1408.5
22.5°	1793.6	1790.6	1776.3	1746.0	1714.7	1672.8	1624.1	1572.3	1517.2	1462.2	1413.0
25°	1933.6	1914.1	1905.3	1867.9	1826.7	1765.1	1698.4	1622.5	1553.9	1481.2	1418.3
27.5°	2011.2	2005.1	1995.3	1969.2	1925.8	1860.0	1781.4	1688.8	1592.1	1500.4	1418.0
30°	1995.6	1996.5	1997.5	1989.1	1961.4	1911.8	1833.6	1734.0	1619.2	1515.9	1420.6
32.5°	1857.9	1874.7	1890.8	1909.9	1917.6	1908.2	1859.1	1769.2	1651.1	1533.7	1419.1
35°	1552.0	1557.2	1609.4	1661.3	1731.7	1786.4	1822.9	1783.2	1683.6	1548.8	1417.3
37.5°	1210.1	1235.2	1271.4	1330.0	1431.6	1522.5	1639.5	1693.3	1661.2	1553.7	1414.1
40°	1031.6	1054.8	1078.3	1138.1	1223.8	1334.0	1466.9	1580.3	1606.7	1538.2	1402.9
42.5°	893.9	912.1	938.3	983.3	1054.9	1152.4	1279.4	1427.7	1518.9	1493.0	1379.7
45°	731.6	743.2	763.6	799.2	851.0	927.5	1039.5	1201.6	1342.7	1389.6	1324.3
47.5°	626.2	626.1	641.9	666.6	704.0	768.9	851.8	978.7	1129.6	1241.2	1236.0
50°	567.7	565.3	577.8	599.1	628.7	671.8	751.0	852.4	997.4	1123.7	1159.0
52.5°	517.3	517.5	525.2	541.0	565.8	602.6	661.7	753.1	877.0	1006.7	1073.0
55°	451.0	449.2	457.9	468.6	486.6	510.7	553.3	623.2	723.7	851.5	937.6
57.5°	390.2	395.3	398.9	406.3	421.2	437.4	473.3	524.6	604.3	714.0	805.0
60°	354.6	359.8	362.6	370.0	382.0	395.9	423.7	465.4	532.4	627.0	717.2
62.5°	322.8	326.8	327.7	334.4	344.2	357.8	379.6	414.6	467.6	550.3	638.7
65°	276.9	276.9	278.7	285.7	290.3	302.4	319.1	344.5	387.1	451.5	526.9
67.5°	232.6	234.9	234.3	237.5	241.7	251.0	263.0	284.0	315.6	362.6	422.9
70°	203.8	205.5	205.1	207.4	212.0	218.1	227.8	247.7	270.4	310.7	362.6
72.5°	177.8	178.5	177.4	180.4	183.2	188.4	199.3	209.9	231.1	265.1	307.7
75°	136.2	137.1	137.9	139.8	142.6	145.3	151.0	161.6	175.5	201.0	228.3
77.5°	102.0	100.3	102.5	102.3	103.8	105.9	110.8	116.5	127.9	144.0	165.1
80°	76.9	77.3	77.3	77.8	80.1	81.5	85.7	89.8	98.6	110.7	125.5
82.5°	56.1	57.3	56.6	57.4	59.4	60.4	62.7	66.1	71.2	80.7	91.4
85°	30.6	28.3	29.2	30.1	30.1	30.6	32.4	33.8	36.6	40.3	44.4
87.5°	13.6	14.4	14.5	14.5	14.9	14.5	15.8	15.6	16.5	17.4	18.5
90°	23.8	23.8	22.8	22.8	22.8	20.7	19.7	18.6	17.7	16.6	14.5
92.5°	66.1	67.8	69.2	71.7	85.0	100.3	133.2	183.6	270.5	334.0	339.5
95°	243.5	260.1	268.3	299.4	373.0	460.0	587.5	744.9	898.3	918.0	749.1
97.5°	588.5	601.8	631.9	689.8	753.9	874.9	999.1	1109.5	1136.7	980.3	669.0
100°	808.2	824.7	863.1	937.7	1009.1	1117.0	1223.7	1274.4	1194.6	935.6	596.8
102.5°	1053.6	1066.0	1107.6	1160.7	1237.2	1310.1	1361.3	1330.0	1159.8	856.8	542.1
105°	1372.9	1385.3	1406.0	1440.2	1473.4	1484.8	1439.2	1297.3	1048.6	751.2	489.0
107.5°	1542.4	1550.7	1557.6	1557.7	1541.0	1486.8	1369.8	1180.4	935.0	678.4	466.6
110°	1598.7	1598.7	1591.5	1571.8	1525.2	1437.1	1291.0	1094.1	870.3	644.4	460.0



TEST NUMBER: P333243-940

CATALOG NUMBER: S125DIP-S850D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1592.1	1584.7	1566.6	1532.9	1464.6	1360.8	1213.1	1026.2	822.2	624.6	460.0
115°	1529.3	1515.8	1486.8	1437.1	1356.3	1243.3	1101.4	940.8	769.8	603.1	463.2
117.5°	1419.2	1411.0	1382.2	1330.8	1250.0	1146.4	1024.1	885.6	738.5	592.5	470.0
120°	1348.0	1339.7	1311.7	1262.0	1185.4	1094.1	980.2	855.9	721.1	587.5	476.6
122.5°	1285.0	1277.6	1249.6	1204.0	1135.6	1050.3	948.7	833.5	706.2	583.4	482.4
125°	1205.1	1194.6	1171.9	1129.4	1071.4	996.8	906.6	800.9	685.9	578.2	492.1
127.5°	1136.7	1132.1	1110.5	1073.0	1020.4	950.6	866.4	767.8	667.3	575.7	503.1
130°	1099.3	1093.1	1072.4	1038.2	986.4	919.1	838.2	747.1	654.9	574.0	509.8
132.5°	1062.0	1055.0	1035.9	1001.7	949.9	885.0	811.7	726.3	644.9	574.0	517.2
135°	1000.9	994.7	976.1	941.8	896.3	837.2	770.9	699.4	633.1	574.0	527.4
137.5°	935.6	928.8	911.6	880.5	839.7	789.5	734.4	676.6	622.5	575.2	536.7
140°	890.0	884.8	869.3	842.4	804.1	760.5	712.8	664.1	617.5	576.0	540.8
142.5°	847.7	843.4	828.7	805.9	773.4	735.7	694.6	653.4	613.4	576.9	543.3
145°	789.5	785.4	774.0	756.3	731.5	703.6	671.4	639.3	607.2	576.0	546.1
147.5°	740.2	738.3	731.7	717.6	697.9	676.8	652.1	626.1	600.7	573.4	547.1
150°	712.8	711.9	707.7	695.3	679.7	661.0	641.4	618.6	595.8	570.9	547.1
152.5°	691.3	690.3	686.1	676.2	663.2	648.6	630.6	610.3	590.0	567.6	546.3
155°	662.1	661.0	657.9	650.7	640.3	628.9	614.4	597.8	580.2	561.6	543.9
157.5°	636.0	636.1	633.3	627.2	619.2	610.3	599.1	585.4	571.1	555.4	541.3
160°	618.6	619.6	617.5	612.3	605.1	597.8	587.5	577.1	563.7	551.3	538.8
162.5°	602.8	603.1	602.6	598.2	592.6	586.2	577.6	568.0	557.1	546.3	536.3
165°	580.2	580.2	580.2	578.2	574.0	568.8	562.6	555.4	547.1	538.8	532.5
167.5°	559.5	559.7	560.5	558.7	556.6	552.9	548.1	543.3	537.3	531.5	526.7
170°	547.1	548.1	548.1	547.1	545.0	543.0	539.8	536.7	531.5	527.4	524.3
172.5°	535.5	536.5	538.1	536.3	535.9	534.7	532.4	529.2	525.8	522.5	520.9
175°	521.2	522.2	524.3	523.3	523.3	523.3	521.2	521.2	518.1	517.0	517.0
177.5°	513.9	513.9	516.4	515.6	516.4	516.4	516.4	515.6	514.8	513.9	513.9
180°	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9



TEST NUMBER: P333243-940

CATALOG NUMBER: S125DIP-S850D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	1122.4	1119.8	1116.8	1111.6	1105.4	1102.0	1096.8	1093.5	1086.8	1081.3	1075.3
5°	1179.3	1167.2	1156.2	1141.8	1126.1	1115.9	1103.8	1090.4	1076.6	1062.2	1046.4
7.5°	1238.3	1217.0	1193.8	1168.9	1144.6	1122.2	1100.8	1079.8	1060.2	1036.4	1016.4
10°	1277.9	1251.1	1222.4	1188.6	1155.7	1127.0	1097.9	1072.4	1046.4	1018.7	994.1
12.5°	1317.6	1281.8	1241.3	1204.2	1164.6	1130.0	1095.6	1063.1	1030.6	999.8	971.2
15°	1345.6	1314.0	1276.6	1223.8	1179.3	1131.7	1086.3	1044.1	1004.8	970.5	934.4
17.5°	1364.0	1323.4	1283.2	1232.5	1174.2	1120.9	1069.5	1021.3	976.9	933.4	898.7
20°	1367.3	1325.6	1283.5	1233.9	1174.2	1113.1	1061.8	1003.8	956.2	911.2	868.6
22.5°	1366.2	1319.0	1273.1	1222.1	1163.9	1107.6	1045.4	986.4	934.7	890.5	846.1
25°	1355.8	1305.3	1247.9	1196.5	1139.1	1079.3	1016.4	955.2	902.4	851.9	808.0
27.5°	1347.0	1281.6	1216.6	1156.6	1101.2	1046.4	986.1	923.5	865.0	813.9	772.4
30°	1336.3	1264.5	1191.3	1128.8	1071.9	1018.7	961.7	900.6	839.5	789.4	745.0
32.5°	1326.7	1243.0	1165.8	1097.8	1037.4	985.7	933.2	875.0	815.0	764.3	719.8
35°	1308.1	1211.3	1122.8	1046.0	981.6	928.4	884.4	830.2	775.1	726.0	683.4
37.5°	1284.4	1169.6	1074.7	994.1	923.5	867.5	826.5	784.9	732.0	684.7	646.2
40°	1265.9	1140.0	1039.5	957.1	884.0	825.5	787.6	748.2	704.3	660.3	619.6
42.5°	1242.6	1113.3	1004.0	915.3	842.8	786.0	746.1	712.7	673.9	632.8	595.0
45°	1199.7	1065.0	946.5	851.0	777.8	721.8	680.6	655.7	626.5	587.5	555.6
47.5°	1136.7	1006.9	884.3	785.9	710.3	658.4	619.8	595.8	575.2	546.4	517.4
50°	1080.7	963.6	839.5	741.7	666.3	613.9	578.4	556.5	539.0	516.7	492.2
52.5°	1018.1	909.1	795.4	698.8	624.1	572.5	537.6	518.4	503.8	487.9	463.7
55°	918.6	826.1	720.5	628.7	559.8	509.3	478.8	462.1	450.0	438.0	423.2
57.5°	809.0	736.6	643.1	559.4	495.8	449.9	421.3	405.1	395.8	389.6	380.8
60°	732.0	670.0	589.4	513.0	451.0	410.3	382.5	370.0	362.1	357.0	350.5
62.5°	660.6	609.7	534.9	465.2	411.0	372.5	347.7	335.6	328.0	325.5	320.1
65°	555.2	515.9	454.2	396.4	350.1	317.2	296.3	284.7	280.1	277.3	277.9
67.5°	451.4	427.4	377.9	328.6	291.6	264.0	247.4	238.4	236.1	232.5	232.4
70°	388.0	370.0	328.3	285.3	252.4	231.0	216.2	207.0	204.6	202.8	202.3
72.5°	332.1	316.3	280.1	245.6	216.1	197.3	185.1	179.6	175.8	174.7	174.6
75°	249.6	240.8	212.0	184.8	164.3	151.4	143.1	137.9	135.2	134.7	135.2
77.5°	177.5	169.8	151.5	132.2	119.3	109.5	102.5	100.7	97.6	97.6	97.1
80°	133.3	128.2	116.7	101.4	90.8	82.4	78.7	75.4	74.5	73.1	74.5
82.5°	96.7	91.2	83.4	73.7	64.8	59.8	56.1	55.1	54.6	53.9	54.2
85°	47.7	48.2	43.5	36.1	32.4	29.6	27.3	27.3	26.8	26.4	26.8
87.5°	19.0	17.8	16.1	14.6	12.4	10.8	10.1	10.2	9.3	9.4	10.2
90°	13.5	11.4	10.3	8.3	6.2	4.1	2.1	1.1	2.1	4.1	6.2
92.5°	236.5	141.5	85.0	54.8	36.9	24.1	15.3	12.7	15.3	24.1	36.9
95°	463.2	235.2	124.3	77.7	54.9	43.5	35.2	34.2	35.2	43.5	54.9
97.5°	369.7	202.7	129.3	95.8	75.3	63.8	58.1	56.8	58.1	63.8	75.3
100°	335.7	201.0	140.9	109.9	90.2	78.7	74.6	72.5	74.6	78.7	90.2
102.5°	321.6	208.5	155.0	124.8	106.7	94.5	91.2	90.0	91.2	94.5	106.7
105°	316.0	223.8	178.3	149.2	132.6	122.3	117.1	117.1	117.1	122.3	132.6
107.5°	325.6	246.6	202.4	176.4	159.2	150.6	145.7	143.6	145.7	150.6	159.2
110°	334.7	263.1	220.7	193.8	178.3	168.9	164.8	162.6	164.8	168.9	178.3



TEST NUMBER: P333243-940

CATALOG NUMBER: S125DIP-S850D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	346.3	278.9	238.1	212.0	196.4	187.1	183.8	181.7	183.8	187.1	196.4
115°	363.6	303.6	265.3	239.3	223.8	214.5	211.3	209.3	211.3	214.5	223.8
117.5°	383.6	328.9	292.6	267.5	249.9	240.6	237.3	234.2	237.3	240.6	249.9
120°	396.8	347.1	310.9	284.9	267.3	258.0	253.9	250.7	253.9	258.0	267.3
122.5°	411.8	364.5	328.2	302.4	283.0	273.8	270.5	268.1	270.5	273.8	283.0
125°	432.0	387.5	353.3	326.4	306.7	297.4	292.2	290.1	292.2	297.4	306.7
127.5°	450.8	409.7	376.7	349.8	328.9	317.1	310.4	307.3	310.4	317.1	328.9
130°	463.2	423.7	391.6	364.7	343.0	329.5	321.2	318.1	321.2	329.5	343.0
132.5°	473.9	437.0	404.9	378.0	355.4	340.3	330.3	326.4	330.3	340.3	355.4
135°	489.0	454.9	422.8	394.8	373.0	356.4	344.0	339.8	344.0	356.4	373.0
137.5°	500.2	467.5	438.3	409.5	388.2	371.6	360.0	356.9	360.0	371.6	388.2
140°	507.7	476.6	446.6	418.6	399.0	382.4	369.9	366.8	369.9	382.4	399.0
142.5°	511.8	482.4	454.1	427.8	408.8	392.3	380.7	378.4	380.7	392.3	408.8
145°	518.1	492.1	465.2	441.4	422.8	408.2	397.9	395.8	397.9	408.2	422.8
147.5°	521.8	498.4	474.7	453.8	437.7	424.2	415.3	414.0	415.3	424.2	437.7
150°	524.3	502.5	479.7	462.1	447.6	434.2	426.9	424.8	426.9	434.2	447.6
152.5°	525.9	506.7	485.5	469.6	455.9	444.1	437.7	436.4	437.7	444.1	455.9
155°	527.4	510.8	493.2	478.7	468.3	458.0	451.7	451.7	451.7	458.0	468.3
157.5°	528.4	514.3	499.2	488.2	479.1	470.2	465.2	465.5	465.2	470.2	479.1
160°	528.4	516.0	502.5	493.2	484.9	477.7	473.5	474.6	473.5	477.7	484.9
162.5°	527.6	517.6	505.9	498.2	491.5	485.1	481.0	482.0	481.0	485.1	491.5
165°	526.4	518.1	509.8	503.5	499.4	494.3	491.2	493.2	491.2	494.3	499.4
167.5°	523.9	518.1	511.2	507.3	504.4	501.5	499.6	500.7	499.6	501.5	504.4
170°	522.2	518.1	512.9	509.8	507.7	505.6	504.6	505.6	504.6	505.6	507.7
172.5°	520.6	517.2	512.9	511.4	510.1	508.1	507.1	509.0	507.1	508.1	510.1
175°	518.1	516.0	512.9	512.9	512.9	511.8	510.8	512.9	510.8	511.8	512.9
177.5°	515.6	514.8	513.1	513.1	513.9	513.1	513.1	514.8	513.1	513.1	513.9
180°	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9



TEST NUMBER: P333243-940

CATALOG NUMBER: S125DIP-S850D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	1072.0	1067.9	1064.6	1057.2	1053.1	1047.6	1043.1	1047.9	1042.8	1045.0	1041.6
5°	1038.6	1025.6	1016.4	1002.9	991.3	980.7	972.9	971.4	967.7	965.9	960.3
7.5°	998.4	982.1	966.3	948.7	933.8	918.7	909.1	901.2	895.9	888.9	884.2
10°	974.6	952.9	934.4	913.1	894.6	878.3	865.4	858.9	852.9	844.1	840.9
12.5°	945.4	922.9	900.3	877.5	859.8	841.7	830.5	820.7	816.6	806.6	805.7
15°	910.3	876.6	854.3	831.2	806.6	791.8	782.5	771.9	767.2	760.3	755.2
17.5°	868.4	838.3	810.5	786.5	765.4	753.0	741.5	734.1	726.2	721.7	713.4
20°	838.1	809.4	781.6	756.1	739.9	725.6	716.3	709.4	701.1	698.7	690.4
22.5°	812.5	780.9	754.2	732.8	715.1	698.9	688.8	684.2	678.4	671.3	669.6
25°	771.0	738.1	715.4	694.1	678.3	663.5	656.6	650.6	645.0	639.9	638.0
27.5°	735.0	705.6	678.7	659.4	645.8	632.2	626.1	618.8	614.7	610.6	605.6
30°	709.8	679.8	656.1	637.6	622.8	610.7	604.2	599.1	595.5	591.7	589.0
32.5°	683.9	656.0	633.1	615.0	600.2	591.1	585.3	581.8	577.7	573.2	569.7
35°	649.6	619.0	596.8	581.1	569.5	562.6	556.1	552.9	548.2	548.2	544.5
37.5°	611.0	584.6	565.0	550.6	540.3	534.0	527.0	524.8	521.8	519.9	518.6
40°	588.1	563.5	545.0	530.7	519.5	514.4	508.9	505.2	503.3	501.0	500.1
42.5°	564.4	540.9	523.2	509.9	500.2	495.9	490.7	488.1	484.4	481.3	480.8
45°	528.3	505.6	489.5	478.8	470.5	465.4	462.1	456.6	454.7	451.0	450.5
47.5°	494.1	472.3	456.5	447.7	440.4	436.2	431.1	425.6	423.5	421.6	421.4
50°	468.6	448.7	433.8	425.5	418.6	412.6	407.4	403.8	402.3	402.3	403.3
52.5°	442.6	425.7	413.1	403.0	396.4	389.9	385.2	383.0	380.8	383.1	384.8
55°	404.7	387.5	378.3	368.5	362.1	354.6	352.4	351.4	350.1	353.7	355.6
57.5°	364.5	352.5	341.6	332.0	326.2	321.9	318.8	318.2	320.7	322.5	328.6
60°	338.9	325.0	315.3	307.9	301.0	298.2	297.3	296.3	298.2	303.3	311.1
62.5°	310.8	299.5	289.0	283.5	278.4	273.8	273.6	274.1	277.9	283.7	291.5
65°	269.5	259.8	252.8	246.3	242.2	239.4	240.3	242.2	246.3	254.2	263.0
67.5°	227.6	220.9	214.6	209.4	205.4	205.4	206.3	209.1	214.0	223.1	231.1
70°	200.5	193.1	188.0	185.7	182.4	180.6	183.3	188.0	192.2	200.5	207.4
72.5°	173.4	167.2	163.2	161.6	160.2	158.7	159.6	164.6	170.3	178.6	186.7
75°	133.3	131.0	128.2	126.4	125.0	125.9	126.9	131.5	136.2	144.9	154.2
77.5°	97.3	94.9	93.3	92.8	92.0	92.5	95.1	98.5	103.1	109.5	116.5
80°	73.7	72.7	71.8	71.3	71.3	71.8	75.4	77.8	81.9	88.0	93.5
82.5°	53.6	53.1	52.9	52.8	53.1	53.2	55.5	58.5	62.0	66.5	71.3
85°	28.3	27.3	28.7	29.2	28.3	29.6	30.6	32.4	33.8	36.1	38.4
87.5°	10.9	12.0	11.9	12.7	12.9	14.1	13.9	15.6	16.5	17.5	17.6
90°	8.3	10.3	11.4	13.5	14.5	16.6	17.7	18.6	19.7	20.7	22.8
92.5°	54.8	85.0	141.5	236.5	339.5	334.0	270.5	183.6	133.2	100.3	85.0
95°	77.7	124.3	235.2	463.2	749.1	918.0	898.3	744.9	587.5	460.0	373.0
97.5°	95.8	129.3	202.7	369.7	669.0	980.3	1136.7	1109.5	999.1	874.9	753.9
100°	109.9	140.9	201.0	335.7	596.8	935.6	1194.6	1274.4	1223.7	1117.0	1009.1
102.5°	124.8	155.0	208.5	321.6	542.1	856.8	1159.8	1330.0	1361.3	1310.1	1237.2
105°	149.2	178.3	223.8	316.0	489.0	751.2	1048.6	1297.3	1439.2	1484.8	1473.4
107.5°	176.4	202.4	246.6	325.6	466.6	678.4	935.0	1180.4	1369.8	1486.8	1541.0
110°	193.8	220.7	263.1	334.7	460.0	644.4	870.3	1094.1	1291.0	1437.1	1525.2



TEST NUMBER: P333243-940

CATALOG NUMBER: S125DIP-S850D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	212.0	238.1	278.9	346.3	460.0	624.6	822.2	1026.2	1213.1	1360.8	1464.6
115°	239.3	265.3	303.6	363.6	463.2	603.1	769.8	940.8	1101.4	1243.3	1356.3
117.5°	267.5	292.6	328.9	383.6	470.0	592.5	738.5	885.6	1024.1	1146.4	1250.0
120°	284.9	310.9	347.1	396.8	476.6	587.5	721.1	855.9	980.2	1094.1	1185.4
122.5°	302.4	328.2	364.5	411.8	482.4	583.4	706.2	833.5	948.7	1050.3	1135.6
125°	326.4	353.3	387.5	432.0	492.1	578.2	685.9	800.9	906.6	996.8	1071.4
127.5°	349.8	376.7	409.7	450.8	503.1	575.7	667.3	767.8	866.4	950.6	1020.4
130°	364.7	391.6	423.7	463.2	509.8	574.0	654.9	747.1	838.2	919.1	986.4
132.5°	378.0	404.9	437.0	473.9	517.2	574.0	644.9	726.3	811.7	885.0	949.9
135°	394.8	422.8	454.9	489.0	527.4	574.0	633.1	699.4	770.9	837.2	896.3
137.5°	409.5	438.3	467.5	500.2	536.7	575.2	622.5	676.6	734.4	789.5	839.7
140°	418.6	446.6	476.6	507.7	540.8	576.0	617.5	664.1	712.8	760.5	804.1
142.5°	427.8	454.1	482.4	511.8	543.3	576.9	613.4	653.4	694.6	735.7	773.4
145°	441.4	465.2	492.1	518.1	546.1	576.0	607.2	639.3	671.4	703.6	731.5
147.5°	453.8	474.7	498.4	521.8	547.1	573.4	600.7	626.1	652.1	676.8	697.9
150°	462.1	479.7	502.5	524.3	547.1	570.9	595.8	618.6	641.4	661.0	679.7
152.5°	469.6	485.5	506.7	525.9	546.3	567.6	590.0	610.3	630.6	648.6	663.2
155°	478.7	493.2	510.8	527.4	543.9	561.6	580.2	597.8	614.4	628.9	640.3
157.5°	488.2	499.2	514.3	528.4	541.3	555.4	571.1	585.4	599.1	610.3	619.2
160°	493.2	502.5	516.0	528.4	538.8	551.3	563.7	577.1	587.5	597.8	605.1
162.5°	498.2	505.9	517.6	527.6	536.3	546.3	557.1	568.0	577.6	586.2	592.6
165°	503.5	509.8	518.1	526.4	532.5	538.8	547.1	555.4	562.6	568.8	574.0
167.5°	507.3	511.2	518.1	523.9	526.7	531.5	537.3	543.3	548.1	552.9	556.6
170°	509.8	512.9	518.1	522.2	524.3	527.4	531.5	536.7	539.8	543.0	545.0
172.5°	511.4	512.9	517.2	520.6	520.9	522.5	525.8	529.2	532.4	534.7	535.9
175°	512.9	512.9	516.0	518.1	517.0	517.0	518.1	521.2	521.2	523.3	523.3
177.5°	513.1	513.1	514.8	515.6	513.9	513.9	514.8	515.6	516.4	516.4	516.4
180°	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9



TEST NUMBER: P333243-940

CATALOG NUMBER: S125DIP-S850D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	1039.4	1042.0	1039.7	1042.8	1039.7	1042.0	1039.4	1041.6	1045.0	1042.8	1047.9
5°	958.0	953.9	956.6	954.8	956.6	953.9	958.0	960.3	965.9	967.7	971.4
7.5°	882.8	878.8	874.3	872.2	874.3	878.8	882.8	884.2	888.9	895.9	901.2
10°	835.8	830.6	830.2	827.0	830.2	830.6	835.8	840.9	844.1	852.9	858.9
12.5°	801.3	796.6	791.3	790.0	791.3	796.6	801.3	805.7	806.6	816.6	820.7
15°	752.4	748.7	745.5	748.2	745.5	748.7	752.4	755.2	760.3	767.2	771.9
17.5°	711.8	708.7	708.1	704.7	708.1	708.7	711.8	713.4	721.7	726.2	734.1
20°	686.2	683.9	684.8	678.8	684.8	683.9	686.2	690.4	698.7	701.1	709.4
22.5°	665.8	661.3	660.8	659.5	660.8	661.3	665.8	669.6	671.3	678.4	684.2
25°	633.9	631.6	629.3	631.6	629.3	631.6	633.9	638.0	639.9	645.0	650.6
27.5°	606.0	603.2	602.6	602.9	602.6	603.2	606.0	605.6	610.6	614.7	618.8
30°	589.0	584.3	584.8	584.3	584.8	584.3	589.0	589.0	591.7	595.5	599.1
32.5°	570.4	567.3	566.7	565.8	566.7	567.3	570.4	569.7	573.2	577.7	581.8
35°	543.1	543.1	540.8	540.8	540.8	543.1	543.1	544.5	548.2	548.2	552.9
37.5°	517.5	517.0	515.6	515.9	515.6	517.0	517.5	518.6	519.9	521.8	524.8
40°	498.2	497.8	496.3	493.6	496.3	497.8	498.2	500.1	501.0	503.3	505.2
42.5°	479.7	478.1	477.5	476.5	477.5	478.1	479.7	480.8	481.3	484.4	488.1
45°	450.5	450.5	449.6	449.2	449.6	450.5	450.5	450.5	451.0	454.7	456.6
47.5°	422.2	423.0	424.8	424.5	424.8	423.0	422.2	421.4	421.6	423.5	425.6
50°	405.1	405.6	407.0	407.4	407.0	405.6	405.1	403.3	402.3	402.3	403.8
52.5°	386.3	389.0	390.7	390.4	390.7	389.0	386.3	384.8	383.1	380.8	383.0
55°	359.8	363.0	366.2	366.8	366.2	363.0	359.8	355.6	353.7	350.1	351.4
57.5°	333.6	338.1	341.5	342.6	341.5	338.1	333.6	328.6	322.5	320.7	318.2
60°	315.8	321.8	326.0	327.8	326.0	321.8	315.8	311.1	303.3	298.2	296.3
62.5°	298.7	305.5	309.7	310.0	309.7	305.5	298.7	291.5	283.7	277.9	274.1
65°	270.9	277.9	281.5	284.3	281.5	277.9	270.9	263.0	254.2	246.3	242.2
67.5°	240.9	247.8	251.9	254.1	251.9	247.8	240.9	231.1	223.1	214.0	209.1
70°	219.0	226.0	231.5	233.4	231.5	226.0	219.0	207.4	200.5	192.2	188.0
72.5°	197.5	203.8	208.2	210.4	208.2	203.8	197.5	186.7	178.6	170.3	164.6
75°	160.2	168.5	172.7	175.0	172.7	168.5	160.2	154.2	144.9	136.2	131.5
77.5°	123.5	131.2	133.7	134.8	133.7	131.2	123.5	116.5	109.5	103.1	98.5
80°	99.1	103.7	106.9	107.5	106.9	103.7	99.1	93.5	88.0	81.9	77.8
82.5°	76.2	80.0	81.1	82.2	81.1	80.0	76.2	71.3	66.5	62.0	58.5
85°	41.6	43.5	44.0	43.5	44.0	43.5	41.6	38.4	36.1	33.8	32.4
87.5°	18.3	17.9	18.1	18.8	18.1	17.9	18.3	17.6	17.5	16.5	15.6
90°	22.8	22.8	23.8	23.8	23.8	22.8	22.8	22.8	20.7	19.7	18.6
92.5°	71.7	69.2	67.8	66.1	67.8	69.2	71.7	85.0	100.3	133.2	183.6
95°	299.4	268.3	260.1	243.5	260.1	268.3	299.4	373.0	460.0	587.5	744.9
97.5°	689.8	631.9	601.8	588.5	601.8	631.9	689.8	753.9	874.9	999.1	1109.5
100°	937.7	863.1	824.7	808.2	824.7	863.1	937.7	1009.1	1117.0	1223.7	1274.4
102.5°	1160.7	1107.6	1066.0	1053.6	1066.0	1107.6	1160.7	1237.2	1310.1	1361.3	1330.0
105°	1440.2	1406.0	1385.3	1372.9	1385.3	1406.0	1440.2	1473.4	1484.8	1439.2	1297.3
107.5°	1557.7	1557.6	1550.7	1542.4	1550.7	1557.6	1557.7	1541.0	1486.8	1369.8	1180.4
110°	1571.8	1591.5	1598.7	1598.7	1598.7	1591.5	1571.8	1525.2	1437.1	1291.0	1094.1



TEST NUMBER: P333243-940

CATALOG NUMBER: S125DIP-S850D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1532.9	1566.6	1584.7	1592.1	1584.7	1566.6	1532.9	1464.6	1360.8	1213.1	1026.2
115°	1437.1	1486.8	1515.8	1529.3	1515.8	1486.8	1437.1	1356.3	1243.3	1101.4	940.8
117.5°	1330.8	1382.2	1411.0	1419.2	1411.0	1382.2	1330.8	1250.0	1146.4	1024.1	885.6
120°	1262.0	1311.7	1339.7	1348.0	1339.7	1311.7	1262.0	1185.4	1094.1	980.2	855.9
122.5°	1204.0	1249.6	1277.6	1285.0	1277.6	1249.6	1204.0	1135.6	1050.3	948.7	833.5
125°	1129.4	1171.9	1194.6	1205.1	1194.6	1171.9	1129.4	1071.4	996.8	906.6	800.9
127.5°	1073.0	1110.5	1132.1	1136.7	1132.1	1110.5	1073.0	1020.4	950.6	866.4	767.8
130°	1038.2	1072.4	1093.1	1099.3	1093.1	1072.4	1038.2	986.4	919.1	838.2	747.1
132.5°	1001.7	1035.9	1055.0	1062.0	1055.0	1035.9	1001.7	949.9	885.0	811.7	726.3
135°	941.8	976.1	994.7	1000.9	994.7	976.1	941.8	896.3	837.2	770.9	699.4
137.5°	880.5	911.6	928.8	935.6	928.8	911.6	880.5	839.7	789.5	734.4	676.6
140°	842.4	869.3	884.8	890.0	884.8	869.3	842.4	804.1	760.5	712.8	664.1
142.5°	805.9	828.7	843.4	847.7	843.4	828.7	805.9	773.4	735.7	694.6	653.4
145°	756.3	774.0	785.4	789.5	785.4	774.0	756.3	731.5	703.6	671.4	639.3
147.5°	717.6	731.7	738.3	740.2	738.3	731.7	717.6	697.9	676.8	652.1	626.1
150°	695.3	707.7	711.9	712.8	711.9	707.7	695.3	679.7	661.0	641.4	618.6
152.5°	676.2	686.1	690.3	691.3	690.3	686.1	676.2	663.2	648.6	630.6	610.3
155°	650.7	657.9	661.0	662.1	661.0	657.9	650.7	640.3	628.9	614.4	597.8
157.5°	627.2	633.3	636.1	636.0	636.1	633.3	627.2	619.2	610.3	599.1	585.4
160°	612.3	617.5	619.6	618.6	619.6	617.5	612.3	605.1	597.8	587.5	577.1
162.5°	598.2	602.6	603.1	602.8	603.1	602.6	598.2	592.6	586.2	577.6	568.0
165°	578.2	580.2	580.2	580.2	580.2	580.2	578.2	574.0	568.8	562.6	555.4
167.5°	558.7	560.5	559.7	559.5	559.7	560.5	558.7	556.6	552.9	548.1	543.3
170°	547.1	548.1	548.1	547.1	548.1	548.1	547.1	545.0	543.0	539.8	536.7
172.5°	536.3	538.1	536.5	535.5	536.5	538.1	536.3	535.9	534.7	532.4	529.2
175°	523.3	524.3	522.2	521.2	522.2	524.3	523.3	523.3	523.3	521.2	521.2
177.5°	515.6	516.4	513.9	513.9	513.9	516.4	515.6	516.4	516.4	516.4	515.6
180°	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9



TEST NUMBER: P333243-940

CATALOG NUMBER: S125DIP-S850D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	1043.1	1047.6	1053.1	1057.2	1064.6	1067.9	1072.0	1075.3	1081.3	1086.8	1093.5
5°	972.9	980.7	991.3	1002.9	1016.4	1025.6	1038.6	1046.4	1062.2	1076.6	1090.4
7.5°	909.1	918.7	933.8	948.7	966.3	982.1	998.4	1016.4	1036.4	1060.2	1079.8
10°	865.4	878.3	894.6	913.1	934.4	952.9	974.6	994.1	1018.7	1046.4	1072.4
12.5°	830.5	841.7	859.8	877.5	900.3	922.9	945.4	971.2	999.8	1030.6	1063.1
15°	782.5	791.8	806.6	831.2	854.3	876.6	910.3	934.4	970.5	1004.8	1044.1
17.5°	741.5	753.0	765.4	786.5	810.5	838.3	868.4	898.7	933.4	976.9	1021.3
20°	716.3	725.6	739.9	756.1	781.6	809.4	838.1	868.6	911.2	956.2	1003.8
22.5°	688.8	698.9	715.1	732.8	754.2	780.9	812.5	846.1	890.5	934.7	986.4
25°	656.6	663.5	678.3	694.1	715.4	738.1	771.0	808.0	851.9	902.4	955.2
27.5°	626.1	632.2	645.8	659.4	678.7	705.6	735.0	772.4	813.9	865.0	923.5
30°	604.2	610.7	622.8	637.6	656.1	679.8	709.8	745.0	789.4	839.5	900.6
32.5°	585.3	591.1	600.2	615.0	633.1	656.0	683.9	719.8	764.3	815.0	875.0
35°	556.1	562.6	569.5	581.1	596.8	619.0	649.6	683.4	726.0	775.1	830.2
37.5°	527.0	534.0	540.3	550.6	565.0	584.6	611.0	646.2	684.7	732.0	784.9
40°	508.9	514.4	519.5	530.7	545.0	563.5	588.1	619.6	660.3	704.3	748.2
42.5°	490.7	495.9	500.2	509.9	523.2	540.9	564.4	595.0	632.8	673.9	712.7
45°	462.1	465.4	470.5	478.8	489.5	505.6	528.3	555.6	587.5	626.5	655.7
47.5°	431.1	436.2	440.4	447.7	456.5	472.3	494.1	517.4	546.4	575.2	595.8
50°	407.4	412.6	418.6	425.5	433.8	448.7	468.6	492.2	516.7	539.0	556.5
52.5°	385.2	389.9	396.4	403.0	413.1	425.7	442.6	463.7	487.9	503.8	518.4
55°	352.4	354.6	362.1	368.5	378.3	387.5	404.7	423.2	438.0	450.0	462.1
57.5°	318.8	321.9	326.2	332.0	341.6	352.5	364.5	380.8	389.6	395.8	405.1
60°	297.3	298.2	301.0	307.9	315.3	325.0	338.9	350.5	357.0	362.1	370.0
62.5°	273.6	273.8	278.4	283.5	289.0	299.5	310.8	320.1	325.5	328.0	335.6
65°	240.3	239.4	242.2	246.3	252.8	259.8	269.5	277.9	277.3	280.1	284.7
67.5°	206.3	205.4	205.4	209.4	214.6	220.9	227.6	232.4	232.5	236.1	238.4
70°	183.3	180.6	182.4	185.7	188.0	193.1	200.5	202.3	202.8	204.6	207.0
72.5°	159.6	158.7	160.2	161.6	163.2	167.2	173.4	174.6	174.7	175.8	179.6
75°	126.9	125.9	125.0	126.4	128.2	131.0	133.3	135.2	134.7	135.2	137.9
77.5°	95.1	92.5	92.0	92.8	93.3	94.9	97.3	97.1	97.6	97.6	100.7
80°	75.4	71.8	71.3	71.3	71.8	72.7	73.7	74.5	73.1	74.5	75.4
82.5°	55.5	53.2	53.1	52.8	52.9	53.1	53.6	54.2	53.9	54.6	55.1
85°	30.6	29.6	28.3	29.2	28.7	27.3	28.3	26.8	26.4	26.8	27.3
87.5°	13.9	14.1	12.9	12.7	11.9	12.0	10.9	10.2	9.4	9.3	10.2
90°	17.7	16.6	14.5	13.5	11.4	10.3	8.3	6.2	4.1	2.1	1.1
92.5°	270.5	334.0	339.5	236.5	141.5	85.0	54.8	36.9	24.1	15.3	12.7
95°	898.3	918.0	749.1	463.2	235.2	124.3	77.7	54.9	43.5	35.2	34.2
97.5°	1136.7	980.3	669.0	369.7	202.7	129.3	95.8	75.3	63.8	58.1	56.8
100°	1194.6	935.6	596.8	335.7	201.0	140.9	109.9	90.2	78.7	74.6	72.5
102.5°	1159.8	856.8	542.1	321.6	208.5	155.0	124.8	106.7	94.5	91.2	90.0
105°	1048.6	751.2	489.0	316.0	223.8	178.3	149.2	132.6	122.3	117.1	117.1
107.5°	935.0	678.4	466.6	325.6	246.6	202.4	176.4	159.2	150.6	145.7	143.6
110°	870.3	644.4	460.0	334.7	263.1	220.7	193.8	178.3	168.9	164.8	162.6



TEST NUMBER: P333243-940

CATALOG NUMBER: S125DIP-S850D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	822.2	624.6	460.0	346.3	278.9	238.1	212.0	196.4	187.1	183.8	181.7
115°	769.8	603.1	463.2	363.6	303.6	265.3	239.3	223.8	214.5	211.3	209.3
117.5°	738.5	592.5	470.0	383.6	328.9	292.6	267.5	249.9	240.6	237.3	234.2
120°	721.1	587.5	476.6	396.8	347.1	310.9	284.9	267.3	258.0	253.9	250.7
122.5°	706.2	583.4	482.4	411.8	364.5	328.2	302.4	283.0	273.8	270.5	268.1
125°	685.9	578.2	492.1	432.0	387.5	353.3	326.4	306.7	297.4	292.2	290.1
127.5°	667.3	575.7	503.1	450.8	409.7	376.7	349.8	328.9	317.1	310.4	307.3
130°	654.9	574.0	509.8	463.2	423.7	391.6	364.7	343.0	329.5	321.2	318.1
132.5°	644.9	574.0	517.2	473.9	437.0	404.9	378.0	355.4	340.3	330.3	326.4
135°	633.1	574.0	527.4	489.0	454.9	422.8	394.8	373.0	356.4	344.0	339.8
137.5°	622.5	575.2	536.7	500.2	467.5	438.3	409.5	388.2	371.6	360.0	356.9
140°	617.5	576.0	540.8	507.7	476.6	446.6	418.6	399.0	382.4	369.9	366.8
142.5°	613.4	576.9	543.3	511.8	482.4	454.1	427.8	408.8	392.3	380.7	378.4
145°	607.2	576.0	546.1	518.1	492.1	465.2	441.4	422.8	408.2	397.9	395.8
147.5°	600.7	573.4	547.1	521.8	498.4	474.7	453.8	437.7	424.2	415.3	414.0
150°	595.8	570.9	547.1	524.3	502.5	479.7	462.1	447.6	434.2	426.9	424.8
152.5°	590.0	567.6	546.3	525.9	506.7	485.5	469.6	455.9	444.1	437.7	436.4
155°	580.2	561.6	543.9	527.4	510.8	493.2	478.7	468.3	458.0	451.7	451.7
157.5°	571.1	555.4	541.3	528.4	514.3	499.2	488.2	479.1	470.2	465.2	465.5
160°	563.7	551.3	538.8	528.4	516.0	502.5	493.2	484.9	477.7	473.5	474.6
162.5°	557.1	546.3	536.3	527.6	517.6	505.9	498.2	491.5	485.1	481.0	482.0
165°	547.1	538.8	532.5	526.4	518.1	509.8	503.5	499.4	494.3	491.2	493.2
167.5°	537.3	531.5	526.7	523.9	518.1	511.2	507.3	504.4	501.5	499.6	500.7
170°	531.5	527.4	524.3	522.2	518.1	512.9	509.8	507.7	505.6	504.6	505.6
172.5°	525.8	522.5	520.9	520.6	517.2	512.9	511.4	510.1	508.1	507.1	509.0
175°	518.1	517.0	517.0	518.1	516.0	512.9	512.9	512.9	511.8	510.8	512.9
177.5°	514.8	513.9	513.9	515.6	514.8	513.1	513.1	513.9	513.1	513.1	514.8
180°	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9



TEST NUMBER: P333243-940

CATALOG NUMBER: S125DIP-S850D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	1096.8	1102.0	1105.4	1111.6	1116.8	1119.8	1122.4	1124.6	1127.2	1129.4	1135.7
5°	1103.8	1115.9	1126.1	1141.8	1156.2	1167.2	1179.3	1190.0	1198.8	1211.3	1221.0
7.5°	1100.8	1122.2	1144.6	1168.9	1193.8	1217.0	1238.3	1258.2	1276.3	1298.2	1317.3
10°	1097.9	1127.0	1155.7	1188.6	1222.4	1251.1	1277.9	1305.3	1325.2	1353.0	1376.5
12.5°	1095.6	1130.0	1164.6	1204.2	1241.3	1281.8	1317.6	1337.5	1367.8	1390.0	1418.1
15°	1086.3	1131.7	1179.3	1223.8	1276.6	1314.0	1345.6	1384.5	1412.6	1440.9	1471.5
17.5°	1069.5	1120.9	1174.2	1232.5	1283.2	1323.4	1364.0	1401.5	1435.2	1473.1	1511.1
20°	1061.8	1113.1	1174.2	1233.9	1283.5	1325.6	1367.3	1408.5	1445.6	1494.2	1538.2
22.5°	1045.4	1107.6	1163.9	1222.1	1273.1	1319.0	1366.2	1413.0	1462.2	1517.2	1572.3
25°	1016.4	1079.3	1139.1	1196.5	1247.9	1305.3	1355.8	1418.3	1481.2	1553.9	1622.5
27.5°	986.1	1046.4	1101.2	1156.6	1216.6	1281.6	1347.0	1418.0	1500.4	1592.1	1688.8
30°	961.7	1018.7	1071.9	1128.8	1191.3	1264.5	1336.3	1420.6	1515.9	1619.2	1734.0
32.5°	933.2	985.7	1037.4	1097.8	1165.8	1243.0	1326.7	1419.1	1533.7	1651.1	1769.2
35°	884.4	928.4	981.6	1046.0	1122.8	1211.3	1308.1	1417.3	1548.8	1683.6	1783.2
37.5°	826.5	867.5	923.5	994.1	1074.7	1169.6	1284.4	1414.1	1553.7	1661.2	1693.3
40°	787.6	825.5	884.0	957.1	1039.5	1140.0	1265.9	1402.9	1538.2	1606.7	1580.3
42.5°	746.1	786.0	842.8	915.3	1004.0	1113.3	1242.6	1379.7	1493.0	1518.9	1427.7
45°	680.6	721.8	777.8	851.0	946.5	1065.0	1199.7	1324.3	1389.6	1342.7	1201.6
47.5°	619.8	658.4	710.3	785.9	884.3	1006.9	1136.7	1236.0	1241.2	1129.6	978.7
50°	578.4	613.9	666.3	741.7	839.5	963.6	1080.7	1159.0	1123.7	997.4	852.4
52.5°	537.6	572.5	624.1	698.8	795.4	909.1	1018.1	1073.0	1006.7	877.0	753.1
55°	478.8	509.3	559.8	628.7	720.5	826.1	918.6	937.6	851.5	723.7	623.2
57.5°	421.3	449.9	495.8	559.4	643.1	736.6	809.0	805.0	714.0	604.3	524.6
60°	382.5	410.3	451.0	513.0	589.4	670.0	732.0	717.2	627.0	532.4	465.4
62.5°	347.7	372.5	411.0	465.2	534.9	609.7	660.6	638.7	550.3	467.6	414.6
65°	296.3	317.2	350.1	396.4	454.2	515.9	555.2	526.9	451.5	387.1	344.5
67.5°	247.4	264.0	291.6	328.6	377.9	427.4	451.4	422.9	362.6	315.6	284.0
70°	216.2	231.0	252.4	285.3	328.3	370.0	388.0	362.6	310.7	270.4	247.7
72.5°	185.1	197.3	216.1	245.6	280.1	316.3	332.1	307.7	265.1	231.1	209.9
75°	143.1	151.4	164.3	184.8	212.0	240.8	249.6	228.3	201.0	175.5	161.6
77.5°	102.5	109.5	119.3	132.2	151.5	169.8	177.5	165.1	144.0	127.9	116.5
80°	78.7	82.4	90.8	101.4	116.7	128.2	133.3	125.5	110.7	98.6	89.8
82.5°	56.1	59.8	64.8	73.7	83.4	91.2	96.7	91.4	80.7	71.2	66.1
85°	27.3	29.6	32.4	36.1	43.5	48.2	47.7	44.4	40.3	36.6	33.8
87.5°	10.1	10.8	12.4	14.6	16.1	17.8	19.0	18.5	17.4	16.5	15.6
90°	2.1	4.1	6.2	8.3	10.3	11.4	13.5	14.5	16.6	17.7	18.6
92.5°	15.3	24.1	36.9	54.8	85.0	141.5	236.5	339.5	334.0	270.5	183.6
95°	35.2	43.5	54.9	77.7	124.3	235.2	463.2	749.1	918.0	898.3	744.9
97.5°	58.1	63.8	75.3	95.8	129.3	202.7	369.7	669.0	980.3	1136.7	1109.5
100°	74.6	78.7	90.2	109.9	140.9	201.0	335.7	596.8	935.6	1194.6	1274.4
102.5°	91.2	94.5	106.7	124.8	155.0	208.5	321.6	542.1	856.8	1159.8	1330.0
105°	117.1	122.3	132.6	149.2	178.3	223.8	316.0	489.0	751.2	1048.6	1297.3
107.5°	145.7	150.6	159.2	176.4	202.4	246.6	325.6	466.6	678.4	935.0	1180.4
110°	164.8	168.9	178.3	193.8	220.7	263.1	334.7	460.0	644.4	870.3	1094.1



TEST NUMBER: P333243-940

CATALOG NUMBER: S125DIP-S850D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	183.8	187.1	196.4	212.0	238.1	278.9	346.3	460.0	624.6	822.2	1026.2
115°	211.3	214.5	223.8	239.3	265.3	303.6	363.6	463.2	603.1	769.8	940.8
117.5°	237.3	240.6	249.9	267.5	292.6	328.9	383.6	470.0	592.5	738.5	885.6
120°	253.9	258.0	267.3	284.9	310.9	347.1	396.8	476.6	587.5	721.1	855.9
122.5°	270.5	273.8	283.0	302.4	328.2	364.5	411.8	482.4	583.4	706.2	833.5
125°	292.2	297.4	306.7	326.4	353.3	387.5	432.0	492.1	578.2	685.9	800.9
127.5°	310.4	317.1	328.9	349.8	376.7	409.7	450.8	503.1	575.7	667.3	767.8
130°	321.2	329.5	343.0	364.7	391.6	423.7	463.2	509.8	574.0	654.9	747.1
132.5°	330.3	340.3	355.4	378.0	404.9	437.0	473.9	517.2	574.0	644.9	726.3
135°	344.0	356.4	373.0	394.8	422.8	454.9	489.0	527.4	574.0	633.1	699.4
137.5°	360.0	371.6	388.2	409.5	438.3	467.5	500.2	536.7	575.2	622.5	676.6
140°	369.9	382.4	399.0	418.6	446.6	476.6	507.7	540.8	576.0	617.5	664.1
142.5°	380.7	392.3	408.8	427.8	454.1	482.4	511.8	543.3	576.9	613.4	653.4
145°	397.9	408.2	422.8	441.4	465.2	492.1	518.1	546.1	576.0	607.2	639.3
147.5°	415.3	424.2	437.7	453.8	474.7	498.4	521.8	547.1	573.4	600.7	626.1
150°	426.9	434.2	447.6	462.1	479.7	502.5	524.3	547.1	570.9	595.8	618.6
152.5°	437.7	444.1	455.9	469.6	485.5	506.7	525.9	546.3	567.6	590.0	610.3
155°	451.7	458.0	468.3	478.7	493.2	510.8	527.4	543.9	561.6	580.2	597.8
157.5°	465.2	470.2	479.1	488.2	499.2	514.3	528.4	541.3	555.4	571.1	585.4
160°	473.5	477.7	484.9	493.2	502.5	516.0	528.4	538.8	551.3	563.7	577.1
162.5°	481.0	485.1	491.5	498.2	505.9	517.6	527.6	536.3	546.3	557.1	568.0
165°	491.2	494.3	499.4	503.5	509.8	518.1	526.4	532.5	538.8	547.1	555.4
167.5°	499.6	501.5	504.4	507.3	511.2	518.1	523.9	526.7	531.5	537.3	543.3
170°	504.6	505.6	507.7	509.8	512.9	518.1	522.2	524.3	527.4	531.5	536.7
172.5°	507.1	508.1	510.1	511.4	512.9	517.2	520.6	520.9	522.5	525.8	529.2
175°	510.8	511.8	512.9	512.9	512.9	516.0	518.1	517.0	517.0	518.1	521.2
177.5°	513.1	513.1	513.9	513.1	513.1	514.8	515.6	513.9	513.9	514.8	515.6
180°	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9



TEST NUMBER: P333243-940

CATALOG NUMBER: S125DIP-S850D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	1140.9	1143.9	1150.1	1147.9	1150.9	1152.4	1153.9
5°	1233.1	1247.9	1254.4	1253.4	1263.1	1260.8	1258.5
7.5°	1337.1	1352.7	1361.4	1372.3	1378.5	1378.9	1384.5
10°	1396.1	1416.4	1424.8	1436.3	1443.7	1447.9	1447.4
12.5°	1441.2	1457.1	1475.9	1481.5	1491.5	1496.7	1494.9
15°	1495.6	1521.1	1540.5	1550.2	1562.7	1566.4	1571.6
17.5°	1544.1	1578.2	1601.0	1631.1	1642.5	1649.5	1645.4
20°	1580.7	1625.7	1648.4	1684.5	1704.4	1715.0	1711.4
22.5°	1624.1	1672.8	1714.7	1746.0	1776.3	1790.6	1793.6
25°	1698.4	1765.1	1826.7	1867.9	1905.3	1914.1	1933.6
27.5°	1781.4	1860.0	1925.8	1969.2	1995.3	2005.1	2011.2
30°	1833.6	1911.8	1961.4	1989.1	1997.5	1996.5	1995.6
32.5°	1859.1	1908.2	1917.6	1909.9	1890.8	1874.7	1857.9
35°	1822.9	1786.4	1731.7	1661.3	1609.4	1557.2	1552.0
37.5°	1639.5	1522.5	1431.6	1330.0	1271.4	1235.2	1210.1
40°	1466.9	1334.0	1223.8	1138.1	1078.3	1054.8	1031.6
42.5°	1279.4	1152.4	1054.9	983.3	938.3	912.1	893.9
45°	1039.5	927.5	851.0	799.2	763.6	743.2	731.6
47.5°	851.8	768.9	704.0	666.6	641.9	626.1	626.2
50°	751.0	671.8	628.7	599.1	577.8	565.3	567.7
52.5°	661.7	602.6	565.8	541.0	525.2	517.5	517.3
55°	553.3	510.7	486.6	468.6	457.9	449.2	451.0
57.5°	473.3	437.4	421.2	406.3	398.9	395.3	390.2
60°	423.7	395.9	382.0	370.0	362.6	359.8	354.6
62.5°	379.6	357.8	344.2	334.4	327.7	326.8	322.8
65°	319.1	302.4	290.3	285.7	278.7	276.9	276.9
67.5°	263.0	251.0	241.7	237.5	234.3	234.9	232.6
70°	227.8	218.1	212.0	207.4	205.1	205.5	203.8
72.5°	199.3	188.4	183.2	180.4	177.4	178.5	177.8
75°	151.0	145.3	142.6	139.8	137.9	137.1	136.2
77.5°	110.8	105.9	103.8	102.3	102.5	100.3	102.0
80°	85.7	81.5	80.1	77.8	77.3	77.3	76.9
82.5°	62.7	60.4	59.4	57.4	56.6	57.3	56.1
85°	32.4	30.6	30.1	30.1	29.2	28.3	30.6
87.5°	15.8	14.5	14.9	14.5	14.5	14.4	13.6
90°	19.7	20.7	22.8	22.8	22.8	23.8	23.8
92.5°	133.2	100.3	85.0	71.7	69.2	67.8	66.1
95°	587.5	460.0	373.0	299.4	268.3	260.1	243.5
97.5°	999.1	874.9	753.9	689.8	631.9	601.8	588.5
100°	1223.7	1117.0	1009.1	937.7	863.1	824.7	808.2
102.5°	1361.3	1310.1	1237.2	1160.7	1107.6	1066.0	1053.6
105°	1439.2	1484.8	1473.4	1440.2	1406.0	1385.3	1372.9
107.5°	1369.8	1486.8	1541.0	1557.7	1557.6	1550.7	1542.4
110°	1291.0	1437.1	1525.2	1571.8	1591.5	1598.7	1598.7



TEST NUMBER: P333243-940

CATALOG NUMBER: S125DIP-S850D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1213.1	1360.8	1464.6	1532.9	1566.6	1584.7	1592.1
115°	1101.4	1243.3	1356.3	1437.1	1486.8	1515.8	1529.3
117.5°	1024.1	1146.4	1250.0	1330.8	1382.2	1411.0	1419.2
120°	980.2	1094.1	1185.4	1262.0	1311.7	1339.7	1348.0
122.5°	948.7	1050.3	1135.6	1204.0	1249.6	1277.6	1285.0
125°	906.6	996.8	1071.4	1129.4	1171.9	1194.6	1205.1
127.5°	866.4	950.6	1020.4	1073.0	1110.5	1132.1	1136.7
130°	838.2	919.1	986.4	1038.2	1072.4	1093.1	1099.3
132.5°	811.7	885.0	949.9	1001.7	1035.9	1055.0	1062.0
135°	770.9	837.2	896.3	941.8	976.1	994.7	1000.9
137.5°	734.4	789.5	839.7	880.5	911.6	928.8	935.6
140°	712.8	760.5	804.1	842.4	869.3	884.8	890.0
142.5°	694.6	735.7	773.4	805.9	828.7	843.4	847.7
145°	671.4	703.6	731.5	756.3	774.0	785.4	789.5
147.5°	652.1	676.8	697.9	717.6	731.7	738.3	740.2
150°	641.4	661.0	679.7	695.3	707.7	711.9	712.8
152.5°	630.6	648.6	663.2	676.2	686.1	690.3	691.3
155°	614.4	628.9	640.3	650.7	657.9	661.0	662.1
157.5°	599.1	610.3	619.2	627.2	633.3	636.1	636.0
160°	587.5	597.8	605.1	612.3	617.5	619.6	618.6
162.5°	577.6	586.2	592.6	598.2	602.6	603.1	602.8
165°	562.6	568.8	574.0	578.2	580.2	580.2	580.2
167.5°	548.1	552.9	556.6	558.7	560.5	559.7	559.5
170°	539.8	543.0	545.0	547.1	548.1	548.1	547.1
172.5°	532.4	534.7	535.9	536.3	538.1	536.5	535.5
175°	521.2	523.3	523.3	523.3	524.3	522.2	521.2
177.5°	516.4	516.4	516.4	515.6	516.4	513.9	513.9
180°	513.9	513.9	513.9	513.9	513.9	513.9	513.9

(END OF REPORT)