

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331256-930

Luminaire Tested: **SA2XXDIP-C290D530U930-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331256-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C290D530U930-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2522.7 lumens
Efficiency: N/A
Efficacy: 98.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331256-930
CATALOG NUMBER: SA2XXDIP-C290D530U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331256-930

CATALOG NUMBER: SA2XXDIP-C290D530U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39				
1	95	91	87	84	86	83	80	77	68	65	63	54	52	51	41	40	39	33				
2	87	79	73	68	79	72	67	63	59	55	52	47	44	42	36	34	33	27				
3	79	70	63	57	72	64	57	52	52	48	44	42	38	36	32	30	28	23				
4	72	62	54	48	65	56	50	44	46	41	37	37	33	31	28	26	24	20				
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21	17				
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	20	18	15				
7	56	44	37	31	51	41	34	29	34	28	25	27	23	20	21	18	16	14				
8	52	40	33	27	47	37	30	25	31	25	22	25	21	18	19	17	15	12				
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11				
10	45	34	26	22	41	31	25	20	26	21	17	21	17	15	17	14	12	10				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6218	6218	6218
5°	6242	6152	6190
10°	6205	6091	6120
15°	6128	6011	6006
20°	6019	5893	5887
25°	5911	5747	5747
30°	5774	5614	5565
35°	5643	5452	5373
40°	5480	5292	5191
45°	5318	5133	5005
50°	5144	4968	4793
55°	4963	4777	4597
60°	4760	4543	4379
65°	4542	4317	4118
70°	4263	4036	3843
75°	3880	3718	3624
80°	3440	3347	3171
85°	2816	2668	2408



TEST NUMBER: P331256-930

CATALOG NUMBER: SA2XXDIP-C290D530U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.2	1.4
10°-20°	101.9	4.0
20°-30°	149.8	5.9
30°-40°	174.0	6.9
40°-50°	173.8	6.9
50°-60°	151.6	6.0
60°-70°	112.1	4.4
70°-80°	63.5	2.5
80°-90°	19.3	0.8
90°-100°	34.9	1.4
100°-110°	108.4	4.3
110°-120°	185.3	7.3
120°-130°	243.7	9.7
130°-140°	273.5	10.8
140°-150°	268.2	10.6
150°-160°	225.0	8.9
160°-170°	149.2	5.9
170°-180°	52.2	2.1
0°-30°	287.9	11.4
0°-40°	461.9	18.3
0°-60°	787.3	31.2
0°-90°	982.2	38.9
90°-120°	328.7	13.0
90°-150°	1114.2	44.2
90°-180°	1540.0	61.0
0°-180°	2522.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	385	385	385	385	385	
5°	385	384	380	382	382	37
15°	367	364	360	361	359	103
25°	332	329	323	323	323	153
35°	286	282	277	274	273	179
45°	233	230	225	221	219	180
55°	176	174	170	165	163	158
65°	119	117	113	110	108	118
75°	62	61	60	58	58	66
85°	15	15	14	13	13	17
90°	0	6	16	15	16	2
95°	24	29	30	30	29	28
105°	100	101	102	103	103	106
115°	186	189	188	187	186	184
125°	271	274	273	272	272	242
135°	350	355	356	356	354	270
145°	425	428	431	431	430	265
155°	486	487	489	491	490	224
165°	529	528	528	531	529	149
175°	550	549	548	551	548	52
180°	551	551	551	551	551	



TEST NUMBER: P331256-930

CATALOG NUMBER: SA2XXDIP-C290D530U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1
2.5°	386.9	386.6	386.3	386.0	385.6	385.1	384.4	383.7	382.9	382.2	382.9
5°	385.1	384.8	384.5	384.2	383.8	383.3	382.4	381.5	380.5	379.6	380.3
7.5°	381.8	381.2	380.7	380.3	379.8	379.0	378.1	377.2	376.3	375.4	376.0
10°	378.5	378.0	377.4	376.8	376.2	375.4	374.5	373.5	372.5	371.5	372.1
12.5°	374.1	373.6	373.1	372.5	372.0	371.3	370.3	369.3	368.4	367.4	367.8
15°	366.6	366.2	365.7	365.2	364.7	363.9	362.8	361.7	360.7	359.6	360.0
17.5°	357.2	356.7	356.2	355.7	355.2	354.4	353.4	352.2	351.1	350.1	350.4
20°	350.3	349.8	349.4	348.9	348.4	347.6	346.4	345.3	344.1	343.0	343.2
22.5°	343.6	342.8	342.2	341.4	340.8	339.9	338.8	337.7	336.6	335.6	335.6
25°	331.8	331.2	330.5	329.9	329.2	328.2	326.8	325.4	324.0	322.6	322.8
27.5°	318.5	318.0	317.3	316.7	316.2	315.3	314.2	313.1	312.0	310.9	310.6
30°	309.7	309.0	308.3	307.7	307.0	306.1	304.8	303.6	302.3	301.1	300.8
32.5°	300.1	299.6	299.1	298.6	298.1	297.1	295.8	294.6	293.3	292.0	291.5
35°	286.3	285.4	284.6	283.8	283.0	281.9	280.6	279.3	278.0	276.6	276.1
37.5°	270.7	269.9	269.2	268.5	267.7	266.8	265.5	264.2	262.8	261.5	260.9
40°	260.0	259.3	258.7	258.0	257.4	256.4	255.0	253.7	252.4	251.1	250.4
42.5°	249.6	249.0	248.3	247.7	247.0	246.0	244.7	243.4	242.1	240.8	239.9
45°	232.9	232.4	231.8	231.2	230.6	229.8	228.5	227.3	226.1	224.8	223.9
47.5°	216.4	215.8	215.3	214.7	214.2	213.3	212.0	210.8	209.5	208.1	207.2
50°	204.8	204.4	204.0	203.6	203.2	202.4	201.2	200.1	198.9	197.8	196.7
52.5°	193.6	193.0	192.5	191.9	191.4	190.5	189.5	188.4	187.3	186.2	185.2
55°	176.3	175.8	175.3	174.8	174.3	173.6	172.6	171.6	170.6	169.7	168.6
57.5°	159.0	158.6	158.2	157.8	157.4	156.6	155.6	154.5	153.4	152.3	151.3
60°	147.4	147.1	146.8	146.4	146.1	145.4	144.2	143.1	141.9	140.7	139.8
62.5°	136.2	135.6	135.1	134.6	134.0	133.3	132.4	131.6	130.7	129.8	128.9
65°	118.9	118.4	117.9	117.4	116.9	116.3	115.4	114.6	113.8	113.0	112.2
67.5°	101.3	100.9	100.5	100.1	99.8	99.2	98.4	97.7	96.9	96.2	95.6
70°	90.3	90.0	89.7	89.4	89.0	88.5	87.8	87.1	86.3	85.5	85.0
72.5°	79.1	78.8	78.4	78.1	77.8	77.4	76.9	76.5	76.0	75.5	74.9
75°	62.2	62.0	61.9	61.7	61.6	61.3	60.9	60.4	60.0	59.6	59.1
77.5°	47.1	46.8	46.6	46.3	46.0	45.7	45.6	45.4	45.2	45.1	44.8
80°	37.0	36.9	36.9	36.8	36.7	36.6	36.4	36.3	36.1	36.0	35.7
82.5°	27.6	27.6	27.6	27.5	27.5	27.4	27.3	27.2	27.1	27.1	26.7
85°	15.2	15.1	15.0	14.9	14.8	14.8	14.7	14.6	14.5	14.4	14.2
87.5°	5.5	5.5	5.6	5.8	5.9	6.1	6.4	6.8	7.1	7.4	7.2
90°	0.5	1.7	2.9	4.2	5.5	7.2	9.5	11.7	14.0	16.3	16.1
92.5°	8.3	9.2	10.1	11.0	11.9	12.6	13.2	13.7	14.3	14.8	14.8
95°	24.2	25.2	26.3	27.3	28.3	28.9	29.1	29.4	29.5	29.8	29.8
97.5°	44.2	45.1	46.0	46.9	47.8	48.4	48.8	49.2	49.7	50.1	50.1
100°	59.0	59.8	60.7	61.6	62.4	62.9	63.3	63.5	63.8	64.2	64.2
102.5°	74.7	75.3	76.0	76.6	77.3	77.9	78.3	78.6	79.0	79.4	79.5
105°	100.0	100.3	100.6	100.9	101.2	101.4	101.7	101.8	102.1	102.3	102.5
107.5°	125.5	125.9	126.4	126.8	127.3	127.5	127.5	127.5	127.5	127.5	127.6
110°	141.8	142.4	143.0	143.7	144.3	144.6	144.6	144.6	144.6	144.6	144.6



TEST NUMBER: P331256-930

CATALOG NUMBER: SA2XXDIP-C290D530U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	159.6	160.3	160.9	161.5	162.2	162.4	162.3	162.2	162.2	162.1	161.8
115°	186.0	186.6	187.2	187.8	188.4	188.7	188.4	188.3	188.0	187.8	187.8
117.5°	212.2	213.0	213.9	214.7	215.5	215.6	215.1	214.4	213.9	213.3	213.0
120°	229.7	230.5	231.3	232.1	233.0	233.0	232.1	231.3	230.5	229.7	229.7
122.5°	245.6	246.6	247.7	248.7	249.6	249.8	249.2	248.7	248.1	247.5	247.3
125°	270.6	271.5	272.5	273.4	274.3	274.6	274.3	274.0	273.7	273.4	273.0
127.5°	294.8	296.0	297.2	298.4	299.5	299.9	299.6	299.2	298.9	298.5	298.1
130°	310.1	311.4	312.7	314.1	315.4	316.0	315.8	315.6	315.4	315.2	315.0
132.5°	327.2	328.3	329.4	330.5	331.6	332.2	332.2	332.2	332.3	332.3	331.9
135°	350.1	351.2	352.4	353.5	354.7	355.3	355.5	355.7	356.0	356.1	356.0
137.5°	374.1	375.1	376.0	377.0	377.9	378.5	378.8	379.0	379.3	379.5	379.4
140°	388.7	389.6	390.5	391.4	392.4	393.1	393.6	394.1	394.7	395.2	395.2
142.5°	403.6	404.5	405.4	406.3	407.2	407.9	408.3	408.6	409.0	409.3	409.4
145°	424.9	425.7	426.4	427.1	427.9	428.5	429.1	429.7	430.4	431.0	431.0
147.5°	444.0	444.8	445.7	446.6	447.4	448.1	448.5	448.9	449.3	449.8	450.0
150°	457.1	457.6	458.3	458.9	459.5	460.0	460.4	460.8	461.2	461.7	461.9
152.5°	468.6	469.2	469.8	470.4	471.0	471.6	472.1	472.5	473.0	473.6	473.9
155°	485.8	486.2	486.5	486.7	487.1	487.4	487.7	488.0	488.3	488.6	489.2
157.5°	500.6	500.8	501.0	501.2	501.5	501.7	501.8	502.1	502.2	502.4	503.1
160°	509.6	509.7	510.0	510.1	510.4	510.5	510.6	510.7	510.9	510.9	511.6
162.5°	517.7	517.8	517.8	517.9	517.9	518.0	518.0	518.2	518.3	518.4	519.1
165°	528.6	528.5	528.4	528.3	528.2	528.2	528.2	528.2	528.2	528.2	528.9
167.5°	537.7	537.4	537.1	536.8	536.5	536.3	536.3	536.3	536.2	536.2	537.0
170°	542.6	542.3	541.9	541.6	541.4	541.1	541.0	540.9	540.8	540.7	541.4
172.5°	545.9	545.6	545.3	544.9	544.7	544.5	544.4	544.3	544.1	544.0	544.8
175°	550.0	549.7	549.3	549.1	548.8	548.5	548.3	548.1	547.9	547.6	548.4
177.5°	551.7	551.4	551.1	550.9	550.7	550.5	550.3	550.2	550.0	549.8	550.3
180°	550.9	550.9	550.9	550.9	550.9	550.9	550.9	550.9	550.9	550.9	550.9



TEST NUMBER: P331256-930

CATALOG NUMBER: SA2XXDIP-C290D530U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1
2.5°	383.5	384.2	384.8	385.1	385.0	384.8	384.7	384.6
5°	381.0	381.6	382.3	382.5	382.4	382.2	382.0	381.9
7.5°	376.7	377.3	378.0	378.2	378.1	377.8	377.6	377.5
10°	372.8	373.5	374.1	374.3	374.1	373.8	373.6	373.3
12.5°	368.3	368.7	369.2	369.3	369.2	368.9	368.8	368.6
15°	360.3	360.6	360.9	360.9	360.5	360.1	359.7	359.3
17.5°	350.8	351.2	351.6	351.6	351.1	350.8	350.4	350.0
20°	343.5	343.7	344.0	343.9	343.6	343.2	342.9	342.6
22.5°	335.7	335.7	335.7	335.7	335.5	335.3	335.1	334.9
25°	322.9	323.1	323.3	323.3	323.1	322.9	322.8	322.6
27.5°	310.4	310.1	309.9	309.6	309.2	308.8	308.4	308.0
30°	300.6	300.4	300.1	299.9	299.5	299.2	298.9	298.5
32.5°	291.1	290.6	290.2	289.8	289.4	289.1	288.8	288.5
35°	275.7	275.2	274.7	274.3	273.9	273.5	273.0	272.6
37.5°	260.2	259.7	259.0	258.5	258.1	257.7	257.4	257.0
40°	249.6	248.9	248.2	247.6	247.3	247.0	246.6	246.3
42.5°	239.1	238.3	237.5	236.8	236.4	235.9	235.5	235.1
45°	223.0	222.1	221.2	220.5	220.2	219.9	219.6	219.2
47.5°	206.3	205.3	204.3	203.6	203.2	202.7	202.2	201.7
50°	195.5	194.3	193.1	192.4	192.0	191.6	191.2	190.8
52.5°	184.3	183.4	182.4	181.6	181.1	180.6	180.0	179.4
55°	167.6	166.6	165.7	165.0	164.6	164.1	163.7	163.3
57.5°	150.3	149.4	148.4	147.7	147.5	147.2	146.8	146.5
60°	138.9	138.0	137.1	136.6	136.3	136.1	135.8	135.6
62.5°	128.1	127.3	126.5	125.9	125.6	125.2	124.9	124.6
65°	111.5	110.7	110.0	109.4	109.0	108.6	108.2	107.8
67.5°	95.1	94.5	93.9	93.4	93.1	92.8	92.5	92.1
70°	84.4	83.8	83.2	82.8	82.5	82.1	81.8	81.4
72.5°	74.4	73.8	73.2	72.7	72.5	72.2	72.0	71.7
75°	58.6	58.1	57.6	57.5	57.6	57.8	58.0	58.1
77.5°	44.6	44.4	44.1	43.9	43.6	43.5	43.2	43.0
80°	35.5	35.2	35.0	34.7	34.6	34.4	34.2	34.1
82.5°	26.4	26.1	25.8	25.6	25.6	25.5	25.5	25.5
85°	13.9	13.7	13.5	13.3	13.2	13.1	13.0	13.0
87.5°	6.9	6.7	6.4	6.3	6.3	6.2	6.2	6.1
90°	15.9	15.7	15.4	15.4	15.5	15.6	15.7	15.8
92.5°	14.8	14.9	14.9	15.0	15.0	15.0	15.1	15.1
95°	29.8	29.8	29.8	29.7	29.4	29.3	29.0	28.9
97.5°	50.1	50.1	50.1	50.0	50.0	50.0	50.0	49.9
100°	64.2	64.2	64.2	64.1	64.0	63.9	63.8	63.7
102.5°	79.6	79.7	79.7	79.7	79.7	79.5	79.4	79.3
105°	102.7	102.9	103.1	103.2	103.2	103.2	103.2	103.2
107.5°	127.7	127.8	127.8	127.6	127.1	126.7	126.2	125.7
110°	144.6	144.6	144.6	144.5	144.1	143.8	143.5	143.2



TEST NUMBER: P331256-930

CATALOG NUMBER: SA2XXDIP-C290D530U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	161.6	161.3	161.1	160.9	160.6	160.4	160.1	160.0
115°	187.6	187.5	187.4	187.2	186.9	186.6	186.3	186.0
117.5°	212.8	212.5	212.3	212.1	211.7	211.4	211.1	210.8
120°	229.7	229.7	229.7	229.5	229.2	228.9	228.6	228.3
122.5°	247.0	246.8	246.5	246.3	246.1	245.8	245.6	245.4
125°	272.7	272.5	272.1	271.9	271.8	271.7	271.6	271.5
127.5°	297.7	297.3	297.0	296.6	296.3	296.0	295.6	295.3
130°	314.8	314.6	314.4	314.1	313.6	313.2	312.8	312.4
132.5°	331.4	330.9	330.5	330.1	329.8	329.5	329.1	328.8
135°	356.0	355.8	355.7	355.5	355.2	354.9	354.6	354.2
137.5°	379.4	379.3	379.2	379.0	378.5	378.1	377.7	377.3
140°	395.2	395.2	395.2	395.0	394.5	394.1	393.7	393.3
142.5°	409.4	409.5	409.6	409.4	409.0	408.6	408.2	407.8
145°	431.2	431.3	431.4	431.2	430.8	430.4	430.0	429.6
147.5°	450.2	450.5	450.7	450.6	450.2	449.8	449.4	449.0
150°	462.3	462.6	462.9	462.9	462.6	462.3	461.9	461.7
152.5°	474.3	474.7	475.2	475.2	474.7	474.3	473.9	473.6
155°	489.7	490.2	490.7	490.8	490.5	490.2	489.8	489.6
157.5°	503.8	504.5	505.2	505.3	504.8	504.3	503.9	503.3
160°	512.2	512.8	513.4	513.6	513.1	512.7	512.3	511.8
162.5°	519.8	520.5	521.2	521.3	520.8	520.3	519.8	519.3
165°	529.6	530.4	531.0	531.2	530.6	530.1	529.6	529.0
167.5°	537.7	538.4	539.2	539.2	538.7	538.2	537.6	537.0
170°	542.2	542.9	543.6	543.6	543.0	542.4	541.8	541.2
172.5°	545.5	546.3	546.9	547.0	546.4	545.8	545.1	544.5
175°	549.1	549.8	550.6	550.7	550.0	549.3	548.8	548.1
177.5°	550.8	551.3	551.8	551.8	551.3	550.8	550.3	549.8
180°	550.9	550.9	550.9	550.9	550.9	550.9	550.9	550.9

(END OF REPORT)