

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333247-940

Luminaire Tested: **S125DIP-S850D1205U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333247-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S850D1205U940-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7342.1 lumens
Efficiency: N/A
Efficacy: 129.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333247-940

CATALOG NUMBER: S125DIP-S850D1205U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333247-940

CATALOG NUMBER: S125DIP-S850D1205U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	42
1	96	92	88	84	87	84	80	77	69	66	64	55	54	52	43	42	41	35
2	87	80	74	69	79	73	68	63	60	56	53	48	46	43	37	36	34	29
3	80	70	63	57	72	64	58	53	53	48	45	43	39	37	33	31	29	25
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	30	27	25	21
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	18
6	61	49	41	36	56	45	38	33	38	32	28	31	27	24	24	21	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	40	33	28	48	37	30	26	31	26	22	26	22	19	20	17	15	13
9	49	37	29	24	45	34	27	23	29	23	20	23	20	17	19	16	14	12
10	46	34	27	22	42	31	25	20	26	21	18	22	18	15	17	15	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7559	7559	7559
5°	7577	7505	7553
10°	7531	7452	7494
15°	7449	7362	7393
20°	7332	7236	7249
25°	7207	7088	7081
30°	7052	6927	6893
35°	6885	6754	6659
40°	6715	6566	6473
45°	6530	6395	6268
50°	6327	6187	6002
55°	6132	5954	5788
60°	5898	5717	5515
65°	5619	5434	5251
70°	5351	5108	4932
75°	4876	4716	4551
80°	4340	4273	4169
85°	3772	3846	3631



TEST NUMBER: P333247-940

CATALOG NUMBER: S125DIP-S850D1205U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.4	1.5
10°-20°	311.8	4.2
20°-30°	460.3	6.3
30°-40°	537.2	7.3
40°-50°	539.5	7.3
50°-60°	473.6	6.5
60°-70°	352.9	4.8
70°-80°	201.8	2.7
80°-90°	61.6	0.8
90°-100°	50.8	0.7
100°-110°	313.1	4.3
110°-120°	567.9	7.7
120°-130°	728.8	9.9
130°-140°	783.9	10.7
140°-150°	735.8	10.0
150°-160°	595.2	8.1
160°-170°	384.9	5.2
170°-180°	132.8	1.8
0°-30°	882.5	12.0
0°-40°	1419.6	19.3
0°-60°	2432.7	33.1
0°-90°	3049.0	41.5
90°-120°	931.8	12.7
90°-150°	3180.2	43.3
90°-180°	4293.0	58.5
0°-180°	7342.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1170	1170	1170	1170	1170	
5°	1169	1166	1158	1165	1165	111
15°	1114	1111	1101	1106	1106	314
25°	1011	1006	995	996	994	465
35°	873	869	857	852	845	546
45°	715	711	700	690	686	551
55°	545	541	529	521	514	486
65°	368	365	356	348	344	365
75°	195	193	189	186	182	208
85°	51	52	52	51	49	57
90°	1	9	17	22	25	5
95°	59	54	17	22	22	75
105°	305	309	309	309	308	323
115°	572	577	578	574	568	567
125°	814	820	821	817	814	726
135°	1015	1020	1019	1016	1010	782
145°	1176	1178	1178	1179	1173	735
155°	1295	1290	1291	1294	1286	597
165°	1367	1361	1362	1367	1360	386
175°	1398	1392	1393	1400	1392	133
180°	1398	1398	1398	1398	1398	



TEST NUMBER: P333247-940

CATALOG NUMBER: S125DIP-S850D1205U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5
2.5°	1173.6	1173.0	1172.6	1172.1	1171.5	1170.5	1168.9	1167.2	1165.6	1164.0	1165.6
5°	1168.8	1168.3	1167.9	1167.5	1167.1	1165.8	1163.8	1161.7	1159.7	1157.6	1159.5
7.5°	1158.0	1157.6	1157.2	1156.7	1156.4	1155.0	1152.7	1150.5	1148.3	1145.9	1147.7
10°	1148.3	1148.0	1147.5	1147.1	1146.7	1145.4	1143.1	1140.9	1138.6	1136.3	1138.0
12.5°	1136.5	1135.8	1135.1	1134.3	1133.5	1132.1	1130.1	1127.9	1125.8	1123.7	1125.1
15°	1114.1	1113.5	1112.9	1112.2	1111.6	1110.2	1108.0	1105.6	1103.4	1101.1	1102.2
17.5°	1088.3	1087.4	1086.5	1085.7	1084.8	1083.1	1080.8	1078.4	1076.0	1073.7	1075.0
20°	1066.8	1066.5	1066.0	1065.6	1065.2	1063.6	1061.0	1058.3	1055.6	1052.9	1054.4
22.5°	1045.4	1044.6	1043.9	1043.1	1042.4	1040.8	1038.3	1035.7	1033.2	1030.7	1031.7
25°	1011.3	1010.3	1009.2	1008.2	1007.2	1005.3	1002.6	1000.0	997.3	994.6	995.1
27.5°	971.4	970.9	970.3	969.6	969.0	967.3	964.6	961.8	959.0	956.3	956.4
30°	945.6	944.9	944.3	943.7	943.1	941.2	938.2	935.0	931.9	928.9	928.4
32.5°	917.4	916.4	915.5	914.5	913.6	911.8	909.0	906.2	903.5	900.7	900.0
35°	873.3	872.4	871.6	870.8	870.0	868.2	865.3	862.4	859.5	856.7	855.6
37.5°	827.6	826.5	825.5	824.5	823.4	821.5	818.9	816.1	813.4	810.7	809.1
40°	796.5	795.4	794.4	793.4	792.3	790.4	787.5	784.6	781.8	778.8	777.0
42.5°	763.1	762.2	761.3	760.5	759.6	757.8	754.9	752.0	749.1	746.3	744.6
45°	715.0	714.1	713.3	712.5	711.7	710.0	707.6	705.1	702.6	700.2	697.7
47.5°	663.1	663.2	663.2	663.2	663.3	661.8	658.8	655.9	652.9	650.0	647.4
50°	629.7	629.1	628.5	627.9	627.3	625.7	623.3	620.8	618.3	615.8	613.1
52.5°	595.7	595.2	594.8	594.3	593.9	592.3	589.7	587.0	584.4	581.8	579.4
55°	544.6	543.9	543.3	542.7	542.1	540.3	537.4	534.6	531.6	528.8	526.9
57.5°	490.6	490.4	490.0	489.6	489.4	487.9	485.5	483.1	480.6	478.2	475.8
60°	456.6	455.8	455.0	454.1	453.3	451.7	449.4	447.2	445.0	442.6	440.6
62.5°	421.0	420.4	419.7	419.0	418.4	417.1	415.2	413.2	411.3	409.3	407.2
65°	367.7	367.2	366.8	366.4	366.0	364.7	362.4	360.2	357.8	355.6	353.7
67.5°	316.0	315.1	314.2	313.3	312.5	311.2	309.6	307.9	306.2	304.5	302.9
70°	283.4	282.3	281.3	280.3	279.3	277.9	276.0	274.1	272.2	270.5	269.2
72.5°	247.8	247.1	246.4	245.8	245.0	244.1	242.9	241.7	240.5	239.3	237.9
75°	195.4	195.0	194.6	194.2	193.8	193.1	192.0	191.0	189.9	189.0	188.3
77.5°	147.0	146.9	146.8	146.6	146.4	146.1	145.4	144.9	144.3	143.7	143.4
80°	116.7	116.7	116.7	116.7	116.7	116.5	116.1	115.7	115.2	114.9	114.7
82.5°	90.0	89.7	89.3	89.0	88.7	88.5	88.4	88.4	88.3	88.2	87.8
85°	50.9	51.2	51.4	51.5	51.7	51.9	51.9	51.9	51.9	51.9	51.6
87.5°	20.2	20.6	21.0	21.3	21.7	21.9	22.1	22.3	22.4	22.6	22.8
90°	1.1	2.9	4.7	6.6	8.4	10.2	11.8	13.4	15.0	16.6	17.7
92.5°	16.0	14.7	13.4	12.1	10.8	10.9	12.3	13.7	15.2	16.6	17.7
95°	59.0	58.4	57.7	57.0	56.3	51.6	42.8	34.1	25.3	16.6	17.7
97.5°	123.3	124.6	125.8	127.1	128.3	120.3	102.9	85.6	68.3	51.0	44.5
100°	173.1	173.8	174.4	175.1	175.8	176.6	177.5	178.5	179.4	180.3	146.0
102.5°	223.6	224.5	225.4	226.2	227.1	227.8	228.4	229.0	229.5	230.1	223.6
105°	304.7	305.6	306.5	307.5	308.4	308.8	308.8	308.8	308.8	308.8	308.8
107.5°	388.9	388.9	388.9	388.9	388.9	389.1	389.5	389.9	390.5	390.9	390.9
110°	443.5	443.5	443.5	443.5	443.5	443.8	444.3	444.7	445.1	445.6	445.0



TEST NUMBER: P333247-940

CATALOG NUMBER: S125DIP-S850D1205U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	495.0	495.5	496.1	496.6	497.1	497.6	497.8	498.1	498.4	498.6	497.8
115°	572.0	573.2	574.4	575.5	576.7	577.4	577.6	577.8	578.0	578.3	577.4
117.5°	651.8	651.8	651.8	651.8	651.7	652.1	653.0	653.8	654.7	655.6	654.4
120°	701.6	701.3	701.2	700.9	700.7	700.9	701.6	702.3	702.9	703.6	703.2
122.5°	745.6	746.5	747.3	748.1	749.0	749.7	749.9	750.3	750.6	750.9	750.5
125°	813.5	815.1	816.7	818.3	819.9	820.7	820.7	820.7	820.7	820.7	819.8
127.5°	878.4	879.6	880.7	881.8	883.0	883.5	883.3	883.2	883.1	883.0	882.4
130°	918.2	919.4	920.5	921.7	922.8	923.5	923.7	924.0	924.2	924.4	923.7
132.5°	958.0	959.3	960.6	962.0	963.3	963.8	963.2	962.7	962.2	961.7	961.6
135°	1014.6	1015.9	1017.4	1018.7	1020.1	1020.6	1020.1	1019.7	1019.1	1018.7	1018.2
137.5°	1066.6	1067.8	1069.0	1070.1	1071.4	1071.7	1071.4	1070.9	1070.5	1070.1	1070.2
140°	1100.5	1101.1	1101.5	1102.0	1102.4	1102.5	1102.3	1102.1	1101.9	1101.6	1102.1
142.5°	1131.2	1131.5	1131.8	1132.1	1132.4	1132.7	1133.0	1133.3	1133.6	1134.0	1134.1
145°	1176.3	1176.7	1177.1	1177.6	1178.0	1178.3	1178.3	1178.3	1178.3	1178.3	1178.6
147.5°	1215.6	1215.5	1215.4	1215.3	1215.2	1215.3	1215.6	1215.8	1216.2	1216.5	1216.7
150°	1240.5	1240.0	1239.6	1239.1	1238.7	1238.7	1239.1	1239.6	1240.0	1240.5	1240.9
152.5°	1264.5	1263.6	1262.5	1261.5	1260.4	1260.2	1260.7	1261.1	1261.6	1262.0	1262.5
155°	1295.4	1294.1	1292.6	1291.3	1289.9	1289.4	1289.9	1290.3	1290.8	1291.3	1292.0
157.5°	1319.3	1318.4	1317.6	1316.8	1315.9	1315.5	1315.6	1315.6	1315.7	1315.7	1316.4
160°	1335.9	1334.4	1333.1	1331.7	1330.3	1329.7	1330.0	1330.2	1330.4	1330.6	1331.6
162.5°	1349.1	1347.7	1346.3	1345.0	1343.5	1343.0	1343.2	1343.5	1343.7	1343.9	1345.2
165°	1366.9	1365.6	1364.1	1362.8	1361.4	1360.8	1361.0	1361.3	1361.5	1361.7	1363.2
167.5°	1380.2	1378.8	1377.3	1375.9	1374.5	1373.9	1374.1	1374.3	1374.6	1374.8	1376.4
170°	1387.7	1386.1	1384.4	1382.8	1381.2	1380.5	1380.7	1381.0	1381.2	1381.4	1383.3
172.5°	1392.6	1391.0	1389.4	1387.8	1386.2	1385.5	1386.0	1386.4	1386.8	1387.2	1388.9
175°	1398.0	1396.6	1395.3	1393.8	1392.5	1391.9	1392.1	1392.4	1392.6	1392.9	1394.6
177.5°	1400.5	1399.4	1398.3	1397.2	1396.1	1395.6	1395.8	1396.0	1396.2	1396.3	1397.7
180°	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0



TEST NUMBER: P333247-940

CATALOG NUMBER: S125DIP-S850D1205U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5
2.5°	1167.2	1168.9	1170.5	1171.3	1171.1	1170.9	1170.7	1170.5
5°	1161.4	1163.1	1165.0	1165.8	1165.6	1165.5	1165.2	1165.0
7.5°	1149.6	1151.4	1153.2	1154.0	1153.8	1153.6	1153.3	1153.2
10°	1139.6	1141.3	1142.9	1143.6	1143.4	1143.2	1143.0	1142.8
12.5°	1126.3	1127.7	1129.0	1129.6	1129.6	1129.5	1129.5	1129.4
15°	1103.2	1104.2	1105.3	1105.7	1105.7	1105.7	1105.7	1105.7
17.5°	1076.3	1077.5	1078.8	1079.0	1077.9	1076.9	1075.8	1074.9
20°	1055.9	1057.3	1058.7	1058.9	1057.9	1056.9	1055.9	1054.8
22.5°	1032.6	1033.6	1034.6	1034.7	1033.9	1033.2	1032.5	1031.9
25°	995.4	995.9	996.3	996.1	995.6	995.0	994.3	993.7
27.5°	956.4	956.5	956.6	956.4	955.7	955.1	954.5	953.9
30°	928.1	927.6	927.2	926.8	926.1	925.5	924.9	924.3
32.5°	899.2	898.5	897.8	896.8	895.7	894.6	893.5	892.4
35°	854.6	853.5	852.6	851.2	849.5	847.9	846.2	844.6
37.5°	807.6	806.1	804.6	803.3	802.5	801.5	800.6	799.6
40°	775.2	773.3	771.4	770.2	769.5	769.0	768.4	767.8
42.5°	742.9	741.2	739.5	738.2	737.3	736.3	735.3	734.4
45°	695.2	692.7	690.3	688.7	688.1	687.5	686.9	686.3
47.5°	644.9	642.4	639.9	637.9	636.5	635.1	633.6	632.1
50°	610.5	607.8	605.1	603.1	601.6	600.2	598.8	597.4
52.5°	577.1	574.7	572.4	570.4	568.8	567.2	565.6	564.0
55°	525.1	523.3	521.4	519.8	518.3	516.8	515.4	514.0
57.5°	473.5	471.1	468.7	467.1	466.3	465.6	464.8	464.0
60°	438.5	436.5	434.4	432.7	431.2	429.8	428.4	427.0
62.5°	404.9	402.7	400.5	398.8	397.7	396.5	395.5	394.3
65°	352.0	350.1	348.2	346.9	346.1	345.3	344.4	343.6
67.5°	301.4	299.8	298.3	297.2	296.8	296.2	295.7	295.2
70°	268.0	266.7	265.5	264.5	263.6	262.8	262.0	261.2
72.5°	236.5	235.1	233.7	232.6	231.8	231.0	230.2	229.3
75°	187.7	187.1	186.5	185.7	184.9	184.0	183.2	182.4
77.5°	143.0	142.6	142.2	141.8	141.2	140.6	140.1	139.5
80°	114.4	114.2	114.0	113.7	113.3	112.9	112.4	112.1
82.5°	87.4	87.0	86.7	86.5	86.4	86.3	86.2	86.1
85°	51.5	51.3	51.0	50.7	50.3	49.9	49.5	49.0
87.5°	23.0	23.3	23.5	23.5	23.4	23.1	22.9	22.7
90°	18.9	20.1	21.2	22.1	22.8	23.5	24.2	24.9
92.5°	18.9	20.1	21.2	21.9	22.2	22.6	22.9	23.2
95°	18.9	20.1	21.2	21.8	21.8	21.8	21.8	21.8
97.5°	38.0	31.5	25.0	21.8	21.8	21.8	21.8	21.8
100°	111.7	77.4	43.1	25.4	24.5	23.6	22.6	21.8
102.5°	217.0	210.6	204.1	193.1	177.4	161.7	146.1	130.4
105°	308.8	308.8	308.8	308.7	308.4	308.3	308.0	307.8
107.5°	391.0	391.0	391.1	390.7	390.0	389.4	388.7	388.0
110°	444.3	443.5	442.8	442.6	442.8	443.1	443.4	443.5



TEST NUMBER: P333247-940

CATALOG NUMBER: S125DIP-S850D1205U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	497.0	496.1	495.2	494.5	494.3	493.9	493.7	493.3
115°	576.4	575.5	574.6	573.5	572.0	570.7	569.3	567.9
117.5°	653.2	652.0	650.8	649.9	649.3	648.7	648.1	647.5
120°	702.8	702.3	701.9	701.1	699.9	698.7	697.6	696.4
122.5°	750.0	749.6	749.1	748.1	746.8	745.5	744.2	742.9
125°	818.9	818.0	817.1	816.3	815.6	814.9	814.2	813.5
127.5°	881.9	881.5	880.9	879.9	878.2	876.4	874.7	873.0
130°	923.0	922.3	921.7	920.7	919.5	918.5	917.3	916.1
132.5°	961.4	961.3	961.2	960.6	959.4	958.2	957.1	955.9
135°	1017.8	1017.4	1016.9	1015.9	1014.6	1013.2	1011.8	1010.4
137.5°	1070.3	1070.4	1070.5	1070.0	1068.7	1067.6	1066.3	1065.1
140°	1102.5	1103.0	1103.5	1103.0	1101.6	1100.3	1098.9	1097.5
142.5°	1134.2	1134.3	1134.3	1133.7	1132.3	1131.0	1129.5	1128.2
145°	1178.8	1179.0	1179.2	1178.7	1177.2	1175.9	1174.5	1173.1
147.5°	1217.0	1217.3	1217.5	1216.8	1215.2	1213.5	1211.9	1210.2
150°	1241.4	1241.9	1242.3	1241.6	1239.8	1238.0	1236.1	1234.3
152.5°	1262.9	1263.5	1263.9	1263.3	1261.6	1260.0	1258.3	1256.7
155°	1292.6	1293.3	1294.1	1293.4	1291.6	1289.8	1287.9	1286.1
157.5°	1317.2	1317.9	1318.7	1318.1	1316.3	1314.5	1312.6	1310.7
160°	1332.5	1333.4	1334.4	1333.9	1332.0	1330.2	1328.4	1326.5
162.5°	1346.5	1347.8	1349.1	1348.7	1346.7	1344.6	1342.6	1340.6
165°	1364.5	1365.9	1367.3	1367.0	1365.2	1363.3	1361.5	1359.7
167.5°	1378.1	1379.7	1381.4	1381.3	1379.1	1377.1	1375.0	1373.0
170°	1385.1	1387.0	1388.8	1388.7	1386.6	1384.6	1382.5	1380.4
172.5°	1390.5	1392.2	1393.8	1393.7	1391.6	1389.6	1387.4	1385.4
175°	1396.5	1398.4	1400.2	1400.1	1398.0	1396.0	1393.8	1391.8
177.5°	1398.9	1400.3	1401.5	1401.4	1400.0	1398.5	1397.0	1395.5
180°	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0	1398.0

(END OF REPORT)