

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333207-940

Luminaire Tested: **S125DIP-S850D365U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333207-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S850D365U940-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4251.3 lumens  
Efficiency: N/A  
Efficacy: 121.5 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 35  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333207-940

CATALOG NUMBER: S125DIP-S850D365U940-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333207-940

CATALOG NUMBER: S125DIP-S850D365U940-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	77	77	77	72
1	103	99	95	91	98	94	90	87	85	82	80	76	74	72	68	67	66	62
2	94	87	80	75	89	82	77	72	75	70	66	67	64	61	61	58	56	52
3	86	76	69	63	81	73	66	61	66	61	56	60	55	52	54	51	48	44
4	79	68	60	54	75	65	57	52	59	53	48	53	49	45	48	44	41	38
5	73	61	52	46	69	58	50	45	53	47	42	48	43	39	44	39	36	33
6	67	55	46	40	63	52	45	39	48	41	37	44	38	34	40	35	32	29
7	62	50	41	36	59	47	40	35	43	37	32	40	34	30	36	32	28	26
8	58	45	37	32	55	43	36	31	40	33	29	36	31	27	33	29	25	23
9	54	41	34	28	51	40	32	28	36	30	26	34	28	24	31	26	23	21
10	50	38	31	26	48	36	30	25	34	28	24	31	26	22	28	24	21	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	7045	7045	7045	7045
5°	8159	7069	6190	7069
10°	9492	7033	5423	7033
15°	10508	6981	5003	6981
20°	11762	6899	4665	6899
25°	13779	6807	4501	6807
30°	14882	6716	4357	6716
35°	12236	6545	4264	6545
40°	8697	6308	4161	6308
45°	6682	5989	4103	5989
50°	5704	5591	4093	5591
55°	5078	5203	4130	5203
60°	4580	4779	4234	4779
65°	4232	4351	4345	4351
70°	3848	3909	4407	3909
75°	3399	3441	4367	3441
80°	2860	2804	3998	2804
85°	2267	2023	3223	2023



TEST NUMBER: P333207-940

CATALOG NUMBER: S125DIP-S850D365U940-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	105.0	2.5
10°-20°	312.7	7.4
20°-30°	507.7	11.9
30°-40°	619.3	14.6
40°-50°	563.4	13.3
50°-60°	448.8	10.6
60°-70°	312.6	7.4
70°-80°	166.7	3.9
80°-90°	42.9	1.0
90°-100°	113.3	2.7
100°-110°	243.6	5.7
110°-120°	228.6	5.4
120°-130°	185.2	4.4
130°-140°	148.7	3.5
140°-150°	112.2	2.6
150°-160°	79.0	1.9
160°-170°	46.5	1.1
170°-180°	15.1	0.4
0°-30°	925.4	21.8
0°-40°	1544.8	36.3
0°-60°	2556.9	60.1
0°-90°	3079.2	72.4
90°-120°	585.4	13.8
90°-150°	1031.5	24.3
90°-180°	1172.0	27.6
0°-180°	4251.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1091	1091	1091	1091	1091	
5°	1258	1090	955	1090	1258	127
15°	1572	1044	748	1044	1572	450
25°	1934	955	632	955	1934	883
35°	1552	830	541	830	1552	950
45°	732	656	449	656	732	586
55°	451	462	367	462	451	406
65°	277	285	284	285	277	275
75°	136	138	175	138	136	147
85°	31	27	44	27	31	35
90°	7	0	7	0	7	6
95°	74	10	74	10	74	105
105°	418	36	418	36	418	415
115°	465	64	465	64	465	454
125°	366	88	366	88	366	332
135°	304	103	304	103	304	236
145°	240	120	240	120	240	153
155°	201	137	201	137	201	94
165°	176	150	176	150	176	50
175°	158	156	158	156	158	15
180°	156	156	156	156	156	



TEST NUMBER: P333207-940

CATALOG NUMBER: S125DIP-S850D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	1153.9	1152.4	1150.9	1147.9	1150.1	1143.9	1140.9	1135.7	1129.4	1127.2	1124.6
5°	1258.5	1260.8	1263.1	1253.4	1254.4	1247.9	1233.1	1221.0	1211.3	1198.8	1190.0
7.5°	1384.5	1378.9	1378.5	1372.3	1361.4	1352.7	1337.1	1317.3	1298.2	1276.3	1258.2
10°	1447.4	1447.9	1443.7	1436.3	1424.8	1416.4	1396.1	1376.5	1353.0	1325.2	1305.3
12.5°	1494.9	1496.7	1491.5	1481.5	1475.9	1457.1	1441.2	1418.1	1390.0	1367.8	1337.5
15°	1571.6	1566.4	1562.7	1550.2	1540.5	1521.1	1495.6	1471.5	1440.9	1412.6	1384.5
17.5°	1645.4	1649.5	1642.5	1631.1	1601.0	1578.2	1544.1	1511.1	1473.1	1435.2	1401.5
20°	1711.4	1715.0	1704.4	1684.5	1648.4	1625.7	1580.7	1538.2	1494.2	1445.6	1408.5
22.5°	1793.6	1790.6	1776.3	1746.0	1714.7	1672.8	1624.1	1572.3	1517.2	1462.2	1413.0
25°	1933.6	1914.1	1905.3	1867.9	1826.7	1765.1	1698.4	1622.5	1553.9	1481.2	1418.3
27.5°	2011.2	2005.1	1995.3	1969.2	1925.8	1860.0	1781.4	1688.8	1592.1	1500.4	1418.0
30°	1995.6	1996.5	1997.5	1989.1	1961.4	1911.8	1833.6	1734.0	1619.2	1515.9	1420.6
32.5°	1857.9	1874.7	1890.8	1909.9	1917.6	1908.2	1859.1	1769.2	1651.1	1533.7	1419.1
35°	1552.0	1557.2	1609.4	1661.3	1731.7	1786.4	1822.9	1783.2	1683.6	1548.8	1417.3
37.5°	1210.1	1235.2	1271.4	1330.0	1431.6	1522.5	1639.5	1693.3	1661.2	1553.7	1414.1
40°	1031.6	1054.8	1078.3	1138.1	1223.8	1334.0	1466.9	1580.3	1606.7	1538.2	1402.9
42.5°	893.9	912.1	938.3	983.3	1054.9	1152.4	1279.4	1427.7	1518.9	1493.0	1379.7
45°	731.6	743.2	763.6	799.2	851.0	927.5	1039.5	1201.6	1342.7	1389.6	1324.3
47.5°	626.2	626.1	641.9	666.6	704.0	768.9	851.8	978.7	1129.6	1241.2	1236.0
50°	567.7	565.3	577.8	599.1	628.7	671.8	751.0	852.4	997.4	1123.7	1159.0
52.5°	517.3	517.5	525.2	541.0	565.8	602.6	661.7	753.1	877.0	1006.7	1073.0
55°	451.0	449.2	457.9	468.6	486.6	510.7	553.3	623.2	723.7	851.5	937.6
57.5°	390.2	395.3	398.9	406.3	421.2	437.4	473.3	524.6	604.3	714.0	805.0
60°	354.6	359.8	362.6	370.0	382.0	395.9	423.7	465.4	532.4	627.0	717.2
62.5°	322.8	326.8	327.7	334.4	344.2	357.8	379.6	414.6	467.6	550.3	638.7
65°	276.9	276.9	278.7	285.7	290.3	302.4	319.1	344.5	387.1	451.5	526.9
67.5°	232.6	234.9	234.3	237.5	241.7	251.0	263.0	284.0	315.6	362.6	422.9
70°	203.8	205.5	205.1	207.4	212.0	218.1	227.8	247.7	270.4	310.7	362.6
72.5°	177.8	178.5	177.4	180.4	183.2	188.4	199.3	209.9	231.1	265.1	307.7
75°	136.2	137.1	137.9	139.8	142.6	145.3	151.0	161.6	175.5	201.0	228.3
77.5°	102.0	100.3	102.5	102.3	103.8	105.9	110.8	116.5	127.9	144.0	165.1
80°	76.9	77.3	77.3	77.8	80.1	81.5	85.7	89.8	98.6	110.7	125.5
82.5°	56.1	57.3	56.6	57.4	59.4	60.4	62.7	66.1	71.2	80.7	91.4
85°	30.6	28.3	29.2	30.1	30.1	30.6	32.4	33.8	36.6	40.3	44.4
87.5°	10.3	11.1	11.4	11.4	11.8	11.6	13.0	13.0	14.0	15.1	16.4
90°	7.2	7.2	7.0	7.0	7.0	6.3	6.0	5.7	5.4	5.1	4.4
92.5°	20.1	20.6	21.0	21.8	25.9	30.5	40.5	55.8	82.2	101.6	103.3
95°	74.1	79.1	81.6	91.0	113.4	139.9	178.7	226.6	273.2	279.2	227.8
97.5°	179.0	183.1	192.2	209.8	229.3	266.1	303.9	337.4	345.7	298.2	203.5
100°	245.8	250.8	262.5	285.2	306.9	339.7	372.2	387.6	363.4	284.5	181.6
102.5°	320.5	324.2	336.9	353.0	376.3	398.5	414.0	404.5	352.8	260.6	164.9
105°	417.6	421.3	427.7	438.0	448.2	451.6	437.7	394.6	319.0	228.5	148.7
107.5°	469.1	471.6	473.8	473.8	468.7	452.2	416.6	359.0	284.4	206.3	142.0
110°	486.2	486.2	484.0	478.0	463.9	437.1	392.7	332.8	264.7	196.0	139.9



TEST NUMBER: P333207-940

CATALOG NUMBER: S125DIP-S850D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	484.3	482.0	476.5	466.2	445.5	413.9	369.0	312.1	250.1	189.9	139.9
115°	465.1	461.0	452.2	437.1	412.5	378.2	335.0	286.1	234.2	183.4	140.9
117.5°	431.7	429.2	420.4	404.7	380.2	348.7	311.5	269.4	224.6	180.2	142.9
120°	410.0	407.5	399.0	383.9	360.5	332.8	298.1	260.3	219.4	178.7	145.0
122.5°	390.8	388.6	380.0	366.2	345.4	319.4	288.6	253.5	214.8	177.5	146.7
125°	366.5	363.4	356.4	343.5	325.8	303.2	275.7	243.6	208.7	175.8	149.7
127.5°	345.7	344.3	337.8	326.4	310.3	289.1	263.5	233.5	203.0	175.1	153.0
130°	334.4	332.5	326.2	315.8	300.1	279.6	254.9	227.2	199.2	174.6	155.1
132.5°	323.0	320.8	315.0	304.7	288.9	269.2	246.9	220.9	196.2	174.6	157.3
135°	304.4	302.6	296.9	286.5	272.6	254.7	234.4	212.8	192.5	174.6	160.4
137.5°	284.5	282.5	277.2	267.8	255.4	240.1	223.4	205.8	189.3	175.0	163.3
140°	270.7	269.1	264.4	256.2	244.5	231.3	216.8	202.0	187.8	175.2	164.5
142.5°	257.9	256.5	252.1	245.1	235.2	223.7	211.2	198.8	186.5	175.5	165.2
145°	240.1	238.9	235.4	230.1	222.5	214.0	204.2	194.5	184.7	175.2	166.0
147.5°	225.2	224.5	222.6	218.3	212.3	205.9	198.3	190.4	182.7	174.4	166.4
150°	216.8	216.5	215.3	211.4	206.7	201.1	195.1	188.2	181.2	173.6	166.4
152.5°	210.3	209.9	208.7	205.6	201.7	197.2	191.8	185.7	179.4	172.6	166.1
155°	201.3	201.1	200.1	197.9	194.7	191.3	186.9	181.8	176.5	170.9	165.4
157.5°	193.4	193.5	192.6	190.8	188.3	185.7	182.2	178.1	173.7	168.9	164.6
160°	188.2	188.4	187.8	186.3	184.0	181.8	178.7	175.6	171.5	167.6	163.9
162.5°	183.3	183.4	183.2	182.0	180.3	178.3	175.7	172.7	169.4	166.1	163.1
165°	176.5	176.5	176.5	175.8	174.6	173.0	171.1	168.9	166.4	163.9	162.0
167.5°	170.1	170.2	170.5	170.0	169.3	168.2	166.7	165.2	163.5	161.7	160.2
170°	166.4	166.7	166.7	166.4	165.8	165.1	164.2	163.3	161.7	160.4	159.4
172.5°	162.8	163.2	163.7	163.1	163.0	162.6	161.9	161.0	159.9	158.9	158.5
175°	158.5	158.8	159.4	159.2	159.2	159.2	158.5	158.5	157.6	157.3	157.3
177.5°	156.3	156.3	157.0	156.9	157.0	157.0	157.0	156.9	156.6	156.3	156.3
180°	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3



TEST NUMBER: P333207-940

CATALOG NUMBER: S125DIP-S850D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	1122.4	1119.8	1116.8	1111.6	1105.4	1102.0	1096.8	1093.5	1086.8	1081.3	1075.3
5°	1179.3	1167.2	1156.2	1141.8	1126.1	1115.9	1103.8	1090.4	1076.6	1062.2	1046.4
7.5°	1238.3	1217.0	1193.8	1168.9	1144.6	1122.2	1100.8	1079.8	1060.2	1036.4	1016.4
10°	1277.9	1251.1	1222.4	1188.6	1155.7	1127.0	1097.9	1072.4	1046.4	1018.7	994.1
12.5°	1317.6	1281.8	1241.3	1204.2	1164.6	1130.0	1095.6	1063.1	1030.6	999.8	971.2
15°	1345.6	1314.0	1276.6	1223.8	1179.3	1131.7	1086.3	1044.1	1004.8	970.5	934.4
17.5°	1364.0	1323.4	1283.2	1232.5	1174.2	1120.9	1069.5	1021.3	976.9	933.4	898.7
20°	1367.3	1325.6	1283.5	1233.9	1174.2	1113.1	1061.8	1003.8	956.2	911.2	868.6
22.5°	1366.2	1319.0	1273.1	1222.1	1163.9	1107.6	1045.4	986.4	934.7	890.5	846.1
25°	1355.8	1305.3	1247.9	1196.5	1139.1	1079.3	1016.4	955.2	902.4	851.9	808.0
27.5°	1347.0	1281.6	1216.6	1156.6	1101.2	1046.4	986.1	923.5	865.0	813.9	772.4
30°	1336.3	1264.5	1191.3	1128.8	1071.9	1018.7	961.7	900.6	839.5	789.4	745.0
32.5°	1326.7	1243.0	1165.8	1097.8	1037.4	985.7	933.2	875.0	815.0	764.3	719.8
35°	1308.1	1211.3	1122.8	1046.0	981.6	928.4	884.4	830.2	775.1	726.0	683.4
37.5°	1284.4	1169.6	1074.7	994.1	923.5	867.5	826.5	784.9	732.0	684.7	646.2
40°	1265.9	1140.0	1039.5	957.1	884.0	825.5	787.6	748.2	704.3	660.3	619.6
42.5°	1242.6	1113.3	1004.0	915.3	842.8	786.0	746.1	712.7	673.9	632.8	595.0
45°	1199.7	1065.0	946.5	851.0	777.8	721.8	680.6	655.7	626.5	587.5	555.6
47.5°	1136.7	1006.9	884.3	785.9	710.3	658.4	619.8	595.8	575.2	546.4	517.4
50°	1080.7	963.6	839.5	741.7	666.3	613.9	578.4	556.5	539.0	516.7	492.2
52.5°	1018.1	909.1	795.4	698.8	624.1	572.5	537.6	518.4	503.8	487.9	463.7
55°	918.6	826.1	720.5	628.7	559.8	509.3	478.8	462.1	450.0	438.0	423.2
57.5°	809.0	736.6	643.1	559.4	495.8	449.9	421.3	405.1	395.8	389.6	380.8
60°	732.0	670.0	589.4	513.0	451.0	410.3	382.5	370.0	362.1	357.0	350.5
62.5°	660.6	609.7	534.9	465.2	411.0	372.5	347.7	335.6	328.0	325.5	320.1
65°	555.2	515.9	454.2	396.4	350.1	317.2	296.3	284.7	280.1	277.3	277.9
67.5°	451.4	427.4	377.9	328.6	291.6	264.0	247.4	238.4	236.1	232.5	232.4
70°	388.0	370.0	328.3	285.3	252.4	231.0	216.2	207.0	204.6	202.8	202.3
72.5°	332.1	316.3	280.1	245.6	216.1	197.3	185.1	179.6	175.8	174.7	174.6
75°	249.6	240.8	212.0	184.8	164.3	151.4	143.1	137.9	135.2	134.7	135.2
77.5°	177.5	169.8	151.5	132.2	119.3	109.5	102.5	100.7	97.6	97.6	97.1
80°	133.3	128.2	116.7	101.4	90.8	82.4	78.7	75.4	74.5	73.1	74.5
82.5°	96.7	91.2	83.4	73.7	64.8	59.8	56.1	55.1	54.6	53.9	54.2
85°	47.7	48.2	43.5	36.1	32.4	29.6	27.3	27.3	26.8	26.4	26.8
87.5°	17.1	16.2	14.7	13.5	11.5	10.3	9.7	10.1	9.0	8.7	9.3
90°	4.1	3.5	3.1	2.5	1.9	1.2	0.6	0.4	0.6	1.2	1.9
92.5°	71.9	43.1	25.9	16.7	11.2	7.3	4.6	3.8	4.6	7.3	11.2
95°	140.9	71.5	37.8	23.6	16.7	13.2	10.7	10.4	10.7	13.2	16.7
97.5°	112.4	61.6	39.3	29.2	22.9	19.4	17.7	17.3	17.7	19.4	22.9
100°	102.1	61.2	42.9	33.4	27.4	24.0	22.6	22.0	22.6	24.0	27.4
102.5°	97.8	63.4	47.2	38.0	32.5	28.7	27.7	27.4	27.7	28.7	32.5
105°	96.1	68.0	54.2	45.4	40.3	37.2	35.6	35.6	35.6	37.2	40.3
107.5°	99.0	75.0	61.6	53.7	48.4	45.8	44.3	43.7	44.3	45.8	48.4
110°	101.8	80.1	67.1	58.9	54.2	51.4	50.1	49.5	50.1	51.4	54.2





TEST NUMBER: P333207-940

CATALOG NUMBER: S125DIP-S850D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	105.3	84.8	72.4	64.5	59.7	56.9	55.9	55.3	55.9	56.9	59.7
115°	110.6	92.4	80.7	72.8	68.0	65.3	64.3	63.7	64.3	65.3	68.0
117.5°	116.6	100.0	89.0	81.4	76.0	73.2	72.1	71.2	72.1	73.2	76.0
120°	120.7	105.6	94.5	86.7	81.3	78.5	77.2	76.2	77.2	78.5	81.3
122.5°	125.2	110.8	99.9	91.9	86.1	83.3	82.2	81.6	82.2	83.3	86.1
125°	131.4	117.9	107.5	99.2	93.3	90.4	88.9	88.3	88.9	90.4	93.3
127.5°	137.1	124.6	114.6	106.4	100.0	96.4	94.4	93.5	94.4	96.4	100.0
130°	140.9	128.9	119.1	110.9	104.3	100.2	97.7	96.8	97.7	100.2	104.3
132.5°	144.2	133.0	123.1	114.9	108.1	103.5	100.5	99.2	100.5	103.5	108.1
135°	148.7	138.3	128.6	120.1	113.4	108.4	104.6	103.3	104.6	108.4	113.4
137.5°	152.1	142.2	133.3	124.6	118.1	113.0	109.5	108.5	109.5	113.0	118.1
140°	154.4	145.0	135.8	127.3	121.4	116.3	112.5	111.6	112.5	116.3	121.4
142.5°	155.7	146.7	138.1	130.1	124.4	119.3	115.7	115.1	115.7	119.3	124.4
145°	157.6	149.7	141.5	134.3	128.6	124.1	121.0	120.4	121.0	124.1	128.6
147.5°	158.7	151.6	144.4	138.0	133.1	129.0	126.3	125.9	126.3	129.0	133.1
150°	159.4	152.8	145.9	140.5	136.2	132.1	129.8	129.2	129.8	132.1	136.2
152.5°	160.0	154.1	147.7	142.9	138.7	135.1	133.1	132.8	133.1	135.1	138.7
155°	160.4	155.3	150.0	145.6	142.4	139.3	137.4	137.4	137.4	139.3	142.4
157.5°	160.7	156.4	151.9	148.5	145.7	143.0	141.5	141.6	141.5	143.0	145.7
160°	160.7	156.9	152.8	150.0	147.5	145.3	144.0	144.4	144.0	145.3	147.5
162.5°	160.5	157.5	153.8	151.5	149.5	147.6	146.3	146.6	146.3	147.6	149.5
165°	160.1	157.6	155.1	153.2	151.9	150.3	149.4	150.0	149.4	150.3	151.9
167.5°	159.3	157.6	155.5	154.3	153.4	152.6	151.9	152.3	151.9	152.6	153.4
170°	158.8	157.6	156.0	155.1	154.4	153.8	153.5	153.8	153.5	153.8	154.4
172.5°	158.4	157.3	156.0	155.5	155.2	154.5	154.3	154.8	154.3	154.5	155.2
175°	157.6	156.9	156.0	156.0	156.0	155.7	155.3	156.0	155.3	155.7	156.0
177.5°	156.9	156.6	156.0	156.0	156.3	156.0	156.0	156.6	156.0	156.0	156.3
180°	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3



TEST NUMBER: P333207-940

CATALOG NUMBER: S125DIP-S850D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	1072.0	1067.9	1064.6	1057.2	1053.1	1047.6	1043.1	1047.9	1042.8	1045.0	1041.6
5°	1038.6	1025.6	1016.4	1002.9	991.3	980.7	972.9	971.4	967.7	965.9	960.3
7.5°	998.4	982.1	966.3	948.7	933.8	918.7	909.1	901.2	895.9	888.9	884.2
10°	974.6	952.9	934.4	913.1	894.6	878.3	865.4	858.9	852.9	844.1	840.9
12.5°	945.4	922.9	900.3	877.5	859.8	841.7	830.5	820.7	816.6	806.6	805.7
15°	910.3	876.6	854.3	831.2	806.6	791.8	782.5	771.9	767.2	760.3	755.2
17.5°	868.4	838.3	810.5	786.5	765.4	753.0	741.5	734.1	726.2	721.7	713.4
20°	838.1	809.4	781.6	756.1	739.9	725.6	716.3	709.4	701.1	698.7	690.4
22.5°	812.5	780.9	754.2	732.8	715.1	698.9	688.8	684.2	678.4	671.3	669.6
25°	771.0	738.1	715.4	694.1	678.3	663.5	656.6	650.6	645.0	639.9	638.0
27.5°	735.0	705.6	678.7	659.4	645.8	632.2	626.1	618.8	614.7	610.6	605.6
30°	709.8	679.8	656.1	637.6	622.8	610.7	604.2	599.1	595.5	591.7	589.0
32.5°	683.9	656.0	633.1	615.0	600.2	591.1	585.3	581.8	577.7	573.2	569.7
35°	649.6	619.0	596.8	581.1	569.5	562.6	556.1	552.9	548.2	548.2	544.5
37.5°	611.0	584.6	565.0	550.6	540.3	534.0	527.0	524.8	521.8	519.9	518.6
40°	588.1	563.5	545.0	530.7	519.5	514.4	508.9	505.2	503.3	501.0	500.1
42.5°	564.4	540.9	523.2	509.9	500.2	495.9	490.7	488.1	484.4	481.3	480.8
45°	528.3	505.6	489.5	478.8	470.5	465.4	462.1	456.6	454.7	451.0	450.5
47.5°	494.1	472.3	456.5	447.7	440.4	436.2	431.1	425.6	423.5	421.6	421.4
50°	468.6	448.7	433.8	425.5	418.6	412.6	407.4	403.8	402.3	402.3	403.3
52.5°	442.6	425.7	413.1	403.0	396.4	389.9	385.2	383.0	380.8	383.1	384.8
55°	404.7	387.5	378.3	368.5	362.1	354.6	352.4	351.4	350.1	353.7	355.6
57.5°	364.5	352.5	341.6	332.0	326.2	321.9	318.8	318.2	320.7	322.5	328.6
60°	338.9	325.0	315.3	307.9	301.0	298.2	297.3	296.3	298.2	303.3	311.1
62.5°	310.8	299.5	289.0	283.5	278.4	273.8	273.6	274.1	277.9	283.7	291.5
65°	269.5	259.8	252.8	246.3	242.2	239.4	240.3	242.2	246.3	254.2	263.0
67.5°	227.6	220.9	214.6	209.4	205.4	205.4	206.3	209.1	214.0	223.1	231.1
70°	200.5	193.1	188.0	185.7	182.4	180.6	183.3	188.0	192.2	200.5	207.4
72.5°	173.4	167.2	163.2	161.6	160.2	158.7	159.6	164.6	170.3	178.6	186.7
75°	133.3	131.0	128.2	126.4	125.0	125.9	126.9	131.5	136.2	144.9	154.2
77.5°	97.3	94.9	93.3	92.8	92.0	92.5	95.1	98.5	103.1	109.5	116.5
80°	73.7	72.7	71.8	71.3	71.3	71.8	75.4	77.8	81.9	88.0	93.5
82.5°	53.6	53.1	52.9	52.8	53.1	53.2	55.5	58.5	62.0	66.5	71.3
85°	28.3	27.3	28.7	29.2	28.3	29.6	30.6	32.4	33.8	36.1	38.4
87.5°	9.8	10.6	10.3	10.8	10.9	11.8	11.4	13.0	13.8	14.6	14.4
90°	2.5	3.1	3.5	4.1	4.4	5.1	5.4	5.7	6.0	6.3	7.0
92.5°	16.7	25.9	43.1	71.9	103.3	101.6	82.2	55.8	40.5	30.5	25.9
95°	23.6	37.8	71.5	140.9	227.8	279.2	273.2	226.6	178.7	139.9	113.4
97.5°	29.2	39.3	61.6	112.4	203.5	298.2	345.7	337.4	303.9	266.1	229.3
100°	33.4	42.9	61.2	102.1	181.6	284.5	363.4	387.6	372.2	339.7	306.9
102.5°	38.0	47.2	63.4	97.8	164.9	260.6	352.8	404.5	414.0	398.5	376.3
105°	45.4	54.2	68.0	96.1	148.7	228.5	319.0	394.6	437.7	451.6	448.2
107.5°	53.7	61.6	75.0	99.0	142.0	206.3	284.4	359.0	416.6	452.2	468.7
110°	58.9	67.1	80.1	101.8	139.9	196.0	264.7	332.8	392.7	437.1	463.9



TEST NUMBER: P333207-940

CATALOG NUMBER: S125DIP-S850D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	64.5	72.4	84.8	105.3	139.9	189.9	250.1	312.1	369.0	413.9	445.5
115°	72.8	80.7	92.4	110.6	140.9	183.4	234.2	286.1	335.0	378.2	412.5
117.5°	81.4	89.0	100.0	116.6	142.9	180.2	224.6	269.4	311.5	348.7	380.2
120°	86.7	94.5	105.6	120.7	145.0	178.7	219.4	260.3	298.1	332.8	360.5
122.5°	91.9	99.9	110.8	125.2	146.7	177.5	214.8	253.5	288.6	319.4	345.4
125°	99.2	107.5	117.9	131.4	149.7	175.8	208.7	243.6	275.7	303.2	325.8
127.5°	106.4	114.6	124.6	137.1	153.0	175.1	203.0	233.5	263.5	289.1	310.3
130°	110.9	119.1	128.9	140.9	155.1	174.6	199.2	227.2	254.9	279.6	300.1
132.5°	114.9	123.1	133.0	144.2	157.3	174.6	196.2	220.9	246.9	269.2	288.9
135°	120.1	128.6	138.3	148.7	160.4	174.6	192.5	212.8	234.4	254.7	272.6
137.5°	124.6	133.3	142.2	152.1	163.3	175.0	189.3	205.8	223.4	240.1	255.4
140°	127.3	135.8	145.0	154.4	164.5	175.2	187.8	202.0	216.8	231.3	244.5
142.5°	130.1	138.1	146.7	155.7	165.2	175.5	186.5	198.8	211.2	223.7	235.2
145°	134.3	141.5	149.7	157.6	166.0	175.2	184.7	194.5	204.2	214.0	222.5
147.5°	138.0	144.4	151.6	158.7	166.4	174.4	182.7	190.4	198.3	205.9	212.3
150°	140.5	145.9	152.8	159.4	166.4	173.6	181.2	188.2	195.1	201.1	206.7
152.5°	142.9	147.7	154.1	160.0	166.1	172.6	179.4	185.7	191.8	197.2	201.7
155°	145.6	150.0	155.3	160.4	165.4	170.9	176.5	181.8	186.9	191.3	194.7
157.5°	148.5	151.9	156.4	160.7	164.6	168.9	173.7	178.1	182.2	185.7	188.3
160°	150.0	152.8	156.9	160.7	163.9	167.6	171.5	175.6	178.7	181.8	184.0
162.5°	151.5	153.8	157.5	160.5	163.1	166.1	169.4	172.7	175.7	178.3	180.3
165°	153.2	155.1	157.6	160.1	162.0	163.9	166.4	168.9	171.1	173.0	174.6
167.5°	154.3	155.5	157.6	159.3	160.2	161.7	163.5	165.2	166.7	168.2	169.3
170°	155.1	156.0	157.6	158.8	159.4	160.4	161.7	163.3	164.2	165.1	165.8
172.5°	155.5	156.0	157.3	158.4	158.5	158.9	159.9	161.0	161.9	162.6	163.0
175°	156.0	156.0	156.9	157.6	157.3	157.3	157.6	158.5	158.5	159.2	159.2
177.5°	156.0	156.0	156.6	156.9	156.3	156.3	156.6	156.9	157.0	157.0	157.0
180°	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3



TEST NUMBER: P333207-940

CATALOG NUMBER: S125DIP-S850D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	1039.4	1042.0	1039.7	1042.8	1039.7	1042.0	1039.4	1041.6	1045.0	1042.8	1047.9
5°	958.0	953.9	956.6	954.8	956.6	953.9	958.0	960.3	965.9	967.7	971.4
7.5°	882.8	878.8	874.3	872.2	874.3	878.8	882.8	884.2	888.9	895.9	901.2
10°	835.8	830.6	830.2	827.0	830.2	830.6	835.8	840.9	844.1	852.9	858.9
12.5°	801.3	796.6	791.3	790.0	791.3	796.6	801.3	805.7	806.6	816.6	820.7
15°	752.4	748.7	745.5	748.2	745.5	748.7	752.4	755.2	760.3	767.2	771.9
17.5°	711.8	708.7	708.1	704.7	708.1	708.7	711.8	713.4	721.7	726.2	734.1
20°	686.2	683.9	684.8	678.8	684.8	683.9	686.2	690.4	698.7	701.1	709.4
22.5°	665.8	661.3	660.8	659.5	660.8	661.3	665.8	669.6	671.3	678.4	684.2
25°	633.9	631.6	629.3	631.6	629.3	631.6	633.9	638.0	639.9	645.0	650.6
27.5°	606.0	603.2	602.6	602.9	602.6	603.2	606.0	605.6	610.6	614.7	618.8
30°	589.0	584.3	584.8	584.3	584.8	584.3	589.0	589.0	591.7	595.5	599.1
32.5°	570.4	567.3	566.7	565.8	566.7	567.3	570.4	569.7	573.2	577.7	581.8
35°	543.1	543.1	540.8	540.8	540.8	543.1	543.1	544.5	548.2	548.2	552.9
37.5°	517.5	517.0	515.6	515.9	515.6	517.0	517.5	518.6	519.9	521.8	524.8
40°	498.2	497.8	496.3	493.6	496.3	497.8	498.2	500.1	501.0	503.3	505.2
42.5°	479.7	478.1	477.5	476.5	477.5	478.1	479.7	480.8	481.3	484.4	488.1
45°	450.5	450.5	449.6	449.2	449.6	450.5	450.5	450.5	451.0	454.7	456.6
47.5°	422.2	423.0	424.8	424.5	424.8	423.0	422.2	421.4	421.6	423.5	425.6
50°	405.1	405.6	407.0	407.4	407.0	405.6	405.1	403.3	402.3	402.3	403.8
52.5°	386.3	389.0	390.7	390.4	390.7	389.0	386.3	384.8	383.1	380.8	383.0
55°	359.8	363.0	366.2	366.8	366.2	363.0	359.8	355.6	353.7	350.1	351.4
57.5°	333.6	338.1	341.5	342.6	341.5	338.1	333.6	328.6	322.5	320.7	318.2
60°	315.8	321.8	326.0	327.8	326.0	321.8	315.8	311.1	303.3	298.2	296.3
62.5°	298.7	305.5	309.7	310.0	309.7	305.5	298.7	291.5	283.7	277.9	274.1
65°	270.9	277.9	281.5	284.3	281.5	277.9	270.9	263.0	254.2	246.3	242.2
67.5°	240.9	247.8	251.9	254.1	251.9	247.8	240.9	231.1	223.1	214.0	209.1
70°	219.0	226.0	231.5	233.4	231.5	226.0	219.0	207.4	200.5	192.2	188.0
72.5°	197.5	203.8	208.2	210.4	208.2	203.8	197.5	186.7	178.6	170.3	164.6
75°	160.2	168.5	172.7	175.0	172.7	168.5	160.2	154.2	144.9	136.2	131.5
77.5°	123.5	131.2	133.7	134.8	133.7	131.2	123.5	116.5	109.5	103.1	98.5
80°	99.1	103.7	106.9	107.5	106.9	103.7	99.1	93.5	88.0	81.9	77.8
82.5°	76.2	80.0	81.1	82.2	81.1	80.0	76.2	71.3	66.5	62.0	58.5
85°	41.6	43.5	44.0	43.5	44.0	43.5	41.6	38.4	36.1	33.8	32.4
87.5°	15.1	14.7	14.8	15.5	14.8	14.7	15.1	14.4	14.6	13.8	13.0
90°	7.0	7.0	7.2	7.2	7.2	7.0	7.0	7.0	6.3	6.0	5.7
92.5°	21.8	21.0	20.6	20.1	20.6	21.0	21.8	25.9	30.5	40.5	55.8
95°	91.0	81.6	79.1	74.1	79.1	81.6	91.0	113.4	139.9	178.7	226.6
97.5°	209.8	192.2	183.1	179.0	183.1	192.2	209.8	229.3	266.1	303.9	337.4
100°	285.2	262.5	250.8	245.8	250.8	262.5	285.2	306.9	339.7	372.2	387.6
102.5°	353.0	336.9	324.2	320.5	324.2	336.9	353.0	376.3	398.5	414.0	404.5
105°	438.0	427.7	421.3	417.6	421.3	427.7	438.0	448.2	451.6	437.7	394.6
107.5°	473.8	473.8	471.6	469.1	471.6	473.8	473.8	468.7	452.2	416.6	359.0
110°	478.0	484.0	486.2	486.2	486.2	484.0	478.0	463.9	437.1	392.7	332.8



TEST NUMBER: P333207-940

CATALOG NUMBER: S125DIP-S850D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	466.2	476.5	482.0	484.3	482.0	476.5	466.2	445.5	413.9	369.0	312.1
115°	437.1	452.2	461.0	465.1	461.0	452.2	437.1	412.5	378.2	335.0	286.1
117.5°	404.7	420.4	429.2	431.7	429.2	420.4	404.7	380.2	348.7	311.5	269.4
120°	383.9	399.0	407.5	410.0	407.5	399.0	383.9	360.5	332.8	298.1	260.3
122.5°	366.2	380.0	388.6	390.8	388.6	380.0	366.2	345.4	319.4	288.6	253.5
125°	343.5	356.4	363.4	366.5	363.4	356.4	343.5	325.8	303.2	275.7	243.6
127.5°	326.4	337.8	344.3	345.7	344.3	337.8	326.4	310.3	289.1	263.5	233.5
130°	315.8	326.2	332.5	334.4	332.5	326.2	315.8	300.1	279.6	254.9	227.2
132.5°	304.7	315.0	320.8	323.0	320.8	315.0	304.7	288.9	269.2	246.9	220.9
135°	286.5	296.9	302.6	304.4	302.6	296.9	286.5	272.6	254.7	234.4	212.8
137.5°	267.8	277.2	282.5	284.5	282.5	277.2	267.8	255.4	240.1	223.4	205.8
140°	256.2	264.4	269.1	270.7	269.1	264.4	256.2	244.5	231.3	216.8	202.0
142.5°	245.1	252.1	256.5	257.9	256.5	252.1	245.1	235.2	223.7	211.2	198.8
145°	230.1	235.4	238.9	240.1	238.9	235.4	230.1	222.5	214.0	204.2	194.5
147.5°	218.3	222.6	224.5	225.2	224.5	222.6	218.3	212.3	205.9	198.3	190.4
150°	211.4	215.3	216.5	216.8	216.5	215.3	211.4	206.7	201.1	195.1	188.2
152.5°	205.6	208.7	209.9	210.3	209.9	208.7	205.6	201.7	197.2	191.8	185.7
155°	197.9	200.1	201.1	201.3	201.1	200.1	197.9	194.7	191.3	186.9	181.8
157.5°	190.8	192.6	193.5	193.4	193.5	192.6	190.8	188.3	185.7	182.2	178.1
160°	186.3	187.8	188.4	188.2	188.4	187.8	186.3	184.0	181.8	178.7	175.6
162.5°	182.0	183.2	183.4	183.3	183.4	183.2	182.0	180.3	178.3	175.7	172.7
165°	175.8	176.5	176.5	176.5	176.5	176.5	175.8	174.6	173.0	171.1	168.9
167.5°	170.0	170.5	170.2	170.1	170.2	170.5	170.0	169.3	168.2	166.7	165.2
170°	166.4	166.7	166.7	166.4	166.7	166.7	166.4	165.8	165.1	164.2	163.3
172.5°	163.1	163.7	163.2	162.8	163.2	163.7	163.1	163.0	162.6	161.9	161.0
175°	159.2	159.4	158.8	158.5	158.8	159.4	159.2	159.2	159.2	158.5	158.5
177.5°	156.9	157.0	156.3	156.3	156.3	157.0	156.9	157.0	157.0	157.0	156.9
180°	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3



TEST NUMBER: P333207-940

CATALOG NUMBER: S125DIP-S850D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	1043.1	1047.6	1053.1	1057.2	1064.6	1067.9	1072.0	1075.3	1081.3	1086.8	1093.5
5°	972.9	980.7	991.3	1002.9	1016.4	1025.6	1038.6	1046.4	1062.2	1076.6	1090.4
7.5°	909.1	918.7	933.8	948.7	966.3	982.1	998.4	1016.4	1036.4	1060.2	1079.8
10°	865.4	878.3	894.6	913.1	934.4	952.9	974.6	994.1	1018.7	1046.4	1072.4
12.5°	830.5	841.7	859.8	877.5	900.3	922.9	945.4	971.2	999.8	1030.6	1063.1
15°	782.5	791.8	806.6	831.2	854.3	876.6	910.3	934.4	970.5	1004.8	1044.1
17.5°	741.5	753.0	765.4	786.5	810.5	838.3	868.4	898.7	933.4	976.9	1021.3
20°	716.3	725.6	739.9	756.1	781.6	809.4	838.1	868.6	911.2	956.2	1003.8
22.5°	688.8	698.9	715.1	732.8	754.2	780.9	812.5	846.1	890.5	934.7	986.4
25°	656.6	663.5	678.3	694.1	715.4	738.1	771.0	808.0	851.9	902.4	955.2
27.5°	626.1	632.2	645.8	659.4	678.7	705.6	735.0	772.4	813.9	865.0	923.5
30°	604.2	610.7	622.8	637.6	656.1	679.8	709.8	745.0	789.4	839.5	900.6
32.5°	585.3	591.1	600.2	615.0	633.1	656.0	683.9	719.8	764.3	815.0	875.0
35°	556.1	562.6	569.5	581.1	596.8	619.0	649.6	683.4	726.0	775.1	830.2
37.5°	527.0	534.0	540.3	550.6	565.0	584.6	611.0	646.2	684.7	732.0	784.9
40°	508.9	514.4	519.5	530.7	545.0	563.5	588.1	619.6	660.3	704.3	748.2
42.5°	490.7	495.9	500.2	509.9	523.2	540.9	564.4	595.0	632.8	673.9	712.7
45°	462.1	465.4	470.5	478.8	489.5	505.6	528.3	555.6	587.5	626.5	655.7
47.5°	431.1	436.2	440.4	447.7	456.5	472.3	494.1	517.4	546.4	575.2	595.8
50°	407.4	412.6	418.6	425.5	433.8	448.7	468.6	492.2	516.7	539.0	556.5
52.5°	385.2	389.9	396.4	403.0	413.1	425.7	442.6	463.7	487.9	503.8	518.4
55°	352.4	354.6	362.1	368.5	378.3	387.5	404.7	423.2	438.0	450.0	462.1
57.5°	318.8	321.9	326.2	332.0	341.6	352.5	364.5	380.8	389.6	395.8	405.1
60°	297.3	298.2	301.0	307.9	315.3	325.0	338.9	350.5	357.0	362.1	370.0
62.5°	273.6	273.8	278.4	283.5	289.0	299.5	310.8	320.1	325.5	328.0	335.6
65°	240.3	239.4	242.2	246.3	252.8	259.8	269.5	277.9	277.3	280.1	284.7
67.5°	206.3	205.4	205.4	209.4	214.6	220.9	227.6	232.4	232.5	236.1	238.4
70°	183.3	180.6	182.4	185.7	188.0	193.1	200.5	202.3	202.8	204.6	207.0
72.5°	159.6	158.7	160.2	161.6	163.2	167.2	173.4	174.6	174.7	175.8	179.6
75°	126.9	125.9	125.0	126.4	128.2	131.0	133.3	135.2	134.7	135.2	137.9
77.5°	95.1	92.5	92.0	92.8	93.3	94.9	97.3	97.1	97.6	97.6	100.7
80°	75.4	71.8	71.3	71.3	71.8	72.7	73.7	74.5	73.1	74.5	75.4
82.5°	55.5	53.2	53.1	52.8	52.9	53.1	53.6	54.2	53.9	54.6	55.1
85°	30.6	29.6	28.3	29.2	28.7	27.3	28.3	26.8	26.4	26.8	27.3
87.5°	11.4	11.8	10.9	10.8	10.3	10.6	9.8	9.3	8.7	9.0	10.1
90°	5.4	5.1	4.4	4.1	3.5	3.1	2.5	1.9	1.2	0.6	0.4
92.5°	82.2	101.6	103.3	71.9	43.1	25.9	16.7	11.2	7.3	4.6	3.8
95°	273.2	279.2	227.8	140.9	71.5	37.8	23.6	16.7	13.2	10.7	10.4
97.5°	345.7	298.2	203.5	112.4	61.6	39.3	29.2	22.9	19.4	17.7	17.3
100°	363.4	284.5	181.6	102.1	61.2	42.9	33.4	27.4	24.0	22.6	22.0
102.5°	352.8	260.6	164.9	97.8	63.4	47.2	38.0	32.5	28.7	27.7	27.4
105°	319.0	228.5	148.7	96.1	68.0	54.2	45.4	40.3	37.2	35.6	35.6
107.5°	284.4	206.3	142.0	99.0	75.0	61.6	53.7	48.4	45.8	44.3	43.7
110°	264.7	196.0	139.9	101.8	80.1	67.1	58.9	54.2	51.4	50.1	49.5



TEST NUMBER: P333207-940

CATALOG NUMBER: S125DIP-S850D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	250.1	189.9	139.9	105.3	84.8	72.4	64.5	59.7	56.9	55.9	55.3
115°	234.2	183.4	140.9	110.6	92.4	80.7	72.8	68.0	65.3	64.3	63.7
117.5°	224.6	180.2	142.9	116.6	100.0	89.0	81.4	76.0	73.2	72.1	71.2
120°	219.4	178.7	145.0	120.7	105.6	94.5	86.7	81.3	78.5	77.2	76.2
122.5°	214.8	177.5	146.7	125.2	110.8	99.9	91.9	86.1	83.3	82.2	81.6
125°	208.7	175.8	149.7	131.4	117.9	107.5	99.2	93.3	90.4	88.9	88.3
127.5°	203.0	175.1	153.0	137.1	124.6	114.6	106.4	100.0	96.4	94.4	93.5
130°	199.2	174.6	155.1	140.9	128.9	119.1	110.9	104.3	100.2	97.7	96.8
132.5°	196.2	174.6	157.3	144.2	133.0	123.1	114.9	108.1	103.5	100.5	99.2
135°	192.5	174.6	160.4	148.7	138.3	128.6	120.1	113.4	108.4	104.6	103.3
137.5°	189.3	175.0	163.3	152.1	142.2	133.3	124.6	118.1	113.0	109.5	108.5
140°	187.8	175.2	164.5	154.4	145.0	135.8	127.3	121.4	116.3	112.5	111.6
142.5°	186.5	175.5	165.2	155.7	146.7	138.1	130.1	124.4	119.3	115.7	115.1
145°	184.7	175.2	166.0	157.6	149.7	141.5	134.3	128.6	124.1	121.0	120.4
147.5°	182.7	174.4	166.4	158.7	151.6	144.4	138.0	133.1	129.0	126.3	125.9
150°	181.2	173.6	166.4	159.4	152.8	145.9	140.5	136.2	132.1	129.8	129.2
152.5°	179.4	172.6	166.1	160.0	154.1	147.7	142.9	138.7	135.1	133.1	132.8
155°	176.5	170.9	165.4	160.4	155.3	150.0	145.6	142.4	139.3	137.4	137.4
157.5°	173.7	168.9	164.6	160.7	156.4	151.9	148.5	145.7	143.0	141.5	141.6
160°	171.5	167.6	163.9	160.7	156.9	152.8	150.0	147.5	145.3	144.0	144.4
162.5°	169.4	166.1	163.1	160.5	157.5	153.8	151.5	149.5	147.6	146.3	146.6
165°	166.4	163.9	162.0	160.1	157.6	155.1	153.2	151.9	150.3	149.4	150.0
167.5°	163.5	161.7	160.2	159.3	157.6	155.5	154.3	153.4	152.6	151.9	152.3
170°	161.7	160.4	159.4	158.8	157.6	156.0	155.1	154.4	153.8	153.5	153.8
172.5°	159.9	158.9	158.5	158.4	157.3	156.0	155.5	155.2	154.5	154.3	154.8
175°	157.6	157.3	157.3	157.6	156.9	156.0	156.0	156.0	155.7	155.3	156.0
177.5°	156.6	156.3	156.3	156.9	156.6	156.0	156.0	156.3	156.0	156.0	156.6
180°	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3



TEST NUMBER: P333207-940

CATALOG NUMBER: S125DIP-S850D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	1096.8	1102.0	1105.4	1111.6	1116.8	1119.8	1122.4	1124.6	1127.2	1129.4	1135.7
5°	1103.8	1115.9	1126.1	1141.8	1156.2	1167.2	1179.3	1190.0	1198.8	1211.3	1221.0
7.5°	1100.8	1122.2	1144.6	1168.9	1193.8	1217.0	1238.3	1258.2	1276.3	1298.2	1317.3
10°	1097.9	1127.0	1155.7	1188.6	1222.4	1251.1	1277.9	1305.3	1325.2	1353.0	1376.5
12.5°	1095.6	1130.0	1164.6	1204.2	1241.3	1281.8	1317.6	1337.5	1367.8	1390.0	1418.1
15°	1086.3	1131.7	1179.3	1223.8	1276.6	1314.0	1345.6	1384.5	1412.6	1440.9	1471.5
17.5°	1069.5	1120.9	1174.2	1232.5	1283.2	1323.4	1364.0	1401.5	1435.2	1473.1	1511.1
20°	1061.8	1113.1	1174.2	1233.9	1283.5	1325.6	1367.3	1408.5	1445.6	1494.2	1538.2
22.5°	1045.4	1107.6	1163.9	1222.1	1273.1	1319.0	1366.2	1413.0	1462.2	1517.2	1572.3
25°	1016.4	1079.3	1139.1	1196.5	1247.9	1305.3	1355.8	1418.3	1481.2	1553.9	1622.5
27.5°	986.1	1046.4	1101.2	1156.6	1216.6	1281.6	1347.0	1418.0	1500.4	1592.1	1688.8
30°	961.7	1018.7	1071.9	1128.8	1191.3	1264.5	1336.3	1420.6	1515.9	1619.2	1734.0
32.5°	933.2	985.7	1037.4	1097.8	1165.8	1243.0	1326.7	1419.1	1533.7	1651.1	1769.2
35°	884.4	928.4	981.6	1046.0	1122.8	1211.3	1308.1	1417.3	1548.8	1683.6	1783.2
37.5°	826.5	867.5	923.5	994.1	1074.7	1169.6	1284.4	1414.1	1553.7	1661.2	1693.3
40°	787.6	825.5	884.0	957.1	1039.5	1140.0	1265.9	1402.9	1538.2	1606.7	1580.3
42.5°	746.1	786.0	842.8	915.3	1004.0	1113.3	1242.6	1379.7	1493.0	1518.9	1427.7
45°	680.6	721.8	777.8	851.0	946.5	1065.0	1199.7	1324.3	1389.6	1342.7	1201.6
47.5°	619.8	658.4	710.3	785.9	884.3	1006.9	1136.7	1236.0	1241.2	1129.6	978.7
50°	578.4	613.9	666.3	741.7	839.5	963.6	1080.7	1159.0	1123.7	997.4	852.4
52.5°	537.6	572.5	624.1	698.8	795.4	909.1	1018.1	1073.0	1006.7	877.0	753.1
55°	478.8	509.3	559.8	628.7	720.5	826.1	918.6	937.6	851.5	723.7	623.2
57.5°	421.3	449.9	495.8	559.4	643.1	736.6	809.0	805.0	714.0	604.3	524.6
60°	382.5	410.3	451.0	513.0	589.4	670.0	732.0	717.2	627.0	532.4	465.4
62.5°	347.7	372.5	411.0	465.2	534.9	609.7	660.6	638.7	550.3	467.6	414.6
65°	296.3	317.2	350.1	396.4	454.2	515.9	555.2	526.9	451.5	387.1	344.5
67.5°	247.4	264.0	291.6	328.6	377.9	427.4	451.4	422.9	362.6	315.6	284.0
70°	216.2	231.0	252.4	285.3	328.3	370.0	388.0	362.6	310.7	270.4	247.7
72.5°	185.1	197.3	216.1	245.6	280.1	316.3	332.1	307.7	265.1	231.1	209.9
75°	143.1	151.4	164.3	184.8	212.0	240.8	249.6	228.3	201.0	175.5	161.6
77.5°	102.5	109.5	119.3	132.2	151.5	169.8	177.5	165.1	144.0	127.9	116.5
80°	78.7	82.4	90.8	101.4	116.7	128.2	133.3	125.5	110.7	98.6	89.8
82.5°	56.1	59.8	64.8	73.7	83.4	91.2	96.7	91.4	80.7	71.2	66.1
85°	27.3	29.6	32.4	36.1	43.5	48.2	47.7	44.4	40.3	36.6	33.8
87.5°	9.7	10.3	11.5	13.5	14.7	16.2	17.1	16.4	15.1	14.0	13.0
90°	0.6	1.2	1.9	2.5	3.1	3.5	4.1	4.4	5.1	5.4	5.7
92.5°	4.6	7.3	11.2	16.7	25.9	43.1	71.9	103.3	101.6	82.2	55.8
95°	10.7	13.2	16.7	23.6	37.8	71.5	140.9	227.8	279.2	273.2	226.6
97.5°	17.7	19.4	22.9	29.2	39.3	61.6	112.4	203.5	298.2	345.7	337.4
100°	22.6	24.0	27.4	33.4	42.9	61.2	102.1	181.6	284.5	363.4	387.6
102.5°	27.7	28.7	32.5	38.0	47.2	63.4	97.8	164.9	260.6	352.8	404.5
105°	35.6	37.2	40.3	45.4	54.2	68.0	96.1	148.7	228.5	319.0	394.6
107.5°	44.3	45.8	48.4	53.7	61.6	75.0	99.0	142.0	206.3	284.4	359.0
110°	50.1	51.4	54.2	58.9	67.1	80.1	101.8	139.9	196.0	264.7	332.8





TEST NUMBER: P333207-940

CATALOG NUMBER: S125DIP-S850D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	55.9	56.9	59.7	64.5	72.4	84.8	105.3	139.9	189.9	250.1	312.1
115°	64.3	65.3	68.0	72.8	80.7	92.4	110.6	140.9	183.4	234.2	286.1
117.5°	72.1	73.2	76.0	81.4	89.0	100.0	116.6	142.9	180.2	224.6	269.4
120°	77.2	78.5	81.3	86.7	94.5	105.6	120.7	145.0	178.7	219.4	260.3
122.5°	82.2	83.3	86.1	91.9	99.9	110.8	125.2	146.7	177.5	214.8	253.5
125°	88.9	90.4	93.3	99.2	107.5	117.9	131.4	149.7	175.8	208.7	243.6
127.5°	94.4	96.4	100.0	106.4	114.6	124.6	137.1	153.0	175.1	203.0	233.5
130°	97.7	100.2	104.3	110.9	119.1	128.9	140.9	155.1	174.6	199.2	227.2
132.5°	100.5	103.5	108.1	114.9	123.1	133.0	144.2	157.3	174.6	196.2	220.9
135°	104.6	108.4	113.4	120.1	128.6	138.3	148.7	160.4	174.6	192.5	212.8
137.5°	109.5	113.0	118.1	124.6	133.3	142.2	152.1	163.3	175.0	189.3	205.8
140°	112.5	116.3	121.4	127.3	135.8	145.0	154.4	164.5	175.2	187.8	202.0
142.5°	115.7	119.3	124.4	130.1	138.1	146.7	155.7	165.2	175.5	186.5	198.8
145°	121.0	124.1	128.6	134.3	141.5	149.7	157.6	166.0	175.2	184.7	194.5
147.5°	126.3	129.0	133.1	138.0	144.4	151.6	158.7	166.4	174.4	182.7	190.4
150°	129.8	132.1	136.2	140.5	145.9	152.8	159.4	166.4	173.6	181.2	188.2
152.5°	133.1	135.1	138.7	142.9	147.7	154.1	160.0	166.1	172.6	179.4	185.7
155°	137.4	139.3	142.4	145.6	150.0	155.3	160.4	165.4	170.9	176.5	181.8
157.5°	141.5	143.0	145.7	148.5	151.9	156.4	160.7	164.6	168.9	173.7	178.1
160°	144.0	145.3	147.5	150.0	152.8	156.9	160.7	163.9	167.6	171.5	175.6
162.5°	146.3	147.6	149.5	151.5	153.8	157.5	160.5	163.1	166.1	169.4	172.7
165°	149.4	150.3	151.9	153.2	155.1	157.6	160.1	162.0	163.9	166.4	168.9
167.5°	151.9	152.6	153.4	154.3	155.5	157.6	159.3	160.2	161.7	163.5	165.2
170°	153.5	153.8	154.4	155.1	156.0	157.6	158.8	159.4	160.4	161.7	163.3
172.5°	154.3	154.5	155.2	155.5	156.0	157.3	158.4	158.5	158.9	159.9	161.0
175°	155.3	155.7	156.0	156.0	156.0	156.9	157.6	157.3	157.3	157.6	158.5
177.5°	156.0	156.0	156.3	156.0	156.0	156.6	156.9	156.3	156.3	156.6	156.9
180°	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3



TEST NUMBER: P333207-940

CATALOG NUMBER: S125DIP-S850D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	1140.9	1143.9	1150.1	1147.9	1150.9	1152.4	1153.9
5°	1233.1	1247.9	1254.4	1253.4	1263.1	1260.8	1258.5
7.5°	1337.1	1352.7	1361.4	1372.3	1378.5	1378.9	1384.5
10°	1396.1	1416.4	1424.8	1436.3	1443.7	1447.9	1447.4
12.5°	1441.2	1457.1	1475.9	1481.5	1491.5	1496.7	1494.9
15°	1495.6	1521.1	1540.5	1550.2	1562.7	1566.4	1571.6
17.5°	1544.1	1578.2	1601.0	1631.1	1642.5	1649.5	1645.4
20°	1580.7	1625.7	1648.4	1684.5	1704.4	1715.0	1711.4
22.5°	1624.1	1672.8	1714.7	1746.0	1776.3	1790.6	1793.6
25°	1698.4	1765.1	1826.7	1867.9	1905.3	1914.1	1933.6
27.5°	1781.4	1860.0	1925.8	1969.2	1995.3	2005.1	2011.2
30°	1833.6	1911.8	1961.4	1989.1	1997.5	1996.5	1995.6
32.5°	1859.1	1908.2	1917.6	1909.9	1890.8	1874.7	1857.9
35°	1822.9	1786.4	1731.7	1661.3	1609.4	1557.2	1552.0
37.5°	1639.5	1522.5	1431.6	1330.0	1271.4	1235.2	1210.1
40°	1466.9	1334.0	1223.8	1138.1	1078.3	1054.8	1031.6
42.5°	1279.4	1152.4	1054.9	983.3	938.3	912.1	893.9
45°	1039.5	927.5	851.0	799.2	763.6	743.2	731.6
47.5°	851.8	768.9	704.0	666.6	641.9	626.1	626.2
50°	751.0	671.8	628.7	599.1	577.8	565.3	567.7
52.5°	661.7	602.6	565.8	541.0	525.2	517.5	517.3
55°	553.3	510.7	486.6	468.6	457.9	449.2	451.0
57.5°	473.3	437.4	421.2	406.3	398.9	395.3	390.2
60°	423.7	395.9	382.0	370.0	362.6	359.8	354.6
62.5°	379.6	357.8	344.2	334.4	327.7	326.8	322.8
65°	319.1	302.4	290.3	285.7	278.7	276.9	276.9
67.5°	263.0	251.0	241.7	237.5	234.3	234.9	232.6
70°	227.8	218.1	212.0	207.4	205.1	205.5	203.8
72.5°	199.3	188.4	183.2	180.4	177.4	178.5	177.8
75°	151.0	145.3	142.6	139.8	137.9	137.1	136.2
77.5°	110.8	105.9	103.8	102.3	102.5	100.3	102.0
80°	85.7	81.5	80.1	77.8	77.3	77.3	76.9
82.5°	62.7	60.4	59.4	57.4	56.6	57.3	56.1
85°	32.4	30.6	30.1	30.1	29.2	28.3	30.6
87.5°	13.0	11.6	11.8	11.4	11.4	11.1	10.3
90°	6.0	6.3	7.0	7.0	7.0	7.2	7.2
92.5°	40.5	30.5	25.9	21.8	21.0	20.6	20.1
95°	178.7	139.9	113.4	91.0	81.6	79.1	74.1
97.5°	303.9	266.1	229.3	209.8	192.2	183.1	179.0
100°	372.2	339.7	306.9	285.2	262.5	250.8	245.8
102.5°	414.0	398.5	376.3	353.0	336.9	324.2	320.5
105°	437.7	451.6	448.2	438.0	427.7	421.3	417.6
107.5°	416.6	452.2	468.7	473.8	473.8	471.6	469.1
110°	392.7	437.1	463.9	478.0	484.0	486.2	486.2



TEST NUMBER: P333207-940

CATALOG NUMBER: S125DIP-S850D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	369.0	413.9	445.5	466.2	476.5	482.0	484.3
115°	335.0	378.2	412.5	437.1	452.2	461.0	465.1
117.5°	311.5	348.7	380.2	404.7	420.4	429.2	431.7
120°	298.1	332.8	360.5	383.9	399.0	407.5	410.0
122.5°	288.6	319.4	345.4	366.2	380.0	388.6	390.8
125°	275.7	303.2	325.8	343.5	356.4	363.4	366.5
127.5°	263.5	289.1	310.3	326.4	337.8	344.3	345.7
130°	254.9	279.6	300.1	315.8	326.2	332.5	334.4
132.5°	246.9	269.2	288.9	304.7	315.0	320.8	323.0
135°	234.4	254.7	272.6	286.5	296.9	302.6	304.4
137.5°	223.4	240.1	255.4	267.8	277.2	282.5	284.5
140°	216.8	231.3	244.5	256.2	264.4	269.1	270.7
142.5°	211.2	223.7	235.2	245.1	252.1	256.5	257.9
145°	204.2	214.0	222.5	230.1	235.4	238.9	240.1
147.5°	198.3	205.9	212.3	218.3	222.6	224.5	225.2
150°	195.1	201.1	206.7	211.4	215.3	216.5	216.8
152.5°	191.8	197.2	201.7	205.6	208.7	209.9	210.3
155°	186.9	191.3	194.7	197.9	200.1	201.1	201.3
157.5°	182.2	185.7	188.3	190.8	192.6	193.5	193.4
160°	178.7	181.8	184.0	186.3	187.8	188.4	188.2
162.5°	175.7	178.3	180.3	182.0	183.2	183.4	183.3
165°	171.1	173.0	174.6	175.8	176.5	176.5	176.5
167.5°	166.7	168.2	169.3	170.0	170.5	170.2	170.1
170°	164.2	165.1	165.8	166.4	166.7	166.7	166.4
172.5°	161.9	162.6	163.0	163.1	163.7	163.2	162.8
175°	158.5	159.2	159.2	159.2	159.4	158.8	158.5
177.5°	157.0	157.0	157.0	156.9	157.0	156.3	156.3
180°	156.3	156.3	156.3	156.3	156.3	156.3	156.3

(END OF REPORT)