

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331321-930

Luminaire Tested: **SA2XXDIP-C485D1080U930-4F0-1E-UDD-A**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331321-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C485D1080U930-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1080 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5261.0 lumens  
Efficiency: N/A  
Efficacy: 106.5 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 49.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331321-930

CATALOG NUMBER: SA2XXDIP-C485D1080U930-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331321-930

CATALOG NUMBER: SA2XXDIP-C485D1080U930-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33
1	94	90	87	83	85	82	78	76	65	63	61	50	49	48	36	36	35	29
2	86	79	73	68	77	72	67	63	58	54	51	45	42	40	32	31	30	24
3	79	70	63	57	71	63	57	53	51	47	43	40	37	34	29	27	26	21
4	72	62	54	49	65	56	50	45	45	41	37	35	32	30	26	24	23	18
5	66	55	47	42	60	50	44	39	41	36	32	32	29	26	24	22	20	16
6	61	50	42	36	55	45	38	34	37	32	28	29	25	23	22	19	18	14
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	20	17	16	13
8	52	41	33	28	47	37	31	26	30	26	22	24	21	18	18	16	14	12
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13	11
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	13	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	12791	12791	12791	12791
5°	14340	12875	11408	12875
10°	16433	12770	9875	12770
15°	18180	12535	8724	12535
20°	17904	12283	7952	12283
25°	16142	11948	7464	11948
30°	13340	11415	7107	11415
35°	9723	10857	6853	10857
40°	7765	10197	6713	10197
45°	6786	9435	6521	9435
50°	6380	8696	6393	8696
55°	5880	7947	6221	7947
60°	5389	7149	5958	7149
65°	4909	6434	5700	6434
70°	4456	5736	5320	5736
75°	3949	4959	4710	4959
80°	3394	4110	3794	4110
85°	3057	3057	2242	3057



TEST NUMBER: P331321-930

CATALOG NUMBER: SA2XXDIP-C485D1080U930-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	75.5	1.4
10°-20°	219.3	4.2
20°-30°	318.3	6.1
30°-40°	335.9	6.4
40°-50°	297.4	5.7
50°-60°	237.4	4.5
60°-70°	161.3	3.1
70°-80°	82.7	1.6
80°-90°	22.9	0.4
90°-100°	40.0	0.8
100°-110°	146.5	2.8
110°-120°	391.7	7.4
120°-130°	646.5	12.3
130°-140°	687.6	13.1
140°-150°	639.1	12.1
150°-160°	513.8	9.8
160°-170°	331.1	6.3
170°-180°	114.0	2.2
0°-30°	613.1	11.7
0°-40°	949.1	18.0
0°-60°	1483.9	28.2
0°-90°	1750.8	33.3
90°-120°	578.1	11.0
90°-150°	2551.3	48.5
90°-180°	3510.0	66.7
0°-180°	5261.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	792	792	792	792	792	
5°	885	794	704	794	885	88
15°	1088	750	522	750	1088	300
25°	906	671	419	671	906	410
35°	493	551	348	551	493	321
45°	297	413	286	413	297	234
55°	209	282	221	282	209	187
65°	128	168	149	168	128	128
75°	63	80	76	80	63	68
85°	16	16	12	16	16	19
90°	23	1	23	1	23	11
95°	37	56	37	56	37	35
105°	66	264	66	264	66	68
115°	71	498	71	498	71	178
125°	741	705	741	705	741	641
135°	900	872	900	872	900	694
145°	1027	1012	1027	1012	1027	642
155°	1115	1114	1115	1114	1115	514
165°	1171	1174	1171	1174	1171	331
175°	1193	1200	1193	1200	1193	114
180°	1198	1198	1198	1198	1198	



TEST NUMBER: P331321-930

CATALOG NUMBER: SA2XXDIP-C485D1080U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2
2.5°	828.8	829.1	829.5	825.7	825.2	825.2	821.7	818.8	815.4	810.7	811.2
5°	884.8	888.2	889.4	885.7	880.3	879.6	874.5	865.9	858.0	851.7	847.1
7.5°	951.7	953.0	950.1	945.3	941.2	933.8	924.2	914.8	901.6	889.4	880.4
10°	1002.3	1004.2	999.0	992.0	986.2	977.7	963.7	949.3	932.1	915.3	901.9
12.5°	1040.8	1045.4	1038.7	1037.8	1027.8	1016.2	999.5	992.2	967.8	944.5	930.1
15°	1087.6	1087.3	1087.9	1082.1	1074.8	1073.0	1055.3	1036.2	1001.8	988.1	964.3
17.5°	1074.1	1078.7	1080.8	1080.8	1080.6	1079.5	1073.7	1061.7	1044.4	1022.2	994.8
20°	1042.0	1048.0	1049.0	1056.0	1059.9	1065.1	1067.2	1063.9	1053.2	1034.6	1010.9
22.5°	992.2	993.9	996.8	1007.7	1016.3	1029.2	1036.0	1047.3	1043.2	1034.1	1014.3
25°	906.1	903.1	913.7	919.2	939.0	959.7	974.6	991.1	1005.7	1014.6	1008.8
27.5°	802.7	798.2	814.2	828.7	844.7	867.2	890.4	917.9	940.7	969.3	979.1
30°	715.5	718.3	733.5	749.0	773.4	805.0	831.2	861.4	894.0	925.9	948.1
32.5°	621.5	632.0	641.6	665.4	686.9	722.2	760.6	798.3	838.9	875.2	909.6
35°	493.3	505.4	518.9	536.2	566.3	601.4	638.8	689.7	745.1	794.7	835.5
37.5°	415.2	413.3	420.9	433.5	457.9	486.2	529.2	579.5	644.7	703.0	760.6
40°	368.4	367.2	372.7	384.3	402.8	423.5	461.3	505.4	566.1	637.2	705.8
42.5°	336.2	337.0	340.1	348.2	360.9	378.0	406.3	443.8	499.3	566.4	640.0
45°	297.2	299.3	302.6	306.6	313.9	327.9	343.7	370.6	414.4	470.4	542.9
47.5°	269.0	269.1	272.5	276.0	280.3	288.2	301.2	318.0	348.9	394.5	456.8
50°	254.0	251.8	254.2	257.0	261.5	267.0	275.6	291.4	312.1	348.9	401.0
52.5°	235.5	235.5	237.7	238.7	242.8	248.3	256.1	267.0	285.8	314.6	357.4
55°	208.9	210.4	211.7	213.4	217.1	221.0	227.1	234.5	249.1	270.7	302.3
57.5°	183.9	184.4	185.6	189.1	191.4	195.0	200.8	207.5	217.0	233.0	256.8
60°	166.9	166.9	169.3	170.8	173.8	177.5	182.1	188.5	197.0	210.1	229.3
62.5°	151.2	151.0	152.0	154.5	156.8	160.2	164.8	170.2	178.2	189.9	205.6
65°	128.5	127.9	129.7	130.3	132.7	136.1	139.7	145.5	152.0	160.5	174.5
67.5°	106.6	107.3	108.3	109.4	110.8	114.3	116.8	120.8	126.2	133.3	142.8
70°	94.4	94.4	94.4	95.3	97.1	99.0	101.4	104.8	109.9	116.0	124.5
72.5°	80.7	81.7	82.7	82.2	84.5	85.5	88.5	90.3	95.3	99.2	106.7
75°	63.3	63.3	63.3	64.8	65.8	66.7	68.5	70.4	72.8	77.6	81.6
77.5°	47.3	47.1	47.5	47.8	48.8	49.9	50.4	52.1	54.3	56.6	59.9
80°	36.5	37.2	37.4	38.1	38.1	38.6	39.0	41.1	42.6	44.2	46.3
82.5°	28.3	28.4	28.5	28.5	28.8	29.2	29.9	30.7	31.1	32.4	34.1
85°	16.5	16.1	16.1	16.7	16.5	16.5	17.0	17.7	17.7	17.9	18.9
87.5°	11.0	10.9	11.1	10.8	10.7	10.8	10.6	10.2	10.3	10.3	10.2
90°	23.4	23.0	22.7	22.3	21.9	21.2	20.2	19.2	18.3	17.4	15.8
92.5°	23.4	23.2	22.9	22.7	22.5	22.1	21.6	21.1	20.6	20.1	19.3
95°	37.3	37.4	37.7	37.8	38.1	37.7	36.7	35.7	34.7	33.8	32.4
97.5°	49.7	49.5	49.3	49.1	48.8	48.3	47.5	46.8	46.0	45.2	42.2
100°	58.0	57.7	57.3	56.9	56.5	55.6	54.1	52.5	51.0	49.4	46.1
102.5°	62.2	61.7	61.1	60.6	60.1	58.8	56.8	54.8	52.8	50.8	48.2
105°	65.9	65.1	64.3	63.6	62.8	61.3	59.2	57.1	55.0	52.8	50.4
107.5°	67.8	67.0	66.2	65.5	64.7	63.5	62.5	61.7	61.8	61.8	61.8
110°	68.5	67.7	66.9	66.1	65.4	64.6	63.9	63.2	62.4	61.6	60.3



TEST NUMBER: P331321-930

CATALOG NUMBER: SA2XXDIP-C485D1080U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	69.1	68.6	67.9	67.3	66.7	101.5	171.8	242.1	312.3	382.5	396.3
115°	71.1	85.0	98.8	112.7	126.5	178.1	267.3	356.4	445.6	534.8	529.9
117.5°	290.2	335.7	381.3	426.9	472.5	506.1	527.6	549.2	570.7	592.3	589.0
120°	528.7	554.6	580.7	606.7	632.7	644.6	642.2	639.9	637.6	635.3	631.9
122.5°	659.7	664.8	669.8	674.9	679.9	681.8	680.4	679.0	677.6	676.2	672.5
125°	741.0	740.5	739.9	739.3	738.7	737.8	736.4	735.1	733.7	732.4	728.7
127.5°	792.3	792.2	792.1	792.0	791.9	790.8	788.9	786.9	785.0	783.0	780.2
130°	824.3	824.4	824.6	824.8	825.0	824.0	821.9	819.8	817.7	815.5	813.4
132.5°	855.4	855.7	855.8	856.0	856.2	855.4	853.6	851.7	849.9	848.2	846.0
135°	900.5	900.9	901.2	901.6	902.0	901.2	899.4	897.4	895.5	893.6	891.9
137.5°	941.6	942.2	942.9	943.5	944.2	943.5	941.7	939.8	937.9	936.0	934.1
140°	967.3	968.2	969.1	970.1	971.1	970.7	969.0	967.3	965.5	963.8	961.6
142.5°	992.2	993.2	994.1	995.1	996.1	995.7	994.2	992.5	991.0	989.4	987.0
145°	1027.0	1028.0	1029.0	1030.0	1030.9	1030.7	1029.3	1028.0	1026.6	1025.3	1022.1
147.5°	1057.7	1058.5	1059.3	1060.1	1060.9	1060.9	1059.9	1058.8	1057.9	1056.9	1053.6
150°	1076.4	1077.4	1078.4	1079.3	1080.3	1080.2	1079.0	1077.9	1076.8	1075.5	1072.5
152.5°	1092.4	1093.6	1094.9	1096.2	1097.5	1097.6	1096.4	1095.2	1094.1	1092.9	1090.0
155°	1114.6	1116.1	1117.7	1119.2	1120.7	1121.0	1119.8	1118.6	1117.4	1116.3	1114.0
157.5°	1134.8	1136.4	1137.8	1139.4	1140.8	1140.9	1139.6	1138.3	1137.0	1135.7	1134.1
160°	1146.6	1148.0	1149.3	1150.7	1152.0	1152.1	1151.0	1149.8	1148.7	1147.5	1146.4
162.5°	1156.3	1158.0	1159.7	1161.3	1162.9	1163.2	1161.8	1160.5	1159.2	1157.9	1156.9
165°	1170.9	1172.2	1173.6	1174.9	1176.3	1176.3	1174.9	1173.6	1172.2	1170.9	1170.4
167.5°	1180.1	1181.9	1183.6	1185.3	1187.0	1187.2	1185.9	1184.5	1183.2	1181.9	1181.3
170°	1185.6	1187.4	1189.1	1190.8	1192.5	1192.8	1191.4	1190.1	1188.7	1187.4	1187.0
172.5°	1189.8	1191.6	1193.3	1195.0	1196.8	1196.9	1195.6	1194.3	1192.9	1191.6	1191.2
175°	1193.4	1195.4	1197.3	1199.2	1201.2	1201.4	1200.1	1198.7	1197.4	1196.0	1195.6
177.5°	1195.7	1197.1	1198.5	1199.9	1201.3	1201.4	1200.3	1199.2	1198.2	1197.1	1196.9
180°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8



TEST NUMBER: P331321-930

CATALOG NUMBER: SA2XXDIP-C485D1080U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2
2.5°	812.9	811.0	809.8	805.4	801.5	797.6	796.4	796.9	791.5	786.4	784.2
5°	844.7	838.5	832.7	824.5	814.8	804.1	798.7	794.4	783.7	772.2	765.5
7.5°	873.0	864.3	853.1	837.7	823.5	806.7	796.1	786.7	771.0	754.7	744.8
10°	890.3	878.4	864.1	845.2	827.9	807.5	793.2	778.9	760.6	741.1	729.0
12.5°	905.1	889.2	875.1	850.8	830.3	804.8	787.8	767.7	748.4	725.3	713.3
15°	940.5	911.0	884.2	856.8	831.5	795.9	777.1	749.9	724.6	696.0	682.3
17.5°	967.8	934.7	892.5	857.7	828.2	788.7	761.0	728.6	698.6	665.9	647.3
20°	983.5	945.4	900.0	858.7	823.3	778.3	748.1	714.9	679.9	643.0	623.0
22.5°	992.7	952.8	907.8	855.0	813.6	769.7	731.8	695.5	659.9	620.2	599.1
25°	995.6	959.1	911.6	851.9	801.4	751.8	706.0	670.7	627.9	590.7	559.9
27.5°	981.1	955.0	909.3	846.2	787.3	729.3	678.4	638.4	593.0	552.8	521.8
30°	963.4	948.1	903.7	840.3	776.1	713.7	657.7	612.3	567.3	526.4	494.8
32.5°	935.9	932.5	893.5	832.1	764.2	694.0	636.0	590.1	540.2	500.1	469.9
35°	881.7	896.4	871.7	813.6	741.7	665.9	603.2	550.8	499.0	460.6	432.4
37.5°	809.3	845.6	839.2	786.4	711.3	635.4	566.1	511.4	462.0	423.3	395.5
40°	759.4	805.7	812.4	765.7	690.0	611.7	538.3	483.8	435.7	400.4	372.3
42.5°	705.8	759.9	778.3	740.9	666.6	586.9	513.5	457.1	409.4	375.0	350.3
45°	616.0	687.5	720.7	699.4	627.5	545.9	470.4	413.2	370.0	337.7	318.5
47.5°	532.0	610.2	654.8	647.3	584.1	503.3	428.7	373.7	331.7	305.9	288.7
50°	472.5	552.9	606.8	609.3	552.9	472.9	397.9	346.2	307.5	283.5	269.5
52.5°	420.9	497.7	556.4	569.3	518.1	441.2	370.4	318.9	284.9	262.8	250.2
55°	353.5	418.3	483.6	507.3	466.2	393.1	327.6	282.3	250.3	235.1	224.1
57.5°	293.9	348.0	408.1	434.4	409.0	346.5	285.1	245.7	219.8	206.4	198.0
60°	262.4	305.1	358.7	390.0	368.1	312.4	258.8	221.4	200.1	188.2	180.3
62.5°	233.3	271.0	316.3	345.0	333.0	280.5	232.5	199.4	181.1	169.9	164.2
65°	192.4	222.3	257.3	283.8	275.9	235.9	196.7	168.4	153.8	145.0	140.4
67.5°	158.4	180.0	204.3	227.5	221.1	192.8	161.3	139.3	128.3	120.7	118.1
70°	137.1	153.4	175.0	193.6	188.5	165.3	140.4	121.5	112.0	105.7	102.9
72.5°	116.6	130.0	146.6	161.8	158.2	139.0	118.2	104.0	96.7	90.8	88.5
75°	88.0	98.3	108.4	118.5	117.6	102.6	90.4	79.5	73.7	69.1	68.2
77.5°	65.0	70.8	77.6	83.6	81.9	73.4	63.8	57.6	53.3	50.2	49.7
80°	49.7	53.0	57.9	62.1	60.0	56.3	48.8	44.2	41.1	38.1	36.9
82.5°	36.0	39.4	42.2	44.6	43.0	39.5	34.8	31.7	29.9	27.8	27.3
85°	18.9	20.7	21.9	22.5	21.9	19.8	17.7	16.5	14.9	14.0	13.7
87.5°	10.2	9.9	9.5	9.7	8.5	8.1	6.7	5.5	5.7	5.9	5.8
90°	14.3	12.7	11.2	9.4	7.3	5.1	3.0	0.9	3.0	5.1	7.3
92.5°	18.6	17.8	17.0	16.7	17.0	17.1	17.3	17.5	17.3	17.1	17.0
95°	31.1	29.8	28.4	30.9	37.3	43.6	50.0	56.3	50.0	43.6	37.3
97.5°	39.0	35.9	32.8	40.2	58.0	76.0	93.9	111.8	93.9	76.0	58.0
100°	42.9	39.5	36.3	47.9	74.3	100.6	127.0	153.4	127.0	100.6	74.3
102.5°	105.6	133.0	160.4	176.8	182.4	188.0	193.6	199.2	193.6	188.0	182.4
105°	158.0	210.6	263.2	286.6	280.8	275.0	269.3	263.5	269.3	275.0	280.8
107.5°	200.2	263.2	326.3	355.5	350.7	346.1	341.4	336.8	341.4	346.1	350.7
110°	263.0	318.6	374.3	400.1	396.1	392.1	388.0	383.9	388.0	392.1	396.1





TEST NUMBER: P331321-930

CATALOG NUMBER: SA2XXDIP-C485D1080U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	410.1	423.8	437.6	442.6	439.0	435.5	431.9	428.4	431.9	435.5	439.0
115°	525.1	520.3	515.5	511.4	508.2	504.9	501.7	498.4	501.7	504.9	508.2
117.5°	585.7	582.4	579.0	575.6	571.9	568.3	564.6	560.9	564.6	568.3	571.9
120°	628.4	624.9	621.4	618.2	615.4	612.5	609.6	606.7	609.6	612.5	615.4
122.5°	668.6	664.9	661.1	657.7	654.7	651.6	648.6	645.6	648.6	651.6	654.7
125°	725.0	721.4	717.7	714.6	712.2	709.6	707.1	704.7	707.1	709.6	712.2
127.5°	777.5	774.8	772.0	769.3	766.5	763.8	761.0	758.2	761.0	763.8	766.5
130°	811.3	809.2	807.1	804.5	801.4	798.3	795.2	792.1	795.2	798.3	801.4
132.5°	843.9	841.8	839.7	837.3	834.7	832.1	829.5	826.8	829.5	832.1	834.7
135°	890.1	888.4	886.6	884.2	881.2	878.1	875.0	871.9	875.0	878.1	881.2
137.5°	932.1	930.2	928.1	926.1	924.0	921.8	919.7	917.5	919.7	921.8	924.0
140°	959.5	957.4	955.3	953.5	951.9	950.4	948.8	947.3	948.8	950.4	951.9
142.5°	984.6	982.1	979.7	977.8	976.4	975.0	973.6	972.2	973.6	975.0	976.4
145°	1018.7	1015.5	1012.2	1010.6	1010.9	1011.1	1011.2	1011.5	1011.2	1011.1	1010.9
147.5°	1050.4	1047.2	1043.9	1042.7	1043.4	1044.2	1044.9	1045.6	1044.9	1044.2	1043.4
150°	1069.4	1066.3	1063.2	1062.4	1063.7	1065.1	1066.4	1067.8	1066.4	1065.1	1063.7
152.5°	1087.0	1084.1	1081.2	1080.5	1082.0	1083.5	1085.0	1086.5	1085.0	1083.5	1082.0
155°	1111.7	1109.4	1107.1	1106.8	1108.5	1110.3	1112.0	1113.7	1112.0	1110.3	1108.5
157.5°	1132.5	1130.9	1129.3	1129.2	1130.7	1132.1	1133.6	1135.1	1133.6	1132.1	1130.7
160°	1145.2	1144.0	1142.9	1142.9	1144.0	1145.2	1146.4	1147.5	1146.4	1145.2	1144.0
162.5°	1155.9	1154.9	1153.9	1154.0	1155.1	1156.3	1157.5	1158.6	1157.5	1156.3	1155.1
165°	1169.8	1169.1	1168.6	1168.9	1170.0	1171.2	1172.3	1173.5	1172.3	1171.2	1170.0
167.5°	1180.7	1180.2	1179.7	1180.0	1181.1	1182.3	1183.5	1184.6	1183.5	1182.3	1181.1
170°	1186.6	1186.3	1185.9	1186.3	1187.4	1188.5	1189.7	1190.8	1189.7	1188.5	1187.4
172.5°	1190.7	1190.4	1190.0	1190.4	1191.6	1192.7	1193.8	1195.0	1193.8	1192.7	1191.6
175°	1195.3	1194.9	1194.5	1195.0	1196.4	1197.7	1199.1	1200.4	1199.1	1197.7	1196.4
177.5°	1196.8	1196.6	1196.5	1196.9	1198.0	1199.1	1200.2	1201.3	1200.2	1199.1	1198.0
180°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8



TEST NUMBER: P331321-930

CATALOG NUMBER: SA2XXDIP-C485D1080U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2
2.5°	781.8	780.3	775.2	772.5	768.2	764.0	761.3	762.5	763.5	763.0	762.3
5°	759.4	753.6	744.8	737.1	731.6	721.6	717.4	715.3	713.4	711.3	709.1
7.5°	732.7	723.6	710.9	700.1	689.8	677.4	670.3	665.9	661.5	656.7	652.5
10°	713.7	700.9	687.5	672.3	660.1	648.8	638.8	632.1	626.0	620.2	616.0
12.5°	693.7	679.0	662.4	641.6	628.2	612.0	610.6	598.8	589.2	585.6	580.7
15°	661.9	641.2	620.2	595.6	584.9	570.3	561.2	552.0	543.8	538.0	536.5
17.5°	625.8	599.0	578.1	560.4	543.0	528.0	519.6	512.3	505.5	497.7	496.8
20°	598.3	575.2	552.4	536.8	518.9	503.6	493.3	485.9	480.1	475.6	471.7
22.5°	572.3	546.9	526.0	509.0	491.3	479.0	470.8	463.8	459.0	454.0	450.2
25°	530.4	510.6	487.8	468.6	454.0	446.1	439.4	433.3	430.2	426.9	422.7
27.5°	493.8	471.8	450.5	435.6	422.7	415.7	411.0	406.8	404.0	402.0	399.6
30°	468.0	445.7	429.0	414.4	403.7	396.7	393.7	391.3	387.9	386.7	385.5
32.5°	443.1	423.1	408.8	396.2	386.0	381.4	378.6	376.4	373.8	372.6	370.1
35°	408.0	391.3	377.2	370.2	362.0	358.1	356.0	352.9	350.5	349.3	348.9
37.5°	375.0	360.4	351.1	342.2	338.7	336.2	333.4	331.3	330.5	330.4	330.0
40°	353.5	341.6	333.4	326.1	324.6	320.9	318.5	316.7	316.7	317.0	316.7
42.5°	334.0	323.3	316.1	309.8	308.0	305.8	303.4	303.3	303.8	304.8	303.8
45°	304.5	296.9	291.7	288.6	285.3	283.2	282.8	283.8	284.1	284.4	285.3
47.5°	277.3	272.2	267.6	264.2	262.8	262.4	262.0	263.6	265.1	265.6	267.0
50°	261.2	255.4	251.5	249.4	248.2	247.5	248.2	250.0	251.2	252.7	253.6
52.5°	243.2	239.1	236.4	234.7	234.2	234.6	234.7	236.8	238.8	239.3	239.8
55°	218.3	215.2	214.7	211.9	213.1	212.8	214.3	215.6	217.4	219.2	219.6
57.5°	193.5	191.0	189.4	189.6	190.0	191.4	192.6	194.8	196.7	198.6	198.9
60°	176.9	175.7	174.8	174.8	175.4	177.2	178.7	180.8	182.1	183.3	184.2
62.5°	161.8	160.6	159.6	160.1	161.8	162.8	164.6	165.8	167.0	168.2	168.6
65°	137.9	137.3	138.3	138.8	139.2	140.6	142.8	143.7	145.0	145.5	147.7
67.5°	115.9	116.1	115.9	116.8	118.5	119.0	120.9	123.1	123.4	124.5	125.9
70°	101.1	101.7	102.3	102.9	104.4	105.0	106.6	107.5	108.7	109.6	110.6
72.5°	87.5	87.6	88.2	88.1	89.4	90.7	92.0	92.9	94.1	95.2	96.1
75°	67.3	67.3	67.9	68.2	69.7	71.3	70.9	71.6	72.8	74.0	74.6
77.5°	49.2	48.5	49.2	49.4	49.9	51.2	51.4	52.3	53.7	53.3	54.0
80°	37.4	36.5	37.4	37.7	37.7	39.3	39.3	39.9	40.8	39.9	40.8
82.5°	26.7	26.3	27.0	27.1	27.6	27.6	28.0	28.2	29.1	28.7	29.1
85°	13.4	13.1	13.4	13.1	13.4	13.7	13.7	13.4	13.4	14.0	13.1
87.5°	6.0	6.1	6.2	6.5	6.6	6.6	6.6	6.8	6.9	6.7	6.8
90°	9.4	11.2	12.7	14.3	15.8	17.4	18.3	19.2	20.2	21.2	21.9
92.5°	16.7	17.0	17.8	18.6	19.3	20.1	20.6	21.1	21.6	22.1	22.5
95°	30.9	28.4	29.8	31.1	32.4	33.8	34.7	35.7	36.7	37.7	38.1
97.5°	40.2	32.8	35.9	39.0	42.2	45.2	46.0	46.8	47.5	48.3	48.8
100°	47.9	36.3	39.5	42.9	46.1	49.4	51.0	52.5	54.1	55.6	56.5
102.5°	176.8	160.4	133.0	105.6	78.2	50.8	52.8	54.8	56.8	58.8	60.1
105°	286.6	263.2	210.6	158.0	105.4	52.8	55.0	57.1	59.2	61.3	62.8
107.5°	355.5	326.3	263.2	200.2	137.1	74.0	71.8	69.7	67.5	65.4	64.7
110°	400.1	374.3	318.6	263.0	207.3	151.6	132.4	113.2	93.9	74.6	65.4



TEST NUMBER: P331321-930

CATALOG NUMBER: SA2XXDIP-C485D1080U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	442.6	437.6	423.8	410.1	396.3	382.5	312.3	242.1	171.8	101.5	66.7
115°	511.4	515.5	520.3	525.1	529.9	534.8	445.6	356.4	267.3	178.1	126.5
117.5°	575.6	579.0	582.4	585.7	589.0	592.3	570.7	549.2	527.6	506.1	472.5
120°	618.2	621.4	624.9	628.4	631.9	635.3	637.6	639.9	642.2	644.6	632.7
122.5°	657.7	661.1	664.9	668.6	672.5	676.2	677.6	679.0	680.4	681.8	679.9
125°	714.6	717.7	721.4	725.0	728.7	732.4	733.7	735.1	736.4	737.8	738.7
127.5°	769.3	772.0	774.8	777.5	780.2	783.0	785.0	786.9	788.9	790.8	791.9
130°	804.5	807.1	809.2	811.3	813.4	815.5	817.7	819.8	821.9	824.0	825.0
132.5°	837.3	839.7	841.8	843.9	846.0	848.2	849.9	851.7	853.6	855.4	856.2
135°	884.2	886.6	888.4	890.1	891.9	893.6	895.5	897.4	899.4	901.2	902.0
137.5°	926.1	928.1	930.2	932.1	934.1	936.0	937.9	939.8	941.7	943.5	944.2
140°	953.5	955.3	957.4	959.5	961.6	963.8	965.5	967.3	969.0	970.7	971.1
142.5°	977.8	979.7	982.1	984.6	987.0	989.4	991.0	992.5	994.2	995.7	996.1
145°	1010.6	1012.2	1015.5	1018.7	1022.1	1025.3	1026.6	1028.0	1029.3	1030.7	1030.9
147.5°	1042.7	1043.9	1047.2	1050.4	1053.6	1056.9	1057.9	1058.8	1059.9	1060.9	1060.9
150°	1062.4	1063.2	1066.3	1069.4	1072.5	1075.5	1076.8	1077.9	1079.0	1080.2	1080.3
152.5°	1080.5	1081.2	1084.1	1087.0	1090.0	1092.9	1094.1	1095.2	1096.4	1097.6	1097.5
155°	1106.8	1107.1	1109.4	1111.7	1114.0	1116.3	1117.4	1118.6	1119.8	1121.0	1120.7
157.5°	1129.2	1129.3	1130.9	1132.5	1134.1	1135.7	1137.0	1138.3	1139.6	1140.9	1140.8
160°	1142.9	1142.9	1144.0	1145.2	1146.4	1147.5	1148.7	1149.8	1151.0	1152.1	1152.0
162.5°	1154.0	1153.9	1154.9	1155.9	1156.9	1157.9	1159.2	1160.5	1161.8	1163.2	1162.9
165°	1168.9	1168.6	1169.1	1169.8	1170.4	1170.9	1172.2	1173.6	1174.9	1176.3	1176.3
167.5°	1180.0	1179.7	1180.2	1180.7	1181.3	1181.9	1183.2	1184.5	1185.9	1187.2	1187.0
170°	1186.3	1185.9	1186.3	1186.6	1187.0	1187.4	1188.7	1190.1	1191.4	1192.8	1192.5
172.5°	1190.4	1190.0	1190.4	1190.7	1191.2	1191.6	1192.9	1194.3	1195.6	1196.9	1196.8
175°	1195.0	1194.5	1194.9	1195.3	1195.6	1196.0	1197.4	1198.7	1200.1	1201.4	1201.2
177.5°	1196.9	1196.5	1196.6	1196.8	1196.9	1197.1	1198.2	1199.2	1200.3	1201.4	1201.3
180°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8



TEST NUMBER: P331321-930

CATALOG NUMBER: SA2XXDIP-C485D1080U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2
2.5°	759.9	759.4	759.4	757.2	759.4	759.4	759.9	762.3	763.0	763.5	762.5
5°	704.9	703.9	702.5	703.9	702.5	703.9	704.9	709.1	711.3	713.4	715.3
7.5°	650.5	646.9	646.3	642.7	646.3	646.9	650.5	652.5	656.7	661.5	665.9
10°	610.8	608.4	608.1	602.3	608.1	608.4	610.8	616.0	620.2	626.0	632.1
12.5°	580.6	574.7	575.9	572.6	575.9	574.7	580.6	580.7	585.6	589.2	598.8
15°	528.2	528.2	527.1	521.9	527.1	528.2	528.2	536.5	538.0	543.8	552.0
17.5°	490.7	490.1	487.1	488.6	487.1	490.1	490.7	496.8	497.7	505.5	512.3
20°	468.3	466.4	462.8	462.8	462.8	466.4	468.3	471.7	475.6	480.1	485.9
22.5°	447.1	446.9	443.1	444.3	443.1	446.9	447.1	450.2	454.0	459.0	463.8
25°	422.3	419.9	418.1	419.0	418.1	419.9	422.3	422.7	426.9	430.2	433.3
27.5°	398.8	397.5	397.4	394.8	397.4	397.5	398.8	399.6	402.0	404.0	406.8
30°	385.1	382.1	382.7	381.2	382.7	382.1	385.1	385.5	386.7	387.9	391.3
32.5°	369.6	368.5	367.9	366.6	367.9	368.5	369.6	370.1	372.6	373.8	376.4
35°	348.3	348.6	347.1	347.7	347.1	348.6	348.3	348.9	349.3	350.5	352.9
37.5°	329.8	330.8	330.0	330.2	330.0	330.8	329.8	330.0	330.4	330.5	331.3
40°	317.6	317.6	317.6	318.5	317.6	317.6	317.6	316.7	317.0	316.7	316.7
42.5°	305.9	305.4	304.9	304.8	304.9	305.4	305.9	303.8	304.8	303.8	303.3
45°	285.9	286.8	287.1	285.6	287.1	286.8	285.9	285.3	284.4	284.1	283.8
47.5°	267.8	267.9	267.8	269.1	267.8	267.9	267.8	267.0	265.6	265.1	263.6
50°	255.2	254.5	255.2	254.5	255.2	254.5	255.2	253.6	252.7	251.2	250.0
52.5°	241.7	241.9	241.5	241.4	241.5	241.9	241.7	239.8	239.3	238.8	236.8
55°	220.8	221.4	221.0	221.0	221.0	221.4	220.8	219.6	219.2	217.4	215.6
57.5°	199.0	199.6	200.0	198.6	200.0	199.6	199.0	198.9	198.6	196.7	194.8
60°	183.9	185.4	185.2	184.5	185.2	185.4	183.9	184.2	183.3	182.1	180.8
62.5°	170.0	170.6	170.5	170.4	170.5	170.6	170.0	168.6	168.2	167.0	165.8
65°	148.5	149.2	148.3	149.2	148.3	149.2	148.5	147.7	145.5	145.0	143.7
67.5°	125.5	125.7	126.4	126.8	126.4	125.7	125.5	125.9	124.5	123.4	123.1
70°	111.1	110.8	111.8	112.7	111.8	110.8	111.1	110.6	109.6	108.7	107.5
72.5°	96.0	96.7	96.4	97.1	96.4	96.7	96.0	96.1	95.2	94.1	92.9
75°	74.0	74.9	74.6	75.5	74.6	74.9	74.0	74.6	74.0	72.8	71.6
77.5°	53.5	53.6	53.5	54.0	53.5	53.6	53.5	54.0	53.3	53.7	52.3
80°	40.8	40.2	39.5	40.8	39.5	40.2	40.8	40.8	39.9	40.8	39.9
82.5°	28.4	28.8	28.1	28.1	28.1	28.8	28.4	29.1	28.7	29.1	28.2
85°	13.1	12.8	12.1	12.1	12.1	12.8	13.1	13.1	14.0	13.4	13.4
87.5°	6.8	6.7	6.8	6.6	6.8	6.7	6.8	6.8	6.7	6.9	6.8
90°	22.3	22.7	23.0	23.4	23.0	22.7	22.3	21.9	21.2	20.2	19.2
92.5°	22.7	22.9	23.2	23.4	23.2	22.9	22.7	22.5	22.1	21.6	21.1
95°	37.8	37.7	37.4	37.3	37.4	37.7	37.8	38.1	37.7	36.7	35.7
97.5°	49.1	49.3	49.5	49.7	49.5	49.3	49.1	48.8	48.3	47.5	46.8
100°	56.9	57.3	57.7	58.0	57.7	57.3	56.9	56.5	55.6	54.1	52.5
102.5°	60.6	61.1	61.7	62.2	61.7	61.1	60.6	60.1	58.8	56.8	54.8
105°	63.6	64.3	65.1	65.9	65.1	64.3	63.6	62.8	61.3	59.2	57.1
107.5°	65.5	66.2	67.0	67.8	67.0	66.2	65.5	64.7	65.4	67.5	69.7
110°	66.1	66.9	67.7	68.5	67.7	66.9	66.1	65.4	74.6	93.9	113.2



TEST NUMBER: P331321-930

CATALOG NUMBER: SA2XXDIP-C485D1080U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	67.3	67.9	68.6	69.1	68.6	67.9	67.3	66.7	101.5	171.8	242.1
115°	112.7	98.8	85.0	71.1	85.0	98.8	112.7	126.5	178.1	267.3	356.4
117.5°	426.9	381.3	335.7	290.2	335.7	381.3	426.9	472.5	506.1	527.6	549.2
120°	606.7	580.7	554.6	528.7	554.6	580.7	606.7	632.7	644.6	642.2	639.9
122.5°	674.9	669.8	664.8	659.7	664.8	669.8	674.9	679.9	681.8	680.4	679.0
125°	739.3	739.9	740.5	741.0	740.5	739.9	739.3	738.7	737.8	736.4	735.1
127.5°	792.0	792.1	792.2	792.3	792.2	792.1	792.0	791.9	790.8	788.9	786.9
130°	824.8	824.6	824.4	824.3	824.4	824.6	824.8	825.0	824.0	821.9	819.8
132.5°	856.0	855.8	855.7	855.4	855.7	855.8	856.0	856.2	855.4	853.6	851.7
135°	901.6	901.2	900.9	900.5	900.9	901.2	901.6	902.0	901.2	899.4	897.4
137.5°	943.5	942.9	942.2	941.6	942.2	942.9	943.5	944.2	943.5	941.7	939.8
140°	970.1	969.1	968.2	967.3	968.2	969.1	970.1	971.1	970.7	969.0	967.3
142.5°	995.1	994.1	993.2	992.2	993.2	994.1	995.1	996.1	995.7	994.2	992.5
145°	1030.0	1029.0	1028.0	1027.0	1028.0	1029.0	1030.0	1030.9	1030.7	1029.3	1028.0
147.5°	1060.1	1059.3	1058.5	1057.7	1058.5	1059.3	1060.1	1060.9	1060.9	1059.9	1058.8
150°	1079.3	1078.4	1077.4	1076.4	1077.4	1078.4	1079.3	1080.3	1080.2	1079.0	1077.9
152.5°	1096.2	1094.9	1093.6	1092.4	1093.6	1094.9	1096.2	1097.5	1097.6	1096.4	1095.2
155°	1119.2	1117.7	1116.1	1114.6	1116.1	1117.7	1119.2	1120.7	1121.0	1119.8	1118.6
157.5°	1139.4	1137.8	1136.4	1134.8	1136.4	1137.8	1139.4	1140.8	1140.9	1139.6	1138.3
160°	1150.7	1149.3	1148.0	1146.6	1148.0	1149.3	1150.7	1152.0	1152.1	1151.0	1149.8
162.5°	1161.3	1159.7	1158.0	1156.3	1158.0	1159.7	1161.3	1162.9	1163.2	1161.8	1160.5
165°	1174.9	1173.6	1172.2	1170.9	1172.2	1173.6	1174.9	1176.3	1176.3	1174.9	1173.6
167.5°	1185.3	1183.6	1181.9	1180.1	1181.9	1183.6	1185.3	1187.0	1187.2	1185.9	1184.5
170°	1190.8	1189.1	1187.4	1185.6	1187.4	1189.1	1190.8	1192.5	1192.8	1191.4	1190.1
172.5°	1195.0	1193.3	1191.6	1189.8	1191.6	1193.3	1195.0	1196.8	1196.9	1195.6	1194.3
175°	1199.2	1197.3	1195.4	1193.4	1195.4	1197.3	1199.2	1201.2	1201.4	1200.1	1198.7
177.5°	1199.9	1198.5	1197.1	1195.7	1197.1	1198.5	1199.9	1201.3	1201.4	1200.3	1199.2
180°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8



TEST NUMBER: P331321-930

CATALOG NUMBER: SA2XXDIP-C485D1080U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2
2.5°	761.3	764.0	768.2	772.5	775.2	780.3	781.8	784.2	786.4	791.5	796.9
5°	717.4	721.6	731.6	737.1	744.8	753.6	759.4	765.5	772.2	783.7	794.4
7.5°	670.3	677.4	689.8	700.1	710.9	723.6	732.7	744.8	754.7	771.0	786.7
10°	638.8	648.8	660.1	672.3	687.5	700.9	713.7	729.0	741.1	760.6	778.9
12.5°	610.6	612.0	628.2	641.6	662.4	679.0	693.7	713.3	725.3	748.4	767.7
15°	561.2	570.3	584.9	595.6	620.2	641.2	661.9	682.3	696.0	724.6	749.9
17.5°	519.6	528.0	543.0	560.4	578.1	599.0	625.8	647.3	665.9	698.6	728.6
20°	493.3	503.6	518.9	536.8	552.4	575.2	598.3	623.0	643.0	679.9	714.9
22.5°	470.8	479.0	491.3	509.0	526.0	546.9	572.3	599.1	620.2	659.9	695.5
25°	439.4	446.1	454.0	468.6	487.8	510.6	530.4	559.9	590.7	627.9	670.7
27.5°	411.0	415.7	422.7	435.6	450.5	471.8	493.8	521.8	552.8	593.0	638.4
30°	393.7	396.7	403.7	414.4	429.0	445.7	468.0	494.8	526.4	567.3	612.3
32.5°	378.6	381.4	386.0	396.2	408.8	423.1	443.1	469.9	500.1	540.2	590.1
35°	356.0	358.1	362.0	370.2	377.2	391.3	408.0	432.4	460.6	499.0	550.8
37.5°	333.4	336.2	338.7	342.2	351.1	360.4	375.0	395.5	423.3	462.0	511.4
40°	318.5	320.9	324.6	326.1	333.4	341.6	353.5	372.3	400.4	435.7	483.8
42.5°	303.4	305.8	308.0	309.8	316.1	323.3	334.0	350.3	375.0	409.4	457.1
45°	282.8	283.2	285.3	288.6	291.7	296.9	304.5	318.5	337.7	370.0	413.2
47.5°	262.0	262.4	262.8	264.2	267.6	272.2	277.3	288.7	305.9	331.7	373.7
50°	248.2	247.5	248.2	249.4	251.5	255.4	261.2	269.5	283.5	307.5	346.2
52.5°	234.7	234.6	234.2	234.7	236.4	239.1	243.2	250.2	262.8	284.9	318.9
55°	214.3	212.8	213.1	211.9	214.7	215.2	218.3	224.1	235.1	250.3	282.3
57.5°	192.6	191.4	190.0	189.6	189.4	191.0	193.5	198.0	206.4	219.8	245.7
60°	178.7	177.2	175.4	174.8	174.8	175.7	176.9	180.3	188.2	200.1	221.4
62.5°	164.6	162.8	161.8	160.1	159.6	160.6	161.8	164.2	169.9	181.1	199.4
65°	142.8	140.6	139.2	138.8	138.3	137.3	137.9	140.4	145.0	153.8	168.4
67.5°	120.9	119.0	118.5	116.8	115.9	116.1	115.9	118.1	120.7	128.3	139.3
70°	106.6	105.0	104.4	102.9	102.3	101.7	101.1	102.9	105.7	112.0	121.5
72.5°	92.0	90.7	89.4	88.1	88.2	87.6	87.5	88.5	90.8	96.7	104.0
75°	70.9	71.3	69.7	68.2	67.9	67.3	67.3	68.2	69.1	73.7	79.5
77.5°	51.4	51.2	49.9	49.4	49.2	48.5	49.2	49.7	50.2	53.3	57.6
80°	39.3	39.3	37.7	37.7	37.4	36.5	37.4	36.9	38.1	41.1	44.2
82.5°	28.0	27.6	27.6	27.1	27.0	26.3	26.7	27.3	27.8	29.9	31.7
85°	13.7	13.7	13.4	13.1	13.4	13.1	13.4	13.7	14.0	14.9	16.5
87.5°	6.6	6.6	6.6	6.5	6.2	6.1	6.0	5.8	5.9	5.7	5.5
90°	18.3	17.4	15.8	14.3	12.7	11.2	9.4	7.3	5.1	3.0	0.9
92.5°	20.6	20.1	19.3	18.6	17.8	17.0	16.7	17.0	17.1	17.3	17.5
95°	34.7	33.8	32.4	31.1	29.8	28.4	30.9	37.3	43.6	50.0	56.3
97.5°	46.0	45.2	42.2	39.0	35.9	32.8	40.2	58.0	76.0	93.9	111.8
100°	51.0	49.4	46.1	42.9	39.5	36.3	47.9	74.3	100.6	127.0	153.4
102.5°	52.8	50.8	78.2	105.6	133.0	160.4	176.8	182.4	188.0	193.6	199.2
105°	55.0	52.8	105.4	158.0	210.6	263.2	286.6	280.8	275.0	269.3	263.5
107.5°	71.8	74.0	137.1	200.2	263.2	326.3	355.5	350.7	346.1	341.4	336.8
110°	132.4	151.6	207.3	263.0	318.6	374.3	400.1	396.1	392.1	388.0	383.9



TEST NUMBER: P331321-930

CATALOG NUMBER: SA2XXDIP-C485D1080U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	312.3	382.5	396.3	410.1	423.8	437.6	442.6	439.0	435.5	431.9	428.4
115°	445.6	534.8	529.9	525.1	520.3	515.5	511.4	508.2	504.9	501.7	498.4
117.5°	570.7	592.3	589.0	585.7	582.4	579.0	575.6	571.9	568.3	564.6	560.9
120°	637.6	635.3	631.9	628.4	624.9	621.4	618.2	615.4	612.5	609.6	606.7
122.5°	677.6	676.2	672.5	668.6	664.9	661.1	657.7	654.7	651.6	648.6	645.6
125°	733.7	732.4	728.7	725.0	721.4	717.7	714.6	712.2	709.6	707.1	704.7
127.5°	785.0	783.0	780.2	777.5	774.8	772.0	769.3	766.5	763.8	761.0	758.2
130°	817.7	815.5	813.4	811.3	809.2	807.1	804.5	801.4	798.3	795.2	792.1
132.5°	849.9	848.2	846.0	843.9	841.8	839.7	837.3	834.7	832.1	829.5	826.8
135°	895.5	893.6	891.9	890.1	888.4	886.6	884.2	881.2	878.1	875.0	871.9
137.5°	937.9	936.0	934.1	932.1	930.2	928.1	926.1	924.0	921.8	919.7	917.5
140°	965.5	963.8	961.6	959.5	957.4	955.3	953.5	951.9	950.4	948.8	947.3
142.5°	991.0	989.4	987.0	984.6	982.1	979.7	977.8	976.4	975.0	973.6	972.2
145°	1026.6	1025.3	1022.1	1018.7	1015.5	1012.2	1010.6	1010.9	1011.1	1011.2	1011.5
147.5°	1057.9	1056.9	1053.6	1050.4	1047.2	1043.9	1042.7	1043.4	1044.2	1044.9	1045.6
150°	1076.8	1075.5	1072.5	1069.4	1066.3	1063.2	1062.4	1063.7	1065.1	1066.4	1067.8
152.5°	1094.1	1092.9	1090.0	1087.0	1084.1	1081.2	1080.5	1082.0	1083.5	1085.0	1086.5
155°	1117.4	1116.3	1114.0	1111.7	1109.4	1107.1	1106.8	1108.5	1110.3	1112.0	1113.7
157.5°	1137.0	1135.7	1134.1	1132.5	1130.9	1129.3	1129.2	1130.7	1132.1	1133.6	1135.1
160°	1148.7	1147.5	1146.4	1145.2	1144.0	1142.9	1142.9	1144.0	1145.2	1146.4	1147.5
162.5°	1159.2	1157.9	1156.9	1155.9	1154.9	1153.9	1154.0	1155.1	1156.3	1157.5	1158.6
165°	1172.2	1170.9	1170.4	1169.8	1169.1	1168.6	1168.9	1170.0	1171.2	1172.3	1173.5
167.5°	1183.2	1181.9	1181.3	1180.7	1180.2	1179.7	1180.0	1181.1	1182.3	1183.5	1184.6
170°	1188.7	1187.4	1187.0	1186.6	1186.3	1185.9	1186.3	1187.4	1188.5	1189.7	1190.8
172.5°	1192.9	1191.6	1191.2	1190.7	1190.4	1190.0	1190.4	1191.6	1192.7	1193.8	1195.0
175°	1197.4	1196.0	1195.6	1195.3	1194.9	1194.5	1195.0	1196.4	1197.7	1199.1	1200.4
177.5°	1198.2	1197.1	1196.9	1196.8	1196.6	1196.5	1196.9	1198.0	1199.1	1200.2	1201.3
180°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8



TEST NUMBER: P331321-930

CATALOG NUMBER: SA2XXDIP-C485D1080U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2
2.5°	796.4	797.6	801.5	805.4	809.8	811.0	812.9	811.2	810.7	815.4	818.8
5°	798.7	804.1	814.8	824.5	832.7	838.5	844.7	847.1	851.7	858.0	865.9
7.5°	796.1	806.7	823.5	837.7	853.1	864.3	873.0	880.4	889.4	901.6	914.8
10°	793.2	807.5	827.9	845.2	864.1	878.4	890.3	901.9	915.3	932.1	949.3
12.5°	787.8	804.8	830.3	850.8	875.1	889.2	905.1	930.1	944.5	967.8	992.2
15°	777.1	795.9	831.5	856.8	884.2	911.0	940.5	964.3	988.1	1001.8	1036.2
17.5°	761.0	788.7	828.2	857.7	892.5	934.7	967.8	994.8	1022.2	1044.4	1061.7
20°	748.1	778.3	823.3	858.7	900.0	945.4	983.5	1010.9	1034.6	1053.2	1063.9
22.5°	731.8	769.7	813.6	855.0	907.8	952.8	992.7	1014.3	1034.1	1043.2	1047.3
25°	706.0	751.8	801.4	851.9	911.6	959.1	995.6	1008.8	1014.6	1005.7	991.1
27.5°	678.4	729.3	787.3	846.2	909.3	955.0	981.1	979.1	969.3	940.7	917.9
30°	657.7	713.7	776.1	840.3	903.7	948.1	963.4	948.1	925.9	894.0	861.4
32.5°	636.0	694.0	764.2	832.1	893.5	932.5	935.9	909.6	875.2	838.9	798.3
35°	603.2	665.9	741.7	813.6	871.7	896.4	881.7	835.5	794.7	745.1	689.7
37.5°	566.1	635.4	711.3	786.4	839.2	845.6	809.3	760.6	703.0	644.7	579.5
40°	538.3	611.7	690.0	765.7	812.4	805.7	759.4	705.8	637.2	566.1	505.4
42.5°	513.5	586.9	666.6	740.9	778.3	759.9	705.8	640.0	566.4	499.3	443.8
45°	470.4	545.9	627.5	699.4	720.7	687.5	616.0	542.9	470.4	414.4	370.6
47.5°	428.7	503.3	584.1	647.3	654.8	610.2	532.0	456.8	394.5	348.9	318.0
50°	397.9	472.9	552.9	609.3	606.8	552.9	472.5	401.0	348.9	312.1	291.4
52.5°	370.4	441.2	518.1	569.3	556.4	497.7	420.9	357.4	314.6	285.8	267.0
55°	327.6	393.1	466.2	507.3	483.6	418.3	353.5	302.3	270.7	249.1	234.5
57.5°	285.1	346.5	409.0	434.4	408.1	348.0	293.9	256.8	233.0	217.0	207.5
60°	258.8	312.4	368.1	390.0	358.7	305.1	262.4	229.3	210.1	197.0	188.5
62.5°	232.5	280.5	333.0	345.0	316.3	271.0	233.3	205.6	189.9	178.2	170.2
65°	196.7	235.9	275.9	283.8	257.3	222.3	192.4	174.5	160.5	152.0	145.5
67.5°	161.3	192.8	221.1	227.5	204.3	180.0	158.4	142.8	133.3	126.2	120.8
70°	140.4	165.3	188.5	193.6	175.0	153.4	137.1	124.5	116.0	109.9	104.8
72.5°	118.2	139.0	158.2	161.8	146.6	130.0	116.6	106.7	99.2	95.3	90.3
75°	90.4	102.6	117.6	118.5	108.4	98.3	88.0	81.6	77.6	72.8	70.4
77.5°	63.8	73.4	81.9	83.6	77.6	70.8	65.0	59.9	56.6	54.3	52.1
80°	48.8	56.3	60.0	62.1	57.9	53.0	49.7	46.3	44.2	42.6	41.1
82.5°	34.8	39.5	43.0	44.6	42.2	39.4	36.0	34.1	32.4	31.1	30.7
85°	17.7	19.8	21.9	22.5	21.9	20.7	18.9	18.9	17.9	17.7	17.7
87.5°	6.7	8.1	8.5	9.7	9.5	9.9	10.2	10.2	10.3	10.3	10.2
90°	3.0	5.1	7.3	9.4	11.2	12.7	14.3	15.8	17.4	18.3	19.2
92.5°	17.3	17.1	17.0	16.7	17.0	17.8	18.6	19.3	20.1	20.6	21.1
95°	50.0	43.6	37.3	30.9	28.4	29.8	31.1	32.4	33.8	34.7	35.7
97.5°	93.9	76.0	58.0	40.2	32.8	35.9	39.0	42.2	45.2	46.0	46.8
100°	127.0	100.6	74.3	47.9	36.3	39.5	42.9	46.1	49.4	51.0	52.5
102.5°	193.6	188.0	182.4	176.8	160.4	133.0	105.6	78.2	50.8	52.8	54.8
105°	269.3	275.0	280.8	286.6	263.2	210.6	158.0	105.4	52.8	55.0	57.1
107.5°	341.4	346.1	350.7	355.5	326.3	263.2	200.2	137.1	74.0	71.8	69.7
110°	388.0	392.1	396.1	400.1	374.3	318.6	263.0	207.3	151.6	132.4	113.2





TEST NUMBER: P331321-930

CATALOG NUMBER: SA2XXDIP-C485D1080U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	431.9	435.5	439.0	442.6	437.6	423.8	410.1	396.3	382.5	312.3	242.1
115°	501.7	504.9	508.2	511.4	515.5	520.3	525.1	529.9	534.8	445.6	356.4
117.5°	564.6	568.3	571.9	575.6	579.0	582.4	585.7	589.0	592.3	570.7	549.2
120°	609.6	612.5	615.4	618.2	621.4	624.9	628.4	631.9	635.3	637.6	639.9
122.5°	648.6	651.6	654.7	657.7	661.1	664.9	668.6	672.5	676.2	677.6	679.0
125°	707.1	709.6	712.2	714.6	717.7	721.4	725.0	728.7	732.4	733.7	735.1
127.5°	761.0	763.8	766.5	769.3	772.0	774.8	777.5	780.2	783.0	785.0	786.9
130°	795.2	798.3	801.4	804.5	807.1	809.2	811.3	813.4	815.5	817.7	819.8
132.5°	829.5	832.1	834.7	837.3	839.7	841.8	843.9	846.0	848.2	849.9	851.7
135°	875.0	878.1	881.2	884.2	886.6	888.4	890.1	891.9	893.6	895.5	897.4
137.5°	919.7	921.8	924.0	926.1	928.1	930.2	932.1	934.1	936.0	937.9	939.8
140°	948.8	950.4	951.9	953.5	955.3	957.4	959.5	961.6	963.8	965.5	967.3
142.5°	973.6	975.0	976.4	977.8	979.7	982.1	984.6	987.0	989.4	991.0	992.5
145°	1011.2	1011.1	1010.9	1010.6	1012.2	1015.5	1018.7	1022.1	1025.3	1026.6	1028.0
147.5°	1044.9	1044.2	1043.4	1042.7	1043.9	1047.2	1050.4	1053.6	1056.9	1057.9	1058.8
150°	1066.4	1065.1	1063.7	1062.4	1063.2	1066.3	1069.4	1072.5	1075.5	1076.8	1077.9
152.5°	1085.0	1083.5	1082.0	1080.5	1081.2	1084.1	1087.0	1090.0	1092.9	1094.1	1095.2
155°	1112.0	1110.3	1108.5	1106.8	1107.1	1109.4	1111.7	1114.0	1116.3	1117.4	1118.6
157.5°	1133.6	1132.1	1130.7	1129.2	1129.3	1130.9	1132.5	1134.1	1135.7	1137.0	1138.3
160°	1146.4	1145.2	1144.0	1142.9	1142.9	1144.0	1145.2	1146.4	1147.5	1148.7	1149.8
162.5°	1157.5	1156.3	1155.1	1154.0	1153.9	1154.9	1155.9	1156.9	1157.9	1159.2	1160.5
165°	1172.3	1171.2	1170.0	1168.9	1168.6	1169.1	1169.8	1170.4	1170.9	1172.2	1173.6
167.5°	1183.5	1182.3	1181.1	1180.0	1179.7	1180.2	1180.7	1181.3	1181.9	1183.2	1184.5
170°	1189.7	1188.5	1187.4	1186.3	1185.9	1186.3	1186.6	1187.0	1187.4	1188.7	1190.1
172.5°	1193.8	1192.7	1191.6	1190.4	1190.0	1190.4	1190.7	1191.2	1191.6	1192.9	1194.3
175°	1199.1	1197.7	1196.4	1195.0	1194.5	1194.9	1195.3	1195.6	1196.0	1197.4	1198.7
177.5°	1200.2	1199.1	1198.0	1196.9	1196.5	1196.6	1196.8	1196.9	1197.1	1198.2	1199.2
180°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8



TEST NUMBER: P331321-930

CATALOG NUMBER: SA2XXDIP-C485D1080U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	792.2	792.2	792.2	792.2	792.2	792.2	792.2
2.5°	821.7	825.2	825.2	825.7	829.5	829.1	828.8
5°	874.5	879.6	880.3	885.7	889.4	888.2	884.8
7.5°	924.2	933.8	941.2	945.3	950.1	953.0	951.7
10°	963.7	977.7	986.2	992.0	999.0	1004.2	1002.3
12.5°	999.5	1016.2	1027.8	1037.8	1038.7	1045.4	1040.8
15°	1055.3	1073.0	1074.8	1082.1	1087.9	1087.3	1087.6
17.5°	1073.7	1079.5	1080.6	1080.8	1080.8	1078.7	1074.1
20°	1067.2	1065.1	1059.9	1056.0	1049.0	1048.0	1042.0
22.5°	1036.0	1029.2	1016.3	1007.7	996.8	993.9	992.2
25°	974.6	959.7	939.0	919.2	913.7	903.1	906.1
27.5°	890.4	867.2	844.7	828.7	814.2	798.2	802.7
30°	831.2	805.0	773.4	749.0	733.5	718.3	715.5
32.5°	760.6	722.2	686.9	665.4	641.6	632.0	621.5
35°	638.8	601.4	566.3	536.2	518.9	505.4	493.3
37.5°	529.2	486.2	457.9	433.5	420.9	413.3	415.2
40°	461.3	423.5	402.8	384.3	372.7	367.2	368.4
42.5°	406.3	378.0	360.9	348.2	340.1	337.0	336.2
45°	343.7	327.9	313.9	306.6	302.6	299.3	297.2
47.5°	301.2	288.2	280.3	276.0	272.5	269.1	269.0
50°	275.6	267.0	261.5	257.0	254.2	251.8	254.0
52.5°	256.1	248.3	242.8	238.7	237.7	235.5	235.5
55°	227.1	221.0	217.1	213.4	211.7	210.4	208.9
57.5°	200.8	195.0	191.4	189.1	185.6	184.4	183.9
60°	182.1	177.5	173.8	170.8	169.3	166.9	166.9
62.5°	164.8	160.2	156.8	154.5	152.0	151.0	151.2
65°	139.7	136.1	132.7	130.3	129.7	127.9	128.5
67.5°	116.8	114.3	110.8	109.4	108.3	107.3	106.6
70°	101.4	99.0	97.1	95.3	94.4	94.4	94.4
72.5°	88.5	85.5	84.5	82.2	82.7	81.7	80.7
75°	68.5	66.7	65.8	64.8	63.3	63.3	63.3
77.5°	50.4	49.9	48.8	47.8	47.5	47.1	47.3
80°	39.0	38.6	38.1	38.1	37.4	37.2	36.5
82.5°	29.9	29.2	28.8	28.5	28.5	28.4	28.3
85°	17.0	16.5	16.5	16.7	16.1	16.1	16.5
87.5°	10.6	10.8	10.7	10.8	11.1	10.9	11.0
90°	20.2	21.2	21.9	22.3	22.7	23.0	23.4
92.5°	21.6	22.1	22.5	22.7	22.9	23.2	23.4
95°	36.7	37.7	38.1	37.8	37.7	37.4	37.3
97.5°	47.5	48.3	48.8	49.1	49.3	49.5	49.7
100°	54.1	55.6	56.5	56.9	57.3	57.7	58.0
102.5°	56.8	58.8	60.1	60.6	61.1	61.7	62.2
105°	59.2	61.3	62.8	63.6	64.3	65.1	65.9
107.5°	67.5	65.4	64.7	65.5	66.2	67.0	67.8
110°	93.9	74.6	65.4	66.1	66.9	67.7	68.5



TEST NUMBER: P331321-930

CATALOG NUMBER: SA2XXDIP-C485D1080U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	171.8	101.5	66.7	67.3	67.9	68.6	69.1
115°	267.3	178.1	126.5	112.7	98.8	85.0	71.1
117.5°	527.6	506.1	472.5	426.9	381.3	335.7	290.2
120°	642.2	644.6	632.7	606.7	580.7	554.6	528.7
122.5°	680.4	681.8	679.9	674.9	669.8	664.8	659.7
125°	736.4	737.8	738.7	739.3	739.9	740.5	741.0
127.5°	788.9	790.8	791.9	792.0	792.1	792.2	792.3
130°	821.9	824.0	825.0	824.8	824.6	824.4	824.3
132.5°	853.6	855.4	856.2	856.0	855.8	855.7	855.4
135°	899.4	901.2	902.0	901.6	901.2	900.9	900.5
137.5°	941.7	943.5	944.2	943.5	942.9	942.2	941.6
140°	969.0	970.7	971.1	970.1	969.1	968.2	967.3
142.5°	994.2	995.7	996.1	995.1	994.1	993.2	992.2
145°	1029.3	1030.7	1030.9	1030.0	1029.0	1028.0	1027.0
147.5°	1059.9	1060.9	1060.9	1060.1	1059.3	1058.5	1057.7
150°	1079.0	1080.2	1080.3	1079.3	1078.4	1077.4	1076.4
152.5°	1096.4	1097.6	1097.5	1096.2	1094.9	1093.6	1092.4
155°	1119.8	1121.0	1120.7	1119.2	1117.7	1116.1	1114.6
157.5°	1139.6	1140.9	1140.8	1139.4	1137.8	1136.4	1134.8
160°	1151.0	1152.1	1152.0	1150.7	1149.3	1148.0	1146.6
162.5°	1161.8	1163.2	1162.9	1161.3	1159.7	1158.0	1156.3
165°	1174.9	1176.3	1176.3	1174.9	1173.6	1172.2	1170.9
167.5°	1185.9	1187.2	1187.0	1185.3	1183.6	1181.9	1180.1
170°	1191.4	1192.8	1192.5	1190.8	1189.1	1187.4	1185.6
172.5°	1195.6	1196.9	1196.8	1195.0	1193.3	1191.6	1189.8
175°	1200.1	1201.4	1201.2	1199.2	1197.3	1195.4	1193.4
177.5°	1200.3	1201.4	1201.3	1199.9	1198.5	1197.1	1195.7
180°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8

(END OF REPORT)