

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333216-940

Luminaire Tested: **S125DIP-S850D590U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333216-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S850D590U940-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4971.7 lumens  
Efficiency: N/A  
Efficacy: 123.4 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 40.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333216-940

CATALOG NUMBER: S125DIP-S850D590U940-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333216-940

CATALOG NUMBER: S125DIP-S850D590U940-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	96	93	89	94	91	87	84	79	77	75	69	67	66	60	58	57	53
2	92	85	78	73	86	79	74	69	70	66	62	61	58	55	53	51	49	45
3	84	75	67	61	78	70	64	58	62	57	53	54	50	47	47	44	42	38
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	39	36	33
5	71	59	51	45	66	56	48	43	49	44	39	44	39	35	38	34	32	29
6	65	53	45	39	61	50	43	37	45	39	34	39	35	31	35	31	28	25
7	60	48	40	34	57	45	38	33	41	35	30	36	31	27	32	28	25	22
8	56	44	36	30	53	41	34	29	37	31	27	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20	18
10	49	37	29	24	46	35	28	24	31	26	22	28	23	20	25	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	7045	7045	7045	7045
5°	8159	7069	6190	7069
10°	9492	7033	5423	7033
15°	10508	6981	5003	6981
20°	11762	6899	4665	6899
25°	13779	6807	4501	6807
30°	14882	6716	4357	6716
35°	12236	6545	4264	6545
40°	8697	6308	4161	6308
45°	6682	5989	4103	5989
50°	5704	5591	4093	5591
55°	5078	5203	4130	5203
60°	4580	4779	4234	4779
65°	4232	4351	4345	4351
70°	3848	3909	4407	3909
75°	3399	3441	4367	3441
80°	2860	2804	3998	2804
85°	2267	2023	3223	2023



TEST NUMBER: P333216-940

CATALOG NUMBER: S125DIP-S850D590U940-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	105.0	2.1
10°-20°	312.7	6.3
20°-30°	507.7	10.2
30°-40°	619.3	12.5
40°-50°	563.4	11.3
50°-60°	448.8	9.0
60°-70°	312.6	6.3
70°-80°	166.7	3.4
80°-90°	43.5	0.9
90°-100°	182.9	3.7
100°-110°	393.1	7.9
110°-120°	369.0	7.4
120°-130°	299.0	6.0
130°-140°	240.0	4.8
140°-150°	181.1	3.6
150°-160°	127.5	2.6
160°-170°	75.1	1.5
170°-180°	24.4	0.5
0°-30°	925.4	18.6
0°-40°	1544.8	31.1
0°-60°	2556.9	51.4
0°-90°	3079.7	61.9
90°-120°	945.0	19.0
90°-150°	1665.0	33.5
90°-180°	1892.0	38.1
0°-180°	4971.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1091	1091	1091	1091	1091	
5°	1258	1090	955	1090	1258	127
15°	1572	1044	748	1044	1572	450
25°	1934	955	632	955	1934	883
35°	1552	830	541	830	1552	950
45°	732	656	449	656	732	586
55°	451	462	367	462	451	406
65°	277	285	284	285	277	275
75°	136	138	175	138	136	147
85°	31	27	44	27	31	36
90°	12	0	12	0	12	9
95°	120	17	120	17	120	169
105°	674	58	674	58	674	670
115°	751	103	751	103	751	734
125°	592	142	592	142	592	535
135°	491	167	491	167	491	381
145°	388	194	388	194	388	246
155°	325	222	325	222	325	151
165°	285	242	285	242	285	81
175°	256	252	256	252	256	25
180°	252	252	252	252	252	



TEST NUMBER: P333216-940

CATALOG NUMBER: S125DIP-S850D590U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	1153.9	1152.4	1150.9	1147.9	1150.1	1143.9	1140.9	1135.7	1129.4	1127.2	1124.6
5°	1258.5	1260.8	1263.1	1253.4	1254.4	1247.9	1233.1	1221.0	1211.3	1198.8	1190.0
7.5°	1384.5	1378.9	1378.5	1372.3	1361.4	1352.7	1337.1	1317.3	1298.2	1276.3	1258.2
10°	1447.4	1447.9	1443.7	1436.3	1424.8	1416.4	1396.1	1376.5	1353.0	1325.2	1305.3
12.5°	1494.9	1496.7	1491.5	1481.5	1475.9	1457.1	1441.2	1418.1	1390.0	1367.8	1337.5
15°	1571.6	1566.4	1562.7	1550.2	1540.5	1521.1	1495.6	1471.5	1440.9	1412.6	1384.5
17.5°	1645.4	1649.5	1642.5	1631.1	1601.0	1578.2	1544.1	1511.1	1473.1	1435.2	1401.5
20°	1711.4	1715.0	1704.4	1684.5	1648.4	1625.7	1580.7	1538.2	1494.2	1445.6	1408.5
22.5°	1793.6	1790.6	1776.3	1746.0	1714.7	1672.8	1624.1	1572.3	1517.2	1462.2	1413.0
25°	1933.6	1914.1	1905.3	1867.9	1826.7	1765.1	1698.4	1622.5	1553.9	1481.2	1418.3
27.5°	2011.2	2005.1	1995.3	1969.2	1925.8	1860.0	1781.4	1688.8	1592.1	1500.4	1418.0
30°	1995.6	1996.5	1997.5	1989.1	1961.4	1911.8	1833.6	1734.0	1619.2	1515.9	1420.6
32.5°	1857.9	1874.7	1890.8	1909.9	1917.6	1908.2	1859.1	1769.2	1651.1	1533.7	1419.1
35°	1552.0	1557.2	1609.4	1661.3	1731.7	1786.4	1822.9	1783.2	1683.6	1548.8	1417.3
37.5°	1210.1	1235.2	1271.4	1330.0	1431.6	1522.5	1639.5	1693.3	1661.2	1553.7	1414.1
40°	1031.6	1054.8	1078.3	1138.1	1223.8	1334.0	1466.9	1580.3	1606.7	1538.2	1402.9
42.5°	893.9	912.1	938.3	983.3	1054.9	1152.4	1279.4	1427.7	1518.9	1493.0	1379.7
45°	731.6	743.2	763.6	799.2	851.0	927.5	1039.5	1201.6	1342.7	1389.6	1324.3
47.5°	626.2	626.1	641.9	666.6	704.0	768.9	851.8	978.7	1129.6	1241.2	1236.0
50°	567.7	565.3	577.8	599.1	628.7	671.8	751.0	852.4	997.4	1123.7	1159.0
52.5°	517.3	517.5	525.2	541.0	565.8	602.6	661.7	753.1	877.0	1006.7	1073.0
55°	451.0	449.2	457.9	468.6	486.6	510.7	553.3	623.2	723.7	851.5	937.6
57.5°	390.2	395.3	398.9	406.3	421.2	437.4	473.3	524.6	604.3	714.0	805.0
60°	354.6	359.8	362.6	370.0	382.0	395.9	423.7	465.4	532.4	627.0	717.2
62.5°	322.8	326.8	327.7	334.4	344.2	357.8	379.6	414.6	467.6	550.3	638.7
65°	276.9	276.9	278.7	285.7	290.3	302.4	319.1	344.5	387.1	451.5	526.9
67.5°	232.6	234.9	234.3	237.5	241.7	251.0	263.0	284.0	315.6	362.6	422.9
70°	203.8	205.5	205.1	207.4	212.0	218.1	227.8	247.7	270.4	310.7	362.6
72.5°	177.8	178.5	177.4	180.4	183.2	188.4	199.3	209.9	231.1	265.1	307.7
75°	136.2	137.1	137.9	139.8	142.6	145.3	151.0	161.6	175.5	201.0	228.3
77.5°	102.0	100.3	102.5	102.3	103.8	105.9	110.8	116.5	127.9	144.0	165.1
80°	76.9	77.3	77.3	77.8	80.1	81.5	85.7	89.8	98.6	110.7	125.5
82.5°	56.1	57.3	56.6	57.4	59.4	60.4	62.7	66.1	71.2	80.7	91.4
85°	30.6	28.3	29.2	30.1	30.1	30.6	32.4	33.8	36.6	40.3	44.4
87.5°	11.2	11.9	12.2	12.2	12.6	12.4	13.8	13.6	14.7	15.7	16.9
90°	11.7	11.7	11.1	11.1	11.1	10.2	9.6	9.2	8.6	8.1	7.1
92.5°	32.5	33.3	34.0	35.2	41.7	49.2	65.5	90.2	132.8	164.0	166.7
95°	119.6	127.7	131.7	147.0	183.2	225.9	288.4	365.7	441.0	450.7	367.7
97.5°	288.9	295.4	310.1	338.7	370.1	429.5	490.4	544.7	558.0	481.3	328.4
100°	396.7	404.9	423.7	460.3	495.4	548.3	600.7	625.6	586.5	459.3	293.0
102.5°	517.2	523.3	543.8	569.8	607.3	643.1	668.2	652.9	569.4	420.6	266.1
105°	674.0	680.1	690.3	707.0	723.3	728.9	706.5	636.9	514.8	368.8	240.0
107.5°	757.2	761.3	764.6	764.7	756.4	730.0	672.4	579.4	459.1	333.1	229.1
110°	784.9	784.9	781.3	771.6	748.8	705.5	633.8	537.2	427.3	316.4	225.9



TEST NUMBER: P333216-940

CATALOG NUMBER: S125DIP-S850D590U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	781.6	777.9	769.1	752.5	719.1	668.1	595.6	503.8	403.7	306.7	225.9
115°	750.8	744.1	730.0	705.5	665.8	610.4	540.7	461.8	377.9	296.0	227.4
117.5°	696.8	692.7	678.6	653.4	613.7	562.8	502.7	434.8	362.6	290.9	230.7
120°	661.7	657.7	644.0	619.6	581.9	537.2	481.2	420.2	354.0	288.4	234.0
122.5°	630.8	627.1	613.4	591.0	557.5	515.6	465.7	409.2	346.7	286.4	236.8
125°	591.6	586.5	575.3	554.5	525.9	489.4	445.1	393.2	336.7	283.8	241.7
127.5°	558.0	555.7	545.2	526.7	501.0	466.6	425.3	376.9	327.6	282.6	247.0
130°	539.7	536.6	526.5	509.7	484.2	451.2	411.5	366.8	321.5	281.8	250.3
132.5°	521.4	517.9	508.5	491.8	466.4	434.5	398.5	356.6	316.6	281.8	254.0
135°	491.3	488.3	479.1	462.4	440.0	411.0	378.4	343.3	310.8	281.8	258.9
137.5°	459.3	455.9	447.5	432.2	412.2	387.6	360.5	332.2	305.6	282.4	263.5
140°	436.9	434.4	426.8	413.6	394.8	373.4	350.0	326.0	303.2	282.9	265.6
142.5°	416.2	414.0	406.8	395.7	379.7	361.1	341.0	320.7	301.1	283.2	266.7
145°	387.6	385.6	380.0	371.3	359.1	345.4	329.6	313.9	298.1	282.9	268.0
147.5°	363.4	362.5	359.2	352.3	342.6	332.3	320.1	307.4	294.9	281.5	268.6
150°	350.0	349.5	347.4	341.3	333.7	324.5	314.9	303.6	292.5	280.3	268.6
152.5°	339.4	338.9	336.8	332.0	325.6	318.4	309.6	299.6	289.6	278.7	268.1
155°	325.0	324.5	323.0	319.4	314.3	308.7	301.7	293.5	284.8	275.7	267.1
157.5°	312.2	312.3	310.9	307.9	304.0	299.6	294.1	287.4	280.4	272.6	265.7
160°	303.6	304.2	303.2	300.6	297.0	293.5	288.4	283.3	276.7	270.6	264.5
162.5°	296.0	296.0	295.9	293.7	291.0	287.8	283.6	278.8	273.5	268.1	263.3
165°	284.8	284.8	284.8	283.8	281.8	279.3	276.2	272.6	268.6	264.5	261.4
167.5°	274.6	274.7	275.2	274.3	273.2	271.4	269.1	266.7	263.8	260.9	258.6
170°	268.6	269.1	269.1	268.6	267.5	266.5	265.0	263.5	260.9	258.9	257.3
172.5°	262.9	263.4	264.2	263.3	263.1	262.4	261.4	259.8	258.1	256.5	255.7
175°	255.8	256.4	257.3	256.9	256.9	256.9	255.8	255.8	254.3	253.8	253.8
177.5°	252.3	252.3	253.5	253.1	253.5	253.5	253.5	253.1	252.7	252.3	252.3
180°	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3



TEST NUMBER: P333216-940

CATALOG NUMBER: S125DIP-S850D590U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	1122.4	1119.8	1116.8	1111.6	1105.4	1102.0	1096.8	1093.5	1086.8	1081.3	1075.3
5°	1179.3	1167.2	1156.2	1141.8	1126.1	1115.9	1103.8	1090.4	1076.6	1062.2	1046.4
7.5°	1238.3	1217.0	1193.8	1168.9	1144.6	1122.2	1100.8	1079.8	1060.2	1036.4	1016.4
10°	1277.9	1251.1	1222.4	1188.6	1155.7	1127.0	1097.9	1072.4	1046.4	1018.7	994.1
12.5°	1317.6	1281.8	1241.3	1204.2	1164.6	1130.0	1095.6	1063.1	1030.6	999.8	971.2
15°	1345.6	1314.0	1276.6	1223.8	1179.3	1131.7	1086.3	1044.1	1004.8	970.5	934.4
17.5°	1364.0	1323.4	1283.2	1232.5	1174.2	1120.9	1069.5	1021.3	976.9	933.4	898.7
20°	1367.3	1325.6	1283.5	1233.9	1174.2	1113.1	1061.8	1003.8	956.2	911.2	868.6
22.5°	1366.2	1319.0	1273.1	1222.1	1163.9	1107.6	1045.4	986.4	934.7	890.5	846.1
25°	1355.8	1305.3	1247.9	1196.5	1139.1	1079.3	1016.4	955.2	902.4	851.9	808.0
27.5°	1347.0	1281.6	1216.6	1156.6	1101.2	1046.4	986.1	923.5	865.0	813.9	772.4
30°	1336.3	1264.5	1191.3	1128.8	1071.9	1018.7	961.7	900.6	839.5	789.4	745.0
32.5°	1326.7	1243.0	1165.8	1097.8	1037.4	985.7	933.2	875.0	815.0	764.3	719.8
35°	1308.1	1211.3	1122.8	1046.0	981.6	928.4	884.4	830.2	775.1	726.0	683.4
37.5°	1284.4	1169.6	1074.7	994.1	923.5	867.5	826.5	784.9	732.0	684.7	646.2
40°	1265.9	1140.0	1039.5	957.1	884.0	825.5	787.6	748.2	704.3	660.3	619.6
42.5°	1242.6	1113.3	1004.0	915.3	842.8	786.0	746.1	712.7	673.9	632.8	595.0
45°	1199.7	1065.0	946.5	851.0	777.8	721.8	680.6	655.7	626.5	587.5	555.6
47.5°	1136.7	1006.9	884.3	785.9	710.3	658.4	619.8	595.8	575.2	546.4	517.4
50°	1080.7	963.6	839.5	741.7	666.3	613.9	578.4	556.5	539.0	516.7	492.2
52.5°	1018.1	909.1	795.4	698.8	624.1	572.5	537.6	518.4	503.8	487.9	463.7
55°	918.6	826.1	720.5	628.7	559.8	509.3	478.8	462.1	450.0	438.0	423.2
57.5°	809.0	736.6	643.1	559.4	495.8	449.9	421.3	405.1	395.8	389.6	380.8
60°	732.0	670.0	589.4	513.0	451.0	410.3	382.5	370.0	362.1	357.0	350.5
62.5°	660.6	609.7	534.9	465.2	411.0	372.5	347.7	335.6	328.0	325.5	320.1
65°	555.2	515.9	454.2	396.4	350.1	317.2	296.3	284.7	280.1	277.3	277.9
67.5°	451.4	427.4	377.9	328.6	291.6	264.0	247.4	238.4	236.1	232.5	232.4
70°	388.0	370.0	328.3	285.3	252.4	231.0	216.2	207.0	204.6	202.8	202.3
72.5°	332.1	316.3	280.1	245.6	216.1	197.3	185.1	179.6	175.8	174.7	174.6
75°	249.6	240.8	212.0	184.8	164.3	151.4	143.1	137.9	135.2	134.7	135.2
77.5°	177.5	169.8	151.5	132.2	119.3	109.5	102.5	100.7	97.6	97.6	97.1
80°	133.3	128.2	116.7	101.4	90.8	82.4	78.7	75.4	74.5	73.1	74.5
82.5°	96.7	91.2	83.4	73.7	64.8	59.8	56.1	55.1	54.6	53.9	54.2
85°	47.7	48.2	43.5	36.1	32.4	29.6	27.3	27.3	26.8	26.4	26.8
87.5°	17.7	16.7	15.1	13.8	11.7	10.4	9.8	10.1	9.1	8.9	9.5
90°	6.6	5.6	5.1	4.1	3.0	2.1	1.0	0.5	1.0	2.1	3.0
92.5°	116.1	69.5	41.7	26.8	18.1	11.8	7.5	6.2	7.5	11.8	18.1
95°	227.4	115.5	61.1	38.2	26.9	21.4	17.3	16.8	17.3	21.4	26.9
97.5°	181.5	99.5	63.5	47.0	36.9	31.3	28.4	27.9	28.4	31.3	36.9
100°	164.8	98.7	69.2	53.9	44.2	38.7	36.6	35.6	36.6	38.7	44.2
102.5°	157.9	102.4	76.1	61.3	52.4	46.4	44.8	44.1	44.8	46.4	52.4
105°	155.2	109.9	87.5	73.2	65.1	60.0	57.5	57.5	57.5	60.0	65.1
107.5°	159.8	121.1	99.4	86.6	78.1	73.9	71.5	70.5	71.5	73.9	78.1
110°	164.3	129.2	108.3	95.1	87.5	82.9	80.9	79.9	80.9	82.9	87.5





TEST NUMBER: P333216-940

CATALOG NUMBER: S125DIP-S850D590U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	170.0	137.0	116.9	104.1	96.5	91.8	90.2	89.3	90.2	91.8	96.5
115°	178.5	149.0	130.2	117.5	109.9	105.3	103.8	102.7	103.8	105.3	109.9
117.5°	188.3	161.5	143.7	131.3	122.7	118.2	116.5	114.9	116.5	118.2	122.7
120°	194.8	170.4	152.6	139.9	131.3	126.6	124.7	123.1	124.7	126.6	131.3
122.5°	202.2	179.0	161.1	148.5	138.9	134.4	132.8	131.6	132.8	134.4	138.9
125°	212.1	190.2	173.4	160.2	150.5	146.0	143.5	142.4	143.5	146.0	150.5
127.5°	221.2	201.1	184.9	171.7	161.5	155.7	152.4	150.9	152.4	155.7	161.5
130°	227.4	208.0	192.3	179.1	168.4	161.8	157.7	156.1	157.7	161.8	168.4
132.5°	232.6	214.5	198.8	185.6	174.5	167.0	162.2	160.2	162.2	167.0	174.5
135°	240.0	223.3	207.5	193.8	183.2	175.0	168.9	166.8	168.9	175.0	183.2
137.5°	245.6	229.5	215.2	201.0	190.6	182.4	176.7	175.2	176.7	182.4	190.6
140°	249.2	234.0	219.3	205.5	195.8	187.7	181.6	180.0	181.6	187.7	195.8
142.5°	251.3	236.8	222.9	210.0	200.7	192.6	186.9	185.7	186.9	192.6	200.7
145°	254.3	241.7	228.4	216.7	207.5	200.4	195.3	194.3	195.3	200.4	207.5
147.5°	256.2	244.7	233.1	222.7	214.8	208.2	203.8	203.2	203.8	208.2	214.8
150°	257.3	246.7	235.5	226.9	219.7	213.1	209.6	208.6	209.6	213.1	219.7
152.5°	258.2	248.7	238.4	230.5	223.8	218.0	214.8	214.3	214.8	218.0	223.8
155°	258.9	250.7	242.1	235.0	229.9	224.8	221.8	221.8	221.8	224.8	229.9
157.5°	259.4	252.5	245.0	239.7	235.2	230.9	228.4	228.5	228.4	230.9	235.2
160°	259.4	253.3	246.7	242.1	238.1	234.5	232.5	233.0	232.5	234.5	238.1
162.5°	259.0	254.1	248.3	244.6	241.3	238.2	236.1	236.7	236.1	238.2	241.3
165°	258.4	254.3	250.3	247.2	245.1	242.6	241.1	242.1	241.1	242.6	245.1
167.5°	257.2	254.3	250.9	249.1	247.6	246.2	245.3	245.8	245.3	246.2	247.6
170°	256.4	254.3	251.8	250.3	249.2	248.3	247.7	248.3	247.7	248.3	249.2
172.5°	255.6	254.0	251.8	251.1	250.5	249.4	249.0	249.9	249.0	249.4	250.5
175°	254.3	253.3	251.8	251.8	251.8	251.3	250.7	251.8	250.7	251.3	251.8
177.5°	253.1	252.7	251.9	251.9	252.3	251.9	251.9	252.7	251.9	251.9	252.3
180°	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3



TEST NUMBER: P333216-940

CATALOG NUMBER: S125DIP-S850D590U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	1072.0	1067.9	1064.6	1057.2	1053.1	1047.6	1043.1	1047.9	1042.8	1045.0	1041.6
5°	1038.6	1025.6	1016.4	1002.9	991.3	980.7	972.9	971.4	967.7	965.9	960.3
7.5°	998.4	982.1	966.3	948.7	933.8	918.7	909.1	901.2	895.9	888.9	884.2
10°	974.6	952.9	934.4	913.1	894.6	878.3	865.4	858.9	852.9	844.1	840.9
12.5°	945.4	922.9	900.3	877.5	859.8	841.7	830.5	820.7	816.6	806.6	805.7
15°	910.3	876.6	854.3	831.2	806.6	791.8	782.5	771.9	767.2	760.3	755.2
17.5°	868.4	838.3	810.5	786.5	765.4	753.0	741.5	734.1	726.2	721.7	713.4
20°	838.1	809.4	781.6	756.1	739.9	725.6	716.3	709.4	701.1	698.7	690.4
22.5°	812.5	780.9	754.2	732.8	715.1	698.9	688.8	684.2	678.4	671.3	669.6
25°	771.0	738.1	715.4	694.1	678.3	663.5	656.6	650.6	645.0	639.9	638.0
27.5°	735.0	705.6	678.7	659.4	645.8	632.2	626.1	618.8	614.7	610.6	605.6
30°	709.8	679.8	656.1	637.6	622.8	610.7	604.2	599.1	595.5	591.7	589.0
32.5°	683.9	656.0	633.1	615.0	600.2	591.1	585.3	581.8	577.7	573.2	569.7
35°	649.6	619.0	596.8	581.1	569.5	562.6	556.1	552.9	548.2	548.2	544.5
37.5°	611.0	584.6	565.0	550.6	540.3	534.0	527.0	524.8	521.8	519.9	518.6
40°	588.1	563.5	545.0	530.7	519.5	514.4	508.9	505.2	503.3	501.0	500.1
42.5°	564.4	540.9	523.2	509.9	500.2	495.9	490.7	488.1	484.4	481.3	480.8
45°	528.3	505.6	489.5	478.8	470.5	465.4	462.1	456.6	454.7	451.0	450.5
47.5°	494.1	472.3	456.5	447.7	440.4	436.2	431.1	425.6	423.5	421.6	421.4
50°	468.6	448.7	433.8	425.5	418.6	412.6	407.4	403.8	402.3	402.3	403.3
52.5°	442.6	425.7	413.1	403.0	396.4	389.9	385.2	383.0	380.8	383.1	384.8
55°	404.7	387.5	378.3	368.5	362.1	354.6	352.4	351.4	350.1	353.7	355.6
57.5°	364.5	352.5	341.6	332.0	326.2	321.9	318.8	318.2	320.7	322.5	328.6
60°	338.9	325.0	315.3	307.9	301.0	298.2	297.3	296.3	298.2	303.3	311.1
62.5°	310.8	299.5	289.0	283.5	278.4	273.8	273.6	274.1	277.9	283.7	291.5
65°	269.5	259.8	252.8	246.3	242.2	239.4	240.3	242.2	246.3	254.2	263.0
67.5°	227.6	220.9	214.6	209.4	205.4	205.4	206.3	209.1	214.0	223.1	231.1
70°	200.5	193.1	188.0	185.7	182.4	180.6	183.3	188.0	192.2	200.5	207.4
72.5°	173.4	167.2	163.2	161.6	160.2	158.7	159.6	164.6	170.3	178.6	186.7
75°	133.3	131.0	128.2	126.4	125.0	125.9	126.9	131.5	136.2	144.9	154.2
77.5°	97.3	94.9	93.3	92.8	92.0	92.5	95.1	98.5	103.1	109.5	116.5
80°	73.7	72.7	71.8	71.3	71.3	71.8	75.4	77.8	81.9	88.0	93.5
82.5°	53.6	53.1	52.9	52.8	53.1	53.2	55.5	58.5	62.0	66.5	71.3
85°	28.3	27.3	28.7	29.2	28.3	29.6	30.6	32.4	33.8	36.1	38.4
87.5°	10.1	11.1	10.8	11.3	11.4	12.4	12.1	13.6	14.5	15.3	15.2
90°	4.1	5.1	5.6	6.6	7.1	8.1	8.6	9.2	9.6	10.2	11.1
92.5°	26.8	41.7	69.5	116.1	166.7	164.0	132.8	90.2	65.5	49.2	41.7
95°	38.2	61.1	115.5	227.4	367.7	450.7	441.0	365.7	288.4	225.9	183.2
97.5°	47.0	63.5	99.5	181.5	328.4	481.3	558.0	544.7	490.4	429.5	370.1
100°	53.9	69.2	98.7	164.8	293.0	459.3	586.5	625.6	600.7	548.3	495.4
102.5°	61.3	76.1	102.4	157.9	266.1	420.6	569.4	652.9	668.2	643.1	607.3
105°	73.2	87.5	109.9	155.2	240.0	368.8	514.8	636.9	706.5	728.9	723.3
107.5°	86.6	99.4	121.1	159.8	229.1	333.1	459.1	579.4	672.4	730.0	756.4
110°	95.1	108.3	129.2	164.3	225.9	316.4	427.3	537.2	633.8	705.5	748.8



TEST NUMBER: P333216-940

CATALOG NUMBER: S125DIP-S850D590U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	104.1	116.9	137.0	170.0	225.9	306.7	403.7	503.8	595.6	668.1	719.1
115°	117.5	130.2	149.0	178.5	227.4	296.0	377.9	461.8	540.7	610.4	665.8
117.5°	131.3	143.7	161.5	188.3	230.7	290.9	362.6	434.8	502.7	562.8	613.7
120°	139.9	152.6	170.4	194.8	234.0	288.4	354.0	420.2	481.2	537.2	581.9
122.5°	148.5	161.1	179.0	202.2	236.8	286.4	346.7	409.2	465.7	515.6	557.5
125°	160.2	173.4	190.2	212.1	241.7	283.8	336.7	393.2	445.1	489.4	525.9
127.5°	171.7	184.9	201.1	221.2	247.0	282.6	327.6	376.9	425.3	466.6	501.0
130°	179.1	192.3	208.0	227.4	250.3	281.8	321.5	366.8	411.5	451.2	484.2
132.5°	185.6	198.8	214.5	232.6	254.0	281.8	316.6	356.6	398.5	434.5	466.4
135°	193.8	207.5	223.3	240.0	258.9	281.8	310.8	343.3	378.4	411.0	440.0
137.5°	201.0	215.2	229.5	245.6	263.5	282.4	305.6	332.2	360.5	387.6	412.2
140°	205.5	219.3	234.0	249.2	265.6	282.9	303.2	326.0	350.0	373.4	394.8
142.5°	210.0	222.9	236.8	251.3	266.7	283.2	301.1	320.7	341.0	361.1	379.7
145°	216.7	228.4	241.7	254.3	268.0	282.9	298.1	313.9	329.6	345.4	359.1
147.5°	222.7	233.1	244.7	256.2	268.6	281.5	294.9	307.4	320.1	332.3	342.6
150°	226.9	235.5	246.7	257.3	268.6	280.3	292.5	303.6	314.9	324.5	333.7
152.5°	230.5	238.4	248.7	258.2	268.1	278.7	289.6	299.6	309.6	318.4	325.6
155°	235.0	242.1	250.7	258.9	267.1	275.7	284.8	293.5	301.7	308.7	314.3
157.5°	239.7	245.0	252.5	259.4	265.7	272.6	280.4	287.4	294.1	299.6	304.0
160°	242.1	246.7	253.3	259.4	264.5	270.6	276.7	283.3	288.4	293.5	297.0
162.5°	244.6	248.3	254.1	259.0	263.3	268.1	273.5	278.8	283.6	287.8	291.0
165°	247.2	250.3	254.3	258.4	261.4	264.5	268.6	272.6	276.2	279.3	281.8
167.5°	249.1	250.9	254.3	257.2	258.6	260.9	263.8	266.7	269.1	271.4	273.2
170°	250.3	251.8	254.3	256.4	257.3	258.9	260.9	263.5	265.0	266.5	267.5
172.5°	251.1	251.8	254.0	255.6	255.7	256.5	258.1	259.8	261.4	262.4	263.1
175°	251.8	251.8	253.3	254.3	253.8	253.8	254.3	255.8	255.8	256.9	256.9
177.5°	251.9	251.9	252.7	253.1	252.3	252.3	252.7	253.1	253.5	253.5	253.5
180°	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3



TEST NUMBER: P333216-940

CATALOG NUMBER: S125DIP-S850D590U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	1039.4	1042.0	1039.7	1042.8	1039.7	1042.0	1039.4	1041.6	1045.0	1042.8	1047.9
5°	958.0	953.9	956.6	954.8	956.6	953.9	958.0	960.3	965.9	967.7	971.4
7.5°	882.8	878.8	874.3	872.2	874.3	878.8	882.8	884.2	888.9	895.9	901.2
10°	835.8	830.6	830.2	827.0	830.2	830.6	835.8	840.9	844.1	852.9	858.9
12.5°	801.3	796.6	791.3	790.0	791.3	796.6	801.3	805.7	806.6	816.6	820.7
15°	752.4	748.7	745.5	748.2	745.5	748.7	752.4	755.2	760.3	767.2	771.9
17.5°	711.8	708.7	708.1	704.7	708.1	708.7	711.8	713.4	721.7	726.2	734.1
20°	686.2	683.9	684.8	678.8	684.8	683.9	686.2	690.4	698.7	701.1	709.4
22.5°	665.8	661.3	660.8	659.5	660.8	661.3	665.8	669.6	671.3	678.4	684.2
25°	633.9	631.6	629.3	631.6	629.3	631.6	633.9	638.0	639.9	645.0	650.6
27.5°	606.0	603.2	602.6	602.9	602.6	603.2	606.0	605.6	610.6	614.7	618.8
30°	589.0	584.3	584.8	584.3	584.8	584.3	589.0	589.0	591.7	595.5	599.1
32.5°	570.4	567.3	566.7	565.8	566.7	567.3	570.4	569.7	573.2	577.7	581.8
35°	543.1	543.1	540.8	540.8	540.8	543.1	543.1	544.5	548.2	548.2	552.9
37.5°	517.5	517.0	515.6	515.9	515.6	517.0	517.5	518.6	519.9	521.8	524.8
40°	498.2	497.8	496.3	493.6	496.3	497.8	498.2	500.1	501.0	503.3	505.2
42.5°	479.7	478.1	477.5	476.5	477.5	478.1	479.7	480.8	481.3	484.4	488.1
45°	450.5	450.5	449.6	449.2	449.6	450.5	450.5	450.5	451.0	454.7	456.6
47.5°	422.2	423.0	424.8	424.5	424.8	423.0	422.2	421.4	421.6	423.5	425.6
50°	405.1	405.6	407.0	407.4	407.0	405.6	405.1	403.3	402.3	402.3	403.8
52.5°	386.3	389.0	390.7	390.4	390.7	389.0	386.3	384.8	383.1	380.8	383.0
55°	359.8	363.0	366.2	366.8	366.2	363.0	359.8	355.6	353.7	350.1	351.4
57.5°	333.6	338.1	341.5	342.6	341.5	338.1	333.6	328.6	322.5	320.7	318.2
60°	315.8	321.8	326.0	327.8	326.0	321.8	315.8	311.1	303.3	298.2	296.3
62.5°	298.7	305.5	309.7	310.0	309.7	305.5	298.7	291.5	283.7	277.9	274.1
65°	270.9	277.9	281.5	284.3	281.5	277.9	270.9	263.0	254.2	246.3	242.2
67.5°	240.9	247.8	251.9	254.1	251.9	247.8	240.9	231.1	223.1	214.0	209.1
70°	219.0	226.0	231.5	233.4	231.5	226.0	219.0	207.4	200.5	192.2	188.0
72.5°	197.5	203.8	208.2	210.4	208.2	203.8	197.5	186.7	178.6	170.3	164.6
75°	160.2	168.5	172.7	175.0	172.7	168.5	160.2	154.2	144.9	136.2	131.5
77.5°	123.5	131.2	133.7	134.8	133.7	131.2	123.5	116.5	109.5	103.1	98.5
80°	99.1	103.7	106.9	107.5	106.9	103.7	99.1	93.5	88.0	81.9	77.8
82.5°	76.2	80.0	81.1	82.2	81.1	80.0	76.2	71.3	66.5	62.0	58.5
85°	41.6	43.5	44.0	43.5	44.0	43.5	41.6	38.4	36.1	33.8	32.4
87.5°	16.0	15.6	15.7	16.4	15.7	15.6	16.0	15.2	15.3	14.5	13.6
90°	11.1	11.1	11.7	11.7	11.7	11.1	11.1	11.1	10.2	9.6	9.2
92.5°	35.2	34.0	33.3	32.5	33.3	34.0	35.2	41.7	49.2	65.5	90.2
95°	147.0	131.7	127.7	119.6	127.7	131.7	147.0	183.2	225.9	288.4	365.7
97.5°	338.7	310.1	295.4	288.9	295.4	310.1	338.7	370.1	429.5	490.4	544.7
100°	460.3	423.7	404.9	396.7	404.9	423.7	460.3	495.4	548.3	600.7	625.6
102.5°	569.8	543.8	523.3	517.2	523.3	543.8	569.8	607.3	643.1	668.2	652.9
105°	707.0	690.3	680.1	674.0	680.1	690.3	707.0	723.3	728.9	706.5	636.9
107.5°	764.7	764.6	761.3	757.2	761.3	764.6	764.7	756.4	730.0	672.4	579.4
110°	771.6	781.3	784.9	784.9	784.9	781.3	771.6	748.8	705.5	633.8	537.2



TEST NUMBER: P333216-940

CATALOG NUMBER: S125DIP-S850D590U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	752.5	769.1	777.9	781.6	777.9	769.1	752.5	719.1	668.1	595.6	503.8
115°	705.5	730.0	744.1	750.8	744.1	730.0	705.5	665.8	610.4	540.7	461.8
117.5°	653.4	678.6	692.7	696.8	692.7	678.6	653.4	613.7	562.8	502.7	434.8
120°	619.6	644.0	657.7	661.7	657.7	644.0	619.6	581.9	537.2	481.2	420.2
122.5°	591.0	613.4	627.1	630.8	627.1	613.4	591.0	557.5	515.6	465.7	409.2
125°	554.5	575.3	586.5	591.6	586.5	575.3	554.5	525.9	489.4	445.1	393.2
127.5°	526.7	545.2	555.7	558.0	555.7	545.2	526.7	501.0	466.6	425.3	376.9
130°	509.7	526.5	536.6	539.7	536.6	526.5	509.7	484.2	451.2	411.5	366.8
132.5°	491.8	508.5	517.9	521.4	517.9	508.5	491.8	466.4	434.5	398.5	356.6
135°	462.4	479.1	488.3	491.3	488.3	479.1	462.4	440.0	411.0	378.4	343.3
137.5°	432.2	447.5	455.9	459.3	455.9	447.5	432.2	412.2	387.6	360.5	332.2
140°	413.6	426.8	434.4	436.9	434.4	426.8	413.6	394.8	373.4	350.0	326.0
142.5°	395.7	406.8	414.0	416.2	414.0	406.8	395.7	379.7	361.1	341.0	320.7
145°	371.3	380.0	385.6	387.6	385.6	380.0	371.3	359.1	345.4	329.6	313.9
147.5°	352.3	359.2	362.5	363.4	362.5	359.2	352.3	342.6	332.3	320.1	307.4
150°	341.3	347.4	349.5	350.0	349.5	347.4	341.3	333.7	324.5	314.9	303.6
152.5°	332.0	336.8	338.9	339.4	338.9	336.8	332.0	325.6	318.4	309.6	299.6
155°	319.4	323.0	324.5	325.0	324.5	323.0	319.4	314.3	308.7	301.7	293.5
157.5°	307.9	310.9	312.3	312.2	312.3	310.9	307.9	304.0	299.6	294.1	287.4
160°	300.6	303.2	304.2	303.6	304.2	303.2	300.6	297.0	293.5	288.4	283.3
162.5°	293.7	295.9	296.0	296.0	296.0	295.9	293.7	291.0	287.8	283.6	278.8
165°	283.8	284.8	284.8	284.8	284.8	284.8	283.8	281.8	279.3	276.2	272.6
167.5°	274.3	275.2	274.7	274.6	274.7	275.2	274.3	273.2	271.4	269.1	266.7
170°	268.6	269.1	269.1	268.6	269.1	269.1	268.6	267.5	266.5	265.0	263.5
172.5°	263.3	264.2	263.4	262.9	263.4	264.2	263.3	263.1	262.4	261.4	259.8
175°	256.9	257.3	256.4	255.8	256.4	257.3	256.9	256.9	256.9	255.8	255.8
177.5°	253.1	253.5	252.3	252.3	252.3	253.5	253.1	253.5	253.5	253.5	253.1
180°	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3



TEST NUMBER: P333216-940

CATALOG NUMBER: S125DIP-S850D590U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	1043.1	1047.6	1053.1	1057.2	1064.6	1067.9	1072.0	1075.3	1081.3	1086.8	1093.5
5°	972.9	980.7	991.3	1002.9	1016.4	1025.6	1038.6	1046.4	1062.2	1076.6	1090.4
7.5°	909.1	918.7	933.8	948.7	966.3	982.1	998.4	1016.4	1036.4	1060.2	1079.8
10°	865.4	878.3	894.6	913.1	934.4	952.9	974.6	994.1	1018.7	1046.4	1072.4
12.5°	830.5	841.7	859.8	877.5	900.3	922.9	945.4	971.2	999.8	1030.6	1063.1
15°	782.5	791.8	806.6	831.2	854.3	876.6	910.3	934.4	970.5	1004.8	1044.1
17.5°	741.5	753.0	765.4	786.5	810.5	838.3	868.4	898.7	933.4	976.9	1021.3
20°	716.3	725.6	739.9	756.1	781.6	809.4	838.1	868.6	911.2	956.2	1003.8
22.5°	688.8	698.9	715.1	732.8	754.2	780.9	812.5	846.1	890.5	934.7	986.4
25°	656.6	663.5	678.3	694.1	715.4	738.1	771.0	808.0	851.9	902.4	955.2
27.5°	626.1	632.2	645.8	659.4	678.7	705.6	735.0	772.4	813.9	865.0	923.5
30°	604.2	610.7	622.8	637.6	656.1	679.8	709.8	745.0	789.4	839.5	900.6
32.5°	585.3	591.1	600.2	615.0	633.1	656.0	683.9	719.8	764.3	815.0	875.0
35°	556.1	562.6	569.5	581.1	596.8	619.0	649.6	683.4	726.0	775.1	830.2
37.5°	527.0	534.0	540.3	550.6	565.0	584.6	611.0	646.2	684.7	732.0	784.9
40°	508.9	514.4	519.5	530.7	545.0	563.5	588.1	619.6	660.3	704.3	748.2
42.5°	490.7	495.9	500.2	509.9	523.2	540.9	564.4	595.0	632.8	673.9	712.7
45°	462.1	465.4	470.5	478.8	489.5	505.6	528.3	555.6	587.5	626.5	655.7
47.5°	431.1	436.2	440.4	447.7	456.5	472.3	494.1	517.4	546.4	575.2	595.8
50°	407.4	412.6	418.6	425.5	433.8	448.7	468.6	492.2	516.7	539.0	556.5
52.5°	385.2	389.9	396.4	403.0	413.1	425.7	442.6	463.7	487.9	503.8	518.4
55°	352.4	354.6	362.1	368.5	378.3	387.5	404.7	423.2	438.0	450.0	462.1
57.5°	318.8	321.9	326.2	332.0	341.6	352.5	364.5	380.8	389.6	395.8	405.1
60°	297.3	298.2	301.0	307.9	315.3	325.0	338.9	350.5	357.0	362.1	370.0
62.5°	273.6	273.8	278.4	283.5	289.0	299.5	310.8	320.1	325.5	328.0	335.6
65°	240.3	239.4	242.2	246.3	252.8	259.8	269.5	277.9	277.3	280.1	284.7
67.5°	206.3	205.4	205.4	209.4	214.6	220.9	227.6	232.4	232.5	236.1	238.4
70°	183.3	180.6	182.4	185.7	188.0	193.1	200.5	202.3	202.8	204.6	207.0
72.5°	159.6	158.7	160.2	161.6	163.2	167.2	173.4	174.6	174.7	175.8	179.6
75°	126.9	125.9	125.0	126.4	128.2	131.0	133.3	135.2	134.7	135.2	137.9
77.5°	95.1	92.5	92.0	92.8	93.3	94.9	97.3	97.1	97.6	97.6	100.7
80°	75.4	71.8	71.3	71.3	71.8	72.7	73.7	74.5	73.1	74.5	75.4
82.5°	55.5	53.2	53.1	52.8	52.9	53.1	53.6	54.2	53.9	54.6	55.1
85°	30.6	29.6	28.3	29.2	28.7	27.3	28.3	26.8	26.4	26.8	27.3
87.5°	12.1	12.4	11.4	11.3	10.8	11.1	10.1	9.5	8.9	9.1	10.1
90°	8.6	8.1	7.1	6.6	5.6	5.1	4.1	3.0	2.1	1.0	0.5
92.5°	132.8	164.0	166.7	116.1	69.5	41.7	26.8	18.1	11.8	7.5	6.2
95°	441.0	450.7	367.7	227.4	115.5	61.1	38.2	26.9	21.4	17.3	16.8
97.5°	558.0	481.3	328.4	181.5	99.5	63.5	47.0	36.9	31.3	28.4	27.9
100°	586.5	459.3	293.0	164.8	98.7	69.2	53.9	44.2	38.7	36.6	35.6
102.5°	569.4	420.6	266.1	157.9	102.4	76.1	61.3	52.4	46.4	44.8	44.1
105°	514.8	368.8	240.0	155.2	109.9	87.5	73.2	65.1	60.0	57.5	57.5
107.5°	459.1	333.1	229.1	159.8	121.1	99.4	86.6	78.1	73.9	71.5	70.5
110°	427.3	316.4	225.9	164.3	129.2	108.3	95.1	87.5	82.9	80.9	79.9



TEST NUMBER: P333216-940

CATALOG NUMBER: S125DIP-S850D590U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	403.7	306.7	225.9	170.0	137.0	116.9	104.1	96.5	91.8	90.2	89.3
115°	377.9	296.0	227.4	178.5	149.0	130.2	117.5	109.9	105.3	103.8	102.7
117.5°	362.6	290.9	230.7	188.3	161.5	143.7	131.3	122.7	118.2	116.5	114.9
120°	354.0	288.4	234.0	194.8	170.4	152.6	139.9	131.3	126.6	124.7	123.1
122.5°	346.7	286.4	236.8	202.2	179.0	161.1	148.5	138.9	134.4	132.8	131.6
125°	336.7	283.8	241.7	212.1	190.2	173.4	160.2	150.5	146.0	143.5	142.4
127.5°	327.6	282.6	247.0	221.2	201.1	184.9	171.7	161.5	155.7	152.4	150.9
130°	321.5	281.8	250.3	227.4	208.0	192.3	179.1	168.4	161.8	157.7	156.1
132.5°	316.6	281.8	254.0	232.6	214.5	198.8	185.6	174.5	167.0	162.2	160.2
135°	310.8	281.8	258.9	240.0	223.3	207.5	193.8	183.2	175.0	168.9	166.8
137.5°	305.6	282.4	263.5	245.6	229.5	215.2	201.0	190.6	182.4	176.7	175.2
140°	303.2	282.9	265.6	249.2	234.0	219.3	205.5	195.8	187.7	181.6	180.0
142.5°	301.1	283.2	266.7	251.3	236.8	222.9	210.0	200.7	192.6	186.9	185.7
145°	298.1	282.9	268.0	254.3	241.7	228.4	216.7	207.5	200.4	195.3	194.3
147.5°	294.9	281.5	268.6	256.2	244.7	233.1	222.7	214.8	208.2	203.8	203.2
150°	292.5	280.3	268.6	257.3	246.7	235.5	226.9	219.7	213.1	209.6	208.6
152.5°	289.6	278.7	268.1	258.2	248.7	238.4	230.5	223.8	218.0	214.8	214.3
155°	284.8	275.7	267.1	258.9	250.7	242.1	235.0	229.9	224.8	221.8	221.8
157.5°	280.4	272.6	265.7	259.4	252.5	245.0	239.7	235.2	230.9	228.4	228.5
160°	276.7	270.6	264.5	259.4	253.3	246.7	242.1	238.1	234.5	232.5	233.0
162.5°	273.5	268.1	263.3	259.0	254.1	248.3	244.6	241.3	238.2	236.1	236.7
165°	268.6	264.5	261.4	258.4	254.3	250.3	247.2	245.1	242.6	241.1	242.1
167.5°	263.8	260.9	258.6	257.2	254.3	250.9	249.1	247.6	246.2	245.3	245.8
170°	260.9	258.9	257.3	256.4	254.3	251.8	250.3	249.2	248.3	247.7	248.3
172.5°	258.1	256.5	255.7	255.6	254.0	251.8	251.1	250.5	249.4	249.0	249.9
175°	254.3	253.8	253.8	254.3	253.3	251.8	251.8	251.8	251.3	250.7	251.8
177.5°	252.7	252.3	252.3	253.1	252.7	251.9	251.9	252.3	251.9	251.9	252.7
180°	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3



TEST NUMBER: P333216-940

CATALOG NUMBER: S125DIP-S850D590U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	1096.8	1102.0	1105.4	1111.6	1116.8	1119.8	1122.4	1124.6	1127.2	1129.4	1135.7
5°	1103.8	1115.9	1126.1	1141.8	1156.2	1167.2	1179.3	1190.0	1198.8	1211.3	1221.0
7.5°	1100.8	1122.2	1144.6	1168.9	1193.8	1217.0	1238.3	1258.2	1276.3	1298.2	1317.3
10°	1097.9	1127.0	1155.7	1188.6	1222.4	1251.1	1277.9	1305.3	1325.2	1353.0	1376.5
12.5°	1095.6	1130.0	1164.6	1204.2	1241.3	1281.8	1317.6	1337.5	1367.8	1390.0	1418.1
15°	1086.3	1131.7	1179.3	1223.8	1276.6	1314.0	1345.6	1384.5	1412.6	1440.9	1471.5
17.5°	1069.5	1120.9	1174.2	1232.5	1283.2	1323.4	1364.0	1401.5	1435.2	1473.1	1511.1
20°	1061.8	1113.1	1174.2	1233.9	1283.5	1325.6	1367.3	1408.5	1445.6	1494.2	1538.2
22.5°	1045.4	1107.6	1163.9	1222.1	1273.1	1319.0	1366.2	1413.0	1462.2	1517.2	1572.3
25°	1016.4	1079.3	1139.1	1196.5	1247.9	1305.3	1355.8	1418.3	1481.2	1553.9	1622.5
27.5°	986.1	1046.4	1101.2	1156.6	1216.6	1281.6	1347.0	1418.0	1500.4	1592.1	1688.8
30°	961.7	1018.7	1071.9	1128.8	1191.3	1264.5	1336.3	1420.6	1515.9	1619.2	1734.0
32.5°	933.2	985.7	1037.4	1097.8	1165.8	1243.0	1326.7	1419.1	1533.7	1651.1	1769.2
35°	884.4	928.4	981.6	1046.0	1122.8	1211.3	1308.1	1417.3	1548.8	1683.6	1783.2
37.5°	826.5	867.5	923.5	994.1	1074.7	1169.6	1284.4	1414.1	1553.7	1661.2	1693.3
40°	787.6	825.5	884.0	957.1	1039.5	1140.0	1265.9	1402.9	1538.2	1606.7	1580.3
42.5°	746.1	786.0	842.8	915.3	1004.0	1113.3	1242.6	1379.7	1493.0	1518.9	1427.7
45°	680.6	721.8	777.8	851.0	946.5	1065.0	1199.7	1324.3	1389.6	1342.7	1201.6
47.5°	619.8	658.4	710.3	785.9	884.3	1006.9	1136.7	1236.0	1241.2	1129.6	978.7
50°	578.4	613.9	666.3	741.7	839.5	963.6	1080.7	1159.0	1123.7	997.4	852.4
52.5°	537.6	572.5	624.1	698.8	795.4	909.1	1018.1	1073.0	1006.7	877.0	753.1
55°	478.8	509.3	559.8	628.7	720.5	826.1	918.6	937.6	851.5	723.7	623.2
57.5°	421.3	449.9	495.8	559.4	643.1	736.6	809.0	805.0	714.0	604.3	524.6
60°	382.5	410.3	451.0	513.0	589.4	670.0	732.0	717.2	627.0	532.4	465.4
62.5°	347.7	372.5	411.0	465.2	534.9	609.7	660.6	638.7	550.3	467.6	414.6
65°	296.3	317.2	350.1	396.4	454.2	515.9	555.2	526.9	451.5	387.1	344.5
67.5°	247.4	264.0	291.6	328.6	377.9	427.4	451.4	422.9	362.6	315.6	284.0
70°	216.2	231.0	252.4	285.3	328.3	370.0	388.0	362.6	310.7	270.4	247.7
72.5°	185.1	197.3	216.1	245.6	280.1	316.3	332.1	307.7	265.1	231.1	209.9
75°	143.1	151.4	164.3	184.8	212.0	240.8	249.6	228.3	201.0	175.5	161.6
77.5°	102.5	109.5	119.3	132.2	151.5	169.8	177.5	165.1	144.0	127.9	116.5
80°	78.7	82.4	90.8	101.4	116.7	128.2	133.3	125.5	110.7	98.6	89.8
82.5°	56.1	59.8	64.8	73.7	83.4	91.2	96.7	91.4	80.7	71.2	66.1
85°	27.3	29.6	32.4	36.1	43.5	48.2	47.7	44.4	40.3	36.6	33.8
87.5°	9.8	10.4	11.7	13.8	15.1	16.7	17.7	16.9	15.7	14.7	13.6
90°	1.0	2.1	3.0	4.1	5.1	5.6	6.6	7.1	8.1	8.6	9.2
92.5°	7.5	11.8	18.1	26.8	41.7	69.5	116.1	166.7	164.0	132.8	90.2
95°	17.3	21.4	26.9	38.2	61.1	115.5	227.4	367.7	450.7	441.0	365.7
97.5°	28.4	31.3	36.9	47.0	63.5	99.5	181.5	328.4	481.3	558.0	544.7
100°	36.6	38.7	44.2	53.9	69.2	98.7	164.8	293.0	459.3	586.5	625.6
102.5°	44.8	46.4	52.4	61.3	76.1	102.4	157.9	266.1	420.6	569.4	652.9
105°	57.5	60.0	65.1	73.2	87.5	109.9	155.2	240.0	368.8	514.8	636.9
107.5°	71.5	73.9	78.1	86.6	99.4	121.1	159.8	229.1	333.1	459.1	579.4
110°	80.9	82.9	87.5	95.1	108.3	129.2	164.3	225.9	316.4	427.3	537.2





TEST NUMBER: P333216-940

CATALOG NUMBER: S125DIP-S850D590U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	90.2	91.8	96.5	104.1	116.9	137.0	170.0	225.9	306.7	403.7	503.8
115°	103.8	105.3	109.9	117.5	130.2	149.0	178.5	227.4	296.0	377.9	461.8
117.5°	116.5	118.2	122.7	131.3	143.7	161.5	188.3	230.7	290.9	362.6	434.8
120°	124.7	126.6	131.3	139.9	152.6	170.4	194.8	234.0	288.4	354.0	420.2
122.5°	132.8	134.4	138.9	148.5	161.1	179.0	202.2	236.8	286.4	346.7	409.2
125°	143.5	146.0	150.5	160.2	173.4	190.2	212.1	241.7	283.8	336.7	393.2
127.5°	152.4	155.7	161.5	171.7	184.9	201.1	221.2	247.0	282.6	327.6	376.9
130°	157.7	161.8	168.4	179.1	192.3	208.0	227.4	250.3	281.8	321.5	366.8
132.5°	162.2	167.0	174.5	185.6	198.8	214.5	232.6	254.0	281.8	316.6	356.6
135°	168.9	175.0	183.2	193.8	207.5	223.3	240.0	258.9	281.8	310.8	343.3
137.5°	176.7	182.4	190.6	201.0	215.2	229.5	245.6	263.5	282.4	305.6	332.2
140°	181.6	187.7	195.8	205.5	219.3	234.0	249.2	265.6	282.9	303.2	326.0
142.5°	186.9	192.6	200.7	210.0	222.9	236.8	251.3	266.7	283.2	301.1	320.7
145°	195.3	200.4	207.5	216.7	228.4	241.7	254.3	268.0	282.9	298.1	313.9
147.5°	203.8	208.2	214.8	222.7	233.1	244.7	256.2	268.6	281.5	294.9	307.4
150°	209.6	213.1	219.7	226.9	235.5	246.7	257.3	268.6	280.3	292.5	303.6
152.5°	214.8	218.0	223.8	230.5	238.4	248.7	258.2	268.1	278.7	289.6	299.6
155°	221.8	224.8	229.9	235.0	242.1	250.7	258.9	267.1	275.7	284.8	293.5
157.5°	228.4	230.9	235.2	239.7	245.0	252.5	259.4	265.7	272.6	280.4	287.4
160°	232.5	234.5	238.1	242.1	246.7	253.3	259.4	264.5	270.6	276.7	283.3
162.5°	236.1	238.2	241.3	244.6	248.3	254.1	259.0	263.3	268.1	273.5	278.8
165°	241.1	242.6	245.1	247.2	250.3	254.3	258.4	261.4	264.5	268.6	272.6
167.5°	245.3	246.2	247.6	249.1	250.9	254.3	257.2	258.6	260.9	263.8	266.7
170°	247.7	248.3	249.2	250.3	251.8	254.3	256.4	257.3	258.9	260.9	263.5
172.5°	249.0	249.4	250.5	251.1	251.8	254.0	255.6	255.7	256.5	258.1	259.8
175°	250.7	251.3	251.8	251.8	251.8	253.3	254.3	253.8	253.8	254.3	255.8
177.5°	251.9	251.9	252.3	251.9	251.9	252.7	253.1	252.3	252.3	252.7	253.1
180°	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3



TEST NUMBER: P333216-940

CATALOG NUMBER: S125DIP-S850D590U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	1140.9	1143.9	1150.1	1147.9	1150.9	1152.4	1153.9
5°	1233.1	1247.9	1254.4	1253.4	1263.1	1260.8	1258.5
7.5°	1337.1	1352.7	1361.4	1372.3	1378.5	1378.9	1384.5
10°	1396.1	1416.4	1424.8	1436.3	1443.7	1447.9	1447.4
12.5°	1441.2	1457.1	1475.9	1481.5	1491.5	1496.7	1494.9
15°	1495.6	1521.1	1540.5	1550.2	1562.7	1566.4	1571.6
17.5°	1544.1	1578.2	1601.0	1631.1	1642.5	1649.5	1645.4
20°	1580.7	1625.7	1648.4	1684.5	1704.4	1715.0	1711.4
22.5°	1624.1	1672.8	1714.7	1746.0	1776.3	1790.6	1793.6
25°	1698.4	1765.1	1826.7	1867.9	1905.3	1914.1	1933.6
27.5°	1781.4	1860.0	1925.8	1969.2	1995.3	2005.1	2011.2
30°	1833.6	1911.8	1961.4	1989.1	1997.5	1996.5	1995.6
32.5°	1859.1	1908.2	1917.6	1909.9	1890.8	1874.7	1857.9
35°	1822.9	1786.4	1731.7	1661.3	1609.4	1557.2	1552.0
37.5°	1639.5	1522.5	1431.6	1330.0	1271.4	1235.2	1210.1
40°	1466.9	1334.0	1223.8	1138.1	1078.3	1054.8	1031.6
42.5°	1279.4	1152.4	1054.9	983.3	938.3	912.1	893.9
45°	1039.5	927.5	851.0	799.2	763.6	743.2	731.6
47.5°	851.8	768.9	704.0	666.6	641.9	626.1	626.2
50°	751.0	671.8	628.7	599.1	577.8	565.3	567.7
52.5°	661.7	602.6	565.8	541.0	525.2	517.5	517.3
55°	553.3	510.7	486.6	468.6	457.9	449.2	451.0
57.5°	473.3	437.4	421.2	406.3	398.9	395.3	390.2
60°	423.7	395.9	382.0	370.0	362.6	359.8	354.6
62.5°	379.6	357.8	344.2	334.4	327.7	326.8	322.8
65°	319.1	302.4	290.3	285.7	278.7	276.9	276.9
67.5°	263.0	251.0	241.7	237.5	234.3	234.9	232.6
70°	227.8	218.1	212.0	207.4	205.1	205.5	203.8
72.5°	199.3	188.4	183.2	180.4	177.4	178.5	177.8
75°	151.0	145.3	142.6	139.8	137.9	137.1	136.2
77.5°	110.8	105.9	103.8	102.3	102.5	100.3	102.0
80°	85.7	81.5	80.1	77.8	77.3	77.3	76.9
82.5°	62.7	60.4	59.4	57.4	56.6	57.3	56.1
85°	32.4	30.6	30.1	30.1	29.2	28.3	30.6
87.5°	13.8	12.4	12.6	12.2	12.2	11.9	11.2
90°	9.6	10.2	11.1	11.1	11.1	11.7	11.7
92.5°	65.5	49.2	41.7	35.2	34.0	33.3	32.5
95°	288.4	225.9	183.2	147.0	131.7	127.7	119.6
97.5°	490.4	429.5	370.1	338.7	310.1	295.4	288.9
100°	600.7	548.3	495.4	460.3	423.7	404.9	396.7
102.5°	668.2	643.1	607.3	569.8	543.8	523.3	517.2
105°	706.5	728.9	723.3	707.0	690.3	680.1	674.0
107.5°	672.4	730.0	756.4	764.7	764.6	761.3	757.2
110°	633.8	705.5	748.8	771.6	781.3	784.9	784.9



TEST NUMBER: P333216-940

CATALOG NUMBER: S125DIP-S850D590U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	595.6	668.1	719.1	752.5	769.1	777.9	781.6
115°	540.7	610.4	665.8	705.5	730.0	744.1	750.8
117.5°	502.7	562.8	613.7	653.4	678.6	692.7	696.8
120°	481.2	537.2	581.9	619.6	644.0	657.7	661.7
122.5°	465.7	515.6	557.5	591.0	613.4	627.1	630.8
125°	445.1	489.4	525.9	554.5	575.3	586.5	591.6
127.5°	425.3	466.6	501.0	526.7	545.2	555.7	558.0
130°	411.5	451.2	484.2	509.7	526.5	536.6	539.7
132.5°	398.5	434.5	466.4	491.8	508.5	517.9	521.4
135°	378.4	411.0	440.0	462.4	479.1	488.3	491.3
137.5°	360.5	387.6	412.2	432.2	447.5	455.9	459.3
140°	350.0	373.4	394.8	413.6	426.8	434.4	436.9
142.5°	341.0	361.1	379.7	395.7	406.8	414.0	416.2
145°	329.6	345.4	359.1	371.3	380.0	385.6	387.6
147.5°	320.1	332.3	342.6	352.3	359.2	362.5	363.4
150°	314.9	324.5	333.7	341.3	347.4	349.5	350.0
152.5°	309.6	318.4	325.6	332.0	336.8	338.9	339.4
155°	301.7	308.7	314.3	319.4	323.0	324.5	325.0
157.5°	294.1	299.6	304.0	307.9	310.9	312.3	312.2
160°	288.4	293.5	297.0	300.6	303.2	304.2	303.6
162.5°	283.6	287.8	291.0	293.7	295.9	296.0	296.0
165°	276.2	279.3	281.8	283.8	284.8	284.8	284.8
167.5°	269.1	271.4	273.2	274.3	275.2	274.7	274.6
170°	265.0	266.5	267.5	268.6	269.1	269.1	268.6
172.5°	261.4	262.4	263.1	263.3	264.2	263.4	262.9
175°	255.8	256.9	256.9	256.9	257.3	256.4	255.8
177.5°	253.5	253.5	253.5	253.1	253.5	252.3	252.3
180°	252.3	252.3	252.3	252.3	252.3	252.3	252.3

(END OF REPORT)