

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333222-940

Luminaire Tested: **S125DIP-S850D590U940-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333222-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S850D590U940-4F0-1E-UDD-F4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4939.5 lumens  
Efficiency: N/A  
Efficacy: 122.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 40.3  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333222-940

CATALOG NUMBER: S125DIP-S850D590U940-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P333222-940

CATALOG NUMBER: S125DIP-S850D590U940-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	100	96	92	88	94	90	86	83	79	76	74	68	67	65	59	58	56	52
2	91	84	77	72	85	79	73	68	69	65	61	60	57	54	52	50	47	43
3	83	74	66	60	78	69	62	57	61	56	51	53	49	46	46	43	40	37
4	76	65	57	51	71	61	54	48	54	48	44	47	43	39	41	38	35	31
5	70	58	50	44	65	55	47	42	48	42	38	43	38	34	37	33	30	27
6	65	52	44	38	60	49	42	36	44	38	33	38	34	30	34	30	27	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	26	31	27	24	21
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	30	25	21	26	22	19	17
10	48	36	29	24	45	34	27	23	31	25	21	27	23	19	24	20	17	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7559	7559	7559
5°	7577	7505	7553
10°	7531	7452	7494
15°	7449	7362	7393
20°	7332	7236	7249
25°	7207	7088	7081
30°	7052	6927	6893
35°	6885	6754	6659
40°	6715	6566	6473
45°	6530	6395	6268
50°	6327	6187	6002
55°	6132	5954	5788
60°	5898	5717	5515
65°	5619	5434	5251
70°	5351	5108	4932
75°	4876	4716	4551
80°	4340	4273	4169
85°	3772	3846	3631



TEST NUMBER: P333222-940

CATALOG NUMBER: S125DIP-S850D590U940-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	110.4	2.2
10°-20°	311.8	6.3
20°-30°	460.3	9.3
30°-40°	537.2	10.9
40°-50°	539.5	10.9
50°-60°	473.6	9.6
60°-70°	352.9	7.1
70°-80°	201.8	4.1
80°-90°	60.1	1.2
90°-100°	182.9	3.7
100°-110°	393.1	8.0
110°-120°	369.0	7.5
120°-130°	299.0	6.1
130°-140°	240.0	4.9
140°-150°	181.1	3.7
150°-160°	127.5	2.6
160°-170°	75.1	1.5
170°-180°	24.4	0.5
0°-30°	882.5	17.9
0°-40°	1419.6	28.7
0°-60°	2432.7	49.3
0°-90°	3047.5	61.7
90°-120°	945.0	19.1
90°-150°	1665.0	33.7
90°-180°	1892.0	38.3
0°-180°	4939.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1170	1170	1170	1170	1170	
5°	1169	1166	1158	1165	1165	111
15°	1114	1111	1101	1106	1106	314
25°	1011	1006	995	996	994	465
35°	873	869	857	852	845	546
45°	715	711	700	690	686	551
55°	545	541	529	521	514	486
65°	368	365	356	348	344	365
75°	195	193	189	186	182	208
85°	51	52	52	51	49	57
90°	0	5	8	11	12	4
95°	17	50	451	205	120	18
105°	58	80	369	726	674	61
115°	103	124	296	638	751	101
125°	142	167	284	508	592	126
135°	167	201	282	426	491	129
145°	194	223	283	352	388	122
155°	222	239	276	312	325	102
165°	242	249	264	281	285	68
175°	252	252	254	257	256	24
180°	252	252	252	252	252	



TEST NUMBER: P333222-940

CATALOG NUMBER: S125DIP-S850D590U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5
2.5°	1173.6	1173.0	1172.6	1172.1	1171.5	1170.5	1168.9	1167.2	1165.6	1164.0	1165.6
5°	1168.8	1168.3	1167.9	1167.5	1167.1	1165.8	1163.8	1161.7	1159.7	1157.6	1159.5
7.5°	1158.0	1157.6	1157.2	1156.7	1156.4	1155.0	1152.7	1150.5	1148.3	1145.9	1147.7
10°	1148.3	1148.0	1147.5	1147.1	1146.7	1145.4	1143.1	1140.9	1138.6	1136.3	1138.0
12.5°	1136.5	1135.8	1135.1	1134.3	1133.5	1132.1	1130.1	1127.9	1125.8	1123.7	1125.1
15°	1114.1	1113.5	1112.9	1112.2	1111.6	1110.2	1108.0	1105.6	1103.4	1101.1	1102.2
17.5°	1088.3	1087.4	1086.5	1085.7	1084.8	1083.1	1080.8	1078.4	1076.0	1073.7	1075.0
20°	1066.8	1066.5	1066.0	1065.6	1065.2	1063.6	1061.0	1058.3	1055.6	1052.9	1054.4
22.5°	1045.4	1044.6	1043.9	1043.1	1042.4	1040.8	1038.3	1035.7	1033.2	1030.7	1031.7
25°	1011.3	1010.3	1009.2	1008.2	1007.2	1005.3	1002.6	1000.0	997.3	994.6	995.1
27.5°	971.4	970.9	970.3	969.6	969.0	967.3	964.6	961.8	959.0	956.3	956.4
30°	945.6	944.9	944.3	943.7	943.1	941.2	938.2	935.0	931.9	928.9	928.4
32.5°	917.4	916.4	915.5	914.5	913.6	911.8	909.0	906.2	903.5	900.7	900.0
35°	873.3	872.4	871.6	870.8	870.0	868.2	865.3	862.4	859.5	856.7	855.6
37.5°	827.6	826.5	825.5	824.5	823.4	821.5	818.9	816.1	813.4	810.7	809.1
40°	796.5	795.4	794.4	793.4	792.3	790.4	787.5	784.6	781.8	778.8	777.0
42.5°	763.1	762.2	761.3	760.5	759.6	757.8	754.9	752.0	749.1	746.3	744.6
45°	715.0	714.1	713.3	712.5	711.7	710.0	707.6	705.1	702.6	700.2	697.7
47.5°	663.1	663.2	663.2	663.2	663.3	661.8	658.8	655.9	652.9	650.0	647.4
50°	629.7	629.1	628.5	627.9	627.3	625.7	623.3	620.8	618.3	615.8	613.1
52.5°	595.7	595.2	594.8	594.3	593.9	592.3	589.7	587.0	584.4	581.8	579.4
55°	544.6	543.9	543.3	542.7	542.1	540.3	537.4	534.6	531.6	528.8	526.9
57.5°	490.6	490.4	490.0	489.6	489.4	487.9	485.5	483.1	480.6	478.2	475.8
60°	456.6	455.8	455.0	454.1	453.3	451.7	449.4	447.2	445.0	442.6	440.6
62.5°	421.0	420.4	419.7	419.0	418.4	417.1	415.2	413.2	411.3	409.3	407.2
65°	367.7	367.2	366.8	366.4	366.0	364.7	362.4	360.2	357.8	355.6	353.7
67.5°	316.0	315.1	314.2	313.3	312.5	311.2	309.6	307.9	306.2	304.5	302.9
70°	283.4	282.3	281.3	280.3	279.3	277.9	276.0	274.1	272.2	270.5	269.2
72.5°	247.8	247.1	246.4	245.8	245.0	244.1	242.9	241.7	240.5	239.3	237.9
75°	195.4	195.0	194.6	194.2	193.8	193.1	192.0	191.0	189.9	189.0	188.3
77.5°	147.0	146.9	146.8	146.6	146.4	146.1	145.4	144.9	144.3	143.7	143.4
80°	116.7	116.7	116.7	116.7	116.7	116.5	116.1	115.7	115.2	114.9	114.7
82.5°	90.0	89.7	89.3	89.0	88.7	88.5	88.4	88.4	88.3	88.2	87.8
85°	50.9	51.2	51.4	51.5	51.7	51.9	51.9	51.9	51.9	51.9	51.6
87.5°	20.1	20.2	20.4	20.6	20.8	21.0	20.9	21.0	20.9	20.9	21.0
90°	0.5	1.0	2.1	3.0	4.1	5.1	5.6	6.6	7.1	8.1	8.6
92.5°	6.2	7.5	11.8	18.1	26.8	41.7	69.5	116.1	166.7	164.0	132.8
95°	16.8	17.3	21.4	26.9	38.2	61.1	115.5	227.4	367.7	450.7	441.0
97.5°	27.9	28.4	31.3	36.9	47.0	63.5	99.5	181.5	328.4	481.3	558.0
100°	35.6	36.6	38.7	44.2	53.9	69.2	98.7	164.8	293.0	459.3	586.5
102.5°	44.1	44.8	46.4	52.4	61.3	76.1	102.4	157.9	266.1	420.6	569.4
105°	57.5	57.5	60.0	65.1	73.2	87.5	109.9	155.2	240.0	368.8	514.8
107.5°	70.5	71.5	73.9	78.1	86.6	99.4	121.1	159.8	229.1	333.1	459.1
110°	79.9	80.9	82.9	87.5	95.1	108.3	129.2	164.3	225.9	316.4	427.3



TEST NUMBER: P333222-940

CATALOG NUMBER: S125DIP-S850D590U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	89.3	90.2	91.8	96.5	104.1	116.9	137.0	170.0	225.9	306.7	403.7
115°	102.7	103.8	105.3	109.9	117.5	130.2	149.0	178.5	227.4	296.0	377.9
117.5°	114.9	116.5	118.2	122.7	131.3	143.7	161.5	188.3	230.7	290.9	362.6
120°	123.1	124.7	126.6	131.3	139.9	152.6	170.4	194.8	234.0	288.4	354.0
122.5°	131.6	132.8	134.4	138.9	148.5	161.1	179.0	202.2	236.8	286.4	346.7
125°	142.4	143.5	146.0	150.5	160.2	173.4	190.2	212.1	241.7	283.8	336.7
127.5°	150.9	152.4	155.7	161.5	171.7	184.9	201.1	221.2	247.0	282.6	327.6
130°	156.1	157.7	161.8	168.4	179.1	192.3	208.0	227.4	250.3	281.8	321.5
132.5°	160.2	162.2	167.0	174.5	185.6	198.8	214.5	232.6	254.0	281.8	316.6
135°	166.8	168.9	175.0	183.2	193.8	207.5	223.3	240.0	258.9	281.8	310.8
137.5°	175.2	176.7	182.4	190.6	201.0	215.2	229.5	245.6	263.5	282.4	305.6
140°	180.0	181.6	187.7	195.8	205.5	219.3	234.0	249.2	265.6	282.9	303.2
142.5°	185.7	186.9	192.6	200.7	210.0	222.9	236.8	251.3	266.7	283.2	301.1
145°	194.3	195.3	200.4	207.5	216.7	228.4	241.7	254.3	268.0	282.9	298.1
147.5°	203.2	203.8	208.2	214.8	222.7	233.1	244.7	256.2	268.6	281.5	294.9
150°	208.6	209.6	213.1	219.7	226.9	235.5	246.7	257.3	268.6	280.3	292.5
152.5°	214.3	214.8	218.0	223.8	230.5	238.4	248.7	258.2	268.1	278.7	289.6
155°	221.8	221.8	224.8	229.9	235.0	242.1	250.7	258.9	267.1	275.7	284.8
157.5°	228.5	228.4	230.9	235.2	239.7	245.0	252.5	259.4	265.7	272.6	280.4
160°	233.0	232.5	234.5	238.1	242.1	246.7	253.3	259.4	264.5	270.6	276.7
162.5°	236.7	236.1	238.2	241.3	244.6	248.3	254.1	259.0	263.3	268.1	273.5
165°	242.1	241.1	242.6	245.1	247.2	250.3	254.3	258.4	261.4	264.5	268.6
167.5°	245.8	245.3	246.2	247.6	249.1	250.9	254.3	257.2	258.6	260.9	263.8
170°	248.3	247.7	248.3	249.2	250.3	251.8	254.3	256.4	257.3	258.9	260.9
172.5°	249.9	249.0	249.4	250.5	251.1	251.8	254.0	255.6	255.7	256.5	258.1
175°	251.8	250.7	251.3	251.8	251.8	251.8	253.3	254.3	253.8	253.8	254.3
177.5°	252.7	251.9	251.9	252.3	251.9	251.9	252.7	253.1	252.3	252.3	252.7
180°	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3



TEST NUMBER: P333222-940

CATALOG NUMBER: S125DIP-S850D590U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5
2.5°	1167.2	1168.9	1170.5	1171.3	1171.1	1170.9	1170.7	1170.5
5°	1161.4	1163.1	1165.0	1165.8	1165.6	1165.5	1165.2	1165.0
7.5°	1149.6	1151.4	1153.2	1154.0	1153.8	1153.6	1153.3	1153.2
10°	1139.6	1141.3	1142.9	1143.6	1143.4	1143.2	1143.0	1142.8
12.5°	1126.3	1127.7	1129.0	1129.6	1129.6	1129.5	1129.5	1129.4
15°	1103.2	1104.2	1105.3	1105.7	1105.7	1105.7	1105.7	1105.7
17.5°	1076.3	1077.5	1078.8	1079.0	1077.9	1076.9	1075.8	1074.9
20°	1055.9	1057.3	1058.7	1058.9	1057.9	1056.9	1055.9	1054.8
22.5°	1032.6	1033.6	1034.6	1034.7	1033.9	1033.2	1032.5	1031.9
25°	995.4	995.9	996.3	996.1	995.6	995.0	994.3	993.7
27.5°	956.4	956.5	956.6	956.4	955.7	955.1	954.5	953.9
30°	928.1	927.6	927.2	926.8	926.1	925.5	924.9	924.3
32.5°	899.2	898.5	897.8	896.8	895.7	894.6	893.5	892.4
35°	854.6	853.5	852.6	851.2	849.5	847.9	846.2	844.6
37.5°	807.6	806.1	804.6	803.3	802.5	801.5	800.6	799.6
40°	775.2	773.3	771.4	770.2	769.5	769.0	768.4	767.8
42.5°	742.9	741.2	739.5	738.2	737.3	736.3	735.3	734.4
45°	695.2	692.7	690.3	688.7	688.1	687.5	686.9	686.3
47.5°	644.9	642.4	639.9	637.9	636.5	635.1	633.6	632.1
50°	610.5	607.8	605.1	603.1	601.6	600.2	598.8	597.4
52.5°	577.1	574.7	572.4	570.4	568.8	567.2	565.6	564.0
55°	525.1	523.3	521.4	519.8	518.3	516.8	515.4	514.0
57.5°	473.5	471.1	468.7	467.1	466.3	465.6	464.8	464.0
60°	438.5	436.5	434.4	432.7	431.2	429.8	428.4	427.0
62.5°	404.9	402.7	400.5	398.8	397.7	396.5	395.5	394.3
65°	352.0	350.1	348.2	346.9	346.1	345.3	344.4	343.6
67.5°	301.4	299.8	298.3	297.2	296.8	296.2	295.7	295.2
70°	268.0	266.7	265.5	264.5	263.6	262.8	262.0	261.2
72.5°	236.5	235.1	233.7	232.6	231.8	231.0	230.2	229.3
75°	187.7	187.1	186.5	185.7	184.9	184.0	183.2	182.4
77.5°	143.0	142.6	142.2	141.8	141.2	140.6	140.1	139.5
80°	114.4	114.2	114.0	113.7	113.3	112.9	112.4	112.1
82.5°	87.4	87.0	86.7	86.5	86.4	86.3	86.2	86.1
85°	51.5	51.3	51.0	50.7	50.3	49.9	49.5	49.0
87.5°	21.1	21.2	21.3	21.3	21.0	20.7	20.4	20.2
90°	9.2	9.6	10.2	11.1	11.1	11.1	11.7	11.7
92.5°	90.2	65.5	49.2	41.7	35.2	34.0	33.3	32.5
95°	365.7	288.4	225.9	183.2	147.0	131.7	127.7	119.6
97.5°	544.7	490.4	429.5	370.1	338.7	310.1	295.4	288.9
100°	625.6	600.7	548.3	495.4	460.3	423.7	404.9	396.7
102.5°	652.9	668.2	643.1	607.3	569.8	543.8	523.3	517.2
105°	636.9	706.5	728.9	723.3	707.0	690.3	680.1	674.0
107.5°	579.4	672.4	730.0	756.4	764.7	764.6	761.3	757.2
110°	537.2	633.8	705.5	748.8	771.6	781.3	784.9	784.9





TEST NUMBER: P333222-940

CATALOG NUMBER: S125DIP-S850D590U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	503.8	595.6	668.1	719.1	752.5	769.1	777.9	781.6
115°	461.8	540.7	610.4	665.8	705.5	730.0	744.1	750.8
117.5°	434.8	502.7	562.8	613.7	653.4	678.6	692.7	696.8
120°	420.2	481.2	537.2	581.9	619.6	644.0	657.7	661.7
122.5°	409.2	465.7	515.6	557.5	591.0	613.4	627.1	630.8
125°	393.2	445.1	489.4	525.9	554.5	575.3	586.5	591.6
127.5°	376.9	425.3	466.6	501.0	526.7	545.2	555.7	558.0
130°	366.8	411.5	451.2	484.2	509.7	526.5	536.6	539.7
132.5°	356.6	398.5	434.5	466.4	491.8	508.5	517.9	521.4
135°	343.3	378.4	411.0	440.0	462.4	479.1	488.3	491.3
137.5°	332.2	360.5	387.6	412.2	432.2	447.5	455.9	459.3
140°	326.0	350.0	373.4	394.8	413.6	426.8	434.4	436.9
142.5°	320.7	341.0	361.1	379.7	395.7	406.8	414.0	416.2
145°	313.9	329.6	345.4	359.1	371.3	380.0	385.6	387.6
147.5°	307.4	320.1	332.3	342.6	352.3	359.2	362.5	363.4
150°	303.6	314.9	324.5	333.7	341.3	347.4	349.5	350.0
152.5°	299.6	309.6	318.4	325.6	332.0	336.8	338.9	339.4
155°	293.5	301.7	308.7	314.3	319.4	323.0	324.5	325.0
157.5°	287.4	294.1	299.6	304.0	307.9	310.9	312.3	312.2
160°	283.3	288.4	293.5	297.0	300.6	303.2	304.2	303.6
162.5°	278.8	283.6	287.8	291.0	293.7	295.9	296.0	296.0
165°	272.6	276.2	279.3	281.8	283.8	284.8	284.8	284.8
167.5°	266.7	269.1	271.4	273.2	274.3	275.2	274.7	274.6
170°	263.5	265.0	266.5	267.5	268.6	269.1	269.1	268.6
172.5°	259.8	261.4	262.4	263.1	263.3	264.2	263.4	262.9
175°	255.8	255.8	256.9	256.9	256.9	257.3	256.4	255.8
177.5°	253.1	253.5	253.5	253.5	253.1	253.5	252.3	252.3
180°	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3

(END OF REPORT)