

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333225-940

Luminaire Tested: **S125DIP-S850D810U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333225-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S850D810U940-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5673.6 lumens
Efficiency: N/A
Efficacy: 123.6 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333225-940

CATALOG NUMBER: S125DIP-S850D810U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333225-940

CATALOG NUMBER: S125DIP-S850D810U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	87	92	88	85	82	76	73	71	64	62	61	53	52	51	46
2	90	83	77	72	84	77	72	67	66	63	59	57	54	51	47	45	43	39
3	83	73	66	60	76	68	62	57	59	54	50	50	47	43	42	39	37	33
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32	29
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	34	31	28	25
6	64	52	44	38	59	49	41	36	42	37	32	36	32	29	31	27	25	22
7	59	47	39	33	55	44	37	32	38	33	28	33	29	25	28	25	22	20
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	22	20	17
9	51	39	31	26	47	37	30	25	32	27	23	28	23	20	24	20	18	16
10	48	36	28	24	44	34	27	23	30	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7045	7045	7045	7045
5°	8159	7069	6190	7069
10°	9492	7033	5423	7033
15°	10508	6981	5003	6981
20°	11762	6899	4665	6899
25°	13779	6807	4501	6807
30°	14882	6716	4357	6716
35°	12236	6545	4264	6545
40°	8697	6308	4161	6308
45°	6682	5989	4103	5989
50°	5704	5591	4093	5591
55°	5078	5203	4130	5203
60°	4580	4779	4234	4779
65°	4232	4351	4345	4351
70°	3848	3909	4407	3909
75°	3399	3441	4367	3441
80°	2860	2804	3998	2804
85°	2267	2023	3223	2023



TEST NUMBER: P333225-940

CATALOG NUMBER: S125DIP-S850D810U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.0	1.9
10°-20°	312.7	5.5
20°-30°	507.7	8.9
30°-40°	619.3	10.9
40°-50°	563.4	9.9
50°-60°	448.8	7.9
60°-70°	312.6	5.5
70°-80°	166.7	2.9
80°-90°	44.0	0.8
90°-100°	250.7	4.4
100°-110°	538.9	9.5
110°-120°	505.7	8.9
120°-130°	409.8	7.2
130°-140°	328.9	5.8
140°-150°	248.2	4.4
150°-160°	174.7	3.1
160°-170°	103.0	1.8
170°-180°	33.5	0.6
0°-30°	925.4	16.3
0°-40°	1544.8	27.2
0°-60°	2556.9	45.1
0°-90°	3080.2	54.3
90°-120°	1295.2	22.8
90°-150°	2282.2	40.2
90°-180°	2593.0	45.7
0°-180°	5673.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1091	1091	1091	1091	1091	
5°	1258	1090	955	1090	1258	127
15°	1572	1044	748	1044	1572	450
25°	1934	955	632	955	1934	883
35°	1552	830	541	830	1552	950
45°	732	656	449	656	732	586
55°	451	462	367	462	451	406
65°	277	285	284	285	277	275
75°	136	138	175	138	136	147
85°	31	27	44	27	31	36
90°	16	1	16	1	16	12
95°	164	23	164	23	164	232
105°	924	79	924	79	924	918
115°	1029	141	1029	141	1029	1005
125°	811	195	811	195	811	734
135°	674	229	674	229	674	522
145°	531	266	531	266	531	338
155°	446	304	446	304	446	208
165°	390	332	390	332	390	112
175°	351	345	351	345	351	34
180°	346	346	346	346	346	



TEST NUMBER: P333225-940

CATALOG NUMBER: S125DIP-S850D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	1153.9	1152.4	1150.9	1147.9	1150.1	1143.9	1140.9	1135.7	1129.4	1127.2	1124.6
5°	1258.5	1260.8	1263.1	1253.4	1254.4	1247.9	1233.1	1221.0	1211.3	1198.8	1190.0
7.5°	1384.5	1378.9	1378.5	1372.3	1361.4	1352.7	1337.1	1317.3	1298.2	1276.3	1258.2
10°	1447.4	1447.9	1443.7	1436.3	1424.8	1416.4	1396.1	1376.5	1353.0	1325.2	1305.3
12.5°	1494.9	1496.7	1491.5	1481.5	1475.9	1457.1	1441.2	1418.1	1390.0	1367.8	1337.5
15°	1571.6	1566.4	1562.7	1550.2	1540.5	1521.1	1495.6	1471.5	1440.9	1412.6	1384.5
17.5°	1645.4	1649.5	1642.5	1631.1	1601.0	1578.2	1544.1	1511.1	1473.1	1435.2	1401.5
20°	1711.4	1715.0	1704.4	1684.5	1648.4	1625.7	1580.7	1538.2	1494.2	1445.6	1408.5
22.5°	1793.6	1790.6	1776.3	1746.0	1714.7	1672.8	1624.1	1572.3	1517.2	1462.2	1413.0
25°	1933.6	1914.1	1905.3	1867.9	1826.7	1765.1	1698.4	1622.5	1553.9	1481.2	1418.3
27.5°	2011.2	2005.1	1995.3	1969.2	1925.8	1860.0	1781.4	1688.8	1592.1	1500.4	1418.0
30°	1995.6	1996.5	1997.5	1989.1	1961.4	1911.8	1833.6	1734.0	1619.2	1515.9	1420.6
32.5°	1857.9	1874.7	1890.8	1909.9	1917.6	1908.2	1859.1	1769.2	1651.1	1533.7	1419.1
35°	1552.0	1557.2	1609.4	1661.3	1731.7	1786.4	1822.9	1783.2	1683.6	1548.8	1417.3
37.5°	1210.1	1235.2	1271.4	1330.0	1431.6	1522.5	1639.5	1693.3	1661.2	1553.7	1414.1
40°	1031.6	1054.8	1078.3	1138.1	1223.8	1334.0	1466.9	1580.3	1606.7	1538.2	1402.9
42.5°	893.9	912.1	938.3	983.3	1054.9	1152.4	1279.4	1427.7	1518.9	1493.0	1379.7
45°	731.6	743.2	763.6	799.2	851.0	927.5	1039.5	1201.6	1342.7	1389.6	1324.3
47.5°	626.2	626.1	641.9	666.6	704.0	768.9	851.8	978.7	1129.6	1241.2	1236.0
50°	567.7	565.3	577.8	599.1	628.7	671.8	751.0	852.4	997.4	1123.7	1159.0
52.5°	517.3	517.5	525.2	541.0	565.8	602.6	661.7	753.1	877.0	1006.7	1073.0
55°	451.0	449.2	457.9	468.6	486.6	510.7	553.3	623.2	723.7	851.5	937.6
57.5°	390.2	395.3	398.9	406.3	421.2	437.4	473.3	524.6	604.3	714.0	805.0
60°	354.6	359.8	362.6	370.0	382.0	395.9	423.7	465.4	532.4	627.0	717.2
62.5°	322.8	326.8	327.7	334.4	344.2	357.8	379.6	414.6	467.6	550.3	638.7
65°	276.9	276.9	278.7	285.7	290.3	302.4	319.1	344.5	387.1	451.5	526.9
67.5°	232.6	234.9	234.3	237.5	241.7	251.0	263.0	284.0	315.6	362.6	422.9
70°	203.8	205.5	205.1	207.4	212.0	218.1	227.8	247.7	270.4	310.7	362.6
72.5°	177.8	178.5	177.4	180.4	183.2	188.4	199.3	209.9	231.1	265.1	307.7
75°	136.2	137.1	137.9	139.8	142.6	145.3	151.0	161.6	175.5	201.0	228.3
77.5°	102.0	100.3	102.5	102.3	103.8	105.9	110.8	116.5	127.9	144.0	165.1
80°	76.9	77.3	77.3	77.8	80.1	81.5	85.7	89.8	98.6	110.7	125.5
82.5°	56.1	57.3	56.6	57.4	59.4	60.4	62.7	66.1	71.2	80.7	91.4
85°	30.6	28.3	29.2	30.1	30.1	30.6	32.4	33.8	36.6	40.3	44.4
87.5°	12.1	12.8	13.1	13.1	13.5	13.2	14.5	14.4	15.3	16.3	17.5
90°	16.1	16.1	15.3	15.3	15.3	13.9	13.3	12.6	11.9	11.1	9.7
92.5°	44.5	45.6	46.5	48.2	57.2	67.5	89.7	123.6	182.0	224.8	228.4
95°	163.8	175.0	180.6	201.5	251.0	309.6	395.3	501.3	604.5	617.8	504.1
97.5°	396.0	404.9	425.2	464.2	507.3	588.7	672.3	746.6	764.8	659.7	450.1
100°	543.9	555.0	580.8	631.0	679.1	751.6	823.4	857.6	803.9	629.6	401.6
102.5°	708.9	717.3	745.3	781.0	832.5	881.5	916.1	894.9	780.5	576.6	364.8
105°	923.8	932.2	946.1	969.1	991.5	999.2	968.5	872.9	705.6	505.5	329.1
107.5°	1037.9	1043.5	1048.0	1048.2	1036.9	1000.5	921.8	794.2	629.2	456.6	314.1
110°	1075.8	1075.8	1070.9	1057.7	1026.3	967.1	868.7	736.3	585.7	433.6	309.6



TEST NUMBER: P333225-940

CATALOG NUMBER: S125DIP-S850D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1071.4	1066.3	1054.2	1031.4	985.6	915.7	816.3	690.5	553.3	420.3	309.6
115°	1029.1	1020.0	1000.5	967.1	912.7	836.7	741.2	633.1	518.0	405.8	311.7
117.5°	955.0	949.5	930.1	895.5	841.2	771.4	689.1	596.0	497.0	398.7	316.3
120°	907.0	901.5	882.7	849.2	797.6	736.3	659.6	575.9	485.3	395.3	320.7
122.5°	864.7	859.7	840.9	810.2	764.2	706.7	638.4	560.9	475.2	392.5	324.6
125°	810.8	803.9	788.5	760.0	720.9	670.7	610.1	539.0	461.5	389.1	331.2
127.5°	764.8	761.8	747.3	722.0	686.6	639.6	583.0	516.7	449.0	387.4	338.6
130°	739.8	735.6	721.7	698.7	663.8	618.4	564.1	502.7	440.7	386.3	343.0
132.5°	714.6	709.9	697.1	674.0	639.2	595.6	546.2	488.7	434.0	386.3	348.0
135°	673.5	669.3	656.7	633.7	603.1	563.4	518.7	470.6	426.0	386.3	354.9
137.5°	629.6	625.0	613.4	592.5	565.0	531.3	494.2	455.3	418.9	387.1	361.1
140°	598.9	595.4	585.0	566.9	541.0	511.8	479.7	446.9	415.5	387.6	363.9
142.5°	570.4	567.6	557.7	542.3	520.4	495.0	467.4	439.7	412.8	388.3	365.6
145°	531.3	528.5	520.8	509.0	492.2	473.4	451.8	430.2	408.6	387.6	367.5
147.5°	498.1	496.9	492.4	482.9	469.7	455.4	438.8	421.2	404.2	385.8	368.1
150°	479.7	479.0	476.2	467.9	457.4	444.8	431.6	416.3	400.9	384.1	368.1
152.5°	465.2	464.5	461.7	455.0	446.2	436.5	424.4	410.6	397.0	381.9	367.6
155°	445.5	444.8	442.7	437.8	430.9	423.2	413.5	402.3	390.5	377.9	366.0
157.5°	427.9	428.1	426.1	422.1	416.7	410.6	403.1	394.0	384.3	373.7	364.3
160°	416.3	417.0	415.5	412.1	407.2	402.3	395.3	388.3	379.3	371.0	362.6
162.5°	405.6	405.8	405.5	402.6	398.8	394.5	388.6	382.2	374.8	367.6	360.9
165°	390.5	390.5	390.5	389.1	386.3	382.8	378.6	373.7	368.1	362.6	358.4
167.5°	376.5	376.7	377.2	375.9	374.5	372.0	368.8	365.6	361.6	357.7	354.5
170°	368.1	368.8	368.8	368.1	366.8	365.3	363.3	361.1	357.7	354.9	352.8
172.5°	360.3	361.1	362.1	360.9	360.6	359.8	358.2	356.1	353.7	351.5	350.5
175°	350.7	351.4	352.8	352.1	352.1	352.1	350.7	350.7	348.6	347.9	347.9
177.5°	345.8	345.8	347.5	347.0	347.5	347.5	347.5	347.0	346.3	345.8	345.8
180°	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8



TEST NUMBER: P333225-940

CATALOG NUMBER: S125DIP-S850D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	1122.4	1119.8	1116.8	1111.6	1105.4	1102.0	1096.8	1093.5	1086.8	1081.3	1075.3
5°	1179.3	1167.2	1156.2	1141.8	1126.1	1115.9	1103.8	1090.4	1076.6	1062.2	1046.4
7.5°	1238.3	1217.0	1193.8	1168.9	1144.6	1122.2	1100.8	1079.8	1060.2	1036.4	1016.4
10°	1277.9	1251.1	1222.4	1188.6	1155.7	1127.0	1097.9	1072.4	1046.4	1018.7	994.1
12.5°	1317.6	1281.8	1241.3	1204.2	1164.6	1130.0	1095.6	1063.1	1030.6	999.8	971.2
15°	1345.6	1314.0	1276.6	1223.8	1179.3	1131.7	1086.3	1044.1	1004.8	970.5	934.4
17.5°	1364.0	1323.4	1283.2	1232.5	1174.2	1120.9	1069.5	1021.3	976.9	933.4	898.7
20°	1367.3	1325.6	1283.5	1233.9	1174.2	1113.1	1061.8	1003.8	956.2	911.2	868.6
22.5°	1366.2	1319.0	1273.1	1222.1	1163.9	1107.6	1045.4	986.4	934.7	890.5	846.1
25°	1355.8	1305.3	1247.9	1196.5	1139.1	1079.3	1016.4	955.2	902.4	851.9	808.0
27.5°	1347.0	1281.6	1216.6	1156.6	1101.2	1046.4	986.1	923.5	865.0	813.9	772.4
30°	1336.3	1264.5	1191.3	1128.8	1071.9	1018.7	961.7	900.6	839.5	789.4	745.0
32.5°	1326.7	1243.0	1165.8	1097.8	1037.4	985.7	933.2	875.0	815.0	764.3	719.8
35°	1308.1	1211.3	1122.8	1046.0	981.6	928.4	884.4	830.2	775.1	726.0	683.4
37.5°	1284.4	1169.6	1074.7	994.1	923.5	867.5	826.5	784.9	732.0	684.7	646.2
40°	1265.9	1140.0	1039.5	957.1	884.0	825.5	787.6	748.2	704.3	660.3	619.6
42.5°	1242.6	1113.3	1004.0	915.3	842.8	786.0	746.1	712.7	673.9	632.8	595.0
45°	1199.7	1065.0	946.5	851.0	777.8	721.8	680.6	655.7	626.5	587.5	555.6
47.5°	1136.7	1006.9	884.3	785.9	710.3	658.4	619.8	595.8	575.2	546.4	517.4
50°	1080.7	963.6	839.5	741.7	666.3	613.9	578.4	556.5	539.0	516.7	492.2
52.5°	1018.1	909.1	795.4	698.8	624.1	572.5	537.6	518.4	503.8	487.9	463.7
55°	918.6	826.1	720.5	628.7	559.8	509.3	478.8	462.1	450.0	438.0	423.2
57.5°	809.0	736.6	643.1	559.4	495.8	449.9	421.3	405.1	395.8	389.6	380.8
60°	732.0	670.0	589.4	513.0	451.0	410.3	382.5	370.0	362.1	357.0	350.5
62.5°	660.6	609.7	534.9	465.2	411.0	372.5	347.7	335.6	328.0	325.5	320.1
65°	555.2	515.9	454.2	396.4	350.1	317.2	296.3	284.7	280.1	277.3	277.9
67.5°	451.4	427.4	377.9	328.6	291.6	264.0	247.4	238.4	236.1	232.5	232.4
70°	388.0	370.0	328.3	285.3	252.4	231.0	216.2	207.0	204.6	202.8	202.3
72.5°	332.1	316.3	280.1	245.6	216.1	197.3	185.1	179.6	175.8	174.7	174.6
75°	249.6	240.8	212.0	184.8	164.3	151.4	143.1	137.9	135.2	134.7	135.2
77.5°	177.5	169.8	151.5	132.2	119.3	109.5	102.5	100.7	97.6	97.6	97.1
80°	133.3	128.2	116.7	101.4	90.8	82.4	78.7	75.4	74.5	73.1	74.5
82.5°	96.7	91.2	83.4	73.7	64.8	59.8	56.1	55.1	54.6	53.9	54.2
85°	47.7	48.2	43.5	36.1	32.4	29.6	27.3	27.3	26.8	26.4	26.8
87.5°	18.1	17.1	15.4	14.1	11.9	10.5	9.9	10.2	9.2	9.1	9.7
90°	9.1	7.7	7.0	5.6	4.2	2.8	1.4	0.7	1.4	2.8	4.2
92.5°	159.1	95.2	57.2	36.8	24.8	16.1	10.3	8.5	10.3	16.1	24.8
95°	311.7	158.3	83.6	52.3	36.9	29.2	23.7	23.0	23.7	29.2	36.9
97.5°	248.8	136.3	87.0	64.4	50.6	43.0	39.1	38.2	39.1	43.0	50.6
100°	225.9	135.3	94.8	73.9	60.6	53.0	50.2	48.8	50.2	53.0	60.6
102.5°	216.4	140.3	104.3	83.9	71.8	63.6	61.3	60.5	61.3	63.6	71.8
105°	212.7	150.6	119.9	100.4	89.3	82.3	78.8	78.8	78.8	82.3	89.3
107.5°	219.1	165.9	136.3	118.7	107.1	101.4	98.0	96.7	98.0	101.4	107.1
110°	225.2	177.1	148.5	130.4	119.9	113.6	110.8	109.5	110.8	113.6	119.9



TEST NUMBER: P333225-940

CATALOG NUMBER: S125DIP-S850D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	233.0	187.7	160.2	142.7	132.2	125.9	123.7	122.3	123.7	125.9	132.2
115°	244.7	204.3	178.5	161.0	150.6	144.4	142.2	140.8	142.2	144.4	150.6
117.5°	258.2	221.3	196.9	180.0	168.2	161.9	159.7	157.6	159.7	161.9	168.2
120°	267.1	233.5	209.2	191.7	179.9	173.6	170.9	168.7	170.9	173.6	179.9
122.5°	277.1	245.3	220.9	203.5	190.5	184.2	182.0	180.5	182.0	184.2	190.5
125°	290.7	260.7	237.7	219.6	206.3	200.1	196.6	195.2	196.6	200.1	206.3
127.5°	303.3	275.7	253.5	235.4	221.3	213.4	208.9	206.8	208.9	213.4	221.3
130°	311.7	285.2	263.6	245.4	230.8	221.7	216.2	214.0	216.2	221.7	230.8
132.5°	318.9	294.1	272.5	254.3	239.2	229.0	222.3	219.6	222.3	229.0	239.2
135°	329.1	306.1	284.5	265.6	251.0	239.9	231.5	228.7	231.5	239.9	251.0
137.5°	336.6	314.6	294.9	275.5	261.2	250.0	242.2	240.1	242.2	250.0	261.2
140°	341.6	320.7	300.5	281.7	268.4	257.3	248.9	246.8	248.9	257.3	268.4
142.5°	344.5	324.6	305.5	287.8	275.1	263.9	256.2	254.6	256.2	263.9	275.1
145°	348.6	331.2	313.1	297.0	284.5	274.7	267.7	266.4	267.7	274.7	284.5
147.5°	351.2	335.4	319.5	305.4	294.5	285.4	279.5	278.6	279.5	285.4	294.5
150°	352.8	338.1	322.8	310.9	301.2	292.1	287.2	285.9	287.2	292.1	301.2
152.5°	353.9	340.9	326.7	316.0	306.7	298.8	294.5	293.6	294.5	298.8	306.7
155°	354.9	343.8	331.9	322.1	315.1	308.2	304.0	304.0	304.0	308.2	315.1
157.5°	355.6	346.1	335.9	328.5	322.4	316.4	313.1	313.2	313.1	316.4	322.4
160°	355.6	347.2	338.1	331.9	326.3	321.5	318.6	319.3	318.6	321.5	326.3
162.5°	355.0	348.3	340.4	335.2	330.7	326.5	323.7	324.3	323.7	326.5	330.7
165°	354.2	348.6	343.0	338.9	336.1	332.6	330.5	331.9	330.5	332.6	336.1
167.5°	352.5	348.6	344.0	341.3	339.4	337.4	336.2	336.9	336.2	337.4	339.4
170°	351.4	348.6	345.1	343.0	341.6	340.3	339.6	340.3	339.6	340.3	341.6
172.5°	350.3	348.0	345.1	344.1	343.3	341.9	341.3	342.5	341.3	341.9	343.3
175°	348.6	347.2	345.1	345.1	345.1	344.5	343.8	345.1	343.8	344.5	345.1
177.5°	347.0	346.3	345.3	345.3	345.8	345.3	345.3	346.3	345.3	345.3	345.8
180°	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8



TEST NUMBER: P333225-940

CATALOG NUMBER: S125DIP-S850D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	1072.0	1067.9	1064.6	1057.2	1053.1	1047.6	1043.1	1047.9	1042.8	1045.0	1041.6
5°	1038.6	1025.6	1016.4	1002.9	991.3	980.7	972.9	971.4	967.7	965.9	960.3
7.5°	998.4	982.1	966.3	948.7	933.8	918.7	909.1	901.2	895.9	888.9	884.2
10°	974.6	952.9	934.4	913.1	894.6	878.3	865.4	858.9	852.9	844.1	840.9
12.5°	945.4	922.9	900.3	877.5	859.8	841.7	830.5	820.7	816.6	806.6	805.7
15°	910.3	876.6	854.3	831.2	806.6	791.8	782.5	771.9	767.2	760.3	755.2
17.5°	868.4	838.3	810.5	786.5	765.4	753.0	741.5	734.1	726.2	721.7	713.4
20°	838.1	809.4	781.6	756.1	739.9	725.6	716.3	709.4	701.1	698.7	690.4
22.5°	812.5	780.9	754.2	732.8	715.1	698.9	688.8	684.2	678.4	671.3	669.6
25°	771.0	738.1	715.4	694.1	678.3	663.5	656.6	650.6	645.0	639.9	638.0
27.5°	735.0	705.6	678.7	659.4	645.8	632.2	626.1	618.8	614.7	610.6	605.6
30°	709.8	679.8	656.1	637.6	622.8	610.7	604.2	599.1	595.5	591.7	589.0
32.5°	683.9	656.0	633.1	615.0	600.2	591.1	585.3	581.8	577.7	573.2	569.7
35°	649.6	619.0	596.8	581.1	569.5	562.6	556.1	552.9	548.2	548.2	544.5
37.5°	611.0	584.6	565.0	550.6	540.3	534.0	527.0	524.8	521.8	519.9	518.6
40°	588.1	563.5	545.0	530.7	519.5	514.4	508.9	505.2	503.3	501.0	500.1
42.5°	564.4	540.9	523.2	509.9	500.2	495.9	490.7	488.1	484.4	481.3	480.8
45°	528.3	505.6	489.5	478.8	470.5	465.4	462.1	456.6	454.7	451.0	450.5
47.5°	494.1	472.3	456.5	447.7	440.4	436.2	431.1	425.6	423.5	421.6	421.4
50°	468.6	448.7	433.8	425.5	418.6	412.6	407.4	403.8	402.3	402.3	403.3
52.5°	442.6	425.7	413.1	403.0	396.4	389.9	385.2	383.0	380.8	383.1	384.8
55°	404.7	387.5	378.3	368.5	362.1	354.6	352.4	351.4	350.1	353.7	355.6
57.5°	364.5	352.5	341.6	332.0	326.2	321.9	318.8	318.2	320.7	322.5	328.6
60°	338.9	325.0	315.3	307.9	301.0	298.2	297.3	296.3	298.2	303.3	311.1
62.5°	310.8	299.5	289.0	283.5	278.4	273.8	273.6	274.1	277.9	283.7	291.5
65°	269.5	259.8	252.8	246.3	242.2	239.4	240.3	242.2	246.3	254.2	263.0
67.5°	227.6	220.9	214.6	209.4	205.4	205.4	206.3	209.1	214.0	223.1	231.1
70°	200.5	193.1	188.0	185.7	182.4	180.6	183.3	188.0	192.2	200.5	207.4
72.5°	173.4	167.2	163.2	161.6	160.2	158.7	159.6	164.6	170.3	178.6	186.7
75°	133.3	131.0	128.2	126.4	125.0	125.9	126.9	131.5	136.2	144.9	154.2
77.5°	97.3	94.9	93.3	92.8	92.0	92.5	95.1	98.5	103.1	109.5	116.5
80°	73.7	72.7	71.8	71.3	71.3	71.8	75.4	77.8	81.9	88.0	93.5
82.5°	53.6	53.1	52.9	52.8	53.1	53.2	55.5	58.5	62.0	66.5	71.3
85°	28.3	27.3	28.7	29.2	28.3	29.6	30.6	32.4	33.8	36.1	38.4
87.5°	10.3	11.4	11.1	11.8	11.9	12.9	12.8	14.4	15.2	16.1	16.1
90°	5.6	7.0	7.7	9.1	9.7	11.1	11.9	12.6	13.3	13.9	15.3
92.5°	36.8	57.2	95.2	159.1	228.4	224.8	182.0	123.6	89.7	67.5	57.2
95°	52.3	83.6	158.3	311.7	504.1	617.8	604.5	501.3	395.3	309.6	251.0
97.5°	64.4	87.0	136.3	248.8	450.1	659.7	764.8	746.6	672.3	588.7	507.3
100°	73.9	94.8	135.3	225.9	401.6	629.6	803.9	857.6	823.4	751.6	679.1
102.5°	83.9	104.3	140.3	216.4	364.8	576.6	780.5	894.9	916.1	881.5	832.5
105°	100.4	119.9	150.6	212.7	329.1	505.5	705.6	872.9	968.5	999.2	991.5
107.5°	118.7	136.3	165.9	219.1	314.1	456.6	629.2	794.2	921.8	1000.5	1036.9
110°	130.4	148.5	177.1	225.2	309.6	433.6	585.7	736.3	868.7	967.1	1026.3



TEST NUMBER: P333225-940

CATALOG NUMBER: S125DIP-S850D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	142.7	160.2	187.7	233.0	309.6	420.3	553.3	690.5	816.3	915.7	985.6
115°	161.0	178.5	204.3	244.7	311.7	405.8	518.0	633.1	741.2	836.7	912.7
117.5°	180.0	196.9	221.3	258.2	316.3	398.7	497.0	596.0	689.1	771.4	841.2
120°	191.7	209.2	233.5	267.1	320.7	395.3	485.3	575.9	659.6	736.3	797.6
122.5°	203.5	220.9	245.3	277.1	324.6	392.5	475.2	560.9	638.4	706.7	764.2
125°	219.6	237.7	260.7	290.7	331.2	389.1	461.5	539.0	610.1	670.7	720.9
127.5°	235.4	253.5	275.7	303.3	338.6	387.4	449.0	516.7	583.0	639.6	686.6
130°	245.4	263.6	285.2	311.7	343.0	386.3	440.7	502.7	564.1	618.4	663.8
132.5°	254.3	272.5	294.1	318.9	348.0	386.3	434.0	488.7	546.2	595.6	639.2
135°	265.6	284.5	306.1	329.1	354.9	386.3	426.0	470.6	518.7	563.4	603.1
137.5°	275.5	294.9	314.6	336.6	361.1	387.1	418.9	455.3	494.2	531.3	565.0
140°	281.7	300.5	320.7	341.6	363.9	387.6	415.5	446.9	479.7	511.8	541.0
142.5°	287.8	305.5	324.6	344.5	365.6	388.3	412.8	439.7	467.4	495.0	520.4
145°	297.0	313.1	331.2	348.6	367.5	387.6	408.6	430.2	451.8	473.4	492.2
147.5°	305.4	319.5	335.4	351.2	368.1	385.8	404.2	421.2	438.8	455.4	469.7
150°	310.9	322.8	338.1	352.8	368.1	384.1	400.9	416.3	431.6	444.8	457.4
152.5°	316.0	326.7	340.9	353.9	367.6	381.9	397.0	410.6	424.4	436.5	446.2
155°	322.1	331.9	343.8	354.9	366.0	377.9	390.5	402.3	413.5	423.2	430.9
157.5°	328.5	335.9	346.1	355.6	364.3	373.7	384.3	394.0	403.1	410.6	416.7
160°	331.9	338.1	347.2	355.6	362.6	371.0	379.3	388.3	395.3	402.3	407.2
162.5°	335.2	340.4	348.3	355.0	360.9	367.6	374.8	382.2	388.6	394.5	398.8
165°	338.9	343.0	348.6	354.2	358.4	362.6	368.1	373.7	378.6	382.8	386.3
167.5°	341.3	344.0	348.6	352.5	354.5	357.7	361.6	365.6	368.8	372.0	374.5
170°	343.0	345.1	348.6	351.4	352.8	354.9	357.7	361.1	363.3	365.3	366.8
172.5°	344.1	345.1	348.0	350.3	350.5	351.5	353.7	356.1	358.2	359.8	360.6
175°	345.1	345.1	347.2	348.6	347.9	347.9	348.6	350.7	350.7	352.1	352.1
177.5°	345.3	345.3	346.3	347.0	345.8	345.8	346.3	347.0	347.5	347.5	347.5
180°	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8



TEST NUMBER: P333225-940

CATALOG NUMBER: S125DIP-S850D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	1039.4	1042.0	1039.7	1042.8	1039.7	1042.0	1039.4	1041.6	1045.0	1042.8	1047.9
5°	958.0	953.9	956.6	954.8	956.6	953.9	958.0	960.3	965.9	967.7	971.4
7.5°	882.8	878.8	874.3	872.2	874.3	878.8	882.8	884.2	888.9	895.9	901.2
10°	835.8	830.6	830.2	827.0	830.2	830.6	835.8	840.9	844.1	852.9	858.9
12.5°	801.3	796.6	791.3	790.0	791.3	796.6	801.3	805.7	806.6	816.6	820.7
15°	752.4	748.7	745.5	748.2	745.5	748.7	752.4	755.2	760.3	767.2	771.9
17.5°	711.8	708.7	708.1	704.7	708.1	708.7	711.8	713.4	721.7	726.2	734.1
20°	686.2	683.9	684.8	678.8	684.8	683.9	686.2	690.4	698.7	701.1	709.4
22.5°	665.8	661.3	660.8	659.5	660.8	661.3	665.8	669.6	671.3	678.4	684.2
25°	633.9	631.6	629.3	631.6	629.3	631.6	633.9	638.0	639.9	645.0	650.6
27.5°	606.0	603.2	602.6	602.9	602.6	603.2	606.0	605.6	610.6	614.7	618.8
30°	589.0	584.3	584.8	584.3	584.8	584.3	589.0	589.0	591.7	595.5	599.1
32.5°	570.4	567.3	566.7	565.8	566.7	567.3	570.4	569.7	573.2	577.7	581.8
35°	543.1	543.1	540.8	540.8	540.8	543.1	543.1	544.5	548.2	548.2	552.9
37.5°	517.5	517.0	515.6	515.9	515.6	517.0	517.5	518.6	519.9	521.8	524.8
40°	498.2	497.8	496.3	493.6	496.3	497.8	498.2	500.1	501.0	503.3	505.2
42.5°	479.7	478.1	477.5	476.5	477.5	478.1	479.7	480.8	481.3	484.4	488.1
45°	450.5	450.5	449.6	449.2	449.6	450.5	450.5	450.5	451.0	454.7	456.6
47.5°	422.2	423.0	424.8	424.5	424.8	423.0	422.2	421.4	421.6	423.5	425.6
50°	405.1	405.6	407.0	407.4	407.0	405.6	405.1	403.3	402.3	402.3	403.8
52.5°	386.3	389.0	390.7	390.4	390.7	389.0	386.3	384.8	383.1	380.8	383.0
55°	359.8	363.0	366.2	366.8	366.2	363.0	359.8	355.6	353.7	350.1	351.4
57.5°	333.6	338.1	341.5	342.6	341.5	338.1	333.6	328.6	322.5	320.7	318.2
60°	315.8	321.8	326.0	327.8	326.0	321.8	315.8	311.1	303.3	298.2	296.3
62.5°	298.7	305.5	309.7	310.0	309.7	305.5	298.7	291.5	283.7	277.9	274.1
65°	270.9	277.9	281.5	284.3	281.5	277.9	270.9	263.0	254.2	246.3	242.2
67.5°	240.9	247.8	251.9	254.1	251.9	247.8	240.9	231.1	223.1	214.0	209.1
70°	219.0	226.0	231.5	233.4	231.5	226.0	219.0	207.4	200.5	192.2	188.0
72.5°	197.5	203.8	208.2	210.4	208.2	203.8	197.5	186.7	178.6	170.3	164.6
75°	160.2	168.5	172.7	175.0	172.7	168.5	160.2	154.2	144.9	136.2	131.5
77.5°	123.5	131.2	133.7	134.8	133.7	131.2	123.5	116.5	109.5	103.1	98.5
80°	99.1	103.7	106.9	107.5	106.9	103.7	99.1	93.5	88.0	81.9	77.8
82.5°	76.2	80.0	81.1	82.2	81.1	80.0	76.2	71.3	66.5	62.0	58.5
85°	41.6	43.5	44.0	43.5	44.0	43.5	41.6	38.4	36.1	33.8	32.4
87.5°	16.8	16.4	16.6	17.3	16.6	16.4	16.8	16.1	16.1	15.2	14.4
90°	15.3	15.3	16.1	16.1	16.1	15.3	15.3	15.3	13.9	13.3	12.6
92.5°	48.2	46.5	45.6	44.5	45.6	46.5	48.2	57.2	67.5	89.7	123.6
95°	201.5	180.6	175.0	163.8	175.0	180.6	201.5	251.0	309.6	395.3	501.3
97.5°	464.2	425.2	404.9	396.0	404.9	425.2	464.2	507.3	588.7	672.3	746.6
100°	631.0	580.8	555.0	543.9	555.0	580.8	631.0	679.1	751.6	823.4	857.6
102.5°	781.0	745.3	717.3	708.9	717.3	745.3	781.0	832.5	881.5	916.1	894.9
105°	969.1	946.1	932.2	923.8	932.2	946.1	969.1	991.5	999.2	968.5	872.9
107.5°	1048.2	1048.0	1043.5	1037.9	1043.5	1048.0	1048.2	1036.9	1000.5	921.8	794.2
110°	1057.7	1070.9	1075.8	1075.8	1075.8	1070.9	1057.7	1026.3	967.1	868.7	736.3



TEST NUMBER: P333225-940

CATALOG NUMBER: S125DIP-S850D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1031.4	1054.2	1066.3	1071.4	1066.3	1054.2	1031.4	985.6	915.7	816.3	690.5
115°	967.1	1000.5	1020.0	1029.1	1020.0	1000.5	967.1	912.7	836.7	741.2	633.1
117.5°	895.5	930.1	949.5	955.0	949.5	930.1	895.5	841.2	771.4	689.1	596.0
120°	849.2	882.7	901.5	907.0	901.5	882.7	849.2	797.6	736.3	659.6	575.9
122.5°	810.2	840.9	859.7	864.7	859.7	840.9	810.2	764.2	706.7	638.4	560.9
125°	760.0	788.5	803.9	810.8	803.9	788.5	760.0	720.9	670.7	610.1	539.0
127.5°	722.0	747.3	761.8	764.8	761.8	747.3	722.0	686.6	639.6	583.0	516.7
130°	698.7	721.7	735.6	739.8	735.6	721.7	698.7	663.8	618.4	564.1	502.7
132.5°	674.0	697.1	709.9	714.6	709.9	697.1	674.0	639.2	595.6	546.2	488.7
135°	633.7	656.7	669.3	673.5	669.3	656.7	633.7	603.1	563.4	518.7	470.6
137.5°	592.5	613.4	625.0	629.6	625.0	613.4	592.5	565.0	531.3	494.2	455.3
140°	566.9	585.0	595.4	598.9	595.4	585.0	566.9	541.0	511.8	479.7	446.9
142.5°	542.3	557.7	567.6	570.4	567.6	557.7	542.3	520.4	495.0	467.4	439.7
145°	509.0	520.8	528.5	531.3	528.5	520.8	509.0	492.2	473.4	451.8	430.2
147.5°	482.9	492.4	496.9	498.1	496.9	492.4	482.9	469.7	455.4	438.8	421.2
150°	467.9	476.2	479.0	479.7	479.0	476.2	467.9	457.4	444.8	431.6	416.3
152.5°	455.0	461.7	464.5	465.2	464.5	461.7	455.0	446.2	436.5	424.4	410.6
155°	437.8	442.7	444.8	445.5	444.8	442.7	437.8	430.9	423.2	413.5	402.3
157.5°	422.1	426.1	428.1	427.9	428.1	426.1	422.1	416.7	410.6	403.1	394.0
160°	412.1	415.5	417.0	416.3	417.0	415.5	412.1	407.2	402.3	395.3	388.3
162.5°	402.6	405.5	405.8	405.6	405.8	405.5	402.6	398.8	394.5	388.6	382.2
165°	389.1	390.5	390.5	390.5	390.5	390.5	389.1	386.3	382.8	378.6	373.7
167.5°	375.9	377.2	376.7	376.5	376.7	377.2	375.9	374.5	372.0	368.8	365.6
170°	368.1	368.8	368.8	368.1	368.8	368.8	368.1	366.8	365.3	363.3	361.1
172.5°	360.9	362.1	361.1	360.3	361.1	362.1	360.9	360.6	359.8	358.2	356.1
175°	352.1	352.8	351.4	350.7	351.4	352.8	352.1	352.1	352.1	350.7	350.7
177.5°	347.0	347.5	345.8	345.8	345.8	347.5	347.0	347.5	347.5	347.5	347.0
180°	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8



TEST NUMBER: P333225-940

CATALOG NUMBER: S125DIP-S850D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	1043.1	1047.6	1053.1	1057.2	1064.6	1067.9	1072.0	1075.3	1081.3	1086.8	1093.5
5°	972.9	980.7	991.3	1002.9	1016.4	1025.6	1038.6	1046.4	1062.2	1076.6	1090.4
7.5°	909.1	918.7	933.8	948.7	966.3	982.1	998.4	1016.4	1036.4	1060.2	1079.8
10°	865.4	878.3	894.6	913.1	934.4	952.9	974.6	994.1	1018.7	1046.4	1072.4
12.5°	830.5	841.7	859.8	877.5	900.3	922.9	945.4	971.2	999.8	1030.6	1063.1
15°	782.5	791.8	806.6	831.2	854.3	876.6	910.3	934.4	970.5	1004.8	1044.1
17.5°	741.5	753.0	765.4	786.5	810.5	838.3	868.4	898.7	933.4	976.9	1021.3
20°	716.3	725.6	739.9	756.1	781.6	809.4	838.1	868.6	911.2	956.2	1003.8
22.5°	688.8	698.9	715.1	732.8	754.2	780.9	812.5	846.1	890.5	934.7	986.4
25°	656.6	663.5	678.3	694.1	715.4	738.1	771.0	808.0	851.9	902.4	955.2
27.5°	626.1	632.2	645.8	659.4	678.7	705.6	735.0	772.4	813.9	865.0	923.5
30°	604.2	610.7	622.8	637.6	656.1	679.8	709.8	745.0	789.4	839.5	900.6
32.5°	585.3	591.1	600.2	615.0	633.1	656.0	683.9	719.8	764.3	815.0	875.0
35°	556.1	562.6	569.5	581.1	596.8	619.0	649.6	683.4	726.0	775.1	830.2
37.5°	527.0	534.0	540.3	550.6	565.0	584.6	611.0	646.2	684.7	732.0	784.9
40°	508.9	514.4	519.5	530.7	545.0	563.5	588.1	619.6	660.3	704.3	748.2
42.5°	490.7	495.9	500.2	509.9	523.2	540.9	564.4	595.0	632.8	673.9	712.7
45°	462.1	465.4	470.5	478.8	489.5	505.6	528.3	555.6	587.5	626.5	655.7
47.5°	431.1	436.2	440.4	447.7	456.5	472.3	494.1	517.4	546.4	575.2	595.8
50°	407.4	412.6	418.6	425.5	433.8	448.7	468.6	492.2	516.7	539.0	556.5
52.5°	385.2	389.9	396.4	403.0	413.1	425.7	442.6	463.7	487.9	503.8	518.4
55°	352.4	354.6	362.1	368.5	378.3	387.5	404.7	423.2	438.0	450.0	462.1
57.5°	318.8	321.9	326.2	332.0	341.6	352.5	364.5	380.8	389.6	395.8	405.1
60°	297.3	298.2	301.0	307.9	315.3	325.0	338.9	350.5	357.0	362.1	370.0
62.5°	273.6	273.8	278.4	283.5	289.0	299.5	310.8	320.1	325.5	328.0	335.6
65°	240.3	239.4	242.2	246.3	252.8	259.8	269.5	277.9	277.3	280.1	284.7
67.5°	206.3	205.4	205.4	209.4	214.6	220.9	227.6	232.4	232.5	236.1	238.4
70°	183.3	180.6	182.4	185.7	188.0	193.1	200.5	202.3	202.8	204.6	207.0
72.5°	159.6	158.7	160.2	161.6	163.2	167.2	173.4	174.6	174.7	175.8	179.6
75°	126.9	125.9	125.0	126.4	128.2	131.0	133.3	135.2	134.7	135.2	137.9
77.5°	95.1	92.5	92.0	92.8	93.3	94.9	97.3	97.1	97.6	97.6	100.7
80°	75.4	71.8	71.3	71.3	71.8	72.7	73.7	74.5	73.1	74.5	75.4
82.5°	55.5	53.2	53.1	52.8	52.9	53.1	53.6	54.2	53.9	54.6	55.1
85°	30.6	29.6	28.3	29.2	28.7	27.3	28.3	26.8	26.4	26.8	27.3
87.5°	12.8	12.9	11.9	11.8	11.1	11.4	10.3	9.7	9.1	9.2	10.2
90°	11.9	11.1	9.7	9.1	7.7	7.0	5.6	4.2	2.8	1.4	0.7
92.5°	182.0	224.8	228.4	159.1	95.2	57.2	36.8	24.8	16.1	10.3	8.5
95°	604.5	617.8	504.1	311.7	158.3	83.6	52.3	36.9	29.2	23.7	23.0
97.5°	764.8	659.7	450.1	248.8	136.3	87.0	64.4	50.6	43.0	39.1	38.2
100°	803.9	629.6	401.6	225.9	135.3	94.8	73.9	60.6	53.0	50.2	48.8
102.5°	780.5	576.6	364.8	216.4	140.3	104.3	83.9	71.8	63.6	61.3	60.5
105°	705.6	505.5	329.1	212.7	150.6	119.9	100.4	89.3	82.3	78.8	78.8
107.5°	629.2	456.6	314.1	219.1	165.9	136.3	118.7	107.1	101.4	98.0	96.7
110°	585.7	433.6	309.6	225.2	177.1	148.5	130.4	119.9	113.6	110.8	109.5



TEST NUMBER: P333225-940

CATALOG NUMBER: S125DIP-S850D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	553.3	420.3	309.6	233.0	187.7	160.2	142.7	132.2	125.9	123.7	122.3
115°	518.0	405.8	311.7	244.7	204.3	178.5	161.0	150.6	144.4	142.2	140.8
117.5°	497.0	398.7	316.3	258.2	221.3	196.9	180.0	168.2	161.9	159.7	157.6
120°	485.3	395.3	320.7	267.1	233.5	209.2	191.7	179.9	173.6	170.9	168.7
122.5°	475.2	392.5	324.6	277.1	245.3	220.9	203.5	190.5	184.2	182.0	180.5
125°	461.5	389.1	331.2	290.7	260.7	237.7	219.6	206.3	200.1	196.6	195.2
127.5°	449.0	387.4	338.6	303.3	275.7	253.5	235.4	221.3	213.4	208.9	206.8
130°	440.7	386.3	343.0	311.7	285.2	263.6	245.4	230.8	221.7	216.2	214.0
132.5°	434.0	386.3	348.0	318.9	294.1	272.5	254.3	239.2	229.0	222.3	219.6
135°	426.0	386.3	354.9	329.1	306.1	284.5	265.6	251.0	239.9	231.5	228.7
137.5°	418.9	387.1	361.1	336.6	314.6	294.9	275.5	261.2	250.0	242.2	240.1
140°	415.5	387.6	363.9	341.6	320.7	300.5	281.7	268.4	257.3	248.9	246.8
142.5°	412.8	388.3	365.6	344.5	324.6	305.5	287.8	275.1	263.9	256.2	254.6
145°	408.6	387.6	367.5	348.6	331.2	313.1	297.0	284.5	274.7	267.7	266.4
147.5°	404.2	385.8	368.1	351.2	335.4	319.5	305.4	294.5	285.4	279.5	278.6
150°	400.9	384.1	368.1	352.8	338.1	322.8	310.9	301.2	292.1	287.2	285.9
152.5°	397.0	381.9	367.6	353.9	340.9	326.7	316.0	306.7	298.8	294.5	293.6
155°	390.5	377.9	366.0	354.9	343.8	331.9	322.1	315.1	308.2	304.0	304.0
157.5°	384.3	373.7	364.3	355.6	346.1	335.9	328.5	322.4	316.4	313.1	313.2
160°	379.3	371.0	362.6	355.6	347.2	338.1	331.9	326.3	321.5	318.6	319.3
162.5°	374.8	367.6	360.9	355.0	348.3	340.4	335.2	330.7	326.5	323.7	324.3
165°	368.1	362.6	358.4	354.2	348.6	343.0	338.9	336.1	332.6	330.5	331.9
167.5°	361.6	357.7	354.5	352.5	348.6	344.0	341.3	339.4	337.4	336.2	336.9
170°	357.7	354.9	352.8	351.4	348.6	345.1	343.0	341.6	340.3	339.6	340.3
172.5°	353.7	351.5	350.5	350.3	348.0	345.1	344.1	343.3	341.9	341.3	342.5
175°	348.6	347.9	347.9	348.6	347.2	345.1	345.1	345.1	344.5	343.8	345.1
177.5°	346.3	345.8	345.8	347.0	346.3	345.3	345.3	345.8	345.3	345.3	346.3
180°	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8



TEST NUMBER: P333225-940

CATALOG NUMBER: S125DIP-S850D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	1096.8	1102.0	1105.4	1111.6	1116.8	1119.8	1122.4	1124.6	1127.2	1129.4	1135.7
5°	1103.8	1115.9	1126.1	1141.8	1156.2	1167.2	1179.3	1190.0	1198.8	1211.3	1221.0
7.5°	1100.8	1122.2	1144.6	1168.9	1193.8	1217.0	1238.3	1258.2	1276.3	1298.2	1317.3
10°	1097.9	1127.0	1155.7	1188.6	1222.4	1251.1	1277.9	1305.3	1325.2	1353.0	1376.5
12.5°	1095.6	1130.0	1164.6	1204.2	1241.3	1281.8	1317.6	1337.5	1367.8	1390.0	1418.1
15°	1086.3	1131.7	1179.3	1223.8	1276.6	1314.0	1345.6	1384.5	1412.6	1440.9	1471.5
17.5°	1069.5	1120.9	1174.2	1232.5	1283.2	1323.4	1364.0	1401.5	1435.2	1473.1	1511.1
20°	1061.8	1113.1	1174.2	1233.9	1283.5	1325.6	1367.3	1408.5	1445.6	1494.2	1538.2
22.5°	1045.4	1107.6	1163.9	1222.1	1273.1	1319.0	1366.2	1413.0	1462.2	1517.2	1572.3
25°	1016.4	1079.3	1139.1	1196.5	1247.9	1305.3	1355.8	1418.3	1481.2	1553.9	1622.5
27.5°	986.1	1046.4	1101.2	1156.6	1216.6	1281.6	1347.0	1418.0	1500.4	1592.1	1688.8
30°	961.7	1018.7	1071.9	1128.8	1191.3	1264.5	1336.3	1420.6	1515.9	1619.2	1734.0
32.5°	933.2	985.7	1037.4	1097.8	1165.8	1243.0	1326.7	1419.1	1533.7	1651.1	1769.2
35°	884.4	928.4	981.6	1046.0	1122.8	1211.3	1308.1	1417.3	1548.8	1683.6	1783.2
37.5°	826.5	867.5	923.5	994.1	1074.7	1169.6	1284.4	1414.1	1553.7	1661.2	1693.3
40°	787.6	825.5	884.0	957.1	1039.5	1140.0	1265.9	1402.9	1538.2	1606.7	1580.3
42.5°	746.1	786.0	842.8	915.3	1004.0	1113.3	1242.6	1379.7	1493.0	1518.9	1427.7
45°	680.6	721.8	777.8	851.0	946.5	1065.0	1199.7	1324.3	1389.6	1342.7	1201.6
47.5°	619.8	658.4	710.3	785.9	884.3	1006.9	1136.7	1236.0	1241.2	1129.6	978.7
50°	578.4	613.9	666.3	741.7	839.5	963.6	1080.7	1159.0	1123.7	997.4	852.4
52.5°	537.6	572.5	624.1	698.8	795.4	909.1	1018.1	1073.0	1006.7	877.0	753.1
55°	478.8	509.3	559.8	628.7	720.5	826.1	918.6	937.6	851.5	723.7	623.2
57.5°	421.3	449.9	495.8	559.4	643.1	736.6	809.0	805.0	714.0	604.3	524.6
60°	382.5	410.3	451.0	513.0	589.4	670.0	732.0	717.2	627.0	532.4	465.4
62.5°	347.7	372.5	411.0	465.2	534.9	609.7	660.6	638.7	550.3	467.6	414.6
65°	296.3	317.2	350.1	396.4	454.2	515.9	555.2	526.9	451.5	387.1	344.5
67.5°	247.4	264.0	291.6	328.6	377.9	427.4	451.4	422.9	362.6	315.6	284.0
70°	216.2	231.0	252.4	285.3	328.3	370.0	388.0	362.6	310.7	270.4	247.7
72.5°	185.1	197.3	216.1	245.6	280.1	316.3	332.1	307.7	265.1	231.1	209.9
75°	143.1	151.4	164.3	184.8	212.0	240.8	249.6	228.3	201.0	175.5	161.6
77.5°	102.5	109.5	119.3	132.2	151.5	169.8	177.5	165.1	144.0	127.9	116.5
80°	78.7	82.4	90.8	101.4	116.7	128.2	133.3	125.5	110.7	98.6	89.8
82.5°	56.1	59.8	64.8	73.7	83.4	91.2	96.7	91.4	80.7	71.2	66.1
85°	27.3	29.6	32.4	36.1	43.5	48.2	47.7	44.4	40.3	36.6	33.8
87.5°	9.9	10.5	11.9	14.1	15.4	17.1	18.1	17.5	16.3	15.3	14.4
90°	1.4	2.8	4.2	5.6	7.0	7.7	9.1	9.7	11.1	11.9	12.6
92.5°	10.3	16.1	24.8	36.8	57.2	95.2	159.1	228.4	224.8	182.0	123.6
95°	23.7	29.2	36.9	52.3	83.6	158.3	311.7	504.1	617.8	604.5	501.3
97.5°	39.1	43.0	50.6	64.4	87.0	136.3	248.8	450.1	659.7	764.8	746.6
100°	50.2	53.0	60.6	73.9	94.8	135.3	225.9	401.6	629.6	803.9	857.6
102.5°	61.3	63.6	71.8	83.9	104.3	140.3	216.4	364.8	576.6	780.5	894.9
105°	78.8	82.3	89.3	100.4	119.9	150.6	212.7	329.1	505.5	705.6	872.9
107.5°	98.0	101.4	107.1	118.7	136.3	165.9	219.1	314.1	456.6	629.2	794.2
110°	110.8	113.6	119.9	130.4	148.5	177.1	225.2	309.6	433.6	585.7	736.3



TEST NUMBER: P333225-940

CATALOG NUMBER: S125DIP-S850D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	123.7	125.9	132.2	142.7	160.2	187.7	233.0	309.6	420.3	553.3	690.5
115°	142.2	144.4	150.6	161.0	178.5	204.3	244.7	311.7	405.8	518.0	633.1
117.5°	159.7	161.9	168.2	180.0	196.9	221.3	258.2	316.3	398.7	497.0	596.0
120°	170.9	173.6	179.9	191.7	209.2	233.5	267.1	320.7	395.3	485.3	575.9
122.5°	182.0	184.2	190.5	203.5	220.9	245.3	277.1	324.6	392.5	475.2	560.9
125°	196.6	200.1	206.3	219.6	237.7	260.7	290.7	331.2	389.1	461.5	539.0
127.5°	208.9	213.4	221.3	235.4	253.5	275.7	303.3	338.6	387.4	449.0	516.7
130°	216.2	221.7	230.8	245.4	263.6	285.2	311.7	343.0	386.3	440.7	502.7
132.5°	222.3	229.0	239.2	254.3	272.5	294.1	318.9	348.0	386.3	434.0	488.7
135°	231.5	239.9	251.0	265.6	284.5	306.1	329.1	354.9	386.3	426.0	470.6
137.5°	242.2	250.0	261.2	275.5	294.9	314.6	336.6	361.1	387.1	418.9	455.3
140°	248.9	257.3	268.4	281.7	300.5	320.7	341.6	363.9	387.6	415.5	446.9
142.5°	256.2	263.9	275.1	287.8	305.5	324.6	344.5	365.6	388.3	412.8	439.7
145°	267.7	274.7	284.5	297.0	313.1	331.2	348.6	367.5	387.6	408.6	430.2
147.5°	279.5	285.4	294.5	305.4	319.5	335.4	351.2	368.1	385.8	404.2	421.2
150°	287.2	292.1	301.2	310.9	322.8	338.1	352.8	368.1	384.1	400.9	416.3
152.5°	294.5	298.8	306.7	316.0	326.7	340.9	353.9	367.6	381.9	397.0	410.6
155°	304.0	308.2	315.1	322.1	331.9	343.8	354.9	366.0	377.9	390.5	402.3
157.5°	313.1	316.4	322.4	328.5	335.9	346.1	355.6	364.3	373.7	384.3	394.0
160°	318.6	321.5	326.3	331.9	338.1	347.2	355.6	362.6	371.0	379.3	388.3
162.5°	323.7	326.5	330.7	335.2	340.4	348.3	355.0	360.9	367.6	374.8	382.2
165°	330.5	332.6	336.1	338.9	343.0	348.6	354.2	358.4	362.6	368.1	373.7
167.5°	336.2	337.4	339.4	341.3	344.0	348.6	352.5	354.5	357.7	361.6	365.6
170°	339.6	340.3	341.6	343.0	345.1	348.6	351.4	352.8	354.9	357.7	361.1
172.5°	341.3	341.9	343.3	344.1	345.1	348.0	350.3	350.5	351.5	353.7	356.1
175°	343.8	344.5	345.1	345.1	345.1	347.2	348.6	347.9	347.9	348.6	350.7
177.5°	345.3	345.3	345.8	345.3	345.3	346.3	347.0	345.8	345.8	346.3	347.0
180°	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8



TEST NUMBER: P333225-940

CATALOG NUMBER: S125DIP-S850D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	1140.9	1143.9	1150.1	1147.9	1150.9	1152.4	1153.9
5°	1233.1	1247.9	1254.4	1253.4	1263.1	1260.8	1258.5
7.5°	1337.1	1352.7	1361.4	1372.3	1378.5	1378.9	1384.5
10°	1396.1	1416.4	1424.8	1436.3	1443.7	1447.9	1447.4
12.5°	1441.2	1457.1	1475.9	1481.5	1491.5	1496.7	1494.9
15°	1495.6	1521.1	1540.5	1550.2	1562.7	1566.4	1571.6
17.5°	1544.1	1578.2	1601.0	1631.1	1642.5	1649.5	1645.4
20°	1580.7	1625.7	1648.4	1684.5	1704.4	1715.0	1711.4
22.5°	1624.1	1672.8	1714.7	1746.0	1776.3	1790.6	1793.6
25°	1698.4	1765.1	1826.7	1867.9	1905.3	1914.1	1933.6
27.5°	1781.4	1860.0	1925.8	1969.2	1995.3	2005.1	2011.2
30°	1833.6	1911.8	1961.4	1989.1	1997.5	1996.5	1995.6
32.5°	1859.1	1908.2	1917.6	1909.9	1890.8	1874.7	1857.9
35°	1822.9	1786.4	1731.7	1661.3	1609.4	1557.2	1552.0
37.5°	1639.5	1522.5	1431.6	1330.0	1271.4	1235.2	1210.1
40°	1466.9	1334.0	1223.8	1138.1	1078.3	1054.8	1031.6
42.5°	1279.4	1152.4	1054.9	983.3	938.3	912.1	893.9
45°	1039.5	927.5	851.0	799.2	763.6	743.2	731.6
47.5°	851.8	768.9	704.0	666.6	641.9	626.1	626.2
50°	751.0	671.8	628.7	599.1	577.8	565.3	567.7
52.5°	661.7	602.6	565.8	541.0	525.2	517.5	517.3
55°	553.3	510.7	486.6	468.6	457.9	449.2	451.0
57.5°	473.3	437.4	421.2	406.3	398.9	395.3	390.2
60°	423.7	395.9	382.0	370.0	362.6	359.8	354.6
62.5°	379.6	357.8	344.2	334.4	327.7	326.8	322.8
65°	319.1	302.4	290.3	285.7	278.7	276.9	276.9
67.5°	263.0	251.0	241.7	237.5	234.3	234.9	232.6
70°	227.8	218.1	212.0	207.4	205.1	205.5	203.8
72.5°	199.3	188.4	183.2	180.4	177.4	178.5	177.8
75°	151.0	145.3	142.6	139.8	137.9	137.1	136.2
77.5°	110.8	105.9	103.8	102.3	102.5	100.3	102.0
80°	85.7	81.5	80.1	77.8	77.3	77.3	76.9
82.5°	62.7	60.4	59.4	57.4	56.6	57.3	56.1
85°	32.4	30.6	30.1	30.1	29.2	28.3	30.6
87.5°	14.5	13.2	13.5	13.1	13.1	12.8	12.1
90°	13.3	13.9	15.3	15.3	15.3	16.1	16.1
92.5°	89.7	67.5	57.2	48.2	46.5	45.6	44.5
95°	395.3	309.6	251.0	201.5	180.6	175.0	163.8
97.5°	672.3	588.7	507.3	464.2	425.2	404.9	396.0
100°	823.4	751.6	679.1	631.0	580.8	555.0	543.9
102.5°	916.1	881.5	832.5	781.0	745.3	717.3	708.9
105°	968.5	999.2	991.5	969.1	946.1	932.2	923.8
107.5°	921.8	1000.5	1036.9	1048.2	1048.0	1043.5	1037.9
110°	868.7	967.1	1026.3	1057.7	1070.9	1075.8	1075.8



TEST NUMBER: P333225-940

CATALOG NUMBER: S125DIP-S850D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	816.3	915.7	985.6	1031.4	1054.2	1066.3	1071.4
115°	741.2	836.7	912.7	967.1	1000.5	1020.0	1029.1
117.5°	689.1	771.4	841.2	895.5	930.1	949.5	955.0
120°	659.6	736.3	797.6	849.2	882.7	901.5	907.0
122.5°	638.4	706.7	764.2	810.2	840.9	859.7	864.7
125°	610.1	670.7	720.9	760.0	788.5	803.9	810.8
127.5°	583.0	639.6	686.6	722.0	747.3	761.8	764.8
130°	564.1	618.4	663.8	698.7	721.7	735.6	739.8
132.5°	546.2	595.6	639.2	674.0	697.1	709.9	714.6
135°	518.7	563.4	603.1	633.7	656.7	669.3	673.5
137.5°	494.2	531.3	565.0	592.5	613.4	625.0	629.6
140°	479.7	511.8	541.0	566.9	585.0	595.4	598.9
142.5°	467.4	495.0	520.4	542.3	557.7	567.6	570.4
145°	451.8	473.4	492.2	509.0	520.8	528.5	531.3
147.5°	438.8	455.4	469.7	482.9	492.4	496.9	498.1
150°	431.6	444.8	457.4	467.9	476.2	479.0	479.7
152.5°	424.4	436.5	446.2	455.0	461.7	464.5	465.2
155°	413.5	423.2	430.9	437.8	442.7	444.8	445.5
157.5°	403.1	410.6	416.7	422.1	426.1	428.1	427.9
160°	395.3	402.3	407.2	412.1	415.5	417.0	416.3
162.5°	388.6	394.5	398.8	402.6	405.5	405.8	405.6
165°	378.6	382.8	386.3	389.1	390.5	390.5	390.5
167.5°	368.8	372.0	374.5	375.9	377.2	376.7	376.5
170°	363.3	365.3	366.8	368.1	368.8	368.8	368.1
172.5°	358.2	359.8	360.6	360.9	362.1	361.1	360.3
175°	350.7	352.1	352.1	352.1	352.8	351.4	350.7
177.5°	347.5	347.5	347.5	347.0	347.5	345.8	345.8
180°	345.8	345.8	345.8	345.8	345.8	345.8	345.8

(END OF REPORT)