

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331292-930

Luminaire Tested: **SA2XXDIP-C485D330U930-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331292-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C485D330U930-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2566.8 lumens
Efficiency: N/A
Efficacy: 93.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331292-930
CATALOG NUMBER: SA2XXDIP-C485D330U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331292-930

CATALOG NUMBER: SA2XXDIP-C485D330U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	63
1	101	96	92	89	94	90	87	84	79	77	74	69	67	66	60	59	57	53
2	92	84	78	72	86	79	73	69	70	65	62	61	58	55	53	50	48	44
3	84	74	66	60	78	70	63	58	61	56	52	54	50	46	47	44	41	38
4	77	66	57	51	71	62	54	49	55	49	44	48	43	40	42	38	35	32
5	70	58	50	44	66	55	48	42	49	43	38	43	38	35	38	34	31	28
6	65	53	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27	25
7	60	48	39	34	56	45	38	32	40	34	30	36	31	27	31	27	24	22
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	20
9	52	40	32	27	49	38	30	26	34	28	24	30	25	22	27	23	20	18
10	49	36	29	24	46	35	28	23	31	25	21	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10224	10224	10224
5°	10263	10115	10175
10°	10203	10012	10063
15°	10076	9884	9872
20°	9897	9689	9677
25°	9720	9449	9449
30°	9491	9229	9148
35°	9278	8966	8834
40°	9010	8703	8534
45°	8745	8439	8229
50°	8457	8166	7877
55°	8158	7848	7561
60°	7824	7472	7195
65°	7465	7095	6770
70°	7010	6637	6326
75°	6382	6114	5964
80°	5662	5486	5207
85°	4613	4390	3946



TEST NUMBER: P331292-930

CATALOG NUMBER: SA2XXDIP-C485D330U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.5	2.3
10°-20°	167.6	6.5
20°-30°	246.3	9.6
30°-40°	286.1	11.1
40°-50°	285.8	11.1
50°-60°	249.2	9.7
60°-70°	184.3	7.2
70°-80°	104.4	4.1
80°-90°	29.4	1.1
90°-100°	21.6	0.8
100°-110°	67.2	2.6
110°-120°	114.8	4.5
120°-130°	151.0	5.9
130°-140°	169.5	6.6
140°-150°	166.2	6.5
150°-160°	139.4	5.4
160°-170°	92.4	3.6
170°-180°	32.3	1.3
0°-30°	473.4	18.4
0°-40°	759.4	29.6
0°-60°	1294.4	50.4
0°-90°	1612.4	62.8
90°-120°	203.6	7.9
90°-150°	690.3	26.9
90°-180°	954.0	37.2
0°-180°	2566.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	633	633	633	633	633	
5°	633	631	624	629	628	60
15°	603	599	591	593	591	170
25°	546	540	530	531	530	251
35°	471	464	455	451	448	294
45°	383	378	370	363	360	295
55°	290	286	279	272	269	259
65°	195	192	186	180	177	193
75°	102	101	98	95	96	109
85°	25	24	24	22	21	29
90°	0	4	10	10	10	2
95°	15	18	18	18	18	17
105°	62	63	63	64	64	65
115°	115	117	116	116	115	114
125°	168	170	169	168	168	150
135°	217	220	221	220	220	168
145°	263	265	267	267	266	164
155°	301	302	303	304	303	138
165°	328	327	327	329	328	92
175°	341	340	339	341	340	32
180°	341	341	341	341	341	



TEST NUMBER: P331292-930

CATALOG NUMBER: SA2XXDIP-C485D330U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2
2.5°	636.2	635.6	635.1	634.5	634.0	633.2	631.9	630.8	629.6	628.4	629.5
5°	633.2	632.7	632.2	631.6	631.1	630.1	628.6	627.1	625.6	624.1	625.2
7.5°	627.6	626.8	626.0	625.1	624.3	623.1	621.6	620.1	618.6	617.0	618.2
10°	622.3	621.3	620.4	619.5	618.5	617.2	615.6	614.0	612.4	610.7	611.8
12.5°	615.0	614.2	613.3	612.5	611.6	610.4	608.8	607.2	605.5	603.9	604.6
15°	602.8	602.0	601.2	600.4	599.6	598.3	596.5	594.8	593.0	591.3	591.7
17.5°	587.2	586.4	585.6	584.8	584.0	582.7	580.9	579.1	577.3	575.5	576.2
20°	576.0	575.2	574.4	573.6	572.7	571.4	569.5	567.6	565.7	563.9	564.3
22.5°	564.8	563.7	562.6	561.4	560.3	558.8	557.0	555.2	553.4	551.6	551.7
25°	545.6	544.5	543.4	542.3	541.3	539.6	537.3	534.9	532.6	530.4	530.6
27.5°	523.7	522.7	521.7	520.7	519.8	518.4	516.6	514.7	512.9	511.1	510.7
30°	509.1	507.9	506.9	505.8	504.7	503.1	501.1	499.1	497.1	495.0	494.6
32.5°	493.4	492.6	491.7	490.8	490.0	488.4	486.3	484.2	482.1	480.0	479.2
35°	470.7	469.3	468.0	466.6	465.3	463.5	461.4	459.2	457.0	454.9	454.0
37.5°	445.0	443.8	442.6	441.4	440.2	438.5	436.3	434.2	432.0	429.9	428.8
40°	427.5	426.3	425.3	424.2	423.1	421.5	419.3	417.2	415.0	412.9	411.6
42.5°	410.4	409.3	408.2	407.2	406.1	404.5	402.3	400.1	397.9	395.7	394.4
45°	383.0	382.0	381.1	380.2	379.2	377.7	375.7	373.7	371.6	369.6	368.1
47.5°	355.7	354.8	353.9	353.0	352.1	350.7	348.5	346.4	344.3	342.2	340.6
50°	336.7	336.1	335.3	334.7	334.0	332.7	330.8	329.0	327.0	325.1	323.3
52.5°	318.2	317.3	316.4	315.5	314.6	313.3	311.5	309.7	307.9	306.1	304.6
55°	289.8	289.0	288.2	287.4	286.6	285.4	283.7	282.1	280.5	278.8	277.3
57.5°	261.3	260.7	260.0	259.4	258.8	257.6	255.8	254.0	252.2	250.4	248.7
60°	242.3	241.8	241.2	240.7	240.2	239.0	237.1	235.1	233.3	231.4	229.9
62.5°	223.8	223.0	222.1	221.2	220.4	219.2	217.8	216.3	214.8	213.4	212.0
65°	195.4	194.6	193.8	193.0	192.2	191.1	189.8	188.4	187.0	185.7	184.5
67.5°	166.6	165.9	165.3	164.6	164.0	163.1	161.8	160.6	159.4	158.2	157.3
70°	148.5	148.1	147.5	146.9	146.4	145.5	144.3	143.1	141.9	140.6	139.7
72.5°	130.0	129.6	129.0	128.4	127.9	127.3	126.5	125.6	124.9	124.1	123.1
75°	102.3	102.0	101.7	101.5	101.2	100.8	100.0	99.4	98.7	98.0	97.2
77.5°	77.5	77.0	76.6	76.1	75.6	75.3	75.0	74.7	74.4	74.2	73.8
80°	60.9	60.7	60.7	60.5	60.3	60.2	59.8	59.6	59.4	59.0	58.6
82.5°	45.3	45.2	45.2	45.2	45.2	45.1	44.9	44.8	44.6	44.4	43.9
85°	24.9	24.9	24.7	24.5	24.5	24.3	24.1	24.1	23.9	23.7	23.3
87.5°	8.8	8.7	8.7	8.6	8.6	8.6	8.6	8.7	8.8	8.8	8.5
90°	0.3	1.1	1.8	2.6	3.3	4.5	5.9	7.3	8.6	10.1	9.9
92.5°	5.1	5.7	6.3	6.8	7.4	7.8	8.2	8.5	8.8	9.1	9.2
95°	15.0	15.7	16.2	16.9	17.5	17.9	18.0	18.2	18.3	18.4	18.4
97.5°	27.4	28.0	28.5	29.0	29.6	30.0	30.2	30.5	30.7	31.0	31.0
100°	36.6	37.1	37.6	38.2	38.6	39.0	39.1	39.4	39.5	39.8	39.8
102.5°	46.2	46.6	47.0	47.5	47.9	48.3	48.4	48.7	48.9	49.2	49.2
105°	62.0	62.1	62.3	62.5	62.7	62.9	63.0	63.1	63.3	63.3	63.5
107.5°	77.7	78.0	78.3	78.6	78.8	79.0	79.0	79.0	79.0	79.0	79.0
110°	87.9	88.2	88.6	89.0	89.4	89.6	89.6	89.6	89.6	89.6	89.6



TEST NUMBER: P331292-930

CATALOG NUMBER: SA2XXDIP-C485D330U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	98.9	99.3	99.7	100.0	100.4	100.6	100.5	100.5	100.4	100.4	100.3
115°	115.2	115.6	116.0	116.3	116.8	116.9	116.8	116.6	116.5	116.3	116.3
117.5°	131.4	132.0	132.5	133.0	133.5	133.6	133.2	132.9	132.5	132.2	132.0
120°	142.3	142.8	143.3	143.8	144.3	144.3	143.8	143.3	142.8	142.3	142.3
122.5°	152.2	152.8	153.4	154.0	154.7	154.8	154.4	154.1	153.7	153.4	153.2
125°	167.6	168.2	168.8	169.3	169.9	170.2	169.9	169.7	169.6	169.3	169.2
127.5°	182.7	183.4	184.2	184.8	185.6	185.8	185.6	185.4	185.2	184.9	184.7
130°	192.2	193.0	193.8	194.6	195.4	195.8	195.7	195.6	195.4	195.3	195.2
132.5°	202.8	203.4	204.1	204.7	205.5	205.8	205.8	205.9	205.9	205.9	205.6
135°	216.9	217.6	218.3	219.0	219.7	220.1	220.3	220.4	220.5	220.6	220.5
137.5°	231.8	232.4	232.9	233.6	234.2	234.5	234.6	234.8	235.0	235.1	235.1
140°	240.8	241.4	242.0	242.6	243.1	243.5	243.9	244.2	244.5	244.8	244.8
142.5°	250.1	250.6	251.2	251.8	252.3	252.7	252.9	253.2	253.4	253.6	253.6
145°	263.3	263.7	264.2	264.6	265.1	265.5	265.9	266.3	266.6	267.0	267.1
147.5°	275.1	275.7	276.1	276.7	277.2	277.6	277.9	278.2	278.4	278.7	278.8
150°	283.2	283.6	283.9	284.3	284.7	285.0	285.3	285.5	285.8	286.0	286.3
152.5°	290.3	290.7	291.1	291.5	291.8	292.2	292.4	292.8	293.1	293.4	293.7
155°	301.0	301.2	301.4	301.6	301.7	302.0	302.1	302.3	302.6	302.7	303.0
157.5°	310.1	310.3	310.4	310.5	310.7	310.8	311.0	311.0	311.1	311.3	311.7
160°	315.7	315.8	315.9	316.1	316.2	316.3	316.3	316.4	316.5	316.6	316.9
162.5°	320.7	320.8	320.8	320.8	320.9	320.9	321.0	321.1	321.1	321.1	321.6
165°	327.5	327.4	327.3	327.3	327.3	327.2	327.2	327.2	327.2	327.2	327.7
167.5°	333.1	333.0	332.8	332.6	332.4	332.3	332.2	332.2	332.2	332.2	332.6
170°	336.1	336.0	335.7	335.6	335.4	335.3	335.2	335.1	335.1	335.0	335.4
172.5°	338.2	338.0	337.9	337.6	337.5	337.3	337.3	337.2	337.1	337.0	337.5
175°	340.8	340.6	340.4	340.1	340.0	339.8	339.7	339.6	339.4	339.3	339.7
177.5°	341.8	341.6	341.4	341.4	341.2	341.0	341.0	340.9	340.7	340.6	341.0
180°	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4



TEST NUMBER: P331292-930

CATALOG NUMBER: SA2XXDIP-C485D330U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2
2.5°	630.6	631.6	632.7	633.2	632.9	632.7	632.5	632.3
5°	626.3	627.4	628.4	628.8	628.6	628.3	628.0	627.8
7.5°	619.2	620.3	621.4	621.7	621.5	621.2	620.9	620.6
10°	612.9	614.0	615.1	615.4	615.0	614.6	614.2	613.8
12.5°	605.4	606.2	606.9	607.2	606.8	606.6	606.3	605.9
15°	592.3	592.9	593.4	593.3	592.6	592.0	591.3	590.6
17.5°	576.7	577.4	578.0	578.0	577.3	576.7	576.1	575.4
20°	564.7	565.1	565.5	565.4	564.8	564.3	563.8	563.2
22.5°	551.8	551.9	552.0	551.9	551.5	551.2	550.9	550.6
25°	530.9	531.2	531.4	531.4	531.2	530.9	530.6	530.4
27.5°	510.3	509.9	509.5	509.0	508.3	507.7	507.0	506.4
30°	494.2	493.8	493.4	492.9	492.4	491.9	491.3	490.7
32.5°	478.5	477.8	477.0	476.4	475.8	475.3	474.7	474.2
35°	453.2	452.4	451.6	450.9	450.2	449.5	448.8	448.2
37.5°	427.9	426.9	425.9	425.0	424.4	423.7	423.1	422.5
40°	410.4	409.2	408.0	407.1	406.5	406.0	405.4	404.9
42.5°	393.1	391.8	390.4	389.5	388.7	387.9	387.2	386.4
45°	366.6	365.2	363.6	362.6	362.1	361.6	361.0	360.4
47.5°	339.1	337.5	335.9	334.8	333.9	333.2	332.4	331.6
50°	321.4	319.4	317.6	316.3	315.6	315.0	314.2	313.6
52.5°	303.0	301.4	299.9	298.6	297.7	296.9	296.0	295.1
55°	275.7	274.0	272.4	271.3	270.5	269.9	269.2	268.6
57.5°	247.2	245.6	244.0	243.0	242.4	241.9	241.4	240.8
60°	228.4	226.9	225.4	224.5	224.0	223.6	223.2	222.8
62.5°	210.6	209.2	207.8	206.9	206.4	205.9	205.4	204.8
65°	183.3	182.1	180.8	179.9	179.2	178.6	177.9	177.2
67.5°	156.3	155.3	154.4	153.7	153.1	152.5	152.1	151.5
70°	138.8	137.8	136.9	136.2	135.6	135.0	134.5	134.0
72.5°	122.2	121.2	120.3	119.6	119.2	118.7	118.3	117.9
75°	96.4	95.6	94.8	94.5	94.8	95.1	95.3	95.6
77.5°	73.4	73.0	72.6	72.2	71.7	71.4	71.0	70.6
80°	58.2	57.8	57.5	57.1	56.8	56.6	56.3	56.0
82.5°	43.5	42.9	42.4	42.1	42.1	42.0	41.9	41.9
85°	22.9	22.5	22.1	21.9	21.7	21.6	21.4	21.3
87.5°	8.2	7.7	7.4	7.2	7.1	7.0	6.9	6.8
90°	9.9	9.7	9.5	9.5	9.6	9.7	9.7	9.8
92.5°	9.2	9.2	9.3	9.3	9.3	9.3	9.3	9.3
95°	18.4	18.4	18.4	18.3	18.3	18.1	18.0	17.9
97.5°	31.0	31.0	31.0	31.0	31.0	31.0	31.0	30.9
100°	39.8	39.8	39.8	39.7	39.6	39.6	39.5	39.5
102.5°	49.3	49.3	49.4	49.4	49.3	49.2	49.2	49.2
105°	63.6	63.8	63.9	63.9	63.9	63.9	63.9	63.9
107.5°	79.1	79.2	79.2	79.1	78.8	78.5	78.2	77.9
110°	89.6	89.6	89.6	89.5	89.3	89.1	88.9	88.7



TEST NUMBER: P331292-930

CATALOG NUMBER: SA2XXDIP-C485D330U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	100.1	100.0	99.8	99.6	99.5	99.4	99.2	99.1
115°	116.3	116.2	116.1	116.0	115.8	115.6	115.4	115.2
117.5°	131.8	131.7	131.5	131.3	131.2	131.0	130.8	130.6
120°	142.3	142.3	142.3	142.2	142.0	141.8	141.6	141.5
122.5°	153.0	152.9	152.7	152.6	152.5	152.3	152.1	152.1
125°	169.0	168.8	168.6	168.4	168.4	168.4	168.3	168.2
127.5°	184.5	184.3	184.0	183.8	183.6	183.4	183.2	183.0
130°	195.0	194.9	194.8	194.6	194.4	194.0	193.8	193.6
132.5°	205.3	205.0	204.8	204.6	204.3	204.2	203.9	203.7
135°	220.5	220.5	220.4	220.3	220.0	219.9	219.7	219.5
137.5°	235.1	235.0	235.0	234.8	234.6	234.3	234.1	233.7
140°	244.8	244.8	244.8	244.7	244.4	244.2	243.9	243.7
142.5°	253.7	253.7	253.8	253.7	253.5	253.2	252.9	252.7
145°	267.2	267.2	267.3	267.2	266.9	266.7	266.4	266.1
147.5°	278.9	279.1	279.2	279.2	278.9	278.7	278.4	278.2
150°	286.4	286.6	286.8	286.8	286.6	286.4	286.3	286.0
152.5°	293.9	294.2	294.4	294.4	294.2	293.9	293.7	293.4
155°	303.4	303.7	304.0	304.1	303.9	303.7	303.5	303.3
157.5°	312.1	312.6	313.0	313.1	312.7	312.4	312.2	311.9
160°	317.3	317.7	318.1	318.1	317.9	317.6	317.4	317.2
162.5°	322.0	322.5	322.9	322.9	322.7	322.4	322.0	321.7
165°	328.1	328.6	329.0	329.1	328.7	328.4	328.1	327.8
167.5°	333.1	333.5	334.0	334.1	333.8	333.4	333.0	332.7
170°	335.9	336.3	336.8	336.8	336.5	336.1	335.7	335.3
172.5°	337.9	338.4	338.8	338.9	338.5	338.1	337.8	337.4
175°	340.2	340.6	341.1	341.1	340.8	340.4	340.0	339.6
177.5°	341.3	341.5	341.9	341.9	341.5	341.3	341.0	340.6
180°	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4

(END OF REPORT)