

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333231-940

Luminaire Tested: **S125DIP-S850D810U940-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333231-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S850D810U940-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5641.4 lumens
Efficiency: N/A
Efficacy: 122.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333231-940

CATALOG NUMBER: S125DIP-S850D810U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333231-940

CATALOG NUMBER: S125DIP-S850D810U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	94	90	87	91	88	84	81	75	72	70	63	62	60	53	52	50	45
2	90	82	76	71	83	76	71	66	66	62	58	56	53	50	46	44	42	38
3	82	72	65	59	76	67	61	55	58	53	49	49	45	42	41	38	36	32
4	75	64	56	50	69	60	53	47	51	46	42	44	40	36	37	34	31	28
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	30	27	24
6	63	51	43	37	59	48	40	35	41	36	31	36	31	28	30	27	24	21
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21	19
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19	17
9	51	38	31	26	47	36	29	24	31	26	22	27	23	20	23	20	17	15
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7559	7559	7559
5°	7577	7505	7553
10°	7531	7452	7494
15°	7449	7362	7393
20°	7332	7236	7249
25°	7207	7088	7081
30°	7052	6927	6893
35°	6885	6754	6659
40°	6715	6566	6473
45°	6530	6395	6268
50°	6327	6187	6002
55°	6132	5954	5788
60°	5898	5717	5515
65°	5619	5434	5251
70°	5351	5108	4932
75°	4876	4716	4551
80°	4340	4273	4169
85°	3772	3846	3631



TEST NUMBER: P333231-940

CATALOG NUMBER: S125DIP-S850D810U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.4	2.0
10°-20°	311.8	5.5
20°-30°	460.3	8.2
30°-40°	537.2	9.5
40°-50°	539.5	9.6
50°-60°	473.6	8.4
60°-70°	352.9	6.3
70°-80°	201.8	3.6
80°-90°	60.6	1.1
90°-100°	250.7	4.4
100°-110°	538.9	9.6
110°-120°	505.7	9.0
120°-130°	409.8	7.3
130°-140°	328.9	5.8
140°-150°	248.2	4.4
150°-160°	174.7	3.1
160°-170°	103.0	1.8
170°-180°	33.5	0.6
0°-30°	882.5	15.6
0°-40°	1419.6	25.2
0°-60°	2432.7	43.1
0°-90°	3048.0	54.0
90°-120°	1295.2	23.0
90°-150°	2282.2	40.5
90°-180°	2593.0	46.0
0°-180°	5641.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1170	1170	1170	1170	1170	
5°	1169	1166	1158	1165	1165	111
15°	1114	1111	1101	1106	1106	314
25°	1011	1006	995	996	994	465
35°	873	869	857	852	845	546
45°	715	711	700	690	686	551
55°	545	541	529	521	514	486
65°	368	365	356	348	344	365
75°	195	193	189	186	182	208
85°	51	52	52	51	49	57
90°	1	6	11	15	16	4
95°	23	68	618	280	164	24
105°	79	110	506	995	924	83
115°	141	170	406	875	1029	139
125°	195	229	389	696	811	173
135°	229	275	386	583	674	178
145°	266	305	388	483	531	167
155°	304	327	378	427	446	140
165°	332	341	363	385	390	93
175°	345	345	348	352	351	33
180°	346	346	346	346	346	



TEST NUMBER: P333231-940

CATALOG NUMBER: S125DIP-S850D810U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5
2.5°	1173.6	1173.0	1172.6	1172.1	1171.5	1170.5	1168.9	1167.2	1165.6	1164.0	1165.6
5°	1168.8	1168.3	1167.9	1167.5	1167.1	1165.8	1163.8	1161.7	1159.7	1157.6	1159.5
7.5°	1158.0	1157.6	1157.2	1156.7	1156.4	1155.0	1152.7	1150.5	1148.3	1145.9	1147.7
10°	1148.3	1148.0	1147.5	1147.1	1146.7	1145.4	1143.1	1140.9	1138.6	1136.3	1138.0
12.5°	1136.5	1135.8	1135.1	1134.3	1133.5	1132.1	1130.1	1127.9	1125.8	1123.7	1125.1
15°	1114.1	1113.5	1112.9	1112.2	1111.6	1110.2	1108.0	1105.6	1103.4	1101.1	1102.2
17.5°	1088.3	1087.4	1086.5	1085.7	1084.8	1083.1	1080.8	1078.4	1076.0	1073.7	1075.0
20°	1066.8	1066.5	1066.0	1065.6	1065.2	1063.6	1061.0	1058.3	1055.6	1052.9	1054.4
22.5°	1045.4	1044.6	1043.9	1043.1	1042.4	1040.8	1038.3	1035.7	1033.2	1030.7	1031.7
25°	1011.3	1010.3	1009.2	1008.2	1007.2	1005.3	1002.6	1000.0	997.3	994.6	995.1
27.5°	971.4	970.9	970.3	969.6	969.0	967.3	964.6	961.8	959.0	956.3	956.4
30°	945.6	944.9	944.3	943.7	943.1	941.2	938.2	935.0	931.9	928.9	928.4
32.5°	917.4	916.4	915.5	914.5	913.6	911.8	909.0	906.2	903.5	900.7	900.0
35°	873.3	872.4	871.6	870.8	870.0	868.2	865.3	862.4	859.5	856.7	855.6
37.5°	827.6	826.5	825.5	824.5	823.4	821.5	818.9	816.1	813.4	810.7	809.1
40°	796.5	795.4	794.4	793.4	792.3	790.4	787.5	784.6	781.8	778.8	777.0
42.5°	763.1	762.2	761.3	760.5	759.6	757.8	754.9	752.0	749.1	746.3	744.6
45°	715.0	714.1	713.3	712.5	711.7	710.0	707.6	705.1	702.6	700.2	697.7
47.5°	663.1	663.2	663.2	663.2	663.3	661.8	658.8	655.9	652.9	650.0	647.4
50°	629.7	629.1	628.5	627.9	627.3	625.7	623.3	620.8	618.3	615.8	613.1
52.5°	595.7	595.2	594.8	594.3	593.9	592.3	589.7	587.0	584.4	581.8	579.4
55°	544.6	543.9	543.3	542.7	542.1	540.3	537.4	534.6	531.6	528.8	526.9
57.5°	490.6	490.4	490.0	489.6	489.4	487.9	485.5	483.1	480.6	478.2	475.8
60°	456.6	455.8	455.0	454.1	453.3	451.7	449.4	447.2	445.0	442.6	440.6
62.5°	421.0	420.4	419.7	419.0	418.4	417.1	415.2	413.2	411.3	409.3	407.2
65°	367.7	367.2	366.8	366.4	366.0	364.7	362.4	360.2	357.8	355.6	353.7
67.5°	316.0	315.1	314.2	313.3	312.5	311.2	309.6	307.9	306.2	304.5	302.9
70°	283.4	282.3	281.3	280.3	279.3	277.9	276.0	274.1	272.2	270.5	269.2
72.5°	247.8	247.1	246.4	245.8	245.0	244.1	242.9	241.7	240.5	239.3	237.9
75°	195.4	195.0	194.6	194.2	193.8	193.1	192.0	191.0	189.9	189.0	188.3
77.5°	147.0	146.9	146.8	146.6	146.4	146.1	145.4	144.9	144.3	143.7	143.4
80°	116.7	116.7	116.7	116.7	116.7	116.5	116.1	115.7	115.2	114.9	114.7
82.5°	90.0	89.7	89.3	89.0	88.7	88.5	88.4	88.4	88.3	88.2	87.8
85°	50.9	51.2	51.4	51.5	51.7	51.9	51.9	51.9	51.9	51.9	51.6
87.5°	20.2	20.2	20.6	20.9	21.1	21.3	21.3	21.4	21.4	21.5	21.7
90°	0.7	1.4	2.8	4.2	5.6	7.0	7.7	9.1	9.7	11.1	11.9
92.5°	8.5	10.3	16.1	24.8	36.8	57.2	95.2	159.1	228.4	224.8	182.0
95°	23.0	23.7	29.2	36.9	52.3	83.6	158.3	311.7	504.1	617.8	604.5
97.5°	38.2	39.1	43.0	50.6	64.4	87.0	136.3	248.8	450.1	659.7	764.8
100°	48.8	50.2	53.0	60.6	73.9	94.8	135.3	225.9	401.6	629.6	803.9
102.5°	60.5	61.3	63.6	71.8	83.9	104.3	140.3	216.4	364.8	576.6	780.5
105°	78.8	78.8	82.3	89.3	100.4	119.9	150.6	212.7	329.1	505.5	705.6
107.5°	96.7	98.0	101.4	107.1	118.7	136.3	165.9	219.1	314.1	456.6	629.2
110°	109.5	110.8	113.6	119.9	130.4	148.5	177.1	225.2	309.6	433.6	585.7



TEST NUMBER: P333231-940

CATALOG NUMBER: S125DIP-S850D810U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	122.3	123.7	125.9	132.2	142.7	160.2	187.7	233.0	309.6	420.3	553.3
115°	140.8	142.2	144.4	150.6	161.0	178.5	204.3	244.7	311.7	405.8	518.0
117.5°	157.6	159.7	161.9	168.2	180.0	196.9	221.3	258.2	316.3	398.7	497.0
120°	168.7	170.9	173.6	179.9	191.7	209.2	233.5	267.1	320.7	395.3	485.3
122.5°	180.5	182.0	184.2	190.5	203.5	220.9	245.3	277.1	324.6	392.5	475.2
125°	195.2	196.6	200.1	206.3	219.6	237.7	260.7	290.7	331.2	389.1	461.5
127.5°	206.8	208.9	213.4	221.3	235.4	253.5	275.7	303.3	338.6	387.4	449.0
130°	214.0	216.2	221.7	230.8	245.4	263.6	285.2	311.7	343.0	386.3	440.7
132.5°	219.6	222.3	229.0	239.2	254.3	272.5	294.1	318.9	348.0	386.3	434.0
135°	228.7	231.5	239.9	251.0	265.6	284.5	306.1	329.1	354.9	386.3	426.0
137.5°	240.1	242.2	250.0	261.2	275.5	294.9	314.6	336.6	361.1	387.1	418.9
140°	246.8	248.9	257.3	268.4	281.7	300.5	320.7	341.6	363.9	387.6	415.5
142.5°	254.6	256.2	263.9	275.1	287.8	305.5	324.6	344.5	365.6	388.3	412.8
145°	266.4	267.7	274.7	284.5	297.0	313.1	331.2	348.6	367.5	387.6	408.6
147.5°	278.6	279.5	285.4	294.5	305.4	319.5	335.4	351.2	368.1	385.8	404.2
150°	285.9	287.2	292.1	301.2	310.9	322.8	338.1	352.8	368.1	384.1	400.9
152.5°	293.6	294.5	298.8	306.7	316.0	326.7	340.9	353.9	367.6	381.9	397.0
155°	304.0	304.0	308.2	315.1	322.1	331.9	343.8	354.9	366.0	377.9	390.5
157.5°	313.2	313.1	316.4	322.4	328.5	335.9	346.1	355.6	364.3	373.7	384.3
160°	319.3	318.6	321.5	326.3	331.9	338.1	347.2	355.6	362.6	371.0	379.3
162.5°	324.3	323.7	326.5	330.7	335.2	340.4	348.3	355.0	360.9	367.6	374.8
165°	331.9	330.5	332.6	336.1	338.9	343.0	348.6	354.2	358.4	362.6	368.1
167.5°	336.9	336.2	337.4	339.4	341.3	344.0	348.6	352.5	354.5	357.7	361.6
170°	340.3	339.6	340.3	341.6	343.0	345.1	348.6	351.4	352.8	354.9	357.7
172.5°	342.5	341.3	341.9	343.3	344.1	345.1	348.0	350.3	350.5	351.5	353.7
175°	345.1	343.8	344.5	345.1	345.1	345.1	347.2	348.6	347.9	347.9	348.6
177.5°	346.3	345.3	345.3	345.8	345.3	345.3	346.3	347.0	345.8	345.8	346.3
180°	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8



TEST NUMBER: P333231-940

CATALOG NUMBER: S125DIP-S850D810U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5
2.5°	1167.2	1168.9	1170.5	1171.3	1171.1	1170.9	1170.7	1170.5
5°	1161.4	1163.1	1165.0	1165.8	1165.6	1165.5	1165.2	1165.0
7.5°	1149.6	1151.4	1153.2	1154.0	1153.8	1153.6	1153.3	1153.2
10°	1139.6	1141.3	1142.9	1143.6	1143.4	1143.2	1143.0	1142.8
12.5°	1126.3	1127.7	1129.0	1129.6	1129.6	1129.5	1129.5	1129.4
15°	1103.2	1104.2	1105.3	1105.7	1105.7	1105.7	1105.7	1105.7
17.5°	1076.3	1077.5	1078.8	1079.0	1077.9	1076.9	1075.8	1074.9
20°	1055.9	1057.3	1058.7	1058.9	1057.9	1056.9	1055.9	1054.8
22.5°	1032.6	1033.6	1034.6	1034.7	1033.9	1033.2	1032.5	1031.9
25°	995.4	995.9	996.3	996.1	995.6	995.0	994.3	993.7
27.5°	956.4	956.5	956.6	956.4	955.7	955.1	954.5	953.9
30°	928.1	927.6	927.2	926.8	926.1	925.5	924.9	924.3
32.5°	899.2	898.5	897.8	896.8	895.7	894.6	893.5	892.4
35°	854.6	853.5	852.6	851.2	849.5	847.9	846.2	844.6
37.5°	807.6	806.1	804.6	803.3	802.5	801.5	800.6	799.6
40°	775.2	773.3	771.4	770.2	769.5	769.0	768.4	767.8
42.5°	742.9	741.2	739.5	738.2	737.3	736.3	735.3	734.4
45°	695.2	692.7	690.3	688.7	688.1	687.5	686.9	686.3
47.5°	644.9	642.4	639.9	637.9	636.5	635.1	633.6	632.1
50°	610.5	607.8	605.1	603.1	601.6	600.2	598.8	597.4
52.5°	577.1	574.7	572.4	570.4	568.8	567.2	565.6	564.0
55°	525.1	523.3	521.4	519.8	518.3	516.8	515.4	514.0
57.5°	473.5	471.1	468.7	467.1	466.3	465.6	464.8	464.0
60°	438.5	436.5	434.4	432.7	431.2	429.8	428.4	427.0
62.5°	404.9	402.7	400.5	398.8	397.7	396.5	395.5	394.3
65°	352.0	350.1	348.2	346.9	346.1	345.3	344.4	343.6
67.5°	301.4	299.8	298.3	297.2	296.8	296.2	295.7	295.2
70°	268.0	266.7	265.5	264.5	263.6	262.8	262.0	261.2
72.5°	236.5	235.1	233.7	232.6	231.8	231.0	230.2	229.3
75°	187.7	187.1	186.5	185.7	184.9	184.0	183.2	182.4
77.5°	143.0	142.6	142.2	141.8	141.2	140.6	140.1	139.5
80°	114.4	114.2	114.0	113.7	113.3	112.9	112.4	112.1
82.5°	87.4	87.0	86.7	86.5	86.4	86.3	86.2	86.1
85°	51.5	51.3	51.0	50.7	50.3	49.9	49.5	49.0
87.5°	21.8	21.9	22.0	22.2	21.8	21.5	21.3	21.0
90°	12.6	13.3	13.9	15.3	15.3	15.3	16.1	16.1
92.5°	123.6	89.7	67.5	57.2	48.2	46.5	45.6	44.5
95°	501.3	395.3	309.6	251.0	201.5	180.6	175.0	163.8
97.5°	746.6	672.3	588.7	507.3	464.2	425.2	404.9	396.0
100°	857.6	823.4	751.6	679.1	631.0	580.8	555.0	543.9
102.5°	894.9	916.1	881.5	832.5	781.0	745.3	717.3	708.9
105°	872.9	968.5	999.2	991.5	969.1	946.1	932.2	923.8
107.5°	794.2	921.8	1000.5	1036.9	1048.2	1048.0	1043.5	1037.9
110°	736.3	868.7	967.1	1026.3	1057.7	1070.9	1075.8	1075.8



TEST NUMBER: P333231-940

CATALOG NUMBER: S125DIP-S850D810U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	690.5	816.3	915.7	985.6	1031.4	1054.2	1066.3	1071.4
115°	633.1	741.2	836.7	912.7	967.1	1000.5	1020.0	1029.1
117.5°	596.0	689.1	771.4	841.2	895.5	930.1	949.5	955.0
120°	575.9	659.6	736.3	797.6	849.2	882.7	901.5	907.0
122.5°	560.9	638.4	706.7	764.2	810.2	840.9	859.7	864.7
125°	539.0	610.1	670.7	720.9	760.0	788.5	803.9	810.8
127.5°	516.7	583.0	639.6	686.6	722.0	747.3	761.8	764.8
130°	502.7	564.1	618.4	663.8	698.7	721.7	735.6	739.8
132.5°	488.7	546.2	595.6	639.2	674.0	697.1	709.9	714.6
135°	470.6	518.7	563.4	603.1	633.7	656.7	669.3	673.5
137.5°	455.3	494.2	531.3	565.0	592.5	613.4	625.0	629.6
140°	446.9	479.7	511.8	541.0	566.9	585.0	595.4	598.9
142.5°	439.7	467.4	495.0	520.4	542.3	557.7	567.6	570.4
145°	430.2	451.8	473.4	492.2	509.0	520.8	528.5	531.3
147.5°	421.2	438.8	455.4	469.7	482.9	492.4	496.9	498.1
150°	416.3	431.6	444.8	457.4	467.9	476.2	479.0	479.7
152.5°	410.6	424.4	436.5	446.2	455.0	461.7	464.5	465.2
155°	402.3	413.5	423.2	430.9	437.8	442.7	444.8	445.5
157.5°	394.0	403.1	410.6	416.7	422.1	426.1	428.1	427.9
160°	388.3	395.3	402.3	407.2	412.1	415.5	417.0	416.3
162.5°	382.2	388.6	394.5	398.8	402.6	405.5	405.8	405.6
165°	373.7	378.6	382.8	386.3	389.1	390.5	390.5	390.5
167.5°	365.6	368.8	372.0	374.5	375.9	377.2	376.7	376.5
170°	361.1	363.3	365.3	366.8	368.1	368.8	368.8	368.1
172.5°	356.1	358.2	359.8	360.6	360.9	362.1	361.1	360.3
175°	350.7	350.7	352.1	352.1	352.1	352.8	351.4	350.7
177.5°	347.0	347.5	347.5	347.5	347.0	347.5	345.8	345.8
180°	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8

(END OF REPORT)