

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333608-940

Luminaire Tested: **S125RDIP-S1090D1205U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333608-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1090D1205U940-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7483.7 lumens  
Efficiency: N/A  
Efficacy: 114.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 65.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333608-940

CATALOG NUMBER: S125RDIP-S1090D1205U940-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333608-940

CATALOG NUMBER: S125RDIP-S1090D1205U940-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	69	69	69	56	56	56	50
1	98	94	90	87	90	87	84	81	74	71	69	61	60	58	50	49	48	43
2	89	82	76	71	82	76	71	66	65	61	58	54	51	49	44	43	41	36
3	82	72	65	59	75	67	61	56	57	52	49	48	45	42	40	37	35	31
4	75	64	56	50	69	60	53	47	51	46	42	43	39	36	35	33	30	27
5	69	57	49	43	63	53	46	41	46	40	36	39	34	31	32	29	26	23
6	63	51	43	38	58	48	41	36	41	36	31	35	31	27	29	26	23	21
7	59	47	39	33	54	43	36	31	37	32	28	32	28	24	27	23	21	18
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	25	21	19	16
9	51	39	31	26	47	36	29	25	31	26	22	27	23	20	23	19	17	15
10	47	35	28	24	44	33	27	22	29	24	20	25	21	18	21	18	15	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10293	10293	10293
5°	10317	10200	10263
10°	10239	10105	10105
15°	10117	9900	9819
20°	9961	9614	9498
25°	9779	9333	9128
30°	9552	9004	8717
35°	9320	8665	8257
40°	9104	8312	7804
45°	8840	7916	7311
50°	8575	7486	6797
55°	8268	7076	6248
60°	7962	6577	5660
65°	7597	5997	4985
70°	7183	5274	4296
75°	6608	4447	3573
80°	5821	3492	2998
85°	4905	2853	2675



TEST NUMBER: P333608-940

CATALOG NUMBER: S125RDIP-S1090D1205U940-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	149.9	2.0
10°-20°	418.8	5.6
20°-30°	607.3	8.1
30°-40°	692.2	9.2
40°-50°	674.7	9.0
50°-60°	567.9	7.6
60°-70°	398.1	5.3
70°-80°	204.6	2.7
80°-90°	54.6	0.7
90°-100°	89.2	1.2
100°-110°	263.4	3.5
110°-120°	446.1	6.0
120°-130°	587.0	7.8
130°-140°	657.8	8.8
140°-150°	644.7	8.6
150°-160°	541.5	7.2
160°-170°	359.9	4.8
170°-180°	126.0	1.7
0°-30°	1176.0	15.7
0°-40°	1868.2	25.0
0°-60°	3110.9	41.6
0°-90°	3768.2	50.4
90°-120°	798.6	10.7
90°-150°	2688.1	35.9
90°-180°	3716.0	49.7
0°-180°	7483.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1594	1594	1594	1594	1594	
5°	1591	1586	1573	1585	1583	151
15°	1513	1505	1481	1479	1469	426
25°	1372	1353	1310	1294	1281	631
35°	1182	1152	1099	1065	1047	740
45°	968	931	867	820	800	746
55°	734	694	628	576	555	657
65°	497	455	392	346	326	492
75°	265	228	178	153	143	280
85°	66	45	38	37	36	74
90°	1	9	17	22	25	7
95°	67	70	80	87	89	72
105°	236	242	248	254	257	252
115°	447	451	453	452	451	442
125°	652	658	659	657	656	584
135°	848	854	855	855	851	653
145°	1027	1031	1034	1034	1031	642
155°	1175	1175	1176	1180	1175	541
165°	1278	1276	1277	1280	1274	360
175°	1328	1324	1324	1330	1323	126
180°	1332	1332	1332	1332	1332	



TEST NUMBER: P333608-940

CATALOG NUMBER: S125RDIP-S1090D1205U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8
2.5°	1596.7	1596.1	1595.4	1594.7	1594.1	1592.8	1590.6	1588.5	1586.4	1584.2	1586.4
5°	1591.4	1590.4	1589.3	1588.2	1587.2	1585.1	1582.2	1579.2	1576.3	1573.3	1576.0
7.5°	1575.7	1574.8	1573.7	1572.7	1571.6	1569.4	1565.8	1562.4	1558.8	1555.3	1557.2
10°	1561.3	1560.5	1559.7	1558.9	1558.1	1555.9	1552.1	1548.4	1544.6	1540.9	1541.7
12.5°	1544.9	1543.9	1542.9	1541.9	1540.9	1537.8	1532.9	1527.8	1522.8	1517.7	1518.3
15°	1513.1	1511.5	1509.9	1508.3	1506.7	1503.2	1497.5	1491.9	1486.3	1480.7	1480.4
17.5°	1477.3	1474.8	1472.4	1469.9	1467.4	1462.7	1455.6	1448.6	1441.5	1434.4	1433.1
20°	1449.4	1446.7	1444.0	1441.4	1438.7	1433.1	1424.5	1415.9	1407.4	1398.8	1397.5
22.5°	1418.5	1415.9	1413.2	1410.5	1407.8	1402.0	1393.0	1384.0	1375.0	1366.0	1363.4
25°	1372.3	1368.3	1364.3	1360.3	1356.3	1349.3	1339.4	1329.5	1319.6	1309.7	1306.3
27.5°	1319.4	1314.5	1309.6	1304.8	1299.8	1292.2	1281.6	1271.0	1260.3	1249.7	1244.9
30°	1280.9	1275.8	1270.7	1265.6	1260.5	1252.3	1241.1	1229.8	1218.6	1207.4	1201.2
32.5°	1243.2	1237.3	1231.4	1225.5	1219.5	1210.9	1199.4	1187.9	1176.4	1165.0	1158.2
35°	1182.1	1175.7	1169.3	1162.9	1156.5	1147.2	1135.1	1123.1	1111.1	1099.0	1091.3
37.5°	1122.1	1114.4	1106.5	1098.8	1090.9	1080.8	1068.4	1056.0	1043.6	1031.2	1021.8
40°	1079.8	1071.7	1063.7	1055.7	1047.7	1037.2	1024.4	1011.6	998.7	985.9	975.7
42.5°	1035.5	1027.3	1019.0	1010.8	1002.6	991.8	978.5	965.3	952.0	938.7	929.0
45°	967.9	960.1	952.3	944.6	936.8	925.6	910.9	896.2	881.5	866.7	856.0
47.5°	897.8	889.6	881.4	873.3	865.0	853.5	838.7	823.9	809.0	794.2	783.2
50°	853.5	844.6	835.8	827.0	818.1	806.1	790.9	775.6	760.4	745.1	733.9
52.5°	805.3	796.3	787.2	778.2	769.2	757.4	743.1	728.6	714.3	699.9	687.8
55°	734.3	725.8	717.2	708.6	700.1	688.3	673.3	658.4	643.4	628.4	616.4
57.5°	662.5	653.4	644.3	635.1	626.0	614.2	599.8	585.3	570.9	556.4	544.7
60°	616.4	607.0	597.6	588.3	578.9	566.9	552.5	538.1	523.6	509.2	497.4
62.5°	567.2	558.3	549.4	540.4	531.5	519.7	505.1	490.4	475.7	461.0	450.1
65°	497.1	488.0	478.9	469.8	460.7	449.2	435.0	420.8	406.6	392.4	381.7
67.5°	427.6	418.5	409.4	400.3	391.2	379.9	366.2	352.7	339.1	325.5	315.8
70°	380.4	371.3	362.2	353.1	344.0	332.8	319.4	306.0	292.7	279.3	271.0
72.5°	334.2	325.3	316.4	307.6	298.6	287.9	275.4	262.9	250.4	237.9	230.2
75°	264.8	256.8	248.8	240.8	232.7	223.1	211.9	200.6	189.4	178.2	172.3
77.5°	196.0	189.6	183.2	176.7	170.3	162.6	153.6	144.6	135.6	126.6	122.5
80°	156.5	150.1	143.7	137.2	130.8	123.9	116.4	108.9	101.4	93.9	91.5
82.5°	118.0	112.2	106.4	100.7	94.9	89.4	84.3	79.1	74.0	68.8	67.8
85°	66.2	61.3	56.5	51.7	46.9	43.9	42.5	41.2	39.9	38.5	38.3
87.5°	22.4	21.2	20.1	19.0	17.8	17.3	17.5	17.6	17.7	17.7	18.0
90°	1.1	2.9	4.7	6.6	8.4	10.2	11.8	13.4	15.0	16.6	17.7
92.5°	25.1	26.4	27.6	29.0	30.2	31.8	33.9	35.8	37.8	39.8	41.3
95°	67.3	67.8	68.3	68.8	69.2	70.5	72.9	75.2	77.5	79.8	81.4
97.5°	111.9	112.1	112.3	112.4	112.6	114.3	117.5	120.6	123.9	127.1	128.6
100°	145.1	145.1	145.1	145.1	145.1	146.6	149.5	152.6	155.5	158.5	160.6
102.5°	180.7	181.6	182.5	183.5	184.4	185.7	187.2	188.7	190.2	191.7	193.9
105°	236.2	237.4	238.5	239.7	240.9	242.1	243.5	244.9	246.3	247.6	249.1
107.5°	297.6	298.7	299.9	301.0	302.2	303.3	304.3	305.4	306.5	307.6	308.3
110°	339.9	341.0	342.1	343.3	344.5	345.4	346.1	346.8	347.5	348.1	348.8



TEST NUMBER: P333608-940

CATALOG NUMBER: S125RDIP-S1090D1205U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	383.0	383.6	384.1	384.8	385.4	386.1	387.0	387.9	388.7	389.6	389.9
115°	446.6	447.5	448.4	449.3	450.3	450.9	451.5	451.9	452.4	452.8	452.6
117.5°	510.4	510.9	511.3	511.7	512.1	512.5	512.9	513.4	513.7	514.2	514.3
120°	550.2	551.3	552.5	553.7	554.8	555.5	555.7	556.0	556.2	556.4	556.4
122.5°	593.3	593.8	594.1	594.6	594.9	595.5	596.1	596.7	597.3	597.9	597.7
125°	651.8	653.2	654.5	655.9	657.3	658.1	658.4	658.5	658.8	659.1	658.5
127.5°	714.0	714.7	715.5	716.3	717.1	717.6	717.9	718.2	718.5	718.7	718.5
130°	751.3	752.4	753.6	754.7	755.8	756.7	757.2	757.6	758.0	758.5	758.3
132.5°	788.5	790.4	792.4	794.2	796.1	797.0	796.9	796.8	796.7	796.7	796.4
135°	847.7	849.0	850.4	851.8	853.2	854.0	854.2	854.4	854.6	854.9	854.9
137.5°	903.1	904.5	905.8	907.1	908.5	909.5	909.9	910.4	911.0	911.4	911.7
140°	938.8	940.0	941.1	942.3	943.4	944.3	945.0	945.7	946.4	947.1	947.5
142.5°	974.5	975.4	976.4	977.3	978.3	979.3	980.1	981.0	981.9	982.8	983.0
145°	1026.9	1027.8	1028.8	1029.7	1030.6	1031.4	1032.1	1032.8	1033.4	1034.1	1034.1
147.5°	1075.4	1075.8	1076.4	1076.9	1077.4	1077.9	1078.5	1079.1	1079.6	1080.1	1080.7
150°	1107.7	1107.5	1107.2	1107.1	1106.8	1107.1	1108.0	1108.9	1109.9	1110.8	1110.8
152.5°	1134.3	1134.5	1134.9	1135.2	1135.5	1135.9	1136.2	1136.6	1137.0	1137.4	1137.9
155°	1175.1	1175.1	1175.1	1175.1	1175.1	1175.2	1175.5	1175.6	1175.9	1176.1	1177.1
157.5°	1211.6	1211.0	1210.5	1210.1	1209.5	1209.3	1209.6	1209.9	1210.1	1210.3	1211.2
160°	1233.1	1232.4	1231.7	1231.0	1230.3	1230.1	1230.3	1230.6	1230.8	1231.0	1231.9
162.5°	1252.1	1251.7	1251.2	1250.6	1250.1	1249.9	1249.9	1250.0	1250.0	1250.1	1251.2
165°	1277.6	1277.2	1276.8	1276.3	1275.8	1275.7	1275.9	1276.1	1276.4	1276.6	1277.6
167.5°	1299.2	1298.2	1297.4	1296.5	1295.5	1295.0	1295.0	1295.0	1295.0	1295.0	1296.5
170°	1310.8	1309.9	1308.9	1308.1	1307.2	1306.6	1306.6	1306.6	1306.6	1306.6	1308.1
172.5°	1319.1	1318.2	1317.2	1316.3	1315.5	1314.9	1314.9	1314.9	1314.9	1314.9	1316.3
175°	1328.4	1327.5	1326.6	1325.6	1324.7	1324.3	1324.3	1324.3	1324.3	1324.3	1325.6
177.5°	1333.2	1332.5	1331.7	1331.0	1330.3	1329.8	1329.6	1329.5	1329.2	1329.0	1330.2
180°	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5



TEST NUMBER: P333608-940

CATALOG NUMBER: S125RDIP-S1090D1205U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8
2.5°	1588.5	1590.6	1592.8	1593.7	1593.5	1593.3	1593.0	1592.9
5°	1578.7	1581.4	1584.0	1585.1	1584.6	1584.0	1583.5	1583.0
7.5°	1559.1	1560.9	1562.8	1563.4	1562.8	1562.3	1561.7	1561.0
10°	1542.5	1543.3	1544.1	1544.1	1543.3	1542.5	1541.7	1540.9
12.5°	1518.9	1519.5	1520.1	1519.7	1518.5	1517.3	1516.1	1514.8
15°	1480.2	1479.9	1479.6	1478.3	1475.9	1473.5	1471.1	1468.6
17.5°	1431.7	1430.4	1429.1	1427.5	1425.4	1423.4	1421.5	1419.5
20°	1396.2	1394.8	1393.5	1391.6	1389.2	1386.8	1384.4	1382.0
22.5°	1360.8	1358.2	1355.6	1353.3	1351.3	1349.3	1347.3	1345.3
25°	1302.8	1299.3	1295.8	1292.6	1289.7	1286.7	1283.8	1280.9
27.5°	1240.0	1235.2	1230.3	1226.5	1223.6	1220.8	1217.9	1215.1
30°	1195.1	1188.9	1182.8	1178.5	1176.1	1173.7	1171.3	1168.9
32.5°	1151.5	1144.6	1137.8	1132.9	1129.9	1126.9	1123.7	1120.7
35°	1083.5	1075.8	1068.0	1062.3	1058.5	1054.8	1051.1	1047.3
37.5°	1012.5	1003.3	993.9	987.5	983.8	980.2	976.5	972.9
40°	965.5	955.4	945.2	938.5	935.3	932.1	928.9	925.7
42.5°	919.3	909.5	899.7	892.5	887.8	883.2	878.4	873.7
45°	845.3	834.6	823.9	816.5	812.5	808.5	804.5	800.5
47.5°	772.2	761.2	750.2	742.4	738.0	733.5	729.2	724.7
50°	722.6	711.4	700.2	692.6	688.6	684.6	680.6	676.5
52.5°	675.7	663.6	651.5	643.5	639.4	635.4	631.4	627.4
55°	604.3	592.3	580.2	572.0	567.8	563.5	559.2	554.9
57.5°	532.9	521.1	509.3	501.5	497.8	493.9	490.1	486.3
60°	485.6	473.9	462.1	454.2	450.2	446.2	442.2	438.2
62.5°	439.3	428.3	417.4	409.9	405.9	401.9	397.9	393.9
65°	371.0	360.3	349.6	342.2	338.2	334.2	330.2	326.2
67.5°	305.9	296.1	286.3	279.8	276.6	273.4	270.2	267.0
70°	262.7	254.4	246.1	240.3	237.1	233.9	230.7	227.5
72.5°	222.6	214.9	207.2	202.3	200.2	198.0	195.9	193.8
75°	166.4	160.5	154.6	150.7	148.8	147.0	145.1	143.2
77.5°	118.4	114.3	110.1	107.4	106.0	104.6	103.3	101.8
80°	89.1	86.7	84.3	82.8	82.2	81.7	81.1	80.6
82.5°	66.6	65.5	64.4	63.7	63.3	63.0	62.7	62.3
85°	38.0	37.7	37.5	37.2	36.9	36.6	36.4	36.1
87.5°	18.2	18.5	18.7	18.7	18.7	18.6	18.5	18.5
90°	18.9	20.1	21.2	22.1	22.8	23.5	24.2	24.9
92.5°	42.8	44.3	45.8	46.9	47.3	47.9	48.4	48.9
95°	83.0	84.6	86.2	87.3	87.7	88.2	88.6	89.1
97.5°	130.1	131.6	133.1	134.0	134.3	134.6	134.8	135.1
100°	162.6	164.8	166.8	168.1	168.5	169.0	169.5	170.0
102.5°	196.2	198.5	200.7	202.2	202.9	203.5	204.1	204.7
105°	250.4	251.8	253.2	254.2	254.9	255.6	256.3	257.0
107.5°	308.9	309.6	310.3	310.7	310.6	310.6	310.5	310.4
110°	349.6	350.3	350.9	351.2	350.9	350.7	350.4	350.3





TEST NUMBER: P333608-940

CATALOG NUMBER: S125RDIP-S1090D1205U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	390.3	390.6	390.9	390.8	390.5	390.0	389.6	389.2
115°	452.4	452.1	451.9	451.7	451.5	451.2	450.9	450.8
117.5°	514.5	514.7	514.9	514.5	513.6	512.7	511.8	510.9
120°	556.4	556.4	556.4	556.0	555.1	554.1	553.2	552.3
122.5°	597.5	597.4	597.2	596.7	595.9	595.2	594.5	593.8
125°	658.1	657.6	657.2	656.8	656.7	656.4	656.1	655.9
127.5°	718.3	718.0	717.8	717.5	717.0	716.5	716.0	715.6
130°	758.0	757.8	757.6	757.2	756.8	756.3	755.8	755.4
132.5°	796.2	795.9	795.7	795.3	794.6	794.0	793.4	792.7
135°	854.9	854.9	854.9	854.4	853.5	852.6	851.7	850.7
137.5°	912.0	912.3	912.6	912.1	911.0	909.8	908.7	907.5
140°	948.0	948.5	949.0	948.6	947.4	946.3	945.1	944.0
142.5°	983.3	983.6	983.8	983.4	982.2	981.1	980.0	978.8
145°	1034.1	1034.1	1034.1	1033.8	1033.1	1032.4	1031.7	1031.0
147.5°	1081.3	1081.8	1082.4	1081.8	1080.3	1078.7	1077.2	1075.6
150°	1110.8	1110.8	1110.8	1110.6	1110.1	1109.6	1109.2	1108.8
152.5°	1138.4	1139.0	1139.5	1139.4	1138.6	1137.7	1136.9	1136.1
155°	1177.9	1178.8	1179.8	1179.6	1178.5	1177.3	1176.3	1175.1
157.5°	1212.1	1213.1	1214.0	1213.7	1212.2	1210.7	1209.2	1207.6
160°	1232.9	1233.8	1234.7	1234.6	1233.4	1232.3	1231.1	1230.0
162.5°	1252.3	1253.4	1254.5	1254.4	1253.0	1251.7	1250.4	1249.0
165°	1278.4	1279.3	1280.3	1280.1	1278.7	1277.3	1275.9	1274.5
167.5°	1297.8	1299.2	1300.6	1300.6	1299.1	1297.7	1296.3	1294.9
170°	1309.4	1310.8	1312.2	1312.1	1310.5	1308.9	1307.2	1305.6
172.5°	1317.7	1319.1	1320.4	1320.4	1319.0	1317.6	1316.2	1314.7
175°	1327.0	1328.4	1329.8	1329.7	1328.1	1326.5	1324.8	1323.2
177.5°	1331.2	1332.4	1333.5	1333.4	1332.1	1330.8	1329.5	1328.2
180°	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5

(END OF REPORT)