

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331308-930

Luminaire Tested: **SA2XXDIP-C485D725U930-4F0-1E-UDD-D4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331308-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C485D725U930-4F0-1E-UDD-D4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3912.0 lumens
Efficiency: N/A
Efficacy: 101.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.32 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.08')
CIE Type: Semi-Indirect

Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331308-930
CATALOG NUMBER: SA2XXDIP-C485D725U930-4F0-1E-UDD-D4

Luminous Intensity Polar Plot





TEST NUMBER: P331308-930

CATALOG NUMBER: SA2XXDIP-C485D725U930-4F0-1E-UDD-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36				36
1	94	89	85	81	84	80	77	74	65	62	60	50	48	47	37	36	35				28	
2	85	77	71	65	76	70	64	59	56	52	49	43	41	38	32	30	28				23	
3	77	67	60	54	69	61	54	49	49	44	40	38	35	32	28	26	24				19	
4	70	59	51	45	63	54	47	41	43	38	34	34	30	27	25	22	20				16	
5	64	53	44	38	58	48	40	35	39	33	29	30	26	23	22	19	17				14	
6	59	47	39	33	53	43	35	30	35	29	25	27	23	20	20	17	15				12	
7	55	42	34	29	49	38	31	26	31	26	22	24	20	18	18	15	13				10	
8	50	38	30	25	45	35	28	23	28	23	19	22	18	15	17	14	12				9	
9	47	35	27	22	42	32	25	20	26	21	17	20	17	14	15	13	11				8	
10	44	32	24	20	39	29	23	18	24	19	15	19	15	12	14	11	10				7	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6783	6783	6783
5°	6816	6530	6505
10°	6774	6337	6266
15°	6681	6133	6014
20°	6562	5913	5771
25°	6445	5701	5552
30°	6282	5486	5330
35°	6116	5276	5174
40°	5941	5099	5017
45°	5775	4940	4885
50°	5598	4794	4753
55°	5410	4638	4620
60°	5180	4477	4479
65°	4944	4290	4310
70°	4679	4085	4131
75°	4335	3888	3964
80°	3800	3685	3794
85°	3277	3510	3661



TEST NUMBER: P331308-930

CATALOG NUMBER: SA2XXDIP-C485D725U930-4F0-1E-UDD-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.8	1.0
10°-20°	114.2	2.9
20°-30°	173.0	4.4
30°-40°	210.7	5.4
40°-50°	226.7	5.8
50°-60°	220.1	5.6
60°-70°	192.2	4.9
70°-80°	148.0	3.8
80°-90°	102.3	2.6
90°-100°	200.9	5.1
100°-110°	499.6	12.8
110°-120°	510.7	13.1
120°-130°	411.7	10.5
130°-140°	323.5	8.3
140°-150°	240.0	6.1
150°-160°	167.7	4.3
160°-170°	98.7	2.5
170°-180°	32.1	0.8
0°-30°	327.0	8.4
0°-40°	537.7	13.7
0°-60°	984.5	25.2
0°-90°	1427.0	36.5
90°-120°	1211.3	31.0
90°-150°	2186.4	55.9
90°-180°	2485.0	63.5
0°-180°	3912.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	420	420	420	420	420	
5°	421	419	416	419	419	40
15°	402	403	403	408	408	113
25°	365	370	375	382	384	168
35°	315	325	337	350	354	197
45°	258	275	296	314	321	199
55°	198	220	251	273	281	177
65°	135	165	201	225	234	134
75°	75	109	148	173	182	79
85°	22	60	99	123	133	24
90°	7	50	102	124	133	5
95°	27	89	320	187	173	27
105°	81	139	525	917	799	86
115°	140	183	432	870	1007	138
125°	192	229	401	697	809	171
135°	225	269	382	574	660	174
145°	256	294	374	467	514	161
155°	291	314	363	410	426	134
165°	317	327	347	368	374	89
175°	331	331	334	338	337	31
180°	331	331	331	331	331	



TEST NUMBER: P331308-930

CATALOG NUMBER: SA2XXDIP-C485D725U930-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	420.1	420.1	420.1	420.1	420.1	420.1	420.1	420.1	420.1	420.1	420.1
2.5°	422.6	422.2	421.9	421.6	421.3	420.7	420.0	419.2	418.5	417.7	418.2
5°	421.3	420.9	420.5	420.1	419.7	419.1	418.3	417.5	416.7	415.9	416.7
7.5°	417.6	417.3	417.0	416.8	416.5	416.0	415.4	414.8	414.2	413.5	414.5
10°	414.7	414.4	414.1	413.8	413.6	413.3	412.9	412.5	412.1	411.6	412.7
12.5°	409.8	409.9	409.9	409.9	410.0	409.9	409.6	409.3	409.0	408.7	409.8
15°	401.9	402.1	402.4	402.7	402.9	403.1	403.1	403.1	403.1	403.1	404.3
17.5°	391.7	392.2	392.8	393.4	394.0	394.4	394.8	395.3	395.7	396.2	397.4
20°	384.8	385.5	386.2	386.9	387.5	388.2	388.7	389.2	389.8	390.3	391.8
22.5°	377.5	378.3	379.1	379.8	380.7	381.4	382.2	382.9	383.7	384.5	386.0
25°	365.3	366.3	367.2	368.2	369.1	370.2	371.5	372.7	373.9	375.0	376.7
27.5°	350.7	352.3	353.8	355.4	356.9	358.4	359.8	361.3	362.6	364.1	366.2
30°	341.0	342.8	344.5	346.3	348.1	349.8	351.6	353.3	355.1	356.8	359.0
32.5°	330.3	332.2	334.2	336.2	338.2	340.2	342.3	344.4	346.4	348.5	351.0
35°	314.8	317.1	319.4	321.7	324.0	326.4	329.0	331.6	334.1	336.7	339.7
37.5°	298.0	300.7	303.3	306.0	308.6	311.6	315.0	318.2	321.6	324.9	328.2
40°	286.8	289.8	292.8	295.7	298.7	302.0	305.7	309.3	313.0	316.7	320.2
42.5°	276.1	279.1	282.0	285.0	288.0	291.6	295.8	299.9	304.2	308.3	312.2
45°	258.2	261.8	265.5	269.1	272.8	277.0	281.7	286.4	291.2	296.0	300.1
47.5°	240.5	244.5	248.5	252.4	256.4	261.2	266.8	272.3	277.9	283.4	287.8
50°	228.4	232.5	236.8	240.9	245.1	250.2	256.3	262.4	268.6	274.6	279.2
52.5°	216.6	221.0	225.4	229.9	234.3	239.7	246.1	252.5	258.9	265.4	270.0
55°	197.9	202.8	207.7	212.5	217.4	223.3	230.4	237.4	244.4	251.4	256.3
57.5°	179.4	184.9	190.4	195.8	201.4	207.7	214.8	222.0	229.2	236.4	241.7
60°	166.2	172.0	177.9	183.7	189.5	196.2	204.0	211.7	219.4	227.1	232.3
62.5°	154.5	160.5	166.6	172.7	178.7	185.6	193.2	201.0	208.7	216.4	221.8
65°	135.2	141.8	148.5	155.1	161.7	169.0	177.0	185.0	193.0	201.0	206.5
67.5°	117.4	124.3	131.3	138.2	145.1	152.6	160.9	169.0	177.2	185.3	190.9
70°	104.8	111.8	118.8	125.8	132.9	140.6	149.0	157.4	165.8	174.1	179.9
72.5°	93.0	100.3	107.5	114.8	122.1	130.0	138.4	146.9	155.4	163.9	169.7
75°	74.9	82.5	90.0	97.6	105.2	113.3	122.0	130.6	139.3	148.0	153.8
77.5°	57.4	65.3	73.2	81.1	89.1	97.4	106.2	115.0	123.8	132.6	138.4
80°	45.7	53.9	62.2	70.4	78.7	87.2	96.0	104.8	113.6	122.4	128.1
82.5°	36.0	44.1	52.2	60.3	68.5	77.0	85.9	94.8	103.7	112.7	118.3
85°	21.9	30.3	38.7	47.1	55.4	64.0	72.6	81.3	90.0	98.7	104.4
87.5°	12.1	20.5	29.1	37.4	45.7	54.5	63.8	73.3	82.8	91.6	96.9
90°	6.8	16.5	26.9	36.0	45.2	55.3	67.2	80.2	92.8	102.1	106.8
92.5°	13.4	24.1	36.0	46.1	57.8	71.6	94.3	122.9	149.4	158.8	151.2
95°	27.1	36.1	48.8	60.9	77.5	100.0	137.5	201.0	283.1	319.8	293.8
97.5°	40.6	49.7	62.1	76.4	93.8	117.9	162.5	247.5	378.2	491.3	517.2
100°	53.3	60.3	71.0	86.2	104.0	128.1	169.4	254.8	400.0	564.4	661.1
102.5°	64.6	70.5	80.9	95.6	113.5	137.3	175.9	252.3	387.1	563.5	712.7
105°	80.8	87.2	95.6	109.2	127.1	150.4	187.4	251.2	363.4	524.6	698.9
107.5°	99.1	104.2	111.7	123.6	140.6	163.5	199.3	255.5	349.2	483.4	637.7
110°	110.8	116.0	122.5	133.5	149.6	172.8	207.5	260.0	344.4	463.2	599.4



TEST NUMBER: P331308-930

CATALOG NUMBER: SA2XXDIP-C485D725U930-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	122.0	126.8	133.5	143.5	158.7	181.9	215.2	264.9	341.8	448.6	571.5
115°	139.5	144.1	149.4	158.6	172.8	193.8	227.3	272.3	340.1	431.7	536.5
117.5°	156.9	160.5	165.3	173.0	186.2	207.3	238.4	280.5	340.2	420.7	512.3
120°	168.2	171.3	175.6	181.9	195.2	216.0	246.3	286.1	340.6	414.2	499.0
122.5°	178.9	181.2	185.2	191.6	204.6	225.6	254.0	291.0	341.5	409.2	487.2
125°	192.4	194.3	198.1	205.8	218.6	238.6	265.8	298.8	342.7	400.6	469.9
127.5°	203.7	206.0	211.2	219.6	231.6	251.7	277.4	306.7	344.6	394.0	453.7
130°	210.3	212.7	218.9	227.7	240.3	259.5	284.6	311.7	346.4	390.0	443.0
132.5°	216.4	219.3	226.1	235.4	248.5	267.3	290.8	316.7	348.2	386.6	433.8
135°	224.9	227.5	235.1	244.7	259.3	277.9	299.6	323.3	350.2	382.0	421.3
137.5°	233.6	236.7	244.3	254.5	269.0	285.8	306.6	327.9	351.7	378.4	411.4
140°	240.3	242.6	250.1	260.2	274.1	290.7	310.1	330.2	352.1	375.9	405.5
142.5°	246.9	248.7	255.8	265.9	279.2	294.7	313.4	332.7	352.9	375.0	400.6
145°	256.2	258.8	265.1	274.7	287.4	301.4	318.7	336.5	354.3	373.5	394.7
147.5°	266.9	268.8	274.9	283.7	294.3	306.8	323.0	338.7	354.9	371.2	389.1
150°	274.0	276.0	281.0	289.3	298.9	310.4	325.1	339.7	354.3	369.7	384.9
152.5°	281.2	282.1	287.1	294.4	303.5	314.0	327.1	340.2	353.4	367.1	381.4
155°	291.2	291.9	295.7	302.7	309.7	319.3	330.1	341.0	351.8	362.6	374.7
157.5°	299.7	300.3	303.4	309.5	315.1	323.1	332.3	341.0	348.9	358.1	368.5
160°	305.2	305.9	308.4	313.6	318.7	325.6	333.3	341.0	347.3	355.0	363.9
162.5°	310.9	310.5	313.1	317.2	321.7	327.2	333.9	340.5	345.8	352.5	359.8
165°	317.4	316.7	318.0	321.9	325.1	328.9	334.6	339.1	342.9	347.3	353.1
167.5°	322.8	322.0	323.1	325.5	327.8	330.3	334.4	338.2	340.0	342.9	346.4
170°	326.3	325.1	325.6	327.6	328.9	330.8	333.9	337.1	338.4	340.3	342.9
172.5°	328.3	327.6	327.2	329.1	329.9	331.3	333.5	335.6	336.4	337.3	339.3
175°	330.8	330.1	329.5	330.8	330.8	331.4	332.6	333.9	333.3	333.9	334.6
177.5°	331.9	330.9	330.4	331.4	331.4	331.4	331.9	333.0	331.9	331.4	331.9
180°	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4



TEST NUMBER: P331308-930

CATALOG NUMBER: SA2XXDIP-C485D725U930-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	420.1	420.1	420.1	420.1	420.1	420.1	420.1	420.1
2.5°	418.8	419.3	419.9	420.0	419.8	419.6	419.4	419.1
5°	417.5	418.3	419.1	419.5	419.3	419.2	419.1	418.9
7.5°	415.5	416.5	417.4	417.8	417.8	417.6	417.4	417.4
10°	413.8	414.8	416.0	416.5	416.3	416.1	416.0	415.9
12.5°	410.8	412.0	413.0	413.5	413.4	413.2	413.1	412.9
15°	405.5	406.8	408.0	408.5	408.4	408.2	408.1	408.0
17.5°	398.7	400.0	401.2	401.9	401.9	401.9	401.9	401.9
20°	393.3	394.8	396.2	397.0	397.0	397.0	397.0	397.0
22.5°	387.4	388.9	390.4	391.3	391.5	391.7	391.9	392.2
25°	378.3	379.9	381.6	382.6	383.0	383.4	383.8	384.3
27.5°	368.3	370.3	372.3	373.5	373.8	374.1	374.4	374.7
30°	361.2	363.3	365.5	366.7	367.1	367.5	367.9	368.4
32.5°	353.5	356.0	358.5	360.1	360.9	361.6	362.3	363.1
35°	342.7	345.7	348.6	350.6	351.6	352.5	353.4	354.4
37.5°	331.5	334.8	338.1	340.2	341.3	342.3	343.2	344.3
40°	323.7	327.2	330.7	333.0	334.3	335.5	336.7	337.9
42.5°	316.0	319.8	323.7	326.3	327.4	328.6	329.9	331.1
45°	304.4	308.5	312.7	315.4	316.8	318.2	319.5	320.9
47.5°	292.1	296.5	300.9	303.9	305.3	306.8	308.3	309.8
50°	283.8	288.4	293.0	296.0	297.6	299.1	300.5	302.0
52.5°	274.8	279.5	284.2	287.3	288.9	290.6	292.1	293.8
55°	261.2	266.1	270.9	274.3	276.1	277.8	279.6	281.3
57.5°	246.9	252.1	257.4	260.9	262.7	264.5	266.3	268.1
60°	237.4	242.6	247.7	251.2	253.1	255.0	256.9	258.8
62.5°	227.3	232.8	238.2	241.9	243.7	245.5	247.3	249.1
65°	212.1	217.6	223.1	226.8	228.5	230.3	232.0	233.8
67.5°	196.6	202.1	207.7	211.5	213.3	215.2	217.0	218.8
70°	185.8	191.6	197.4	201.1	202.8	204.4	206.0	207.7
72.5°	175.4	181.1	186.8	190.6	192.5	194.4	196.4	198.4
75°	159.6	165.4	171.2	175.0	176.8	178.6	180.3	182.1
77.5°	144.2	150.0	155.8	159.6	161.5	163.4	165.3	167.2
80°	133.8	139.4	145.1	148.9	150.8	152.7	154.6	156.5
82.5°	124.0	129.7	135.3	139.1	140.9	142.7	144.5	146.3
85°	110.0	115.7	121.4	125.1	127.0	129.0	130.9	132.7
87.5°	102.3	107.6	113.3	117.1	118.9	120.6	122.3	124.0
90°	111.6	115.7	122.5	126.5	128.2	129.8	131.4	133.1
92.5°	142.2	139.6	139.5	139.0	140.1	139.7	141.9	142.4
95°	247.3	213.5	191.9	181.3	174.6	171.1	170.9	173.1
97.5°	464.5	398.6	334.7	292.0	263.1	249.0	241.2	237.5
100°	652.8	578.8	496.4	422.6	371.2	345.3	328.2	318.3
102.5°	775.1	762.1	703.2	624.7	568.7	523.3	501.8	487.7
105°	836.2	913.0	925.9	908.0	870.0	832.0	806.1	798.7
107.5°	782.9	895.9	966.7	1000.6	1007.1	1006.4	1002.4	992.0
110°	738.3	856.6	942.6	997.7	1026.6	1040.2	1047.4	1048.3



TEST NUMBER: P331308-930

CATALOG NUMBER: SA2XXDIP-C485D725U930-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	697.1	810.9	902.5	965.2	1004.9	1026.6	1038.9	1043.8
115°	645.6	747.9	835.4	903.8	950.6	981.4	999.4	1006.7
117.5°	605.6	695.8	775.5	839.8	887.3	919.7	938.5	944.7
120°	584.9	667.7	739.1	799.7	845.8	877.3	897.2	905.1
122.5°	568.0	644.1	711.8	766.6	808.0	838.6	856.4	863.0
125°	543.0	612.3	672.0	722.3	760.4	785.9	803.0	809.3
127.5°	518.2	581.0	637.2	683.6	717.1	740.9	755.9	761.2
130°	502.3	560.4	614.0	658.2	690.6	713.3	727.1	733.3
132.5°	487.0	540.9	590.3	631.9	663.7	686.4	699.2	704.9
135°	465.5	510.5	555.3	593.0	621.5	643.6	656.2	659.7
137.5°	447.7	485.3	521.2	554.0	579.9	598.9	609.9	614.7
140°	436.3	469.1	500.6	530.1	551.4	568.8	579.1	583.8
142.5°	427.4	455.1	482.1	506.8	526.8	542.6	551.9	553.3
145°	415.2	437.1	457.6	476.9	492.8	504.3	511.4	514.0
147.5°	406.1	422.7	438.3	452.0	465.0	473.9	478.6	480.0
150°	400.2	414.3	427.6	439.1	448.7	456.3	460.2	460.8
152.5°	394.6	407.6	419.0	428.9	436.4	443.0	445.9	446.0
155°	386.9	397.1	406.6	413.6	420.6	425.1	427.6	426.4
157.5°	377.8	386.4	394.4	399.8	404.8	408.5	409.7	409.7
160°	372.2	379.2	386.2	390.7	395.2	398.4	398.9	398.9
162.5°	366.6	372.6	378.5	382.0	386.5	388.7	389.3	388.7
165°	358.2	362.6	367.1	369.7	372.2	374.7	374.7	374.1
167.5°	350.2	353.6	356.6	359.0	360.1	361.5	361.3	360.6
170°	346.1	348.0	350.5	351.8	352.5	354.3	353.7	352.5
172.5°	341.4	342.9	345.0	345.7	346.3	347.2	346.6	345.8
175°	336.5	337.1	337.8	338.4	338.4	339.1	338.4	337.1
177.5°	333.0	333.0	333.5	333.5	333.5	333.5	333.0	331.9
180°	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4

(END OF REPORT)