

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331318-930

Luminaire Tested: **SA2XXDIP-C485D925U930-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331318-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C485D925U930-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 925 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4629.2 lumens  
Efficiency: N/A  
Efficacy: 104.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 44.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331318-930

CATALOG NUMBER: SA2XXDIP-C485D925U930-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331318-930

CATALOG NUMBER: SA2XXDIP-C485D925U930-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35				
1	94	90	86	83	85	82	78	75	66	63	61	51	49	48	37	36	36	29				
2	86	79	73	68	77	71	66	62	57	54	51	45	42	40	33	31	30	25				
3	78	69	62	56	70	63	57	52	51	46	43	39	36	34	29	27	25	21				
4	72	61	53	48	64	55	49	44	45	40	36	35	32	29	26	24	22	18				
5	66	54	46	41	59	49	43	37	40	35	31	31	28	25	23	21	19	16				
6	60	49	41	35	54	44	37	32	36	31	27	28	25	22	21	19	17	14				
7	56	44	36	31	50	40	33	28	33	28	24	26	22	19	19	17	15	12				
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	15	13	11				
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12	10				
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	13	11	9				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10224	10224	10224
5°	10263	10115	10175
10°	10203	10012	10063
15°	10076	9884	9872
20°	9897	9689	9677
25°	9720	9449	9449
30°	9491	9229	9148
35°	9278	8966	8834
40°	9010	8703	8534
45°	8745	8439	8229
50°	8457	8166	7877
55°	8158	7848	7561
60°	7824	7472	7195
65°	7465	7095	6770
70°	7010	6637	6326
75°	6382	6114	5964
80°	5662	5486	5207
85°	4613	4390	3946



TEST NUMBER: P331318-930

CATALOG NUMBER: SA2XXDIP-C485D925U930-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	59.5	1.3
10°-20°	167.6	3.6
20°-30°	246.3	5.3
30°-40°	286.1	6.2
40°-50°	285.8	6.2
50°-60°	249.2	5.4
60°-70°	184.3	4.0
70°-80°	104.4	2.3
80°-90°	30.6	0.7
90°-100°	34.3	0.7
100°-110°	125.9	2.7
110°-120°	336.5	7.3
120°-130°	555.4	12.0
130°-140°	590.7	12.8
140°-150°	549.0	11.9
150°-160°	441.4	9.5
160°-170°	284.5	6.1
170°-180°	97.9	2.1
0°-30°	473.4	10.2
0°-40°	759.4	16.4
0°-60°	1294.4	28.0
0°-90°	1613.6	34.9
90°-120°	496.7	10.7
90°-150°	2191.9	47.3
90°-180°	3016.0	65.2
0°-180°	4629.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	633	633	633	633	633	
5°	633	631	624	629	628	60
15°	603	599	591	593	591	170
25°	546	540	530	531	530	251
35°	471	464	455	451	448	294
45°	383	378	370	363	360	295
55°	290	286	279	272	269	259
65°	195	192	186	180	177	193
75°	102	101	98	95	96	109
85°	25	24	24	22	21	29
90°	1	9	15	18	20	3
95°	48	26	29	33	32	59
105°	226	236	45	53	57	242
115°	428	441	459	131	61	421
125°	605	615	629	634	637	540
135°	749	761	768	775	774	578
145°	869	869	881	886	882	543
155°	957	951	959	963	958	441
165°	1008	1004	1006	1011	1006	285
175°	1031	1026	1028	1032	1025	98
180°	1029	1029	1029	1029	1029	



TEST NUMBER: P331318-930

CATALOG NUMBER: SA2XXDIP-C485D925U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2
2.5°	636.2	635.6	635.1	634.5	634.0	633.2	631.9	630.8	629.6	628.4	629.5
5°	633.2	632.7	632.2	631.6	631.1	630.1	628.6	627.1	625.6	624.1	625.2
7.5°	627.6	626.8	626.0	625.1	624.3	623.1	621.6	620.1	618.6	617.0	618.2
10°	622.3	621.3	620.4	619.5	618.5	617.2	615.6	614.0	612.4	610.7	611.8
12.5°	615.0	614.2	613.3	612.5	611.6	610.4	608.8	607.2	605.5	603.9	604.6
15°	602.8	602.0	601.2	600.4	599.6	598.3	596.5	594.8	593.0	591.3	591.7
17.5°	587.2	586.4	585.6	584.8	584.0	582.7	580.9	579.1	577.3	575.5	576.2
20°	576.0	575.2	574.4	573.6	572.7	571.4	569.5	567.6	565.7	563.9	564.3
22.5°	564.8	563.7	562.6	561.4	560.3	558.8	557.0	555.2	553.4	551.6	551.7
25°	545.6	544.5	543.4	542.3	541.3	539.6	537.3	534.9	532.6	530.4	530.6
27.5°	523.7	522.7	521.7	520.7	519.8	518.4	516.6	514.7	512.9	511.1	510.7
30°	509.1	507.9	506.9	505.8	504.7	503.1	501.1	499.1	497.1	495.0	494.6
32.5°	493.4	492.6	491.7	490.8	490.0	488.4	486.3	484.2	482.1	480.0	479.2
35°	470.7	469.3	468.0	466.6	465.3	463.5	461.4	459.2	457.0	454.9	454.0
37.5°	445.0	443.8	442.6	441.4	440.2	438.5	436.3	434.2	432.0	429.9	428.8
40°	427.5	426.3	425.3	424.2	423.1	421.5	419.3	417.2	415.0	412.9	411.6
42.5°	410.4	409.3	408.2	407.2	406.1	404.5	402.3	400.1	397.9	395.7	394.4
45°	383.0	382.0	381.1	380.2	379.2	377.7	375.7	373.7	371.6	369.6	368.1
47.5°	355.7	354.8	353.9	353.0	352.1	350.7	348.5	346.4	344.3	342.2	340.6
50°	336.7	336.1	335.3	334.7	334.0	332.7	330.8	329.0	327.0	325.1	323.3
52.5°	318.2	317.3	316.4	315.5	314.6	313.3	311.5	309.7	307.9	306.1	304.6
55°	289.8	289.0	288.2	287.4	286.6	285.4	283.7	282.1	280.5	278.8	277.3
57.5°	261.3	260.7	260.0	259.4	258.8	257.6	255.8	254.0	252.2	250.4	248.7
60°	242.3	241.8	241.2	240.7	240.2	239.0	237.1	235.1	233.3	231.4	229.9
62.5°	223.8	223.0	222.1	221.2	220.4	219.2	217.8	216.3	214.8	213.4	212.0
65°	195.4	194.6	193.8	193.0	192.2	191.1	189.8	188.4	187.0	185.7	184.5
67.5°	166.6	165.9	165.3	164.6	164.0	163.1	161.8	160.6	159.4	158.2	157.3
70°	148.5	148.1	147.5	146.9	146.4	145.5	144.3	143.1	141.9	140.6	139.7
72.5°	130.0	129.6	129.0	128.4	127.9	127.3	126.5	125.6	124.9	124.1	123.1
75°	102.3	102.0	101.7	101.5	101.2	100.8	100.0	99.4	98.7	98.0	97.2
77.5°	77.5	77.0	76.6	76.1	75.6	75.3	75.0	74.7	74.4	74.2	73.8
80°	60.9	60.7	60.7	60.5	60.3	60.2	59.8	59.6	59.4	59.0	58.6
82.5°	45.3	45.2	45.2	45.2	45.2	45.1	44.9	44.8	44.6	44.4	43.9
85°	24.9	24.9	24.7	24.5	24.5	24.3	24.1	24.1	23.9	23.7	23.3
87.5°	8.9	9.0	9.2	9.4	9.5	9.6	9.6	9.7	9.8	9.8	9.6
90°	0.7	2.5	4.4	6.2	8.0	9.6	10.9	12.2	13.5	14.9	15.7
92.5°	15.0	14.8	14.7	14.5	14.3	14.6	15.3	16.0	16.6	17.3	17.7
95°	48.4	43.0	37.5	32.0	26.6	24.4	25.6	26.7	27.9	29.0	29.8
97.5°	96.0	80.6	65.3	49.9	34.5	28.1	30.8	33.5	36.2	38.9	39.5
100°	131.8	109.1	86.4	63.8	41.1	31.2	34.0	36.9	39.6	42.5	43.8
102.5°	171.1	166.3	161.5	156.7	151.9	137.8	114.2	90.7	67.2	43.6	45.3
105°	226.3	231.3	236.3	241.2	246.2	226.1	180.9	135.7	90.6	45.4	47.2
107.5°	289.3	293.3	297.3	301.3	305.4	280.3	226.1	171.9	117.7	63.6	61.7
110°	329.9	333.4	336.8	340.3	343.7	321.6	273.8	225.9	178.1	130.3	113.7



TEST NUMBER: P331318-930

CATALOG NUMBER: SA2XXDIP-C485D925U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	367.9	371.0	374.1	377.2	380.3	375.9	364.1	352.3	340.5	328.6	268.3
115°	428.1	431.0	433.7	436.6	439.4	442.9	447.0	451.2	455.3	459.4	382.8
117.5°	481.9	485.0	488.2	491.4	494.5	497.5	500.3	503.2	506.1	508.8	490.3
120°	521.2	523.7	526.2	528.6	531.2	533.9	536.9	539.8	542.8	545.8	547.8
122.5°	554.6	557.2	559.8	562.4	565.0	567.9	571.2	574.5	577.7	581.0	582.1
125°	605.4	607.5	609.7	611.8	614.0	616.6	619.8	622.9	626.1	629.2	630.4
127.5°	651.3	653.8	656.2	658.5	660.9	663.2	665.6	668.0	670.3	672.7	674.3
130°	680.6	683.2	685.8	688.5	691.1	693.4	695.2	697.0	698.9	700.7	702.5
132.5°	710.4	712.6	714.9	717.1	719.3	721.4	723.3	725.0	726.8	728.6	730.3
135°	749.1	751.7	754.4	757.0	759.7	761.7	763.2	764.8	766.2	767.7	769.3
137.5°	788.2	790.1	792.0	793.8	795.7	797.4	799.1	800.8	802.5	804.2	805.8
140°	813.8	815.2	816.5	817.8	819.1	820.8	822.6	824.3	826.2	828.0	829.5
142.5°	835.3	836.5	837.7	838.9	840.1	841.7	843.8	845.9	848.0	850.0	851.4
145°	868.9	868.8	868.6	868.5	868.3	869.6	872.5	875.2	878.1	880.8	882.0
147.5°	898.3	897.6	897.1	896.4	895.8	896.8	899.6	902.5	905.2	908.0	908.8
150°	917.4	916.2	915.0	913.9	912.7	913.5	916.2	918.8	921.5	924.1	925.0
152.5°	933.4	932.1	930.8	929.6	928.3	928.9	931.4	933.9	936.5	939.0	940.0
155°	956.8	955.4	953.8	952.4	950.9	951.1	953.1	955.1	957.1	959.0	960.0
157.5°	975.1	973.9	972.7	971.3	970.1	970.2	971.6	973.0	974.4	975.8	976.9
160°	985.9	984.9	983.9	982.8	981.9	981.9	982.8	983.9	984.9	985.9	986.8
162.5°	995.4	994.4	993.4	992.4	991.4	991.3	992.2	993.0	993.9	994.8	995.9
165°	1008.2	1007.2	1006.2	1005.2	1004.2	1004.0	1004.4	1004.9	1005.5	1006.0	1007.1
167.5°	1017.7	1016.8	1015.8	1014.7	1013.7	1013.5	1014.0	1014.4	1014.9	1015.4	1016.5
170°	1023.1	1022.1	1021.1	1020.1	1019.1	1018.8	1019.1	1019.5	1019.8	1020.1	1021.2
172.5°	1026.6	1025.6	1024.7	1023.7	1022.7	1022.4	1022.7	1023.0	1023.4	1023.7	1024.8
175°	1031.3	1030.1	1029.0	1027.8	1026.6	1026.2	1026.5	1026.9	1027.2	1027.5	1028.7
177.5°	1032.0	1031.1	1030.2	1029.2	1028.3	1027.9	1028.1	1028.2	1028.3	1028.4	1029.4
180°	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1



TEST NUMBER: P331318-930

CATALOG NUMBER: SA2XXDIP-C485D925U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2
2.5°	630.6	631.6	632.7	633.2	632.9	632.7	632.5	632.3
5°	626.3	627.4	628.4	628.8	628.6	628.3	628.0	627.8
7.5°	619.2	620.3	621.4	621.7	621.5	621.2	620.9	620.6
10°	612.9	614.0	615.1	615.4	615.0	614.6	614.2	613.8
12.5°	605.4	606.2	606.9	607.2	606.8	606.6	606.3	605.9
15°	592.3	592.9	593.4	593.3	592.6	592.0	591.3	590.6
17.5°	576.7	577.4	578.0	578.0	577.3	576.7	576.1	575.4
20°	564.7	565.1	565.5	565.4	564.8	564.3	563.8	563.2
22.5°	551.8	551.9	552.0	551.9	551.5	551.2	550.9	550.6
25°	530.9	531.2	531.4	531.4	531.2	530.9	530.6	530.4
27.5°	510.3	509.9	509.5	509.0	508.3	507.7	507.0	506.4
30°	494.2	493.8	493.4	492.9	492.4	491.9	491.3	490.7
32.5°	478.5	477.8	477.0	476.4	475.8	475.3	474.7	474.2
35°	453.2	452.4	451.6	450.9	450.2	449.5	448.8	448.2
37.5°	427.9	426.9	425.9	425.0	424.4	423.7	423.1	422.5
40°	410.4	409.2	408.0	407.1	406.5	406.0	405.4	404.9
42.5°	393.1	391.8	390.4	389.5	388.7	387.9	387.2	386.4
45°	366.6	365.2	363.6	362.6	362.1	361.6	361.0	360.4
47.5°	339.1	337.5	335.9	334.8	333.9	333.2	332.4	331.6
50°	321.4	319.4	317.6	316.3	315.6	315.0	314.2	313.6
52.5°	303.0	301.4	299.9	298.6	297.7	296.9	296.0	295.1
55°	275.7	274.0	272.4	271.3	270.5	269.9	269.2	268.6
57.5°	247.2	245.6	244.0	243.0	242.4	241.9	241.4	240.8
60°	228.4	226.9	225.4	224.5	224.0	223.6	223.2	222.8
62.5°	210.6	209.2	207.8	206.9	206.4	205.9	205.4	204.8
65°	183.3	182.1	180.8	179.9	179.2	178.6	177.9	177.2
67.5°	156.3	155.3	154.4	153.7	153.1	152.5	152.1	151.5
70°	138.8	137.8	136.9	136.2	135.6	135.0	134.5	134.0
72.5°	122.2	121.2	120.3	119.6	119.2	118.7	118.3	117.9
75°	96.4	95.6	94.8	94.5	94.8	95.1	95.3	95.6
77.5°	73.4	73.0	72.6	72.2	71.7	71.4	71.0	70.6
80°	58.2	57.8	57.5	57.1	56.8	56.6	56.3	56.0
82.5°	43.5	42.9	42.4	42.1	42.1	42.0	41.9	41.9
85°	22.9	22.5	22.1	21.9	21.7	21.6	21.4	21.3
87.5°	9.5	9.3	9.1	9.0	9.0	9.0	9.0	8.9
90°	16.6	17.4	18.2	18.8	19.1	19.4	19.8	20.1
92.5°	18.1	18.6	19.0	19.3	19.5	19.7	19.9	20.1
95°	30.7	31.6	32.4	32.7	32.5	32.4	32.2	32.0
97.5°	40.2	40.8	41.5	41.9	42.2	42.3	42.6	42.7
100°	45.1	46.4	47.8	48.6	48.9	49.2	49.6	49.9
102.5°	47.0	48.8	50.5	51.6	52.1	52.5	53.0	53.5
105°	49.1	50.9	52.7	54.0	54.6	55.3	55.9	56.6
107.5°	59.8	58.0	56.2	55.6	56.3	56.9	57.6	58.2
110°	97.2	80.6	64.1	56.2	56.8	57.5	58.1	58.9





TEST NUMBER: P331318-930

CATALOG NUMBER: SA2XXDIP-C485D925U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	208.0	147.6	87.2	57.3	57.8	58.4	58.9	59.4
115°	306.2	229.6	153.0	108.7	96.8	84.9	73.0	61.1
117.5°	471.8	453.3	434.7	405.9	366.7	327.6	288.5	249.3
120°	549.8	551.8	553.8	543.6	521.2	498.9	476.5	454.2
122.5°	583.3	584.5	585.7	584.2	579.8	575.4	571.1	566.8
125°	631.5	632.7	633.8	634.6	635.1	635.6	636.2	636.7
127.5°	676.0	677.8	679.5	680.3	680.4	680.5	680.6	680.7
130°	704.3	706.1	707.9	708.8	708.7	708.4	708.3	708.1
132.5°	731.8	733.4	734.9	735.6	735.4	735.2	735.1	734.9
135°	771.0	772.7	774.3	774.9	774.6	774.3	774.0	773.6
137.5°	807.4	809.0	810.7	811.2	810.7	810.1	809.5	808.9
140°	831.0	832.5	834.0	834.3	833.5	832.7	831.8	831.0
142.5°	852.7	854.1	855.5	855.7	854.9	854.1	853.3	852.4
145°	883.2	884.4	885.5	885.7	884.8	884.0	883.2	882.4
147.5°	909.7	910.5	911.4	911.5	910.8	910.1	909.4	908.7
150°	926.0	927.1	928.1	928.1	927.3	926.4	925.6	924.8
152.5°	940.9	941.9	942.9	942.9	941.8	940.7	939.6	938.5
155°	961.1	962.1	963.0	962.9	961.6	960.2	958.9	957.6
157.5°	978.0	979.1	980.2	980.2	978.8	977.5	976.2	975.0
160°	987.8	988.9	989.9	989.8	988.6	987.4	986.3	985.1
162.5°	997.0	998.2	999.3	999.1	997.8	996.3	994.9	993.4
165°	1008.3	1009.4	1010.6	1010.6	1009.4	1008.3	1007.1	1006.0
167.5°	1017.7	1018.8	1020.0	1019.8	1018.3	1016.8	1015.4	1013.8
170°	1022.5	1023.6	1024.7	1024.6	1023.1	1021.6	1020.1	1018.6
172.5°	1026.0	1027.2	1028.3	1028.2	1026.6	1025.2	1023.7	1022.2
175°	1029.9	1031.0	1032.2	1031.9	1030.3	1028.7	1027.0	1025.3
177.5°	1030.3	1031.3	1032.2	1032.0	1030.9	1029.6	1028.4	1027.3
180°	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1

(END OF REPORT)