

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331320-930

Luminaire Tested: **SA2XXDIP-C485D925U930-4F0-1E-UDD-F4**

Issue Date: 10/7/2019


Test Information

Test Method: LM-79-08
Report Number: P331320-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C485D925U930-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4559.2 lumens
Efficiency: N/A
Efficacy: 102.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331320-930

CATALOG NUMBER: SA2XXDIP-C485D925U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331320-930

CATALOG NUMBER: SA2XXDIP-C485D925U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35
1	95	90	86	83	85	82	79	76	66	64	62	51	50	48	38	37	36	30
2	86	79	73	68	78	71	66	62	58	54	51	45	43	40	33	32	30	25
3	78	69	62	56	71	63	57	52	51	46	43	40	37	34	29	27	26	21
4	72	61	53	48	65	56	49	44	45	40	36	35	32	29	26	24	22	18
5	66	54	46	41	59	50	43	37	40	35	31	32	28	25	24	21	19	16
6	60	49	41	35	54	44	37	32	36	31	27	29	25	22	21	19	17	14
7	56	44	36	31	50	40	33	28	33	28	24	26	22	19	20	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	15	14	11
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	17	14	12	10
10	45	33	26	21	41	30	24	20	25	20	17	20	16	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10224	10224	10224
5°	10263	10115	10175
10°	10203	10012	10063
15°	10076	9884	9872
20°	9897	9689	9677
25°	9720	9449	9449
30°	9491	9229	9148
35°	9278	8966	8834
40°	9010	8703	8534
45°	8745	8439	8229
50°	8457	8166	7877
55°	8158	7848	7561
60°	7824	7472	7195
65°	7465	7095	6770
70°	7010	6637	6326
75°	6382	6114	5964
80°	5662	5486	5207
85°	4613	4390	3946



TEST NUMBER: P331320-930

CATALOG NUMBER: SA2XXDIP-C485D925U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.5	1.3
10°-20°	167.6	3.7
20°-30°	246.3	5.4
30°-40°	286.1	6.3
40°-50°	285.8	6.3
50°-60°	249.2	5.5
60°-70°	184.3	4.0
70°-80°	104.4	2.3
80°-90°	31.9	0.7
90°-100°	169.2	3.7
100°-110°	574.1	12.6
110°-120°	609.9	13.4
120°-130°	502.1	11.0
130°-140°	403.2	8.8
140°-150°	304.7	6.7
150°-160°	214.1	4.7
160°-170°	126.0	2.8
170°-180°	41.0	0.9
0°-30°	473.4	10.4
0°-40°	759.4	16.7
0°-60°	1294.4	28.4
0°-90°	1614.9	35.4
90°-120°	1353.2	29.7
90°-150°	2563.1	56.2
90°-180°	2944.0	64.6
0°-180°	4559.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	633	633	633	633	633	
5°	633	631	624	629	628	60
15°	603	599	591	593	591	170
25°	546	540	530	531	530	251
35°	471	464	455	451	448	294
45°	383	378	370	363	360	295
55°	290	286	279	272	269	259
65°	195	192	186	180	177	193
75°	102	101	98	95	96	109
85°	25	24	24	22	21	29
90°	1	11	28	26	27	3
95°	28	70	319	120	93	30
105°	99	150	603	1078	917	106
115°	175	221	504	1041	1207	173
125°	244	289	485	843	979	217
135°	286	342	479	709	811	221
145°	327	376	477	592	648	205
155°	372	402	463	524	544	171
165°	405	417	443	470	478	114
175°	422	423	426	432	430	40
180°	423	423	423	423	423	



TEST NUMBER: P331320-930

CATALOG NUMBER: SA2XXDIP-C485D925U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2
2.5°	636.2	635.6	635.1	634.5	634.0	633.2	631.9	630.8	629.6	628.4	629.5
5°	633.2	632.7	632.2	631.6	631.1	630.1	628.6	627.1	625.6	624.1	625.2
7.5°	627.6	626.8	626.0	625.1	624.3	623.1	621.6	620.1	618.6	617.0	618.2
10°	622.3	621.3	620.4	619.5	618.5	617.2	615.6	614.0	612.4	610.7	611.8
12.5°	615.0	614.2	613.3	612.5	611.6	610.4	608.8	607.2	605.5	603.9	604.6
15°	602.8	602.0	601.2	600.4	599.6	598.3	596.5	594.8	593.0	591.3	591.7
17.5°	587.2	586.4	585.6	584.8	584.0	582.7	580.9	579.1	577.3	575.5	576.2
20°	576.0	575.2	574.4	573.6	572.7	571.4	569.5	567.6	565.7	563.9	564.3
22.5°	564.8	563.7	562.6	561.4	560.3	558.8	557.0	555.2	553.4	551.6	551.7
25°	545.6	544.5	543.4	542.3	541.3	539.6	537.3	534.9	532.6	530.4	530.6
27.5°	523.7	522.7	521.7	520.7	519.8	518.4	516.6	514.7	512.9	511.1	510.7
30°	509.1	507.9	506.9	505.8	504.7	503.1	501.1	499.1	497.1	495.0	494.6
32.5°	493.4	492.6	491.7	490.8	490.0	488.4	486.3	484.2	482.1	480.0	479.2
35°	470.7	469.3	468.0	466.6	465.3	463.5	461.4	459.2	457.0	454.9	454.0
37.5°	445.0	443.8	442.6	441.4	440.2	438.5	436.3	434.2	432.0	429.9	428.8
40°	427.5	426.3	425.3	424.2	423.1	421.5	419.3	417.2	415.0	412.9	411.6
42.5°	410.4	409.3	408.2	407.2	406.1	404.5	402.3	400.1	397.9	395.7	394.4
45°	383.0	382.0	381.1	380.2	379.2	377.7	375.7	373.7	371.6	369.6	368.1
47.5°	355.7	354.8	353.9	353.0	352.1	350.7	348.5	346.4	344.3	342.2	340.6
50°	336.7	336.1	335.3	334.7	334.0	332.7	330.8	329.0	327.0	325.1	323.3
52.5°	318.2	317.3	316.4	315.5	314.6	313.3	311.5	309.7	307.9	306.1	304.6
55°	289.8	289.0	288.2	287.4	286.6	285.4	283.7	282.1	280.5	278.8	277.3
57.5°	261.3	260.7	260.0	259.4	258.8	257.6	255.8	254.0	252.2	250.4	248.7
60°	242.3	241.8	241.2	240.7	240.2	239.0	237.1	235.1	233.3	231.4	229.9
62.5°	223.8	223.0	222.1	221.2	220.4	219.2	217.8	216.3	214.8	213.4	212.0
65°	195.4	194.6	193.8	193.0	192.2	191.1	189.8	188.4	187.0	185.7	184.5
67.5°	166.6	165.9	165.3	164.6	164.0	163.1	161.8	160.6	159.4	158.2	157.3
70°	148.5	148.1	147.5	146.9	146.4	145.5	144.3	143.1	141.9	140.6	139.7
72.5°	130.0	129.6	129.0	128.4	127.9	127.3	126.5	125.6	124.9	124.1	123.1
75°	102.3	102.0	101.7	101.5	101.2	100.8	100.0	99.4	98.7	98.0	97.2
77.5°	77.5	77.0	76.6	76.1	75.6	75.3	75.0	74.7	74.4	74.2	73.8
80°	60.9	60.7	60.7	60.5	60.3	60.2	59.8	59.6	59.4	59.0	58.6
82.5°	45.3	45.2	45.2	45.2	45.2	45.1	44.9	44.8	44.6	44.4	43.9
85°	24.9	24.9	24.7	24.5	24.5	24.3	24.1	24.1	23.9	23.7	23.3
87.5°	9.0	9.2	9.6	9.8	9.9	10.1	10.8	11.7	12.4	12.4	11.9
90°	0.8	3.3	6.5	8.2	9.8	12.2	16.3	21.9	26.8	27.6	26.8
92.5°	9.9	14.3	20.2	23.7	29.3	36.9	55.4	81.2	104.3	105.7	89.4
95°	28.5	31.7	39.9	47.2	60.3	79.7	117.2	187.9	282.3	318.9	279.1
97.5°	46.4	50.8	59.4	70.4	85.4	107.5	154.6	253.2	410.1	544.5	571.2
100°	62.6	65.1	72.4	85.4	101.7	124.5	167.6	266.9	442.6	642.8	760.0
102.5°	77.6	79.4	86.7	99.8	116.7	139.5	179.4	267.6	430.3	646.0	830.3
105°	99.3	102.6	108.2	120.4	138.4	161.1	199.3	271.7	406.0	602.9	819.4
107.5°	122.7	125.3	130.9	142.1	159.8	182.8	219.9	283.0	394.0	556.8	748.0
110°	138.4	141.6	146.4	157.0	174.1	197.7	233.5	292.1	391.4	534.6	703.0



TEST NUMBER: P331320-930

CATALOG NUMBER: SA2XXDIP-C485D925U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	152.6	155.9	161.4	171.4	187.8	212.1	246.5	301.9	392.0	520.2	671.8
115°	175.0	179.0	183.9	193.6	209.9	231.9	266.9	316.5	395.4	504.5	633.1
117.5°	198.0	201.3	206.2	214.8	230.4	253.2	285.6	332.2	401.3	496.8	608.6
120°	212.4	215.6	220.5	227.8	244.1	266.9	298.6	342.6	405.2	492.3	595.7
122.5°	226.1	228.6	233.5	241.5	257.8	281.2	311.0	351.6	409.8	489.7	584.6
125°	244.1	246.5	251.4	261.2	277.4	300.3	329.5	366.2	416.6	484.9	568.8
127.5°	258.4	261.7	268.5	279.2	294.9	318.3	346.8	379.7	423.6	482.2	554.2
130°	266.9	270.1	278.3	289.7	306.0	328.7	357.2	388.2	428.8	480.9	544.4
132.5°	274.7	278.6	287.4	299.5	316.3	339.2	366.3	396.6	434.0	480.2	536.5
135°	286.4	289.7	299.5	311.6	330.4	353.1	379.2	407.6	440.2	479.2	525.6
137.5°	297.5	301.4	311.1	324.2	342.8	363.9	389.6	416.1	445.7	479.1	518.0
140°	306.0	309.2	318.9	332.0	349.9	371.0	395.4	420.7	448.3	478.4	513.5
142.5°	314.4	317.0	326.1	339.2	356.4	376.3	400.0	424.6	450.3	478.4	508.9
145°	327.1	330.4	338.5	350.7	367.0	384.9	406.8	429.7	452.4	476.8	502.9
147.5°	340.8	343.2	351.0	362.2	375.8	391.8	412.4	432.4	453.1	473.9	496.7
150°	349.9	352.3	358.8	369.4	381.6	396.2	415.0	433.7	452.4	472.0	491.5
152.5°	359.0	360.1	366.6	375.9	387.5	400.8	417.6	434.3	451.1	468.7	486.9
155°	371.9	372.7	377.6	386.5	395.4	407.6	421.5	435.3	449.1	463.0	478.4
157.5°	382.6	383.4	387.3	395.1	402.3	412.5	424.3	435.3	445.4	457.1	470.5
160°	389.8	390.6	393.8	400.3	406.8	415.8	425.6	435.3	443.4	453.2	464.6
162.5°	396.9	396.4	399.7	404.9	410.7	417.8	426.2	434.6	441.5	450.0	459.4
165°	405.2	404.4	406.0	410.9	415.0	419.9	427.2	432.9	437.7	443.4	450.8
167.5°	412.1	411.1	412.5	415.6	418.6	421.7	427.1	431.8	434.0	437.7	442.3
170°	416.6	415.0	415.8	418.2	419.9	422.3	426.4	430.5	432.1	434.5	437.7
172.5°	419.2	418.2	417.8	420.2	421.2	423.0	425.7	428.5	429.5	430.6	433.3
175°	422.3	421.5	420.7	422.3	422.3	423.1	424.8	426.4	425.6	426.4	427.2
177.5°	423.8	422.5	421.8	423.1	423.1	423.1	423.8	425.1	423.8	423.1	423.8
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1



TEST NUMBER: P331320-930

CATALOG NUMBER: SA2XXDIP-C485D925U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2
2.5°	630.6	631.6	632.7	633.2	632.9	632.7	632.5	632.3
5°	626.3	627.4	628.4	628.8	628.6	628.3	628.0	627.8
7.5°	619.2	620.3	621.4	621.7	621.5	621.2	620.9	620.6
10°	612.9	614.0	615.1	615.4	615.0	614.6	614.2	613.8
12.5°	605.4	606.2	606.9	607.2	606.8	606.6	606.3	605.9
15°	592.3	592.9	593.4	593.3	592.6	592.0	591.3	590.6
17.5°	576.7	577.4	578.0	578.0	577.3	576.7	576.1	575.4
20°	564.7	565.1	565.5	565.4	564.8	564.3	563.8	563.2
22.5°	551.8	551.9	552.0	551.9	551.5	551.2	550.9	550.6
25°	530.9	531.2	531.4	531.4	531.2	530.9	530.6	530.4
27.5°	510.3	509.9	509.5	509.0	508.3	507.7	507.0	506.4
30°	494.2	493.8	493.4	492.9	492.4	491.9	491.3	490.7
32.5°	478.5	477.8	477.0	476.4	475.8	475.3	474.7	474.2
35°	453.2	452.4	451.6	450.9	450.2	449.5	448.8	448.2
37.5°	427.9	426.9	425.9	425.0	424.4	423.7	423.1	422.5
40°	410.4	409.2	408.0	407.1	406.5	406.0	405.4	404.9
42.5°	393.1	391.8	390.4	389.5	388.7	387.9	387.2	386.4
45°	366.6	365.2	363.6	362.6	362.1	361.6	361.0	360.4
47.5°	339.1	337.5	335.9	334.8	333.9	333.2	332.4	331.6
50°	321.4	319.4	317.6	316.3	315.6	315.0	314.2	313.6
52.5°	303.0	301.4	299.9	298.6	297.7	296.9	296.0	295.1
55°	275.7	274.0	272.4	271.3	270.5	269.9	269.2	268.6
57.5°	247.2	245.6	244.0	243.0	242.4	241.9	241.4	240.8
60°	228.4	226.9	225.4	224.5	224.0	223.6	223.2	222.8
62.5°	210.6	209.2	207.8	206.9	206.4	205.9	205.4	204.8
65°	183.3	182.1	180.8	179.9	179.2	178.6	177.9	177.2
67.5°	156.3	155.3	154.4	153.7	153.1	152.5	152.1	151.5
70°	138.8	137.8	136.9	136.2	135.6	135.0	134.5	134.0
72.5°	122.2	121.2	120.3	119.6	119.2	118.7	118.3	117.9
75°	96.4	95.6	94.8	94.5	94.8	95.1	95.3	95.6
77.5°	73.4	73.0	72.6	72.2	71.7	71.4	71.0	70.6
80°	58.2	57.8	57.5	57.1	56.8	56.6	56.3	56.0
82.5°	43.5	42.9	42.4	42.1	42.1	42.0	41.9	41.9
85°	22.9	22.5	22.1	21.9	21.7	21.6	21.4	21.3
87.5°	11.4	10.8	10.8	10.7	10.6	10.4	10.4	10.3
90°	26.0	24.4	26.0	26.8	26.8	26.8	26.8	26.8
92.5°	70.9	60.9	54.1	49.0	48.3	45.7	46.4	45.1
95°	213.2	163.5	129.4	111.5	100.9	94.4	92.0	92.8
97.5°	497.5	407.0	318.9	260.2	221.4	201.3	189.4	182.6
100°	742.9	642.0	530.5	432.1	364.5	329.5	306.0	291.3
102.5°	903.7	880.9	799.4	695.0	621.7	561.9	532.5	512.7
105°	988.6	1080.6	1091.2	1064.3	1013.8	963.4	928.4	917.0
107.5°	927.5	1065.9	1150.6	1189.9	1196.3	1193.5	1186.5	1171.4
110°	874.7	1020.3	1124.5	1191.2	1226.2	1241.7	1249.0	1248.2



TEST NUMBER: P331320-930

CATALOG NUMBER: SA2XXDIP-C485D925U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	826.6	966.4	1077.7	1154.1	1202.8	1228.7	1242.5	1246.9
115°	767.3	892.6	999.2	1083.0	1140.8	1178.2	1199.4	1206.7
117.5°	722.7	832.7	929.4	1008.0	1066.9	1106.4	1128.8	1134.9
120°	700.6	801.5	887.7	961.8	1018.7	1057.0	1080.6	1088.8
122.5°	683.0	775.4	857.1	924.1	975.1	1012.7	1033.7	1040.6
125°	657.5	741.3	812.9	873.9	921.1	952.0	972.3	978.8
127.5°	632.3	708.1	775.6	831.9	873.1	902.0	919.7	924.9
130°	616.0	685.9	750.2	804.0	843.8	871.5	887.7	894.2
132.5°	600.3	665.1	724.1	774.6	813.8	841.6	856.5	862.3
135°	578.5	632.3	685.9	731.5	766.5	793.4	808.0	811.2
137.5°	561.1	606.0	648.7	688.4	720.3	743.4	756.3	761.2
140°	550.1	589.1	626.6	662.3	688.4	709.6	721.8	726.6
142.5°	541.0	574.1	606.3	636.3	661.0	680.3	691.1	692.1
145°	528.1	555.0	580.2	603.7	623.3	637.2	645.2	647.7
147.5°	518.1	539.3	559.0	576.3	592.4	603.4	608.9	610.4
150°	511.0	528.9	546.0	560.6	572.8	582.6	587.5	588.3
152.5°	503.9	520.4	534.9	547.6	557.2	565.7	569.2	569.4
155°	493.9	507.0	519.1	528.1	537.0	542.7	546.0	544.4
157.5°	482.3	493.3	503.5	510.5	516.8	521.5	523.0	523.0
160°	475.2	484.1	493.1	498.8	504.5	508.6	509.4	509.4
162.5°	468.1	475.6	483.3	487.7	493.4	496.2	497.0	496.4
165°	457.3	463.0	468.7	472.0	475.2	478.4	478.4	477.6
167.5°	447.0	451.4	455.3	458.3	459.7	461.5	461.4	460.4
170°	441.8	444.3	447.5	449.1	450.0	452.4	451.6	450.0
172.5°	435.9	437.7	440.3	441.3	442.1	443.3	442.5	441.5
175°	429.7	430.5	431.3	432.1	432.1	432.9	432.1	430.5
177.5°	425.1	425.1	425.7	425.7	425.7	425.7	425.1	423.8
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1

(END OF REPORT)